



lifeAGLOW®

HINKLEY

L I G H T I N G

HINKLEY

L I G H T I N G

THIS SUPPLEMENT INCLUDES NEW PRODUCTS AND LINE
ADDITIONS FOR INTERIOR, BATH AND OUTDOOR LIGHTING.
FOR LANDSCAPE LIGHTING, SEE HINKLEYLIGHTING.COM.

FREDRICK RAMOND

FOR ADDITIONAL INTERIOR STYLES, SEE
THE FULL LINE FREDRICK RAMOND CATALOG.

TABLE OF CONTENTS

Explore lighting that merges luxury and simplicity to enhance the enjoyment and functionality of any space.

WHAT'S YOUR #hinkleystyle?

Follow @hinkleylighting for the latest in lighting, style, décor and more!



INTERIOR COLLECTIONS

BILLIE	S023
CLANCY	S028
CLARENDON	S008
COLBIN	S032
EVERETT	S012
FULHAM	S027
FULTON	S030
LOWELL	S031
MIDTOWN	S017
NASH	S024
REFINERY	S026
STINSON	S004
SURREY	S018
TINSLEY	S006
WARBY	S022

BATH COLLECTIONS

ALTO	S048
BRANSON	S044
CLANCY	S040
FRITZ	S038
KARLIE	S037
LAUREL	S037
PLANTATION	S037
PORTIA	S036
RIXON	S042
SISLEY	S047
THISTLEDOWN	S046

OUTDOOR COLLECTIONS

ALFORD PLACE	S066
ARCADIA	S072
ATWATER	S056
DREXLER	S063
FINLEY	S064
HAMILTON	S062
JAYMES	S070
REFINERY	S074
REPUBLIC	S053
RHODES	S058
ROOK	S075
ROWLEY	S060

ICON DESCRIPTIONS



ADA COMPLIANT

Indicates fixtures that adhere to the standards and guidelines listed by the Americans with Disabilities Act.



INVISI-MOUNT

Indicates fixtures where the mounting hardware is hidden on the back plate.



LED

Fixtures supplied with fully integrated LEDs and drivers or specifically matched LED lamps based on performance and application.



OPEN AIR

Indicates fixtures that are appropriate and rated for both interior and exterior applications.



OVAL-SHAPED FIXTURE

Indicates chandeliers that are oval in shape.

FINISH CODES AND NAMES

AC	AGED COPPER BRONZE	KZ	BUCKEYE BRONZE
AH	ASH BRONZE	LS	LIGHT ANTIQUE BRASS
AN	ANTIQUENICKEL	LZ	LIGHT OILED BRONZE
AR	ANCHOR BRONZE	MB	MUSEUM BLACK
BB	BURNISHED BRASS	OR	OILED BRONZE
BK	BLACK	OZ	OIL RUBBED BRONZE
BN	BRUSHED NICKEL	PL	POLISHED ANTIQUENICKEL
BR	BRUSHED BRONZE	PN	POLISHED NICKEL
BZ	BRONZE	SI	SATIN NICKEL
CM	CHROME	SK	SATIN BLACK
DS	DARK ANTIQUE BRASS	SL	SILVER LEAF
DZ	AGED ZINC	TT	TITANIUM
HB	HERITAGE BRASS	WB	WARM BRONZE
HR	HEIRLOOM BRASS		



house warming

EVOKE FEELINGS OF SERENITY AND CALMNESS WITH NATURE-INSPIRED STYLE

Layer your look by pairing minimalist lighting with earthy textures and rustic design elements like wood, rope and shells to create fresh, modern living spaces that feel both cozy and chic.

ABOVE: THE WARBY PENDANT | 3747PL, PAGE S022
OPPOSITE PAGE: THE SOMERSET PENDANT | HINKLEYLIGHTING.COM

INTERIOR COLLECTIONS



BILLIE	S023	COLBIN	S032	FULTON	S030	NASH	S024	SURREY	S018
CLANCY	S028	EVERETT	S012	LOWELL	S031	REFINERY	S026	TINSLEY	S006
CLARENDON	S008	FULHAM	S027	MIDTOWN	S017	STINSON	S004	WARBY	S022

STINSON™

FINISH BLACK WITH
POLISHED NICKEL

For a classic statement-maker, Stinson hits the mark. A robust open and airy cage, designed for maximum impact in a bold Black and Polished Nickel finish, is accompanied by refined sparkling crystal accents to create the perfect mix of traditional appeal and industrial panache.



3536 BK
18" W, 27¼" H



3533 BK
13" W, 13½" H



3535 BK
16" W, 23" H



3534 BK
34" W, 25" H

ITEM	MAXIMUM WATTAGE	DEPTH	CANOPY	WIRE/CHAIN
3533 BK	4-60w Cand.		6" Square	
3534 BK	8-60w Cand.	16"	4½" W, 18" L	6', 5'
3535 BK	4-60w Cand.		6" Square	6', 5'
3536 BK	4-60w Cand.		6" Square	6', 5'

TINSLEY™

FINISH SILVER LEAF

Sleek and sophisticated, Tinsley gracefully blends updated traditional elements with Art Deco flair. These artfully crafted designs impart a soft yet dramatic statement in a luxurious Silver Leaf finish.



3106 SL
22" W, 28" H



3104 SL
13½" W, 28" H



3107 SL
7¼" W, 10½" H
42¾" MAX. H*



3102 SL
7¼" W, 17¼" H



3108 SL
16" W, 40¾" H



3105 SL
42" W, 22¾" H

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED
3102 SL	2-100w Med.		7¼"	8¾"	6¾" W, 17" H Back Plate		
3104 SL	4-60w Cand.				5¼" Square Canopy	10', 5'	
3105 SL	5-60w Cand.	12"			4¾" W, 12" L Canopy	10', 5'	
3106 SL	6-60w Cand.				5¼" Square Canopy	10', 5'	
3107 SL	1-100w Med.				5¼" Square Canopy	10' Wire	1-6", 2-12"
3108 SL	8-100w Med.				5¼" Square Canopy	12', 10'	

*Maximum achievable height with stems included. Additional 12" stems available, FR84312SLF3. 3012 SL and 3107 SL shown with G30 bulbs. 3108 SL shown with G40 bulbs. Ideal for vintage filament bulbs (not included).

CLARENDON™

FINISH AGED ZINC
WITH ANTIQUE NICKEL
GLASS CLEAR

Clarendon is a classic four sided foyer lantern group designed in an elegant two tone finish and constructed in forged iron with cast ball details and clear glass panels. Clarendon is updated tradition at its finest.

ADDITIONAL FINISHES

Bronze with Heirloom Brass (HR)



3419 DZ
30" W, 65" H



3415 DZ
12" W, 26½" H



3414 DZ
16" W, 33¾" H



3413 DZ
8" W, 18¼" H



3416 DZ
36" W, 15" H
48¾" MAX. H*



3418 DZ
20" W, 44" H

ITEM	MAXIMUM WATTAGE	DEPTH	CANOPY	WIRE/CHAIN	STEMS INCLUDED
3413 DZ	3-60w Cand.		5" Square	12', 10'	
3414 DZ	6-60w Cand.		5" Square	12', 10'	
3415 DZ	4-60w Cand.		5" Square	12', 10'	
3416 DZ	5-60w Cand.	12"	4½" W, 9" L	10' Wire	2-6", 4-12"
3418 DZ	8-60w Cand.		9" Square	12', 10'	
3419 DZ**	12-60w Cand.		9" Square	12', 10'	

*Maximum achievable height with stems included. Additional 12" stems available, 6065 AN. **3419 DZ is an open frame fixture without glass.

CLARENDON™

FINISH BRONZE WITH
HEIRLOOM BRASS
GLASS CLEAR

Clarendon is a classic four sided foyer lantern group designed in an elegant two tone finish and constructed in forged iron with cast ball details and clear glass panels. Clarendon is updated tradition at its finest.

ADDITIONAL FINISHES

Aged Zinc with Antique Nickel (DZ)



3419 BZ
30" W, 65" H



3415 BZ
12" W, 26½" H



3414 BZ
16" W, 33¾" H



3413 BZ
8" W, 18¼" H



3416 BZ
36" W, 15" H
48¾" MAX. H*



3418 BZ
20" W, 44" H

ITEM	MAXIMUM WATTAGE	DEPTH	CANOPY	WIRE/CHAIN	STEMS INCLUDED
3413 BZ	3-60w Cand.		5" Square	12', 10'	
3414 BZ	6-60w Cand.		5" Square	12', 10'	
3415 BZ	4-60w Cand.		5" Square	12', 10'	
3416 BZ	5-60w Cand.	12"	4½" W, 9" L	10' Wire	2-6", 4-12"
3418 BZ	8-60w Cand.		9" Square	12', 10'	
3419 BZ**	12-60w Cand.		9" Square	12', 10'	

*Maximum achievable height with stems included. Additional 12" stems available, 6065 LB. **3419 BZ is an open frame fixture without glass.

EVERETT™

FINISH BRONZE WITH
HERITAGE BRASS

The striking hammered plates are a distinctive focal point in Everett's design. Amplifying its unique look is the rich two-tone finish, imparting a refined elegance to this modern yet rustic chandelier. The use of vintage filament bulbs is recommended.

ADDITIONAL FINISHES
Brushed Nickel (BN)



4398 BZ
32" DIA., 24" H
58¼" MAX. H*



4395 BZ
24½" DIA., 22" H
56¼" MAX. H*



4390 BZ
5" W, 8¼" H



4396 BZ
48¼" W, 24½" H
59¼" MAX. H*



ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
4390 BZ	1-100w Med.		3¾"	4¼"	5" W, 8¼" H Back Plate		
4395 BZ	6-100w Med.				6" Dia. Canopy	10'	1-6", 2-12"
4396 BZ	12-75w Med.	17½"			9" W, 6" L Canopy	10'	2-6", 4-12"
4398 BZ	9-100w Med.				6" Dia. Canopy	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6037 BZ. Vintage filament bulbs not included.

EVERETT™

FINISH BRUSHED NICKEL


The striking hammered plates are a distinctive focal point in Everett's design. Amplifying its unique look is the rich two-tone finish, imparting a refined elegance to this modern yet rustic chandelier. The use of vintage filament bulbs is recommended.

ADDITIONAL FINISHES

Bronze with Heritage Brass (BZ)



4398 BN
32" DIA., 24" H
58¼" MAX. H*



4395 BN
24½" DIA., 22" H
56¼" MAX. H*



4390 BN
5" W, 8¼" H



4396 BN
48¼" W, 24½" H
59¼" MAX. H*



ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
4390 BN	1-100w Med.		3¾"	4¼"	5" W, 8¼" H Back Plate		
4395 BN	6-100w Med.				6" Dia. Canopy	10'	1-6", 2-12"
4396 BN	12-75w Med.	17½"			9" W, 6" L Canopy	10'	2-6", 4-12"
4398 BN	9-100w Med.				6" Dia. Canopy	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6037 BN. Vintage filament bulbs not included.



Midtown's clean, transitional style is both refined and bold. Strong design elements and rich finish options reflect its robust construction, while elegant glass shades add sophistication.

FINISH OIL RUBBED BRONZE
WITH HERITAGE BRASS
GLASS CLEAR

MIDTOWN™

ADDITIONAL FINISHES
Brushed Nickel (BN)



4975 OZ
24" DIA., 22¼" H



4970 OZ
5" W, 9¾" H



4978 OZ
32" DIA., 29" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
4970 OZ	1-100w Med.	6¼"	5¾"	5" W, 8" H Back Plate	
4975 OZ	5-100w Med.			6" Dia. Canopy	6', 5'
4978 OZ	9-100w Med.			6" Dia. Canopy	12', 10'

Ideal for vintage filament bulbs (not included).

SURREY™

FINISH OILED BRONZE
SHADE WHITE LINEN

Surrey combines traditional elegance and dazzling crystal details into a fresh, streamlined silhouette. Slim, tapered arms in Oiled Bronze with faceted crystal bobeches surround a striking oblong center. Optional white fabric shades add a discreet layer of glamour.

ADDITIONAL FINISHES
Polished Nickel (PN)



4009 OR
30¼" DIA., 35" H
31¼" DIA. (with shades)



4006 OR
28" DIA., 32" H
(shown with optional shades)



4005 OR
24" DIA., 31¾" H



4000 SH
5¾" DIA., 6" H
(optional shade)



4006 OR
26½" DIA., 32" H



4002 OR
11¾" W, 15¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
4000 SH	Do not exceed 40w				
4002 OR	2-60w Cand.	6"	13¼"	4½" Square Back Plate	
4005 OR	5-60w Cand.			6" Dia. Canopy	12', 10'
4006 OR	6-60w Cand.			6" Dia. Canopy	12', 10'
4009 OR	9-60w Cand.			6" Dia. Canopy	12', 10'

SURREY™

FINISH POLISHED NICKEL
SHADE WHITE LINEN

Surrey combines traditional elegance and dazzling crystal details into a fresh, streamlined silhouette. Slim, tapered arms in Polished Nickel with faceted crystal bobeches surround a striking oblong center. Optional white fabric shades add a discreet layer of glamour.

ADDITIONAL FINISHES
Oiled Bronze (OR)



4009 PN
30¼" DIA., 35" H
31¾" DIA. (with shades)



4006 PN
28" DIA., 32" H
(shown with optional shades)



4005 PN
24" DIA., 31¾" H



4000 SH
5¾" DIA., 6" H
(optional shade)



4006 PN
26½" DIA., 32" H




4002 PN
11¾" W, 15¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
4000 SH	Do not exceed 40w				
4002 PN	2-60w Cand.	6"	13¼"	4½" Square Back Plate	
4005 PN	5-60w Cand.			6" Dia. Canopy	12', 10'
4006 PN	6-60w Cand.			6" Dia. Canopy	12', 10'
4009 PN	9-60w Cand.			6" Dia. Canopy	12', 10'

WARBY™

FINISH AGED ZINC WITH HERITAGE BRASS, HERITAGE BRASS, LIGHT OILED BRONZE, POLISHED ANTIQUE NICKEL
GLASS CLEAR

Everything goes with Warby. Combining the best of vintage classic and mid-century modern elements, this clean and minimal pendant adds a unique blend of warmth and freshness into any space. Perfect combined with vintage filament bulbs.



3747 DZ
 9½" DIA., 10¾" H
 43¾" MAX. H*



3747 HB
 9½" DIA., 10¾" H
 43¾" MAX. H*



3747 LZ
 9½" DIA., 10¾" H
 43¾" MAX. H*



3747 PL
 9½" DIA., 10¾" H
 43¾" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3747 DZ	1-100w Med.	5" Dia.	10'	1-6", 2-12"
3747 HB	1-100w Med.	5" Dia.	10'	1-6", 2-12"
3747 LZ	1-100w Med.	5" Dia.	10'	1-6", 2-12"
3747 PL	1-100w Med.	5" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6037 DZ, HB, LZ and 4312 PL. Vintage filament bulbs not included.

Billie brings a breath of fresh air to industrial farmhouse style. From the cast strap detail and distinct rivets to the vintage-infused Hinkley medallion and subtle up-light glow, Billie's smart silhouette provides a bold statement in any room.

FINISH BRUSHED NICKEL,
OIL RUBBED BRONZE

BILLIE™



4047 BN
15" DIA., 9" H
41¾" MAX. H*



4047 OZ
15" DIA., 9" H
41¾" MAX. H*



Billie fixtures have a diffused downlight.

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
4047 BN	1-100w Med.	6" Dia.	10'	1-6", 2-12"
4047 OZ	1-100w Med.	6" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 BN and 6037 OZ.

NASH™

FINISH ANTIQUE NICKEL,
HEIRLOOM BRASS
SHADE CERAMIC

Fresh and welcoming, Nash merges sculptural and functional features with coastal inspiration. Hand-painted stripes and contrasting tipping complete the thrown ceramic shade. Combined with a thick jute rope, the details of Nash bring organic warmth and texture to any space.



3364 AN
10" DIA., 21¾" H



3364 AN-GR
10" DIA., 21¾" H



3364 HR-NV
10" DIA., 21¾" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN
3364 AN	1-100w Med.	5" Dia.	10', 5'
3364 AN-GR	1-100w Med.	5" Dia.	10', 5'
3364 HR-NV	1-100w Med.	5" Dia.	10', 5'



"I like an entryway that is bright and welcoming with plenty of light. By adding layers of lighting — a pendant above with a lamp on a console table, you are able to adjust throughout the day to ensure your home always appears warm and inviting."



BECKI OWENS
BECKIOWENS.COM
SOUTHERN CALIFORNIA

ABOVE: THE NASH PENDANT | 3364AN-GR, PAGE S024

REFINERY™

FINISH BRUSHED NICKEL
GLASS CLEAR, SMOKED

Refinery is a chic interpretation of modern-industrial design. A variety of stylish glass and finish options ensure this pared down style can seamlessly add a dash of retro-modern charm to any space.

ADDITIONAL FINISHES
Black (BK), Chrome (CM)



63306 BN-CL
43¾" W, 11¼" H
56" MAX. H*

63306 BN-SM
43¾" W, 11¼" H
56" MAX. H*

ITEM	MAXIMUM WATTAGE	DEPTH	CANOPY	WIRE	STEMS INCLUDED
63306 BN-CL	6-100w Med.	8¼"	4¾" W, 18½" L	10'	4-6", 6-12"
63306 BN-SM	6-100w Med.	8¼"	4¾" W, 18½" L	10'	4-6", 6-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6034 BN. Ideal for vintage filament bulbs (not included).

Fulham's bold design highlights clear beveled glass lenses that punctuate the minimalist elegance with an industrial edge. Its sleek lines combine with cast sockets and mid-century elements for a dynamic transitional style.

FINISH BUCKEYE BRONZE
 WITH HERITAGE BRASS,
 POLISHED ANTIQUE NICKEL
 GLASS CLEAR BEVELED

FULHAM™



3926 PL
 42" W, 12¾" H
 44¾" MAX. H*



3926 KZ
 42" W, 12¾" H
 44¾" MAX. H*

ITEM	MAXIMUM WATTAGE	DEPTH	CANOPY	WIRE	STEMS INCLUDED
3926 KZ	4-100w Med.	9"	4" W, 9" L	10'	2-6", 4-12"
3926 PL	4-100w Med.	9"	4" W, 9" L	10'	2-6", 4-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 PL and 6037 HB. Ideal for vintage filament bulbs (not included).

CLANCY™

FINISH AGED ZINC, BRUSHED NICKEL,
BUCKEYE BRONZE, HERITAGE BRASS,
POLISHED NICKEL
GLASS CLEAR

Clancy's transitional design features a clear glass urn, retro decorative construction elements and soft curves for an elegant style with vintage overtones.



3030 HB
6" W, 11¼" H



3030 BN
6" W, 11¼" H



3030 PN
6" W, 11¼" H



3030 KZ
6" W, 11¼" H



3030 DZ
6" W, 11¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
3030 BN	1-100w Med.	6½"	5"	5" Dia.
3030 DZ	1-100w Med.	6½"	5"	5" Dia.
3030 HB	1-100w Med.	6½"	5"	5" Dia.
3030 KZ	1-100w Med.	6½"	5"	5" Dia.
3030 PN	1-100w Med.	6½"	5"	5" Dia.


Ideal for vintage filament bulbs (not included).



FULTON™

FINISH AGED ZINC WITH ANTIQUE
NICKEL, BRONZE WITH HEIRLOOM
BRASS

Fulton's minimalist beauty emphasizes 'less is more' with vintage industrial style. This clean, airy tapered cage design is constructed without glass.



3331 BZ
18" W, 7¼" H



3331 DZ
18" W, 7¼" H

ITEM	MAXIMUM WATTAGE	CANOPY
3331 BZ	4-60w Med.	13¾" Dia.
3331 DZ	4-60w Med.	13¾" Dia.

Ideal for vintage filament bulbs (not included).

Lowell is a transitional design with clean lines and a subtle mid-century modern overtone. Robust cast L-bracket details combine with a twist lock system to maintain a sleek appearance that fits any décor.

FINISH ANTIQUE NICKEL,
BRUSHED BRONZE, CHROME
GLASS ETCHED OPAL

LOWELL™



3243 AN
16" DIA., 4¾" H



3243 CM
16" DIA., 4¾" H



3243 BR
16" DIA., 4¾" H



3241 AN
13¼" DIA., 4¾" H



3241 CM
13¼" DIA., 4¾" H



3241 BR
13¼" DIA., 4¾" H

ITEM	MAXIMUM WATTAGE	CANOPY
3241 AN, BR, CM	2-60w Med.	13" Dia.
3243 AN, BR, CM	3-60w Med.	15¾" Dia.

COLBIN™

FINISH AGED ZINC, BRUSHED NICKEL,
HERITAGE BRASS, OIL RUBBED BRONZE
GLASS ETCHED OPAL

Colbin is sleek, chic and poised. Its etched opal glass and decorative knurled knobs enhance a design that easily crosses style boundaries, from traditional to modern.



3233 HB
16½" DIA., 5¾" H



3233 OZ
16½" DIA., 5¾" H



3233 BN
16½" DIA., 5¾" H



3233 DZ
16½" DIA., 5¾" H



3231 HB
12½" DIA., 5¼" H



3231 OZ
12½" DIA., 5¼" H



3231 BN
12½" DIA., 5¼" H



3231 DZ
12½" DIA., 5¼" H



3230 HB
7" DIA., 3¼" H



3230 OZ
7" DIA., 3¼" H




3230 BN
7" DIA., 3¼" H



3230 DZ
7" DIA., 3¼" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	CANOPY
		3230 BN, DZ, HB, OZ	16w LED	950	2700K	96	1-100w	6" Dia.
3231 BN, DZ, HB, OZ	2-60w Med.							11" Dia.
3233 BN, DZ, HB, OZ	3-60w Med.							14¾" Dia.



MARIE FLANIGAN
MARIE FLANIGAN INTERIORS
HOUSTON, TX

“Channel your inner mix-master and free yourself from the rules you always listened to growing up. Have fun mixing metals and finishes, and playing with scale and color.”

ABOVE: THE RIGBY BATH BAR | 5293AN, HINKLEYLIGHTING.COM
OPPOSITE PAGE: THE LATITUDE SCONCE | 5651OZ, HINKLEYLIGHTING.COM

BATH COLLECTIONS



ALTO	S048	FRITZ	S038	PLANTATION	S037	SISLEY	S047
BRANSON	S044	KARLIE	S037	PORTIA	S036	THISTLEDOWN	S046
CLANCY	S040	LAUREL	S037	RIXON	S042		

NEW EXTENDED SIZE VANITY LIGHTING FOR EVERY STYLE

IT'S A LONG STORY

As bathrooms continue to gain square footage, the trend is impacting the design and functionality of this essential area.

Luxe vanities have become elongated to accommodate chic, narrow vessel sinks and extra-long tubs encourage spa-like soaks. In these situations, invest in lighting that is up to the task of illuminating larger areas. Look for extended bath bars that deliver the appropriate light output across a broader spectrum.


FOR FULL FAMILY OPTIONS, REFER TO HINKLEYLIGHTING.COM.

PORTIA

FINISH BRUSHED NICKEL (BN), POLISHED NICKEL (PN)
GLASS ETCHED OPAL



52113 PN
24½" W, 4¾" H



52113 BN
24½" W, 4¾" H



52113 PN
24½" W, 3" H
(shown without junction box cover plate)



52113 BN
24½" W, 3" H
(shown without junction box cover plate)



LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE	INV
52113 BN	21w LED	1800	2700K	90	1-75w	3¾"**, 4"	1½, 2½"***	6" W, 3" H*	•
52113 PN	21w LED	1800	2700K	90	1-75w	3¾"**, 4"	1½, 2½"***	6" W, 3" H*	•

*Back plate height is 4¾" when mounted with optional junction box cover plate. **Extension when mounted without optional junction box cover plate. ***Top to outlet when mounted with optional junction box cover plate. For complete product details and LED specifications, refer to hinkleylighting.com.

LAUREL

FINISH BRUSHED NICKEL (BN), POLISHED NICKEL (PN)
GLASS ETCHED OPAL



57555 BN
 35¾" W, 8" H



57555 PN
 35¾" W, 8" H

KARLIE

FINISH BRUSHED NICKEL (BN), CHROME (CM)
GLASS ETCHED OPAL



54625 CM
 35½" W, 7½" H



54625 BN
 35½" W, 7½" H

PLANTATION

FINISH BURNISHED BRASS (BB), POLISHED ANTIQUE NICKEL (PL)
GLASS CLEAR OPTIC



5315 PL
 37" W, 8¼" H



5315 BB
 37" W, 8¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5315 BB	5-100w Med.	6¾"	4¾"	12" W, 5" H	
5315 PL	5-100w Med.	6¾"	4¾"	12" W, 5" H	
54625 BN	5-100w Incan. or 5-17w LED Med.	6"	5½"	7¼" W, 4½" H	•
54625 CM	5-100w Incan. or 5-17w LED Med.	6"	5½"	7¼" W, 7½" H	•
57555 BN	5-100w Incan. or 5-17w LED Med.	5"	5½"	6¾" W, 5" H	
57555 PN	5-100w Incan. or 5-17w LED Med.	5"	5½"	6¾" W, 5" H	

Fixtures can be mounted facing up or down.

FRITZ™

FINISH BRUSHED NICKEL
GLASS CLEAR

Charming and classic, Fritz embraces a simplicity that is anything but basic. Industrial design elements are balanced with sturdy cast details and gleaming, refined finishes for a timeless silhouette.

ADDITIONAL FINISHES
Chrome (CM)



5032 BN
14½" W, 11¾" H



5030 BN
5" W, 11¾" H



5033 BN
24" W, 11¾" H



5034 BN
33¾" W, 11¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5030 BN	1-100w Med.	6½"	2½"	5" Dia.	•
5032 BN	2-100w Med.	6½"	2½"	5" Dia.	•
5033 BN	3-100w Med.	6½"	2½"	5" Dia.	•
5034 BN	4-100w Med.	6½"	2½"	5" Dia.	•

Ideal for vintage filament bulbs (not included).

Charming and classic, Fritz embraces a simplicity that is anything but basic. Industrial design elements are balanced with sturdy cast details and gleaming, refined finishes for a timeless silhouette.

FINISH CHROME
GLASS CLEAR

FRITZ™

ADDITIONAL FINISHES
Brushed Nickel (BN)



5032 CM
14½" W, 11¾" H



5033 CM
24" W, 11¾" H



5030 CM
5" W, 11¾" H



5034 CM
33¾" W, 11¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5030 CM	1-100w Med.	6½"	2½"	5" Dia.	•
5032 CM	2-100w Med.	6½"	2½"	5" Dia.	•
5033 CM	3-100w Med.	6½"	2½"	5" Dia.	•
5034 CM	4-100w Med.	6½"	2½"	5" Dia.	•

Ideal for vintage filament bulbs (not included).

CLANCY™

FINISH BRUSHED NICKEL
GLASS CLEAR

Clancy's transitional design features a glass urn, retro decorative construction elements and soft curves for an elegant style with vintage overtones.



5442 BN-CL
16" W, 8¼" H



3030 BN
6" W, 11¼" H



5443 BN-CL
25" W, 8¼" H



5444 BN-CL
32¾" W, 8¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
3030 BN	1-100w Med.	6½"	5"	5" Dia.
5442 BN-CL	2-100w Med.	6½"	5"	7" W, 5" H
5443 BN-CL	3-100w Med.	6½"	5"	9" W, 5" H
5444 BN-CL	4-100w Med.	6½"	5"	9" W, 5" H

Clancy's transitional design features a glass urn, retro decorative construction elements and soft curves for an elegant style with vintage overtones.

FINISH BRUSHED NICKEL
GLASS ETCHED OPAL

CLANCY™



5442 BN
16" W, 8¼" H



5443 BN
25" W, 8¼" H



5440 BN
6" W, 11¼" H



5444 BN
32¾" W, 8¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5440 BN	1-100w Incan. or 1-17w LED Med.	6½"	6¼"	5" Dia.
5442 BN	2-100w Incan. or 2-17w LED Med.	6½"	5"	7" W, 5" H
5443 BN	3-100w Incan. or 3-17w LED Med.	6½"	5"	9" W, 5" H
5444 BN	4-100w Incan. or 4-17w LED Med.	6½"	5"	9" W, 5" H

RIXON™

FINISH CHROME
GLASS CLEAR OUTER,
ETCHED OPAL INNER

Spanning a variety of styles, Rixon adds a unique flair to any bathroom space. Uniting industrial, mid-century modern and traditional elements, Rixon boldly merges elegant double-glass shades, decorative knobs and robust cast arms for a sleek, stylish statement.

ADDITIONAL FINISHES

Heritage Brass (HB)



5492 CM
5492 CM-LL
14½" W, 7" H



5490 CM
5490 CM-LL
5½" W, 7" H



5493 CM
5493 CM-LL
24" W, 7" H



5494 CM
5494 CM-LL
33¾" W, 7" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5490 CM	1-60w G9*	5490 CM-LL	1-4.5w G9 LED**	6¼"	2¾"	5½" Dia.	•
5492 CM	2-60w G9*	5492 CM-LL	2-4.5w G9 LED**	6¼"	2¾"	5½" Dia.	•
5493 CM	3-60w G9*	5493 CM-LL	3-4.5w G9 LED**	6¼"	2¾"	5½" Dia.	•
5494 CM	4-60w G9*	5494 CM-LL	4-4.5w G9 LED**	6¼"	2¾"	5½" Dia.	•

*G9 halogen bulbs included. **G9 LED bulb included. For complete product details and LED specifications, refer to hinkleylighting.com.

Spanning a variety of styles, Rixon adds a unique flair to any bathroom space. Uniting industrial, mid-century modern and traditional elements, Rixon boldly merges elegant double-glass shades, decorative knobs and robust cast arms for a sleek, stylish statement.

FINISH HERITAGE BRASS
GLASS CLEAR OUTER,
ETCHED OPAL INNER

RIXON™

ADDITIONAL FINISHES
Chrome (CM)



5492 HB
5492 HB-LL
14½" W, 7" H



5493 HB
5493 HB-LL
24" W, 7" H



5490 HB
5490 HB-LL
5½" W, 7" H



5494 HB
5494 HB-LL
33¾" W, 7" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5490 HB	1-60w G9*	5490 HB-LL	1-4.5w G9 LED**	6¼"	2¾"	5½" Dia.	•
5492 HB	2-60w G9*	5492 HB-LL	2-4.5w G9 LED**	6¼"	2¾"	5½" Dia.	•
5493 HB	3-60w G9*	5493 HB-LL	3-4.5w G9 LED**	6¼"	2¾"	5½" Dia.	•
5494 HB	4-60w G9*	5494 HB-LL	4-4.5w G9 LED**	6¼"	2¾"	5½" Dia.	•

*G9 halogen bulbs included. **G9 LED bulb included. For complete product details and LED specifications, refer to hinkleylighting.com.

BRANSON™

FINISH BRUSHED NICKEL
GLASS CLEAR

Branson features a strong, minimalist profile with subtle mid-century modern and industrial overtones, letting the clean tapered glass and cast decorative knobs remain a focal point. Designed for maximum flexibility, Branson can be mounted up or down.

ADDITIONAL FINISHES

Chrome (CM)



5402 BN
14½" W, 7¼" H



5400 BN
8½" W, 7¼" H



5403 BN
24¼" W, 7¼" H



5404 BN
34" W, 7¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5400 BN	1-100w Med.	6¾"	5"	8½" W, 4¾" H	•
5402 BN	2-100w Med.	6¾"	5"	8½" W, 4¾" H	•
5403 BN	3-100w Med.	6¾"	5"	8½" W, 4¾" H	•
5404 BN	4-100w Med.	6¾"	5"	8½" W, 4¾" H	•

Branson features a strong, minimalist profile with subtle mid-century modern and industrial overtones, letting the clean tapered glass and cast decorative knobs remain a focal point. Designed for maximum flexibility, Branson can be mounted up or down.

FINISH CHROME
GLASS CLEAR

BRANSON™

ADDITIONAL FINISHES
Brushed Nickel (BN)



5402 CM
14½" W, 7¼" H



5403 CM
24¼" W, 7¼" H



5400 CM
8½" W, 7¼" H



5404 CM
34" W, 7¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5400 CM	1-100w Med.	6¾"	5"	8½" W, 4¾" H	•
5402 CM	2-100w Med.	6¾"	5"	8½" W, 4¾" H	•
5403 CM	3-100w Med.	6¾"	5"	8½" W, 4¾" H	•
5404 CM	4-100w Med.	6¾"	5"	8½" W, 4¾" H	•

THISTLEDOWN™

FINISH BUCKEYE BRONZE
GLASS CLEAR SEEDY

Thisistledown is an updated traditional design with smooth, flowing lines and a practical elegance that adds sophistication to any space.

ADDITIONAL FINISHES

Brushed Nickel (BN), Polished Nickel (PN)



51802 KZ
16" W, 10¼" H



51800 KZ
5¼" W, 10½" H



51803 KZ
24" W, 10½" H



51804 KZ
30" W, 10¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
51800 KZ	1-100w Med.	6¼"	7"	5" W, 7" H
51802 KZ	2-100w Med.	6¼"	8"	7" W, 5" H
51803 KZ	3-100w Med.	6¼"	8"	7" W, 5" H
51804 KZ	4-100w Med.	6¼"	8"	9" W, 5" H

Sisley perfects sophisticated spa lighting. Merging the best of contemporary and classic features, Sisley produces an exceptional light pattern that matches its striking appearance.

FINISH POLISHED NICKEL
GLASS OPAL

SISLEY™

exclusively available in
HIGH-PERFORMANCE LED 



52102 PN
14½" W, 5" H



52103 PN
22" W, 5" H



52100 PN
7" W, 5" H



52104 PN
29¾" W, 5" H




LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE	INV
52100 PN	7w LED	600	2700K	97	1-60w	3¼"	2½"	7" W, 5" H	•
52102 PN	14w LED	1200	2700K	97	2-60w	3¼"	2½"	14½" W, 5" H	•
52103 PN	21w LED	1800	2700K	97	3-60w	3¼"	2½"	22" W, 5" H	•
52104 PN	28w LED	2400	2700K	97	4-60w	3¼"	2½"	29¾" W, 5" H	•

For complete product details and LED specifications, refer to hinkleylighting.com.

ALTO™



FINISH BRUSHED NICKEL
GLASS ETCHED WHITE
ACRYLIC

Sleek and chic, the LED, ADA-compliant Alto effortlessly takes center stage. Mastering both form and function, Alto unifies energy-efficiency, durability and sophistication.



 exclusively available in
HIGH-PERFORMANCE LED

ADDITIONAL FINISHES
Chrome (CM)





51402 BN
18" W, 4¾" H
 






51403 BN
24" W, 4¾" H
 



51404 BN
30" W, 4¾" H
(mounted vertically)
 



51404 BN
30" W, 4¾" H
 

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE	
51402 BN	26w LED	2000	3000K	95	3-60w	3"	2½"	4¾" Square	•
51403 BN	29w LED	2400	3000K	95	4-60w	3"	2½"	4¾" Square	•
51404 BN	44w LED	3200	3000K	95	5-60w	3"	2½"	4¾" Square	•

Allto fixtures are dimmable. For complete product details and LED specifications, refer to hinkleylighting.com.

Sleek and chic, the LED, ADA-compliant Alto effortlessly takes center stage. Mastering both form and function, Alto unifies energy-efficiency, durability and sophistication.


FINISH CHROME
GLASS ETCHED WHITE
ACRYLIC

ALTO™



exclusively available in
HIGH-PERFORMANCE LED 

ADDITIONAL FINISHES
Brushed Nickel (BN)





51404 CM
30" W, 4¾" H
(mounted vertically)
 






51402 CM
18" W, 4¾" H
 



51403 CM
24" W, 4¾" H
 



51404 CM
30" W, 4¾" H
 

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE	
51402 CM	26w LED	2000	3000K	95	3-60w	3"	2½"	4¾" Square	•
51403 CM	29w LED	2400	3000K	95	4-60w	3"	2½"	4¾" Square	•
51404 CM	44w LED	3200	3000K	95	5-60w	3"	2½"	4¾" Square	•

Alto fixtures are dimmable. For complete product details and LED specifications, refer to hinkleylighting.com.



LISA MCDENNON
LISAMCDENNONDESIGN.COM
LAGUNA BEACH, CA

“Lighting needs to have personality and should emulate a signature style, whether it stands alone or is integrated into the design of a space.”

ABOVE: THE PORTER LANTERN | 2805DZ, HINKLEYLIGHTING.COM
OPPOSITE PAGE: THE ALFORD PLACE LANTERN | 2568MB, PAGE S066

OUTDOOR COLLECTIONS



ALFORD PLACE	S066	DREXLER	S063	JAYMES	S070	RHODES	S058
ARCADIA	S072	FINLEY	S064	REFINERY	S074	ROOK	S075
ATWATER	S056	HAMILTON	S062	REPUBLIC	S053	ROWLEY	S060

NEW

COASTAL ELEMENTS™ collection

OUTDOOR ENVIRONMENTS WERE NOT CREATED EQUAL



REPUBLIC
SATIN NICKEL FINISH



REPUBLIC
OIL RUBBED BRONZE FINISH



ATWATER
ASH BRONZE FINISH

The Coastal Elements™ collection from Hinkley Lighting was developed to mitigate the effects of harsh environmental conditions that are often present in coastal regions.

- CONSTRUCTED OF DURABLE COMPOSITE MATERIALS AND COATED WITH ANTI-FADING FINISH
- SPECIFICALLY DESIGNED TO COMBAT ATMOSPHERIC SALT, HIGH LEVELS OF UV EXPOSURE AND TEMPERATURE EXTREMES
- HIGHLY RESISTANT TO RUST AND CORROSION
- COMPOSITE MATERIAL IS RoHS COMPLIANT
- 5-YEAR FINISH WARRANTY

FOR FULL WARRANTY INFORMATION, VISIT HINKLEYLIGHTING.COM

Republic's striking double frame design, constructed from a composite material and treated with an anti-fading agent for maximum durability, is at home on the coast or a country lodge. The Oil Rubbed Bronze and Satin Nickel high performance finishes feature a 5 year warranty and are resistant to rust and corrosion. Vintage filament bulbs are recommended to complete a stylish look.

FINISH OIL RUBBED
BRONZE
GLASS CLEAR SEEDY

REPUBLIC™

COASTAL ELEMENTS™
collection

IDEAL FOR HARSH CLIMATES, THESE VERSATILE
DESIGNS OFFER MAXIMUM DURABILITY.

ADDITIONAL FINISHES
Satin Nickel (SI)



1002 OZ
7" W, 16¾" H



1004 OZ
7" W, 16" H



1000 OZ
7" W, 12" H



1007 OZ
8" W, 16½" H



1005 OZ
7" W, 20" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1000 OZ	1-100w Med.	6¾"	4¾"	5" W, 6½" H Back Plate	
1002 OZ	1-100w Med.			5¼" Dia. Canopy	6', 5'
1004 OZ	1-100w Med.	6¾"	4¾"	5" W, 6½" H Back Plate	
1005 OZ	1-100w Med.	6¾"	4¾"	5" W, 6½" H Back Plate	
1007 OZ	1-100w Med.			8" Square Base	

Vintage filament bulbs not included.

REPUBLIC™

FINISH SATIN NICKEL
GLASS CLEAR SEEDY

Republic's striking double frame design, constructed from a composite material and treated with an anti-fading agent for maximum durability, is at home on the coast or a country lodge. The Oil Rubbed Bronze and Satin Nickel high performance finishes feature a 5 year warranty and are resistant to rust and corrosion. Vintage filament bulbs are recommended to complete a stylish look.

COASTAL ELEMENTS™ collection

IDEAL FOR HARSH CLIMATES, THESE VERSATILE
DESIGNS OFFER MAXIMUM DURABILITY.

ADDITIONAL FINISHES
Oil Rubbed Bronze (OZ)



1005 SI
7" W, 20" H



1002 SI
7" W, 16¾" H



1000 SI
7" W, 12" H



1007 SI
8" W, 16½" H



1004 SI
7" W, 16" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1000 SI	1-100w Med.	6¾"	4¾"	5" W, 6½" H Back Plate	
1002 SI	1-100w Med.			5¼" Dia. Canopy	6', 5'
1004 SI	1-100w Med.	6¾"	4¾"	5" W, 6½" H Back Plate	
1005 SI	1-100w Med.	6¾"	4¾"	5" W, 6½" H Back Plate	
1007 SI	1-100w Med.			8" Square Base	

Vintage filament bulbs not included.

ATWATER™

FINISH ASH BRONZE
GLASS CLEAR SEEDY

Classic and elegant, Atwater offers beauty and endurance. Constructed from a composite material and treated with an anti-fading agent, the updated coastal design incorporates elegant brass accents, handle, and an inner glass that creates a faux candle effect. The Ash Bronze high performance finish is resistant to rust and corrosion with a 5 year warranty.

COASTAL ELEMENTS™ collection

IDEAL FOR HARSH CLIMATES, THESE VERSATILE
DESIGNS OFFER MAXIMUM DURABILITY.



1165 AH
9½" W, 20½" H



1162 AH
9½" W, 21½" H



1164 AH
8¼" W, 17½" H



1160 AH
6½" W, 14" H



1167 AH
9½" W, 21½" H



1161 AH
9½" W, 23" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1160 AH	1-100w Med.	7"	8¾"	5" W, 9¾" H Back Plate	
1161 AH	1-100w Med.			3" Dia. Post Fitter	
1162 AH	1-100w Med.			5¼" Dia. Canopy	6', 5'
1164 AH	1-100w Med.	8¾"	10¾"	6¾" W, 12" H Back Plate	
1165 AH	1-100w Med.	10¼"	12½"	6¾" W, 12" H Back Plate	
1167 AH	1-100w Med.			9½" Square Base	

Ideal for vintage filament bulbs (not included). For posts and pier mounts, refer to hinkleylighting.com.

RHODES™

FINISH WARM BRONZE
GLASS CLEAR SEEDY

Rhodes exudes warmth and a handsome appeal with a clean transitional design and generous proportions. Perfectly suited for either exterior or interior spaces, the Warm Bronze finish and clear seedy glass perfectly complement the robust framework. Vintage-inspired filament bulbs are recommended to complement these designs.

 **OPEN AIR**
collection

CHIC DESIGNS RATED FOR USE IN BOTH
INTERIOR AND EXTERIOR SPACES



29304 WB
18¼" W, 28¼" H



29307 WB
7¼" W, 10½" H
42½" MAX. H*



29300 WB
7¼" W, 12½" H



29302 WB
7¼" W, 16¾" H



29306 WB
42¼" W, 21¼" H

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED
29300 WB	1-100w Med.		7"	6¼"	6¾" W, 12¼" H Back Plate		
29302 WB	1-100w Med.		7"	8½"	6¾" W, 16¾" H Back Plate		
29304 WB	4-60w Cand.				5¼" Square Canopy	10', 5'	
29306 WB	6-100w Med.	12"			4¾" W, 12" L Canopy	10', 5'	
29307 WB	1-100w Med.				5¼" Square Canopy	10' Wire	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6033 WB. Vintage filament bulbs not included.

ROWLEY™

FINISH LIGHT ANTIQUE BRASS
GLASS CLEAR

A stunning, rounded silhouette and arched roof composed of solid brass make Rowley a design standout. Weaving elements of classic Americana and industrial flair into a chic design with timeless appeal, this style features generous panes of clear glass and a functional front door for ease of lamping. Pair with vintage filament bulbs to highlight the luxe Light Antique Brass finish.

Heritage
COLLECTION

TIMELESS LANTERN DESIGNS THAT
PAY TRIBUTE TO THE NOSTALGIA OF
AMERICA'S PAST.



2524 LS
8¼" W, 18" H



2525 LS
9½" W, 21" H



2520 LS
6" W, 13¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
2520 LS	1-75w Med.	5"	6¾"	5" W, 8¼" H
2524 LS	2-60w Cand.	5"	9¾"	5" W, 9¼" H
2525 LS	3-60w Cand.	5"	11¾"	5" W, 10¼" H

Vintage filament bulbs not included.



HAMILTON™

FINISH DARK ANTIQUE BRASS
GLASS CLEAR

Hamilton's sleek profile, constructed of solid brass, blends classic early American style with industrial influence. Quality and artistry is at the core of this design, with the pocket lantern featuring prominent rivets and a functional door in its gleaming, authentic Dark Antique Brass finish.

Heritage
COLLECTION

TIMELESS LANTERN DESIGNS THAT
PAY TRIBUTE TO THE NOSTALGIA OF
AMERICA'S PAST.



2000 DS
7¼" W, 10½" H



2005 DS
8½" W, 18¼" H



2004 DS
7¼" W, 14¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
2000 DS	2-60w Cand.	5"	5½"	6" W, 9" H
2004 DS	2-60w Cand.	5"	7¼"	6" W, 13" H
2005 DS	2-60w Cand.	5"	9¼"	7¼" W, 16¾" H

Ideal for vintage filament bulbs (not included).

A new take on nautical, the transitional design of Drexler offers a fresh interpretation of coastal appeal. The highlight of the design is a unique framed outer cage in a versatile Oil Rubbed Bronze with Heritage Brass accents.

FINISH OIL RUBBED BRONZE
WITH HERITAGE BRASS
GLASS CLEAR SEEDY

DREXLER™



1172 OZ
9½" W, 17¼" H
50¼" MAX. H*



1170 OZ
6¼" W, 13" H



1174 OZ
8½" W, 17" H



1175 OZ
9½" W, 18¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
1170 OZ	1-100w Med.	7"	3¾"	4½" W, 7¼" H Back Plate		
1172 OZ	1-100w Med.			6" Dia. Canopy	10'	1-6", 2-12"
1174 OZ	1-100w Med.	8¾"	4"	4¾" W, 8" H Back Plate		
1175 OZ	1-100w Med.	10"	4"	4¾" W, 8" H Back Plate		

*Maximum achievable height with stems included. Additional 12" stems available, 6034OZOD. Ideal for vintage filament bulbs (not included).

FINLEY™

FINISH AGED ZINC,
OIL RUBBED BRONZE
GLASS CLEAR

Finley's modest composition makes a vintage statement with an austere, clean design. The classic shape is accentuated by clear glass and matching bottom trim ring for an authentic look.



2515 OZ
10" W, 18¼" H



2515 DZ
10" W, 18¼" H



2510 OZ
6" W, 11¾" H



2514 OZ
8" W, 14¾" H



2514 DZ
8" W, 14¾" H



2510 DZ
6" W, 11¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
2510 DZ	1-100w Med.	7½"	3¾"	5" Dia.
2510 OZ	1-100w Med.	7½"	3¾"	5" Dia.
2514 DZ	1-100w Med.	9¼"	4¾"	4½" W, 8" H
2514 OZ	1-100w Med.	9¼"	4¾"	4½" W, 8" H
2515 DZ	1-100w Med.	10"	5¾"	4½" W, 8" H
2515 OZ	1-100w Med.	10"	5¾"	4½" W, 8" H

Ideal for vintage filament bulbs (not included).

ALFORD PLACE™

FINISH MUSEUM BLACK
GLASS CLEAR

The clean and classic design of Alford Place features a precision die-cast frame, hanging arm and top loop, paired with a sealed glass roof, providing excellent illumination from all sides.

ADDITIONAL FINISHES
Oil Rubbed Bronze (OZ)



2568 MB
14" W, 24" H



2562 MB
12" W, 19½" H



2565 MB
12" W, 20½" H



2560 MB
8" W, 14" H



2564 MB
10" W, 17½" H



2561 MB
10" W, 20¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2560 MB	2-60w Cand.	9"	7"	4¾" W, 6¾" H Back Plate	
2561 MB	2-60w Cand.			3" Dia. Post Fitter	
2562 MB	3-60w Cand.			5" Square Canopy	6', 5'
2564 MB	2-60w Cand.	11¼"	8¼"	4¾" W, 6¾" H Back Plate	
2565 MB	3-60w Cand.	13½"	9½"	5½" W, 8¼" H Back Plate	
2568 MB	4-60w Cand.	15½"	10¾"	5½" W, 8¼" H Back Plate	

For posts and pier mounts, refer to hinkleylighting.com.

ALFORD PLACE™

FINISH OIL RUBBED BRONZE
GLASS CLEAR

The clean and classic design of Alford Place features a precision die-cast frame, hanging arm and top loop, paired with a sealed glass roof, providing excellent illumination from all sides.

ADDITIONAL FINISHES
Museum Black (MB)



2568 OZ
14" W, 24" H



2562 OZ
12" W, 19½" H



2565 OZ
12" W, 20½" H



2560 OZ
8" W, 14" H



2564 OZ
10" W, 17½" H



2561 OZ
10" W, 20¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2560 OZ	2-60w Cand.	9"	7"	4¾" W, 6¾" H Back Plate	
2561 OZ	2-60w Cand.			3" Dia. Post Fitter	
2562 OZ	3-60w Cand.			5" Square Canopy	6', 5'
2564 OZ	2-60w Cand.	11¼"	8¼"	4¾" W, 6¾" H Back Plate	
2565 OZ	3-60w Cand.	13½"	9½"	5½" W, 8¼" H Back Plate	
2568 OZ	4-60w Cand.	15½"	10¾"	5½" W, 8¼" H Back Plate	

For posts and pier mounts, refer to hinkleylighting.com.

JAYMES™

FINISH OIL RUBBED BRONZE
GLASS CLEAR

Jaymes features an updated traditional silhouette in an Oil Rubbed Bronze finish that is both modern and elegant. Constructed of die-cast aluminum, the rivet details, cast finials and sweeping roof signify a new classic in lantern design. Ideal for vintage filament bulbs for a timeless appearance.



1295 OZ
9¼" W, 24" H



1292 OZ
9¼" W, 26¼" H



1294 OZ
7¾" W, 19½" H



1290 OZ
6½" W, 15¾" H



1291 OZ
7¾" W, 22¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1290 OZ	1-100w Med.	8"	7½"	4½" W, 7" H Back Plate	
1291 OZ	1-100w Med.			3" Dia. Post Fitter	
1292 OZ	3-60w Cand.			5" Square Canopy	6', 5'
1294 OZ	1-100w Med.	9½"	8"	4½" W, 7" H Back Plate	
1295 OZ	3-60w Cand.	11"	10¾"	4½" W, 11½" H Back Plate	

Vintage filament bulbs not included. For posts and pier mounts, refer to hinkleylighting.com.

ARCADIA™

FINISH AGED COPPER BRONZE
GLASS CLEAR

Arcadia smartly transforms a classic carriage lantern into fresh, transitional design with bold features complemented by striking tapered glass. Constructed of durable aluminum in an Aged Copper Bronze finish, Arcadia is a statement-making style that will instantly enhance any exterior. Ideal for vintage filament bulbs.



1135 AC
8¾" W, 18½" H



1132 AC
6¾" W, 15½" H



1134 AC
6¾" W, 14¼" H



1130 AC
5¾" W, 12" H



1131 AC
6¾" W, 19" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1130 AC	1-100w Med.	6¼"	6¾"	5" W, 6" H Back Plate	
1131 AC	1-100w Med.			3" Dia. Post Fitter	
1132 AC	1-100w Med.			4½" Square Canopy	6', 5'
1134 AC	1-100w Med.	7¼"	7¾"	5½" W, 7¼" H Back Plate	
1135 AC	1-100w Med.	9¼"	10¼"	6¾" W, 9¼" H Back Plate	

Vintage filament bulbs not included. For posts and pier mounts, refer to hinkleylighting.com.

REFINERY™

FINISH BLACK,
OIL RUBBED BRONZE
GLASS CLEAR SEEDY

Refinery is a chic interpretation of modern industrial design. The pared down style confidently imparts a vibrant dash of retro charisma to any space.



2824 OZ
7¾" W, 12¾" H



2825 OZ
9½" W, 16¾" H



2825 BK
9½" W, 16¾" H



2824 BK
7¾" W, 12¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
2824 BK	1-100w Med.	9¼"	4"	4¾" W, 8" H
2824 OZ	1-100w Med.	9¼"	4"	4¾" W, 8" H
2825 BK	1-100w Med.	11"	4"	4¾" W, 8" H
2825 OZ	1-100w Med.	11"	4"	4¾" W, 8" H

Ideal for vintage filament bulbs (not included).

With a strong and imperial presence, Rook features clean, modern lines with a down light softly grazing the clear seedy glass. The bold Bronze, Titanium and Satin Black finish options accentuate its sturdy frame and aluminum construction.

FINISH SATIN BLACK
GLASS CLEAR SEEDY

ROOK™

ADDITIONAL FINISHES
Bronze (BZ), Titanium (TT)



1784 SK
1784 SK-LL
4¾" W, 12" H



1780 SK
1780 SK-LL
4¾" W, 9½" H



1788 SK
1788 SK-LL
5¾" W, 20" H



1785 SK
1785 SK-LL
4¾" W, 15" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
1780 SK	1-50w GU10*	1780 SK-LL	1-6.5w GU10 LED**	5½"	2½"	4¾" Square
1784 SK	1-50w GU10*	1784 SK-LL	1-6.5w GU10 LED**	5½"	2½"	4¾" Square
1785 SK	1-50w GU10*	1785 SK-LL	1-6.5w GU10 LED**	5½"	2½"	4¾" Square
1788 SK	1-50w GU10*	1788 SK-LL	1-6.5w GU10 LED**	6½"	2½"	5¾" W, 4¾" H

*GU10 bulb included. **GU10 LED bulb included. For full product details and LED specifications, refer to hinkleylighting.com.

ROOK™

FINISH BRONZE
GLASS CLEAR SEEDY


With a strong and imperial presence, Rook features clean, modern lines with a down light softly grazing the clear seedy glass. The bold Bronze, Titanium and Satin Black finish options accentuate its sturdy frame and aluminum construction.

ADDITIONAL FINISHES


Satin Black (SK), Titanium (TT)



1785 BZ
1785 BZ-LL
4¾" W, 15" H



1780 BZ
1780 BZ-LL
4¾" W, 9½" H



1784 BZ
1784 BZ-LL
4¾" W, 12" H



1788 BZ
1788 BZ-LL
5¾" W, 20" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
1780 BZ	1-50w GU10*	1780 BZ-LL	1-6.5w GU10 LED**	5½"	2½"	4¾" Square
1784 BZ	1-50w GU10*	1784 BZ-LL	1-6.5w GU10 LED**	5½"	2½"	4¾" Square
1785 BZ	1-50w GU10*	1785 BZ-LL	1-6.5w GU10 LED**	5½"	2½"	4¾" Square
1788 BZ	1-50w GU10*	1788 BZ-LL	1-6.5w GU10 LED**	6½"	2½"	5¾" W, 4¾" H

*GU10 bulb included. **GU10 LED bulb included. For full product details and LED specifications, refer to hinkleylighting.com.

With a strong and imperial presence, Rook features clean, modern lines with a down light softly grazing the clear seedy glass. The bold Bronze, Titanium and Satin Black finish options accentuate its sturdy frame and aluminum construction.

FINISH TITANIUM
GLASS CLEAR SEEDY

ROOK™

ADDITIONAL FINISHES
Bronze (BZ), Titanium (TT)



1784 TT
1784 TT-LL
4¾" W, 12" H



1780 TT
1780 TT-LL
4¾" W, 9½" H



1788 TT
1788 TT-LL
5¾" W, 20" H



1785 TT
1785 TT-LL
4¾" W, 15" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
1780 TT	1-50w GU10*	1780 TT-LL	1-6.5w GU10 LED**	5½"	2½"	4¾" Square
1784 TT	1-50w GU10*	1784 TT-LL	1-6.5w GU10 LED**	5½"	2½"	4¾" Square
1785 TT	1-50w GU10*	1785 TT-LL	1-6.5w GU10 LED**	5½"	2½"	4¾" Square
1788 TT	1-50w GU10*	1788 TT-LL	1-6.5w GU10 LED**	6½"	2½"	5¾" W, 4¾" H

*GU10 bulb included. **GU10 LED bulb included. For full product details and LED specifications, refer to hinkleylighting.com.

INDEX

1000OZ	S053	2000DS	S062	3107SL	S007	3747HB	S022	51802KZ	S046
1000SI	S055	2004DS	S062	3108SL	S007	3747LZ	S022	51803KZ	S046
1002OZ	S053	2005DS	S062	3230BN	S033	3747PL	S022	51804KZ	S046
1002SI	S055	2510DZ	S065	3230DZ	S033	3926KZ	S027	52100PN	S047
1004OZ	S053	2510OZ	S065	3230HB	S033	3926PL	S027	52102PN	S047
1004SI	S055	2514DZ	S065	3230OZ	S033	4000SH	S019	52103PN	S047
1005OZ	S053	2514OZ	S065	3231BN	S033	4002OR	S019	52104PN	S047
1005SI	S054	2515DZ	S064	3231DZ	S033	4002PN	S021	52113BN	S036
1007OZ	S053	2515OZ	S064	3231HB	S033	4005OR	S019	52113CM	S036
1007SI	S055	2520LS	S060	3231OZ	S033	4005PN	S021	52113PN	S036
1130AC	S073	2524LS	S060	3233BN	S032	4006OR	S019	5315BB	S037
1131AC	S073	2525LS	S060	3233DZ	S032	4006PN	S021	5315PL	S037
1132AC	S073	2560MB	S067	3233HB	S032	4009OR	S018	5400BN	S044
1134AC	S073	2560OZ	S069	3233OZ	S032	4009PN	S020	5400CM	S045
1135AC	S072	2561MB	S067	3241AN	S031	4047BN	S023	5402BN	S044
1160AH	S057	2561OZ	S069	3241BR	S031	4047OZ	S023	5402CM	S045
1161AH	S057	2562MB	S067	3241CM	S031	4390BN	S015	5403BN	S044
1162AH	S057	2562OZ	S069	3243AN	S031	4390BZ	S013	5403CM	S045
1164AH	S057	2564MB	S067	3243BR	S031	4395BN	S015	5404BN	S044
1165AH	S056	2564OZ	S069	3243CM	S031	4395BZ	S013	5404CM	S045
1167AH	S057	2565MB	S067	3331BZ	S030	4396BN	S015	5440BN	S041
1170OZ	S063	2565OZ	S069	3331DZ	S030	4396BZ	S013	5442BN	S041
1172OZ	S063	2568MB	S066	3364AN	S024	4398BN	S014	5442BN-CL	S040
1174OZ	S063	2568OZ	S068	3364AN-GR	S024	4398BZ	S012	5443BN	S041
1175OZ	S063	2824BK	S074	3364HR-NV	S024	4970OZ	S017	5443BN-CL	S040
1290OZ	S071	2824OZ	S074	3413BZ	S011	4975OZ	S017	5444BN	S041
1291OZ	S071	2825BK	S074	3413DZ	S009	4979OZ	S017	5444BN-CL	S040
1292OZ	S071	2825OZ	S074	3414BZ	S011	5030BN	S038	54625BN	S037
1294OZ	S071	29300WB	S059	3414DZ	S009	5030CM	S039	54625CM	S037
1295OZ	S070	29302WB	S059	3415BZ	S011	5032BN	S038	5490CM	S042
1780BZ	S076	29304WB	S058	3415DZ	S009	5032CM	S039	5490HB	S043
1780SK	S075	29306WB	S059	3416BZ	S011	5033BN	S038	5492CM	S042
1780TT	S077	29307WB	S059	3416DZ	S009	5033CM	S039	5492HB	S043
1784BZ	S076	3030BN	S028	3418BZ	S011	5034BN	S038	5493CM	S042
1784SK	S075	3030DZ	S028	3418DZ	S009	5034CM	S039	5493HB	S043
1784TT	S077	3030HB	S028	3419BZ	S010	51402BN	S048	5494CM	S042
1785BZ	S076	3030KZ	S028	3419DZ	S008	51402CM	S049	5494HB	S043
1785SK	S075	3030PN	S028	3533BK	S005	51403BN	S048	57555BN	S037
1785TT	S077	3102SL	S007	3534BK	S005	51403CM	S049	57555PN	S037
1788BZ	S076	3104SL	S007	3535BK	S005	51404BN	S048	63306BN-CL	S026
1788SK	S075	3105SL	S007	3536BK	S004	51404CM	S049	63306BN-SM	S026
1788TT	S077	3106SL	S006	3747DZ	S022	51800KZ	S046		

We want you to enjoy your experience with Hinkley.

There is nothing complicated about it: we want to deliver a great product and treat you the way we'd like to be treated. So whether you are flipping through our catalog, surfing our site, getting inspired through social media, chatting with a member of our team or checking out our lighting in a retail shop—we want it to be time well-spent. Here's all you need to know:

PRODUCT CATALOGS

Hinkley catalogs feature our current and complete offering along with important product specs and detailed photography. A must for the print-loving researcher who likes to tab their favorites. Stop by your local showroom for your own copy.

HINKLEYLIGHTING.COM

Dive in! Our easy-to-use site makes your product research process a snap, with the added benefit of tips, trends, installation guidelines and a quick connection to our retail partners.

SOCIAL CLIMBERS

We don't mean to brag, but we are connected. Look for @hinkleylighting on:




REAL PEOPLE

Want to chat? Contact us at service@hinkleylighting.com or 1.800.HINKLEY.

Hinkley Lighting stands behind the quality of our lighting fixtures with product warranties that are among the strongest in the industry. For details of warranty coverage on specific products, please refer to hinkleylighting.com or consult a qualified Hinkley retail distributor.

Several Hinkley Lighting products are protected under U.S. Patent and foreign patent, or patent pending. For current information regarding Hinkley Lighting's patent portfolio, please visit hinkleylighting.com.

©2018 Hinkley Lighting, Inc. All rights reserved in all copyrightable works.



Hinkley Lighting is a proud partner of the American Lighting Association.

HINKLEY

L I G H T I N G

GLOBAL HEADQUARTERS

33000 Pin Oak Parkway | Avon Lake, Ohio 44012
T 440 653 5500 | F 440 653 5555 | hinkleylighting.com

SHOWROOM

Dallas Trade Mart 3210 | Dallas, Texas 75207



Connect with us | [#hinkleystyle](https://twitter.com/hinkleystyle)

SUPPLEMENT I : 2018 SUP118

