



MAXIM[®]
L I G H T I N G

June 2014 Supplement

TABLE OF CONTENTS

Arabesque	24
Axis	55
Balboa DC	99
Balboa EE	107
Calistoga EE	113
Castille EE	116
Contessa	31
Convert	119
Copenhagen	1
Corona	67
CounterMax MX-L120-EL	118
CounterMax MX-L120-LO	117
Diverse	122
Drops	19
Fairmont	27
Flask	49
Fusion	41
Hi-Bay	75
Horgen	3
Java	15
Jewel	37
Knoxville	91
Knoxville EE	115
Lightray	79
Lightray LED	82
Logan	63
Manhattan	21
Mini Hi-Bay	71
Moda	86
Mosaic	88
Nebula	77
Oakville EE	111
Orbit	25
Oslo EE	109
Profile EE	121
Radcliffe	95
Radcliffe EE	103
Ritz	35
Saki	5
Sienna	97
Sienna EE	105
Starfire	7
StarStrand LV Star	123
Stefan	59
Sync	45
Terrace	93
Terrace EE	101
Urban Nights	11
View EE	89
View LED	90
Weave	87
Wharf	92

For 45 years, Maxim Lighting has defined lifestyle lighting, offering a variety of high-quality, decorative fixtures for the home, including chandeliers, sconces, pendants, ceiling mounts, and bath vanities. Design inspiration from around the world characterizes our collections from the traditional to the unusual. Our exclusive products complement your distinct sense of style and add a touch of flair to every setting. Whether it's an elegant chandelier to complete your dining room or a set of beautiful pendants to enhance your kitchen, you're certain to discover just the right product at Maxim Lighting.



facebook.com/maximlighting



follow us @maximlighting

800.486.2946

maximlighting.com

LEGEND

CA California
T24 Title 24

 ADA Compliant

 Installs on Slope Ceiling

 Installs Up or Down

 LED

 LED Dimmer

 Dimmable



COPENHAGEN COLLECTION

The Copenhagen collection embraces hanging organic sculptures that are illuminated by LEDs that diffuse through slats of natural ash wood in curved forms and coated in a natural oil finish for durability and long lasting color. This eye-catching trend forerunner adds an exotic edge to any room from the foyer to family room.



27537UD

4-Light Pendant

Uddo

21"W x 41"H x 161"OAH

4 x 2.5W LED (Included)

700 Rated Lumens



COPENHAGEN COLLECTION

- 3000 K color temperature
- Dimmable in LED
- Slats of natural ash wood
- Natural oil finish allowing for a neutral color tone and long term protection



27536UD
3-Light Pendant
Uddo
14"W x 28"H x 148"OAH
3 x 2.5W LED (Included)
525 Rated Lumens



Close up of Ash wood

HORGEN COLLECTION

Contemporary forms of ash wood, finished with a natural Uddo oil, create sculptural lighting designs sure to become the focal point of the room. The downlights enhance the beauty of the wood, while creating a unique lighting effect.

27535UD

1-Light Pendant

Uddo

23.5"W x 12"H x 132"OAH

1 x 60W MB Bulb



HORGEN COLLECTION

- Slats of natural ash wood
- Natural oil finish allowing for a neutral color tone and long term protection



Close up of Ash wood



27533UD
1-Light Pendant
Uddo
14"W x 15"H x 135"OAH
1 x 60W MB Bulb
120°



SAKI COLLECTION

Geometric frames of wood finished in Uddo create forms inspired by Japanese contemporary design. Light mysteriously appears from high powered LED modules which are cleverly concealed within the frame.

SAKI COLLECTION

- Dimmable LED
- 3000 K color temperature
- Matching wood canopy
- Rayon cord



27525UD
1-Light Pendant
Uddo
21"W x 18"H x 150"OAH
1 x 10W LED (Included)




27524UD
1-Light Pendant
Uddo
17"W x 24"H x 155"OAH
1 x 10W LED (Included)



27527UD
1-Light Pendant
Uddo
23"W x 34"H x 165"OAH
1 x 15W LED (Included)






39747BCPC
40-Light Chandelier
Polished Chrome
44"W x 62"H x 100"OAH
40 x 35W G9Bulbs (Included)

STARFIRE COLLECTION

STARFIRE COLLECTION

Spectacular display of Beveled Crystal beads of various sizes which are mounted on sculptures Polished Chrome metal formations which will sure to be the focal point of your room. The high power Xenon bulbs add sparkle to the crystal while producing a natural whitelight.

- Various sized beveled crystal beads
- Polished Chrome formations
- Easy to assemble



(LED Option)
BUL-2.9W-G9-CL-12V
G9 LED Bulb
2.9W
Color Temperature: 3000 K
Total Rated Lumens: 189
Life Rated: 25,000 Hours
CRI: 75
Dimmable



39746BCPC
18-Light Chandelier
Polished Chrome
32"W x 43.75"H x 83"OAH
18 x 40W G9Bulbs (Included)

120°



Close up of Crystal

STARFIRE COLLECTION

- Various sized beveled crystal beads
- Polished Chrome formations
- Easy to assemble



(LED Option)

BUL-2.9W-G9-CL-12V

G9 LED Bulb

2.9W

Color Temperature: 3000 K

Total Rated Lumens: 189

Life Rated: 25,000 Hours

CRI: 75

Dimmable

LED



39745BCPC

11-Light Chandelier

Polished Chrome

22"W x 34.5"H x 72"OAH

11 x 40W G9Bulbs (Included)



STARFIRE COLLECTION



Close up of Crystal

39743BCPC
3-Light Wall Sconce
Polished Chrome
17"W x 10"H x 10"Ext.
3 x 40W G9Bulbs (Included)



39740BCPC
8-Light Flush Mount
Polished Chrome
22"W x 16.5"H
8 x 40W G9Bulbs (Included)

URBAN NIGHTS COLLECTION

Urban Nights is a chic collection in perfect sync with on-trend transitional styles. Each fixture fuses modern geometric forms with frosted glass cylinders, illuminated by Xenon bulbs to create a two-way light source. Underneath the frame, LED downlights provide the second source of light. Urban Nights is available in a linear or circular black metal base with luminous cylinders set at various heights for visual movement.



32468FTTXB

29-Light Chandelier
Textured Black

49.25"W x 18.5"H x 62"OAH

23 x 25W G9 Xenon Bulbs (Included)
+ 6 x 2.5W LED (Included)

- Includes Two 6" stems
- Includes Six 12" stems
- Additional stems available:
6" order - STR06206TXB
12" order - STR06212TXB



URBAN NIGHTS COLLECTION

- Fully Dimmable
- Xenon uplights and LED downlights
- 3000 K dimmable downlights
- Warm glow of Xenon uplights
- Varied-sized frosted glass



(LED Option)
BUL-2.9W-G9-CL-12V
G9 LED Bulb
2.9W
Color Temperature: 3000 K
Total Rated Lumens: 189
Life Rated: 25,000 Hours
CRI: 75
Dimmable



32467FTTXB
20-Light Chandelier
Textured Black
37.25"W x 18.5"H x 62"OAH
16 x 25W G9 Xenon Bulbs (Included)
+ 4 x 2.5W LED (Included)

- Includes Two 6" stems
- Includes Six 12" stems
- Additional stems available:
6" order - STR06206TXB
12" order - STR06212TXB



Close up of Glass

URBAN NIGHTS COLLECTION

- Fully Dimmable
- Xenon uplights and LED downlights
- 3000 K dimmable downlights
- Warm glw of Xenon uplights
- Varied-sized frosted glass



32466FTTXB

13-Light Chandelier
Textured Black

49"L x 7"W x 16"H x 60"OAH

10 x 25W G9 Xenon Bulbs (Included)

+ 3 x 2.5W LED (Included)

- Includes Two 6" stems
- Includes Six 12" stems
- Additional stems available:
6" order - STR06206TXB
12" order - STR06212TXB



URBAN NIGHTS COLLECTION



(LED Option)

BUL-2.9W-G9-CL-12V

G9 LED Bulb

2.9W

Color Temperature: 3000 K

Total Rated Lumens: 189

Life Rated: 25,000 Hours

CRI: 75

Dimmable



32464FTTXB

28-Light Chandelier

Textured Black

28.25"W x 21.25"H x 65.5"OAH

24 x 25W G9 Xenon Bulbs (Included)

+ 4 x 2.5W LED (Included)

- Includes One 6" stems
- Includes Three 12" stems
- Additional stems available:
6" order - STR06206TXB
12" order - STR06212TXB



JAVA COLLECTION

The Java collection meets the demand for handmade, unique objects, fueled by "The Made Movement" in home fashion that merges artisanal techniques with the raw beauty of recycled and repurposed materials. Each shade is handcrafted of recycled corrugated paper in a Java finish, with alternating opaque and translucent layers, through which beautiful light patterns are casted.



9106JVBK

1-Light Pendant
Black

17.75"W x 18"H x 138"OAH


1 x 60W MB Bulb



JAVA COLLECTION



- Java finished material
- Handmade shaded recycled corrugated paper
- Alternating layers allow for light to penetrate through sides of shades



Close up of Shade



9105JVBK

1-Light Pendant
Black

17"W x 9"H x 129"OAH
1 x 60W MB Bulb



JAVA COLLECTION

- Java finished material
- Handmade shaded recycled corrugated paper
- Alternating layers allow for light to penetrate through sides of shades



9103JVBK
1-Light Pendant
Black
9.75"W x 18.75"H x 138.75"OAH
1 x 60W MB Bulb



9104JVBK
1-Light Pendant
Black
10.5"W x 12"H x 132"OAH
1 x 60W MB Bulb





9101JVBK
1-Light Pendant
Black
13.75"W x 10.75"H x 130.75"OAH
1 x 60W MB Bulb
120°



9102JVBK
1-Light Pendant
Black
17.25"W x 14"H x 134"OAH
1 x 60W MB Bulb
120°

DROPS COLLECTION

The Drops collection doubles as kinetic art with hanging crystal teardrops descending from a chrome-plated grid of crystals and anchored by a Brushed Aluminum frame. The 20 Watt G4 Xenon bulbs give the crystal drops an ethereal glow, drawing the eye upwards. The Drops collection riffs on the roaring 20's with its Great Gatsby-esque art deco styling.



Close up of Crystal

30725CLAL
15-Light Chandelier
Brushed Aluminum
31.5"L x 15.75"W x 31.5"H x 128"OAH
15 x 20W G4 Bulbs (Included)
Crystal Included

DROPS COLLECTION

- Brushed Aluminum Frame
- Crystal drops suspended from a chrome plated grid
- Varying lengths of teardrop crystals
- 20W G4 Xenon included



30720CLAL
9-Light Flush Mount
Brushed Aluminum
17.5"W x 21.5"H
9 x 20W G4 Bulbs (Included)
Crystal Included



30724CLAL
9-Light Chandelier
Brushed Aluminum
17.5"W x 20"H x 126"OAH
9 x 20W G4 Bulbs (Included)
Crystal Included

MANHATTAN COLLECTION

Contrasting array of Beveled Crystal create an elegant contemporary style that integrates seamlessly into today's interior design. The Polished Chrome frame provides a touch of shimmer without competing with the brilliance of the crystal



(LED Option)

BUL-2.9W-G9-CL-12V

G9 LED Bulb

2.9W

Color Temperature: 3000 K


Total Rated Lumens: 189

Life Rated: 25,000 Hours

CRI: 75

Dimmable

LED



39785BCPC

8-Light Chandelier


Polished Chrome

39.75"L x 9.5"W x 4.75"H x 124.75"OAH

8 x 40W G9Bulbs (Included)

MANHATTAN COLLECTION

- Patterned glass diffuser
- Mixture of square and rectangular crystals



39781BCPC
8-Light Flush Mount
Polished Chrome
23.25"W x 5.5"H
8 x 40W G9Bulbs (Included)



39780BCPC
4-Light Flush Mount
Polished Chrome
15.25"W x 5.5"H
4 x 40W G9Bulbs (Included)



39782BCPC
1-Light Wall Sconce
Polished Chrome
6"W x 7"H x 3.5"Ext.
1 x 40W G9Bulb (Included)



39783BCPC
2-Light Wall Sconce
Polished Chrome
8.25"W x 9"H x 3.5"Ext.
2 x 40W G9Bulbs (Included)

MANHATTAN COLLECTION

- Patterned glass diffuser
- Mixture of square and rectangular crystals



39787BCPC
2-Light Bath Vanity
Polished Chrome
18"W x 4.5"H x 3.5"Ext.
2 x 40W G9Bulbs (Included)



39788BCPC
4-Light Bath Vanity
Polished Chrome
23.25"W x 4.5"H x 3.5"Ext.
4 x 40W G9Bulbs (Included)



39789BCPC
4-Light Bath Vanity
Polished Chrome
33"W x 4.5"H x 3.5"Ext.
4 x 40W G9Bulbs (Included)



LED

(LED Option)
BUL-2.9W-G9-CL-12V
G9 LED Bulb
2.9W
Color Temperature: 3000 K
Total Rated Lumens: 189
Life Rated: 25,000 Hours
CRI: 75
Dimmable

- Finished in silver and gold leaf
- Precision laser cut design
- Inner hanging crystals



(LED Option)

BUL-2.9W-G9-CL-12V

G9 LED Bulb

2.9W

Color Temperature: 3000 K

Total Rated Lumens: 189

Life Rated: 25,000 Hours

CRI: 75

Dimmable

LED

ARABESQUE COLLECTION

The Arabesque collection's intricate patterns are formed in metal and finished in Golden Silver. Strands of crystal beads add sparkle as they shimmer through the xenon lamps. Unique oval-shaped pendants add a touch of class to any room.



24159BCGS

13-Light Pendant

Golden Silver

30"W x 30"H x 74"OAH

13 x 40W G9 Bulbs (Included)

Crystal Included

- Includes One 6" stem
- Includes Three 12" stems
- Additional stems available:
6" stem - STR06206GS-A
12" stem - STR06212GS-A




• For additional items in this collection, see catalog LMXCAT1311, pg 127.

ORBIT COLLECTION

A spherical frame of metal surround a simple line chandelier draped in crystal for a transitional style that fits any interior design.

Orbit is available in 2 sizes and 2 finishes. Oil Rubbed Bronze with Cognac crystal and a combo finish of Anthracite and Polished Nickel with Clear crystal.



25145 OI, ARPN
9-Light Pendant
30"W x 33"H
9 x 60W CABulbs
Crystal Included

ORBIT COLLECTION

- Polished Chrome interior
- Clear crystal strands
- Anthracite finish exterior



25144 OI, ARPN
6-Light Pendant
25"W x 28"H
6 x 60W CABulbs
Crystal Included



25142 OI, ARPN
4-Light Pendant
19"W x 21.5"H
4 x 60W CABulbs
Crystal Included



25140 OI, ARPN
3-Light Pendant
12"W x 14"H
3 x 60W CABulbs
Crystal Included



FAIRMONT COLLECTION

Arched channels of metal finished in your choice of Natural Aged Brass or Polished Nickel, form this minimalistic approach to traditional lighting. Oatmeal fabric shades adorn the top of metal candle covers that give this collection a tailored look.

FAIRMONT COLLECTION



22379 OMNAB, WTPN

2-Light Wall Sconce
18"W x 13"H x 11"Ext.
2 x 60W CA Bulbs



22376 OMNAB, WTPN

6-Light Chandelier
41"L x 22"W x 32"H
6 x 40W CA Bulbs

FAIRMONT COLLECTION



22370 SWNAB, SWPN
2-Light Flush Mount
13"W x 4"H
2 x 60W MB Bulbs



22371 SWNAB, SWPN
3-Light Flush Mount
16"W x 5"H
3 x 40W MB Bulbs



22375 OMNAB, WTPN
6-Light Chandelier
30"W x 32"H
6 x 40W CA Bulbs

FAIRMONT COLLECTION



22372 NAB, PN
3-Light Pendant
16"W x 25"H
3 x 60W CABulbs



22373 NAB, PN
5-Light Pendant
22"W x 30 "H
5 x 60W CABulbs

CONTESSA COLLECTION

This transitional approach to a classic traditional style features rectangular tubing finished in our Natural Aged Brass. The Satin White cylindrical shades provide a soft diffused light while adding a contemporary flair to the design.



22419SWNAB
12-Light Chandelier
35"W x 28"H
12 x 40W CA Bulbs

CONTESSA COLLECTION

- Rectangular tubing
- Natural Aged Brass finish
- Soft diffused light



22418SWNAB
9-Light Chandelier
27"W x 24"H
9 x 40W CA Bulbs

CONTESSA COLLECTION

- Rectangular tubing
- Natural Aged Brass finish
- Soft diffused light



22416SWNAB
6-Light Chandelier
19"W x 23"H
6 x 40W CA Bulbs

CONTESSA COLLECTION



22411SWNAB
1-Light Wall Sconce
5"W x 10"H x 4"Ext.
1 x 40W CA Bulb



22413SWNAB
3-Light Bath Vanity
20.75"W x 10"H x 4"Ext.
3 x 40W CA Bulbs



22414SWNAB
4-Light Bath Vanity
28.75"W x 10"H x 4"Ext.
4 x 40W CA Bulbs



22415SWNAB
5-Light Bath Vanity
36.75"W x 10"H x 4"Ext.
5 x 40W CA Bulbs

RITZ COLLECTION

A collection of classic colonial design which features formed metal frames finished in a rich Natural Aged Brass. The Clear glass panels are framed in a contrast black which gives the designs dimension.



22396CLNAB
5-Light Chandelier
Natural Aged Brass
31.5"W x 25"H
5 x 60W CA Bulbs

RITZ COLLECTION

- Formed metal frames finished in Natural Aged Brass
- Clear glass panels with black frame



22392CLNAB
4-Light Semi-Flush Mount
Natural Aged Brass
22.5"W x 14.5"H
4 x 60W CA Bulbs



22395CLNAB
4-Light Chandelier
Natural Aged Brass
26"W x 22"H
4 x 60W CA Bulbs



22398CLNAB
4-Light Chandelier
Natural Aged Brass
21.75"W x 30"H
4 x 60W CA Bulbs



22393CLNAB
2-Light Wall Sconce
Natural Aged Brass
12"W x 16"H x 6.5"Ext.
2 x 60W CA Bulbs

JEWEL COLLECTION

This is not your grandmothers crystal! Crystal design is taken into another dimension with the Jewel collection formed of steel bent in a wavy pattern and finished in Polished Chrome. The large scale jewel Beveled Crystal pendants sparkles in the night like stars while the internal crystal beads delicately reflect the light from the xenon lamps included with each fixture.



JEWEL COLLECTION



39924BCPC
12-Light Pendant
Polished Chrome
18"W x 14"H x 135" OAH
12 x 25W G9 Bulbs (Included)

- Steel bent in a wavy pattern
- Beveled Crystals trip frame
- Internal Crystal beads



(LED Option)
BUL-2.9W-G9-CL-12V
G9 LED Bulb
2.9W
Color Temperature: 3000 K
Total Rated Lumens: 189
Life Rated: 25,000 Hours
CRI: 75
Dimmable

39926BCPC
19-Light Pendant
Polished Chrome
28"L x 11.5"W x 11"H x 132" OAH
19 x 25W G9 Bulbs (Included)



JEWEL COLLECTION

39925BCPC
20-Light Pendant
Polished Chrome
22"W x 14" H x 135" OAH
20 x 25W G9 Bulbs (Included)



(LED Option)
BUL-2.9W-G9-CL-12V
G9 LED Bulb
2.9W
Color Temperature: 3000 K
Total Rated Lumens: 189
Life Rated: 25,000 Hours
CRI: 75
Dimmable



Close up of Crystal

39929BCPC
24-Light Pendant
Polished Chrome
26"W x 17" H x 150" OAH
24 x 25W G9 Bulbs (Included)

JEWEL COLLECTION

- Steel bent in a wavy pattern
- Beveled Crystals trip frame
- Internal Crystal beads



39928BCPC
23-Light Flush Mount
Polished Chrome
36"L x 20"W x 13.5"H
23 x 25W G9 Bulbs (Included)




39923BCPC
22-Light Flush Mount
Polished Chrome
24"W x 15.5"H
22 x 25W G9 Bulbs (Included)



39920BCPC
12-Light Flush Mount
Polished Chrome
17.75"W x 14"H
12 x 25W G9 Bulbs (Included)

FUSION COLLECTION

The Fusion features a mixture of rustic metal frames finished in Anthracite and the high tech illumination of LED lighting which magically shine through cylinders of ultra thick Clear glass. This collection is fully dimmable and feature replaceable LEDs which are rated for 40,000 hours.



32456CLAR

8-Light Chandelier
Anthracite


32"L x 20"W x 12.5"H x 57"OAH
6 x 4.5W LED (Included)
2 x 2.8W Downlight (Included)

- Includes Two 6" stems
- Includes Six 12" stems
- Additional stems available:
6" order - STR06206AR
12" order - STR06212AR



FUSION COLLECTION

- Dimmable LED
- 3000 K color temperature
- Indirect LED up light
- Direct LED down light
- heavy weight hand blown glass
- Concealed LED source allows for playful design



32457CLAR

8-Light Chandelier
Anthracite

43"W x 12.5"H x 57"OAH

6 x 4.5W LED (Included)


2 x 2.8W Downlight (Included)

- Includes Two 6" stems
- Includes Six 12" stems
- Additional stems available:
6" order - STR06206AR
12" order - STR06212AR



FUSION COLLECTION


- Dimmable LED
- 3000 K color temperature
- Indirect LED up light
- Direct LED down light
- heavy weight hand blown glass
- Concealed LED source allows for playful design



92450CLAR

2-Light Mini Pendant
 Anthracite
 4"W x 14.5"H x 59"OAH
 1 x 2.4W LED (Included)
 1 x 2.4W Downlight (Included)

- Includes One 6" stems
- Includes Three 12" stems
- Additional stems available:
 6" order - STR04506AR
 12" order - STR04512AR



32455CLAR

5-Light Chandelier
 Anthracite
 16"W x 12.5"H x 57"OAH
 4 x 4.5W LED (Included)
 1 x 2.8W Downlight (Included)

- Includes One 6" stems
- Includes Three 12" stems
- Additional stems available:
 6" order - STR04506AR
 12" order - STR04512AR



Close up of Glass

FUSION COLLECTION



32451CLAR
2-Light Wall Sconce
Anthracite
4.5"W x 8.5"H x 6"Ext.
1 x 2.4W LED (Included)
1 x 2.4W Downlight (Included)



32453CLAR
6-Light Bath Vanity
Anthracite
18.75"W x 8.5"H x 6"Ext.
3 x 2.4W LED (Included)
3 x 2.4W Downlight (Included)



32454CLAR
8-Light Bath Vanity
Anthracite
25.5"W x 8.5"H x 6"Ext.
4 x 2.4W LED (Included)
4 x 2.4W Downlight (Included)



SYNC COLLECTION

Rods of bubble glass are encased inside a Clear glass cylinder which are supported in a cast Polished Chrome frame. Dual LED modules bring the bubble glass to life while also providing ample illumination to the surface below.



20909CLPC

16-Light Chandelier
Polished Chrome

32"W x 20.5"H x 66"OAH
16 x 2.4W LED (Included)

- Includes Two 6" stems
- Includes Six 12" stems
- Additional stems available:
6" order - STR06206PC
12" order - STR06212PC



SYNC COLLECTION



- Dimmable LED
- 3000 K color temperature
- Indirect LED up light
- Direct LED down light
- Clear outer glass with solid bubble glass interior



20907CLPC
12-Light Chandelier
Polished Chrome
27.25"W x 18"H x 63.5"OAH
12 x 2.4W LED (Included)

- Includes Two 6" stems
- Includes Six 12" stems
- Additional stems available:
6" order - STR06206PC
12" order - STR06212PC



SYNC COLLECTION

- Dimmable LED
- 3000 K color temperature
- Indirect LED up light
- Direct LED down light
- Clear outer glass with solid bubble glass interior



Close up image

20908CLPC

16-Light Chandelier
Polished Chrome
35.25"L x 11.5"W x 7"H x 165"OAH
16 x 2.4W LED (Included)

- Includes Two 6" stems
- Includes Six 12" stems
- Additional stems available:
6" order - STR06206PC
12" order - STR06212PC



SYNC COLLECTION



20901CLPC
2-Light Wall Sconce
Polished Chrome
5"W x 7.5"H x 5"Ext.
2 x 2.4W LED (Included)



20902CLPC
4-Light Bath Vanity
Polished Chrome
14"W x 7.5"H x 5"Ext.
4 x 2.4W LED (Included)



20903CLPC
6-Light Bath Vanity
Polished Chrome
21"W x 7.5"H x 5"Ext.
6 x 2.4W LED (Included)



20904CLPC
8-Light Bath Vanity
Polished Chrome
27"W x 7.5"H x 5"Ext.
8 x 2.4W LED (Included)



20906CLPC
12-Light Bath Vanity
Polished Chrome
40.5"W x 7.5"H x 5"Ext.
12 x 2.4W LED (Included)





FLASK COLLECTION

Heavy weight handblown Clear glass shades are cradled on a geometric metal frame of Polished Chrome. The glass comes to life when illuminated by dimmable LEDs which are cleverly concealed in the frame.

FLASK COLLECTION

- Dimmable LED
- 3000 K color temperature
- Hand blown glass shades



33006CLPC

8-Light Chandelier

Polished Chrome

31"W x 15"H x 58"OAH

8 x 2.8W LED (Included)

1568 Lumens

- Includes Two 6" stems
- Includes Six 12" stems
- Additional stems available:
6" order - STR06206PC
12" order - STR06212PC



FLASK COLLECTION

- Dimmable LED
- 3000 K color temperature
- Hand blown glass shades



LED



33008CLPC

8-Light Chandelier
Polished Chrome

42"L x 24"W x 15"H x 58"OAH

8 x 2.8W LED (Included)

1568 Lumens

- Includes Two 6" stems
- Includes Six 12" stems
- Additional stems available:
6" order - STR06206PC
12" order - STR06212PC



FLASK COLLECTION



33013CLPC

3-Light Chandelier
 24.5"L x 4.75"W x 7.5"H x 69"OAH
 3 x 2.8W LED (Included)
 588 Lumens



93000CLPC

1-Light Mini Pendant
 Polished Chrome
 4.5"W x 7"H x 51"OAH
 1 x 2.8W LED (Included)
 196 Lumens

- Includes One 6" stems
- Includes Three 12" stems
- Additional stems available:
 6" order - STR04506PC
 12" order - STR04512PC



FLASK COLLECTION

- Dimmable LED
- 3000 K color temperature
- Hand blown glass shades



33014CLPC
4-Light Chandelier
34.75"L x 4.75"W x 8.25"H x 69"OAH
4 x 2.8W LED (Included)
784 Lumens



FLASK COLLECTION



33000CLPC
 4-Light Flush Mount
 Polished Chrome
 16"W x 11.5"H
 4 x 2.8W LED (Included)
 784 Lumens



33001CLPC
 1-Light Wall Sconce
 Polished Chrome
 4.75"W x 7.5"H x 6.25"Ext.
 1 x 2.8W LED (Included)
 196 Lumens



33003CLPC
 3-Light Bath Vanity
 Polished Chrome
 18.75"W x 8"H x 7"Ext.
 3 x 2.8W LED (Included)
 588 Lumens



33004CLPC
 4-Light Bath Vanity
 Polished Chrome
 25.25"W x 8"H x 7"Ext.
 4 x 2.8W LED (Included)
 784 Lumens





11228 FTOI, FTSN
15-Light Chandelier
43"W x 40.25"H
15 x 40W MB Bulbs

AXIS COLLECTION

This transitional design works in any style home. Intersecting, rectangular tubing finished in your choice of Satin Nickel or Oil Rubbed Bronze gently curves to support simple line Frost glass shades.

AXIS COLLECTION

- Frosted glass shades
- Intersecting rectangular tubing



11225 FTOI, FTSN
5-Light Chandelier
24"W x 20.5"H
5 x 60WMB Bulbs



11226 FTOI, FTSN
9-Light Chandelier
28"W x 26.5"H
9 x 60WMB Bulbs

AXIS COLLECTION

- Frosted glass shades
- Intersecting rectangular tubing



5840 FTOI,FTSN
1-Light Flushmount
11.5"W x 6"H
1 x 60W MB Bulb



5849FTSN
2-Light Flushmount
Satin Nickel
11.5"W x 6"H
2 x 60W MB Bulbs



5841 FTOI,FTSN
2-Light Flushmount
13.5"W x 6"H
2 x 60W MB Bulbs



5842 FTOI,FTSN
3-Light Flushmount
15.5"W x 6"H
3 x 60W MB Bulbs



11223 FTOI, FTSN
3-Light Chandelier
18"W x 16.25"H
3 x 60W MB Bulbs



11311 FTOI,FTPC,FTSN
 1-Light Wall Sconce
 5"W x 8"H x 6.5"Ext.
 1 x 60WMB Bulb



11312 FTOI,FTPC,FTSN
 2-Light Bath Vantiy
 13"W x 8.5"H x 6.5"Ext.
 2 x 60WMB Bulbs



11313 FTOI,FTPC,FTSN
 3-Light Bath Vantiy
 21"W x 8.5"H x 6.5"Ext.
 3 x 60WMB Bulbs



11314 FTOI,FTPC,FTSN
 4-Light Bath Vantiy
 28.5"W x 8.5"H x 6.5"Ext.
 4 x 60WMB Bulbs



92061 FTOI, FTSN

1-Light Mini Pendant
 5"W x 6"H x 50.5"OAH
 1 x 60W MB Bulb

- Includes One 6" stems
- Includes Three 12" stems
- Additional stems available:
 6" order - STR04506OI, SN
 12" order - STR04512OI, SN





10066 FTOI, FTSN
9-Light Chandelier
30"W x 30"H
9 x 60W MBBulbs

STEFAN COLLECTION

A transitional look that works in a broad range of interiors featuring metal frames finished in either Oiled Rub Bronze for the traditional home or Satin Nickel for a more contemporary look. Simple Frost glass shades compliment the overall design.



10065 FTOI, FTSN
5-Light Chandelier
25"W x 23.5"H
5 x 60W MBBulbs

STEFAN COLLECTION



10042 FTOI, FTSN
2-Light Semi-Flush Mount
13"W x 11"H
2 x 60W MBBulbs

92061 FTOI, FTSN

1-Light Mini Pendant
5"W x 6"H x 50.5"OAH
1 x 60W MBBulb

- Includes One 6" stem
- Includes Three 12" stems
- Additional stems available:
6" order - STR04506OI, SN
12" order - STR04512OI, SN

120°



10064 FTOI, FTSN
3-Light Chandelier
21"W x 22"H
3 x 60W MBBulbs

STEFAN COLLECTION



10071 FTOI, FTSN
1-Light Wall Sconce
5"W x 8"H x 8"Ext.
1 x 60W MBBulb



10072 FTOI, FTSN
2-Light Bath Vanity
13.25"W x 8"H x 8"Ext.
2 x 60W MBBulbs



10073 FTOI, FTSN
3-Light Bath Vanity
21.5"W x 8"H x 8"Ext.
3 x 60W MBBulbs



10074 FTOI, FTSN
4-Light Bath Vanity
29.75"W x 8"H x 8"Ext.
4 x 60W MBBulbs





10046 FTOI, FTSN

9-Light Chandelier

28.5"W x 30.5"H

9 x 60W MBBulbs

LOGAN COLLECTION

Modern style at a competitive price will make this collection the next builder standard. Tall profile Frost glass shades adorn a minimalistic frame in your choice of Satin Nickel or Oil Rubbed Bronze.



10045 FTOI, FTSN
5-Light Chandelier
20"W x 18"H
5 x 60W MBBulbs



10043 FTOI, FTSN
3-Light Chandelier
17"W x 19"H
3 x 60W MBBulbs

LOGAN COLLECTION



10042 FTOI, FTSN
2-Light Semi-Flush Mount
13"W x 8.5"H
2 x 60W MBBulbs



10044 FTOI, FTSN
3-Light Pendant
15.5"W x 17"H
3 x 100W MBBulbs



92040 FTOI, FTSN
1-Light Mini Pendant
4.5"W x 7.5"H x 51.5"OAH
1 x 60W MBBulb

- Includes One 6" stem
- Includes Three 12" stems
- Additional stems available:
6" order - STR04506OI, SN
12" order - STR04512OI, SN



LOGAN COLLECTION



10051 FTOI, FTSN
1-Light Wall Sconce
5"W x 8.5"H x 8.75"Ext.
1 x 60W MBBulb



10052 FTOI, FTSN
2-Light Bath Vanity
14"W x 8.5"H x 7"Ext.
2 x 60W MBBulbs




10053 FTOI, FTSN
3-Light Bath Vanity
19"W x 8.5"H x 7"Ext.
3 x 60W MBBulbs



10054 FTOI, FTSN
4-Light Bath Vanity
28"W x 8.5"H x 7"Ext.
4 x 60W MBBulbs





10206FTSN
9-Light Chandelier
Satin Nickel
28"W x 23"H
9 x 60W MB Bulbs

CORONA COLLECTION

Minimalistic frames finished in Satin Nickel support cylinders of Frost glass shades.
A clean contemporary look at a very affordable price.



10205FTSN
5-Light Chandelier
Satin Nickel
22"W x 19"H
5 x 60W MB Bulbs

CORONA COLLECTION



90200FTSN
1-Light Mini Pendant
Satin Nickel
5"W x 6"H x 50.5"OAH
1 x 60W MB Bulb

- Includes One 6" stem
- Includes Three 12" stems
- Additional stems available:
6" order - STR04506SN
12" order - STR04512SN



10203FTSN
3-Light Chandelier
Satin Nickel
18"W x 18"H
3 x 60W MB Bulbs

CORONA COLLECTION



10211 FTOI,FTPC,FTSN
1-Light Wall Sconce
Satin Nickel
4.5"W x 8.25"H x 6"Ext.
1 x 60W MB Bulb



10212 FTOI,FTPC,FTSN
2-Light Bath Vanity
Satin Nickel
12"W x 9"H x 6"Ext.
2 x 60W MB Bulbs



10213 FTOI,FTPC,FTSN
3-Light Bath Vanity
Satin Nickel
19.25"W x 9"H x 6"Ext.
3 x 60W MB Bulbs



10214 FTOI,FTPC,FTSN
4-Light Bath Vanity
Satin Nickel
26.25"W x 9"H x 6"Ext.
4 x 60W MB Bulbs






MINI HI-BAY COLLECTION


Small pendants reminiscent of yesteryear are available in your choice of Bronze, Antique Copper, Satin Nickel, and Polished Nickel. In addition to the numerous metal shades, glass shades in Clear, Mirror Smoke, and Satin White are also offered. The optional Antique Replica light bulb adds to the authentic look.

MINI HI-BAY COLLECTION



25031 ACP, BZ,
PN, SN (*Without Bulb*)
25031 ACP/BUI, BZ/BUI,
PN/BUI, SN/BUI (*With Bulb*)
1-Light Pendant
11"W x 11"H x 70"OAH
1 x 60W MB Bulb

120°



25030 ACP, BZ,
PN, SN (*Without Bulb*)
25030 ACP/BUI, BZ/BUI,
PN/BUI, SN/BUI (*With Bulb*)
1-Light Pendant
8"W x 13.25"H x 72.25"OAH
1 x 60W MB Bulb


120°



BUI-60W-ST64-E26-CL-120V
60 Wattage
Antique Light Bulb
Sold Separately


• For additional items in this collection, see catalog LMXCAT1311, pg 321.

MINI HI-BAY COLLECTION



**25051 ACP, BZ,
PN, SN (Without Bulb)**
**25051 ACP/BUI,
BZ/BUI, PN/BUI,
SN/BUI (With Bulb)**
1-Light Pendant
11"W x 16.5"H x 60.75"OAH
1 x 60W MB Bulb

- Includes One 6" stem
- Includes Three 12" stems
- Additional stems available:
6" stem - STR04506ACP, BZ, PN, SN
12" stem - STR04512ACP, BZ, PN, SN



**25050 ACP, BZ,
PN, SN (Without Bulb)**
**25050 ACP/BUI,
BZ/BUI, PN/BUI,
SN/BUI (With Bulb)**
1-Light Pendant
8"W x 12.25"H x 56.5"OAH
1 x 60W MB Bulb

- Includes One 6" stem
- Includes Three 12" stems
- Additional stems available:
6" stem - STR04506ACP, BZ, PN, SN
12" stem - STR04512ACP, BZ, PN, SN



BUI-60W-ST64-E26-CL-120V
60 Wattage
Antique Light Bulb
Sold Separately

MINI HI-BAY COLLECTION



25070 ACP, BZ,
PN, SN (Without Bulb)
25070 ACP/BUI, BZ/BUI,
PN/BUI, SN/BUI (With Bulb)
1-Light Wall Sconce
8"W x 13.25"H x 10.5"Ext.
1 x 60W MB Bulb



25071 ACP, BZ,
PN, SN (Without Bulb)
25071 ACP/BUI, BZ/BUI,
PN/BUI, SN/BUI (With Bulb)
1-Light Wall Sconce
11"W x 11"H x 10.5"Ext.
1 x 60W MB Bulb



25091 ACP, BZ,
PN, SN (Without Bulb)
25091 ACP/BUI, BZ/BUI,
PN/BUI, SN/BUI (With Bulb)
1-Light Wall Sconce
11"W x 13.25"H x 11.25"Ext.
1 x 60W MB Bulb



25090 ACP, BZ,
PN, SN (Without Bulb)
25090 ACP/BUI, BZ/BUI,
PN/BUI, SN/BUI (With Bulb)
1-Light Wall Sconce
8"W x 15.5"H x 11.25"Ext.
1 x 60W MB Bulb



HI-BAY COLLECTION

Inspired by industrial lighting, the Hi-Bay collection's refined designs maintain the boldness of their predecessors but possess refined details throughout. Hi-Bay fixtures with Clear halophane glass are available in choice of finish of Bronze or Satin Nickel. Hi-Bay fixtures with solid metal shades are available in three choices of finish including Bronze, Polished Nickel and Satin Nickel, and include a Frost glass diffuser which conceals the light source and gently diffuses the incandescent illumination.

HI-BAY COLLECTION



25117 SWBZ, SWPN, SWSN

1-Light Pendant
17.75"W x 17"H x 61"OAH
1 x 100W MB Bulb

- Includes One 6" stem
- Includes Three 12" stems
- Additional stems available:
6" stem - STR07506BZ, PN, SN
12" stem - STR07512BZ, PN, SN

120°



25116 SWBZ, SWPN, SWSN

1-Light Pendant
14"W x 23.5"H x 67.5"OAH
1 x 100W MB Bulb

- Includes One 6" stem
- Includes Three 12" stems
- Additional stems available:
6" stem - STR07506BZ, PN, SN
12" stem - STR07512BZ, PN, SN

120°

• For additional items in this collection, see catalog LMXCAT1311, pg 331.



85853 WTBZ, WTWT
LED Flush Mount
31.5"L x 25"W x 4.75"H
54W LED (Included)
3780 Lumens



85855 WTBZ, WTWT
LED Flush Mount
40"L x 23"W x 4.75"H
78W LED (Included)
5460 Lumens




NEBULA COLLECTION

Soft rounded frames of steel available in your choice of White or Bronze are intelligently illuminated by state of the art LED modules which are dimmable. A two layer bottom allows a splash of light for highlight.

NEBULA COLLECTION

- Dimmable LED
- 3000 K color temperature
- Laser cut steel frame
- Acrylic lens
- Layered light diffusion



View from below

85851 WTBZ, WTWT
LED Flush Mount
25"L x 20"W x 4.75"H
42W LED (Included)
2940 Lumens



LIGHTRAY COLLECTION

Indirect exterior lighting not only provides illumination where you want it but also highlights the building structure for a beautiful architectural effect. Our collection of up and down lighting fixtures are available in both Architectural Bronze and Brushed Aluminum. They are also available in both incandescent and LED. The fixtures are sealed with screw lenses that are water tight and allows for the use of standard light bulbs.



6123 ABZ, AL
2-Light Wall Sconce
4"W x 10.25"H x 6"Ext.
2 x 50W R20 MB Bulbs

• up/down light



6125 ABZ, AL
1-Light Wall Sconce
4.25"W x 7.75"H x 6.5"Ext.
1 x 75W R30 MB Bulb



6122 ABZ, AL
1-Light Wall Sconce
4"W x 6.25"H x 6"Ext.
1 x 50W R20 MB Bulb



6126 ABZ, AL
2-Light Wall Sconce
4.25"W x 12"H x 6.5"Ext.
2 x 75W R30 MB Bulbs

• up/down light



LIGHTRAY COLLECTION

- Removeable water-tight lens
- Cast and Machined Aluminum construction



6102 ABZ, AL
2-Light Wall Sconce
5"W x 15.75"H x 7.75"Ext.
2 x 75W R30MB Bulbs

- up/down light



6101 ABZ, AL
1-Light Wall Sconce
5"W x 9.25"H x 7.75"Ext.
1 x 75W R30MB Bulb

- up/down light



6110 ABZ, AL
1-Light Wall Sconce
4.25"W x 8"H x 6.5"Ext.
1 x 50W R20MB Bulb



6112 ABZ, AL
2-Light Wall Sconce
4.25"W x 12"H x 6.5"Ext.
2 x 50W R20MB Bulbs

- up/down light



LIGHTRAY COLLECTION

- Removeable water-tight lens
- Cast and Machined Aluminum construction



6100 ABZ, AL
1-Light Flush Mount
5"W x 7.75"H x 5"Ext.
1 x 75W R30 MB Bulb



6115 ABZ, AL
2-Light Wall Sconce
4.75"W x 10.25"H x 5.75"Ext.
2 x 50W R20MB Bulbs

- up/down light



6117 ABZ, AL
2-Light Wall Sconce
6"W x 12.5"H x 6.75"Ext.
2 x 75W R30 MB Bulbs

- up/down light



- Dimmable LED
- 3000 K color temperature
- Removeable water-tight lens
- Cast and Machined Aluminum construction

LIGHTRAY LED COLLECTION

They are also available in both LED and Incandescent



86104 ABZ, AL
 1-Light Flush Mount
 5"W x 6.25"H x 5"Ext.
 1 x 15W LED (Included)
 1050 Lumens



86106 ABZ, AL
 2-Light Wall Sconce
 4"W x 4"H x 5.75"Ext.
 2 x 4.5W LED (Included)
 630 Lumens

• up/down light



86107 ABZ, AL
 2-Light Wall Sconce
 4"W x 4"H x 5.75"Ext.
 2 x 4.5W LED (Included)
 630 Lumens

• up/down light



86109 ABZ, AL
 2-Light Wall Sconce
 4"W x 6.5"H x 5"Ext.
 2 x 4.5W LED (Included)
 630 Lumens

• up/down light



86108 ABZ, AL
 1-Light Wall Sconce
 4"W x 5.25"H x 5"Ext.
 1 x 4.5W LED (Included)
 315 Lumens

• up/down light



LIGHTRAY LED COLLECTION



86129 ABZ, AL
 2-Light Wall Sconce
 4.25"W x 11.25"H x 4"Ext.
 2 x 10W LED (Included)
 1400 Lumens

• up/down light



86128 ABZ, AL
 1-Light Wall Sconce
 4.25"W x 6.25"H x 4"Ext.
 1 x 10W LED (Included)
 700 Lumens



86110 ABZ, AL
 1-Light Wall Sconce
 4.25"W x 8"H x 6.5"Ext.
 1 x 10W LED (Included)
 700 Lumens



86112 ABZ, AL
 2-Light Wall Sconce
 4.25"W x 12"H x 6.5"Ext.
 2 x 10W LED (Included)
 1400 Lumens

• up/down light

- Dimmable LED
- 3000 K color temperature
- Removeable water-tight lens
- Cast and Machined Aluminum construction

LIGHTRAY LED COLLECTION



86117 ABZ, AL
 2-Light Wall Sconce
 6"W x 12.5"H x 6.75"Ext.
 2 x 15W LED (Included)
 2100 Lumens

• up/down light



86101 ABZ, AL
 1-Light Wall Sconce
 5"W x 9.25"H x 7.75"Ext.
 1 x 15W LED (Included)
 1050 Lumens



86115 ABZ, AL
 2-Light Wall Sconce
 4.75"W x 10.25"H x 5.75"Ext.
 2 x 10W LED (Included)
 1400 Lumens

• up/down light



86102 ABZ, AL
 2-Light Wall Sconce
 5"W x 15.75"H x 7.75"Ext.
 2 x 15W LED (Included)
 2100 Lumens



LIGHTRAY LED COLLECTION

- Dimmable LED
- 3000 K color temperature
- Removeable water-tight lens
- Cast and Machined Aluminum construction



86122 ABZ, AL
 1-Light Wall Sconce
 4"W x 6.25"H x 6"Ext.
 1 x 10W LED (Included)
 700 Lumens



86123 ABZ, AL
 2-Light Wall Sconce
 4"W x 10.25"H x 6"Ext.
 2 x 10W LED (Included)
 1400 Lumens

- up/down light



86126 ABZ, AL
 2-Light Wall Sconce
 4.25"W x 12"H x 6.5"Ext.
 2 x 10W LED (Included)
 1400 Lumens

- up/down light



86125 ABZ, AL
 1-Light Wall Sconce
 4.25"W x 7.75"H x 6.5"Ext.
 1 x 10W LED (Included)
 700 Lumens



- Dimmable LED
- 3500 K color temperature
- Stainless Steel construction
- Indoor/Outdoor application

MODA COLLECTION

Solid blocks of glass infused with tiny bubbles come to life when illuminated by high power LED concealed in the frame above. Frames are constructed of Stainless Steel and is also available in Bronze.



88272 BGBZ, BGSST

LED Wall Sconce
7"W x 12"H x 2.25"Ext.
9W LED (Included)
600 Lumens



88274 BGBZ, BGSST

LED Wall Sconce
13"W x 6"H x 2.25"Ext.
15W LED (Included)
900 Lumens



WEAVE COLLECTION

Woven bands of brushed Aluminum create an interesting and unique lighting design. Elegant enough for interior walls but is also suitable to be installed outdoors. Long lasting LED modules are concealed on the top for glare free illumination.

- Dimmable LED
- Indirect 3500 K color temperature
- Powder coated aluminum
- Indoor/Outdoor application



88293AL
LED Wall Sconce
Aluminum
7.75"W x 12"H x 2"Ext.
9W LED (Included)
600 Lumens



88292AL
LED Wall Sconce
Aluminum
12.5"W x 6.5"H x 2"Ext.
15W LED (Included)
900 Lumens



MOSAIC COLLECTION

Blocks of extruded Aluminum are brushed in a contemporary design and highlighted by energy efficient LED that wash the face with light. Additional LED is enclosed inside to provide exceptional downlight.

- Dimmable LED
- Indirect 3500 K color temperature
- Powder coated aluminum
- Indoor/Outdoor application



88283AL
LED Wall Sconce
Aluminum
7"W x 12.5"H x 3.5"Ext.
12W LED (Included)
6W Downlight (Included)
1260 Lumens



88285AL
LED Wall Sconce
Aluminum
10.75"W x 6.25"H x 3.5"Ext.
12W LED (Included)
6W Downlight (Included)
1260 Lumens



VIEW EE COLLECTION

The View collection brings a contemporary edge and versatility to indoor and outdoor illumination. In each Stainless Steel and Bronze rectangle, LED fluorescent light plays with geometric cutouts, casting up and down lighting. A polycarbonate backing provides water resistance for moist environments. The View collection is a subtle, sleek light source with restrained style, that is offered with either Fluorescent or LED lamping options

- 2700 K color temperature
- Self-Ballasted GU24 Bulbs
- 10,000 Rated Life Hours
- Stainless Steel covers
- Polycarbonate backing
- LED option



54321 WTBZ, WTSST

1-Light Wall Sconce
8"W x 10.75"H x 3.5"Ext.
1 x 13W GU24 Bulb (Included)
900 Rated Lumens



54322 WTBZ, WTSST

1-Light Wall Sconce
8"W x 10.75"H x 3.5"Ext.
1 x 13W GU24 Bulb (Included)
900 Rated Lumens



VIEW LED COLLECTION

- 3000 K color temperature
- Stainless Steel covers
- Polycarbonate backing
- LED option



54332 WTBZ, WTSST
1-Light Wall Sconce
8"W x 10.75"H x 3.5"Ext.
1 x 11W LED (Included)
900 Initial Lumens



54331 WTBZ, WTSST
1-Light Wall Sconce
8"W x 10.75"H x 3.5"Ext.
1 x 11W LED (Included)
900 Initial Lumens



KNOXVILLE COLLECTION



1127FSBZ
 1-Light Outdoor Wall
 Bronze
 11"W x 23.75"H x 14.75"Ext.
 HCO13.75" • BP7.25"W x 15.75"H
 1 x 100W MB Bulb



1125FSBZ
 1-Light Outdoor Wall
 Bronze
 9"W x 18.5"H x 12.25"Ext.
 HCO11.25" • BP5.25"W x 10.5"H
 1 x 100W MB Bulb



1123FSBZ
 1-Light Outdoor Wall
 Bronze
 7"W x 11"H x 8.25"Ext.
 HCO3.5" • BP5.25"W x 6.5"H
 1 x 60W MB Bulb



1129FSBZ
 1-Light Outdoor Pendant
 Bronze
 11"W x 17.25"H
 1 x 100W MB Bulb



1120FSBZ
 1-Light Outdoor Post
 Bronze
 9"W x 19.5"H
 1 x 100W MB Bulb



1121FSBZ
 1-Light Outdoor Post
 Bronze
 11"W x 23"H
 1 x 100W MB Bulb

WHARF COLLECTION

- White interior to reflect more light
- Removable bottom cage undercarriage



35011 EB,OB
1-Light Outdoor Wall
8"W x 14"H x 10"Ext.
HCO7.5" • BP4.5"W x 4.5"H
1 x 100W MB Bulb



35013 EB,OB
1-Light Outdoor Wall
12"W x 16.75"H x 14"Ext.
HCO8.5" • BP4.5"W x 4.5"H
1 x 100W MB Bulb



35012 EB,OB
1-Light Outdoor Wall
10"W x 15.25"H x 12"Ext.
HCO8" • BP4.5"W x 4.5"H
1 x 100W MB Bulb

TERRACE COLLECTION

Simple lines create a transitional style that fits a wide variety of exterior home design. Available in both Platinum and Bronze finish with Frosted Seedy glass in fluorescent or incandescent. Fluorescent models can easily be adapted to LED with the optional LED GU24 lamp.



3254 FSBZ, FSPL
1-Light Outdoor Wall
8"W x 16"H x 9.5"Ext.
HCO2.5" • BP5.25"W x 7.75"H
1 x 100WMB Bulb
Die Cast Aluminum



3252 FSBZ, FSPL
1-Light Outdoor Wall
5.25"W x 11"H x 6.75"Ext.
HCO2.5" • BP4.5"W x 7"H
1 x 60WMB Bulb
Die Cast Aluminum

TERRACE COLLECTION



3253 FSBZ, FSPL
1-Light Outdoor Wall
7"W x 13.75"H x 8.5"Ext.
HCO2.5" • BP5.25"W x 7.75"H
1 x 60W MB Bulb
Die Cast Aluminum



3250 FSBZ, FSPL
1-Light Outdoor Post
8"W x 19.25"H
1 x 100W MB Bulb
Die Cast Aluminum

RADCLIFFE COLLECTION

Classical, traditional style finished in a rustic Black Oxide finish with Weathered Frost glass sure to add elegance to your home's exterior. Available in both incandescent and fluorescent versions with an optional LED source to consider.



3343WFBO

1-Light Outdoor Wall
Black Oxide
9"W x 14.5"H x 10.5"Ext.
HCO5" • BP4.75"W x 10"H
1 x 100WMB Bulb
Die Cast Aluminum



3344WFBO

1-Light Outdoor Wall
Black Oxide
9"W x 16.75"H x 11.75"Ext.
HCO8.25" • BP4.75"W x 10"H
1 x 100WMB Bulb
Die Cast Aluminum



3346WFBO

1-Light Outdoor Wall
Black Oxide
11"W x 20.5"H x 14.25"Ext.
HCO10.25" • BP6.25"W x 12.5"H
1 x 100WMB Bulb
Die Cast Aluminum

RADCLIFFE COLLECTION

FOR
WET
LOCATION



3342WFBO
1-Light Outdoor Wall
Black Oxide
7"W x 11.25"H x 8.25"Ext.
HCO4" • BP4.75"W x 7.75"H
1 x 60WMB Bulb
Die Cast Aluminum



3349WFBO
1-Light Outdoor Pendant
Black Oxide
11"W x 16.5"H
1 x 100WMB Bulb
Die Cast Aluminum



3340WFBO
1-Light Outdoor Post
Black Oxide
9"W x 17.5"H
1 x 100WMB Bulb
Die Cast Aluminum

SIENNA COLLECTION

This craftsman inspired design features a rich Earth Tone finish combined with Frosted Seedy glass that provides an upscale look at a competitive price. Available in both incandescent and fluorescent versions with an optional LED source to consider.



3322FSET
1-Light Outdoor Wall
Earth Tone
6"W x 9.25"H x 7.5"Ext.
HCO2.25" • BP4.75"W x 6"H
1 x 60W MB Bulb
Die Cast Aluminum



3324FSET
1-Light Outdoor Wall
Earth Tone
9"W x 13.25"H x 11"Ext.
HCO2.5" • BP4.75"W x 8.75"H
1 x 100W MB Bulb
Die Cast Aluminum

SIENNA COLLECTION

FOR
WET
LOCATION



3323FSET

1-Light Outdoor Wall
Earth Tone

7.5"W x 11.5"H x 9.25"Ext.
HCO2.5" • BP4.75"W x 8.75"H
1 x 60WMB Bulb
Die Cast Aluminum



3320FSET

1-Light Outdoor Post
Earth Tone

9"W x 15.5"H
1 x 100WMB Bulb
Die Cast Aluminum

BALBOA DC COLLECTION

This transitional design in die cast aluminum at a remarkable price point. Finished in Copper Oxide with a hand painted Lace glass and two lamping options with both fluorescent and incandescent versions available. Optional LED lamping adds additional energy savings and long life.



3802LACO

1-Light Outdoor Wall
Copper Oxide
6.5"W x 9.5"H x 8.5"Ext.
HCO2.5" • BP4.5"W x 6.75"H
1 x 60W MB Bulb
Die Cast Aluminum



3804LACO

1-Light Outdoor Wall
Copper Oxide
10"W x 14.5"H x 12.25"Ext.
HCO3.5" • BP5.25"W x 7.75"H
1 x 100W MB Bulb
Die Cast Aluminum



3806LACO

1-Light Outdoor Wall
Copper Oxide
12"W x 17.25"H x 14.25"Ext.
HCO5.25" • BP5.25"W x 7.75"H
1 x 100W MB Bulb
Die Cast Aluminum

BALBOA DC COLLECTION

FOR
WET
LOCATION



3809LACO

1-Light Outdoor Pendant
Copper Oxide
12"W x 17.25"H
1 x 100WMB Bulb
Die Cast Aluminum



3800LACO

1-Light Outdoor Post
Copper Oxide
10"W x 17.25"H
1 x 100WMB Bulb
Die Cast Aluminum

TERRACE EE COLLECTION


Simple lines create a transitional style that fits a wide variety of exterior home design. Available in both Platinum and Bronze finish with Frosted Seedy glass in fluorescent or incandescent. Fluorescent models can easily be adapted to LED with the optional LED GU24 lamp.



85754 FSBZ, FSPL

1-Light Outdoor Wall
8"W x 16"H x 9.5"Ext.
HCO2.5" • BP5.25"W x 7.75"H
1 x 26W GU24 Bulb (Included)
1760 Rated Lumens
Die Cast Aluminum

CA
T24



85752 FSBZ, FSPL

1-Light Outdoor Wall
5.25"W x 11"H x 6.75"Ext.
HCO2.5" • BP4.5"W x 7"H
1 x 13W GU24 Bulb (Included)
900 Rated Lumens
Die Cast Aluminum

CA
T24

TERRACE EE COLLECTION

- Self-Ballasted GU24 Bulbs
- 2700 K Color Temperature
- 10,000 Rated Life Hours
- Die Cast Aluminum



85753 FSBZ, FSPL

1-Light Outdoor Wall
7"W x 13.75"H x 8.5"Ext.
HCO2.5" • BP5.25"W x 7.75"H
1 x 18W GU24 Bulb (Included)
1355 Rated Lumens
Die Cast Aluminum

CA
T24



85750 FSBZ, FSPL

1-Light Outdoor Post
8"W x 19.25"H
1 x 26W GU24 Bulb (Included)
1760 Rated Lumens
Die Cast Aluminum

CA
T24

RADCLIFFE EE COLLECTION

Classical, traditional style finished in a rustic Black Oxide finish with Weathered Frost glass sure to add elegance to your home's exterior. Available in both incandescent and fluorescent versions with an optional LED source to consider.



85643WFBO

1-Light Outdoor Wall
Black Oxide
9"W x 14.5"H x 10.5"Ext.
HCO5" • BP4.75"W x 10"H
1 x 18WGU24 Bulb (Included)
1355 Rated Lumens
Die Cast Aluminum

CA
T24



85644WFBO

1-Light Outdoor Wall
Black Oxide
9"W x 16.75"H x 11.75"Ext.
HCO8.25" • BP4.75"W x 10"H
1 x 18WGU24 Bulb (Included)
1355 Rated Lumens
Die Cast Aluminum

CA
T24



85646WFBO

1-Light Outdoor Wall
Black Oxide
11"W x 20.5"H x 14.25"Ext.
HCO10.25" • BP6.25"W x 12.5"H
1 x 26WGU24 Bulb (Included)
1760 Rated Lumens
Die Cast Aluminum

CA
T24

RADCLIFFE EE COLLECTION

- Self-Ballasted GU24 Bulbs
- 2700 K Color Temperature
- 10,000 Rated Life Hours
- Die Cast Aluminum



85642WFBO

1-Light Outdoor Wall
Black Oxide
7"W x 11.25"H x 8.25"Ext.
HCO4" • BP4.75"W x 7.75"H
1 x 13W GU24 Bulb (Included)
900 Rated Lumens
Die Cast Aluminum

CA
T24



FOR
WET
LOCATION

85649WFBO

1-Light Outdoor Pendant
Black Oxide
11"W x 16.5"H
1 x 26W GU24 Bulb (Included)
1760 Rated Lumens
Die Cast Aluminum

CA
T24



85640WFBO

1-Light Outdoor Post
Black Oxide
9"W x 17.5"H
1 x 18W GU24 Bulb (Included)
1355 Rated Lumens
Die Cast Aluminum

CA
T24

SIENNA EE COLLECTION

This craftsman inspired design features a rich Earth Tone finish combined with Frosted Seedy glass that provides an upscale look at a competitive price. Available in both incandescent and fluorescent versions with an optional LED source to consider.



85692FSET

1-Light Outdoor Wall
Earth Tone

6"W x 9.25"H x 7.5"Ext.
HCO2.25" • BP4.75"W x 6"H
1 x 13W GU24 Bulb (Included)
900 Rated Lumens
Die Cast Aluminum

CA
T24



85694FSET

1-Light Outdoor Wall
Earth Tone

9"W x 13.25"H x 11"Ext.
HCO2.5" • BP4.75"W x 8.75"H
1 x 18W GU24 Bulb (Included)
1355 Rated Lumens
Die Cast Aluminum

CA
T24

SIENNA EE COLLECTION

- Self-Ballasted GU24 Bulbs
- 2700 K Color Temperature
- 10,000 Rated Life Hours
- Die Cast Aluminum



85693FSET

1-Light Outdoor Wall
Earth Tone

7.5"W x 11.5"H x 9.25"Ext.
HCO2.5" • BP4.75"W x 8.75"H
1 x 13W GU24 Bulb (Included)
900 Rated Lumens
Die Cast Aluminum

CA
T24



85690FSET

1-Light Outdoor Post
Earth Tone

9"W x 15.5"H
1 x 18W GU24 Bulb (Included)
1355 Rated Lumens
Die Cast Aluminum

CA
T24

BALBOA EE COLLECTION

This transitional design in die cast aluminum at a remarkable price point. Finished in Copper Oxide with a hand painted Lace glass and two lamping options with both fluorescent and incandescent versions available. Optional LED lamping adds additional energy savings and long life.



85502LACO

1-Light Outdoor Wall
Copper Oxide
6.5"W x 9.5"H x 8.5"Ext.
HCO2.5" • BP4.5"W x 6.75"H
1 x 13W GU24 Bulb (Included)
900 Rated Lumens
Die Cast Aluminum

CA
T24



85504LACO

1-Light Outdoor Wall
Copper Oxide
10"W x 14.5"H x 12.25"Ext.
HCO3.5" • BP5.25"W x 7.75"H
1 x 18W GU24 Bulb (Included)
1355 Rated Lumens
Die Cast Aluminum

CA
T24



85506LACO

1-Light Outdoor Wall
Copper Oxide
12"W x 17.25"H x 14.25"Ext.
HCO5.25" • BP5.25"W x 7.75"H
1 x 26W GU24 Bulb (Included)
1760 Rated Lumens
Die Cast Aluminum

CA
T24

BALBOA EE COLLECTION

- Self-Ballasted GU24 Bulbs
- 2700 K Color Temperature
- 10,000 Rated Life Hours
- Die Cast Aluminum



85509LACO

1-Light Outdoor Pendant

Copper Oxide

12"W x 17.25"H

1 x 26W GU24 Bulb (Included)

1760 Rated Lumens

Die Cast Aluminum

CA
T24



85500LACO

1-Light Outdoor Post

Copper Oxide

10"W x 17.25"H

1 x 18W GU24 Bulb (Included)

1355 Rated Lumens

Die Cast Aluminum

CA
T24


OSLO EE COLLECTION

A modern look in outdoor, at a very competitive price, features die cast construction finished in your choice of Platinum or Bronze with White UV resistant acrylic diffusers for durability. Standard model is supplied with 2700 K fluorescent but is also available in a LED upgrade for ultimate energy savings and long lamp life.



85312 WTABZ, WTPL
1-Light Outdoor Wall
7.25"W x 10"H x 9.5"Ext.
HCO 7.5" • BP 5"W x 5"H
1 x 13W GU24 Bulb (Included)
900 Rated Lumens
Die Cast Aluminum

CA
T24



85315 WTABZ, WTPL
1-Light Outdoor Wall
9"W x 14.5"H x 11.5"Ext.
HCO 12.25" • BP 5"W x 5"H
1 x 26W GU24 Bulb (Included)
1760 Rated Lumens
Die Cast Aluminum

CA
T24



OSLO EE COLLECTION

- Self-Ballasted GU24 Bulbs
- 2700 K Color Temperature
- 10,000 Rated Life Hours
- Die Cast Aluminum



85313 WTABZ, WTPL

1-Light Outdoor Wall
9"W x 11.5"H x 11.5"Ext.
HCO9.25" • BP5"W x 5"H
1 x 18W GU24 Bulb (Included)
1355 Rated Lumens
Die Cast Aluminum

CA
T24



85310 WTABZ, WTPL

1-Light Outdoor Post
9"W x 11.75"H
1 x 18W Gu24 Bulb (Included)
1355 Rated Lumens
Die Cast Aluminum

CA
T24

OAKVILLE EE COLLECTION

- Self-Ballasted GU24 Bulbs
- 2700 K color temperature
- 10,000 Rated Life Hours
- Die Cast Aluminum
- 90+ CRI



85782WGBO

1-Light Outdoor Wall
Black Oxide
6.25"W x 9.5"H x 7"Ext.
HCO2.5" • BP4.75"W x 5.75"H
1 x 13W GU24 Bulb (Included)
900 Rated Lumens
Die Cast Aluminum

CA
T24

85784WGBO

1-Light Outdoor Wall
Black Oxide
8"W x 14.25"H x 10"Ext.
HCO7" • BP4.75"W x 8.5"H
1 x 13W GU24 Bulb (Included)
900 Rated Lumens
Die Cast Aluminum

CA
T24



85786WGBO

1-Light Outdoor Wall
Black Oxide
12"W x 21"H x 14.5"Ext.
HCO10" • BP4.75"W x 8.5"H
1 x 26W GU24 Bulb (Included)
1760 Rated Lumens
Die Cast Aluminum

CA
T24

OAKVILLE EE COLLECTION



85785WGBO
1-Light Outdoor Wall
Black Oxide
10"W x 17.5"H x 12"Ext.
HCO8.25" • BP4.75"W x 8.5"H
1 x 18W GU24 Bulb (Included)
1355 Rated Lumens
Die Cast Aluminum
CA
T24



85788WGBO
1-Light Outdoor Pendant
Black Oxide
12"W x 19"H
1 x 26W GU24 Bulb (Included)
1760 Rated Lumens
Die Cast Aluminum
CA
T24



85780WGBO
1-Light Outdoor Post
Black Oxide
10"W x 17.75"H
1 x 18W GU24 Bulb (Included)
1355 Rated Lumens
Die Cast Aluminum
CA
T24

CALISTOGA EE COLLECTION

- Self-Ballasted GU24 Bulbs
- 2700 K color temperature
- 10,000 Rated Life Hours
- Die Cast Aluminum
- 90+ CRI



85432SWAE
1-Light Outdoor Wall
Adobe
7"W x 10"H x 8.75"Ext.
HCO5" • BP4.25"W x 5"H
1 x 13WGU24 Bulb (Included)
900 Rated Lumens
Die Cast Aluminum

CA
T24



85436SWAE
1-Light Outdoor Wall
Adobe
10.25"W x 15.5"H x 12.75"Ext.
HCO7.5" • BP4.75"W x 8.5"H
1 x 26WGU24 Bulb (Included)
1760 Rated Lumens
Die Cast Aluminum

CA
T24



85434SWAE
1-Light Outdoor Wall
Adobe
9"W x 12.5"H x 11"Ext.
HCO6.5" • BP4.75"W x 6.5"H
1 x 18WGU24 Bulb (Included)
1355 Rated Lumens
Die Cast Aluminum

CA
T24

CALISTOGA EE COLLECTION



85439SWAE
1-Light Outdoor Pendant
Adobe
10.25"W x 17"H
1 x 26W GU24 Bulb (Included)
1760 Rated Lumens
Die Cast Aluminum
CA
T24



85430SWAE
1-Light Outdoor Post
Adobe
10.25"W x 19"H
1 x 26W GU24 Bulb (Included)
1760 Rated Lumens
Die Cast Aluminum
CA
T24

KNOXVILLE EE COLLECTION

- Self-Ballasted GU24 Bulbs
- 2700 K Color Temperature
- 10,000 Rated Life Hours

85625FSBZ

1-Light Outdoor Wall
Bronze
9"W x 18.5"H x 12.25"Ext.
HCO11.25" • BP5.25"W x 10.5"H
1 x 18W GU24 Bulb (Included)
1355 Rated Lumens

CA
T24



85627FSBZ

1-Light Outdoor Wall
Bronze
11"W x 23.75"H x 14.75"Ext.
HCO13.75" • BP7.25"W x 15.75"H
1 x 26W GU24 Bulb (Included)
1760 Rated Lumens

CA
T24



85623FSBZ

1-Light Outdoor Wall
Bronze
7"W x 11"H x 8.25"Ext.
HCO3.5" • BP5.25"W x 6.5"H
1 x 13W GU24 Bulb (Included)
900 Rated Lumens

CA
T24



85629FSBZ

1-Light Outdoor Pendant
Bronze
11"W x 17.25"H
1 x 26W GU24 Bulb (Included)
1760 Rated Lumens

CA
T24

85621FSBZ

1-Light Outdoor Post
Bronze
11"W x 23"H
1 x 26W GU24 Bulb (Included)
1760 Rated Lumens

CA
T24



CASTILLE EE COLLECTION

- Self-Ballasted GU24 Bulbs
- 2700 K Color Temperature
- 10,000 Rated Life Hours



86231FTCF

1-Light Outdoor Wall
Country Forge
6.5"W x 9.5"H x 9.5"Ext.
HCO4.75" • BP5"W x 7.5"H
1 x 13W GU24 Bulb (Included)
900 Rated Lumens

CA
T24



86232FTCF

1-Light Outdoor Wall
Country Forge
8.5"W x 17"H x 11.25"Ext.
HCO10" • BP5.5"W x 10.5"H
1 x 18W GU24 Bulb (Included)
1355 Rated Lumens

CA
T24



86234FTCF

1-Light Outdoor Wall
Country Forge
11.25"W x 24"H x 14.5"Ext.
HCO11.25" • BP5.5"W x 16"H
1 x 26W GU24 Bulb (Included)
1760 Rated Lumens

CA
T24

MX-L120-LO SERIES


COUNTERMAX®

LED UNDER CABINET LIGHTING


The MX-L120-LO is our economy LED undercounter. It features an extruded aluminum body with anodized finishes and a frosted acrylic lens. Its easy mount end caps makes for easy and quick installation without the use of clips. Can be direct wired with the use of direct wire box or plugged directly into an outlet.

Features:

- Warm 3000K light
- 80+ CRI
- Non-Dimmable
- Linkable end to end or with MX Interlink 5
- Value pricing
- Frosted Lens



10" LED Under Cabinet
89901BRZ Anodized Bronze
89901WT White
10"L x 4"W x 1"H
6W
390 Initial Lumens



21" LED Under Cabinet
89902BRZ Anodized Bronze
89902WT White
21"L x 4"W x 1"H
10W
650 Initial Lumens



30" LED Under Cabinet
89903BRZ Anodized Bronze
89903WT White
30"L x 4"W x 1"H
12W
780 Initial Lumens



40" LED Under Cabinet
89904BRZ Anodized Bronze
89904WT White
40"L x 4"W x 1"H
14W
910 Initial Lumens



MXInterLink5 Connector Cord
9" **89951WT** White 24" **89953WT** White
9" **89951BK** Black 24" **89953BK** Black
18" **89952WT** White
18" **89952BK** Black



Plastic Wire Clip
53255
.5"W x 0.25"H x 1"L



MXInterLink5 Power Cord
89954WT White
89954BK Black
72"L
Includes on/off switch



MXInterLink5 Direct Wire Box
89958WT White
89958BK Black
6.5"L x 2.75"W x 1"H

Features:

- Warm white 2700K light
- 90+ CRI, 120° beam spread
- 3/8" Knockouts connector included
- Dimmable with standard dimmer (Lutron CL recommended)
- Linkable end to end or with MXInterlink 4
- No glare lens

The MX-L120-EL features a new edge illuminated technology which provides even light without the common LED spots on the counter. The enclosed design does not need to be open for either wiring or for mounting. Knockouts for wiring are on a removable plate on the back for quick and easy wiring.



Anodized Bronze



Brushed Aluminum



White



10" LED Under Cabinet

89962AL Brushed Aluminum
89962BRZ Anodized Bronze
89962WT White
 10"L x 4"W x 1"H
 4.8W
 320 Initial Lumens

13" LED Under Cabinet

89963AL Brushed Aluminum
89963BRZ Anodized Bronze
89963WT White
 13"L x 4"W x 1"H
 6.5W
 420 Initial Lumens

21" LED Under Cabinet

89964AL Brushed Aluminum
89964BRZ Anodized Bronze
89964WT White
 21"L x 4"W x 1"H
 10.5W
 680 Initial Lumens

30" LED Under Cabinet

89965AL Brushed Aluminum
89965BRZ Anodized Bronze
89965WT White
 30"L x 4"W x 1"H
 15W
 975 Initial Lumens

40" LED Under Cabinet

89966AL Brushed Aluminum
89966BRZ Anodized Bronze
89966WT White
 40"L x 4"W x 1"H
 20W
 1400 Initial Lumens



MXInterLink4 Connector Cord

9" **87876WT** White 24" **87878WT** White
 9" **87876BK** Black 24" **87878BK** Black
 18" **87877WT** White
 18" **87877BK** Black



Plastic Wire Clip
53255

.5"W x 0.25"H x 1"L



MXInterLink4 Power Cord

87880WT White
87880BK Black
 72"L



MXInterLink4 Direct Wire Box

87885WT White
87885BK Black
 5"L x 2.25"W x 1"H

CONVERT COLLECTION

Now you can convert a standard 3" outlet box to a low profile LED recessed fixture. Convert's patent pending design allows for the driver to install into an electrical box which requires no fire rated cover. This creates a fixture with only a 1" extension from the ceiling. High efficiency and smooth dimming down to 5% makes this an excellent choice for hallways, kitchens, and utility lighting.

- 110V Input Voltage
- CRI 80
- Beam Angle 110°
- Power Factor 90+
- THD less than 10%
- Dimmable to 5%
- For Damp Location



87615WTBZ



87615WTWT
87617WTWT
87620WTWT



87615WTSN

87620WTWT

LED Flush Mount
White
8"W x 1.1"H
20W LED (Included)
1400 Lumens
2800/2900K Color Temperature



87617WTWT

LED Flush Mount
White
8"W x 1.1"H
15W LED (Included)
1100 Lumens
4000K Color Temperature




87615 WTBZ, WTSN, WTWT

LED Flush Mount
8"W x 1.1"H
15W LED (Included)
1050 Lumens
2800/2900K Color Temperature



New Construction

- Mounts to 3 1/4" and 4" J-Box with a minimum depth of 2.25"
- Converts standard electrical box to a recessed styled fixture.
- 1" Extension
- Cast Aluminum heat sink provides long LED diode life
- Commercial and Residential application
- High powered dimmable LED
- Cost effective solution for Fire Rated Downlighting applications, as there is no need for fire rated covers




Installs into 3 1/4" and 4" electrical box with a minimum 2.5" depth

Recommended Dimmers:
The Convert is designed to dim with a standard Triac forward phase dimmer. Dimming levels will vary by dimmer.

- Lutron MACL-153M
- Lutron DVL-153P
- Lutron SCL-153P
- Leviton IPL06-10Z
- Leviton 6674-POW


Due to the inrush, current wattage should not exceed 150 watts of product for a 600 watt dimmer.

Model: 87615 / 87617




Photometric Test Report


Model: 87615 / 87617



Model: 87620



Model: 87620



PROFILE EE COLLECTION

Our economy line of LED flushmounts has just been improved. The base is now made of steel for better heat dissipation, as well as the ability to offer not only Bronze, but White and Satin Nickel as a finish. We still offer the PMMA lens for extreme durability and maximum light transmission.

- 3000 K color temperature
- CRI > 80
- Input Voltage 100V - 277V
- Non Dimmable



87597 WTBZ, WTSN, WTWT
LED Flush Mount
13.75"W x 2.5"H
12W LED (Included)
1200 Initial Lumens
984 Delivered Lumens



87595 WTBZ, WTSN, WTWT
LED Flush Mount
11.75"W x 2.5"H
8W LED (Included)
800 Initial Lumens
656 Delivered Lumens



87598 WTBZ, WTSN, WTWT
LED Flush Mount
13.75"W x 2.5"H
12W LED (Included)
1200 Initial Lumens
984 Delivered Lumens

- Emergency backup mode gives 25% illumination for up to 3 hours



87599 WTBZ, WTSN, WTWT
LED Flush Mount
15.75"W x 2.5"H
15W LED (Included)
1500 Initial Lumens
1230 Delivered Lumens




DIVERSE COLLECTION

- 3000 K color temperature
- Not recommended for 24/7 applications
- Suitable for Wet Locations

This very compact LED flush mount easily installs on any 3.25" octagon box and gives the look of a recessed trim. Constructed of die cast aluminum, this diverse luminaire is dimmable and also approved for wet location so can be used in virtually any ceiling application including showers.



87610WTWT



87610WTSN



87610WTBZ

87610 WTBZ, WTSN, WTWT

LED Flush Mount
6.5"W x 1.75"H
10W LED (Included)
1000 Initial Lumens
700 Delivered Lumens



LV STAR COLLECTION



LED STARSTRAND®

Features

- Easy to install just plug it in
- Includes AC/DC converter (no driver required)
- Warm 3000K color temperature
- Plugs directly into line voltage outlet
- Suitable for wet locations (cannot be submersed into water)
- Supplied with 1 mounting clip forevery 24"
- Field cut every 20" (cannot bereconnected)

Applications

- Cove and accent lighting
- Outdoor porch and patio
- Pathway lighting
- Backlighting of signs and displays
- Under cabinet lighting



Tape Sections:

- 53581-LVST-110V-30K-60
- 53582-LVST-110V-30K-120
- 53583-LVST-110V-30K-180
- 53584-LVST-110V-30K-240
- 53585-LVST-110V-30K-300
- 53586-LVST-110V-30K-360
- 53588-LVST-110V-30K-480
- 53590-LVST-110V-30K-600

Item	Length	Diodes	Wattage	Lumens	Color Temp	CRI	PC Board	Beam	Voltage	Current
53581	5'	90	7.2	375	3000 K	70 - 75	White	120°	110V	66mA
53582	10'	180	14.4	750	3000 K	70 - 75	White	120°	110V	132mA
53583	15'	270	21.6	1125	3000 K	70 - 75	White	120°	110V	198mA
53584	20'	360	28.8	1500	3000 K	70 - 75	White	120°	110V	264mA
53585	25'	450	36	1875	3000 K	70 - 75	White	120°	110V	330mA
53586	30'	540	43.3	2250	3000 K	70 - 75	White	120°	110V	396mA
53588	40'	720	57.6	3000	3000 K	70 - 75	White	120°	110V	528mA
53590	50'	930	74.4	3875	3000 K	70 - 75	White	120°	110V	682mA

Mounting Chips



53577

- Clips x 10 pcs
- screws x 20 pcs
- White Box Packing

INDEX

1120.....	91	6110.....	80	10206.....	67
1121.....	91	6112.....	80	10211.....	70
1123.....	91	6115.....	81	10212.....	70
1125.....	91	6117.....	81	10213.....	70
1127.....	91	6122.....	79	10214.....	70
1129.....	91	6123.....	79	11223.....	57
3250.....	94	6125.....	79	11225.....	56
3252.....	93	6126.....	79	11226.....	56
3253.....	94	9101.....	18	11228.....	55
3254.....	93	9102.....	18	11311.....	58
3320.....	98	9103.....	17	11312.....	58
3322.....	97	9104.....	17	11313.....	58
3323.....	98	9105.....	16	11314.....	58
3324.....	97	9106.....	15	20901.....	48
3340.....	96	10042.....	61,65	20902.....	48
3342.....	96	10043.....	64	20903.....	48
3343.....	95	10044.....	65	20904.....	48
3344.....	95	10045.....	64	20906.....	48
3346.....	95	10046.....	63	20907.....	46
3349.....	96	10051.....	66	20908.....	47
3800.....	100	10052.....	66	20909.....	45
3802.....	99	10053.....	66	22370.....	29
3804.....	99	10054.....	66	22371.....	29
3806.....	99	10064.....	61	22372.....	30
3809.....	100	10065.....	60	22373.....	30
5840.....	57	10066.....	59	22375.....	29
5841.....	57	10071.....	62	22376.....	28
5842.....	57	10072.....	62	22379.....	28
5849.....	57	10073.....	62	22392.....	36
6100.....	81	10074.....	62	22393.....	36
6101.....	80	10203.....	69	22395.....	36
6102.....	80	10205.....	68	22396.....	35

INDEX

22398.....	36	30725.....	19	39787.....	23
22411.....	34	32451.....	44	39788.....	23
22413.....	34	32453.....	44	39789.....	23
22414.....	34	32454.....	44	39920.....	40
22415.....	34	32455.....	43	39923.....	40
22416.....	33	32456.....	41	39924.....	38
22418.....	32	32457.....	42	39925.....	39
22419.....	31	32464.....	14	39926.....	38
24159.....	24	32466.....	13	39928.....	40
25030.....	72	32467.....	12	39929.....	39
25031.....	72	32468.....	11	53255.....	117,118
25050.....	73	33000.....	54	53577.....	123
25051.....	73	33001.....	54	53581.....	123
25070.....	74	33003.....	54	53582.....	123
25071.....	74	33004.....	54	53583.....	123
25090.....	74	33006.....	50	53584.....	123
25091.....	74	33008.....	51	53585.....	123
25116.....	76	33013.....	52	53586.....	123
25117.....	76	33014.....	53	53588.....	123
25140.....	26	35011.....	92	53590.....	123
25142.....	26	35012.....	92	54321.....	89
25144.....	26	35013.....	92	54322.....	89
25145.....	25	39740.....	10	54331.....	90
27524.....	6	39743.....	10	54332.....	90
27525.....	6	39745.....	9	85310.....	110
27527.....	6	39746.....	8	85312.....	109
27533.....	4	39747.....	7	85313.....	110
27535.....	3	39780.....	22	85315.....	109
27536.....	2	39781.....	22	85430.....	114
27537.....	1	39782.....	22	85432.....	113
30720.....	20	39783.....	22	85434.....	113
30724.....	20	39785.....	21	85436.....	113

INDEX

85439.....	114	85853.....	77	87878.....	118
85500.....	108	85855.....	77	87880.....	118
85502.....	107	86101.....	84	87885.....	118
85504.....	107	86102.....	84	88272.....	86
85506.....	107	86104.....	82	88274.....	86
85509.....	108	86106.....	82	88283.....	88
85621.....	115	86107.....	82	88285.....	88
85623.....	115	86108.....	82	88292.....	87
85625.....	115	86109.....	82	88293.....	87
85627.....	115	86110.....	83	89901.....	117
85629.....	115	86112.....	83	89902.....	117
85640.....	104	86115.....	84	89903.....	117
85642.....	104	86117.....	84	89904.....	117
85643.....	103	86122.....	85	89951.....	117
85644.....	103	86123.....	85	89952.....	117
85646.....	103	86125.....	85	89953.....	117
85649.....	104	86126.....	85	89954.....	117
85690.....	106	86128.....	83	89958.....	117
85692.....	105	86129.....	83	89962.....	118
85693.....	106	86231.....	116	89963.....	118
85694.....	105	86232.....	116	89964.....	118
85750.....	102	86234.....	116	89965.....	118
85752.....	101	87595.....	121	89966.....	118
85753.....	102	87597.....	121	90200.....	69
85754.....	101	87598.....	121	92040.....	65
85780.....	112	87599.....	121	92061.....	58,61
85782.....	111	87610.....	122	92450.....	43
85784.....	111	87615.....	119	93000.....	52
85785.....	112	87617.....	119		
85786.....	111	87620.....	119		
85788.....	112	87876.....	118		
85851.....	78	87877.....	118		

FINISH

ABZ	Architectural Bronze
ACP	Antique Copper
AE	Adobe
AL	Brushed Aluminum
AR	Anthracite
ARPN	Anthracite and Polished Nickel
BK	Black
BO	Black Oxide
BRZ	Anodized Bronze
BZ	Bronze
CF	Country Froge
CO	Copper Oxide
EB	Empire Bronze
ET	Earth Tone
GS	Golden Silver
MB	Metalic Bronze
MS	Matte Silver
NAB	Natural Aged Brass
OB	Oriental Bronze
OI	Oil Rubbed Bronze
PC	Polished Chrome
PL	Platinum
PN	Polished Nickel
SN	Satin Nickel
SST	Stainless Steel
TXB	Textured Black
UD	Uddo
WT	White

GLASS STYLES

BC	Beveled Crystal
BG	Bubble Glass
CL	Clear
FS	Frosted Seedy
FT	Frosted
LA	Lace
MSK	Mirror Smoke
SW	Satin White
WF	Weathered Frost
WG	Waterglass
WT	White











SHADES








JV	Jave
OM	Oatmeal Fabric
WT	White

REPLACEMENT BULBS

Item	Description	Type	Code	Watts	Note
BUCF-FT18-2G11-827	2700 K Twin Tube	Fluorescent	2G11	18	
BUCF-FT13-2GX7-827	Twin Tube 4 Pin 2GX7	Fluorescent	2GX7	13	2700 K Twin Tube
BUCF-CFQ13-G24Q-1-827	Quad Tube 4 Pin G24q-2 Base5.75" MOL	Fluorescent	G24q-1	13	2700 K Quad Tube
BUCF-CFQ18-G24Q-2-827	Quad Tube 4 Pin G24q-2 Base5.75" MOL	Fluorescent	G24q-2	18	2700 K Quad Tube
BUCF-CFQ26-G24Q-3-827	CFL Quad 4 Pin	Fluorescent	G24q-3	26	3000 K Quad Tube
BUF-SP13-GU24-827	CFL Bi-Pin GU24 Base	Fluorescent	GU24	13	2700 K Self-Ballasted
BUF-SP18-GU24-827	Fluorescent Low Profile Spiral	Fluorescent	GU24	18	2700K
BUF-SPLP13-GU24-827	CFL Bi-Pin GU24 Base	Fluorescent	GU24	13	2700K
BUF-SPLP18-GU24-827	CFL Bi-Pin GU24 Base	Fluorescent	GU24	18	2700K
BUF-SPLP26-GU24-827	Low Profile Spiral	Fluorescent	GU24	26	Long Shape 2700K
BUF-F8T5-827	Mini Bi-Pin Base .625" W	Fluorescent	Mini Bi-Pin T5	8	12" Long 2700K
BUF-F13T5-827	T5 Linear Mini Bi-Pin	Fluorescent	Mini Bi-Pin T5	13	21" Long 2700K
BUF-F16T5-827	T5 Linear Mini Bi-Pin	Fluorescent	T5	16	24" Long 2700K
BUF-F26T5-827	T5 Linear Mini Bi-Pin	Fluorescent	T5	26	48" Long 2700K
BUF-FC8T9-WW	T9 Circline 4 Pin Bulb	Fluorescent	Circline T9	22	2700K
BUF-FC12T9-WW	T9 Circline 4 Pin Bulb	Fluorescent	Circline T9	32	2700K
BUF-FC16T9-WW	T9 Circline 4 Pin Bulb	Fluorescent	Circline T9	40	3100K
BUH-50W-GU10-CL-120V	Halogen G10 110-130V Bulbs Clear	Halogen	GU10	50	Bulb Clear
BUI-60W-T10-E26-IF-120V	Incandescent MB	Incandescent	MB T10	60	Inside Frost
BUI-60W-ST64-E26-CL-120V	Incandescent E26 ST64 120V	Incandescent	E26	60	Bulb Clear
BUL-1.5W-G4-CL-12V		LED	G4	1.5	Bulb Clear
BUL-3W-MR16-FL-CL-12V	MR16 LED	LED		3	3000K Clear
BUL-7W-MR16-FL-CL-12V	LED MR16	LED	MR16	7	3000K Clear
BUL-1.3W-MR16-FL-CL-12V	LED GX5.3	LED	GX5.3	1.3	Bulb Clear
BUL-3.7W-MR16-FL-CL-12V	LED GX5.3	LED	GX5.3	3.7	Bulb Clear
BUL-2.9W-G9-CL-12V	Dimmable LED	LED	G9	2.9	Bulb Clear
BUL-4W-GU10-CL-120V	Dimmable LED	LED	GU10	4	Bulb Clear
BUX-20W-G8-CL-120V	Xenon Bi-Pin	Xenon	G8	20	Bulb Clear
BUX-25W-G9-CL-120V	Xenon Bi-Pin	Xenon	G9	25	Clear
BUX-40W-G9-CL-120V	Xenon Bi-Pin	Xenon	G9	40	Clear
BUX-40W-G9-FT-120V	Xenon Bi-Pin	Xenon	G9	40	Frosted
BUX-50W-G9-CL-120V	Xenon Bi-Pin	Xenon	G9	50	Clear
BUX-50W-G9-FT-120V	Xenon Bi-Pin	Xenon	G9	50	Frosted
BUX-60W-G9-CL-120V	Xenon Bi-Pin	Xenon	G9	60	Clear
BUX-60W-G9-FT-120V	Xenon Bi-Pin	Xenon	G9	60	Frosted
BUX-75W-G9-CL-120V	Xenon Bi-Pin	Xenon	G9	75	Clear
BUX-75W-G9-FT-120V	Xenon Bi-Pin	Xenon	G9	75	Frosted
BUX-18W-WEDGE-CL-12V	Xenon Wedge	Xenon		18	Bulb Clear

LAMPING

Linedrawings	Item	Type	Base	Watt	Color	Description
	BUCF-FT18-2G11-827	CF	2G11	18	SW	18W CFL 2G11 Bulb
	BUCF-FT13-2GX7-827	CF	2GX7	13	SW	13W CFL Twin 4 Pin 2GX7 Bulb 2700K
	BUCF-CFQ13-G24Q-1-827	CF	G24q-1	13	SW	13W CFL Quad 4 Pin G24q-1 Bulb 2700K
	BUCF-CFQ18-G24Q-2-827	CF	G24q-2	18	SW	18W CFL Quad 4 Pin G24q-2 Bulb 2700K
	BUCF-CFQ26-G24Q-3-827	CF	G24q-3	26	SW	26W CFL Quad 4 Pin G24q-3 Bulb 3000 K
	BUF-SP13-GU24-827	F	GU24	13	SW	13W FL Spiral GU24 Bulb 2700K
	BUF-SP18-GU24-827	F	GU24	18	SW	18W FL Spiral GU24 Bulb 2700K
	BUF-SPLP13-GU24-827	F	GU24	13	SW	13W FL Low Profile Spiral GU24 Bulb 2700K
	BUF-SPLP18-GU24-827	F	GU24	18	SW	18W FL Low Profile Spiral GU24 Bulb 2700K
	BUF-SPLP26-GU24-827	F	GU24	26	SW	26W FL Low Profile Spiral GU24 Bulb 2700K
	BUF-F8T5-827	F	T5	8	SW	8W FL T5 Linear Mini Bi-Pin Bulb 2700K
	BUF-F13T5-827	F	T5	13	SW	13W FL T5 Linear Mini Bi-Pin Bulb 2700K 21"L
	BUF-F16T5-827	F	T5	16	SW	16W FL T5 Linear Mini Bi-Pin Bulb 3500K 23.5"L
	BUF-F26T5-827	F	T5	26	SW	26W FL T5 Linear Mini Bi-Pin Bulb 3500K 41.5"L
	BUF-FC8T9-WW	F	T9	22	SW	22W FL T9 Circline 4 Pin Bulb 2700K
	BUF-FC12T9-WW	F	T9	32	SW	32W FL T9 Circline 4 Pin Bulb 2700K
	BUF-FC16T9-WW	F	T9	40	SW	40W FL T9 Circline 4 Pin Bulb 3100K
	BUH-50W-GU10-CL-120V	H	GU10	50	CL	50W Halogen GU10 110-130V Bulb Clear
	BUI-60W-T10-E26-IF-120V	I	E26	60	IF	60W Incandescent MB T10 Bulb Inside Frost
	BUI-60W-ST64-E26-CL-120V	I	E26	60	CL	60W Incandescent MB ST64 120V Bulb Clear

Linedrawings	Item	Type	Base	Watt	Color	Description
	BUL-1.5W-G4-CL-12V	L	G4	1.5	CL	1.5W LED G4 Bulb Clear
	BUL-3W-MR16-FL-CL-12V	L	G4	3	CL	3W LED MR16 3000K Bulb Clear
	BUL-7W-MR16-FL-CL-12V	L	G4	7	CL	7W LED MR16 3000K Clear
	BUL-1.3W-MR16-FL-CL-12V	L	G5.3	1.3	CL	1.3W LED GX5.3 MR16 Bulb Clear
	BUL-3.7W-MR16-FL-CL-12V	L	G5.3	3.7	CL	3.7W LED GX5.3 MR16 Bulb Clear
	BUL-2.9W-G9-CL-12V	L	G9	2.9	CL	2.9W LED G9 Bulb Clear
	BUL-4W-GU10-CL-120V	L	GU10	4	CL	4W Dimmable LED GU10 Bulb Clear
	BUX-20W-G8-CL-120V	X	G8	20	CL	20W Xenon Bi-Pin G8 Bulb Clear
	BUX-25W-G9-CL-120V	X	Xenon	25	CL	25W Xenon Bi-Pin G9 Bulb Clear
	BUX-40W-G9-CL-120V	X	Xenon	40	CL	40W Xenon Bi-Pin G9 Bulb Clear
	BUX-40W-G9-FT-120V	X	Xenon	40	FT	40W Xenon Bi-Pin G9 Bulb Frosted
	BUX-50W-G9-CL-120V	X	Xenon	50	CL	50W Xenon Bi-Pin G9 Bulb Clear
	BUX-50W-G9-FT-120V	X	Xenon	50	FT	50W Xenon Bi-Pin G9 Bulb Frosted
	BUX-60W-G9-CL-120V	X	Xenon	60	CL	60W Xenon Bi-Pin G9 Bulb Clear
	BUX-60W-G9-FT-120V	X	Xenon	60	FT	60W Xenon Bi-Pin G9 Bulb Frosted
	BUX-75W-G9-CL-120V	X	Xenon	75	CL	75W Xenon Bi-Pin G9 Bulb Clear
	BUX-75W-G9-FT-120V	X	Xenon	75	FT	75W Xenon Bi-Pin G9 Bulb Frosted
	BUX-18W-WEDGE-CL-12V	X	WEDGE	18	CL	18W Xenon Xelogen Wedge Bulb Clear

Bulb Type Glossary

CF - Compact Fluorescent
 F - Fluorescent
 H - Halogen

I - Incandescent
 L - LED
 X - Xenon

Energy Efficiency

CA California
T24 Title 24

All new homes, additions, alterations and most commercial buildings in California must meet minimum energy efficiency standards contained in Title 24, Part 6 of the California Code of Regulations. When you see the California Title 24 symbol next to a Maxim Lighting fixture, you can be assured that the fixture complies. More information on California Title 24 can be found on the California Energy Commission web site at energy.ca.gov/title24.



Dimmable using standard dimmer.
Lutron® CL dimmers are recommended

Warranty and Other Information

- For specific and detailed warranty information, ask your Maxim Lighting sales representative or visit www.maximlighting.com/warranty.
- Maxim Lighting reserves the right to change details of design, materials, colors and finishes. Color may vary from what is pictured due to limitations inherent to the photographic process.
- Always consult a qualified, licensed electrician before installation of any product weighing 35 pounds or more. We recommend that a qualified, licensed electrician do installations. Always install to a mechanically sound structure.
- Products in this supplement are UL or ETL certified. All electrical products are certified and listed to standards for use in the United States of America or Canada.
- Bulbs are not included unless otherwise noted.



CounterMax, Maxim Lighting and StarStrand are registered trademarks of Maxim Lighting International, Inc. All designs, logos, products and images © Copyright 2014 Maxim Lighting International, Inc. All Rights Reserved. Printed in China

LMXCAT1406

\$5.00



facebook.com/maximlighting



follow us @maximlighting



Get the free mobile app for your phone
<http://gettag.mobi>



Maxim Lighting International

253 North Vineland Avenue
City of Industry, California
91746
USA

General Info: 626.956.4200
Customer Service: 800.486.2946
General Fax: 626.956.4235

Dallas Trade Mart: 214.748.8455
Showroom: 3901
Email: info@maximlighting.com
Web: www.maximlighting.com

Maxim Lighting and all designs, logos and images ©2014 Maxim Lighting International. All Rights Reserved. Printed in China