



2016 CEILING FAN COLLECTION



New Fans & Accessories For 2016



LURAY ECO
CF860 - pg 42


- 60" blade span
- Integrated L.E.D. light fixture uses 17 watts
- 4.5" downrod included
- Optional no-light plate included



PENBROOKE SELECT ECO
CF5200 - pg 12



- Blades Sold Separately
- 44", 54" or 60" blade span
- Light fixture adaptable
- Accent light adaptable (AL100)
- 4.5" downrod included



KEANE
CF320 - pg 40



- 52" blade span
- 3 reversible blades
- 4.5" downrod included



VOLTA
CF590 - pg 92



- 54" blade span
- Integrated L.E.D. light kit
- 4.5" downrod included
- Optional no-light plate included



ASHLAND
CF717 - pg 110



- **New!** Medium-base light fixture with three 13-watt CFL bulbs (included)

NEW FINISH!

















G54WS White Wash - pg 135
G60CH Chocolate - pg 135
G60DM Dark Mahogany - pg 135
G60SW Satin White - pg 135
G60WA Walnut - pg 135


















VINTAGE BULB ADAPTERS
VB100 - pg 132



Transitional









 PENBROOKE SELECT ECO CF5200 - pg 12	 PENBROOKE SELECT CF5100 - pg 14	 PORTLAND ECO CF965 - pg 16	 CROFTON CF790 - pg 18	 CARRERA CF784 - pg 20	 CARRERA GRANDE ECO CF788 - pg 22
 LACLEDE ECO CF995 - pg 24	 AMHURST CF880 - pg 26	 HIGHGROVE CF990 - pg 28	 MONTEREY LUMINA CF776 - pg 30	 MONTEREY™ II CF772 - pg 32	 42" MONTEREY II CF773 - pg 33
 BRADDOCK CF440 - pg 34	 52" BELLA & 42" BELLA™ CF452/CF442 - pg 36				

Contemporary

 KEANE CF320 - pg 40	 LURAY ECO CF860 - pg 42	 AIRA ECO CF985 - pg 44	 SOUTHTOWNE CF4900 - pg 46	 HIGHRISE CF430 - pg 48	 4TH AVENUE CF766 - pg 50
 MIDWAY ECO CF955 - pg 52	 LUXE ECO CF550 - pg 54	 HIGHPOINTE CF205 - pg 56	 LOFT CF765 - pg 58	 52" & 44" CURVA SKY™ CF152/CF144 - pg 60	 52" & 44" CURVA™ CF252/CF244 - pg 62
 ATOMICAL CF930 - pg 64	 VELOCE CF230 - pg 66	 TILO CF130 - pg 67			

Classic









 MONACO CF830 - pg 70	 CROWN SELECT CF4501 - pg 72	 CORNERSTONE CF1 - pg 74	 ZURICH CF935 - pg 75
--	--	--	---

-  **ECOMOTOR**
-  **K55 MOTOR**
-  **BLADE SELECT SERIES**
-  **ENERGY STAR LISTED**
-  **L.E.D. LIGHT FIXTURE ADAPTABLE**
-  **INTEGRATED L.E.D. LIGHTING**
-  **DAMP LOCATION RATED***
-  **WET LOCATION RATED***











*Certain finishes only. See fan pages for details

Specifications and product availability subject to change without notice. For up to date information go to emersonfans.com.










Traditional

 AVANT ECO CF921 - pg 78	 PREMIUM SELECT CF4801 - pg 80	 PRIMA CF901 - pg 82	 DESIGNER CF755 - pg 84
 29" NORTHWIND CF702 - pg 86	 PRIMA SNUGGER CF905 - pg 87	 52" SNUGGER CF805S - pg 88	 SNUGGER CF804S - pg 89

Indoor/Outdoor

 VOLTA CF590 - pg 92	 WELLAND CF610 - pg 94	 BATALIE BREEZE CF621 - pg 96	 MAUI BAY CF2000 - pg 98	 SUMMERHAVEN CF850 - pg 100	 52" & 42" VERANDA CF552/CF542 - pg 102
 DEVONSHIRE CF670 - pg 104	 SEA BREEZE CF654 - pg 105	 52" SUMMER NIGHT CF652 - pg 106	 42" SUMMER NIGHT CF742PF - pg 107		

Pro Series

 ASHLAND UPDATED! CF717 - pg 110	 PRO SERIES CF712 - pg 112	 PRO SERIES ES CF713 - pg 114	 50" PRO SERIES II CF711 - pg 116	 42" PRO SERIES II CF710 - pg 118	 BUILDER CF700 - pg 120
 60" INDUSTRIAL FAN HF1160 - pg 122	 56" INDUSTRIAL FAN HF956 - pg 122	 48" INDUSTRIAL FAN HF948 - pg 122			

Accessories

 L.E.D. LIGHT FIXTURES pg 126	 CUSTOM FINISH LIGHT FIXTURES pg 128	 LIGHT FIXTURES & FITTERS pg 130	 2 1/4" GLASS pg 133	 BLADE SELECT SERIES BLADES pg 134	 CONTROLS pg 136
 FINISHES & DOWNRODS pg 5	<ul style="list-style-type: none"> · Installation Guide - pg 8-9 · Fan Specifications - pg 142-145 				

WHEN ENERGY MATTERS...



ECOMOTOR®

Look for this logo for fans that carry Emerson's most energy efficient motor



- Up to 3 times more efficient than typical ceiling fan motors - costs less than 1¢ per hour to run.
- Uses a maximum of 33 watts of energy
- Drives higher degree blade pitch more efficiently
- Built-in electronics with 6-speed control with every fan
- EcoMotor fans, which are also part of our Blade Select Series, are adaptable to 42/44", 52/54", 58/60" or 70/72" fans for added versatility & quiet operation*



* Some blade restrictions apply. Please refer to individual product pages for more information.

WHEN POWER MATTERS...

K55 K55XL MOTOR

Look for this logo for fans that carry Emerson's excellent power & performance motor



- The largest steel ball bearings in the ceiling fan industry ensure quiet operation
- Thick motor laminations and over 2200 feet of quality copper wiring for optimal performance and longevity
- The patented K55XL Silent Rubber Hub works as a shock absorber to isolate the blades and eliminate noise transmission.



FINISHES / DOWNRODS



NEW FINISH!
PT - Platinum

Complete catalog number by selecting your downrod length, then adding the finish code to the model number



- 1. Choose downrod length**
- 2.5" = CFDR25¹
 - 12" = CFDR1
 - 18" = CFDR18
 - 24" = CFDR2
 - 36" = CFDR3
 - 48" = CFDR4
 - 60" = CFDR5
 - 70" = CFDR70
- 2. Choose downrod finish**
- See chart below for finish color codes



WW - Appliance White



SW - Satin White



AW - Summer White



AP - Antique Pewter



BS - Brushed Steel



VS - Vintage Steel



AB - Antique Brass



ORB - Oil Rubbed Bronze



GBZ - Gilded Bronze



VNB - Venetian Bronze



GES - Golden Espresso



BQ - Barbeque Black

BLADE SELECT SERIES

- Step 1 CHOOSE YOUR FAN  Step 2 CHOOSE YOUR FINISH  Step 3 CHOOSE YOUR BLADE 

Your style, hundreds of possibilities

6 Fan Models

8 Finishes

50+ Blade Options



Penbrooke Select Eco*
CF5200 - pg 12




Penbrooke Select*
CF5100 - pg 14



Carrera Grande Eco
CF788 - pg 22



Crown Select*
CF4501 - pg 72



Avant Eco*
CF921 - pg 78



Premium Select*
CF4801 - pg 80

* Some restrictions apply - See product pages for details.



Patented Sloped Ceiling Kit

CFSCKXXX - SLOPED CEILING KIT (Up to 45°)

- For use on cathedral and sloped ceilings up to 45°
- Features a screw-in safety strap to lock the hanger ball in place
- Complete catalog number by adding the finish code to the model number. See chart above.
- Shown in WW. Also available in AB, AP, AW, BQ, BS, GBZ, GES, ORB, SW, VNB and VS
- For use with horseshoe receivers: RC188 and RCK55

Note: Our standard hanging system can be used for sloped ceilings up to 26° and 5/12 pitch ceiling.



Close-To-The-Ceiling Downrod

CFDR25 - CLOSE-TO-THE-CEILING DOWNRODS

- 2½" downrod allows fans to be installed closer to the ceiling
- (In most instances you will save at least 2" of space if you bring your fan closer to the ceiling)
- Shown in WW. Also available in AB, AP, AW, BQ, BS, GBZ, GES, ORB, SW, VNB, and VS

CFDC - DOWNROD COUPLER

- Connect 2 or more downrods for taller ceiling applications.



Shown in BS. Also available in AB, AP, AW, BQ, GBZ, GES, ORB, SW, VNB, VS and WW

Emerson's Commitment To Quality

Higher Motor Standards



153 mm Motor
AIRFLOW:
GOOD



172 mm Motor
AIRFLOW:
GOOD



188 mm Motor
AIRFLOW:
VERY GOOD



K55 XL Motor
AIRFLOW:
EXCELLENT



EcoMotor
AIRFLOW:
EXCELLENT



EMERSON VS. TYPICAL RETAIL:

- Quieter
- Higher quality bearings
- Stricter sound testing criteria
- Flatter laminations to prevent motor buzz noise
- Lifetime Motor Warranty
- Higher grade materials
- Precision-machined motor endshields
- More quality checkpoints for defect-free motors

How We Test Air Flow

Emerson tests every ceiling fan to standardized industry testing parameters. The CFM data (Cubic Feet per Minute) is printed on every fan carton and in every catalog. This is what the user feels when beneath the fan. CFM is an objective approach to making competitive comparisons.

Blade pitch, RPM (revolutions per minute), blade length and overall design are used to maximize CFM. CFM is the true measure of air flow.



Visit MyEmersonFans.com/Videos to view professional, highly-detailed videos about the features of many of our fans and accessories, and learn valuable installation tips and instructions.

While browsing our collections, look for these special features:



Choose from 6 fan models, 8 finishes and 50+ blade options



Emerson's most energy efficient fan motor



Emerson's excellent power and performance fan motor



Fans rated for use in covered outdoor areas



Fans rated for use in outdoor areas directly exposed to precipitation



Fans that earned an Energy Star listing for superb energy efficiency



Emerson's most efficient and longest-lasting lighting



Emerson's newest line of L.E.D. LK GLO Light Fixtures (pg 126) can be added to these Emerson fans as an optional accessory



Fans built with special features for easy, time-saving installation



Fans and compatible optional accessories that can be ordered and shipped to Canada



Fans that can be ordered and shipped to Canada but not with all compatible optional accessories



Measurement of a fan model from its lowest point to its highest



Fans that come with integrated accent lighting



An accent lighting fixture can be added to these Emerson Fans as an optional accessory



Have a question?
Contact Customer Service
1-800-237-6511
FanCS@emerson.com



LIMITED LIFETIME MOTOR WARRANTY



LIMITED 2 YEAR MOTOR WARRANTY



LIMITED 5 YEAR MOTOR WARRANTY

We're so confident our fans will last for years to come that we've backed them with Emerson's Limited Lifetime Motor Warranty. Industrial fans carry Emerson's 2 or 5 year Limited Motor Warranty.

Installation

Installation Information

STANDARD 8 FOOT CEILINGS

Most Emerson fans are designed to fit a standard eight-foot ceiling, which puts the blades seven feet from the floor for the best air movement and clearance.

CEILING HEIGHTS LESS THAN 8 FEET

Choose an Emerson Snugger model to achieve the desired seven-foot blade clearance or consider a close-to-the-ceiling downrod (CFDR25). See pg 5 for model compatibility.

CEILING HEIGHTS ABOVE 8 FEET


To maximize air movement, the fan should be hung by a downrod eight or nine feet from the floor. If necessary, order an accessory downrod to achieve the proper length. See the Accessory Downrod chart at the top of pg 5.

WARRANTY


All Emerson fans, except Industrial Fans, carry a limited lifetime motor warranty.

HANGING SYSTEM


All Emerson residential ceiling fans feature a die-cast zinc hanging ball and bracket for durability. This system is textured to minimize wobble and provide superior stability. Emerson heat fans feature a J-hook hanging system for easy installation and smooth performance.



MATCH DOWNROD LENGTH TO CEILING HEIGHT



If your ceiling fan has a light kit, reduce the length of the downrod by 12"




Installation

Choose The Right Fan To Fit Your Room


To maximize performance, choose the right fan size for your room. For long or large rooms, consider more than one fan to handle your cooling requirements. For maximum comfort, the fan should be placed as close to the center of the room as possible and blade tips should be at least 18 inches from any wall.

Recommended blade span for room size based on aesthetic & airflow considerations




Room size (in square feet)

ENERGY SAVINGS CREATED BY THE ADDITION OF A CEILING FAN



Ceiling fans create a wind chill effect that can make a room feel cooler, allowing the user to raise his or her thermostat setting by 4°, resulting in a reduction of overall energy usage costs.



Setting a ceiling fan to rotate clockwise at a low speed during the winter will also create energy savings. This warms the entire room by mixing the warm air sitting at the ceiling with the cooler air at the bottom of the room.

Room Without a Ceiling Fan



Higher energy usage cost



Room With a Ceiling Fan



Reduced energy usage cost

Penbrooke Select
Eco
CF5200 - pg 12



TRANSITIONAL DESIGN



PENBROOKE SELECT ECO
CF5200 - pg 12



PENBROOKE SELECT
CF5100 - pg 14



PORTLAND ECO
CF965 - pg 16




CROFTON
CF790 - pg 18



CARRERA
CF784 - pg 20



CARRERA GRANDE ECO
CF788 - pg 22



LACLEDE ECO
CF995 - pg 24



AMHURST
CF880 - pg 26



HIGHGROVE
CF990 - pg 28



MONTEREY LUMINA
CF776 - pg 30



MONTEREY II
CF772 - pg 32









42" MONTEREY II
CF773 - pg 33



BRADDOCK
CF440 - pg 34



52" BELLA & 42" BELLA™
CF452/CF442 - pg 36


-  **ECOMOTOR**
-  **K55 MOTOR**
-  **ENERGY STAR LISTED**
-  **DAMP LOCATION RATED**
-  **BLADE SELECT SERIES**
-  **L.E.D. LIGHT FIXTURE ADAPTABLE**

*Certain finishes only. See fan pages for details.

NEW!

Penbrooke Select Eco

Penbrooke Select Eco Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt	13.0" FAN HEIGHT
7400*	32*	231.3*	

*Estimated. Visit our website at emersonfans.com for up-to-date information.



- Blades Sold Separately
- 44", 54", 60" or 72" blade span
- Light fixture adaptable
- Accent light adaptable (AL100)
- 4.5" downrod included

Shown with accessory Riley L.E.D. Light Fixture (LK180LEDBS, pg 127), 25" Dark Mahogany Solid Wood Blades (B78DM, pg 134) & accessory 12" downrod



A. Penbrooke Select Eco - Brushed Steel CF5200BS

Shown with accessory 22" Satin White Blades (G54SW, pg 135)



B. Penbrooke Select Eco -Satin White CF5200SW

A. PENBROOKE SELECT ECO- BRUSHED STEEL

CF5200BS - Blade Select Series

- 4.5" downrod included
- Light fixture & accent light adaptable
- SW605 Wall Control
- Blades sold separately (see pg 134-135)

B. PENBROOKE SELECT ECO - SATIN WHITE

CF5200SW - Blade Select Series

- 4.5" downrod included
- Light fixture & accent light adaptable
- SW605 Wall Control
- Blades sold separately (see pg 134-135)

C. PENBROOKE SELECT ECO- OIL RUBBER BRONZE

CF5200BS - Blade Select Series

- 4.5" downrod included
- Light fixture & accent light adaptable
- SW605 Wall Control
- Blades sold separately (see pg 134-135)



Look for this logo for fans that carry Emerson's Most Energy Efficient Motor - **The EcoMotor**

- Up to 3 times more efficient than typical ceiling fan motors - costs less than 1¢ per hour to run
- CF5200 EcoMotor only uses a maximum of 33 watts of energy
- Built-in electronics with 6-speed control with every fan
- Proven design for reliable & quiet operation



Emerson EcoMotor®

See pg 4 for more information.



Penbrooke Select Eco

Shown with accessory 22" Heritage Walnut Blades (G54HWA, pg 135), Four-Light Arm Fitter (F440, pg 132), and Vintage Bulb Adapters (VB100, pg 132). Bulbs not included

C. Penbrooke Select Eco - Oil Rubbed Bronze CF5200ORB



your style, hundreds of possibilities...

For the Complete Blade Select Lineup Turn to Page 134

Included:



SW605 Wall Control

Sold Separately:




BLADE SELECT SERIES BLADES* pg 134-135



LK GLO SERIES L.E.D. LIGHT FIXTURE pg 126-127



AL100 OPTIONAL ACCENT Light Accessory



SR600 Remote Control

* B79 Blades not recommended for use on the CF5200.

Penbrooke Select

Penbrooke Select Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
6222	98	63

13.0"
FAN HEIGHT

- Blades Sold Separately
- 44", 54" or 60" blade span
- Light fixture adaptable
- Accent light adaptable (AL100)
- 4.5" downrod included



BLADE SELECT
SERIES



**OPTIONAL
ACCENT
LIGHTING**



K55 MOTOR



**L.E.D. LIGHT
FIXTURE ADAPTABLE**



SHIPS TO CANADA



**LIMITED LIFETIME
MOTOR WARRANTY**

Shown with accessory 22" Walnut Solid Wood Blades (B77WA, pg 134)



A. Penbrooke Select - Oil Rubbed Bronze CF5100ORB

Shown with accessory 22" Satin White Blades (G54SW, pg 135)



B. Penbrooke Select - Satin White CF5100SW

Shown with accessory Riley L.E.D. Light Fixture (LK180LEDBS, pg 127), 25" Dark Mahogany Solid Wood Blades (B78DM, pg 134) & accessory 12" downrod



C. Penbrooke Select - Brushed Steel CF5100BS

Shown with accessory 22" Vintage Walnut Hand Carved Rattan Blades (B102VWA, pg 135)



D. Penbrooke Select - Venetian Bronze CF5100VNB

A. PENBROOKE SELECT – OIL RUBBED BRONZE

- CF5100ORB** - Blade Select Series
- 4.5" downrod included
 - Light fixture & accent light adaptable
 - "Smooth" & pull chain switchcup
 - Blades sold separately (see pg 134-135)

B. PENBROOKE SELECT – SATIN WHITE

- CF5100SW** - Blade Select Series
- 4.5" downrod included
 - Light fixture & accent light adaptable
 - "Smooth" & pull chain switchcup
 - Blades sold separately (see pg 134-135)

C. PENBROOKE SELECT – BRUSHED STEEL

- CF5100BS** - Blade Select Series
- 4.5" downrod included
 - Light fixture & accent light adaptable
 - "Smooth" & pull chain switchcup
 - Blades sold separately (see pg 134-135)

D. PENBROOKE SELECT – VENETIAN BRONZE

- CF5100VNB** - Blade Select Series
- 4.5" downrod included
 - Light fixture & accent light adaptable
 - "Smooth" & pull chain switchcup
 - Blades sold separately (see pg 134-135)

E. PENBROOKE SELECT – VINTAGE STEEL

- CF5100VS** - Blade Select Series
- 4.5" downrod included
 - Light fixture & accent light adaptable
 - "Smooth" & pull chain switchcup
 - Blades sold separately (see pg 134-135)



For the Complete Blade Select Lineup
Turn to Page 134



Penbrooke Select

Shown with accessory 22" Heritage Walnut Blades (G54HWA, pg 135)



E. Penbrooke Select - Vintage Steel CF5100VS

Included:



"SMOOTH" AND
PULL CHAIN
SWITCHCUPS²

Sold Separately:



**BLADE SELECT
SERIES BLADES**
pg 134-135



**LK GLO SERIES
L.E.D. LIGHT FIXTURE**
pg 126-127



**AL100
OPTIONAL
ACCENT
Light Accessory**



SR600
Remote Control



SW605
Wall Control



RCK55
Horseshoe
Receiver

¹ B79 Blades not recommended for use on the CF5100.

² Installation option for use with accessory control and transmitter. Secondary switch cup does not have pull chain or reverse switch holes.

Portland Eco

Portland Eco Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
6389	33.5	190.7

12.0"
FAN HEIGHT

- 54" blade span
- Integrated light fixture uses three 50-watt halogen bulbs (included)
- Accent Light adaptable (AL100)
- 4.5" downrod included



ECOMOTOR®



**OPTIONAL
ACCENT
LIGHTING**



SHIPS TO CANADA



**LIMITED LIFETIME
MOTOR WARRANTY**

View videos about Portland Eco's features and installation at MyEmersonFans.com/Videos



Shown with Walnut Blades

A. **Portland Eco - Brushed Steel** CF965BS
Dark Mahogany/Walnut Blades



Shown with Dark Mahogany Blades

B. **Portland Eco - Venetian Bronze** CF965VNB
Dark Mahogany/Walnut Blades



Look for this logo for fans that carry Emerson's Most Energy Efficient Motor - **The EcoMotor®**

- Up to 3 times more efficient than typical ceiling fan motors - costs less than 1¢ per hour to run
- CF965 EcoMotor only uses a maximum of 33 watts of energy
- Drives higher degree blade pitch more efficiently
- Built-in electronics with 6-speed control with every fan
- Proven design for reliable & quiet operation



Emerson EcoMotor®

See pg 4 for more information.

- A. **PORTLAND ECO - BRUSHED STEEL** CF965BS - Dark Mahogany/Walnut Blades, Opal Matte Glass
- 5 reversible blades
 - Integrated light fixture
 - Accent light adaptable
 - SW605 wall control
 - 4.5" downrod included

- B. **PORTLAND ECO - VENETIAN BRONZE** CF965VNB - Dark Mahogany/Walnut Blades, Opal Matte Glass
- 5 reversible blades
 - Integrated light fixture
 - Accent light adaptable
 - SW605 wall control
 - 4.5" downrod included

Included:



FIVE REVERSIBLE BLADES



INTEGRATED LIGHT FIXTURE



SW605
Wall Control

Sold Separately:



SR600
Remote Control



AL100
Optional Accent Light Accessory

Crofton

Crofton Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
6445	77.6	83.1

13.2"
FAN HEIGHT

- 58" blade span
- Light fixture adaptable
- 4.5" downrod included

L.E.D. LIGHT
FIXTURE ADAPTABLE

SHIPS TO CANADA

LIMITED LIFETIME
MOTOR WARRANTY

View videos about Crofton's
features and installation at
MyEmersonFans.com/Videos

Shown with
Walnut Blades



A. Crofton - Venetian Bronze CF790VNB
Dark Mahogany/Walnut Blades



Shown with
Dark Mahogany Blades



B. Crofton - Brushed Steel CF790BS
Dark Mahogany/Walnut Blades



Shown with
Satin White Blades



C. Crofton - Satin White CF790SW
Satin White/Maple Blades



Included:



FIVE
REVERSIBLE
BLADES



SW405
Wall Control
with Receiver

Sold Separately:



LK GLO SERIES
L.E.D. LIGHT FIXTURE
pg 126-127



SR400
Remote Control
with Receiver

Shown with Riverwash Blades



D. Crofton - Vintage Steel CF790VS
Riverwash/Walnut Blades



Carrera®

Carrera Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
7510	94	79

14.5"
FAN HEIGHT

- 60" blade span
- Light fixture adaptable
- 4.5" downrod included



DAMP LOCATION²
RATED

L.E.D. LIGHT
FIXTURE ADAPTABLE

SHIPS TO CANADA
FAN ONLY

LIMITED LIFETIME
MOTOR WARRANTY



View videos about Carrera's
features and installation at
MyEmersonFans.com/Videos

Carrera

Shown with Walnut Blades &
accessory 12" downrod



B. Carrera - Oil Rubbed Bronze CF784ORB
Dark Mahogany/Walnut Blades

Shown with Satin White Blades
& accessory 12" downrod



C. Carrera - Satin White CF784SW
Satin White/Maple Blades

Shown with Chocolate Blades
& accessory 12" downrod



D. Carrera - Golden Espresso CF784GES
Dark Cherry/Chocolate Blades

A. Carrera - Brushed Steel CF784BS
Dark Mahogany/Walnut Blades

Shown with Walnut Blades





- A. **CARRERA – BRUSHED STEEL**
CF784BS - Dark Mahogany/Walnut Blades
 - Light fixture adaptable
 - 4.5" downrod included
- B. **CARRERA – OIL RUBBED BRONZE**
CF784ORB - Dark Mahogany/Walnut Blades
 - Light fixture adaptable
 - 4.5" downrod included
- C. **CARRERA – SATIN WHITE**
CF784SW - Satin White/Maple Blades
 - Light fixture adaptable
 - 4.5" downrod included
- D. **CARRERA – GOLDEN ESPRESSO**
CF784GES - Chocolate/Dark Cherry Blades
 - Light fixture adaptable
 - 4.5" downrod included

Included:



FIVE
REVERSIBLE
BLADES




"SMOOTH" AND
PULL CHAIN
SWITCHCUPS¹

Sold Separately:



LK GLO SERIES
L.E.D. LIGHT FIXTURE
pg 126-127



SR600
Remote Control
with Receiver



RC188
Horseshoe
Receiver

¹ Installation option for use with accessory control and transmitter.
Secondary switch cup does not have pull chain or reverse switch holes.

Carrera Grande® Eco

Carrera Grande® Eco Energy Ratings at High Speed

Airflow Cubic Ft. Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft. Per Min. Per Watt
7930	29.9	265



FAN HEIGHT

- Blades sold separately
- 44", 54", 60" or 72" blade span
- Light fixture adaptable
- 4.5" downrod included

BLADE SELECT
SERIES

ECOMOTOR®

ENERGY STAR

DAMP LOCATION²
RATED

L.E.D. LIGHT
FIXTURE ADAPTABLE

SHIPS TO CANADA
FAN ONLY

LIMITED LIFETIME
MOTOR WARRANTY

Shown with accessory 25" Hand Carved Classic Vintage Black Blades (B90VBL, pg 142) & accessory Riley L.E.D. Light Fixture (LK180LEDGES, pg 135)

Carrera Grande Eco



Shown with accessory 22" Dark Oak Hand Carved Blades (B100DO, pg 135)

A. Carrera Grande Eco - Gilded Bronze CF788GBZ

- A. CARRERA GRANDE ECO – GILDED BRONZE CF788GBZ** - Blade Select Series
- Blades sold separately
 - 6-Speed wall control with receiver
 - Light fixture adaptable
 - 4.5" downrod included



Shown with accessory 25" Solid Wood Satin White Blades (B78SW, pg 134)

B. Carrera Grande Eco - Satin White CF788SW

- B. CARRERA GRANDE ECO – SATIN WHITE CF788SW** - Blade Select Series
- Blades sold separately
 - 6-Speed wall control with receiver
 - Light fixture adaptable
 - 4.5" downrod included

- C. CARRERA GRANDE ECO – VENETIAN BRONZE CF788VNB** - Blade Select Series
- Blades sold separately
 - 6-Speed wall control with receiver
 - Light fixture adaptable
 - 4.5" downrod included



Shown with accessory 22" Honey Oak Blades (G54HO, pg 135)

C. Carrera Grande Eco - Venetian Bronze CF788VNB

- D. CARRERA GRANDE ECO – ANTIQUE PEWTER² CF788AP** - Blade Select Series
- Blades sold separately
 - 12" downrod (CFDR1AP)
 - 6-Speed wall control with receiver
 - Light fixture adaptable
 - 4.5" downrod included

- E. CARRERA GRANDE ECO – OIL RUBBED BRONZE CF788ORB** - Blade Select Series
- Blades sold separately
 - 6-Speed wall control with receiver
 - Light fixture adaptable
 - 4.5" downrod included

- F. CARRERA GRANDE ECO – GOLDEN ESPRESSO CF788GES** - Blade Select Series
- Blades sold separately
 - 6-Speed wall control with receiver
 - Light fixture adaptable
 - 4.5" downrod included

ULTRA ENERGY EFFICIENT!



Look for this logo for fans that carry Emerson's Most Energy Efficient Motor - **The EcoMotor®**

- Up to 3 times more efficient than typical ceiling fan motors - costs less than 1¢ per hour to run
- CF788 EcoMotor only uses a maximum of 33 watts of energy
- Drives higher degree blade pitch more efficiently
- Built-in electronics with 6-speed control with every fan
- Proven design for reliable & quiet operation



Emerson EcoMotor®

See pg 4 for more information.

Included:



6-Speed
Wall Control
with Receiver²

Sold Separately:



SR650
Remote
Control³




SR600
Remote
Control³



LK GLO SERIES
L.E.D. LIGHT FIXTURE
pg 126-127



BLADE SELECT
SERIES BLADES
pg 134-135



BLADE SELECT
SERIES



*your style,
hundreds of possibilities...*

For the Complete Blade Select Lineup Turn to Page 134

¹ Energy Star testing completed with B78 blade series.
² Damp Location rated for GES, SW, VNB, GBZ & ORB finishes only. AP finish not suitable for Damp Locations.
³ Controls are recommended for indoor use only.



Shown with accessory 31" Chocolate Solid Wood Blades (B79CH, pg 134) & accessory 12" Downrod

D. Carrera Grande Eco - Antique Pewter CF788AP²



Shown with accessory 22" Riverwash Blades (G54RW, pg 135)

E. Carrera Grande Eco - Oil Rubbed Bronze CF788ORB

Laclede Eco

Laclede Eco Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
6381	30	212

20.0"
FAN HEIGHT



- 62" blade span
- Integrated light fixture uses five 13-watt medium base compact fluorescent bulbs (included) and the accent light uses four 13-watt medium base compact fluorescent bulbs (included)
- 10" downrod included

Shown with Dark Mahogany Blades



A. **Laclede Eco - Brushed Steel** CF995BS
Charcoal Gray/Dark Mahogany Blades, Opal Matte Glass

Shown with Charcoal Blades



A. **Laclede Eco - Brushed Steel** CF995BS
Charcoal Gray/Dark Mahogany Blades, Opal Matte Glass

Shown with Walnut Blades



B. **Laclede Eco - Venetian Bronze** CF995VNB
Dark Mahogany/Walnut Blades, Vintage Cream Glass



Look for this logo for fans that carry Emerson's Most Energy Efficient Motor - **The EcoMotor®**

- Up to 3 times more efficient than typical ceiling fan motors - costs less than 1¢ per hour to run
- CF995 EcoMotor only uses a maximum of 33 watts of energy
- Drives higher degree blade pitch more efficiently
- Built-in electronics with 6-speed control with every fan
- Proven design for reliable & quiet operation




Emerson EcoMotor®

See pg 4 for more information.

- A. **LACLEDE ECO - BRUSHED STEEL**
CF995BS - Charcoal Gray/Dark Mahogany Blades, Opal Matte Glass
- Integrated light fixture & accent light
 - 10" downrod included
 - 5 reversible blades
 - SR600 remote control
 - Removable decorative sleeve
- B. **LACLEDE ECO - VENETIAN BRONZE**
CF995VNB - Reversible Dark Mahogany/Walnut Blades, Vintage Cream Glass
- Integrated light fixture & accent light
 - 10" downrod included
 - 5 reversible blades
 - SR600 remote control
 - Removable decorative sleeve

B. **Laclede Eco - Venetian Bronze** CF995VNB
Dark Mahogany/Walnut Blades, Vintage Cream Glass

Included:



FIVE REVERSIBLE BLADES



REMOVABLE DECORATIVE SLEEVE



SR600
Remote Control

Sold Separately:



SW605
Wall Control

Laclede Eco

Shown with Dark Mahogany Blades



Amhurst Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
5422	67	80

15.1"
FAN HEIGHT

SHIPS TO CANADA LIMITED LIFETIME MOTOR WARRANTY

- 54" blade span
- Integrated light fixture uses two 60-watt candelabra bulbs (included)
- 4.5" downrod included




Shown with Dark Cherry Blades



Shown with Chocolate Blades

A. Amhurst - Brushed Steel CF880BS
Dark Cherry/Chocolate Blades, Opal Matte Glass



Shown with Dark Cherry Blades



Shown with Riverwash Blades

B. Amhurst - Vintage Steel CF880VS
Riverwash/Walnut Blades, Cream Bubble Glass



Walnut Blades shown




Shown with Honey Oak Blades


C. Amhurst - Venetian Bronze CF880VNB
Dark Cherry/Honey Oak Blades, Cream Bubble Glass

- A. **AMHURST - BRUSHED STEEL**
CF880BS - Dark Cherry/Chocolate Blades, Opal Matte Glass
- Integrated light fixture
 - 5 reversible blades
 - SW405 wall control with receiver
 - 4.5" downrod included
- B. **AMHURST - VINTAGE STEEL**
CF880VS - Riverwash/Walnut Blades, Cream Bubble Glass
- Integrated light fixture
 - 5 reversible blades
 - SW405 wall control with receiver
 - 4.5" downrod included
- C. **AMHURST - VENETIAN BRONZE**
CF880VNB - Dark Cherry/Honey Oak Blades, Cream Bubble Glass
- Integrated light fixture
 - 5 reversible blades
 - SW405 wall control with receiver
 - 4.5" downrod included


Included:



FIVE REVERSIBLE BLADES




INTEGRATED LIGHT FIXTURE



SW405 Wall Control with Receiver

Sold Separately:



SR401 Remote Control



Highgrove

Highgrove - Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
5116	62	81

15.0"
FAN HEIGHT



OPTIONAL
ACCENT
LIGHTING

SHIPS TO CANADA

LIMITED LIFETIME
MOTOR WARRANTY

- 53" blade span
- Integrated light fixture uses two 50-watt halogen mini-candelabra base bulbs (included)
- Accent light adaptable (AL100)
- 4.5" downrod included

A. Highgrove - Brushed Steel CF990BS
Dark Mahogany Blades, Opal Matte Glass



B. Highgrove - Venetian Bronze CF990VNB
Walnut Blades, Vintage Cream Glass

- A. HIGHGROVE - BRUSHED STEEL
CF990BS - Dark Mahogany Blades, Opal Matte Glass
- Integrated light fixture
 - Accent light adaptable (AL100)
 - 5 blades
 - SR400 remote control
 - 4.5" downrod included

- B. HIGHGROVE - VENETIAN BRONZE
CF990VNB - Walnut Blades, Vintage Cream Glass
- Integrated light fixture
 - Accent light adaptable (AL100)
 - 5 blades
 - SR400 remote control
 - 4.5" downrod included

Included:



FIVE
BLADES



INTEGRATED
LIGHT
FIXTURE




SR400
Remote Control
with receiver

Sold Separately:



SW406
Wall Control



SR600*
Remote Control



SW605*
Wall Control



AL100
OPTIONAL
ACCENT*
Light Accessory



RC188*
Horseshoe
Receiver

* If an AL100 Optional Accent Light is purchased, SR600 or SW605, must be used to control the accent light and the downlight separately. Please note that the SR400 (included) or the SW405/SW406 will operate the accent light and downlight simultaneously. The SR600 and SW605 require the installation of the RC188.



Monterey Lumina

Monterey Lumina Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
5625	70	79

19.1"
FAN HEIGHT

- 52" blade span
- Low Profile light fixture uses three 60-watt candelabra bulbs (included)
- 4.5" downrod included

SHIPS TO CANADA LIMITED LIFETIME MOTOR WARRANTY



Shown with Dark Cherry Blades

A. Monterey Lumina - Brushed Steel CF776BS
Dark Cherry/Dark Mahogany Blades, Opal Matte Light Fixture



Shown with Dark Cherry Blades

B. Monterey Lumina - Oil Rubbed Bronze CF776ORB
Dark Cherry/Walnut Blades, Amber Mist Light Fixture




Shown with Satin White Blades

C. Monterey Lumina - Satin White CF776SW
Satin White/Maple Blades, Opal Matte Light Fixture




- A. **MONTEREY LUMINA – BRUSHED STEEL CF776BS** - Dark Cherry/Dark Mahogany Blades, Opal Matte Light Fixture
 - 5 reversible blades
 - Low profile light fixture
 - 4.5" downrod included
- B. **MONTEREY LUMINA – OIL RUBBED BRONZE CF776ORB** - Dark Cherry/Walnut Blades, Amber Mist Light Fixture
 - 5 reversible blades
 - Low profile light fixture
 - 4.5" downrod included
- C. **MONTEREY LUMINA – SATIN WHITE CF776SW** - Satin White/Maple Blades, Opal Matte Light Fixture
 - 5 reversible blades
 - Low profile light fixture
 - 4.5" downrod included

Included:



Sold Separately:



52" Monterey II

52" Monterey II Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
5625	70	79

15.0"
FAN HEIGHT

L.E.D. LIGHT FIXTURE ADAPTABLE SHIPS TO CANADA LIMITED LIFETIME MOTOR WARRANTY

- 52" blade span
- Light fixture adaptable
- 4.5" downrod included

Monterey II

42" Monterey II

42" Monterey™ II Energy Ratings at High Speed


Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
3556	47	75

15.0"
FAN HEIGHT

L.E.D. LIGHT FIXTURE ADAPTABLE SHIPS TO CANADA LIMITED LIFETIME MOTOR WARRANTY

- 42" blade span
- Light fixture adaptable
- 4.5" downrod included

42" Monterey II



Shown with Dark Cherry Blades

A. Monterey II - Oil Rubbed Bronze CF772ORB
Dark Cherry/Walnut Blades



Shown with Dark Cherry Blades

B. Monterey II - Brushed Steel CF772BS
Dark Cherry/Dark Mahogany Blades



Shown with Satin White Blades

C. Monterey II - Satin White CF772SW
Satin White/Maple Blades



A. MONTEREY II – OIL RUBBED BRONZE CF772ORB - Dark Cherry/Walnut Blades

- 5 reversible blades
- Light fixture adaptable
- 4.5" downrod included

B. MONTEREY II – BRUSHED STEEL CF772BS - Dark Cherry/Dark Mahogany Blades

- 5 reversible blades
- Light fixture adaptable
- 4.5" downrod included

C. MONTEREY II – SATIN WHITE CF772SW - Satin White/Maple Blades

- 5 reversible blades
- Light fixture adaptable
- 4.5" downrod included



Shown with Walnut Blades

D. 42" Monterey II - Brushed Steel CF773BS
Dark Cherry/Dark Mahogany Blades



Shown with Walnut Blades

E. 42" Monterey II - Oil Rubbed Bronze CF773ORB
Dark Cherry/Walnut Blades



Shown with Satin White Blades

F. 42" Monterey II - Satin White CF773SW
Satin White/Maple Blades



D. 42" MONTEREY II – BRUSHED STEEL CF773BS - Dark Cherry/Dark Mahogany Blades

- 5 reversible blades
- Light fixture adaptable
- 4.5" downrod included


E. 42" MONTEREY II – OIL RUBBED BRONZE CF773ORB - Dark Cherry/Walnut Blades

- 5 reversible blades
- Light fixture adaptable
- 4.5" downrod included

F. 42" MONTEREY II – SATIN WHITE CF773SW - Satin White/Maple Blades

- 5 reversible blades
- Light fixture adaptable
- 4.5" downrod included

Included:



FIVE REVERSIBLE BLADES

Sold Separately:



SR400 Remote Control with Receiver



SW405 Wall Control with Receiver



LK GLO SERIES L.E.D. LIGHT FIXTURE pg 126-127

Included:



FIVE REVERSIBLE BLADES

Sold Separately:



SR400 Remote Control with Receiver



SW405 Wall Control with Receiver



LK GLO SERIES L.E.D. LIGHT FIXTURE pg 126-127

Braddock


Braddock Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
6311	64	99

16.2"
FAN HEIGHT




- 54" blade span
- Integrated light fixture uses two 60-watt candelabra bulbs (included) & the accent light uses four 15-watt candelabra bulbs (included)
- 4.5" downrod included



A. **Braddock - Venetian Bronze** CF440VNB
Custom Hand Carved Dark Mahogany Blades, Amber Mist Glass

- A. **BRADDOCK – VENETIAN BRONZE**
CF440VNB - Custom Hand Carved Dark Mahogany Blades, Amber Mist Glass
- 5 hand carved wood blades
 - SR400 remote control with receiver
 - Integrated light fixture & accent light
 - 4.5' downrod included

Included:



FIVE WOOD, HAND CARVED BLADES



SR400
Remote Control with Receiver*

Sold Separately:



SW406
Wall Control

* SR600 or SW605 must be used to control the accent light and the downlight separately. Please note that the SR400 (included) or the SW405/SW406 will operate the accent light and downlight simultaneously.



52" & 42" Bella™

- 52" or 42" blade span (42" in ORB & SW only)
- Light fixture adaptable
- 4.5" downrod included

Bella™ Energy Ratings at High Speed

Blade Span	Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
42"	4181	54	77
52"	5614	72	78

14.0"
FAN HEIGHT

- L.E.D. LIGHT FIXTURE ADAPTABLE
- SHIPS TO CANADA FAN ONLY
- LIMITED LIFETIME MOTOR WARRANTY



Shown with Walnut Blades & accessory Ashton L.E.D. Light Fixture in White Mist (LK91LEDBS, pg 127)

A. 52" Bella - Brushed Steel CF452BS
Dark Cherry/Walnut Blades



Shown with 52" Satin White Blades, accessory Opal Matte Harlow Light Fixture (LK150OMSW, pg 129) & 12" downrod (CFDR1SW, pg 5)

B. 52" & 42" Bella - Satin White CF452SW / CF442SW
Satin White/Maple Blades



Shown with Walnut Blades

C. 52" Bella - Vintage Steel CF452VS
Dark Mahogany/Walnut Blades



D. 52" Bella - Summer White CF452AW
Summer White/Summer White Blades



Shown with Dark Cherry Blades

E. 52" Bella - Venetian Bronze CF452VNB
Dark Cherry/Walnut Blades



Shown with 52" Dark Mahogany Blades

F. 52" & 42" Bella - Oil Rubbed Bronze CF452ORB / CF442ORB
Dark Mahogany/Walnut Blades



- A. **52" BELLA – BRUSHED STEEL**
CF452BS - Dark/Cherry Walnut Blades
 - 5 reversible blades
 - Light fixture adaptable
 - 4.5" downrod included
- B. **52" & 42" BELLA – SATIN WHITE**
CF452SW - 52" Satin White/Maple Blades
CF442SW - 42" Satin White/Maple Blades
 - 5 reversible blades
 - Light fixture adaptable
 - 4.5" downrod included
- C. **52" BELLA – VINTAGE STEEL**
CF452VS - 52" Dark Mahogany/Walnut Blades
 - 5 reversible blades
 - Light fixture adaptable
 - 4.5" downrod included
- D. **52" BELLA – SUMMER WHITE**
CF452AW - 52" Summer White/Summer White Blades
 - 5 Reversible Blades
 - Light Fixture adaptable
 - 4.5" downrod included
- E. **52" BELLA – VENETIAN BRONZE**
CF452VNB - 52" Dark Cherry/Walnut Blades
 - 5 Reversible Blades
 - Light Fixture adaptable
 - 4.5" downrod included
- F. **52" & 42" BELLA – OIL RUBBED BRONZE**
CF452ORB - 52" Dark Mahogany/Walnut Blades
CF442ORB - 42" Dark Mahogany/Walnut Blades
 - 5 Reversible Blades
 - Light Fixture adaptable
 - 4.5" downrod included

Included:



FIVE REVERSIBLE BLADES

Sold Separately:



SR400
Remote Control
with Receiver



SW405
Wall Control
with Receiver

Recommended Light Fixtures:

Sold separately.



LK GLO SERIES
L.E.D. LIGHT FIXTURE
pg 126-127



LK53
Low Profile Light Fixture, pg 129



LK92XXX
Ashton Light Fixture, pg 129

See pg 126-133 for additional light accessories.

Luxe Eco
CF550 - pg 54



CONTEMPORARY DESIGN



KEANE
CF320 - pg 40



LURAY ECO
CF860 - pg 42



AIRA ECO
CF985 - pg 44



SOUTHTOWNE
CF4900 - pg 46



HIGHRISE
CF430 - pg 48



4TH AVENUE
CF766 - pg 50



MIDWAY ECO
CF955 - pg 52



LUXE ECO
CF550 - pg 54



HIGHPOINT
CF205 - pg 56



LOFT
CF765 - pg 58



52" & 44" CURVA SKY
CF152/CF144 - pg 60



52" & 44" CURVA
CF252/CF244 - pg 62



ATOMICAL
CF930 - pg 64



VELOCE
CF230 - pg 66



TILO
CF130 - pg 67



ECOMOTOR



DAMP LOCATION RATED



K55 MOTOR



WET LOCATION RATED



ENERGY STAR LISTED



INTEGRATED L.E.D. LIGHTING

*Certain finishes only. See fan pages for details.

NEW!

Keane

Keane Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
5200*	49*	106*

*Estimated. Visit our website at emersonfans.com for up-to-date information.




10.9"
FAN HEIGHT



SHIPS TO CANADA

LIMITED LIFETIME MOTOR WARRANTY

- 52" blade span
- 3 reversible blades
- 4.5" downrod included



Shown with Barbeque Black Blades

A. Keane - Brushed Steel CF320SBS
Brushed Steel/Barbeque Black Blades



Shown with Walnut Blades

B. Keane - Brushed Steel CF320CBS
Natural Cherry/Walnut Blades



Shown with Maple Blades

C. Keane - Brushed Steel CF320WBS
Satin White/Maple Blades



Shown with Satin White Blades

D. Keane - Satin White CF320WSW
Satin White/Maple Blades



Shown with Natural Cherry Blades

E. Keane - Satin White CF320CSW
Natural Cherry/Walnut Blades



CF320 X XX


Keane model # 1 2

1. Choose blades



S: Brushed Steel/Barbecue
C: Natural Cherry/Walnut
W: Satin White/Walnut


2. Choose fan finish



BS: Brushed Steel
SW: Satin White

- A. **KEANE - BRUSHED STEEL**
CF320SBS - Brushed Steel/Barbecue Black Blades
 - 3 reversible blades
 - SW46W 4-speed fan slide control
 - 4.5" downrod included
 - Not Light Fixture Adaptable
- B. **KEANE - BRUSHED STEEL**
CF320CBS - Natural Cherry/Walnut Blades
 - 3 reversible blades
 - SW46W 4-speed fan slide control
 - 4.5" downrod included
 - Not Light Fixture Adaptable
- C. **KEANE - BRUSHED STEEL**
CF320WBS - Satin White/Maple Blades
 - 3 reversible blades
 - SW46W 4-speed fan slide control
 - 4.5" downrod included
 - Not Light Fixture Adaptable
- D. **KEANE - SATIN WHITE**
CF320WSW - Satin White/Maple Blades
 - 3 reversible blades
 - SW46W 4-speed fan slide control
 - 4.5" downrod included
 - Not Light Fixture Adaptable
- E. **KEANE - SATIN WHITE**
CF320CSW - Natural Cherry/Walnut Blades
 - 3 reversible blades
 - SW46W 4-speed fan slide control
 - 4.5" downrod included
 - Not Light Fixture Adaptable

Included:



THREE REVERSIBLE BLADES



SW46W
4-Speed Fan Slide Control



NEW!

Luray Eco

Luray Eco Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
8500*	33*	258*

*Estimated. Visit our website at emersonfans.com for up-to-date information.


14.5"
FAN HEIGHT

- 60" blade span
- Integrated L.E.D. light kit
- 2,600 Lumens
- 95 CRI
- 3,000K CCT
- 32 Watts
- 4.5" downrod included



Look for this logo for fans that carry Emerson's Most Energy Efficient Motor - **The EcoMotor®**

- Up to 3 times more efficient than typical ceiling fan motors - costs less than 1¢ per hour to run
- CF860 EcoMotor only uses a maximum of 33 watts of energy
- Drives higher degree blade pitch more efficiently
- Built-in electronics with 6-speed control with every fan
- Proven design for reliable & quiet operation



Emerson EcoMotor®

See pg 4 for more information.

Luray Eco



A. Luray Eco - Platinum CF860PT
Platinum Blades




B. Luray Eco - Barbeque Black CF860BQ
Barbeque Black Blades



C. Luray Eco - Appliance White CF860WW
Appliance White Blades


Included:



THREE CUSTOM BLADES



INTEGRATED L.E.D. LIGHT FIXTURE



REMOVABLE NO-LIGHT PLATE



6-Speed Wall Control²

- A. **LURAY ECO – PLATINUM CF860PT** - Platinum Blades
- 3 custom blades
 - Integrated L.E.D. light fixture
 - SW605 wall control
 - Removable no-light plate
 - 4.5" downrod included


- B. **LURAY ECO – BARBEQUE BLACK CF860BQ** - Barbeque Black Blades
- 3 custom blades
 - Integrated L.E.D. light fixture
 - SW605 wall control
 - Removable no-light plate
 - 4.5" downrod included

- C. **LURAY ECO – APPLIANCE WHITE CF860WW** - Appliance White Blades
- 3 custom blades
 - Integrated L.E.D. light fixture
 - SW605 wall control
 - Removable no-light plate
 - 4.5" downrod included

Sold Separately:



SR600 Remote Control



Aira Eco

Aira Eco Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
9782	33.7	290

12.5"
FAN HEIGHT



View videos about Aira Eco's features and installation at MyEmersonFans.com/Videos

ECOMOTOR®

DAMP LOCATION¹ RATED


SHIPS TO CANADA

LIMITED LIFETIME MOTOR WARRANTY



Look for this logo for fans that carry Emerson's Most Energy Efficient Motor - **The EcoMotor®**

- Up to 3 times more efficient than typical ceiling fan motors - costs less than 1¢ per hour to run
- CF985 EcoMotor only uses a maximum of 33 watts of energy
- Drives higher degree blade pitch more efficiently
- Built-in electronics with 6-speed control with every fan
- Proven design for reliable & quiet operation



Emerson EcoMotor®

See pg 4 for more information.

- 72" blade span
- Integrated light fixture uses two 50-watt halogen bulbs (included)
- 6" downrod included
- Optional no-light plate included

A. Aira Eco - Brushed Steel CF985BS
Weather-Resistant Walnut Blades, Opal Matte Glass




B. Aira Eco - Oil Rubbed Bronze CF985ORB
Weather-Resistant Walnut Blades, Opal Matte Glass

- A. **AIRA ECO - BRUSHED STEEL CF985BS** - Weather-Resistant Walnut Blades, Opal Matte Glass
- 8 weather-resistant blades
 - Integrated light fixture
 - 6 speed wall control with receiver
 - 6" downrod included
 - Optional no-light plate included

- B. **AIRA ECO - OIL RUBBED BRONZE CF985ORB** - Weather-Resistant Walnut Blades, Opal Matte Glass
- 8 weather-resistant blades
 - Integrated light fixture
 - 6 speed wall control with receiver
 - 6" downrod included
 - Optional no-light plate included


Included:



EIGHT WEATHER-RESISTANT BLADES



INTEGRATED LIGHT FIXTURE



OPTIONAL NO-LIGHT PLATE



6-Speed Wall Control²

Sold Separately:



SR650
2-in-1 Remote Control



SR600
L.E.D. Remote Control

¹ Damp Location rated for ORB finish. BS finish not suitable for Damp locations
² Controls are recommended for indoor use only.



Southtowne

Southtowne Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
5556	97	57

15.0"
FAN HEIGHT

K55 K55 MOTOR SHIPS TO CANADA LIMITED LIFETIME MOTOR WARRANTY

- 54" blade span
- Integrated light fixture uses two 50-watt mini candelabra base halogen bulbs (included)
- 4.5" downrod included

Shown with Walnut Blades



A. Southtowne - Brushed Steel CF4900BS
Dark Mahogany/Walnut Blades, Opal Matte Glass



Shown with Walnut Blades



B. Southtowne - Oil Rubbed Bronze CF4900ORB
Chocolate/Walnut Blades, Opal Matte Glass



- A. **SOUTHTOWNE – BRUSHED STEEL CF4900BS** - Dark Mahogany/Walnut Blades, Opal Matte Glass
- 5 reversible blades
 - SW605 wall control & RCK55 receiver
 - Integrated light fixture
 - Removable no-light plate
 - 4.5" downrod included
- B. **SOUTHTOWNE – OIL RUBBED BRONZE CF4900ORB** - Chocolate/Walnut Blades, Opal Matte Glass
- 5 reversible blades
 - SW605 wall control & RCK55 receiver
 - Integrated light fixture
 - Removable no-light plate
 - 4.5" downrod included
- C. **SOUTHTOWNE – VINTAGE STEEL CF4900VS** - Riverwash/Walnut Blades, Opal Matte Glass
- 5 reversible blades
 - SW605 wall control & RCK55 receiver
 - Integrated light fixture
 - Removable no-light plate
 - 4.5" downrod included

Shown with Riverwash Blades



C. Southtowne - Vintage Steel CF4900VS
Riverwash/Walnut Blades, Opal Matte Glass



Included:




FIVE REVERSIBLE BLADES



6-Speed
Wall Control
with Receiver



INTEGRATED LIGHT FIXTURE



REMOVABLE NO-LIGHT PLATE

Sold Separately:



SR600
Remote Control



SR650
2-in-1
Remote Control

Highrise

Highrise Energy Ratings at High Speed


Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
4263	49	85



FAN HEIGHT

- INTEGRATED L.E.D. LIGHTING
- SHIPS TO CANADA
- LIMITED LIFETIME MOTOR WARRANTY

- 50" blade span
- Integrated L.E.D. light fixture
 - 1,300 Lumens
 - 17 Watts
 - 80 CRI
 - 3,000K CCT
- 4.5" downrod included



Shown with Dark Mahogany Blades

A. Highrise - Brushed Steel CF430BS
Natural Cherry/Dark Mahogany Blades, Opal Matte Glass



Shown with Natural Cherry Blades

B. Highrise - Oil Rubbed Bronze CF430ORB
Natural Cherry/Dark Mahogany Blades, Opal Matte Glass



Shown with Satin White Blades

C. Highrise - Satin White CF430SW
Satin White/Maple Blades, Opal Matte Glass



- A. **HIGHRISE – BRUSHED STEEL**
CF430BS - Natural Cherry/Dark Mahogany Blades, Opal Matte Glass
 - 4 reversible blades
 - Integrated L.E.D. light fixture
 - SW405 wall control with receiver
 - 4.5" downrod included
- B. **HIGHRISE – OIL RUBBED BRONZE**
CF430ORB - Natural Cherry/Dark Mahogany Blades, Opal Matte Glass
 - 4 reversible blades
 - Integrated L.E.D. light fixture
 - SW405 wall control with receiver
 - 4.5" downrod included
- C. **HIGHRISE – SATIN WHITE**
CF430SW - Satin White/Maple Blades, Opal Matte Glass
 - 4 reversible blades
 - Integrated L.E.D. light fixture
 - SW405 wall control with receiver
 - 4.5" downrod included

Included:

- FOUR REVERSIBLE BLADES**
- INTEGRATED L.E.D. LIGHT FIXTURE¹**
- SW405**
Wall Control with Receiver

¹ Please note there is no dimming feature with the L.E.D. integrated light fixture of the CF430

Sold Separately:

- SR401**
Remote Control



4th Avenue

4th Avenue Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
6403	48	132

17.9"

FAN HEIGHT



- 60" blade span
- Integrated light fixture uses two 60-watt candelabra bulbs (included)
- 8" downrod included



A. 4th Avenue - Brushed Steel CF766SBS
Brushed Steel Blades, Opal Matte Glass



B. 4th Avenue - Vintage Steel CF766VS
Riverwash Blades, Vintage Cream Glass

- A. **4TH AVENUE – BRUSHED STEEL CF766SBS** - Brushed Steel Blades, Opal Matte Glass
- 3 custom blades
 - Integrated light fixture
 - SW405 wall control with receiver
 - 8" downrod included

- B. **4TH AVENUE – VINTAGE STEEL CF766VS** - Riverwash Blades, Vintage Cream Glass
- 3 custom blades
 - Integrated light fixture
 - SW405 wall control with receiver
 - 8" downrod included

- C. **4TH AVENUE – BRUSHED STEEL CF766BS** - Chocolate Blades, Opal Matte Glass
- 3 custom blades
 - Integrated light fixture
 - SW405 wall control with receiver
 - 8" downrod included

Included:



THREE CUSTOM BLADES



INTEGRATED LIGHT FIXTURE



SW405
Wall Control with Receiver


Sold Separately:



SR401
Remote Control



C. 4th Avenue - Brushed Steel CF766BS
Chocolate Blades, Opal Matte Glass



Midway Eco™

Midway Eco™ Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
6085	18	336

16.5"
FAN HEIGHT



View videos about Midway Eco's features and installation at MyEmersonFans.com/Videos



- 54" airfoil design blade
- Integrated light fixture uses four 13-watt GU24 fluorescent bulbs (included)
- 4.5" downrod included

Shown with 12" Downrod (CFDR1BS, pg 5)

A. Midway Eco - Brushed Steel CF955BS
Midnight Bordeaux Blades, Opal Matte Glass



Look for this logo for fans that carry Emerson's Most Energy Efficient Motor - **The EcoMotor®**


- Up to 3 times more efficient than typical ceiling fan motors-costs less than 1¢ per hour to run
- CF955 EcoMotor only uses 18 watts of energy
- Drives higher degree blade pitch more efficiently
- Built-in electronics with 6-speed control with every fan
- Proven design for reliable & quiet operation



Emerson EcoMotor®

See pg 4 for more information.

Included:



FIVE AIRFOIL BLADES



INTEGRATED LIGHT FIXTURE¹



6 SPEED Remote Control with Receiver

¹ GU24 base fluorescent bulbs are not dimmable.

Sold Separately:



SR650
2-in-1 Remote Control



SW605
Wall Control with Receiver

WITH 6-SPEED REMOTE CONTROL



B. Midway Eco - Oil Rubbed Bronze CF955ORB
Oil Rubbed Bronze Blades, Opal Matte Glass



Shown with 12" Downrod (CFDR1WW, pg 5)

C. Midway Eco - Appliance White CF955WW
Appliance White Blades, Opal Matte Glass

- A. **MIDWAY ECO – BRUSHED STEEL**
CF955BS - Midnight Bordeaux Blades, Opal Matte Glass
- 5 airfoil blades
 - Integrated light fixture
 - 6 speed remote control with receiver
 - 4.5" downrod included
- B. **MIDWAY ECO – OIL RUBBED BRONZE**
CF955ORB - Oil Rubbed Bronze Blades, Opal Matte Glass
- 5 airfoil blades
 - Integrated light fixture
 - 6 speed remote control with receiver
 - 4.5" downrod included
- C. **MIDWAY ECO – APPLIANCE WHITE**
CF955WW - Appliance White Blades, Opal Matte Glass
- 5 airfoil blades
 - Integrated light fixture
 - 6 speed remote control with receiver
 - 4.5" downrod included

C

Luxe Eco

Luxe Eco Energy Ratings at High Speed

Airflow Cubic Ft. Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft. Per Min. Per Watt
6974	33	210

15.8"
FAN HEIGHT



- 54" blade span
- Integrated light fixture uses two 50-watt mini-candelabra base halogen bulbs (included)
- 4.5" downrod included



Look for this logo for fans that carry Emerson's Most Energy Efficient Motor - **The EcoMotor**

- Up to 3 times more efficient than typical ceiling fan motors - costs less than 1¢ per hour to run
- CF550 EcoMotor only uses 33 watts of energy
- Drives higher degree blade pitch more efficiently
- Built-in electronics with 6-speed control with every fan
- Proven design for reliable & quiet operation



Emerson EcoMotor® See pg 4 for more information.



D. Luxe Eco - Brushed Steel CF550DMBS
Dark Mahogany Blades, Opal Matte Glass



A. Luxe Eco - Brushed Steel CF550WABS
Walnut Blades, Opal Matte Glass




B. Luxe Eco - Oil Rubbed Bronze CF550WAORB
Walnut Blades, Opal Matte Glass





Shown with 12" Downrod (CFDR1ORB, pg 5)

C. Luxe Eco - Oil Rubbed Bronze CF550DMORB
Dark Mahogany Blades, Opal Matte Glass





- A. **LUXE ECO – BRUSHED STEEL**
CF550WABS - 54" Walnut Blades, Opal Matte Glass
- 5 custom wood veneer blades included
 - 4.5" downrod included
 - Removable no-light plate included
 - Integrated light fixture
- B. **LUXE ECO – OIL RUBBED BRONZE**
CF550WAORB - 54" Walnut Blades, Opal Matte Glass
- 5 custom wood veneer blades included
 - 4.5" downrod included
 - Removable no-light plate included
 - Integrated light fixture
- C. **LUXE ECO – OIL RUBBED BRONZE**
CF550DMORB - 54" Dark Mahogany Blades, Opal Matte Glass
- 5 custom wood veneer blades included
 - 4.5" downrod included
 - Removable no-light plate included
 - Integrated light fixture
- D. **LUXE ECO – BRUSHED STEEL**
CF550DMBS - 54" Dark Mahogany Blades, Opal Matte Glass
- 5 custom wood veneer blades included
 - 4.5" downrod included
 - Removable no-light plate included
 - Integrated light fixture



Included:



Sold Separately



Highpoint™

Highpoint™ Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
5678	66	86

16.5"
22.5"
FAN HEIGHT

SHIPS TO CANADA LIMITED LIFETIME MOTOR WARRANTY

- 54" blade span
- Integrated light fixture uses two 50-watt mini-candelabra base halogen bulbs (included)
- Two downrods included: 6" & 12"



Shown with Removable Decorative Cables & 12" Downrod

A. Highpoint - Brushed Steel CF205BS
Dark Mahogany Blades, Opal Matte Glass



Shown with Removable Decorative Cables & 12" Downrod

B. Highpoint - Golden Espresso CF205GES
Chocolate Blades, Sandstone Glass



Shown with Removable No-Light Plate & 6" Downrod

B. Highpoint - Golden Espresso CF205GES
Chocolate Blades

- A. **HIGHPOINTE – BRUSHED STEEL**
CF205BS - Dark Mahogany Blades, Opal Matte Glass
- 3 custom blades
 - Removable no-light plate
 - Removable decorative cables
 - Integrated light fixture
 - SR400 remote control with receiver
 - Two downrods included: 6" & 12"

- B. **HIGHPOINTE – GOLDEN ESPRESSO**
CF205GES - Chocolate Blades, Sandstone Glass
- 3 custom blades
 - Removable no-light plate
 - Removable decorative cables
 - Integrated light fixture
 - SR400 remote control with receiver
 - Two downrods included: 6" & 12"

- C. **HIGHPOINTE – VINTAGE STEEL**
CF205VS - Honey Oak/Riverwash Blades, Vintage Cream Glass
- 3 custom blades
 - Removable no-light plate
 - Removable decorative cables
 - Integrated light fixture
 - SR400 remote control with receiver
 - Two downrods included: 6" & 12"



Shown with Riverwash Blades, Removable No-Light Plate, Removable Decorative Cables & 12" Downrod

C. Highpoint - Vintage Steel CF205VS
Honey Oak/Riverwash Blades



Shown with Honey Oak Blades, Removable Decorative Cables & 12" Downrod

C. Highpoint - Vintage Steel CF205VS
Honey Oak/Riverwash Blades, Vintage Cream Glass


Included:




THREE CUSTOM BLADES



REMOVABLE DECORATIVE CABLES¹



INTEGRATED LIGHT FIXTURE



REMOVABLE NO-LIGHT PLATE



SR400 Remote Control with Receiver

¹ Removable decorative cables for use on 9' ceilings or higher

Sold Separately:



SW406 Wall Control

Airflow Cubic Ft. Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft. Per Min. Per Watt
7579	81	92



View videos about Loft's features and installation at MyEmersonFans.com/Videos

- 60" blade span
- Not light fixture adaptable
- 6" downrod included



A. **Loft - Brushed Steel** CF765BS
Weather-Resistant Brushed Steel Blades



B. **Loft - Barbeque Black** CF765BQ
Weather-Resistant Barbeque Black Blades



C. **Loft - Appliance White** CF765WW
Weather-Resistant Appliance White Blades



- A. **LOFT - BRUSHED STEEL¹**
CF765BS - Weather-Resistant Brushed Steel Blades
- 3 high-efficiency airfoil blades
 - SW46 wall control
 - 6" downrod included

- B. **LOFT - BARBEQUE BLACK**
CF765BQ - Weather-Resistant Barbeque Black Blades
- 3 high-efficiency airfoil blades
 - SW46 wall control
 - 6" downrod included

- C. **LOFT - APPLIANCE WHITE**
CF765WW - Weather-Resistant Appliance White Blades
- 3 high-efficiency airfoil blades
 - SW46 wall control
 - 6" downrod included

Included:



THREE HIGH-EFFICIENCY AIRFOIL BLADES



SW46
Wall Control²

¹ Damp Location rated for BQ and WW finishes. BS finish not suitable for Damp Locations
² Controls are recommended for indoor use only.


52" & 44" Curva Sky™

52" & 44" Curva Sky™ Energy Ratings at High Speed

Blade Span	Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
52"	5393	46	116
44"	4217	45	93



- 52" or 44" blade span
- Integrated light fixture uses two 50-watt mini-candelabra base halogen bulbs (included)



52" & 44" Curva Sky

Shown with 52" Blades



A. 52" Curva Sky - Brushed Steel CF152BS
Weather-Resistant Brushed Steel Blades, Opal Matte Glass

- A. **52" CURVA SKY – BRUSHED STEEL¹**
CF152BS - 52" Brushed Steel Finished Blades, Opal Matte Glass
- 3 weather-resistant blades
 - Removable no-light plate
 - Integrated light fixture
 - 6 speed remote control with receiver



Shown with Removable No-Light Plate

B. 44" Curva Sky - Brushed Steel CF144BS
Weather-Resistant Brushed Steel Blades, Opal Matte Glass

- B. **44" CURVA SKY – BRUSHED STEEL¹**
CF144BS - 44" Brushed Steel Finished Blades, Opal Matte Glass
- 3 weather-resistant blades
 - Removable no-light plate
 - Integrated light fixture
 - 6 speed remote control with receiver

- C. **52" & 44" CURVA SKY – APPLIANCE WHITE**
CF152WW - 52" Weather-Resistant Appliance White Blades, Opal Matte Glass
CF144WW - 44" Weather-Resistant Appliance White Blades, Opal Matte Glass
- 3 weather-resistant blades
 - Removable no-light plate
 - Integrated light fixture
 - 6 speed remote control with receiver

- D. **52" & 44" CURVA SKY – OIL RUBBED BRONZE**
CF152ORB - 52" Weather-Resistant Oil Rubbed Bronze Blades, Opal Matte Glass
CF144ORB - 44" Weather-Resistant Oil Rubbed Bronze Blades, Opal Matte Glass
- 3 weather-resistant blades
 - Removable no-light plate
 - Integrated light fixture
 - 6 speed remote control with receiver

- D. **52" & 44" Curva Sky - Oil Rubbed Bronze**
CF152ORB / CF144ORB
Weather-Resistant Oil Rubbed Blades, Opal Matte Glass


WITH 6-SPEED
REMOTE CONTROL




Shown with 52" Blades

C. 52" & 44" Curva Sky - Appliance White CF152WW / CF144WW
Weather-Resistant Appliance White Blades, Opal Matte Glass

Included:



THREE WEATHER-RESISTANT BLADES



REMOVABLE NO-LIGHT PLATE



INTEGRATED LIGHT FIXTURE



6 SPEED Remote Control with Receiver²

Sold Separately:



SR650
2-in-1 Remote Control²



SW605
Wall Control²

¹ ORB and WW finishes wet location approved. BS finish not recommended for outdoor use.
² Controls are recommended for indoor use only.



52" & 44" Curva™


- 52" or 44" blade span
- Integrated light fixture uses two 50-watt mini-candelabra base halogen bulbs (included)
- 4.5" downrod included

52" & 44" Curva™ Energy Ratings at High Speed

Blade Span	Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
44"	4280	44	97
52"	5329	45	118



14.9"
FAN HEIGHT



A. 52" Curva - Oil Rubbed Bronze CF252ORB
Weather-Resistant Oil Rubbed Bronze Blades, Opal Matte Glass



Shown with Removable No-Light Plate

B. 44" Curva - Oil Rubbed Bronze CF244ORB
Weather-Resistant Oil Rubbed Blades, Opal Matte Glass



Shown with 52" Blades

C. 52" & 44" Curva - Brushed Steel CF252BS / CF244BS
Weather-Resistant Brushed Steel Blades, Opal Matte Glass



Shown with 52" Blades

D. 52" & 44" Curva - Appliance White CF252WW / CF244WW
Weather-Resistant Appliance White Blades, Opal Matte Glass

52" & 44" Curva

- A. **52" CURVA – OIL RUBBED BRONZE CF252ORB** - 52" Weather-Resistant Oil Rubbed Bronze Blades, Opal Matte Glass
- 3 weather-resistant blades
 - Removable no-light plate
 - Integrated light fixture
 - 6 speed remote control with receiver
 - 4.5" downrod included

- B. **44" CURVA – OIL RUBBED BRONZE CF244ORB** - 44" Weather-Resistant Oil Rubbed Bronze Blades, Opal Matte Glass
- 3 weather-resistant blades
 - Removable no-light plate (Shown)
 - Integrated light fixture
 - 6 speed remote control with receiver
 - 4.5" downrod included


- C. **52" & 44" CURVA – BRUSHED STEEL¹ CF252BS** - 52" Brushed Steel Finished Blades, Opal Matte Glass
CF244BS - 44" Brushed Steel Finished Blades, Opal Matte Glass
- 3 weather-resistant blades
 - Removable no-light plate
 - Integrated light fixture
 - 6 speed remote control with receiver
 - 4.5" downrod included

- D. **52" & 44" CURVA – APPLIANCE WHITE CF252WW** - 52" Weather-Resistant Appliance White Blades, Opal Matte Glass
CF244WW - 44" Weather-Resistant Appliance White Blades, Opal Matte Glass
- 3 weather-resistant blades
 - Removable no-light plate
 - Integrated light fixture
 - 6 speed remote control with receiver
 - 4.5" downrod included


Included:



THREE WEATHER-RESISTANT BLADES



REMOVABLE NO-LIGHT PLATE



INTEGRATED LIGHT FIXTURE



6 SPEED Remote Control with Receiver²

Sold Separately:



SR650
2-in-1 Remote Control²



SW605
Wall Control²

¹ ORB and WW finishes are wet location approved. BS finish is not recommended for outdoor use.
² Controls are recommended for indoor use only.



Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
4515	59	76



15.8"

FAN HEIGHT

DAMP LOCATION RATED¹ SHIPS TO CANADA LIMITED LIFETIME MOTOR WARRANTY

- 52" blade span
- Integrated light fixture uses two 60-watt candelabra bulbs (included)
- No-light plate (CP930) sold separately
- 4.5" downrod Included

Shown with Optional No-Light Plate (CP300ORB, see below)



A. Atomical - Oil Rubbed Bronze CF930ORB
Mahogany Blades, Opal Matte Glass




B. Atomical - Appliance White CF930WW
Appliance White Blades, Opal Matte Glass


Optional No-Light Plates



Included:



FIVE CUSTOM BLADES



INTEGRATED LIGHT FIXTURE



SR400
Remote Control with Receiver²

Sold Separately:



CP930- XXX
Optional No-Light Plate



SW406
Wall Control

- A. **ATOMICAL – OIL RUBBED BRONZE CF930ORB** - Mahogany Blades, Opal Matte Glass
 - 5 custom blades
 - Integrated light fixture
 - SR400 remote control with receiver
 - 4.5" downrod included
- B. **ATOMICAL – APPLIANCE WHITE CF930WW** - Appliance White Blades, Opal Matte Glass
 - 5 custom blades
 - Integrated light fixture
 - SR400 remote control with receiver
 - 4.5" downrod included
- C. **ATOMICAL – BRUSHED STEEL CF930BS** - Dark Cherry Blades, Opal Matte Glass
 - 5 custom blades
 - Integrated light fixture
 - SR400 remote control with receiver
 - 4.5" downrod included

C. Atomical - Brushed Steel CF930BS
Dark Cherry Blades, Opal Matte Glass



¹ Damp Location rated for ORB and WW finishes. BS is not suitable for Damp Locations.
² Controls are recommended for indoor use only.

Veloce™

Veloce™ Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
5250	52	102

14.4"
11.1"
FAN HEIGHT

SHIPS TO CANADA **LIMITED LIFETIME MOTOR WARRANTY**

- 46" blade span
- Integrated light fixture uses one 50-watt GU10 base MR16 halogen bulb (included)
- No-light plate (CP230) sold separately
- Dual mounting for close-to-the-ceiling or downrod installation
- 4.5" downrod included

Veloce



A. **Veloce - Brushed Steel** CF230BS
Brushed Steel/Chocolate Blades



B. **Veloce - Brushed Steel** CF230BS
Brushed Steel/Chocolate Blades



- A. **VELOCE – BRUSHED STEEL**
CF230BS - Brushed Steel/Chocolate Blades
- 4 reversible blades
 - Dual-Mount feature
 - Integrated light fixture
 - SR400 remote control with receiver
 - 4.5" downrod included
- B. **VELOCE – BRUSHED STEEL**
CF230BS - Brushed Steel/Chocolate Blades
- 4 reversible blades
 - Dual-Mount feature
 - Integrated light fixture
 - SR400 remote control with receiver
 - 4.5" downrod included


Included:



FOUR REVERSIBLE BLADES



DUAL-MOUNT FEATURE




INTEGRATED LIGHT FIXTURE



SR400
Remote Control with Receiver¹

Sold Separately:



CP230BS
No-Light Plate



SW406
Four Speed Wall Control

Tilo™

Tilo™ Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
2278	42	54

9.5"
13.3"
FAN HEIGHT

DAMP LOCATION RATED² **SHIPS TO CANADA** **LIMITED LIFETIME MOTOR WARRANTY**

- 30" blade span
- Light fixture adaptable (LK130, sold separately, pg 130)
- 4.5" downrod included

Tilo



E. **Tilo - Appliance White** CF130WW
Appliance White Blades



C. **Tilo - Oil Rubbed Bronze** CF130ORB
Dark Cherry Blades



D. **Tilo - Brushed Steel** CF130BS
Dark Cherry Blades

- C. **TILO – OIL RUBBED BRONZE**
CF130ORB - Dark Cherry Blades
- 3 curved blades
 - Dual-Mount feature
 - SW46 wall control
 - 4.5" downrod included

- D. **TILO – BRUSHED STEEL**
CF130BS - Dark Cherry Blades
- 3 curved blades
 - Dual-Mount feature
 - SW46 wall control
 - 4.5" downrod included

- E. **TILO – APPLIANCE WHITE**
CF130WW - Appliance White Blades
- 3 curved blades
 - Dual-Mount feature
 - SW46 wall control
 - 4.5" downrod included



OPTIONAL TILO LIGHT FIXTURE
LK130 - Opal Matte Glass

- Includes BS, ORB, and WW bowl caps.
- Two 50-watt Mini-Candelabra Halogen Bulbs (included)

Included:



THREE CURVED BLADES



DUAL-MOUNT FEATURE



SW46
Wall Control³

Sold Separately:



LK130
LIGHT FIXTURE
pg 130

² Damp Location rated for ORB and WW finishes. BS is not suitable for Damp Locations.
³ Controls are recommended for indoor use only.

Zurich
CF935 - pg 75

C
CLASSIC DESIGN



MONACO
CF830 - pg 70




CROWN SELECT
CF4501 - pg 72




CORNERSTONE
CF1 - pg 74



ZURICH
CF935 - pg 75

 **BLADE SELECT SERIES**

 **K55 MOTOR**

 **L.E.D. LIGHT FIXTURE ADAPTABLE**

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
6156	98	63

15.5"
21.0"
FAN HEIGHT



ACCENT LIGHTING



**L.E.D. LIGHT
FIXTURE ADAPTABLE**



**LIMITED LIFETIME
MOTOR WARRANTY**

- 60" blade span
- Accent lighting uses four 40-watt candelabra bulbs (included)
- Light fixture adaptable
- Two downrods included: 4.5" & 10"




A. Monaco - Golden Espresso CF830GES
Vintage Black Hand Carved Blades




A. Monaco - Golden Espresso CF830GES
Vintage Black Hand Carved Blades

- A. **MONACO – GOLDEN ESPRESSO**
CF830GES - Vintage Black Hand Carved Blades
- 5 hand carved wood blades
 - Removable decorative sleeve
 - Accent lighting
 - Light fixture adaptable
 - SW90W wall control
 - 4.5" & 10" downrods included

Included:



**FIVE HAND CARVED
WOOD BLADES**



**ACCENT
LIGHTING**



SW90W
Wall Control



**REMOVABLE
DECORATIVE
SLEEVE¹**

Recommended Light Fixtures:

Sold separately.



LK71LEDGES
Amber Parchment L.E.D. Light Fixture,
pg 126

See pg 126-133 for
additional light accessories.

Sold Separately:



SR400
Remote Control
with Receiver



SW405
Wall Control
with Receiver



SR600
Remote Control²



SW605
Wall Control²



RC188
Receiver

¹ Recommended for ceiling height of at least 9 feet (for lower ceilings, use a shorter downrod without decorative sleeve).
² For use with an accessory light fixture. Reverse button will not function. Please note that the SR400/SW405 will control the accent light and an accessory light kit simultaneously. To operate the accent light and an accessory light kit separately, the SR600/SW605 controls with the RC188 Receiver must be used.



Crown Select™

Crown Select™ Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
7155	100	72

14.0"
FAN HEIGHT



K55
K55XL
MOTOR



L.E.D. LIGHT
FIXTURE ADAPTABLE

LIMITED LIFETIME
MOTOR WARRANTY

- Blades Sold Separately
- 42", 52" or 58" blade span¹
- Accent lighting with patented swivel sockets use three 25-watt candelabra bulbs (included)
- Light fixture adaptable
- 4.5" downrod included

Shown with 25" Hand Carved Ornate Blades (B97DWA, pg 134)



A. Crown Select - Gilded Bronze CF4501GBZ

- A. **CROWN SELECT – GILDED BRONZE**
CF4501GBZ - Blade Select Series
- Blades sold separately
 - Accent lighting with patented swivel socket
 - Light fixture adaptable
 - 4.5" downrod included


- B. **CROWN SELECT – ANTIQUE PEWTER**
CF4501AP - Blade Select Series
- Blades sold separately
 - Accent lighting with patented swivel socket
 - Light fixture adaptable
 - 4.5" downrod included

- C. **CROWN SELECT – VENETIAN BRONZE**
CF4501VNB - Blade Select Series
- Blades sold separately
 - Accent lighting with patented swivel socket
 - Light fixture adaptable
 - 4.5" downrod included

Shown with 22" Solid Wood Dark Mahogany Blades (B77DM, pg 134)



B. Crown Select - Antique Pewter CF4501AP




BLADE SELECT
SERIES



*your style,
hundreds of possibilities...*

For the Complete Blade Select Lineup
Turn to Page 134

Included:



ACCENT LIGHTING
WITH PATENTED
SWIVEL SOCKET

Sold Separately:



BLADE SELECT
SERIES BLADES¹
See pg 134-135



LK GLO SERIES
L.E.D. LIGHT FIXTURE
pg 126-127



SR650
2-in-1
Remote
Control



SR600
Remote
Control



SW605
Wall
Control



RCK55
Horseshoe
Receiver

Shown with 22" Walnut Blades (G54WA, pg 135) and Transitional Fitter (F490, pg 132) with Vintage Bulb Adapters (VB100, pg 132), Bulbs Not Included



C. Crown Select - Venetian Bronze CF4501VNB



Crown Select

¹ CF4501 not suitable with B79, B61, B62 or B63 blades.

Cornerstone™

Cornerstone™ Energy Ratings at High Speed

	Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
Two Blades	5345	99	54
Four Blades	6257	101	62

17.8"
31.3"
FAN HEIGHT

- Blades Sold Separately
- 54" blade span
- Adaptable to 2 or 4 blades
- Light fixture adaptable
- Two downrods included: 4.5" & 18"

K55
K55XL
MOTOR

L.E.D. LIGHT
FIXTURE ADAPTABLE


SHIPS TO CANADA
FAN ONLY

LIMITED LIFETIME
MOTOR WARRANTY

Cornerstone

Shown with Mahogany Blades (B1MH) and 2-blade Installation Option

A1. Cornerstone - Oil Rubbed Bronze CF1ORB



Shown with Mahogany Blades (B1MH), 4-blade Installation Option and Removable Decorative Sleeve



A2. Cornerstone - Oil Rubbed Bronze CF1ORB

A. CORNERSTONE – OIL RUBBED BRONZE CF1ORB -

- Blades Sold Separately
- Adaptable to 2 or 4 blades
- Light Fixture Adaptable
- Removable Decorative Sleeve
- Unique Serialized Nameplate
- 4.5" & 18" downrods included

Included:



REMOVABLE DECORATIVE SLEEVE



UNIQUE SERIALIZED NAMEPLATE

Sold Separately:



B1 Blades



SR400
Remote Control with Receiver



LK GLO SERIES L.E.D. LIGHT FIXTURE
pg 126-127

Blade Finishes for Cornerstone



* Sold in sets of 4

Zurich™

Zurich™ Energy Ratings at High Speed

	Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
	5958	69	86

14.5"
FAN HEIGHT

- 52" blade span
- Light fixture adaptable (sold separately)
- 4.5" downrod included

L.E.D. LIGHT
FIXTURE ADAPTABLE

SHIPS TO CANADA
FAN ONLY

LIMITED LIFETIME
MOTOR WARRANTY

Zurich

Shown with Dark Cherry Blades



B1. Zurich - Oil Rubbed Bronze CF935ORB
Dark Cherry/Medium Oak Blades



Shown with Dark Cherry Blades, Amber Mist L.E.D. Light Fixture (LK70LEDORB, pg 126) and 12" Downrod (CFDR1ORB, pg 5)



B2. Zurich - Oil Rubbed Bronze CF935ORB
Dark Cherry/Medium Oak Blades

B. ZURICH – OIL RUBBED BRONZE CF935ORB -

- Dark Cherry/Medium Oak Blades
- 5 reversible blades
- Light fixture adaptable
- 4.5" downrod included

Included:



FIVE REVERSIBLE BLADES

Sold Separately:



SR400
Remote Control with Receiver



SW405
Wall Control with Receiver



LK GLO SERIES L.E.D. LIGHT FIXTURE
pg 126-127



Avant Eco
CF921 - pg 78



TRADITIONAL DESIGN



AVANT ECO
CF921 - pg 78



PREMIUM SELECT
CF4801 - pg 80



PRIMA
CF901 - pg 82



DESIGNER
CF755 - pg 84



29" NORTHWIND
CF702 - pg 86




PRIMA SNUGGER
CF905 - pg 87



52" SNUGGER
CF8055 - pg 88



SNUGGER
CF8045 - pg 89

-  **ECOMOTOR**
-  **BLADE SELECT SERIES**
-  **K55 MOTOR**
-  **L.E.D. LIGHT FIXTURE ADAPTABLE**
-  **ENERGY STAR LISTED**

*Certain finishes only. See fan pages for details.

Avant Eco™

Avant Eco™ Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
7985	31	256

13.0"

FAN HEIGHT




L.E.D. LIGHT
FIXTURE ADAPTABLE

SHIPS TO CANADA
FAN ONLY

LIMITED LIFETIME
MOTOR WARRANTY

- Blades Sold Separately
- 44", 54", 60" or 72" blade span²
- Light fixture adaptable
- Accent light adaptable (AL100)
- 4.5" downrod included




Shown with 22" Art Deco Hand Carved Wood Blades (B101WA pg 135)

Avant Eco

ULTRA ENERGY EFFICIENT!

Shown with 22" Hand Carved Leaf Dark Oak Blades (B109DO, pg 135)



A. Avant Eco - Brushed Steel CF921BS

Shown with 22" Satin White Blades (G54SW, pg 135) and 12" Downrod (CFDR1SW, pg 5)



B. Avant Eco - Satin White CF921SW

Shown with 22" Honey Oak Blades (G54HO, pg 135) and 12" Downrod (CFDR1ORB, pg 5)



C. Avant Eco - Oil Rubbed Bronze CF921ORB



Look for this logo for fans that carry Emerson's Most Energy Efficient Motor - **The EcoMotor®**

- Up to 3 times more efficient than typical ceiling fan motors - costs less than 1¢ per hour to run
- CF921 EcoMotor only uses 31 watts of energy
- Drives higher degree blade pitch more efficiently
- Built-in electronics with 6-speed control with every fan
- Proven design for reliable & quiet operation



Emerson EcoMotor® See pg 4 for more information.

A. AVANT ECO – BRUSHED STEEL

- CF921BS** - Blade Select Series
- Blades sold separately
 - SR600 remote control with receiver
 - Light fixture adaptable
 - Accent light adaptable
 - 4.5" downrod included

B. AVANT ECO – SATIN WHITE

- CF921SW** - Blade Select Series
- Blades sold separately
 - SR600 remote control with receiver
 - Light fixture adaptable
 - Accent light adaptable
 - 4.5" downrod included

C. AVANT ECO – OIL RUBBED BRONZE

- CF921ORB** - Blade Select Series
- Blades sold separately
 - SR600 remote control with receiver
 - Light fixture adaptable
 - Accent light adaptable
 - 4.5" downrod included


D. AVANT ECO – VENETIAN BRONZE

- CF921VNB** - Blade Select Series
- Blades sold separately
 - SR600 remote control with receiver
 - Light fixture adaptable
 - Accent light adaptable
 - 4.5" downrod included

WITH 6-SPEED
REMOTE CONTROL



AL100
Optional Accent Light Accessory
Uses Four 25-watt Candelabra Base
Bulbs (included)




BLADE SELECT
SERIES



*your style,
hundreds of possibilities...*

For the Complete Blade Select
Lineup Turn to Page 134



D. Avant Eco - Venetian Bronze CF921VNB

Included:



SR600
Remote Control
with
Receiver

Sold Separately:



**BLADE SELECT
SERIES BLADES**
pg 134-135



SW605
Wall Control



SR650
2-in-1
Remote Control



AL100
Optional Accent
Light Accessory

¹ Energy Star testing completed with B78 blade series.
² CF921 is not suitable for use with B61, B62 or B63 blades.


Premium Select™

Premium Select™ Energy Ratings at High Speed

Airflow Cubic Ft. Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft. Per Min. Per Watt
7264	100	73


15.0"
FAN HEIGHT

- Blades Sold Separately
- 42", 52" or 58" blade span
- Accent lighting with patented swivel sockets uses three 25-watt candelabra bulbs (included)
- Light fixture adaptable
- 4.5" downrod included




BLADE SELECT
SERIES

K55
K55XL
MOTOR



ACCENT LIGHTING

L.E.D. LIGHT
FIXTURE ADAPTABLE



LIMITED LIFETIME
MOTOR WARRANTY



Shown with 22" Mahogany Veneer Blades (G54MH, pg 135), Opal Matte Harlow L.E.D. Light Fixture (LK150OMLEDBS, pg 127) and 12" Downrod (CFDR1BS, pg 5)

B. Premium Select - Brushed Steel CF4801BS



A. Premium Select - Oil Rubbed Bronze CF4801ORB

Shown with 25" Art Deco Hand Carved Walnut Blades (B91WA, pg 134) and 12" Downrod (CFDR1ORB, pg 5)

Shown with 22" Satin White Blades




C. Premium Select - Satin White CF4801SW

- A. PREMIUM SELECT – OIL RUBBED BRONZE CF4801ORB - Blade Select Series**
- Blades sold separately
 - Accent lighting with patented swivel sockets
 - Light fixture adaptable
 - 4.5" downrod included

- B. PREMIUM SELECT – BRUSHED STEEL CF4801BS - Blade Select Series**
- Blades sold separately
 - Accent lighting with patented swivel sockets
 - Light fixture adaptable
 - 4.5" downrod included

- C. PREMIUM SELECT – SATIN WHITE CF4801SW - Blade Select Series**
- Blades sold separately
 - Accent lighting with patented swivel sockets
 - Light fixture adaptable
 - 4.5" downrod included

Included:



ACCENT LIGHTING WITH PATENTED SWIVEL SOCKET



BLADE SELECT
SERIES



*your style,
hundreds of possibilities...*

For the Complete Blade Select Lineup Turn to Page 134

1 CF4801 is not suitable for use with B79, B61, B62 or B63 blades

Sold Separately:



BLADE SELECT SERIES BLADES¹
See pg 134-135



LK GLO SERIES L.E.D. LIGHT FIXTURE
pg 126-127



SW605
Wall Control



SR650
2-in-1 Remote Control



SR600
Remote Control




RCK55
Horseshoe Receiver

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
5263	59	89

13.0"
FAN HEIGHT

- 52" blade span
- Light fixture adaptable
- Accent light adaptable (AL100)
- 4.5" downrod included



Shown with Dark Cherry Blades

A. Prima - Oil Rubbed Bronze CF901ORB
Dark Cherry/Walnut Blades



Shown with Walnut
Blades and 12" Downrod
(CFDR1ORB, pg 5)

B. Prima - Venetian Bronze CF901VNB
Dark Cherry/Walnut Blades



Shown with Dark Cherry
Blades and Low Profile Light
Fixture (LK53BS, pg 129)

C. Prima - Brushed Steel CF901BS
Dark Cherry/Chocolate Blades




Shown with Satin White
Blades, Moon Light Fixture
(LK65SW, pg 129) and 12"
Downrod (CFDR1SW, pg 5)

D. Prima - Satin White CF901SW
Satin White/Maple Blades



Included:



FIVE
REVERSIBLE
BLADES



SW46
Wall Control

- A. **PRIMA – OIL RUBBED BRONZE**
CF901ORB - Dark Cherry/Walnut Blades
- 5 reversible blades
 - SW46 wall control
 - Light fixture adaptable
 - Accent light adaptable
 - 4.5" downrod included

- B. **PRIMA – VENETIAN BRONZE**
CF901VNB - Dark Cherry/Walnut Blades
- 5 reversible blades
 - SW46 wall control
 - Light fixture adaptable
 - Accent light adaptable
 - 4.5" downrod included

- C. **PRIMA – BRUSHED STEEL**
CF901BS - Dark Cherry/Chocolate Blades
- 5 reversible blades
 - SW46 wall control
 - Light fixture adaptable
 - Accent light adaptable
 - 4.5" downrod included

- D. **PRIMA – SATIN WHITE**
CF901SW - Satin White/Maple Blades
- 5 reversible blades
 - SW46 wall control
 - Light fixture adaptable
 - Accent light adaptable
 - 4.5" downrod included

Sold Separately:



AL100
OPTIONAL
ACCENT
Light Accessory




LK GLO SERIES
L.E.D. LIGHT FIXTURE
pg 126-127

UPGRADE BUNDLES


CONTROL + LIGHT ACCESSORY

Bundle & Save!


UB100 Upgrade Bundle



UB200 Upgrade Bundle



UB300 Upgrade Bundle



T

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
5794	69	83



L.E.D. LIGHT
FIXTURE ADAPTABLE

SHIPS TO CANADA

LIMITED LIFETIME
MOTOR WARRANTY

- 52" blade span
- Light fixture adaptable
- 3.5" downrod included


Shown with Dark Cherry Blades and Low Profile Light Fixture (LK53ORB, pg 129)



A. Designer - Oil Rubbed Bronze CF755ORB
Dark Cherry/Medium Oak Blades



Shown with Appliance White Blades & Moon Light Fixture (LK65WW, pg 129)



B. Designer - Appliance White CF755WW
Appliance White/Bleached Oak Blades



Shown with Dark Cherry Blades



C. Designer - Antique Brass CF755AB
Dark Cherry/Mahogany Blades



Shown with Dark Cherry Blades



D. Designer - Brushed Steel CF755BS
Dark Cherry/Mahogany Blades



Shown with Dark Cherry Blades

Included:



FIVE
REVERSIBLE
BLADES

Sold Separately:



SR400
Remote Control
with Receiver



SW405
Wall Control
with Receiver

Recommended Accessories

Sold separately.




LK1500MLEDXXX
Opal Matte Harlow L.E.D. Light Fixture,
pg 127



CFFC4XXX
Four-Light Contemporary Fitter, pg 132

See pg 126-133 for additional
light accessories & finishes.



E. Designer - Venetian Bronze CF755VNB
Dark Cherry/Mahogany Blades



T

29" Northwind

29" Northwind Energy Ratings at High Speed


Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
3430	47	73



- 29" blade span
- Light fixture adaptable
- 3.5" downrod included



Shown with Dark Cherry Blades



A. 29" Northwind - Oil Rubbed Bronze CF702ORB
Dark Cherry/Walnut Blades



Shown with Appliance White
Blades and Tilo Light Fixture
(LK130, pg 130)

B. 29" Northwind - Appliance White CF702WW
Appliance White/Bleached Oak Blades

- A. **29" NORTHWIND – OIL RUBBED BRONZE CF702ORB** - Dark Cherry/Walnut Blades
- 5 reversible blades
 - Light fixture adaptable
 - 3.5" downrod included

- B. **29" NORTHWIND – APPLIANCE WHITE CF702WW** - Appliance White/Bleached Oak Blades
- 5 reversible blades
 - Light fixture adaptable
 - 3.5" downrod included

Included:



Sold Separately:



29" Northwind

Prima Snuggler™

Prima Snuggler™ Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
5145	64	80



- 52" blade span
- Light fixture adaptable



Shown with Dark Cherry
Blades and Low Light
Fixture (LK53BS, pg 129)



C. **Prima Snuggler - Brushed Steel CF905BS**
Dark Cherry/Chocolate Blades

Shown with Satin White Blades




D. **Prima Snuggler - Satin White CF905SW**
Satin White/Maple Blades

Shown with Walnut Blades and
Ashton Light L.E.D. Light Fixture in
Amber Mist (LK90LEDORB, pg 127)



E. **Prima Snuggler - Oil Rubbed Bronze CF905ORB**
Dark Cherry/Walnut Blades

Shown with Walnut Blades



F. **Prima Snuggler - Venetian Bronze CF905VNB**
Dark Cherry/Walnut Blades

- C. **PRIMA SNUGGER – BRUSHED STEEL CF905BS** - Dark Cherry/Chocolate Blades
- 5 reversible blades
 - Light fixture adaptable

- D. **PRIMA SNUGGER – SATIN WHITE CF905SW** - Satin White/Maple Blades
- 5 reversible blades
 - Light fixture adaptable

- E. **PRIMA SNUGGER – OIL RUBBED BRONZE CF905ORB** - Dark Cherry/Walnut Blades
- 5 reversible blades
 - Light fixture adaptable

- F. **PRIMA SNUGGER – VENETIAN BRONZE CF905VNB** - Dark Cherry/Walnut Blades
- 5 reversible blades
 - Light fixture adaptable

Recommended Accessories

Sold separately.




**LK GLO SERIES
L.E.D. LIGHT FIXTURE**
pg 126-127

See pg 126-133 for additional
light accessories.

Included:



Sold Separately:



52" Snugger

52" Snugger Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
4887	76	64



FAN HEIGHT

- L.E.D. LIGHT FIXTURE ADAPTABLE
- SHIPS TO CANADA
- LIMITED LIFETIME MOTOR WARRANTY

- 52" blade span
- Light fixture adaptable

Shown with Dark Cherry Blades



A. 52" Snugger - Oil Rubbed Bronze CF805SORB
Dark Cherry/Medium Oak Blades



Shown with Dark Cherry Blades and Low Profile Light Fixture (LK53BS, pg 129)



B. 52" Snugger - Brushed Steel CF805SBS
Dark Cherry/Mahogany Blades



Shown with Satin White Blades



C. 52" Snugger - Appliance White CF805SWW
Appliance White/Bleached Oak Blades



- A. **52" SNUGGER - OIL RUBBED BRONZE**
CF805SORB - Dark Cherry/Medium Oak Blades
 - 5 reversible blades
 - Light fixture adaptable
- B. **52" SNUGGER - BRUSHED STEEL**
CF805SBS - Dark Cherry/Mahogany Blades
 - 5 reversible blades
 - Light fixture adaptable
- C. **52" SNUGGER - APPLIANCE WHITE**
CF805SWW - Appliance White/Bleached Oak Blades
 - 5 reversible blades
 - Light fixture adaptable

Included:



FIVE REVERSIBLE BLADES

Sold Separately:



LK GLO SERIES L.E.D. LIGHT FIXTURE
pg 126-127



SW46
Wall Control



SW90
Wall Control

52" Snugger

42" Snugger

42" Snugger Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
3761	82	46



FAN HEIGHT

- L.E.D. LIGHT FIXTURE ADAPTABLE
- SHIPS TO CANADA
- LIMITED LIFETIME MOTOR WARRANTY

- 42" blade span
- Light fixture adaptable

Shown with Dark Cherry Blades



D. 42" Snugger - Brushed Steel CF804SBS
Dark Cherry/Mahogany Blades



Shown with Satin White Blades



E. 42" Snugger - Appliance White CF804SWW
Appliance White/Bleached Oak Blades



- D. **42" SNUGGER - BRUSHED STEEL**
CF804SBS - Dark Cherry/Mahogany Blades
 - 5 reversible blades
 - Light fixture adaptable
- E. **42" SNUGGER - APPLIANCE WHITE**
CF804SWW - Appliance White/Bleached Oak Blades
 - 5 reversible blades
 - Light fixture adaptable
- F. **42" SNUGGER - OIL RUBBED BRONZE**
CF804SORB - Dark Cherry/Medium Oak Blades
 - 5 reversible blades
 - Light fixture adaptable

Included:



FIVE REVERSIBLE BLADES

Sold Separately:



LK GLO SERIES L.E.D. LIGHT FIXTURE
pg 126-127



SW46
Wall Control



SW90
Wall Control

Shown with Dark Cherry Blades and Moon Light Fixture (LK65ORB, pg 129)



F. 42" Snugger - Oil Rubbed Bronze CF804SORB
Dark Cherry/Medium Oak Blades



T

Batalie Breeze
CF621 - pg 96

I/O

INDOOR/OUTDOOR DESIGN



VOLTA
CF590 - pg 92



WELLAND
CF610 - pg 94



BATALIE BREEZE
CF621 - pg 96



MAUI BAY
CF2000 - pg 98



SUMMERHAVEN
CF850 - pg 100



52" & 42" VERANDA
CF552/CF542 - pg 102



DEVONSHIRE
CF670 - pg 104



SEA BREEZE
CF654 - pg 105



52" SUMMER NIGHT
CF652 - pg 106



42" SUMMER NIGHT
CF742PF - pg 107

DAMP LOCATION RATED

K55 MOTOR

WET LOCATION RATED

L.E.D. LIGHT FIXTURE ADAPTABLE


INTEGRATED L.E.D. LIGHTING



WET LOCATION

Wet location fans can be placed in outdoor areas directly exposed to precipitation.

- 52" Curva Sky* pg 60
- 44" Curva Sky* pg 60
- 52" Curva* pg 62
- 44" Curva* pg 62
- Volta pg 92
- Welland pg 94
- Batalie Breeze pg 96
- Summerhaven pg 100
- 52" Veranda pg 102
- 42" Veranda pg 102
- Sea Breeze pg 105



DAMP LOCATION

Damp location fans can be placed in covered outdoor areas.

- Carrera pg 20
- Carrera Grande Eco* pg 22
- Aira Eco* pg 44
- Loft* pg 58
- Atomical* pg 64
- Tilo* pg 67
- Maui Bay* pg 98
- Devonshire pg 104
- 52" Summer Night pg 106
- 42" Summer Night pg 107

*Certain finishes only. See fan pages for details.

NEW!

Volta

Volta Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
6300*	81.5*	77.3*

14.5"  FAN HEIGHT

*Estimated. Visit our website at emersonfans.com for up-to-date information.

 WET LOCATION RATED

 SHIPS TO CANADA

 INTEGRATED L.E.D. LIGHTING

 LIMITED LIFETIME MOTOR WARRANTY

- 54" blade span
- Integrated L.E.D. light kit
 - 2,600 Lumens
 - 95 CRI
 - 3,000K CCT
 - 32 Watts
- 4.5" downrod included
- Optional no-light plate included



A. **Volta - Platinum CF590PT**
Weather-Resistant Platinum Blades

- A. **VOLTA - PLATINUM CF590PT** - Weather-Resistant Platinum Blades
- 3 custom blades
 - SW405 wall control
 - Integrated L.E.D. light fixture
 - Removable no-light plate
 - 4.5" downrod included



B. **Volta - Satin White CF590SW**
Weather-Resistant Satin White Blades


- B. **VOLTA - SATIN WHITE CF590SW** - Weather-Resistant Satin White Blades
- 3 custom blades
 - SW405 wall control
 - Integrated L.E.D. light fixture
 - Removable no-light plate
 - 4.5" downrod included



C. **Volta - Barbeque Black CF590BQ**
Weather-Resistant Natural Cherry Blades

- C. **VOLTA - BARBEQUE BLACK CF590BQ** - Weather-Resistant Natural Cherry Blades
- 3 custom blades
 - SW405 wall control
 - Integrated L.E.D. light fixture
 - Removable no-light plate
 - 4.5" downrod included

Included:



THREE CUSTOM BLADES



REMOVABLE NO-LIGHT PLATE



INTEGRATED L.E.D. LIGHT FIXTURE



SW405 Wall Control¹ with Receiver

¹ Controls recommended for indoor use only.



C. **Volta - Barbeque Black CF590BQ**
Weather-Resistant Natural Cherry Blades

Volta

|o

Welland

Welland Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
5081	57.8	87.9

12.3"
FAN HEIGHT

- WET LOCATION RATED
- SHIPS TO CANADA
- L.E.D. LIGHT FIXTURE ADAPTABLE
- LIMITED LIFETIME MOTOR WARRANTY

View videos about Welland's features and installation at MyEmersonFans.com/Videos



A. Welland - Venetian Bronze CF610VNB
Rustic Tropical Medium Antique Brown Blades

- A. **WELLAND – VENETIAN BRONZE CF610VNB** - Rustic Tropical Medium Antique Brown Blades
- 5 weather-resistant blades
 - Light fixture adaptable
 - 4.5" downrod included

- B. **WELLAND – VINTAGE STEEL CF610VS** - Rustic Tropical Medium Antique Brown Blades
- 5 weather-resistant blades
 - Light fixture adaptable
 - 4.5" downrod included

Included:



FIVE WEATHER-RESISTANT BLADES

Welland

B. Welland - Vintage Steel CF610VS
Rustic Tropical Medium Antique Brown Blades



Batalie Breeze

Batalie Breeze Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
5255	75	70

14.5"
FAN HEIGHT

WET LOCATION RATED SHIPS TO CANADA LIMITED LIFETIME MOTOR WARRANTY

- 52" blade span
- Light fixture adaptable
- 4.5" downrod included



A. Batalie Breeze - Venetian Bronze CF621VNB
Weather-Resistant Antique Stain Wicker Leaf Blades




B. Batalie Breeze - Satin White CF621SW
Weather-Resistant Satin White Highlights Wicker Leaf Blades

- A. **BATALIE BREEZE – VENETIAN BRONZE CF621VNB** - Weather-Resistant Antique Stain Wicker Leaf Blades
- 5 custom blades
 - Light fixture adaptable
 - 4.5" downrod included

- B. **BATALIE BREEZE – SATIN WHITE CF621SW** - Weather-Resistant Satin White Highlights Wicker Leaf Blades
- 5 custom blades
 - Light fixture adaptable
 - 4.5" downrod included

Included:



**FIVE
CUSTOM
BLADES**

Suggested Light Fixture

Sold separately.



LK92VNB
Ashton Wet Light Fixture, pg 129

See pg 126-133 for additional light accessories.

Sold Separately:



SR400
Remote Control¹
with Receiver



SW405
Wall Control¹
with Receiver



SW46
Wall Control¹

¹ Controls recommended for indoor use only.

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
5140	56	92

15.0"
FAN HEIGHT

K55
K55XL
MOTOR

L.E.D. LIGHT
FIXTURE ADAPTABLE

DAMP LOCATION RATED¹

SHIPS TO CANADA
FAN ONLY

LIMITED LIFETIME
MOTOR WARRANTY

View videos about Maui Bay's features and installation at MyEmersonFans.com/Videos

- 52" blade span
- Light fixture adaptable
- 6" downrod included
- 4 or 5 blade assembly option

Shown with Hand Carved Walnut Blades (B50HCW, see below) and Boardwalk Light Fixture (LK40ORB, pg 131)



Shown with Dark Mahogany Bentwood Blades (B65DM, see below) and Ashton L.E.D. Light Fixture in Amber Mist (LK90LEDORB, pg 127)



B1. Maui Bay - Oil Rubbed Bronze CF2000ORB

- B. MAUI BAY - OIL RUBBED BRONZE CF2000ORB -
- Light Fixture Adaptable
 - 4 or 5 Blade Assembly Option
 - 6" downrod included

B2. Maui Bay - Oil Rubbed Bronze CF2000ORB

Choose from any of the following blades to complete your custom Maui Bay ceiling fan. For optimum air movement use four blades. Blades come in sets of 5.



B50DC
• Dark Cherry Hand Carved Leaf



B50DO
• Dark Oak Hand Carved Leaf



B50HCW
• Hand Carved Walnut



B65DM
• Dark Mahogany Bent Wood (80" blade span)



B65DO
• Dark Oak Bent Wood (80" blade span)

B65 blade performance specifications- High Speed: 50 RPM; Medium Speed: 35 RPM; Low Speed: 15 RPM

Sold Separately:



MAUI BAY
CUSTOM
BLADES



LK GLO SERIES
L.E.D. LIGHT FIXTURE
pg 126-127



SW605
Wall Control²



SR650
2-in-1 Remote
Control²




SR600
Remote
Control²



RCK55
Horseshoe
Receiver²

¹ Damp location with select blades. Damp location rated for ORB finish only.
² Controls are recommended for indoor use only.



Summerhaven

Summerhaven Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
6118	61	99

14.4"
FAN HEIGHT

- 52" blade span
- Integrated light fixture uses three 25-watt candelabra bulbs
- 4.5" downrod included

WET LOCATION RATED SHIPS TO CANADA LIMITED LIFETIME MOTOR WARRANTY



A. Summerhaven - Venetian Bronze CF850VNB
Weather-Resistant Venetian Bronze Blades, Amber Mist Glass

Summerhaven



B. Summerhaven - Golden Espresso CF850GES
Weather-Resistant Golden Espresso Blades, Amber Mist Glass

- A. **SUMMERHAVEN – VENETIAN BRONZE**
CF850VNB - Weather-Resistant Venetian Bronze Blades, Amber Mist Glass
- 5 weather-resistant blades
 - Integrated light fixture
 - 4.5" downrod included
- B. **SUMMERHAVEN – GOLDEN ESPRESSO**
CF850GES - Weather-Resistant Golden Espresso Blades, Amber Mist Glass
- 5 weather-resistant blades
 - Integrated light fixture
 - 4.5" downrod included

Included:



FIVE WEATHER-RESISTANT BLADES



INTEGRATED LIGHT FIXTURE

Sold Separately:



SR400
Remote Control¹
with Receiver



SW405
Wall Control¹
with Receiver

¹ Controls are recommended for indoor use only.

52" & 42" Veranda™

52" & 42" Veranda™ Energy Ratings at High Speed

Blade	Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
52"	5967	73	82
42"	4421	53	83



- 52" or 42" blade span (42" Select Finishes Only)
- Light fixture adaptable
- 4.5" downrod included

Shown with 12" Downrod (CFDR1ORB, pg 5) and Boardwalk Light Fixture (LK40ORB, pg 131)



A. 52" & 42" Veranda - Oil Rubbed Bronze CF552ORB / CF542ORB
Weather-Resistant Oil Rubbed Bronze Blades



Shown with 12" Downrod (CFDR1GES, pg 5)

B. 52" Veranda - Golden Espresso CF552GES
Weather-Resistant Chocolate Blades



B. 52" Veranda - Summer White CF552AW
Weather-Resistant Summer White Blades

- A. **52" & 42" VERANDA – OIL RUBBED BRONZE**
CF552ORB - 52" Weather-Resistant Oil Rubbed Bronze Blades
CF542ORB - 42" Weather-Resistant Oil Rubbed Bronze Blades
- 5 weather-resistant blades
 - Light fixture adaptable
 - 4.5" downrod included
- B. **52" VERANDA – GOLDEN ESPRESSO**
CF552GES - 52" Weather-Resistant Chocolate Blades
- 5 weather-resistant blades
 - Light fixture adaptable
 - 4.5" downrod included
- B. **52" VERANDA – SUMMER WHITE**
CF552AW - 52" Weather-Resistant Summer White Blades
- 5 weather-resistant blades
 - Light fixture adaptable
 - 4.5" downrod included
- C. **52" VERANDA – VINTAGE STEEL**
CF552VS - 52" Weather-Resistant Walnut Blades
- 5 weather-resistant blades
 - Light fixture adaptable
 - 4.5" downrod included

Suggested Light Fixture

Sold separately.




LK40
Boardwalk Cage Light Fixture, pg 131



LK92
Ashton Wet Light Fixture, pg 129

See pg 134-141 for additional light accessories.

Included:



FIVE WEATHER-RESISTANT BLADES

Sold Separately:



SR400
Remote Control¹
with Receiver



SW405
Wall Control¹
with Receiver



SW46
Wall Control¹

¹ Controls recommended for indoor use only.

52" & 42" Veranda



D. 52" Veranda - Vintage Steel CF552VS
Weather-Resistant Walnut Blades



Devonshire™

Devonshire™ Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
6186	70	89

12.0"
FAN HEIGHT

- L.E.D. LIGHT FIXTURE ADAPTABLE
- DAMP LOCATION RATED
- SHIPS TO CANADA
- LIMITED LIFETIME MOTOR WARRANTY

- 52" blade span
- Light fixture adaptable
- 4.5" downrod included

Devonshire

A. Devonshire - Oil Rubbed Bronze CF670ORB
Weather-Resistant Oil Rubbed Bronze Blades



A. DEVONSHIRE – OIL RUBBED BRONZE
CF670ORB - Weather-Resistant Oil Rubbed Bronze Blades
• 5 weather-resistant blades
• Light fixture adaptable
• 4.5" downrod included

Included:



FIVE WEATHER-RESISTANT BLADES

Sold Separately:



SR400
Remote Control¹
with Receiver



SW405
Wall Control¹
with Receiver



SW46
Wall Control¹

Suggested Light Fixtures

Sold separately.



LK GLO SERIES L.E.D. LIGHT FIXTURE
pg 126-127



LK92
Ashton Wet Light Fixture, pg 129



WLP100XXX
Wet Location Plate, pg 128

See pg 126-133
for additional light
accessories.

¹ Controls are recommended for indoor use only.

Sea Breeze™

Sea Breeze™ Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
6492	72	90

14.0"
FAN HEIGHT

- L.E.D. LIGHT FIXTURE ADAPTABLE
- WET LOCATION RATED
- SHIPS TO CANADA
- LIMITED LIFETIME MOTOR WARRANTY

- 52" blade span
- Light fixture adaptable
- 3.5" downrod included

Sea Breeze

Shown with Seaside Light Fixture (LK46ORB, pg 131)



B. Sea Breeze - Oil Rubbed Bronze CF654ORB
Weather-Resistant Oil Rubbed Bronze Blades



C. Sea Breeze - Appliance White CF654WW
Weather-Resistant Appliance White Blades

B. SEA BREEZE – OIL RUBBED BRONZE
CF654ORB - Weather-Resistant Oil Rubbed Bronze Blades
• 5 weather-resistant blades
• Light fixture adaptable
• 3.5" downrod included

C. SEA BREEZE – APPLIANCE WHITE
CF654WW - Weather-Resistant Appliance White Blades
• 5 weather-resistant blades
• Light fixture adaptable
• 3.5" downrod included

Included:



FIVE WEATHER-RESISTANT BLADES

Sold Separately:



SR400
Remote Control¹
with Receiver



SW405
Wall Control¹
with Receiver



SW46
Wall Control¹

Recommended Accessories:

Sold separately.



LK71XXX
Amber Parchment
Light Fixture, pg 128



LK46
Seaside Light Fixture, pg 131



WLP100XXX
Wet Location Plate, pg 128



LK40
Boardwalk Cage Light Fixture, pg 131

See pg 126-133 for additional light accessories.

¹ Controls are recommended for indoor use only.

52" Summer Night®

52" Summer Night® Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
5334	62	86

11.8"
FAN HEIGHT

- L.E.D. LIGHT FIXTURE ADAPTABLE
- DAMP LOCATION RATED
- SHIPS TO CANADA
- LIMITED LIFETIME MOTOR WARRANTY

- 52" blade span
- Light fixture adaptable
- 3.5" downrod included



A. 52" Summer Night - Oil Rubbed Bronze CF652ORB
Weather-Resistant Oil Rubbed Bronze Blades

Shown with Low-Profile Light Fixture (LK53WW, pg 129)



B. 52" Summer Night - Appliance White CF652WW
Weather-Resistant Appliance White Blades

- A. **52" SUMMER NIGHT – OIL RUBBED BRONZE CF652ORB** - Weather-Resistant Oil Rubbed Bronze Blades
 - 5 weather-resistant blades
 - Light fixture adaptable
 - 3.5" downrod included
- B. **52" SUMMER NIGHT – APPLIANCE WHITE CF652WW** - Weather-Resistant Appliance White Blades
 - 5 weather-resistant blades
 - Light fixture adaptable
 - 3.5" downrod included

52" Summer Night

42" Summer Night®

42" Summer Night® Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
4105	47	88

12.0"
FAN HEIGHT


- L.E.D. LIGHT FIXTURE ADAPTABLE
- DAMP LOCATION RATED
- SHIPS TO CANADA
- LIMITED LIFETIME MOTOR WARRANTY

- 42" blade span
- Light fixture adaptable
- 3.5" downrod included



C. 42" Summer Night - Oil Rubbed Bronze CF742PFORB
Weather-Resistant Oil Rubbed Bronze Blades

Shown with Schoolhouse Damp Light Fixture (CFSLKPFWW, pg 131)



D. 42" Summer Night - Appliance White CF742PFWW
Weather-Resistant Appliance White Blades

- C. **42" SUMMER NIGHT – OIL RUBBED BRONZE CF742PFORB** - Weather-Resistant Oil Rubbed Bronze Blades
 - 5 weather-resistant blades
 - Light fixture adaptable
 - 3.5" downrod included
- D. **42" SUMMER NIGHT – APPLIANCE WHITE CF742PFWW** - Weather-Resistant Appliance White Blades
 - 5 weather-resistant blades
 - Light fixture adaptable
 - 3.5" downrod included

Included:



FIVE WEATHER-RESISTANT BLADES

Sold Separately:



LK GLO SERIES L.E.D. LIGHT FIXTURE
pg 126-127



SW46
Wall Control¹



SW90
Wall Control¹

¹ Controls are recommended for indoor use only.

Sold Separately:



LK GLO SERIES L.E.D. LIGHT FIXTURE
pg 126-127



SW46
Wall Control¹



SW90
Wall Control¹

¹ Controls are recommended for indoor use only.

Included:



FIVE WEATHER-RESISTANT BLADES

Ashland
CF717 - pg 110

P
PRO SERIES DESIGN



ASHLAND
CF717 - pg 110



PRO SERIES
CF712 - pg 112



PRO SERIES ES
CF713 - pg 114




50" PRO SERIES II
CF711 - pg 116



42" PRO SERIES II
CF710 - pg 118



BUILDER
CF700 - pg 120



60" INDUSTRIAL FAN
HF1160 - pg 122



56" INDUSTRIAL FAN
HF956 - pg 122



48" INDUSTRIAL FAN
HF948 - pg 122



UPDATED! Ashland


Ashland Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
4939	56	88

17.5"
13.0"
FAN HEIGHT

LIMITED LIFETIME MOTOR WARRANTY

- **New!** No-Light Option included
- **New!** Medium-base light fixture with three 13-watt CFL bulbs (included)
- 52" blade span
- 4.5" downrod included

 [View videos about Ashland's features and installation at MyEmersonFans.com/Videos](http://MyEmersonFans.com/Videos)



Shown with Walnut Blades and Included Opal Matte Glass Light Fixture

A. Ashland - Brushed Steel CF717BS
Dark Cherry/Walnut Blades, Opal Matte Glass



Shown with Dark Cherry Blades and Included No-Light Option Installed



Shown with Dark Cherry Blades and Included Opal Matte Glass Light Fixture

B. Ashland - Oil Rubbed Bronze CF717ORB
Dark Cherry/Walnut Blades, Opal Matte Glass




Shown with Maple Blades and Included No-Light Option


C. Ashland - Satin White CF717SW
Satin White/Maple Blades, Opal Matte Glass




Included:



NEW!
NO-LIGHT SWITCH CUP



FIVE REVERSIBLE BLADES



LIGHT FIXTURE



DUAL-MOUNT FEATURE

- A. ASHLAND – BRUSHED STEEL CF717BS** - Dark Cherry/Walnut Blades, Opal Matte Glass
- **New No-Light Option Included**
 - 5 reversible blades
 - Light fixture
 - Dual-Mount feature
 - 4.5" downrod included
- B. ASHLAND – OIL RUBBED BRONZE CF717ORB** - Dark Cherry/Walnut Blades, Opal Matte Glass
- **New No-Light Option Included**
 - 5 reversible blades
 - Light fixture
 - Dual-Mount feature
 - 4.5" downrod included
- C. ASHLAND – SATIN WHITE CF717SW** - Satin White/Maple Blades, Opal Matte Glass
- **New No-Light Option Included**
 - 5 reversible blades
 - Light fixture
 - Dual-Mount feature
 - 4.5" downrod included

Pro Series™

Pro Series™ Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
5224	61	85

18.5"
14.8"
FAN HEIGHT

**QUICK & EASY
INSTALLATION**

SHIPS TO CANADA

**LIMITED LIFETIME
MOTOR WARRANTY**

[View installation help
videos for the Pro Series at
MyEmersonFans.com/Videos](#)

- 50" blade span
- Light fixture uses three 60-watt candelabra base bulbs (included)
- Precision-Lock™ blade arms with pre-attached screws allow for quick and easy assembly of blades
- Removable light fixture can be replaced with switch cover if desired (included)
- Easy install mounting bracket
- Dual mounting for close-to-the-ceiling or downrod installation
- 4.5" downrod included - Adaptable up to 3' downrod

Shown with
Dark Cherry Blades



A. **Pro Series - Oil Rubbed Bronze** CF712WORB
Dark Cherry/Medium Oak Blades, Opal Matte Glass



Shown with Appliance
White Blades &
12" Downrod
(CFDRWW, pg 5)



B. **Pro Series - Appliance White** CF712WW
Appliance White/Bleached Oak Blades, Opal Matte Glass



Shown with
Dark Cherry Blades



C. **Pro Series - Oil Rubbed Bronze** CF712ORB
Dark Cherry/Medium Oak Blades, Amber Scavo Glass



Shown with
Summer White Blades



D. **Pro Series - Summer White** CF712AW
Summer White/Bleached Oak Blades, Opal Matte Glass



- A. PRO SERIES – OIL RUBBED BRONZE**
CF712WORB - Dark Cherry/Medium Oak Blades, Opal Matte Glass
- 5 reversible blades
 - Dual-Mount feature
 - Light fixture
 - Removable no-light cover
 - Easy install mounting bracket
 - 4.5" downrod included – Adaptable up to 3' downrod
- B. PRO SERIES – APPLIANCE WHITE**
CF712WW - Appliance White/Bleached Oak Blades, Opal Matte Glass
- 5 reversible blades
 - Dual-Mount feature
 - Light fixture
 - Removable no-light cover
 - Easy install mounting bracket
 - 4.5" downrod included – Adaptable up to 3' downrod
- C. PRO SERIES – OIL RUBBED BRONZE**
CF712ORB - Dark Cherry/Medium Oak Blades, Amber Scavo Glass
- 5 reversible blades
 - Dual-Mount feature
 - Light fixture
 - Removable no-light cover
 - Easy install mounting bracket
 - 4.5" downrod included – Adaptable up to 3' downrod
- D. PRO SERIES – SUMMER WHITE**
CF712AW - Summer White/Bleached Oak Blades, Opal Matte Glass
- 5 reversible blades
 - Dual-Mount feature
 - Light fixture
 - Removable no-light cover
 - Easy install mounting bracket
 - 4.5" downrod included – Adaptable up to 3' downrod
- E. PRO SERIES – BRUSHED STEEL**
CF712BS - Mahogany/Dark Cherry Blades, Opal Matte Glass
- 5 reversible blades
 - Dual-Mount feature
 - Light fixture
 - Removable no-light cover
 - Easy install mounting bracket
 - 4.5" downrod included – Adaptable up to 3' downrod
- F. PRO SERIES – ANTIQUE BRASS**
CF712AB - Medium Oak/Walnut Blades, Opal Matte Glass
- 5 reversible blades
 - Dual-Mount feature
 - Light fixture
 - Removable no-light cover
 - Easy install mounting bracket
 - 4.5" downrod included – Adaptable up to 3' downrod

Pro Series




Shown with Dark Cherry Blades

E. **Pro Series - Brushed Steel** CF712BS
Mahogany/Dark Cherry Blades, Opal Matte Glass




P


Included:




**FIVE
REVERSIBLE
BLADES**



**DUAL-MOUNT
FEATURE**



**LIGHT
FIXTURE**



**REMOVABLE
NO-LIGHT
COVER**



Shown with
Walnut Blades

F. **Pro Series - Antique Brass** CF712AB
Medium Oak/Walnut Blades, Opal Matte Glass



Sold Separately:



SW90
Wall Control



SW46
Wall Control

Pro Series ES

Pro Series ES Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
5027	65	77


18.5"
14.8"
FAN HEIGHT

INCLUDES FLUORESCENT
GU-24 BULBS


- 50" blade span
- Light fixture uses three 13-watt GU-24 bulbs (included)
- Precision-Lock™ blade arms with pre-attached screws for quick & easy assembly of blades
- Removable light fixture can be replaced with switch cover if desired (included)
- Easy install mounting bracket
- Dual mounting for close-to-the-ceiling or downrod installation
- 4.5" downrod included - adaptable up to 3' downrod



B. Pro Series ES - Oil Rubbed Bronze CF713ORB
Dark Cherry/Medium Oak Blades, Amber Scavo Glass



C. Pro Series ES - Appliance White CF713WW
Appliance White/Bleached Oak Blades, Alabaster Glass



Shown with Dark Cherry Blades


A. Pro Series ES - Brushed Steel CF713BS
Dark Cherry/Mahogany Blades, Alabaster Glass

- A. **PRO SERIES ES – BRUSHED STEEL**
CF713BS - Dark Cherry/Mahogany Blades, Alabaster Glass
- 5 reversible blades
 - Dual-Mount feature
 - Light fixture
 - Removable no-light switch cover
 - Easy install mounting bracket
 - 4.5" downrod included – adaptable up to 3' downrod
- B. **PRO SERIES ES – OIL RUBBED BRONZE**
CF713ORB - Dark Cherry/Medium Oak Blades, Amber Scavo Glass
- 5 reversible blades
 - Dual-Mount feature
 - Light fixture
 - Removable no-light switch cover
 - Easy install mounting bracket
 - 4.5" downrod included – adaptable up to 3' downrod
- C. **PRO SERIES ES – APPLIANCE WHITE**
CF713WW - Appliance White/Bleached Oak Blades, Alabaster Glass
- 5 reversible blades
 - Dual-Mount feature
 - Light fixture
 - Removable no-light switch cover
 - Easy install mounting bracket
 - 4.5" downrod included – adaptable up to 3' downrod


Included:



FIVE REVERSIBLE
BLADES



DUAL-MOUNT
FEATURE



LIGHT
FIXTURE



REMOVABLE
NO-LIGHT
COVER

50" Pro Series II

50" Pro Series II Energy Ratings at High Speed

Airflow Cubic Ft. Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft. Per Min. Per Watt
5403	64	84

14.8"
18.5"
FAN HEIGHT



QUICK & EASY
INSTALLATION



LIMITED LIFETIME
MOTOR WARRANTY

- 50" blade span
- Easy install mounting bracket
- Snap-on glass for easy installation
- Light fixture furnished with four 13-watt medium base compact fluorescent bulbs (included)
- UL rated for four 60-watt incandescent
- Precision-Lock™ blade arms with pre-attached screws allow for quick and easy assembly of blades
- Removable light fixture can be replaced with switch cover if desired (included)
- Dual mounting for close-to-the-ceiling or downrod installation
- 4.5" downrod included - adaptable up to 3' downrod

Shown with Mahogany Blades



50" Pro Series II

Shown with Dark Cherry Blades



A. 50" Pro Series II - Oil Rubbed Bronze CF711ORB
Dark Cherry/Medium Oak Blades, Opal Matte Glass



Shown with Appliance White Blades & 12" Downrod (CFDRWW, pg 5)



B. 50" Pro Series II - Appliance White CF711WW
Appliance White/Bleached Oak Blades, Opal Matte Glass



Shown with Dark Cherry Blades



C. 50" Pro Series II - Oil Rubbed Bronze CF711ORS
Dark Cherry/Medium Oak Blades, Amber Scavo Glass



Shown with Walnut Blades



D. 50" Pro Series II - Antique Brass CF711AB
Walnut/Medium Oak Blades, Opal Matte Glass



A. 50" PRO SERIES II – OIL RUBBED BRONZE

- CF711ORB** - Dark Cherry/Medium Oak Blades, Opal Matte Glass
- 5 reversible blades
 - 4-Way light fixture
 - Dual-Mount feature
 - Removable no-light cover
 - Easy install mounting bracket & snap-on glass
 - Precision-Lock™ blade arms with pre-attached screws
 - 4.5" downrod included – adaptable up to 3' downrod

B. 50" PRO SERIES II – APPLIANCE WHITE

- CF711WW** - Appliance White/Bleached Oak Blades, Opal Matte Glass
- 5 reversible blades
 - 4-Way light fixture
 - Dual-Mount feature
 - Removable no-light cover
 - Easy install mounting bracket & snap-on glass
 - Precision-Lock™ blade arms with pre-attached screws
 - 4.5" downrod included – adaptable up to 3' downrod

C. 50" PRO SERIES II – OIL RUBBED BRONZE

- CF711ORS** - Dark Cherry/Medium Oak Blades, Amber Scavo Glass
- 5 reversible blades
 - 4-Way light fixture
 - Dual-Mount feature
 - Removable no-light cover
 - Easy install mounting bracket & snap-on glass
 - Precision-Lock™ blade arms with pre-attached screws
 - 4.5" downrod included – adaptable up to 3' downrod

D. 50" PRO SERIES II – ANTIQUE BRASS

- CF711AB** - Walnut/Medium Oak Blades, Opal Matte Glass
- 5 reversible blades
 - 4-Way light fixture
 - Dual-Mount feature
 - Removable no-light cover
 - Easy install mounting bracket & snap-on glass
 - Precision-Lock™ blade arms with pre-attached screws
 - 4.5" downrod included – adaptable up to 3' downrod


E. 50" PRO SERIES II – BRUSHED STEEL

- CF711BS** - Dark Cherry/Mahogany Blades, Opal Matte Glass
- 5 reversible blades
 - 4-Way light fixture
 - Dual-Mount feature
 - Removable no-light cover
 - Easy install mounting bracket & snap-on glass
 - Precision-Lock™ blade arms with pre-attached screws
 - 4.5" downrod included – adaptable up to 3' downrod


E. 50" Pro Series II - Brushed Steel CF711BS
Dark Cherry/Mahogany Blades, Opal Matte Glass




Included:




FIVE REVERSIBLE BLADES



DUAL-MOUNT FEATURE



4-WAY LIGHT FIXTURE



REMOVABLE NO-LIGHT COVER


Sold Separately:



SW90
Wall Control



SW46
Wall Control



P

42" Pro Series II

42" Pro Series II Energy Ratings at High Speed


Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
3834	45	86

14.5"
17.3"
FAN HEIGHT

QUICK & EASY
INSTALLATION

LIMITED LIFETIME
MOTOR WARRANTY

- 42" blade span
- Easy install mounting bracket
- Snap-on glass for easy installation
- Light fixture furnished with three 13-watt medium base compact fluorescent bulbs (included)
- UL rated for three 60-watt incandescent
- Precision-Lock™ blade arms with pre-attached screws allow for quick and easy assembly of blades
- Removable light fixture can be replaced with switch cover if desired (included)
- Dual mounting for close-to-the-ceiling or downrod installation
- 3.5" downrod included - adaptable up to 3' downrod



Shown with Mahogany Blades

A. 42" Pro Series II - Brushed Steel CF710BS
Dark Cherry/Mahogany Blades, Opal Matte Glass



Shown with
Dark Cherry Blades



B. 42" Pro Series II - Oil Rubbed Bronze CF710ORB
Dark Cherry/Medium Oak Blades, Opal Matte Glass



Shown with Appliance
White Blades & 12" Downrod
(CFDRWW, pg 5)



C. 42" Pro Series II - Appliance White CF710WW
Appliance White/Bleached Oak Blades, Opal Matte Glass



A. 42" PRO SERIES II - BRUSHED STEEL

- CF710BS** - Dark Cherry/Mahogany Blades, Opal Matte Glass
- 5 reversible blades
 - 3-Way light fixture
 - Dual-Mount feature
 - Removable no-light cover
 - Easy install mounting bracket & snap-on glass
 - Precision-Lock™ blade arms with pre-attached screws
 - 3.5" downrod included - adaptable up to 3' downrod


B. 42" PRO SERIES II - OIL RUBBED BRONZE

- CF710ORB** - Dark Cherry/Medium Oak Blades, Opal Matte Glass
- 5 reversible blades
 - 3-Way light fixture
 - Dual-Mount feature
 - Removable no-light cover
 - Easy install mounting bracket & snap-on glass
 - Precision-Lock™ blade arms with pre-attached screws
 - 3.5" downrod included - adaptable up to 3' downrod


C. 42" PRO SERIES II - APPLIANCE WHITE

- CF710WW** - Appliance White/Bleached Oak Blades, Opal Matte Glass
- 5 reversible blades
 - 3-Way light fixture
 - Dual-Mount feature
 - Removable no-light cover
 - Easy install mounting bracket & snap-on glass
 - Precision-Lock™ blade arms with pre-attached screws
 - 3.5" downrod included - adaptable up to 3' downrod

Included:



FIVE
REVERSIBLE
BLADES



DUAL-MOUNT
FEATURE



3-WAY
LIGHT
FIXTURE



REMOVABLE
NO-LIGHT
COVER

Sold Separately:



SW90
Wall Control



SW46
Wall Control

Builder

Builder Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt	12.0" FAN HEIGHT
5241	64	80	



- 52" blade span
- Die-cast hanger ball and bracket
- Light fixture adaptable
- 4.5" downrod included – adaptable up to 3' downrod



L.E.D. LIGHT FIXTURE ADAPTABLE

SHIPS TO CANADA FAN ONLY

LIMITED LIFETIME MOTOR WARRANTY

Shown with Mahogany Blades & 12" Downrod (CFDRWW, pg 5)



A. Builder – Brushed Steel CF700BS
Dark Cherry/Mahogany Blades



Shown with Appliance White Blades & 12" Downrod (CFDRWW, pg 5)



B. Builder – Appliance White CF700WW
Appliance White/Bleached Oak Blades



A. BUILDER – BRUSHED STEEL

- CF700BS** - Dark Cherry/Mahogany Blades
- 5 reversible blades
 - Die-cast hanger ball and bracket
 - Light fixture adaptable
 - 4.5" downrod included – adaptable up to 3' downrod

B. BUILDER – APPLIANCE WHITE

- CF700WW** - Appliance White/Bleached Oak Blades
- 5 reversible blades
 - Die-cast hanger ball and bracket
 - Light fixture adaptable
 - 4.5" downrod included – adaptable up to 3' downrod

C. BUILDER – OIL RUBBED BRONZE

- CF700ORB** - Dark Cherry/Medium Oak Blades
- 5 reversible blades
 - Die-cast hanger ball and bracket
 - Light fixture adaptable
 - 4.5" downrod included – adaptable up to 3' downrod

Included:



FIVE REVERSIBLE BLADES

Recommended Accessories:

Sold separately.



LK GLO SERIES L.E.D. LIGHT FIXTURE
pg 126-127



LK53 Low Profile Light Fixture, pg 129



F330 Three-Light Turtle Fitter, pg 132

See pg 126-133 for additional light accessories.

Sold Separately:



SW90 Wall Control



SW46 Wall Control

Shown with Dark Cherry Blades



C. Builder – Oil Rubbed Bronze CF700ORB
Dark Cherry/Medium Oak Blades



60" Industrial Fans HF1160


- **NEW! SW95 Wall Control now included**
- 60" span high-efficiency airfoil blades
- Blades must be mounted at least 10 feet above the floor
- Single speed fan using 120 volts
- Fan hung at 20 feet covers 3,500 sq. ft.
- Fan hung at 30 feet covers 2,900 sq. ft.
- Fan hung at 40 feet covers 2,200 sq. ft.
- Not reversible
- 6" downrod included
- Approved for residential and commercial use when blades are installed at least ten feet above the floor.

60" Industrial Fans Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
11562	93	124



12.8"
FAN HEIGHT



A. 60" Industrial Fan - Brushed Steel
HF1160BS
Brushed Steel Blades



B. 60" Industrial Fan - Appliance White
HF1160WW
Appliance White Blades

A. 60" INDUSTRIAL FAN – BRUSHED STEEL
HF1160BS - Brushed Steel Blades

B. 60" INDUSTRIAL FAN – APPLIANCE WHITE
HF1160WW - Appliance White Blades

C. 60" INDUSTRIAL FAN – BARBEQUE BLACK
HF1160BQ - Barbeque Black Blades

Included:



THREE AIRFOIL BLADES



SW95
Wall Control

C. 60" Industrial Fan - Barbeque Black HF1160BQ
Barbeque Black Blades

56" Industrial Fans HF956

- **NEW! SW95 Wall Control now included**
- 56" span contoured metal blades
- Supplied with "J" hook for easy installation and smooth performance
- Blades must be mounted at least 10 feet above the floor
- Single speed fan using 120 volts
- Fan hung at 20 feet covers 1,800 sq. ft.
- Fan hung at 30 feet covers 1,500 sq. ft.
- Fan hung at 40 feet covers 900 sq. ft.
- Not reversible
- 22" downrod included
- Approved for residential and commercial use when blades are installed at least ten feet above the floor.

56" Industrial Fans Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
9757	95	103



33.5"
FAN HEIGHT



D. 56" Industrial Fan - Barbeque Black
HF956BQ
Barbeque Black Blades



E. 56" Industrial Fan - Appliance White
HF956W
Appliance White Blades

D. 56" INDUSTRIAL FAN – BARBEQUE BLACK
HF956BQ - Barbeque Black Blades


E. 56" INDUSTRIAL FAN – APPLIANCE WHITE
HF956W - Appliance White Blades

F. 56" INDUSTRIAL FAN – BRUSHED STEEL
HF956BS - Brushed Steel Blades

Included:



THREE CONTOURED
METAL BLADES



SW95
Wall Control

F. 56" Industrial Fan - Brushed Steel HF956BS
Brushed Steel Blades

48" Industrial Fans HF948

- **NEW! SW95 Wall Control now included**
- 48" span contoured metal blades
- Supplied with "J" hook for easy installation and smooth performance
- Blades must be mounted at least 10 feet above the floor
- Single speed fan using 120 volts
- Fan hung at 20 feet covers 1,500 sq. ft.
- Fan hung at 30 feet covers 1,200 sq. ft.
- Fan hung at 40 feet covers 700 sq. ft.
- Not reversible
- 8" and 22" downrod included
- Approved for residential and commercial use when blades are installed at least ten feet above the floor.

48" Industrial Fans Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
6879	72	95



19.5"
33.5"
FAN HEIGHT



G. 48" Industrial Fan - Brushed Steel
HF948BS
Brushed Steel Blades



H. 48" Industrial Fan - Appliance White
HF948W
Appliance White Blades


G. 48" INDUSTRIAL FAN – BRUSHED STEEL
HF948BS - Brushed Steel Blades

H. 48" INDUSTRIAL FAN – APPLIANCE WHITE
HF948W - Appliance White Blades

Included:



THREE CONTOURED
METAL BLADES




SW95
Wall Control

Sold Separately, Compatible with
All Industrial Fans on this Page:



SW81

- Control
- 2-wire
 - Infinitely variable
 - 3 amps
 - Faceplate included



SW82

- Control
- 2-wire
 - Infinitely variable
 - 12 amps
 - Faceplate included

Penbrooke Select - Brushed Steel
CF5100BS - pg 14
Shown with LK180LEDBS Riley Opal Matte L.E.D. Light Fixture, pg 129

| A |

ACCESSORIES



**L.E.D. LIGHT
FIXTURES**
pg 126



**CUSTOM FINISH
LIGHT FIXTURES**
pg 128



**LIGHT FIXTURES
& FITTERS**
pg 130



2 1/4" GLASS
pg 133



**BLADE SELECT
SERIES BLADES**
pg 134



CONTROLS
pg 136



**FINISHES &
DOWNRODS**
pg 5



**BLADE SELECT
SERIES**



**INTEGRATED
L.E.D. LIGHTING**

L.E.D. LIGHT FIXTURES

LK GLO SERIES

L.E.D. Light Fixtures

Harnessing the technology of light-emitting diodes, we created our most energy efficient and longest-lasting light fixtures yet and backed them with the Emerson limited 5 year warranty. Our state-of-the-art LK GLO Series Light Fixtures come in 13 custom finishes, produce a softer, more uniform glow than conventional bulbs and last nearly three times as long. Look for the L.E.D. icon throughout the catalog for ceiling fans that feature integrated L.E.D. lighting or are compatible with L.E.D. light fixtures.




LIMITED 5 YEAR WARRANTY

On all LK GLO Series L.E.D. Light Fixtures



52" Bella- Brushed Steel
CF452BS - pg 36
Shown with Ashton L.E.D. Light
Fixture in White Mist (LK91LEDDBS)



All light fixture bowl caps shown with ORB finish. To complete the Ashton Light Fixture model number, replace xxx with finish code. Available in AB, AP, AW, BS, GBZ, GES, ORB, SW, VNB, VS and WW finishes. Finial packs: Include 3 versions of plates for various pull chain configurations, no hole, 1 hole & 2 hole options included in each pack. See page 5 for images of finishes.

LK90LEDXXX
ASHTON LIGHT FIXTURE
Amber Mist
(3.3" H x 11.5" W)
One 16 Watt L.E.D. array
Light Output: 1,200 Lumens
Color Temperature: 2,700 K
Color Rendering Index: > 80



LK91LED XXX
ASHTON LIGHT FIXTURE
White Mist
(3.3" H x 11.5" W)
One 16 Watt L.E.D. array
Light Output: 1,200 Lumens
Color Temperature: 2,700 K
Color Rendering Index: > 80



All light fixture bowl caps shown with ORB finish. To complete the Harlow and Riley Light Fixture models number, replace xxx with finish code. Available in AP, AW, BS, GBZ, GES, ORB, SW, VNB, VS and WW finishes. Finial packs: Include 3 versions of plates for various pull chain configurations, no hole, 1 hole & 2 hole options included in each pack. See page 5 for images of finishes.

LK1500MLEDXXX
HARLOW LIGHT FIXTURE
OPAL MATTE GLASS
(3.8" H X 11" W)
One 18 Watt L.E.D. array
Light Output: 1,400 Lumens
Color Temperature: 3,000 K
Color Rendering Index: > 80



LK180LEDXXX
RILEY LIGHT FIXTURE
OPAL MATTE
(3.3" H X 15.4" W)
One 18 Watt L.E.D. array
Light Output: 1,400 Lumens
Color Temperature: 3,000 K
Color Rendering Index: > 80



All light fixture bowl caps shown with ORB finish. To complete the model number, replace xxx with finish code. Bowl caps available in AB, AP, AW, BS, GBZ, GES, ORB, SW, VNB, VS and WW finishes. Finial packs: Include 3 versions of plates for various pull chain configurations, no hole, 1 hole & 2 hole options included in each pack. See page 5 for images of finishes.



LK70LEDXXX
AMBER MIST
(4.5" H x 12.38" W)
One 16 Watt L.E.D. array
Light Output: 1,200 Lumens
Color Temperature: 2,700 K
Color Rendering Index: > 80



LK71LEDXXX
AMBER PARCHMENT
(4.5" H X 12.38" W)
One 16 Watt L.E.D. array
Light Output: 1,200 Lumens
Color Temperature: 2,700 K
Color Rendering Index: > 80



LK72LEDXXX
AMBER SCAVO
(4.5" H X 12.38" W)
One 16 Watt L.E.D. array
Light Output: 1,200 Lumens
Color Temperature: 2,700 K
Color Rendering Index: > 80



LK81LEDXXX
OPAL MATTE
(4.25" H X 12.38" W)
One 16 Watt L.E.D. array
Light Output: 1,200 Lumens
Color Temperature: 2,700 K
Color Rendering Index: > 80



LK83LEDXXX
WHITE LINEN
(4.25" H X 12.38" W)
One 16 Watt L.E.D. array
Light Output: 1,200 Lumens
Color Temperature: 2,700 K
Color Rendering Index: > 80



LK141LEDXXX
GRANDE LIGHT FIXTURE
WHITE MIST
(4.25" H X 12.5" W)
One 16 Watt L.E.D. array
Light Output: 1,200 Lumens
Color Temperature: 2,700 K
Color Rendering Index: > 80



LK74LEDXXX
OPAL MATTE
(4.5" H X 12.38" W)
One 16 Watt L.E.D. array
Light Output: 1,200 Lumens
Color Temperature: 2,700 K
Color Rendering Index: > 80



LK77LEDXXX
WHITE LINEN
(4.5" H X 12.38" W)
One 16 Watt L.E.D. array
Light Output: 1,200 Lumens
Color Temperature: 2,700 K
Color Rendering Index: > 80



LK80LEDXXX
AMBER MIST
(4.25" H X 12.38" W)
One 16 Watt L.E.D. array
Light Output: 1,200 Lumens
Color Temperature: 2,700 K
Color Rendering Index: > 80

Please note that the pull chain can be removed when the ceiling fan is installed with a light control system.

CUSTOM FINISH LIGHT FIXTURES

USE IN ANY INDOOR OR OUTDOOR LOCATION*

Choose Light Fixture model #

LK70XXX

Choose Final Finish



Example:
LK70ORB:
Oil Rubbed Bronze

See page 5 for images of finishes

All light fixture bowl caps shown with ORB finish. To complete the model number, replace xxx with finish code. Bowl caps available in AB, AP, AW, BS, GBZ, GES, ORB, SW, VNB, VS and WW finishes. Final packs: Include 3 versions of plates for various pull chain configurations, no hole, 1 hole & 2 hole options included in each pack. To use in wet locations, optional wet location plate (WLP100) must be used, see below.*



LK70XXX
AMBER MIST
(4.5" H X 12.38" W)
Three 13-watt medium base compact fluorescent bulbs included. Rated for three 60-watt incandescent.



LK71XXX
AMBER PARCHMENT
(4.5" H X 12.38" W)
Three 13-watt medium base compact fluorescent bulbs included. Rated for three 60-watt incandescent.



LK72XXX
AMBER SCAVO
(4.5" H X 12.38" W)
Three 13-watt medium base compact fluorescent bulbs included. Rated for three 60-watt incandescent.



LK74XXX
OPAL MATTE
(4.5" H X 12.38" W)
Three 13-watt medium base compact fluorescent bulbs included. Rated for three 60-watt incandescent.



LK77XXX
WHITE LINEN
(4.5" H X 12.38" W)
Three 13-watt medium base compact fluorescent bulbs included. Rated for three 60-watt incandescent.



LK80XXX
AMBER MIST
(4.25" H X 12.38" W)
Three 13-watt medium base compact fluorescent bulbs included. Rated for three 60-watt incandescent.



LK81XXX
OPAL MATTE
(4.25" H X 12.38" W)
Three 13-watt medium base compact fluorescent bulbs included. Rated for three 60-watt incandescent.



LK83XXX
WHITE LINEN
(4.25" H X 12.38" W)
Three 13-watt medium base compact fluorescent bulbs included. Rated for three 60-watt incandescent.



LK141XXX
GRANDE LIGHT FIXTURE
WHITE MIST
(4.25" H X 12.5" W)
Three 60-watt candelabra bulbs (included)



WLP100

WET LOCATION

* ADD THE OPTIONAL WET LOCATION PLATE TO ANY LIGHT FIXTURE ON THIS PAGE FOR OUTDOOR USE:

Wet Location Plate for use with LK7x, LK8x, LK14x series. Shown in ORB. Also available in: AW, GES, SW, VS and WW.

LOW PROFILE LIGHT FIXTURES



Prima - Brushed Steel
CF901BS - pg 84
Shown with Low Profile Light Fixture (LK53BS)

All light fixture bowl caps shown with ORB finish. To complete the Ashton Light Fixture model number, replace xxx with finish code. Available in AB, AP, AW, BS, GBZ, GES, ORB, SW, VNB, VS and WW finishes. Final packs: Include 3 versions of plates for various pull chain configurations, no hole, 1 hole & 2 hole options included in each pack.



LK90XXX
ASHTON LIGHT FIXTURE
AMBER MIST
(3.3" H x 11.5" W)
Three 60-watt candelabra bulbs (included)



LK91XXX
ASHTON LIGHT FIXTURE
WHITE MIST
(3.3" H x 11.5" W)
Three 60-watt candelabra bulbs (included)

All light fixture bowl caps shown with ORB finish. To complete the Ashton Wet Light Fixture model numbers, replace xxx with finish code. Available in ORB and VNB finishes. Final packs: Include 3 versions of plates for various pull chain configurations, no hole, 1 hole & 2 hole options included in each pack. All Ashton Wet Light Fixtures include a Wet Location plate in the same finish as the finial.



LK92XXX
ASHTON WET LIGHT FIXTURE
AMBER MIST
(3.3" H x 11.5" W)
Three 40-watt candelabra bulbs (included)

All light fixture bowl caps shown with ORB finish. To complete the Harlow and Riley Light Fixture models number, replace xxx with finish code. Available in AP, AW, BS, GBZ, GES, ORB, SW, VNB, VS and WW finishes. Final packs: Include 3 versions of plates for various pull chain configurations, no hole, 1 hole & 2 hole options included in each pack.



LK1500MXXX
HARLOW LIGHT FIXTURE
OPAL MATTE GLASS
(3.8" H X 11" W)
Three 60-watt candelabra bulbs (included)



LK180XXX
RILEY LIGHT FIXTURE
OPAL MATTE
(3.3" H X 15.4" W)
Four 13-watt medium base compact fluorescent bulbs



LK65
MOON LIGHT FIXTURE
OPAL MATTE GLASS
(3.75" H X 10" W)
Shown in ORB. Also available in BS, SW & WW
Two 60-watt candelabra, incandescent torpedo bulbs (included)



LK53
LOW PROFILE LIGHT FIXTURE
FEATHER SWIRL GLASS
(4.5" H X 12" W)
Shown in VNB. Also available in BS, SW, ORB & WW. Three 60-watt candelabra bulbs (included)

LIGHT FIXTURES



LK51
TEASTAINED CLASSIC LIGHT FIXTURE
(5.25" H X 13" W)
Three 60-watt candelabra base bulbs (included)



LK130
TILO OPAL MATTE LIGHT FIXTURE
(3.9" H X 8" W)
Two 50-watt mini-candelabra halogen bulbs (included)
Includes BS, ORB & WW bowl caps



LK52
ALABASTER SWIRL CLASSIC LIGHT FIXTURE
(5.25" H X 13" W)
Three 60-watt candelabra base bulbs (included)



CFSLK1
SCHOOLHOUSE SINGLE LIGHT FIXTURE
(6.33" H X 8.5" W)
Available in WW.
One 23-watt medium base compact fluorescent bulb (included). Rated for one 100-watt incandescent.



CFSLKPF
SCHOOLHOUSE SINGLE DAMP LIGHT FIXTURE
(6.33" H X 8.5" W)
Shown in WW. Also available in ORB.
One 23-watt medium base compact fluorescent bulb (included). Rated for one 100-watt incandescent.



LK36
FOUR SPOT MESH LIGHT FIXTURE
(7" H X 10" W)
Shown in BS. Also available in ORB.
Four 13-watt medium base compact fluorescent bulbs (included). Rated for four 60-watt incandescent.



CFMLK4
FOUR SPOT TRAK LIGHT FIXTURE
(6.5" H X 7.5" W)
Shown in WW. Also available in ORB. Four 13-watt compact fluorescent bulbs (included). Rated for four 60-watt incandescent.



LK40
BOARDWALK CAGE LIGHT FIXTURE
(7.5" H X 16.5" W)
Shown in ORB. Also available in VNB. Three 9-watt medium base compact fluorescent bulbs (included). Rated for three 60-watt incandescent.



LK46
SEASIDE LIGHT FIXTURE
(7" H X 9" W)
Shown in ORB. Also available in AW & WW. One 13-watt medium base compact fluorescent bulb (included). Rated for one 100-watt incandescent.

FITTERS

Fitters and glass offer one more way to personalize your Emerson fan. Simply match your favorite fitter to your glass selection. Multi-light fitters accommodate 2 1/4" glass (pg 133). Each fitter has threaded sockets and includes an assembly tool for easy installation. Fitters are available in the finish listed below each model.

NEW! **VB100**
VINTAGE BULB ADAPTERS
 Shown in ORB. Also available in BS and VNB.
 Set of 4. Bulbs not included.



For an industrial look, convert any fitter in an instant with our Vintage Bulb Adapters. Customize the look with your favorite style of vintage bulbs.



Crofton - Venetian Bronze
 CF790VNB - pg 18
 Shown with Walnut Blades and Three-Light Turtle Fitter (F330, pg 132) with Vintage Bulb Adapters (VB100VNB), Bulbs Not Included

2 1/4" GLASS

All glass is packaged and sold in sets of four. All Emerson 2 1/4" glass only adapts to Emerson Fitters (pg 132).



CFFC4
FOUR-LIGHT CONTEMPORARY ADJUSTABLE FITTER
 (3" H X 11" W)
 Shown in BS. Also available in ORB. Four 13-watt medium base compact fluorescent bulbs (included). Rated for four 60-watt incandescent.



F330
THREE-LIGHT TURTLE FITTER
 (3.5" H X 5.5" W)
 Shown in WW. Also available in BS & ORB. Three 13-watt medium base compact fluorescent bulbs (included). Rated for three 60-watt incandescent.



F440
FOUR-LIGHT ARM FITTER
 (3" H X 8.75" W)
 Shown in ORB. Also available in AB, BS, SW, VNB & WW. Four 13-watt medium base compact fluorescent bulbs (included). Rated for four 60-watt incandescent.



F490
TRANSITIONAL FITTER
 (6.5" H X 13.15" W)
 Shown in GES. Also available in GBZ, ORB & VNB. Four 13-watt medium base compact fluorescent bulbs (included). Rated for four 60-watt incandescent.



AL100
OPTIONAL ACCENT LIGHT ACCESSORY
 Four 25-watt candelabra-base bulbs (included).
 *Only applicable to Penbrooke Select (CF5100), Penbrooke Select Eco (CF5200), Prima (CF901), Avant Eco (CF921), Portland Eco (CF965) & Highgrove (CF990)

COMPONENT PARTS (AVAILABLE FOR SINGULAR PARTS PURCHASE)



FN100
FINIAL PACK
 One Pack Includes No-hole, one-hole and two-hole options. Available in AB, AP, AW, BS, GBZ, GES, ORB, SW, VS, WW & VNB



F480WW
MEDIUM BASE FITTER
 Uses three 13-watt medium base compact fluorescent bulbs (included). Rated for three 60-watt incandescent.



CFGW1
 Traditional White



G18
 Frosted Ice



G19
 Washed Frosted



G26
 Clear Ribbed



G44
 Alabaster Swirl



G47
 Teastained



G53
 Sandstone



G55
 Opal Matte



G56
 Amber Scavo



G57
 Clouded Swirl



G58
 Amber Mist



G59
 Swirl




G65
 Teadust



BLADE SELECT™ SERIES

Choose from any of the blades shown on pages 134 - 135 to complete your custom Blade Select Series ceiling fan. All Blade Select Series blades shown are compatible with the following ceiling fans:



PENBROOKE SELECT ECO
CF5200 - pg 12

CARRERA GRANDE ECO
CF788 - pg 22

AVANT ECO²
CF921 - pg 78

PENBROOKE SELECT¹
CF5100 - pg 14

CROWN SELECT¹
CF4501 - pg 72

PREMIUM SELECT¹
CF4801 - pg 80

DAMP LOCATION

DECORATIVE HAND CARVED BLADES - 25" Length, 58-60" Span Blades
Solid wood blades with decorative detailing. All of the following blades are suitable for damp location and indoor listed fans.



B90DO
25" CLASSIC CARVED WOOD
Dark Oak

B90VBL
25" CLASSIC CARVED WOOD
Vintage Black

B91WA
25" DECO CARVED WOOD
Walnut

B92VWA¹
25" RATTAN CARVED WOOD
Vintage Walnut

B97DWA
25" ORNATE CARVED WOOD
Dark Walnut

DAMP LOCATION

SOLID WOOD BLADES - 22", 25", 31" Length, 52/54", 58/60", 70/72" Span Blades
B77 blades are 22" (52-54" Span). B78 blades are 25" (58-60" Span). B79 blades are 31" (70-72" Span). All B77, B78 & B79 are suitable for damp location and indoor listed fans. These solid wood blades feature a large bevel.



B78CH (SHOWN)
25" SOLID WOOD
Chocolate

B78DM (SHOWN)
25" SOLID WOOD
Dark Mahogany

B78NC (SHOWN)
25" SOLID WOOD
Natural Cherry

B78SW (SHOWN)
25" SOLID WOOD
Satin White

B78TK (SHOWN)
25" SOLID WOOD
Teak

B78WA (SHOWN)
25" SOLID WOOD
Walnut

DAMP LOCATION

DECORATIVE HAND CARVED BLADES - 22" Length, 52-54" Span Blades
Solid wood blades with decorative detailing. All of the following blades are suitable for damp location and indoor listed fans.



B100DO
22" CLASSIC CARVED WOOD
Dark Oak

B101WA
22" DECO CARVED WOOD
Walnut

B102VWA
22" RATTAN CARVED WOOD
Vintage Walnut

B103DWA
22" ORNATE CARVED WOOD
Dark Walnut

B107HCT
22" TAPERED CARVED WOOD
Dark Walnut

B108HCW
22" CARVED WOOD
Walnut

B109DC
22" HAND CARVED LEAF
Dark Cherry

B109DO
22" HAND CARVED LEAF
Dark Oak

WOOD VENEER BLADES³ - G54 Series, 22" Length, 52-54" Span Blades, G44 Series, 18" Length, 42-44" Span Blades, G60 Series, 25" Length, 58-60" Span Blades
Micro-balanced to within one gram. 6-layer wood veneer blades are cross-laminated for stability and warp resistance. Sealed to resist moisture. CH, SW, WW finishes are custom painted to match housing.



G54BS
Brushed Steel

G54CH³
Chocolate

G54DC/ G44DC
Dark Cherry

G54DM
Dark Mahogany

G54HO
Honey Oak

G54HWA
Heritage Walnut

G54MH
Mahogany

G54MO
Medium Oak

G54NC
Natural Cherry

G54RW
Riverwash

G54SW³
Satin White

G54TK/ G44TK
Teak

G54WA/ G44WA
Walnut

G54WS
White Wash

G54WW³/ G44WW³
Appliance White

NEW!
G60 SERIES
25" Blades

G60CH
Chocolate

G60DM
Dark Mahogany

G60SW
Satin White

G60WA
Walnut

1 CF5100, CF4501, CF4801 will not accept B79 blades.
2 CF921 will not accept B61, B62, B63 blades.

3 CH, SW, WW and WHW are painted blades


CEILING FAN CONTROLS AND RECEIVERS

For remote compatibility, please refer to the Controls Guide on pages 138-141



View installation help videos for controls & receivers at MyEmersonFans.com/Videos

4 Speed Controls with Receivers



3 Upgrade Bundles Available:

UB100
Includes the SR600 control, AL100 accent light & RC188 Receiver

UB200
Includes the SW605 control, AL100 accent light & RC188 Receiver

UB300
Includes the SR650 control, AL100 accent light & RC188 Receiver

Adaptable to Prima (CF901)



- SR400**
Four-Speed Remote Control with Receiver
- Four fan speeds
 - Full range light dimmer with incandescent bulbs (250 Watts max)
 - Canopy mount receiver included (Not for use on sloped ceilings)
 - Operates from up to 30 ft.
 - 1.0 amp fan load
 - Non-reversing
 - One-year limited warranty
 - Two AAA batteries included
 - Remote Only: SR401



- SW405**
Four-Speed Wall Control with Receiver
- Four fan speeds
 - Full range light dimmer with incandescent bulbs (250 Watts max)
 - Canopy mount receiver included (Not for use on sloped ceilings)
 - Operates from up to 30 ft.
 - 1.0 amp fan load
 - White, light almond and ivory switch cover plate included
 - Non-reversing
 - One year limited warranty
 - Wall Control Only: SW406

(USE WITH RCFP RECEIVER)

Six Speed Controls



- SR600**
Six-Speed LED Remote Control
- Six fan speeds with LED indicator
 - Independent uplight/downlight operation
 - Full range light dimmer with incandescent bulbs
 - One-touch reverse
 - For use with RC188 & RCK55 receivers
 - Two AAA batteries included



- SW605**
Six-Speed LED Wall Control
- Six fan speeds with LED indicator
 - Full range light dimmer with incandescent bulbs (250 Watts max)
 - Independent uplight/downlight operation
 - One-touch reverse
 - 1.0 amps fan load
 - White, light almond and ivory switch cover plates included
 - Canopy mount receiver sold separately
 - For use with RC188 & RCK55 receivers



- SR650**
Six-Speed 2-in-1 LED Remote Control
- Six fan speeds with LED indicator
 - Independent uplight/downlight operation
 - Full range light dimmer with incandescent bulbs
 - One-touch reverse
 - Can be used mounted on the wall or as a remote control
 - Single & Dual-gang decorative plate included
 - Canopy mount receiver sold separately
 - For use with RC188 & RCK55 receivers
 - Two CR2032 batteries included



- SR650**
Shown in dual-gang decorative plate (Rocker switch not included)

(USE WITH RC188 & RCK55 RECEIVERS)

RECEIVERS



- RCFP**
Flat Pack Receiver
- Canopy mount receiver
 - Full range light dimmer (250 Watts max)
 - 1.0 amp fan load
 - Non-sloped ceiling mount only
 - For use with SR401 and SW406 controls



- RC188**
Horseshoe Receiver
- Six fan speeds
 - Reverse module
 - Independent uplight/downlight operation
 - Full range light dimmer (500 Watts max total, 300 Watts down and 200 Watts uplight)
 - 1.0 amp fan load
 - For use with 188mm motor fan models
 - Designed for SR600, SW605, and SR650 controls



- RCK55**
Horseshoe Receiver
- Six fan speeds
 - Reverse module
 - Independent uplight/downlight operation
 - Full range light dimmer (500 Watts max total, 300 Watts down and 200 Watts uplight)
 - 1.0 amp fan load
 - For use with Emerson K55XL motor fan models
 - Designed for SR600, SW605 and SR650 controls

KNOBS & SLIDE CONTROLS



- SW46W (WHITE) / SW46LA (ALMOND)**
4-Speed Fan Slide Control
- Fan control only
 - 2-wire installation
 - 4 fan speeds
 - 1.2 amps maximum
 - Decorative faceplate included
 - Please note setting:
 - 1 High
 - 2 Med-High
 - 3 Med-Low
 - 4 Low



- SW90W (WHITE) / SW90LA (ALMOND)**
Dual Slide Control
- Fan & light control
 - 3-wire installation
 - 4 fan speeds
 - Continuous light dimming (300 Watts max.)
 - 1.25 amps fan load
 - Decorative faceplate included
 - Please note setting:
 - 1 High
 - 2 Med-High
 - 3 Med-Low
 - 4 Low



- SW93**
2-Fan Control
- Fan control only
 - 2-wire installation
 - 3 fan speeds
 - 3 amps maximum
 - Faceplate not included
 - White and almond knobs included
 - Please note setting:
 - 1 High
 - 2 Med
 - 3 Low



- SW95**
4-Speed Fan Knob Control
- Fan control only
 - 2-wire installation
 - 4 fan speeds
 - 1.5 amps maximum
 - Faceplate not included
 - White and Almond knobs included
 - Please note setting:
 - 1 High
 - 2 Med-High
 - 3 Med-Low
 - 4 Low



- SW96**
4-Speed Fan Control
- 4 fan speeds
 - 5 amps maximum
 - White and Almond knobs included
 - Faceplate not included



- SW81**
- 2-wire
 - Infinitely variable
 - 3 amps
 - Faceplate included



- SW82**
- 2-wire
 - Infinitely variable
 - 12 amps
 - Faceplate included



View installation help videos for controls & receivers at MyEmersonFans.com/Videos

TURN PAGE FOR MORE REMOTE INFORMATION

SR400 SERIES



**SR400
SR401**
4 Speed
Remote Control

**SW405
SW406**
4 Speed
Wall Control

RCFP
Flat Pack
Receiver

Uses RCFP; SR400 & SW405:
Receiver Included

SR600 SERIES

Require Receiver for Operation



SR600
6 Speed
LED Remote
Control

SR650
6 Speed
2-in-1 LED
Remote Control

SW605
6 Speed LED
Wall Control


TBSR600
6 Speed
LED Remote
Control

Uses RCK55 or RC188
Receiver Sold Separately

Model Number	Model	SR400 SR401	SW405 SW406	RCFP	SR600	SR650	SW605	TBSR600
CF1	Cornerstone	●	●	●	●	●	●	●
CF130	Tilo							
CF144	44" Curva Sky				+	+	+	
CF152	52" Curva Sky				+	+	+	
CF2000	Maui Bay	●	●	●	+	+	+	
CF205	Highpointe	■	●	■				
CF230	Veloce	■	●	■				
CF244	44" Curva				+	+	+	
CF252	52" Curva				+	+	+	
CF320	Keane	▲	▲	▲				
CF430	Highrise	●	■	■				
CF440	Braddock	■	●	■				
CF442	42" Bella	●	●	●	+	+	+	
CF4501	Crown Select				●	●	●	
CF452	52" Bella	●	●	●	+	+	+	
CF4801	Premium Select				●	●	●	
CF4900	Southtowne				+	+	+	
CF5100	Penbrooke Select				●	●	●	
CF5200	Penbrooke Select Eco				●	●	■	
CF550	Luxe Eco				+	+	+	
CF542	42" Veranda	●	●	●				
CF552	52" Veranda	●	●	●				
CF590	Volta	●	■	■				
CF610	Welland	●	●	●	+	+	+	
CF621	Batalie Breeze	●	●	●	+	+	+	
CF652	52" Summer Night							
CF654	Sea Breeze	●	●	●				
CF670	Devonshire	●	●	●	+	+	+	
CF700	Builder							
CF702	29" Northwind							
CF710	42" Pro Series II							
CF711	50" Pro Series II							
CF712	Pro Series							
CF713	Pro Series ES							

- Key:
- ✚ Fan model does not have nor is adaptable to accent light. Accent Light function will not operate.
 - ✖ Reverse function will not operate remotely.
 - ▲ Light button cannot be used.
 - * Must use these controls/receivers to operate accent light and downlight separately.
 - Supplied with fan.
 - Compatible

SR600 RECEIVERS



RC188

RCK55



SW46
4-Speed Slide
Wall Control

SW95
4-Speed Knob
Wall Control

SW96
5-Amp
Four-Speed
Multi-Fan Knob
Wall Control

SW93
2-Fan,
3 Speed
Knob Control

SW90
Fan & Light Dual
Slide Control

SW81
Variable Speed
Control

SW82
Variable Speed
Wall Control

Separate lighting circuit required for fans
with integrated or accessory lights

Model Number	Model	RC188	RCK55	SW46	SW95	SW96	SW93	SW90	SW81	SW82
CF1	Cornerstone		●	●	●	●	●	●		
CF130	Tilo			■	●	●	●	●		
CF144	44" Curva Sky	■								
CF152	52" Curva Sky	■								
CF2000	Maui Bay		+	●	●	●	●	●		
CF205	Highpointe			●	●	●	●	●		
CF230	Veloce			■	●	●	●	●		
CF244	44" Curva	■								
CF252	52" Curva	■								
CF320	Keane			●	●	●	●	▲		
CF430	Highrise			●	●	●	●	●		
CF440	Braddock			●	●	●	●	●		
CF442	42" Bella	+		●	●	●	●	●		
CF4501	Crown Select		●	●	●	●	●	●		
CF452	52" Bella	+		●	●	●	●	●		
CF4801	Premium Select		●	●	●	●	●	●		
CF4900	Southtowne		■							
CF5100	Penbrooke Select		●	●	●	●	●	●		
CF5200	Penbrooke Select Eco									
CF550	Luxe Eco									
CF542	42" Veranda			●	●	●	●	●		
CF552	52" Veranda			●	●	●	●	●		
CF590	Volta			●	●	●	●	●		
CF610	Welland	+		●	●	●	●	●		
CF621	Batalie Breeze	+		●	●	●	●	●		
CF652	52" Summer Night			●	●	●	●	●		
CF654	Sea Breeze			●	●	●	●	●		
CF670	Devonshire	+		●	●	●	●	●		
CF700	Builder			●	●	●	●	●		
CF702	29" Northwind			●	●	●	●	●		
CF710	42" Pro Series II			●	●	●	●	●		
CF711	50" Pro Series II			●	●	●	●	●		
CF712	Pro Series			●	●	●	●	●		
CF713	Pro Series ES			●	●	●	●	●		

See page 144 for more remote information.

SR400 SERIES



SR400 SR401
4 Speed Remote Control

SW405 SW406
4 Speed Wall Control

RCFP
Flat Pack Receiver

Uses RCFP; SR400 & SW405: Receiver Included

SR600 SERIES

Require Receiver for Operation



SR600
6 Speed LED Remote Control

SR650
6 Speed 2-in-1 LED Remote Control

SW605
6 Speed LED Wall Control


TBSR600
6 Speed LED Remote Control

Uses RCK55 or RC188 Receiver Sold Separately

Model Number	Model	SR400 SR401	SW405 SW406	RCFP	SR600	SR650	SW605	TBSR600
CF717	Ashland							
CF742PF	42" Summer Night							
CF755	Designer	●	●	●	+	+	+	
CF765	Loft	▲	▲	▲				
CF766	4th Avenue	●	■	■				
CF772	52" Monterey II	●	●	●				
CF773	42" Monterey II	●	●	●				
CF776	Monterey Lumina	●	●	●				
CF784	Carrera	●	●	●	+	+	+	
CF788	Carrera Grande Eco	●	●	●	+	+	+	
CF790	Crofton	●	■	■				
CF804S	42" Snugger							
CF805S	52" Snugger							
CF830	Monaco	●	●	●	×	×	×	
CF850	Summerhaven	●	●	●				
CF860	Luray Eco				+	+	+	
CF880	Amhurst	●	■	■				
CF901	Prima				*	*	*	
CF905	Prima Snugger	●	●	●				
CF921	Avant Eco				■	●	●	
CF930	Atomical	■	●	■				
CF935	Zurich	●	●	●				
CF955	Midway Eco				+	+	+	
CF965	Portland Eco					●	■	
CF985	Aira Eco				+	+	■	
CF990	Highgrove	■	●	■	×	×	×	
CF995	Laclede Eco				■	●	●	
HF1160	60" Industrial Fan							
HF948	48" Industrial Fan							
HF956	56" Industrial Fan							

- Key:**
- ✚ Fan model does not have nor is adaptable to accent light. Accent Light function will not operate.
 - ✖ Reverse function will not operate remotely.
 - ▲ Light button cannot be used.
 - * Must use these controls/receivers to operate accent light and downlight separately.
 - Supplied with fan.
 - Compatible

SR600 RECEIVERS



RC188

RCK55



SW46
4-Speed Slide Wall Control

SW95
4-Speed Knob Wall Control

SW96
5-Amp Four-Speed Multi-Fan Knob Wall Control

SW93
2-Fan, 3 Speed Knob Control

SW90
Fan & Light Dual Slide Control

SW81
Variable Speed Control


SW82
Variable Speed Wall Control

Separate lighting circuit required for fans with integrated or accessory lights

Model Number	Model	RC188	RCK55	SW46	SW95	SW96	SW93	SW90	SW81	SW82
CF717	Ashland			●	●	●	●	●		
CF742PF	42" Summer Night			●	●	●	●	●		
CF755	Designer	✚		●	●	●	●	●		
CF765	Loft			■	●	●	●			
CF766	4th Avenue			●	●	●	●	●		
CF772	52" Monterey II			●	●	●	●	●		
CF773	42" Monterey II			●	●	●	●	●		
CF776	Monterey Lumina			●	●	●	●	●		
CF784	Carrera	✚		●	●	●	●	●		
CF788	Carrera Grande Eco									
CF790	Crofton			●	●	●	●	●		
CF804S	42" Snugger			●	●	●	●	●		
CF805S	52" Snugger			●	●	●	●	●		
CF830	Monaco	✖		●	●	●	●	■		
CF850	Summerhaven			●	●	●	●	●		
CF860	Luray Eco									
CF880	Amhurst			●	●	●	●	●		
CF901	Prima	*		■	●	●	●	●		
CF905	Prima Snugger			■	●	●	●	●		
CF921	Avant Eco									
CF930	Atomical			●	●	●	●	●		
CF935	Zurich			●	●	●	●	●		
CF955	Midway Eco									
CF965	Portland Eco									
CF985	Aira Eco									
CF990	Highgrove	✖								
CF995	Laclede Eco									
HF1160	60" Industrial Fan			●	●	●	●	●	●	●
HF948	48" Industrial Fan			●	●	●	●	●	●	●
HF956	56" Industrial Fan			●	●	●	●	●	●	●

See page 144 for more remote information.


Fan Specifications



Model Number	Model	Pg	Motor	Fan Diameter	Blade Pitch	A	B	C	D	RPM Range	Motor Warranty	Energy Star	High Speed Amps	Accepts 2.5" DR	Model Number	Model	Pg	Wet/ Damp	CFM	Watts	CFM/W	Control Included	Receiver Included	Manual/Remote Reverse Switch	Dimming Light	Downrod Length	AL100 Adaptable	Ships To Canada
CF1	Cornerstone	74	K55XL	54"	14°/20°	17.8"/31.3"	11.0"/24.5"	9.5"	6.4"	35-160	Lifetime	No	0.83	Yes	CF1	Cornerstone	74	Indoor	5345 ¹ 6257 ²	99 ¹ 101 ²	54 ¹ 62 ²	Pull Chain	N/A	Manual	N/A	4.5 & 18	No	Yes
CF130	Tilo	67	153x10mm	30"	12°	9.5"/13.3"	8.1"x 11.9"	7.3"	5.1"	110-280	Lifetime	No	0.4	Yes	CF130	Tilo	67	Indoor	2278	42	54	SW46	N/A	Manual	N/A	4.5	No	Yes
CF144	44" Curva Sky	60	153x18mm	44"	12°	12.6"	10.0"	9.6"	9.9"	130-280	Lifetime	No	0.5	No	CF144	44" Curva Sky	60	Wet ³	4217	45	93	6 Speed Remote Control	RC188	Remote	Yes	N/A	No	Yes
CF152	52" Curva Sky	60	153x18mm	52"	12°	12.6"	10.0"	9.6"	9.9"	75-195	Lifetime	No	0.5	No	CF152	52" Curva Sky	60	Wet ³	5393	46	116	6 Speed Remote Control	RC188	Remote	Yes	N/A	No	Yes
CF2000	Maui Bay	98	K55XL	52"	20°	15.0"	14.5"	8.6"	5.3"	25-100	Lifetime	No	0.77	Yes	CF2000	Maui Bay	98	Damp ³	5140	56	92	Pull Chain	N/A	Manual	N/A	6	No	Yes
CF205	Highpointe	56	153x22mm	54"	14°	16.5"/22.5"	15.0"/21.0"	8.0"	6.3"	59-189	Lifetime	No	0.55	Yes	CF205	Highpointe	56	Indoor	5678	66	86	SR400	RCFP	Manual	Yes	6 & 12	No	Yes
CF230	Veloce	66	153x18mm	46"	12°	14.4"/11.1"	11.9"	7.5"	5"	102-206	Lifetime	No	0.43	Yes	CF230	Veloce	66	Damp ³	5250	52	102	SR400	RCFP	Manual	Yes	4.5	No	Yes
CF244	44" Curva	62	153x18mm	44"	12°	14.9"	12.0"	9.6"	6.5"	130-280	Lifetime	No	0.5	Yes	CF244	44" Curva	62	Wet ³	4280	44	97	6 Speed Remote Control	RC188	Remote	Yes	4.5	No	Yes
CF252	52" Curva	62	153x18mm	52"	12°	14.9"	12.0"	9.6"	6.5"	75-195	Lifetime	No	0.5	Yes	CF252	52" Curva	62	Wet ³	5329	45	118	6 Speed Remote Control	RC188	Remote	Yes	4.5	No	Yes
CF320	Keane	40	153x17mm	52"	12°	10.9"	10.4"	11.0"	5.9"	680-185	Lifetime	Yes	.40	Yes	CF320	Keane	40	Indoor	5200 ⁴	49 ⁴	106 ⁴	SW46	N/A	Manual	N/A	4.5	No	Yes
CF430	Highrise	48	153x17mm	50"	13°	13.5"	11.2"	8.0"	5.9"	72-168	Lifetime	No	0.42	Yes	CF430	Highrise	48	Indoor	4263	49	85	SW405	RCFP	Manual	No-LED	4.5	No	Yes
CF440	Braddock	34	188x18mm	54"	12.5°	16.2"	11.45"	12.8"	6.4"	77-175	Lifetime	No	0.53	No	CF440	Braddock	34	Indoor	6311	64	99	SR400	RCFP	Manual	Yes	4.5	No	No
CF442	42" Bella	36	153x18mm	42"	13°	14.0"	12.0"	11.5"	7.1"	100-240	Lifetime	No	0.45	No	CF442	42" Bella	36	Indoor	4181	54	77	Pull Chain	N/A	Manual	N/A	4.5	No	Yes
CF4501	Crown Select	72	K55XL	42"/52"/58"/70"	12°	14.0"	13.0"	12.3"	6.4"	40-205	Lifetime	No	0.85	Yes	CF4501	Crown Select	72	Indoor	7155	100	72	Pull Chain	N/A	Manual	N/A	4.5	No	No
CF452	52" Bella	36	188x15mm	52"	13°	14.0"	12.0"	11.5"	7.1"	60-180	Lifetime	No	0.6	No	CF452	52" Bella	36	Indoor	5614	72	78	Pull Chain	N/A	Manual	N/A	4.5	No	Yes
CF4801	Premium Select	80	K55XL	42"/52"/58"/70"	12°	15.0"	14.0"	12.3"	6.4"	40-205	Lifetime	No	0.85	Yes	CF4801	Premium Select	80	Indoor	7264	100	73	Pull Chain	N/A	Manual	N/A	4.5	No	No
CF4900	Southtowne	46	K55XL	54"	12°	15.0"	10.5"	12.0"	6.25"	43-186	Lifetime	No	0.8	Yes	CF4900	Southtowne	46	Indoor	5556	97	57	6 Speed Wall Control	RCK55	Remote	Yes	4.5	No	Yes
CF5100	Penbrooke Select	14	K55XL	44"/54"/60"	12°	13.0"	12.0"	13.0"	6.7"	35-150	Lifetime	No	0.82	Yes	CF5100	Penbrooke Select	14	Indoor	6222	98	63	N/A	N/A	Remote	Yes	4.5	Yes	Yes
CF5200	Penbrooke Select Eco	12	EcoMotor	44"/54"/60"/72"	12°	13.0"	12.0"	13.0"	6.7"	50-180	Lifetime	No	0.47	Yes	CF5200	Penbrooke Select Eco	12	Indoor	7400 ⁴	32 ⁴	231.3 ⁴	SW605	EcoMotor Receiver	Remote	N/A	4.5	Yes	Yes
CF550	Luxe Eco	54	EcoMotor	54"	18°	15.8"	12.0"	9.6"	6.4"	50-155	Lifetime	No	0.30	No	CF550	Luxe Eco	54	Indoor	6974	33	210	6 Speed Wall Control	EcoMotor Receiver	Remote	Yes	4.5	No	Yes
CF542	42" Veranda	102	153x18mm	42"	13°	14.0"	12.0"	11.5"	7.1"	100-260	Lifetime	No	0.44	No	CF542	42" Veranda	102	Wet	4421	53	83	Pull Chain	N/A	Manual	N/A	4.5	No	Yes
CF552	52" Veranda	102	188x15mm	52"	13°	14.0"	12.0"	11.5"	7.1"	60-180	Lifetime	No	0.61	No	CF552	52" Veranda	102	Wet	5967	73	82	Pull Chain	N/A	Manual	N/A	4.5	No	Yes
CF590	Volta	92	172x20mm	54"	12°	14.5"	13.2"	8.7"	5.8"	60-170	Lifetime	No	0.7	Yes	CF590	Volta	92	Wet	6300 ⁴	81.5 ⁴	77.3 ⁴	SR400	4 Speed	Manual	Yes	4.5	No	Yes
CF610	Welland	94	188x15mm	54"	12°	14.9"	12.3"	13.75"	6.8"	65-165	Lifetime	No	0.5	Yes	CF610	Welland	94	Wet	5081	57.8	88	Pull Chain	N/A	Manual	N/A	4.5	No	Yes
CF621	Batalie Breeze	96	188x20mm	52"	14°	14.5"	13.2"	9.8"	7.1"	75-180	Lifetime	No	0.62	Yes	CF621	Batalie Breeze	96	Wet	5255	75	70	Pull Chain	N/A	Manual	N/A	4.5	No	Yes
CF652	52" Summer Night	106	153x15mm	52"	12°	11.8"	9.8"	11.5"	5.3"	80-200	Lifetime	No	0.52	Yes	CF652	52" Summer Night	106	Damp	5334	62	86	Pull Chain	N/A	Manual	N/A	3.5	No	Yes
CF654	Sea Breeze	105	188x15mm	52"	14°	14.0"	12.0"	12.0"	6.5"	60-200	Lifetime	No	0.6	Yes	CF654	Sea Breeze	105	Wet	6492	72	90	Pull Chain	N/A	Manual	N/A	3.5	No	Yes
CF670	Devonshire	104	188x15mm	52"	14°	12.0"	10.0"	12.0"	7.0"	70-175	Lifetime	No	0.58	Yes	CF670	Devonshire	104	Damp	6186	70	89	Pull Chain	N/A	Manual	N/A	4.5	No	Yes
CF700	Builder	120	153x15mm	52"	11°	12.0"	11.0"	11.5"	5.1"	58-175	Lifetime	Yes	0.53	Yes	CF700	Builder	120	Indoor	5241	64	80	Pull Chain	N/A	Manual	Yes	4.5	No	Yes
CF702	29" Northwind	86	153x10mm	29"	22°	10.8"	10.5"	9.0"	5.3"	130-285	Lifetime	No	0.39	Yes	CF702	29" Northwind	86	Indoor	3430	47	73	Pull Chain	N/A	Manual	N/A	3.5	No	Yes
CF710	42" Pro Series II	118	153x15mm	42"	12°	14.5"/17.3"	8.3"/11.0"	11.5"	5.2"	75-195	Lifetime	No	0.38	No	CF710	42" Pro Series II	118	Indoor	3834	45	86	Pull Chain	N/A	Manual	No	3.5 & Dualmount	No	No
CF711	50" Pro Series II	116	153x15mm	50"	12°	14.8"/18.5"	8.3"/11.0"	11.5"	5.2"	65-170	Lifetime	No	0.53	No	CF711	50" Pro Series II	116	Indoor	5403	84	64	Pull Chain	N/A	Manual	No	4.5 & Dualmount	No	No
CF712	Pro Series	112	153x15mm	50"	12°	14.8"/18.5"	8.3"/11.5"	11.5"	5.2"	65-170	Lifetime	No	0.51	No	CF712	Pro Series	112	Indoor	5224	61	85	Pull Chain	N/A	Manual	No	4.5 & Dualmount	No	Yes
CF713	Pro Series ES	114	153x15mm	50"	12°	14.8"/18.5"	8.3"/11.5"	11.5"	5.2"	75-175	Lifetime	Yes	0.50	No	CF713	Pro Series ES	114	Indoor	5027	65	77	Pull Chain	N/A	Manual	No	4.5 & Dualmount	No	Yes

¹ 2 blades
² 4 blades
³ Damp or Wet Location ratings may apply to certain finishes only
⁴ Estimated data. Visit our website at emersonfans.com for up-to-date information.

Fan Specifications



Model Number	Model	Pg	Motor	Fan Diameter	Blade Pitch	A	B	C	D	RPM Range	Motor Warranty	Energy Star	High Speed Amps	Accepts 2.5" DR	Model Number	Model	Pg	Wet/Damp	CFM	Watts	CFM/W	Control Included	Receiver Included	Manual/Remote Reverse Switch	Dimming Light	Downrod Length	AL100 Adaptable	Ships To Canada
CF717	Ashland	110	153x17mm	52"	11.5°	17.0"/13.0"	9.5"/13.5"	12.0"	5.3"	70-170	Lifetime	No	0.47	No	CF717	Ashland	110	Indoor	4939	56	88	Pull Chain	N/A	Manual	Yes	4.5 & Dualmount	No	Yes
CF742PF	42" Summer Night	107	153x10mm	42"	12°	12.0"	10.0"	11.5"	5.2"	80-200	Lifetime	No	0.39	Yes	CF742PF	42" Summer Night	107	Damp	4105	47	88	Pull Chain	N/A	Manual	N/A	3.5	No	Yes
CF755	Designer	84	188x15mm	52"	14°	14.0"	12.0"	12.0"	6.4"	60-200	Lifetime	Yes	0.62	Yes	CF755	Designer	84	Indoor	5794	69	83	Pull Chain	N/A	Manual	N/A	3.5	No	Yes
CF765	Loft	58	188x15mm	60"	Contoured	12.8"	12.8"	7.5"	6.5"	60-190	Lifetime	Yes	0.66	Yes	CF765	Loft	58	Damp ³	7579	81	92	SW46	N/A	Manual	N/A	6	No	Yes
CF766	4th Avenue	50	188x20mm	60"	14°	17.9"	12.6"	8.7"	6.4"	65-150	Lifetime	No	0.41	No	CF766	4th Avenue	50	Indoor	6403	48	132	SW405	RCFP	Manual	Yes	8	No	Yes
CF772	52" Monterey II	32	188x15mm	52"	13°	15"	11.5"	13"	6.8"	65-195	Lifetime	No	0.58	No	CF772	52" Monterey II	32	Indoor	5625	70	79	Pull Chain	N/A	Manual	N/A	4.5	No	Yes
CF773	42" Monterey II	33	172x14mm	42"	12.5°	15.0"	12.5"	12.5"	6.5"	100-225	Lifetime	No	0.4	Yes	CF773	42" Monterey II	33	Indoor	3556	47	75.7	Pull Chain	N/A	Manual	N/A	4.5	No	Yes
CF776	Monterey Lumina	30	188x15mm	52"	13°	19.1"	11.5"	13"	6.8"	65-195	Lifetime	No	0.58	Yes	CF776	Monterey Lumina	30	Indoor	5625	70	79	Pull Chain	N/A	Manual	Yes	4.5	No	Yes
CF784	Carrera	16	188x25mm	60"	14°	14.5"	13.0"	13.4"	6.8"	50-160	Lifetime	No	0.80	No	CF784	Carrera	16	Indoor	5081	57.8	87.9	Pull Chain	N/A	Manual	N/A	4.5	No	Yes
CF788	Carrera Grande Eco	22	EcoMotor	44"/54"/60"/72"	16°	14.5"	13.0"	13.4"	7.1"	50-150	Lifetime	Yes	0.30	No	CF788	Carrera Grande Eco	22	Damp ³	7930	29.9	265	6 Speed Wall Control	EcoMotor Receiver	Remote	N/A	4.5	No	Yes
CF790	Crofton	18	188x25mm	58"	12°	13.2"	12.0"	13.7"	6.5"	50-135	Lifetime	No	0.66	No	CF790	Crofton	18	Indoor	6445	77.6	83.1	SW405	RCFP	Manual	N/A	4.5	No	Yes
CF804S	42" Snugger	89	153x12mm	42"	12°	7.3"	6.5"	9.1"	N/A	80-205	Lifetime	No	0.38	No	CF804S	42" Snugger	89	Indoor	N/A	N/A	N/A	Pull Chain	N/A	Manual	N/A	N/A	No	Yes
CF805S	52" Snugger	88	153x15mm	52"	12°	7.3"	7.6"	11.0"	N/A	60-165	Lifetime	No	0.53	No	CF805S	52" Snugger	88	Indoor	N/A	N/A	N/A	Pull Chain	N/A	Manual	N/A	N/A	No	Yes
CF830	Monaco	70	188x25mm	60"	14°	15.5"/21.0"	13.0"/18.5"	16.0"	8.9"	50-160	Lifetime	No	0.82	No	CF830	Monaco	70	Indoor	6156	98	63	SW90	N/A	Manual	Yes	4.5 & 10	No	No
CF850	Summerhaven	100	188x15mm	52"	12°	14.4"	9.7"	11.7"	6.7"	102-206	Lifetime	No	0.43	Yes	CF850	Summerhaven	100	Wet	6118	61	99	Pull Chain	N/A	Manual	Yes	4.5	No	Yes
CF860	Luray Eco	42	EcoMotor	60"	Contoured	14.1"	14.5"	9.8"	6.5"	50-160	Lifetime	Yes	0.28	No	CF860	Luray Eco	42	Indoor	8500 ⁴	33 ⁴	258 ⁴	SW605	EcoMotor Receiver	Remote	Yes	4.5	No	Yes
CF880	Amhurst	26	188x15mm	54"	12°	15.1"	11.8"	9.1"	6.3"	60-170	Lifetime	No	0.58	Yes	CF880	Amhurst	26	Indoor	5422	67	80	SW405	RCFP	Manual	Yes	4.5	No	Yes
CF901	Prima	82	188x15mm	52"	13°	13.0"	12.0"	12.0"	6.3"	70-180	Lifetime	Yes	0.49	Yes	CF901	Prima	82	Indoor	5263	59	89	SW46	N/A	Manual	N/A	4.5	Yes	Yes
CF905	Prima Snugger	87	172x14mm	52"	13°	8.0"	7.0"	11.6"	N/A	70-165	Lifetime	No	0.54	No	CF905	Prima Snugger	87	Indoor	5145	64	80	SW46	N/A	Manual	N/A	N/A	No	Yes
CF921	Avant Eco	78	EcoMotor	44"/54"/60"/72"	16°	13.0"	12.0"	12.0"	6.3"	50-150	Lifetime	Yes	0.30	No	CF921	Avant Eco	78	Indoor	7985	31	256	SR600	EcoMotor Receiver	Control	N/A	4.5	Yes	Yes
CF930	Atomical	64	153x18mm	52"	13°	15.8"	12.0"	9.5"	6.5"	70-160	Lifetime	No	0.49	Yes	CF930	Atomical	64	Damp ³	4515	59	76	SR400	RCFP	Manual	Yes	4.5	No	Yes
CF935	Zurich	75	188x15mm	52"	14°	14.5"	13.5"	13.3"	7.0"	50-170	Lifetime	No	0.58	Yes	CF935	Zurich	75	Indoor	5958	69	86	Pull Chain	N/A	Manual	N/A	4.5	No	Yes
CF955	Midway Eco	52	EcoMotor	54"	29°	16.5"	9"	12.5"	5.1"	50-211	Lifetime	Yes	0.15	No	CF955	Midway Eco	52	Indoor	6085	18	336	6 Speed Remote Control	EcoMotor Receiver	Remote	No	4.5	No	Yes
CF965	Portland Eco	16	EcoMotor	54"	18°	15.6"	12.0"	13.2"	6.4"	50-155	Lifetime	No	0.3	Yes	CF965	Portland Eco	16	Indoor	6389	33.5	190.7	SW605	EcoMotor Receiver	Remote	Yes	4.5	Yes	Yes
CF985	Aira Eco	44	EcoMotor	72"	15°	14.4"	12.5"	8.4"	6.4"	30-100	Lifetime	No	0.3	Yes	CF985	Aira Eco	44	Damp	9782	33.7	290	SW605	EcoMotor Receiver	Remote	Yes	6.0	No	Yes
CF990	Highgrove	28	188x15mm	53"	12°	15"	13"	13"	6.4"	55-160	Lifetime	No	0.52	No	CF990	Highgrove	28	Indoor	5258	62	84	SR400	RCFP	Manual	Yes	4.5	Yes	Yes
CF995	Laclede Eco	24	EcoMotor	62"	12°	20.0"	16.0"	17.0"	8.0"	50-135	Lifetime	No	0.30	No	CF995	Laclede Eco	24	Indoor	6381	30	212	SR600	EcoMotor Receiver	Remote	No	10	No	No
HF1160	60" Industrial Fan	122	188x20mm	60"	Airfoil	12.8"	12.8"	7.5"	5.2"	270	5 Years	No	0.98	No	HF1160	60" Industrial Fan	122	Indoor	10649	118	90	SW95	N/A	N/A	N/A	6	No	Yes
HF948	48" Industrial Fan	122	188x18mm	48"	Contoured	19.5"/33.5"	16.0"/30.0"	7.5"	4.8"	330	2 Years	No	0.6	No	HF948	48" Industrial Fan	122	Indoor	6879	72	95	SW95	N/A	N/A	N/A	8 & 22	No	Yes
HF956	56" Industrial Fan	122	188x25mm	58"	Contoured	33.5"	30.0"	7.5"	4.8"	310	2 Years	No	0.79	No	HF956	56" Industrial Fan	122	Indoor	9757	95	103	SW95	N/A	N/A	N/A	22	No	Yes

¹ 2 blades
² 4 blades
³ Damp or Wet Location ratings may apply to certain finishes only
⁴ Estimated data. Visit our website at emersonfans.com for up-to-date information.

go ABOVE



EMERSON[™]

Air Comfort Products division of Emerson Electric Co.
8100 West Florissant Ave. • Saint Louis, Missouri 63136

Customer Service Tel: 1-800-237-6511

Customer Service Fax: 1-800-525-7248

Customer Service Email: FanCS@emerson.com

emersonfans.com



Share pictures of your Emerson fans on Pinterest,
Facebook and Twitter using #MyEmersonFan

