



2016  
INTRODUCTION



**NEW**  
F617L-GM



**NEW**  
F617L-BN



## RAPTOR

This contemporary design is coupled with the energy saving advancements of DC motor technology and an integrated 17 watt **LED** light source. An option of three transitional finishes.

### FEATURES

- 14° Blade Pitch • 60" 5-Blades • 172x12mm DC Motor
- Special Hand Held Remote Control System - RC600 Incl.
- Integrated LED Light Uses 17W LED Incl., 3 Year Warranty • 1,100 Lumens • 3000 Kelvin • CRI 80

### ENERGY INFORMATION\* (Excludes Lights)

- Airflow CFM: 6,000 • Electricity Used Watts: 30 • Airflow Efficiency CFM/Watts: 200



# RAPTOR

LED



**NEW**  
F617L-ORB/AB

**F617L-GM** • Gun Metal Finish • Gun Metal Blades • Etched Opal Glass  
**F617L-BN** • Brushed Nickel Finish • Silver Blades • Etched Opal Glass  
**F617L-ORB/AB** • Oil Rubbed Bronze/Antique Brass Finish • Tobacco Blades • Tinted Opal Glass

# CONTRACTOR UNI-PACK LED

WITH LIGHT KIT

LED



**NEW**  
F656L-BN/DW

## FEATURES

- 12° Blade Pitch • 52" 5-Blades • 172x14mm Motor • 3-Speed Pull Chain
- Low Profile LED Light Uses 26W LED Incl., 3 Year Warranty • 1,899 Lumens • 3,000 Kelvin • CRI 81

## ENERGY INFORMATION\* (Excludes Lights)

- Airflow CFM: 5,966 • Electricity Used Watts: 66.5 • Airflow Efficiency CFM/Watts: 89.71



**NEW**  
F656L-ORB



**NEW**  
F656L-WH

## CONTRACTOR UNI-PACK LED

Introducing a full feature LED Contractor 52-inch fan. Featuring the incredible 26 watt LED, 1,899 Lumens, 3,000 Kelvin light source and a 172x14mm heavy duty motor.

**F656L-BN/DW** • Brushed Nickel Finish • Reversible Medium Maple/Dark Walnut Blades  
(Shown with Dark Walnut Blades) • Frosted White Glass

**F656L-ORB** • Oil Rubbed Bronze Finish • Reversible Medium Maple/Dark Walnut Blades  
(Shown with Dark Walnut Blades) • Frosted White Glass

**F656L-WH** • White Finish • White Blades • Frosted White Glass

*Indoor/Outdoor*

**NEW**  
F624-ABD



**NEW**  
F624-WHF



## ROTO XL

Roto XL features a sleek and contemporary design with a classic industrial look. Well edited and an impeccably executed design features a slight "fold" construction along the length of the blades to increase the flow of air. A perfect marriage of form and function. Roto XL features a full 62-inch spread combined with a wet location specification use for indoor or outdoors.

**F624-ABD** • Brushed Aluminum Finish • Silver Blades

**F624-WHF** • Flat White Finish • Flat White Blades

**F624-ORB** • Oil Rubbed Bronze Finish • Oil Brushed Bronze Blades

# ROTO XL

*Indoor/Outdoor*

**NEW**  
F624-ORB

*Indoor/Outdoor*

## FEATURES

- 20° Blade Pitch • 62" 3-Blades • 172x16mm Motor • Aluminum Construction
- 2-Wire Installation Wall Control Converts to Electronic Control System - WC105-WH Incl.
- Indoor/Outdoor Use - UL Listed for Wet Locations

U.S. Patent(s): Pending

## ENERGY INFORMATION\* (Excludes Lights)

- Airflow CFM: 7,567 • Electricity Used Watts: 70.69 • Airflow Efficiency CFM/Watts: 107.04





**NEW**  
**F753L-BNW**



**NEW**  
**F753L-WHF**



**NEW**  
**F753L-PN**  
*(Indoor Use Only)*



## *Indoor/Outdoor*

**F753L-BNW** • Brushed Nickel Wet Finish • Silver Blades • Etched Opal Glass

**F753L-WHF** • Flat White Finish • Flat White Blades • Etched Opal Glass

**F753L-PN** • Polished Nickel Finish • Silver Blades • Etched Opal Glass • *(Indoor Use Only)*

**F753L-KA** • Kocoo Finish • Kocoo Blades • Etched Opal Glass



# JAVA LED

*Indoor/Outdoor*

**NEW**  
**F753L-KA**

## JAVA LED

Minka-Aire's "everywhere" fan with a unique contemporary twist that is suitable for all environments. The Java LED features an integrated 16 watt LED light. Features indoor or outdoor usage.

### FEATURES

- 14° Blade Pitch • 54" 3-Blades • 153x18mm Motor
- Hand Held Remote Control System - RCS213 Incl.
- Integrated LED Light Uses 16W LED Incl., 3 Year Warranty • 1,550 Lumens • 3,000 Kelvin • CRI 80
- Indoor/Outdoor Use - UL Listed for Wet Locations

### ENERGY INFORMATION\* (Excludes Lights)

- Airflow CFM: 5,681 • Electricity Used Watts: 60 • Airflow Efficiency CFM/Watts: 94



# NINETY-NINE

LED



**NEW**  
F899L-BN/SL

## FEATURES

- Variable Blade Pitch • 99" 9-Blades • 172x25mm DC Motor
- Special Hand Held Remote Control System - RC600 Incl.
- Integrated LED Light Uses 26W LED Incl., 3 Year Warranty • 1,899 Lumens • 2,700 Kelvin • CRI 81

## ENERGY INFORMATION\* (Excludes Lights)

- Airflow CFM: 13,000 • Electricity Used Watts: 30 • Airflow Efficiency CFM/Watts: 433



## *Ninety-Nine*

# NINETY-NINE

Minka-Aire® introduces our Ninety-Nine fan, featuring a total circumference of 99-inches in diameter! A refreshing transitional design featuring 9-blades, 26 watt LED and a DC motor. Ideal for residential and commercial use where air movement is required. A hand held remote to control six speeds and is reversible to use in winter and summer.

**F899L-BN/SL** • Brushed Nickel Finish • Silver Blades • Etched Opal Glass

# NINETY-NINE

LED

*Ninety-Nine*



**NEW**  
F899L-ORB

**F899L-ORB** • Oil Rubbed Bronze Finish • Tobacco Blades • Etched Opal Glass  
**F899L-DK** • Distressed Koa Finish • Distressed Koa Blades • Etched Opal Glass



# Ninety-Nine

minkaAire®



**NEW**  
F899L-DK

## FEATURES

- Variable Blade Pitch • 99" 9-Blades • 172x25mm DC Motor
- Special Hand Held Remote Control System - RC600 Incl.
- Integrated LED Light Uses 26W LED Incl., 3 Year Warranty • 1,899 Lumens • 2,700 Kelvin • CRI 81

## ENERGY INFORMATION\* (Excludes Lights)

- Airflow CFM: 13,000 • Electricity Used Watts: 30 • Airflow Efficiency CFM/Watts: 433

\* Estimated

WWW.MINKAIRE.COM

minkaAire®

**NEW**  
F727-DK



**NEW**  
F727-BN/SL



**NEW**  
F727-ORB



- F727-DK** • Distressed Koa Finish • Distressed Koa Blades
- F727-BN/SL** • Brushed Nickel Finish • Silver Blades
- F727-ORB** • Oil Rubbed Bronze Finish • Tobacco Blades
- F727-BN/MM** • Brushed Nickel Finish • Medium Maple Blades





# RUDOLPH

**NEW**  
F727-BN/MM

## RUDOLPH

Inspired by a contemporary architect of the 50's, this clean three blade design best exemplifies today's trend in home furnishings. Included is a wall control, cast blade holders, 172x16mm motor for great air movement.

### FEATURES

- 21° Blade Pitch • 52" 3-Blades • 172x16mm Motor
- 2-Wire Installation Wall Control Converts to Electronic Control System - WC105-WH Incl.
- Universal Light Kit Adaptable (Sold Separately)

### ENERGY INFORMATION\* (Excludes Lights)

- Airflow CFM: 5,500 • Electricity Used Watts: 50 • Airflow Efficiency CFM/Watts: 110

\* Estimated

WWW.MINKAIRE.COM

minkaAire®

15

# CAGE FREE GYRO™

LED



**NEW**  
F304L-BN/SL


*Gyro Fans  
Rotate 360°*

## FEATURES

- High Performance Twin Turbofans Total Sweep 42" • 23° Blade Pitch • 70x16mm Motor
- Full Function Wall Control System - WCS212 Incl. • LED Light Uses 17W LED Incl., 3 Year Warranty
- 1,550 Lumens • 3,000 Kelvin • CRI 80

## ENERGY INFORMATION\* (Excludes Lights)

- Airflow CFM: 3,000 • Electricity Used Watts: 45 • Airflow Efficiency CFM/Watts: 66



**NEW**  
**F304L-ORB/MM**

Gyro Fans  
Rotate 360°



## CAGE FREE GYRO™

A wonderful addition to our Gyro™ series. Simple, clean design featuring twin turbo fans, 17 watt LED and cage free blades allow for a classic transitional spirit.

**F304L-BN/SL** • Brushed Nickel Finish • Silver Blades • Etched Opal Glass  
**F304L-ORB/MM** • Oil Rubbed Bronze Finish • Medium Maple Blades • Etched Opal Glass

# ELEMENTAL GYRO™

LED



**NEW**  
F306L-BS/SL

*Gyro Fans  
Rotate 360°*

## FEATURES

- High Performance Twin Turbofans Total Sweep 42" • 23° Blade Pitch • 70x16mm Motor
- Full Function Wall Control System - WCS212 Incl. • LED Light Uses 17W LED Incl., 3 Year Warranty
- 1,550 Lumens • 3,000 Kelvin • CRI 80

## ENERGY INFORMATION\* (Excludes Lights)

- Airflow CFM: 3,000 • Electricity Used Watts: 45 • Airflow Efficiency CFM/Watts: 66





**NEW**  
**F306L-ORB/MM**

## ELEMENTAL GYRO™

Elemental Gyro™ by Minka-Aire® is our newest addition of our Gyro™ series. A clean, industrial spirit combined with a **LED** light source and etched opal glass. The Gyro™ series continues to offer air movement throughout the entire room, or stopped to position air in only one area. Adjustment of the actual fan cages is a feature to further enhance air movement.

**F306L-BS/SL** • Brushed Steel Finish • Silver Blades • Etched Opal Glass

**F306L-ORB/MM** • Oil Rubbed Bronze Finish • Medium Maple Blades • Etched Opal Glass

# FORCE

LED



**NEW**  
**F838L-DK**


**FEATURES**

- Variable Blade Pitch • 60" 3-Blades • 168x12mm DC Motor
- Special Hand Held Remote Control System - RC400 Incl.
- Integrated LED Light Uses 15W LED Incl., 3 Year Warranty • 1,100 Lumens • 3,000 Kelvin • CRI 80
- Optional LED Light Kit, Sold Separately. Part #: 6F838LLK01

**ENERGY INFORMATION\*** (Excludes Lights)

- Airflow CFM: 6,600 • Electricity Used Watts: 26 • Airflow Efficiency CFM/Watts: 253





**NEW**  
**F838L-WH**



**NEW**  
**F838L-SL**

*Shown with  
Optional Light Kit  
Part #: 6F838LLK01*

## FORCE

A sleek, well proportioned, contemporary design featuring an integrated 15 watt LED with a 60-inch blade sweep. The Force by Minka-Aire® will make a design statement in any décor.

- F838L-DK** • Distressed Koa Finish • Distressed Koa Blades • Etched Lens
- F838L-WH** • White Finish • White Blades • Etched Lens
- F838L-SL** • Silver Finish • Silver Blades • Etched Lens • Shown with Optional Light Kit



**NEW**  
F681-GL/WS



**NEW**  
F681-BK/WS



**NEW**  
F681-PN

- F681-GL/WS** • Galvanized/Weathered Steel Finish • Dark Pine Blades • Clear Fresnel Lens
- F681-BK/WS** • Black/Weathered Steel Finish • Charcoal Driftwood Blades • Clear Fresnel Lens
- F681-PN** • Polished Nickel Finish • Silver Blades • Clear Fresnel Lens
- F681-ORB** • Oil Rubbed Bronze Finish • Dark Pine Blades • Clear Fresnel Lens

# GROTON



**NEW**  
**F681-ORB**

## GROTON

Inspired by the clear Fresnel lens used in light houses along the coast of Connecticut, we are introducing our Groton collection. Classic design combined with nautical spirit in various finishes.

### FEATURES

- 14° Blade Pitch • 56" 5-Blades • 188x25mm Motor • Hand Held Remote Control System - RCS212 Incl.
- Integrated Halogen Light Uses 2-50W Mini-Can Halogen Bulbs Incl.

### ENERGY INFORMATION\* (Excludes Lights)

- Airflow CFM: 6,500 • Electricity Used Watts: 90 • Airflow Efficiency CFM/Watts: 72

\* Estimated

[WWW.MINKAIRE.COM](http://WWW.MINKAIRE.COM)

**minkaAire**



**NEW**  
**F787-SL**

*Shown with  
Optional Light Kit  
Part #: K9787L-SL*



**NEW**  
**F787-WHF**

*Shown with Optional  
Light Kit  
Part #: K9787L-WHF*

## SIMPLE

So simple! We gave this wonderful design a name that best denotes it's spirit! Incredibly delicate and merely invisible. This design best displays the advancement in technology with indoor/outdoor use, DC motor, optional **LED** light kit and a hand held remote.

**F787-SL** • Silver Finish • Silver Blades • Shown with Optional Light Kit

**F787-WHF** • Flat White Finish • Flat White Blades

**F787-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades

# SIMPLE



**NEW**  
F787-ORB

## FEATURES

- 14° Blade Pitch • 52" 3-Blades • 123x30mm DC Motor
- Special Hand Held Remote Control System - RC600 Incl.
- Optional 15W LED Light Kit, Sold Separately. Part #: K9787L-ORB, K9787L-SL, K9787L-WHF
- Indoor/Outdoor Use - ETL Listed for Wet Locations



## ENERGY INFORMATION\* (Excludes Lights)


- Airflow CFM: 6,600 • Electricity Used Watts: 25 • Airflow Efficiency CFM/Watts: 264

\* Estimated

WWW.MINKAIRE.COM

minkaAire®

25



F581-BG



## FEATURES

- 14° Blade Pitch • 52" 4-Blades • 188x20mm Motor
- Stainless Steel Hardware and All Weather Blades
- Full Function Wall Control System - WCS212 Incl.
- Integrated Halogen Light Uses 1-50W MR16 120V 2-Pin Halogen Bulb Incl.
- Indoor/Outdoor Use - UL Listed for Wet Locations • Cap for Non-Light Use Incl.
- Optional Low Ceiling Adapter, Sold Separately. Part #: A581-BG, A581-ORB, A561-WHF

U.S. Patent(s): D513,319; D514,691; D514,692; D516,703; D517,201; D519,199

## ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 4,834 • Electricity Used Watts: 52 • Airflow Efficiency CFM/Watts: 92.97





**F581-BG**  
*Shown with Optional  
Low Ceiling Adapter  
Part #: A581-BG*



**F581-ORB**  
*Shown with Optional  
Low Ceiling Adapter  
Part #: A581-ORB*



**F581-WHF**  
*Shown with Optional  
Low Ceiling Adapter  
Part #: A581-WHF*

## GAUGUIN™

Tropical style influences the Gauguin™ by incorporating a remarkable combination of performance and unique design elements.

- F581-BG** • Bahama Beige™ Finish • Bahama Beige™ Blades • Etched Glass
- F581-ORB** • Oil Rubbed Bronze Finish • Bahama Beige™ Blades • Etched Glass
- F581-WHF** • Flat White Finish • Flat White Blades • Etched Glass

# PANCAKE



F738-DK

## PANCAKE

Our Pancake ceiling fan magically houses all the needed components of a high performance ceiling fan into a slim 3" deep body. Minimal, elegant and smooth, the profile is narrow, allowing for an unobtrusive, non-competing addition to any room.



### FEATURES

- 12° Blade Pitch • 52" 4-Blades • 6" Internally Threaded Downrod • 153x18mm Motor
- Full Function Hand Held Control System - RCS212 Incl. • Max Ceiling Slope Angle 18°

U.S. Patent(s): Pending

### ENERGY INFORMATION (Excludes Lights)


- Airflow CFM: 5,405 • Electricity Used Watts: 63.9 • Airflow Efficiency CFM/Watts: 84.58



**NEW**  
F738-SL



F738-ORB



F738-WHF

**F738-DK** • Distressed Koa Finish • Distressed Koa Blades

**F738-SL** • Silver Finish • Silver Blades

**F738-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades

**F738-WHF** • Flat White Finish • Flat White Blades




• **Cage Free Gyro™**  
F304  
Pages 16 - 17



• **Contractor Uni-Pack LED**  
F656  
Pages 4 - 5



• **Elemental Gyro™**  
F306  
Pages 18 - 19



• **Force**  
F838  
Pages 20 - 21



**Gauguin™**  
F581  
Pages 26 - 27



**Groton**  
F681  
Pages 22 - 23



• **Java LED**  
F753  
Pages 8 - 9



• **Ninety-Nine**  
F899  
Pages 10 - 13



• **Pancake**  
F738  
Pages 28 - 29



• **Raptor**  
F617  
Pages 2 - 3



**Roto XL**  
F624  
Pages 6 - 7



**Rudolph**  
F727  
Pages 14 - 15



**Simple**  
F787  
Pages 24 - 25



World Headquarters  
1151 West Bradford Court, Corona, California 92882

Showroom  
Dallas Market Center  
2100 Stemmons, Suite 3725, Dallas, TX 75207

951.278.3267 (FANS) 800.307.3267 Fax: 951.278.2828

[sales@minkagroup.net](mailto:sales@minkagroup.net) | [www.minkaaire.com](http://www.minkaaire.com) | [www.minkagroup.net](http://www.minkagroup.net)

MKADALLAS2016-01





2 0 1 5



The products depicted in this catalog are protected by United States Federal and/or State Law, including Patent, Trademark and/or Copyright laws.

Catalog and all elements of catalog design are protected by United States Federal and/or State Law, including Patent, Trademark and/or Copyright laws.

# Table of Contents

<b>Table of Contents</b> . . . . .	1-9	Iconic™ . . . . .	102-103	Supra® 52" . . . . .	194-197
<b>Welcome</b> . . . . .	10-11	Lineage™ . . . . .	107	Supra® 52" with Light . . . . .	192-193
<b>Contemporary Collection</b>		Napoli™ . . . . .	110	Timeless . . . . .	176-179
Aluma . . . . .	70-71	Napoli™ II . . . . .	111	Traditional Mojo . . . . .	166-167
Artemis™ . . . . .	34-39	Salon Grand™ . . . . .	108	Ultra-Max™ . . . . .	190-191
Artemis™ XL5 . . . . .	56-57	Santa Lucia™ . . . . .	106		
Aviation . . . . .	28-31	Traditional Mojo . . . . .	166-167	<b>Economy Collection</b>	
Cirque™ . . . . .	78-79	Volterra™ . . . . .	112-113	Contractor 42" . . . . .	218-219
Como™ . . . . .	80-81			Contractor 52" . . . . .	216-217
Concept™ I . . . . .	66-67	<b>Gyro Collection</b>		Contractor LED . . . . .	204-205
Concept™ II 44" . . . . .	64-65	Gyrette™ . . . . .	120	Contractor Plus . . . . .	206-207
Concept™ II 52" . . . . .	62-63	Gyro™ . . . . .	118	Contractor Uni-Pack . . . . .	208-215
Flyte® . . . . .	72-73	Gyro™ Wet . . . . .	119, 162	Mesa . . . . .	220
Gilera . . . . .	48-51	Traditional Gyro™ . . . . .	115		
Java . . . . .	68-69, 144-145	Vintage Gyro™ . . . . .	116-117	<b>Finish Guide</b> . . . . .	221, Fold Out
Kewl . . . . .	58-59			<b>Fan Control Systems</b>	
Light Wave . . . . .	44-45	<b>Indoor/Outdoor Collection</b>		Compatibility Chart . . . . .	224-225
Moda . . . . .	60-61	Aluma Wet . . . . .	142-143	Fan Controls . . . . .	222-223
Pancake . . . . .	52-53	Concept™ II Wet . . . . .	146-147		
Raptor . . . . .	22-23	Concept™ I Wet 52" . . . . .	124-125	<b>Fan Hanging Systems</b>	
Roto . . . . .	54-55	Concept™ I Wet 58" . . . . .	122-123	Accessories . . . . .	228
Sabot . . . . .	24-25	Craftsman™ . . . . .	128	Downrods . . . . .	226-227
San Francisco® . . . . .	74-75	Gauguin™ . . . . .	154-155		
Slipstream . . . . .	32-33	Gyro™ Wet . . . . .	119, 162	<b>Light Kits</b>	
Slipstream XXL . . . . .	132-137	Java . . . . .	68-69, 144-145	Custom Light Kits . . . . .	235
Spectre . . . . .	12-15	Magellan® . . . . .	140-141	Universal Light Kits . . . . .	229-234
Symbio . . . . .	26-27	Rainman™ . . . . .	130-131		
Uchiwa . . . . .	76-77	Shangri-La® . . . . .	129	<b>Accessory Fan Blades</b> . . . . .	236-237
Wave . . . . .	46-47	Slipstream . . . . .	32-33	<b>Glass Shades</b> . . . . .	238-239
Wing . . . . .	40-43	Slipstream XXL . . . . .	132-137	<b>Bulb Reference</b> . . . . .	240
Zen . . . . .	82-83	Strata . . . . .	138-139	<b>Index</b> . . . . .	241-243
		Sundance™ . . . . .	160-161		
<b>Transitional Collection</b>		Sundowner® . . . . .	156-159	<b>Room Size &amp; Ceiling Height</b>	
Airus™ . . . . .	84-85	Sunseeker . . . . .	126-127	<b>Recommendations</b> . . . . .	244
Delano® . . . . .	94-95	Terrana . . . . .	152-153	<b>Dimensions &amp; Specifications</b> . . . . .	
Delano® II . . . . .	96-97	Traditional Concept™ 44" . . . . .	88-89,		
New Era . . . . .	92-93	. . . . .	150-151		
Spacesaver . . . . .	90-91	Traditional Concept™ 52" . . . . .	86-87,		
Traditional Concept™ 44" . . . . .	88-89,	. . . . .	148-149		
. . . . .	150, 151				
Traditional Concept™ 52" . . . . .	86-87,	<b>Value Collection</b>			
. . . . .	148, 149	Bolo™ . . . . .	174-175		
		Classica . . . . .	188-189		
<b>Retro Collection</b>		Dyno . . . . .	164-165		
Acero™ . . . . .	98-99	Hilo . . . . .	172-173		
Hassock Aire . . . . .	101	Kafé . . . . .	186-187		
Retro Style Fan . . . . .	100	Kafé-XL . . . . .	184-185		
Xtreme . . . . .	16-21	Kola . . . . .	182-183		
		Kola-XL . . . . .	180-181		
<b>Traditional Collection</b>		Mojo . . . . .	168-169		
Calais™ . . . . .	114	Mojo II . . . . .	170-171		
Cristafano™ . . . . .	109	Supra® 32" . . . . .	202-203		
Great Room Traditional . . . . .	104-105	Supra® 44" . . . . .	200-201		
		Supra® 44" with Light . . . . .	198-199		

# Ceiling Fans



**Acero™**  
F601  
Pages 98-99



**Airus™**  
F598  
Pages 84-85



**Aluma**  
F521  
Pages 70-71



**Aluma Wet**  
F523  
Pages 142-143



**Artemis™**  
F803  
Pages 34-39



**Artemis™ XL5**  
F905  
Pages 56-57



• **Aviation**  
F853  
Pages 28-31



**Bolo™**  
F620  
Pages 174-175



**Calais™**  
F544  
Page 114



**Cirque™**  
F596  
Pages 78-79



• **Classica**  
F659  
Pages 188-189



**Classica - Gallery Edition**  
F759  
Page 188

# Ceiling Fans



**Como™**  
F603  
Pages 80-81



**Concept™ I 44"**  
F516  
Pages 66-67



**Concept™ I 52"**  
F517  
Pages 66-67



**Concept™ I Wet 52"**  
F476 / F577  
Pages 124-125



**Concept™ I Wet 58"**  
F477  
Pages 122-123



**Concept™ II 44"**  
F518  
Pages 64-65



**Concept™ II 52"**  
F519  
Pages 62-63



**Concept™ II Wet 52"**  
F474 / F574  
Pages 146-147



**Contractor 42"**  
F546  
Pages 218-219



**Contractor 52"**  
F547  
Pages 216-217



• • **Contractor LED**  
F556L  
Pages 204-205



• • **Contractor Plus**  
F556  
Pages 206-207

# Ceiling Fans



**Contractor Uni-Pack**  
F548  
Pages 212-215



**Contractor Uni-Pack**  
F647  
Pages 208-209



**Contractor Uni-Pack**  
F648  
Pages 210-211t



**Craftsman™**  
F840  
Page 128



**Cristafano™**  
F900  
Page 109




**Delano®**  
F701  
Pages 94-95



**Delano® II**  
F711  
Pages 96-97



• **Dyno**  
F1000  
Pages 164-165



**Flyte®**  
F531  
Pages 72-73



**Gauguin™**  
F581  
Pages 154-155



**Gilera**  
F733  
Pages 48-51



**Great Room Traditional**  
F539  
Pages 104-105



# Ceiling Fans



**Gyrette™**  
F302  
Page 120



**Gyro™**  
F602  
Page 118



**Gyro™ Wet**  
F402  
Page 119, 162



**Haddock Aire**  
F315  
Pages 101



• **Hilo**  
F470  
Pages 172-173



**Iconic™**  
F672  
Pages 102-103



**Java**  
F753  
Pages 68-69, 144-145



• **Kafé**  
F695  
Pages 186-187



• **Kafé-XL**  
F696  
Pages 184-185



• **Kewl**  
F833  
Pages 58-59



• **Kola**  
F688  
Pages 182-183



• **Kola-XL**  
F689  
Pages 180-181

# Ceiling Fans



• **Light Wave**  
F844  
Pages 44-45



**Lineage**  
F812  
Pages 107



**Magellan®**  
F579  
Pages 140-141



**Mesa™**  
F565 / F566  
Pages 220



**Moda**  
F737  
Pages 60-61



**Mojo**  
F522  
Page 168-169



• **Mojo II**  
F533  
Pages 170-171



**Napoli™**  
F705  
Page 110



**Napoli™ II**  
F715  
Page 111



**New Era**  
F513  
Pages 92-93



• **Pancake**  
F738  
Pages 52-53



**Rainman™**  
F582  
Pages 130-131

# Ceiling Fans



•• **Raptor**  
F617  
Pages 22-23



**Retro Style Fan**  
F300  
Page 100



• **Roto**  
F524  
Pages 54-55



•• **Sabot**  
F745  
Pages 24-25



**Salon Grand™**  
F707  
Page 108



**San Francisco®**  
F528 / F529  
Pages 74-75



**Santa Lucia™**  
F820  
Page 106



**Shangri-La®**  
F580  
Page 129



**Slipstream**  
F888  
Pages 32-33



• **Slipstream XXL**  
F889  
Pages 132-137



**Spacesaver**  
F510  
Pages 90-91



•• **Spectre**  
F726  
Pages 12-15

# Ceiling Fans



**Strata**  
F734  
Pages 138-139



• **Sundance™**  
F571 / F572  
Pages 160-161



• **Sundowner®**  
F589  
Pages 156-159



• **Sunseeker**  
F532  
Pages 126-127



**Supra® 32"**  
F562  
Pages 202-203



**Supra® 44"**  
F563  
Pages 200-201



**Supra® -SP 44"**  
F563-SP  
Pages 198-199



• **Supra® 52"**  
F568  
Pages 194-197



**Supra® 52"**  
F569  
Pages 192-193



• • **Symbio**  
F828  
Pages 26-27



**Terrana**  
F680  
Pages 152-153



• **Timeless**  
F614  
Pages 176-179

# Ceiling Fans



**Traditional Concept™ 44"**  
F593  
Pages 88-89, 150-151



**Traditional Concept™ 52"**  
F594  
Pages 86-87, 148-149



**Traditional Gyro™**  
F502  
Pages 115



• **Traditional Mojo**  
F622  
Pages 166-167



**Uchiwa**  
F824  
Pages 76-77



• **Ultra-Max™**  
F588  
Pages 190-191



**Vintage Gyro™**  
F802  
Pages 116-117




**Volterra™**  
F702  
Pages 112-113



• **Wave**  
F843  
Pages 46-47



• **Wing**  
F823  
Pages 40-43




• **Xtreme**  
F887  
Pages 16-21



• **Zen**  
F514  
Pages 82-83





Aviation - F853  
Page(s): 28

Minka-Aire® invites you to view our ceiling fan collection designed for today's varying lifestyles.

Within this catalog, you will find designs of contemporary flair with elegant grace, transitional timeless styles and a collection from our licensed design series.



San Francisco® - F529  
Page(s): 74

The architectural trend toward Great Rooms has led Minka-Aire® to redesign some of our most popular styles with enlarged bodies and longer blades to circulate more air and complement the spaciousness of these rooms.

Our Outdoor Series of fans allows your friends and family to enjoy outdoor dining or time in your spa while continuing to have pleasant surroundings.

We offer many design choices for the outdoors; rated for

all-weather exposure.

Minka-Aire® ceiling fans offer a wide variety of designs for the American home.



Timeless - F614  
Page(s): 176

## Our Products Feature:

- Finishes that complement today's interiors and exteriors
- Advanced technology with our control systems
- Ease of installation
- Limited Lifetime Warranty on our motors
- Wide variety of unique designs from sleek contemporary to classic traditional
- Powerful motors that conserve energy use in the home
- Flawless craftsmanship
- Designs that coordinate with our Minka-Lavery® lighting collections



Gauguin™ - F581  
Page(s): 154

- Safe  and  manufacturing approval products

Our energy-saving Minka-Aire® ceiling fans are manufactured to the highest quality standards.

We are privileged to partner with some of the most recognized designers in the home furnishing industry. The products under our Designer Collection features George Kovacs®, Hearst Castle® and Jessica McClintock Home, The Romance Collection™. Our Designer Collection combines a unique blend of style with performance. All of these designs exemplify elegance and a timeless spirit that is the hallmark of Minka-Aire®.



# Spectre

with LED Light

LED



## F726-BN/SL

Brushed Nickel Finish  
Silver Blades  
with Clear Lens

LED

### Features:

- 14° Blade Pitch
- 60" 4 Blades
- DC 188 x 10MM Motor
- 3½" and 6" Downrods
- Integrated LED Light  
Uses 18W LED (Included)  
3 Year Warranty
- 1100 Lumens
- 3000K
- CRI 80
- Special Hand Held Remote Control  
System Included - RC400

U.S. Patent(s): Pending

### \* Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,000	82	187.5

\* Estimated



## RC400

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222

Versatile, industrial styling and creative details are the key to Spectre. The distinctive blade irons hug the fan body, providing a unique look compatible with contemporary environments.

LED

Lifetime  
WARRANTY

Remote  
CONTROL  
FULL FUNCTION

LED



**F726-WHF/BN**

Flat White / Brushed Nickel Finish  
Flat White Blades  
with Clear Lens



**F726-BN/ORG**

Brushed Nickel / Orange Finish  
Orange Blades  
with Clear Lens

LED



# Spectre

with LED Light

LED

## F726-ORB/AB

Oil Rubbed Bronze with  
Antique Brass Finish  
Tobacco Blades  
with Clear Lens

LED

### Features:

- 14° Blade Pitch
- 60" 4 Blades
- DC 188 x 10MM Motor
- 3½" and 6" Downrods
- Integrated LED Light  
Uses 18W LED (Included)  
3 Year Warranty
- 1100 Lumens
- 3000K
- CRI 80
- Special Hand Held Remote Control  
System Included - RC400

U.S. Patent(s): Pending

### \* Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,000	82	187.5

\* Estimated



## RC400

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222

LED

## F726-WHF/BN

Flat White / Brushed Nickel Finish  
Flat White Blades  
with Clear Lens

Lifetime  
WARRANTY

Remote  
CONTROL  
FULL FUNCTION



LED

**F726-ORB/BN**


Oil Rubbed Bronze / Brushed Nickel Finish  
Oil Rubbed Bronze Blades  
with Clear Lens

Versatile, industrial styling and creative details is the key to Spectre. The distinctive blade irons hug the fan body, providing a unique look compatible with contemporary environments.

LED

LED

# Xtreme



**T**his industrial size fan lends itself to almost any setting. Xtreme's clean, sleek, contemporary design with a DC motor and a choice of blade sizes makes it perfect for large areas.



**F887-72-BN 72"**  
**F887-80-BN 80"**  
**F887-88-BN 88"** (Shown)  
**F887-96-BN 96"**

□ Brushed Nickel Finish  
 Silver Blades

**Features:**

- 4° Blade Pitch
- 72", 80", 88" or 96" 9 Blades
- DC 165 x 25mm Motor
- 3½" and 6" Downrods
- Aluminum Blades
- Install with Blades at least 10' from the Floor
- Special Hand Held Remote Control System Included - RC400

**Energy Information for 72"**  
 (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
10,203	29	351.83



**RC400**

□ Full Function Hand Held Remote Control Included  
 For Details See Page(s): <?>

**Lifetime**  
 WARRANTY

**Remote**  
 CONTROL  
 FULL FUNCTION


# Xtreme








# Xtreme



This industrial size fan lends itself to almost any setting. Xtreme's clean, sleek, contemporary design with a DC motor and a choice of blade sizes makes it perfect for large areas.



**F887-72-ORB 72"**  
**F887-80-ORB 80"**  
**F887-88-ORB 88"** (Shown)  
**F887-88-ORB 96"**

Oil Rubbed Bronze Finish  
 Oil Rubbed Bronze Blades

**Features:**

- 4° Blade Pitch
- 72", 80", 88" or 96" 9 Blades
- DC 165 x 25mm Motor
- 3½" and 6" Downrods
- Aluminum Blades
- Install with Blades at least 10' from the Floor
- Special Hand Held Remote Control System Included - RC400

**Energy Information for 72"**  
 (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
10,203	29	351.83



**RC400**

Full Function Hand Held Remote Control Included  
 For Details See Page(s): <?>

**Lifetime**  
 WARRANTY

**Remote**  
 CONTROL  
 FULL FUNCTION



LED

LED

**F617-GM**

Gun Metal Finish  
Gun Metal Blades  
with Etched Opal Glass

This contemporary design is coupled with the energy saving advancements of DC motor technology and an integrated LED light source.

LED



**F617-WH**

White Finish  
White Blades  
with Etched Opal Glass

# Raptor

with LED Light

LED



**F617-ORB/AB**

Oil Rubbed Bronze / Antique Brass Finish  
Tobacco Blades  
with Tinted Opal Glass



**F617-BN**

Brushed Nickel Finish  
Silver Blades  
with Etched Opal Glass

LED

**Features:**

- 14° Blade Pitch
- 60" 5 Blades
- 3½" and 6" Downrods
- DC 172 x 12mm Motor
- Integrated LED Light  
Uses 17W LED (Included)  
3 Year Warranty
- 1100 Lumens
- 3000K
- CRI 80
- Special Hand Held Remote Control System Included - RC600

**\* Energy Information (Excludes Lights)**

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
<b>6,000</b>	<b>30</b>	<b>200</b>

\* Estimated

**Lifetime**  
WARRANTY

**Remote**  
CONTROL  
FULL FUNCTION



**RC600**

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222

# Sabot

with LED Light

LED

LED

## F745-DK

Distressed Koa Finish  
Reversible Medium Maple / Dark Walnut Blades  
with White Lens  
(Shown with Dark Walnut Blades)

### Features:

- 12° Blade Pitch
- 52" 5 Blades
- DC 172 x 12mm Motor
- 3½" and 6" Downrods
- Integrated LED Light  
Uses 17W LED (Included)  
3 Year Warranty
- 1100 Lumens
- 3000K
- CRI 80
- Special Hand Held Remote Control  
System - RC600

U.S. Patent(s): Pending

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,000	30	166.6



## RC600

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222

Sabot's sleek, contemporary design has created a vision for today's interiors. Its low profile provides maximum air management in rooms with minimal ceiling heights.

The Sabot's integrated, energy efficient LED light will bring any room to life.

LED

Lifetime  
WARRANTY

Remote  
CONTROL  
FULL FUNCTION



LED



LED

**F745-BN**

Brushed Nickel Finish  
Silver Blades  
with White Lens



**F745-ORB**

Oil Rubbed Bronze Finish  
Reversible Medium Maple / Dark Walnut Blades  
with White Lens  
(Shown with Dark Walnut Blades)

LED

# Symbio

with LED Light

LED



**F828-BN**

Brushed Nickel Finish  
Silver Blades  
with Etched Glass

LED



**F828-ORB**

Oil Rubbed Bronze  
Medium Maple Blades  
with Tea Stain Glass

LED



**F828-WHF**

Flat White Finish  
Flat White Blades  
with Etched Glass

LED

**F828-BN/DW**

Brushed Nickel Finish  
Dark Walnut Blades  
with Etched Glass

LED

This clean contemporary powerhouse delivers the air flow of larger fans using DC motor technology to keep energy consumption to a minimum while the integrated LED light provides energy efficient illumination.

**Features:**

- 13° Blade Pitch
- 56" 5 Blades
- 3½" and 6" Downrods
- Integrated LED Light  
Uses 16W DC LED (Included)  
3 Year Warranty
- 1352 Lumens
- 2700K
- CRI 80
- Special Hand Held Remote Control System Included - RC400

U.S. Patent(s): Pending

**\* Energy Information (Excludes Lights)**

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
<b>6,000</b>	<b>35</b>	<b>171</b>

\* Estimated

**Lifetime**  
WARRANTY

**Remote**  
CONTROL  
FULL FUNCTION



**RC400**

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222

LED

**F828-BN/WH**

Brushed Nickel Finish  
White Blades  
with Etched Glass

# Aviation

## F853-BN/DK

Brushed Nickel Finish  
Distressed Koa Blades

### Features:

- Variable Blade Pitch
- 60" 3 Blades
- DC 120 x 25mm Motor
- 3½" and 6" Downrods
- Special Hand Held Remote Control System Included - RC500

U.S. Patent(s): D721,429; D721,800; D726,298

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,604	25.92	254.80

Lifetime  
WARRANTY

Remote  
CONTROL  
FULL FUNCTION



## RC500

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222

A close-up photograph of a ceiling fan's motor housing and a wooden blade. The blade is a rich, dark brown color with a visible wood grain. The motor housing is also a matching dark brown color and has a sleek, modern design. The background is a plain, light color.

Inspired by the classic form of vintage aircraft propellers, our Aviation fan has an updated appeal that addresses a new audience with sleek, elegant lines and a combination of finish techniques that work for all of today's trends.

**F853-RW**

Rosewood Finish  
Rosewood Blades



# Aviation

## F853-WH

White Finish  
White Blades

### Features:

- Variable Blade Pitch
- 60" 3 Blades
- DC 120 x 25mm Motor
- 3½" and 6" Downrods
- Special Hand Held Remote Control System Included - RC500

U.S. Patent(s): D721,429; D721,800; D726,298

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,604	25.92	254.80

**Lifetime**  
WARRANTY

**Remote**  
CONTROL  
FULL FUNCTION



## RC500

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222





**F853-BN/MM**

Brushed Nickel Finish  
Medium Maple Blades



**F853-BN/SL**

Brushed Nickel Finish  
Silver Blades

# Slipstream



## F888-BNW

Brushed Nickel Wet Finish  
Silver Blades  
with Etched Opal Glass

### Features:

- 14° Blade Pitch
- 65" 8 Concave Blades
- DC 165 x 25mm Motor
- Galvanized Steel  
3½" and 6" Downrods
- Stainless Steel Hardware and  
All Weather Blades
- Special Hand Held Remote Control  
System Included - RC400
- Integrated Light  
Uses 1-18W GU24 Non-Dimmable  
Squat CFL (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use  
UL Listed for Wet Locations



## RC400

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
8,778	27.6	318.04

Slipstream's sleek industrial styling  
destines this 8-bladed  
wonder to make a cool  
statement in any indoor or  
outdoor setting.

U.S. Patent(s): D715,917



For Wet Location





**F888-WHF**

Flat White Finish  
Flat White Blades  
with Etched Opal Glass



**F888-DK**

Distressed Koa Finish  
Distressed Koa Blades  
with Tinted Opal Glass



**F888-ORB**

Oil Rubbed Bronze Finish  
Oil Rubbed Bronze Blades  
with Tinted Opal Glass

Shown with Cap for Non-Light Use

# Artemis™



**F803-DK**  
 Distressed Koa Finish  
 with Tinted Opal Glass

## Features:

- Contoured Aerodynamic Vanes
- Variable Blade Pitch
- 58" 3 Vanes
- 3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light  
 Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D535,011; D535,015; D535,387;  
 D535,388; D536,083; 7,481,626

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,453	95	67.92



**F803-LN**  
 Liquid Nickel Finish  
 with Etched Opal Glass



**WCS212**  
 Full Function Wall Control System Included  
 For Details See Page(s): 223

**Lifetime**  
 WARRANTY

**WallControl**  
 FULL FUNCTION



The distinct profile of the Artemis™ is captured by the Flying Vanes™ that incorporate the fan housing. A true design statement!

Winner of the 2005 Chicago Athenaeum: Museum of Architecture and Design's Good Design Award.

**F803-MG**

Mahogany Finish  
with Etched Opal Glass

# Artemis™



## F803-RD

High Gloss Pure Red Finish  
with Etched Opal Glass

### Features:

- Contoured Aerodynamic Vanes
- Variable Blade Pitch
- 58" 3 Vanes
- 3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen  
Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D535,011; D535,015; D535,387;  
D535,388; D536,083; 7,481,626

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,453	95	67.92



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

**Lifetime**  
WARRANTY

**WallControl**  
FULL FUNCTION



**F803-CPBR**

Copper Bronze Finish  
with Tinted Opal Glass



**F803-SL**

Silver Finish  
with Etched Opal Glass

# Artemis™



## F803-WH

High Gloss White Finish  
with Etched Opal Glass



## F803-TL

Translucent Finish  
with Etched Opal Glass

## Features:

- Contoured Aerodynamic Vanes
- Variable Blade Pitch
- 58" 3 Vanes
- 3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen  
Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D535,011; D535,015; D535,387;  
D535,388; D536,083; 7,481,626

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,453	95	67.92



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

**Lifetime**  
WARRANTY

**WallControl**  
FULL FUNCTION



**F803-BK**

High Gloss Black Finish  
with Etched Opal Glass



**F803-MP**

Maple Finish  
with Etched Opal Glass



# Wing



**F823-DK**  
Distressed Koa Finish



## Features:

- Variable Blade Pitch
- 52" 1 Wing
- DC 125 x 30mm Motor
- 6" Downrod
- Special Hand Held Remote Control System Included - RC400

U.S. Patent(s): D678,977; 9,004,863

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,974	30.2	197.81

**Lifetime**  
WARRANTY

**Remote**  
CONTROL  
FULL FUNCTION



**RC400**

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222



A unique 52" single wing fan that transcends all conventional designs.

Winner of the 2010 Chicago  
Athenaeum: Museum of Architecture  
and Design's Good Design Award.

**F823-WH**

High Gloss White Finish

# Wing

## F823-MG

Mahogany Finish

### Features:

- Variable Blade Pitch
- 52" 1 Wing
- DC 125 x 30mm Motor
- 6" Downrod
- Special Hand Held Remote Control System Included - RC400

U.S. Patent(s): D678,977; 9,004,863

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,974	30.2	197.81

Lifetime  
WARRANTY

Remote  
CONTROL  
FULL FUNCTION



## RC400


Full Function Hand Held Remote Control Included  
For Details See Page(s): 222





□ **F823-SL**

Silver Finish



□ **F823-MP**

Maple Finish

# Light Wave

with LED Light

LED

LED



## F844-DK

Distressed Koa Finish  
Distressed Koa Blades  
with Etched Lens

### Features:

- 48° Blade Pitch
- 52" 3 Blades
- 4½" and 6" Downrods
- Integrated Light  
Uses 17W Dimmable LED  
(Included) 3 Year Warranty
- 1100 Lumens
- 3000K
- CRI 80
- Hand Held Remote Control System
- Replacement LED Assembly  
(Part #6F844LK01)

U.S. Patent(s): Pending

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,024	65.3	76.94



## RCS213

Hand Held Remote Control Included  
For Details See Page(s): 222

Light Wave is the next generation of our highly successful, ground-breaking Wave fan. Its energy-efficient LED\* light source integrates light without compromising design.

LED

**Lifetime**  
WARRANTY

**Remote**  
CONTROL



# LED

**F844-WH**


White Finish  
White Blades  
with Etched Lens



**F844-SL**

Silver Finish  
Silver Blades  
with Etched Lens

# Wave



**F843-SL**

Silver Finish

## Features:

- 48° Blade Pitch
- 52" 3 Blades
- 4½" and 6" Downrods
- Hand Held Remote Control System

U.S. Patent(s): D715,419; D715,421

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,580	66.4	99

A truly unique design that draws inspiration from the ocean's graceful and tubular wave formations.

**Lifetime**  
WARRANTY

**Remote**  
CONTROL



**RCS213**

Hand Held Remote Control Included  
For Details See Page(s): 222





**F843-DK**

Distressed Koa Finish



**F843-WH**

White Finish

# Gilera



## F733-BK/RW

Black / Rosewood Finish  
Rosewood Blades

### Features:

- 14° Blade Pitch
- 62" 3 Blades
- 3½" and 6" Downrods
- Full Function Wall Control System

U.S. Patent(s): Pending

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,431	102.8	62.55



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

**Lifetime**  
WARRANTY

**WallControl**  
FULL FUNCTION

Vintage Italian racing motorcycles served as the design vision for the Gilera ceiling fan. With its 62-inch blade, Gilera is specially designed for use in rooms with greater ceiling heights. Highly detailed and dramatically proportioned, Gilera is destined to become an heirloom of the future.

**F733-SL**

Silver Finish  
Silver Blades



# Gilera



## F733-BS/BN

Brushed Steel / Brushed Nickel Finish  
Medium Maple Blades



## F733-PN

Polished Nickel Finish  
Silver Blades

### Features:

- 14° Blade Pitch
- 62" 3 Blades
- 3½" and 6" Downrods
- Full Function Wall Control System

U.S. Patent(s): Pending

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,431	102.8	62.55



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

Lifetime  
WARRANTY

WallControl  
FULL FUNCTION



**F733-WH**

White Finish  
White Blades



# Pancake



## F738-BN

Brushed Nickel Finish  
Silver Blades

## Features:

- 12° Blade Pitch
- 52" 4 Blades
- **6" Internally Threaded Downrod**  
Downrod sizes of 48", 60" and 72" are currently not available in BN and PN finishes.  
See Page(s): 228 for Details
- Max Ceiling Slope Angle 18°
- Full Function Hand Held Remote Control System

U.S. Patent(s): Pending

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,405	63.9	84.58



## F738-ORB

Oil Rubbed Bronze Finish  
Oil Rubbed Bronze Blades

Lifetime WARRANTY

Remote CONTROL  
FULL FUNCTION



## RCS212

Full Function Hand Held Remote Control Included  
For Details See Page(s): 223





**F738-DK**

Distressed Koa Finish  
Distressed Koa Blades

Our Pancake ceiling fan magically houses all the needed components of a high performance ceiling fan into a slim 3-inch deep body. Minimal, elegant and smooth, the profile is narrow, allowing for an unobtrusive, non-competing addition to any room.



**F738-WHF**

Flat White Finish  
Flat White Blades

# Roto



## F524-ABD

Brushed Aluminum Finish  
Silver Blades

### Features:

- 22° Blade Pitch
- 52" 3 Blades
- 3½" and 6" Downrods
- Aluminum Construction
- 2-Wire Installation Wall Control  
Converts to Electronic Control  
System

U.S. Patent(s): Pending

### Energy Information

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,816	51.5	113

Roto features a sleek and contemporary design with a classic industrial look. Well edited and an impeccably executed design features a slight "fold" construction along the length of the blades to increase the flow of air. A perfect marriage of form and function.

Lifetime  
WARRANTY

WallControl



## WC105-WH

Wall Control System Included  
For Details See Page(s): 223





**F524-WHF**  
Flat White Finish  
Flat White Blades



**F524-DK**  
Distressed Koa Finish  
Distressed Koa Blades




**F524-ORB**  
Oil Rubbed Bronze Finish  
Oil Rubbed Bronze Blades

GEORGE  
KOVACS®

by

minkaAire®  
A Minka Group® Co.



**F905-SL**

Silver Finish  
with Etched Opal Glass

**Features:**

- Variable Blade Pitch
- 62" 5 Blades
- DC 172 x 25mm Motor
- 3½" and 6" Downrods
- Special Hand Held Remote Control System Included - RC600
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D721,430

**Energy Information** (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
8,289	41.48	199.83

The big brother of our original Artemis™, the distinct profile of the Artemis™ XL5 is captured by the five Flying Vanes™ that encase the fan housing - creating a true design statement!




**RC600**

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222

**Lifetime**  
WARRANTY


**Remote**  
CONTROL  
FULL FUNCTION

# Artemis™ XL5



## F905-DK

Distressed Koa Finish  
with Tinted Opal Glass




## F905-WH

White Finish  
with Etched Opal Glass

Shown with Cap for Non-Light Use

# Kewl



□ **F833-RD**  
Red Finish

## Features:

- 22° Blade Pitch
- 52" 3 Blades
- 3½" and 6" Downrods
- 2-Wire Installation Wall Control  
Converts to Electronic Control System

U.S. Patent(s): D715,418; D726,299

## Special Note:

- Custom Finish Orders Accepted
  - 200 Piece Minimum Order Per Finish
  - 90 Day Lead Time

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,304	55	114.62



□ **WC105-WH**  
Wall Control System Included  
For Details See Page(s): 223



□ **F833-WH**  
White Finish

**Lifetime**  
WARRANTY

WallControl





**F833-SL**  
Silver Finish



**F833-BK**  
Black Finish





# Moda



## F737-BN

Brushed Nickel Finish  
Silver Blades  
with Etched White Glass

### Features:

- 20° Blade Pitch
- 60" 3 Blades
- DC 188 x 14mm Motor
- 3½" and 6" Downrods
- Integrated Uplight  
Use 10-15W Candelabra Bulbs  
(Included)
- Special Hand Held Remote Control  
System Included - RC500

U.S. Patent(s): Pending

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,458	26.5	281.43



## F737-ORB

Oil Rubbed Bronze Finish  
Dark Maple Blades  
with Tea Stained Glass



## RC500

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222

**Lifetime**  
WARRANTY

**Remote**  
CONTROL  
FULL FUNCTION

Versatility, transitional styling and creative details are the key to Moda. With hand-crafted blades, which uniquely hug close to the hub, Moda incorporates a tinted glass shade that directs light up toward the ceiling, producing a glowing up-light effect.



**F737-WH**

White Finish  
White Blades  
with Etched White Glass

# Concept™ II

## 52"

### F519-BN

Brushed Nickel Finish  
Silver Blades  
with White Opal Glass

### F519-ORB

Oil Rubbed Bronze Finish  
Taupe Blades  
with White Opal Glass

### F519-PN

Polished Nickel Finish  
Silver Blades  
with White Opal Glass



**F519-WH**

White Finish  
White Blades  
with White Opal Glass

As the name implies, “a taste of things to come,” simple in style, yet ingenious by design, the Concept™ II requires 75% less time and labor to assemble than conventional ceiling fans.

**Features:**

- 14° Blade Pitch
- 52" 3 Concave Blades
- Flush Mount - Ideal for Low Ceilings  
Total Hanging Depth 11½" with or without Light
- Full Function Hand Held Remote Control System
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D478,654; D478,974; D478,980; 7,008,192

**Energy Information** (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,710	55	103.82



**F519-MG**

Mahogany Finish  
Mahogany Blades  
with White Opal Glass

**Lifetime**  
WARRANTY

**Remote**  
CONTROL  
FULL FUNCTION



**RCS212**

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222

Accessory Blades Available. See Page(s): 236

# Concept™ II

44"



## F518-WH

White Finish  
White Blades  
with White Opal Glass

As the name implies, "a taste of things to come," simple in style, yet ingenious by design, the Concept™ II requires 75% less time and labor to assemble than conventional ceiling fans.



## F518-BN

Brushed Nickel Finish  
Silver Blades  
with White Opal Glass





**F518-ORB**

Oil Rubbed Bronze Finish  
Taupe Blades  
with White Opal Glass



**F518-PN**

Polished Nickel Finish  
Silver Blades  
with White Opal Glass  
Shown with Cap for Non-Light Use

**Features:**

- 14° Blade Pitch
- 44" 3 Concave Blades
- Flush Mount - Ideal for Low Ceilings  
Total Hanging Depth 11½" with or without Light
- Full Function Hand Held Remote Control System
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D478,654; D478,974; D478,980; 7,008,192

**Energy Information** (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,071	43.7	93.16

**Lifetime**  
WARRANTY

**Remote**  
CONTROL  
FULL FUNCTION



**RGS212**

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222

Accessory Blades Available. See Page(s): 236



**F516-ORB 44"**

**F517-ORB 52"**

Oil Rubbed Bronze Finish  
Taupe Blades  
with White Opal Glass



**F516-WH 44"**

**F517-WH 52"**

White Finish  
White Blades  
with White Opal Glass

# Concept™ I

**F516-PN 44"**  
**F517-PN 52"**

Polished Nickel Finish  
Silver Blades  
with White Opal Glass



**F516-BN 44"**  
**F517-BN 52"**

Brushed Nickel Finish  
Silver Blades  
with White Opal Glass

Shown with Cap for Non-Light Use



**RCS212**

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222

**Features:**

- 14° Blade Pitch
- 44" or 52" 3 Concave Blades
- 3½" and 6" Downrods
- Full Function Hand Held Remote Control System
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D475,782; D476,408; D478,654;  
D478,980; 7,008,192

**F516 Energy Information** (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
<b>3,987</b>	<b>46</b>	<b>86.68</b>

**F517 Energy Information** (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
<b>6,028</b>	<b>61</b>	<b>98.82</b>

**Lifetime**  
WARRANTY

**Remote**  
CONTROL  
FULL FUNCTION

Accessory Blades Available. See Page(s): 236

# Java



## F753-KA

Kocoa Finish  
Kocoa Blades

### Features:

- 14° Blade Pitch
- 54" 3 Blades
- 3½" and 6" Downrods
- Hand Held Remote Control System
- Indoor/Outdoor Use  
UL Listed for Wet Locations

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,681	60	94

Lifetime  
WARRANTY

Remote  
CONTROL



## RCS213

Hand Held Remote Control Included  
For Details See Page(s): 222



## F753-BNW

Brushed Nickel Wet Finish  
Silver Blades



LISTED  
For Wet Location





**F753-PN**

Polished Nickel Finish  
Silver Blades  
(Finish For Indoor Use Only)

Minka-Aire's "everywhere" fan with a unique contemporary twist that is suitable for all environments.



**F753-WHF**

Flat White Finish  
Flat White Blades

# Aluma



## F521-ABD

Brushed Aluminum Finish  
Silver Blades  
with Etched Opal Glass

### Features:

- 12° Blade Pitch
- 52" 4 Blades
- 3½" and 6" Downrods
- WC106 4-Speed Full Range Dimmer  
3-Wire Installation Wall Control  
Converts to Electronic Control System
- All Aluminum Construction
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,471	66.6	82.15



## WC106-WH

Wall Control System Included  
For Details See Page(s): 223



## F521-ORB

Oil Rubbed Bronze Finish  
Oil Rubbed Bronze Blades  
with Tinted Opal Glass

Lifetime  
WARRANTY

WallControl



With its 4-speed control, full range dimmer, 52-inch sweep, halogen light and optional cap for non-light use, the Aluma is minimal in form with a youthful soft contemporary twist that makes it a fan with universal appeal.



**F521-WHF**

Flat White Finish  
Flat White Blades  
with Etched Opal Glass  
Shown with Cap for Non-Light Use



**F531-L-BN**

Brushed Nickel Finish  
Birdseye Maple Blades  
with White Opal Glass



**F531-L-WH**

White Finish  
High Gloss White Blades  
with White Opal Glass



## F531-L-BN/MG

Brushed Nickel Finish  
Mahogany Blades  
with White Opal Glass  
Mahogany Downlink™

Shown with Cap for Non-Light Use

The essence of simplicity and elegance, the Flyte® fan's combination of integrated halogen light and distinctive hanging system gives this contemporary design a compelling and sophisticated presence.

Winner of the 2001 Chicago  
Athenaeum: Museum of Architecture  
and Design's Good Design Award

## Features:

- 14° Blade Pitch
- 56" 3 Blades
- Includes 9" Downlink™ Hanging System with ½" I.D. Downrod
- Wall Control System
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Suitable for Installation on Vaulted Ceilings up to 21°
- Capable of using 3½" Downrod for Low Ceiling Application (Part #DR235-44 and #DR235-BN)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D453,216

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,703	67	85.12



## WCS213

Wall Control System Included  
For Details See Page(s): 223

**Lifetime** WARRANTY **WallControl**

Accessory Blades Available. See Page(s): 236

Additional Downlink™ Options Available  
See Page(s): 228

Winner of the 1998 Chicago  
Athenaeum: Museum of Architecture  
and Design's Good Design Award

**F529-L-ORB**

- Oil Rubbed Bronze Finish  
Medium Maple Blades  
with Tinted Opal Glass

**F528-L-BS/CH**

- Brushed Steel / Chrome Finish  
Birdseye Maple Blades

# San Francisco®



## F529-L-BS/CH

Brushed Steel / Chrome Finish  
Birdseye Maple Blades  
with Frosted Glass

The bold, clean lines and simplicity of the San Francisco® fan make it a timeless architectural design element, suited for any interior.

## Features:

- 13° Blade Pitch
- 56" 3 Blades
- Includes 12" Pre-Wired Downbridge™ Hanging System
- Wall Control System
- Integrated Halogen Light Uses 1-75W JDR Intermediate Base Bulb (Included)
- Suitable for Installation on Vaulted Ceilings up to 30°

U.S. Patent(s): 5,951,253; 6,158,964; 6,171,060; 6,250,885

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,780	77	75.02



## WCS213

Wall Control System Included  
For Details See Page(s): 223

**Lifetime WARRANTY** WallControl

Accessory Blades Available. See Page(s): 236

Additional Downbridge™ Options Available.  
See Page(s): 228

# Uchiwa



## F824-ORB/TB

Oil Rubbed Bronze / Toned Brass Finish  
Oil Rubbed Bronze Blades  
with Tinted Opal Glass

うちわ

Harmoniously marked by characteristics and finishes of the present period, the Uchiwa is a functional art piece.

### Features:

- 16° Blade Pitch
- 56" 3 Blades
- 3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light  
Uses 1-75W Mini-Can Halogen Bulb (Included)

U.S. Patent(s): D618,786; D618,787; D620,586

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,574	58	78.86



### WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

Lifetime WARRANTY

WallControl FULL FUNCTION





**F824-BK/CH**

Black / Chrome Finish  
Silver Blades  
with Etched Opal Glass



**F824-WH**

White Finish  
White Blades  
with Etched Opal Glass

by



**F596-BN**

Brushed Nickel Finish  
Silver Blades

Winner of the 2003 Chicago  
Athenaeum: Museum of Architecture  
and Design's Good Design Award

**Features:**

- 14° Blade Pitch
- 54" 3 Blades and 25" 3 Blades
- 4" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light  
Uses 1-50W MR16 120V 2-Pin  
Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D510,621; D513,316; D514,689;  
D524,433; D549,816

**Energy Information** (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,087	49	103.81



**WCS212**

Full Function Wall Control System Included  
For Details See Page(s): 223



**F596-BN**

Brushed Nickel Finish  
Shown with Optional FB196-MG Blades

**Lifetime**  
WARRANTY

**WallControl**  
FULL FUNCTION

Accessory Blades Available. See Page(s): 236

# Cirque™



## F596-PN/TL

Polished Nickel Finish  
Translucent Blades



## F596-BN

Brushed Nickel Finish  
Shown with Optional FB196-RYB Blades



**F603-ORB**

- Oil Rubbed Bronze Finish  
Tobacco Blades  
with Satin White Opal Glass



**F603-WH**

- White Finish  
White Blades  
with Satin White Opal Glass



## F603-BN

Brushed Nickel Finish  
Silver Blades  
with Satin White Opal Glas

Como™ is a harmonious, versatile design with clean, contemporary lines highlighted with subtle chrome, bronze and brushed nickel accents.

### Features:

- 14° Blade Pitch
- 54" 5 Blades
- 3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light  
Uses 2-75W Mini-Can Halogen Bulbs (Included)

U.S. Patent(s): D476,728

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,761	92	73.29



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

**Lifetime**  
WARRANTY

**WallControl**  
FULL FUNCTION



**F514-ORB**

- Oil Rubbed Bronze Finish
- Medium Maple Blades
- with Tinted Opal Glass



**F514-BN**

- Brushed Nickel Finish
- Silver Blades
- with White Frosted Glass
- Shown with Optional Cap for Non-Light Use



# Zen



## F514-WH

White Finish  
White Blades  
with White Frosted Glass

A clean modern profile is accentuated in three finish options.

### Features:

- 14° Blade Pitch
- 52" 4 Blades
- 3½" and 6" Downrods
- Full Function Hand Held Remote Control System
- Integrated Light Kit  
Uses 2-13W Non-Dimmable GU24 CFL Bulbs (Included)
- Cap for Non-Light Use (Included)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,148	71	86.05



## RCS212

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222

Lifetime  
WARRANTY

Remote  
CONTROL  
FULL FUNCTION



# Airus™



## F598-ORB

Oil Rubbed Bronze Finish  
Medium Maple Blades  
with Excavation Glass

### Features:

- 14° Blade Pitch
- 54" 5 Blades
- 3½" and 6" Downrods
- Full Function Wall Control System Independent Up/Downlight
- Integrated Halogen Uplight and Downlight
- Uses 4-50W Mini-Can Halogen Bulbs (Included)

U.S. Patent(s): D471,269; D473,639; D475,776

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,668	82	69.12



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

Airus™ is poetry in motion.  
Its graceful silhouette comfortably fits in any transitional setting. Featured uplight can be controlled independently of the halogen light below.

Lifetime WARRANTY

WallControl FULL FUNCTION



**F598-WH**

White Finish  
High Gloss White Blades  
with Acid Etched Glass



**F598-BN**

Brushed Nickel Finish  
Silver Blades  
with Acid Etched Glass

# Traditional Concept™ 52"



## F594-ORB

Oil Rubbed Bronze Finish  
Medium Maple Blades  
with Tinted Opal Glass

### Features:

- 14° Blade Pitch
- 52" 3 Blades
- Flush Mount - Ideal for Low Ceilings  
Total Hanging Depth 10 3/4"
- Full Function Wall Control System
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use  
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,565	60.5	108.58

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more traditional indoor and outdoor settings.

Lifetime  
WARRANTY

WallControl  
FULL FUNCTION



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223



LISTED  
For Wet Location





**F594-PW**

Pewter Finish  
Dark Maple Blades  
with Opal Glass



**F594-WH**

White Finish  
White Blades  
with Opal Glass

# Traditional Concept™ 44"



## F593-PW

Pewter Finish  
Dark Maple Blades  
with Opal Glass

### Features:

- 14° Blade Pitch
- 44" 3 Blades
- Flush Mount - Ideal for Low Ceilings  
Total Hanging Depth 10¾"
- Full Function Wall Control System
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use  
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,940	49	100

Lifetime  
WARRANTY

WallControl  
FULL FUNCTION



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

UL  
LISTED  
For Wet Location



A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more traditional indoor and outdoor settings.





**F593-ORB**

Oil Rubbed Bronze Finish  
Medium Maple Blades  
with Tinted Opal Glass



**F593-WH**

White Finish  
White Blades  
with Opal Glass

Shown with Cap for Non-Light Use



**F510-BS**

- Brushed Steel Finish  
Silver Blades  
with Etched Opal Glass



**F510-WH**

- White Finish  
White Blades  
with Etched Opal Glass

# Spacesaver



## F510-ORB

Oil Rubbed Bronze Finish  
Oil Rubbed Bronze Blades  
with Tinted Opal Glass

Contemporary styling and superb air circulation for those smaller spaces in your home; perfect for kitchens and food preparation areas, bathrooms, walk-in closets and hallways.

## Features:

- 14° Blade Pitch
- 26" 3 Blades
- Flush Mount - Ideal for Low Ceilings  
Total Hanging Depth 10 $\frac{3}{4}$ "
- 4-Speed Fan  
Full Range Dimmer  
3-Wire Installation Wall Control  
Converts to Electronic Control
- Integrated Halogen Light  
Uses 1-50W Mini-Can Halogen Bulb (Included)

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
2,132	30	71.07



## WC110-WH

Wall Control System Included  
For Details See Page(s): 223

Lifetime  
WARRANTY

WallControl



**F513-BN**

Brushed Nickel Finish  
Dark Walnut Blades

**Features:**

- 14° Blade Pitch
- 52" 4 Blades
- 3½" and 6" Downrods
- Full Function Hand Held Remote Control System
- ENERGY STAR® Light Kits Available (Part #K9380-1 and #K9380-2 Page(s): 229)

**Energy Information (Excludes Lights)**

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,230	73	85.25



**F513-ORB**

Oil Rubbed Bronze Finish  
Medium Maple Blades

**Lifetime**  
WARRANTY

**Remote**  
CONTROL  
FULL FUNCTION



**RCS212**

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222



# New Era

Traditional in styling, yet defined by simple, soft lines.



**F513-WH**

White Finish  
White Blades



**F513-KA**

Kocoo Finish  
Reversible Toned Medium Maple / Dark Maple Blades  
(Shown with Toned Medium Maple Blades)



**F701-PW**

Pewter Finish  
Natural Walnut Blades  
with Etched Marble Glass

**Features:**

- 14° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- Wall Control System  
Independent Up/Downlight
- Integrated Uplight  
Use 6-15W Candelabra Bulbs  
(Included)
- Integrated Halogen Downlight  
Uses 2-50W Mini-Can Halogen  
Bulbs (Included)

U.S. Patent(s): D453,218; D457,235; D458,363

**Energy Information (Excludes Lights)**

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,278	72	73.31



**F701-DRB**

Dark Restoration Bronze™ Finish  
Dark Walnut Blades  
with Rustic Scavo Glass



**WCS213**

Wall Control System Control Included  
For Details See Page(s): 223



# Delano®

## F701-PN

Polished Nickel Finish  
Silver Blades  
with White Frosted Glass

## F701-KA

Kocoo Finish  
Reversible Toned Medium Maple / Dark Walnut Blades  
with Rustic Scavo Glass  
(Shown with Toned Medium Maple Blades)

## F701-DRF

Driftwood Finish  
Driftwood Blades  
with Bone White Glass

# Delano® II



## F711-DRB

Dark Restoration Bronze™ Finish  
Dark Walnut Blades  
with Rustic Scavo Glass

### Features:

- 14° Blade Pitch
- 52" 5 Blades
- Flush Mount - Ideal for Low Ceilings  
Less than 11" Drop from Ceiling
- Full Function Wall Control System
- Integrated Halogen Light  
Uses 2-50W Mini-Can Halogen Bulbs (Included)

U.S. Patent(s): D595,403; D597,655

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,367	69.5	77



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

Inspired by a long-time favorite, the Delano® II offers the same clean, neo-transitional look but with less than an 11-inch drop from the ceiling.

**Lifetime**  
WARRANTY

**WallControl**  
FULL FUNCTION



**F711-PN**

Polished Nickel Finish  
Silver Blades  
with White Frosted Glass



**F711-PW**

Pewter Finish  
Natural Walnut Blades  
with Etched Marble Glass

# Acero™

Winner of the 1999 Chicago Athenaeum: Museum of Architecture and Design's Good Design Award



## F601-BS/MG

Brushed Steel / Mahogany Finish  
Mahogany Blades  
with Opal Frosted Glass

## Features:

- 14° Blade Pitch
- 52" 3 Blades (Concave Style)
- 3½" and 6" Downrods
- Unique Wire Form Design
- Full Function Wall Control System
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D461,553; 6,354,801; 6,517,316

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,465	69	93.69



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223



## F601-BS/BN

Brushed Steel / Brushed Nickel Finish  
Silver Blades  
with Opal Frosted Glass

Shown with Cap for Non-Light Use

Lifetime  
WARRANTY

WallControl  
FULL FUNCTION



**F601-PN**

- Polished Nickel Finish
- Silver Blades
- with Opal Frosted Glass

An evolution of form and function merging today's technology with retro styling, this fan comes with an integrated light.



**F601-ORB**

- Oil Rubbed Bronze Finish
- Aaron Mahogany Blades
- with Opal Frosted Glass



# Portable Series

A special series of fans that go where you go. These portable fans offer the same style, quality and value you expect from Minka-Aire® in a compact and portable design.

## Retro Style Fan

An accent that is reminiscent of times past, our Retro Style Fan is your quiet companion; a stylistic, subtle, tabletop solution for your comfort needs in any room.



**F300-ORB**

Oil Rubbed Bronze Finish  
Oil Rubbed Bronze Blades



**F300-BN**

Brushed Nickel Finish  
Brushed Nickel Blades

### Features:

- 10" 4 Blade Turbofan
- 3 Speeds: 1,250, 1,400 and 1,500 R.P.M.
- Oscillates 70° Side to Side
- Manual Tilt
- Portable (Net Weight 7lbs.)
- 72" Heavy Duty Cord Length
- Steel Construction
- One Year Limited Warranty



# Hassock Aire

Our 1950s-inspired replica of a classic portable floor fan, Hassock Aire has been created with a wink to the past and a nod to the future; it is a nostalgic reminder of simpler times where multi-tasking items were a must. Hassock Aire has three speeds and is designed to gently circulate air in any room, even bringing fresh air in from an open window. Ideal for use in areas of the home where indirect air flow is preferred, such as nursery, home office or bedroom. As a plus, Hassock Aire can be used as an ottoman, providing extra seating or a place to rest your feet.

## F315-KA

Kocoa Finish  
Black Fins



## F315-SL

Silver Finish  
Black Fins

### Features:

- 12" 3 Blade Turbofan
- 3 Speeds
- Portable (Net Weight 16.31lbs.)
- 112" Cord
- 14" Overall Height
- Supports up to 400lbs.
- UL Listed
- Two Year Limited Warranty



**F672-WH/BN**

White / Brushed Nickel Finish  
White Blades  
with Acid Etched Glass

Shown with Cap for Non-Light Use

**Features:**

- 14° Blade Pitch
- 60" 5 Blades
- 3½" and 6" Downrods
- Integrated Halogen Light  
Uses 1-50W GU10 Halogen Bulb  
(Included)
- Hand Held Remote Control
- Cap for Non-Light Use (Included)

U.S. Patent(s): Pending

**\* Energy Information (Excludes Lights)**

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,894	75	80

**Lifetime**  
WARRANTY

**Remote**  
CONTROL



**RCS212**

Hand Held Remote Control Included  
For Details See Page(s): 222



**F672-ORB**

Oil Rubbed Bronze  
Reversible Medium Maple / Dark Maple Blades  
with Acid Etched Glass  
(Shown with Medium Maple Blades)

Shown with Cap for Non-Light Use

# Iconic™



**F672-ORB/AB**

Oil Rubbed Bronze / Antique Brass Finish  
Reversible Medium Maple / Dark Maple Blades  
with Acid Etched Glass  
(Shown with Dark Maple Blades)

Shown with Cap for Non-Light Use

Classic lines combined with advanced technology provide our traditional customers with a work horse that transcends time and will perform for many years to come. Die cast blade irons and face plate give a three-dimensional effect.



**F672-MBK/BN**

Matte Black / Brushed Nickel Finish  
Reversible Medium Maple / Dark Maple Blades  
with Acid Etched Glass  
(Shown with Dark Maple Blades)

Shown with Cap for Non-Light Use

# Great Room Traditional



## F539-BCW

Belcaro Walnut™ Finish  
Dark Walnut Blades

### Features:

- 14° Blade Pitch
- 72" 5 Blades
- 3½" and 6" Downrods
- Full Function Wall Control System
- Universal Light Kit Adaptable  
(Sold Separately. See K9376-1 and K9376-2 on page(s): 230)
- Quick Connect Switch Cup

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
9,071	106	85.36



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

Great Room interiors require new ways to manage air. We have accomplished this with expanded blade spans, larger motors and enhanced housings in styles designed to complement those rooms.

Lifetime  
WARRANTY

WallControl  
FULL FUNCTION



**F539-ORB**

Oil Rubbed Bronze Finish  
Dark Walnut Blades



**F539-BN**

Brushed Nickel Finish  
Dark Walnut Blades



# Santa Lucia™

minkaAire®  
A Minka Group® Co.



**F820-CT**  
Cattera Bronze™ Finish  
Dark Walnut Blades  
with Cognac Fluted Etched Glass



## Features:

- 14° Blade Pitch
- 60" 5 Blades
- 3½" and 6" Downrods
- Full Function Wall Control System with Independent Up/Downlight Control
- Integrated Uplight  
Uses 5-15W Candelabra Bulbs (Included)
- Integrated Halogen Downlight  
Uses 2-50W Mini-Can Halogen Bulbs (Included)

U.S. Patent(s): D556,882; D559,436; D568,984; D570,986; D574,948; D599,000; D599,466; 5,554,006  
© 2006 Minka Lighting, Inc.

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,534	100	65.34



**F820-IBR**  
Illuminati Bronze™ Finish  
Dark Walnut Blades  
with Silver Patina Glass



**CM8222-IBR 22"**  
Illuminati Bronze™ Finish  
22" Diameter  
Matching Ceiling Medallion for F820-IBR  
© 2005 Minka Lighting, Inc.



**WCS212**  
Full Function Wall Control System Included  
For Details See Page(s): 223

Lifetime  
WARRANTY

WallControl  
FULL FUNCTION





**F812-10**

Iron Oxide Finish  
Dark Walnut Blades  
with Venetian Scavo Glass

**Features:**

- 14° Blade Pitch
- 54" 5 Blades
- 3½" and 6" Downrods
- Full Function Wall Control System  
Independent Up/Downlight
- Integrated Uplight and Downlight  
Uses 6-15W and 2-60W  
Candelabra Bulbs (Included)
- Complements Lighting Available  
Through Minka-Lavery®

U.S. Patent(s): D528,652; D531,298; D532,098;  
D533,292; D535,012; D563,540

**Energy Information (Excludes Lights)**

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
<b>6,534</b>	<b>100</b>	<b>65.34</b>



**WCS212**

Full Function Wall Control System Included  
For Details See Page(s): 223

Simple, clean, architectural lines  
have been utilized to define  
the Lineage™.



# Salon Grand™



**F707-FLP**

Florence Patina™ Finish  
Dark Walnut Blades  
with Salon Scavo™ Glass

Inspired by Jessica McClintock's designs, the Salon Grand™ ceiling fan's exquisite styling, elegance and beauty exemplify her passion and love for romance.



JESSICA MCCLINTOCK HOME  
*The Romance Collection®*  
by  
minkaAire  
A Minka Group® Co.

**Features:**

- 14° Blade Pitch
- 56" 5 Blades
- 3½" and 10" Downrods
- Full Function Wall Control System
- Integrated Halogen Light  
Uses 2-50W Mini-Can Halogen  
Bulbs (Included)
- Complements Lighting Available  
Through Minka-Lavery®



U.S. Patent(s): D531,345; D532,152  
© 2005 Minka Lighting, Inc.

**Energy Information (Excludes Lights)**

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,825	97	70.16



**WCS212**

Full Function Wall Control System Included  
For Details See Page(s): 223



**CM1550-FLP 22"**

Florence Patina™ Finish  
22" Diameter  
Matching Ceiling Medallion for F707-FLP  
© 2005 Minka Lighting, Inc.





**F900-BCW**

Belcaro Walnut™ Finish  
Dark Walnut Blades

Shown with Optional **GC900 SET**  
MADE WITH SPECTRA® CRYSTAL



**F900-BCW**

Belcaro Walnut™ Finish  
Dark Walnut Blades

**Features:**

- 14° Blade Pitch
- 68" 5 Blades
- 3½" and 16" Downrods
- Full Function Wall Control System with Independent Up/Downlight Control Feature
- Precision Machine Cut and Polished Lead-Free SPECTRA® CRYSTAL
- Integrated Uplight  
Uses 5-15W Candelabra Bulbs (Included)
- Integrated Halogen Downlight  
Uses 2-50W Mini-Can Halogen Bulbs (Included)

© 2005 Minka Lighting, Inc.

**Energy Information** (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,022	95	63.39



**WCS212**

Full Function Wall Control System Included  
For Details See Page(s): 223



# Napoli™

minkaAire®  
A Minka Group® Co.



## F705-TSP

Tuscan Patina™ Finish  
Tuscan Patina™ Shaded Blades  
with Aged Champagne Glass



## F705-STW

Sterling Walnut™ Finish  
Sterling Walnut™ Shaded Blades  
with Aged Champagne Glass

## Features:

- 14° Blade Pitch
- 56" 5 Blades
- 3½" and 12" Downrods
- Full Function Wall Control System
- Integrated Halogen Light  
Uses 2-50W Mini-Can Halogen  
Bulbs (Included)

U.S. Patent(s): D513,532; D514,685; D514,690;  
D516,702; D521,627; D522,122

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,765	93	72



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223



## CM7022-STW 22"

Sterling Walnut™ Finish  
Matching Ceiling Medallion for F705/F715  
© 2005 Minka Lighting, Inc.

Also Available:

## CM7022-TSP 22"

Tuscan Patina™ Finish

Lifetime  
WARRANTY

WallControl  
FULL FUNCTION





**F715-STW**

Sterling Walnut™ Finish  
Sterling Walnut™ Shaded Blades  
with Aged Champagne Glass



**F715-TSP**

Tuscan Patina™ Finish  
Tuscan Patina™ Shaded Blades  
with Aged Champagne Glass



**CM7038-TSP 38"**

Tuscan Patina™ Finish  
Matching Ceiling Medallion for F705/F715  
© 2005 Minka Lighting, Inc.

Also Available:

**CM7038-STW 38"**

Sterling Walnut™ Finish



**WCS212**

Full Function Wall Control System Included  
For Details See Page(s): 223

**Features:**

- 14° Blade Pitch
- 68" 5 Blades
- 3½" and 12" Downrods
- Full Function Wall Control System
- Integrated Halogen Light  
Uses 2-50W Mini-Can Halogen  
Bulbs (Included)

U.S. Patent(s): D513,532; D514,685; D514,690;  
D516,702; D521,627; D522,122

**Energy Information (Excludes Lights)**

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
<b>7,581</b>	<b>104</b>	<b>72.84</b>

**Lifetime**  
WARRANTY

**WallControl**  
FULL FUNCTION

Volterra™ is a neo-classical inspiration,  
incorporating an uplight with an integrated  
halogen downlight.



**F702-VB**

Volterra Bronze™ Finish  
Natural Walnut Blades  
with French Scavo Glass



# Volterra™



## F702-BCW

Belcaro Walnut™ Finish  
Natural Walnut Blades  
with Aged Champagne Glass



## Features:

- 14° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- Wall Control System  
Independent Up/Downlight
- Integrated Uplight  
Uses 6-15W Candelabra Bulbs  
(Included)
- Integrated Halogen Downlight  
Uses 2-50W Mini-Can Halogen  
Bulbs (Included)

© 2002 Minka Lighting, Inc.

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,425	67	80.97



## WCS213

Wall Control System Included  
For Details See Page(s): 223

**Lifetime**  
WARRANTY

WallControl

# Calais™

minkaAire®  
A Minka Group® Co.



## F544-BCW

Belcaro Walnut™ Finish  
Dark Walnut Blades  
with Aged Champagne Glass

Elegance, style and performance for low ceiling applications, this fan has less than an 11-inch drop from ceiling to cap.

### Features:

- 14° Blade Pitch
- 52" 5 Blades
- Flush Mount - Ideal for Low Ceilings  
Less than 11" Drop from Ceiling
- Hand Held Remote Control System
- Integrated Light  
Uses 2-60W Candelabra Bulbs (Included)

U.S. Patent(s): D526,714; D527,094; D530,415; D532,896; D536,777

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,050	80	75.63



## F544-GBZ

Golden Bronze Finish  
Dark Walnut Blades  
with Excavation Glass



## RCS213

Hand Held Remote Control Included  
For Details See Page(s): 222

**Lifetime** WARRANTY  
**Remote** CONTROL

# Traditional Gyro™



A magnificent rendition of the original Gyro™ design, the traditional finish transcends the turns of time.

Gyro Fans Rotate 360°

## F502-PBL

Provençal Blanc Finish  
Provençal Blanc Blades  
Pearl White Glass

### Features:

- High Performance Twin Turbofans Total Sweep 42"
- 20° Blade Pitch
- 4½" and 12" Downrods
- 1,000 - 1,500 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360° at 3 R.P.M.
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Axis Rotation
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)



Gyro Fans Rotate 360°

## F502-BCW

Belcaro Walnut™ Finish  
Belcaro Walnut™ Blades  
with Belcaro Walnut™ Glass



### WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,050	102	49.51

U.S. Patent(s): D523,548; D523,549; D523,550; D523,983; D524,438; D526,059; D526,400; D526,712; D530,810; D532,097; D567,350; 6,832,902; 7,183,680; 7,229,255  
© 2004 Minka Lighting, Inc.

Lifetime WARRANTY

WallControl FULL FUNCTION



Gyro Fans Rotate 360°

**F802-KA**

Kocoa Finish  
Kocoa Blades  
with Tinted Opal Glass

An addition to our popular Gyro™ family, the Vintage Gyro™ performs with the same efficiency and unsurpassed level of comfort as our other Gyro™ models, but with an early 20<sup>th</sup> Century style.



# Vintage Gyro™



## F802-ORB

Oil Rubbed Bronze Finish  
Oil Rubbed Bronze Blades  
with Tinted Opal Glass

Gyro Fans Rotate 360°



## F802-BN/CH

Brushed Nickel / Chrome Finish  
Rosewood Blades  
with Etched Opal Glass

Gyro Fans Rotate 360°



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

## Features:

- High Performance Twin Turbofans  
Total Sweep 42"
- 20° Blade Pitch
- 3½" and 6" Downrods
- 1,000 - 1,500 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360°  
at 3 R.P.M.
- Full Function Wall Control System  
Incorporating Fully Independent  
Fan Head Speeds and Axis  
Rotation
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen  
Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): 6,832,902; 7,183,680; 7,229,255

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,050	102	49.51

Lifetime  
WARRANTY

WallControl  
FULL FUNCTION



## F602-RRB

Restoration Bronze™ Finish  
Restoration Bronze™ Blades  
with Etched Opal School House Globe Glass

Gyro Fans Rotate 360°

## Features:

- High Performance Twin Turbofans  
Total Sweep 42"
- 3½" and 6" Downrods
- 1,000 - 1,500 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360°  
at 3 R.P.M.
- Full Function Wall Control System  
Incorporating Fully Independent  
Fan Head Speeds and Axis  
Rotation
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen  
Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D478,975; D489,443, D489,809;  
D490,146; 6,832,902; 7,183,680; 7,229,255

## Energy Information (Excludes Lights)


Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,050	102	49.51



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

A truly unique design offering an unsurpassed level of comfort. The Gyro™ fan's ability to precisely control the direction and intensity of the cooling breeze efficiently circulates air in any environment.



Gyro Fans Rotate 360°

## F602-BN/CH

Brushed Nickel / Chrome Finish  
with Chrome Accents and Cages  
Rosewood Blades  
with Etched Opal Glass



# Gyro™ Wet



## F402-ORB

Oil Rubbed Bronze Finish  
Oil Rubbed Bronze Blades  
with Etched Opal School House Globe Glass

Gyro Fans Rotate 360°

Capturing the design elements of the original Gyro™, the Gyro™ Wet provides unsurpassed performance and comfort levels in the toughest environments. Rotating 360°, and controlled by a wall control system, it offers wonderful cooling in any area and the option to stop and redirect air for maximum benefit.

## Features:

- High Performance Twin Turbofans Total Sweep 42"
- 1,000 - 1,500 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360° at 3 R.P.M.
- Galvanized Steel 3½" and 6" Downrods
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Lighting Fixture
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): D478,975; D489,443; D489,809; D490,146; 6,832,902; 7,183,680; 7,229,255

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,050	102	49.51



## F402-BNW

Brushed Nickel Wet Finish  
Silver Blades  
with Etched Opal Glass

Shown with Cap for Non-Light Use

Gyro Fans Rotate 360°



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

Lifetime  
WARRANTY

WallControl  
FULL FUNCTION



For Wet Location

# Gyrette™



## F302-RRB

Restoration Bronze™ Finish  
Restoration Bronze™ Blades

The Gyrette™ captures the design elements of the original Gyro™ in a smaller format. We have utilized flexible arms to maximize air circulation.

### Features:

- High Performance Twin Turbofans  
Total Sweep 36"
- Adjustable Turbofan Heads
- 14° Blade Pitch
- Complete Assembly Rotates 360°  
at 3 R.P.M.
- 3-Speeds: 880, 1,120, 1,350  
R.P.M.
- 30° Flexible Arms
- 4½" Downrod
- Full Function Hand Held Remote  
Control System

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
2,418	53	45.62



## F302-BN

Brushed Nickel Finish  
Brushed Nickel Blades



## RCS212

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222



# Indoor/Outdoor Collection



**M**inka-Aire® recognizes a need in today's al fresco lifestyle by offering an Outdoor Series of ceiling fans. All are UL or ETL Listed for wet location usage, making these fans perfect for patios, porches, and other exposed areas. Motor housings and blades are fully protected against water and all weather conditions. Particular models have a combined waterproof light kit to provide additional lighting outdoors. These fans feature various designer finishes to complement your patio furniture.

Now you are able to enjoy a wonderful breeze on your patio, in your gazebo or over your outdoor spa! Of course, you may use all of these models indoors as well.

# Concept™ I Wet 58"

STAINLESS STEEL



#### F477-ORB

Oil Rubbed Bronze Finish  
Oil Rubbed Bronze Blades  
with Pietra Glass

#### Features:

- 14° Blade Pitch
- 58" 3 Blades
- **Marine Grade Stainless Steel Construction**
- Stainless Steel  
3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen  
Bulb (Included)
- Indoor/Outdoor Use  
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

U.S. Patent(s): D475,782; D476,408; D478,654;  
D478,980; 7,008,192

#### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,400	64	115



#### F477-WH

White Finish  
White Blades  
with White Opal Glass

Shown with Cap for Non-Light Use

**Lifetime**  
WARRANTY

**WallControl**  
FULL FUNCTION



#### WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223



**LISTED**

For Wet Location





## STAINLESS STEEL

### **F477-BNW**

Brushed Nickel Wet Finish  
Silver Blades  
with White Opal Glass

Shown with Cap for Non-Light Use

## STAINLESS STEEL

UL listed for use indoors and outdoors, furthering the versatility and timeless perfection that is the Concept™ I series. Concept™ I Wet is constructed of marine grade stainless steel to ensure long lasting appearance and function in the toughest environments.

## STAINLESS STEEL

# Concept™ I Wet 52"



## F577-BNW

Brushed Nickel Wet Finish  
Silver Blades  
with White Opal Glass

### Features:

- 14° Blade Pitch
- 52" 3 Blades
- Galvanized Steel  
3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen  
Bulb (Included)
- Indoor/Outdoor Use  
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

U.S. Patent(s): D475,782; D476,408; D478,654;  
D478,980; 7,008,192

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,991	51.2	117.01

The Concept™ I ceiling fan collection is the most successful series in the history of Minka-Aire®. It is only natural that we would produce a new version that is UL listed for use indoors and outdoors, furthering the versatility and timeless perfection that is the Concept™ I series.

**Lifetime**  
WARRANTY

**WallControl**  
FULL FUNCTION

**UL**  
LISTED  
For Wet Location



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223





**F476-ORB**

Oil Rubbed Bronze Finish  
Taupe Blades  
with Pietra Glass



**F476-WH**

White Finish  
White Blades  
with White Opal Glass

Shown with Cap for Non-Light Use

# Sunseeker

## F532-BWH

Bone White Finish  
Bone White Blades

### Features:

- 14° Blade Pitch
- 60" 5 Blades
- Galvanized Steel  
3½" and 6" Downrods
- Stainless Steel Hardware and  
All Weather Blades
- 3-Speed Pull Chain
- Indoor/Outdoor Use  
UL Listed for Wet Locations
- UL Wet Location Light Kits  
Available  
(Sold Separately. Page(s): 231)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,783	65	104.19

Lifetime  
WARRANTY

  
**LISTED**  
For Wet Location



The Sunseeker features a 60-inch blade span, stylish transitional design and superb value. These elements make it an ideal choice for enjoying hot summer days outdoors.



**F532-BNW**

Brushed Nickel Wet Finish  
Silver Blades



**F532-DRF**

Driftwood Finish  
Driftwood Blades



**F532-ORB**

Oil Rubbed Bronze Finish  
Oil Rubbed Bronze Blades




**F840-CF**

Craftsman™ Finish  
Craftsman™ Blades  
with Craftsman™ Glass

**Features:**

- 14° Blade Pitch
- 52" 5 Blades
- Galvanized Steel  
3½" and 6" Downrods
- Stainless Steel Hardware and  
All Weather Blades
- Full Function Wall Control System
- Light Kit with Enclosed Glass  
Shades  
Uses 3-60W Candelabra Bulbs  
(Included)
- Indoor/Outdoor Use  
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)



**F840-CF**

Shown with Cap for  
Non-Light Use

U.S. Patent(s): D579,097; D579,098; D579,103;  
D581,512; D583,044

**Energy Information (Excludes Lights)**

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,374	77.7	69.16



**WCS212**

Full Function Wall Control System Included  
For Details See Page(s): 223

Inspired by the Craftsman architecture of the early 1900s, this fan best defines the spirit of the era. It can be used in both interior and exterior applications.

**Lifetime**  
WARRANTY

**WallControl**  
FULL FUNCTION



LISTED  
For Wet Location





**F580-VR/BB**

Vintage Rust™ Finish  
Bamboo All Weather Blades  
Shown with Cap for Non-Light Use

Our wicker design, coupled with a Vintage Rust™ finish, replicates a highly popular tropical motif.

**Features:**

- 14° Blade Pitch
- 52" 5 Blades
- Galvanized Steel  
3½" and 6" Downrods
- Stainless Steel Hardware and All Weather Blades
- 3-Speed Pull Chain
- Snap Lock/Set Screw Blade Assembly System
- Integrated Halogen Caged Etched Glass Light  
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use  
UL Listed for Wet Location
- Cap for Non-Light Use (Included)

U.S. Patent(s): D501,251; D501,922; D501,923; D502,770; D508,287; D514,215; D522,643; 7,008,192

**Energy Information** (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,375	79	68.03



**F580-VR/BB**

Vintage Rust™ Finish  
Bamboo All Weather Blades  
with Caged Etched Glass

Lifetime  
WARRANTY



For Wet Location







**F582-ORB**

Oil Rubbed Bronze Finish  
Taupe Blades  
with Vintage Amber Glass



**F582-BNW**

Brushed Nickel Wet Finish  
Silver Blades  
with Acid Etched Glass



# Rainman™



## F582-GL

Galvanized Finish  
Silver Blades  
with Acid Etched Glass

Reminiscent of lighting often found along shoreline walkways, the Rainman™, as the name suggests, is an excellent choice for exterior as well as interior use.

## Features:

- 14° Blade Pitch
- 54" 5 Blades
- Galvanized Steel  
3½" and 6" Downrods
- Stainless Steel Hardware and All Weather Blades
- Wall Control System
- Integrated Halogen Caged Light  
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use  
UL Listed for Wet Locations

U.S. Patent(s): D460,549

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,508	58	94.96



## WCS213

Wall Control System Included  
For Details See Page(s): 223

Lifetime  
WARRANTY

WallControl




LISTED  
For Wet Location

# Slipstream XXL



**S**lipstream XXL is the second generation of our uniquely designed 8 blade, 65-inch fan. Slipstream XXL has grown to 84 inches, making this a power house of air flow and a form with enough presence to be used in both residential and commercial environments. In addition, it has a UL listing for both indoor and outdoor spaces.



**F889-BNW**

Brushed Nickel Wet Finish  
Silver Blades  
with Etched Opal Glass



**RC400**

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222

**Features:**

- 14° Blade Pitch
- 84" 8 Concave Blades
- DC 165 x 25mm Motor
- Galvanized Steel 3½" and 6" Downrods
- Stainless Steel Hardware and All Weather Blades
- Special Hand Held Remote Control System Included - RC400
- Integrated Light Uses 1-26W Non-Dimmable GU24 CFL (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use  
UL Listed for Wet Locations

**Energy Information (Excludes Lights)**

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
11,022	26.8	411.27


U.S. Patent(s): D715,917



# Slipstream XXL



Slipstream XXL is the second generation of our uniquely designed 8 blade, 65-inch fan. Slipstream XXL has grown to 84 inches, making this a power house of air flow and a form with enough presence to be used in both residential and commercial environments. In addition, it has a UL listing for both indoor and outdoor spaces.



**F889-SI**

Smoked Iron Finish  
Smoked Iron Blades  
with Etched Opal Glass



**RC400**

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222

**Features:**

- 14° Blade Pitch
- 84" 8 Concave Blades
- DC 165 x 25mm Motor
- Galvanized Steel  
3½" and 6" Downrods
- Stainless Steel Hardware and  
All Weather Blades
- Special Hand Held Remote Control  
System Included - RC400
- Integrated Light  
Uses 1-26W Non-Dimmable GU24  
CFL (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use  
UL Listed for Wet Locations

**Energy Information (Excludes Lights)**

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
11,022	26.8	411.27




# Slipstream XXL



Slipstream XXL is the second generation of our uniquely designed 8 blade, 65-inch fan. Slipstream XXL has grown to 84 inches, making this a power house of air flow and a form with enough presence to be used in both residential and commercial environments. In addition, it has a UL listing for both indoor and outdoor spaces.





**F889-ORB**

Oil Rubbed Bronze Finish  
Oil Rubbed Bronze Blades  
with Tinted Opal Glass

Shown with Cap for Non-Light Use

**Features:**

- 14° Blade Pitch
- 84" 8 Concave Blades
- DC 165 x 25mm Motor
- Galvanized Steel  
3½" and 6" Downrods
- Stainless Steel Hardware and  
All Weather Blades
- Special Hand Held Remote Control  
System Included - RC400
- Integrated Light  
Uses 1-26W Non-Dimmable GU24  
CFL (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use  
UL Listed for Wet Locations



**RC400**

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222

**Energy Information (Excludes Lights)**

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
11,022	26.8	411.27

U.S. Patent(s): D715,917



# Strata



## F734-ORB

Oil Rubbed Bronze Finish  
Oil Rubbed Bronze Blades  
with Tinted Opal Glass



## F734-ORB

Shown with Cap for  
Non-Light Use

### Features:

- 12° Blade Pitch
- 52" 4 Blades
- Galvanized Steel  
3½" and 6" Downrods  
(Uses ¾" I.D. DR5 Series Downrod)
- Hand Held Remote Control System
- Integrated Light  
Uses 1-75W Mini-Can Halogen  
Bulb (Included)
- Indoor/Outdoor Use  
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,098	47.6	107

**Lifetime**  
WARRANTY

**Remote**  
CONTROL

**UL**  
LISTED  
For Wet Location



## RCS213

Hand Held Remote Control Included  
For Details See Page(s): 222

The Strata with its Smoked Iron or Galvanized finishes adds a rustic yet contemporary style to your home.



**F734-GL**

Galvanized Finish  
Silver Blades  
with Etched Opal Glass



**F734-GL**

Shown with Cap for  
Non-Light Use



**F734-SI**

Smoked Iron Finish  
Smoked Iron Blades  
with Etched Opal Glass



**F579-L-BNW**

- Brushed Nickel Wet Finish  
Silver Blades  
with Frosted Seeded Glass



**F579-L-BNW**

- Shown with Cap for  
Non-Light Use

# Magellan®

## F579-L-ORB

Oil Rubbed Bronze Finish  
Parchment Blades  
with Vintage Amber Seeded Glass

## Features:

- 16° Blade Pitch
- 60" 5 Sail Blades
- Galvanized Steel  
3½" and 6" Downrods
- Stainless Steel Hardware and  
All Weather Blades
- Wall Control System
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen  
Bulb (Included)
- Indoor/Outdoor Use  
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

U.S. Patent(s): D446,296; D449,372; D449,682;  
D449,683; D450,832

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,343	65	82.20

## F579-L-ORB

Shown with Cap for  
Non-Light Use



## WCS213

Wall Control System Included  
For Details See Page(s): 223

Lifetime  
WARRANTY

WallControl



For Wet Location

www.minkaaire.com

141

# Aluma Wet



## F523-ABD

Brushed Aluminum Finish  
Silver Blades  
with Etched Opal Glass

Shown with Cap for Non-Light Use

### Features:

- 12° Blade Pitch
- 52" 4 Blades
- 3½" and 6" Downrods
- All Aluminum Construction
- Hand Held Remote Control System
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen  
Bulb (Included)
- Cap for Non-Light Use (Included)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,988	52	96



## F523-ORB

Oil Rubbed Bronze Finish  
Oil Rubbed Bronze Blades  
with Tinted Opal Glass



## RCS213

Hand Held Remote Control Included  
For Details See Page(s): 222

Lifetime  
WARRANTY

Remote  
CONTROL



LISTED

For Wet Location







**F523-WHF**

Flat White Finish  
Flat White Blades  
with Etched Opal Glass

**A**luma Wet is our answer to the fan that goes anywhere and has everything. For use indoors and outdoors, Aluma Wet is UL listed for use in wet locations. Produced from weather resistant materials, the Aluma Wet provides air circulation for every location including patio, porch and pergola.

# Java



## F753-KA

Kocoa Finish  
Kocoa Blades

### Features:

- 14° Blade Pitch
- 54" 3 Blades
- 3½" and 6" Downrods
- Hand Held Remote Control System
- Indoor/Outdoor Use  
UL Listed for Wet Locations

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,681	60	94

Minka-Aire's "everywhere" fan with a unique contemporary twist that is suitable for all environments.

Lifetime  
WARRANTY

Remote  
CONTROL



LISTED  
For Wet Location



## RCS213

Hand Held Remote Control Included  
For Details See Page(s): 222



□ **F753-WHF**

Flat White Finish  
Flat White Blades



□ **F753-BNW**

Brushed Nickel Wet Finish  
Silver Blades



**F474-ORB**

Oil Rubbed Bronze Finish  
Taupe Blades  
with Pietra Glass



**F474-WH**

White Finish  
White Blades  
with White Opal Glass  
Shown with Cap for Non-Light Use

# Concept™ II Wet



## F574-BNW

Brushed Nickel Wet Finish  
Silver Blades  
with White Opal Glass

As the name implies, the Concept™ II Wet ceiling fan is “a taste of things to come.” Simple in style, yet ingenious by design and UL Listed for wet locations.

## Features:

- 14° Blade Pitch
- 52" 3 Concave Blades
- Flush Mount - Ideal for Low Ceilings  
Total Hanging Depth 12"
- Full Function Wall Control System
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use  
UL Listed for Wet Locations  
(Will Not Pendulum In Windy Conditions)



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,053	51.3	117.99

U.S. Patent(s): D478,654; D478,974; D478,980;  
7,008,192



**UL**  
**LISTED**  
For Wet Location

**Lifetime**  
WARRANTY

**WallControl**  
FULL FUNCTION

# Traditional Concept™ 52"



## F594-ORB

Oil Rubbed Bronze Finish  
Medium Maple Blades  
with Tinted Opal Glass

### Features:

- 14° Blade Pitch
- 52" 3 Blades
- Flush Mount - Ideal for Low Ceilings  
Total Hanging Depth 10 3/4"
- Full Function Wall Control System
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use  
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,565	61	108.52

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more traditional indoor and outdoor settings.

**Lifetime**  
WARRANTY

**WallControl**  
FULL FUNCTION



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223



**LISTED**

For Wet Location







**F594-PW**

Pewter Finish  
Dark Maple Blades  
with Opal Glass



**F594-WH**

White Finish  
White Blades  
with Opal Glass

# Traditional Concept™ 44"



## Features:

- 14° Blade Pitch
- 44" 3 Blades
- Flush Mount - Ideal for Low Ceilings  
Total Hanging Depth 10 3/4"
- Full Function Wall Control System
- Integrated Halogen Light  
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use  
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,940	49	100

## F593-PW

Pewter Finish  
Dark Maple Blades  
with Opal Glass

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more traditional indoor and outdoor settings.



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

Lifetime  
WARRANTY

WallControl  
FULL FUNCTION



LISTED  
For Wet Location





**F593-ORB**

Oil Rubbed Bronze Finish  
Medium Maple Blades  
with Tinted Opal Glass



**F593-WH**

White Finish  
White Blades  
with Opal Glass

Shown with Cap for Non-Light Use

# Terrana



## Features:

- 16° Blade Pitch
- 52" 2 or 3 Blades (Included)
- 2 Sets of Blade Irons (For Each Configuration)
- Galvanized Steel 3½" and 6" Downrods
- Full Function Hand Held Remote Control System
- Integrated Light Uses 1-75W Mini Can Halogen Bulb (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

## F680-KA

Kocoa Finish  
Palm / Rattan Reversible Blades  
with Tinted Opal Glass



2-Blade Option Shown with Rattan Blades and Cap for Non-Light Use

## 2 Blade Energy Information

(Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,439	52	85.7

## 3 Blade Energy Information

(Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,155	52.5	79



2-Blade Option Shown with Palm Blades with Tinted Opal Glass



## RCS212

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222

Lifetime WARRANTY

Remote CONTROL FULL FUNCTION



LISTED For Wet Location





**F680-BG**


Bahama Beige™ Finish  
Palm / Rattan Reversible Blades  
with Tinted Opal Glass

With its 2 or 3-blade configurations and reversible blade styles, the Terrana evokes a sense of tropical breezes in any setting. Unique options and superb functionality are paramount in the Terrana.



Eight Different Configurations all in One Box. Includes Palm/Rattan Reversible Blades.

2-Blade Option Shown with Rattan Blades and Cap for Non-Light Use



3-Blade Option Shown with Palm Blades and Cap for Non-Light Use



# Gauguin™



## F581-BG

Bahama Beige™ Finish  
Bahama Beige™ Blade  
with Etched Glass

### Features:

- 14° Blade Pitch
- 52" 4 Blades
- Galvanized Steel  
3½" and 6" Downrods  
(Uses ¾" I.D. DR5 Series Downrod)
- Stainless Steel Hardware and  
All Weather Blades
- Full Function Wall Control System
- Integrated Halogen Light  
Uses 1-50W MR16 120V 2-Pin  
Halogen Bulb (Included)
- Indoor/Outdoor Use  
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

U.S. Patent(s): D513,319; D514,691; D514,692;  
D516,703; D517,201; D519,199

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,834	52	92.97

Tropical style influences the Gauguin™ by incorporating a remarkable combination of performance and unique design elements.

Lifetime  
WARRANTY

WallControl  
FULL FUNCTION



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

UL  
LISTED  
For Wet Location







**F581-WHF**

Flat White Finish  
Flat White Blades  
with Etched Glass



**F581-ORB**

Oil Rubbed Bronze Finish  
Bahama Beige™ Blades  
with Etched Glass

# Sundowner®

## F589-ORB

Oil Rubbed Bronze Finish  
Dark Maple Blades

### Features:

- 16° Blade Pitch
- 54" 5 Blades
- Galvanized Steel  
3½" and 6" Downrods
- Stainless Steel Hardware and  
All Weather Blades
- 3-Speed Pull Chain
- Poly Molded and ABS Components
- Indoor/Outdoor Use  
UL Listed for Wet Locations
- UL Wet Location Light Kits  
Available  
(Sold Separately. Page(s): 231)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,523	79	82

Lifetime  
WARRANTY



Accessory Blades Available. See Page(s): 236

Highly recommended for the most challenging environments, the Sundowner® combines superior performance with weatherproof components designed to withstand all outdoor conditions.

## F589-BWH

Bone White Finish  
Bone White Blades



**F589-SWH**

Shell White Finish  
Shell White Blades



**F589-DRF**

Driftwood Finish  
Driftwood Blades



**F589-MW**

Mossoro Walnut™ Finish  
Mossoro Walnut™ Blades

# Sundowner®



## F589-HT

Heritage™ Finish  
Black Blades

### Features:

- 16° Blade Pitch
- 54" 5 Blades
- Galvanized Steel  
3½" and 6" Downrods
- Stainless Steel Hardware and  
All Weather Blades
- 3-Speed Pull Chain
- Poly Molded and ABS Components
- Indoor/Outdoor Use  
UL Listed for Wet Locations
- UL Wet Location Light Kits  
Available  
(Sold Separately. Page(s): 231)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,523	79	82

Lifetime  
WARRANTY



Accessory Blades Available. See Page(s): 236



## F589-WH

White Finish  
White Blades



**F589-VRT**

Vintage Rust™ Finish  
Dark Maple Blades



**F589-BI/AI**

Black Iron with Aged Iron Accents Finish  
Black Iron Blades





□ **F571-DRF 52"**

Driftwood Finish  
Gray Blades



□ **F571-WH 52"**

White Finish  
White Blades



□ **F571-ORB 52"**

Oil Rubbed Bronze Finish  
Dark Oak Finish Blades



# Sundance™



**F572-WH 42"**

White Finish  
White Blades

Perfect for the porch, patio, gazebo or courtyard, the Sundance™ was designed to withstand all of the elements.

## Features:

- 12° Blade Pitch
- 52" or 42" 5 Blades
- Galvanized Steel  
3½" and 6" Downrods
- Stainless Steel Hardware and All Weather Blades
- 3-Speed Pull Chain
- Indoor/Outdoor Use  
UL Listed for Wet Locations
- UL Wet Location Light Kits Available  
(Sold Separately. Page(s): 231)

## F571 Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,596	63	88.4

## F572 Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
3,428	52	65.64



**F572-ORB 42"**

Oil Rubbed Bronze Finish  
Dark Oak Finish Blades

Lifetime  
WARRANTY



For Wet Location

# Gyro™ Wet



## F402-ORB

Oil Rubbed Bronze Finish  
Oil Rubbed Bronze Blades  
with Etched Opal School House Globe Glass

Gyro Fans Rotate 360°

Capturing the design elements of the original Gyro™, the Gyro™ Wet provides unsurpassed performance and comfort levels in the toughest environments. Rotating 360°, and controlled by a wall control system, it offers wonderful cooling in any area and the option to stop and redirect air for maximum benefit.

## Features:

- High Performance Twin Turbofans Total Sweep 42"
- 1,000 - 1,500 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360° at 3 R.P.M.
- Galvanized Steel 3½" and 6" Downrods
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Lighting Fixture
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

U.S. Patent(s): D478,975; D489,443; D489,809; D490,146; 6,832,902; 7,183,680; 7,229,255

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,050	102	49.51



## F402-BNW

Brushed Nickel Wet Finish  
Silver Blades  
with Etched Opal Glass

Shown with Cap for Non-Light Use

Gyro Fans Rotate 360°



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

Lifetime WARRANTY

WallControl FULL FUNCTION



LISTED For Wet Location



**F1000-BN**

□ Brushed Nickel Finish  
Reversible Medium Maple / Dark Walnut Finish Blades  
with Etched Lens  
(Shown with Dark Walnut Blades)

# Value Collection

With the Minka-Aire® Value Collection, one need not sacrifice style and performance for affordability.

Choose from several finishes and light kit options to find the right Minka-Aire® ceiling fan with timeless style and design for the budget-conscious customer.

# Dyno

with LED Light

LED

LED

## F1000-BN

Brushed Nickel Finish  
Reversible Medium Maple / Dark Walnut Finish Blades  
with Etched Lens  
(Shown with Dark Walnut Blades)

### Features:

- 12° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- Integrated Light  
Uses 17W Dimmable LED  
(Included) 3 Year Warranty
- 1100 Lumens
- 2700K
- CRI 80
- Hand Held Remote Control System
- Replacement LED Assembly  
(Part #6F1000LK01)

U.S. Patent(s): Pending

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,295	64	77



## RCS213

Hand Held Remote Control Included  
For Details See Page(s): 222

A new addition to our Value Collection, featuring performance and design features at an affordable price. For the first time in our Value offerings, we introduce a fan with an integrated LED\* light source. Generous in size, style, adaptability and function, Dyno becomes one of our core fan offerings.

LED







LED

LED

**F1000-ORB**

Oil Rubbed Bronze Finish  
Reversible Medium Maple / Dark Walnut Finish Blades  
with Etched Lens  
(Shown with Dark Walnut Blades)



**F1000-WH**

White Finish  
White Finish Blades  
with Etched Lens

# Traditional Mojo



## F622-BWH

Bone White Finish  
Bone White Blades  
with Bone White Glass

The Traditional Mojo is the next generation of our highly successful Mojo series. Traditional accents integrate perfectly for your home.



## F622-ORB

Oil Rubbed Bronze Finish  
Reversible Medium Maple / Dark Walnut Blades  
with Etched White Glass  
(Shown with Medium Maple Blades)





**F622-ORB/TS**

Oil Rubbed Bronze Finish  
Reversible Medium Maple / Dark Walnut Blades  
with Tea Stain Glass  
(Shown with Medium Maple Blades)



**F622-PW**

Pewter Finish  
Reversible Medium Maple / Dark Walnut Blades  
with Etched White Glass  
(Shown with Dark Walnut Blades)

**Features:**

- 12° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrod
- 3-Speed Pull Chain
- Low Profile Bowl Light Kit  
Uses 3-60W Candelabra Bulbs  
(Included)
- Cap for Non-Light Use (Included)
- Solid Cap and Finial Included for  
Adaptation for Remote Control Use

**Energy Information** (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,699	66.1	86.22

**Lifetime**  
WARRANTY

# Mojo



## F522-ORB/TS

Oil Rubbed Bronze Finish  
Reversible Medium Maple / Dark Walnut Blades  
with Tea Stain Glass  
(Shown with Medium Maple Blades)

## Features:

- 12° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Low Profile Light Kit  
Uses 3-60W Candelabra Bulbs  
(Included)
- Warp Resistant Plywood Blades
- Cap for Non-Light Use (Included)
- Solid Cap and Finial Included for  
Adaptation for Remote Control Use

## Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,295	65.7	81



## F522-BN

Brushed Nickel Finish  
Reversible Medium Maple / Dark Walnut Blades  
with Frosted White Glass  
(Shown with Medium Maple Blades)

Lifetime  
WARRANTY



□ **F522-WH**

White Finish  
White Blades  
with Frosted White Glass



□ **F522-BWH**

Bone White Finish  
Bone White Blades  
with Frosted White Glass



□ **F522-ORB**

Oil Rubbed Bronze Finish  
Reversible Medium Maple / Dark Walnut Blades  
with Frosted White Glass  
(Shown with Medium Maple Blades)

# Mojo II



## F533-BN

Brushed Nickel Finish  
Reversible Medium Maple / Dark Walnut Blades  
with Frosted White Glass  
(Shown with Dark Walnut Blades)



## F533-DK

Distressed Koa Finish  
Reversible Medium Maple / Dark Walnut Blades  
with Tea Stain Glass  
(Shown with Dark Walnut Blades)



## F533-WH

White Finish  
White Blades  
with Frosted White Glass



**F533-ORB**

Oil Rubbed Bronze Finish  
Reversible Medium Maple / Dark Walnut Blades  
with Tea Stain Glass  
(Shown with Dark Walnut Blades)

The Mojo II is the newest addition to our Value Collection featuring a wealth of performance and an integrated light source. A great value for low ceiling applications.

**Features:**

- 14° Blade Pitch
- 52" 4 Blades
- Flush Mount - Ideal for Low Ceilings  
Total Hanging Depth 13" with Light
- 3-Speed Pull Chain
- Integrated Downlight  
Uses 3-60W Candelabra Bulbs (Included)
- Solid Cap and Finial Included for Adaptation for Remote Control Use

**Energy Information** (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,138	62.6	82



**F533-BWH**

Bone White Finish  
Bone White Blades  
with Bone White Glass



# Hilo



## F470-BN

Brushed Nickel Finish  
Medium Maple / Dark Walnut Blades  
with Frosted White Glass  
(Shown with Dark Walnut Blades)

### Features:

- 12° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrod
- 3-Speed Pull Chain
- Reversible Warp Resistant Blades
- Bowl Light Kit  
Uses 3-40W Candelabra Bulbs  
(Included)
- Cap for Non- Light Use

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,828	64.7	74.62

The Hilo's clean lines provide elegance and simplicity suitable for a variety of environments.

**Lifetime**  
WARRANTY





**F470-WH**

White Finish  
White / Medium Maple Blades  
with Frosted White Glass  
(Shown with White Blades)



**F470-ORB**

Oil Rubbed Bronze Finish  
Medium Walnut / Dark Walnut Blades  
with Tea Stain Glass  
(Shown with Medium Maple)

# Bolo™



Four of our best selling finishes accent this fan, creating a decorative alternative to an everyday need. Includes glass bowl light kit and remote control system.

## F620-BN

Brushed Nickel Finish  
Dark Walnut Blades  
with Etched Swirl Glass



## F620-ORB

Oil Rubbed Bronze Finish  
Medium Maple Blades  
with Excavation Glass

### Features:

- 14° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- Hand Held Remote Control System
- Bowl Light Kit  
Uses 3-60W Candelabra Bulbs  
(Included)
- Cap for Non-Light Use (Included)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,712	74	77.19



## RCS213

Hand Held Remote Control Included  
For Details See Page(s): 222





**F620-DBB**

□ Dark Brushed Bronze Finish  
Dark Maple Blades  
with Avorio Mezzo™ Glass



**F620-BCW**

□ Belcaro Walnut™ Finish  
Dark Walnut Blades  
with Excavation Glass



**F614-DBB**

Dark Brushed Bronze Finish  
Dark Maple Blades

**Features:**

- 14° Blade Pitch
- 54" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Universal Light Kit Adaptable  
(Sold Separately. Page(s): 229)
- Custom Light Kit K9614 Available  
(Sold Separately. Page(s): 235)

**Energy Information** (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,257	70.5	89

A smooth blend of finish and form distinguishes the Timeless fan, enhanced by simple clean lines and a unique blade iron design.



# Timeless



**F614-MCG**

Mottled Copper with Gold Highlights Finish  
Dark Walnut Blades



**F614-PI**

Patina Iron Finish  
Dark Maple Blades





**F614-PW**

Pewter Finish  
Dark Walnut Blades

**Features:**

- 14° Blade Pitch
- 54" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)
- Custom Light Kit K9614 Available (Sold Separately. Page(s): 235)

**Energy Information** (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,257	70.5	89



**F614-FB**

French Beige Finish  
Medium Maple Blades





# Timeless

A smooth blend of finish and form distinguishes the Timeless fan, enhanced by simple clean lines and a unique blade iron design.



**F614-ORB**

Oil Rubbed Bronze Finish  
Medium Maple Blades



**F689-KA**

Kocoa Finish  
Reversible Toned Medium Maple / Dark Maple Blades  
(Shown with Toned Medium Maple Blades)

The Kola-XL 60-inch fan features the same design elements as the Kola 52-inch. It has been upgraded to provide the performance necessary for larger rooms and has the convenience of an electronic control system.



**F689-PW**

Pewter Finish  
Reversible Dark Maple / Dark Walnut Blades  
(Shown with Dark Maple Blades)

# Kola-XL



## F689-WH

White Finish  
White Blades



## F689-DBB

Dark Brushed Bronze Finish  
Reversible Dark Maple / Dark Walnut Blades  
(Shown with Dark Walnut Blades)

### Features:

- 12° Blade Pitch
- 60" 5 Blades
- 3½" and 6" Downrods
- Full Function Hand Held Remote Control System
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,557	84.6	89



**Lifetime**  
WARRANTY

**Remote**  
CONTROL  
FULL FUNCTION

## RCS212

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222





**F688-PW**

Pewter Finish  
Reversible Dark Maple / Dark Walnut Blades  
(Shown with Dark Maple Blades)

**Features:**

- 12° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Universal Light Kit Adaptable  
(Sold Separately. Page(s): 229)

**Energy Information** (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,002	71.3	84



**F688-KA**

Cocoa Finish  
Reversible Toned Medium Maple / Dark Maple Blades  
(Shown with Toned Medium Maple Blades)




# Kola



**F688-WH**

White Finish  
White Blades

Smooth lines with a sleek blade iron design and a robust body make the Kola a perfect complement to any home decor.



**F688-DBB**

Dark Brushed Bronze Finish  
Reversible Dark Maple / Dark Walnut Blades  
(Shown with Dark Walnut Blades)



**F696-CC**

□ Cognac Finish  
Reversible Natural Walnut / Dark Walnut Blades  
(Shown with Natural Walnut Blades)



**F696-KA**

□ Kocoa Finish  
Reversible Toned Medium Maple / Dark Maple Blades  
(Shown with Toned Medium Maple Blades)



# Kafé-XL



**F696-WH**

White Finish  
White Blades

Simple elegance defined in rich new finishes, the Kafé-XL brings an exciting new look with enhanced features to our value collection.



**F696-VP**

Vineyard Patina Finish  
Reversible Dark Maple / Dark Walnut Blades  
(Shown with Dark Walnut Blades)



**RCS212**

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222

**Features:**

- 12° Blade Pitch
- 60" 5 Blades
- 3½" and 6" Downrods
- Full Function Hand Held Remote Control System
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)

**Energy Information** (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,557	84.6	89

**Lifetime**  
WARRANTY

**Remote**  
CONTROL  
FULL FUNCTION





**F695-KA**

Kocoo Finish  
Reversible Toned Medium Maple / Dark Maple Blades  
(Shown with Toned Medium Maple Blades)

**Features:**

- 12° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Universal Light Kit Adaptable  
(Sold Separately. Page(s): 229)

**Energy Information** (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,002	71.3	84

Simple yet elegant in several finishes, the Kafé brings a refreshing new look to our value collection.



# Kafé



**F695-CC**

Cognac Finish  
Reversible Natural Walnut / Dark Walnut Blades  
(Shown with Natural Walnut Blades)



**F695-WH**


White Finish  
White Blades



**F695-VP**

Vineyard Patina Finish  
Reversible Dark Maple / Dark Walnut Blades  
(Shown with Dark Maple Blades)

# Classica



## F759-PBL Gallery Edition

Provencal Blanc Finish  
Provencal Blanc Blades  
with Etched Glass

Includes:  
Integrated 3-Light Kit  
Uses 3-60W Candelabra Bulbs  
(Included)  
Hand Held Remote Control System

**Lifetime**  
WARRANTY

**Remote**  
CONTROL  
FULL FUNCTION

## Features:

- 14° Blade Pitch
- 54" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Universal Light Kit Adaptable  
(Sold Separately. Page(s): 229)
- Custom Light Kit K9659 Available  
(Sold Separately. Page(s): 235)

Old world hand-painted finishes accentuate the hand-carved details to create a traditional European style fan.

© 2009 Minka Lighting, Inc.

## Energy Information (Excludes Lights)


Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,313	71.6	88

**Lifetime**  
WARRANTY



## F659-PBL

Provencal Blanc Finish  
Provencal Blanc Blades





**F659-BCW**

Belcaro Walnut™ Finish  
Dark Walnut Blades



**F659-FB**

French Beige Finish  
Medium Maple Blades



**F659-DRF**

Driftwood Finish  
Driftwood Blades



**F659-PI**

Patina Iron Finish  
Dark Walnut Blades





**F588-SP-WH**

White Finish  
White Blades

Ultra-Max™, by name and performance, is engineered with a 14° blade pitch to provide maximum comfort in even the largest areas. Its clean, traditional styling will be “right at home” in any setting.



**F588-SP-BN**

Brushed Nickel Finish  
Dark Walnut Blades



# Ultra-Max™



## F588-SP-BCW

Belcaro Walnut™ Finish  
Dark Walnut Blades



## F588-SP-BWH

Bone White Finish  
Bone White Blades

### Features:

- 14° Blade Pitch
- 54" 5 Blades
- 3½" and 6" Downrods
- Full Function Wall Control System and Hand Held Remote Control
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,341	76.4	83



## RCS212

Full Function Hand Held Remote Control Included  
For Details See Page(s): 222



## WCS212

Full Function Wall Control System Included  
For Details See Page(s): 223

Lifetime  
WARRANTY

WallControl  
FULL FUNCTION

Remote  
CONTROL  
FULL FUNCTION



**F569-BS**

Brushed Steel Finish  
Silver Blades  
with Opal Glass

A truly exceptional value! All the benefits of the Supra® 52" packaged with additional bells and whistles including a matching light kit and RCS223 Remote Control System.

**F569-ORB**

Oil Rubbed Bronze Finish  
Medium Maple Blades  
with Opal Glass

# Supra<sup>®</sup> 52"

with Light Kit  
and Remote Control System



## F569-BS/DW

Brushed Steel Finish  
Dark Walnut Blades  
with Opal Glass



## F569-WH

White Finish  
White Blades  
with Opal Glass



## RCS223

Hand Held Remote Control Included  
For Details See Page(s): 222

### Features:

- 14° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- Hand Held Remote Control System
- Halogen Light Kit  
Uses 1-100W Mini-Can Halogen Bulb (Included)
- 6-Ply Warp Resistant Blades

U.S. Patent(s): D450,830

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,755	79	72.85

**Lifetime**  
WARRANTY

**Remote**  
CONTROL



The Supra® 52" offers decorative versatility in multiple finishes. It has clean, modern styling and uncompromising quality with superior performance.

**F568-KA**

Kocoa Finish  
Reversible Toned Medium Maple / Medium Maple Blades  
(Shown with Toned Medium Maple Blades)

**Features:**

- 14° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)
- 6-Ply Warp Resistant Blades

U.S. Patent(s): D450,830

**Energy Information** (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,995.05	75.3	79.62

**F568-BWH**

Bone White Finish  
Bone White Blades



Accessory Blades Available. See Page(s): 236

# Supra<sup>®</sup> 52"



**F568-SWH**

Shell White Finish  
Shell White Blades



**F568-BS/DW**

Brushed Steel Finish  
Dark Walnut Blades





□ **F568-WH**

White Finish  
White Blades



□ **F568-BCW**

Belcaro Walnut™ Finish  
Dark Walnut Blades



# Supra<sup>®</sup> 52"



## F568-ORB

Oil Rubbed Bronze Finish  
Medium Maple Blades



## F568-BS

Brushed Steel Finish  
Silver Blades

### Features:

- 14° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)
- 6-Ply Warp Resistant Blades

U.S. Patent(s): D450,830

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,995.05	75.3	79.62

Lifetime  
WARRANTY



Accessory Blades Available. See Page(s): 236

www.minkaaire.com



**F563-SP**

- Brushed Steel Finish  
Silver Blades  
with Opal Glass



**F563-SP-BS/DW**

- Brushed Steel Finish  
Dark Walnut Blades  
with Opal Glass

# Supra<sup>®</sup> 44"

with Light Kit



## F563-SP-ORB

Oil Rubbed Bronze Finish  
Medium Maple Blades  
with Opal Glass

The Supra<sup>®</sup> 44", model F563-SP is a great economical option, packaged with a light kit to meet every need.



## F563-SP-WH

White Finish  
White Blades  
with Opal Glass

### Features:

- 14° Blade Pitch
- 44" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Halogen Light Kit  
Uses 1-100W Mini-Can Halogen Bulb (Included)
- 6-Ply Warp Resistant Blades

U.S. Patent(s): D450,830

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,272	76	69.37

**Lifetime**  
WARRANTY

# Supra<sup>®</sup> 44"



## F563-BS/DW

Brushed Steel Finish  
Dark Walnut Blades

Designed with superior performance and all of the features found in full-size fans made available for mid-size rooms.

### Features:

- 14° Blade Pitch
- 44" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)
- 6-Ply Warp Resistant Blades

U.S. Patent(s): D450,830

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,272	76	69.37

## F563-BS

Brushed Steel Finish  
Silver Blades



**Lifetime**  
WARRANTY

Accessory Blades Available. See Page(s): 236



**F563-ORB**  
Oil Rubbed Bronze Finish  
Medium Maple Blades



**F563-WH**  
White Finish  
White Blades

# Supra<sup>®</sup> 32"



## F562-WH

White Finish  
White Blades

### Features:

- 22° Blade Pitch
- 32" 6 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)
- 6-Ply Warp Resistant Blades

U.S. Patent(s): D450,830

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,075	66	61.73

Fashion, form and function for the smallest areas are highlighted in the Supra<sup>®</sup> 32". The perfect choice for bathrooms, hallways, entries and walk-in closets.

**Lifetime**  
WARRANTY

Accessory Blades Available. See Page(s): 236





**F562-BS**

Brushed Steel Finish  
Silver Blades



**F562-ORB**

Oil Rubbed Bronze Finish  
Medium Maple Blades



LED

**F556L-BN**

Brushed Nickel Finish  
Silver Blades  
with Etched Lens

**Features:**

- 12° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- Hand Held Remote Control System
- Uses 17W LED (Included)  
3 Year Warranty
- 1100 Lumens
- 3000K
- CRI 80
- Replacements LED Assembly  
(Part #6F1000LK01)

**Energy Information** (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,966	66.5	89.71



**F556L-BWH**

Bone White Finish  
Bone White Blades  
with Etched Lens



**RCS213**

Hand Held Remote Control Included  
For Details See Page(s): 222

**Lifetime**  
WARRANTY

**Remote**  
CONTROL

LED

# Contractor LED

LED

## F556L-ORB

Oil Rubbed Bronze Finish  
Reversible Medium Maple / Dark Walnut Blades  
with Etched Lens  
(Shown with Medium Maple Blades)

Smart simplicity at its best. This contractor LED provides greater performance and offers energy efficiency through the use of the latest LED technology.

LED

## F556L-BN/DW

Brushed Nickel Finish  
Reversible Medium Maple / Dark Walnut Blades  
with Etched Lens  
(Shown with Dark Walnut Blades)



**F556-BN**

Brushed Nickel Finish  
Silver Blades



**F556-BWH**

Bone White Finish  
Bone White Blades

**Features:**

- 12° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain

**Energy Information** (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,966	66.5	89.71



# Contractor Plus



## **F556-ORB**

Oil Rubbed Bronze Finish  
Reversible Medium Maple / Dark Walnut Blades  
(Shown with Medium Maple Blades)

Our new Contractor Plus fan continues our tradition of offering design and reliability in several finishes.



## **F556-BN/DW**

Brushed Nickel Finish  
Reversible Medium Maple / Dark Walnut Blades  
(Shown with Dark Walnut Blades)



# Contractor Uni-Pack

with 3-Light Kit



## F647-BS

Brushed Steel Finish  
Dark Walnut Blades  
with Etched Glass


Offering affordable performance and reliability with designer finishes, the Contractor fan now comes with an integrated light kit.

### Features:

- 12° Blade Pitch
- 52" 4 or 5 Blades
- 4" Downrod
- 3-Speed Pull Chain
- Integrated Light Kit  
Uses 3-60W Candelabra Bulbs  
(Included)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,901	62	79.05



## F647-SWH

Shell White Finish  
Shell White Blades  
with Etched Glass

**Lifetime**  
WARRANTY

Accessory Blades Available. See Page(s): 236





**F647-ORB/TS**

Oil Rubbed Bronze Finish  
Medium Maple Blades  
with Tea Stain Glass



**F647-WH**

White Finish  
White Blades  
with Etched Glass



**F647-ORB**

Oil Rubbed Bronze Finish  
Medium Maple Blades  
with Etched Glass

# Contractor Uni-Pack

with Bowl Light Kit



## F648-BS

Brushed Steel Finish  
Dark Walnut Blades  
with Etched Swirl Glass

### Features:

- 12° Blade Pitch
- 52" 4 or 5 Blades
- 4" Downrod
- 3-Speed Pull Chain
- Bowl Light Kit (Included)  
Uses 2-13W Non-Dimmable GU24  
Spiral CFL Bulbs (Included)
- Pre-Installed One-Piece Motor  
Blade Iron Gasket
- Cap for Non-Light Use (Included)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,408	65	82.69

Our most economical and efficient fan and light combination for the budget-conscious customer, helping to save money and protect the environment through energy efficient products.

Lifetime  
WARRANTY



Accessory Blades Available. See Page(s): 236



□ **F648-ORB/EX**  
Oil Rubbed Bronze Finish  
Medium Maple Blades  
with Excavation Glass



□ **F648-WH**  
White Finish  
White Blades  
with Etched Swirl Glass



□ **F648-ORB**  
Oil Rubbed Bronze Finish  
Medium Maple Blades  
with Etched Swirl Glass



**F548-WH**

White Finish  
White Blades  
with Etched Swirl Glass



**F548-ORB**

Oil Rubbed Bronze Finish  
Medium Maple Blades  
with Etched Swirl Glass

# Contractor Uni-Pack

with Bowl Light Kit



## F548-ORB/EX

Oil Rubbed Bronze Finish  
Medium Maple Blades  
with Excavation Glass

### Features:

- 12° Blade Pitch
- 52" 4 or 5 Blades
- 4" Downrod
- 3-Speed Pull Chain
- Bowl Light Kit (Included)  
Uses 3-60W Candelabra Bulbs (Included)
- Pre-Installed One-Piece Motor Blade Iron Gasket
- Cap for Non-Light Use (Included)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,636	64	73.01


The most economical and efficient fan and light combination for the secondary rooms in the house.

**Lifetime**  
WARRANTY

Accessory Blades Available. See Page(s): 236

[www.minkaaire.com](http://www.minkaaire.com)

213



□ **F548-BS**

Brushed Steel Finish  
Silver Blades  
with Etched Swirl Glass



□ **F548-BWH**

Bone White Finish  
Bone white Blades  
with Etched Swirl Glass



# Contractor Uni-Pack

with Bowl Light Kit



## F548-BS/DW

Brushed Steel Finish  
Dark Walnut Blades  
with Etched Swirl Glass

### Features:

- 12° Blade Pitch
- 52" 4 or 5 Blades
- 4" Downrod
- 3-Speed Pull Chain
- Bowl Light Kit (Included)  
Uses 3-60W Candelabra Bulbs (Included)
- Pre-Installed One-Piece Motor Blade Iron Gasket
- Cap for Non-Light Use (Included)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,636	64	73.01

**Lifetime**  
WARRANTY

Accessory Blades Available. See Page(s): 236

[www.minkaaire.com](http://www.minkaaire.com)

215

# Contractor 52"



## F547-ORB

Oil Rubbed Bronze Finish  
Medium Maple Blades

Our Contractor series offers affordable performance and reliability. Designer finishes have been made available to match current trends and demands.

### Features:

- 12° Blade Pitch
- 52" 4 or 5 Blades
- 4" Downrod  
(Uses 3/4" I.D. DR5 Series Downrod)
- 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup
- Pre-Installed One-Piece Motor/  
Blade Iron Gasket
- Universal Light Kit Adaptable  
(Sold Separately. Page(s): 229)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,565.39	61	74.84



## F547-ABR

Antique Bronze Finish  
Medium Maple Blades

**Lifetime**  
WARRANTY

Accessory Blades Available. See Page(s): 236



**F547-BS/DW**  
□ Brushed Steel Finish  
Dark Walnut Blades



**F547-BWH**  
□ Bone White Finish  
Bone White Blades



**F547-WH**  
□ White Finish  
White Blades



**F547-BS**  
□ Brushed Steel Finish  
Silver Blades



**F546-ORB**

Oil Rubbed Bronze Finish  
Medium Maple Blades



**F546-BS**

Brushed Steel Finish  
Silver Blades

# Contractor 42"



## F546-BS/DW

Brushed Steel Finish  
Dark Walnut Blades

Our Contractor 42" series offers affordable performance and reliability. Designer finishes have been made available to match current trends and demand.



## F546-WH

White Finish  
White Blades

### Features:

- 12° Blade Pitch
- 42" 5 Blades
- 4" Downrod
- 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup
- Pre-Installed One-Piece Motor/ Blade Iron Gasket
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)

### Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
3,290	47	70.01

Lifetime  
WARRANTY

# Mesa

minkaAire®  
A Minka Group® Co.



**F565-WH 52"**

White Finish  
White Blades

Our close-to-ceiling economy model in two sizes will move air in the tightest places.

## Features:

- 12° Blade Pitch
- 52" or 42" 5-Blades
- Flush Mount 8¾" Overall Ceiling Drop
- 3-Speed Pull Chain
- One-Piece Stamped Body
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)

### F565 Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,092	65	78

### F566 Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
3,291	50	65.82



**F566-WH 42"**

White Finish  
White Blades

Lifetime  
WARRANTY



# Finishes



**ABD**  
Brushed Aluminum



**ABR**  
Antique Bronze



**BCW**  
Belcaro Walnut™



**BG**  
Bahama Beige™



**BI/AI**  
Black Iron/  
Aged Iron Accents



**BK**  
Black



**BN**  
Brushed Nickel  
(Plated)



**BNW**  
Brushed Nickel Wet  
(Plated)



**BS**  
Brushed Steel



**BWH**  
Bone White



**CC**  
Cognac



**CF**  
Craftsman™



**CH**  
Chrome  
(Plated)



**CPBR**  
Copper Bronze



**CT**  
Cattera Bronze™



**DBB**  
Dark Brushed Bronze



**DK**  
Distressed Koa



**DKG**  
Distressed Koa  
with Gold Highlights



**DRB**  
Dark Restoration Bronze™



**DRF**  
Driftwood



**FB**  
French Beige



**FLP**  
Florence Patina™



**GBZ**  
Golden Bronze



**GM**  
Gun Metal



**GL**  
Galvanized



**HT**  
Heritage™



**IBR**  
Illuminati Bronze™



**IO**  
Iron Oxide



**KA**  
Kocoo



**LN**  
Liquid Nickel  
(Plated)



**MCG**  
Mottled Copper  
with Gold Highlights



**MG**  
Mahogany



**MP**  
Maple



**MW**  
Mossoro Walnut™



**ORB**  
Oil Rubbed Bronze



**PBL**  
Provencal Blanc



**PI**  
Patina Iron



**PN**  
Polished Nickel  
(Plated)



**PW**  
Pewter



**RD**  
Red



**RRB**  
Restoration Bronze™



**RW**  
Rosewood



**SI**  
Smoked Iron



**SL**  
Silver



**STW**  
Sterling Walnut™



**SWH**  
Shell White



**TB**  
Toned Brass  
(Plated)



**TSP**  
Tuscan Patina™



**VB**  
Volterra Bronze™



**VP**  
Vineyard Patina



**VRT**  
Vintage Rust™



**WH**  
White



**WHF**  
Flat White

Hand-painted finishes and components made from natural material may reflect variations in color and texture. These are not imperfections and enhance the unique appearance of each and every Minka-Aire® fixture. Specifications are subject to change at any time.

# Control Systems



RCS212 - 256 Bit

## RCS212 Full Function Hand Held AireControl® Remote System

- Three Speed Fan Control in Forward and Reverse
- On/Off Plus Full Range Light Dimmer with Independent Up/Downlight Control
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 20-40' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In
- Can be Used in Conjunction with WCS212 Wall Mount AireControl®
- 12 Volt Battery Included

U.S. Patent(s): D533,514; D551,008; 8,253,272



RCS213 - 256 Bit

## RCS213 Hand Held AireControl® Remote System

- Three Speed Fan Control
- On/Off Plus Full Range Light Dimmer
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 20-40' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In
- Can be Used in Conjunction with WCS223 Wall AireControl®
- 12 Volt Battery Included

U.S. Patent(s): D533,514; D551,008; 8,253,272



RCS223 - 256 Bit

## RCS223 Hand Held AireControl® Remote System

- Three Speed Fan Control
- On/Off Plus Full Range Light Dimmer
- Includes One (1) Hand Held Remote Control, Wall Holster and Canopy Mounted Receiver
- Wireless Remote Operation
- Operates at Distance of 20-40' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In
- Can be Used in Conjunction with WCS213 Wall AireControl®
- 12 Volt Battery Included

U.S. Patent(s): D533,514; D551,008; 8,253,272



RC400 / RC500 / RC600

## RC400 AireControl® Remote System

- For F726, F823, F828, F887 and F888 Fans Only
- Six Speed Fan Control in Forward and Reverse
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 23' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In

U.S. Patent(s): D533,514; D551,008

## RC500 AireControl® Remote System

- For F737 and F853 Fans Only
- Same Features as RC400 AireControl® System

U.S. Patent(s): D533,514; D551,008

## RC600 AireControl® Remote System

- For F617, F745 and F905 Fans Only
- Same Features as RC400 AireControl® System

U.S. Patent(s): D533,514; D551,008



Full Function Hand Held Remote Control



An ultra-thin design exclusive to Minka-Aire®, the remote enables the user with one finger to control all functions of Minka-Aire® ceiling fans.

AireControl® by Minka-Aire® controls all functions: reverse, uplight (where applicable), fan light, speed control, as well as off-on. (RCS212 and WCS212)

RCS213, RCS223, WCS213 and WCS223 controls do not include the reverse function.

Included is a holster if you want to wall mount the control for your convenience.

### Please Note:

256 Bit remote systems are not compatible with 32 Bit remote systems.

**WC105-WH  
Speed Control**

- Four Speed Fan Control
- 2-Wire Installation



WC105-WH White

**WC106-WH  
Speed Control**

- Four Speed Fan Control
- Full Range Dimmer
- 3-Wire Installation



WC106-WH White

**WC110  
Speed Control**

- For F510 Fans Only
- Four Speed Fan Control
- Full Range Dimmer
- 3-Wire Installation



WC110

**WCS212  
Full Function AireControl®**

- Same Features as RC212 Hand Held
- Includes Ivory and White Finish Inner/Outer Plates

U.S. Patent(s): D533,514; 8,253,272



WCS212 - 256 Bit

**WCS213  
AireControl®**

- Same Features as RCS213 Hand Held
- Includes Ivory and White Finish Inner/Outer Plates

U.S. Patent(s): D533,514; 8,253,272



WCS213 - 256 Bit

**WCS223  
AireControl®**

- Same Features as RCS223 Hand Held
- Includes Ivory and White Finish Inner/Outer Plates

U.S. Patent(s): D533,514; 8,253,272



WCS223 - 256 Bit

**Please Note:**

256 Bit remote systems are not compatible with 32 Bit remote systems.

# Control Systems

## Fan Control Systems Compatibility Chart

Fan Model	Fan Name	PAGE	RCS212	RCS213	RCS223	WC105-WH	WC106-WH	WCS212	WCS213	WCS223
F302	Gyrette™	120	Incl.					•		
F402	Gyro™ Wet	119, 162	•					Incl.		
F470	Hilo	172-173		•	•		•		•	•
F474	Concept™ II Wet	146-147	•					Incl.		
F476	Concept™ I Wet	124-125	•					Incl.		
F477	Concept I Wet 58"	122-123	•					Incl.		
F502	Traditional Gyro™	115	•					Incl.		
F510	Spacesaver	90-91				Wall Control Included WC110				
F513	New Era	92-93	Incl.					•		
F514	Zen	82-83	Incl.					•		
F516	Concept™ I 44"	66-67	Incl.					•		
F517	Concept™ I 52"	66-67	Incl.					•		
F518	Concept™ II 44"	64-65	Incl.					•		
F519	Concept™ II 52"	62-63	Incl.					•		
F521	Aluma	70-71		•	•		Incl.		•	•
F522	Mojo	168-169		•	•				•	•
F523	Aluma Wet	142-143		Incl.						
F524	Roto	54-55			•	Incl.				•
F528	San Francisco®	74		•			•		Incl.	
F529	San Francisco®	74-75		•			•		Incl.	
F531	Flyte®	72-73		•			•		Incl.	
F532	Sunseeker	126-127				•	•			
F539	Great Room Traditional	104-105	•					Incl.		
F544	Calais™	114		Incl.			•		•	
F546	Contractor 42"	218-219		•	•	•	•		•	•
F547	Contractor 52"	216-217		•	•	•	•		•	•
F548	Contractor Uni-Pack	208-215		•	•		•		•	•
F556L	Contractor LED	204-205		Incl.					•	
F562	Supra® 32"	202-203		•	•	•	•		•	•
F563	Supra® 44"	200-201		•	•	•	•		•	•
F563	Supra® 44" -SP	198-199		•	•	•	•		•	•
F565	Mesa™ 52"	220				•	•			
F566	Mesa™ 42"	220				•	•			
F568	Supra® 52"	194-197		•	•	•	•		•	•
F569	Supra® 52"	192-193		•	Incl.		•		•	•
F571	Sundance™ 52"	160				•	•			
F572	Sundance™ 42"	161				•	•			
F574	Concept™ II Wet	146-147	•					Incl.		
F577	Concept™ I Wet	124-125	•					Incl.		
F579	Magellan®	140-141		•					Incl.	
F580	Shangri-La®	129			•		•		•	
F581	Gauguin™	154-155	•					Incl.		
F582	Rainman™	130-131		•			•		Incl.	
F588	Ultra-Max™	190-191	Incl.		•			Incl.		•
F589	Sundowner®	156-159				•	•			
F593	Traditional Concept™ 44"	88-89	•					Incl.		

• = Compatibility

Please Note: 256 Bit remote systems are not compatible with 32 Bit remote systems.

- 256 Bit systems have a Green LED and Green receiver boxes.

- 32 Bit systems have a Red LED and Black receiver boxes.

Fan Model	Fan Name	PAGE	RCS212	RCS213	RCS223	WC105-WH	WC106-WH	WCS212	WCS213	WCS223
F594	Traditional Concept™ 52"	86-87	•					Incl.		
F596	Cirque™	78-79	•					Incl.		
F598	Airus™	84-85	•					Incl.		
F601	Acero™	98-99	•					Incl.		
F602	Gyro™	118	•					Incl.		
F603	Como™	80-81	•					Incl.		
F614	Timeless	176-179		•	•	•	•		•	•
F617	Raptor	22-23						Special Remote Included RC600		
F620	Bolo™	174-175		Incl.	•		•		•	•
F647	Contractor Uni-Pack	208-209		•	•		•		•	•
F648	Contractor Uni-Pack	210-211		•	•				•	•
F659	Classica	188-189		•	•	•	•		•	•
F672	Iconic	102-103	Incl.					•		
F680	Terrana	152-153	Incl.					•		
F688	Kola	182-183		•	•	•			•	•
F689	Kola-XL	180-181	Incl.					•		
F695	Kafé	186-187		•	•	•			•	•
F696	Kafé-XL	184-185	Incl.					•		
F701	Delano®	94-95		•			•		Incl.	
F702	Volterra™	112-113		•			•		Incl.	
F705	Napoli™	110	•					Incl.		
F707	Salon Grand™	108	•					Incl.		
F711	Delano® II	96-97	•					Incl.		
F715	Napoli™ II	111	•					Incl.		
F726	Spectre	12-15						Special Remote Included RC400		
F733	Gilera	48-51	•					Incl.		
F734	Strata	138-139		Incl.	•					
F737	Moda	60-61						Special Remote Included RC500		
F738	Pancake	52-53	Incl.					•		
F745	Sabot	24-25						Special Remote Included RC600		
F753	Java	68-69		Incl.						
F759	Classica Gallery Edition	188		Incl.					•	
F802	Vintage Gyro™	116-117	•					Incl.		
F803	Artemis™	34-39	•					Incl.		
F812	Lineage™	107	•					Incl.		
F820	Santa Lucia™	106	•					Incl.		
F823	Wing	40-43						Special Remote Included RC400		
F824	Uchiwa	76-77	•					Incl.		
F828	Symbio	26-27						Special Remote Included RC400		
F833	Kewl	58-59			•	Incl.				•
F840	Craftsman™	128	•					Incl.		
F843	Wave	46-47		Incl.					•	
F844	Light Wave	44-45		Incl.					•	
F853	Aviation	28-31						Special Remote Included RC500		
F887	Xtreme	16-21						Special Remote Included RC400		
F888	Slipstream	32-33						Special Remote Included RC400		
F889	Slipstream XXL	132-137						Special Remote Included RC400		
F900	Cristafano™	109	•					Incl.		
F905	Artemis™ XL5	56-57						Special Remote Included RC600		
F1000	Dyno	164-165		Incl.					•	

Please Note: 256 Bit remote systems are not compatible with 32 Bit remote systems.  
- 256 Bit systems have a Green LED and Green receiver boxes.  
- 32 Bit systems have a Red LED and Black receiver boxes.

• = Compatibility

# Hanging Systems



FINISH	ABDD	ABR	BCW	BG	BI	BK	BN	BN/MG	BNW	BS	BWH	CC	CF	CH	CPBR	CT	DBB	DKG	DRB	DRFF	FB	FLP	GL	GM	HT	IBR
--------	------	-----	-----	----	----	----	----	-------	-----	----	-----	----	----	----	------	----	-----	-----	-----	------	----	-----	----	----	----	-----

## DR5 SERIES DOWNROD ARE 3/4" I.D.

DR500-COUPLER	•**	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR512	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR518	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR524	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR536	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR548	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR560	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR572	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•

## PRE-WIRED DOWNBRIDGE™ KIT (FOR USE WITH F528 AND F529 ONLY)

DK06-6"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK24-24"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK36-36"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK48-48"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK60-60"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK72-72"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-

## DOWNLINK™ KIT (FOR USE WITH F531 ONLY)

DL06-6"	-	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL15-15"	-	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL27-27"	-	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL39-39"	-	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL51-51"	-	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL63-63"	-	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL75-75"	-	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-

## MINKA-AIRE® 45° SLOPE CEILING ADAPTER KITS (SCA)

* A245 3/4" I.D.	•**	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
A180	-	•	•	-	•	•	•	-	•	•	•	-	•	•	•	•	•	•	•	-	•	-	•	-	•	•

Minka-Aire® offers a full selection of downrods in 59 finishes and 8 lengths to complement any Minka-Aire® ceiling fan.

\* A245 3/4" I.D. is also available in PR (Primer) finish.

\*\* For F524-ABD, only.





FINISH	IO	KA	LN	MCG	MG	MP	MW	ODK	ORB	PBL	PI	PN	PW	RD	RRB	RW	SI	SL	STW/GOW	SWH	TSP	VB	VP	VRT	WH/44	WHF
--------	----	----	----	-----	----	----	----	-----	-----	-----	----	----	----	----	-----	----	----	----	---------	-----	-----	----	----	-----	-------	-----

**DR5 SERIES DOWNROD ARE 3/4" I.D.**

DR500-COUPLER	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR512	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR518	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR524	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR536	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR548	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR560	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR572	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•

**PRE-WIRED DOWNBRIDGE™ KIT (FOR USE WITH F528 AND F529 ONLY)**

DK06-6"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK24-24"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK36-36"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK48-48"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK60-60"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK72-72"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-

**DOWNLINK™ KIT (FOR USE WITH F531 ONLY)**

DL06-6"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL15-15"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL27-27"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL39-39"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL51-51"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL63-63"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL75-75"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-

**MINKA-AIRE® 45° SLOPE CEILING ADAPTER KITS (SCA)**

* A245 3/4" I.D.	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
A180	-	•	•	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	•	•	•	-	•	•	•	•

All component parts and hardware supplied with your Minka-Aire® ceiling fan have been designed and engineered to assure proper and safe installation of your new ceiling fan. Substituting parts or hardware, such as, but not limited to the hanger ball and the hanger bracket, not supplied with your ceiling fan by Minka-Aire®, will void the Minka-Aire® Warranty.

# Hanging Systems



## Low Ceiling Adapter A180

**For use on:**  
F513, F514, F522, F532, F546, F547, F548, F556, F562, F563, F568, F569, F588, F589, F596, F601, F603, F613, F614, F620, F621, F622, F647, F648, F659, F672, F688, F689, F695, F696, F734, F753, F759, F824




## Slope Ceiling Adapter Kit (SCA) A245-BN

( $\frac{3}{4}$ " I.D.)  
U.S. Patent(s): 7,510,160

## Minka-Aire® 45° Slope Ceiling Adapter Kit (SCA)

Minka-Aire® SCA Kit was designed to meet the needs of the home building industry as demand increases for higher, more steeply angled ceilings. Minka-Aire® A245 SCA is used with  $\frac{3}{4}$ " I.D. DR5 Series Downrod.

Sloped Ceiling Application with standard hanging systems for slopes up to a maximum of 29°



The above kit as shown includes the mounting bracket, the angled ball assembly and locking pin. For fans that weigh in excess of 35lbs, simply use the hanging bracket that comes with the fan in the box (75lbs rating standard) and the kit's angled ball assembly and locking pin. (Fan model numbers F528, F529 and F531 do not apply because of their unique Downbridge™ hanging systems)

### Sloped Ceiling Installation

Minka-Aire® ceiling fans equipped with universal hanging systems may be hung from standard or vaulted ceilings up to 21° pitch.

When ordering SCA specify finish to match your needs.

### Finishes Available:

ABR, BCW, BG, BI, BK, BN, BNW, BS, BWH, CC, CF, CH, CPBR, CT, DBB, DKG, DRB, DRF, FB, FLP, GL, HT, IBR, IO, KA, LN, MCG, MG, MP, MW, ORB, PBL, PI, PN, PR, PW, RD, RRB, SI, SL, SLV, STW/GOW, SWH, TSP, VB, VP, VRT, WH, WHF

(PR - Primer finish ready for painting to match your ceiling)

## Pre-Wired Downbridge™ Kit (for use on F528 and F529 only)



DK36

## Downbridge™ Kit

Maximum length is 72"

(Size and Finish: See Page(s): 74)

## Downlink™ Kit (for use on F531 only)



DL39

## Downlink™ Kit

Maximum length is 72"

(Size and Finish: See Page(s): 74)

*Note: It is not possible to join Downbridge™ or Downlink™ kits together for hanging fans in excess of maximum kit lengths.*



## Downrod Coupler DR500 ( $\frac{3}{4}$ " I.D.)

For those occasions when you need to hang your ceiling fan on a longer than 72" downrod, simply use one of our downrod couplers (DR500) available in finishes to match all our fans and downrods. The coupler enables you to couple our  $\frac{3}{4}$ " downrods together and hang fans on total downrod lengths of up to 144".

## F738 Fan Only



## Internal Threaded Downrod

( $\frac{3}{4}$ " I.D.)

	BN	DK	ORB	WHF
DR1512	•	•	•	•
DR1518	•	•	•	•
DR1524	•	•	•	•
DR1536	•	•	•	•
DR1548	N/A	•	•	•
DR1560	N/A	•	•	•
DR1572	N/A	•	•	•

Downrod sizes of 48", 60" and 72" are currently not available in BN finish.

# Universal Light Kits



## K9500

Two Light  
Belcaro Walnut™  
60W Candelabra Base (Included)  
11 ¼" Dia. x 6 ½"H



## K9515-1

Three Light  
Frosted White  
40W Candelabra Base (Included)  
12 ¼" Dia. x 2 ½"H  
Includes Polished Nickel & White Caps



## K9515-2

Three Light  
Tea Stain  
40W Candelabra Base (Included)  
12 ¼" Dia. x 2 ½"H  
Includes Dark Brushed Bronze &  
Oil Rubbed Bronze Caps



## K9525-1

Three Light  
Frosted White  
40W Candelabra Base (Included)  
12 ¼" Dia. x 2 ½"H  
Includes Polished Nickel & White Caps



## K9525-2

Three Light  
Tea Stain  
40W Candelabra Base (Included)  
12 ¼" Dia. x 2 ½"H  
Includes Dark Brushed Bronze &  
Oil Rubbed Bronze Caps



## \* K9548

Three Light  
Etched Swirl  
60W Candelabra Base (Included)  
12" Dia. x 5"H



## K9380-1

Two Light  
French Scavo  
13W GU24 Spiral CFL Base (Included)  
11 ½" Dia. x 5 ½"H



## K9380-2

Two Light  
Excavation  
13W GU24 Spiral CFL Base (Included)  
11 ½" Dia. x 5 ½"H



Please Note: All Light Kits include Chain with Decorative Fob. (Not shown)

\* Additional Cap Finishes Available

# Universal Light Kits



**\* K9369-L**

Three Light  
Etched Swirl  
60W Candelabra Base (Included)  
13 1/4\"/>



**K9372-1**

Three Light  
Caspian™  
60W Candelabra Base (Included)  
13 1/4\"/>



**K9372-2**

Three Light  
Excavation  
60W Candelabra Base (Included)  
13 1/4\"/>



**K9372-3**

Three Light  
Parchment  
60W Candelabra Base (Included)  
13 1/4\"/>



**K9372-4**

Three Light  
Venetian Scavo  
60W Candelabra Base (Included)  
13 1/4\"/>



**K9372-5**

Three Light  
Alabaster Dust™  
60W Candelabra Base (Included)  
13 1/4\"/>



**\* K9363-L**

Three Light  
Etched Marble  
60W Candelabra Base (Included)  
13 1/4\"/>



**\* K9376-1**

Three Light  
Caspian™  
60W Candelabra Base (Included)  
16\"/>



**\* K9376-2**

Three Light  
Excavation  
60W Candelabra Base (Included)  
16\"/>

Please Note: All Light Kits Include Chain with Decorative Fob. (Not Shown)

**\* Additional Cap Finishes Available**



- |           |                     |               |                                     |
|-----------|---------------------|---------------|-------------------------------------|
| AC100     | Swirled Glass       | AC100-KA      | Kocoa                               |
| AC100-ABR | Antique Bronze      | AC100-MCG     | Mottled Copper with Gold Highlights |
| AC100-BCW | Belcaro Walnut™     | AC100-ORB     | Oil Rubbed Bronze                   |
| AC100-BS  | Brushed Steel       | AC100-PBL     | Provencal Blanc                     |
| AC100-BWH | Bone White          | AC100-PI      | Patina Iron                         |
| AC100-CT  | Cattera Bronze™     | AC100-PW      | Pewter                              |
| AC100-DBB | Dark Brushed Bronze | AC100-STW/GOW | Sterling Walnut™/Golden Walnut      |
| AC100-EX  | Excavation          | AC100-SWH     | Shell White                         |
| AC100-FB  | French Beige        | AC100-VRT     | Vintage Rust™                       |



**K9373**

One Light Opal Glass  
50W Mini-Can Xenon (Included)  
9 1/2" Dia. x 5 1/4"H  
For 30"/32" Sweep Fans



**K9374**

One Light Opal Glass  
50W Mini-Can Xenon (Included)  
10 1/2" Dia. x 5 1/4"H  
For 40"/44" Sweep Fans



**K9375**

One Light Opal Glass  
50W Mini-Can Xenon (Included)  
11 1/2" Dia. x 5 3/4"H  
For 50"/56" Sweep Fans



*Please Note: All Light Kits Include Chain with Decorative Fob. (Not Shown)*

**Wet Location**

**K9401**

Two Light Opal Glass  
13W GU24 Spiral CFL Bulbs (Included)  
10 1/2" Dia. x 5 1/2"H



**K9402**

One Light Opal Glass  
60W Candelabra Base (Included)  
7 3/4" Dia. x 8 1/2"H



**Finish Codes**

BCW	Belcaro Walnut™	ORB	Oil Rubbed Bronze
BS	Brushed Steel	SWH	Shell White
BWH	Bone White	VRT	Vintage Rust™
HT	Heritage™	WH/44	White
MW	Mossoro Walnut™		

# Universal Light Kits

## K37

Four Light  
40W Candelabra Base (Included)  
2 1/4" Side Shade  
13"Dia. x 6 1/2"H



K37-L-BCW

## K1

Four Light  
40W Candelabra Base (Included)  
2 1/4" Side Fitter  
11 3/4"Dia. x 3"H



K1-ABR



K1-L-BCW



K1-L-BS



K1-L-ORB



K1-L-SWH



K1-L-44

## K1099

One Light  
Opal Glass  
60W Candelabra Base (Included)  
8 1/2"Dia. x 6 3/4"H



K1099-1-L-44



## K9365-L-44 (Low Profile)

Three Light  
Etched Marble  
60W Candelabra Base (Included)  
12 1/2"Dia. x 4 1/2"H



## GC900 SET

Optional Crystal Set  
Available Only for the F900 Fan



## Finish Codes

ABR	Antique Bronze	BS	Brushed Steel	SWH	Shell White
BCW	Belcaro Walnut™	ORB	Oil Rubbed Bronze	WVH/44	White

Please Note: All Light Kits Include Chain with Decorative Fob. (Not Shown)





**K33**  
Three Light  
60W Candelabra Base (Included)  
2 1/4" Side Shade  
6 1/4"Dia. x 3 1/2"H



**K35**  
Three Light  
13W Spiral Medium Base  
(Included)  
2 1/4" Side Shade  
7 1/4"Dia. x 3 1/2"H



**Finish Codes**

ABR	Antique Bronze	KA	Kocoa	VP	Vineyard Patina
BCW	Belcaro Walnut™	MCG	Mottled Copper w/Gold	WH/44	White
BN	Brushed Nickel	ORB	Oil Rubbed Bronze		
BS	Brushed Steel	PBL	Provencal Blanc		
CC	Cognac	PI	Patina Iron		
DBB	Dark Brushed Bronze	PW	Pewter		
FB	French Beige	SWH	Shell White		

*Please Note: All Light Kits Include Chain with Decorative Fob. (Not Shown)*

# Universal Light Kits

## K34

Four Light  
13W Spiral Medium Base  
(Included)  
2 1/4" Side Shade  
11 3/4" Dia. x 2 3/4" H



K34-BCW



K34-BN




K34-BS



K34-CC



K34-DBB



K34-KA



K34-MCG



K34-ORB



K34-PI



K34-PW



K34-SWH



K34-44

## Finish Codes

BCW	Belcaro Walnut™	FB	French Beige	PI	Patina Iron
BN	Brushed Nickel	KA	Kocoa	PW	Pewter
BS	Brushed Steel	MCG	Mottled Copper w/Gold	SWH	Shell White
CC	Cognac	ORB	Oil Rubbed Bronze	VP	Vineyard Patina
DBB	Dark Brushed Bronze	PBL	Provencal Blanc	WH/44	White

*Please Note: All Light Kits Include Chain  
with Decorative Fob. (Not Shown)*



# Custom Light Kits



K9614-DBB



K9614-FB



K9614-MCG

## K9614

Three Light  
60W Candelabra Base (Included)  
2 1/4" Side Shade  
8 1/2"Dia. x 3 1/4"H

Compatible with the  
F614 Timeless Fans Only



K9614-ORB



K9614-PI



K9614-PW



K9659-BCW



K9659-DRF



K9659-FB

## K9659

Three Light  
60W Candelabra Base (Included)  
2 1/4" Side Shade  
7 1/2"Dia. x 3 1/2"H

Compatible with the  
F659 Classica Fans Only



K9659-MCG



K9659-PBL



K9659-PI

## Finish Codes


BCW	Belcaro Walnut™	FB	French Beige	PBL	Provencal Blanc
DBB	Dark Brushed Bronze	MCG	Mottled Copper w/Gold	PI	Patina Iron
DRF	Driftwood	ORB	Oil Rubbed Bronze	PW	Pewter

Please Note: All Light Kits Include Chain with Decorative Fob. (Not Shown)

# Accessory Fan Blades




**CW**  
Cherry Wood



**DC**  
Dark Cherry



**DM**  
Dark Maple



**DW**  
Dark Walnut



**LC**  
Light Cherry



**LM**  
Light Maple



**ML**  
Reversible  
Medium Oak



**MM**  
Medium Maple

## Fan Blade Compatibility Chart


Model	Fan Name	CW	DC	DM	DW	LC	LM	ML	MM	MO
F516	Concept™ I	N/A	N/A	FB216-DM	FB216-DW	N/A	N/A	N/A	N/A	N/A
F517	Concept™ I	N/A	N/A	FB217-DM	FB217-DW	N/A	N/A	N/A	N/A	N/A
F518	Concept™ II	N/A	N/A	FB216-DM	FB216-DW	N/A	N/A	N/A	N/A	N/A
F519	Concept™ II	N/A	N/A	FB217-DM	FB217-DW	N/A	N/A	N/A	N/A	N/A
F528	San Francisco®	FB106-CW	N/A	N/A	N/A	N/A	N/A	N/A	FB106-MM	N/A
F529	San Francisco®	FB106-CW	N/A	N/A	N/A	N/A	N/A	N/A	FB106-MM	N/A
F547	Contractor	N/A	N/A	FB103S-DM	FB103S-DW	FB103S-LC	FB103S-LM	FB103S-ML	FB103S-MM	N/A
F548	Contractor Uni-Pack	N/A	N/A	FB103S-DM	FB103S-DW	FB103S-LC	FB103S-LM	FB103S-ML	FB103S-MM	N/A
F562	Supra® 32"	N/A	FB422-DC	FB422-DM	FB422-DW	FB422-LC	FB422-LM	N/A	FB422-MM	N/A
F563	Supra® 44"	N/A	FB423-DC	FB423-DM	FB423-DW	FB423-LC	FB423-LM	N/A	FB423-MM	N/A
F568	Supra® 52"	N/A	FB424-DC	FB424-DM	FB424-DW	FB424-LC	FB424-LM	N/A	FB424-MM	N/A
F588	Ultra-Max™ 54"	FB107T-CW	N/A	N/A	FB107T-DW	FB107T-LC	N/A	N/A	FB107T-MM	N/A
F589	Sundowner®	N/A	N/A	FB107P-DM	FB107P-DW	N/A	N/A	N/A	FB107P-MM	N/A
F596	Cirque™	Optional Blades Sets are the FB196-RYB (Multi-colored, Red, Yellow, Blue) and the FB196-MG (Mahogany Finish)								




**MO**  
Medium Oak



**NM**  
Natural Maple



**NW**  
Natural Walnut




**RW**  
High Gloss  
Rosewood




**SL**  
Silver



**SWH**  
Shell White



**WO**  
Washed Oak



**WP**  
Weathered Pine

## Fan Blade Compatibility Chart

Model	Fan Name	NM	NP	NW	ORB	RW	SL	SWH	WO	WP
F516	Concept™ I	N/A	N/A	N/A	FB216-ORB	N/A	N/A	N/A	N/A	N/A
F517	Concept™ I	N/A	N/A	N/A	FB217-ORB	N/A	N/A	N/A	N/A	N/A
F518	Concept™ II	N/A	N/A	N/A	FB216-ORB	N/A	N/A	N/A	N/A	N/A
F519	Concept™ II	N/A	N/A	N/A	FB217-ORB	N/A	N/A	N/A	N/A	N/A
F528	San Francisco®	N/A	N/A	N/A	N/A	N/A	FB106-SL	N/A	N/A	N/A
F529	San Francisco®	N/A	N/A	N/A	N/A	N/A	FB106-SL	N/A	N/A	N/A
F547	Contractor	FB103S-NM	N/A	FB103S-NW	N/A	FB103S-RW	FB103S-SL	FB103S-SWH	FB103S-WO	FB103S-WP
F548	Contractor Uni-Pack	FB103S-NM	N/A	FB103S-NW	N/A	FB103S-RW	FB103S-SL	FB103S-SWH	FB103S-WO	FB103S-WP
F562	Supra® 32"	N/A	N/A	FB422-NW	N/A	N/A	FB422-SL	N/A	FB422-WO	FB422-WP
F563	Supra® 44"	N/A	N/A	FB423-NW	N/A	N/A	FB423-SL	N/A	FB423-WO	FB423-WP
F568	Supra® 52"	N/A	N/A	FB424-NW	N/A	N/A	FB424-SL	FB424-SWH	FB424-WO	FB424-WP
F588	Ultra-Max™ 54"	N/A	FB107T-NP	FB107T-NW	N/A	FB107T-RW	N/A	N/A	FB107T-WO	FB107T-WP
F589	Sundowner®	N/A	N/A	N/A	N/A	N/A	N/A	FB107P-SWH	N/A	N/A
F596	Cirque™	Optional Blades Sets are the FB196-RYB (Multi-colored, Red, Yellow, Blue) and the FB196-MG (Mahogany Finish)								

# 2 1/4" Glass Shades



**2010**

Frosted/Ribbed  
4 1/4" Dia. x 5"H



**2018A**

Opal  
4 3/4" Dia. x 4 1/2"H



**\* 2548**

Etched Opal  
5 3/4" Dia. x 4 1/2"H



**\* 2549**

Etched Marble  
5 3/4" Dia. x 4 1/2"H



**\* 2560**

Frosted/Clear  
5" Dia. x 4 3/4"H



**2565**

Etched Seeded  
4 3/4" Dia. x 4 3/4"H



**2567**

Etched Marble  
5 1/4" Dia. x 4 3/4"H



**\* 2593-1**

Aged Champagne  
5" Dia. x 5 1/4"H

\* An Original Minka Group® Design





\* 2593-2

Excavation  
5"Dia. x 5 1/4"H



\* 2593-4

Venetian Scavo  
5"Dia. x 5 1/4"H



\* 2593-5

French Cream  
5"Dia. x 5 1/4"H



2632

Salon Scavo™  
5"Dia. x 4 3/4"H



2636

Tuscan Scavo  
5"Dia. x 4 3/4"H



2645

Linen  
5"Dia. x 5 1/4"H



2646

Tuscan Scavo  
5"Dia. x 5 1/4"H



2648

Etched Marble with Toned Edges  
5 1/2"Dia. x 5"H



4099

4" Opal Glass Shade  
8 1/2"Dia. x 5 1/2"H

# Bulb Reference



**Watts: 10W / 20W**  
XENON JCX 12V  
G4 BI-PIN BASE

Frosted JX4-20 (20W)  
Clear JX4C-10 (10W)  
JX4C-20 (20W)



**Watts: 35W / 50W**  
XENON JCX 12V  
GY6.35 BI-PIN BASE

Frosted JX6-35 (35W)  
JX6-50 (50W)



**Watts: 25W / 35W / 40W / 60W / 75W**  
G9 XENON 120V  
G9 BASE

Frosted JX9-025 (25W)  
JX9-035 (35W)  
JX9-040 (45W)  
JX9-060 (60W)  
JX9-075 (75W)  
Clear JX9C-025 (25W)  
JX9C-040 (40W)



**Watts: 20W / 50W**  
XENON 120V  
DC (BAYONET)

JXB15-20 (20W)  
JXB15-50 (50W)



**Watts: 75W**  
XENON 120V  
E12 (CANDELABRA) BASE

Frosted JDXF-12-075 (75W)



**Watts: 50W / 75W / 100W**  
MINI-CAN XENON 120V  
E11 (CANDELABRA) BASE

Frosted JDX-050 (50W)  
JDX-75 (75W)



**Watts: 50W / 75W / 100W**  
MINI-CAN HALOGEN 120V  
E11 (CANDELABRA) BASE

Frosted JD-50 (50W)  
JD-75 (75W)  
JD-100 (100W)  
Clear JDC-50 (50W)  
JDC-75 (75W)  
JDC-100 (100W)



**Watts: 50W**  
JDD XENON 120V  
E12 (CANDELABRA) BASE

JDX2-050 (50W) Clear  
JDX2F-050 (50W) Frosted



**Watts: 100W / 150W**  
78MM 120V DOUBLE ENDED  
HALOGEN (J-TYPE)  
R7S BASE

JB-100 (100W)  
JB-150 (150W)



**Watts: 8W DC / 10W AC**  
LED MODULE

L-L8-MD590  
L-AC10-MODULE



**Watts: 50W**  
PAR16 HALOGEN  
E26 (MEDIUM) BASE

PAR16-50 (50W)



**Watts: 35W / 50W**  
XENON JCX 12V  
GU10 BASE

JGU-035 (35W)  
JGU-50 (50W)



**Watts: 20W / 35W / 50W**  
HALOGEN MR16  
GX5.3 BI-PIN BASE

Clear JMR16-C-20 (20W 12V)  
JMR16-C-35 (35W 12V)  
JMR16-C-50 (50W 12V)  
Frosted JMR16-20 (20W 120V)  
JMR16-35 (35W 120V)  
JMR16-50/120V (50W 120V)



**Watts: 13W / 26W**  
SPIRAL CFL  
E26 (MEDIUM) BASE

FLB-13S (13W)



**Watts: 13W / 26W**  
SPIRAL CFL  
GU24 BASE

FLB-13M (13W)  
FLB-26M (26W)



**Watts: 18W / 26W**  
SQUAT SPIRAL CFL  
GU24 BASE

FLS-18M (18W)  
FLS-26M (26W)



**Watts: 40W**  
FERRO  
E26 (MEDIUM) BASE

E26-FW1910-40W (40W)



**Watts: 40W / 60W / 100W**  
T10 120V  
E26 (MEDIUM) BASE

Clear JT10-040C (40W)  
JT10-060C (60W)  
JT10-100C (100W)  
Frosted JT10-060F (60W)



**Watts: 27W**  
FULL 24 CFL  
GX10q-4 BASE

JT4-27 (27W)



**Watts: 13W**  
4-PIN (PL-C)  
G24q-1 BASE

FLT-13Q (13W)



**Watts: 27W**  
CFL  
GX10q-4 BASE

JT2-27 (27W)



**Watts: 32W**  
FC12T9 T9 CIRCULINE  
G10Q

FLC-22 (22W)  
FLC-32 (32W)  
FLC-40 (40W)



**Watts: 8W / 13W**  
FLUORESCENT  
T5 G13 BI-PIN BASE

Ballast: BLST08-T5  
JT5-8  
JT5-13



**Watts: 7W**  
C7 CFL  
E12 (CANDELABRA) BASE

FLB-07C (7W)



**Watts: 75W**  
MR16  
E17 BASE

JDR-75 (75W)



**Watts: 40W / 60W**  
B10.5  
E12 (CANDELABRA) BASE



**Watts: 60W**  
BR30  
E26 (MEDIUM) BASE



**Watts: 40W / 60W**  
A15  
E26 (MEDIUM) BASE



**Watts: 40W / 60W / 75W / 100W**  
A19  
E26 (MEDIUM) BASE



**Watts: 150W**  
A21 (3-WAY)  
E26 (MEDIUM) BASE



**Watts: 25W / 40W / 60W**  
G16 1/2  
E12 (CANDELABRA) BASE



**Watts: 60W / 100W**  
G25  
E26 (MEDIUM) BASE



**Watts: 60W / 100W**  
G30  
E26 (MEDIUM) BASE



**Watts: 40W / 60W / 100W**  
G40  
E26 (MEDIUM) BASE

## ACCESSORIES

AC100	230
AC100-ABR	230
AC100-BCW	230
AC100-BS	230
AC100-BWH	230
AC100-CT	230
AC100-DBB	230
AC100-EX	230
AC100-FB	230
AC100-KA	230
AC100-MCG	230
AC100-ORB	230
AC100-PBL	230
AC100-PI	230
AC100-PW	230
AC100-STW/GOW	230
AC100-SWH	230
AC100-VRT	230
GC900 SET	109, 232

## ACCESSORY BLADES

FB103S-DM	236
FB103S-DW	236
FB103S-LC	236
FB103S-LM	236
FB103S-ML	236
FB103S-MM	236
FB103S-NM	237
FB103S-NW	237
FB103S-RW	237
FB103S-SL	237
FB103S-SWH	237
FB103S-WO	237
FB103S-WP	237
FB106-CW	236
FB106-MM	236
FB106-SL	237
FB107P-DM	236
FB107P-DW	236
FB107P-MM	236
FB107P-SWH	237
FB107T-CW	236
FB107T-DW	236
FB107T-LC	236
FB107T-MM	236
FB107T-NP	237
FB107T-NW	237
FB107T-RW	237
FB107T-WO	237
FB107T-WP	237

FB196-MG	78, 236, 237
FB196-RYB	79, 236, 237
FB216-DM	236
FB216-DW	236
FB216-ORB	237
FB217-DM	236
FB217-DW	236
FB217-ORB	237
FB422-DC	236
FB422-DM	236
FB422-DW	236
FB422-LC	236
FB422-LM	236
FB422-MM	236
FB422-NW	237
FB422-SL	237
FB422-WO	237
FB422-WP	237
FB423-DC	236
FB423-DM	236
FB423-DW	236
FB423-LC	236
FB423-LM	236
FB423-MM	236
FB423-NW	237
FB423-SL	237
FB423-WO	237
FB423-WP	237
FB424-DC	236
FB424-DM	236
FB424-DW	236
FB424-LC	236
FB424-LM	236
FB424-MM	236
FB424-NW	237
FB424-SL	237
FB424-SWH	237
FB424-WO	237
FB424-WP	237

## CEILING FANS

F300-BN	100
F300-ORB	100
F302-BN	120
F302-RRB	120
F315-KA	101
F315-SL	101
F402-BNW	119, 162
F402-ORB	119, 162
F470-BN	172
F470-ORB	173

F470-WH	173
F474-ORB	146
F474-WH	146
F476-ORB	125
F476-WH	125
F477-BNW	123
F477-ORB	122
F477-WH	122
F502-BCW	115
F502-PBL	115
F510-BS	90
F510-ORB	91
F510-WH	90
F513-BN	92
F513-KA	93
F513-ORB	92
F513-WH	93
F514-BN	82
F514-ORB	82
F514-WH	83
F516-BN	67
F516-ORB	66
F516-PN	67
F516-WH	66
F517-BN	67
F517-ORB	66
F517-PN	67
F517-WH	66
F518-BN	64
F518-ORB	65
F518-PN	65
F518-WH	64
F519-BN	62
F519-MG	63
F519-ORB	62
F519-PN	62
F519-WH	63
F521-ABD	70
F521-ORB	70
F521-WHF	71
F522-BN	168
F522-BWH	169
F522-ORB	169
F522-ORB/TS	168
F522-WH	169
F523-ABD	142
F523-ORB	142
F523-WHF	143
F524-ABD	54
F524-DK	55

F524-ORB	55
F524-WHF	55
F528-L-BS/CH	74
F529-L-BS/CH	75
F529-L-ORB	74
F531-L-BN	72
F531-L-BN/MG	73
F531-L-WH	72
F532-BNW	127
F532-BWH	126
F532-DRF	127
F532-ORB	127
F533-BN	170
F533-BWH	171
F533-DK	170
F533-ORB	171
F533-WH	170
F539-BCW	104
F539-BN	105
F539-ORB	105
F544-BCW	114
F544-GBZ	114
F546-BS	218
F546-BS/DW	219
F546-ORB	218
F546-WH	219
F547-ABR	216
F547-BS	217
F547-BS/DW	217
F547-BWH	217
F547-ORB	216
F547-WH	217
F548-BS	214
F548-BS/DW	215
F548-BWH	214
F548-ORB	212
F548-ORB/EX	213
F548-WH	212
F556-BN	206
F556-BN/DW	207
F556-BWH	206
F556L-BN	204
F556L-BN/DW	205
F556L-BWH	204
F556L-ORB	205
F556-ORB	207
F562-BS	203
F562-ORB	203
F562-WH	202
F563-BS	200

# Index

F563-BS/DW . . . . .	200
F563-ORB . . . . .	201
F563-SP . . . . .	198
F563-SP-BS/DW . . . . .	198
F563-SP-ORB . . . . .	199
F563-SP-WH . . . . .	199
F563-WH . . . . .	201
F565-WH . . . . .	220
F566-WH . . . . .	220
F568-BCW . . . . .	196
F568-BS . . . . .	197
F568-BS/DW . . . . .	195
F568-BWH . . . . .	194
F568-KA . . . . .	194
F568-ORB . . . . .	197
F568-SWH . . . . .	195
F568-WH . . . . .	196
F569-BS . . . . .	192
F569-BS/DW . . . . .	193
F569-ORB . . . . .	192
F569-WH . . . . .	193
F571-DRF . . . . .	160
F571-ORB . . . . .	160
F571-WH . . . . .	160
F572-ORB . . . . .	161
F572-WH . . . . .	161
F574-BNW . . . . .	147
F577-BNW . . . . .	124
F579-L-BNW . . . . .	140
F579-L-ORB . . . . .	141
F580-VR/BB . . . . .	129
F581-BG . . . . .	154
F581-ORB . . . . .	155
F581-WHF . . . . .	155
F582-BNW . . . . .	130
F582-GL . . . . .	131
F582-ORB . . . . .	130
F588-SP-BCW . . . . .	191
F588-SP-BN . . . . .	190
F588-SP-BWH . . . . .	191
F588-SP-WH . . . . .	190
F589-BI/AI . . . . .	159
F589-BWH . . . . .	156
F589-DRF . . . . .	157
F589-HT . . . . .	158
F589-MW . . . . .	157
F589-ORB . . . . .	156
F589-SWH . . . . .	157
F589-VRT . . . . .	159
F589-WH . . . . .	158

F593-ORB . . . . .	89, 151
F593-PW . . . . .	88, 150
F593-WH . . . . .	89, 151
F594-ORB . . . . .	86, 148
F594-PW . . . . .	87, 149
F594-WH . . . . .	87, 149
F596-BN . . . . .	78, 79
F596-PN/TL . . . . .	79
F598-BN . . . . .	85
F598-ORB . . . . .	84
F598-WH . . . . .	85
F601-BS/BN . . . . .	98
F601-BS/MG . . . . .	98
F601-ORB . . . . .	99
F601-PN . . . . .	99
F602-BN/CH . . . . .	118
F602-RRB . . . . .	118
F603-BN . . . . .	81
F603-ORB . . . . .	80
F603-WH . . . . .	80
F614-DBB . . . . .	176
F614-FB . . . . .	178
F614-MCG . . . . .	177
F614-ORB . . . . .	179
F614-PI . . . . .	177
F614-PW . . . . .	178
F617-BN . . . . .	23
F617-GM . . . . .	22
F617-ORB/AB . . . . .	23
F617-WH . . . . .	22
F620-BCW . . . . .	175
F620-BN . . . . .	174
F620-DBB . . . . .	175
F620-ORB . . . . .	174
F622-BWH . . . . .	166
F622-ORB . . . . .	166
F622-ORB/TS . . . . .	167
F622-PW . . . . .	167
F647-BS . . . . .	208
F647-ORB . . . . .	209
F647-ORB/TS . . . . .	209
F647-SWH . . . . .	208
F647-WH . . . . .	209
F648-BS . . . . .	210
F648-ORB . . . . .	211
F648-ORB/EX . . . . .	211
F648-WH . . . . .	211
F659-BCW . . . . .	189
F659-DRF . . . . .	189
F659-FB . . . . .	189

F659-PBL . . . . .	188
F659-PI . . . . .	189
F672-MBK/BN . . . . .	103
F672-ORB . . . . .	102
F672-ORB/AB . . . . .	103
F672-WH/BN . . . . .	102
F680-BG . . . . .	153
F680-KA . . . . .	152
F688-DBB . . . . .	183
F688-KA . . . . .	182
F688-PW . . . . .	182
F688-WH . . . . .	183
F689-DBB . . . . .	181
F689-KA . . . . .	180
F689-PW . . . . .	180
F689-WH . . . . .	181
F695-CC . . . . .	187
F695-KA . . . . .	186
F695-VP . . . . .	187
F695-WH . . . . .	187
F696-CC . . . . .	184
F696-KA . . . . .	184
F696-VP . . . . .	185
F696-WH . . . . .	185
F701-DRB . . . . .	94
F701-DRF . . . . .	95
F701-KA . . . . .	95
F701-PN . . . . .	95
F701-PW . . . . .	94
F702-BCW . . . . .	113
F702-VB . . . . .	112
F705-STW . . . . .	110
F705-TSP . . . . .	110
F707-FLP . . . . .	108
F711-DRB . . . . .	96
F711-PN . . . . .	97
F711-PW . . . . .	97
F715-STW . . . . .	111
F715-TSP . . . . .	111
F726-BN/ORG . . . . .	13
F726-BN/SL . . . . .	12
F726-ORB/AB . . . . .	14
F726-ORB/BN . . . . .	15
F726-WHF/BN . . . . .	13, 14
F733-BK/RW . . . . .	48
F733-BS/BN . . . . .	50
F733-PN . . . . .	50
F733-SL . . . . .	49
F733-WH . . . . .	51
F734-GL . . . . .	139

F734-ORB . . . . .	138
F734-SI . . . . .	139
F737-BN . . . . .	60
F737-ORB . . . . .	60
F737-WH . . . . .	61
F738-BN . . . . .	52
F738-DK . . . . .	53
F738-ORB . . . . .	52
F738-WHF . . . . .	53
F745-BN . . . . .	25
F745-DK . . . . .	24
F745-ORB . . . . .	25
F753-BNW . . . . .	68, 145
F753-KA . . . . .	68, 144
F753-PN . . . . .	69
F753-WHF . . . . .	69, 145
F759-PBL . . . . .	188
F802-BN/CH . . . . .	117
F802-KA . . . . .	116
F802-ORB . . . . .	117
F803-BK . . . . .	39
F803-CPBR . . . . .	37
F803-DK . . . . .	34
F803-LN . . . . .	34
F803-MG . . . . .	35
F803-MP . . . . .	39
F803-RD . . . . .	36
F803-SL . . . . .	37
F803-TL . . . . .	38
F803-WH . . . . .	38
F812-IO . . . . .	107
F820-CT . . . . .	106
F820-IBR . . . . .	106
F823-DK . . . . .	40
F823-MG . . . . .	42
F823-MP . . . . .	43
F823-SL . . . . .	43
F823-WH . . . . .	41
F824-BK/CH . . . . .	77
F824-ORB/TB . . . . .	76
F824-WH . . . . .	77
F828-BN . . . . .	26
F828-BN/DW . . . . .	27
F828-BN/WH . . . . .	27
F828-ORB . . . . .	26
F828-WHF . . . . .	26
F833-BK . . . . .	59
F833-RD . . . . .	58
F833-SL . . . . .	59
F833-WH . . . . .	58

F840-CF . . . . .	128
F843-DK . . . . .	47
F843-SL . . . . .	46
F843-WH . . . . .	47
F844-DK . . . . .	44
F844-SL . . . . .	45
F844-WH . . . . .	45
F853-BN/DK . . . . .	28
F853-BN/MM . . . . .	31
F853-BN/SL . . . . .	31
F853-RW . . . . .	29
F853-WH . . . . .	30
F887-72-BN . . . . .	17
F887-72-ORB . . . . .	20
F887-80-BN . . . . .	17
F887-80-ORB . . . . .	20
F887-88-BN . . . . .	17
F887-88-ORB . . . . .	20
F887-96-BN . . . . .	17
F887-96-ORB . . . . .	20
F888-BNW . . . . .	32
F888-DK . . . . .	33
F888-ORB . . . . .	33
F888-WHF . . . . .	33
F889-BNW . . . . .	133
F889-ORB . . . . .	137
F889-SI . . . . .	135
F900-BCW . . . . .	109
F905-DK . . . . .	57
F905-SL . . . . .	56
F905-WH . . . . .	57
F1000-BN . . . . .	163, 164
F1000-ORB . . . . .	165
F1000-WH . . . . .	165

**CEILING MEDALLIONS**

CM1550-FLP . . . . .	108
CM7022-STW . . . . .	110
CM7022-TSP . . . . .	110
CM7038-STW . . . . .	111
CM7038-TSP . . . . .	111
CM8222-IBR . . . . .	106

**CONTROL SYSTEMS**

RC400 . . . . .	222
RC500 . . . . .	222
RC600 . . . . .	222
RCS212 . . . . .	222
RCS213 . . . . .	222
RCS223 . . . . .	222
WC105-WH . . . . .	223

WC106-WH . . . . .	223
WC110 . . . . .	223
WCS212 . . . . .	223
WCS213 . . . . .	223
WCS223 . . . . .	223

**GLASS SHADES**

2010 . . . . .	238
2018A . . . . .	238
2548 . . . . .	238
2549 . . . . .	238
2560 . . . . .	238
2565 . . . . .	238
2567 . . . . .	238
2593-1 . . . . .	238
2593-2 . . . . .	239
2593-4 . . . . .	239
2593-5 . . . . .	239
2632 . . . . .	239
2636 . . . . .	239
2645 . . . . .	239
2646 . . . . .	239
2648 . . . . .	239
4099 . . . . .	239

**HANGING SYSTEMS**

A180 . . . . .	226, 227, 228
A245 . . . . .	226, 227
A245-BN . . . . .	228
DK06 . . . . .	226, 227
DK24 . . . . .	226, 227
DK36 . . . . .	226, 227, 228
DK48 . . . . .	226, 227
DK60 . . . . .	226, 227
DK72 . . . . .	226, 227
DL06 . . . . .	226, 227
DL15 . . . . .	226, 227
DL27 . . . . .	226, 227
DL39 . . . . .	226, 227, 228
DL51 . . . . .	226, 227
DL63 . . . . .	226, 227
DL75 . . . . .	226, 227
DR235 . . . . .	73
DR500 . . . . .	226, 227, 228
DR512 . . . . .	226, 227
DR518 . . . . .	226, 227
DR524 . . . . .	226, 227
DR536 . . . . .	226, 227
DR548 . . . . .	226, 227
DR560 . . . . .	226, 227
DR572 . . . . .	226, 227

DR1512 . . . . .	228
DR1518 . . . . .	228
DR1524 . . . . .	228
DR1536 . . . . .	228
DR1548 . . . . .	228
DR1560 . . . . .	228
DR1572 . . . . .	228

**LIGHT KITS - CUSTOM**

K9614-DBB . . . . .	235
K9614-FB . . . . .	235
K9614-MCG . . . . .	235
K9614-ORB . . . . .	235
K9614-PI . . . . .	235
K9614-PW . . . . .	235
K9659-BCW . . . . .	235
K9659-DRF . . . . .	235
K9659-FB . . . . .	235
K9659-MCG . . . . .	235
K9659-PBL . . . . .	235
K9659-PI . . . . .	235

**LIGHT KITS - UNIVERSAL**

K1-ABR . . . . .	232
K1-L-44 . . . . .	232
K1-L-BCW . . . . .	232
K1-L-BS . . . . .	232
K1-L-ORB . . . . .	232
K1-L-SWH . . . . .	232
K33-L-44 . . . . .	233
K33-L-BS . . . . .	233
K33-L-DBB . . . . .	233
K33-L-FB . . . . .	233
K33-L-MCG . . . . .	233
K33-L-ORB . . . . .	233
K33-L-PI . . . . .	233
K34-44 . . . . .	234
K34-BCW . . . . .	234
K34-BN . . . . .	234
K34-BS . . . . .	234
K34-CC . . . . .	234
K34-DBB . . . . .	234
K34-KA . . . . .	234
K34-MCG . . . . .	234
K34-ORB . . . . .	234
K34-PI . . . . .	234
K34-PW . . . . .	234
K34-SWH . . . . .	234
K35-44 . . . . .	233
K35-BCW . . . . .	233
K35-BN . . . . .	233





K35-BS . . . . .	233
K35-CC . . . . .	233
K35-DBB . . . . .	233
K35-FB . . . . .	233
K35-KA . . . . .	233
K35-MCG . . . . .	233
K35-ORB . . . . .	233
K35-PBL . . . . .	233
K35-PI . . . . .	233
K35-PW . . . . .	233
K35-SWH . . . . .	233
K35-VP . . . . .	233
K37-L-BCW . . . . .	232
K1099-1-L-44 . . . . .	232
K9363-L . . . . .	230
K9365-L-44 . . . . .	232
K9369-L . . . . .	230
K9372-1 . . . . .	230
K9372-2 . . . . .	230
K9372-3 . . . . .	230
K9372-4 . . . . .	230
K9372-5 . . . . .	230
K9373-L-BS . . . . .	231
K9373-L-ORB . . . . .	231
K9373-L-WH . . . . .	231
K9374-L-BS . . . . .	231
K9374-L-WH . . . . .	231
K9375-L-BS . . . . .	231
K9375-L-BWH . . . . .	231
K9375-L-ORB . . . . .	231
K9375-L-WH . . . . .	231
K9376-1 . . . . .	230
K9376-2 . . . . .	230
K9380-1 . . . . .	229
K9380-2 . . . . .	229
K9401-L-BWH . . . . .	231
K9401-L-DRF . . . . .	231
K9401-L-HT . . . . .	231
K9401-L-MW . . . . .	231
K9401-L-ORB . . . . .	231
K9401-L-VRT . . . . .	231
K9401-L-WH . . . . .	231
K9402-L-44 . . . . .	231
K9402-L-ORB . . . . .	231
K9500 . . . . .	229
K9515-1 . . . . .	229
K9515-2 . . . . .	229
K9525-1 . . . . .	229
K9525-2 . . . . .	229
K9548 . . . . .	229

# Room Size and Ceiling Height Recommendations










## ROOM SIZE

These measurements are for general air flow requirements only. Decorating plans or aesthetic considerations should influence your fan choices beyond these room size specifications. For very large rooms, multiple fans is an option.

				
<b>Blade Sweep</b>	26"-42"	44"	52"-54"	60"-72"
<b>Approximate Room Size</b>	6' x 8' 40-60 sq. ft.	8' x 10' 70-90 sq. ft.	10' x 12' 100-150 sq. ft.	12' x 15' (Great Room) Over 160 sq. ft.

## CEILING HEIGHT

Be sure there is at least 7 feet of clearance under your ceiling fan blades. The standard 3½" and 6" downrods should work in most 8 feet ceiling installations. This will position the blades far enough from the ceiling to have enough "supply" air above the blades to provide good air movement. If greater floor to fan clearance is needed, some fans can use our low ceiling adapter (A180) without using any downrod. However, air movement is reduced using the low ceiling adapter. This chart shows recommended downrod lengths for various ceiling heights.

	Downrod Length Needed						
	12"	18"	24"	36"	48"	60"	72"
9'							
10'							
12'							
14'							
16'							
18'							
20'							



# Notes



# Notes

# Notes

Lined area for notes, featuring horizontal ruling lines and a large, faint, curved graphic element on the left side.

		Page Number	Blade Sweep	No. of Blades	Blade Pitch	Motor Size (m/m)	RPM (Hi/Low)	Warranty	Light Kit	Downrods ¾" I.D.	Downrods ½" I.D.	Lead Wire	Dimensions A	Dimensions B	Hanging Weight
F300	Retro Style Fan	100	10"	3	14°	70 x 70	1253/1525	One Year	N/A	N/A	N/A	72"	N/A	N/A	6 lbs
F302	Gyrette™	120	10"	8	14°	82 x 25	1555/1328	Lifetime	N/A	4½"	N/A	54"	14"	18"	18 lbs
F315	Hassock Aire	101	12"	3	14°	N/A	N/A	One Year	N/A	N/A	N/A	112"	N/A	N/A	15 lbs
F402	Gyro™ Wet	119,162	42"	6	20°	82 x 25	1360/720	Lifetime	Integrated	3½" & 6"	N/A	80"	18½"	17"	28 lbs
F470	Hilo	172-173	52"	5	12°	153 x 17	173/69	Lifetime	N/A	3½" & 6"	N/A	80"	16"	9½"	18 lbs
F474	Concept™ II Wet 52"	146-147	52"	3	14°	188 x 20	168/90	Lifetime	Integrated	N/A	N/A	8"	11¾"	9"	26 lbs
F476	Concept™ I Wet 52"	124-125	52"	3	14°	188 x 20	166/91	Lifetime	Integrated	3½" & 6"	N/A	80"	15½"	13¾"	26 lbs
F477	Concept™ I Wet 58"	122-123	58"	3	14°	188 x 22	171/102	Lifetime	Integrated	3½" & 6"	N/A	80"	15"	12"	30 lbs
F502	Traditional Gyro™	115	42"	6	20°	80 x 25	1360/720	Lifetime	Integrated	3½" & 12"	N/A	80"	19¾"	16½"	35 lbs
F510	Spacesaver	90-91	26"	3	14°	153 x 12	392/120	Lifetime	Integrated	N/A	N/A	8"	11"	6¼"	11 lbs
F513	New Era	92-93	52"	4	14°	172 x 16	199/64	Lifetime	Adaptable	3½" & 6"	N/A	80"	13"	11¾"	18 lbs
F514	Zen	82-83	52"	4	14°	172 x 16	187/63	Lifetime	Integrated	3½" & 6"	N/A	80"	16¼"	11¾"	23 lbs
F516	Concept™ I 44"	66-67	44"	3	14°	153 x 15	190/80	Lifetime	Integrated	3½" & 6"	N/A	80"	15"	13"	21 lbs
F517	Concept™ I 52"	66-67	52"	3	14°	172 x 20	180/70	Lifetime	Integrated	3½" & 6"	N/A	80"	15"	13"	25 lbs
F518	Concept™ II 44"	64-65	44"	3	14°	153 x 15	184/86	Lifetime	Integrated	N/A	N/A	8"	11½"	9½"	23 lbs
F519	Concept™ II 52"	62-63	52"	3	14°	172 x 20	179/70	Lifetime	Integrated	N/A	N/A	8"	11½"	9½"	26 lbs
F521	Aluma	70-71	52"	4	12°	153 x 15	160/63	Lifetime	Integrated	3½" & 6"	N/A	80"	13½"	11¾"	20 lbs
F522	Mojo	168-169	52"	5	12°	153 x 15	162/60	Lifetime	Included	3½" & 6"	N/A	80"	17½"	12¼"	27 lbs
F523	Aluma Wet	142-143	52"	4	12°	153 x 20	160/63	Lifetime	Integrated	3½" & 6"	N/A	80"	13"	11"	23 lbs
F524	Roto	54-55	52"	3	22°	153 x 15	212/74	Lifetime	N/A	3½" & 6"	N/A	80"	10½"	9"	20 lbs
F528	San Francisco®	74	56"	3	13°	172 x 17	200/72	Lifetime	N/A	N/A	12" DB	6"	20¾"	18¾"	19 lbs
F529	San Francisco®	74-75	56"	3	13°	172 x 17	200/72	Lifetime	Integrated	N/A	12" DB	6"	23½"	18½"	22 lbs
F531	Flyte®	72-73	56"	3	14°	188 x 25	180/80	Lifetime	Integrated	N/A	9" DL	80"	18"	17½"	26 lbs
F532	Sunseeker	126-127	60"	5	14°	188 x 25	133/48	Lifetime	Integrated	3½" & 6"	N/A	80"	13¾"	13½"	30 lbs
F533	Mojo II	170-171	52"	4	14°	153 x 15	166/82	Lifetime	Integrated	N/A	N/A	12"	13"	7½"	22 lbs
F539	Great Room Traditional	104-105	72"	5	14°	212 x 25	120/60	Lifetime	Adaptable	3½" & 6"	N/A	80"	13"	12¼"	30 lbs
F544	Calais™	114	52"	5	14°	172 x 17	170/65	Lifetime	Integrated	N/A	N/A	8"	12"	8"	28 lbs
F546	Contractor 42"	218-219	42"	5	12°	153 x 10	240/106	Lifetime	Adaptable	4"	N/A	80"	11½"	9¼"	11 lbs
F547	Contractor 52"	216-217	52"	4/5	12°	153 x 13	162/67	Lifetime	Adaptable	4"	N/A	80"	12¾"	10¼"	13 lbs
F548	Contractor Uni-Pack	208-215	52"	5	12°	153 x 13	160/56	Lifetime	Included	4"	N/A	80"	17½"	9¾"	17 lbs
F556	Contractor Plus	206-207	52"	5	12°	153 x 15	160/155	Lifetime	Adaptable	3½" & 6"	N/A	80"	12¼"	10½"	17 lbs
F556L	Contractor LED	204-205	52"	5	12°	153 x 15	160/155	Lifetime	Adaptable	3½" & 6"	N/A	80"	13"	10¾"	17 lbs
F562	Supra® 32"	202-203	32"	6	22°	153 x 16	262/95	Lifetime	Adaptable	3½" & 6"	N/A	80"	12½"	12"	14 lbs
F563	Supra® 44"	200-201	44"	5	14°	188 x 15	259/79	Lifetime	Adaptable	3½" & 6"	N/A	80"	12½"	12"	18 lbs
F563	Supra® 44" -SP	198-199	44"	5	14°	188 x 15	259/79	Lifetime	Included	3½" & 6"	N/A	80"	16½"	12"	20 lbs
F565	Mesa™ 52"	220	52"	5	12°	153 x 14	175/64	Lifetime	Adaptable	N/A	N/A	8"	8¾"	7¾"	14 lbs
F566	Mesa™ 42"	220	42"	5	12°	153 x 10	215/108	Lifetime	Adaptable	N/A	N/A	8"	8"	6¾"	11 lbs
F568	Supra® 52"	194-197	52"	5	14°	188 x 15	181/54	Lifetime	Adaptable	3½" & 6"	N/A	80"	13"	11¼"	21 lbs
F569	Supra® 52"	192-193	52"	5	14°	188 x 15	170/50	Lifetime	Included	3½" & 6"	N/A	80"	16¾"	12¼"	25 lbs
F571	Sundance™ 52"	160	52"	5	12°	153 x 15	170/70	Lifetime	Adaptable	3½" & 6"	N/A	80"	12"	12¾"	16 lbs
F572	Sundance™ 42"	161	42"	5	12°	153 x 10	210/95	Lifetime	Adaptable	3½" & 6"	N/A	80"	12¼"	10½"	12 lbs
F574	Concept™ II Wet 52"	146-147	52"	3	14°	188 x 20	158/80	Lifetime	Integrated	N/A	N/A	8"	11¾"	9"	26 lbs
F577	Concept™ I Wet 52"	124-125	52"	3	14°	188 x 20	158/80	Lifetime	Integrated	3½" & 6"	N/A	80"	15½"	13¾"	26 lbs
F579	Magellan®	140-141	60"	5	16°	188 x 25	135/62	Lifetime	Included	3½" & 6"	N/A	80"	16½"	8½"	27 lbs
F580	Shangri-La®	129	52"	5	14°	188 x 20	169/57	Lifetime	Included	3½" & 6"	N/A	80"	21¾"	13¼"	33 lbs
F581	Gauguin™	154-155	52"	4	14°	188 x 20	140/70	Lifetime	Integrated	3½" & 6"	N/A	80"	14"	14¾"	27 lbs
F582	Rainman™	130-131	54"	5	14°	172 x 20	145/70	Lifetime	Integrated	3½" & 6"	N/A	80"	24"	13½"	27 lbs
F588	Ultra-Max™ -SP	190-191	54"	5	14°	188 x 25	182/76	Lifetime	Adaptable	3½" & 6"	N/A	80"	12"	9½"	20 lbs
F589	Sundowner®	156-159	54"	5	16°	188 x 20	166/53	Lifetime	Adaptable	3½" & 6"	N/A	80"	12"	11¼"	28 lbs
F593	Traditional Concept™ 44"	88-89	44"	3	14°	153 x 17	195/83	Lifetime	Integrated	N/A	N/A	8"	11"	7½"	23 lbs
F594	Traditional Concept™ 52"	86-87	52"	3	14°	172 x 20	180/70	Lifetime	Integrated	N/A	N/A	8"	11"	7½"	26 lbs

SPECIFICATIONS

Minka-Aire® ceiling fans are warranted to be free from defects in material and workmanship only if purchased from an authorized Minka-Aire® distributor:

Fan motor - Limited Lifetime Warranty to original purchaser with proof of purchase as long as fan remains in its original installation location and is installed using only the original hardware provided (including hanger bracket).

All other parts & controls - warranted to original purchaser with proof of purchase for one (1) year from date of purchase.

		Page Number	Blade Sweep	No. of Blades	Blade Pitch	Motor Size (m/m)	RPM (H/L/ov)	Warranty	Light Kit	Downrods ¾" I.D.	Downrods ½" I.D.	Lead Wire	Dimensions A	Dimensions B	Hanging Weight
F596	Cirque™	78-79	54"	6	14°	188 x 25	125/65	Lifetime	Integrated	4" & 6"	N/A	80"	15"	10½"	26 lbs
F598	Airus™	84-85	54"	5	14°	188 x 18	183/65	Lifetime	Integrated	3½" & 6"	N/A	80"	14"	10"	26 lbs
F601	Acero™	98-99	52"	3	14°	188 x 15	183/74	Lifetime	Integrated	3½" & 6"	N/A	80"	13¾"	11½"	24 lbs
F602	Gyro™	118	42"	6	20°	82 x 25	1360/720	Lifetime	Integrated	3½" & 6"	N/A	80"	13¾"	16"	28 lbs
F603	Como™	80-81	54"	5	14°	188 x 20	170/70	Lifetime	Integrated	3½" & 6"	N/A	80"	13¾"	12¼"	28 lbs
F614	Timeless	176-179	54"	5	14°	188 x 15	161/57	Lifetime	Adaptable	3½" & 6"	N/A	80"	14"	12¾"	22 lbs
F617	Raptor	22-23	60"	5	14°	DC172 x 12	150/60	Lifetime	Integrated	3½" & 6"	N/A	80"	15¼"	8½"	29 lbs
F620	Bolo™	174-175	52"	5	14°	172 x 17	170/70	Lifetime	Included	3½" & 6"	N/A	80"	20"	11½"	29 lbs
F622	Traditional Mojo	166-167	52"	5	12°	153 x 15	162/60	Lifetime	Included	3½" & 6"	N/A	80"	15"	9½"	23 lbs
F647	Contractor Uni-Pack	208-209	52"	5	12°	153 x 13	162/67	Lifetime	Included	4"	N/A	80"	17¾"	10½"	15 lbs
F648	Contractor Uni-Pack	210-211	52"	5	12°	153 x 15	180/60	Lifetime	Included	4"	N/A	80"	18¾"	9½"	17 lbs
F659	Classica	188-189	54"	5	14°	172 x 16	187/63	Lifetime	Adaptable	3½" & 6"	N/A	80"	14"	11¾"	24 lbs
F672	Iconic™	102-103	60"	5	12°	188 x 20	160/57	Lifetime	Integrated	3½" & 6"	N/A	80"	16¾"	14½"	35 lbs
F680	Terrana	152-153	52"	2	14°	172 x 17	145/68	Lifetime	Integrated	3½" & 6"	N/A	80"	15"	14"	33 lbs
F688	Kola	182-183	52"	5	12°	172 x 14	168/64	Lifetime	Adaptable	3½" & 6"	N/A	80"	13¼"	11"	22 lbs
F689	Kola-XL	180-181	60"	5	14°	188 x 20	145/64	Lifetime	Adaptable	3½" & 6"	N/A	80"	13¼"	11"	22 lbs
F695	Kafé	186-187	52"	5	12°	172 x 14	168/64	Lifetime	Adaptable	3½" & 6"	N/A	80"	13"	11"	22 lbs
F696	Kafé-XL	184-185	60"	5	14°	188 x 20	145/64	Lifetime	Adaptable	3½" & 6"	N/A	80"	13"	11"	22 lbs
F701	Delano®	94-95	52"	5	14°	172 x 20	172/74	Lifetime	Integrated	3½" & 6"	N/A	80"	15½"	8¾"	26 lbs
F702	Volterra™	112-113	52"	5	14°	172 x 20	172/74	Lifetime	Integrated	3½" & 6"	N/A	80"	15¼"	8½"	26 lbs
F705	Napoli™	110	56"	5	14°	188 x 25	144/81	Lifetime	Integrated	3½" & 12"	N/A	80"	16¼"	10¾"	40 lbs
F707	Salon Grand™	108	56"	5	14°	188 x 25	144/81	Lifetime	Integrated	3½" & 10"	N/A	80"	16¼"	7¼"	38 lbs
F711	Delano® II	96-97	52"	5	14°	172 x 20	155/75	Lifetime	Integrated	N/A	N/A	8"	11¾"	8"	23 lbs
F715	Napoli™ II	111	68"	5	14°	212 x 25	110/50	Lifetime	Integrated	3½" & 12"	N/A	80"	16¼"	10"	46 lbs
F726	Spectre	12-15	60"	4	14°	DC188 x 10	120/50	Lifetime	Integrated	3½" & 6"	N/A	80"	14½"	11"	22 lbs
F733	Gilera	48-51	62"	3	14°	212 x 25	100/45	Lifetime	N/A	3½" & 6"	N/A	80"	14"	14½"	35 lbs
F734	Strata	138-139	52"	4	12°	172 x 17	153/60	Lifetime	Integrated	3½" & 6"	N/A	80"	15"	13"	19 lbs
F737	Moda	60-61	60"	3	20°	DC188 x 14	152/53	Lifetime	N/A	3½" & 6"	N/A	80"	12"	12½"	35 lbs
F738	Pancake	52-53	52"	4	12°	153 x 18	180/70	Lifetime	N/A	6"	N/A	12"	9¾"	8¾"	19 lbs
F745	Sabot	24-25	52"	5	12°	DC172 x 12	150/65	Lifetime	Integrated	3½" & 6"	N/A	80"	9½"	7¾"	19 lbs
F753	Java	68-69	54"	3	14°	153 x 18	169/75	Lifetime	N/A	3½" & 6"	N/A	80"	12½"	11½"	19 lbs
F759	Classica Gallery Edition	188	54"	5	14°	172 x 16	187/63	Lifetime	Adaptable	3½" & 6"	N/A	80"	18¼"	10½"	26 lbs
F802	Vintage Gyro™	116-117	42"	6	20°	82 x 25	1360/720	Lifetime	Integrated	3½" & 6"	N/A	80"	15½"	18½"	28 lbs
F803	Artemis™	34-39	58"	3	Variable	188 x 25	135/75	Lifetime	Integrated	3½" & 6"	N/A	80"	13"	11½"	25 lbs
F812	Lineage™	107	54"	5	14°	188 x 25	144/81	Lifetime	Integrated	3½" & 6"	N/A	80"	13½"	12½"	40 lbs
F820	Santa Lucia™	106	60"	5	14°	188 x 25	146/70	Lifetime	Integrated	3½" & 6"	N/A	80"	18"	13¼"	39 lbs
F823	Wing	40-43	52"	1	Variable	DC125 x 30	150/50	Lifetime	N/A	6"	N/A	80"	10¾"	10"	11 lbs
F824	Uchiwa	76-77	56"	3	20°	172 x 25	130/70	Lifetime	Integrated	3½" & 6"	N/A	80"	18¼"	10¼"	26 lbs
F828	Symbio	26-27	60"	5	13°	DC125 x 30	150/50	Lifetime	Integrated	3½" & 6"	N/A	80"	15½"	13¼"	25 lbs
F833	Kewl	58-59	52"	3	22°	153 x 15	201/46	Lifetime	N/A	3½" & 6"	N/A	80"	11"	8¾"	19 lbs
F840	Craftsman™	128	52"	5	14°	172 x 20	180/75	Lifetime	Included	3½" & 6"	N/A	80"	21¼"	13¼"	31 lbs
F843	Wave	46-47	52"	3	48°	172 x 14	153/61	Lifetime	N/A	4½" & 6"	N/A	80"	13"	9½"	19 lbs
F844	Light Wave	44-45	52"	3	48°	172 x 14	139/57	Lifetime	Integrated	4½" & 6"	N/A	80"	13½"	11½"	20 lbs
F853	Aviation	28-31	60"	3	Variable	DC120 x 25	115/44	Lifetime	N/A	3½" & 6"	N/A	80"	12"	10½"	19 lbs
F887	Xtreme	16-21	88"	9	4°	DC165 x 12	80/50	Lifetime	N/A	3½" & 6"	N/A	80"	15"	13½"	50 lbs
F888	Slipstream	32-33	65"	8	14°	DC165 x 25	98/50	Lifetime	Integrated	3½" & 6"	N/A	80"	14"	11½"	35 lbs
F889	Slipstream XXL	132-137	84"	8	14°	DC165 x 25	90/50	Lifetime	Integrated	3½" & 6"	N/A	80"	15½"	10¼"	45 lbs
F900	Cristafano™	109	68"	5	14°	212 x 25	112/52	Lifetime	Integrated	3½" & 6"	N/A	80"	14"	13"	29 lbs
F905	Artemis™ XL5	56-57	62"	5	28°	DC172 x 25	91/50	Lifetime	Integrated	3½" & 6"	N/A	80"	16½"	13¾"	35 lbs
F1000	Dyno	164-165	52"	5	14°	153 x 17	170/62	Lifetime	Integrated	3½" & 6"	N/A	80"	12"	10¼"	19 lbs

\* Dimensions A & B were measured with the shortest downrod enclosed with the fan (See the Finish Codes page for Picture Diagrams)

\*\* F601 dimensions A & B were measured without light kit

\*\*\* All Conventional Motors are 16 Poles





# Finish Codes


## Minka-Aire® / Minka-Lavery® Finish Compatibility Chart

Minka-Lavery®	Minka-Aire®
	AB Antique Brass
	ABD Brushed Aluminum
126	BCW Belcaro Walnut™
	BG Bahama Beige™
	BI/AI Black Iron with Aged Iron Accents
66	BK Black
84	BN Brushed Nickel
	BNW Brushed Nickel Wet
	BS Brushed Steel
	BWH Bone White
	CC Cognac
	CF Craftsman™
77	CH Chrome
	CPBR Copper Bronze
	CT Cattera Bronze™
267C	DBB Dark Brushed Bronze
	DK Distressed Koa
	DKG Distressed Koa with Gold Highlights
37B	DRB Dark Restoration Bronze™
	DRF Driftwood
	FB French Beige
477	FLP Florence Patina™
355	GBZ Golden Bronze
	GL Galvanized
	GM Gun Metal
94	HT Heritage™
177	IBR Illuminati Bronze™
357	IO Iron Oxide
	KA Kocoa
	LN Liquid Nickel
	MBK Matte Black
	MCG Mottled Copper with Gold Highlights
	MG Mahogany Finish
	MP Maple Finish
	MW Mossoro Walnut™
	ODK Outdoor Distress Koa
143	ORB Oil Rubbed Bronze
	ORG Orange
648	PBL Provencal Blanc
573	PI Patina Iron
613	PN Polished Nickel
	PW Pewter
	RD Red
37	RRB Restoration Bronze™
	RW Rosewood
172	SI Smoked Iron
	SL Silver
	STW Sterling Walnut™
	SWH Shell White
	TB Toned Brass
	TL Translucent
196C	TSP Tuscan Patina™
	VB Volterra Bronze™
	VP Vineyard Patina
61	VRT Vintage Rust™
44	WH White
	WHF Flat White
	YW Yellow

Dimensions A and B were measured with the shortest downrod enclosed with the fan.



Minka-Aire® ceiling fans are suitable for year-round use and can contribute to your comfort in the summer and winter. With our reverse switch, in the winter you will be able to move the heat from your ceiling and circulate the air in your living area. In the summer you will save energy by recirculating air from the outside into your room and also if your air conditioning is used, save on energy costs.



We Support



Member



Graphic Design: Minka Group® Graphics  
Product Originals: Minka Group®

Product specifications subject to change at any time.

Minka-Aire®, A Minka Group® Company  
Catalog MKACAT2015-04  
Printed in U.S.A.  
© 1993-2015 Minka Lighting, Inc.



World Headquarters

1151 West Bradford Court, Corona, California 92882

Showroom

Dallas Market Center

2100 Stemmons, Suite 3725, Dallas, TX 75207

951.278.3267 (FANS) 800.307.3267 Fax: 951.278.2828

[sales@minkagroup.net](mailto:sales@minkagroup.net) | [www.minkaaire.net](http://www.minkaaire.net) | [www.minkagroup.net](http://www.minkagroup.net)

\$10.00