


Busway Flex-A-Power™ Busway

Type DH
Plugs

Section 13

Unfused - Type TB Three-Phase, Four-Wire, Single-Phase, Three-Wire


Amperage	Voltage	Product Number
60	600	DHIP4TB2



Type TB

Unfused - Type TB Three-Phase, Three-Wire

Amperage	Voltage	Product Number
60	600	DHIP3TB2



Circuit Breaker Plugs - Type TQL Single-Phase, Three-Wire

Amperage	Frame Type	Voltage	Product Number
15-50	TQL	240 Max	DFPTQL3N
15-50	TQLX	240 Max	DFPTQLX3N
15-50	TQLR	240 Max	DFPTQLR3N
15-50	TQLRC	240 Max	DFPTQLRC4 ¹

(With Space Only for Three THQL Breaker Poles)

Order breakers separately.

¹“C” in Product Number indicates screw tightening housing clips.


Handle-Operated Type TQL

Circuit Breaker Plugs - Type TQL Three-Phase, Three-Wire

Amperage	Frame Type	Voltage	Product Number
15-50	TQL	240 Max	DFPTQL3
15-50	TQLX	240 Max	DFPTQLX3
15-50	TQLR	240 Max	DFPTQLR3

(With Space Only for Three THQL Breaker Poles)

Order breakers separately.



Type TQLR with Receptacle Provision


Circuit Breaker Plugs - Type TQL Three-Phase, Four-Wire

Amperage	Frame Type	Voltage	Product Number
15-50	TQL	240 Max	DFPTQL4
15-50	TQLX	240 Max	DFPTQLX4
15-50	TQLR	240 Max	DFPTQLR4
15-50	TQLC	240 Max	DFPTQLC4 ¹
15-50	TQLRC	240 Max	DFPTQLRC4 ¹

(With Space Only for Three THQL Breaker Poles)

Order breakers separately.

¹“C” in Product Number indicates screw tightening housing clips.




Type TQLX Externally Operated Handle

Circuit Breaker Plugs - Type TE Single-Phase, Three-Wire

Amperage	Frame Type	Voltage	Product Number
15-70	TE	600 Max	DFPTE3N
15-70	TEX	600 Max	DFPTEX3N
15-70	TER	600 Max	DFPTER3N

(With Space Only for Three TEB or TED4 Breaker Poles)

Order breakers separately.




Handle-Operated TE

Circuit Breaker Plugs - Type TE Three-Phase, Three-Wire

Amperage	Frame Type	Voltage	Product Number
15-70	TE	600 Max	DFPTE3
15-70	TEX	600 Max	DFPTEX3
15-70	TER	600 Max	DFPTER3

(With Space Only for Three TEB or TED4 Breaker Poles)

Order breakers separately.




TER with Receptacle Provision

Circuit Breaker Plugs - Type TE Three-Phase, Four-Wire

Amperage	Frame Type	Voltage	Product Number
15-70	TE	600 Max	DFPTE4
15-70	TEX	600 Max	DFPTEX4
15-70	TER	600 Max	DFPTER4
15-70	TEC	600 Max	DFPTEC4
15-70	TERC	600 Max	DFPTERC4

(With Space Only for Three TEB or TED4 Breaker Poles)

Order breakers separately.



TEX Externally Operated Handle

