

VAST



P2550-0930K shown with Brushed Nickel blades

Beautiful and expansive in design, the 72" Vast ceiling fan is ideal for use in large areas and outdoor covered areas for maximum cooling. A white opal shade complements a variety of finish options, including Brushed Nickel with Chrome accents, Antique Bronze or White with Chrome Accents.

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC motor
- Aluminum blades
- White opal glass
- Remote control with batteries is included

SIZE

72" dia., 16-3/4" ht.
80" lead wires

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2550-0930K

Brushed Nickel shown
with Chrome Accents
with Brushed Nickel blades



Brushed Nickel



P2550-2030K

Antique Bronze shown
with Antique Bronze blades




Antique Bronze



P2550-3030K

White shown
with Chrome Accents
and White blades



White



ENERGY INFORMATION AT HIGH SPEED

AIRFLOW:	7,982 cubic feet per minute
ELECTRICITY USE:	28 watts (excludes lights)
AIRFLOW EFFICIENCY:	285 cubic feet per minute per watt

LAMPING INFORMATION

18w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.

PROGRESSLIGHTING.COM



Fan



Light



Damp
Indoor/Outdoor



Full Function Remote Control Included
Full-range dimming for light
Six-speed fan operation
Reverse direction control