



FEISS®

EST. 1955



DELIVERING A WIDE ARRAY OF UNIQUELY BEAUTIFUL, STYLISH AND CLASSIC LIGHTING COLLECTIONS

ICONS



ADA COMPLIANT

Meets the Americans with Disabilities Act parameter of maximum 4" extension



DAMP LOCATION

Listed for damp locations



WET LOCATION

Listed for wet locations



STONESTRONG

Constructed with a unique synthetic composition engineered to withstand even the harshest environmental conditions, and backed by a 5-year warranty

TABLE OF CONTENTS

CATALOG INTRODUCTION

VISUAL INDEX	2
--------------	----------

MAIN CATEGORIES

CHANDELIER COLLECTIONS	4
PENDANTS	11
WALL SCONCES	14
BATH/VANITY	17
OUTDOOR	20

RESOURCES

INDEX BY ITEM	24
FINISHES	24
HARDWARE	24

FEISS®

EST. 1955

VISUAL INDEX

CHANDELIER COLLECTIONS

ALLIER 6



Weathered Oak Wood / Antique Forged Iron

LINE EXTENSION

GANNET 4



Weathered Oak Wood / Antique Forged Iron

GREENBRIER 10



Iron Oxide

HARROW 8



Polished Nickel or Oil Rubbed Bronze

LINE EXTENSION

NORI 7



Dark Weathered Zinc / Driftwood Grey

LINE EXTENSION

PENDANTS

BAYLOR 12



Oil Rubbed Bronze or Satin Nickel

LAWLER 13



Burnished Brass or Satin Nickel

LINE EXTENSION

LORAS 11



Chrome or Dark Weathered Iron

LINE EXTENSION

WALL SCONCES

HEWITT 14



Antique Bronze or Polished Nickel

QUINN 16



Antique Bronze or Polished Nickel

SILO 15



Antique Bronze or Polished Nickel

BATH/VANITY

MERCER 17



Chrome

VOLO 18



Chrome

OUTDOOR

COTSWOLD LANE 20



Black

NEWPORT 22



Painted Brushed Steel

LINE EXTENSION

GANNET

GANNET'S STORY

The new Gannet Collection exudes rustic charm with a two-tone finish of painted, distressed Weathered Oak on an Antique Forged Iron metal frame. Crisp edges and bold lines pair with open, airy frames on the sides and crown to soften this classic lantern silhouette.

GANNET DETAIL

Weathered Oak Wood Finish



F3192/6WOW/AF
6-Light Chandelier

Canopy



Linear Canopy



F3191/4WOW/AF
4-Light Chandelier



F3190/4WOW/AF
4-Light Chandelier




F3193/5WOW/AF
5-Light Island Chandelier



WB1877WOW/AF
1-Light Wall Sconce

GANNET Weathered Oak Wood & Antique Forged Iron (WOW/AF)

PRODUCT #	DESCRIPTION	BULB TYPE	BULB QTY.	DIMENSIONS	NOTES
F3190/4WOW/AF	4-Light Chandelier	60 W Cand.	4 Bulbs	L:12" W:12" H:17" Adj. H: 20.5"- 62.5"	(3) 12" Stems & (1) 6" Stems, 15' of wire
F3191/4WOW/AF	4-Light Chandelier	60 W Cand.	4 Bulbs	L:18" W:18" H:26.75" Adj. H: 30.25"- 84.25"	(4) 12" Stems & (1) 6" Stems, 15' of wire
F3192/6WOW/AF	6-Light Chandelier	60 W Cand.	6 Bulbs	L:25.5" W:25.5" H:36" Adj. H: 39.5"- 93.5"	(4) 12" Stems & (1) 6" Stems, 15' of wire
F3193/5WOW/AF	5-Light Island Chandelier	60 W Med.	5 Bulbs	L:50" W:14" H:14.625" Adj. H: 17.5"- 71.5"	(8) 12" Stems & (2) 6" Stems, 15' of wire
WB1877WOW/AF	1-Light Wall Sconce	60 W Cand.	1 Bulb	W:8.625" H:14.125" E:4.625"	Height from center of outlet box up: 7.125", 8" of wire



ALLIER

FOR COMPLETE ALLIER COLLECTION, SEE OUR 2017 FULL LINE CATALOG (PG. 134)

Canopy



ALLIER'S STORY

A new, large-scale 38" diameter globe has been added to the popular Allier Collection, named for a French forest from which wood is used for wine barrels. Each fixture is made of aged oak, which is kiln-dried to prevent cracking. The combination of natural wood with metal hardware in a modern globe silhouette makes an elegantly rustic statement.



F3186/6WOW/AF
6-Light Chandelier

LINE EXTENSION | ALLIER



ALLIER Weathered Oak Wood & Antique Forged Iron (WOW/AF)

PRODUCT #	DESCRIPTION	BULB TYPE	BULB QTY.	DIMENSIONS	CHAIN	NOTES
F3186/6WOW/AF	6-Light Chandelier	60 W Cand.	6 Bulbs	D:38" H:40.875"	5'	15' of wire

NORI



F3187/4DWZ/DWG
4-Light Chandelier

Canopy



NORI'S STORY

Three new fixtures expand the Nori Collection and feature the same vintage elements as the original chandelier, like beautifully cascading Driftwood Grey Wood beads and the rustic flair of our Dark Weathered Zinc finish. On all the chandeliers, a large Driftwood Grey Wood bead suspends from the center of the frame, adding an elegant finishing touch. Exposed candelabra lamping completes the time-worn feel.

NORI DETAIL

Driftwood Grey Wood Beads



F3129/6DWZ/DWG
6-Light Chandelier



F3188/3DWZ/DWG
3-Light Chandelier



WB1875DWZ/DWG
2-Light Wall Sconce

NORI Dark Weathered Zinc & Driftwood Grey (DWZ/DWG)

PRODUCT #	DESCRIPTION	BULB TYPE	BULB QTY.	DIMENSIONS	CHAIN	NOTES
F3129/6DWZ/DWG	6-Light Chandelier	60 W Cand.	6 Bulbs	D:32.5" H:34.5"	5'	15' of wire
F3187/4DWZ/DWG	4-Light Chandelier	60 W Cand.	4 Bulbs	D:17.125" H:29"	5'	15' of wire
F3188/3DWZ/DWG	3-Light Chandelier	60 W Cand.	3 Bulbs	D:14.75" H:24"	5'	15' of wire
WB1875DWZ/DWG	2-Light Wall Sconce	60 W Cand.	2 Bulbs	W:11" H:19.625" E:5.75"		Height from center of outlet box up:15.625", 8" of wire



FINISH / Oil Rubbed Bronze (ORB) or Polished Nickel (PN), **MATERIALS** / Clear Seeded Glass

HARROW

FOR COMPLETE HARROW COLLECTION, SEE OUR 2017 FULL LINE CATALOG (PG. 120)

HARROW'S STORY

Three new fixtures expand the Harrow Collection, bringing the same beautiful design aesthetic to a drum silhouette, available in a pendant and a semi-flushmount design. Slumped, clear seeded glass panels are secured in a sleek frame, with either a Polished Nickel or Oil Rubbed Bronze finish.

HARROW DETAIL

Clear Seeded Glass



F3199/4ORB
4-Light Pendant



F3199/4PN
4-Light Pendant

Canopy



SF342ORB

3-Light Semi Flush Mount



SF342PN

3-Light Semi Flush Mount



SF341ORB

2-Light Semi Flush Mount



SF341PN

2-Light Semi Flush Mount

HARROW Polished Nickel (PN) or Oil Rubbed Bronze (ORB)

PRODUCT #	DESCRIPTION	BULB TYPE	BULB QTY.	DIMENSIONS	NOTES
F3199/4ORB	4-Light Pendant	60 W Med.	4 Bulbs	D:19.625" H:9.875" Adj. H: 13.625"- 67.625"	(4) 12" Stems & (1) 6" Stems, 15' of wire
F3199/4PN	4-Light Pendant	60 W Med.	4 Bulbs	D:19.625" H:9.875" Adj. H: 13.625"- 67.625"	(4) 12" Stems & (1) 6" Stems, 15' of wire
SF341ORB	2-Light Semi Flush Mount	60 W Med.	2 Bulbs	D:15" H:10.125"	8" of wire
SF341PN	2-Light Semi Flush Mount	60 W Med.	2 Bulbs	D:15" H:10.125"	8" of wire
SF342ORB	3-Light Semi Flush Mount	60 W Med.	3 Bulbs	D:19.625" H:10.125"	8" of wire
SF342PN	3-Light Semi Flush Mount	60 W Med.	3 Bulbs	D:19.625" H:10.125"	8" of wire

PN

ORB

HARROW | LINE EXTENSION

GREENBRIER

Canopy




GREENBRIER'S STORY

The gently curved, overlapping straps of the new Greenbrier Collection take inspiration from tall grasses gently sweeping in the wind across an open prairie field and provide a stunning contrast to the open panes, crisp edges and clean lines of the outer frame. Our new Iron Oxide finish gives the collection a farmhouse look and feel.

GREENBRIER DETAIL

New! Iron Oxide Finish



F3197/610
6-Light Chandelier



F3195/410
4-Light Chandelier



F3196/310
3-Light Chandelier

GREENBRIER Iron Oxide (10)

PRODUCT #	DESCRIPTION	BULB TYPE	BULB QTY.	DIMENSIONS	NOTES
F3195/410	4-Light Chandelier	60 W Cand.	4 Bulbs	L:17" W:17" H:22.375" Adj. H: 26" - 68"	(4) 12" Stems & (1) 6" Stems, 15' of wire
F3196/310	3-Light Chandelier	60 W Cand.	3 Bulbs	L:12" W:12" H:15.25" Adj. H: 18.75" - 60.75"	(4) 12" Stems & (1) 6" Stems, 15' of wire
F3197/610	6-Light Chandelier	60 W Cand.	6 Bulbs	L:17" W:17" H:29.375" Adj. H: 33" - 75"	(4) 12" Stems & (1) 6" Stems, 15' of wire

LORAS


FOR COMPLETE LORAS COLLECTION, SEE OUR 2017 FULL LINE CATALOG (PG. 86)

Canopy



P1459CH

1-Light Pendant



P1459DWI

1-Light Pendant

LORAS' STORY

A large-scale pendant has been added to the beautiful Loras Collection and takes the same contemporary twist on vintage-inspired, industrial design as the rest of the collection. The new 1-light pendant is a stately 14" high, and the Clear Seeded Glass shade ensures any chosen medium base bulb will be a central accent to the overall look.

LORAS DETAIL

Clear Seeded Glass



LORAS Chrome (CH) or Dark Weathered Iron (DWI)

PRODUCT #	DESCRIPTION	BULB TYPE	BULB QTY.	DIMENSIONS	NOTES
P1459CH	1-Light Pendant	60 W Med.	1 Bulb	D:11.5" H:14.75" Adj. H: 18.25"- 60.25"	(3) 12" Stems & (1) 6" Stems, 15' of wire
P1459DWI	1-Light Pendant	60 W Med.	1 Bulb	D:11.5" H:14.75" Adj. H: 18.25"- 60.25"	(3) 12" Stems & (1) 6" Stems, 15' of wire



BAYLOR

Canopy




BAYLOR'S STORY


Taking inspiration from the generous vessel and slender neck of a vintage glass jug, the new Baylor pendants make their presence known in an understated way, with an eye-catching yet simple silhouette. Through the Clear Seeded glass shade, the exposed bulb is central to the overall look, so an Edison-style lamp is a perfect choice to reinforce that classic design.

BAYLOR DETAIL

Clear Seeded Glass



P1461ORB
1-Light Pendant



P1461SN
1-Light Pendant

NEW COLLECTIONS | BAYLOR

BAYLOR Oil Rubbed Bronze (ORB) or Satin Nickel (SN)

PRODUCT #	DESCRIPTION	BULB TYPE	BULB QTY.	DIMENSIONS	NOTES
P1461ORB	1-Light Pendant	60 W Med.	1 Bulb	D:12" H:17.25" Adj. H: 20.75" - 62.75"	(3) 12" Stems & (1) 6" Stems, 15' of wire
P1461SN	1-Light Pendant	60 W Med.	1 Bulb	D:12" H:17.25" Adj. H: 20.75" - 62.75"	(3) 12" Stems & (1) 6" Stems, 15' of wire

ORB

SN

LAWLER

FOR COMPLETE LAWLER COLLECTION, SEE OUR 2017 FULL LINE CATALOG (PG. 335)



F3155/3BBS
3-Light Pendant



F3155/3SN
3-Light Pendant



F3154/3BBS
3-Light Pendant



F3154/3SN
3-Light Pendant

Canopy




LAWLER'S STORY

The Lawler Collection is now offered in two additional finishes, Satin Nickel and Burnished Brass, to be offered alongside the original Chrome finish. Capturing the cozy charm of classic, historic bell and orb silhouettes, these pendants feature candelabra lamping suspended from the center to appear as if floating within the Clear glass shade.

LAWLER DETAIL

Burnished Brass Finish



LAWLER Burnished Brass (BBS) or Satin Nickel (SN)

PRODUCT #	DESCRIPTION	BULB TYPE	BULB QTY.	DIMENSIONS	CHAIN	NOTES
F3154/3BBS	3-Light Pendant	60 W Cand.	3 Bulbs	D:14.75" H:19"	5'	15' of wire
F3154/3SN	3-Light Pendant	60 W Cand.	3 Bulbs	D:14.75" H:19"	5'	15' of wire
F3155/3BBS	3-Light Pendant	60 W Cand.	3 Bulbs	D:16" H:16.75"	5'	15' of wire
F3155/3SN	3-Light Pendant	60 W Cand.	3 Bulbs	D:16" H:16.75"	5'	15' of wire

BBS

SN

HEWITT

HEWITT'S STORY

The new Hewitt Wall Sconce is a modern interpretation of the classic torchiere sconce, with a slim vertical profile cleverly affixed to a sleek cast arm detail. While the overall design aesthetic is understated, the 19" high fixture still makes a dramatic statement in either an Antique Bronze or Polished Nickel finish. A White, lined Parchment shade softly diffuses the light, producing a subtle, elegant glow.

HEWITT DETAIL

White, Lined Parchment Shade



WB1873ANBZ
1-Light Wall Sconce



WB1873PN
1-Light Wall Sconce

- ANBZ
- PN

HEWITT Antique Bronze (ANBZ) or Polished Nickel (PN)

PRODUCT #	DESCRIPTION	BULB TYPE	BULB QTY.	DIMENSIONS	NOTES
WB1873ANBZ	1-Light Wall Sconce	60 W Cand.	1 Bulb	W:5" H:19.5" E:5"	Height from center of outlet box up:12", 8" of wire
WB1873PN	1-Light Wall Sconce	60 W Cand.	1 Bulb	W:5" H:19.5" E:5"	Height from center of outlet box up:12", 8" of wire

SILO



WB1874ANBZ
1-Light Wall Sconce



WB1874PN
1-Light Wall Sconce

SILO'S STORY

The new Silo Wall Sconce makes a real statement with a vertical, cylindrical design true to its name. The 15" high fixture is crafted using a double-shade technique, with a Clear glass outer shade surrounding a Metal Mesh inner shade, creating a layered look with a rustic, yet refined quality. A square base and thoughtfully-positioned "arm" with clean, seamless edges secure the shade, which lifts up easily to enable quick re-lamping.

SILO DETAIL

Metal Mesh Insert



SILO Antique Bronze (ANBZ) or Polished Nickel (PN)

PRODUCT #	DESCRIPTION	BULB TYPE	BULB QTY.	DIMENSIONS	NOTES
WB1874ANBZ	1-Light Wall Sconce	60 W Cand.	1 Bulb	W:4.75" H:15" E:4"	Height from center of outlet box up: 7.5", 8" of wire
WB1874PN	1-Light Wall Sconce	60 W Cand.	1 Bulb	W:4.75" H:15" E:4"	Height from center of outlet box up: 7.5", 8" of wire

ANBZ

PN

QUINN

QUINN'S STORY

The new Quinn Wall Sconce is elegantly simple with contemporary flair, featuring bold, cast details like square arms with a crisp 90° square-edged transition, contrasted by a circular candle tube sitting atop a square bobèche. A delicate, White, lined Parchment shade softly diffuses the light. Overall, the angular profile achieves a tailored, modern look for those looking for an updated classic design.

QUINN DETAIL

White, Lined Parchment Shade



WB1872ANBZ
1-Light Wall Sconce



WB1872PN
1-Light Wall Sconce

QUINN Antique Bronze (ANBZ) or Polished Nickel (PN)

PRODUCT #	DESCRIPTION	BULB TYPE	BULB QTY.	DIMENSIONS	NOTES
WB1872ANBZ	1-Light Wall Sconce	60 W Cand.	1 Bulb	W:5" H:14.875" E:5"	Height from center of outlet box up: 12.375", 8" of wire
WB1872PN	1-Light Wall Sconce	60 W Cand.	1 Bulb	W:5" H:14.875" E:5"	Height from center of outlet box up: 12.375", 8" of wire

ANBZ

PN

MERCER



VS24303CH
3-Light Vanity

MERCER'S STORY

Modern details, like the clean square supports of the cross arm and the sleek rectangular backplate, are defining features of the new Mercer Collection. Bright Chrome hardware pairs with tapered Clear Seeded glass shades to complete the clean and tailored look.

MERCER DETAIL

Clear Seeded Glass



VS24304CH
4-Light Vanity



VS24302CH
2-Light Vanity



VS24301CH
1-Light Wall Sconce

MERCER Chrome (CH)

PRODUCT #	DESCRIPTION	BULB TYPE	BULB QTY.	DIMENSIONS	NOTES
VS24301CH	1-Light Wall Sconce	60 W Med.	1 Bulb	W:5" H:8.875" E:5.875"	Height from center of outlet box up: 3.75", 8" of wire
VS24302CH	2-Light Vanity	60 W Med.	2 Bulbs	W:12.5" H:8.875" E:6.875"	Height from center of outlet box up: 2.5", 8" of wire
VS24303CH	3-Light Vanity	60 W Med.	3 Bulbs	W:21.5" H:8.875" E:6.875"	Height from center of outlet box up: 2.5", 8" of wire
VS24304CH	4-Light Vanity	60 W Med.	4 Bulbs	W:28.625" H:8.875" E:6.875"	Height from center of outlet box up: 2.5", 8" of wire

CH

VOLO

VOLO'S STORY

The clean, modern design of the new Volo Collection features a delicate, clear glass-wrapped shade and an inner opal etched glass diffuser to provide a warm layered glow. The horizontal bar features a subtle knock-out detail in which each glass shade nests within the arm, creating a refined appearance, while the Chrome finish and a crisp square backplate complete the look. All hardware is cleverly hidden to ensure the sleek beauty of the fixtures.



VS24201CH
1-Light Wall Sconce



VS24202CH
2-Light Vanity



VS24203CH
3-Light Vanity



VS24204CH
4-Light Vanity

VOLO Chrome (CH)

PRODUCT #	DESCRIPTION	BULB TYPE	BULB QTY.	DIMENSIONS	NOTES
VS24201CH	1-Light Wall Sconce	40 W G9 Halogen (Included)	1 Bulb	W:5.625" H:6.5" E:6.25"	Height from center of outlet box up: 3.25", 8" of wire
VS24202CH	2-Light Vanity	40 W G9 Halogen (Included)	2 Bulbs	W:13.625" H:5.5" E:6.25"	Height from center of outlet box up: 3", 8" of wire
VS24203CH	3-Light Vanity	40 W G9 Halogen (Included)	3 Bulbs	W:22.5" H:5.5" E:6.25"	Height from center of outlet box up: 3", 8" of wire
VS24204CH	4-Light Vanity	40 W G9 Halogen (Included)	4 Bulbs	W:31" H:5.5" E:6.25"	Height from center of outlet box up: 3", 8" of wire

CH

COTSWOLD LANE

FOR COMPLETE COTSWOLD LANE COLLECTION, SEE OUR 2017 FULL LINE CATALOG (PG. 654)

COTSWOLD LANE'S STORY

A new glass option, Clear Seeded glass, can now be coupled with the Black finish in our supremely successful Cotswold Lane Collection. The classic design features dentil molding at the top of each pane of glass which adds to the more formal, traditional aesthetic of this antique gas lantern inspired outdoor collection.

COTSWOLD LANE DETAIL

Clear Seeded Glass



OL5424BK
3-Light Wall Lantern



OL5422BK
3-Light Wall Lantern



OL5421BK
2-Light Wall Lantern



OL5420BK
1-Light Wall Lantern



OL5431BK
3-Light Hanging Lantern



OL5432BK
3-Light Hanging Lantern



OL5428BK
3-Light Post Lantern



OL5427BK
3-Light Post Lantern



OL5423BK
2-Light Wall Lantern



OL5433BK
2-Light Flush Mount

COTSWOLD LANE Black (BK)

PRODUCT #	DESCRIPTION	BULB TYPE	BULB QTY.	DIMENSIONS	CHAIN	NOTES
OL5420BK	1-Light Wall Lantern	100 W Med.	1 Bulb	W:6.5" H:11.5" E:7.75"		Height from center of outlet box up: 3.5", 8" of wire
OL5421BK	2-Light Wall Lantern	60 W Cand.	2 Bulbs	W:9" H:20.5" E:11.625"		Height from center of outlet box up: 8.625", 8" of wire
OL5422BK	3-Light Wall Lantern	60 W Cand.	3 Bulbs	W:9.5" H:23.75" E:13.375"		Height from center of outlet box up: 10.5", 8" of wire
OL5423BK	2-Light Wall Lantern	60 W Cand.	2 Bulbs	W:9.5" H:16" E:6"		Height from center of outlet box up: 9.5", 8" of wire
OL5424BK	3-Light Wall Lantern	60 W Cand.	3 Bulbs	W:12" H:30" E:16.25"		Height from center of outlet box up: 12.875", 8" of wire
OL5427BK	3-Light Post Lantern	60 W Cand.	3 Bulbs	W:9.5" H:22.5"		8" of wire
OL5428BK	3-Light Post Lantern	60 W Cand.	3 Bulbs	W:12" H:27.5"		8" of wire
OL5431BK	3-Light Hanging Lantern	60 W Cand.	3 Bulbs	W:9.5" H:21.5"	5'	15' of wire
OL5432BK	3-Light Hanging Lantern	60 W Cand.	3 Bulbs	W:12" H:26.5"	5'	15' of wire
OL5433BK	2-Light Flush Mount	60 W Med.	2 Bulbs	W:11.5" H:6.625"		8" of wire



NEWPORT

**5 YEAR
WARRANTY**

NEWPORT'S STORY

The new nautical, coastal-inspired Newport Collection features lighthouse details including a vented top and a cylindrical cast frame surrounding an inner Opal Etched glass shade. Newport features our new Painted Brushed Steel outdoor finish and is comprised of StoneStrong material - a unique synthetic composition that is made tough enough to withstand harsh environmental conditions and boasts a 5-year warranty, making it an excellent choice for coastal applications.



OL14303PBS

2-Light Wall Lantern

WHAT IS STONESTRONG?

StoneStrong is an innovative, specially engineered composite material comprised of ground marble, emery and latex that are bonded together with industrial adhesive. The density of this unique synthetic material has twice the tensile strength of resin for maximum strength, durability and longevity. StoneStrong has the ability to withstand even the most harsh outdoor conditions, especially in Coastal areas.

KEY BENEFITS & FEATURES

- 5 Year Warranty
- Exquisite Molding for Highly Visible Detailing
- Superior Finish Adhesion
- RoHS Compliant (Restriction of Hazardous Substances Directive)
- High Tensile Strength
- Non-Corrosive
- UV-Resistant
- Acid & Alkali Resistance
- Fade Resistant
- Fire Retardant

FOR THE COMPLETE STONESTRONG COLLECTION, SEE OUR FULL LINE CATALOG (PG. 602)



BOYNTON



TOVE



URBANDALE



WELLFLEET

Canopy





OL14302PBS
 1-Light Wall Lantern





OL14301PBS
 1-Light Wall Lantern




OL14300PBS
 1-Light Wall Lantern




OL14309PBS
 1-Light Hanging Lantern




OL14307PBS
 1-Light Post Lantern

NEWPORT Painted Brushed Steel (PBS)

PRODUCT #	DESCRIPTION	BULB TYPE	BULB QTY.	DIMENSIONS	CHAIN	NOTES
OL14300PBS	1-Light Wall Lantern	75 W Med.	1 Bulb	W:6.25" H:9" E:7.625"		Height from center of outlet box up: 4.125", 8" of wire
OL14301PBS	1-Light Wall Lantern	75 W Med.	1 Bulb	W:7.5" H:13" E:8.875"		Height from center of outlet box up: 4.625", 8" of wire
OL14302PBS	1-Light Wall Lantern	75 W Med.	1 Bulb	W:9.25" H:15.875" E:10.875"		Height from center of outlet box up: 5.625", 8" of wire
OL14303PBS	2-Light Wall Lantern	75 W Med.	2 Bulbs	W:10.5" H:19.875" E:12.125"		Height from center of outlet box up: 6", 8" of wire
OL14307PBS	1-Light Post Lantern	75 W Med.	1 Bulb	D:9.25" H:18.5"		8" of wire
OL14309PBS	1-Light Hanging Lantern	75 W Med.	1 Bulb	D:9.25" H:18.5"	5'	15' of wire

PBS


INDEX BY ITEM

F3129/6 DWZ/DWG	7	F3199/4ORB	9	OL14303PBS	23	VS24301CH	17
F3154/3BBS	13	F3199/4PN	9	OL14307PBS	23	VS24302CH	17
F3154/3SN	13	OL5420BK	21	OL14309PBS	23	VS24303CH	17
F3155/3BBS	13	OL5421BK	21	P1459CH	11	VS24304CH	17
F3155/3SN	13	OL5422BK	21	P1459DWI	11	WB1872ANBZ	16
F3186/6WOW/AF	6	OL5423BK	21	P1461ORB	12	WB1872PN	16
F3187/4DWZ/DWG	7	OL5424BK	21	P1461SN	12	WB1873ANBZ	14
F3188/3DWZ/DWG	7	OL5427BK	21	SF341ORB	9	WB1873PN	14
F3190/4WOW/AF	5	OL5428BK	21	SF341PN	9	WB1874ANBZ	15
F3191/4WOW/AF	5	OL5431BK	21	SF342ORB	9	WB1874PN	15
F3192/6WOW/AF	5	OL5432BK	21	SF342PN	9	WB1875DWZ/DWG	7
F3193/5WOW/AF	5	OL5433BK	21	VS24201CH	19	WB1877WOW/AF	5
F3195/4IO	10	OL14300PBS	23	VS24202CH	19		
F3196/3IO	10	OL14301PBS	23	VS24203CH	19		
F3197/6IO	10	OL14302PBS	23	VS24204CH	19		

FINISH SWATCHES



Antique Forged Iron




Antique Bronze



Burnished Brass




Black




Chrome



Driftwood Grey




Dark Weathered Iron



Dark Weathered Zinc




Iron Oxide



Oil Rubbed Bronze




Painted Brushed Steel



Polished Nickel



Satin Nickel



Weathered Oak Wood

MOUNTING HARDWARE

All fixtures come with mounting hardware included. Below is a list of installation hardware that comes standard with all Feiss Fixtures.

CHAIN LENGTH

5' / 1 tier fixtures / or 30" or less in diameter upright fixtures / and less than 50 lbs.

6' / Up to 8 light fixtures / or 32" or less in diameter upright fixtures / and less than 50 lbs. weight

7' / 2 or more tier fixtures / or bigger than 32" diameter upright fixtures / or 50 lbs. or more weight.

8' / 9 or more light fixtures / or bigger than 32" diameter upright fixtures / or 50 lbs. or more weight

WIRE LENGTH

8' / fixtures with 6" chain

10' / fixtures with 8" chain

15' / 5' chain fixtures / or 7' chain fixtures with less than 35 lbs.

20' / 7' chain fixtures (with 35 lbs. or more weight)

STEM HUNG FIXTURE

(4) 12" stems + (1) 6" stem / and 15' wire

(4) 12" stems + (1) 6" stem / and 8' wire

(3) 12" stems + (1) 6" stem / and 15' wire (Mini Pendants Only)

(3) 12" stems + (1) 6" stem and 8' wire (Mini Pendants Only)

VAULTED CEILINGS

All Feiss pendants featuring stem kits come with canopies equipped with a 90° swivel to allow for mounting on vaulted ceilings.



QUICK LINKS

All Feiss chain hung fixtures include two quick links for easy installation.





FEISS®

EST. 1955

7400 Linder Ave.
Skokie, IL 60077 USA

Toll Free: 800.969.3347
Fax: 866.490.7765

sales@feiss.com
feiss.com

FSUP2017

GENERATION BRANDS