

PRO
SERIES

C-LITE™
LED LIGHTING BY CREE

CREE 



**C-Lite™ Products,
Cree Pro Series Lamps and Downlights
Canada**



C-LITE™ - YOUR TRUSTED VALUE BRAND.

C-Lite™ LED Lighting by Cree offers a broad range of reliable, easy to install LED lighting products with all the options you need. All products meet Cree’s rigorous testing standards in order to provide superior quality and dependability, and are fully backed by Cree.

SIMPLE

Our mission is simple: provide high performance, go-to LED lighting at incredible value. Contractors have enough to worry about—C-Lite™ products make lighting projects one less hurdle in a day full of them.

EASY

From easy installation to making sure our products are always in stock, easy to find and ready to work, we make jobs of all sizes quick, easy and painless. C-Lite™ LED Lighting by Cree is your no hassle, “hey, that was easy” choice.

QUALITY

Cree won’t put their name on just any box. Engineered to deliver great energy savings and powerful performance, C-Lite™ LED Lighting by Cree is backed by a great warranty and Cree’s world-class live customer support. You can relax knowing that with this, Cree has got your back.



PRODUCTS

C-LITE™ - LED OUTDOOR

LED Area Lights	4
Dusk to Dawn LED Area Lights	4
Shoebox LED Area Lights	5
LED Area Light Accessories	6
LED Canopy Lights	7
Compact LED Floodlights	8
High Performance LED Floodlights & Accessories	9
LED Wall Mounts	10
Slimline LED Wall Packs	11
Slimline LED Wall Pack Accessories	12
LED Wall Packs (Non Cutoff)	13
LED Wall Pack (Full Cutoff) & Accessories	14
LED Vapor Tights & Accessories	15

LED INDOOR

C-Lite™ LED Downlights	16
Cree® LED Downlights	17
Cree® LED Downlight Accessories	18
Cree® LED Surface Mount Disk Lights & Accessories	19
C-Lite™ LED Flat Panel Troffers	20
C-Lite™ LED Strips & Wraps	21
C-Lite™ LED Round Low Bays	22
C-Lite™ LED Linear High Bays	23
C-Lite™ LED High & Low Bay Accessories	24
C-Lite™ General LED Accessories	25

LED LAMPS

C-Lite™ LED Lamps	26
Cree® Professional Series LED Lamps	27

Cree® Professional Series LED Lamps & LED Downlights

LIGHT YOUR SPACE LIKE A PRO.

The NEW Cree® PRO Series LED lamps and LED downlights feature a remarkable combination of performance and quality, designed exclusively for spec-grade projects. They feature beautiful, high-CRI light that provides exceptional colour quality, making colours appear vibrant, rich and natural. These lamps and downlights are backed by a no-hassle warranty—making Cree the easy choice for your LED lamp and downlight needs.

SERIES FEATURES

- Exceptional 90+ CRI colour consistency
- Exceeds ENERGY STAR® rated lifetime requirements for most products, up to 25,000 hours
- Meets CEC Title 20/Title 24 JA-8 performance requirements
- Enclosure-rated lamps for use in more applications
- Higher lumen lamps and downlights offer more light for higher ceilings
- Shatterproof lamps
- Smooth, superior dimmability
- No-hassle 5-year limited warranty



All Professional Series lamps and downlights offered in single cartons.



* See cree.com/canada/warranty for details



C-AR-A-2LD



C-AR-A-4LD

LED AREA LIGHTS

Stylish Modern Design, Type III Optimized Distribution

- Category: LED Outdoor Area Light
- CRI: >70
- Location Type: Wet
- Voltage: 120-277V
- High LPW: up to 103
- Watts: 117 to 228
- Non-Dimmable
- Cree LEDs, quality driver

Item	SKU	Replaces	CCT	Lumens	Finish Colour
C-LITE™ Type III LED Area - 12,000 Lumens					
LED Area Light	C-AR-A-2LD-12L-40K-DB°	250W PSMH	4000K	12,400	Dark Bronze
LED Area Light	C-AR-A-2LD-12L-50K-DB°	250W PSMH	5000K	12,200	Dark Bronze
C-LITE™ Type III LED Area - 23,000 Lumens					
LED Area Light	C-AR-A-4LD-23L-40K-DB°	400W PSMH	4000K	23,100	Dark Bronze
LED Area Light	C-AR-A-4LD-23L-50K-DB°	400W PSMH	5000K	22,800	Dark Bronze

DUSK TO DAWN LED AREA LIGHTS

Versatile, Reliable, Efficient

- Category: LED Outdoor Area Light
- CRI: >70
- Location Type: Wet
- Voltage: 120-277V
- Watts: 23
- Non-Dimmable
- Finish Colour: Gray



C-AR-A-DD-3L-50K-GR

Item	SKU	Replaces	CCT	Lumens	Size
C-LITE™ Dusk to Dawn LED Area Light					
LED Area Light	C-AR-A-DD-3L-50K-GR♦	70W MH	5000K	2,800	12" L x 7-12" W x 6-3/4" H

NOTE: For Area Light accessories refer to Page 6, for General LED lighting accessories refer to page 25



°DLC Standard ♦DLC Premium
Subject to Change.

*See cree.com/canada/warranty for details



C-AR-A-SQT3
C-AR-A-SQT5
C-AR-A-SQT7

SHOEBOX LED AREA LIGHTS

Stylish, Modern Design; Type III, V and VII Optimized Distributions

- Category: LED Outdoor Area Light
- CRI: >70
- Location Type: Wet
- Voltage: 120-277V
- Cree LEDs, quality driver
- High LPW: up to 143
- Watts: 119
- Non-Dimmable
- Finish Colour: Dark Bronze

Item	SKU	Replaces	CCT	Lumens	Size
C-LITE™ Type III Shoebox LED Area Light					
LED Area Light	C-AR-A-SQT3-16L-40K-DB♦	320W PSMH / 400W MH	4000K	16,100	16-1/5" x 16-1/5"
LED Area Light	C-AR-A-SQT3-17L-50K-DB♦	320W PSMH / 400W MH	5000K	17,100	16-1/5" x 16-1/5"
C-LITE™ Type V Shoebox LED Area Light					
LED Area Light	C-AR-A-SQT5-15L-50K-DB♦	320W PSMH / 400W MH	5000K	15,200	16-1/5" x 16-1/5"
LED Area Light	C-AR-A-SQT5-16L-40K-DB♦	320W PSMH / 400W MH	4000K	16,100	16-1/5" x 16-1/5"
C-LITE™ Type VII Shoebox LED Area Light					
LED Area Light	C-AR-A-SQT7-17L-50K-DB♦	320W PSMH / 400W MH	5000K	16,900	16-1/5" x 16-1/5"
LED Area Light	C-AR-A-SQT7-17L-40K-DB♦	320W PSMH / 400W MH	4000K	16,900	16-1/5" x 16-1/5"

NOTE: For Area Light accessories refer to Page 6, for General LED lighting accessories refer to page 25



◊ DLC Standard ♦ DLC Premium
Subject to Change.

*See cree.com/canada/warranty for details



LED Adjustable U-Bracket



LED 6" Mounting Arm



LED Mount Slipfitter 2in



LED Mounting Arm Kit



LED Photocell 120V/208V/240V/277V

LED AREA LIGHT ACCESSORIES

Accessories for C-Lite™ Area Lights

• Category: LED Outdoor Accessories

Product/Item	SKU	Finish Colour	Size/Fits
LED Adjustable U-Bracket	C-ACC-A-AUB-2X5X6-DB	Dark Bronze	Fits C-AR-A-2LD Series, 2" X 5" X 6"
LED 6" Mounting Arm	C-ACC-A-MTARM-6IN-DB	Dark Bronze	6in, Fits C-AR-A-2LD, C-AR-A-4LD Series
LED Adjustable U-Bracket	C-ACC-A-AUB-3X5X5-DB	Dark Bronze	Fits C-AR-A-4LD Series, 3" X 5" X 5"
LED Mount Slipfitter 2"	C-ACC-A-MTSL-2IN-DB	Dark Bronze	2in, Fits C-AR-A-2LD, C-AR-A-4LD, C-AR-A-SQT5, C-AR-A-SQT7 Series
LED 6" Mounting Arm	C-ACC-A-SBMTARM-6IN-DB	Dark Bronze	Fits C-AR-A-SQT3, C-AR-A-SQT5, C-AR-A-SQT7 Series
LED Mounting Arm Kit	C-ACC-A-SMDDPOLE-GR	Gray	For C-AR-A-DD-3L Series
LED Adjustable U-Bracket	C-ACC-A-AUB-DB	Dark Bronze	Fits C-AR-A-SQT3, AR-A-SQT5, C-AR-A-SQT7 Series
LED Photocell 120V	C-ACC-A-PCCELL-LV	-	120V, Fits C-AR-A-2LD, C-AR-A-4LD, C-AR-A-SQT3, C-AR-A-SQT5, C-AR-A-SQT7 Series
LED Photocell 208-277V	C-ACC-A-PCCELL-HV-TL	-	208-277V, Fits C-AR-A-2LD, C-AR-A-4LD, C-AR-A-SQT3, C-AR-A-SQT5, C-AR-A-SQT7 Series

*See cree.com/canada/warranty for details

LED CANOPY LIGHTS

Traditional Style; Easy Installation

- Category: LED Outdoor Canopy
- CRI: >70
- Location Type: Wet
- Voltage: 120-277V
- High LPW: Up to 136
- Watts: 28 to 95
- Non-Dimmable
- Cree LEDs, quality driver



C-CP-A-SQ-30/49L
Dark Bronze



C-CP-A-SQ-79L
Dark Bronze



C-CP-A-SQ-120L
Dark Bronze

Item	SKU	Replaces	CCT	Lumens	Finish Colour	Size/Fits
C-LITE™ Square Canopy - 30L						
Square LED Canopy	C-CP-A-SQ-30L-40K-DB◊	70W PSMH	4000K	3,000	Dark Bronze	Hole Size: 9-7/8" x 9-7/8"
Square LED Canopy	C-CP-A-SQ-30L-40K-WH◊	70W PSMH	4000K	3,000	White	Hole Size: 9-7/8" x 9-7/8"
Square LED Canopy	C-CP-A-SQ-30L-50K-DB◊	70W PSMH	5000K	3,000	Dark Bronze	Hole Size: 9-7/8" x 9-7/8"
Square LED Canopy	C-CP-A-SQ-30L-50K-WH◊	70W PSMH	5000K	3,000	White	Hole Size: 9-7/8" x 9-7/8"
C-LITE™ Square Canopy - 49L						
Square LED Canopy	C-CP-A-SQ-49L-40K-DB◊	100W PSMH	4000K	4,900	Dark Bronze	Hole Size: 9-7/8" x 9-7/8"
Square LED Canopy	C-CP-A-SQ-49L-40K-WH◊	100W PSMH	4000K	4,900	White	Hole Size: 9-7/8" x 9-7/8"
Square LED Canopy	C-CP-A-SQ-49L-50K-DB◊	100W PSMH	5000K	4,900	Dark Bronze	Hole Size: 9-7/8" x 9-7/8"
Square LED Canopy	C-CP-A-SQ-49L-50K-WH◊	100W PSMH	5000K	4,900	White	Hole Size: 9-7/8" x 9-7/8"
C-LITE™ Square Canopy - 79L						
Square LED Canopy	C-CP-A-SQ-79L-40K-DB◊	150W PSMH 175W MH 200W MH	4000K	7,900	Dark Bronze	Hole Size: 13-1/3" x 13-1/3"
Square LED Canopy	C-CP-A-SQ-79L-40K-WH◊	150W PSMH 175W MH 200W MH	4000K	7,900	White	Hole Size: 13-1/3" x 13-1/3"
Square LED Canopy	C-CP-A-SQ-79L-50K-DB◊	150W PSMH 175W MH 200W MH	5000K	7,900	Dark Bronze	Hole Size: 13-1/3" x 13-1/3"
Square LED Canopy	C-CP-A-SQ-79L-50K-WH◊	150W PSMH 175W MH 200W MH	5000K	7,900	White	Hole Size: 13-1/3" x 13-1/3"
C-LITE™ Square Canopy - 120L						
Square LED Canopy	C-CP-A-SQ-120L-40K-DB◊	250W PSMH	4000K	12,000	Dark Bronze	Hole Size: 14" x 14"
Square LED Canopy	C-CP-A-SQ-120L-40K-WH◊	250W PSMH	4000K	12,000	White	Hole Size: 14" x 14"
Square LED Canopy	C-CP-A-SQ-120L-50K-DB◊	250W PSMH	5000K	12,000	Dark Bronze	Hole Size: 14" x 14"
Square LED Canopy	C-CP-A-SQ-120L-50K-WH◊	250W PSMH	5000K	12,000	White	Hole Size: 14" x 14"



◊ DLC Standard ♦ DLC Premium
Subject to Change.

*See cree.com/canada/warranty for details

COMPACT LED FLOODLIGHTS

High Quality; Easy Installation; 5 Year Limited Warranty*

- Category: LED Outdoor Floodlights/Spot Lights
- CRI: >70
- Location Type: Wet
- Voltage: 120-277V
- Non-Dimmable
- High LPW: Up to 106
- Watts: 9 to 35
- Cree LEDs, quality driver



C-FL-A-RC-2L
White



C-FL-A-RC-3L
Dark Bronze



C-FL-A-RDC
Small, Black



C-FL-A-RDW
Wide



C-FL-A-RDM
Medium

Item	SKU	Replaces	CCT	Lumens	Finish Colour	Size/Fits
C-LITE™ Premium LED Compact Flood - 1,600L						
Premium LED Compact Flood	C-FL-A-RC-2L-40K-DB	50W MH	4000K	1,600	Dark Bronze	4-3/4" H x 6-1/8" W x 4-3/4" D
Premium LED Compact Flood	C-FL-A-RC-2L-40K-WH	50W MH	4000K	1,600	White	4-3/4" H x 6-1/8" W x 4-3/4" D
C-LITE™ Premium LED Compact Flood - 2,900L						
Premium LED Compact Flood	C-FL-A-RC-3L-40K-DB ^o	100W PSMH	4000K	2,900	Dark Bronze	6" H x 7-3/4" W x 4-3/4" D
Premium LED Compact Flood	C-FL-A-RC-3L-40K-WH ^o	100W PSMH	4000K	2,900	White	6" H x 7-3/4" W x 4-3/4" D
Premium LED Compact Flood	C-FL-A-RC-3L-50K-DB ^o	100W PSMH	5000K	2,900	Dark Bronze	6" H x 7-3/4" W x 4-3/4" D
Premium LED Compact Flood	C-FL-A-RC-3L-50K-WH ^o	100W PSMH	5000K	2,900	White	6" H x 7-3/4" W x 4-3/4" D
C-LITE™ Premium LED Directional Flood - Small						
Premium LED Directional Flood	C-FL-A-RDC-1L-40K-BK	50W Halogen	4000K	700	Black	4" H x 4" W x 4-5/8" D
Premium LED Directional Flood	C-FL-A-RDC-1L-40K-WH	50W Halogen	4000K	700	White	4" H x 4" W x 4-5/8" D
C-LITE™ Premium LED Directional Flood - Wide						
Premium LED Directional Flood	C-FL-A-RDW-3L-40K-DB ^o	100W PSMH / 70W MH	4000K	3,200	Dark Bronze	7-2/5" H x 6" W x 8-1/2" D
Premium LED Directional Flood	C-FL-A-RDW-3L-50K-DB ^o	100W PSMH / 70W MH	5000K	3,400	Dark Bronze	7-2/5" H x 6" W x 8-1/2" D
C-LITE™ Premium LED Directional Flood - Medium						
Premium LED Directional Flood	C-FL-A-RDM-3L-40K-DB ^o	100W PSMH / 70W MH	4000K	3,500	Dark Bronze	7-2/5" H x 6" W x 8-1/2" D
Premium LED Directional Flood	C-FL-A-RDM-4L-50K-DB ^o	100W PSMH / 70W MH	5000K	3,800	Dark Bronze	7-2/5" H x 6" W x 8-1/2" D



^oDLC Standard ♦DLC Premium
Subject to Change.

*See cree.com/canada/warranty for details

HIGH PERFORMANCE LED FLOODLIGHTS & ACCESSORIES

High Quality; Easy Installation; 5 Year Limited Warranty*

- Category: LED Outdoor Floodlights & Accessories
- CRI: >70
- Location Type: Wet
- Voltage: 120-277V
- Non-Dimmable
- Finish Colour: Dark Bronze
- High LPW: Up to 118
- Watts: 74 to 234



C-FL-A-RTF1
Small, Wide



C-FL-A-RTS1
Small, Narrow



C-FL-A-RTF2
Large, Wide



C-FL-A-RTF4
High-Output, Wide



LED Photocell 120V-277V

Item	SKU	Replaces	CCT	Lumens	Size/Fits
C-LITE™ Premium LED Flood - Small, Wide					
Premium LED Floodlight - Small	C-FL-A-RTF1-8L-40K-DB°	150W PSMH / 175W MH	4000K	8,100	11" H x 9-4/9"W x 5-1/2" D
Premium LED Floodlight - Small	C-FL-A-RTF1-7L-50K-DB°	150W PSMH / 175W MH	5000K	7,400	11" H x 9-4/9" W x 5-1/2" D
C-LITE™ Premium LED Flood - Small, Narrow					
Premium LED Floodlight - Small	C-FL-A-RTS1-8L-40K-DB°	150W PSMH / 175W MH	4000K	8,000	11" H x 9-4/9" W x 5-1/2" D
Premium LED Floodlight - Small	C-FL-A-RTS1-7L-50K-DB°	150W PSMH / 175W MH	5000K	7,300	11" H x 9-4/9" W x 5-1/2" D
C-LITE™ Premium LED Flood - Large, Wide					
Premium LED Floodlight - Large	C-FL-A-RTF2-12L-40K-DB°	250W PSMH	4000K	12,300	14-5/8" H x 12-3/4" W x 7-3/8" D
Premium LED Floodlight - Large	C-FL-A-RTF2-12L-50K-DB°	250W PSMH	5000K	12,400	14-5/8" H x 12-3/4" W x 7-3/8" D
C-LITE™ Premium LED Flood - Large, Narrow					
Premium LED Floodlight - Large	C-FL-A-RTS2-13L-40K-DB°	250W PSMH	4000K	13,600	14-5/8" H x 12-3/4" W x 7-3/8" D
Premium LED Floodlight -Large	C-FL-A-RTS2-14L-50K-DB°	250W PSMH	5000K	13,900	14-5/8" H x 12-3/4" W x 7-3/8" D
C-LITE™ High-Output LED Flood - Wide					
High-Output LED Floodlight	C-FL-A-RTF4-26L-40K-DB°	400W PSMH	4000K	26,500	16-1/16" H x 17-3/4" W x 7-5/16" D
High-Output LED Floodlight	C-FL-A-RTF4-26L-50K-DB°	400W PSMH	5000K	26,300	16-1/16" H x 17-3/4" W x 7-5/16" D
C-LITE™ High-Output LED Flood - Narrow					
High-Output LED Floodlight	C-FL-A-RTS4-23L-40K-DB°	400W PSMH	4000K	22,900	16-1/16" H x 17-3/4" W x 7-5/16" D
High-Output LED Floodlight	C-FL-A-RTS4-23L-50K-DB°	400W PSMH	5000K	22,800	16-1/16" H x 17-3/4" W x 7-5/16" D
ACCESSORIES					
LED Photocell 120V	C-ACC-A-PCCELL-LV				120V, Fits C-FL-A-RTF2, C-FL-A-RTS2, C-FL-A-RTF4, C-FL-A-RTS4 Series
LED Photocell 208-277V	C-ACC-A-PCCELL-HV-TL				208-277V, Fits C-FL-A-RTF2, C-FL-A-RTS2, C-FL-A-RTF4, C-FL-A-RTS4 Series

°DLC Standard ♦DLC Premium
Subject to Change.



*See cree.com/canada/warranty for details



C-WM-A-WLAR
Architectural



C-WM-A-WLCY
Cylinder



C-WM-A-WLHR



C-WM-A-WLHO
High-Output



C-WM-A-WLSL



C-WM-A-WLSP
Spherical

LED WALL MOUNTS

Easy Installation; Versatile; Efficient

- Category: LED Outdoor Wall Mounts with Photo Cell
- CRI: >70
- Location Type: Wet
- Voltage: 120V
- Non-Dimmable
- High LPW: Up to 97
- Watts: 14 to 36

Item	SKU	Replaces	CCT	Lumens	Finish Colour	Size/Fits
C-LITE™ Architectural Wall Mount						
Architectural Wall Mount (120-277V)	C-WM-A-WLAR-11L-50K-MB	100W Incandescent	5000K	1,100	Medium Bronze	Size: 6" H x 5-2/5" W x 7-1/4" L
C-LITE™ Wall Mount - Cylinder						
Wall Mount Cylinder	C-WM-A-WLCY-6L-40K-WH	60W Incandescent	4000K	600	White	Size: 9-1/3" H x 4-3/4" W x 6-1/2" D
Wall Mount Cylinder	C-WM-A-WLCY-6L-40K-DB	60W Incandescent	4000K	600	Dark Bronze	Size: 9-1/3" H x 4-3/4" W x 6-1/2" D
C-LITE™ Wall Mount - 1,000/1,200 Lumens						
Wall Mount	C-WM-A-WLHR-10L-40K-MB	100W Incandescent	4000K	1,000	Medium Bronze	Size: 9" H x 5-3/4" W x 4" D
Wall Mount	C-WM-A-WLHR-10L-40K-WH	100W Incandescent	4000K	1,000	White	Size: 9" H x 5-3/4" W x 4" D
Wall Mount	C-WM-A-WLHR-12L-40K-MB	120W Incandescent	4000K	1,200	Medium Bronze	Size: 9" H x 5-3/4" W x 4" D
Wall Mount	C-WM-A-WLHR-12L-40K-WH	120W Incandescent	4000K	1,200	White	Size: 9" H x 5-3/4" W x 4" D
C-LITE™ Wall Mount - High-Output						
High-Output Wall Mount	C-WM-A-WLHO-34L-40K-MB	100W PSMH	4000K	3,400	Medium Bronze	Size: 11" H x 7-1/8" W x 4-1/4" D
High-Output Wall Mount	C-WM-A-WLHO-36L-50K-MB	100W PSMH	5000K	3,600	Medium Bronze	Size: 11" H x 7-1/8" W x 4-1/4" D
C-LITE™ Wall Mount - 1,500 Lumens						
Wall Mount	C-WM-A-WLSL-14L-50K-MB	120W Incandescent	5000K	1,400	Medium Bronze	Size: 12-3/5" H x 7-3/4" W x 4-3/5" D
C-LITE™ Wall Mount - Spherical						
Wall Mount Spherical	C-WM-A-WLSP-8L-40K-WH	75W Incandescent	4000K	800	White	Size: 9-4/5" H x 4-2/5" W x 5-4/5" L
Wall Mount Spherical	C-WM-A-WLSP-8L-40K-DB	75W Incandescent	4000K	800	Dark Bronze	Size: 9-4/5" H x 4-2/5" W x 5-4/5" L

*See cree.com/canada/warranty for details

SLIMLINE LED WALL PACKS

Efficient; Architectural Design; Easy Installation; 5 Year Limited Warranty*

- Category: LED Outdoor Wall Packs
- CRI: >70
- Location Type: Wet
- Voltage: 120-277V
- Non-Dimmable
- Finish Colour: Dark Bronze
- High LPW: Up to 105
- Watts: 40 to 150
- Cree LEDs, quality driver



C-WP-A-SL-4L
Small



C-WP-A-SL-8L
Medium



C-WP-A-SL-16L
Large

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
C-LITE™ Architectural Slim Wall Pack - Small						
Architectural Slim	C-WP-A-SL-4L-40K-DB ^o	100W PSMH	4000K	3,900	40	Size: 8" H x 7-1/2" W x 2-4/5" L
Architectural Slim	C-WP-A-SL-4L-50K-DB ^o	100W PSMH	5000K	3,900	40	Size: 8" H x 7-1/2" W x 2-4/5" L
C-LITE™ Architectural Slim Wall Pack - Medium						
Architectural Slim	C-WP-A-SL-8L-40K-DB ^o	250W MH	4000K	8,100	80	Size: 12-4/5" H x 14-1/5" W x 5" L
Architectural Slim	C-WP-A-SL-8L-50K-DB ^o	250W MH	5000K	8,100	80	Size: 12-4/5" H x 14-1/5" W x 5" L
C-LITE™ Architectural Slim Wall Pack - Large						
Architectural Slim	C-WP-A-SL-16L-40K-DB ^o	320W PSMH / 400W MH	4000K	15,800	150	Size: 12-4/5" H x 14-1/5" W x 5" L
Architectural Slim	C-WP-A-SL-16L-50K-DB ^o	320W PSMH / 400W MH	5000K	15,800	150	Size: 12-4/5" H x 14-1/5" W x 5" L

NOTE: For Slimline LED Wall Pack Light accessories refer to Page 12; for General LED Wall Pack lighting accessories refer to page 14



^oDLC Standard ♦DLC Premium
Subject to Change.

*See cree.com/canada/warranty for details



LED Photocell, 120V <1000W



Adjustable U-Bracket Mount Kit



Adjustable Slip Fitter



Adjustable Swivel Fitter



Adjustable U-Bracket



Surface Mounting Box

SLIMLINE LED WALL PACK ACCESSORIES

Efficient; Architectural Design; Easy Installation; 5 Year Limited Warranty*

- Category: LED Outdoor Accessories

Item	SKU	Size/Fits
LED Photocell, 120V	C-ACC-A-PCCELL-LV	120V, Fits C-WP-A Series
LED Photocell, 208-277V	C-ACC-A-PCCELL-HV	208-277V, Fits C-WP-A -SL Series
Adjustable U-Bracket	C-ACC-A-AUBAS-SM-DB	For Slimline Wallpacks C-WP-A-SL-4L Series
Adjustable Slip Fitter	C-ACC-A-2SFAS-SM-DB	2", For Slimline Wallpacks C-WP-A-SL-4L Series
Adjustable Swivel Fitter	C-ACC-A-12SFAS-SM-DB	1/2" NPS, For Slimline Wallpacks C-WP-A-SL-4L Series
Adjustable U-Bracket	C-ACC-A-AUBAS-LG-DB	For Slimline Wallpacks C-WP-A-SL-8L/16L Series
Adjustable Slip Fitter	C-ACC-A-2SFAS-LG-DB	2", For Slimline Wallpacks C-WP-A-SL-8L/16L Series
Surface Mounting Box	C-ACC-A-SMBAS-DB	For Slimline Wallpacks C-WP-A-SL-4L, C-WP-A-SL-8L/16L Series

*See cree.com/canada/warranty for details

LED WALL PACKS (NON CUTOFF)

Efficient; Easy Installation; 5 Year Limited Warranty*

- Category: LED Outdoor Wall Packs
- CR1: >70
- Location Type: Wet
- Voltage: 120-277V
- Non-Dimmable
- Finish Colour: Dark Bronze
- High LPW: Up to 144
- Watts: 20 to 158



C-WP-A-TRAD-3L
C-WP-A-TR-4L
Small, Non-Cutoff



C-WP-A-TRAD-8L
C-WP-A-TR-21L
Large, Non-Cutoff
High Output, Non-Cutoff



C-WP-A-TR-1L
Non-Cutoff



C-WP-A-TR-12L
Large, Non-Cutoff



C-WP-A-TR-15L/16L
High-Output, Non-Cutoff

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
C-LITE™ Traditional Style Non-Cutoff - 3,400 Lumens - Small						
Traditional (non cutoff)	C-WP-A-TRAD-3L-40K-DB	100W PSMH	4000K	3,200	33	Size: 9-1/4" H x 14-1/8" W x 7-1/2" D
Traditional (non cutoff)	C-WP-A-TRAD-3L-50K-DB	100W PSMH	5000K	3,400	33	Size: 9-1/4" H x 14-1/8" W x 7-1/2" D
C-LITE™ Traditional Style Non-Cutoff - 8,900 Lumens - Large						
Traditional (non cutoff)	C-WP-A-TRAD-8L-40K-DB	250W MH	4000K	8,600	85	Size: 9-3/4" H x 18" W x 9-3/8" D
Traditional (non cutoff)	C-WP-A-TRAD-8L-50K-DB	250W MH	5000K	8,900	87	Size: 9-3/4" H x 18" W x 9-3/8" D
C-LITE™ Traditional Style Non-Cutoff - 1,300 Lumens						
Traditional (non cutoff) 120V only	C-WP-A-TR-1L-40K-DB	50W MH	4000K	1,300	20	Size: 8-9/16" H x 7-3/16" W x 7-5/16" L
C-LITE™ Traditional Style Non-Cutoff - 4,600 Lumens - Small						
Traditional (non cutoff)	C-WP-A-TR-4L-30K-DB	100W PSMH	3000K	4,600	43	Size: 9-1/4" H x 14-1/8" W x 7-1/2" D
Traditional (non cutoff)	C-WP-A-TR-4L-40K-DB	100W PSMH	4000K	4,600	43	Size: 9-1/4" H x 14-1/8" W x 7-1/2" D
Traditional (non cutoff)	C-WP-A-TR-4L-50K-DB	100W PSMH	5000K	4,600	43	Size: 9-1/4" H x 14-1/8" W x 7-1/2" D
C-LITE™ Traditional Style Non-Cutoff - 13,000-13,100 Lumens - Large						
Traditional (non cutoff)	C-WP-A-TR-12L-40K-DB	250W MH	4000K	13,000	108	Size: 9-5/6" H x 18" W x 9-3/8" D
Traditional (non cutoff)	C-WP-A-TR-12L-50K-DB	250W MH	5000K	13,100	108	Size: 9-5/6" H x 18" W x 9-3/8" D
C-LITE™ Traditional Style Non-Cutoff - 15,000-15,900 Lumens - High Output						
Traditional (non cutoff)	C-WP-A-TR-15L-40K-DB	320W PSMH / 400W MH	4000K	15,000	119	Size: 9-7/8" H x 18" W x 13" D
Traditional (non cutoff)	C-WP-A-TR-16L-50K-DB	320W PSMH / 400W MH	5000K	15,900	119	Size: 9-7/8" H x 18" W x 13" D
C-LITE™ Traditional Style Non-Cutoff - 21,100 Lumens - High Output						
Traditional (non cutoff)	C-WP-A-TR-21L-40K-DB	400W PSMH	4000K	21,100	158	Size: 9-3/4" H x 18" W x 9-3/8" D
Traditional (non cutoff)	C-WP-A-TR-21L-50K-DB	400W PSMH	5000K	21,100	158	Size: 9-3/4" H x 18" W x 9-3/8" D

NOTE: For General LED Wall Pack lighting accessories refer to page 14

◊ DLC Standard ◊ DLC Premium
Subject to Change.



*See cree.com/canada/warranty for details



C-WP-A-TRFC
Medium, Full-Cutoff



C-WP-A-FCT3-3L
Small, Full-Cutoff



C-WP-A-FCT3-6L
Medium, Full-Cutoff



C-WP-A-FCT3-18L
Full-Cutoff

LED WALL PACKS (FULL CUTOFF)

Efficient; Easy Installation; 5 Year Limited Warranty*

- Category: LED Outdoor Wall Packs
- CRI: >70
- Location Type: Wet
- Voltage: 120-277V
- Non-Dimmable
- Finish Colour: Dark Bronze
- High LPW: Up to 144
- Watts: 20 to 157

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
C-LITE™ Traditional Style Full-Cutoff - 6,600 Lumens - Medium						
Traditional (full cutoff)	C-WP-A-TRFC-6L-40K-DB°	150W PSMH / 175W MH	4000K	6,400	66	Size: 14-1/4" D x 9-1/4" W x 9" H
Traditional (full cutoff)	C-WP-A-TRFC-6L-50K-DB°	150W PSMH / 175W MH	5000K	6,600	66	Size: 14-1/4" D x 9-1/4" W x 9" H
C-LITE™ Premium Full-Cutoff Wall Pack - 3,200 - 3,600 Lumens - Small						
Premium (full cutoff)	C-WP-A-FCT3-3L-30K-DB♦	100W PSMH	3000K	3,200	32	Size: 4-1/2" H x 8-3/4" W x 9-1/2" D
Premium (full cutoff)	C-WP-A-FCT3-3L-40K-DB♦	100W PSMH	4000K	3,500	33	Size: 4-1/2" H x 8-3/4" W x 9-1/2" D
Premium (full cutoff)	C-WP-A-FCT3-3L-50K-DB♦	100W PSMH	5000K	3,600	33	Size: 4-1/2" H x 8-3/4" W x 9-1/2" D
C-LITE™ Premium Full-Cutoff Wall Pack - 5,100 - 6,200 Lumens - Medium						
Premium (full cutoff)	C-WP-A-FCT3-6L-30K-DB°	150W PSMH / 175W MH	3000K	5,100	57	Size: 4-11/16" H x 10" W x 10-5/16" D
Premium (full cutoff)	C-WP-A-FCT3-6L-40K-DB°	150W PSMH / 175W MH	4000K	6,000	65	Size: 4-11/16" H x 10" W x 10-5/16" D
Premium (full cutoff)	C-WP-A-FCT3-6L-50K-DB°	150W PSMH / 175W MH	5000K	6,200	66	Size: 4-11/16" H x 10" W x 10-5/16" D
C-LITE™ Premium Full-Cutoff Wall Pack - 18,000 Lumens						
Premium (full cutoff)	C-WP-A-FCT3-18L-40K-DB°	320W PSMH / 400W MH	4000K	18,000	157	Size: 5-1/2" H x 13-1/2" W x 12-1/2" D
Premium (full cutoff)	C-WP-A-FCT3-18L-50K-DB°	320W PSMH / 400W MH	5000K	18,000	157	Size: 5-1/2" H x 13-1/2" W x 12-1/2" D



LED Photocell, 120V <1000W

LED WALL PACK ACCESSORIES

Efficient; Easy Installation; 5 Year Limited Warranty*

- Category: LED Outdoor Accessories

Item	SKU	Size/Fits
LED Photocell, 120V	C-ACC-A-PCCELL-LV	120V, Fits C-WP-A Series
LED Photocell, 208-277V	C-ACC-A-PCCELL-HV	208-277V, Fits C-WP-A-TRAD/TRFC/TR Series
LED Photocell, 208-277V	C-ACC-A-PCCELL-HV-TL	208-277V, Fits C-WP-A FCT3 Series



° DLC Standard ♦ DLC Premium
Subject to Change.

*See cree.com/canada/warranty for details

LED VAPOR TIGHTS

Efficient; Traditional Design; Easy To Install; 5 Year Limited Warranty*

- Category: LED Outdoor Vapor Tights
- CRI: >70
- Location Type: Wet
- Voltage: 120V
- Non-Dimmable
- High LPW: Up to 98
- Watts: 14 to 22
- Cree LEDs, quality driver



Small Large
LED Vapor Pendant Mounts



Small Large
LED Vapor Ceiling Mounts



Small Large
LED Vapor Wall Mounts



LED Linear Vapor Tight Strip

Item	SKU	Replaces	CCT	Lumens	Finish Colour	Size/Fits
C-LITE™ Vapor Tight - Pendant Mount						
LED Vapor Tight, Small Pendant Mount	C-VT-A-SMPD-9L-40K-GR	100W Incandescent	4000K	900	GR = Gray	10" H x 4-1/2" Diameter
LED Vapor Tight, Large Pendant Mount	C-VT-A-LGPD-12L-40K-GR	120W Incandescent	4000K	1200	GR = Gray	12-2/5" H x 5-4/5" Diameter
C-LITE™ Vapor Tight - Ceiling Mount						
LED Vapor Tight, Small Ceiling Mount	C-VT-A-SMCL-9L-40K-GR	100W Incandescent	4000K	900	GR = Gray	9-1/3" H x 4-1/2" Diameter
LED Vapor Tight, Large Ceiling Mount	C-VT-A-LGCL-12L-40K-GR	120W Incandescent	4000K	1200	GR = Gray	11-3/5" H x 5-4/5" Diameter
C-LITE™ Vapor Tight - Wall Mount						
LED Vapor Tight, Small Wall Mount	C-VT-A-SMWL-9L-40K-GR	100W Incandescent	4000K	900	GR = Gray	10" H x 4-2/5" W x 5-4/5" L
LED Vapor Tight, Large Wall Mount	C-VT-A-LGWL-12L-40K-GR	120W Incandescent	4000K	1200	GR = Gray	12-2/5" H x 5-4/5" W x 9" L
C-LITE™ Vapor Tight - Linear						
LED Linear Vapor Tight Strip	C-VT-A-LIN4-52L-40K-GR♦	2-Lamp F32T8	4000K	5,200	Gray	50" L x 4-1/2" W x 3-1/2" H
LED Linear Vapor Tight Strip	C-VT-A-LIN4-52L-50K-GR♦	2-Lamp F32T8	5000K	5,200	Gray	50" L x 4-1/2" W x 3-1/2" H

LED VAPOR TIGHT ACCESSORIES

Accessories for C-Lite™ LED Vapor Tights



LED Vapor Tight Shroud

Item	SKU	Finish Colour	Size/Fits
LED Vapor Tight, Small Shroud	C-ACC-A-VTSHR-SM-GR	Gray	Small, For C-VT-A-SMCL/SMPD Series Not suited for wall mounts
LED Vapor Tight, Large Shroud	C-ACC-A-VTSHR-LG-GR	Gray	Large, For C-VT-A-LGCL/LGPD Series Not suited for wall mounts



°DLC Standard ♦DLC Premium
Subject to Change.

*See cree.com/canada/warranty for details



4" Downlight



6" Downlight



LED GU24 Connector

LED DOWNLIGHTS

Best Combination of Performance and Value; 5 Year Limited Warranty*

- Category: LED Downlights
- CRI: 90
- Location Type: Damp
- Voltage: 120V
- Input Power: 7.6 to 8.6 Watts
- Initial Delivered Lumens: 575 to 650
- Dimmable to 10%
- Base: E26

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
C-LITE™ Downlights - 4 inch						
LED Downlight 4"	C-DL4-A-575L-27K-B1	55W Incandescent	2700K	575	7.6	2-9/10" H x 5" Dia (Trim Width)
LED Downlight 4"	C-DL4-A-575L-30K-B1	55W Incandescent	3000K	575	7.6	2-9/10" H x 5" Dia (Trim Width)
LED Downlight 4"	C-DL4-A-575L-40K-B1	55W Incandescent	4000K	575	7.6	2-9/10" H x 5" Dia (Trim Width)
C-LITE™ Downlights - 6 inch						
LED Downlight 6"	C-DL6-A-650L-27K-B1	65W Incandescent	2700K	650	8.6	2-9/10" H x 7.2" Dia. (Trim Width)
LED Downlight 6"	C-DL6-A-650L-30K-B1	65W Incandescent	3000K	650	8.6	2-9/10" H x 7.2" Dia. (Trim Width)
LED Downlight 6"	C-DL6-A-650L-40K-B1	65W Incandescent	4000K	650	8.6	12-9/10" H x 7.2" Dia. (Trim Width)
ACCESSORIES						
LED GU24 Connector	C-ACC-A-DL-GU24					120V, Fits C-DL4 & DL6 Series

*See cree.com/canada/warranty for details

LED DOWNLIGHTS

High Efficacy and High Quality; 5 Year Limited Warranty*

- Category: LED Downlights
- CRI: 90+
- Location Type: Damp and Wet
- Voltage: 120V
- Dimmable to 5%
- White, Metal Finish
- Mounting: Recessed



4" Downlight (E26)



6" Downlight (E26)



4" Downlight (GU24)



6" Downlight (GU24)

Both the E26 and GU24 Connector come standard with each downlight.

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
Cree® CR4T - 4" Downlights - 790 Lumens						
LED Downlight 4"	CR4T-790L-27K-12-E26GU24	75W Incandescent	2700K	790	10.5	2.6" H x 5" Dia (Trim Width)
LED Downlight 4"	CR4T-790L-30K-12-E26GU24	75W Incandescent	3000K	790	10.5	2.6" H x 5" Dia (Trim Width)
LED Downlight 4"	CR4T-790L-35K-12-E26GU24	75W Incandescent	3500K	790	10.5	2.6" H x 5" Dia (Trim Width)
LED Downlight 4"	CR4T-790L-40K-12-E26GU24	75W Incandescent	4000K	790	10.5	2.6" H x 5" Dia (Trim Width)
Cree® CR6T - 6" Downlights - 825 Lumens						
LED Downlight 6"	CR6T-825L-27K-12-E26GU24	75W Incandescent	2700K	825	11	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-825L-30K-12-E26GU24	75W Incandescent	3000K	825	11	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-825L-35K-12-E26GU24	75W Incandescent	3500K	825	11	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-825L-40K-12-E26GU24	75W Incandescent	4000K	825	11	3.5" H x 7.4" Dia (Trim Width)
Cree® CR6T - 6" Downlights - 1,100 Lumens						
LED Downlight 6"	CR6T-1100L-27K-12-E26GU24	100W Incandescent	2700K	1,100	14.5	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-1100L-30K-12-E26GU24	100W Incandescent	3000K	1,100	14.5	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-1100L-35K-12-E26GU24	100W Incandescent	3500K	1,100	14.5	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-1100L-40K-12-E26GU24	100W Incandescent	4000K	1,100	14.5	3.5" H x 7.4" Dia (Trim Width)
Cree® CR6T - 6" Downlights - 1,600 Lumens						
LED Downlight 6"	CR6T-1600L-27K-12-E26GU24	150W Incandescent	2700K	1,600	21	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-1600L-30K-12-E26GU24	150W Incandescent	3000K	1,600	21	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-1600L-35K-12-E26GU24	150W Incandescent	3500K	1,600	21	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-1600L-40K-12-E26GU24	150W Incandescent	4000K	1,600	21	3.5" H x 7.4" Dia (Trim Width)

NOTE: For Downlight accessories refer to Page 18

*See cree.com/canada/warranty for details

LED DOWNLIGHT ACCESSORIES

Accessories for Cree® CRT Downlights



Black Satin Nickel Bronze



CRT Downlight Trims

ACCESSORIES	SKU	FITS
4" Downlight Plastic Trim - Black	CR4T-TRMBKAN-1	CR4T Series Downlights
4" Downlight Plastic Trim - Satin Nickel	CR4T-TRMSTAN-1	CR4T Series Downlights
4" Downlight Plastic Trim - Bronze	CR4T-TRMBRAN-1	CR4T Series Downlights
6" Downlight Plastic Trim - Black	CR6T-TRMBKAN-1	CR6T Series Downlights
6" Downlight Plastic Trim - Satin Nickel	CR6T-TRMSTAN-1	CR6T Series Downlights
6" Downlight Plastic Trim - Bronze	CR6T-TRMBRAN-1	CR6T Series Downlights
6" Downlight Plastic Trim - Black with Extended Black Flange	CR6T-TRMBKBB-1	CR6T Series Downlights

*See cree.com/canada/warranty for details

LED SURFACE MOUNT DISK LIGHTS

Maximum flexibility for installation; High Efficacy and High Quality; 5 Year Limited Warranty*

- Category: LED Surface Mount Disk Light
- CRI: 90+
- Location Type: Damp and Wet
- Voltage: 120V
- Dimmable to 5% with select dimmers
- LPW: 83
- White, Metal Finish
- Mounting: Surface Mount



4" Surface Mount Disk Light



6" Surface Mount Disk Light

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
------	-----	----------	-----	--------	-------	-----------

Cree® DDS - 4" Disk Light - 790 Lumens

LED Surface Mount Disk Light 4"	DS4-750L-27K-U1	65W Incandescent	2700K	750	9	1.9" H x 6" Dia (Trim Width)
LED Surface Mount Disk Light 4"	DS4-750L-30K-U1	65W Incandescent	3000K	750	9	1.9" H x 6" Dia (Trim Width)
LED Surface Mount Disk Light 4"	DS4-750L-40K-U1	65W Incandescent	4000K	750	9	1.9" H x 6" Dia (Trim Width)

Cree® DDS - 6" Disk Light - 900 Lumens

LED Surface Mount Disk Light 6"	DS6-900L-27K-U1	75W Incandescent	2700K	900	10.5	2.3" H x 7.4" Dia (Trim Width)
LED Surface Mount Disk Light 6"	DS6-900L-30K-U1	75W Incandescent	3000K	900	10.5	2.3" H x 7.4" Dia (Trim Width)
LED Surface Mount Disk Light 6"	DS6-900L-40K-U1	75W Incandescent	4000K	900	10.5	2.3" H x 7.4" Dia (Trim Width)

LED SURFACE MOUNT DISK LIGHT ACCESSORIES

Downlight Adapter Accessory Packs for Cree® Surface Mount Disk Lights



4" Disk Light GU24 Accessory Kit



4" Disk Light E26 Accessory Kit



6" Disk Light GU24 Accessory Kit



6" Disk Light E26 Accessory Kit

ACCESSORIES	SKU	FITS
-------------	-----	------

4" Disk Light GU24 Accessory Kit

Includes GU24 socket adapter and flip clip mount for use in recessed cans with GU24 sockets

DS4-GU24-ACCES-1

LED Surface Mount Disk Light 4"

4" Disk Light E26 Accessory Kit

Includes E26 socket adapter and flip clip mount for use in recessed cans with Edison sockets

DS4-E26-ACCES-1

LED Surface Mount Disk Light 4"

6" Disk Light GU24 Accessory Kit

Includes GU24 socket adapter and flip clip mount for use in recessed cans with GU24 sockets

DS6-GU24-ACCES-1

LED Surface Mount Disk Light 6"

6" Disk Light E26 Accessory Kit

Includes E26 socket adapter and flip clip mount for use in recessed cans with Edison sockets

DS6-E26-ACCES-1

LED Surface Mount Disk Light 6"

*See cree.com/canada/warranty for details



1' X 4' LED Flat Panel



2' X 2' LED Flat Panel



2' X 4' LED Flat Panel

LED FLAT PANEL TROFFERS

Low Profile Design; High Efficiency; 5 Year Limited Warranty*

- Category: LED Indoor Troffers
- CRI: 80
- Location Type: Damp
- Voltage: 120-277V
- Non-Dimmable, 0-10V
- White
- Watts: 40 or 50
- Mounting: Recessed

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
C-LITE™ 1' x 4' Flat Panel						
LED Flat Panel Troffer 1' X 4'	C-TR-A-FP14-40L-35K-WH ^o	2 x F32T8	3500K	4,000	40	47-3/4" L x 11-3/4" W x 1/2" H (Panel)
LED Flat Panel Troffer 1' X 4'	C-TR-B-FP14-40L-40K-WH ^o	2 x F32T8	4000K	4,000	40	47-3/4" L x 11-3/4" W x 1/2" H (Panel)
LED Flat Panel Troffer 1' X 4'	C-TR-A-FP14-40L-50K-WH ^o	2 x F32T8	5000K	4,000	40	47-3/4" L x 11-3/4" W x 1/2" H (Panel)
C-LITE™ 2' x 2' Flat Panel						
LED Flat Panel Troffer 2' X 2'	C-TR-A-FP22-40L-35K-WH ^o	2 x F32T8/U6	3500K	4,000	40	23-3/4" L x 23-3/4" W x 1/2" H (Panel)
LED Flat Panel Troffer 2' X 2'	C-TR-A-FP22-40L-40K-WH ^o	2 x F32T8/U6	4000K	4,000	40	23-3/4" L x 23-3/4" W x 1/2" H (Panel)
LED Flat Panel Troffer 2' X 2'	C-TR-A-FP22-40L-50K-WH ^o	2 x F32T8/U6	5000K	4,000	40	23-3/4" L x 23-3/4" W x 1/2" H (Panel)
C-LITE™ 2' x 4' Flat Panel						
LED Flat Panel Troffer 2' X 4'	C-TR-A-FP24-50L-35K-WH ^o	3 x F32T8	3500K	5,000	50	47-3/4" L x 23-3/4" W x 1/2" H (Panel)
LED Flat Panel Troffer 2' X 4'	C-TR-B-FP24-50L-40K-WH ^o	3 x F32T8	4000K	5,000	50	47-3/4" L x 23-3/4" W x 1/2" H (Panel)
LED Flat Panel Troffer 2' X 4'	C-TR-B-FP24-50L-50K-WH ^o	3 x F32T8	5000K	5,000	50	47-3/4" L x 23-3/4" W x 1/2" H (Panel)

NOTE: For General LED lighting accessories refer to page 25



^oDLC Standard ♦DLC Premium
Subject to Change.

*See cree.com/canada/warranty for details

LED STRIPS & WRAPS

Easy Installation; High Efficiency; 5 Year Limited Warranty*



2 Ft. LED Linear Wrap



4 Ft. LED Linear Wrap

- Category: LED Strips & Wraps
- CRI: ≥80
- Location Type: Damp
- Voltage: 120-277V
- 0-10V Dimming
- Finish Colour: White
- Watts: 19 or 39
- Mounting Height: 8 to 12 feet

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
C-LITE™ 2 Ft. LED Linear Wrap						
LED Linear Wrap 2-ft.	C-WR-A-WLIN2-24L-30K-WH♦	70W MH	3000K	2,400	19	24 3/8" L x 5 1/8" W x 2 3/4" H
LED Linear Wrap 2-ft.	C-WR-A-WLIN2-24L-35K-WH♦	70W MH	3500K	2,400	19	24 3/8" L x 5 1/8" W x 2 3/4" H
LED Linear Wrap 2-ft.	C-WR-A-WLIN2-24L-40K-WH♦	70W MH	4000K	2,400	19	24 3/8" L x 5 1/8" W x 2 3/4" H
C-LITE™ 4 Ft. LED Linear Wrap						
LED Linear Wrap 4-ft.	C-WR-A-WLIN4-48L-30K-WH°	100PSMH	3000K	4,800	39	48" L x 5 1/8" W x 2 3/4" H
LED Linear Wrap 4-ft.	C-WR-A-WLIN4-48L-35K-WH°	100PSMH	3500K	4,800	39	48" L x 5 1/8" W x 2 3/4" H
LED Linear Wrap 4-ft.	C-WR-A-WLIN4-48L-40K-WH°	100PSMH	4000K	4,800	39	48" L x 5 1/8" W x 2 3/4" H



°DLC Standard ♦DLC Premium
Subject to Change.

*See cree.com/canada/warranty for details



C-LB-A-RDAL
Low Bay with Aluminum Reflector



C-LB-A-RDAC
Low Bay with Prismatic Reflector

LED ROUND LOW BAYS

Easy Installation; High Efficiency; 5 Year Limited Warranty*

- Category: LED Indoor High Bays and Low Bays
- CRI: >70
- Location Type: Damp
- Voltage: 120-277V
- Non-Dimmable
- Finish Colour: White
- High LPW: Up to 124
- Watts: 59
- Cree LEDs, quality driver

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
C-LITE™ Round Low Bay						
LED Round Low Bay	C-LB-A-RDAL-8L-50K-WH♦	150W PSMH 175W MH	5000K	8,000	59	10" H x 14" W x 6-1/2" L Includes 14" Spun Aluminum Reflector
LED Round Low Bay	C-LB-A-RDAL-8L-40K-WH♦	150W PSMH 175W MH	4000K	8,000	59	10" H x 14" W x 6-1/2" L Includes 14" Spun Aluminum Reflector
LED Round Low Bay	C-LB-A-RDAC-8L-50K-WH♦	150W PSMH 175W MH	5000K	8,000	59	10" H x 14" W x 6-1/2" L Includes 14" Clear Acrylic Reflector
LED Round Low Bay	C-LB-A-RDAC-8L-40K-WH♦	150W PSMH 175W MH	4000K	8,000	59	10" H x 14" W x 6-1/2" L Includes 14" Clear Acrylic Reflector

NOTE: For LED High & Low Bay Light Accessories refer to Page 24, for General LED lighting accessories refer to page 25



°DLC Standard ♦DLC Premium
Subject to Change.

*See cree.com/canada/warranty for details

LED LINEAR HIGH BAYS

Easy Installation; High Efficiency; 5 Year Limited Warranty*

- Category: LED Indoor Linear High Bays
- CRI: 80
- Location Type: Damp
- Voltage: 120-277V
- Non-Dimmable, 0-10V
- White
- High LPW: Up to 129
- Watts: 108 to 220



C-HB-A-L4F-20L-50K-WH



C-HB-A-L4F-28L-50K-WH



C-PHB-A-L2F-13L



C-PHB-A-L2F-20L



C-PHB-A-L4F-27L

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
C-LITE™ Linear High Bay						
Linear High Bay	C-HB-A-L4F-20L-50K-WH ^o	4-lamp T5HO 54W 8-lamp T8 32W	5000K	20,500	160	3-1/2" H x 12" W x 47-1/2" L
Linear High Bay	C-HB-A-L4F-28L-50K-WH ^o	6-lamp T5HO 54W	5000K	28,500	220	3-1/2" H x 12" W x 47-1/2" L
C-LITE™ Premium Linear High Bay - 13,000 Lumens						
Premium Linear High Bay	C-PHB-A-L2F-13L-40K-WH ^o	6-lamp T8 32W	4000K	13,000	108	3-3/5" H x 12-3/5" W x 23-4/5" L
Premium Linear High Bay	C-PHB-A-L2F-13L-50K-WH ^o	6-lamp T8 32W	5000K	13,000	108	3-3/5" H x 12-3/5" W x 23-4/5" L
C-LITE™ Premium Linear High Bay - 20,000 Lumens						
Premium Linear High Bay	C-PHB-A-L2F-20L-40K-WH ^o	4-lamp T5HO 54W 8-lamp T8 32W	4000K	20,000	160	3-3/5" H x 17-3/10" W x 23-4/5" L
Premium Linear High Bay	C-PHB-A-L2F-20L-50K-WH ^o	4-lamp T5HO 54W 8-lamp T8 32W	5000K	20,000	160	3-3/5" H x 17-3/10" W x 23-4/5" L
C-LITE™ Premium Linear High Bay - 27,000 Lumens						
Premium Linear High Bay	C-PHB-A-L4F-27L-40K-WH ^o	6-lamp T5HO 54W	4000K	27,000	220	3-3/5" H x 12- 3/5" W x 46" L
Premium Linear High Bay	C-PHB-A-L4F-27L-50K-WH ^o	6-lamp T5HO 54W	5000K	27,000	220	3-3/5" H x 12- 3/5" W x 46" L

NOTE: For LED High & Low Bay Light Accessories refer to Page 24, for General LED lighting accessories refer to page 25

^oDLC Standard ^oDLC Premium
Subject to Change.



*See cree.com/canada/warranty for details




Premium Linear High Bay PIR Sensor



Premium Linear High Bay Pendant Mount Kit



Linear High Bay Frosted Lens



Premium Linear High Bay Wire Guard



LED Hook & Cord Kits



1/2" Hook

LED HIGH & LOW BAY ACCESSORIES

Accessories for C-Lite™ LED High & Low Bays

Item	SKU	Size/Fits
Premium Linear High Bay PIR Sensor	C-PHB-A-HBPIR	Suits C-PHB Series
Premium Linear High Bay Pendant Mount Kit	C-PHB-A-HBPM	Suits C-PHB Series
Linear High Bay Frosted Lens	C-HB-A-LHBFL-12X48	Suits C-HB Series 12" x 47-1/2" Fixtures
Premium Linear High Bay Wire Guard	C-PHB-A-LHBWG-12X24	Suits C-PHB Series 12-3/5" x 23-4/5" Fixtures
Premium Linear High Bay Wire Guard	C-PHB-A-LHBWG-18X24	Suits C-PHB Series 17-3/10" x 23-4/5" Fixtures
Premium Linear High Bay Wire Guard	C-PHB-A-LHBWG-12X46	Suits C-PHB Series 12-3/5" x 46" Fixtures
LED Hook & Cord Kit, 6 ft, 120-277V, No Plug	C-ACC-A-HKCRD-6FT-LV-NP	6ft, 120V-277V, No Plug, Fits 120-277V High Bays / Low Bays
LED Hook & Cord Kit, 6 ft, 120V, Twist Lock Plug	C-ACC-A-HKCRD-6FT-LV-TL	6ft, 120V, Twist Lock Plug, Fits 120V High Bays / Low Bays
LED Hook & Cord Kit, 6 ft, 120V, Straight Blade Plug	C-ACC-A-HKCRD-6FT-LV-SB	6ft, 120V, Straight Blade Plug, Fits 120V High Bays / Low Bays
LED Hook & Cord Kit, 6 ft, 277V, Twist Lock Plug	C-ACC-A-HKCRD-6FT-HV-TL	6ft, 277V, Twist Lock Plug, Fits 277V High Bays / Low Bays
LED Hook & Cord, 208-240V, Twist Lock Plug	C-ACC-A-HKCRD-6FT-MV-TL	6ft, 208-240V, Twist Lock Plug, Fits 208-240V High Bays / Low Bays
1/2" Hook	C-ACC-A-HK12	1/2", Fits High Bays / Low Bays

*See cree.com/canada/warranty for details



Cord, 6 ft. Straight Blade Plug



Cord, 6 ft, Twist Lock Plug



Receptacle, 15A, Twist Lock

GENERAL LED ACCESSORIES

Quality; Reliability

- Voltage: 120-277V

Item	SKU	Size/Fits
LED Cord w-Strain Relief	C-ACC-A-CRDS-6FT-LV-TL	6ft, 120V, Twist Lock Plug, Fits any 120V Fixture
LED Cord w-Strain Relief	C-ACC-A-CRDS-6FT-LV-SB	6ft, 120V, Straight Blade Plug, Fits any 120V Fixture
LED Cord w-Strain Relief	C-ACC-A-CRDS-6FT-HV-TL	6ft, 277V, Twist Lock Plug, Fits any 277V Fixture
LED Cord w-Strain Relief	C-ACC-A-CRDS-6FT-MV-TL	6ft, 208-240V, Twist Lock Plug, Fits any 208-240V Fixture
LED Cord	C-ACC-A-CRD-6FT-LV-TL	6ft, 120V, Twist Lock Plug, Fits any 120V Fixture
LED Cord	C-ACC-A-CRD-6FT-LV-SB	6ft, 120V, Straight Blade Plug, Fits any 120V Fixture
LED Cord	C-ACC-A-CRD-6FT-MV-TL	6ft, 208-240V, Twist Lock Plug, Fits any 208-240V Fixture
LED Cord	C-ACC-A-CRD-6FT-HV-TL	6ft, 277V, Twist Lock Plug, Fits any 277V Fixture
LED Receptacle	C-ACC-A-RECEP-LV-TL	3-Wire, 15A / 120V, Twist Lock
LED Receptacle	C-ACC-A-RECEP-HV-TL	3-Wire, 15A / 277V, Twist Lock
LED Receptacle	C-ACC-A-RECEP-MV-TL	3-Wire, 15A / 208-240V, Twist Lock

*See cree.com/canada/warranty for details



A19



BR30

LED LAMPS

Best Combination of Performance and Value; 5 Year Limited Warranty*

- Category: LED Lamps
- CRl: ≥ 80
- Initial Delivered Lumens: 440 to 1,050
- Dimmable: Yes (-DIM Series)
- Base: E26

Item	SKU	Replaces	CCT	Lumens	Watts	LPW	Base Type	Pack Size
C-LITE™ LED A19 Lamp - Non-dimming								
LED A19 Lamp	C-A19-A-40W-ND-27K-B4	40W Incandescent	2700K	440	5.5	80	E26	4 Pack
LED A19 Lamp	C-A19-A-60W-ND-27K-B4	60W Incandescent	2700K	750	9.0	84	E26	4 Pack
LED A19 Lamp	C-A19-A-60W-ND-30K-B4	60W Incandescent	3000K	750	9.0	84	E26	4 Pack
LED A19 Lamp	C-A19-A-75W-ND-27K-B2	75W Incandescent	2700K	1,050	11.0	95	E26	2 Pack
C-LITE™ LED A19 Lamp - Energy Star - Dimmable								
LED A19 Energy Star Lamp	C-A19-A-40W-DIM-27K-B2	40W Incandescent	2700K	450	6.0	75	E26	2 Pack
LED A19 Energy Star Lamp	C-A19-A-60W-DIM-27K-B2	60W Incandescent	2700K	800	9.0	89	E26	2 Pack
LED A19 Energy Star Lamp	C-A19-A-60W-DIM-30K-B2	60W Incandescent	3000K	800	9.0	89	E26	2 Pack
LED A19 Energy Star Lamp	C-A19-A-75W-DIM-27K-B2	75W Incandescent	2700K	1,100	12.0	92	E26	2 Pack
C-LITE™ LED BR30 Lamp								
LED BR30 Lamp	C-BR30-A-65W-DIM-27K-B2	65W Incandescent	2700K	750	8.5	88	E26	2 Pack
LED BR30 Lamp	C-BR30-A-65W-DIM-30K-B2	65W Incandescent	3000K	800	8.5	94	E26	2 Pack

*See cree.com/canada/warranty for details

PRO
SERIES

PRO SERIES A - LED LAMPS



A19



A21

CREE® PROFESSIONAL SERIES A19 & A21 LED LAMPS

Light your space like a Pro; 5 Year Limited Warranty*

- A19 Series & A21 Series
- CRI: 90+
- Omnidirectional Light
- Smooth Dimming
- Damp Location Rated
- Meets ENERGY STAR, CEC Title 20/Title 24 JA-8 requirements

Item	SKU	Replaces	CCT	Lumens	Watts	LPW	Base Type
Cree® Pro Series LED A19 Lamp							
Pro Series A19 LED Lamp	A19-40W-P1-27K-E26-U1	40W Incandescent	2700K	460	5.5	84	E26
Pro Series A19 LED Lamp	A19-40W-P1-30K-E26-U1	40W Incandescent	3000K	460	5.5	84	E26
Pro Series A19 LED Lamp	A19-40W-P1-50K-E26-U1	40W Incandescent	5000K	460	5.5	84	E26
Pro Series A19 LED Lamp	A19-60W-P1-27K-E26-U1	60W Incandescent	2700K	815	10	81	E26
Pro Series A19 LED Lamp	A19-60W-P1-30K-E26-U1	60W Incandescent	3000K	815	10	81	E26
Pro Series A19 LED Lamp	A19-60W-P1-40K-E26-U1	60W Incandescent	4000K	815	10	81	E26
Pro Series A19 LED Lamp	A19-60W-P1-50K-E26-U1	60W Incandescent	5000K	815	10	81	E26
Pro Series A19 LED Lamp	A19-75W-P1-27K-E26-U1	75W Incandescent	2700K	1,100	12	92	E26
Pro Series A19 LED Lamp	A19-75W-P1-30K-E26-U1	75W Incandescent	3000K	1,100	12	92	E26
Pro Series A19 LED Lamp	A19-75W-P1-50K-E26-U1	75W Incandescent	5000K	1,100	12	92	E26
Cree® Pro Series LED A21 Lamp							
Pro Series A21 LED Lamp	A21-100W-P1-27K-E26-U1	100W Incandescent	2700K	1,600	17	94	E26
Pro Series A21 LED Lamp	A21-100W-P1-30K-E26-U1	100W Incandescent	3000K	1,600	17	94	E26
Pro Series A21 LED Lamp	A21-100W-P1-50K-E26-U1	100W Incandescent	5000K	1,600	17	94	E26
Pro Series A21 3-Way LED Lamp	A21-3WAY-P1-27K-E26-U1	3 Way Incandescent	2700K	450/ 800/ 1,420	5.5/ 9/17	84	E26

*See cree.com/canada/warranty for details



PAR38

CREE® PROFESSIONAL SERIES PAR38 LED LAMPS

Light your space like a Pro; 5 Year Limited Warranty*

- PAR38 Series
- Focused 40° flood beam
- 90+ CRI
- Smooth Dimming
- Meets ENERGY STAR, CEC Title 20/Title 24 JA-8 requirements

Item	SKU	Replaces	CCT	Lumens	Watts	LPW	Base Type
Cree® Pro Series LED PAR38 Lamp							
Pro Series PAR38 LED Lamp	PAR38-150W-30K-40FL-E26-U1	150W Incandescent	3000K	1,500	19	79	E26

*See cree.com/canada/warranty for details

CREE® PROFESSIONAL SERIES BR30, BR40 & R20 LED LAMPS

PRO SERIES

PRO SERIES REFLECTOR LED LAMPS

Optimal for recessed downlights and track lights; 5 Year Limited Warranty*

- BR30, BR40 & R20 Series
- CRI: 90+
- Flood Lighting
- Smooth Dimming
- Damp Location Rated
- Meets ENERGY STAR, CEC Title 20/Title 24 JA-8 requirements



BR30



BR40



R20

Item	SKU	Replaces	CCT	Lumens	Watts	LPW	Base Type
Cree® Pro Series LED BR30 Lamp							
Pro Series BR30 LED Lamp	BR30-65W-27K-U1	65W Incandescent	2700K	665	8.8	76	E26
Pro Series BR30 LED Lamp	BR30-65W-30K-U1	65W Incandescent	3000K	665	8.8	76	E26
Pro Series BR30 LED Lamp	BR30-65W-40K-U1	65W Incandescent	4000K	665	8.8	76	E26
Pro Series BR30 LED Lamp	BR30-100W-P1-27K-E26-U1	100W Incandescent	2700K	1,400	16	87	E26
Pro Series BR30 LED Lamp	BR30-100W-P1-30K-E26-U1	100W Incandescent	3000K	1,400	16	87	E26
Pro Series BR30 LED Lamp	BR30-100W-P1-50K-E26-U1	100W Incandescent	5000K	1,400	16	87	E26
Cree® Pro Series LED BR40 Lamp							
Pro Series BR40 LED Lamp	BR40-120W-P1-27K-E26-U1	120W Incandescent	2700K	1,750	23	76	E26
Pro Series BR40 LED Lamp	BR40-120W-P1-30K-E26-U1	120W Incandescent	3000K	1,750	23	76	E26
Pro Series BR40 LED Lamp	BR40-120W-P1-50K-E26-U1	120W Incandescent	5000K	1,750	23	76	E26
Cree® Pro Series LED R20 Lamp							
Pro Series R20 LED Lamp	R20-50W-P1-27K-E26-U1	50W Incandescent	2700K	560	7	80	E26
Pro Series R20 LED Lamp	R20-50W-P1-50K-E26-U1	50W Incandescent	5000K	560	7	80	E26
Pro Series R20 LED Lamp	R20-75W-P1-27K-E26-U1	75W Incandescent	2700K	980	13	75	E26
Pro Series R20 LED Lamp	R20-75W-P1-50K-E26-U1	75W Incandescent	5000K	980	13	75	E26

*See cree.com/canada/warranty for details



B11

CREE® PROFESSIONAL SERIES B11 LED LAMPS



Optimal for decorative lighting, chandeliers, and ceiling fans; 5 Year Limited Warranty*

- Category: LED Lamps
- B11 Series
- Clear glass shell offers omnidirectional light
- 90+ CRI
- Smooth Dimming
- Meets ENERGY STAR, CEC Title 20/Title 24 JA-8 requirements

Item	SKU	Replaces	CCT	Lumens	Watts	LPW	Base Type
Cree® Pro Series LED B11 Lamp							
Pro Series B11 LED Lamp	B11-25W-P1-27K-E12-U1	25W Incandescent	2700K	220	2.6	85	E12
Pro Series B11 LED Lamp	B11-25W-P1-50K-E12-U1	25W Incandescent	5000K	220	2.6	85	E12
Pro Series B11 LED Lamp	B11-40W-P1-27K-E12-U1	40W & 60W Incandescent	2700K	350	4	87	E12
Pro Series B11 LED Lamp	B11-40W-P1-50K-E12-U1	40W & 60W Incandescent	5000K	350	4	87	E12
Pro Series B11 LED Lamp	B11-60W-P1-27K-E12-U1	40W & 60W Incandescent	2700K	515	5.5	94	E12
Pro Series B11 LED Lamp	B11-60W-P1-50K-E12-U1	40W & 60W Incandescent	5000K	515	5.5	94	E12

*See cree.com/canada/warranty for details

Learn more at: c-lite.ca and cree.com/canada | 800.473.1234

PRO
SERIES

C-LITE
LED LIGHTING BY CREE

CREE 

©2018 Cree, Inc. All rights reserved. For informational purposes only. Not a warranty or specification. Cree® is a registered trademark and C-Lite™, the C-Lite logo and Cree™ are trademarks of Cree Inc. ENERGY STAR® is a registered trademark of U.S. EPA. CAT/CREE-0515 Rev. Date 10/24/2018