


dweLED

by WAC Lighting

LED Pendants + Chandeliers.....	3-88
LED Ceiling Mounts.....	89-108
LED Sconces + Bath.....	109-148
LED Sconces.....	149-174
LED Display + Picture.....	175-180
LED Bedside Wall + Swing Arms.....	181-188
LED Outdoor.....	189-236









LED Pendants + Chandeliers

Generations of design trends are more forgiving of clean proportions than ornate decorations, but good lighting design is always a welcome constant.

This is the guiding principle behind our dweLED offering of LED Pendants and Chandeliers. Stunning additions to commercial offices or kitchen islands, dweLED pendants have been specified into hundreds of designs.

Custom engineered modules with perfectly spaced LED arrays ensure even illumination for an immaculate impression. Universal Dimming (ELV or 0-10V) and Universal Voltage (120V-220V-277V) are standard features in many of these designs, and everything in the line typically ships within 48 hours.

Houdini

4, 6 & 12 Light LED Chandeliers



TITLE 24
CALIFORNIA



PD-55912-BN shown



PD-55906-BK/AB shown

Houdini

4, 6 & 12 Light LED Chandeliers




TITLE 24
CALIFORNIA




PD-55904-BK/AB shown


Waving wands deliver cutting edge LED magic.



PD-55912




PD-55906



PD-55904

- Color Temp: 3000K
- CRI: 90
- Dimming: 100% - 10% ELV
- Rated Life: 36,000 hours
- Input: 120-277V



- Frosted acrylic rod diffuser on dual planar rotatable aluminum bars
- Driver located within the canopy
- Integral swivel for sloped ceilings
- Three 12 inch and one 6 inch rods included (additional extension rods available)

	Light	Watt	LED Lumens	Delivered Lumens	Finish
PD-55904	4	11W	457	287	BK/AB Black /Aged Brass BN Brushed Nickel 
PD-55906	6	16W	658	427	
PD-55912	12	31W	1370	796	

Example: PD-55906-BK/AB

Solaris

40" LED Pendant & Ceiling Mount



PD-94940

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV / 0-10V / Triac
Rated Life: 50,000 hours
Input: 120V-277V

- Aluminum body with composite diffuser for desired look
- Driver located within the canopy
- Universal voltage driver (120V-220V-277V) concealed within fixture
- Integral swivel for sloped ceilings
- Three 12" and one 6" downrod included (additional downrods available)

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-94940	40"	31W	2098	1329	AB Aged Brass BK Black CH Chrome

Example: **PD-94940-AB**

Solaris


40" LED Pendant & Ceiling Mount



Three rings. One perfect look. A true design statement.

Charmed


24", 32" & 34" LED Chandelier




PD-54932-BN shown

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV / 0-10V / Triac
Rated Life: 54,000 hours
Input: 120-277V

- Classic chain-link aluminum body design with composite diffuser
- Thin powered cables provide an ultra-clean look
- Driver concealed within the canopy
- Can be mounted on a sloped ceiling



	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-54924	24"	37W	3000	2000	BN Brushed Nickel SG Soft Gold 
PD-54932	32"	94W	6400	4230	
PD-54934	34"	112W	8000	5210	

Example: **PD-54924-SG**

Charmed

24", 32" & 34" LED Chandelier

ETL LISTED us DAMP TITLE 24 CALIFORNIA



PD-54934-SG shown

Radiance. Elegance defined.

Divergence


44" & 64" LED Chandelier



PD-60944-CH shown

- Color Temp:** 3000K
- CRI:** 90
- Dimming:** 100% - 10% ELV / 0-10V / Triac (PD-60964)
100% - 10% ELV (PD-60944)
- Rated Life:** 50,000 hours
- Input:** 120V-277V (PD-60944 120V Only)

- Flowing pattern extruded aluminum body with composite diffuser
- Thin powered aircraft cables provide an ultra-clean look
- Driver concealed within the canopy
- Can be mounted on a sloped ceiling




	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-60944	44"	93W	7458	4293	CH Chrome
PD-60964	64"	82W	8550	5603	

Example: **PD-60944-CH**

Divergence

44" & 64" LED Chandelier



Flowing bands of light converge in this unique and striking pendant.

Vornado

20", 23" & 35" Linear LED Pendant



Color Temp: 3000K
CRI: 90
Dimming: 100%–5% ELV, 0-10V (20")
 100%–10% ELV (23" & 35")
Rated Life: 60,000 hours
Input: 120–277V


- Aluminum hardware, extruded composite diffuser
- Hand-crafted, seamless construction
- Thin powered cables provide an ultra-clean look
- Can be mounted on a sloped ceiling
- Universal voltage driver (120V-220V-277V) concealed within canopy
- PD-87720 is Title 24 compliant



PD-87720-WT shown



PD-87735-CH shown



Vornado

20", 23" & 35" Linear LED Pendant



PD-87723-CH shown



	Size	Watt	Led Lumens	Delivered Lumens	Finish
PD-87720	20"	30.5W	2825	2075	
PD-87723	23"	52W	5106	3110	WT White
PD-87735	35"	52W	5278	3550	CH Chrome

Example: **PD-87723-CH**

Vornado

29" & 41" LED Pendant




TITLE 24
CALIFORNIA



PD-87729-CH shown

Color Temp: 3000K
CRI: 90
Dimming: 100% -10% ELV
 100%-5%; 0-10V
Rated Life: 50,000 hours
Input: 120-277V

- Aluminum body with composite diffuser
- Hand-crafted, seamless construction
- Thin powered aircraft cables provide an ultra-clean look
- Can be mounted on a sloped ceiling
- Universal voltage driver (120V-220V-277V) concealed within canopy



Vornado

29" & 41" LED Pendant



TITLE 24
CALIFORNIA



PD-87741-CH shown

Bands of silver and light twist in and out like a Möbius strip.

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-87729	29"	87W	7766	5375	CH Chrome 
PD-87741	41"	87W	7818	5861	

Example: **PD-87729-CH**

Interlace


28" & 39" LED Pendant



PD-47839-CH shown

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
 100%-5%; 0-10V
Rated Life: 54,000 hours
Input: 120V-277V

- Aluminum body with composite diffuser
- Two seamless interlocked loops
- Thin powered aircraft cables provide an ultra-clean look
- Can be mounted on a sloped ceiling
- Universal voltage driver (120V-277V) concealed within canopy



Interlace

28" & 39" LED Pendant



Delicate bands of light weave playfully in and out on this flowing modern design. A continuous construction, a flexible diffuser, and powered aircraft cable suspension complete an overall clean, seamless look.

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-47828	28"	57W	4853	3263	CH <i>Chrome</i> 
PD-47839	39"	57W	4734	3241	

Example: **PD-47828-CH**

Tumbling


20", 25", 33", & 54" LED Pendant



TITLE 24
CALIFORNIA



PD-46920 shown



PD-46925 shown




PD-46933 shown

Color Temp: 3500K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours
Input: 120-277V


- Crystal block ring aluminum bands
- Can be mounted on a sloped ceiling
- Thin powered aircraft cables provide an ultra-clean look
- Driver concealed within the canopy



PD-46920



PD-46925



PD-46933

Tumbling


20", 25", 33", & 54" LED Pendant




TITLE 24
CALIFORNIA

PD-46954 shown

Symmetry in design meets
the future of LED technology.



	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-46920	20"	37W	2550	1400	CH Chrome 
PD-46925	25"	32W	2210	1220	
PD-46933	33"	50W	3450	1900	
PD-46954	54"	102W	7050	3880	

Example: **PD-46954-CH**

Orbit

32" & 48" LED Pendant




TITLE 24
CALIFORNIA



Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours
Input: 120V

- Aluminum with acrylic diffuser
- Thin powered cables provide an ultra-clean look
- Driver concealed within the canopy
- Can be mounted on a sloped ceiling
- Two adjustable orbital light bands for various displays options



	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-48932	32"	54W	4850	2700	BK Black
PD-48948	48"	95W	8550	4750	SN Satin Nickel

Example: **PD-48932-SN**

Orbit

32" & 48" LED Pendant



TITLE 24
CALIFORNIA

Streaks of light orbit an invisible circumference.

Voyager

1, 2 & 3 Light LED Pendant




TITLE 24
CALIFORNIA



Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours
Input: 120-277V

- Aluminum with acrylic diffuser
- Thin powered aircraft cables provide an ultra-clean look
- Can be mounted on a sloped ceiling
- Driver concealed within the canopy



	Rings	Watt	LED Lumens	Delivered Lumens	Finish
PD-40901	1	63W	2160	1270	BK Black SN Satin Nickel <div style="display: flex; align-items: center; margin-top: 5px;"> <div style="width: 20px; height: 10px; background-color: black; margin-right: 5px;"></div> <div style="width: 20px; height: 10px; background-color: #cccccc; margin-right: 5px;"></div> </div>
PD-40902	2	70W	3530	2060	
PD-40903	3	122W	5550	3150	

Example: **PD-40903-SN**

Voyager

1, 2 & 3 Light LED Pendant



A gateway to another world of design and technology.


PD-40902-BK shown

Corso


18", 32", 43" & 53" LED Pendant




TITLE 24
CALIFORNIA




PD-33718



PD-33732




PD-33753



PD-33743

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
 100% - 5% 0-10V
Rated Life: 75,000 hours
Input: 120V-277V

- Acrylic diffuse to provide even illumination with no LED hotspots
- Thin powered aircraft cables provide an ultra-clean look
- Can be mounted on sloped ceiling
- Universal voltage driver (120V-220V-277V) concealed within canopy

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-33718	18"	22W	1495	940	WT White BK Black AL Brushed Aluminum 
PD-33732	32"	88W	6340	4435	
PD-33743	43"	125W	11115	7300	
PD-33753	53"	169W	12028	8458	

Example: **PD-33732-BK**

Corso

18", 32", 43" & 53" LED Pendant

ETL LISTED us DAMP TITLE 24 CALIFORNIA



PD-33743-AL shown

Cleverly hidden LED modules and a circular frosted diffuser floating inside a halo of spun aluminum.

Vida

18" & 24" LED Pendant




TITLE 24
CALIFORNIA



Color Temp: 3000K
CRI: 90
Dimming: 100% - 5% ELV / 0-10V
Rated Life: 52,000 hours
Input: 120V-277V

- Thin powered aircraft cables provide an ultra-clean look
- LED modules positioned on tapered platform for more even illumination
- Can be mounted on a sloped ceiling
- Universal voltage driver (120V-220V-277V) concealed within canopy



	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-72718	18"	33W	2450	1755	WT White BK Black AL Brushed Aluminum
PD-72724	24"	43W	3235	2385	

Example: **PD-72718-BK**

Vida

18" & 24" LED Pendant



TITLE 24
CALIFORNIA



PD-72724-AL shown

A refreshing take on a traditional shape, the Vida pendant is crafted from high-quality spun aluminum, now finished in elegant black or white in addition to brushed aluminum. Inside, a powerful integrated LED array projects flawless light time and again.



Illusion

27" & 35" LED Pendant




TITLE 24
CALIFORNIA

±
1/2"
↑
↓



Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV/ 0-10V/Triac
Rated Life: 44,000 hours
Input: 120V-277V

- Ultra thin 1/2" edge-lit disc
- Edge-lit panel evenly illuminates up & down
- Thin powered aircraft cables provide an ultra-clean look
- Universal voltage driver (120V-277V) concealed inside canopy
- Can be mounted on a sloped ceiling



	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-31727	27"	54W	5253	3580	TT Titanium 
PD-31735	35"	85W	7391	4366	BK Black 

Example: **PD-31735-BK**

Illusion

27" & 35" LED Pendant




TITLE 24
CALIFORNIA



Spectacular halo of direct and indirect light from an impossible form.


Stack

3, 6 & 9 Light LED Chandeliers



- Aluminum hardware and extruded acrylic diffuser
- Thin color matched powered aircraft cables and hardware
- Height and slope of each strip can be individually adjusted for personalization
- Can be mounted on a sloped ceiling
- Universal voltage driver (120V-277V) concealed within canopy

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
 100% - 5% 0-10V
Rated Life: 50,000 hours
Input: 120-277V




	Lights	Watt	LED Lumens	Delivered Lumens	Finish
PD-29803	3	42W	4938	3950	AL Brushed Aluminum BK Black
PD-29806	6	84W	9876	7900	
PD-29809	9	126W	14814	11850	

Example: **PD-29809-AL**

Stack

3, 6 & 9 Light LED Chandeliers



A clean look no matter how you hang it



Frame

28" & 58" LED Pendant




TITLE 24
CALIFORNIA



Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV; 100%-3% 0-10V
Rated Life: 50,000 hours*
Input: 120V-277V

- Aluminum hardware and extruded acrylic diffuser
- Crisp mitered joints
- Thin color matched powered aircraft cables and hardware
- Can be mounted on a sloped ceiling
- Universal voltage driver (120V-277V) concealed within canopy



	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-29828	28"	55W	6334	5131	BK Black AL Brushed Aluminum
PD-29858	58"	58W	7160	5800	

Example: **PD-29828-AL**

Frame

28" & 58" LED Pendant



An extruded acrylic diffuser with mitered edges gives this design a clean, elevated look, evenly spreading the powerful LED light for a geometric illumination that matches back to the rectilinear canopy.

Trap

20", 27" & 38" LED Pendant



PD-95820-BK shown




TITLE 24
CALIFORNIA




PD-95827-WT shown




PD-95838-CH shown



PD-95820



PD-95827



PD-95838

Trap


20", 27" & 38" LED Pendant



Futuristic design meets top-tier technology.

Color Temp: 3000K
CRI: 90
Dimming: 100%–10% ELV; 0–10V
Rated Life: 50,000 hours
Input: 120V–277V

- Thin powered aircraft cables match overall finish
- Can be mounted on a sloped ceiling
- Universal voltage driver (120V–277V) concealed within canopy

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-95820	20"	35W	2488	1914	CH Chrome BK Matte Black WT Matte White 
PD-95827	27"	65W	4759	3953	
PD-95838	38"	79W	5580	4293	


Example: **PD-95820-BK**

Radius

2 & 3 Light LED Chandeliers





TITLE 24
CALIFORNIA



Color Temp: 3000K
CRI: 90
Dimming: 100%-10% ELV;
 100%-5%; 0-10V
Rated Life: 50,000 hours*
Input: 120V-277V

- Thin color matched powered aircraft cables and hardware
- Multiple hanging options allow for personalization
- Can be mounted on a sloped ceiling
- Universal voltage driver (120V-277V) concealed within canopy



	Lights	Watt	LED Lumens	Delivered Lumens	Finish
PD-27802	2	58W	6444	5220	BK Black 
PD-27803	3	86W	9767	7912	AL Brushed Aluminum

Example: **PD-27803-AL**

Radius

2 & 3 Light LED Chandeliers




Long graceful stems of aluminum and light create a beautiful display that is both function and modern art. With versatile hanging options, Radius lets you put a personal touch on any room. Choose two or three stems in brushed aluminum or black.

Bossa Nova

34", 38", 44" & 54" LED Chandelier





TITLE 24
CALIFORNIA



Color Temp: 3000K
CRI: 90
Dimming: 100%–10% ELV; 100%–5% 0–10V
Rated Life: 50,000 hours
Input: 120V–277V

- Mouth-blown opal glass
- Easy-to-assemble design with quick connections
- Interchangeable rods are varied in length for personal customization (PD-93834/PD-93844)
- Three 12" and one 6" downrod included
- Can be mounted on a sloped ceiling
- Universal voltage driver (120V-277V) concealed within fixture



	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-93834	34"	44W	3492	2998	BK <i>Black</i> 
PD-93838	38"	66W	5389	4391	
PD-93844	44"	44W	4110	2983	
PD-93854	54"	88W	7394	6158	

Example: **PD-93854-BK**

Bossa Nova

34", 38", 44" & 54" LED Chandelier



TITLE 24
CALIFORNIA



PD-93834-BK shown

With its contrast of simple shapes, Bossa Nova captures the formal energy of Mid-Century modernism, but adds a high-tech twist with cutting-edge LED light and an installation-friendly design.


Ronin

44" LED Pendant



Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV, 0-10V Triac
Rated Life: 50,000 hours
Input: 120V-277V

- Aluminum body with acrylic diffuser
- Ten adjustable points of illumination for customization
- Three 12" and one 6" downrods included (additional downrods available)
- Driver concealed within the canopy



PD-63944

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-63944	44"	30W	2566	1834	BK <i>Black</i> 

Example: **PD-63944-BK**

Ronin

44" LED Pendant



TITLE 24
CALIFORNIA

An umbrella of light powered by cutting edge LED technology.



Trick Box

47" LED Pendant





TITLE 24
CALIFORNIA



Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV ; 0-10V ; Triac
Rated Life: 50,000 hours
Input: 120V-277V

- Super thin, edge-lit LED panel illuminates up and down
- Thin powered aircraft cables provide an ultra-clean look
- Driver concealed within the canopy
- Can be mounted on a sloped ceiling




	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-31947	47"	22W	2125	1212	BK Black 

Example: **PD-31947-BK**

Trick Box

47" LED Pendant




Cutting edge illumination in a smart, geometric design.

Omega


28" LED Pendant

DAMP TITLE 24
CALIFORNIA



Color Temp: 3000K
CRI: 90
Dimming: 100%–10% ELV, 100%–5% 0–10V / Triac
Rated Life: 50,000 hours*
Input: 120V–277V

- Hidden LED modules point at contrast ridges and reflect light downward for broad, even illumination
- Thin powered aircraft cables provide an ultra-clean look
- Universal voltage driver (120V–277V) concealed within canopy
- Can be mounted on a sloped ceiling




	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-21828	28"	33W	2426	864	BK/GR Black/Gold Ribbed WT/GR White/Gold Ribbed 

Example: **PD-21828-WT/GR**

Omega

28" LED Pendant


 **TITLE 24**
DAMP CALIFORNIA



Modern matte finishes and a lustrous contrast of intricate gold ridges.

$$E=MC^2$$


47" Linear LED Pendant



Relatively, speaking. An engineering marvel.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 36,000 hours
Input: 120V- 277V

- Impossibly tiny at just a half inch tall by a half inch wide
- Adjustable leveler provides custom positioning
- Solid aluminum construction
- Cable suspension carrying low voltage may be field shortened
- 2.76" X 1.26" X 1.18" Universal voltage driver
- (120V-220V-277V) Installs within a junction box.



E=MC²

47" Linear LED Pendant



	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-45747	47"	30W	1770	1190	AL <i>Brushed Aluminum</i> BK <i>Brushed Black</i>

Example: **PD-45747-AL**

Vanity


23" LED Pendant



Swivels to adjust light in any direction as inspired by vanity mirrors.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 35,000 hours
Input: 120 - 277V

- Ultra thin 1/2" thick edge-lit disc
- Edge-lit panel illuminates up & down
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V) installs within a junction box
- Vertical and horizontal rotating panel gives 350° directional lighting
- Three 12" and one 6" downrods included (additional downrods available)



*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-60723	23"	28W	3160	1895	TT Titanium 

Example: **PD-60723-TT**

Level

48" & 65" Linear LED Pendant




p. 169 Bath / Sconce

Balanced, consistent lighting elevated.
Remarkable edge-lit linear blade just 1/2" wide.

- Color Temp:** 3500K
- CRI:** 90
- Dimming:** 100% - 10% ELV
- Rated Life:** 84,000 hours
- Input:** 120V (277V special order)

- Edge-lit magic
- Ultra thin profile
- Edge-lit LED panel illuminates, providing ambient light
- Frosted diffuser provides even illumination
- 2.00" x 1.38" x 1.02" transformer located in junction box



*Transformer installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-85648	48"	35W	1620	1565	AL Brushed Aluminum
PD-85665	65"	45W	2100	2015	

Example: **PD-85648-AL**
For 277V, add an "F" before the finish: **PD-85665F-AL**

Line

48" Linear LED Pendant




Edge-lit magic.

The profile of this direct and indirect pendant is under an inch thick.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 80,000 hours
Input: 120V (277V special order)

- Super thin, edge-lit LED panels illuminate up and down
- Integral swivel for sloped ceilings
- Six 12" and two 6" downrods included (additional downrod sold separately)
- 2.00" X 1.38" X 1.02" transformer



*Transformer installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-51148-30	48"	48W	4435	3055	AL Brushed Aluminum
					BK Black 

Example: **PD-51148-30-BK**

For 277V, add an "F" before the color temperature: **PD-51148F-30-BK**

Loophole


52" Linear LED Pendant



Luminous loophole. Clever design details like weighted fasteners that keep the pendant level.

Color Temp: 3000K
CRI: 90
Dimming: 100%–5% ELV
Rated Life: 50,000 hours
Input: 120V–277V

- Flexible composite diffuser
- Thin powered aircraft cables provide an ultra-clean look
- Suspension height can be adjusted easily with quick release
- Fasteners maintain tension to hold fixture level
- Can be mounted on a sloped ceiling
- Universal voltage driver (120V–277V) concealed within canopy



	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-23852	52"	42W	4261	2733	AL <i>Brushed Aluminum</i> BK <i>Black</i>

Example: **PD-23852-BK**



Volo

54" Linear LED Pendant




Wishful lighting.

Ultra thin pendant for the discerning minimalist

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 54,000 hours
Input: 120V (277V special order)

- Solid aluminum construction
- Luminous linear luminaire with beautiful brushed metal
- Frosted diffuser provides even illumination
- Cable suspension carrying low voltage may be field shortened
- Transformer located inside the canopy
- Brushed and anodized metal finishes



	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-22754	54"	56W	3095	2535	AL <i>Brushed Aluminum</i> BK <i>Brushed Black</i>


Example: **PD-22754-AL**
 For 277V, add an "F" before the finish: **PD-22754F-AL**

Flare


13", 25", 37" & 45" Mini LED Pendant




Symmetrical, cylindrical and aerodynamic.
Brilliance alone or as a collection.



PD-70913



PD-70925



PD-70937

PD-70945


Flare

13", 25", 37" & 45" Mini LED Pendant



Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV / 0-10V / Triac
Rated Life: 50,000 hours
Input: 120V-277V

- Aluminum hardware with extruded acrylic diffuser
- Three 12" and one 6" downrods included (additional downrods available)
- Universal driver (120V-277V) concealed within the canopy

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-70913	13"	11W	1099	745	BN Brushed Nickel BK Black 
PD-70925	25"	27W	2426	1700	
PD-70937	37"	37W	3801	2637	
PD-70945	45"	42W	4254	2853	

Example: **PD-70945-BN**

Twinkle Twinkle

13" Mini LED Pendant




TITLE 24
DAMP CALIFORNIA



More than meets the eye

Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10% ELV/0-10V/ Triac (120V)
 100% - 10% 0-10V (277V)
 Rated Life: 42,000 hours
 Input: 120V

- Aluminum body with acrylic diffuser at the bottom and glass diffuser at the top
- Thin powered aircraft cables provide an ultra-clean look
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-277V) installs within a junction box



PD-22912

*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-18913	13"	7W	513	458	BK Black CH Chrome

Example: **PD-18913-CH**

Tenor

12" Mini LED Pendant



Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10% ELV/ 0-10V/Triac (120V)
 100% - 10% 0-10V (277V)
 Rated Life: 52,000 hours
 Input: 120V-277V

- Thin powered aircraft cable provide an ultra-clean look
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-277V)
- Can be mounted on a sloped ceiling



PD-14912

*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-14912	12"	7.8W	513	458	BK <i>Black</i> SN <i>Santin Nickel</i>

Example: **PD-14912-SN**

Vodus

6" Mini LED Pendant



Classic, conventional style with modern LED technology. A winner in any space.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV/0-10V/Triac (120V)
 100% - 10% 0-10V (277V)
Rated Life: 42,000 hours
Input: 120V-277V

- Aluminum body with glass shade surrounding a white diffuser design
- Thin powered aircraft cables provide an ultra-clean look
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-277V)
- Can be mounted on a sloped ceiling



PD-16906

*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-16906	6"	8.5W	897	510	BK Black CH Chrome

Example: **PD-16906-BK**

Smore

11" Mini LED Pendant



Delicious pillows of minimalist style.



Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV/0-10V / Triac (120V)
 100% - 10% 0-10V (277V)
Rated Life: 42,000
Input: 120V-277V

- Aluminum body with acrylic diffuser
- Up and down illumination
- Thin powered aircraft cables provide an ultra-clean look
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-277V)
- Can be mounted on a sloped ceiling



PD-34911

*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-34911	11"	10.6W	871	699	BK Black CH Chrome

Example: **PD-34911-BK**

Smash

11" Mini LED Pendant



An alluring pendant all on its own, in multiples

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV/ 0-10V/ Triac (120V)
 100% - 10% 0-10V (277V)
Rated Life: 42,000 hours
Input: 120V-277V

- Aluminum hardware
- Double acrylic diffuser enclosed design
- Thin powered aircraft cables provide an ultra-clean look
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-277V)
- Can be mounted on a sloped ceiling



PD-12911

*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-12911	11"	5.7W	390	340	BK Black
					CH Chrome

Example: **PD-12911-BK**

Enterprise


12" Mini LED Pendant



An enigmatic ring of light.


Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV/ 0-10V/ Triac
 (120V) 100% - 10% 0-10V (277V)
Rated Life: 42,000 hours
Input: 120V-277V

- Acrylic diffuser encircle glass shade for a unique look
- Thin powered aircraft cables provide an ultra-clean look
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-277V)
- Can be mounted on a sloped ceiling



PD-36912

*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-36912	12"	12.7W	1070	540	BK Black SN Satin Nickel 

Example: **PD-36912-SN**

Vornado



7" Mini LED Pendant



Color Temp: 3000K
CRI: 90
Dimming: 100%-10% ELV
Rated Life: 54,000 hours
Input: 120V-277V

- Hand-crafted, seamless construction, variation expected
- Thin powered aircraft cables provide an ultra-clean look
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-277V)
- The 24 available for special order (driver within the canopy)
- Can be mounted on a sloped ceiling

Canopy dimensions :



PD-84907

*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-84907	7"	14W	1410	943	CH Chrome

Example: **PD-84907-CH**

For the Title 24 option, add "T24" before the finish: **PD-84907-T24-CH**

Vornado

7" Mini LED Pendant



Seamless curves flow infinitely.

Action

8" Mini LED Pendant



TITLE 24
CALIFORNIA




Drops of liquid metal, alone or in multiples for a futuristic look.


Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours
Input: 120V-277V

- Retro style metal housing with die-cast etched acrylic diffuser
- Thin powered aircraft cables provide an ultra-clean look
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-277V)
- The 24 available for special order (driver within the canopy)
- Can be mounted on a sloped ceiling

Canopy dimensions :



Standard



T24 Option

*Driver installs within a junction box



PD-76908

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-76908	8"	8W	674	573	CH Chrome AB Aged Brass BK Black

Example: **PD-76908-AB**

For the add 24, add "T24" before the finish: **PD-76908-T24-AB**

Dimple

9" Mini LED Pendant



Elegance and simplicity partner for a classic statement.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 54,000 hours
Input: 120V-277V

- Twist on glass diffuser
- Thin powered aircraft cables provide an ultra-clean look
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-277V)
- Can be mounted on a sloped ceiling

Canopy dimensions :



PD-64909

*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-64909	9"	11W	763	654	BN <i>Brushed Nickel</i> BK <i>Black</i>

Example: **PD-64909-BK**
 For the 24 option, add "T24" before the finish: **PD-64909-T24-BK**

Future

12" Mini LED Pendant

TITLE 24
CALIFORNIA



PD-72912-BN shown




PD-72912-BK shown




Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours
Input: 120-277V

- Retro style aluminum housing
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)
- The 24 available for special order (driver within the canopy)
- Can be mounted on a sloped ceiling


Canopy dimensions :



Standard



T24 Option



PD-72912

*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-72912	12"	9W	302	71	BN <i>Brushed Nickel</i> AB <i>Aged Brass</i> BK <i>Black</i>



Example: **PD-72912-BN**
For the 24 option add "T24" before the finish: **PD-72912-T24-BN**

Future

12" Mini LED Pendant



Take to the future.

PD-72912-AB shown

Crater



8" Mini LED Pendant




Luxury in layers. A modern take on classic sophistication.

Color Temp: 3500K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours
Input: 120-277V

- Aluminum hardware with clear glass and bubbled acrylic diffuser at the center with balancing pin adjuster
- Thin powered aircraft cables provide an ultra-clean look
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)
- The 24 available for special order (driver within the canopy)
- Can be mounted on a sloped ceiling



*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-98908	8"	6W	338	315	AB Aged Brass 

Example: **PD-98908-AB**
 For the 24 option, add "T24" before the finish: **PD-98908-T24-AB**

Passion

8" Mini LED Pendant



TITLE 24
CALIFORNIA



Color Temp: 3500K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 54,000 hours
Input: 120-277V

- Pattern glass with bubbled acrylic
- Thin powered aircraft cables provide an ultra-clean look
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)
- Can be mounted on a sloped ceiling
- The 24 available for special order (driver within the canopy)

Canopy dimensions :



*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-58908	8"	6W	400	251	CH Chrome

Example: **PD-58908-CH**
 For the 24 option add "T24" before the finish: **PD-58908-T24-CH**

Blast Off

13" Mini LED Pendant




Atmospheric, simple and powerful.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours
Input: 120-277V

- Retro style aluminum with die cast acrylic diffuser
- Thin powered aircraft cables provide an ultra-clean look
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)
- The 24 available for special order (driver within the canopy)
- Can be mounted on a sloped ceiling

Canopy dimensions :



PD-62913

*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-62913	13"	8W	625	531	CH Chrome BK Black WT White

Example: **PD-62913-BK**
 For the 24 option add "T24" before the finish: **PD-62913-T24-BK**

Charmed

4" LED Pendant




Off the chain brilliance, alone or in pairs.

PD-54901-BN shown


PD-54901-SG shown

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 54,000 hours
Input: 120-277V

- Extruded aluminum body with compose diffuser
- Thin powered aircraft cables provide an ultra-clean look
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)
- The 24 available for special order (driver within the canopy)
- Can be mounted on a sloped ceiling



Canopy dimensions :



PD-54901

*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-54901	4"	15W	1100	757	SG Soft Gold BN Brushed Nickel

Example: **PD-54901-SG**
 For the 24 option add "T24" before the finish: **PD-54901-T24-SG**

Tic Toc

6" & 14" Mini LED Pendant



TITLE 24
CALIFORNIA



PD-37806-AL shown


PD-37814-AL shown



An elegant design with up and down illumination.

Color Temp: 3000K
CRI: 80
Dimming: 100%–10% ELV
Rated Life: 54,000 hours
Input: 120V

- Aluminum hardware, PC diffusers
- Thin powered aircraft cable provides an ultra-clean look
- Up and down illumination
- Can be mounted on a sloped ceiling
- Driver concealed within canopy



PD-37806

PD-37814

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-37806	6"	15W	1198	685	AL Brushed Aluminum
PD-37814	14"	28W	3150	1800	

Example: **PD-37806-AL**

Lolli


8" Mini LED Pendant



Unique oval bronze glass pendant with a hammered optic

Color Temp: 2700K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 80,000 hours
Input: 120V-277V

- Cable suspension carrying low voltage may be field shortened
- Universal voltage driver located in standard 4" junction box
- Thin powered aircraft cables provide an ultra-clean look



	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-52008	8"	6.5W	284	165	CH Chrome 

Example: **PD-52008-CH**

Banded



9" Mini LED Pendant



An etched opal glass cylinder wrapped in a sophisticated design.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 60,000 hours
Input: 120V-277V

- Twist on opal glass diffuser
- Thin powered aircraft cables provide an ultra-clean look
- Can be mounted on a sloped ceiling
- 2.76" x 1.26" x 1.18" universal voltage driver (installs within a junction box)
- The 24 available (special order) driver within the canopy



*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-68909	9"	20W	1718	884	BN <i>Brushed Nickel</i> BK <i>Black</i> AB <i>Aged Brass</i>

Example: **PD-68909-BN**
 For title 24 option add "T24" before the finish: **PD-68909-T24-BN**

Rocket


12" Mini LED Pendant



Retro styling with a strong trajectory.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 60,000 hours
Input: 120V (277V special order)

- Retro-style spun metal housing
- Upscale quality plated metal finishes
- Integral swivel for sloped ceilings
- Three 12" and one 6" downrods included (additional downrods available)
- 2.95" X 1.89" X 1.14" Driver




*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-51712	12"	12W	882	420	BN Brushed Nickel  BR Brushed Brass 

Example: **PD-51712-BN**
 For 277V, add an "F" before the finish: **PD-51712F-BN**

Caliber

10" Mini LED Pendant



Clean, modern style for any space.




Caliber

10" Mini LED Pendant



Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10% ELV
 Rated Life: 75,000 hours
 Input: 120-277V

- Hang straight swivel
- Three 12" and one 6" downrods included (additional downrods available)
- Driver located within the fixture



	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-W36610	10"	12W	799	508	BZ <i>Bronze</i> AL <i>Brushed Aluminum</i> BK <i>Black</i> WT <i>White</i>

Example: **PD-W36610-BK**

Elementum


11" & 16" Mini LED Pendant



True chemistry between light and style.

Color Temp: 3000K (2700K / 3500K special order)
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 65,000 hours
Input: 120-277V

- Simple form, big impact
- Evenly lit etched opal glass
- Twist lock glass attachment
- Driver located in standard 4" junction box
- Hang straight swivel canopy
- Three 12" and one 6" downrods included (additional downrods available)
- Universal driver (120V-220V-277V)



PD-26611

PD-26616

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-26611	11"	15W	1187	858	SN Satin Nickel
PD-26616	16"	20W	1769	1363	AB Aged Brass

Example: **PD-26616-SN**

For 2700K add "-27"; 3500K add "-35" before the finish: **PD-26616-27-SN**

Mallow

14" LED Pendant




Simple goodness in a cushy, curvy, design.



Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 54,000 hours
Input: 120V (277V special order)

- Simple evenly lit pillow of light
- Mouth blown etched triplex glass
- Three 12" and one 6" downrods included (additional downrods available)
- No transformer or driver required



PD-36714

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-36714	14"	18W	1620	1520	BN Brushed Nickel 

Example: **PD-36714-BN**
 For 277V, add an "F" before the finish: **PD-36714F-BN**

Napa

12" & 18" LED Pendant



ETL
LISTED
US

DAMP

Napa


12" & 18" LED Pendant



Timeless sophistication meets modern technology.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours
Input: 120V

- Aluminum hardware with extruded acrylic diffuser
- Three 12" and one 6" downrods included (additional downrods available)
- No transformer or driver needed



	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-42912	12"	16W	1400	790	BK Black 
PD-42918	18"	25W	2400	1365	

Example: **PD-42912-BK**

Elektron


20" & 28" LED Pendant + Close-to-Ceiling Mount



Traveling at the speed of light.
One luminaire with two looks.


Elektron

20" & 28" LED Pendant + Close-to-Ceiling Mount



Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 36,000 hours
Input: 120 - 277V

- Uniquely versatile fixture capable of transforming before your eyes
- Edge lit acrylic diffuser with discretely hidden LEDs
- Downrods can be removed to mount as a ceiling fixture or wall sconce
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V) Installs within a junction box
- Three 12" and one 6" downrods included (additional downrods available)
- Universal driver (120V-220V-277V)



*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
FM-21720	20"	20W	1680	1315	AL <i>Brushed Aluminum</i> 
FM-21728	28"	30W	2525	1720	

Example: **FM-21720-AL**

Niveous

7", 10" & 13" LED Pendant

TITLE 24
CALIFORNIA



Niveous

7", 10" & 13" LED Pendant

TITLE 24
CALIFORNIA




The perfect sphere.

Color Temp: 3000K (2700K / 3500K special order)
CRI: 90
Dimming: 100% - 10% ELV; 100%-5% (0-10)
Rated Life: 70,000 hours
Input: 120-277V




p. 107 Ceiling Mount


- Mouth blown etched opal glass provides even illumination
- Integral swivel for sloped ceiling
- Driver located in standard 4" junction box
- Three 12" and one 6" downrods included (additional downrods available)
- 2.95" X 1.88 X 1.14" Universal driver (120V-220V-277V)




PD-52307



PD-52310



PD-52313

	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-52307	7"	10W	777	588	BN Brushed Nickel WT White AB Aged Brass 
PD-52310	10"	14W	906	685	
PD-52313	13"	14W	906	715	

Example: **PD-52310-BN**

For 2700K add "-27"; 3500K add "-35" before the finish: **PD-52310-27-BN**

*Driver installs within a junction box

Manhattan

14", 20", & 26" LED Pendant



TITLE 24
CALIFORNIA


PD-13720-BN shown





Urban chic sophistication.
Luminous fabric shade pendant.

Color Temp: 2700K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours
Input: 120V

- Three 12" and one 6" downrods included (additional downrods available)
- Integral swivel for sloped ceiling
- No transformer or driver required



	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-13714	14"	28W	2400	1794	BN Brushed Nickel  AB Aged Brass 
PD-13720	20"	32W	2800	2222	
PD-13726	26"	48W	4200	3310	

Example: **PD-13720-AB**

Manhattan

14", 20" & 26" LED Close-to-Ceiling Mount




TITLE 24
CALIFORNIA

FM-13114-AB- shown




Color Temp: 2700K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours
Input: 120V


- Trimless look with a modern upgrade
- Urban elegance & LED illumination softened with a fabric shade
- No transformer or driver required







FM-13114



FM-13120



FM-13126

	Size	Watt	LED Lumens	Delivered Lumens	Finish
	FM-13114 14"	28W	2400	1794	BN Brushed Nickel AB Aged Brass 
	FM-13120 20"	32W	2800	2222	
	FM-13126 26"	48W	4200	3310	

Example: FM-13114-AB

FM-13126-BN shown





LED Ceiling Mounts

dweLED Ceiling Mount luminaires are designed to integrate within a variety of spaces ranging from residential and multifamily to commercial and healthcare. These well-engineered luminaires are cleanly finished with no visible hardware, offering a glare-free superbly low-profile quality that is defining of good LED luminaire design. dweLED Ceiling Mount luminaires maximize application versatility with a full range of light outputs and sizes from 6" to 28" in addition to dimming and input voltage options. Expect ample and even illumination across a range of applications, from general illumination in offices to functional lighting with excellent color rendering for walk-in closets.

Madison


16", 22" & 28" LED Ceiling Mount



TITLE 24
CALIFORNIA



Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% Triac
Rated Life: 50,000 hours
Input: 120V-277V



- Driver concealed within the canopy
- Fabric shade in combination with acrylic for multi-faceted design

	Size	Watt	LED Lumens	Delivered Lumens	Finish
FM-96916	16"	23W	1607	1125	BN Brushed Nickel  AB Aged Brass 
FM-96922	22"	41W	2571	1800	
FM-96928	28"	50W	3214	2250	

Example: **FM-96916-BN**

Madison

16", 22" & 28" LED Ceiling Mount



TITLE 24
CALIFORNIA



A vintage look with modern functionality.

Geos


6" & 10" LED Ceiling & Wall Mount



Updated in a stylish brass finish to complement the latest interior trends.

Color Temp: 2700K, 3000K
CRI: 80
Dimming: 100%–10% ELV
Rated Life: 70,000 hours
Input: 120V (277V special order)

- Aluminum hardware, frosted acrylic diffuser
- Edge-lit LED with light-extraction panel for even illumination
- Easy installation with twist-lock mechanism (no visible hardware)
- 2" x 1.38" x 1.02" transformer



* Transformer installs within a junction box


		Size	Color Temp	Watt	LED Lumens	Delivered Lumens	Finish
	FM-4606-27	6"	2700K	8W	551	270	BR Brushed Brass TT Titanium WT White
	FM-4606-30		3000K	8W	608	300	
	FM-4610-27	10"	2700K	12.5W	964	545	
	FM-4610-30		3000K	12.5W	1064	600	

Example: **FM-4606-30-WT**

For 277V special order, add an "F" before the color temperature: **FM-4610F-27-BR**


Geos

15" & 22" LED Ceiling & Wall Mount





Color Temp: 2700K, 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours*
Input: 120-277V

- Aluminum hardware, frosted acrylic diffuser
- Edge-lit LED with light-extraction panel for even illumination
- Easy installation with twist-lock mechanism (no visible hardware)
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)




*Driver installs within a junction box

	Size	Color Temp	Watt	LED Lumens	Delivered Lumens	Finish
	15"	FM-4615-27	2700K	29W	2330	1485
		FM-4615-30	3000K	29W	2355	1660
	22"	FM-4622-27	2700K	44W	3745	2235
		FM-4622-30	3000K	44W	3785	2375

BR Brushed Brass

TT Titanium

WT White



Example: **FM-4622-30-TT**

Corso


18" & 23" LED Ceiling Mount




Promenade of light. A self illuminating halo within.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV / 0-10V
Rated Life: 50,000 hours
Input: 120V-277V

- Aluminum body with acrylic diffuser
- Even illumination with no hotspots
- Universal voltage driver (120V-220V-277V) concealed within fixture



	Size	Watt	LED Lumens	Delivered Lumens	Finish
FM-33718	18"	25W	1675	721	AL <i>Brushed Aluminum</i> 
FM-33723	23"	34W	2166	728	

Example: **FM-33718-AL**

Tetris


18" & 24" LED Ceiling Mount



Simple and symmetrical for virtually any application.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV / 0-10V
Rated Life: 50,000 hours
Input: 120V-277V

- Aluminum body with acrylic diffuser
- Even illumination without hotspots
- Universal voltage driver (120V-220V-277V) concealed within fixture



	Size	Watt	LED Lumens	Delivered Lumens	Finish
FM-38918	18"	29W	2905	917	AL <i>Brushed Aluminum</i> 
FM-38924	24"	36W	3337	1656	

Example: **FM-38918-AL**

Vornado

31" LED Ceiling Mount



TITLE 24
CALIFORNIA

Bands of silver and light twist in and out like a Mobius strip.


Vornado


31" LED Ceiling Mount



Color Temp: 3000K
CRI: 90
Dimming: 100%–10% ELV & 0–10V
 100%–5%; 0–10V
Rated Life: 50,000 hours
Input: 120–277V

- Hand-crafted, seamless construction
- Universal voltage driver (120V-220V-277V) concealed within canopy



	Size	Watt	LED Lumens	Delivered Lumens	Finish
FM-87731	31"	88.4W	7059	5375	CH Chrome 

Example: **FM-87731-CH**

Planets


17" & 22" LED Ceiling Mount




Cosmically proportioned decorative ceiling-mount luminaires
Illuminate evenly for an out of this world experience.

Color Temp: 3500K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 63,000 hours
Input: 120 - 277V

- Large diameter makes a great addition to large rooms or high-ceiling applications
- Low-profile fixture with maximum illumination
- Extruded aluminum trim with no visible hardware
- Driver located inside the fixture
- Mount as a ceiling fixture or wall sconce
- Silk-screened glass diffuser with a white ceramic glaze
- Universal driver (120V-220V-277V)



FM-16617




FM-16622

	Size	Watt	LED Lumens	Delivered Lumens	Finish
FM-16617	17"	60W	5310	2355	BN <i>Brushed Nickel</i> 
FM-16622	22"	88W	8200	3460	

Example: **FM-16617-BN**

Elektron


20" & 28" LED Close-to-Ceiling Mount



Travelling at the speed of light

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 36,000 hours
Input: 120 - 277V

- Uniquely versatile fixture capable of transforming from pendant to ceiling mount
- Edge lit acrylic diffuser to add an even ring of light to any space
- Mount as a ceiling fixture or wall sconce
- Three 12" and one 6" downrods included (additional downrods available)
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)
- Installs within a junction box



FM-21720

FM-21728

*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
FM-21720	20"	20W	1680	1315	AL Brushed Aluminum 
FM-21728	28"	30W	2525	1720	

Example: **FM-21720-AL**


Dot

6", 9", 12" & 15" Interior/Exterior LED Ceiling & Wall Mount




Color Temp: 3000K, 3500K
CRI: 90
Dimming: 100%–10% ELV
Rated Life: 50,000 hours*
Input: 120V (277V special order)


- Weather-resistant 316 stainless steel body
- Lightweight, injection-molded, UV-rated acrylic diffuser enhances brightness, safety lock prevents slippage
- No transformer or driver needed
- 277V option available for 9", 12" & 15" sizes (special order)




FM-W57806





FM-W57809



FM-W57812



FM-W57815

	Size	Watt	LED Lumens	Delivered Lumens	Finish
FM-W57806-30	6"	10.5W	791	535	SS Stainless Steel  BK Black 
FM-W57806-35		10.5W	859	581	
FM-W57809-30	9"	16.5W	1542	939	
FM-W57809-35		16.5W	1674	1019	
FM-W57812-30	12"	26W	2315	1376	
FM-W57812-35		26W	2513	1499	
FM-W57815-30	15"	27W	2934	1654	
FM-W57815-35		27W	3185	1796	

Example: **FM-W57809-30-SS**

For 277V special order, add an "F" before the color temperature: **FM-W57812F-30-SS**

Dot

6", 9", 12" & 15" Interior/Exterior LED Ceiling & Wall Mount



Optical diffuser amplifies the brightness on this durable waterproof outdoor flush mount.

Slice


9", 11" & 15" LED Ceiling Mount & Wall Mount







Clean design of simple shapes with etched water-clear solid glass

Color Temp: 2700K, 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 45,000 hours
Input: 120V (277V special order)

- Etched 3/4" thick pressed glass diffuser with interior ceramic glaze
- Mount as a ceiling fixture or wall sconce
- No transformer or driver required
- Wet location listed for indoor applications



	Size	Color Temp	Watt	LED Lumens	Delivered Lumens	Finish
	9"	2700K	16.5W	1615	700	BN Brushed Nickel BZ Bronze CH Chrome 
		3000K	16.5W	1540	720	
	11"	2700K	26W	2300	1050	
		3000K	26W	2315	1080	
	15"	2700K	25W	2350	1050	
		3000K	25W	2557	1150	

Example: **FM-4111-27-BN**
 For 277V special order, add an "F" before the color temperature: **FM-4111F-27-BN**

Dice

6", 9", 12" & 14" x 5" LED Ceiling Mount & Wall Mount












TITLE 24
CALIFORNIA



Color Temp: 2700K, 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 45,000 hours
Input: 120V (277V special order)

- Etched 3/4" thick pressed glass diffuser with interior ceramic glaze
- Mount as a ceiling fixture or wall sconce
- No transformer or driver required



		Size	Color Temp	Watt	LED Lumens	Delivered Lumens	Finish	
	FM-4006-27	6"	2700K	17.5W	1400	700	BN Brushed Nickel  BZ Bronze  CH Chrome 	
	FM-4006-30		3000K	17.5W	1444	721		
	FM-4009-27	9"	2700K	31W	2750	1495		
	FM-4009-30		3000K	31W	2765	1511		
	FM-4012-27	12"	2700K	25W	2584	1096		
	FM-4012-30		3000K	25W	2668	1145		
	FM-4014-27	14" x 5"	2700K	31W	1323	610		BN Brushed Nickel 
	FM-4014-30		3000K	31W	1356	640		

Example: **FM-4009-30-BN**

For 277V special order, add an "F" before the color temperature: **FM-4006F-27-BN**

*FM-4014 is not Title 24 compliant, EnergyStar or Wet Rated

Manhattan

14", 20" & 26" LED Close-to-Ceiling Mount



TITLE 24
CALIFORNIA








Color Temp: 2700K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours
Input: 120V



p. 155 Sconce

- Trimless look with a modern upgrade
- Urban elegance & LED illumination softened with a fabric shade
- No transformer or driver required



		Size	Watt	LED Lumens	Delivered Lumens	Finish
	FM-13114	14"	26W	2400	1794	BN Brushed Nickel AB Aged Brass 
	FM-13120	20"	37W	2800	2222	
	FM-13126	26"	48W	4200	3310	

Example: **FM-13114-AB**

Meridien


14" LED Ceiling Mount



Longitude of lumens. The epitome of uptown chic.




p. 141 Bath & Sconce



*Driver installs within a junction box

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 53,000 hours
Input: 120 - 277V

- Classic look with a modern upgrade
- Mount as a ceiling fixture or a wall sconce
- Driver located in standard 4" junction box
- Silk-screened glass with a white ceramic glazed center and water clear edge
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)

	Size	Watt	LED Lumens	Delivered Lumens	Finish
FM-57614	14"	22.5W	1660	1145	BN <i>Brushed Nickel</i> 

Example: **FM-57614-BN**

Niveous

6" & 9" inch LED Ceiling + Wall Mount



The perfect sphere.



p. 86 Pendant

Color Temp: 3000K (2700K / 3500K special order)


CRI: 90

Dimming: 100% - 10% ELV

Rated Life: 45,000 hours


Input: 120V (277V special order)

- Spheres of pure light
- Mouth blown etched opal glass diffuser provides even illumination
- Solid aluminum construction
- Mount as a ceiling fixture or wall sconce
- Listed for use in closets
- No transformer or driver required



FM-W52306

FM-W52309

	Size	Watt	LED Lumens	Delivered Lumens	Finish
FM-W52306	6"	9.5W	800	680	WT White 
FM-W52309	9"	18W	1600	1428	

Example: **FM-W52306-WT**

For 277V, add an "F" before the finish: **FM-W52306F-WT**

For 2700K add "-27"; 3500K add "-35" before the finish: **FM-W52306-35-WT**

Vie

14" LED Ceiling Mount



A complete collection of contemporary sconces and bath.




p. 161 Sconce



p. 144 Bath

Color Temp: 2700K (3000K / 3500K special order)
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 80,000 hours
Input: 120V (277V special order)

- Vie adds a luxurious look to modern spaces
- Etched opal glass provides even illumination
- Unblemished plate finishes
- Multiple LED array eliminates socket shadows
- No transformer or driver required



		Size	Watt	LED Lumens	Delivered Lumens	Finish
	FM-4313	14"	30W	2620	1545	BN Brushed Nickel CH Chrome

Example: **FM-4313-CH**
 For 277V, add an "F" before the finish: **FM-4313F-CH**
 For 3000K add "-30"; 3500K add "-35" before the finish: **FM-4313-30-CH**





LED Sconces + Bath

Focused on timeless silhouettes, scaled-up metalwork and enduring finishes, these luminaires feature a tightly engineered fit and finish to coordinate seamlessly with upscale hardware and fixtures. Baths are ideal places to demonstrate illumination performance from proprietary LED technology where color quality and brightness requirements are the greatest. dweLED sconces and bath designs are trained on clean looks with ample illumination in color temperatures best suited for the intended space. Within these pages, you will find certain styles designed for warm white 2700K light, some for neutral white 3000K light, and others for bright white 3500K light. For an optimal lighting design, we recommend specifying luminaires in 2700K, 3000K, or 3500K based on the color palette and intended use of the designed spaces.

Interlace

28" & 38" LED Bath & Sconce




TITLE 24
CALIFORNIA



Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV / 0-10V / Triac
Rated Life: 50,000 hours
Input: 120-277V

- Seamless interlocked loops
- Driver concealed within the canopy



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-47828	28"	21W	1565	1174	CH Chrome
WS-47838	38"	28W	2183	1637	

Example: **WS-47838-CH**

Interlace

28" & 38" LED Bath & Sconce



TITLE 24
CALIFORNIA



Eternally waving bands of light weave playfully in and out on this flowing modern design.

Equation


22", 30" & 40" LED Bath & Sconce



TITLE 24
CALIFORNIA



Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours
Input: 120V




WS-26922

WS-26930

WS-26940

- Steel hardware with co-extruded acrylic diffuser
- No transformer or driver needed

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-26922	22"	32W	2102	1243	BK <i>Black</i> TT <i>Titanium</i> 
WS-26930	30"	47W	2894	1798	
WS-26940	40"	61W	3677	2252	


Example: **WS-26922-TT**

Equation

22", 30" & 40" LED Bath & Sconce



TITLE 24
CALIFORNIA



Clean, minimalistic design houses the most advanced LED technology available.

Wand


31" LED Bath & Sconce



Add sparkle to your sanctuary with a beaded crystal glass wand that shimmers with light.

Color Temp: 3000K
CRI: 90
Dimming (120V): 100%–10% ELV;
 100%–5% 0-10V, Triac
Rated Life: 50,000 hours
Input: 120–277V

- Acrylic tube filled with crystalline beads
- Can be mounted vertically or horizontally
- 3" x 1.25" x 1.13" universal voltage driver (120V-220V-277V) installs



WS-19831

**Driver installs within a junction box*

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-19831	31"	8W	845	584	CH Chrome 

Example: **WS-19831-CH**

Trio




20", 28" and 37" LED Bath & Sconce



A subtly retro-inspired piece that's totally modern at the same time. Trio's evenly illuminated strips hover above a polished chrome backplate, creating an interesting yet understated accent in blissful bathrooms and commercial spas alike. Mount it over a vanity or vertically as a sconce.

Color Temp: 3000K
CRI: 90
Dimming: 100%–5% ELV; 0–10V% Triac
Rated Life: 50,000 hours
Input: 120–277V

- Three individually illuminating chrome plated elements
- Universal voltage driver (120V-220V-277V) concealed within fixture




	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-51820	20"	20W	1522	1061	CH Chrome 
WS-51828	28"	27W	2602	1821	
WS-51837	37"	34W	3351	2346	


Example: **WS-51828-CH**

Endure


20", 27" and 37" LED Bath & Sconce




A continuous band of even light wraps around a finely crafted aluminum structure like the Roman "Circus Maximus." Hollow in the center.



WS-53820



WS-53827




WS-53837

**Driver installs within a junction box*

- Color Temp:** 3000K
- CRI:** 90
- Dimming:** 100%–10% ELV
- Rated Life:** 60,000 hours
- Input:** 120–277V

- Frosted acrylic edge-lit diffuser
- Can be mounted vertically or horizontally
- 3" x 1.25" x 1.13" universal voltage driver (120V-220V-277V)

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-53820	20"	20W	879	703	WT White 
WS-53827	27"	25W	1384	1107	
WS-53837	37"	30W	2040	1632	


Example: **WS-53827-WT**

Esprit


15", 26" and 38" LED Bath & Sconce




High-performance LED modules.
Slim, geometric profile.



WS-69815



WS-69826



WS-69838

**Driver installs within a junction box*

- Color Temp:** 3000K
- CRI:** 90
- Dimming:** 100%–10% ELV
- Rated Life:** 50,000 hours*
- Input:** 120–277V


- Etched acrylic diffuser
- LED modules positioned closer to diffuser for broader spread of illumination
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-69815	15"	10W	845	636	BN Brushed Nickel CH Chrome
WS-69826	26"	20W	1784	1240	
WS-69838	38"	30W	2712	2136	

Example: **WS-69826-BN**

Verge

25" & 37" LED Bath




A vertical curtain of light adapted from our handsome Level sconce design. Verge features an ultra-thin frosted diffuser that helps to spread light evenly without any glare or hot spots.




Color Temp: 3500K
CRI: 90
Dimming: 100%–5% ELV
Rated Life: 54,000 hours
Input: 120–277V

- Half-inch frosted acrylic linear blade
- Edge-lit LED modules give an ambient effect
- Can be mounted up or down
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)



WS-17825



WS-17837

*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-17825	25"	20W	1180	1047	AL Brushed Aluminum WT White
WS-17837	37"	37W	1809	1460	

Example: **WS-17825-WT**


Level

19", 25" & 37" LED Bath & Sconce




Color Temp: 3500K
CRI: 90
Dimming: 100%–10% ELV
Rated Life: 85,000 hours
Input: 120–277V

- Half-inch edge-lit linear blade
- Frosted diffuser provides even illumination
- Adjustable back plate (see spec sheet for adjustable length)
- Conversion plate for 4" junction box included
- Can be mounted vertically or horizontally
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)




*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-85618	19"	15.5W	1300	865	WT White AL Brushed Aluminum BK Black 
WS-85624	25"	20.5W	1735	1255	
WS-85636	37"	30W	2561	1762	

Example: **WS-85618-WT**

Line


18", 24" & 36" LED Bath & Sconce





Edge-lit LED panels provide a downward task light free of any hot spots. The luminaire can be rotated to provide direct or indirect illumination as the need arises.

Color Temp: 2700K, 3000K
CRI: 90
Dimming: 100%–10% ELV
Rated Life: 80,000 hours
Input: 120V (277V special order)



- Ultra-thin light-extraction panel and edge-lit acrylic diffuser
- Adjust rotating panel for indirect, up, down or task lighting
- Can be mounted vertically or horizontally
- 2" x 1.38" x 1.02" transformer




WS-6718



WS-6724



WS-6736



*Transformer installs within a junction box

Line


18", 24" & 36" LED Bath & Sconce



	Size	Watt	Color Temp	LED Lumens	Delivered Lumens	Finish
WS-6718-27	18"	16.5W	2700K	1004	770	BK Brushed Black AL Brushed Aluminum
WS-6718-30			3000K	1109	850	
WS-6724-27	24"	22W	2700K	1339	1035	
WS-6724-30			3000K	1478	1140	
WS-6736-27	36"	29W	2700K	2009	1380	
WS-6736-30			3000K	2218	1520	

Example: **WS-6718-30-BK**

For 277V, add an "F" before the finish: **WS-6718F-30-BK**











Nightstick

19", 25", 37", 49", 61", 73" & 97" LED Wall & Ceiling



Color Temp: 3000K
CRI: 90
Dimming: 100%–5% ELV
Rated Life: 54,000 hours
Input: 120V

- Co-extruded acrylic diffuser
- Available in multiple sizes to meet numerous applications
- Decorative plate to cover up to a standard 4" junction box is included
- Can be mounted vertically, horizontally, at an angle or on ceiling
- No transformer or driver needed



Nightstick

19", 25", 37", 49", 61", 73" & 97" LED Wall & Ceiling



A slender bar of light available in a variety of lengths— from very short (1.5 feet) to very long (over 8 feet)— gives you multiple mounting options for a clean and consistent lighting scheme no matter the size of your environment.

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-35819	19"	17W	1276	787	WT White AL Brushed Aluminum
WS-35825	25"	22W	1708	1054	
WS-35837	37"	34W	2585	1595	
WS-35849	49"	44W	3399	2097	
WS-35861	61"	53W	4213	2228	
WS-35873	73"	64W	4912	3031	
WS-35897	97"	84W	6458	3985	








Example: **WS-35861-AL**

Revel

19", 25", "37", 50", 62", 74" & 98" LED Bath & Sconce



A slender bar of light for a clean and consistent look.




Revel

19", 25", 37", 50", 62", 74" & 98" LED Bath & Sconce



Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10% ELV
 Rated Life: 54,000 hours
 Input: 120V

- Co-extruded acrylic diffuser
- Available in multiple sizes to meet numerous applications
- Can be mounted vertically, horizontally, at an angle or on ceiling
- No transformer or driver needed

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-82919	19"	22W	1492	770	AL Brushed Aluminum 
WS-82925	25"	25W	2071	1142	
WS-82937	37"	44W	3084	1746	
WS-82950	50"	59W	4130	2312	
WS-82962	62"	74W	5394	3074	
WS-82974	74"	89W	6168	3492	
WS-82998	98"	119W	8284	4568	

Example: **WS-82962-AL**

Brink

12", 18", 24" and 36" LED Bath & Sconce



Color Temp: 2700K, 3000K, 3500K


CRI: 90

Dimming: 100%–5% ELV


Rated Life: 85,000 hours

Input: 120–277V


- Co-extruded acrylic diffuser
- Conversion plate for 4" junction box included
- Can be mounted vertically, horizontally or at an angle
- Adjustable backplate
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V) installs within junction box




WS-77612



WS-77618




WS-77624




WS-77636

**Driver installs within a junction box*




A beautiful bar of pure LED light radiates through the co-extruded acrylic diffuser for brighter illumination, and an adjustable back plate adds versatility to this design's many attributes. It's a clean modern sconce anywhere you mount it.

	Size	Color Temp	Watt	LED Lumens	Delivered Lumens	Finish
WS-77612-27	12"	2700K	10.5W	863	779	AL Brushed Aluminum BR Brushed Brass BK Black 
WS-77612-30		3000k	10.5W	905	791	
WS-77612-35		3500K	10.5W	935	840	
WS-77618-27	18"	2700K	15.5W	1155	910	
WS-77618-30		3000K	15.5W	1225	1015	
WS-77618-35		3500K	15.5W	1330	1115	
WS-77624-27	24"	2700K	20.5W	1595	1330	
WS-77624-30		3000K	20.5W	1720	1440	
WS-77624-35		3500K	20.5W	1785	1510	
WS-77636-27	36"	2700K	30W	2365	1985	
WS-77636-30		3000K	30W	2445	2095	
WS-77636-35		3500K	30W	2561	2180	

Example: **WS-77636-30-BR**


Ratio

20", 30" & 40" LED Bath & Sconce




Color Temp: 3000K
 CRI: 90
 Dimming: 100%–10% ELV
 Rated Life: 54,000 hours
 Input: 120V


- Co-extruded acrylic diffuser
- Perfectly even illumination end to end
- No transformer or driver needed




WS-99820



WS-99830




WS-99840

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-99820	20.5"	21W	1880	975	CH Chrome 
WS-99830	30"	28W	2583	1371	
WS-99840	40"	36W	3100	1780	

Example: **WS-99830-CH**

Ratio

20", 30" & 40" LED Bath & Sconce



A thin band of chrome divides the light into even sections on this simple, sophisticated sconce.

Bliss

22", 28" & 36" LED Bath & Sconce



Two polished nickel clips gently restrain the tempered, mitered glass diffuser. An elegant meditation on balance.

Color Temp: 3000K (2700K / 3500K Special Order)


CRI: 90

Dimming: 100%–10% ELV

Rated Life: 50,000 hours*

Input 120V (277V special order)

- Mitered glass diffuser with silk-screen ceramic interior
- Conversion plate for 4" junction box included
- Can be mounted vertically and horizontally
- No transformer or driver needed



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-79622	22"	31W	2600	1500	PN Polished Nickel 
WS-79628	28"	40W	3600	2365	
WS-79636	36"	47W	4100	2800	

Example: **WS-79628-PN**

For 277V special order, add an "F" before the finish: **WS-79622F-PN**

For 2700K add "-27", 3500K add "-35" before finish: **WS-79622-35-PN**

Svelte

16", 22" & 34" LED Bath & Sconce




The picture of refinement.




p. 162 Sconce

Color Temp: 2700K (3000K / 3500K special order)
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 80,000 hours
Input: 120V (277V special order)


- ADA compliant with a 2" depth.
- 5mm thick mitered glass with ceramic glaze
- Can be mounted vertically or horizontally
- No transformer or driver required
- Conversion plate for 4" junction box included



WS-7316



WS-7322



WS-7334

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-7316	16"	24.5W	1845	875	BN Brushed Nickel CH Chrome 
WS-7322	22"	34.5W	2580	1350	
WS-7334	34"	48W	4043	2100	



Example: **WS-7316-CH**

For 277V, add an "F" before the finish: **WS-7316F-CH**

For 3000K add "-30"; 3500K add "-35" before the finish: **WS-7316-30-CH**

Vista


20", 26" & 38" LED Bath & Sconce




A brilliant outlook . Versatile 1 inch narrow spears of light.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 5% ELV
Rated Life: 54,000 hours
Input: 120 - 277V


- Spot free linear illumination
- Conversion plate for 4" junction box included
- Adjustable backplate (see line drawing for range)*
- Co-extruded clear and white acrylic provides substance, luminosity and optical efficacy
- Mount vertically or horizontally
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V) installs within junction box



WS-40720



WS-40726



WS-40738

*Driver installs within a junction box



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-40720	20"	15.5W	1385	1190	AL <i>Brushed Aluminum</i> 
WS-40726	26"	21W	1710	1500	
WS-40738	38"	31.5W	2670	2380	

Example: **WS-40720-AL**

Elementum

13", 22" and 30" LED Bath & Sconce



Color Temp: 2700K (3000K & 3500K Special Order)


CRI: 90

Dimming: 100%–10% ELV


Rated Life: 80,000 hours

Input: 120V (277V special order)


- Opal glass diffuser
- 22" and 30" versions may be mounted vertically or horizontally
- No transformer or driver needed




WS-7213




WS-7222



WS-7230



Updated with a warm brass finish, Elementum brings unparalleled task lighting in to your bathroom. Mount vertically on both sides of a mirror or above a vanity mirror for flattering diffused illumination.

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-7213	13"	13W	1118	730	BR <i>Brushed Brass</i> BN <i>Brushed Nickel</i> CH <i>Chrome</i> 
WS-7222	22"	26W	2236	1505	
WS-7230	30"	31W	2905	1955	

Example: **WS-7222-BR**

For 277V special order, add an "F" before the finish: **WS-7222F-BR**

For 3000K add "-30", 3500K add "-35" before finish: **WS-7230-35-CH**

Theory


25" & 32" LED Bath & Sconce



Bold statement created from a single concept.

Color Temp: 3500K
CRI: 90
Dimming (120V): 100% - 10% ELV
Rated Life: 44,000 hours
Input: 120 - 277V

- Solid die-cast body with a perfect nickel finish
- Mount vertically or horizontally
- Side-lit acrylic diffuser provides unique no-glare illumination
- Universal driver (120V-220V-277V) localatated within the fixture




	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-42725	25"	15.5W	1250	1085	BN <i>Brushed Nickel</i> 
WS-42732	32"	22W	1830	1555	

Example: **WS-42725-BN**

Reflection


23", 29" & 39" LED Bath & Sconce




The meditation of enlightenment. Edge-lit on both sides.

Color Temp: 3500K
CRI: 90
Dimming: 100% - 5% ELV
Rated Life: 46,000 hours
Input: 120 - 277V


- Edge-lit magic
- Ultra low profile design
- Mount vertically or horizontally
- Frosted acrylic diffuser provides even illumination
- WS-59639 features ELV or 0-10V dimming
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)



WS-59623



WS-59629



WS-59639

**Driver installs within a junction box*

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-59623	23"	30.5W	1535	1370	AL <i>Brushed Aluminum</i> 
WS-59629	29"	38W	1920	1750	
WS-59639	35"	51.5W	2535	2410	

Example: **WS-59623-AL**

Strip




18", 24" & 36" LED Bath & Sconce




Lighting with no boundaries.

Color Temp: 2700K, 3000K, 3500K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 54,000 hours
Input: 120 - 277V

- Modern, sleek, clean
- Co-extruded clear and white acrylic provides substance, luminosity and optical efficacy
- Mounts vertically or horizontally
- Listed for use in closets
- Conversion plate for 4" junction box included
- Adjustable backplate
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V) installs within junction box




**Driver installs within a junction box*

	Size	Color Temp	Watt	LED Lumens	Delivered Lumens	Finish
WS-63718-27	18"	2700K	15W	1185	900	AL <i>Brushed Aluminum</i> 
WS-63718-30		3000K	15W	1425	1100	
WS-63718-35		3500K	15W	1500	1200	
WS-63724-27	24"	2700K	19.5W	1645	1390	
WS-63724-30		3000K	19.5W	1875	1490	
WS-63724-35		3500K	19.5W	1975	1640	
WS-63736-27	36"	2700K	28.5W	2660	2275	
WS-63736-30		3000K	28.5W	2855	2330	
WS-63736-35		3500K	28.5W	3020	2405	

Example: **WS-63718-35-AL**

Soho

11", 17" & 23" LED Bath & Sconce



Urban chic for luxury baths.



Color Temp: 2700K (3000K / 3500K special order)


CRI: 90

Dimming: 100% - 10% ELV


Rated Life: 50,000 hours

Input: 120V (277V special order)

- Rounded glass to give a unique appeal to a tried and true look
- Etched opal glass provides even illumination
- Mount vertically or horizontally
- Conversion plate for 4" junction box included
- 2.00" x 1.38" x 1.02" Transformer located in junction box



*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-6111	11"	16W	700	520	BN Brushed Nickel CH Chrome 
WS-6117	17"	25W	1170	860	
WS-6123	23"	33.5W	1597	1245	

Example: **WS-6117-BN**

For 277V special order, add an "F" before the finish: **WS-6117F-BN**

For 3000K add "-30", 3500K add "-35" before finish: **WS-6117-35-PN**


Meridien

9" & 20" LED Bath & Sconce




Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours
Input: 120V

- Silk-screened glass with a white ceramic glazed center and water clear edge
- Mount vertically only
- No transformer or driver required



WS-57609



WS-57620

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-57609	9"	9.5W	665	540	BN <i>Brushed Nickel</i> 
WS-57620	20"	22W	1595	1220	


Example: **WS-57609-BN**




p. 106 Ceiling Mount

Meridien


27" & 37" LED Bath & Sconce



Longitude of lumens. The epitome of uptown chic.



WS-57627



WS-57637

- Color Temp:** 3000K
- CRI:** 90
- Dimming:** 100% - 10% ELV
- Rated Life:** 50,000 hours
- Input:** 120V
- Silk-screened glass with a white ceramic glazed center and water clear edge
- Mount horizontally only
- No transformer or driver required

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-57627	27"	35.5W	2730	2065	BN <i>Brushed Nickel</i> 
WS-57637	37"	58.5W	3585	2790	

Example: **WS-57627-BN**

Horizon


18" & 26" LED Bath & Sconce




Captivating beauty just beyond reach.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 44,000 hours
Input: 120V

- Curved silk-screened glass with a white ceramic glazed center and water clear edge
- No transformer or driver required



WS-58618




WS-58626

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-58618	18"	19.5W	1805	590	CH Chrome
WS-58626	26"	30.5W	2920	900	

Example: **WS-58618-CH**

Vie

18", 24" & 36" LED Bath & Sconce



A complete collection of contemporary sconces and bath.

Color Temp: 2700K (3000K / 3500K special order)




CRI: 90



Dimming: 100% - 10% ELV

Rated Life: 80,000 hours

Input: 120V (277V special order)

- Sleek elegance for narrow applications
- 3 inch wide format
- Silk-screened glass with a white ceramic glazed interior
- Can be mounted vertically or horizontally
- Conversion plate for 4 inch junction box included
- No transformer or driver required



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-6618	18"	25.5W	1845	1085	BN Brushed Nickel  CH Chrome 
WS-6624	24"	35W	2580	1585	
WS-6636	36"	55W	4043	2360	


Example: **WS-6624-BN**

For 277V, add an "F" before the finish: **WS-6624F-BN**


For 3000K add "-30"; 3500K add "-35" before the finish: **WS-6624-30-BN**


Ashton

13" & 22" LED Bath & Sconce



Articulating classic design with modern technology.



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-39513	13"	25.5W	1093	770	PN Polished Nickel 
WS-39522	22"	30W	1373	990	

Example: **WS-39513-PN**

For 277V special order, add an "F" before the finish: **WS-39513F-PN**

For 3000K add "-30", 3500K add "-35" before finish: **WS-39513-35-PN**



Color Temp: 2700K (3000K / 3500K Special order)
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours
Input: 120 (277V Special order)

- Industrial chic never goes out of style
- Etched opal glass diffuser provides even illumination
- Mount vertically or horizontally
- WS-39513 emits downlight as well as ambient light
- No transformer or driver required

Dunhill

20" & 26" LED Bath & Sconce



Cool contemporary bath luminaires and wall sconces.

Color Temp: 2700K (3000K / 3500K special order)


CRI: 90

Dimming: 100% - 10% ELV


Rated Life: 50,000 hours

Input: 120V (277V special order)

- Clean line of light with an energized personality
- Etched opal glass diffuser provides even illumination
- Mount vertically or horizontally
- Conversion plate for 4" junction box included
- 2.00" x 1.38" x 1.02" Transformer



WS-40520



WS-40526

*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-40520	20"	27W	1125	770	PN Polished Nickel 
WS-40526	26"	35.5W	1551	935	

Example: **WS-40520-PN**

For 277V special order, add an "F" before the finish: **WS-40520F-PN**

For 3000K add "-30", 3500K add "-35" before finish: **WS-40520-35-PN**

Rondelle


5" Sconce, 14" & 24" LED Bath & Sconce



Inspired by collectible antique pole-top glass insulators, now illuminated as nostalgic lighting fixtures.




Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 60,000 hours
Input: 120V (277V special order)

- Solid glass shade
- *2.76" x 1.26" x 1.18 universal voltage driver (120V-220V-277V)

	Lights	Watt	LED Lumens	Delivered Lumens	Finish
WS-42505	1 Light	8.5W	230	220	PN Polished Nickel 
WS-42514	2 Lights	16W	518	490	
WS-42524	3 Lights	24.5W	865	805	

Example: **WS-42505-PN**

For 277V special order, add an "F" before the finish: **WS-42524F-PN**



*Driver installs within a junction box





LED Sconces

dweLED sconces are available in a variety of styles and sizes to complement current architectural interiors, from hospitality to upscale residential.

Beautiful ambient illumination from sconces can help define the perimeters of a space while also adding a flattering layer of light at the face level to occupants in the room that is unachievable from overhead lighting. The soft glow of dweLED sconces will create an ambience while the clean designs add visual interest to any room or hallway. Within this section, you will find a timeless variety of generously proportioned wall sconces that also meet ADA requirements. Certain designs also offer universal voltage input or 277V and emergency battery-backup special order options. This opens opportunities for dweLED sconces to add refinement to public spaces while providing important functional service.

Pocket


7" LED Sconce



An appealing cylindrical profile with a powerful LED makes the perfect accent.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours
Input: 120V

- Brushed aluminum
- Mounts up or down
- Driver located within the canopy
- No transformer or driver needed



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-30907	7"	21.5W	1018	713	AB Aged Brass WT White BN Brushed Nickel BK Black

Example: **WS-30907-AB**

Charmed


19" LED Sconce



Off the chain brilliance.

Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10% ELV / Triac / 0-10V
 Rated Life: 54,000 hours
 Input: 120-277V

- Driver concealed within the canopy
- Aluminum hardware with composite diffuser



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-54919	19"	12W	800	570	SG Soft Gold BN Brushed Nickel

Example: **WS-54919-BN**

Blok

12" LED Sconce with Emergency Backup Battery Option



WS-25612-WT- shown

Safety and style. Emergency battery backup concealed within.

- Simple yet bold
- Concealed hardware for a finished look at any viewing angle
- Emergency battery backup option (special order)
- Universal driver (120V-220V-277V) inside the fixture
- Up & down light

Color Temp: 3000K (2700K / 3500K special order)

CRI: 90

Dimming: 100% - 10% ELV, 100%-5% 0-10V

Rated Life: 70,000 hours

Input: 120V-277V



	Size	Watt	LED Lumens	Delivered Lumens	Finish
	WS-25612 12"	29W	1479	1162	SN Satin Nickel WT Textured White BK Black

Example: **WS-25612-WT**

For emergency battery, add -EM after the finish: **WS-25612-WT-EM**

For 2700K add "-27"; 3500K add "-35" before the finish: **WS-25612-27-WT**

Blok


12" LED Sconce with Emergency Backup Battery Option



Sometimes the simplest forms are the most sophisticated. Emergency battery backup option installs within.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 42,000 hours
Input: 120V-277V

- Simple yet bold
- Concealed hardware for a finished look at any viewing angle
- Up & down light
- Emergency battery backup option (special order)
- Universal driver (120V-220V-277V) located inside the fixture



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-32912	12"	16W	1246	800	SN <i>Satin Nickel</i> BK <i>Black</i> WT <i>White</i>

Example: **WS-32912-BK**
 For emergency battery add- **EM** after finish= **WS-32912-SN-EM**

Manhattan





7", 15" & 22" LED Sconce

TITLE 24
CALIFORNIA



WS-13107-AB- shown

Urban chic sophistication.

		Size	Watt	LED Lumens	Delivered Lumens	Finish
	WS-13107	7"	5.5W	439	238	
	WS-13115	15"	10W	842	446	
	WS-13122	22"	16W	1268	729	
						BN <i>Brushed Nickel</i> BO <i>Brushed Bronze</i> AB <i>Aged Brass</i> 

Example: **WS-13107-AB**

For 277V, add an "F" before the finish: **WS-13107F-BN**

Manhattan

7", 15" & 22" LED Sconce

TITLE 24
CALIFORNIA



WS-13122-BN- shown



p. 108 Ceiling Mount

Color Temp: 2700K




CRI: 90

Dimming: 100% - 10% ELV

Rated Life: 85,000 hours

Input: 120V (277V special order)

- Urban elegance softened with a fabric shade.
- Trimless fabric shade illuminates evenly
- Etched glass diffuser on top and below
- No transformer or driver required




Mythical


13", 18" & 24" LED Sconce



TITLE 24
CALIFORNIA



WS-12713




WS-12718



WS-12724

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 54,000 hours
Input: 120V (277V special order)

- Inch-thick solid block of polished clear seeded crystal
- Creates magnificent sparkles as bubbles within catch the light
- Concealed hardware completes this curiosity inspiring sconce
- Mount vertically or horizontally on a standard 4" junction box
- No transformer or driver required

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-12713	13"	8W	392	139	PN Polished Nickel 
WS-12718	18"	16W	771	333	
WS-12724	24"	16W	730	326	

Example: **WS-12718-PN**
 For 277V, add an "F" before the finish: **WS-12718F-PN**

Mythical


12" LED Sconce



Sparkling effervescence of light.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours
Input: 120-277V

- Inch-thick solid block of polished clear seeded crystal
- Creates magnificent sparkles as bubbles within catch the light
- Concealed hardware completes this curiosity inspiring sconce
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)



WS-12712

*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-12712	12"	11W	858	418	PN Polished Nickel 

Example: **WS-12712-PN**

Bric

7" LED Sconce




Luminary building block.



Color Temp: 3000K (2700K / 3500K special order)
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 80,000 hours
Input: 120V (277V special order)

- Concealed hardware for a finished look at any viewing angle
- Sconce may be rotated 180° when mounting
- Mounts on a 2" x 4" horizontal junction box or approved wiring compartment within fixture
- Conversion plate for 4" junction box included
- Replaceable LED module
- No transformer or driver required



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-11807	7"	9W	800	660	BN <i>Brushed Nickel</i> WT <i>White</i> 

Example: **WS-11807-BN**
 For 277V special order, add an "F" before the finish: **WS-11807F-BN**
 For 2700K add "-27"; 3500K add "-35" before the finish: **WS-11807-27-BN**



Vie

14" & 20" LED Sconce





A complete collection of contemporary sconces and bath.




p. 108 Ceiling Mount

Color Temp: 2700K (3000K / 3500K special order)
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 80,000 hours
Input: 120V (277V special order)

- Classic architectural look perfect for any space
- Water clear bent glass with a white ceramic glazed interior
- Can be mounted vertically or horizontally on a standard 4" junction box
- Conversion plate for 4 inch junction box included
- No transformer or driver required



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-6614	14"	18.5W	1462	755	BN Brushed Nickel 
WS-6620	20"	24.5W	1845	1040	CH Chrome 

Example: **WS-6614-BN**
 For 277V, add an "F" before the finish: **WS-6614F-BN**
 For 3000K add "-30"; 3500K add "-35" before the finish: **WS-6614-30-BN**

Float

12" & 18" LED Sconce




An uplifting beacon of light.



p. 132 Bath / Sconce

Color Temp: 3000K (2700K / 3500K special order)
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 85,000 hours
Input: 120V-277V

- Water clear mitered glass with a silk-screened white ceramic glazed interior
- Mount vertically or horizontally
- Magnetic end cap (no exposed mounting screws)
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)



*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-7312	12"	15W	1125	615	BN <i>Brushed Nickel</i> 
WS-7318	18"	20.5W	1555	890	

Example: **WS-7318-BN**

For 2700K add "-27"; 3500K add "-35" before the finish: **WS-7312-27-BN**

Turbo


10" LED Sconce



Aerodynamic design,
propulsive illumination.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 75,000 hours
Input: 120V-277V

- Up & down light
- Conversion plate for 4" junction box included
- Universal driver (120V-220V-277V) located within the fixture.




	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-14610	10"	17.5W	775	555	BN <i>Brushed Nickel</i> 

Example: **WS-14610-BN**

Link


14" LED Sconce



Lovely as a single sconce
or installed in multiples as an interconnected display.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 38,000 hours
Input: 120V-277V

- Silk-screened glass diffuser with a white ceramic glaze
- Can be mounted vertically or horizontally
- Conversion plate for 4" junction box included
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-10614	14"	20.5W	985	380	BN <i>Brushed Nickel</i> 

Example: **WS-10614-BN**

Moderne

15" LED Sconce



Art Deco inspired elegance.

Color Temp: 3000K (2700K / 3500K special order)


CRI: 90

Dimming: 100% - 10% ELV

Rated Life: 55,000 hours

Input: 120V-277V

- Mouth blown etched opal glass diffuser provides even illumination
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)



*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-40615	15"	20W	1482	887	SN Satin Nickel 

Example: **WS-40615-SN**

For 2700K add "-27"; 3500K add "-35" before the finish: **WS-40615-27-SN**

Aviator

18" LED Sconce



A streamlined air of sophistication.

Color Temp: 3000K (2700K / 3500K special order)


CRI: 90

Dimming: 100% - 10% ELV

Rated Life: 85,000 hours

Input: 120V-277V

- Heavy gauge solid nickel plated hardware inspired by classic aviator hood ornaments
- Mouth blown etched opal glass diffuser provides even illumination
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)



*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-43613	18"	16W	1134	761	SN Satin Nickel 

Example: **WS-43613-SN**

For 2700K add "-27"; 3500K add "-35" before the finish: **WS-43613-27-SN**

Prohibition


20" LED Sconce



Modern for today
while nostalgic of a different time.

Color Temp: 3000K (2700K / 3500K special order)
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 55,000 hours
Input: 120V-277V

- Art deco inspired contemporary design updated with LED technology
- Mouth blown etched triplex opal glass diffuser provides even illumination
- Heavy gauge nickel plated hardware
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)



*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-45620	20"	18W	1377	817	SN Satin Nickel 

Example: **WS-45620-SN**
 For 2700K add "-27"; 3500K add "-35" before the finish: **WS-45620-27-SN**

Coco

9" LED Sconce



The Elegant Feminine.

Color Temp: 3000K (2700K / 3500K special order)


CRI: 90

Dimming: 100% - 10% ELV

Rated Life: 80,000 hours

Input: 120V-277V

- Art deco inspired contemporary design
- Mouth blown etched triplex opal glass diffuser provides even illumination
- Heavy gauge nickel plated hardware
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)



*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-46609	9"	21W	1377	873	SN <i>Satin Nickel</i> 

Example: **WS-46609-SN**

For 2700K add "-27"; 3500K add "-35" before the finish: **WS-46609-27-SN**


Level

19", 25" & 37" LED Bath & Sconce



Color Temp: 3500K
CRI: 90
Dimming: 100%–10% ELV
Rated Life: 85,000 hours
Input: 120V–277V

- Half-inch edge-lit linear blade
- Frosted diffuser provides even illumination
- Adjustable back plate (see spec sheet for adjustable length)
- Conversion plate for 4" junction box included
- Can be mounted vertically or horizontally
- 2.76" x 1.26" x 1.18" universal voltage driver (120V–220V–277V)



*Driver installs within a junction box



Adjustable backplate

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-85618	19"	15.5W	1300	865	WT White AL Brushed Aluminum BK Black 
WS-85624	25"	20.5W	1735	1255	
WS-85636	37"	30W	2561	1762	

Example: **WS-85618-WT**

Wedge


18" LED Bath & Sconce



A thin illuminated blade bisects a bent aluminum plate, suggesting kinetic energy and symmetry at the point of light.

- Color Temp:** 3000K
- CRI:** 90
- Dimming:** 100%–5% ELV
- Rated Life:** 50,000 hours
- Input:** 120V

- Brushed aluminum frosted edge-lit acrylic diffuser
- Can be mounted vertically, horizontally, at an angle or on ceiling
- 3" x 1.25" x 1.13" driver



WS-75818

*Driver installs within a junction box

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-75818	18"	9W	535	417	AL Brushed Aluminum

Example: **WS-75818-AL**

Stella


8", 12" & 17" LED Sconce




TITLE 24
CALIFORNIA




Classy and versatile pocket sconce.



WS-13208




WS-13212



WS-13217

Color Temp: 3000K (2700K / 3500K special order)
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 80,000 hours
Input: 120V (277V special order)

- Water clear bent glass with a silk-screened white ceramic glazed interior
- Heavy gauge nickel plated hardware
- Etched glass diffuser top and bottom
- No transformer or driver required

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-13208	8"	9.5W	727	335	BN <i>Brushed Nickel</i> 
WS-13212	12"	15.5W	1118	495	
WS-13217	17"	25.5W	1845	895	

Example: **WS-13217-BN**

For 277V, add an "F" before the finish: **WS-13217F-BN**

For 2700K add "-27"; 3500K add "-35" before the finish: **WS-13217-27-BN**

Corbusier

15" LED Sconce



Upstanding and architectural.

Color Temp: 3000K (2700K / 3500K special order)


CRI: 90

Dimming: 100% - 10% ELV

Rated Life: 85,000 hours

Input: 120V-277V

- Water clear mitered glass with a silk-screened white ceramic glazed interior
- Heavy gauge nickel plated hardware
- 2.76" x 1.26" x 1.18" universal voltage driver (120V-220V-277V)



*Driver installs within a junction box


	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-42618	15"	20W	1476	827	SN Satin Nickel 

Example: **WS-42618-SN**

For 2700K add "-27"; 3500K add "-35" before the finish: **WS-42618-27-SN**

Bossa Nova

32" LED Wall Sconce




Contrast of simple shapes.
Formal energy of Mid-Century Modernism.

WS-93801-BK- shown

Color Temp: 3000K
CRI: 90
Dimming: 100%–10% ELV; 0–10V
Rated Life: 50,000 hours

- Mouth-blown opal glass shades
- 2.95" X 1.88 X 1.14" driver install within junction box
- 3 light sconce has removable lower stems
- 120V (WS-93801)
- 120-277V(WS-93803)



WS-93801


*Driver installs within a junction box

Bossa Nova

32" LED Wall Sconce




WS-93803-BK- shown



WS-93803

*Driver installs within a junction box

	No. of Lights	Watt	LED Lumens	Delivered Lumens	Finish
WS-93801	1	6W	449	373	BK <i>Black</i> 
WS-93803	3	11W	1120	869	

Example: **WS-93803-BK**



LED Display + Picture


Fine art, photographs and wall décor are best displayed and preserved as showcased in a gallery. Unlike conventional luminaires, these LED picture lights provide full spectrum illumination without damaging infrared and ultraviolet rays. Discerning collectors choose LED display and picture lights powered by WAC technology, the time-tested authority in color quality and performance LED lighting since 2006.

Hudson

LED Picture Light




TITLE 24
CALIFORNIA






Fine art illuminated. Available in two designer finishes to complement upscale artwork.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV / Triac / 0-10V
Rated Life: 50,000 hours
Input: 120V-277V

- Conserves artwork while providing vibrant color rendering
- Head rotates 90° up or down
- Driver concealed within the fixture



	Size	Watt	LED Lumens	Delivered Lumens	Finish
	PL-LED17-30 17"	14W	1125	811	BK Black AB Aged Brass <div style="display: flex; justify-content: space-around; margin-top: 5px;"> <div style="width: 15px; height: 10px; background-color: black;"></div> <div style="width: 15px; height: 10px; background-color: #c08040;"></div> </div>
	PL-LED23-30 24"	17.5W	1490	1078	
	PL-LED34-30 34"	24W	1992	1500	

Example: **PL-LED17-30-BK**



Hemmingway



LED Picture Light







Color Temp: 2700K
CRI: 90
Dimming: 100% – 10% ELV
Rated Life: 70,000 hours

- Chronophoton Technology preserves artwork while providing vibrant color rendering
- Head rotates 90° up or down and extends out 14" from mounting surface
- Direct wire only
- Transformer located within canopy




		Size	Power	LED Lumens	Delivered Lumens	Finish
	PL-LED14-27	14"	9.5W	595	354	Hard Wired
	PL-LED24-27	24"	17W	1186	675	Hard Wired

AN Antique Nickel 
BB Burnished Brass 
RB Rubbed Bronze 
PN Polished Nickel 

Example: PL-LED24-27-AN


Fly

LED Picture Light



Color Temp: 3000K
 CRI: 90
 Dimming: N/A
 Rated Life: 36,000 hours
 Input: 120V

- Aluminium construction
- Integral driver in canopy with on/off feature
- Pivotal head

		Power	Lumens	Finish
PL-22916	16"	8.5W	420	BN Brushed Nickel 

Example: **PL-22916-BN**

Vibe


LED Picture Light







The back plate mounts on the wall, and provides a channel for the art frame to hang on up to 20lbs

Color Temp: 2700K
 CRI: 90
 Dimming: 100% – 10% ELV
 Rated Life: 70,000 hours

- Chronophoton Technology conserves artwork while providing vibrant color rendering
- Head rotates 35° up or down
- 110° beam angle
- Direct wire only



				Power	LED Lumens	Delivered Lumens		Finish
	PL-LED15-27	15"	9.5W	595	240	Hard Wired		
	PL-LED25-27	25"	17W	1186	535	Hard Wired	BK Black BN Brushed Nickel	
	PL-LED37-27	37"	26W	1785	850	Hard Wired		

Example: PL-LED25-27-BN






LED Bedside Wall + Swing Arm

Using bedroom wall lights creates symmetry in the bedroom while also providing task lighting for reading. Our ensemble of wall mounted lights for your bedroom include popular styles such as swing arm wall lights, plug in wall lights and discreet recessed headboard lights.

Flip


LED Swing Arm



Bauhaus and beautiful. Versatile design and function.

Color Temp: 3000K
CRI: 85
Dimming: 100% - 10% (integral dimmer)
Rated Life: 30,000 hours
Input: 120-240V

- Bauhaus-style geometry in a left and right paired design
- Aluminum construction
- Fingertip touch dimming on head
- Two 12 inch cord covers included for portable installation
- Mounts to standard 4" junction box when hard-wired
- Driver located inside canopy



			Watt	LED Lumens	Delivered Lumens	Finish
	Left	BL-1021L	9W	489	315	BZ Bronze TT Titanium BK Black
	Right	BL-1021R	9W	489	315	

Example: **BL-1021L-BZ**

Stretch


LED Swing Arm



Color Temp: 3000K
CRI: 90
Dimming: Internal
Rated Life: 30,000 hours
Input: 120V

- A contemporary utilitarian design
- Flexible, yet fixable rubber tube for directing light
- Fingertip touch dimming on back plate
- Individually switched
- Two 12" cord covers, and 8ft cord for hardwired or portable installation
- Conversion plate for 4" junction box included
- Driver located within canopy

Fingertip-touch dimming and cutting-edge LED technology give the bedside lamp a much-needed upgrade. Flexible arms allow for customizable angles and task-oriented applications. Available now with one or two arms and approved for mounting in any orientation.



	No. of Lights	Watt	LED Lumens	Delivered Lumens	Finish
BL-1660	2	17W	936	623	WT White BK Black TT Titanium
BL-1630	1	8W	489	260	

Example: **BL-1660-BK**




Scope


LED WALL



Color Temp: 3000K
CRI: 90
Rated Life: 50,000 hours
Input: 100-240V

- On-off switch on fixture
- Wide pivotable arm with light
- Integral driver
- Surface mount or recessed mount
- Fits 2" x 4" vertical switch box with conversion plate provided
- 8 ft cord included for hard-wired and portable installation
- Hold switch to dim



	Watt	LED Lumens	Delivered Lumens	Finish
BL-29903	8.5W	465	148	BN <i>Brushed Nickel</i> 

Example: **BL-29903-BN**


Scout

LED WALL



Color Temp: 3000K
 CRI: 90
 Rated Life: 50,000 hours
 Input: 100-240V

- On-off switch on fixture
- Pivotal arm with light
- Fits over standard junction box
- Integral driver
- Hold switch to dim



BL28903R


BL28903L

	Watt	LED Lumens	Delivered Lumens	Finish
BL-28903R	9W	465	184	BK Black
BL-28903L				WT White
				BN Brushed Nickel

Example: **BL-28903-BK**


Klein

SWING ARM



Color Temp: 3000K
CRI: 90
Rated Life: 50,000 hours
Input: 120V

- On-off switch on fixture
- Wide pivotable arm with light
- Driver located within the canopy
- Fits over a standard junction box
- Hold switch to dim



	Watt	LED Lumens	Delivered Lumens	Finish
BL-25906	9W	356	259	BK <i>Black</i> WT <i>White</i> TT <i>Titanium</i>

Example: **BL-25906-TT**





LED Outdoor

dweLED outdoor wall sconces add light and style to building exteriors, often serving more than one function. The right outdoor selection is both functional and decorative in providing comfortable nighttime illumination while also adding visual interest to the building envelope. Designed for ambient lighting and architectural complement, dweLED outdoor luminaires are equipped with specifically engineered, energy efficient LEDs to accent architectural surfaces for dramatic visual intrigue while delivering safety illumination of pathways and entrances. Clean designs maintain a timeless architectural aesthetic that reflects the dweLED brand while thoughtful engineering and quality construction delivers lasting robust performance.

Farmhouse


13" & 17" LED Outdoor Sconce



A romantic, rain-against-the-window appearance that sparkles when illuminated.

- Color Temp:** 3000K
- CRI:** 90
- Dimming:** 100% - 10% ELV; 0-10V; Triac
- Rated Life:** 64,000 hours
- Input:** 120-277V

- Aluminum body with seeded hammered glass
- Driver located within the fixture



WS-W68913


WS-W68917

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-W68913	13"	12W	900	205	GH Graphite BK Black
WS-W68917	17"	15W	1100	223	

Example: **WS-W68913-BK**

Farmhouse

13" & 17" LED Outdoor Sconce



Archetype


18" LED Outdoor Sconce



A low-profile, artful design adds a distinctive, sophisticated look in any outdoor application.

Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10% ELV
 Rated Life: 54,000 hours
 Input: 120V

- Aluminum hardware with etched glass diffuser
- No transformer or driver required




	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-W13918	18"	16W	1200	427	BK Black 


Example: **WS-W13918-BK**

Archetype


12", 18" & 24" LED Outdoor Sconce



WS-W15912




WS-W15918



WS-W15924

Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10% ELV
 Rated Life: 54,000 hours
 Input: 120V

- Aluminum hardware with etched glass diffuser
- No transformer or driver required

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-W15912	12"	10W	800	331	BK Black 
WS-W15918	18"	13W	1000	435	
WS-W15924	24"	16W	1200	571	

Example: **WS-W15912-BK**

Archetype


18" LED Outdoor Pendant



A low-profile, artful design adds a distinctive, sophisticated look in any outdoor application.

Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10% ELV
 Rated Life: 54,000 hours
 Input: 120V

- Aluminum hardware with etched glass diffuser
- No transformer or driver needed
- Three 12" and one 6" downrod included (additional rods available)



	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-W15918	18"	10W	800	379	BK Black

Example: PD-W15918-BK


Archetype


28" LED Outdoor Post Mount



Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 54,000 hours
Input: 120V

- Aluminum hardware with etched glass diffuser
- No transformer or driver needed
- Mount on 3" maximum post (not included)




	Size	Watt	LED Lumens	Delivered Lumens	Finish
PM-W15928	28"	16W	1200	382	BK Black 

Example: **PM-W15928-BK**

Slant


11" LED Outdoor Sconce



Cleverly designed, minimalistic lighting.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours
Input: 120V

- Aluminum hardware
- Can be rotated 180 degrees for alternate mounting option
- No transformer or driver needed




	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-W14911	11"	7W	441	353	BK Black
					AL Brushed Aluminum

Example: **WS-W14911-BK**


Passage

14" & 22" LED Outdoor Sconce

The design of this wall sconce features a sliver window of glass, coupled with LEDs that provide up and down lighting to illuminate outdoor pathways.





WS-W66914



WS-W66922

- Color Temp: 3000K
- CRI: 90
- Dimming: 100% - 10% ELV
- Rated Life: 54,000 hours
- Input: 120V

- Aluminum body with glass diffuser
- No transformer or driver needed

	Size	Watt	LED Lumens	Delivered Lumens	Finish
	WS-W66914 14"	16W	1200	57	BK Black GH Graphite <div style="display: flex; align-items: center; margin-top: 5px;"> <div style="width: 20px; height: 10px; background-color: black; margin-right: 5px;"></div> <div style="width: 20px; height: 10px; background-color: #808080; margin-right: 5px;"></div> </div>
	WS-W66922 22"	25W	2000	90	

Example: **WS-W66922-BK**

Barrel

5", 6" & 8" LED Outdoor Sconce



Mid-Century, this century.


Barrel

5", 6" & 8" LED Outdoor Sconce



Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 54,000 hours
Input: 120V

- Aluminum hardware
- Up and down illumination
- No transformer or driver needed
- Compact design



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-W64905	5"	6.5W	622	189	BK Black AL Brushed Aluminum <div style="display: flex; justify-content: space-around; margin-top: 5px;"> <div style="width: 15px; height: 10px; background-color: black;"></div> <div style="width: 15px; height: 10px; background-color: #cccccc;"></div> </div>
WS-W64906	6"	6.5W	622	231	
WS-W64908	8"	21W	1089	447	

Example: **WS-W64905-AL**


Steampunk


9" & 13" LED Outdoor Sconce



Color Temp: 3000K
CRI: 90
Dimming: 100%–10% ELV
Rated Life: 54,000 hours
Input: 120V (277V special order)

- Aluminum construction
- Mouth blown glass is seeded and hammered to create dramatic patterns
- Weather resistant finish
- No transformer or driver required



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-W24509	9"	10W	744	400	BK Black BZ Bronze GH Graphite AB Aged Brass
WS-W24513	13"	10W	818	475	

Example: **WS-W24513-BK**
 For 277V special order, add an "F" before the finish: **WS-W24513F-BK**



Steampunk

9" & 13" LED Outdoor Sconce



Vintage industrial.

Chamber


12", 16", 20", & 25" LED Outdoor Wall Sconce




Bold Mid-Century Modern look with intersecting aluminum frames and cutting-edge LED light.

Color Temp: 3000K
CRI: 90
Dimming: 100%–10% ELV
Rated Life: 50,000 hours*
Input: 120V (277V special order)


- Solid aluminum construction with weather-resistant finish
- Minimal mounting hardware for easy installation
- Light engine is factory sealed for maximum protection from the elements
- No transformer or driver required




WS-W48612



WS-W48616



WS-W48620



WS-W48625


		Size	Watt	LED Lumens	Delivered Lumens	Finish
	WS-W48612	12"	9.5W	800	213	
	WS-W48616	16"	12W	1000	255	
	WS-W48620	20"	18W	1600	519	
	WS-W48625	25"	22W	1800	605	
	BK	Black				
	BZ	Bronze				

Example: **WS-W48616-BK**

For 277V, add an "F" before the finish: **WS-W48616F-BK**

Chamber

16" LED Outdoor
Pendant




	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-W48616	16"	12W	1000	372	BK <i>Black</i> BZ <i>Bronze</i>

Example: **PD-W48616-BK**

Chamber

20" LED Outdoor Post Mount



	Size	Watt	LED Lumens	Delivered Lumens	Finish
PM-W48620	20"	17.5W	1600	634	BK <i>Black</i> BZ <i>Bronze</i>

Example: **PM-W48620-BZ**

Fiction


14", 20" & 26" LED Outdoor Sconce




Modern elegance in a powerful, iconic design.

Color Temp: 3000K
CRI: 90
Dimming: 100%-10% ELV; 0-10V Triac
Rated Life: 50,000 hours
Input: 120V-277V

- Aluminum hardware with acrylic diffuser
- Driver located within the fixture
- Front etched acrylic panel design



	Size	LED Lumens	Watt	Delivered Lumens	Finish
WS-W11914	14"	788	9W	445	BK <i>Black</i> 
WS-W11920	20"	1666	15W	758	
WS-W11926	26"	2855	20W	1132	

Example: **WS-W11914-BK**

Oberon


14", 20", & 26" LED Outdoor Sconce




A timeless contemporary guardian.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 54,000 hours
Input: 120V (277V special order)

- Modern elegance brought to your backyard
- Bent opal glass provides even illumination
- Weather-resistant powder coated finish
- Light engine is factory sealed for maximum protection from the elements
- Mount horizontally or vertically
- Solid aluminum construction
- No transformer or driver required



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-W45714	14"	19.5W	1865	685	BK Black 
WS-W45720	20"	19.5W	1900	745	
WS-W45726	26"	35W	3273	1026	

Example: **WS-W45714-BK**
 For 277V, add an "F" before the finish: **WS-W45720F-BK**


Grate


12", 18" & 28" LED Outdoor Sconce



Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours*
Input: 120V

- Aluminum construction
- Weather-resistant finish
- No transformer or driver needed



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-W39812	12"	8W	602	132	BK <i>Black</i> 
WS-W39818	18"	10W	811	190	
WS-W39828	28"	13W	980	214	

Example: **WS-W39818-BK**



An effortless look of durable heavy-gauge aluminum in black.

Sodor



8" & 10" LED Outdoor Wall Sconce






Steamworks inspired contemporary approach to a traditional lantern.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 54,000 hours
Input: 120V

- Weather-resistant powder coated finishes
- Heavy aluminum shade provides great glare cut off
- Light engine is factory sealed for maximum protection from the elements
- Die-cast aluminum construction
- No transformer or driver required



		Size	Watt	LED Lumens	Delivered Lumens	Finish
	WS-W15708	8"	12W	1000	314	BZ Bronze GH Graphite BK Black 
	WS-W15710	10"	15W	1200	484	

Example: **WS-W15708-GH**

Folsom


10" & 14" LED Outdoor Wall Sconce






Breakout structural design with clean modern elegance.


Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10% ELV
 Rated Life: 45,000 hours
 Input: 120V (277V special order)

- UV rated acrylic
- Weather-resistant powder coated finish
- Light engine is factory sealed for maximum protection from the elements
- Solid aluminum construction
- Mount vertically or horizontally
- No transformer or driver required



	Size	Watt	LED Lumens	Delivered Lumens	Finish
	WS-W23610	10"	7.5W	642	121
	WS-W23614	14"	13W	1158	162


BZ Bronze 

BK Black 

Example: **WS-W23610-BK**
 For 277V special order, add an "F" before the finish: **WS-W23610F-BK**


Inset

12" & 16" LED Interior/Exterior Wall Sconce




Color Temp: 3000K
CRI: 90
Dimming: 100%–10% ELV
Rated Life: 50,000 hours*
Input: 120V–277V

- Customizable - contact factory for options
- Aluminum construction
- UV-rated double-layer acrylic/PC diffuser, additional etched glass diffuser at bottom for downlight
- Universal voltage driver (120V-220V-277V) concealed within fixture



WS-W77812

WS-W77816

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-W77812	12"	20W	1061	743	BK <i>Black</i> 
WS-W77816	16"	27W	1400	980	

Example: **WS-W77812-BK**

Inset

12" & 16" LED Interior/Exterior Wall Sconce



Edge-mounted LED modules stream powerful light into an innovative extraction panel.


Case

9", 14" & 20" LED Outdoor Sconce



Color Temp: 3000K
CRI: 90
Dimming: 100%–10% ELV
Rated Life: 81,000 hours
Input: 120V (277V Special Order)

- Aluminum or 316 stainless steel construction, UV-rated acrylic diffuser
- Weather-resistant black finish in aluminum construction
- No transformer or driver needed




Case

9", 14" & 20" LED Outdoor Sconce



Clean, simple form with weather-resistant black or durable stainless steel. Mount it vertically or horizontally.

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-W47809	9"	13W	1040	411	SS <i>Stainless Steel</i> BK <i>Black</i> 
WS-W47814	14"	22W	1644	885	
WS-W47820	20"	34W	2560	1034	

Example: **WS-W47809-SS**

For 277V special order, add an "F" before the finish: **WS-W47814F-BK**

Block


6" & 8" LED Outdoor Sconce



WS-W61808-AL shown

Color Temp: 3000K
CRI: 90
Dimming: 100%–10% ELV
 100%–5% 0-10V
 100%–5% Triac (WS-W61808)
Rated Life: 50,000 hours
Input: 120V–277V (WS-W61808 120V Only)

- Aluminum construction, die-cast glass accents
- Weather-resistant finish
- 6" version can be mounted vertically or horizontally
- Universal voltage driver (120V-220V-277V for WS-W61808) concealed within fixture



WS-W61806

WS-W61808

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-W61806 <i>One Direction</i>	6"	9W	615	540	AL <i>Brushed Aluminum</i>
WS-W61808 <i>Up & Down light</i>	8"	15W	947	773	BK <i>Black</i>
					BZ <i>Bronze</i>

Example: **WS-W61808-AL**

Block

6" & 8" LED Outdoor Sconce



WS-W61806-BK shown

Eye-catching cast glass on a clean block design.


Cylo

9", 16" & 24" LED Outdoor Sconce




Color Temp: 3000K, 4000K
CRI: 90
Dimming: 100%–10% ELV
Rated Life: 50,000 hours
Input: 120V (277V Special Order)


- Aluminum construction, natural white UV-rated acrylic diffuser
- Weather-resistant finish
- No transformer or driver needed



WS-W91809




WS-W91816




WS-W91824

Cylo

9", 16" & 24" LED Outdoor Sconce



Crafted in aluminum with contrast endcaps in durable weather-resistant finishes.

	Size	Watt	Color Temp	LED Lumens	Delivered Lumens	Finish
WS-W91809-30	9"	11W	3000K	776	537	BZ Bronze TT Titanium 
WS-W91809-40		11W	4000K	807	559	
WS-W91816-30	16"	20W	3000K	1683	1279	
WS-W91816-40		20W	4000K	1788	1359	
WS-W91824-30	24"	37W	3000K	3132	2513	
WS-W91824-40		37W	4000K	3241	2601	

Example: **WS-W91824-40-TT**

For 277V special order, add an "F" before the color temperature: **WS-W91824F-40-BZ**

Caliber

10" & 14" LED Outdoor Sconce



Light projection tuned with precision.


Caliber

10" & 14" LED Outdoor Sconce



Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 72,000 hours
Input: 120V-277V

- Discreet cylinder with minimal mounting hardware
- Light engine is factory sealed for maximum protection from the elements
- Can be mounted vertically or horizontally
- Solid aluminum construction
- Universal driver (120V-220V-277V) located within fixture



WS-W36610

WS-W36614

	Size	Watt	LED Lumens	Delivered Lumens	Finish
	WS-W36610 <i>One Direction</i>	10"	11W	735	560
	WS-W36614 <i>Up & Down Light</i>	14"	21W	1500	1140
					AL Brushed Aluminum BZ Bronze BK Black WT White

Example: **WS-W36614-AL**

Latitude


10", 14" & 20" LED Outdoor Sconce







Classic architectural lighting form offered in complementary sizes.


Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours
Input: 120V (277V special order)

- Classic architectural look that pairs well with a multitude of commercial applications
- Weather-resistant powder coated finishes
- Light engine factory sealed for maximum protection from the elements
- Solid aluminum construction
- Etched opal glass diffuser provides even illumination
- No transformer or driver required



	Size	Watt	LED Lumens	Delivered Lumens	Finish
	WS-W52610	10"	12W	765	415
	WS-W52614	14"	17.5W	1255	735
	WS-W52620	20"	19W	1220	790

BZ Bronze 

BK Black 

Example: **WS-W52610-BK**
 For 277V, add an "F" before the finish: **WS-W52620F-BK**

Funnel

12" & 17" LED Outdoor Sconce




TITLE 24
CALIFORNIA




Virtuosic composition of light and form.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV or 0-10V
Rated Life: 75,000 hours
Input: 120V-277V

- Up & down light
- Light engine is factory sealed for maximum protection from the elements
- Weather resistant powder coated finish
- Die-cast aluminum construction
- Mount vertically or horizontally (WS-W37617)
- Universal driver (120V-220V-277V) located inside the fixture



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-W37612	12"	21W	1546	997	BZ Bronze 
WS-W37617	17"	21W	1546	960	

Example: **WS-W37617-BZ**

Hurricane

10" & 14" LED Outdoor Sconce




A modern interpretation of a familiar icon representing a refuge.



Color Temp: 3000K
CRI: 90
Dimming: 100% - 5% ELV
Rated Life: 54,000 hours
Input: 120V

- Light engine is factory sealed for maximum protection from the elements
- Sconce may be rotated 180° when mounting
- Solid aluminum construction
- Mouth blown etched glass
- No transformer or driver required



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-W38710	10"	11.5W	700	500	BK <i>Black</i> 
WS-W38714	14"	12.5W	750	500	

Example: **WS-W38710-BK**

Hurricane

10" & 14" LED Outdoor Sconce



Mod

6" LED Outdoor Sconce


TITLE 24
CALIFORNIA





Modernistic and always in fashion.
A clean asymmetrical down light.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 70,000 hours
Input: 120V-277V

- Low profile with effective path illumination
- Weather-resistant powder coated finish
- Light engine is factory sealed for maximum protection from the elements
- Die-cast aluminum construction
- Luminaire may be rotated 180° when mounting
- Intergrated driver
- Universal driver (120V-220V-277V)



	Size	Watt	LED Lumens	Delivered Lumens	Finish
	6"	12W	1165	850	BZ Bronze GH Graphite WT White BK Black 
	WS-W65607				

Example: **WS-W65607-BZ**

Zealous


10" & 14" LED Outdoor Sconce




Expressively passionate
but with solemn restraint.

- Front hood provides excellent cut off for a discrete but functional path light
- Weather-resistant powder coated finish
- Light engine is factory sealed for maximum protection from the elements
- Solid aluminum construction
- No transformer or driver required





Color Temp: 3000K
CRI: 90
Dimming: 100% - 5% ELV
Rated Life: 44,000 hours
Input: 120V (277V special order)



WS-W53610



WS-W53614

	Size	Watt	LED Lumens	Delivered Lumens	Finish
	WS-W53610	10"	9.5W	700	330
	WS-W53614	14"	12W	840	365
					BZ Bronze  GH Graphite 

Example: **WS-W53610-BZ**
 For 277V, add an "F" before the finish: **WS-W53614F-BZ**

Icon


14" & 20" LED Outdoor Sconce




Like a simple reference
to something greater,
the up and down lights
accentuate linear architectural forms

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 54,000 hours
Input: 120V-277V




- Simple shape, simple idea, infinite applications
- Shielded light source for great low-glare illumination
- Driver located inside the fixture
- Up & down light
- Universal driver (120V-220V-277V)
- Weather resistant powder coat finish



WS-W54620



WS-W54614

		Size	Watt	LED Lumens	Delivered Lumens	Finish
	WS-W54614	14"	11W	847	458	AL <i>Brushed Aluminum</i> BZ <i>Bronze</i> BK <i>Black</i> 
	WS-W54620	20"	11W	631	478	

Example: **WS-W54614-AL**

Uno


15" LED Outdoor Sconce



This is The One.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 80,000 hours
Input: 120V (277V special order)

- In a class of its own
- The unique illuminating element on the face indirectly reflects light back towards the viewer with an intriguing dimensional character
- May be rotated 180° during mounting
- Solid aluminum construction
- Weather resistant powder coated finishes
- No transformer or driver required



	Size	Watt	LED Lumens	Delivered Lumens	Finish
	15"	15W	1234	875	BZ Bronze
					GH Graphite
					WT White

Example: **WS-W5915-WT**
 For 277V, add an "F" before the finish: **WS-W5915F-WT**

Tao


12" & 18" LED Outdoor Sconce




Architecturally harmonious form.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 80,000 hours
Input: 120V (277V special order)

- Silver crystal glass window adds visual interest
- Gravity cast aluminum housing
- Minimal mounting hardware for easy installation
- Downlight adds functional path lighting
- Weather resistant powder coated finish
- No transformer or driver required



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-W5312	12"	11W	830	220	BZ Bronze 
WS-W5318	18"	15W	1218	250	

Example: **WS-W5318-BZ**
 For 277V, add an "F" before the finish: **WS-W5318F-BZ**

Nest


12" & 16" LED Outdoor Sconce




Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 5% ELV
 Rated Life: 54,000 hours
 Input: 120V

A harmonious blend of modern with arts & crafts.

- Extruded aluminum louvers create a dramatic pattern of light to generate interest
- Solid aluminum construction
- Light engine is factory sealed for maximum protection from the elements
- Weather resistant powder coated finish
- No transformer or driver required



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-W26712	12"	8.5W	180	145	BZ Bronze 
WS-W26716	16"	13W	280	210	

Example: **WS-W26712-BZ**

Spa


16" & 22" LED Outdoor Sconce



Dazzling. Shimmering.
Sparkle of light.


Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 54,000 hours
Input: 120V

- Hand poured pane of art glass creates beautiful, dramatic patterns of light
- Weather resistant powder coated finish
- Light engine is factory sealed for maximum protection from the elements
- Solid aluminum construction
- No transformer or driver required



WS-W41716


WS-W41722

	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-W41716	16"	12.5W	375	185	BZ Bronze 
WS-W41722	22"	12.5W	365	180	

Example: **WS-W41716-BZ**

Mesh


9", 12" & 15" LED Outdoor Sconce




Mesmerizing mesh screen provides exciting visual pattern of this light on the wall or facade

Color Temp: 3000K
CRI: 90
Dimming: 100% - 0% ELV
Rated Life: 44,000 hours
Input: 120V (277V special order)

- Adds a dramatic and industrial flair to any space
- Solid heavy gauge aluminum mesh creates an optical illusion
- Weather resistant powder coated finish
- Light engine factory sealed for maximum protection from the elements
- No transformer or driver required



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-W43709	9"	4.5W	310	55	
WS-W43712	12"	7W	600	85	BZ Bronze 
WS-W43715	15"	9.5W	800	125	

Example: **WS-W43709-BZ**
 For 277V, add an "F" before the finish: **WS-W43709F-BZ**

Verve

14" & 26" LED Outdoor Sconce




TITLE 24
CALIFORNIA





Signature minimalism. Also mounts beautifully as elongated horizontal sconces with up & down illumination.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 56,000 hours
Input: 120V (277V special order)

- Silk-screened diffuser with a white ceramic glaze
- Seamless exterior makes for a clean design
- Up & down light
- Mount vertically or horizontally
- No transformer or driver required
- Conversion plate for 4" junction box included



	Size	Watt	LED Lumens	Delivered Lumens	Finish
	WS-W17714 14"	23W	1000	495	AL Brushed Aluminum BK Black WT White
	WS-W17726 26"	46W	2000	1092	

Example: **WS-W17714-AL**
 For 277V, add an "F" before the finish: **WS-W17714F-AL**

Panorama


18" & 24" LED Outdoor Sconce




Breathtaking presentation of light.
Vertical or landscape design.

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 36,000 hours
Input: 120V

- Edge-lit magic
- Finally, edge lighting for outdoor use
- Mount vertically or horizontally
- Water drainage designed into fixture
- Edge-lit acrylic diffuser for unique no-glare illumination
- No transformer or driver required



	Size	Watt	LED Lumens	Delivered Lumens	Finish
WS-W29718	18"	11.5W	800	245	AL <i>Brushed Aluminum</i> 
WS-W29724	24"	23.5W	2000	515	

Example: **WS-W29718-AL**

Copa

9", 13" & 17" Interior/Exterior
LED Pendant





TITLE 24
CALIFORNIA



Color Temp: 3000K
CRI: 90
Dimming: 100% - 5% ELV / 0-10V
Rated Life: 50,000 hours*
Input: 120V

- Aluminum construction
- Smooth round exterior with weather-resistant finish, contrast ribbing on interior
- Three 12" and one 6" downrod included, additional rods available
- Can be mounted on a sloped ceiling, swivel attachment included for seismic protection
- Driver concealed within canopy
- IP65 rated



	Size	Watt	LED Lumens	Delivered Lumens	Finish
PD-W55809	9"	17W	853	403	WT/GR White/Gold Ribbed BK/GR Black/Gold Ribbed 
PD-W55813	13"	18W	1201	620	
PD-W55817	17"	19W	1344	677	

Example: **PD-W55813-BK/GR**

Copa

9", 13" & 17" Interior/Exterior
LED Pendant



TITLE 24
CALIFORNIA



The smooth graceful lines of the matte-finished shade contrast with the textured gold interior on this elegant pendant, perfect for dining rooms, kitchens, alcoves, restaurants and hospitality spaces.

Index

A

ACTION 65
ARCHETYPE 193,194,195,196
ASHTON 145
AVIATOR 166

B

BANDED 75
BARREL 200
BLAST OFF 71
BLISS 131
BLOCK 215
BLOK 153,154
BOSSA NOVA 39,174
BRIC 159
BRINK 128

C

CALIBER 78,220
CASE 214
CHAMBER 203,204
CHARMED 9,72,152
COCO 168
COPA 235
CORBUSIER 172
CORSO 25,95
CRATER 69
CYLO 218

D

DICE 104
DIMPLE 66
DIVERGENCE 11
DOT 101
DUNHILL 147

E

E=MC2 48
ELEKTRON 84,100
ELEMENTUM 79,136
ENDURE 117
ENTERPRISE 62
EQUATION 113
ESPRIT 118

F

FARMHOUSE 191
FICTION 205
FLARE 56
FLIP 183
FLOAT 162
FLY 179
FOLSOM 210
FRAME 33
FUNNEL 222
FUTURE 67

G

GEOS 93,94

GRATE 207

H

HEMMINGWAY 178
HORIZON 143
HOUDINI 6
HUDSON 177
HURRICANE 223

I

ICON 227
ILLUSION 29
INSET 211
INTERLACE 18,111

K

KLEIN 188

L

LATITUDE 221
LEVEL 50,120,169
LINE 51,122
LINK 164
LOLLI 74
LOOPHOLE 52

M

MADISON 91
MALLOW 80
MANHATTAN 87,88,105,155
MERIDIEN 106,141,142
MESH 232
MOD 225
MODERNE 165
MYTHICAL 157,158

N

NAPA 82
NEST 230
NIGHTSTICK 124
NIVEOUS 86,107

O

OBERON 206
OMEGA 45
ORBIT 21

P

PANORAMA 234
PASSAGE 198
PASSION 70
PLANETS 99
POCKET 151
PROHIBITION 167

R

RADIUS 37
RATIO 129
REFLECTION 138

REVEL 126
ROCKET 76
RONDELLE 148
RONIN 41

S

SCOPE 186,187
SLANT 197
SLICE 103
SMASH 61
SMORE 60
SODOR 209
SOHO 140
SOLARIS 7
SPA 231
STACK 31
STEAMPUNK 201
STELLA 171
STRETCH 184
STRIP 139
SVELTE 132

T

TAO 229
TENOR 58
TETRIS 96
THEORY 137
TICTOC 73
TRAP 36
TRICK BOX 43,44
TRIO 116
TUMBLING 20
TURBO 163
TWINKLETWINKLE 57

U

UNO 228

V

VANITY 49
VERGE 119
VERVE 233
VIBE 180
VIDA 27
VIE 108,144,161
VISTA 134
VODUS 59
VOLO 54
VORNADO 14,16,63,98
VOYAGER 23

W

WAND 115
WEDGE 170

Z

ZEALOUS 226

Index

B

BL-1021	183
BL-1630	184
BL-1660	184
BL-29903	186
BL-25906	188
BL-28903	187

F

FM-4006	104
FM-4009	104
FM-4012	104
FM-4014	104
FM-4109	103
FM-4111	103
FM-4115	103
FM-4313	108
FM-4606	93
FM-4610	93
FM-4615	94
FM-4622	94
FM-13114	88,105
FM-13120	88,105
FM-13126	88,105
FM-16617	99
FM-16622	99
FM-21720	84,100
FM-21728	84,100
FM-33718	95
FM-33723	95
FM-38918	96
FM-38924	96
FM-57614	106
FM-87731	98
FM-96916	91
FM-96922	91
FM-96928	91
FM-W52306	107
FM-W52309	107
FM-W57806	101
FM-W57809	101
FM-W57812	101
FM-W57815	101

P

PD-12911	61
PD-13714	87
PD-13720	87
PD-13726	87
PD-14912	58
PD-16906	59
PD-18913	57
PD-21828	45
PD-22754	54

PD-23852	52
PD-26611	79
PD-26616	79
PD-27802	37
PD-27803	37
PD-29803	31
PD-29806	31
PD-29809	31
PD-29828	33
PD-29858	33
PD-31727	29
PD-31735	29
PD-31947	43
PD-33718	25
PD-33732	25
PD-33743	25
PD-33753	25
PD-34911	60
PD-36714	80
PD-36912	62
PD-37806	73
PD-37814	73
PD-40901	23
PD-40902	23
PD-40903	23
PD-42912	82
PD-42918	82
PD-45747	48
PD-46920	20
PD-46925	20
PD-46933	20
PD-46954	20
PD-47828	18
PD-47839	18
PD-48932	21
PD-48948	21
PD-51148	51
PD-51712	76
PD-52008	74
PD-52307	86
PD-52310	86
PD-52313	86
PD-54901	72
PD-54924	9
PD-54932	9
PD-54934	9
PD-55904	6
PD-55906	6
PD-55912	6
PD-58908	70
PD-60723	49
PD-60944	11
PD-60964	11
PD-62913	71
PD-63944	41
PD-64909	66
PD-68909	75
PD-70913	56
PD-70925	56
PD-70937	56
PD-70945	56
PD-72718	27
PD-72724	27
PD-72912	67
PD-76908	65
PD-84907	63
PD-85648	50
PD-85665	50
PD-87720	14
PD-87723	14
PD-87729	16
PD-87735	14
PD-87741	16
PD-93834	39

PD-93838	39
PD-93844	39
PD-93854	39
PD-94940	7
PD-95820	36
PD-95827	36
PD-95838	36
PD-98908	69
PD-W15918	195
PD-W15928	196
PD-W36610	78
PD-W48616	204
PD-W55809	235
PD-W55813	235
PD-W55817	235
PL-22916	179
PL-LED14	178
PL-LED15	180
PL-LED17	177
PL-LED23	177
PL-LED24	178
PL-LED25	180
PL-LED34	177
PL-LED37	180
PM-W48620	204

W

WS-6111	140
WS-6117	140
WS-6123	140
WS-6614	161
WS-6618	144
WS-6620	161
WS-6624	144
WS-6636	144
WS-6718	122
WS-6724	122
WS-6736	122
WS-7213	136
WS-7222	136
WS-7230	136
WS-7312	162
WS-7316	132
WS-7318	162
WS-7322	132
WS-7334	132
WS-10614	164
WS-11807	159
WS-12712	158
WS-12713	157
WS-12718	157
WS-12724	157
WS-13107	155
WS-13115	155
WS-13122	155
WS-13208	171
WS-13212	171
WS-13217	171
WS-19831	115
WS-14610	163
WS-17825	119
WS-17837	119
WS-19831	115
WS-25612	153
WS-26922	113
WS-26930	113
WS-26940	113
WS-30907	151
WS-32912	154
WS-35819	124

WS-35825	124	WS-W11920	205
WS-35837	124	WS-W11926	205
WS-35849	124	WS-W13918	193
WS-35861	124	WS-W14911	197
WS-35873	124	WS-W15708	209
WS-35897	124	WS-W15710	209
WS-39513	145	WS-W15912	194
WS-39522	145	WS-W15918	194
WS-40520	147	WS-W15924	194
WS-40526	147	WS-W17714	233
WS-40615	165	WS-W17726	233
WS-40720	134	WS-W23610	210
WS-40726	134	WS-W23614	210
WS-40738	134	WS-W24509	201
WS-42505	148	WS-W24513	201
WS-42514	148	WS-W26712	230
WS-42524	148	WS-W26716	230
WS-42618	172	WS-W29718	234
WS-42725	137	WS-W29724	234
WS-42732	137	WS-W36610	220
WS-43613	166	WS-W36614	220
WS-45620	167	WS-W37612	222
WS-46609	168	WS-W37617	222
WS-47828	111	WS-W38710	223
WS-47838	111	WS-W38714	223
WS-51820	116	WS-W39812	207
WS-51828	116	WS-W39818	207
WS-51837	116	WS-W39828	207
WS-53820	117	WS-W41716	231
WS-53827	117	WS-W41722	231
WS-53837	117	WS-W43709	232
WS-54919	152	WS-W43712	232
WS-57609	141	WS-W43715	232
WS-57620	141	WS-W45714	206
WS-57627	142	WS-W45720	206
WS-57637	142	WS-W45726	206
WS-58618	143	WS-W47809	214
WS-58626	143	WS-W47814	214
WS-59623	138	WS-W47820	214
WS-59629	138	WS-W48612	203
WS-59639	138	WS-W48616	203
WS-63718	139	WS-W48620	203
WS-63724	139	WS-W48625	203
WS-63736	139	WS-W52610	221
WS-69815	118	WS-W52614	221
WS-69826	118	WS-W52620	221
WS-69838	118	WS-W53610	226
WS-75818	170	WS-W53614	226
WS-77612	128	WS-W54614	227
WS-77618	128	WS-W54620	227
WS-77624	128	WS-W61806	215
WS-77636	128	WS-W61808	215
WS-79622	131	WS-W64905	200
WS-79628	131	WS-W64906	200
WS-79636	131	WS-W64908	200
WS-82919	126	WS-W65607	225
WS-82925	126	WS-W66914	198
WS-82937	126	WS-W66922	198
WS-82950	126	WS-W68913	191
WS-82962	126	WS-W68917	191
WS-82974	126	WS-W77812	211
WS-82998	126	WS-W77816	211
WS-85618	120,169	WS-W91809	218
WS-85624	120,169	WS-W91816	218
WS-85636	120,169	WS-W91824	218
WS-93801	174		
WS-93803	174		
WS-99820	129		
WS-99830	129		
WS-99840	129		
WS-W5312	229		
WS-W5318	229		
WS-W5915	228		
WS-W11914	205		

