



UNBREAKABLE THERMOPLASTIC WALLPLATES

Standard Size
Midi Size
Custom Marking
Special Applications





Features and Benefits

Mulberry Unbreakable Thermoplastic Wallplates

STRENGTH

- Made from rugged thermoplastic resin, Mulberry wallplates will not crack during installation or after many years of use.
- Withstand several times more impact, torque and load deflection than thermoset plates.
- Flexible design fits over uneven wall surfaces.
- Thicker than nylon plates.
- Will not fade or warp due to UV light or humidity.
- Resist grease, oils and solvents.
- Excellent color retention – will not fade or discolor.

SELECTION

- Wide selection of plastic wallplate openings.
- Individually wrapped and bar coded
- Standard configurations available from 1 to 6 gang.
- 4 colors.
- Matching metal screws.

SPECIAL APPLICATIONS



- Specification grade material, suitable for hospitals, schools and other institutional facilities.
- Custom wallplates – Mulberry thermoplastic is uniquely suited to stamping special openings.
- Ideal for custom marking. In-house engraving and silk screening available.

Meet or exceed UL, CSA and NEC requirements



THERMOPLASTIC

Standard Size



- 1-Toggle Switch (1T)
- 2-Toggle Switches (2T)
- 3-Toggle Switches (3T)
- 4-Toggle Switches (4T)
- 5-Toggle Switches (5T)
- 6-Toggle Switches (6T)
- 1-Duplex Receptacle (10DR)
- 2-Duplex Receptacles (20DR)
- 3-Duplex Receptacles (30DR)
- 4-Duplex Receptacles (40DR)
- 1 Single Receptacle (1.405") (1OR)
- 2 Single Receptacles (1.405") (2OR)

	White	Light Almond	Ivory	Red
1-Toggle Switch (1T)	32071	33071	34071	36071
2-Toggle Switches (2T)	32072	33072	34072	36072
3-Toggle Switches (3T)	32073	33073	34073	
4-Toggle Switches (4T)	32074	33074	34074	
5-Toggle Switches (5T)	32075	33075	34075	
6-Toggle Switches (6T)	32076	33076	34076	
1-Duplex Receptacle (10DR)	32101	33101	34101	36101
2-Duplex Receptacles (20DR)	32102	33102	34102	36102
3-Duplex Receptacles (30DR)	32103	33103	34103	
4-Duplex Receptacles (40DR)	32104			
1 Single Receptacle (1.405") (1OR)	32091	33091	34091	36091
2 Single Receptacles (1.405") (2OR)	32092	33092	34092	36092




THERMOPLASTIC

Standard Size




Listed unless marked with an asterisk (*)



2.76"

4.5"



- 1 Blank
(Box Mntg. 3.281") (1B)
- 2 Blanks
(Box Mntg. 3.281") (2B)
- 3 Blanks
(Box Mntg. 3.281") (3B)
- 4 Blanks
(Box Mntg. 3.281") (4B)
- One 20A TL Receptacle
(1.620" ID Hole) (3R)*
- 30/50A 3 Wire
Range/Dryer Receptacle
(2.125" ID Hole) (3D)*
- 30/50A 3 Wire
Range/Dryer Receptacle
(2.125" ID Hole) (N23D)*
- 30/50/60A
4 Wire Receptacles
with 2.625" ID Hole (L5R)*
- One 1/2" ID Phone
(Box Mntg. 3.281") (21)*
- One 5/8" ID Phone
(Box Mntg. 3.281") (01)
- One Phone 1.405"
w/ 1" ID Plastic Bushing
(Box Mntg. 3.281")(71)
- Block
Duplex/
GFI Recept. (SRM)



	White	Light Almond	Ivory	Red
1 Blank (Box Mntg. 3.281") (1B)	32151	33151	34151	
2 Blanks (Box Mntg. 3.281") (2B)	32152	33152	34152	
3 Blanks (Box Mntg. 3.281") (3B)	32153	33153	34153	
4 Blanks (Box Mntg. 3.281") (4B)	32154			
One 20A TL Receptacle (1.620" ID Hole) (3R)*	32111	33111	34111	36111
30/50A 3 Wire Range/Dryer Receptacle (2.125" ID Hole) (3D)*	32221	33221	34221	
30/50A 3 Wire Range/Dryer Receptacle (2.125" ID Hole) (N23D)*	32227	33227	34227	
30/50/60A 4 Wire Receptacles with 2.625" ID Hole (L5R)*	32225	33225	34225	
One 1/2" ID Phone (Box Mntg. 3.281") (21)*	32381	33381	34381	
One 5/8" ID Phone (Box Mntg. 3.281") (01)	32201	33201	34201	
One Phone 1.405" w/ 1" ID Plastic Bushing (Box Mntg. 3.281")(71)	32581	33581	34581	
Block Duplex/GFI Recept. (SRM)	32401	33401	34401	36401

THERMOPLASTIC

Standard Size



Listed unless marked with an asterisk (*)



- 2 Block Duplex/
GFI Recepts.
(2SRM)
- 3 Block Duplex/
GFI Recepts.
(3SRM)
- 4 Block Duplex/
GFI Recepts.
(4SRM)
- 5 Block Duplex/
GFI Recepts.
(5SRM)
- 6 Block Duplex/
GFI Recepts.
(6SRM)
- Toggle Switch,
Duplex Receptacle
(1T-1ODR)
- Duplex Recept., Block
Duplex/GFI Recept.
(1ODR-SRM)
- Toggle Switch, Block
Duplex/GFI
Receptacle (1T-SRM)
- Toggle Switch, Blank
(Box Mntg. 3.281")
(1T-1B)
- Duplex Recept., Blank
(Box Mntg. 3.281")
(1ODR-1B)
- Block Duplex/GFI Recept.,
Blank (Box Mntg. 3.281")
(SRM-1B)
- Duplex Recept., Single
Recept. (1.405" ID Hole)
(1ODR-1OR)

	White	Light Almond	Ivory	Red
2 Block Duplex/ GFI Recepts. (2SRM)	32402	33402	34402	36402
3 Block Duplex/ GFI Recepts. (3SRM)	32403	33403	34403	
4 Block Duplex/ GFI Recepts. (4SRM)	32404	33404	34404	
5 Block Duplex/ GFI Recepts. (5SRM)	32405	33405	34405	
6 Block Duplex/ GFI Recepts. (6SRM)	32406	33406	34406	
Toggle Switch, Duplex Receptacle (1T-1ODR)	32532	33532	34532	
Duplex Recept., Block Duplex/GFI Recept. (1ODR-SRM)	32672	33672	34672	36672
Toggle Switch, Block Duplex/GFI Receptacle (1T-SRM)	32432	33432	34432	36432
Toggle Switch, Blank (Box Mntg. 3.281") (1T-1B)	32522	33522	34522	
Duplex Recept., Blank (Box Mntg. 3.281") (1ODR-1B)	32542	33542	34542	
Block Duplex/GFI Recept., Blank (Box Mntg. 3.281") (SRM-1B)	32422	33422	34422	
Duplex Recept., Single Recept. (1.405" ID Hole) (1ODR-1OR)	32572	33572	34572	




THERMOPLASTIC

Standard Size



Listed unless marked with an asterisk (*)



	Toggle Switch, Single Recept. (1.405" ID Hole) (1T-10R) *
	Single Recept. (1.405" ID Hole) Blank (Box Mntg. 3.281") (10R-1B) *
	Single Recept. (1.405" ID Hole) Block Duplex/GFI Recept. (10R-SRM) *
	2 Toggle Switches, Duplex Receptacle (2T-10DR)
	Toggle Switch, 2 Block Duplex/GFI Recepts. (1T-2SRM)
	2 Toggle Switches, Block Duplex/GFI Recept. (2T-SRM)
	2 Duplex Recepts., Block Duplex/GFI Recept. (20DR-SRM)
	3 Duplex Recepts., Block Duplex/GFI Recept. (30DR-SRM)
	Duplex Recept., 2 Block Duplex/GFI Recepts., (10DR-2SRM)
	3 Toggle Switches, Block Duplex/GFI Recept. (3T-SRM)
	Toggle Switch, 3 Block Duplex/GFI Recepts. (1T-3SRM)
	2 Toggle Switches, 2 Block Duplex/GFI Recepts. (2T-2SRM)
	4 Toggle Switches, Block Duplex/GFI Recept. (4T-SRM)



	White	Light Almond	Ivory	Red
	32512	33512	34512	36512
	32552	33552	34552	
	32442	33442	34442	36442
	32543	33543	34543	
	32453	33453	34453	
	32443	33443	34443	
	32673	33673	34673	
	32674			
	32683	33683	34683	
	32454	33454	34454	
	32654	33654	34654	
	32664	33664	34664	
	32465	33465	34465	

THERMOPLASTIC

Midi Size



Listed unless marked with an asterisk (*)



	White	Light Almond	Ivory
1-Toggle Switch (1T-MIDI)	32871	33871	34871
2-Toggle Switches (2T-MIDI)	32872	33872	34872
3-Toggle Switches (3T-MIDI)	32873	33873	34873
4-Toggle Switches (4T-MIDI)	32874	33874	34874
1-Duplex Receptacle (1ODR-MIDI)	32801	33801	34801
2-Duplex Receptacles (2ODR-MIDI)	32802	33802	34802
Block Duplex/GFI Recept. (SRM-MIDI)	32834	33834	34834
2 Block Duplex/GFI Recepts. (2SRM-MIDI)	32835	33835	34835
3 Block Duplex/GFI Recepts. (3SRM-MIDI)	32836	33836	34836
4 Block Duplex/GFI Recepts. (4SRM-MIDI)	32837	33837	34837
1 Blank (Box Mntg. 3.281") (1B-MIDI)	32851	33851	34851





THERMOPLASTIC


Midi Size





Listed unless marked with an asterisk (*)





- 

2 Blanks
(Box Mntg. 3.281")
(2B-MIDI)
- 

1 Single Receptacle
(1.405") (10R-MIDI)*
- 

Toggle Switch,
Duplex Receptacle
(1T-10DR-MIDI)
- 

Toggle Switch, Block
Duplex/GFI Receptacle
(1T-SRM-MIDI)
- 

Duplex Recept., Block
Duplex/GFI Recept.
(10DR-SRM-MIDI)
- 

2 Toggle Switches,
Block Duplex/GFI Recept.
(2T-SRM-MIDI)

	White	Light Almond	Ivory
2 Blanks (Box Mntg. 3.281") (2B-MIDI)	32852	33852	34852
1 Single Receptacle (1.405") (10R-MIDI)*	32891	33891	34891
Toggle Switch, Duplex Receptacle (1T-10DR-MIDI)	32832	33832	34832
Toggle Switch, Block Duplex/GFI Receptacle (1T-SRM-MIDI)	32865	33865	34865
Duplex Recept., Block Duplex/GFI Recept. (10DR-SRM-MIDI)	32862	33862	34862
2 Toggle Switches, Block Duplex/GFI Recept. (2T-SRM-MIDI)	32883	33883	34883

THERMOPLASTIC

Standard Size – Decorator Screwless Wall Plates

- Provides a clean, seamless look.
- Available in White or Light Almond from 1 to 5-gang.
- Two-piece screwless wall plate and sub plate allow for quick and easy installation.
- An extra 1/8 inch in width and height than standard size wall plates (helps cover any wall imperfections).



White	Light Almond
35401	37401
35402	37402
35403	37403
35404	37404
35405	37405




EMERGENCY, GFCI and ISOLATED GROUND PLATES

Special Applications



RED THERMOPLASTIC PLATES, "EMERGENCY" IN WHITE 1/4" SILK-SCREENED LETTERING


1 Toggle Switch	42071
2 Toggle Switches	42072



1 Duplex Receptacle	42101
2 Duplex Receptacles	42102
1 Single Receptacle	42091




1 Block/GFI Receptacle	42035
2 Block/GFI Receptacles	42036



IVORY THERMOPLASTIC PLATES, "GFCI PROTECTED" IN BLACK 1/4" SILK-SCREENED LETTERING

1 Duplex Receptacle	42112
1 Block/GFI Receptacle	42111



If you do not see what you need, please contact us.
Additional emergency and other metal plates are in Catalog A.

MATERIAL and DIMENSIONS

Mulberry wallplates meet or exceed UL and CSA requirements and comply with the National Electric Code and Federal Specification WP455A.

MATERIAL

- Molded of a rugged polycarbonate that is unmatched for strength and durability.
- Virtually unbreakable: Mulberry wallplates will not crack during installation or use.
- Flexible construction conforms to uneven wall surfaces and tolerates over-tight screws
- Smooth, bright surface for a clean appearance.
- Non-conductive.
- Available in four colors.
- Supplied with matching metal screws.

DIMENSIONS

Standard Size

1-gang	4.5" x 2.76"
2-gang	4.5" x 4.57"
3-gang	4.5" x 6.38"
4-gang	4.5" x 8.19"
5-gang	4.5" x 10.03"
6-gang	4.5" x 11.81"

Midi Size

1-gang	4.88" x 3.11"
2-gang	4.88" x 4.92"
3-gang	4.88" x 6.77"
4-gang	4.88" x 8.58"

Screwless


1-gang	4.625" x 2.875"
2-gang	4.625" x 4.685"
3-gang	4.625" x 6.505"
4-gang	4.625" x 8.315"
5-gang	4.625" x 10.155"

DEPTH / THICKNESS



SCREW HOLE SPACING

Standard Size





0518