

Outdoor

Lighting that defines your **style**™

Welcome



All the comforts of home
for more than 70 years.

Since 1938, Kichler® has offered so much more than just distinctively beautiful lighting. We've also backed each design with award-winning craftsmanship, unparalleled quality and superior service.



New styles. Popular colors. Distinct finishes. Kichler® has long led the industry in interior lighting trends. And now we extend those same design principles to the exterior of your home with Kichler Outdoor Lighting.

This inspirational outdoor lighting collection offers a beautifully diverse selection of innovative **energy efficient** lighting solutions, ranging from the practical to the extraordinary.

Lighting that defines your **style™**

To reflect your particular tastes, budget and lifestyle, Kichler Outdoor Lighting showcases exceptional design details like etched and beveled glass, solid brass, cast aluminum and stainless steel construction. Elegant, practical and functional, these outdoor lighting products add beauty and warmth – all while addressing your personal safety and security concerns.

With this much variety, there is one constant throughout the entire Kichler Outdoor Lighting line: all our outdoor lighting products feature the quality, durable materials and easy installation for which Kichler – the one-stop lighting authority – continues to be known.



“We have a **dramatic sense of style.** And, thanks to **Kichler® Landscape Lighting,** our house and yard reflect that – from the outside in.”




Lighting that defines your **style™**

Kichler® Landscape Lighting

Add style from the ground up.

See your dealer for information on our
full line of **Landscape Lighting**.



Set your home apart before anyone even walks through your door with Kichler Landscape Lighting.

Our professional grade outdoor lighting solutions illuminate your home's total exterior environment. Kichler Landscape Lighting generously brightens all outdoor living spaces – from trees, flowers and shrubs to decks, outdoor rooms, ponds and pathways – for a warm, inviting look.

Our entire line features the latest in energy saving Design Pro LED technology, rugged outdoor materials and long lasting durable finishes – all backed by premium warranties.

View our interactive catalog now at landscapelighting.com.


KICHLER
LIGHTING 

Designs
crafted
to inspire

Kichler is known for setting lighting design trends with popular finishes, fashion-forward collections and handcrafted details.

We take great pride in the craftsmanship that we build into everything we create.

The result is a collection of distinctive outdoor products that help express your unique style, taste and personality – whether it be casual, contemporary or traditional. We take pride in transforming lighting into beautiful, functional works of art that inspire you.



Time to Enlighten Why Choose Outdoor Lighting

1

Enhance Your Home's Beauty

The warm welcoming glow of Kichler Outdoor Lighting can instantly improve your home's curb appeal. With the right outdoor lighting, you can add drama while highlighting certain architectural details – like curves, textures, even windows.



2

Increase Your Family's Safety and Security

Kichler Outdoor Lighting adds visibility, allowing you, your family and your friends to move around more safely and easily after dark. A well-lit exterior decreases the chance of missteps and discourages intruders from approaching your home.

3

Create a Livable Outdoor Space

Outdoor living is one of today's fastest-growing trends. And good outdoor lighting is key in extending your outdoor space's charm and functionality long after sunset. Try coordinating your outdoor lights to your interior décor, or select the understated appeal of lighting that gracefully blends without being noticed.



4

Add Value To Your Home

Recognized for premium quality and style, Kichler Outdoor Lighting can help set your home apart, as well as add curb appeal and long-term value.



Lighting Tip

Match Bulb to Lantern Design

Bulb choice is another important factor to consider. Clear bulbs should be installed in fixtures with clear glass, while frosted bulbs work best in fixtures with frosted or translucent glass.

Symbol Guide

Refer to this symbol guide to help with your outdoor lighting selection














-  Damp Location Certified
-  W Wet Location Certified
-  Dark Sky Compliant
-  ADA A.D.A. Compliant
-  Hybrid
-  **OD** Hybrid Outdoor
-  ENERGY STAR®
-  T24 California Title 24 Compliant
-  Lamp Included
-  Photo Cell Included
-  Installation Instructions:
Fixture must be supported independently of the outlet box unless the outlet box is UL listed for the weight to be supported. Consult a qualified electrician / installer. Required installation parts included.
-  Fixture requires supply wire rated for at least 90° C.
-  Fixture requires supply wire rated for at least 75° C.

Table of Contents

LANTERN COLLECTIONS

Alameda™128-129	Franceasi™20-21	Northbridge™141
Amesbury™52	Franceasi™ LED... 14-15	Olympia™170
Astoria™74-75	Hendrik™104	Outdoor154
Atwood79	High Country™171	Outdoors™99-100
Bay Shore™48	Kirkwood™68-69	Energy Efficient101
Beacon Hill™40-41	La Mesa™126-127	Pasadena114-115
Benton™98	Lafayette™57	Portman Square™86-89
Brockton™84-85	Lancaster Gardens™135	Randolph™49
Cadiz™58	Lantana™80-81	Ripley™144-145
Camden™110-111	Leeds™94-95	Riverbank™120-121
Cameron™82-83	LifeBrite™46	Rockbridge™47
Cayman Shores™134	Luverne™32-33	Royal Marine™142
Celino™102	Lynnewood Gardens™132-133	Rustic™143
Centennial™103	Mackenzie™76-77	Salisbury™62-65
Chesapeake™148	Madison.....70-71	Sausalito™45
Chicago™118-119	Maya Palm™ LED16	Savannah Estates™44
Concord.....140	McCullam™30-31	Seaside™146-147
Corunna™34-35	Melbern™116-117	Takil™ LED17
Cotswold™136-137	Menlo™113	Tourmal™26-29
Courtyard™50-51	Meredith™170	Townhouse™66-67
Creston™105	Metro Park™96-97	Tremillo™92-93
Cross Creek™ ...122-123	Montara™112	Trenton™59
Duquesne™36-37	Morris™124-125	Tularosa™130-131
Eau Claire™42	Mount Vernon54-56	Venetian Rain™22-25
Elgin™43	New Street™ ...149-153	Vidalia.....140
Embassy Row60-61	Newport™102	Warner Park™38-39
Energy Efficient104, 155	North Creek™108-109	Warrington™53
Fallon™78		
	DARK SKY ACCESSORIES 156-157	LEGEND174
	POST & PEDESTAL ACCESSORIES 158-159	ACCESSORIES175
	OUTDOOR LIVING 160-172	INDEX175-177
	LIGHT BULB REFERENCE 173	



Lantern Visual Index



Alameda™
128-129



Amesbury™
52



Astoria™
74-75



Atwood™
79



Bay Shore™
48



Beacon Hill™
40-41



Cayman Shores™
134



Benton™
98



Brockton™
84-85



Cadiz™
58



Camden™
110-111



Cameron™
82-83



Celino™
102



Centennial™
103



Chesapeake™
148



Chicago™
118-119



Concord™
140



Corunna™
34-35



Cotswold™
136-137



Courtyard™
50-51



Creston™
105



Cross Creek™
122-123



Duquesne™
36-37



Eau Claire™
42




Elgin™
43




Embassy Row™
60-61



Fallon™
78



Franceasi™
20-21



Franceasi™ LED
14-15



Hendrik™
104



High Country™
171



Kirkwood™
68-69



La Mesa™
126-127



Lafayette™
57



Lancaster Gardens™
135



Lantana™
80-81



Leeds™
94-95



LifeBrite™
46



Luverne™
32-33



Lynnewood Gardens™
132-133



Mackenzie™
76-77



Madison
70-71



Maya Palm™ LED
16



McCullam™
30-31



Melbern™
116-117



Menlo™
113



Meredith™
170



Metro Park™
96-97



Montara™
112



Morris™
124-125



Mount Vernon
54-56



New Street™
149-153



Newport™
102



North Creek™
108-109




Northbridge™
141



Olympia™
170



Outdoor
154



Outdoors™
99-100



Pasadena
114-115



Portman Square™
86-89



Randolph™
49



Ripley™
144-145



Riverbank™
120-121



Rockbridge™
47



Royal Marine™
142



Rustic™
143



Salisbury™
62-65



Sausalito™
45




Savannah Estates™
44



Tremillo™
92-93



Seaside™
146-147



Takii™ LED
17



Tournai™
26-29



Townhouse™
66-67



Trenton™
59



Tularosa™
130-131



Venitian Rain™
22-25



Vidalia
140



Warner Park™
38-39



Warrington™
53

Energy Efficient Visual Index



Alameda™
128-129



Astoria™
74-75



Atwood
79



Brockton™
84-85



Camden™
110-111



Cameron™
82-83



Corunna™
34-35



Courtyard™
50-51



Energy Efficient
104



Energy Efficient
155



Energy Efficient
155



Lancaster Gardens™
135



Lantana™
80-81



Leeds™
94-95



Luverne™
32-33



Madison
71



McCullam™
30-31



Menlo™
113



Morris™
124-125



Mount Vernon
56



Newport™
102



Randolph™
49



North Creek™
108-109



Outdoors™
100



Outdoor/Indoor
101



Pasadena
114-115



Salisbury™
62-63



Seaside™
146



Tremillo™
92-93



Tularosa™
130-131



Warner Park™
38-39

10


Design Pro LED Visual Index



Franceasi™ LED
14-15



Maya Palm™ LED
16



Takil™ LED
17

Energy Efficient Lighting

Lighting accounts for some 20% of a home's energy costs. Kichler® Outdoor Lighting includes designs that may help decrease your energy bill, as well as your carbon footprint. Look for these symbols throughout our catalog for assistance in making an energy-efficient selection:



ENERGY STAR®

A joint program of the U.S. Environmental Protection Agency and the U.S. Department of Energy committed to energy-efficient products and practices. ENERGY STAR® products have extended warranties, are supplied with bulbs, and are also supplied with photocells.



Title 24

A California government-backed program that helps businesses and individuals protect the environment through superior energy efficiency. Title 24 lighting fixtures reduce energy bills and significantly help to protect our environment.



Design Pro LED

Advanced technology, ENERGY STAR® certified, long life and a pure, even flow of light are just a few of the professional advancements you'll find with Kichler Design Pro LED.



Dark Sky Compliant

Identifies Kichler fixtures that reduce light pollution by directing light downward and outward, not upward. Dark Sky Compliant fixtures also allow lower wattage bulbs to be as effective as higher wattage ones in an effort to conserve energy.

Brightness & Appearance

60-Watts, 75-Watts, 150-Watts. Most people think that wattage means the brightness of a light, but it's actually the amount of electricity consumed by a light bulb. The brightness of any light is measured in lumens.

The most accurate method to compare the brightness of bulbs or fixtures is to compare the lumens they emit. The higher the lumens, the brighter the light; different types of bulbs with the same lumens have the same brightness. If a fixture has multiple bulbs, add the lumens from each bulb together to come up with total lumens.


REMEMBER: Fluorescent bulbs can produce the same number of lumens as an incandescent bulb but at a much lower wattage, thereby using less energy.



Lighting Tip

Surrounding your home

Keep some dark areas to complement the light. Slight variations in wattage and lighting angles, as well as careful placement of lighting fixtures, can enhance your overall lighting design.









Whatever the outdoor application, the Kichler® Design Pro LED collection optimizes it with high-energy efficiency, consistent output and precise illumination.

D

DESIGN PRO LED

The result is a distinctive, beautiful light that enhances a home's exterior and carries a lifetime warranty on the light producing elements.

Symbol Guide

 D	DAMP	 T24	Title 24 Compliant
 W	WET		Lamp Included
 ☾	Dark Sky		Photocell Included
 ADA	ADA Compliant	 i	Installation Requirements
	Hybrid		90° C. Wire Rated
 OD	Hybrid Outdoor		75° C. Wire Rated
	Energy Star		

Franceasi™

Design Pro LED

Olde Bronze® Finish



A 49229 OZ LED



B 49226 OZ LED

Cast Aluminum
construction



Dark Sky
Compliant



POWERED BY
**DESIGN PRO
TECHNOLOGY**

The Design Pro LED technology, incorporated into these innovative lighting fixtures, uses only a fraction of the energy required by an incandescent bulb. Design Pro LED carries a 10 year/40,000 hour warranty on electrical components.



C 49228 OZ LED

Open Filigree
Lantern Back























D 49227 OZ LED

LED Equivalencies

8.8W	Light equivalent to a 40W incandescent bulb	78% energy savings	10 year or 40,000 hour warranty (whichever comes first).
11.4W	Light equivalent to a 60W incandescent bulb	81% energy savings	10 year or 40,000 hour warranty (whichever comes first).

LED
10 YEAR/40,000
HOUR WARRANTY

For more details,
visit kichler.com

	LED ITEM	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	49229 OZ LED	11.4W   	10	25	12	8.75	  Look for revised, open filigree lantern back on all Franceasi™ LED Lanterns
B	49226 OZ LED	8.8W   	5.5	14.5	7	4.75	  Look for revised, open filigree lantern back on all Franceasi™ LED Lanterns
C	49228 OZ LED	11.4W   	8.5	22	10.5	7.50	  Look for revised, open filigree lantern back on all Franceasi™ LED Lanterns
D	49227 OZ LED	8.8W   	7	18	9	6	  Look for revised, open filigree lantern back on all Franceasi™ LED Lanterns

Measurements shown in inches. U.S. Patent Pending. Also available in Incandescent see pages 20-21

Maya Palm™

Aged Bronze

Design Pro LED | Krypton

The Design Pro LED technology, incorporated into these innovative lighting fixtures, uses only a fraction of the energy required by an incandescent bulb. Design Pro LED carries a 10 year/40,000 hour warranty on electrical components.

POWERED BY
**DESIGN PRO
TECHNOLOGY**



A 49249 AGZ LED
49249 AGZ



B 49248 AGZ LED
49248 AGZ
ADA Compliant

LED
10 YEAR/40,000
HOUR WARRANTY













For more details,
visit kichler.com

LED Equivalencies

8.8W	Light equivalent to a 40W incandescent bulb	78% energy savings	10 year or 40,000 hour warranty (whichever comes first).
11.4W	Light equivalent to a 60W incandescent bulb	81% energy savings	10 year or 40,000 hour warranty (whichever comes first).

Cast Aluminum
construction

16

	LED ITEM	INCAND. ITEM	LIGHT SOURCE	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49249 AGZ LED	49249 AGZ	11.4W    	(1) 60W (K)	9.5	13.5	7	4.25	  LED Limited Lifetime Warranty, Incandescent fixtures have tempered glass
B	49248 AGZ LED	49248 AGZ	8.8W    	(1) 60W (K)	8	11	6	3.75	  LED Limited Lifetime Warranty, Incandescent fixtures have tempered glass

Measurements shown in inches. U.S. Patent Pending

Takil™

Aged Bronze

Design Pro LED

The Design Pro LED technology, incorporated into these innovative lighting fixtures, uses only a fraction of the energy required by an incandescent bulb. Design Pro LED carries a 10 year/40,000 hour warranty on electrical components.

POWERED BY
**DESIGN PRO
TECHNOLOGY**

LED
10 YEAR/40,000
HOUR WARRANTY

For more details,
visit kichler.com




A 49251 AGZ LED








B 49250 AGZ LED

Cast Aluminum
construction



Dark Sky
Compliant



	LED ITEM	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	49251 AGZ LED	11.4W    	10	13	8	5.50	  LED Limited Lifetime Warranty
B	49250 AGZ LED	8.8W    	8	10.5	6.5	4.50	  LED Limited Lifetime Warranty

Measurements shown in inches. U.S. Patent Pending



Lighting Tip

The Traditional look

For your colonial or Victorian-style home, complete the look with period-style outdoor lighting. Consider post lights that look like old-fashioned streetlamps to illuminate your yard.











Gracious and inviting, Kichler®
Traditional Lighting blends elegance
with warmth and classical comfort.



TRADITIONAL

Intricate details, rich finishes
and grand scale create a beauty
that's truly timeless.

Symbol Guide

 DAMP	 Title 24 Compliant
 WET	 Lamp Included
 Dark Sky	 Photocell Included
 ADA Compliant	 Installation Requirements
 Hybrid	 90° C. Wire Rated
 Hybrid Outdoor	 75° C. Wire Rated
 Energy Star	

Franceasi™

Olde Bronze® Finish and
Light Umber Seedy Glass

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.



A 49229 OZ



B 49228 OZ

Cast Aluminum
construction

20

	INCAND. ITEM	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49229 OZ	(1) 150W (M)	10	25	12.5	8.75	Ⓜ EOD (30-52W CFL)
B	49228 OZ	(1) 100W (M)	8.5	22	10.5	7.50	Ⓜ EOD (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending



C 49231 Pendant OZ



D 49232 OZ



E 49226 OZ




F 49227 OZ

	INCAND. ITEM	INCAND. BULB	W	H	OVRL H	WIRE (CHAIN)	EXT.	HCWO	NOTES
C	49231 OZ	(1) 100W (M)	7	20.5	94.5	24(72)	---	---	D OD (23-30W CFL) Additional chain 4927 OZ
D	49232 OZ	(2) 60W (M)	11	6.5	---	---	---	---	D OD (13-15W CFL)
E	49226 OZ	(1) 75W (M)	5.5	14.5	---	---	7.5	4.75	W OD (15-18W CFL)
F	49227 OZ	(1) 100W (M)	7	18	---	---	9	6.50	W OD (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending

Venetian Rain™

Burnished Bronze™ Finish
and Vertical Rain Glass



A 49135 BRZ



B 49132 BRZ



C 49130 BRZ
ADA Compliant

Cast Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49135 BRZ	(4) 60W (C)	11.5	37	16	9	W
B	49132 BRZ	(3) 60W (C)	9.5	31	13.5	7	W
C	49130 BRZ	(1) 60W (C)	7	12	4	5.75	W ADA ✓

Measurements shown in inches. U.S. Patent Pending



D 49136 BRZ



E 49134 BRZ



F 49133 BRZ
Shown with Post 9506 BK



G 49131 BRZ

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
D	49136 BRZ	(2) 40W (C)	9.5	6	---	---	---	---	D ❖
E	49134 BRZ	(2) 60W (C)	7.5	25	99	16(72)	---	---	D Additional chain 4927 BRZ
F	49133 BRZ	(3) 60W (C)	9.5	32.5	---	---	16	---	W
G	49131 BRZ	(2) 60W (C)	7.5	25.5	---	---	11	6	W

Measurements shown in inches. U.S. Patent Pending

Venetian Rain™

Black Finish with Gold Highlights
and Vertical Rain Glass



A 49135 BKG



B 49132 BKG



C 49130 BKG
ADA Compliant

Cast Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49135 BKG	(4) 60W (C)	11.5	37	16	9	W
B	49132 BKG	(3) 60W (C)	9.5	31	13.5	7	W
C	49130 BKG	(1) 60W (C)	7	12	4	5.75	W ADA ✓

Measurements shown in inches. U.S. Patent Pending



D 49136 BKG



E 49134 BKG



F 49133 BKG
Shown with Post 9506 BK



G 49131 BKG

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
D	49136 BKG	(2) 40W (C)	9.5	6	---	---	---	---	D ❖
E	49134 BKG	(2) 60W (C)	7.5	25	99	16(72)	---	---	D Additional chain 4927 BKG
F	49133 BKG	(3) 60W (C)	9.5	32.5	---	---	16	---	W
G	49131 BKG	(2) 60W (C)	7.5	25.5	---	---	11	6	W

Measurements shown in inches. U.S. Patent Pending

Tournai™

Londonderry™ Finish and
Clear Seedy Glass



A 9362 LD



B 9855 LD



C 9854 LD

Cast Aluminum
construction





D 9360 LD



E 9564 LD



F 9357 LD

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9362 LD	(5) 100W (M)	25.5	69.5	---	---	37	---	W ⓘ EOD (23-30W CFL) Variable height mounting hardware included, Junction Box 22"-42"
B	9855 LD	(3) 60W (C)	12	25	99	15(72)	---	---	Ⓧ Additional Chain 4927 LD
C	9854 LD	(2) 60W (C)	12	7.5	---	---	---	---	Ⓧ
D	9360 LD	(4) 100W (M)	17	46.5	---	---	25	19.50	W ⓘ EOD (23-30W CFL)
E	9564 LD	(4) 100W (M)	17	33.5	107.5	45(72)	---	---	Ⓧ EOD (23-30W CFL) Additional Chain 4901 LD
F	9357 LD	(2) 60W (C)	10	24	---	---	15	---	W ⓘ Variable height mounting hardware included, Junction Box 6"-17.5"

Measurements shown in inches.

Tournai™

Londonderry™ Finish and
Clear Seedy Glass



A 9359 LD



B 9355 LD



C 9356 LD



D 9358 LD

Cast Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	9359 LD	(4) 60W (C)	14	38	21	---	Ⓜ ⓘ Variable height mounting hardware included, Junction Box 11"-33.25"
B	9355 LD	(1) 100W (M)	6	11	8	4	Ⓜ ⓘ (23-30W CFL)
C	9356 LD	(1) 150W (M)	7.5	18	11.5	---	Ⓜ ⓘ (23-30W CFL) Variable height mounting hardware included, Junction Box 5.75"-11.75"
D	9358 LD	(3) 60W (C)	12	12	18	---	Ⓜ ⓘ Variable height mounting hardware included, Junction Box 6.5"-21.5"

Measurements shown in inches.



E 9559 LD

F 9558 LD

G 9565 LD

	INCAND. ITEM	INCAND. BULB	W	H	NOTES
E	9559 LD	(4) 60W (C)	14	30	W
F	9558 LD	(3) 60W (C)	12	27	W
G	9565 LD	(4) 100W (M)	17	37.5	W 80D (23-30W CFL)

Measurements shown in inches.

Brown Stone Finish and
Umber-Etched Seedy Glass



A 49011 : BST
11049



B 49012 : BST
11043



C 49009 : BST
11041

Cast Aluminum
construction

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB		W	H	EXT.	HCWO	NOTES
A	49011 BST	11049 BST	(1) 150W (M)	(1) 26W (GU24)		11.5	23.5	15.5	11.50	W EOD (23-30W CFL)
B	49012 BST	11043 BST	(1) 150W (M)	(1) 26W (GU24)		11.5	23.5	15.5	9	W EOD (23-30W CFL)
C	49009 BST	11041 BST	(1) 100W (M)	(1) 13W (GU24)		7.5	10.5	7	3.75	W EOD (9-13W CFL)

Measurements shown in inches. U.S. Patent Pending



D 49015 : BST



E 49013 : BST
11050



F 49014 : BST
11051



G 49010 : BST
11042

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
D	49015 BST	---	(2) 60W (C)	---	9.9	6.5	---	---	---	---	Ⓟ ⚡
E	49013 BST	11050 BST	(1) 150W (M)	(1) 26W (GU24)	11.5	21	95	23(72)	---	---	Ⓟ ⚡ (23-30W CFL) Additional chain 4927 BST
F	49014 BST	11051 BST	(1) 150W (M)	(1) 18W (GU24)	11.5	23	---	---	---	---	Ⓟ ⚡ (23-30W CFL)
G	49010 BST	11042 BST	(1) 100W (M)	(1) 18W (GU24)	9	19.5	---	---	13	7.50	Ⓟ ⚡ (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending

Luverne™

Incandescent

Rubbed Bronze™ Finish and
Clear Ribbed Glass



A 49003 RZ



B 49002 RZ



C 49005 RZ



D 49004 RZ



E 49001 RZ

Cast Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	49003 RZ	(1) 150W (M)	11.5	22.5	---	---	13.5	6.50	W EOD (30-52W CFL)
B	49002 RZ	(1) 100W (M)	9.5	18	---	---	11	6.50	W EOD (23-30W CFL)
C	49005 RZ	(1) 150W (M)	11.5	20	94	24(72)	---	---	D EOD (23-30W CFL) Additional chain 4927 RZ
D	49004 RZ	(1) 150W (M)	11.5	21	---	---	---	---	W EOD (23-30W CFL)
E	49001 RZ	(1) 100W (M)	7.5	13.5	---	---	8	4	W EOD (9-13W CFL)

Measurements shown in inches. U.S. Patent Pending

Luverne™

Rubbed Bronze™ Finish and
Satin-Etched Ribbed Glass

Energy Efficient

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.

TRADITIONAL

T



A 11032 RZ



B 11031 RZ


























C 11037 RZ



D 11035 RZ



E 11030 RZ

	FLUOR. ITEM	FLUOR. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	11032 RZ	(1) 26W (GU24)    	11.5	22.5	---	---	13.5	6.50	
B	11031 RZ	(1) 18W (GU24)    	9.5	18	---	---	11	6.50	
C	11037 RZ	(1) 26W (GU24)   	11.5	20	94	24(72)	---	---	D Additional chain 4927 RZ
D	11035 RZ	(1) 18W (GU24)    	11.5	21	---	---	---	---	
E	11030 RZ	(1) 13W (GU24)    	7.5	13.5	---	---	8	4	

Measurements shown in inches. U.S. Patent Pending

Brown Stone Finish and
Umber-Etched Seedy Glass



A 49020
11056 BST














B 49023
11059 BST



C 49019
11055 BST

Cast Aluminum

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	49020 BST	11056 BST	(1) 150W (M)	(1) 26W (GU24)    	11	40	16	---	    30D (30-52W CFL) Variable height mounting hardware incl., Junction Box 15.5"-24"
B	49023 BST	11059 BST	(1) 100W (M)	(1) 18W (GU24)  	8	9.5	---	---	   30D (23-30W CFL)
C	49019 BST	11055 BST	(1) 150W (M)	(1) 26W (GU24)    	11	26.5	15.5	12.25	   30D (30-52W CFL)

Measurements shown in inches. U.S. Patent Pending



F 49022
11057 : BST

















D 49021
11058 : BST



E 49017
11053 : BST



G 49018
11054 : BST

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB		W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
D	49021 BST	11058 BST	(1) 150W (M)	(1) 26W (GU24) 		11	21.5	95.5	11(72)	---	---	 30D (30-52W CFL) Additional chain 4927 BST
E	49017 BST	11053 BST	(1) 100W (M)	(1) 18W (GU24)   		7	15.5	---	---	8	4.50	 30D (23-30W CFL)
F	49022 BST	11057 BST	(1) 150W (M)	(1) 26W (GU24)   		11	31	---	---	---	---	 30D (30-52W CFL)
G	49018 BST	11054 BST	(1) 150W (M)	(1) 18W (GU24)   		9.5	22	---	---	13	11.25	 30D (30-52W CFL)

Measurements shown in inches. U.S. Patent Pending

Duquesne™

Brown Stone Finish and
Umber-Etched Seedy Glass



A 49032 BST



B 49031 BST



C 49030 BST

Cast Aluminum
construction





D 49035 : BST



E 49033 : BST



F 49034 : BST



G 49029 : BST

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	49032 BST	(1) 150W (M)	11.5	20.5	---	---	11	13.50	W OD (30-52W CFL)
B	49031 BST	(1) 150W (M)	9.5	17	---	---	9	9.75	W OD (30-52W CFL)
C	49030 BST	(1) 100W (M)	7.5	12.5	---	---	7	7	W OD (23-30W CFL)
D	49035 BST	(2) 40W (C)	10.5	6.5	---	---	---	---	D
E	49033 BST	(1) 150W (M)	10.5	18	92	24(72)	---	---	D OD (30-52W CFL) Additional chain 4927 BST
F	49034 BST	(1) 150W (M)	10.5	24.5	---	---	---	---	W OD (30-52W CFL)
G	49029 BST	(1) 100W (M)	6	11	---	---	6	6.50	W OD (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending

Warner Park™

Incandescent | Energy Efficient

Rubbed Bronze™ Finish and
Light Golden Seedy Glass



A 49103 RZ
49103 RZ FL



B 49101 RZ
49101 RZ FL



























C 49100 RZ
49100 RZ FL



D 49102 RZ
49102 RZ FL

Cast Aluminum
construction

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB		W	H	EXT.	HCWO	NOTES
A	49103 RZ	49103 RZ FL	(1) 200W (M)	(1) 18W (GU24)   		14	26	16.5	7	   (30-52W CFL)
B	49101 RZ	49101 RZ FL	(1) 100W (M)	(1) 18W (GU24)   		9.5	17	11	4.50	   (23-30W CFL)
C	49100 RZ	49100 RZ FL	(1) 100W (M)	(1) 13W (GU24)   		7	13	8.5	3	   (23-30W CFL)
D	49102 RZ	49102 RZ FL	(1) 150W (M)	(1) 18W (GU24)   		11.5	21.5	13.5	6	   (30-52W CFL)

Measurements shown in inches. U.S. Patent Pending



E 49107 RZ
49107 RZ FL



F 49106 RZ
49106 RZ FL



G 49108 RZ
49108 RZ FL



H 49104 RZ
49104 RZ FL



J 49105 RZ
49105 RZ FL

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB		W	H	OVRL. H	WIRE (CHAIN)	NOTES
E	49107 RZ	49107 RZ FL	(1) 150W (M)	(1) 18W (GU24)		14	28	102	21(72)	(30-52W CFL) Additional chain 4927 RZ
F	49106 RZ	49106 RZ FL	(1) 100W (M)	(1) 18W (GU24)		11.5	23.5	97.5	22(72)	(23-30W CFL) Additional chain 4927 RZ
G	49108 RZ	49108 RZ FL	(1) 100W (M)	(1) 18W (GU24)		9.5	13	---	---	(23-30W CFL)
H	49104 RZ	49104 RZ FL	(1) 100W (M)	(1) 18W (GU24)		11.5	25	---	---	(23-30W CFL)
J	49105 RZ	49105 RZ FL	(1) 150W (M)	(1) 18W (GU24)		14	29	---	---	(30-52W CFL)

Measurements shown in inches. U.S. Patent Pending

Beacon Hill™

Legacy Bronze™ Finish and
Seedy Glass Panels



A 9294 LZ



B 9292 LZ

C 9293 LZ

Cast Aluminum
construction





D 9891 LZ



E 9291 LZ



F 9894 LZ



G 9757 LZ



H 9767 LZ



J 9994 LZ

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9294 LZ	(3) 100W (M)	15	48	---	---	18.5	---	W ① LED (23-30W CFL) Variable height mounting hardware incl., Junction Box 30"-43.75"
B	9292 LZ	(3) 60W (C)	8.5	25.5	---	---	10.5	---	W ① Variable height mounting hardware included, Junction Box 17.25"-21.75"
C	9293 LZ	(3) 60W (C)	11.5	34	---	---	14	---	W ① Variable height mounting hardware included, Junction Box 22"-30"
D	9891 LZ	(3) 40W (C)	14	8	---	---	---	---	D ❖
E	9291 LZ	(1) 100W (M)	6.5	14.5	---	---	7.5	9.25	W LED (23-30W CFL)
F	9894 LZ	(3) 60W (C)	11.5	27	101	13(72)	---	---	D Additional chain 4927 LZ
G	9757 LZ	(3) 60W (C)	11.5	26	---	---	14	---	W ① Variable height mounting hardware included, Junction Box 3.5"-11.75"
H	9767 LZ	(3) 100W (M)	15	38	---	---	18.5	---	W ① LED (23-30W CFL) Variable height mounting hardware incl., Junction Box 4.5"-18"
J	9994 LZ	(3) 60W (C)	11.5	26	---	---	---	---	W

Measurements shown in inches.

Eau Claire™

Olde Bronze® Finish and
Antique Clear Glass

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.



A 9349 OZ



B 9347 OZ



C 9346 OZ



D 9847 OZ



E 9348 OZ



F 9547 OZ

Solid Brass
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9349 OZ	(4) 60W (C)	13	37	---	---	17	18.50	Ⓜ Ⓢ Variable height mounting hardware included, Junction Box 12.75"-24.25"
B	9347 OZ	(1) 150W (M)	9	18.5	---	---	13	10.25	Ⓜ Ⓢ OD (23-30W CFL)
C	9346 OZ	(1) 100W (M)	7	15	---	---	10	8.25	Ⓜ Ⓢ OD (23-30W CFL)
D	9847 OZ	(3) 60W (C)	13	24	98	11(72)	---	---	Ⓢ Additional chain 4927 OZ
E	9348 OZ	(3) 60W (C)	11	32	---	---	15	16.50	Ⓜ Ⓢ Variable height mounting hardware included, Junction Box 12.75"-20"
F	9547 OZ	(3) 60W (C)	11	25	---	---	---	---	Ⓜ

Measurements shown in inches.

Elgin™

Burnished Bronze™ Finish and
Clear Seedy Glass Panels

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.

TRADITIONAL

T



A 9074 BBZ



B 9871 BBZ



D 9072 BBZ



E 9073 BBZ



C 9872 BBZ



F 9572 BBZ

Solid Brass
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9074 BBZ	(3) 60W (C)	11	35	---	---	14	---	Ⓜ Ⓜ Variable height mounting hardware included, Junction Box 12"-23.25"
B	9871 BBZ	(2) 60W (C)	11	9	---	---	---	---	Ⓧ Ⓧ
C	9872 BBZ	(3) 60W (C)	11	21.5	95.5	12(72)	---	---	Ⓧ Additional chain 2996 BBZ
D	9072 BBZ	(1) 100W (M)	7	13.5	---	---	8	5.25	Ⓜ Ⓜ OD (23-30W CFL)
E	9073 BBZ	(2) 60W (C)	8.5	20	---	---	11	11.25	Ⓜ
F	9572 BBZ	(3) 60W (C)	11	23.5	---	---	---	---	Ⓜ

Measurements shown in inches.

Savannah Estates™

Olde Bronze® Finish and
Clear Beveled Glass

See pages 158-158 for our complete selection
of Posts and Pedestal Mount Adaptors.



A 9631 OZ



B 9676 OZ



C 9831 OZ



D 9677 OZ



E 9931 OZ

Solid Brass
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRLL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9631 OZ	(4) 60W (C)	15.5	35	---	---	16	---	Ⓜ Ⓡ Variable height mounting hardware included, Junction Box 18"-25.5"
B	9676 OZ	(2) 60W (C)	9.5	19.5	---	---	9	9	Ⓜ
C	9831 OZ	(4) 60W (C)	15.5	30.5	104.5	6(72)	---	---	Ⓡ Additional chain 4927 OZ
D	9677 OZ	(3) 60W (C)	12	25	---	---	12	12.25	Ⓜ
E	9931 OZ	(3) 60W (C)	12	25	---	---	---	---	Ⓜ

Measurements shown in inches.

Sausalito™

Olde Bronze® Finish and
Clear Ribbed Optic Glass

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.

TRADITIONAL

T



A 9492 OZ



B 9452 OZ



C 9832 OZ



D 9412 OZ



E 9932 OZ

Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9492 OZ	(3) 60W (C)	11.5	28	---	---	13.5	10.50	W
B	9452 OZ	(3) 60W (C)	9.5	24	---	---	12	9.50	W
C	9832 OZ	(3) 60W (C)	11.5	23	97	15(72)	---	---	D Additional chain 4927 OZ
D	9412 OZ	(1) 100W (M)	7	19.5	---	---	9	7.50	W E30D (23-30W CFL)
E	9932 OZ	(3) 60W (C)	11.5	24.5	---	---	---	---	W

Measurements shown in inches.

LifeBrite™

LifeBrite™ Polished Brass Finish and Clear Beveled Glass Panels

See pages 158-159 for our complete selection of Posts and Pedestal Mount Adaptors.



A 9489 PB



B 9439 PB



C 9889 PB



D 9409 PB



E 9989 PB

Solid Brass with
LifeBrite™
By KICHLER®

Kichler's LifeBrite™ Finish has a lifetime finish guarantee to withstand the harshest elements, salt air and extreme weather conditions.

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9489 PB	(3) 60W (C)	10	24	---	---	11.5	11.75	W
B	9439 PB	(2) 60W (C)	8	20	---	---	10	10	W
C	9889 PB	(3) 60W (C)	10	21.5	95.5	16(72)	---	---	D Additional chain 2979 PB
D	9409 PB	(1) 100W (M)	6.5	12.5	---	---	7.5	3.25	W EOD (23-30W CFL)
E	9989 PB	(3) 60W (C)	10	25.5	---	---	---	---	W

Measurements shown in inches.

Rockbridge™

LifeBrite™ Polished Brass Finish
and Clear Seedy Glass

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.

TRADITIONAL

T



A 9038 PB



B 9037 PB



C 9537 PB



D 9596 PB



E 9996 PB



F 9036 PB

Solid Brass with
LifeBrite™
By KICHLER

Kichler's LifeBrite™ Finish has a lifetime finish
guarantee to withstand the harshest elements,
salt air and extreme weather conditions.

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9038 PB	(3) 60W (C)	10.5	21.5	---	---	13	13	W
B	9037 PB	(1) 100W (M)	8.5	17.5	---	---	10.5	10.50	W OD (23-30W CFL)
C	9537 PB	(3) 60W (C)	10.5	22.5	96.5	15(72)	---	---	D Additional chain 2979 PB
D	9596 PB	(3) 40W (C)	14	6.5	---	---	---	---	D
E	9996 PB	(3) 60W (C)	10.5	25	---	---	---	---	W
F	9036 PB	(1) 100W (M)	7.5	14.5	---	---	9	8.50	W OD (23-30W CFL)

Measurements shown in inches.

Bay Shore™

Incandescent

See pages 158-159 for our complete selection of Posts and Pedestal Mount Adaptors.

LifeBrite™ Polished Brass Finish and Clear Beveled Glass Panels



A 9713 ··· PB



B 9711 ··· PB



C 9513 ··· PB



D 9712 ··· PB



E 9913 ··· PB

Solid Brass with
LifeBrite™
By KICHLER®

Kichler's LifeBrite™ Finish has a lifetime finish guarantee to withstand the harshest elements, salt air and extreme weather conditions.

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9713 PB	(1) 100W (M)	9.5	20	---	---	11	15.50	W EOD (23-30W CFL)
B	9711 PB	(1) 100W (M)	6	10.5	---	---	7	4	W EOD (23-30W CFL)
C	9513 PB	(1) 100W (M)	9.5	20	94	25(72)	---	---	D EOD (23-30W CFL) Additional chain 2979 PB
D	9712 PB	(1) 100W (M)	7	15.5	---	---	8	12	W EOD (23-30W CFL)
E	9913 PB	(1) 100W (M)	9.5	22.5	---	---	---	---	W EOD (23-30W CFL)

Measurements shown in inches.

Randolph™

Prairie Rock™ Finish and
Umber-Etched Seedy Glass

Energy Efficient

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.

TRADITIONAL

T



A 10904 PR



B 10905 PR

















C 10906 PR



D 10903 PR

Cast Aluminum
construction

	FLUOR. ITEM	FLUOR. BULB		W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	10904 PR	(1) 18W (GU24)   		7.5	16	---	---	9.5	5.50	
B	10905 PR	(1) 18W (GU24)  		7.5	14.5	88.5	26(72)	---	---	D Additional chain 4927 PR
C	10906 PR	(1) 18W (GU24)   		7.5	20	---	---	---	---	
D	10903 PR	(1) 13W (GU24)   		6	13.5	---	---	7.5	5.25	

Measurements shown in inches.

Courtyard™

Incandescent | Energy Efficient

Rubbed Bronze Finish and Clear Seedy Glass (Incandescent) or Etched Seedy Glass (Fluorescent)



A 9034 : RZ
11012



B 9033 : RZ
11011



C 9035 : RZ
11013

Cast Aluminum
construction





D 9538 RZ



E 9539 11016 RZ




























F 9032 11010 RZ



G 9533 11015 RZ



H 9532 11014 RZ

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9034 RZ	11012 RZ	(3) 60W (C)	(1) 18W (GU24)   	10.5	22.5	---	---	13.5	9	
B	9033 RZ	11011 RZ	(1) 150W (M)	(1) 18W (GU24)   	8.5	18	---	---	11	8	  (23-30W CFL)
C	9035 RZ	11013 RZ	(3) 60W (C)	(1) 26W (GU24)   	12.5	26.5	---	---	16.5	12.75	
D	9538 RZ	---	(3) 40W (C)	---	12.5	6.5	---	---	---	---	 
E	9539 RZ	11016 RZ	(3) 60W (C)	(1) 26W (GU24)  	12.5	21.5	95.5	20(72)	---	---	 Additional chain 4927 RZ
F	9032 RZ	11010 RZ	(1) 100W (M)	(1) 13W (GU24)   	6.5	11	---	---	7.5	3.75	  (23-30W CFL)
G	9533 RZ	11015 RZ	(3) 60W (C)	(1) 26W (GU24)   	12.5	27.5	---	---	---	---	
H	9532 RZ	11014 RZ	(1) 200W (M)	(1) 18W (GU24)   	10.5	24	---	---	---	---	  (23-30W CFL)

Measurements shown in inches. Incandescent comes in Clear Seedy Glass and Florescent comes in Etched-Seedy Glass.

Amesbury™

Tannery Bronze® Finish with
Gold Accents and
Clear Beveled Glass

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.



A 9065 : TZG



B 9064 : TZG



C 9826 : TZG



D 9061 : TZG



E 9806 : TZG



F 9062 : TZG



G 9562 : TZG

Cast Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9065 TZG	(1) 150W (M)	9	27	---	---	11	13.50	W EOD (23-30W CFL)
B	9064 TZG	(1) 100W (M)	6	10	---	---	7	3.25	W EOD (23-30W CFL)
C	9826 TZG	(1) 150W (M)	9	19	93	25(72)	---	---	D EOD (23-30W CFL) Additional chain 4927 TZG
D	9061 TZG	(1) 100W (M)	7	14.5	---	---	8	4	W EOD (23-30W CFL)
E	9806 TZG	(1) 100W (M)	6	9.5	---	---	---	---	D EOD (23-30W CFL)
F	9062 TZG	(1) 100W (M)	9	18.5	---	---	10	5	W EOD (23-30W CFL)
G	9562 TZG	(1) 150W (M)	9	20.5	---	---	---	---	W EOD (23-30W CFL)

Measurements shown in inches.

Warrington™

Cambridge Finish and
Clear Seedy Glass

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.

TRADITIONAL

T



A 9372 CMB



B 9370 CMB



C 9371 CMB



D 9881 CMB



E 9368 CMB



F 9898 CMB



G 9369 CMB

Cast Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9372 CMB	(3) 60W (C)	11.5	24	---	---	12.5	17	W
B	9370 CMB	(1) 150W (M)	9.5	19.5	---	---	10.5	14	W 30D (23-30W CFL)
C	9371 CMB	(3) 60W (C)	11.5	19.5	93.5	14(72)	---	---	D Additional chain 4927 CMB
D	9881 CMB	(2) 40W (C)	12	7.5	---	---	---	---	D ✦
E	9368 CMB	(1) 100W (M)	7.5	13	---	---	8	3.25	W 30D (23-30W CFL)
F	9898 CMB	(3) 60W (C)	11.5	25.5	---	---	---	---	W
G	9369 CMB	(1) 150W (M)	9.5	16.5	---	---	10.5	5.75	W 30D (23-30W CFL)

Measurements shown in inches.

Mount Vernon

Olde Bronze® Finish and Etched Seedy Glass

See pages 158-159 for our complete selection of Posts and Pedestal Mount Adaptors.



A 9703 OZ



B 9809 OZ



C 9804 OZ



D 9708 OZ



E 9704 OZ



F 9707 OZ



G 9709 OZ



H 9909 OZ

Solid Brass
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9703 OZ	(6) 60W (C)	16	32.5	---	---	17	12.25	W
B	9809 OZ	(1) 150W (M)	8.5	18	92.5	23(72)	---	---	D EOD (23-30W CFL) Additional chain 4927 OZ
C	9804 OZ	(4) 60W (C)	13	26	100	7(72)	---	---	D Additional chain 4927 OZ
D	9708 OZ	(1) 150W (M)	7.5	17	---	---	8.5	7	W EOD (23-30W CFL)
E	9704 OZ	(4) 60W (C)	13	28	---	---	14	11.25	W
F	9707 OZ	(1) 100W (M)	5.5	12.5	---	---	6.5	5.25	W EOD (23-30W CFL)
G	9709 OZ	(1) 150W (M)	9.5	19.5	---	---	10.5	7.25	W EOD (23-30W CFL)
H	9909 OZ	(1) 150W (M)	9.5	20.5	---	---	---	---	W EOD (23-30W CFL)

Measurements shown in inches. Complete selection of Dark Sky adapter panels for: D, F on pages 156-157

Mount Vernon

Olde Brick® Finish and Seedy Glass Panels

See pages 158-159 for our complete selection of Posts and Pedestal Mount Adaptors.

TRADITIONAL

T



A 9703 OB



B 9809 OB



C 9804 OB



D 9708 OB



E 9704 OB



F 9707 OB



G 9709 OB



H 9909 OB

Solid Brass
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9703 OB	(6) 60W (C)	16	32.5	---	---	17	12.25	W
B	9809 OB	(1) 150W (M)	8.5	18	92	23(72)	---	---	D 3OD (23-30W CFL) Additional chain 4927 OB
C	9804 OB	(4) 60W (C)	13	26	100	7(72)	---	---	D Additional chain 4927 OB
D	9708 OB	(1) 150W (M)	7.5	17	---	---	8.5	7	W 3OD (23-30W CFL)
E	9704 OB	(4) 60W (C)	13	28	---	---	14	11.25	W
F	9707 OB	(1) 100W (M)	5.5	12.5	---	---	6.5	5.25	W 3OD (23-30W CFL)
G	9709 OB	(1) 150W (M)	9.5	19.5	---	---	10.5	7.25	W 3OD (23-30W CFL)
H	9909 OB	(1) 150W (M)	9.5	20.5	---	---	---	---	W 3OD (23-30W CFL)

Measurements shown in inches.

Mount Vernon

Olde Bronze® Finish and Etched Seedy Glass

Energy Efficient

See pages 158-159 for our complete selection of Posts and Pedestal Mount Adaptors.



A 10909 OZ



B 10907 OZ



C 10910 OZ






















D 10908 OZ



E 10911 OZ

Solid Brass
construction

	FLUOR. ITEM	FLUOR. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	10909 OZ	(1) 18W (GU24)   	9.5	19.5	---	---	10.5	7.25	 W
B	10907 OZ	(1) 13W (GU24)   	5.5	12.5	---	---	6.5	5.50	 W
C	10910 OZ	(1) 18W (GU24)  	9.5	18.5	92.5	23(72)	---	---	 D Additional chain 4927 OZ
D	10908 OZ	(1) 13W (GU24)   	7.5	17	---	---	8.5	7	 W
E	10911 OZ	(1) 18W (GU24)   	9.5	21.5	---	---	---	---	 W

Measurements shown in inches. Complete selection of Dark Sky adapter panels for: B, D on pages 156-157

Lafayette™

Tannery Bronze® Finish
with Gold Accents and
Clear Seedy Glass

Incandescent

Coordinating Landscape Lighting

See the complete line of
Kichler® Landscape Lighting at
LandscapeLighting.com



TRADITIONAL

T



A 9186 · TZG



B 9519 · TZG



C 9183 · TZG



D 9895 · TZG



F 9185 · TZG



G 9585 · TZG



E 9184 · TZG

Cast Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9186 TZG	(3) 60W (C)	13	23.5	---	---	14	7	W
B	9519 TZG	(3) 60W (C)	11	19.5	93.5	17(72)	---	---	D Additional chain 4927 TZG
C	9183 TZG	(1) 100W (M)	7	13	---	---	7.5	4.25	W EOD (23-30W CFL)
D	9895 TZG	(1) 100W (M)	7	11.5	---	---	---	---	D EOD (23-30W CFL)
E	9184 TZG	(2) 60W (C)	9	16	---	---	9	4.75	W
F	9185 TZG	(3) 60W (C)	11	20	---	---	12	6.25	W
G	9585 TZG	(3) 60W (C)	11	21.5	---	---	---	---	W

Measurements shown in inches. U.S. Patent Pending

Cadiz™

Distressed Black Finish
and Clear Seedy Glass

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.



A 9020 DBK



B 9018 DBK



D 9017 DBK



C 9808 DBK



E 9919 DBK



F 9019 DBK

Aluminum &
Solid Brass
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9020 DBK	(3) 60W (C)	13	42.5	---	---	16.5	---	Ⓜ ⓘ Variable height mounting hardware included, Junction Box 15.75"-26.5"
B	9018 DBK	(2) 60W (C)	9	24.5	---	---	11.5	13.25	Ⓜ
C	9808 DBK	(3) 60W (C)	11	24.5	98.5	12(72)	---	---	Ⓧ ⓘ Additional chain 4927 DBK
D	9017 DBK	(1) 100W (M)	7	12	---	---	7	7.75	Ⓜ ⓘ E30D (23-30W CFL)
E	9919 DBK	(3) 60W (C)	11	26	---	---	---	---	Ⓜ
F	9019 DBK	(3) 60W (C)	11	36.5	---	---	14	---	Ⓜ ⓘ Variable height mounting hardware included, Junction Box 14.75"-22"

Measurements shown in inches.

Trenton™

Black Finish and
Clear Beveled Glass

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.

TRADITIONAL

T



A 9252 BK



B 9251 BK



C 9851 BK



D 9250 BK



E 9951 BK



F 9949 BK

Cast Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9252 BK	(3) 60W (C)	13	33.5	---	---	15	27.75	W
B	9251 BK	(3) 60W (C)	9.5	23	---	---	11	17.50	W
C	9851 BK	(3) 60W (C)	8.5	16	90	18(72)	---	---	D Additional chain 4927 BK
D	9250 BK	(1) 100W (M)	8	14	---	---	9	3.25	W EOD (23-30W CFL)
E	9951 BK	(3) 60W (C)	13	29.5	---	---	---	---	W
F	9949 BK	(3) 60W (C)	9.5	23	---	---	---	---	W

Measurements shown in inches.

Embassy Row

Antique Pewter Finish over
Solid Brass and Clear Glass Panels



A 9785 AP



B 9784 AP



C 9783 AP



D 9985 AP

Solid Brass
construction

60

	INCAND. ITEM	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	9785 AP	(3) 60W (C)	11	21	9.5	8.50	W
B	9784 AP	(1) 100W (M)	8.5	15	8	5.50	W E0D (23-30W CFL)
C	9783 AP	(1) 100W (M)	7	11	7	4.25	W E0D (23-30W CFL)
D	9985 AP	(3) 60W (C)	11	21	---	---	W

Measurements shown in inches.

Embassy Row

Olde Bronze® Finish over
Solid Brass and Clear Glass Panels

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.

TRADITIONAL

T



A 9785 OZ



B 9784 OZ



C 9885 OZ



F 9786 OZ



D 9985 OZ



E 9783 OZ

Solid Brass
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9785 OZ	(3) 60W (C)	11	21	---	---	9.5	8.50	W
B	9784 OZ	(1) 100W (M)	8.5	15	---	---	8	5.50	W EOD (23-30W CFL)
C	9885 OZ	(3) 60W (C)	11	19.5	93.5	14(72)	---	---	D Additional chain 4927 OZ
D	9985 OZ	(3) 60W (C)	11	21	---	---	---	---	W
E	9783 OZ	(1) 100W (M)	7	11	---	---	7	4.25	W EOD (23-30W CFL)
F	9786 OZ	(3) 60W (C)	12.5	24.5	---	---	12	9.75	W

Measurements shown in inches.

Rubbed Bronze Finish and
White Linen Glass



A 9043 11005 RZ




B 9041 RZ



C 9042 11004 RZ

Cast Aluminum
construction

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	9043 RZ	11005 RZ	(1) 200W (M)	(1) 26W (GU24)    	12.5	29.5	16.5	14.50	    (23-30W CFL)
B	9041 RZ	---	(1) 100W (M)	---	8	19.5	11	9.50	    (23-30W CFL)
C	9042 RZ	11004 RZ	(1) 150W (M)	(1) 18W (GU24)    	10	24.5	13.5	12.25	    (23-30W CFL)

Measurements shown in inches.



D 9039 RZ
11001 RZ



E 9843 RZ
11006 RZ



F 9848 RZ































G 9040 RZ
11002 RZ



H 9938 RZ
11008 RZ



J 9940 RZ
11009 RZ

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
D	9039 RZ	11001 RZ	(1) 60W (M)	(1) 13W (GU24)    	6	10.5	---	---	7.5	3.50	  0D (13-15W CFL)
E	9843 RZ	11006 RZ	(1) 200W (M)	(1) 26W (GU24) 	12.5	25	99	22(72)	---	---	  0D (23-30W CFL) Additional chain 4927 RZ
F	9848 RZ	---	(2) 60W (M)	---	13.5	7.5	---	---	---	---	  0D (13-15W CFL)
G	9040 RZ	11002 RZ	(1) 100W (M)	(1) 18W (GU24)    	8	19.5	---	---	11	7	  0D (23-30W CFL)
H	9938 RZ	11008 RZ	(1) 150W (M)	(1) 18W (GU24)    	10	22	---	---	---	---	  0D (23-30W CFL)
J	9940 RZ	11009 RZ	(1) 200W (M)	(1) 26W (GU24)    	12.5	26	---	---	---	---	  0D (23-30W CFL)

Measurements shown in inches.

Salisbury™

Black Finish and
White Linen Glass



A 9043 BK



B 9041 BK



C 9040 BK

Cast Aluminum
100% Recycled

	INCAND. ITEM	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	9043 BK	(1) 200W (M)	12.5	29.5	16.5	14.50	W EOD (23-30W CFL)
B	9041 BK	(1) 100W (M)	8	19.5	11	9.50	W EOD (23-30W CFL)
C	9040 BK	(1) 100W (M)	8	19.5	11	7	W EOD (23-30W CFL)

Measurements shown in inches.



D 9039 BK



E 9843 BK



F 9848 BK



G 9042 BK



H 9938 BK



J 9940 BK

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
D	9039 BK	(1) 60W (M)	6	10.5	---	---	7.5	3.50	W EOD (13-15W CFL)
E	9843 BK	(1) 200W (M)	12.5	25	99	22(72)	---	---	D EOD (23-30W CFL) Additional chain 4927 BK
F	9848 BK	(2) 60W (M)	13.5	7.5	---	---	---	---	D EOD (13-15W CFL)
G	9042 BK	(1) 150W (M)	10	24.5	---	---	13.5	12.25	W EOD (23-30W CFL)
H	9938 BK	(1) 150W (M)	10	22	---	---	---	---	W EOD (23-30W CFL)
J	9940 BK	(1) 200W (M)	12.5	26	---	---	---	---	W EOD (23-30W CFL)

Measurements shown in inches.

Townhouse™

Black or Tannery Bronze® Finish
and Clear Beveled Glass Panels



A 49185 BK, TZ



B 9790 BK, TZ



C 9791 BK, TZ



D 9789 BK, TZ

Cast Aluminum
construction

	INCAND. ITEM	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49185	BK, TZ	(3) 60W (C)	12.5	31.5	12.5	23.50	W
B	9790	BK, TZ	(1) 100W (M)	7.5	21.5	10	16.75	W EOD (23-30W CFL)
C	9791	BK, TZ	(1) 100W (M)	9.5	27	10.5	21	W EOD (23-30W CFL)
D	9789	BK, TZ	(1) 100W (M)	7	15.5	9.5	4.50	W EOD (23-30W CFL)

Measurements shown in inches.



E 9892 BK, TZ



F 9886 BK, TZ



G 9788 BK, TZ



H 9992 BK, TZ



J 49188 BK, TZ

INCAND. ITEM	FINISH	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
E	9892 BK, TZ	(1) 100W (M)	9.5	24.5	98.5	23(72)	---	---	D W OD (23-30W CFL) Additional chain 4927 BK, TZ
F	9886 BK, TZ	(2) 40W (C)	12	7.5	---	---	---	---	D W
G	9788 BK, TZ	(1) 100W (M)	6.5	12	---	---	6.5	3	W OD (23-30W CFL)
H	9992 BK, TZ	(1) 100W (M)	9.5	24.5	---	---	---	---	W OD (23-30W CFL)
J	49188 BK, TZ	(3) 60W (C)	12.5	28.5	---	---	---	---	W

Measurements shown in inches.

Kirkwood™

Tannery Bronze® Finish
and Seedy Glass



A 9030 TZ



B 9859 TZ



C 9810 TZ



D 9028 TZ



E 9029 TZ



F 9918 TZ

Cast Aluminum
Construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9030 TZ	(3) 60W (C)	10	21	---	---	11.5	13	W
B	9859 TZ	(1) 100W (M)	7.5	7.5	---	---	---	---	D ✓ EOD (9-13W CFL)
C	9810 TZ	(1) 150W (M)	10	18	92	22(72)	---	---	D EOD (23-30W CFL) Additional chain 4927 TZ
D	9028 TZ	(1) 100W (M)	6.5	13	---	---	7.5	8	W EOD (23-30W CFL)
E	9029 TZ	(1) 150W (M)	8.5	17	---	---	9.5	10.25	W EOD (23-30W CFL)
F	9918 TZ	(3) 60W (C)	10	23.5	---	---	---	---	W

Measurements shown in inches.

Kirkwood™

Black Finish
and Seedy Glass

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.

TRADITIONAL

T



A 9030 BK



B 9859 BK



C 9810 BK



D 9028 BK



E 9029 BK



F 9918 BK

Cast Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9030 BK	(3) 60W (C)	10	21	---	---	11.5	13	W
B	9859 BK	(1) 100W (M)	7.5	7.5	---	---	---	---	D ✓ EOD (9-13W CFL)
C	9810 BK	(1) 150W (M)	10	18	92	22(72)	---	---	D EOD (23-30W CFL) Additional chain 4927 BK
D	9028 BK	(1) 100W (M)	6.5	13	---	---	7.5	8	W EOD (23-30W CFL)
E	9029 BK	(1) 150W (M)	8.5	17	---	---	9.5	10.25	W EOD (23-30W CFL)
F	9918 BK	(3) 60W (C)	10	23.5	---	---	---	---	W

Measurements shown in inches.

Madison

Energy Efficient

Tannery Bronze® Finish
and Light Linen Glass



A 10955 TZ



B 10950 TZ



C 10954 TZ






















D 10953 TZ



E 10956 TZ

Cast Aluminum
construction

	FLUOR. ITEM	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	10955 TZ	(1) 18W (GU24)   	9.5	23.5	10.5	17.75	
B	10950 TZ	(1) 13W (GU24)   	8	15	9	4.50	
C	10954 TZ	(1) 18W (GU24)   	9.5	17	10.5	6.50	
D	10953 TZ	(1) 13W (GU24)   	8	20	9	15.50	
E	10956 TZ	(1) 18W (GU24)   	8.5	23	---	---	

Measurements shown in inches.

Madison

Black, Tannery Bronze® or White Finish and Clear Beveled Glass

Incandescent

See pages 158-159 for our complete selection of Posts and Pedestal Mount Adaptors.

TRADITIONAL

T



A 9650 BK, TZ, WH



B 9653 BK, TZ, WH



C 9805 BK, TZ, WH



D 9654 BK, TZ, WH



E 9655 BK, TZ, WH



F 9850 BK, TZ, WH



G 9956 BK, TZ, WH

INCAND. ITEM	FINISH	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9650	BK, TZ, WH	(1) 100W (M)	8	13	---	---	9 3	W EOD (23-30W CFL)
B	9653	BK, TZ, WH	(1) 100W (M)	8	19.5	---	---	8.5 15.50	W EOD (23-30W CFL)
C	9805	BK, TZ, WH	(1) 100W (M)	9.5	13.5	87.5	65(72)	---	D EOD (23-30W CFL) Additional chain 4927 BK, TZ
D	9654	BK, TZ, WH	(1) 100W (M)	9.5	22	---	---	10.5 16	W EOD (23-30W CFL)
E	9655	BK, TZ, WH	(1) 100W (M)	9.5	15.5	---	---	10.5 6	W EOD (23-30W CFL)
F	9850	BK, TZ, WH	(2) 60W (C)	9.5	7.5	---	---	---	D ♦
G	9956	BK, TZ, WH	(1) 100W (M)	9.5	22	---	---	---	W EOD (23-30W CFL)

Measurements shown in inches.

BK Black

TZ Tannery Bronze®

WH White

KICHLER.COM



Lighting Tip

Planning

Outdoor lighting should illuminate your house without shining into your neighbors' homes. Plan the angles and placement of your exterior lights with consideration for others – and the environment.







Classic style merges with fresh ideas
to create Kichler® Transitional Lighting.



T R A N S I T I O N A L

The minimalist approach limits
ornamentation to keep the focus on
pure simplicity and sophistication.

Symbol Guide

 D	DAMP	 T24	Title 24 Compliant
 W	WET		Lamp Included
	Dark Sky		Photocell Included
	ADA Compliant		Installation Requirements
	Hybrid		90° C. Wire Rated
	Hybrid Outdoor		75° C. Wire Rated
	Energy Star		

Astoria™

Incandescent | Energy Efficient

Olde Bronze® Finish and
Textured Linen Seedy Glass



A 9470 OZ









B 9468
10968 OZ



C 9469
10969 OZ

Solid Brass
construction

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	9470 OZ	---	(1) 150W (M)	---	9	17	10	11.25	W EOD (23-30W CFL)
B	9468 OZ	10968 OZ	(1) 100W (M)	(1) 13W (GU24)   	6	9.5	7	6.75	W EOD (23-30W CFL)
C	9469 OZ	10969 OZ	(1) 100W (M)	(1) 18W (GU24)   	7.5	14	8	9.50	W EOD (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending: B, C (Fluor. Item Only) Complete selection of Dark Sky adapter panels for: A, B, C on pages 156-157



D 9873 OZ



E 9868
10965 OZ



F 9569
10967 OZ

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	OVRL. H	WIRE (CHAIN)	NOTES
D	9873 OZ	---	(2) 100W (M)	---	11.5	7	---	---	D ❖ OD (23-30W CFL)
E	9868 OZ	10965 OZ	(1) 150W (M)	(1) 18W (GU24) TD !	9	17.5	91.5	25(72)	D OD (23-30W CFL) Additional chain 4927 OZ
F	9569 OZ	10967 OZ	(1) 150W (M)	(1) 18W (GU24) TD ! ! !	9	18	---	---	W OD (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending: F (Fluor. Item Only) Complete selection of Dark Sky adapter panels for E on pages 156-157

Mackenzie™

Architectural Bronze® Finish
and Light Umber-Etched Glass



A 49039 AZ



B 49037 AZ



C 49038 AZ

Cast Aluminum
construction





D 49041 AZ



E 49040 AZ



F 49042 AZ

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	49039 AZ	(1) 150W (M)	9	18.5	---	---	9.5	10	W OD (23-30W CFL)
B	49037 AZ	(1) 60W (C/K)	5	9	---	---	5.5	4.50	W
C	49038 AZ	(1) 100W (M)	7	12.5	---	---	7.5	7.25	W OD (23-30W CFL) T type 60W lamp recommended
D	49041 AZ	(1) 100W (M)	11.5	6.5	---	---	---	---	D OD (23-30W CFL)
E	49040 AZ	(1) 150W (M)	9	19.5	93.5	25(72)	---	---	D OD (23-30W CFL) Additional chain 4927 AZ
F	49042 AZ	(1) 150W (M)	9	21.5	---	---	---	---	W OD (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending

Fallon™

Aged Bronze Finish and
Light Umber-Etched Glass

Incandescent

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.



A 9124 AGZ



B 9525 AGZ



C 9126 AGZ



D 9925 AGZ

Cast Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9124 AGZ	(1) 150W (M)	8	14.5	---	---	9.5	5	W
B	9525 AGZ	(1) 150W (M)	10	18.5	92.5	25(72)	---	---	D 30D (23-30W CFL) Additional chain 4901 AGZ
C	9126 AGZ	(1) 150W (M)	10	18	---	---	12	6	W 30D (23-30W CFL)
D	9925 AGZ	(1) 100W (M)	10	22.5	---	---	---	---	W 30D (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending

Atwood

Brown Stone Finish and
Light Umber Mist Glass

Incandescent | Energy Efficient

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.

TRANSITIONAL

T



A 49073 BST
49073 BST FL



B 49071 BST
49071 BST FL



C 49075 BST
49075 BST FL



























D 49072 BST
49072 BST FL



E 49074 BST
49074 BST FL

Cast Aluminum
construction

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	49073 BST	49073 BST FL	(1) 150W (M)	(1) 18W (GU24)   	10	18	---	---	11	3.25	  (30-52W CFL)
B	49071 BST	49071 BST FL	(1) 100W (M)	(1) 13W (GU24)   	6	11.5	---	---	7	2.50	  (23-30W CFL)
C	49075 BST	49075 BST FL	(1) 100W (M)	(1) 18W (GU24)  	10	18	92	24(72)	---	---	  (23-30W CFL) Additional chain 4927 BST
D	49072 BST	49072 BST FL	(1) 100W (M)	(1) 18W (GU24)   	8	14.5	---	---	9	3	  (23-30W CFL)
E	49074 BST	49074 BST FL	(1) 150W (M)	(1) 18W (GU24)   	10	22.5	---	---	---	---	  (30-52W CFL)

Measurements shown in inches.

Lantana™

Architectural Bronze® Finish
and Light Umber Glass

Incandescent | Energy Efficient



B 7002 AZ



C 9567
11066 AZ



A 9168
11069 AZ



D 9166
11067 AZ

































E 9167
11068 AZ



F 9967
11070 AZ

Cast Aluminum
construction

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	OVRLL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9168 AZ	11069 AZ	(1) 150W (M)	(1) 18W (GU24)    	10.5	15	---	---	9	4	  OD (23-30W CFL)
B	7002 AZ	---	(1) 75W (M)	---	9	5.5	---	---	---	---	  OD (18-25W CFL)
C	9567 AZ	11066 AZ	(1) 150W (M)	(1) 18W (GU24)  	11	17.5	91.5	25(72)	---	---	  OD (23-30W CFL) Additional chain 4927 AZ
D	9166 AZ	11067 AZ	(1) 75W (M)	(1) 13W (GU24)    	7	10	---	---	6	3.25	  OD (18-25W CFL)
E	9167 AZ	11068 AZ	(1) 100W (M)	(1) 13W (GU24)    	9	13	---	---	7.5	4	  OD (23-30W CFL)
F	9967 AZ	11070 AZ	(1) 150W (M)	(1) 18W (GU24)    	10.5	19.5	---	---	---	---	  OD (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending

Lantana™

Granite Finish and Etched Opal Glass

Incandescent | Energy Efficient

See pages 158-159 for our complete selection of Posts and Pedestal Mount Adaptors.

TRANSITIONAL

T



A 9168
11069 GNT



B 7002 GNT



D 9166
11067 GNT





























C 9567
11066 GNT



E 9167
11068 GNT



F 9967
11070 GNT

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB		W	H	OVRLL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9168 GNT	11069 GNT	(1) 150W (M)	(1) 18W (GU24)   		10.5	15	---	---	9	4	  OD (23-30W CFL)
B	7002 GNT	---	(1) 75W (M)	---		9	5.5	---	---	---	---	  OD (18-25W CFL)
C	9567 GNT	11066 GNT	(1) 150W (M)	(1) 18W (GU24)  		11	17.5	91.5	25(72)	---	---	  OD (23-30W CFL) Additional chain 4927 GNT
D	9166 GNT	11067 GNT	(1) 75W (M)	(1) 13W (GU24)   		7	10	---	---	6	3.25	  OD (18-25W CFL)
E	9167 GNT	11068 GNT	(1) 100W (M)	(1) 13W (GU24)   		9	13	---	---	7.5	4	  OD (23-30W CFL)
F	9967 GNT	11070 GNT	(1) 150W (M)	(1) 18W (GU24)   		10.5	19.5	---	---	---	---	  OD (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending

Cameron™

Incandescent | Energy Efficient

Prairie Rock™ Finish and
White-Etched Linen Glass



A 9720 : PR
11019



B 9721 : PR




C 9718 : PR
11017



D 9719 : PR
11018

Cast Aluminum
construction

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	9720 PR	11019 PR	(1) 200W (M)	(1) 18W (GU24)    	10	18	11.5	4.50	  (26-30W CFL)
B	9721 PR	---	(1) 200W (M)	---	12	21	13.5	4.50	  (26-30W CFL)
C	9718 PR	11017 PR	(1) 60W (M)	(1) 13W (GU24)    	6	11	7	3	  (26-30W CFL)
D	9719 PR	11018 PR	(1) 150W (M)	(1) 18W (GU24)    	8	14.5	9.5	3.75	  (26-30W CFL)

Measurements shown in inches.



E 9511 PR
11021 PR



F 9811 PR



G 9902 PR
11020 PR



H 9911 PR

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	OVRL. H	WIRE (CHAIN)	NOTES
E	9511 PR	11021 PR	(1) 200W (M)	(1) 18W (GU24)	10	18	92	24(72)	OD (23-30W CFL) Additional chain 4927 PR
F	9811 PR	---	(3) 40W (C)	---	13	7	---	---	
G	9902 PR	11020 PR	(1) 150W (M)	(1) 18W (GU24)	10	20	---	---	OD (23-30W CFL)
H	9911 PR	---	(1) 100W (M)	---	8	17	---	---	OD (23-30W CFL)

Measurements shown in inches.

Anvil Iron Finish and
Satin-Etched Cased
Opal Glass




A 49217 AVI
49217 AVI FL



B 49215 AVI
49215 AVI FL



C 49214 AVI
49214 AVI FL





D 49219 AVI
49219 AVI FL































E 49220 AVI
49220 AVI FL



F 49216 AVI
49216 AVI FL



G 49218 AVI
49218 AVI FL

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	49217 AVI	49217 AVI FL	(1) 150W (M)	(1) 18W (GU24)  	11.5	16	---	---	11.5	7.50	  OD (23-30W CFL)
B	49215 AVI	49215 AVI FL	(1) 100W (M)	(1) 18W (GU24)  	7	10	---	---	7	5	  OD (23-30W CFL)
C	49214 AVI	49214 AVI FL	(1) 75W (M)	(1) 13W (GU24)  	6	9	---	---	5	4.75	  OD (18-25W CFL)
D	49219 AVI	49219 AVI FL	(1) 150W (M)	(1) 18W (GU24)  	11.5	17.5	91.5	24(72)	---	---	  OD (30-52W CFL) Additional chain 4927 AVI
E	49220 AVI	49220 AVI FL	(2) 60W (M)	(2) 18W (GU24)  	11	7	---	---	---	---	  OD (13-15W CFL)
F	49216 AVI	49216 AVI FL	(1) 100W (M)	(1) 18W (GU24)  	9	13	---	---	9.5	6.25	  OD (23-30W CFL)
G	49218 AVI	49218 AVI FL	(1) 150W (M)	(1) 18W (GU24)  	11.5	20	---	---	---	---	  OD (30-52W CFL)

Measurements shown in inches. U.S. Patent Pending

Portman Square™

Olde Bronze® Finish and
Etched Seedy Glass



A 49160 OZ



B 49157 OZ



C 49158 OZ



D 49159 OZ

Solid Brass
construction

	INCAND. ITEM	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49160 OZ	(2) 100W (M)	11	22	6.5	10	W EOD (23-30W CFL)
B	49157 OZ	(1) 100W (M)	6	8	6.5	4	W EOD (23-30W CFL)
C	49158 OZ	(1) 100W (M)	7	11	8	5.25	W EOD (23-30W CFL)
D	49159 OZ	(1) 150W (M)	9	14	10	7.25	W EOD (30-52W CFL)

Measurements shown in inches. U.S. Patent Pending



E 49161 OZ



F 49164 OZ



G 49162 OZ



H 49163 OZ

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	NOTES
E	49161 OZ	(1) 100W (M)	11	18.5	92.5	25(72)	Ⓟ OD (23-30W CFL) Additional chain 4927 OZ
F	49164 OZ	(2) 75W (M)	12	5	---	---	Ⓟ OD (13-15W CFL)
G	49162 OZ	(1) 100W (M)	9	16.5	---	---	Ⓟ OD (23-30W CFL)
H	49163 OZ	(1) 150W (M)	11	18.5	---	---	Ⓟ OD (30-52W CFL)

Measurements shown in inches. U.S. Patent Pending

Portman Square™

Stainless Steel Finish and
Etched Seedy Glass



A 49160 :: SS



B 49157 :: SS



C 49158 :: SS



D 49159 :: SS

Stainless Steel
construction

	INCAND. ITEM	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49160 SS	(2) 100W (M)	11	22	6.5	10	Ⓜ ⓂOD (23-30W CFL)
B	49157 SS	(1) 100W (M)	6	8	6.5	4	Ⓜ ⓂOD (23-30W CFL)
C	49158 SS	(1) 100W (M)	7	11	8	5.25	Ⓜ ⓂOD (23-30W CFL)
D	49159 SS	(1) 150W (M)	9	14	10	7.25	Ⓜ ⓂOD (30-52W CFL)

Measurements shown in inches. U.S. Patent Pending



E 49161 SS



F 49164 SS



G 49162 SS



H 49163 SS

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	NOTES
E	49161 SS	(1) 100W (M)	11	18.5	92.5	25(72)	Ⓟ OD (23-30W CFL) Additional chain 4927 SS
F	49164 SS	(2) 75W (M)	12	5	---	---	Ⓟ OD (13-15W CFL)
G	49162 SS	(1) 100W (M)	9	16.5	---	---	Ⓜ OD (23-30W CFL)
H	49163 SS	(1) 150W (M)	11	18.5	---	---	Ⓜ OD (30-52W CFL)

Measurements shown in inches. U.S. Patent Pending



Lighting Tip

Form follows function

The hallmarks of contemporary style include clean lines, form that follows function and modern design. To create this chic look, choose neutral colors, smooth and understated lighting, and modern materials.













Kichler® Today's Living™ Lighting rearranges lines and angles in new ways for a familiar yet visionary appeal.

TODAY'S LIVING™

A balance of smooth textures with clean, conceptual design reflects today's most modern trends.

Symbol Guide

	DAMP		Title 24 Compliant
	WET		Lamp Included
	Dark Sky		Photocell Included
	ADA Compliant		Installation Requirements
	Hybrid		90° C. Wire Rated
	Hybrid Outdoor		75° C. Wire Rated
	Energy Star		

Tremillo™

Black Finish and Satin-Etched Cased Opal Glass

Incandescent | Energy Efficient



A 49203 BK
49203 BK FL



B 49200 BK
49200 BK FL



D 49202 BK
49202 BK FL



C 49201 BK
49201 BK FL

Cast Aluminum
construction

	INCAND. ITEM	INCAND. ITEM	INCAND. BULB	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	49203 BK	49203 BK FL	(1) 150W (M)	(1) 13W (GU24)	10	20.5	11.5	8.75	W OD (30-52W CFL)
B	49200 BK	49200 BK FL	(1) 75W (M)	(1) 13W (GU24)	6	12	7	5	W OD (13-15W CFL)
C	49201 BK	49201 BK FL	(1) 100W (M)	(1) 13W (GU24)	7	14.5	8.5	6.25	W OD (23-30W CFL)
D	49202 BK	49202 BK FL	(1) 100W (M)	(1) 13W (GU24)	8.5	17.5	10	7.50	W OD (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending



E 49206 BK
49206 BK FL
























F 49205 BK
49205 BK FL



G 49207 BK
49207 BK FL



H 49204 BK
49204 BK FL

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB		W	H	OVRL. H	WIRE (CHAIN)	NOTES
E	49206 BK	49206 BK FL	(2) 100W (M)	(2) 18W (GU24)  		11.5	6	---	---	   (23-30W CFL)
F	49205 BK	49205 BK FL	(1) 100W (M)	(1) 18W (GU24)  		7	17	91	25(72)	  (30-52W CFL) Additional chain 4927 BK
G	49207 BK	49207 BK FL	(1) 100W (M)	(1) 18W (GU24)    		8.5	20	---	---	  (23-30W CFL)
H	49204 BK	49204 BK FL	(1) 200W (M)	(1) 18W (GU24)    		10	23	---	---	  (30-52W CFL)

Measurements shown in inches. U.S. Patent Pending

Leeds™

Incandescent | Energy Efficient

Anvil Iron Finish and
Satin-Etched Cased
Opal Glass



A 49113 AVI
49113 AVI FL



B 49112 AVI
49112 AVI FL



C 49110 AVI
49110 AVI FL

Cast Aluminum
construction





D 49111 AVI
49111 AVI FL











































E 49115 AVI
49115 AVI FL



F 49116 AVI
49116 AVI FL



G 49114 AVI
49114 AVI FL

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB		W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	49113 AVI	49113 AVI FL	(2) 100W (M)	(2) 18W (GU24)    		9.5	20	---	---	7	10	  (23-30W CFL)
B	49112 AVI	49112 AVI FL	(1) 100W (M)	(1) 18W (GU24)    		7.5	16.5	---	---	6	8.25	  (23-30W CFL)
C	49110 AVI	49110 AVI FL	(1) 100W (M)	(1) 13W (GU24)    		6	12.5	---	---	5	6.25	  (13-15W CFL)
D	49111 AVI	49111 AVI FL	(2) 75W (M)	(2) 18W (GU24)    		6	18	---	---	5	9	  (13-15W CFL)
E	49115 AVI	49115 AVI FL	(1) 100W (M)	(1) 18W (GU24)  		8.5	19	93	26(72)	---	---	  (23-30W CFL) Add. chain order 4927 AVI
F	49116 AVI	49116 AVI FL	(2) 60W (M) 	(2) 26W (GU24)   		14	6	---	---	---	---	  (13-15W CFL)
G	49114 AVI	49114 AVI FL	(1) 100W (M)	(1) 26W (GU24)    		8.5	20	---	---	---	---	  (30-52W CFL)

Measurements shown in inches. U.S. Patent Pending

Metro Park™

Brushed Nickel Finish and
Opal-Etched Glass



A 49085 NI



B 49083 NI



C 49084 NI

Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49085 NI	(1) 150W (M)	9	16	10.5	6	Ⓜ ⓄD (30-52W CFL)
B	49083 NI	(1) 100W (M)	6.5	12	8	4.25	Ⓜ ⓄD (23-30W CFL)
C	49084 NI	(1) 100W (M)	7	13	8.5	4.75	Ⓜ ⓄD (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending



D 49088 NI



E 49089 NI



F 49086 NI



G 49087 NI

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	NOTES
D	49088 NI	(1) 100W (M)	7	12	50	66	D 0D (23-30W CFL) Additional chain 2996 NI, stem 2999 (12") NI and/or 2997 (24") NI
E	49089 NI	(2) 60W (M)	9	5.5	---	---	D 0D (13-15W CFL)
F	49086 NI	(1) 100W (M)	7	13.5	---	---	W 0D (23-30W CFL)
G	49087 NI	(1) 150W (M)	9	16.5	---	---	W 0D (30-52W CFL)

Measurements shown in inches. U.S. Patent Pending

Benton™

Olde Bronze® Finish
over Solid Brass and
Light Umber Glass

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.



A 9429 OZ



C 9869 OZ



D 9428 OZ



B 9427 OZ



E 9430 OZ



F 9528 OZ

* Convertible

Two distinct lighting
fixtures in one!

Semi Flush and Pendant

When converted to semi flush,
10.5" H.

G 9800 OZ



Solid Brass
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9429 OZ	(1) 150W (M)	9.5	14.5	---	---	10	6.50	W OD (23-30W CFL)
B	9427 OZ	(1) 60W (C)	6	9	---	---	6	3.75	W
C	9869 OZ	(1) 150W (M)	9	15.5	53.5	63	---	---	D OD (23-30W CFL) Additional chain 4927 OZ and/or stem 2999 (12") OZ
D	9428 OZ	(1) 100W (M)	7.5	11.5	---	---	8	4.75	W OD (23-30W CFL)
E	9430 OZ	(1) 200W (M)	11	17.5	---	---	11.5	8	W OD (23-30W CFL)
F	9528 OZ	(1) 150W (M)	9	17.5	---	---	---	---	W OD (23-30W CFL)
G	9800 OZ	(1) 100W (M)	5.5	9.5	47.5	65	---	---	D OD (23-30W CFL) Additional chain 4927 OZ and/or stem 2999 (12") OZ

Measurements shown in inches. U.S. Patent Pending

Outdoors™

Satin-Etched or
Light Umber Glass



A 9670 AZ



B 9672 AZ



Satin-Etched
Glass

C 9817 AP



Light Umber
Glass

C 9817 OZ

Aluminum
construction

	INCAND. ITEM	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	9670	AZ	(1) 60W (M)	7	12.5	5	6.25	W
B	9672	AZ	(1) 75W (M)	9	16	6	8	W
C	9817	AP, OZ	(2) 100W (M)	13	7	---	---	D ✓ EOD (18-25W CFL)

Measurements shown in inches. U.S. Patent Pending: A, B

AP Antique Pewter

AZ Architectural Bronze®

NI Brushed Nickel

OZ Olde Bronze®

Outdoors™

Architectural Bronze® Finish
and Smoked Umber Glass

Incandescent
Energy Efficient



A 10963 AZ



B 9094 AZ





















C 10922 AZ



D 9095 AZ

Aluminum
construcción

100

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	---	10963 AZ	---	(1) 13W (GU24)    	8	12	6	6	  Dark Sky Panels included
B	9094 AZ	---	(1) 100W (M)	---	8	12	6	6	   0D (23-30W CFL) Dark Sky Panels included
C	---	10922 AZ	---	(1) 13W (GU24)    	7	12	5.5	6	  Dark Sky Panels included
D	9095 AZ	---	(1) 100W (M)	---	7	12	5.5	6	   0D (23-30W CFL) Dark Sky Panels included

Measurements shown in inches. U.S. Patent Pending: B, C

Energy Efficient Outdoor/Indoor

Brushed Aluminum or Architectural Bronze® Finishes
and White Poly-Carbonate Diffuser

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.



A 11095 BA
ADA Compliant



B 11097 BA



B 11097 AZ



A 11095 AZ
ADA Compliant



C 11096 BA
ADA Compliant



C 11096 AZ
ADA Compliant

Cast Aluminum
construction

	FLUOR. ITEM	FINISH	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	11095	AZ, BA	(1) 18W (GU24)	8	16.5	4	6.25	W ADA
B	11097	AZ, BA	(2) 18W (GU24)	10	5	---	---	D
C	11096	AZ, BA	(1) 18W (GU24)	6.5	9	4	4.50	W ADA

Measurements shown in inches. U.S. Patent Pending

Celino™

Brushed Aluminum or
Black Finish and White-
Etched Opal Glass



A 9109 : BA, BK



B 9110 : BA, BK

Cast Aluminum
construction

Newport™

Architectural Bronze® or
Brushed Nickel with White
Acrylic Diffuser and Housing



C 6040 : AZ
ADA Compliant



D 10640 : AZ
ADA Compliant

Aluminum
construction

Incandescent
Energy Efficient



C 6040 : NI
ADA Compliant



D 10640 : NI
ADA Compliant

	INCAND. ITEM	FLUOR. ITEM	FINISH	INCAND. BULB	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	9109	---	BA, BK	(1) 100W (M)	---	5	13.5	5	10.50	W EOD (23-30W CFL)
B	9110	---	BA, BK	(1) 150W (M)	---	7	18.5	7	14.25	W EOD (23-30W CFL)
C	6040	---	AZ, NI	(1) 60W (M)	---	9.5	10.5	4	5.25	W ADA EOD (9-13W CFL)
D	---	10640	AZ, NI	---	(1) 18W (GU24)	9.5	10.5	4	5.25	W ADA

Measurements shown in inches.

Centennial™

Brushed Nickel or Olde Bronze®
Finish and Satin-Etched Cased
Opal Glass

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.



A 9714 NI, OZ



B 9671 NI, OZ



C 9700 NI, OZ



D 9900 NI, OZ

Aluminum
construction

INCAND. ITEM	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	9714	NI, OZ	(1) 100W (M)	10	17	11.5	8	W OD (23-30W CFL)
B	9671	NI, OZ	(1) 100W (M)	6.5	14	7	7	W ✓ OD (23-30W CFL)
C	9700	NI, OZ	(1) 100W (M)	7	12	8	5	W OD (23-30W CFL)
D	9900	NI, OZ	(1) 150W (M)	12	21	---	---	W OD (23-30W CFL)

Measurements shown in inches. U.S. Patent Design No. 408,575: A U.S. Patent Design No. 570,523: B U.S. Patent Pending: C, D

Hendrik™

Textured Architectural
Bronze® Finish and
Light Umber Glass



A 9203 AZT



B 9101 AZT



C 9100 AZT

Cast Aluminum
construction

Energy Efficient

Distressed Copper Finish



D 10925 DCO















E 10924 DCO



F 10926 DCO

Aluminum
construction

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	9203 AZT	---	(1) 100W (M)	---	8	18	11	9	W EOD (23-30W CFL)
B	9101 AZT	---	(1) 100W (M)	---	6.5	15	9.5	7.50	W EOD (23-30W CFL)
C	9100 AZT	---	(1) 150W (M)	---	5.5	11.5	7.5	5.75	W EOD (23-30W CFL)
D	---	10925 DCO	---	(1) 13W (GU24)    	7	11	9	6	W C
E	---	10924 DCO	---	(1) 13W (GU24)    	5	9.5	7.5	5.25	W C
F	---	10926 DCO	---	(1) 18W (GU24)    	9	14.5	12	7.75	W C

Measurements shown in inches. U.S. Patent Pending: A, B, C

Creston™

Aged Bronze Finish and
Light Umber-Etched Glass

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.

TODAY'S LIVING™

T



A 9059 AGZ



B 9557 AGZ



C 9556 AGZ



D 9057 AGZ



E 9058 AGZ



F 9959 AGZ

Cast Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9059 AGZ	(1) 100W (M)	11	14.5	---	---	12	6.25	W 30D (23-30W CFL)
B	9557 AGZ	(1) 100W (M)	10.5	6.5	---	---	---	---	D 30D (23-30W CFL)
C	9556 AGZ	(1) 100W (M)	11	14.5	52.5	64	---	---	D 30D (23-30W CFL) Additional chain 4927 AGZ and/or stem 2999 (12") AGZ
D	9057 AGZ	(1) 60W (M)	7	9.5	---	---	8	4	W 30D (13-15W CFL)
E	9058 AGZ	(1) 60W (M)	9	12	---	---	10	5	W 30D (13-15W CFL)
F	9959 AGZ	(1) 100W (M)	11	17	---	---	---	---	W 30D (23-30W CFL)


Measurements shown in inches. U.S. Patent Pending



Lighting Tip

Your front door

Wall lanterns on either side of the front door or a hanging or ceiling mounted fixture above the door create a well-lit space to welcome guests. Not to mention provides additional security for your family to see out.












M

MISSION / LODGE

Kichler® Mission and Lodge style lanterns bring a touch of the woodlands to your home.

Its charming beauty incorporates angular forms and warm muted colors for a common style influenced by the Arts and Crafts movement.

Symbol Guide

- | | | | |
|---|----------------|---|---------------------------|
|  D | DAMP |  T24 | Title 24 Compliant |
|  W | WET |  | Lamp Included |
|  | Dark Sky |  | Photocell Included |
|  | ADA Compliant |  | Installation Requirements |
|  | Hybrid |  | 90° C. Wire Rated |
|  | Hybrid Outdoor |  | 75° C. Wire Rated |
|  | Energy Star | | |


North Creek™

Incandescent | Energy Efficient

Olde Bronze® Finish and
Light Umber-Etched Seedy Glass



A 49177 OZ
49177 OZ FL



B 49176 OZ
49176 OZ FL

C 49174 OZ
49174 OZ FL

Cast Aluminum
construction





D 49181 OZ
49181 OZ FL



E 49180 OZ
49180 OZ FL



F 49175 OZ
49175 OZ FL



G 49178 OZ
49178 OZ FL



H 49179 OZ
49179 OZ FL

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB		W	H	OVRL. HGT.	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	49177 OZ	49177 OZ FL	(1) 150W (M)	(1) 26W (GU24)		12.5	18	---	---	13.5	5	(30-52W CFL)
B	49176 OZ	49176 OZ FL	(1) 100W (M)	(1) 18W (GU24)		10.5	16.5	---	---	11.5	4.50	(18-25W CFL)
C	49174 OZ	49174 OZ FL	(1) 100W (M)	(1) 13W (GU24)		6.5	8.5	---	---	7.5	3.25	(13-15W CFL)
D	49181 OZ	49181 OZ FL	(2) 75W (M)	(2) 26W (GU24)		12	6.5	---	---	---	---	(18-25W CFL)
E	49180 OZ	49180 OZ FL	(1) 150W (M)	(1) 18W (GU24)		8.5	14.5	88.5	27(72)	---	---	(30-52W CFL) Additional chain 4927 OZ
F	49175 OZ	49175 OZ FL	(1) 100W (M)	(1) 18W (GU24)		8.5	13.5	---	---	9.5	2.75	(23-30W CFL)
G	49178 OZ	49178 OZ FL	(1) 100W (M)	(1) 18W (GU24)		10.5	20	---	---	---	---	(30-52W CFL)
H	49179 OZ	49179 OZ FL	(1) 150W (M)	(1) 26W (GU24)		12.5	22	---	---	---	---	(30-52W CFL)

Measurements shown in inches.

Anvil Iron Finish and
Opal-Etched Glass



A 49122 AVI
49122 AVI FL
















B 49119 AVI
49119 AVI FL



C 49120 AVI
49120 AVI FL

Cast Aluminum
construction

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	49122 AVI	49122 AVI FL	(3) 100W (M)	(3) 18W (GU24)   	9	26.5	11.5	---	  OD (23-30W CFL) Variable height mounting hardware included, Junction box 5.75"-21.5"
B	49119 AVI	49119 AVI FL	(1) 100W (M)	(1) 13W (GU24)   	5	11	6	5.50	 OD (23-30W CFL)
C	49120 AVI	49120 AVI FL	(2) 100W (M)	(2) 18W (GU24)   	6.5	19.5	7.5	9.75	 OD (23-30W CFL)

Measurements shown in inches.



D 49125 AVI
49125 AVI FL























E 49124 AVI
49124 AVI FL



F 49121 AVI
49121 AVI FL



G 49123 AVI
49123 AVI FL

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB		W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
D	49125 AVI	49125 AVI FL	(1) 75W (M)	(1) 18W (GU24)  		10	5.5	---	---	---	---	  OD (18-25W CFL)
E	49124 AVI	49124 AVI FL	(1) 150W (M)	(1) 18W (GU24)  		9.5	19	93	24(72)	---	---	  OD (30-52W CFL) Additional chain 4927 AVI
F	49121 AVI	49121 AVI FL	(2) 75W (M)	(2) 18W (GU24)    		7.5	22.5	---	---	8.5	11.25	  OD (18-25W CFL)
G	49123 AVI	49123 AVI FL	(1) 150W (M)	(1) 26W (GU24)    		9.5	17	---	---	---	---	  OD (30-52W CFL)

Measurements shown in inches.

Montara™

Olde Iron Finish and
Umber-Etched Linen Glass

Incandescent

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.



A 49078 OI
ADA Compliant



B 49076 OI
ADA Compliant



C 49049 OI



D 49077 OI
ADA Compliant



E 49080 OI

Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	49078 OI	(1) 60W (M)	8.5	16	---	---	4	9.50	W ADA T type lamp required
B	49076 OI	(1) 60W (M)	6	8	---	---	4	4.25	W ADA T type lamp required
C	49049 OI	(1) 100W (M)	9.5	13.5	87.5	24(72)	---	---	D Additional chain 4927 OI
D	49077 OI	(1) 60W (M)	7.5	10	---	---	4	6	W ADA T type lamp required
E	49080 OI	(1) 150W (M)	9.5	9.5	---	---	---	---	W

Measurements shown in inches. U.S. Patent Pending

Menlo™

Aged Bronze Finish and
Light-Umber Etched Glass

Incandescent | Energy Efficient

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.

MISSION / LODGE

M



A 49027 11107 AGZ



B 49028 Indoor/Outdoor AGZ













C 49026 AGZ



D 49036 AGZ

Cast Aluminum
construction

113

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	49027 AGZ	11107 AGZ	(1) 100W (M)	(1) 18W (GU24)    	9.5	9.5	---	---	10.5	2.50	  OD (13W CFL)
B	49028 AGZ	---	(1) 100W (M)	---	9.5	8.5	46.5	66	---	---	  OD (13W CFL) Additional chain 4927 AGZ and/or stem 4938 AGZ
C	49026 AGZ	---	(1) 75W (M)	---	8	8.5	---	---	9	2.50	
D	49036 AGZ	---	(1) 100W (M)	---	10.5	12.5	---	---	---	---	

Measurements shown in inches. U.S. Patent Pending: A, B, C


Pasadena

Incandescent | Energy Efficient

Olde Bronze® Finish and
Feathered Cream Glass



A 49140 OZ
49140 OZ FL



B 49139 OZ
49139 OZ FL

C 49138 OZ
49138 OZ FL

Cast Aluminum
construction





D 49137 OZ
49137 OZ FL



E 49143 OZ
49143 OZ FL



F 49144 OZ
49144 OZ FL



G 49141 OZ
49141 OZ FL



H 49142 OZ
49142 OZ FL

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB		W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	49140 OZ	49140 OZ FL	(1) 100W (M)	(1) 26W (GU24)		11	15	---	---	13.5	5.50	W (23-30W CFL)
B	49139 OZ	49139 OZ FL	(1) 100W (M)	(1) 18W (GU24)		9	12	---	---	11	5.50	W (23-30W CFL)
C	49138 OZ	49138 OZ FL	(1) 100W (M)	(1) 13W (GU24)		6.5	8	---	---	7.5	4.25	W (23-30W CFL)
D	49137 OZ	49137 OZ FL	(1) 100W (M)	(1) 13W (GU24)		7.5	11.5	---	---	9.5	4.50	W (23-30W CFL)
E	49143 OZ	49143 OZ FL	(1) 100W (M)	(1) 18W (GU24)		11	16.5	90.5	25(72)	---	---	D (23-30W CFL) Additional chain 4927 OZ
F	49144 OZ	49144 OZ FL	(2) 60W (M)	(2) 26W (GU24)		12.5	7	---	---	---	---	D (13-15W CFL)
G	49141 OZ	49141 OZ FL	(1) 100W (M)	(1) 18W (GU24)		9	16.5	---	---	---	---	W (23-30W CFL)
H	49142 OZ	49142 OZ FL	(1) 100W (M)	(1) 26W (GU24)		11	19	---	---	---	---	W (23-30W CFL)

Measurements shown in inches.

Melbern™

Aged Bronze Finish and
Light Umber-Etched Glass



A 9054 AGZ



B 9052 AGZ



C 9053 AGZ

Cast Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	9054 AGZ	(1) 100W (M)	13	18	15	3.75	W EOD (23-30W CFL)
B	9052 AGZ	(1) 100W (M)	9	13.5	10	2.75	W EOD (23-30W CFL)
C	9053 AGZ	(1) 100W (M)	11	16	12.5	3	W EOD (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending



D 9554 AGZ



E 9555 AGZ



F 9051 AGZ



G 9955 AGZ

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
D	9554 AGZ	(1) 100W (M)	11	13	87	27(72)	---	---	Ⓟ ⓂOD (23-30W CFL) Additional chain 4927 AGZ
E	9555 AGZ	(1) 100W (M)	10	7.5	---	---	---	---	Ⓟ ⓂOD (18-25W CFL)
F	9051 AGZ	(1) 75W (M)	7	11	---	---	8	2.75	Ⓜ ⓂOD (18-25W CFL)
G	9955 AGZ	(1) 100W (M)	11	16.5	---	---	---	---	Ⓜ ⓂOD (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending

Chicago™

Aged Bronze Finish and
Textured Linen Seedy Glass



A 9367 AGZ



B 9364 AGZ



C 9365 AGZ

Cast Aluminum
construction





D 3327 AGZ



E 9827 AGZ



F 9867 AGZ



G 9366 AGZ



H 9975 AGZ

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	STEM TILT	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9367 AGZ	(1) 150W (M)	12	15	---	---	---	13.5	3.5	W EOD (23-30W CFL)
B	9364 AGZ	(1) 60W (M)	7	9.5	---	---	---	8	3	W EOD (13-15W CFL)
C	9365 AGZ	(1) 75W (M)	8	11	---	---	---	9	3	W EOD (18-25W CFL)
D	3327 AGZ	(1) 60W (M)	7	8.5	46	45°(12:12)	66	---	---	D EOD (13-15W CFL) Additional stem 2999 (12") AGZ
E	9827 AGZ	(1) 100W (M)	10	13	87	---	27(72)	---	---	D EOD (23-30W CFL) Additional chain 4927 AGZ
F	9867 AGZ	(2) 75W (M)	12	6	---	---	---	---	---	D EOD (18-25W CFL)
G	9366 AGZ	(1) 100W (M)	10	13	---	---	---	11	3	W EOD (23-30W CFL)
H	9975 AGZ	(1) 150W (M)	12	16	---	---	---	---	---	W EOD (23-30W CFL)

Measurements shown in inches.

Riverbank™

Aged Bronze Finish and
White Linen Mist Glass



A 49148 AGZ



B 49147 AGZ



C 49146 AGZ

Cast Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49148 AGZ	(1) 150W (M)	9	13.5	11.5	4	Ⓜ ⓈOD (23-30W CFL)
B	49147 AGZ	(1) 100W (M)	7	10.5	9	3.25	Ⓜ ⓈOD (23-30W CFL)
C	49146 AGZ	(1) 100W (M)	5	8.5	7	4	Ⓜ ⓈOD (18-25W CFL)

Measurements shown in inches. U.S. Patent Pending



D 49152 AGZ



E 49153 AGZ



F 49150 AGZ

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	NOTES
D	49152 AGZ	(1) 150W (M)	9	15	89	26(72)	Ⓛ 30D (30-52W CFL) Additional chain 4927 AGZ
E	49153 AGZ	(2) 60W (C)	9.5	5.5	---	---	Ⓛ ✦
F	49150 AGZ	(1) 150W (M)	9	16.5	---	---	Ⓛ 30D (30-52W CFL)

Measurements shown in inches. U.S. Patent Pending

Cross Creek™

Aged Bronze Finish and
Textured Linen Seedy Glass

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.



A 9656 AGZ



B 9130 AGZ



C 9830 AGZ



D 9128 AGZ



E 9129 AGZ

Cast Aluminum
construction

122

	INCAND. ITEM	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	9656 AGZ	(2) 150W (M)	7.5	24.5	9.5	12	W EOD (23-30W CFL)
B	9130 AGZ	(1) 150W (M)	9.5	16	10.5	3	W EOD (23-30W CFL)
C	9830 AGZ	(2) 75W (M)	9	5.5	---	---	D EOD (18-25W CFL)
D	9128 AGZ	(1) 100W (M)	6	8.5	7.5	2.5	W EOD (9-13W CFL)
E	9129 AGZ	(1) 150W (M)	7.5	13.5	9	3	W EOD (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending

Coordinating Landscape Lighting

See the complete line of Kichler® Landscape Lighting at LandscapeLighting.com



F 9829 AGZ



H 9132 AGZ



G 9131 AGZ



J 9527 AGZ



K 9529 AGZ

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
F	9829 AGZ	(1) 150W (M)	11.5	14.5	89	25(72)	---	---	D 0D (23-30W CFL) Additional chain 4927 AGZ
G	9131 AGZ	(1) 150W (M)	11.5	18.5	---	---	13	3.5	W 0D (23-30W CFL)
H	9132 AGZ	(1) 200W (M)	13.5	22	---	---	14.5	3.5	W 0D (23-30W CFL)
J	9527 AGZ	(1) 100W (M)	9	14	---	---	---	---	W 0D (23-30W CFL)
K	9529 AGZ	(1) 150W (M)	11.5	17	---	---	---	---	W 0D (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending: F, G, H, K

Morris™

Incandescent | Energy Efficient

Distressed Copper Finish
and Inside-Etched Iridized
Seedy Glass



A 9027 DCO
10930 DCO



B 9026 DCO
10929 DCO















D 9024 DCO



C 9025 DCO
10928 DCO

Cast Aluminum
construction

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	9027 DCO	10930 DCO	(1) 200W (M)	(1) 18W (GU24)    	12	13.5	13	4.50	  OD (23-30W CFL)
B	9026 DCO	10929 DCO	(1) 150W (M)	(1) 13W (GU24)    	10	11	11	3.50	  OD (23-30W CFL)
C	9025 DCO	10928 DCO	(1) 100W (M)	(1) 13W (GU24)    	8	9.5	9	2.75	
D	9024 DCO	---	(1) 60W (M)	---	6.5	8.5	7.5	2.75	

Measurements shown in inches. U.S. Patent Pending



E 9837 DCO
10921 DCO



F 9838 DCO



G 9031 DCO



H 9920 DCO
10927 DCO

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	OVRLL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
E	9837 DCO	10921 DCO	(1) 150W (M)	(1) 18W (GU24)  	12	13	86	28(72)	---	---	 0D (23-30W CFL) Additional chain 4927 DCO
F	9838 DCO	---	(2) 60W (M)	---	12	6	---	---	---	---	 0D (13-15W CFL)
G	9031 DCO	---	(1) 100W (M)	---	8	15	---	---	9	6	 0D (23-30W CFL)
H	9920 DCO	10927 DCO	(1) 200W (M)	(1) 18W (GU24)   	12	15	---	---	---	---	 0D (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending

La Mesa™

Canyon View™ Finish over
Solid Brass and Honey
Opalescent Glass Panels

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.



A 9726 CV



B 9724 CV

Solid Brass
construction



Coordinating Landscape Lighting

See the complete line of
Kichler® Landscape Lighting at
LandscapeLighting.com



C 9824 CV



D 9825 CV



E 9725 CV



F 9926 CV

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9726 CV	(1) 150W (M)	17	14.5	---	---	19	2.75	W EOD (23-30W CFL)
B	9724 CV	(1) 100W (M)	9	8	---	---	10	2.25	W
C	9824 CV	(1) 100W (M)	12	10	84	29(72)	---	---	D EOD (23-30W CFL) Additional chain 4927 CV
D	9825 CV	(2) 75W (M)	11.5	6.5	---	---	---	---	D V EOD (18-25W CFL)
E	9725 CV	(1) 100W (M)	12	10.5	---	---	13.5	2.25	W EOD (23-30W CFL)
F	9926 CV	(1) 150W (M)	17	14	---	---	---	---	W EOD (23-30W CFL)

Measurements shown in inches. Complete selection of Dark Sky adapter panels for: A, B, C, E on pages 156-157

Alameda™

Canyon View™ Finish over
Solid Brass and Honey
Opalescent Glass Panels

Incandescent | Energy Efficient



A 9148 CV



B 9649 CV
10962 CV



C 49090 Indoor/Outdoor Chandelier CV



D 9652 CV
10960 CV



E 9651 CV
10961 CV



G 9147 CV



F 9150 CV
9150 CV FL



H 9143 CV

Solid Brass
construction

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	OVRL. H	L	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9148 CV	---	(1) 150W (M)	---	7	15	---	---	---	8.5	3	W ✓ EOD (18-25W CFL)
B	9649 CV	10962 CV	(1) 75W (M)	(1) 13W (GU24)	5	7	---	---	---	5.5	4	W ✓ EOD (18-25W CFL)
C	49090 CV	---	(3) 100W (M)	---	6	20	58	36	56	---	---	D Additional chain 2996 CV and/or stem 2999 (12") CV
D	9652 CV	10960 CV	(1) 150W (M)	(1) 18W (GU24)	9	14.5	---	---	---	10.5	3.50	W ✓ EOD (23-30W CFL)
E	9651 CV	10961 CV	(1) 100W (M)	(1) 13W (GU24)	7	11.5	---	---	---	8.5	3	W ✓ EOD (23-30W CFL)
F	9150 CV	9150 CV FL	(1) 150W (M)	(1) 18W (GU24)	11	17.5	---	---	---	12.5	4.25	W ✓ EOD (30-52W CFL)
G	9147 CV	---	(1) 100W (M)	---	9	10	---	---	---	5.5	4	W ✓ EOD (23-30W CFL)
H	9143 CV	---	(1) 100W (M)	---	7	8	---	---	---	4	3.75	W ✓ EOD (23-30W CFL)

Measurements shown in inches. Complete selection of Dark Sky adapter panels for: B, D, E on pages 156-157



J 49091 Indoor/Outdoor Chandelier CV



K 9849 10958 CV





L 9825 10957 CV



M 49092 Indoor/Outdoor Chandelier CV



N 9953 10959 CV

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	OVRL. H	L	WIRE (CHAIN)	NOTES
J	49091 CV	---	(4) 100W (M)	---	25	17	55	---	59	Ⓧ Additional chain 2996 CV and/or stem 2999 (12") CV
K	9849 CV	10958 CV	(1) 100W (M)	(1) 13W (GU24)  	7	11.5	85	---	28(72)	Ⓧ  OD (23-30W CFL) Additional chain 4927 CV
L	9825 CV	10957 CV	(2) 75W (M)	(2) 13W (GU24)  	11.5	6.5	---	---	---	Ⓧ   OD (18-25W CFL)
M	49092 CV	---	(6) 100W (M)	---	20	20	56	36	56	Ⓧ Additional chain 4908 CV and/or stem 2999 (12") CV
N	9953 CV	10959 CV	(1) 150W (M)	(1) 18W (GU24)   	9	12.5	---	---	---	Ⓧ  OD (23-30W CFL)

Measurements shown in inches. Complete selection of Dark Sky adapter panels for K on pages 156-157

Tularosa™

Incandescent | Energy Efficient

Canyon View™ Finish over
Solid Brass and Honey
Opalescent Glass Panels



B 9845 CV














A 9645 CV
10945 CV



C 9646 CV
10946 CV

Solid Brass
construction

130

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	9645 CV	10945 CV	(1) 100W (M)	(1) 13W (GU24)   	6	13.5	9.5	2.50	  OD (23-30W CFL)
B	9845 CV	---	(1) 100W (M)	---	9	6.5	---	---	  OD (9-13W CFL)
C	9646 CV	10946 CV	(1) 100W (M)	(1) 18W (GU24)   	8	17	11	3	  OD (23-30W CFL)

Measurements shown in inches. Complete selection of Dark Sky adapter panels for: A, C on pages 156-157






D 9647 CV



E 9846 CV
10949



F 9945 CV
10944

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
D	9647 CV	---	(1) 150W (M)	---	11.5	13.5	---	---	13	3	W 30D (23-30W CFL)
E	9846 CV	10949 CV	(1) 100W (M)	(1) 18W (GU24) 	8	16	90	26(72)	---	---	D 30D (23-30W CFL) Additional chain 4927 CV
F	9945 CV	10944 CV	(1) 150W (M)	(1) 18W (GU24)  	11.5	13	---	---	---	---	W 30D (23-30W CFL)

Measurements shown in inches. Complete selection of Dark Sky adaptor panels for: D, E on pages 156-157

Lynnewood Gardens™

Legacy Bronze™ Finish and
Textured Linen Seedy Glass



A 9014 LZ



B 9015 LZ



C 9011 LZ



D 9012 LZ

Cast Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	9014 LZ	(1) 150W (M)	11	24.5	13	19.50	Ⓜ 30D (23-30W CFL)
B	9015 LZ	(1) 150W (M)	11	23	13	5.25	Ⓜ 30D (23-30W CFL)
C	9011 LZ	(1) 100W (M)	7	15	9	4	Ⓜ 30D (23-30W CFL)
D	9012 LZ	(1) 150W (M)	9	20.5	11	15.75	Ⓜ 30D (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending



E 9013 LZ



F 9815 LZ



G 9814 LZ



H 9016 LZ



J 9010 LZ



K 9514 LZ

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
E	9013 LZ	(1) 150W (M)	9	19	---	---	11	4.75	W OD (23-30W CFL)
F	9815 LZ	(1) 150W (M)	11	19.5	93	25(72)	---	---	D OD (23-30W CFL) Additional chain 4927 LZ
G	9814 LZ	(2) 60W (M)	11	7.5	---	---	---	---	D OD (13-15W CFL)
H	9016 LZ	(1) 200W (M)	13	28.5	---	---	15.5	---	W OD (23-30W CFL) Variable height mounting hardware included, Junction box 6.25"-10.25"
J	9010 LZ	(1) 60W (M)	6	11	---	---	6.5	3	W
K	9514 LZ	(1) 150W (M)	11	22.5	---	---	---	---	W OD (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending

Cayman Shores™

Legacy Bronze™ Finish and
Light Umber Textured Glass

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.



A 49242 LZ



B 49243 LZ



C 49240 LZ



D 49244 LZ



E 49241 LZ

Cast Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	49242 LZ	(1) 100W (MNCN)	9.5	21	---	---	12	10.75	
B	49243 LZ	(1) 100W (MNCN)	9.5	21	95	10(72)	---	---	Additional chain 4927 LZ
C	49240 LZ	(1) 100W (MNCN)	6.5	17.5	---	---	10	9	
D	49244 LZ	(1) 100W (MNCN)	9.5	21	---	---	---	---	
E	49241 LZ	(1) 100W (MNCN)	8	19	---	---	10.5	10	

Measurements shown in inches. U.S. Patent Pending

Lancaster Gardens™

Aged Bronze Finish and Pine Bark Glass

Incandescent
Energy Efficient

See pages 158-159 for our complete selection of Posts and Pedestal Mount Adaptors.

MISSION / LODGE

M



A 49168 AGZ
49168 AGZ FL



B 49167 AGZ
49167 AGZ FL



























C 49166 AGZ
49166 AGZ FL



D 49170 AGZ
49170 AGZ FL


Aluminum
construction

	INCAND. ITEM	FLUOR. ITEM	INCAND. BULB	FLUOR. BULB		W	H	EXT.	HCWO	NOTES
A	49168 AGZ	49168 AGZ FL	(1) 150W (M)	(1) 26W (GU24)    	9.5	15	7.5	6.75	  (30-52W CFL)	
B	49167 AGZ	49167 AGZ FL	(1) 100W (M)	(1) 18W (GU24)    	8	13	6	5.75	  (23-30W CFL)	
C	49166 AGZ	49166 AGZ FL	(1) 100W (M)	(1) 13W (GU24)    	6.5	9	5.5	4	  (13-15W CFL)	
D	49170 AGZ	49170 AGZ FL	(1) 150W (M)	(1) 26W (GU24)    	9.5	19.5	---	---	  (32-50W CFL)	

Measurements shown in inches. U.S. Patent Pending

Aged Bronze Finish and
Weathered White Glass

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.



A 9354 AGZ



B 9352 AGZ




C 9351 AGZ

Cast Aluminum
construction



Coordinating Landscape Lighting

See the complete line of Kichler® Landscape Lighting at LandscapeLighting.com



D 9852 AGZ



E 9802 AGZ



F 9353 AGZ



G 9954 AGZ

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9354 AGZ	(1) 200W (M)	12	19	---	---	16.5	3	W OD (23-30W CFL)
B	9352 AGZ	(1) 100W (M)	8	12.5	---	---	11	2.50	W
C	9351 AGZ	(1) 60W (C)	6	8	---	---	8	2.50	W
D	9852 AGZ	(1) 150W (M)	12	16.5	90	26(72)	---	---	D OD (23-30W CFL) Additional chain 4927 AGZ
E	9802 AGZ	(3) 60W (M)	15	8	---	---	---	---	D OD (13-15W CFL)
F	9353 AGZ	(1) 150W (M)	10	14.5	---	---	14.5	3	W OD (23-30W CFL)
G	9954 AGZ	(1) 200W (M)	12	18	---	---	---	---	W OD (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending



Lighting Tip

Using dimmers improve lighting effects

Adjust the mood quickly by incorporating dimmer switches into your outdoor lighting design. Also keep in mind that the glow from the moon and other sources of natural light may affect areas differently.



NAUTICAL

Bring the serenity of the sea to your front door with Kichler® Nautical Lighting.

Reminiscent of the working lights of Early American schooners, this casual coastal-inspired collection complements any home, whether landlocked or seaside.

Symbol Guide

- | | | | |
|-----|----------------|-----|---------------------------|
| D | DAMP | T24 | Title 24 Compliant |
| W | WET | | Lamp Included |
| | Dark Sky | | Photocell Included |
| ADA | ADA Compliant | i | Installation Requirements |
| | Hybrid | | 90° C. Wire Rated |
| OD | Hybrid Outdoor | | 75° C. Wire Rated |
| | Energy Star | | |

Vidalia

Olde Brick® Finish and Seedy Glass

Coordinating Landscape Lighting

See the complete line of Kichler® Landscape Lighting at LandscapeLighting.com



A 9908 OB



B 9408 OB



C 9407 OB

Aluminum
construction

Concord

Olde Brick® Finish and Seedy Glass

See pages 158-159 for our complete selection of Posts and Pedestal Mount Adaptors.



D 9477 OB



E 9478 OB



F 9979 OB



G 9479 OB

Solid Brass
construction

	INCAND. ITEM	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	9908 OB	(1) 100W (M)	8.5	16	---	---	W EOD (23-30W CFL)
B	9408 OB	(1) 100W (M)	8.5	15	9	5	W EOD (23-30W CFL)
C	9407 OB	(1) 40W (M)	6.5	10.5	7	3.50	W
D	9477 OB	(1) 100W (M)	5	11	5	3	W EOD (23-30W CFL)
E	9478 OB	(1) 100W (M)	6.5	14.5	6	3.75	W EOD (23-30W CFL)
F	9979 OB	(1) 100W (M)	8	20	---	---	W EOD (23-30W CFL)
G	9479 OB	(1) 100W (M)	8	17	8.5	3.75	W EOD (23-30W CFL)

Northbridge™

Distressed Copper
Finish and Clear Seedy Glass

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.

NAUTICAL

N



A 9306 DCO



B 9813 DCO



D 9304 DCO



C 9303 DCO



E 9812 DCO



F 9305 DCO



G 9905 DCO

Aluminum &
Solid Brass
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9306 DCO	(3) 60W (C)	13	22.5	---	---	17.5	12	W
B	9813 DCO	(3) 60W (C)	11	16.5	90	18(72)	---	---	D Additional chain 4927 DCO
C	9303 DCO	(1) 100W (M)	7	9.5	---	---	8	5	W EOD (23-30W CFL)
D	9304 DCO	(1) 150W (M)	9	16	---	---	12	8.25	W EOD (23-30W CFL)
E	9812 DCO	(1) 150W (M)	7	10.5	---	---	---	---	D EOD (23-30W CFL)
F	9305 DCO	(3) 60W (C)	11	19.5	---	---	14.5	10.25	W
G	9905 DCO	(3) 60W (C)	12	17.5	---	---	---	---	W

Measurements shown in inches. U.S. Patent Pending

Royal Marine™

Olde Bronze® Finish
and Etched Seedy Glass

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.



A 49127 OZ



B 49126 OZ



C 49128 OZ



D 49129 OZ

Cast Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49127 OZ	(1) 100W (M)	9.5	18.5	12.5	7.25	W EOD (23-30W CFL)
B	49126 OZ	(1) 100W (M)	7	13.5	9.5	5.75	W EOD (23-30W CFL)
C	49128 OZ	(1) 150W (M)	11.5	22	14.5	9	W EOD (23-30W CFL)
D	49129 OZ	(1) 150W (M)	9.5	19	---	---	W EOD (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending

Rustic™

Rustic Finish over Solid Brass and Clear Beveled Glass Panels

See pages 158-159 for our complete selection of Posts and Pedestal Mount Adaptors.

NAUTICAL

N



A 9762 RST



B 9760 RST



C 9870 RST



D 9759 RST



E 9761 RST



F 9962 RST

Solid Brass
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9762 RST	(1) 150W (M)	11	20.5	---	---	12	8	W EOD (23-30W CFL)
B	9760 RST	(1) 100W (M)	7	13.5	---	---	8	5.50	W EOD (23-30W CFL)
C	9870 RST	(1) 150W (M)	12	18	92	23(72)	---	---	D EOD (23-30W CFL) Additional chain 4927 RST
D	9759 RST	(1) 100W (M)	6	10	---	---	7	2.50	W EOD (23-30W CFL)
E	9761 RST	(1) 150W (M)	9.5	18	---	---	10.5	7	W EOD (23-30W CFL)
F	9962 RST	(1) 150W (M)	9.5	18.5	---	---	---	---	W EOD (23-30W CFL)

Measurements shown in inches.

Ripley™

Olde Bronze® Finish

See pages 158-159 for our complete selection of Posts and Pedestal Mount Adaptors.



B 49062 OZ



C 49059 OZ



A 49061 OZ



D 49060 OZ



E 49063 OZ

Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	49061 OZ	(1) 40W (Type R) or 60W (G type)	12	10	---	---	13	3.25	Dark sky compliant with use of R14, 40W bulb
B	49062 OZ	(1) 40W (Type R) or 60W (G type)	10	8	46	63	9.5	---	Dark sky compliant with use of R14, 40W bulb; Additional chain 4927 OZ and/or stem 2999 (12") OZ
C	49059 OZ	(1) 40W (Type R) or 60W (G type)	8	7.5	---	---	9	2.75	Dark sky compliant with use of R14, 40W bulb
D	49060 OZ	(1) 40W (Type R) or 60W (G type)	10	9	---	---	11.5	3	Dark sky compliant with use of R14, 40W bulb
E	49063 OZ	(1) 40W (Type R) or 60W (G type)	12	16	---	---	---	---	Dark sky compliant with use of R14, 40W bulb

Measurements shown in inches. U.S. Patent Pending: B, E

Ripley™

Brushed Nickel Finish

See pages 158-159 for our complete selection of Posts and Pedestal Mount Adaptors.

NAUTICAL

N



A 49061 NI



B 49059 NI



C 49062 NI



D 49060 NI



E 49063 NI

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	49061 NI	(1) 40W (Type R) or 60W (G type)	12	10	---	---	13	3.25	Ⓜ Ⓞ Dark sky compliant with use of R14, 40W bulb
B	49059 NI	(1) 40W (Type R) or 60W (G type)	8	7.5	---	---	9.5	2.75	Ⓜ Ⓞ Dark sky compliant with use of R14, 40W bulb
C	49062 NI	(1) 40W (Type R) or 60W (G type)	10	8	46	63	---	---	Ⓜ Ⓞ Dark sky compliant with use of R14, 40W bulb; Additional chain 4927 NI, stem 2999 (12") NI and/or stem 2997 (24") NI
D	49060 NI	(1) 40W (Type R) or 60W (G type)	10	9	---	---	11.5	3	Ⓜ Ⓞ Dark sky compliant with use of R14, 40W bulb
E	49063 NI	(1) 40W (Type R) or 60W (G type)	12	16	---	---	---	---	Ⓜ Ⓞ Dark sky compliant with use of R14, 40W bulb

Measurements shown in inches. U.S. Patent Pending: C, E

Seaside™

Black, Brushed Nickel, White,
Olde Brick®, Olde Bronze®

Incandescent | Energy Efficient

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.



A 11099 NI



B 9022 BK, NI, OB, OZ, WH



















C 9023 BK, NI, OB, OZ, WH



D 11098 NI

Aluminum
construction

	INCAND. ITEM	FLUOR. ITEM	FINISH	INCAND. BULB	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	---	11099 NI	NI	---	(1) 14W (GU24)    	10.5	14.5	12	9	  PBCFA14 decorative bulb incl.
B	9022	---	BK, NI, OB, OZ, WH	(1) 100W (M)	---	8	12	9	6	  G type lamp recommended
C	9023	---	BK, NI, OB, OZ, WH	(1) 150W (M)	---	10.5	14.5	11.5	8.75	  G type lamp recommended
D	---	11098 NI	NI	---	(1) 14W (GU24)    	8	12	9.5	6	  PBCFA14 decorative bulb incl.

Measurements shown in inches. U.S. Patent Design 383,239/Canada Patent Design 78917/Taiwan Patent Design ND-053495

Coordinating Landscape Lighting

See the complete line of Kichler® Landscape Lighting at LandscapeLighting.com



E 2621 NI, OB



F 310131 NI, OZ

Kichler® Patio Outdoor Ceiling Fan. See our full line of Ceiling Fans in the Kichler Ceiling Fan Catalog K810 or visit kichler.com.



G 9021 BK, NI, OB, OZ, WH



H 9044 NI, OB



J 9247 NI, OB



K 9923 NI, OB, OZ

	INCAND. ITEM	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	WIRE (CHAIN)	EXT.	HCWO	NOTES
E	2621	NI, OB	(1) 100W (M)	8	10	47	45°(12:12)	62	---	---	D LED (18-25W CFL) Add. stem 2999 (12") NI, OB and/or 2997 (24") NI, G type light rec.
F	310131	NI, OZ	---	---	---	---	---	---	---	---	W See our full line of Ceiling Fans at kichler.com
G	9021	BK, NI, OB, OZ, WH	(1) 60W (M)	6	7.5	---	---	---	6.5	2.25	W G type lamp recommended
H	9044	NI, OB	(1) 150W (M)	11	8	---	---	---	11.5	2.50	W G G type lamp recommended
J	9247	NI, OB	(1) 100W (M)	9	6.5	---	---	---	9.5	2.25	W
K	9923	NI, OB, OZ	(1) 100W (M)	10.5	15	---	---	---	---	---	W LED (23-30W CFL) G type lamp recommended

Measurements shown in inches. U.S. Patent Design 391,003/Canada Patent Design 78917/Taiwan Patent Design ND-053495: G Canada Patent Design 78917: J

BK Black

NI Brushed Nickel

OB Olde Brick®

OZ Olde Bronze®

WH White

KICHLER.COM

Chesapeake™

Black or White Finish and
Clear Beveled Glass Panels

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.

New Street™

Black or Tannery
Bronze® Finish and Clear
Seedy Glass Panels



A 9777 BK, WH



B 9774 BK, WH



C 9776 BK, WH



D 9977 BK, WH



E 9722 BK, TZ



F 9858 BK, TZ

Cast Aluminum
construction

INCAND. ITEM	FINISH	INCAND. BULB	W	H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9777 BK, WH	(3) 60W (C)	7.5	15.5	---	8.5	3.50	W
B	9774 BK, WH	(1) 60W (M)	6	10.5	---	6.5	2.50	W EOD (23-30W CFL)
C	9776 BK, WH	(1) 100W (M)	6.5	12.5	---	8	3.25	W EOD (23-30W CFL)
D	9977 BK, WH	(3) 60W (C)	7.5	17.5	---	---	---	W
E	9722 BK, TZ	(1) 100W (M)	6	13	---	8.5	4.25	W
F	9858 BK, TZ	(1) 100W (M)	7.5	16	112(36)	---	---	D Additional chain 4927 BK, TZ
	49255 BK, TZ, WH	(1) 100W (M)	7	17.5	---	8	14	W
	49256 BK, TZ, WH	(1) 100W (M)	7	18	---	---	---	W

Measurements shown in inches.

New Street™

Black, White, Olde Brick®,
Olde Bronze®, Polished Brass,
Stainless Steel or Tannery Bronze®
Finish and Clear Glass

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.

NAUTICAL

N



A 9611 BK



A 9611 OB



A 9611 OZ



A 9611 PB



A 9611 SS



A 9611 TZ



Clear Beveled
Glass

B 9816 OZ, SS



Clear Beveled
Glass

C 9618 OZ, PB, SS, WH



A 9611 WH



Clear Beveled
Glass

D 9401 PB

Aluminum,
Stainless Steel
or Solid Brass
construction

INCAND. ITEM	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A 9611	BK, OB, OZ, PB, SS, TZ, WH	(1) 60W (M)	5	8.5	6	3	W EOD (23-30W CFL)
B 9816	OZ, SS	(1) 75W (M)	8	8	---	---	D EOD (18-25W CFL)
C 9618	OZ, PB, SS, WH	(1) 100W (M)	5.5	10.5	6	3.25	W EOD (23-30W CFL)
D 9401	PB	(1) 60W (M)	5	13	5.5	8	W EOD (13-15W CFL)

Measurements shown in inches.

OB Olde Brick®

OZ Olde Bronze®

PB Polished Brass

SS Stainless Steel

TZ Tannery Bronze®

KICHLER.COM

New Street™

Black Finish and Clear Beveled Glass
or Tannery Bronze® Finish and
Clear Beveled Glass



A 49184 BK, TZ



B 49186 BK, TZ



C 9735 BK, TZ



D 9736 BK, TZ



E 49187 BK, TZ

Cast Aluminum
construction

	INCAND. ITEM	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49184	BK, TZ	(3) 60W (C)	13	26	12.5	11	W
B	49186	BK, TZ	(1) 100W (M)	10	19	9.5	8	W EOD (23-30W CFL)
C	9735	BK, TZ	(1) 100W (M)	8	15.5	8	6.25	W EOD (23-30W CFL)
D	9736	BK, TZ	(1) 100W (M)	8.5	22	8	15.25	W EOD (23-30W CFL)
E	49187	BK, TZ	(1) 100W (M)	10	18	---	---	W EOD (23-30W CFL)

Measurements shown in inches.



F 9835 BK, TZ



G 9886 BK, TZ



H 9794 BK, TZ



J 49183 BK, TZ



K 9935 BK, TZ

INCAND. ITEM	FINISH	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
F	9835 BK, TZ	(1) 100W (M)	8	13.5	87	25(72)	---	---	(23-30W CFL) Additional chain 4927 BK, TZ
G	9886 BK, TZ	(2) 40W (C)	12	7.5	---	---	---	---	
H	9794 BK, TZ	(1) 100W (M)	5	8.5	---	---	6	2.75	(23-30W CFL)
J	49183 BK, TZ	(1) 100W (M)	6.5	11	---	---	7	2.75	(23-30W CFL)
K	9935 BK, TZ	(1) 100W (M)	8	16	---	---	---	---	(23-30W CFL)

Measurements shown in inches.

New Street™

Black, Tannery Bronze® and
White Finishes

See pages 158-159 for our complete selection
of Posts and Pedestal Mount Adaptors.



A 9859 BK



A 9859 TZ



D 345 BK



B 365 BK



B 365 WH



D 345 TZ



C 1148 BK



C 1148 TZ



C 1148 WH



D 345 WH

INCAND. ITEM	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	9859 : BK, TZ	(1) 100W (M)	7.5	7.5	---	---	D ✓ EOD (9-13W CFL) Seedy Glass
B	365 : BK, WH	(1) 60W (M)	7.5	5	---	---	D ✖ EOD (9-13W CFL) Textured Clear Glass
C	1148 : BK, TZ, WH	(1) 75W (M)	4.5	7.5	6	2.25	W EOD (18-25W CFL) Clear Glass
D	345 : BK, TZ, WH	(2) 60W (M)	9.5	5.5	---	---	D ✖ EOD (9-13W CFL) Textured Clear Glass

Measurements shown in inches.

New Street™

Black or White Finishes

Polypropylene Lanterns

See pages 158-159 for our complete selection of Posts and Pedestal Mount Adaptors.

NAUTICAL

N



A 9302 BK



B 9901 BK



A 9302 WH



B 9901 WH



C 9320 BK



D 9322 BK



C 9320 WH



D 9322 WH



E 9312 BK



E 9312 WH

	INCAND. ITEM	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	9302	BK, WH	(1) 60W (M)	8	14.5	8.5	12	W 300D (13-15W CFL) Clear Beveled Acrylic Panels
B	9901	BK, WH	(1) 60W (M)	8	14	---	---	W 300D (13-15W CFL) Clear Beveled Acrylic Panels
C	9320	BK, WH	(1) 60W (M)	8.5	5	---	---	D Etched White Glass
D	9322	BK, WH	(2) 60W (M)	10.5	5.5	---	---	D ✓ Etched White Glass
E	9312	BK, WH	(1) 60W (M)	6	7.5	7	2.50	W White Glass

Measurements shown in inches.

BK Black

TZ Tannery Bronze®

WH White

Outdoor

Lens Accessories



9534 BK



9536 BK

9534 BK : Glass Lens
use with 9234, 9244

9536 BK : Glass Lens
use with 9236, 9246

Convert open top units to outdoor applications. Heat-resistant glass lens with black frame.

Brightness Control Accessories



9544 BK



9546 BK

9544 BK : Grooved Baffle
use with 9234, 9244

9546 BK : Grooved Baffle
use with 9236, 9246

Grooved black plastic baffles achieve low, even surface brightness.



A 6051 : AZ, WH



B 6052 : AZ, OB, WH



C 9246 : AZ, WH



D 9236 : AZ, WH



E 9234 : AZ, WH



F 9834 : AZ, WH



G 9244 : AZ, WH

INCAND. ITEM	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	6051 AZ, WH	(1) 120W (M) BR-40 or 150W (M) PAR 38	6	11.5	---	---	W Fixture can be wall or ceiling mounted.
B	6052 AZ, OB, WH	(2) 120W (M) BR-40 or 150W (M) PAR 38	6	11.5	---	---	W Fixture can be wall or ceiling mounted.
C	9246 AZ, WH	(2) 120W (M) BR-40	6	15	8.5	7.50	D EOD (23-30W CFL)
D	9236 AZ, WH	(1) 120W (M) BR-40	6	8	8.5	4	W C EOD (13-15W CFL)
E	9234 AZ, WH	(1) 65W (M) BR-30	4.5	7	7	3	W C EOD (13-15W CFL)
F	9834 AZ, WH	(1) 65W (M) BR-30	4.5	8.5	---	---	D EOD (23-30W CFL)
G	9244 AZ, WH	(2) 65W (M) BR-30	4.5	12	7	6	D EOD (13-15W CFL)

Energy Efficient Outdoor



A 10941 BK, WH



B 11029 BK, WH



C 10923 BK, TZ



D 11026 BK, WH



E 10622 BK, WH



F 11027 BK, WH



G 11028 BK, WH

	FLUOR. ITEM	FINISH	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	10941	BK, WH	(1) 18W (GU24)	8	10	4.5	4.25	White Acrylic Panels
B	11029	BK, WH	(1) 18W (GU24)	8.5	5	4.5	3	Frosted Ribbed Panels
C	10923	BK, TZ	(1) 13W (GU24)	5	9	6	2.75	Satin-Etched Glass
D	11026	BK, WH	(1) 18W (GU24)	8.5	5	---	---	Satin-Etched Glass
E	10622	BK, WH	(1) 18W (GU24)	10	5.5	5.5	5	Frosted Ribbed Glass
F	11027	BK, WH	(2) 18W (GU24)	10.5	5.5	---	---	Satin-Etched Glass
G	11028	BK, WH	(1) 18W (GU24)	11.5	5	---	---	Etched Acrylic Panels

Measurements shown in inches.

AZ Architectural Bronze®

BK Black

OB Olde Brick®

TZ Tannery Bronze®

WH White

KICHLER.COM

Dark Sky Accessories



Evening View of Outdoor Lantern without Dark Sky Panel Inserts



Evening View of Outdoor Lantern with Dark Sky Panel Inserts

Help fight light pollution with Kichler® Dark Sky Accessories. Made of lightweight, powder coated aluminum, our Dark Sky panels easily slide behind your light fixture's existing glass. During the day, your light fixture may look conventional. Yet, at night, the panels prevent light from passing through its glass – only to emit a subtle downlight from the fixture's open bottom.

All Fixtures shown on page 157 can be retrofitted with a Dark Sky Adaptor Panel. Panel Sets consists of enough panels to retrofit one fixture. Installation instructions are included.

While we believe these panels will work for most current laws, Dark Sky and Turtle Protection legislation may have specific parameters that need to be met for a municipality or region. It is advisable to review the legislation to ensure compliance is met with these product additions.

Dark Sky Panel Insert Sets

For Use with These Fixtures

4800 WH	9645 CV
4801 WH	9646 CV
4802 WH	9647 CV
4803 WH	9846 CV
4804 WH	9724 CV
4805 WH	9725 CV
4806 WH	9726 CV
4807 WH	9824 CV
4812 WH	9651 CV
4813 WH	9652 CV
4814 WH	9849 CV
4817 WH	9468 OZ
4818 WH	9469 OZ
4819 WH	9470 OZ
4819 WH	9868 OZ
4820 WH	9649 CV
4826 WH	9707 OZ
4826 WH	10907 OZ
4827 WH	9708 OZ
4827 WH	10908 OZ





9707 OZ
Mount Vernon
54



10907 OZ
Mount Vernon
56



9708 OZ
Mount Vernon
54



10908 OZ
Mount Vernon
56



9468 OZ
Astoria™
74



9469 OZ
Astoria™
74



9470 OZ
Astoria™
74



9868 OZ
Astoria™
75



9645 CV
Tularosa™
130



9646 CV
Tularosa™
130



9647 CV
Tularosa™
131



9846 CV
Tularosa™
131



9649 CV
Alameda™
128



9651 CV
Alameda™
128



9652 CV
Alameda™
128



9849 CV
Alameda™
129



9724 CV
La Mesa™
127



9725 CV
La Mesa™
127



9726 CV
La Mesa™
127



9824 CV
La Mesa™
127

Accessories

Decorative Lamp Posts

Cast Aluminum
construction



A 9506 TZ



B 9595 AGZ



C 9510 LD



D 9542 LD




E 9523 LD

Shown with Tournai™
Lantern 9565 LD p. 29

ITEM	FINISH	D	OVRL. W	H	NOTES
A	9506 : AZ, BA, BK, SS, TZ	3	---	84	Direct Burial Aluminum Post, SS uses 304 Stainless Steel
B	9595 : AGZ, AZ, BK, LZ, OB, OZ, TZ	3	---	84	Direct Burial Fluted Aluminum Post
C	9510 : BK, BST, LD, LZ, OB, OZ	3	13	72	Cast Aluminum Post, hardware incl. (J-bolts) for use at time of concrete base pour.
D	9542 : BK, BST, LD, LZ, OZ	3	13	96	Cast Aluminum Post, hardware incl. (J-bolts) for use at time of concrete base pour.
E	9523 : LD	4	13	96	Cast Aluminum Post, hardware incl. (J-bolts) for use at time of concrete base pour.

Measurements shown in inches.



Accessories

Pedestal Mount Adapters



Pedestal Mount Adapter
9530 BK Shown with Salisbury™
Lantern 9938 BK. See page 65

Cast Aluminum
construction

	ITEM	FINISH	OVRLL.			NOTES
			D	W	H	
F	9501	BK, WH	3	---	84	Direct Burial Aluminum Post with Ladder Rest
G	9502	AZ, BK	3	---	84	Direct Burial Aluminum Post with Ladder Rest and Internal Photocell (Repl. Internal Photocell 49950)
H	49904	AZ, BK, WH	4	---	84	Direct Burial Aluminum Post with Ladder Rest and External Photocell (Repl. External Photocell 49951)
J	49907	AZ, BK, WH	3	---	84	Direct Burial Aluminum Post with Ladder Rest, External Photocell and GCO (Replacement External Photocell 49951 or GCO 49952)
K	9530	BK, LZ, OB, OZ, PB, TZG, WH	7	---	4	Cast Aluminum Pedestal Mount (PB is Solid Cast Brass). Hardware not included
L	9551	BK, LD	9.5	---	9.5	Cast Aluminum Pedestal Mount. Hardware included (#10 Philips, SS wood screws)
M	9531	BK, LZ	8	---	9	Cast Aluminum Pedestal Mount. Hardware included (#10 Philips, SS wood screws)
	9505	AZ	3	---	84	Direct Burial Aluminum Post with Ladder Rest
	49914	AZ, BK	3	---	144	Direct Burial Aluminum Post
	49950	BK	---	---	---	Replacement Internal Photocell (Black Only)
	49951	BK	---	---	---	Replacement External Photocell (Black Only)
	49952	BK	---	---	---	Replacement GCO
	49953	AZ, BK, WH	---	---	---	Replacement Ladder Rest

Measurements shown in inches. Do not mount post to Pedestal Mount Adaptor. Fixtures assemble directly to Adaptor.

OB Olde Brick®	OZ Olde Bronze®	PB Polished Brass	TZ Tannery Bronze®	TZG TZ with Gold Accents	WH White
----------------	-----------------	-------------------	--------------------	--------------------------	----------



Lighting Tip

Outdoor living room

Decorate your outdoor space with the same attention to comfort, style and creativity as any other room. To make you feel more at home under the starry sky, complement your lighting with weather-resistant furniture, rugs, appliances and accessories.







OUTDOOR LIVING

Kichler® Outdoor Living Collections mirror decorative indoor lighting styles to create a smooth flow between the two spaces.


Similar to popular all-weather furnishings, fabrics and appliances, they comfortably and fashionably – bring the indoors out.

Symbol Guide

 D	DAMP	 T24	Title 24 Compliant
 W	WET		Lamp Included
	Dark Sky		Photocell Included
 ADA	ADA Compliant		Installation Requirements
	Hybrid		90° C. Wire Rated
	Hybrid Outdoor		75° C. Wire Rated
	Energy Star		

Outdoor Ceiling Fans

30" Canfield™ Outdoor/Indoor Ceiling Fan



A 300103 : OBB

300103 ADC
Adobe Cream™ Finish and Reversible Adobe Cream/Maple Blades

BSS
Brushed Stainless Steel™ Finish and Reversible Light Oak/Medium Oak Blades

300103 NI
Brushed Nickel Finish and Reversible Dark Maple/Marive Cherry Blades

300103 OBB
Oil Brushed Bronze™ Finish and Reversible Cherry/Walnut Blades


300103 SNW
Satin Natural White™ Finish and Satin Natural White™ Blades

300103 WH
White Powder Coat Finish and White Blades

30"

BLADE SWEEP

153 x 17mm Motor



HANGING MEASUREMENTS:
WITH 6" DOWNROD
A - 14" / B - 12" / C - 9.8"

Indoor/Outdoor

D

Adobe Cream

Cherry

Marive Cherry

Maple

Dark Maple

Light Oak

Medium Oak

Satin Natural White

Walnut


White

162

Nothing says "come sit a spell" better than the cool breeze of a Kichler ceiling fan. Outside or in, these moisture-resistant fans are designed to create an oasis of space on a covered porch, patio, pool-side area – anywhere you want to enjoy the weather in cool comfort. Engineered to withstand temperature extremes and run flawlessly.

- A** **BLADES** (5) Blades • 24° Blade Pitch • 30" Blade Sweep
DOWNRODS Includes 6" Downrod With 1" (O.D.)
PRIMARY CONTROL SYSTEM Pull Chain, 3 Speeds Forward and Reverse
DOWNLIGHT Optional Light Kit
LEAD WIRE 78"
LOW CEILING ADAPTABLE with Flush Mount Kit included
AIRFLOW 2,266 Cubic Ft. Per Minute on High • 47W on High.
AIRFLOW EFFICIENCY 48 Cubic Ft. Per Minute Per Watt on High.
Limited Lifetime Warranty. U.S. Patent Pending

Canfield™ Patio Outdoor Ceiling Fan



B 310192 : ADC

- 310192 ADC**
Adobe Cream™ Finish and Reversible Adobe Cream™/Maple Blades
- 310192 TZP**
Tannery Bronze® Finish with Reversible Cherry/Medium Walnut Blades
- 310192 WSP**
Weathered Steel Finish and Reversible Medium Walnut/Teak Blades
- 310192 WCP**
Weathered Copper Finish and Reversible Dark Walnut/Medium Walnut Blades

52"

BLADE SWEEP

172 x 20mm Motor

HANGING MEASUREMENTS:
WITH 4" DOWNROD
A - 13.45" / B - 10.70" / C - 12.60"

Indoor/Outdoor



Harbour Walk™ Patio Outdoor Ceiling Fan



Includes our new
CoolTouch™
Control System
U.S. Patent Pending

C 310102 : GST

- 310102 GST**
Galvanized Steel Finish with Fresnel Lens Glass and Reversible Medium Walnut/Cherry Blades
- 310102 TZP**
Tannery Bronze® Finish with Fresnel Lens Glass and Reversible Medium Walnut/Cherry Blades
- 310102 WCP**
Weathered Copper Finish with Fresnel Lens Glass and Reversible Light Walnut/Dark Walnut Blades


52"

BLADE SWEEP

188 x 20mm Motor

HANGING MEASUREMENTS:
WITH 8" DOWNROD
A - 19.50" / B - 13.00" / C - 15.90"

Indoor/Outdoor



B **BLADES** (5) Blades • 14° Blade Pitch • 52" Blade Sweep
DOWNRODS Includes 4" Downrod With 1" (O.D.)
PRIMARY CONTROL SYSTEM Pull Chain, 3 Speeds Forward and Reverse
DOWNLIGHT Optional Light Kit
LEAD WIRE 78"
LOW CEILING ADAPTABLE
AIRFLOW 6,151 Cubic Ft. Per Minute on High • 65 W on High.
AIRFLOW EFFICIENCY 94 Cubic Ft. Per Minute Per Watt on High.
Limited Lifetime Warranty. U.S. Patent Pending

C **BLADES** (4) Blades • 14° Blade Pitch • 52" Blade Sweep
DOWNRODS Includes 8" Downrod With 1" (O.D.)
PRIMARY CONTROL SYSTEM CoolTouch™ Control System, 3 Speeds Forward & Reverse
DOWNLIGHT Integrated. Uses (4) 40W Krypton T3 Lamps
LEAD WIRE 78"
LOW CEILING ADAPTABLE
AIRFLOW 6,049 Cubic Ft. Per Minute on High • 74W on High.
AIRFLOW EFFICIENCY 82 Cubic Ft. Per Minute Per Watt on High.
Limited Lifetime Warranty. U.S. Patent Pending

Aldrin™ Patio Outdoor Ceiling Fan



A 310127 :: TZP

Includes our new
CoolTouch™
Control System
U.S. Patent Pending



310127 TZP
Tannery Bronze® Finish with White Cased Opal Glass and Reversible Medium Walnut/Cherry Blades


310127 WCP
Weathered Copper Finish with White Cased Opal Glass and Reversible Dark Walnut/Light Walnut Blades

310127 WSP
Weathered Steel Finish with White Cased Opal Glass and Reversible Medium Walnut/Teak Blades

52"

BLADE SWEEP


188 x 15mm Motor



HANGING MEASUREMENTS:
WITH 4" DOWNROD
A - 15.75" / B - 10.25" / C - 12.00"

Indoor/Outdoor

W



Seaside™ Patio Outdoor Ceiling Fan



B 300103 :: NI


310131 NI
Brushed Nickel Finish with White Cased Opal Glass and Light Oak Blades

310131 OZ
Olde Bronze® Finish with White Cased Opal Glass and Walnut Blades

54"

BLADE SWEEP

188 x 20mm Motor



HANGING MEASUREMENTS:
WITH 6" DOWNROD
A - 19.00" / B - 10.00" / C - 15.00"
WITH 12" DOWNROD
A - 25.00" / B - 16.00" / C - 15.00"

Indoor/Outdoor

W



164

A **BLADES** (5) Blades • 14° Blade Pitch • 52" Blade Sweep
DOWNRODS Includes 4" Downrod With 1" (O.D.)
PRIMARY CONTROL SYSTEM CoolTouch™ Control System, 3 Speeds Forward & Reverse
DOWNLIGHT Integrated. Uses (2) 60W Krypton T3 Lamps
LEAD WIRE 78"
LOW CEILING ADAPTABLE
AIRFLOW 5,556 Cubic Ft. Per Minute on High • 66W on High.
AIRFLOW EFFICIENCY 84 Cubic Ft. Per Minute Per Watt on High.
Limited Lifetime Warranty. U.S. Patent Pending

B **BLADES** (4) Blades • 14° Blade Pitch • 54" Blade Sweep
DOWNRODS Includes 6" & 12" Downrod With 1" (O.D.)
PRIMARY CONTROL SYSTEM Pull Chain, 3 Speeds Forward and Reverse
DOWNLIGHT Integrated. Uses (1) GU24/18W CFL Lamp
LEAD WIRE 78"
AIRFLOW 6,790 Cubic Ft. Per Minute on High • 82W on High.
AIRFLOW EFFICIENCY 82 Cubic Ft. Per Minute Per Watt on High.
Limited Lifetime Warranty. U.S. Patent Pending

Hatteras Bay™ Patio Outdoor Ceiling Fan



Includes our new
CoolTouch™
Control System
U.S. Patent Pending



C 310101 :: TZP

310101 TZP
Tannery Bronze® Finish with Fresnel Lens Glass and Reversible Medium Walnut/Cherry Blades

310101 WCP
Weathered Copper Finish with Fresnel Lens Glass and Reversible Light Walnut/Dark Walnut Blades


44"
BLADE SWEEP

153 x 17mm Motor

HANGING MEASUREMENTS:
WITH 12" DOWNROD
A - 22.50" / B - 18.50" / C - 14.00"

Indoor/Outdoor

D



Sterling Manor™ Patio Outdoor Ceiling Fan



D 339520 :: TZP

339520 TZP
Tannery Bronze® Finish and Brown Blades

339520 WH
White Powder Coat Finish and White Blades


52"
BLADE SWEEP

153 x 15mm Motor

HANGING MEASUREMENTS:
WITH 4" DOWNROD
A - 12.25" / B - 10.25" / C - 11.00"

Indoor/Outdoor

W



C **BLADES** (5) Blades • 14° Blade Pitch • 44" Blade Sweep
DOWNRODS Includes 12" Downrod With 1" (O.D.)
PRIMARY CONTROL SYSTEM CoolTouch™ Control System, 3 Speeds Forward & Reverse
DOWNLIGHT Integrated. Uses (4) 40W Krypton T3 Lamps
LEAD WIRE 78"
LOW CEILING ADAPTABLE
AIRFLOW 4,299 Cubic Ft. Per Minute on High • 54W on High.
AIRFLOW EFFICIENCY 80 Cubic Ft. Per Minute Per Watt on High.
Limited Lifetime Warranty. U.S. Patent Pending

D **BLADES** (5) Blades • 11.5° Blade Pitch • 52" Blade Sweep
DOWNRODS Includes 4" Downrod With 1" (O.D.)
PRIMARY CONTROL SYSTEM Pull Chain, 3 Speeds Forward and Reverse
DOWNLIGHT Optional Light Kit
LEAD WIRE 78"
LOW CEILING ADAPTABLE Flush Mount Kit included
AIRFLOW 4,121 Cubic Ft. Per Minute on High • 52W on High.
AIRFLOW EFFICIENCY 79 Cubic Ft. Per Minute Per Watt on High.
Limited Lifetime Warranty. U.S. Patent Pending

Windham™ Indoor/Outdoor Ceiling Fan



A 300119 TZ

300119 NI
Brushed Nickel Finish with Satin-Etched Cased Opal Glass and Reversible Maple/Marive Cherry Blades

300119 OBB
OIL Brushed Bronze™ Finish with Citrine Glass and Reversible Walnut/Light Cherry Blades

300119 TZ
Tannery Bronze® Finish with Sunset Marble Glass and Reversible Light Cherry/Teak Blades

300119 WH
White Finish with Satin-Etched Cased Opal Glass and White Blades


52"
BLADE SWEEP

172 x 20mm Motor

HANGING MEASUREMENTS:
FLUSH MOUNT
A - 12.75" / B - 6.00" / C - 11.50"

Indoor/Outdoor

D



Outdoor Ceiling Fan Accessories

Cased Opal Glass

B 338050 TZP
With Opal-Etched Glass

Cased Opal Glass

C 380900 WSP

Cased Opal Glass

D 380901 WSP

Cased Opal Glass

E 380902 ADC


166

A **BLADES** (5) Blades • 14° Blade Pitch • 52" Blade Sweep
DOWNRODS Flush Mount
PRIMARY CONTROL SYSTEM Pull Chain, 3 Speeds Forward & Reverse
DOWNLIGHT Integrated. Used (3) 40W B-10 Lamps
LEAD WIRE 8"

AIRFLOW 5,058 Cubic Ft. Per Minute on High • 62W on High.
AIRFLOW EFFICIENCY 82 Cubic Ft. Per Minute Per Watt on High.
Limited Lifetime Warranty. U.S. Patent Pending

	FLUOR. ITEM	FINISH	FLUOR. BULB	W	H	
B	338050	TZP, WH	(2) E-26 13W CFL	10	5.5	W
C	380900	TZP, WCP, WSP	(2) 1C 22W CFL	10	5.5	W
D	380901	TZP, WCP, WSP	(2) E-26 13W CFL	10	5.5	W
E	380902	ADC, TZP, WCP, WSP	(2) GU24 13W CFL	10	5.5	W

Outdoor Chandeliers



A 15408 Low Voltage Chandelier : BKT

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	NOTES
A	15408 BKT	(6) 11.6W (12V T-5)	26.5	21.5	95.5	20(72)	On-Off pull switch, 25' of 12/2 Cable included, Transformer not included, Light Umber Glass

Measurements shown in inches. U.S. Patent Pending

Low Voltage Chandeliers



Beige Candle with Clear Top Drip Trim

A 15402 Low Voltage Chandelier : OZ



Textured Amber Seedy Glass

168

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	NOTES
A	15402 OZ	(8) 11.6W (12V T-5)	26	23	61	6	25' of 12/2 Cable included, Transformer not included, 6.5W bulb included.
B	15409 OZ	(4) 16.25W (12V T-5)	25	14.5	52.5	10	On/Off pull switch, 25' of 12/2 Cable included, Transformer not included.

Measurements shown in inches. U.S. Patent Pending

Alameda™

Canyon View™ Finish and
Honey Opalescent Glass Panels



A 49092 Indoor/Outdoor Chandelier CV



B 9147 Wall Sconce CV



C 9849 Pendant CV



D 49090 Indoor/Outdoor Chandelier CV



E 49091 Indoor/Outdoor Chandelier CV

Solid Brass
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	L	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	49092 CV	(6) 100W (M)	20	20	58	36	56	---	---	D 23-30W CFL Additional chain 4908 CV and/or stem 2999 (12") CV
B	9147 CV	(1) 100W (M)	9	10	---	---	---	5.5	4	W 23-30W CFL
C	9849 CV	(1) 100W (M)	7	11.5	85	---	28(72)	---	---	D 23-30W CFL Additional chain 4927 CV
D	49090 CV	(3) 100W (M)	6	20	58	36	56	---	---	D 23-30W CFL Additional chain 2996 CV and/or stem 2999 (12") CV
E	49091 CV	(4) 100W (M)	25	17	55	---	59	---	---	D 18-25W CFL Additional chain 2996 CV and/or stem 2999 (12") CV

Measurements shown in inches. Complete selection of Dark Sky adapter panels for: C on pages 612-613

BKT Textured
Black

CV Canyon
View®

OZ Olde
Bronze®

Meredith™

Distressed Black Finish and
Sunset Marble Glass



A 9334 DBK



B 9335 DBK




C 9336 DBK



D 9833 DBK

Aluminum
construction

Olympia™ Exterience™



Swirled Opalescent
Glass Sides with
Tempered Glass Top

E 9673 TG



F 9674 TG

Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9334 DBK	(1) 100W (M)	6	18	---	---	7	6.75	W EOD (23-30W CFL)
B	9335 DBK	(1) 150W (M)	7.5	24	---	---	9	8.50	W EOD (23-30W CFL)
C	9336 DBK	(1) 150W (M)	9.5	30	---	---	11	10	W EOD (23-30W CFL)
D	9833 DBK	(6) 100W (M)	26	31	105	41(72)	---	---	D EOD (23-30W CFL) Additional chain 4927 DBK
E	9673 TG	(2) 100W (M)	8.5	22	---	---	9.5	11.50	W EOD (23-30W CFL)
F	9674 TG	(4) 100W (M)	10.5	34	---	---	11	---	W I EOD (23-30W CFL) Junction Box 12.25"-22.25", Fixture includes variable height mounting hardware

Measurements shown in inches. U.S. Patent Pending

High Country™

Olde Iron Finish and
Umber Alabaster Swirl Glass



A 9818 OI



B 9273 OI



C 9275 OI



D 9274 OI

Aluminum
construction

	INCAND. ITEM	INCAND. BULB	W	H	OVRL. H	WIRE (CHAIN)	EXT.	HCWO	NOTES
A	9818 OI	(5) 40W (M)	25	29.5	100.5	65(72)	---	---	D OD (9-13W CFL) Additional chain 4927 OI
B	9273 OI	(1) 40W (M)	5.5	19	---	---	7.5	12	W Torpedo shape bulb required
C	9275 OI	(1) 150W (M)	9.5	32.5	---	---	12	20.75	W OD (23-30W CFL)
D	9274 OI	(1) 100W (M)	7.5	24	---	---	10	15	W OD (23-30W CFL)

Measurements shown in inches. U.S. Patent Pending

DBK Distressed Black

OI Olde Iron

Outdoor Living Spaces

Outdoor Table & Floor Lamps



B 70377
Table Lamp



A 74165
Floor Lamp



D 70557
Table Lamp



C 74199
Floor Lamp



E 74212
Floor Lamp



F 70604
Table Lamp



G 70506
Table Lamp




H 70504
Table Lamp

	INCAND. ITEM	INCAND. BULB	H	NOTES
A	70377	(1) 100W	30.5	Ⓜ Brown Bark Finish and Oyster Textured Sunbrella® fabric, removable shade: 9" x 11" x 10". On-off toggle switch.
B	74165	(1) 100W	59.5	Ⓜ Brown Bark Finish and Oyster Textured Sunbrella® fabric, removable shade: 12" x 15" x 11". On-off toggle switch.
C	70557	(1) 100W	31	Ⓜ Brown Bark Finish and Basil Green Textured Sunbrella® fabric, removable shade: 10" x 15" x 11". On-off toggle switch.
D	74199	(1) 100W	60.5	Ⓜ Brown Bark Finish and Basil Green Textured Sunbrella® fabric, removable shade: 15" x 20" x 13.75". On-off toggle switch.
E	70604	(1) 100W	31	Ⓜ Aged Bronze Finish and Linen Sunbrella® fabric, removable shade: 11" x 16" x 12". On-off toggle switch.
F	74212	(1) 100W	60.5	Ⓜ Aged Bronze Finish and Linen Sunbrella® fabric, removable shade: 14" x 17" x 12". On-off toggle switch.
G	70506	(1) 100W	32	Ⓜ Distressed Black Finish with Burnished Copper Accents and Sedona™ Textured Sunbrella® fabric, removable shade: 12.5" x 14" x 12". On-off toggle switch.
H	70504	(1) 100W	31	Ⓜ Distressed Black Finish with Burnished Copper Accents and Sedona Textured Sunbrella® fabric, removable rectangular shade: 6" x 12" x 10" x 18" x 10". On-off toggle switch.

Light Bulb Reference

Incandescent and Compact Fluorescent Light Bulbs



Compact Fluorescent Bulbs (CFL)



Look for this symbol throughout our catalog. This symbol indicates the products best suited for Indoor use with self-ballasted, compact fluorescent lamps sold through electrical distributors and lighting showrooms across the U.S.



This symbol indicates the product best suited for Outdoor use with self-ballasted, compact fluorescent lamps sold through electrical distributors and lighting showrooms across the U.S.





If a light fixture is connected to a dimmer or 3-way switch, you'll need to use a qualified CFL designed to work in these applications. Make sure to look for CFLs that specify use with dimmers or 3-way switches.






Equivalent Light Output

To determine which qualified CFL light bulbs will provide the same amount of light as your current incandescent light bulbs, consult the following chart:

Incandescent Light Bulbs Watts (W)	Incandescent Minimum Light Output Lumens	Common CFL Light Bulbs Watts (W)
40	450	9-13
60	800	13-15
75	1,100	18-25
100	1,600	23-30
150	2,600	30-52

Fluorescent Lamps

Product ID	Description	
4013	Replacement Ballast	
4014	Replacement Lamp	
4020	Replacement Lamp, PLS 13, G24q-1 Base	
4021	Replacement Lamp, PLS 18, G24q-2 Base	
4023	Replacement Lamp, PLT 13, G24q-1 Base	
4024	Replacement Lamp, PLT 18, G24q-2 Base	
4025	Replacement Lamp, PLC 13, G24q-1 Base	
4026	Replacement Lamp, PLC 18, G24q-2 Base	
4027	Replacement Lamp, PLA 13, G24q-1 Base	
4037	Replacement Lamp, PLG 18, G24q-2 Base	



Product ID	Description	
4028	Replacement Lamp, 2C T6 40W, G10q Base	
4029	Replacement Lamp, 2C T6 55W, G10q Base	
4030	Replacement Lamp, 2C T6 70W, G10q Base	
4031	Replacement Ballast, SU13, G24q-1 Base	
4032	Replacement Ballast, SU18, G24q-2 Base	
4034	Replacement Ballast, 40W circline, G10q Base	
4035	Replacement Ballast, 55W circline, G10q Base	
4036	Replacement Ballast, 70W circline, G10q Base	
4043	Replacement Lamp, PBCFS1350, 13W, GU24	
4044	Replacement Lamp, PBCFS1850, 18W, GU24	
4045	Replacement Lamp, PBCFS2670, 26W, GU24	

Halogen Lamps

Product ID	Description
5901 CLR	Clear 50W T-3 Double Contact, Bayonet Base, Tungsten (Suitable for use with all Kichler lights requiring Halogen Lamps)
5902 FST	Frosted 50W GU10 Halogen Lamp
5903 CLR	Clear 100W T-3 Mini-Can Base, Tungsten Halogen Lamp
5904 CLR	Clear 20W T-3 Candelabra Based Krypton Lamp
5904 FST	Frosted 20W T-3 Candelabra Based Krypton Lamp
5905 CLR	Clear 60W T-3 Candelabra Based Krypton Lamp

Product ID	Description
5905 FST	Frosted 60W T-3 Candelabra Based Krypton Lamp
5907 CLR	Clear 40W T-3 Candelabra Based Krypton Lamp
5907 FST	Frosted 40W T-3 Candelabra Based Krypton Lamp
5908 FST	Frosted 60W G9 Halogen Lamp
5909	50W MR16 Shielded GU10 Lamp
5910 CLR	Clear 75W T-3 Mini-Can Base, Tungsten Halogen Lamp

Legend / Symbol Guide

-  = This symbol indicates the product best suited for Indoor use with self-ballasted, compact fluorescent lamps sold through electrical distributors and lighting showrooms across the U.S.
-  = This symbol indicates the product best suited for Outdoor use with self-ballasted, compact fluorescent lamps sold through electrical distributors and lighting showrooms across the U.S.
- (C) = Candelabra based lamp (E-12).
- (C/K) = Candelabra based lamp (E-12) or Krypton candelabra based lamps.
- (K) = Krypton candelabra based lamps.
- (M) = Medium based lamp (E-26).
- (MNCN) = Mini-can based halogen lamps.
- ✓ = Fixture requires supply wire rated for at least 75° C.
- ❖ = Fixture requires supply wire rated for at least 90° C.
- ☆ = When electrical connection is made inside the fixture, supply wire must be rated at least 75° C. When electrical connection is made in an outlet box, supply wire must be rated at least 60° C.
- ⓘ = Installation Instructions: Fixture must be supported independently of the outlet box unless the outlet box is UL listed for the weight to be supported. Consult a qualified electrician/installer. Required installation parts included.
- D = Diameter
- Ext. = Extension
- Fluor. = Fluorescent
- H = Height

HCWO = Height from Center of Wall Opening

Incand. = Incandescent

L = Length

Ovrl. H = Overall Height

W = Width

Wire (Chain) = Wire in excess of chain length.
Example: 19(72) = 19" of extra wire with 72" chain





= Many of the products in this catalog have the ENERGY STAR® logo. This identifies lighting that uses 2/3 less energy than conventional lighting and lasts 6- to 10-times longer. For more information, visit www.energystar.gov.




= Title 24 is a document that contains the building codes for the state of California. All lighting fixtures in this catalog that comply with the August 1, 2009 revision of the California Title 24 standards are marked with the T24 logo. For more information, visit www.energy.ca.gov/title24.

 = ADA Compliant

 = DAMP

 = Dark Sky Compliant

 = Lamp Included

 = Photocell Included

 = WET

- Bulbs not included unless otherwise noted.
- Wattages stated are the maximum recommended, however, you may use lower wattage lamps to suit your lighting needs. Some recommended lamps are not available in the maximum allowable wattage.
- All electrical products are rated as 120-volt, AC unless otherwise noted.
- All electrical products are certified and listed to UL/CSA/ETL Standards for use in U.S.A. and Canada except where noted.
- All products featured in the outdoor section are certified and listed to UL/CSA standards for wet location except where noted.
- All chain drop products equipped with at least 72" of chain.
- Many long life tungsten halogen capsule lamps are now available as alternates to conventional incandescent light bulbs. The halogen capsule lamps may be used to replace any lamp of a higher wattage, but not to exceed the existing specified maximum wattage, i.e., 72W may replace a 75W.
- On some products, in order to accommodate higher than normal ceiling height, extra lead wire is supplied and specified. With additional sections of chain (not included), this allows an added measure of design flexibility.
- Finishes for fixtures installed outdoors are subject to change due to prolonged exposure to sunlight, airborne pollutants and other forms of weathering.
- To serve you better, Kichler® Lighting reserves the right to make improvements to the products in this catalog. Therefore, some products may change during the life of the catalog and the product information contained in this catalog may also have changed.

Abbreviation Key

AB	Antique Brass	BS	Burnished Silver	GNT	Granite	OB	Olde Brick®	RZ	Rubbed Bronze
ABZ	Antique Bronze	BSG	Burnished Silver and Gold	GST	Galvanized Steel	OBZ	Oil Brushed Bronze™	SC	Stucco White
ACK	Antique Crackle™	BST	Brown Stone	HB	Heritage Bronze	OI	Olde Iron	SCK	Seine Crackle™
ADC	Adobe Cream™	BZ	Bronze	LBZ	Lincoln Bronze™	OLZ	Oiled Bronze	SEG	Satin-Etched Glass
AGZ	Aged Bronze	CH	Chrome	LD	Londonderry	OMC	Olde Mill Copper™	SGE	Sage
AP	Antique Pewter	CMB	Cambridge	LED	Light Emitting Diode	OZ	Olde Bronze®	SS	Stainless Steel
AVI	Anvil Iron	CSH	Cashmere™	LZ	Legacy Bronze™	OZU	Olde Bronze® with Umber Glass	SWZ	Shadow Bronze
AZ	Architectural Bronze®	CST	Canyon Slate™	LZG	Legacy Bronze™ with Gold Accents	PB	Polished Brass	SZ	Sedona Bronze™
BA	Brushed Aluminum	CTZ	Colton Bronze™	MBZ	Marbled Bronze	PBC	Polished Brass with Chrome	TRZ	Terrene Bronze
BAB	Burnished Antique Brass	CV	Canyon View™	MCH	Midnight Chrome	PN	Polished Nickel	TZ	Tannery Bronze®
BBZ	Burnished Bronze™	CZ	Carré Bronze®	MIZ	Mission Bronze™	PPW	Polished Pewter	TZG	Tannery Bronze® with Gold
BGN	Burnished Granite™	DBK	Distressed Black	MPC	Mottled Pecan™	PR	Prairie Rock™	TZP	Tannery Bronze® with Polished Brass Accents
BH	Buckhorn™	DBR	Distressed Brass	MUL	Multicolor	PRZ	Parisian Bronze™	VNB	Vintage Natural Brass
BK	Black	DCO	Distressed Copper	NCH	Nickel & Chrome	PZ	Patina Bronze	WBR	Wispy Brûlée™
BKG	Black with Gold Highlights	DZ	Dore Bronze™	NI	Brushed Nickel	RNX	Rubbed Onyx	WCP	Weathered Copper
BKZ	Berkshire Bronze™	FDS	Feldspar™	NIA	Brushed Nickel and Alabaster Swirl Glass	RST	Rustic™	WSP	Weathered Steel
BPT	Brushed Pewter	FZ	Franciscan Bronze™	OAU	Olde Auburn™	RVN	Ravenna™	WH	White
BRL	Brûlée™	GBR	Golden Brûlée™						
BRZ	Brushed Bronze	GD	Gold						

Standard Gauge Chain

Chain may be ordered in 3' lengths to supplement existing chain supplied with Kichler fixtures. To order additional chain, look for the chain recommendations listed for fixtures requiring chain.

- 2979 PB** Polished Brass (LifeBrite™)
- 2996 NI** Brushed Nickel
- 2996 OZ** Olde Bronze®

Outdoor Solid Brass Chain

- 4927 ACK** Antique Crackle™
- 4927 AGZ** Aged Bronze
- 4927 AVI** Anvil Iron
- 4927 AZ** Architectural Bronze®
- 4927 BK** Black
- 4927 BKG** Black with Gold Highlights
- 4927 BRZ** Brushed Bronze
- 4927 BST** Brown Stone
- 4927 CMB** Cambridge
- 4927 CV** Canyon View™
- 4927 DBK** Distressed Black
- 4927 DBR** Distressed Brass
- 4927 DCO** Distressed Copper
- 4927 GNT** Granite
- 4927 LD** Londonderry™
- 4927 LZ** Legacy Bronze™
- 4927 LZG** Legacy Bronze™ with Gold
- 4927 OB** Olde Brick®
- 4927 OI** Olde Iron
- 4927 OLZ** Oiled Bronze
- 4927 OZ** Olde Bronze®
- 4927 PR** Prairie Rock™
- 4927 RNX** Rubbed Onyx
- 4927 RST** Rustic™
- 4927 RZ** Rubbed Bronze
- 4927 SGE** Sage
- 4927 SS** Stainless Steel
- 4927 TZ** Tannery Bronze®
- 4927 TZG** Tannery Bronze® with Gold

Stem Segments

To increase the fixture overall length to a maximum of 5-stem segments you may order:

- 12" Length**
- 2999 AGZ** Aged Bronze
 - 2999 NI** Brushed Nickel
 - 2999 OZ** Olde Bronze®
 - 4938 AGZ** Aged Bronze

- 24" Length**
- 2997 NI** Brushed Nickel

345 BK	152	9041 BK	64	9291 LZ	41	9528 OZ	98
345 TZ	152	9041 RZ	62	9292 LZ	40	9529 AGZ	123
345 WH	152	9042 BK	65	9293 LZ	40	9532 RZ	51
365 BK	152	9042 RZ	62	9294 LZ	40	9533 RZ	51
365 WH	152	9043 BK	64	9302 BK	153	9537 PB	47
1148 BK	152	9043 RZ	62	9302 WH	153	9538 RZ	51
1148 TZ	152	9044 NI	147	9303 DCO	141	9539 RZ	51
1148 WH	152	9044 OB	147	9304 DCO	141	9547 OZ	42
2621 NI	147	9051 AGZ	117	9305 DCO	141	9554 AGZ	117
2621 OB	147	9052 AGZ	116	9306 DCO	141	9555 AGZ	117
3327 AGZ	119	9053 AGZ	116	9312 BK	153	9556 AGZ	105
6040 AZ	102	9054 AGZ	116	9312 WH	153	9557 AGZ	105
6040 NI	102	9057 AGZ	105	9320 BK	153	9558 LD	29
6051 AZ	154	9058 AGZ	105	9320 WH	153	9559 LD	29
6051 WH	154	9059 AGZ	105	9322 BK	153	9562 TZG	52
6052 AZ	154	9061 TZG	52	9322 WH	153	9564 LD	27
6052 OB	154	9062 TZG	52	9334 DBK	170	9565 LD	29
6052 WH	154	9064 TZG	52	9335 DBK	170	9567 AZ	80
7002 AZ	80	9065 TZG	52	9336 DBK	170	9567 GNT	81
7002 GNT	81	9072 BBZ	43	9346 OZ	42	9569 OZ	75
9010 LZ	133	9073 BBZ	43	9347 OZ	42	9572 BBZ	43
9011 LZ	132	9074 BBZ	43	9348 OZ	42	9585 TZG	57
9012 LZ	132	9094 AZ	100	9349 OZ	42	9596 PB	47
9013 LZ	133	9095 AZ	100	9351 AGZ	136	9611 BK	149
9014 LZ	132	9100 AZT	104	9352 AGZ	136	9611 OB	149
9015 LZ	132	9101 AZT	104	9353 AGZ	137	9611 OZ	149
9016 LZ	133	9109 BA	102	9354 AGZ	136	9611 PB	149
9017 DBK	58	9109 BK	102	9355 LD	28	9611 SS	149
9018 DBK	58	9110 BA	102	9356 LD	28	9611 TZ	149
9019 DBK	58	9110 BK	102	9357 LD	27	9611 WH	149
9020 DBK	58	9124 AGZ	78	9358 LD	28	9618 OZ	149
9021 BK	147	9126 AGZ	78	9359 LD	28	9618 PB	149
9021 NI	147	9128 AGZ	122	9360 LD	27	9618 SS	149
9021 OB	147	9129 AGZ	122	9362 LD	26	9618 WH	149
9021 OZ	147	9130 AGZ	122	9364 AGZ	118	9631 OZ	44
9021 WH	147	9131 AGZ	123	9365 AGZ	118	9645 CV	130
9022 BK	146	9132 AGZ	123	9366 AGZ	119	9646 CV	130
9022 NI	146	9143 CV	128	9367 AGZ	118	9647 CV	131
9022 OB	146	9147 CV	128, 169	9368 CMB	53	9649 CV	128
9022 OZ	146	9148 CV	128	9369 CMB	53	9650 BK	71
9022 WH	146	9150 CV	128	9370 CMB	53	9650 TZ	71
9023 BK	146	9166 AZ	80	9371 CMB	53	9650 WH	71
9023 NI	146	9166 GNT	81	9372 CMB	53	9651 CV	128
9023 OB	146	9167 AZ	80	9401 PB	149	9652 CV	128
9023 OZ	146	9167 GNT	81	9407 OB	140	9653 BK	71
9023 WH	146	9168 AZ	80	9408 OB	140	9653 TZ	71
9024 DCO	124	9168 GNT	81	9409 PB	46	9653 WH	71
9025 DCO	124	9183 TZG	57	9412 OZ	45	9654 BK	71
9026 DCO	124	9184 TZG	57	9427 OZ	98	9654 TZ	71
9027 DCO	124	9185 TZG	57	9428 OZ	98	9654 WH	71
9028 BK	69	9186 TZG	57	9429 OZ	98	9655 BK	71
9028 TZ	68	9203 AZT	104	9430 OZ	98	9655 TZ	71
9029 BK	69	9234 AZ	154	9439 PB	46	9655 WH	71
9029 TZ	68	9234 WH	154	9452 OZ	45	9656 AGZ	122
9030 BK	69	9236 AZ	154	9468 OZ	74	9670 AZ	99
9030 TZ	68	9236 WH	154	9469 OZ	74	9671 NI	103
9031 DCO	125	9244 AZ	154	9470 OZ	74	9671 OZ	103
9032 RZ	51	9244 WH	154	9477 OB	140	9672 AZ	99
9033 RZ	50	9246 AZ	154	9478 OB	140	9673 TG	170
9034 RZ	50	9246 WH	154	9479 OB	140	9674 TG	170
9035 RZ	50	9247 NI	147	9489 PB	46	9676 OZ	44
9036 PB	47	9247 OB	147	9492 OZ	45	9677 OZ	44
9037 PB	47	9250 BK	59	9511 PR	83	9700 NI	103
9038 PB	47	9251 BK	59	9513 PB	48	9700 OZ	103
9039 BK	65	9252 BK	59	9514 LZ	133	9703 OB	55
9039 RZ	63	9273 OI	171	9519 TZG	57	9703 OZ	54
9040 BK	64	9274 OI	171	9525 AGZ	78	9704 OB	55
9040 RZ	63	9275 OI	171	9527 AGZ	123	9704 OZ	54

9707 OB	55	9813 DCO	141	9909 OB	55	49030 BST	36	49125 AVI	111	49186 TZ	150
9707 OZ	54	9814 LZ	133	9909 OZ	54	49031 BST	36	49126 OZ	142	49187 BK	150
9708 OB	55	9815 LZ	133	9911 PR	83	49032 BST	36	49127 OZ	142	49187 TZ	150
9708 OZ	54	9816 OZ	149	9913 PB	48	49033 BST	37	49128 OZ	142	49188 BK	67
9709 OB	55	9816 SS	149	9918 BK	69	49034 BST	37	49129 OZ	142	49188 TZ	67
9709 OZ	54	9817 AP	99	9918 TZ	68	49035 BST	37	49130 BKG	25	49200 BK	92
9711 PB	48	9817 OZ	99	9919 DBK	58	49036 AGZ	113	49130 BRZ	23	49201 BK	92
9712 PB	48	9818 OI	171	9920 DCO	125	49037 AZ	76	49131 BKG	25	49202 BK	92
9713 PB	48	9824 CV	127	9923 NI	147	49038 AZ	76	49131 BRZ	23	49203 BK	92
9714 NI	103	9825 CV	127, 129	9923 OB	147	49039 AZ	76	49132 BKG	24	49204 BK	93
9714 OZ	103	9826 TZG	52	9923 OZ	147	49040 AZ	77	49132 BRZ	22	49205 BK	93
9718 PR	82	9827 AGZ	119	9925 AGZ	78	49041 AZ	77	49133 BKG	25	49206 BK	93
9719 PR	82	9829 AGZ	123	9926 CV	127	49042 AZ	77	49133 BRZ	23	49207 BK	93
9720 PR	82	9830 AGZ	122	9931 OZ	44	49049 OI	112	49134 BKG	25	49214 AVI	84
9721 PR	82	9831 OZ	44	9932 OZ	45	49059 NI	145	49134 BRZ	23	49215 AVI	84
9722 BK	148	9832 OZ	45	9935 BK	151	49059 OZ	144	49135 BKG	24	49216 AVI	85
9722 TZ	148	9833 DBK	170	9935 TZ	151	49060 NI	145	49135 BRZ	22	49217 AVI	84
9724 CV	126	9834 AZ	154	9938 BK	65	49060 OZ	144	49136 BKG	25	49218 AVI	85
9725 CV	127	9834 WH	154	9938 RZ	63	49061 NI	145	49136 BRZ	23	49219 AVI	85
9726 CV	126	9835 BK	151	9940 BK	65	49061 OZ	144	49137 OZ	115	49220 AVI	85
9735 BK	150	9835 TZ	151	9940 RZ	63	49062 NI	145	49138 OZ	114	49226 OZ	21
9735 TZ	150	9837 DCO	125	9945 CV	131	49062 OZ	144	49139 OZ	114	49227 OZ	21
9736 BK	150	9838 DCO	125	9949 BK	59	49063 NI	145	49140 OZ	114	49228 OZ	20
9736 TZ	150	9843 BK	65	9951 BK	59	49063 OZ	144	49141 OZ	115	49229 OZ	20
9757 LZ	41	9843 RZ	63	9953 CV	129	49071 BST	79	49142 OZ	115	49231 OZ	21
9759 RST	143	9845 CV	130	9954 AGZ	137	49072 BST	79	49143 OZ	115	49232 OZ	21
9760 RST	143	9846 CV	131	9955 AGZ	117	49073 BST	79	49144 OZ	115	49240 LZ	134
9761 RST	143	9847 OZ	42	9956 BK	71	49074 BST	79	49146 AGZ	120	49241 LZ	134
9762 RST	143	9848 BK	65	9956 TZ	71	49075 BST	79	49147 AGZ	120	49242 LZ	134
9767 LZ	41	9848 RZ	63	9956 WH	71	49076 OI	112	49148 AGZ	120	49243 LZ	134
9774 BK	148	9849 CV	129, 169	9959 AGZ	105	49077 OI	112	49150 AGZ	121	49244 LZ	134
9774 WH	148	9850 BK	71	9962 RST	143	49078 OI	112	49152 AGZ	121	49248 AGZ	16
9776 BK	148	9850 TZ	71	9967 AZ	80	49080 OI	112	49153 AGZ	121	49249 AGZ	16
9776 WH	148	9850 WH	71	9967 GNT	81	49083 NI	96	49157 OZ	86	49255 BK	148
9777 BK	148	9851 BK	59	9975 AGZ	119	49084 NI	96	49157 SS	88	49255 TZ	148
9777 WH	148	9852 AGZ	137	9977 BK	148	49085 NI	96	49158 OZ	86	49255 WH	148
9783 AP	60	9854 LD	26	9977 WH	148	49086 NI	97	49158 SS	88	49256 BK	148
9783 OZ	61	9855 LD	26	9979 OB	140	49087 NI	97	49159 OZ	86	49256 TZ	148
9784 AP	60	9858 BK	148	9985 AP	60	49088 NI	97	49159 SS	88	49256 WH	148
9784 OZ	61	9858 TZ	148	9985 OZ	61	49089 NI	97	49160 OZ	86		
9785 AP	60	9859 BK	69, 152	9989 PB	46	49090 CV	128	49160 SS	88		
9785 OZ	61	9859 TZ	68, 152	9992 BK	67	49090 CV	169	49161 OZ	87		
9786 OZ	61	9867 AGZ	119	9992 TZ	67	49091 CV	129	49161 SS	89		
9788 BK	67	9868 OZ	75	9994 LZ	41	49091 CV	169	49162 OZ	87		
9788 TZ	67	9869 OZ	98	9996 PB	47	49092 CV	129	49162 SS	89		
9789 BK	66	9870 RST	143	49001 RZ	32	49092 CV	169	49163 OZ	87		
9789 TZ	66	9871 BBZ	43	49002 RZ	32	49100 RZ	38	49163 SS	89		
9790 BK	66	9872 BBZ	43	49003 RZ	32	49101 RZ	38	49164 OZ	87		
9790 TZ	66	9873 OZ	75	49004 RZ	32	49102 RZ	38	49164 SS	89		
9791 BK	66	9881 CMB	53	49005 RZ	32	49103 RZ	38	49166 AGZ	135		
9791 TZ	66	9885 OZ	61	49009 BST	30	49104 RZ	39	49167 AGZ	135		
9794 BK	151	9886 BK	67, 151	49010 BST	31	49105 RZ	39	49168 AGZ	135		
9794 TZ	151	9886 TZ	67	49011 BST	30	49106 RZ	39	49170 AGZ	135		
9800 OZ	98	9886 TZ	151	49012 BST	30	49107 RZ	39	49174 OZ	108		
9802 AGZ	137	9889 PB	46	49013 BST	31	49108 RZ	39	49175 OZ	109		
9804 OB	55	9891 LZ	41	49014 BST	31	49110 AVI	94	49176 OZ	108		
9804 OZ	54	9892 BK	67	49015 BST	31	49111 AVI	95	49177 OZ	108		
9805 BK	71	9892 TZ	67	49017 BST	35	49112 AVI	94	49178 OZ	109		
9805 TZ	71	9894 LZ	41	49018 BST	35	49113 AVI	94	49179 OZ	109		
9805 WH	71	9895 TZG	57	49019 BST	34	49114 AVI	95	49180 OZ	109		
9806 TZG	52	9898 CMB	53	49020 BST	34	49115 AVI	95	49181 OZ	109		
9808 DBK	58	9900 NI	103	49021 BST	35	49116 AVI	95	49183 BK	151		
9809 OB	55	9900 OZ	103	49022 BST	35	49119 AVI	110	49183 TZ	151		
9809 OZ	54	9901 BK	153	49023 BST	34	49120 AVI	110	49184 BK	150		
9810 BK	69	9901 WH	153	49026 AGZ	113	49121 AVI	111	49184 TZ	150		
9810 TZ	68	9902 PR	83	49027 AGZ	113	49122 AVI	110	49185 BK	66		
9811 PR	83	9905 DCO	141	49028 AGZ	113	49123 AVI	111	49185 TZ	66		
9812 DCO	141	9908 OB	140	49029 BST	37	49124 AVI	111	49186 BK	150		

Outdoor Living

Outdoor Table and Floor Lamps

70377	172
70504	172
70506	172
70557	172
70604	172
74165	172
74199	172
74212	172

Outdoor Ceiling Fans

300103 NI	162
300103 OBB	162
300103 WH	162
300119 TZP	166
300119 WCP	166
300119 WSP	166
310101 TZP	165
310101 WCP	165
310102 GST	163
310102 TZP	163
310102 WCP	163

310127 TZP 164
 310127 WCP 164
 310127 WSP 164
 310131 NI 164
 310131 OZ 164
 310192 ADC 163
 310192 TZP 160, 163
 310192 WCP 163
 310192 WSP 163
 339520 TZP 165
 339520 WH 165

Outdoor Ceiling Fan Accessories

338050 TZP 166
 338050 WH 166
 380900 TZP 166
 380900 WCP 166
 380900 WSP 166
 380901 TZP 166
 380901 WCP 166
 380901 WSP 166
 380902 ADC 166
 380902 TZP 166
 380902 WCP 166
 380902 WSP 166

Low Voltage Chandeliers

15408 BKT 167
 15402 OZ 168
 15409 OZ 168

Accessories

4800 WH 156
 4801 WH 156
 4802 WH 156
 4803 WH 156
 4804 WH 156
 4805 WH 156
 4806 WH 156
 4807 WH 156
 4812 WH 156
 4813 WH 156
 4814 WH 156
 4817 WH 156
 4818 WH 156
 4819 WH 156
 4819 WH 156
 4820 WH 156
 4826 WH 156
 4826 WH 156
 4827 WH 156
 4827 WH 156
 9501 BK 159
 9501 WH 159
 9502 AZ 159
 9502 BK 159
 9505 AZ 159
 9506 AZ 158
 9506 BA 158
 9506 BK 158
 9506 SS 158
 9506 TZ 158
 9510 BK 158

9510 BST 158
 9510 LD 158
 9510 LZ 158
 9510 OB 158
 9510 OZ 158
 9523 LD 158
 9530 BK 159
 9530 LZ 159
 9530 OB 159
 9530 OZ 159
 9530 PB 159
 9530 TZG 159
 9530 WH 159
 9531 BK 159
 9531 LZ 159
 9534 BK 154
 9536 BK 154
 9542 BK 158
 9542 BST 158
 9542 LZ 158
 9542 OZ 158
 9544 BK 154
 9546 BK 154
 9551 BK 159
 9551 LD 159
 9595 AGZ 158
 9595 AZ 158
 9595 BK 158
 9595 LZ 158
 9595 OB 158
 9595 OZ 158
 9595 TZ 158
 49904 AZ 159
 49904 BK 159
 49904 WH 159
 49907 AZ 159
 49907 BK 159
 49907 WH 159
 49914 AZ 159
 49914 BK 159
 49950 BK 159
 49951 BK 159
 49952 BK 159
 49953 AZ 159
 49953 BK 159
 49953 WH 159

Energy Efficient

9150 CV FL 128
 10622 BK 155
 10622 WH 155
 10640 AZ 102
 10640 NI 102
 10903 PR 49
 10904 PR 49
 10905 PR 49
 10906 PR 49
 10907 OZ 56
 10908 OZ 56
 10909 OZ 56
 10910 OZ 56
 10911 OZ 56
 10921 DCO 125
 10922 AZ 100
 10923 BK 155

10923 TZ 155
 10924 DCO 104
 10925 DCO 104
 10926 DCO 104
 10927 DCO 125
 10928 DCO 124
 10929 DCO 124
 10930 DCO 124
 10941 BK 155
 10941 WH 155
 10944 CV 131
 10945 CV 130
 10946 CV 130
 10949 CV 131
 10950 TZ 70
 10953 TZ 70
 10954 TZ 70
 10955 TZ 70
 10956 TZ 70
 10957 CV 129
 10958 CV 129
 10959 CV 129
 10960 CV 128
 10961 CV 128
 10962 CV 128
 10963 AZ 100
 10965 OZ 75
 10967 OZ 75
 10968 OZ 74
 10969 OZ 74
 11001 RZ 63
 11002 RZ 63
 11004 RZ 62
 11005 RZ 62
 11006 RZ 63
 11008 RZ 63
 11009 RZ 63
 11010 RZ 51
 11011 RZ 50
 11012 RZ 50
 11013 RZ 50
 11014 RZ 51
 11015 RZ 51
 11016 RZ 51
 11017 PR 82
 11018 PR 82
 11019 PR 82
 11020 PR 83
 11021 PR 83
 11026 BK 155
 11026 WH 155
 11027 BK 155
 11027 WH 155
 11028 BK 155
 11028 WH 155
 11029 BK 155
 11029 WH 155
 11030 RZ 33
 11031 RZ 33
 11032 RZ 33
 11035 RZ 33
 11037 RZ 33
 11041 BST 30
 11042 BST 31
 11043 BST 30
 11049 BST 30
 11050 BST 31
 11051 BST 31

11053 BST 35
 11054 BST 35
 11055 BST 34
 11056 BST 34
 11057 BST 35
 11058 BST 35
 11059 BST 34
 11066 AZ 80
 11066 GNT 81
 11067 AZ 80
 11067 GNT 81
 11068 AZ 80
 11068 GNT 81
 11069 AZ 80
 11069 GNT 81
 11070 AZ 80
 11070 GNT 81
 11095 AZ 101
 11095 BA 101
 11096 AZ 101
 11096 BA 101
 11097 AZ 101
 11097 BA 101
 11098 NI 146
 11099 NI 146
 11107 AGZ 113
 49071 BST FL 79
 49072 BST FL 79
 49073 BST FL 79
 49074 BST FL 79
 49075 BST FL 79
 49100 RZ FL 38
 49101 RZ FL 38
 49102 RZ FL 38
 49103 RZ FL 38
 49104 RZ FL 39
 49105 RZ FL 39
 49106 RZ FL 39
 49107 RZ FL 39
 49108 RZ FL 39
 49110 AVI FL 94
 49111 AVI FL 95
 49112 AVI FL 94
 49113 AVI FL 94
 49114 AVI FL 95
 49115 AVI FL 95
 49116 AVI FL 95
 49119 AVI FL 110
 49120 AVI FL 110
 49121 AVI FL 111
 49122 AVI FL 110
 49123 AVI FL 111
 49124 AVI FL 111
 49125 AVI FL 111
 49137 OZ FL 115
 49138 OZ FL 114
 49139 OZ FL 114
 49140 OZ FL 114
 49141 OZ FL 115
 49142 OZ FL 115
 49143 OZ FL 115
 49144 OZ FL 115
 49166 AGZ FL 135
 49167 AGZ FL 135
 49168 AGZ FL 135
 49170 AGZ FL 135
 49174 OZ FL 108
 49175 OZ FL 109

49176 OZ FL 108
 49177 OZ FL 108
 49178 OZ FL 109
 49179 OZ FL 109
 49180 OZ FL 109
 49181 OZ FL 109
 49200 BK FL 92
 49201 BK FL 92
 49202 BK FL 92
 49203 BK FL 92
 49204 BK FL 93
 49205 BK FL 93
 49206 BK FL 93
 49207 BK FL 93
 49214 AVI FL 84
 49215 AVI FL 84
 49216 AVI FL 85
 49217 AVI FL 84
 49218 AVI FL 85
 49219 AVI FL 85
 49220 AVI FL 85

LED

49226 OZ LED 14
 49227 OZ LED 15
 49228 OZ LED 15
 49229 OZ LED 14
 49248 AGZ LED 16
 49249 AGZ LED 16
 49250 AGZ LED 17
 49251 AGZ LED 17

We go to great lengths to assure the metal and glass finishes shown in the catalog match the actual products, but printing variations and variations in chemical finishes and the nature of hand applied finishing will cause some differences between the printed images and actual product, and from one product to another.

We use only non-ferrous materials on the exterior parts of our outdoor lantern products, and use the best available weather-resistant finishes. However, due to some extreme environmental conditions such as acid rain, salt air and ultraviolet exposure, we cannot guarantee our exterior finishes, with the exception of our LifeBrite® lanterns.

Due to environmental conditions such as soil acidity, concrete alkalinity and other corrosive soil and air conditions, we cannot guarantee our direct burial posts.



“My style is **far from ordinary**. That’s why I chose **Kichler® Decorative Lighting** – to make my living room extraordinary.”

Lighting that defines your **style™**

Kichler® Decorative Lighting

Help your true style shine through.

See your dealer for information on our full line of **Decorative Lighting**.



When you need help expressing your individual style, look no further than Kichler Decorative Lighting. Our stunning collections are available in a variety of styles you'll be proud to call your own.

Like traditional collections with intricate detailing, aged finishes and tapered fabric shades. Modern collections with clean lines, geometric forms and metallic finishes. And even some that are in between – classic looks with a slightly contemporary edge.

Select the Kichler Decorative Lighting that beautifully reflects your personality, tastes and lifestyle. And you'll find the style that's all you.

View our interactive catalog now at kichler.com.

KICHLER
LIGHTING 

Featured on Front Cover:
Venetian Rain™ Collection
Lantern 49132 BRZ
Page 22

Featured on Back Cover:
Tremillo™ Collection
Lantern 49201 BK
Page 92

KICHLER LIGHTING
World Headquarters
7711 E. Pleasant Valley Rd.
PO Box 318010
Cleveland, Ohio 44131-8010

www.kichler.com

50M/09-KD-1080
Catalog No. **K210**
Printed in USA
© Copyright All rights reserved.
Kichler Lighting.

The majority of newer Kichler Lighting fixtures are U.S. Patent Pending.
Many are also Patent Pending in Canada.

