

GENERATION
LIGHTING



SEA GULL COLLECTION

PRODUCTS SHOWN: PERRYTON FOUR LIGHT
HALL / FOYER IN BLACKSMITH FINISH
DESIGNER: DESIGN STORMS



Welcome to Generation Lighting.

We started our company in 1919, and are excited to celebrate our 100th anniversary this year. Through the generations, we have always held true to delivering on our promise: beautiful lighting at an affordable value.

Our product portfolio has also evolved to serve the needs of today's builders, contractors and homeowners. From space, to function, to style and energy efficiency, we offer complete solutions and are pleased to present our 2019 Sea Gull Collection.

GENERATION
LIGHTING

Sea Gull
COLLECTION

#generationlighting

Get Inspired @GENERATIONLIGHTING

FINISH NAME & CODES

Antique Bronze	[-71]	Oxford Bronze	[-746]
Antique Brushed Nickel	[-965]	Oxidized Bronze	[-46]
Antique Forged Iron	[-AF]	Painted Antique Bronze	[-171]
Autumn Bronze	[-715]	Painted Brushed Nickel	[-753]
Brushed Oil Rubbed Bronze	[-778]	Pewter	[-155]
Brushed Steel	[-BS]	Plated Bronze	[-787]
Black	[-12]	Polished Brass	[-02]
Blacksmith	[-839]	Polished Nickel	[-PN]
Bronze	[-10]	Roman Bronze	[-191]
Brushed Nickel	[-962]	Satin Aluminum	[-04]
Brushed Pewter	[-255]	Satin Bronze	[-848]
Brushed Stainless	[-98]	Satin Nickel	[-SN]
Burled Iron	[-780]	Sorrel Brown	[-SBR]
Burnt Sienna	[-710]	Stardust	[-846]
Chrome	[-05]	Statuary Bronze	[-51]
Corinthian Bronze	[-CB]	Tinted Aluminum	[-986]
Dark Weathered Zinc /		Two Tone Nickel	[-773]
Weathered Oak	[-DWZ/WO]	Walnut	[-WAL]
Flemish Bronze	[-845]	Washed Pine	[-872]
Forged Iron	[-185]	Weathered Copper	[-44]
Heirloom Bronze	[-782]	Weathered Iron	[-819]
Heritage Bronze	[-HRTG BRZ]	Weathered Pewter	[-57]
Iron Oxide	[-10]	Weathered Zinc	[-797]
Obsidian Mist	[-802]	White	[-15]
Oil Rubbed Bronze	[-ORB]	White Wash	[-808]

ICON LEGEND

ADA ADA Compliant

Meets the 4" maximum extension requirement of the Americans with Disabilities Act.

DAMP Damp Rated

Safety listed for damp location.

☾ Dark Sky

Has 180° light cut-off to minimize light pollution in the night sky.

EN★ ENERGY STAR® Qualified

Meets strict energy efficiency guidelines set by the EPA and Department of Energy.

FL Fluorescent Light Source

Has a fluorescent option.

WOD Integrated LED Warm-On-Dim

LED fixture for which the color temperature warms as the fixture dims.

LED LED

Has integrated LED or has an LED option.

+ Mounting Options

These fixtures may: a) mount up or down, b) have a flush or semi-flush option, or c) have configuration options, such as moveable heads or arms. Details are provided in the item description.

NEW New

These fixtures are new 2019 launches.

SS StoneStrong

Constructed with a unique synthetic composite engineered to withstand even the harshest environmental conditions, and backed by a 5-year warranty.

T24 Title 24

Can be used to comply with California Energy Commission (CEC) 2016 Title 24 Part 6 High Efficacy LED Light Source Requirements if used with lamps (not included) that are registered and appear in the CEC Appliance Database.

T24 Title 24

Can be used to comply with California Energy Commission (CEC) 2016 Title 24 Part 6 High Efficacy LED Light Source Requirements if used with included lamps that are registered and appear in the CEC Appliance Database.

T24 Title 24

Can be used to comply with California Energy Commission (CEC) 2016 Title 24 Part 6 High Efficacy LED Light Source Requirements. These fixtures are registered and appear in the CEC Appliance Database.

T24 Title 24

Can be used to comply with California Energy Commission (CEC) 2016 Title 24 Part 6 High Efficacy LED Light Source Requirements. These fixtures are not required to be registered with the CEC nor appear in the CEC Appliance Database (generally fluorescent and outdoor inseparable LED luminaires).

50Lb Weighs over 50lbs.

This fixture weighs over 50 pounds and must be supported independently of outlet box.

WET Wet Rated

Safety listed for wet location.

TABLE OF CONTENTS

VISUAL INDEX	4
INDOOR COLLECTIONS	50
PENDANT COLLECTIONS	302
CEILING COLLECTIONS	362
WALL / BATH COLLECTIONS	390
OUTDOOR COLLECTIONS	458
RECESSED COLLECTIONS	596
LIGHTING SYSTEMS (LX CABLE/LED TAPE)	628
UNDERCABINET COLLECTIONS	648
LED STEP / BRICK LIGHTING	658
RESOURCES	670
SKU INDEX	680
COLLECTION INDEX	700

ALTURAS

Indoor p.60 | Wall / Bath p.394

FINISHES | MATERIAL

Brushed Nickel [-962]
Etched, White Inside Glass
Satin Bronze [-848]
Etched, White Inside Glass
Oil Rubbed Bronze [-778]
Etched, White Inside Glass
Chrome [-05]
Etched, White Inside Glass
(Wall / Bath Only)

EN★ DAMP T24 T24



Nine Light Chandelier



Five Light Chandelier



Three Light Chandelier



Three Light Pendant



Two Light Semi-Flush Convertible Pendant



One Light Mini-Pendant



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath



Nash Flush Mounts p.364

BANNOCK

Indoor p.272 | Wall / Bath p.419

FINISHES | MATERIALS

Brushed Nickel [-962]
Satin Etched Glass
Heirloom Bronze [-782]
Etched, White Inside Glass

EN★ DAMP T24 T24



Nine Light Chandelier



Five Light Chandelier



Three Light Chandelier



Two Light Semi-Flush Convertible Pendant



One Light Mini-Pendant



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath



Geary Flush Mounts p.366

BARRINGTON

Indoor p.248 | Wall / Bath p.431

FINISHES | MATERIAL

Brushed Steel [-BS]
White Opal Etched Glass
Oil Rubbed Bronze [-ORB]
White Opal Etched Glass

DAMP T24 ADA



Fifteen Light Chandelier



Nine Light Chandelier



Five Light Chandelier



Four Light Chandelier



Three Light Chandelier



Three Light Linear Chandelier



Three Light Uplight



Two Light Uplight



One Light Mini-Pendant



Two Light Semi-Flush Mount



Two Light Semi-Flush Mount



Flush Mount



One Light Wall Sconce



One Light Wall Sconce



Two Light Wall / Bath



Three Light Wall / Bath



Four Light Wall / Bath

BELTON

Indoor p.152 | Wall / Bath p.420

FINISHES | MATERIALS

Brushed Nickel [-962]

Clear Seeded Glass

Heirloom Bronze [-782]

Clear Seeded Glass

EN★ DAMP T24 T24



Five Light Chandelier



Five Light Uplight Chandelier



Three Light Chandelier



Four Light Island Pendant



One Light Pendant



One Light Mini-Pendant



Two Light Semi-Flush



Three Light Semi-Flush



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath



Geary Flush Mounts p.366


BOUGHTON

p.134

FINISH

Antique Forged Iron Finish [-AF]

DAMP T24



Twenty Four Light Chandelier



Eighteen Light Chandelier



Ten Light Chandelier



Six Light Chandelier

CANFIELD

Indoor p.92 | Wall / Bath p.404

FINISHES | MATERIALS

Brushed Nickel [-962]
Etched Glass, White Inside Glass
Burnt Sienna [-710]
Etched Glass, White Inside Glass

EN★ DAMP 50LB T24 T24



Fifteen Light Chandelier



Nine Light Chandelier



Five Light Chandelier



Three Light Chandelier



Three Light Uplight Pendant



Three Light Semi-Flush Ceiling Mount



One Light Mini-Pendant



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath

CARONDELET

Indoor p.180 | Wall / Bath p.443

FINISHES | MATERIALS

Antique Brushed Nickel [-965]
Crystal Glass
Burnt Sienna [-710]
Crystal Glass

EN★ DAMP 50LB T24 T24



Six Light Chandelier



Four Light Chandelier



Two Light Semi-Flush Convertible Pendant



Two Light Ceiling Flush Mount



One Light Mini-Pendant



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath

NEW

CARRA

Indoor p.137 | Wall / Bath p.446

FINISH | MATERIAL

White Wash Finish [-808]
Weathered Zinc Accents

EN★ DAMP T24 ADA



Large
Six Light
Hall / Foyer



Medium
Four Light
Hall / Foyer



Small
Three Light
Hall / Foyer



Four Light
Semi Flush
Mount



Two Light
Bath
Sconce

CHATAUQUA

p.164

FINISHES | MATERIALS

Antique Bronze [-71]
Etched, White Inside Glass
Stardust [-846]
Etched, White Inside Glass

EN★ DAMP T24 ADA



Six Light
Hall / Foyer



Five Light
Chandelier



Four Light
Island Pendant



Three Light
Chandelier



Three Light
Hall / Foyer



One Light
Mini-Pendant



Geary
Flush Mounts
p.366

CORBEILLE

p.138

FINISH | MATERIAL

Stardust [-846] with Ceredus Oak Accents
Creme Parchment Glass

EN★ DAMP T24 ADA



Nine Light
Chandelier



Five Light
Chandelier



Three Light
Pendant



Two Light
Semi-Flush
Convertible
Pendant



Two Light
Ceiling
Flush
Mount

CORSICANA

p.110

FINISH | MATERIAL

Heirloom Bronze [-782]
White Capiz Shell

EN★ DAMP T24 ADA



Five Light
Chandelier



Three Light
Chandelier



One Light
Mini-Pendant



Geary
Flush Mounts
p.366

COWEN

Indoor p.148 | Wall / Bath p.445

FINISH

Obsidian Mist [-802]

DAMP T24



Six Light
Hall / Foyer



Five Light
Island Pendant



Three Light
Pendant



Two Light
Semi-Flush
Convertible
Pendant



One Light
Mini-Pendant



One Light
Wall / Bath

DAVLIN

p.130

FINISH

Stardust [-846] with Cerused Oak Accents

EN★ DAMP T24



Six Light
Large
Hall / Foyer



Four Light
Medium
Hall / Foyer



Three Light
Small
Hall / Foyer

DAYNA

p.176

FINISHES | MATERIALS

Brushed Nickel [-962]

Cream Faux Silk Shade

Burnt Sienna [-710]

Beige Faux Linen Shade

EN★ T24 T24



Four Light
Island Pendant



Four Light
Pendant



Three Light
Pendant



Two Light
Pendant



Two Light Flush /
Semi-Flush
Convertible

DRAWING ROOM

Indoor p.296 | Wall / Bath p.442

FINISH | MATERIAL

Walnut (-WAL)
Amber Snow Scavo Glass

DAMP T24 ADA



Six Light
Single-Tier
Chandelier



Five Light
Kitchen
Chandelier



Four Light
Mini-Chandelier



Four Light
Uplight
Chandelier



Three Light
Kitchen
Chandelier



Three Light
Island Chandelier



Three Light
Indoor
Semi-Flush
Mount



Three Light
Indoor
Flush Mount



Two Light
Uplight
Chandelier



Two Light
Indoor
Semi-Flush
Mount



Two Light
Indoor
Semi-Flush
Mount



Two Light
Indoor
Flush Mount



One Light
Mini-Pendant



One Light
Sconce



One Light
Sconce



One Light
Sconce



Two Light
Wall / Bath



Three Light
Wall / Bath



Four Light
Wall / Bath

DRISCOLL

Indoor p.74 | Wall / Bath p.405

FINISHES | MATERIALS

Brushed Nickel [-962]
Etched, White Inside Glass
Satin Bronze [-848]
Etched, White Inside Glass
Chrome [-05]
Etched, White Inside Glass
(Wall / Bath Only)

EN★ DAMP T24 T24



Nine Light Chandelier



Five Light Chandelier




Three Light Chandelier



One Light Mini-Pendant



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath



Nash Flush Mounts p.364

DUNNING

Indoor p.112 | Wall / Bath p.436

FINISH | MATERIAL

Stardust [-846] with Cerused Oak Accents
Creme Parchment Glass

EN★ DAMP T24 T24



Five Light Chandelier



Three Light Chandelier



Four Light Island Pendant



One Light Mini-Pendant



Two Light Ceiling Flush Mount



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath

NEW

ELLIS HARPER

Indoor p.206 | Wall / Bath p.410

FINISHES | MATERIALS

Brushed Nickel [-962]
 Etched, White Inside Glass
 Brushed Oil Rubbed Bronze [-778]
 Etched, White Inside Glass

EN★ DAMP T24 T24



Eight Light Chandelier



Five Light Island Pendant



Four Light Chandelier



One Light Mini-Pendant



Two Light Flush Mount



Two Light Semi-Flush Mount



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath

NEW

ELMWOOD PARK

Indoor p.230 | Wall / Bath p.392

FINISHES | MATERIALS

Brushed Nickel [-962]
 Satin Etched Glass Interior with Clear Glass Exterior
 Heirloom Bronze [-962]
 Satin Etched Glass Interior with Clear Glass Exterior

EN★ DAMP T24 T24



Nine Light Chandelier



Five Light Chandelier



Four Light Island Pendant



Three Light Chandelier



Three Light Pendant



Three Light Semi-Flush Mount



Two Light Semi-Flush Mount



Two Light Flush Mount



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath

ELSA

p.146

FINISH | MATERIAL

Heirloom Bronze [-782]
Clear Seeded Glass

EN★ DAMP T24 T24



Five Light Chandelier



Three Light Chandelier



Three Light Ceiling Flush Mount



Two Light Ceiling Flush Mount



One Light Pendant



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath

EMMONS

Indoor p.242 | Wall / Bath p.423

FINISHES | MATERIALS

Brushed Nickel [-962]
Satin Etched Glass
Heirloom Bronze [-782]
Satin Etched Glass

EN★ DAMP T24 T24



Nine Light Chandelier



Five Light Chandelier



Three Light Chandelier



Three Light Pendant



One Light Mini-Pendant



Two Light Semi-Flush



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath



Geary Flush Mounts
p.366

ENGLEHORN

Indoor p.184 | Wall / Bath p.400

FINISH | MATERIAL

Chrome [-05]
Etched, White Inside Glass

EN★ DAMP T24 T24



Nine Light Chandelier



Five Light Chandelier



Three Light Chandelier



Three Light Pendant



Two Light Semi-Flush Convertible Pendant



One Light Mini-Pendant



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath



Geary Flush Mounts p.366

FRANPORT

Indoor p.212 | Wall / Bath p.406

FINISHES | MATERIALS

Brushed Nickel [-962]
Etched, White Inside Glass

Burnt Sienna [-710]
Etched, White Inside Glass

EN★ DAMP 50Lb T24 T24



Fifteen Light Chandelier



Nine Light Chandelier



Five Light Chandelier



Three Light Chandelier



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath

GEREON

Indoor p.150 | Wall / Bath p.445

FINISH

Black [-12]

DAMP T24 ADA



Four Light
Large Pendant



Three Light
Medium Pendant



Two Light
Semi-Flush
Convertible Pendant



One Light
Mini-Pendant



One Light
Wall/Bath


GREENBRIER

p.136

FINISH

Iron Oxide [-10]

DAMP T24



Six Light
Chandelier



Four Light
Chandelier



Three Light
Chandelier

HANFORD

Indoor p.224 | Wall / Bath p.416

FINISHES | MATERIALS

Burnt Sienna [-710]

Satin Etched Glass

Brushed Nickel [-962]

Satin Etched Glass

EN★ DAMP 50LB T24 T24



Fifteen Light
Chandelier



Nine Light
Chandelier



Five Light
Chandelier



Three Light
Hall/Foyer



Three Light
Pendant



Three Light
Semi-Flush
Convertible
Pendant



One Light
Mini-Pendant



One Light
Wall/Bath



Two Light
Wall/Bath



Three Light
Wall/Bath



Four Light
Wall/Bath



Nash Flush
Mounts
p.364


HARTSVILLE

Indoor p.132 | Wall / Bath p.446

FINISH | MATERIAL

Dark Weathered Zinc & Weathered Oak Finish [-DWZ/WO]

DAMP T24 ADA



Nine Light Chandelier



Six Light Chandelier



Five Light Chandelier



Three Light Chandelier



One Light Mini-Pendant



One Light Sconce



Two Light Sconce

HETTINGER

Indoor p.194 | Wall / Bath p.396

FINISHES | MATERIALS

Brushed Nickel [-962]

Etched, White Inside Glass

Burnt Sienna [-710]

Etched, White Inside Glass

Chrome [-05]

Etched, White Inside Glass (Wall / Bath Only)

EN★ DAMP T24 T24



Nine Light Chandelier



Six Light Chandelier



Three Light Pendant



Two Light Semi-Flush Convertible Pendant



One Light Mini-Pendant



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath



Geary Flush Mounts p.366

HEWITT

Indoor p.188 | Wall / Bath p.444

FINISHES | MATERIALS

Polished Nickel [-PN]
 White Linen Parchment Shades
 Satin Nickel [-SN]
 White Linen Parchment Shades
 Antique Bronze Finish [-DBZ]
 White Linen Parchment Shades
 (One Light Wall Sconce Only)

DAMP T24



Nine Light Chandelier



Eight Light Linear Chandelier



Six Light Chandelier



Four Light Chandelier



Four Light Semi-Flush Mount



One Light Wall Sconce

HOLMAN

Indoor p.278 | Wall / Bath p.422

FINISHES | MATERIALS

Brushed Nickel [-962]
 Satin Etched Glass
 Heirloom Bronze [-782]
 Satin Etched Glass

EN★ T24 T24



Nine Light Chandelier



Nine Light Chandelier



Six Light Hall/Foyer



Five Light Chandelier



Five Light Chandelier



Three Light Chandelier



Three Light Chandelier



Three Light Hall/Foyer



Three Light Pendant



Two Light Semi-Flush Convertible Pendant



One Light Pendant



One Light Mini-Pendant



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath



Geary Flush Mounts p.366


JOURDANTON

p.178

FINISH | MATERIALS

Brushed Nickel [-962]
Stainless Steel / Faux Silk

EN★ DAMP T24 T24



Four Light
Island Pendant



Four Light
Pendant



Three Light
Pendant



Two Light
Semi-Flush
Convertible Pendant



One Light
Mini-Pendant

KERRVILLE

Indoor p.98 | Wall / Bath p.434

FINISHES | MATERIALS

Chrome [-05]
Satin Etched Glass

Brushed Nickel [-962]
Satin Etched Glass

Heirloom Bronze [-782]
Satin Etched Glass

EN★ DAMP T24 T24



Nine Light
Chandelier



Five Light
Chandelier



Three Light
Chandelier



Three Light
Pendant



One Light
Pendant



Two Light
Semi-Flush
Convertible
Pendant



One Light
Mini-Pendant



One Light
Wall/Bath



Two Light
Wall/Bath



Three Light
Wall/Bath



Four Light
Wall/Bath



Geary
Flush Mounts
p.366

METCALF

Indoor p.254 | Wall / Bath p.417

FINISHES | MATERIALS

Brushed Nickel [-962]
Satin Etched Glass
Autumn Bronze [-715]
Satin Etched Glass

EN★ DAMP T24 T24



Nine Light Chandelier



Five Light Chandelier



Three Light Chandelier



Three Light Pendant



Two Light Semi-Flush Convertible Pendant



One Light Pendant



One Light Mini Pendant



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath



Nash Flush Mounts p.364

MOFFET STREET

Indoor p.170 | Wall / Bath p.447

FINISHES

Brushed Nickel [-962]
Satin Bronze [-848]
Washed Pine [-872] & Chrome Accents

EN★ DAMP T24 T24



Eight Light Hall / Foyer



Six Light Island Pendant



Four Light Hall / Foyer



Three Light Hall / Foyer



One Light Wall/Bath

MORILL

Indoor p.142 | Wall / Bath p.421

FINISH | MATERIAL

Blacksmith [-839]
Clear Seeded Glass

EN★ DAMP T24 T24



Nine Light Chandelier



Five Light Chandelier



Three Light Chandelier



Three Light Hall / Foyer



One Light Pendant



Two Light Semi-Flush



Three Light Ceiling Flush Mount



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath



Geary Flush Mounts p.366

NEW

OGLESBY

p.140

FINISH | MATERIAL

Washed Pine Finish [-872] & Stardust Accents

EN★ DAMP T24 T24



Five Light Chandelier



Four Light Chandelier



Three Light Chandelier



Two Light Chandelier



Three Light Ceiling Flush Mount

OSLO

Indoor p.84 | Wall / Bath p.398

FINISHES | MATERIALS

Chrome [-05]
Cased Opal Etched Glass
Brushed Nickel [-962]
Cased Opal Etched Glass
Blacksmith [-839]
Cased Opal Etched Glass

EN★ DAMP T24 T24



Nine Light Chandelier



Five Light Chandelier



Three Light Chandelier



Three Light Island Pendant



Two Light Semi-Flush Convertible Pendant



One Light Pendant



One Light Mini-Pendant



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath



Geary Flush Mounts p.366

PARKFIELD

Indoor p.200 | Wall / Bath p.408

FINISHES | MATERIALS

Brushed Nickel [-962]
Etched, White Inside Glass
Flemish Bronze [-845]
Creme Parchment Glass

EN★ DAMP T24 T24



Nine Light Chandelier



Five Light Chandelier



Three Light Downlight Chandelier



Three Light Pendant



Two Light Semi-Flush Convertible Pendant



One Light Pendant



One Light Mini-Pendant



Two Light Ceiling Flush Mount



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath

PERRYTON


p.160

FINISHES


Heirloom Bronze [-782]

Blacksmith [-839]

EN★ DAMP T24 T24



Large
Eight Light
Hall / Foyer



Eight Light
Island Pendant



Medium
Four Light
Hall / Foyer



Small
Four Light
Hall / Foyer

RAVENWOOD MANOR

p.158

FINISH

Stardust [-846]

DAMP T24



Nine Light
Chandelier



8 Light
Chandelier



Five Light
Chandelier

SEVILLE

Indoor p.260 | Wall / Bath p.432

FINISHES | MATERIALS

Chrome [-05]

Etched, White Inside Glass
(Wall / Bath Only)

Brushed Nickel [-962]

Etched, White Inside Glass

Burnt Sienna [-710]

Etched, White Inside Glass

EN★ DAMP T24 T24



Nine Light
Chandelier



Five Light
Chandelier



Five Light
Downlight
Chandelier



Five Light
Shade
Chandelier



One Light
Mini-Pendant



One Light
Wall/Bath



Two Light
Wall/Bath



Three Light
Wall/Bath



Four Light
Wall/Bath



Five Light
Wall/Bath

SFERA

Indoor p.114 | Wall / Bath p.401

FINISHES | MATERIALS

Autumn Bronze [-715]

Mercury Glass

Autumn Bronze [-715]

Cafe Tint Glass

(Indoor Items Only)

Autumn Bronze [-715]

Smoke Amber Glass

(Wall / Bath Only)

EN★ DAMP T24 T24



Six Light Chandelier



Four Light Chandelier



Three Light Pendant



Two Light Semi-Flush Convertible Pendant



One Light Mini-Pendant



Three Light Ceiling Flush Mount



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath

SOCORRO

p.120

FINISHES

Stardust [-846] with Cerused Oak Accents

Washed Pine [-872] with Chrome Accents

EN★ DAMP T24 T24



Six Light Chandelier



Six Light Hall/Foyer



Six Light Chandelier



Four Light Hall/Foyer



Four Light Chandelier

STIRLING

Indoor p.290 | Wall / Bath p.399

FINISHES | MATERIALS

Brushed Nickel [-962]
 Cased Opal Etched Glass / White Linen Shades
 Burnt Sienna [-710]
 Cased Opal Etched Glass / Beige Linen Shades
 Chrome [-05]
 Cased Opal Etched Glass
 (Wall / Bath Only)

EN★ DAMP T24 T24



Nine Light Chandelier



Five Light Chandelier



Six Light Island Pendant




Four Light Island Pendant



Three Light Pendant



Two Light Semi-Flush Convertible Pendant



Two Light Ceiling Flush Mount



One Light Pendant



One Light Mini Pendant



One Light Wall Sconce



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath

SUNSET DRIVE

Indoor p.106 | Ceiling p.370
Wall / Bath p.414

FINISHES | MATERIALS

Brushed Steel [-BS]
Striated Pearl Glass
Corinthian Bronze [-CB]
Striated Pearl Glass
(Not available for Wall / Bath)
Chrome [-CH]
White Glass (Ceiling Only)
Oil Rubbed Bronze [-ORB]
White Glass (Ceiling Only)

DAMP T24



Five Light
Single Tier
Chandelier



Three Light
Kitchen
Chandelier



Three Light
Uplight
Chandelier



Three Light
Island Chandelier



One Light
Mini-Pendant



Semi-Flush
Mounts



Flush
Mounts



One Light
Sconce



Two Light
Wall / Bath



Three Light
Wall / Bath



Four Light
Wall / Bath

SUSSEX

Indoor p.218 | Wall / Bath p.424

FINISHES | MATERIAL

Brushed Nickel [-962]
Satin White Glass

Heirloom Bronze [-782]
Satin White Glass

Chrome [-05]
Satin White Glass
(Wall / Bath Only)

EN★ DAMP T24 T24



Nine Light Chandelier



Five Light Chandelier



Three Light Chandelier



Three Light Island Pendant



Three Light Semi-Flush Convertible Pendant



Three Light Ceiling Semi-Flush Mount



One Light Pendant



One Light Mini-Pendant



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath



Gear Flush Mounts p.366

NEW

THORNWOOD

p.126


FINISH

Washed Pine [-872]
with Weathered Iron Accents

EN★ DAMP T24 T24



Large Eight Light Hall / Foyer



Eight Light Island Pendant



Four Light Chandelier



Four Light Ceiling Flush Mounts



Three Light Chandelier



Two Light Wall / Bath

TOWNER

Indoor p.68 | Wall / Bath p.444

FINISHES | MATERIALS

Brushed Nickel [-962]

Black Steel Shade

Satin Bronze [-848]

Black Steel Shade

EN★ DAMP T24 T24



Eight Light
Island Chandelier



Seven Light
Chandelier



Five Light
Chandelier



Five Light
Cluster



Three Light
Chandelier



Three Light
Cluster



One Light
Mini-Pendant



One Light
Wall / Bath



Nash Flush
Mounts
p.364

TRADITIONAL

p.300

FINISH

Brushed Nickel [-962]

EN★ T24 T24



Ten Light
Chandelier



Five Light
Chandelier

VINTNER

Indoor p.236 | Ceiling p.373
Wall / Bath p.418

FINISHES | MATERIALS

Satin Nickel Finish [-SN]
White Opal Etched Glass
Heritage Bronze Finish [-HTBZ]
White Opal Etched Glass

DAMP T24



Eighteen Light Chandelier



Nine Light Chandelier



Five Light Chandelier



Three Light Chandelier



Three Light Chandelier



Three Light Island Chandelier



Three Light Uplight Chandelier



One Light Mini Pendant



Three Light Semi-Flush



Vintner Flush Mounts



One Light Sconce



Two Light Wall / Bath



Three Light Wall / Bath



Four Light Wall / Bath

WHEATON

Indoor p.284 | Wall / Bath p.440

FINISHES | MATERIALS

Brushed Nickel [-962]
Satin Etched Glass
Heirloom Bronze [-782]
Satin Etched Glass

EN★ T24 T24



Nine Light Chandelier



Five Light Chandelier



Three Light Chandelier



Three Light Pendant



Two Light Semi-Flush Convertible Pendant



One Light Pendant



One Light Mini-Pendant



One Light Wall / Bath



Two Light Wall / Bath



Three Light Wall / Bath



Four Light Wall / Bath



Geary Flush Mounts p.366

WINDGATE

Indoor p.266 | Ceiling p.365
Wall / Bath p.441

FINISHES | MATERIALS

Brushed Nickel [-962]

Alabaster Glass

Heirloom Bronze [-782]

Alabaster Glass

Chrome [-05]

Alabaster Glass Glass

(Wall / Bath Only)

EN★ DAMP T24 T24



Five Light Uplight Chandelier



Five Light Downlight Chandelier



Three Light Uplight Chandelier



Three Light Downlight Chandelier



Two Light Pendant



Large One Light Pendant



One Light Pendant



One Light Mini-Pendant



Two Light Semi-Flush Convertible Pendant



Flush Mount



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath

WINNETKA

Indoor p.78 | Wall / Bath p.435
Outdoor p.542

FINISHES | MATERIALS

Brushed Nickel [-962]

Satin Etched Glass


Blacksmith [-839]

Satin Etched Glass

EN★ DAMP 50Lb T24 T24



Fifteen Light Chandelier



Nine Light Chandelier



Five Light Chandelier



Three Light Chandelier



Four Light Pendant



Three Light Pendant



One Light Pendant



One Light Mini-Pendant



Two Light Semi-Flush Convertible Pendant



Three Light Ceiling Flush Mount



Two Light Ceiling Flush Mount



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath



One Light Outdoor Pendant



One Light Outdoor Post Lantern



Large Two Light Outdoor Wall Lantern



Medium One Light Outdoor Wall Lantern



Small One Light Outdoor Wall Lantern



One Light Outdoor Ceiling Flush Mount

NEW

ZIRE

Indoor p.52 | Wall / Bath p.393

FINISHES | MATERIALS

Chrome [-05]

Clear Glass

Brushed Nickel [-962]

Clear Glass

Brushed Oil Rubbed Bronze [-778]

Clear Glass

EN★ DAMP T24 T24




Nine Light
Chandelier



Five Light
Chandelier



Three Light
Chandelier



Five Light
Island Pendant



One Light
Pendant



One Light
Mini-Pendant



One Light
Sconce



Two Light
Wall / Bath



Three Light
Wall / Bath



Four Light
Wall / Bath

ACADEMY

Pendants p.352 | Ceiling p. 372
Wall / Bath p.427

FINISHES | MATERIALS

Chrome [-05]
Satin White Glass
Brushed Nickel [-962]
Satin White Glass
Heirloom Bronze [-782]
Satin White Glass

EN★ WOD DAMP T24 T24



Extra Large
Pendant



Large
Pendant



Medium
Pendant



Small
Pendant



Large Ceiling
Semi-Flush
Mount



Medium Ceiling
Semi-Flush
Mount



One Light
Wall/Bath



Two Light
Wall/Bath



Three Light
Wall/Bath



Four Light
Wall/Bath

ARILDA

p.314

FINISHES | MATERIAL

Brushed Nickel [-962]
Clear Glass
Heirloom Bronze [-782]
Clear Glass

DAMP T24



One Light
Pendant

BAYLOR

p.314

FINISHES | MATERIAL

Satin Nickel [-SN]
Clear Glass
Oil Rubbed Bronze [-ORB]
Clear Glass

DAMP



One Light
Pendant

BRETTON

Pendants p.328 | Ceiling p.376

FINISHES | MATERIAL

Brushed Nickel [-962]
Clear Glass
Heirloom Bronze [-782]
Clear Glass

EN★ T24 T24



Six Light
Hall / Foyer



Three Light
Semi-Flush
Convertible Pendant



Two Light
Semi-Flush
Convertible Pendant



Three Light
Ceiling
Flush Mount



Two Light
Ceiling
Flush Mount

NEW

BRONZEVILLE

p.306

FINISHES | MATERIAL

Brushed Nickel [-962]
Clear Seeded Glass
Satin Bronze [-848]
Clear Seeded Glass

DAMP T24



Three Light
Pendant



One Light
Pendant

CASUAL LUXURY

Pendants p.356 | Ceiling p.372
Wall / Bath p.402

FINISH | MATERIAL

Brushed Steel [-BS]
Silver Organza

DAMP



Three Light
Pendant



One Light
Pendant



One Light
Pendant



One Light
Pendant



One Light
Wall
Sconce



Two Light
Wall / Bath



Three Light
Wall / Bath



Four Light
Wall / Bath

NEW

DAVI

p.304

FINISHES

Chrome [-05]
Satin Bronze [-848]

EN★ DAMP T24 T24



Six Light
Pendant

DAWES

p.320

FINISHES | GLASS

Brushed Nickel [-962]
Clear Seeded Glass
Burnt Sienna [-710]
Clear Seeded Glass

T24 T24



Three Light
Hall / Foyer

DIVISION STREET

p.338

FINISHES

Brushed Nickel [-962]

Stardust [-846]

Burnt Sienna [-710]

EN★ DAMP T24 T24 T24 LED



One Light Pendant

DOYLE

p.317

FINISHES | MATERIAL

Satin Nickel [-SN]

Clear Glass

Oil Rubbed Bronze [-ORB]

Clear Glass

DAMP



One Light Mini-Pendant



One Light Mini-Pendant

FREDRICKSBURG

Pendants p.339 | Outdoor p.568

FINISHES

Weathered Copper Finish [-44]

Satin Aluminum Finish [-04]

EN★ DAMP WET ☾

WOD T24 T24 T24

LED



Outdoor Pendant



Large Outdoor Wall Lantern



Small Outdoor Wall Lantern

GEARY

Pendants p.346 | Ceiling p.366

FINISHES | MATERIAL

Chrome [-05] (Ceiling Only)

Satin Inside Glass

Antique Brushed Nickel [-965] (Ceiling Only)

Satin Inside Glass

Brushed Nickel [-962]

Satin Inside Glass

Burnt Sienna [-710]

Satin Inside Glass

Heirloom Bronze [-782]

Satin Inside Glass

Blacksmith [-839]

Satin Inside Glass

EN★ DAMP WOD T24 T24 LED



Four Light Large Pendant



Four Light Large Semi-Flush Pendant



Three Light Medium Pendant



Three Light Medium Semi-Flush Pendant



Two Light Small Semi-Flush Pendant



Large Flush Mount



Medium Flush Mount



Small Flush Mount

HUDSON STREET

p.340

FINISHES

Satin Aluminum [-04]

Stardust [-846]

Burnt Sienna [-710]

EN★ DAMP T24 T24



One Light
Pendant

JEYNE

p.342

FINISHES

Weathered Copper [-44]

Heirloom Bronze [-782]

EN★ DAMP T24 T24



One Light
Large Pendant



One Light
Medium Pendant



One Light
Small Pendant

KEA

p.316

FINISHES

Brushed Nickel [-962]

Clear Seeded Glass

Heirloom Bronze [-782]

Clear Seeded Glass

DAMP T24



One Light
Pendant

LABETTE

p.322

FINISHES

Heirloom Bronze [-782]

Black [-12]

EN★ DAMP T24 T24



Large
Four Light
Pendant



Medium
Three Light
Pendant



Small
Three Light
Pendant

LEO-HANGING GLOBE

Pendants p.308 | Ceiling p.375

FINISHES | MATERIALS

White [-15]

White Glass

Satin Aluminum [-04]

White Glass

Satin Aluminum [-04]

Clear Seeded Glass

Satin Bronze [-848]

White Glass

Satin Bronze [-848]

Clear Seeded Glass

EN★ DAMP WOD T24 T24 T24 LED



Extra Large
Pendant



Large
Pendant



Medium
Pendant



Small
Pendant



Ceiling
Flush Mount

LONOKE

p.326

FINISHES

Heirloom Bronze [-782]
Stardust [-12]

EN★ DAMP T24 T24



Large
Four Light
Pendant



Medium
Three Light
Pendant



Small
Three Light
Pendant

MARINO

p.315

FINISHES | MATERIAL

Chrome [-CH]
Clear Glass
Satin Nickel [-SN]
Clear Glass
Oil Rubbed Bronze [-ORB]
Clear Glass

DAMP T24



One Light
Pendant

MONTREAL

Pendants p.354
Wall/Bath p.426

FINISHES | MATERIALS

Antique Brushed Nickel [-962]
Etched, White Inside Glass
Burnt Sienna [-710]
Cafe Tint Glass

EN★ DAMP T24 T24



One Light
Pendant



One Light
Wall/Bath



Two Light
Wall/Bath



Three Light
Wall/Bath



Four Light
Wall/Bath

NANCE

p.357

FINISHES | MATERIALS

Brushed Nickel Finish [-962]
Off-White Faux Silk Fabric
Satin Etched Glass Diffuser
Heirloom Bronze Finish [-782]
Off-White Faux Silk Fabric
Satin Etched Glass Diffuser

EN★ T24 T24



Three Light
Pendant



Two Light
Semi-Flush
Convertible Pendant

**PAINTED SHADE
PENDANTS**

p.355

FINISHES

Painted Brushed Steel [-98]
White Inside
Red [-21]
White Inside
Painted Antique Brushed Copper [-63]
White Inside

EN★ T24 T24



One Light
Pendant

PRATT STREET METAL

p.330

FINISHES | MATERIAL

Brushed Nickel [-962]

Prismatic Diffuser

Satin Bronze [-848]

Prismatic Diffuser

Autumn Bronze [-715]

Prismatic Diffuser

EN★ DAMP WOD T24 T24 T24 LED



Large Pendant



Medium Pendant



Small Pendant

PRATT STREET PRISMATIC

p.318

FINISHES | MATERIAL

Brushed Nickel [-962]

Prismatic Glass & Diffuser

Autumn Bronze [-715]

Prismatic Glass & Diffuser

EN★ DAMP T24 T24



Large Pendant



Medium Pendant



Small Pendant

ROME

p.324

FINISHES

Chrome [-05]

Brushed Nickel [-962]

Heirloom Bronze [-782]

EN★ DAMP T24 T24



Large Six Light Hall / Foyer



Small Three Light Hall / Foyer

SEBRING

Pendants p.344 | Outdoor p.538

FINISHES | MATERIAL

Brushed Stainless [-05] White Inside

Clear Seeded Glass

Weathered Copper [-44]

Clear Seeded Glass

Black Finish [-12]

Clear Seeded Glass

EN★ DAMP WET WOD T24 T24 LED



Pendant



Mini-Pendant



Outdoor Post Lantern



Large Outdoor Wall Lantern



Small Outdoor Wall Lantern



Outdoor Ceiling Flush Mount

STONE STREET

p.334

FINISHES | MATERIAL

Brushed Nickel [-962]

Satin Etched Glass Diffuser

Satin Bronze [-848]

Satin Etched Glass Diffuser

Burnt Sienna [-710]

Satin Etched Glass Diffuser

EN★ DAMP T24 T24



Three Light Pendant



Two Light Pendant



One Light Pendant

WESTMINSTER

p.345

FINISH | MATERIAL

Autumn Bronze [-715]
Clear Glass

EN★ DAMP T24 T24



Large
Three Light
Pendant



Small
Three Light
Pendant



Two Light
Semi-Flush
Convertible Pendant

ZOLA

p.315

FINISHES | MATERIAL

Chrome [-CH]
Clear Glass

Satin Nickel [-SN]
Clear Glass

Oil Rubbed Bronze [-ORB]
Clear Glass

DAMP T24



One Light
Pendant

ALEXANDRIA

p.429

FINISH | MATERIAL

Two Tone Nickel Finish [-773]
Highlighted Satin Etched Glass

EN★ DAMP T24 T24



Two Light
Wall / Bath



Three Light
Wall / Bath



Four Light
Wall / Bath

ALDRIDGE

p.451

FINISH | MATERIAL

Brushed Nickel [-962]
White Acrylic Diffuser

EN★ DAMP ADA T24



Small LED
Wall / Bath



Medium LED
Wall / Bath



Large LED
Wall / Bath

BAYFIELD

p.412

FINISH | MATERIAL

Chrome [-05]
Etched, White Inside Glass
Brushed Nickel [-962]
Etched, White Inside Glass
Burnt Sienna [-710]
Etched, White Inside Glass

EN★ DAMP T24 T24



One Light
Wall / Bath



Two Light
Wall / Bath



Three Light
Wall / Bath



Four Light
Wall / Bath

BRAUNFELS

p.454

FINISHES | MATERIAL

Satin Aluminum [-04]
Frosted Acrylic Diffuser
& Clear Acrylic Outer Shade
Burnt Sienna [-710]
Frosted Acrylic Diffuser
& Clear Acrylic Outer Shade

DAMP ADA T24 LED



Small LED
Wall / Bath



Medium LED
Wall / Bath



Large LED
Wall / Bath



Extra Large LED
Wall / Bath

BROOKCHESTER

p.430

FINISHES | MATERIAL

Chrome [-05]
Clear, Ribbed Glass

EN★ DAMP T24 T24



Two Light
Wall / Bath



Three Light
Wall / Bath



Four Light
Wall / Bath

CENTER STAGE

p.456

FINISHES

Chrome Finish [-05]

Brushed Stainless [-98]

DAMP T24



Three Light Wall/Bath



Four Light Wall/Bath



Five Light Wall/Bath



Six Light Wall/Bath



Eight Light Wall/Bath

COLUSA

p.453

FINISH | MATERIAL

Brushed Nickel [-962]

Acrylic Diffuser Glass

DAMP ADA T24 LED



Small LED Wall/Bath



Medium LED Wall/Bath



Large LED Wall/Bath

DE-LOVELY

p.457

FINISHES

Chrome [-05]

Brushed Nickel [-962]

DAMP T24



Four Light Wall/Bath



Six Light Wall/Bath



Eight Light Wall/Bath

DENHELM

p.411

FINISHES | MATERIAL

Brushed Nickel [-962]

Etched, White Inside Glass

Burnt Sienna [-710]

Etched, White Inside Glass

EN★ DAMP T24 T24



One Light Wall/Bath



Two Light Wall/Bath



Three Light Wall/Bath



Four Light Wall/Bath

EAST BENTON

p.450

FINISH | MATERIAL

Brushed Nickel [-962]

Frosted Acrylic Glass

EN★ DAMP T24 T24 ADA



Small LED Wall/Bath



Medium LED Wall/Bath



Large LED Wall/Bath

GLADSTONE

p.438

FINISHES | MATERIALS

Chrome [-05]
Satin Etched Glass
Antique Brushed Nickel [-965]
Satin Etched Glass
Heirloom Bronze [-782]
Smoky Amber Glass

EN★ DAMP T24 T24



JENNIE

p.415

FINISH | MATERIAL

Chrome [-CH]
White Opal Etched Glass
Satin Nickel [-SN]
White Opal Etched Glass

DAMP T24



SAGEMORE

p.428

FINISH | MATERIAL

Chrome [-05]
Satin Etched Glass

EN★ DAMP T24 T24



VANDEVENTER

p.452

FINISH | MATERIAL

Brushed Nickel [-962]
White Acrylic Diffuser Glass

DAMP ADA T24 LED



WASECA

p.407

FINISHES | MATERIAL

Chrome [-05]
Etched, White Inside Glass
Burnt Sienna [-710]
Etched, White Inside Glass

EN★ DAMP T24 T24



One Light
Wall/Bath



Two Light
Wall/Bath



Three Light
Wall/Bath



Four Light
Wall/Bath

WESTMONT

p.430

FINISH | MATERIAL

Brushed Nickel [-962]
Satin White Glass

EN★ DAMP T24 T24



Two Light
Wall/Bath



Three Light
Wall/Bath



Four Light
Wall/Bath

ADDRESS LIGHTS

p.592

FINISHES

- White [-15]
- Antique Bronze Powder [-71]
- Black [-12]

WET LED



120V LED



Low-Voltage

NEW

ALBAN

p.576

FINISHES | MATERIAL

- Satin Aluminum [-04]
- Opal Etched Glass
- Antique Bronze [-71]
- Opal Etched Glass

EN★ WET T24 T24



Large One Light
Outdoor
Lantern



Large One Light
Outdoor
Lantern



Small One Light
Outdoor
Lantern



Small One Light
Outdoor
Lantern

BAKERSVILLE

p.498

FINISHES | MATERIAL

- Heirloom Bronze [-782]
- Clear Glass
- Heirloom Bronze [-782]
- Satin Etched Glass
- Black [-12]
- Clear Glass
- Black [-12]
- Satin Etched Glass

EN★ DAMP WET T24 T24



One Light
Outdoor
Wall Lantern



One Light
Outdoor
Wall Lantern



Two Light
Outdoor Ceiling
Flush Mount

NEW

BARN LIGHT

p.564

FINISHES

- Weathered Pewter [-57]
- Black [-12]

EN★ WET WET T24 T24



Extra Large
One Light
Outdoor
Wall Lantern



Large
One Light
Outdoor
Wall Lantern



Medium
One Light
Outdoor
Wall Lantern



Small
One Light
Outdoor
Wall Lantern

BAYSIDE

p.536

FINISHES | MATERIALS

- White [-15]
- Frosted Ribbed Diffuser
- Black [-12]
- Frosted Ribbed Diffuser

EN★ ADA WET T24 T24



One Light
Outdoor
Wall Lantern



One Light
Outdoor
Wall Lantern



One Light
Outdoor
Wall Lantern



One Light
Outdoor
Wall/Ceiling Mount



One Light
Outdoor
Wall/Ceiling Mount

BRENTWOOD

p.524

FINISHES | MATERIALS

Black [-12]
Clear Glass
Black [-12]
Smooth White Glass

EN★ DAMP WET T24 T24



One Light Outdoor Pendant



One / Three Light Outdoor Post Lantern



Large One Light Outdoor Wall Lantern



Medium One Light Downlight Outdoor Wall Lantern



Medium One Light Uplight Outdoor Wall Lantern



Small One Light Outdoor Wall Lantern



Two Light Outdoor Ceiling Flush Mount

CALDER

p.472

FINISHES | MATERIAL

Antique Bronze [-71]
Satin Etched Glass
Black [-12]
Satin Etched Glass

EN★ DAMP WET SS T24 T24



One Light Outdoor Pendant



One / Three Light Outdoor Post Lantern



Large One Light Outdoor Wall Lantern



Medium One Light Downlight Outdoor Wall Lantern



Small One Light Outdoor Wall Lantern

CAPE MAY

p.496

FINISH | MATERIAL

Burled Iron [-780]
Etched Hammered with Light Amber Tint Glass

EN★ DAMP WET ☾

T24 T24 T24



Outdoor Post Lantern



Extra Large Outdoor Wall Lantern



Large Outdoor Wall Lantern



Medium Outdoor Wall Lantern



Small Outdoor Wall Lantern

CHATHAM

p.478

FINISHES | MATERIALS

Weathered Copper Finish [-44]
Clear Seeded or Frosted Seeded Glass
Oxidized Bronze Finish [-46]
Clear Seeded or Frosted Seeded Glass

EN★ DAMP WET ☾

T24 T24 T24



One / Two Light Outdoor Pendant



One / Two Light Outdoor Post Lantern



Large One / Two Light Outdoor Wall Lantern



Small One Light Outdoor Wall Lantern

CHILDRESS

p.464

FINISHES | MATERIAL

Antique Bronze Finish [-71]
Satin Etched Glass
Black Finish [-12]
Satin Etched Glass

EN★ DAMP WET T24 T24 T24



Outdoor Pendant



Outdoor Post Lantern



Extra Large Outdoor Wall Lantern



Large Outdoor Wall Lantern



Medium Outdoor Wall Lantern



Small Outdoor Wall Lantern



Outdoor Ceiling Flush Mount

CLASSICO

p.510

FINISHES | MATERIAL

Polished Brass [-02]
Clear Beveled Glass

Black [-12]
Clear Beveled Glass

DAMP **WET** **T24**



One Light
Outdoor Semi-Flush
Convertible Pendant



One Light
Outdoor
Post Lantern



Large One
Light Outdoor
Wall Lantern



Medium One
Light Outdoor
Wall Lantern



Small One
Light Outdoor
Wall Lantern

CRITTENDEN

p.572

FINISHES

Satin Aluminum [-04]
Black [-12]

Black [-12]

EN* **WET** **T24** **T24**



One Light
Outdoor
Wall Lantern

CROWELL

p.544

FINISHES | MATERIALS

Antique Bronze [-71]
Creme Parchment Glass

Black [-12]
Satin Etched Glass

Satin Etched Glass

EN* **DAMP** **WET** **T24** **T24**



Outdoor
Pendant



Outdoor
Post Lantern



Large Outdoor
Wall Lantern



Medium Outdoor
Wall Lantern



Small Outdoor
Wall Lantern



Outdoor
Ceiling
Flush Mount

GAELAN

p.470

FINISHES | MATERIALS

Painted Brushed Nickel [-753]
Clear Ribbed Glass

Black [-12]
White Glass

White Glass

EN* **DAMP** **WET** **SS** **T24** **T24**



Outdoor
Pendant



Large
Outdoor
Wall Lantern



Medium
Outdoor
Wall Lantern



Small
Outdoor
Wall Lantern

GALVYN

p.462

FINISHES | MATERIAL

Antique Bronze [-71]
Satin Etched Glass

Black [-12]
Satin Etched Glass

Satin Etched Glass

EN* **SS** **DAMP** **WET** **T24** **T24**



Outdoor
Pendant



Outdoor
Post
Lantern



Extra Large
Outdoor
Wall Lantern



Large
Outdoor
Wall Lantern



Medium
Outdoor
Wall Lantern



Small
Outdoor
Wall Lantern

HERMITAGE

p.486

FINISHES | MATERIALS

Antique Brushed Nickel [-965]
Clear Glass

Antique Bronze [-71]
Clear Glass

Antique Bronze [-71]
Frosted Glass

EN★ DAMP WET ☾ T24 T24



Outdoor
Pendant



Outdoor
Post
Lantern



Large
Outdoor
Wall Lantern



Medium
Outdoor
Wall Lantern



Small
Outdoor
Wall Lantern

HERRINGTON

p.554

FINISHES | MATERIALS

Black [-12]
Clear Seeded Glass

Black [-12]
Etched, White Inside Glass

EN★ DAMP WET T24 T24



One Light
Outdoor
Pendant



One Light
Outdoor
Post Lantern



Medium One
Light Outdoor
Wall Lantern



Small One
Light Outdoor
Wall Lantern



One Light
Outdoor Ceiling
Flush Mount

HUNNINGTON

p.548

FINISHES | MATERIALS

Weathered Pewter [-57]
Clear Seeded Glass

Weathered Pewter [-57]
Etched Seeded

Black [-12]
Clear Seeded Glass

Black [-12]
Etched Seeded

EN★ WOD DAMP WET

T24 T24 T24 LED



Outdoor
Pendant



Outdoor
Post Lantern



Large Outdoor
Wall Lantern



Small Outdoor
Wall Lantern



Outdoor Ceiling
Flush Mount

JAMESTOWNE

p.518

FINISHES | MATERIALS

Antique Brushed Nickel [-965]
Clear Beveled Glass

Antique Brushed Nickel [-965]
Frosted Seeded or Tiffany White

Antique Bronze [-71]
Clear Beveled Glass

Antique Bronze [-71]
Frosted Seeded or Tiffany White

Black [-12]
Clear Beveled Glass

EN★ DAMP WET ☾ T24 T24



One Light
Outdoor
Post Lantern



Extra Large Two
Light Outdoor
Wall Lantern



Large One
Light Outdoor
Wall Lantern



Medium One
Light Outdoor
Wall Lantern



Small One
Light Outdoor
Wall Lantern

KENT

p.504

FINISHES | MATERIALS

Oxford Bronze [-746]
Clear Seeded Glass

Oxford Bronze [-746]
Satin Etched Glass

Black [-12]
Clear Seeded Glass

Black [-12]
Satin Etched Glass

EN★ DAMP WET T24 T24



One Light
Outdoor Semi-Flush
Convertible Pendant



One Light
Outdoor
Post Lantern



Extra Large One
Light Outdoor
Wall Lantern



Large One
Light Outdoor
Wall Lantern



Medium One
Light Outdoor
Wall Lantern



Small One
Light Outdoor
Wall Lantern

LANCASTER

p.512

FINISHES | MATERIAL

Polished Bronze [-02]
Clear Beveled Glass

Antique Bronze [-71]
Clear Beveled Glass

Antique Brushed Nickel [-965]
Clear Beveled Glass

Black [-12]
Clear Beveled Glass

EN★ DAMP WET T24 T24



Three Light
Outdoor
Pendant



Three Light
Outdoor
Post Lantern



Two Light
Outdoor
Post Lantern



Large Three
Light Outdoor
Wall Lantern



Large Two
Light Outdoor
Wall Lantern



Large One
Light Outdoor
Wall Lantern



Medium One
Light Outdoor
Wall Lantern



Small One
Light Outdoor
Wall Lantern

MARINUS

p.562

FINISH | MATERIAL

Blacksmith [-12]
Clear Glass

WET T24



Large One Light
Outdoor
Lantern



Medium One Light
Outdoor
Lantern



Small One Light
Outdoor
Lantern

MARTINSVILLE

p.492

FINISHES | MATERIAL

Corinthian Bronze Finish [-CB]
Clear Seeded Glass

Black Finish [-BK]
Clear Seeded Glass

DAMP WET T24



Three Light
Hanging Lantern



Three Light
Post / Pier Lantern



Four Light
Wall Lantern



Three Light
Wall Lantern



Two Light
Wall Lantern



One Light
Wall Lantern

MEDFORD LAKES

p.556

FINISH | MATERIAL

Statuary Bronze [-51]
Etched Hammered with Light Amber Tint Glass

EN★ DAMP WET T24 T24



One Light
Outdoor
Pendant



One Light
Outdoor
Post Lantern



Large One
Light Outdoor
Wall Lantern



Medium One
Light Outdoor
Wall Lantern



Small One
Light Outdoor
Wall Lantern



Two Light
Outdoor Ceiling
Flush Mount

MELITO

p.528

FINISHES | MATERIAL

Weathered Copper [-44]
Satin Etched Glass

Black [-12]
Satin Etched Glass

EN★ WET SS T24 T24



Large One Light
Outdoor
Lantern



Medium One Light
Outdoor
Lantern



Small One Light
Outdoor
Lantern

MULLBERRY HILL

p.530

FINISHES | MATERIAL

White [-15]
Clear or White Glass

Pewter [-155]
Clear or White Glass

Bronze [-10]
Clear or White Glass

Black [-12]
Clear or White Glass

EN★ WET T24 T24



Outdoor
Wall Lantern

NEW CASTLE

p.522

FINISHES | MATERIALS

White [-15]
Clear or White Glass

Antique Brushed Nickel [-965]
Clear or White Glass

Antique Bronze [-71]
Clear or White Glass

Black [-12]
Clear or White Glass

EN★ WET T24 T24



One Light
Outdoor
Wall Lantern

OUTDOOR CYLINDERS

p.578

FINISHES | MATERIAL

White [-15]
Clear Tempered Glass Diffuser

Painted Brushed Nickel [-753]
Clear Tempered Glass Diffuser

Bronze [-10]
Clear Tempered Glass Diffuser

EN★ DAMP WET WOD

WET T24 T24 T24

LED ☾ 🌧️



Large Two
Light Outdoor
Wall Lantern



Small Two
Light Outdoor
Wall Lantern



Large One
Light Outdoor
Wall Lantern



Small One
Light Outdoor
Wall Lantern



Large One Light
Outdoor Ceiling
Flush Mount



Small One Light
Outdoor Ceiling
Flush Mount

NEW

PERRYWOOD

p.474

FINISH | MATERIAL

Black Finish [-12]
Clear Water Glass

EN★ DAMP WET T24 T24



Three Light
Outdoor
Post Lantern



Three Light
Outdoor
Pendant



Large Three Light
Outdoor
Wall Lantern



Medium Three
Light Outdoor
Wall Lantern



Small One
Light Outdoor
Wall Lantern



Extra Small One
Light Outdoor
Wall Lantern

RENVILLE

p.574

FINISHES | MATERIAL

Satin Aluminum [-04]
Satin Etched Glass

Antique Bronze [-71]
Satin Etched Glass

Black [-12]
Satin Etched Glass

EN★ WET T24 T24



Large One Light Outdoor Wall Lantern



Small One Light Outdoor Wall Lantern

SAUGANASH

p.532

FINISHES | MATERIALS

Antique Bronze [-71]
Clear Seeded Glass

Antique Bronze [-71]
Etched Seeded Glass

Black [-12]
Clear Seeded Glass

Black [-12]
Etched Seeded Glass

EN★ DAMP WET ☾ T24 T24



Outdoor Pendant



Outdoor Post Lantern



Large Outdoor Wall Lantern



Small Outdoor Wall Lantern



Outdoor Ceiling Flush Mount

SEVIER

p.500

FINISHES | MATERIAL

Antique Bronze [-71]
Clear Glass

Black [-12]
Clear Glass

EN★ DAMP WET T24 T24



One Light Outdoor Pendant



One Light Outdoor Post Lantern



Extra Large One Light Downlight Outdoor Wall Lantern



Large One Light Uplight Outdoor Wall Lantern



Large One Light Downlight Outdoor Wall Lantern



Small One Light Uplight Outdoor Wall Lantern



Small One Light Downlight Outdoor Wall Lantern

TERRACE

p.484

FINISH | MATERIAL

Oil Rubbed Bronze [-ORB]
Clear Seeded Glass

DAMP WET T24



One Light Hanging Lantern



One Light Post / Pier Lantern



One Light Wall Lantern



One Light Wall Lantern



One Light Wall Lantern



One Light Wall Lantern

TRAFALGAR

p.494

FINISH | MATERIAL

Oxidized Bronze [-46]
Clear Seeded Glass

EN★ DAMP WET T24 T24



Three Light
Outdoor
Pendant



Three Light
Outdoor
Post Lantern



Large Three
Light Outdoor
Wall Lantern



Medium Two
Light Outdoor
Wall Lantern



Small Two
Light Outdoor
Wall Lantern

WRIGHT HOUSE

p.558

FINISHES | MATERIALS

Sorrel Brown [-SBR]
Striated Ivory Glass
Oil Rubbed Bronze [-SBR]
White Opal Etched Glass

DAMP WET T24



One Light
Outdoor
Pendant



One Light
Outdoor
Post Lantern



One Light
Outdoor
Wall Lantern



One Light
Outdoor
Wall Lantern



One Light
Outdoor
Wall Lantern



Two Light
Outdoor Ceiling
Flush Mount

WYNFIELD

p.508

FINISHES | MATERIALS

Black [-12]
Clear Beveled Glass
Black [-12]
Frosted (Not Available for Post Lantern)
Black [-12]
Etched, White Inside (For Flush Mount Only)

EN★ DAMP WET T24 T24



Two Light
Outdoor
Post Lantern



Large One/Two
Light Outdoor
Wall Lantern



Medium One
Light Outdoor
Wall Lantern



Small One
Light Outdoor
Wall Lantern



Two Light
Outdoor Ceiling
Flush Mount

YORKTOWN

p.476

FINISHES | MATERIAL

Black [-12]
Swirled, Marbleized Glass
Forged Iron [-185]
Swirled, Marbleized Glass

EN★ DAMP WET T24 T24



One Light
Outdoor
Pendant



One Light
Outdoor
Post Lantern



Large One
Light Outdoor
Wall Lantern



Medium One
Light Outdoor
Wall Lantern



Small One
Light Outdoor
Wall Lantern



Two Light
Outdoor Ceiling
Flush Mount

PRODUCT SHOWN: SOCORRO SIX LIGHT HALL / FOYER
IN WASHED PINE FINISH AND CHROME ACCENTS





INDOOR

collections

ZIRE

DAMP

NINE LIGHT CHANDELIER

D: 32" H: 30.25"

10' of wire pre-laced through 6' of chain

T24

3190309-05

(9) Candelabra Base 60w max.

T24 EN★

3190309EN-05

(9) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

See more Chrome Finish
on p.54



CHROME FINISH
CLEAR GLASS

DAMP

NINE LIGHT CHANDELIER

D: 32" H: 30.25"
10' of wire pre-laced through 6' of chain

T24

3190309-962
(9) Candelabra Base 60w max.

T24 EN★

3190309EN-962
(9) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

See more Brushed Nickel Finish
on p.56



BRUSHED NICKEL FINISH
CLEAR GLASS

DAMP

NINE LIGHT CHANDELIER

D: 32" H: 30.25"
10' of wire pre-laced through 6' of chain

T24

3190309-778
(9) Candelabra Base 60w max.

T24 EN★

3190309EN-778
(9) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

See more Brushed Oil Rubbed Bronze Finish
on p.58



BRUSHED OIL RUBBED BRONZE FINISH
CLEAR GLASS

ZIRE

DAMP

FIVE LIGHT ISLAND PENDANT

L: 48" W: 9" H: 11"
Supplied with 10' of wire,
(2) 6" stems, (6) 12" stems

T24

6690305-05
(5) Candelabra Base 60w max.

T24 EN★

6690305EN-05
(5) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

FIVE LIGHT CHANDELIER

D: 26" H: 22.125"
10' of wire pre-laced through 6' of chain

T24

3190305-05
(5) Candelabra Base 60w max.

T24 EN★

3190305EN-05
(5) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP +

THREE LIGHT CHANDELIER

D: 18" H: 21.125" Semi-Flush H: 14"
6' of wire pre-laced through 3' of chain

T24

3190303-05
(3) Candelabra Base 60w max.

T24 EN★

3190303EN-05
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.





DAMP

ONE LIGHT PENDANT

D: 6" H: 10.875"
 Supplied with 10' of wire,
 (3) 12" stems, (1) 6" stem
 and sloped ceiling mounting hardware

T24

6590301-05
 (1) Medium Base 60w max.



DAMP

ONE LIGHT MINI-PENDANT

D: 4" H: 8.5"
 Supplied with 6.5' black
 field adjustable cord

T24

6190301-05
 (1) Medium Base 60w max.



DAMP +

ONE LIGHT WALL / BATH SCONCE

W: 4.375" H: 7.875" E: 6.5"
 Height from center of outlet box
 up: 4.375" down: 3.5"

T24

4190301-05
 (1) Medium Base 75w max.

T24 EN★

4190301EN3-05
 (1) Med. Base LED, 3000K,
 9.5w 800 lumen lamps incl.



DAMP +

ZIRE WALL / BATH COLLECTION

Chrome

See more Zire
 Wall / Bath on p.393

ZIRE

DAMP

FIVE LIGHT ISLAND PENDANT

L: 48" W: 9" H: 11"
Supplied with 10' of wire,
(2) 6" stems, (6) 12" stems

T24

6690305-962

(5) Candelabra Base 60w max.

T24 EN★

6690305EN-962

(5) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

FIVE LIGHT CHANDELIER

D: 26" H: 22.125"
10' of wire pre-laced through 6' of chain

T24

3190305-962

(5) Candelabra Base 60w max.

T24 EN★

3190305EN-962

(5) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP +

THREE LIGHT CHANDELIER

D: 18" H: 21.125" Semi-Flush H: 14"
6' of wire pre-laced through 3' of chain

T24

3190303-962

(3) Candelabra Base 60w max.

T24 EN★

3190303EN-962

(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.





DAMP

ONE LIGHT PENDANT

D: 6" H: 10.875"
 Supplied with 10' of wire,
 (3) 12" stems, (1) 6" stem
 and sloped ceiling mounting hardware

T24

6590301-962
 (1) Medium Base 60w max.



DAMP

ONE LIGHT MINI-PENDANT

D: 4" H: 8.5"
 Supplied with 6.5' black
 field adjustable cord

T24

6190301-962
 (1) Medium Base 60w max.



DAMP +

ONE LIGHT WALL / BATH SCONCE

W: 4.375" H: 7.875" E: 6.5"
 Height from center of outlet box
 up: 4.375" down: 3.5"

T24

4190301-962
 (1) Medium Base 75w max.

T24 EN★

4190301EN3-962
 (1) Med. Base LED, 3000K,
 9.5w 800 lumen lamps incl.



DAMP +

ZIRE WALL / BATH COLLECTION

Brushed Nickel

See more Zire
 Wall / Bath on p.393

ZIRE

DAMP

FIVE LIGHT ISLAND PENDANT

L: 48" W: 9" H: 11"
Supplied with 10' of wire,
(2) 6" stems, (6) 12" stems

T24

6690305-778
(5) Candelabra Base 60w max.

T24 EN★

6690305EN-778
(5) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

FIVE LIGHT CHANDELIER

D: 26" H: 22.125"
10' of wire pre-laced through 6' of chain

T24

3190305-778
(5) Candelabra Base 60w max.

T24 EN★

3190305EN-778
(5) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP +

THREE LIGHT CHANDELIER

D: 18" H: 21.125" Semi-Flush H: 14"
6' of wire pre-laced through 3' of chain

T24

3190303-778
(3) Candelabra Base 60w max.

T24 EN★

3190303EN-778
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.





DAMP

ONE LIGHT PENDANT

D: 6" H: 10.875"
 Supplied with 10' of wire,
 (3) 12" stems, (1) 6" stem
 and sloped ceiling mounting hardware

T24

6590301-778

(1) Medium Base 60w max.



DAMP

ONE LIGHT MINI-PENDANT

D: 4" H: 8.5"
 Supplied with 6.5' black
 field adjustable cord

T24

6190301-778

(1) Medium Base 60w max.



DAMP +

ONE LIGHT WALL / BATH SCONCE

W: 4.375" H: 7.875" E: 6.5"
 Height from center of outlet box
 up: 4.375" down: 3.5"

T24

4190301-778

(1) Medium Base 75w max.

T24 EN★

4190301EN3-778

(1) Med. Base LED, 3000K, 9.5w 800 lumen lamps incl.



DAMP +

ZIRE WALL / BATH COLLECTION

Brushed Oil Rubbed Bronze

See more Zire
 Wall / Bath on p.393

ALTURAS

PRODUCT SHOWN: ALTURAS FIVE LIGHT
CHANDELIER IN SATIN BRONZE FINISH
DESIGN: JLV CREATIVE
BUILDER: CRESCENT HOMES
PHOTOGRAPHER: ROB MCDANIEL



DAMP

NINE LIGHT CHANDELIER

D: 32.5" H: 32.75"
12' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3124609-848
(9) Medium Base 60w max.

T24 EN★

3124609EN3-848
(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Satin Bronze Finish on p.62



SATIN BRONZE FINISH
ETCHED GLASS, WHITE INSIDE



BRUSHED NICKEL FINISH
ETCHED GLASS, WHITE INSIDE



BRUSHED OIL RUBBED BRONZE FINISH
ETCHED GLASS, WHITE INSIDE

DAMP

NINE LIGHT CHANDELIER

D: 32.5" H: 32.75"
12' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3124609-962
(9) Medium Base 60w max.

T24 EN★

3124609EN3-962
(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel Finish on p.64

DAMP

NINE LIGHT CHANDELIER

D: 32.5" H: 32.75"
12' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3124609-778
(9) Medium Base 60w max.

T24 EN★

3124609EN3-778
(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Oil Rubbed Bronze Finish on p.66

ALTURAS

DAMP

FIVE LIGHT CHANDELIER

D: 27.25" H: 27"
12' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3124605-848
(5) Medium Base 100w max.

T24 EN★

3124605EN3-848
(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 19" H: 18.75"
12' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3124603-848
(3) Medium Base 100w max.

T24 EN★

3124603EN3-848
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT PENDANT

D: 19" H: 18.75"
12' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6624603-848
(3) Medium Base 100w max.

T24 EN★

6624603EN3-848
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP +

**TWO LIGHT
SEMI-FLUSH
CONVERTIBLE PENDANT**

D: 14" H: 16.5" Semi-Flush H: 15"
6" wire pre-laced through 3' chain

T24

7724602-848
(2) Medium Base 60w max.

T24 EN★

7724602EN3-848
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

**ONE LIGHT
MINI-PENDANT**

D: 3.5" H: 7.25"
12' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6124601-848
(1) Medium Base 100w max.

T24 EN★

6124601EN3-848
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**ONE LIGHT
WALL / BATH**

W: 4.5" H: 8.75" E: 6.25"
Height from center of outlet box
up: 5.75" down: 3"

T24

4124601-848
(1) Medium Base 100w max.

T24 EN★

4124601EN3-848
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**ALTURAS
WALL / BATH
COLLECTION**

Satin Bronze

See more Alturas
Wall / Bath on p.394

Recommended
Product



NASH CEILING
FLUSH MOUNT
Satin Bronze
p.364

ALTURAS

DAMP

FIVE LIGHT CHANDELIER

D: 27.25" H: 27"
12" wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3124605-962
(5) Medium Base 100w max.

T24 EN★

3124605EN3-962
(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 19" H: 18.75"
12" wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3124603-962
(3) Medium Base 100w max.

T24 EN★

3124603EN3-962
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT PENDANT

D: 19" H: 18.75"
12" wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6624603-962
(3) Medium Base 100w max.

T24 EN★

6624603EN3-962
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP +

**TWO LIGHT
SEMI-FLUSH
CONVERTIBLE PENDANT**

D: 14" H: 16.5" Semi-Flush H: 15"
6" wire pre-laced through 3' chain

T24

7724602-962
(2) Medium Base 60w max.

T24 EN★

7724602EN3-962
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

**ONE LIGHT
MINI-PENDANT**

D: 3.5" H: 7.25"
12' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6124601-962
(1) Medium Base 100w max.

T24 EN★

6124601EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**ONE LIGHT
WALL / BATH**

W: 4.5" H: 8.75" E: 6.25"
Height from center of outlet box
up: 5.75" down: 3"

T24

4124601-962
(1) Medium Base 100w max.

T24 EN★

4124601EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**ALTURAS
WALL / BATH
COLLECTION**

Brushed Nickel

See more Alturas
Wall / Bath on p.394

Recommended
Product



NASH CEILING
FLUSH MOUNT
Brushed Nickel
p.364

ALTURAS

DAMP

FIVE LIGHT CHANDELIER

D: 27.25" H: 27"
12' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3124605-778
(5) Medium Base 100w max.

T24 EN★

3124605EN3-778
(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 19" H: 18.75"
12' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3124603-778
(3) Medium Base 100w max.

T24 EN★

3124603EN3-778
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT PENDANT

D: 19" H: 18.75"
12' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6624603-778
(3) Medium Base 100w max.

T24 EN★

6624603EN3-778
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP +

**TWO LIGHT
SEMI-FLUSH
CONVERTIBLE PENDANT**

D: 14" H: 16.5" Semi-Flush H: 15"
6" wire pre-laced through 3' chain

T24

7724602-778
(2) Medium Base 60w max.

T24 EN★

7724602EN3-778
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

**ONE LIGHT
MINI-PENDANT**

D: 3.5" H: 7.25"
12' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6124601-778
(1) Medium Base 100w max.

T24 EN★

6124601EN3-778
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**ONE LIGHT
WALL / BATH**

W: 4.5" H: 8.75" E: 6.25"
Height from center of outlet box
up: 5.75" down: 3"

T24

4124601-778
(1) Medium Base 100w max.

T24 EN★

4124601EN3-778
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**ALTURAS
WALL / BATH
COLLECTION**

Brushed Oil Rubbed Bronze

See more Alturas
Wall / Bath on p.394

Recommended
Product



NASH CEILING
FLUSH MOUNT
Heirloom Bronze
p.364

TOWNER

DAMP

EIGHT LIGHT ISLAND PENDANT

L: 45" W: 24.5" H: 23.25"
10' wire, (3) 12" stems, (1) 6" stem


T24

6641308-848
(8) Medium Base 60w max.

T24 EN★

6641308EN3-848
(8) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Satin Bronze Finish on p.70



SATIN BRONZE FINISH
BLACK STEEL SHADES

DAMP

**EIGHT LIGHT
ISLAND PENDANT**

L: 45" W: 24.5" H: 23.25"
10" wire, (3) 12" stems, (1) 6" stem

T24

6641308-962
(8) Medium Base 60w max.

T24 EN★

6641308EN3-962
(8) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel Finish on p.72



BRUSHED NICKEL FINISH
BLACK STEEL SHADES

TOWNER

DAMP

SEVEN LIGHT CHANDELIER

D: 35" H: 27.75"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3141307-848

(7) Medium Base 60w max.

T24 EN★

3141307EN3-848

(7) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

FIVE LIGHT CHANDELIER

D: 29" H: 24.75"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3141305-848

(5) Medium Base 60w max.

T24 EN★

3141305EN3-848

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

FIVE LIGHT CLUSTER

D: 17.25" H: 28" (with 5" spacing)
Supplied with 8' black field
adjustable cords

T24

5141305-848

(5) Medium Base 60w max.

T24 EN★

5141305EN3-848

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP

THREE LIGHT CHANDELIER

D: 24" H: 22"
10' wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

3141303-848

(3) Medium Base 60w max.

T24 EN★

3141303EN3-848

(3) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CLUSTER

D: 14.5" H: 18" (with 5" spacing)
Supplied with 8' black field adjustable cords

T24

5141303-848

(3) Medium Base 60w max.

T24 EN★

5141303EN3-848

(3) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT MINI-PENDANT

D: 7" H: 8.5"
Supplied with 10' black field adjustable cord

T24

6141301-848

(1) Medium Base 60w max.

T24 EN★

6141301EN3-848

(1) Med. Base LED 3000K, 9.5w, 800 lumen lamp incl.



DAMP +

ONE LIGHT WALL / BATH

W: 7" H: 8.375" E: 8"
Height from center of outlet box
up: 6" down: 2.375"

T24

4141301-848

(1) Medium Base 60w max.

T24 EN★

4141301EN3-848

(1) Med. Base LED 3000K, 9.5w, 800 lumen lamp incl.

Recommended Products



NASH CEILING FLUSH MOUNTS
Satin Bronze
p.364



MULTI-PORT CANOPIES
Satin Bronze
p.358

TOWNER

DAMP

SEVEN LIGHT CHANDELIER

D: 35" H: 27.75"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3141307-962

(7) Medium Base 60w max.

T24 EN★

3141307EN3-962

(7) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

FIVE LIGHT CHANDELIER

D: 29" H: 24.75"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3141305-962

(5) Medium Base 60w max.

T24 EN★

3141305EN3-962

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

FIVE LIGHT CLUSTER

D: 17.25" H: 28" (with 5" spacing)
Supplied with 8' black field
adjustable cords

T24

5141305-962

(5) Medium Base 60w max.

T24 EN★

5141305EN3-962

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP

THREE LIGHT CHANDELIER

D: 24" H: 22"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3141303-962

(3) Medium Base 60w max.

T24 EN★

3141303EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CLUSTER

D: 14.5" H: 18" (with 5" spacing)
Supplied with 8' black field
adjustable cords

T24

5141303-962

(3) Medium Base 60w max.

T24 EN★

5141303EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

**ONE LIGHT
MINI-PENDANT**

D: 7" H: 8.5"
Supplied with 10' black field
adjustable cord

T24

6141301-962

(1) Medium Base 60w max.

T24 EN★

6141301EN3-962

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**ONE LIGHT
WALL / BATH**

W: 7" H: 8.375" E: 8"
Height from center of outlet box
up: 6" down: 2.375"

T24

4141301-962

(1) Medium Base 60w max.

T24 EN★

4141301EN3-962

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

Recommended
Products

NASH CEILING
FLUSH MOUNTS
Brushed Nickel
p.364



MULTI-PORT
CANOPIES
Brushed Nickel
p.358

DRISCOLL

DAMP

NINE LIGHT CHANDELIER

D: 32" H: 29.75"

10' wire pre-laced through 3' chain

T24

3140409-848

(9) Medium Base 100w max.

T24 EN★

3140409EN3-848

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

See more Satin Bronze Finish on p.76



SATIN BRONZE FINISH
ETCHED GLASS, WHITE INSIDE

DAMP

NINE LIGHT CHANDELIER

D: 32" H: 29.75"

10' wire pre-laced through 3' chain

T24

3140409-962

(9) Medium Base 100w max.

T24 EN★

3140409EN3-962(9) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

See more Brushed Nickel Finish on p.77

BRUSHED NICKEL FINISH
ETCHED GLASS, WHITE INSIDE

DAMP

FIVE LIGHT CHANDELIER

D: 25.25" H: 17.75"
10' wire pre-laced through 3' chain

T24

3140405-848
(5) Medium Base 100w max.

T24 EN★

3140405EN3-848
(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 20.5" H: 16.75"
10' wire pre-laced through 3' chain

T24

3140403-848
(3) Medium Base 100w max.

T24 EN★

3140403EN3-848
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT MINI-PENDANT

D: 5.25" H: 11.75"
Supplied with 6.5' of black
field adjustable cord

T24

6140401-848
(1) Medium Base 100w max.

T24 EN★

6140401EN3-848
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT WALL / BATH

W: 5.25" H: 11.75" E: 6.75"
Height from center of outlet box
up: 8.75"

T24

4140401-848
(1) Medium Base 100w max.

T24 EN★

4140401EN3-848
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

DRISCOLL WALL / BATH COLLECTION

Satin Bronze

See more Driscoll
Wall / Bath on p.405

Recommended
Products



NASH CEILING
FLUSH MOUNT
Satin Bronze
p.364



MULTI-PORT
CANOPIES
Satin Bronze
p.358

DAMP

FIVE LIGHT CHANDELIER

D: 25.25" H: 17.75"
10' wire pre-laced through 3' chain

T24

3140405-962
(5) Medium Base 100w max.

T24 EN★

3140405EN3-962
(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 20.5" H: 16.75"
10' wire pre-laced through 3' chain

T24

3140403-962
(3) Medium Base 100w max.

T24 EN★

3140403EN3-962
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT MINI-PENDANT

D: 5.25" H: 11.75"
Supplied with 6.5' of black
field adjustable cord

T24

6140401-962
(1) Medium Base 100w max.

T24 EN★

6140401EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT WALL / BATH


W: 5.25" H: 11.75" E: 6.75"
Height from center of outlet box
up: 8.75"

T24

4140401-962
(1) Medium Base 100w max.

T24 EN★

4140401EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

DRISCOLL WALL / BATH COLLECTION

Brushed Nickel
Chrome

See more Driscoll
Wall / Bath on p.405

Recommended
Products



NASH CEILING
FLUSH MOUNT
Brushed Nickel
p.364



MULTI-PORT
CANOPIES
Brushed Nickel
p.358

WINNETKA

50LB

FIFTEEN LIGHT CHANDELIER

D: 46.5" H: 42.75"
12' wire pre-laced through 10'
chain

T24

31663-962

(15) Medium Base 60w max.

T24 EN★

31663EN3-962

(15) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel Finish on p.80



BRUSHED NICKEL FINISH
SATIN ETCHED GLASS

50LB

**FIFTEEN LIGHT
CHANDELIER**

D: 46.5" H: 42.75"
12' wire pre-laced through 10'
chain

T24

31663-839

(15) Medium Base 60w max.

T24 EN★

31663EN3-839

(15) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Blacksmith Finish on p.82



BLACKSMITH FINISH
SATIN ETCHED GLASS

WINNETKA

NINE LIGHT CHANDELIER

D: 32" H: 31.75"
12' wire pre-laced through 10' chain

T24

31662-962

(9) Medium Base 100w max.

T24 EN★

31662EN3-962

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



FIVE LIGHT CHANDELIER

D: 25" H: 21.25"
12' wire pre-laced through 10' chain

T24

31661-962

(5) Medium Base 100w max.

T24 EN★

31661EN3-962

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



FOUR LIGHT PENDANT

D: 28.25" H: 27.5"
12' wire pre-laced through 10' chain

T24

65662-962

(4) Medium Base 100w max.

T24 EN★

65662EN3-962

(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT CHANDELIER

D: 21" H: 20.25"
12' wire pre-laced through 10' chain

T24

31660-962

(3) Medium Base 100w max.

T24 EN★

31660EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT PENDANT

D: 18" H: 24"
12' wire pre-laced through 10' chain

T24

65661-962

(3) Medium Base 100w max.

T24 EN★

65661EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

**THREE LIGHT
CEILING FLUSH MOUNT**

D: 17.75" H: 6"

T24

75662-962

(3) Medium Base 60w max.

T24 EN★

75662EN3-962(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

+

**TWO LIGHT
SEMI-FLUSH
CONVERTIBLE PENDANT**D: 14.25" H: 14" Semi-Flush H: 12"
12" wire pre-laced through 10' chain

T24

77660-962

(2) Medium Base 60w max.

T24 EN★

77660EN3-962(2) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

DAMP

**TWO LIGHT
CEILING FLUSH MOUNT**

D: 14" H: 5.25"

T24

75661-962

(2) Medium Base 60w max.

T24 EN★

75661EN3-962(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.**ONE LIGHT PENDANT**D: 16.75" H: 15.25"
12" wire pre-laced through 10'
chain

T24

65660-962

(1) Medium Base 150w max.

T24 EN★

65660EN3-962(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.**ONE LIGHT
MINI-PENDANT**D: 6.25" H: 14.75"
10' wire, (3) 12" stems, 12" chain

T24

61660-962

(1) Medium Base 100w max.

T24 EN★

61660EN3-962(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

DAMP +

**ONE LIGHT
WALL / BATH**W: 6" H: 9.25" E: 7.5"
Height from center of outlet box
up: 4" down: 5.25"

T24

44660-962

(1) Medium Base 100w max.

T24 EN★

44660EN3-962(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

DAMP +

**WINNETKA
WALL / BATH
COLLECTION**

Brushed Nickel

See more Winnetka
Wall / Bath on p.435Recommended
ProductGEARY PENDANT
Brushed Nickel
p.346

WINNETKA

NINE LIGHT CHANDELIER

D: 32" H: 31.75"
12' wire pre-laced through 10' chain

T24

31662-839

(9) Medium Base 100w max.

T24 EN★

31662EN3-839

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



FIVE LIGHT CHANDELIER

D: 25" H: 21.25"
12' wire pre-laced through 10' chain

T24


31661-839

(5) Medium Base 100w max.

T24 EN★

31661EN3-839

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



FOUR LIGHT PENDANT

D: 28.25" H: 27.5"
12' wire pre-laced through 10' chain

T24

65662-839

(4) Medium Base 100w max.

T24 EN★

65662EN3-839

(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT CHANDELIER

D: 21" H: 20.25"
12' wire pre-laced through 10' chain

T24

31660-839

(3) Medium Base 100w max.

T24 EN★

31660EN3-839

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT PENDANT

D: 18" H: 24"
12' wire pre-laced through 10' chain

T24

65661-839

(3) Medium Base 100w max.

T24 EN★

65661EN3-839

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CEILING FLUSH MOUNT

D: 17.75" H: 6"

T24

75662-839

(3) Medium Base 60w max.

T24 EN★

75662EN3-839

(3) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



+

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 14.25" H: 14" Semi-Flush H: 12" 12' wire pre-laced through 10' chain

T24

77660-839

(2) Medium Base 60w max.

T24 EN★

77660EN3-839

(2) Med. Base LED 3000K, 9.5w, 800 lumen lamp incl.



DAMP

TWO LIGHT CEILING FLUSH MOUNT

D: 14" H: 5.25"

T24

75661-839

(2) Medium Base 60w max.

T24 EN★

75661EN3-839

(2) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



ONE LIGHT PENDANT

D: 16.75" H: 15.25" 12' wire pre-laced through 10' chain

T24

65660-839

(1) Medium Base 150w max.

T24 EN★

65660EN3-839

(1) Med. Base LED 3000K, 9.5w, 800 lumen lamp incl.



ONE LIGHT MINI-PENDANT

D: 6.25" H: 14.75" 10' wire, (3) 12" stems, 12" chain

T24

61660-839

(1) Medium Base 100w max.

T24 EN★

61660EN3-839

(1) Med. Base LED 3000K, 9.5w, 800 lumen lamp incl.



DAMP +

ONE LIGHT WALL / BATH

W: 6" H: 9.25" E: 7.5" Height from center of outlet box up: 4" down: 5.25"

T24

44660-839

(1) Medium Base 100w max.

T24 EN★

44660EN3-839

(1) Med. Base LED 3000K, 9.5w, 800 lumen lamp incl.



DAMP +

WINNETKA WALL / BATH COLLECTION

Blacksmith

See more Winnetka Wall / Bath on p.435



DAMP +

WINNETKA OUTDOOR COLLECTION

Forged Iron

See more Winnetka Outdoor on p.542

Recommended Product



GEARY PENDANT
Blacksmith
p.346

OSLO

NINE LIGHT CHANDELIER

D: 26" H: 26.75"
12' wire pre-laced through 10' chain

T24

31162-05

(9) Medium Base 100w max.

T24 EN★

31162EN3-05

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Chrome Finish on p.86



CHROME FINISH
CASED OPAL ETCHED GLASS

NINE LIGHT CHANDELIER

D: 26" H: 26.75"

12' wire pre-laced through 10' chain

T24

31162-962

(9) Medium Base 100w max.

T24 EN★

31162EN3-962(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel Finish on p.88

BRUSHED NICKEL FINISH
CASED OPAL ETCHED GLASS**NINE LIGHT CHANDELIER**

D: 26" H: 26.75"

12' wire pre-laced through 10' chain

T24

31162-839

(9) Medium Base 100w max.

T24 EN★

31162EN3-839(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Blacksmith Finish on p.90

BLACKSMITH FINISH
CASED OPAL ETCHED GLASS

OSLO



FIVE LIGHT CHANDELIER

D: 24" H: 20" Downlight H: 27"
12' wire pre-laced through 10' chain



31161-05

(5) Medium Base 100w max.



31161EN3-05

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT CHANDELIER

D: 15" H: 16.5" Downlight H: 22"
12' wire pre-laced through 10' chain



31160-05

(3) Medium Base 100w max.



31160EN3-05

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT ISLAND PENDANT

L: 25.25" W: 4" H: 9.5"
12' wire, (6) 12" stems, (2) 6" stems



66160-05

(3) Medium Base 100w max.



66160EN3-05

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





ETCHED GLASS, WHITE INSIDE



**TWO LIGHT
SEMI-FLUSH
CONVERTIBLE PENDANT**

D: 13.5" H: 11.25" Semi-Flush H: 10"
12' wire pre-laced through 10' chain



77160-05

(2) Medium Base 100w max.



77160EN3-05

(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



ETCHED GLASS, WHITE INSIDE

ONE LIGHT PENDANT

D: 15.75" H: 8.75"
12' wire pre-laced through 10' chain



65160-05

(1) Medium Base 150w max.



65160EN3-05

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



**ONE LIGHT
MINI-PENDANT**

D: 4" H: 5.75"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware



61160-05

(1) Medium Base 100w max.



61160EN3-05

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



**ONE LIGHT
WALL / BATH**

W: 4.75" H: 8.75" E: 5.5"
Height from center of outlet box
up: 4.75" down: 4"



41160-05

(1) Medium Base 100w max.



41160EN3-05

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



**OSLO
WALL / BATH
COLLECTION**

Chrome

See more Oslo
Wall / Bath on p.398

Recommended
Products



GEARY PENDANT
Brushed Nickel
p.346



GEARY CEILING
FLUSH MOUNT
Chrome
p.366

OSLO



FIVE LIGHT CHANDELIER

D: 24" H: 20" Downlight H: 27"
12' wire pre-laced through 10' chain

T24

31161-962

(5) Medium Base 100w max.

T24 EN★

31161EN3-962

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT CHANDELIER

D: 15" H: 16.5" Downlight H: 22"
12' wire pre-laced through 10' chain

T24

31160-962

(3) Medium Base 100w max.

T24 EN★

31160EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT ISLAND PENDANT

L: 25.25" W: 4" H: 9.5"
12' wire, (6) 12" stems, (2) 6" stems

T24

66160-962

(3) Medium Base 100w max.

T24 EN★

66160EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





ETCHED GLASS, WHITE INSIDE



**TWO LIGHT
SEMI-FLUSH
CONVERTIBLE PENDANT**

D: 13.5" H: 11.25" Semi-Flush H: 10"
12' wire pre-laced through 10' chain

T24

77160-962

(2) Medium Base 100w max.

T24 EN★

77160EN3-962

(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



ETCHED GLASS, WHITE INSIDE

ONE LIGHT PENDANT

D: 15.75" H: 8.75"
12' wire pre-laced through 10' chain

T24

65160-962

(1) Medium Base 150w max.

T24 EN★

65160EN3-962

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



**ONE LIGHT
MINI-PENDANT**

D: 4" H: 5.75"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

61160-962

(1) Medium Base 100w max.

T24 EN★

61160EN3-962

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**ONE LIGHT
WALL / BATH**

W: 4.75" H: 8.75" E: 5.5"
Height from center of outlet box
up: 4.75" down: 4"

T24

41160-962

(1) Medium Base 100w max.

T24 EN★

41160EN3-962

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**OSLO
WALL / BATH
COLLECTION**

Brushed Nickel

See more Oslo
Wall / Bath on p.398

Recommended
Products



GEARY PENDANT
Brushed Nickel
p.346



GEARY CEILING
FLUSH MOUNT
Brushed Nickel
p.366

OSLO



FIVE LIGHT CHANDELIER

D: 24" H: 20" Downlight H: 27"
12' wire pre-laced through 10' chain

T24

31161-839

(5) Medium Base 100w max.

T24 EN★

31161EN3-839

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT CHANDELIER

D: 15" H: 16.5" Downlight H: 22"
12' wire pre-laced through 10' chain

T24

31160-839

(3) Medium Base 100w max.

T24 EN★

31160EN3-839

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT ISLAND PENDANT

L: 25.25" W: 4" H: 9.5"
12' wire, (6) 12" stems, (2) 6" stems

T24

66160-839

(3) Medium Base 100w max.

T24 EN★

66160EN3-839

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





ETCHED GLASS, WHITE INSIDE



**TWO LIGHT
SEMI-FLUSH
CONVERTIBLE PENDANT**

D: 13.5" H: 11.25" Semi-Flush H: 10"
12' wire pre-laced through 10' chain



77160-839
(2) Medium Base 100w max.



77160EN3-839
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



ETCHED GLASS, WHITE INSIDE

ONE LIGHT PENDANT

D: 15.75" H: 8.75"
12' wire pre-laced through 10' chain



65160-839
(1) Medium Base 150w max.



65160EN3-839
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



**ONE LIGHT
MINI-PENDANT**

D: 4" H: 5.75"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware



61160-839
(1) Medium Base 100w max.



61160EN3-839
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



**ONE LIGHT
WALL / BATH**

W: 4.75" H: 8.75" E: 5.5"
Height from center of outlet box
up: 4.75" down: 4"



41160-839
(1) Medium Base 100w max.



41160EN3-839
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



**OSLO
WALL / BATH
COLLECTION**
Blacksmith

See more Oslo
Wall / Bath on p.398

Recommended
Products



GEARY PENDANT
Blacksmith
p.346



GEARY CEILING
FLUSH MOUNTS
Blacksmith
p.366

CANFIELD

PRODUCT SHOWN: CANFIELD THREE LIGHT
UPLIGHT PENDANT IN BURNT SIENNA FINISH



DAMP 50LB

**FIFTEEN LIGHT
CHANDELIER**D: 40.125" H: 39"
12' wire pre-laced through 10' chain

T24

3128815-962
(15) Medium Base 60w max.

T24 EN★

3128815EN3-962
(15) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel Finish on p.94

BRUSHED NICKEL FINISH
ETCHED GLASS, WHITE INSIDE

DAMP 50LB

**FIFTEEN LIGHT
CHANDELIER**D: 40.125" H: 39"
12' wire pre-laced through 10' chain

T24

3128815-710
(15) Medium Base 60w max.

T24 EN★

3128815EN3-710
(15) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Burnt Sienna Finish on p.96

BURNT SIENNA FINISH
ETCHED GLASS, WHITE INSIDE

CANFIELD

DAMP

NINE LIGHT CHANDELIER

D: 31.375" H: 26"
6' of wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3128809-962

(9) Medium Base 100w max.

T24 EN★

3128809EN3-962

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

FIVE LIGHT CHANDELIER

D: 23.875" H: 14.5"
6' of wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3128805-962

(5) Medium Base 100w max.

T24 EN★

3128805EN3-962

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 19.625" H: 13.125"
6' of wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3128803-962

(3) Medium Base 100w max.

T24 EN★

3128803EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP

**THREE LIGHT
UPLIGHT PENDANT**

D: 16" H: 18.5"

10' wire pre-laced through 6' chain

T24

6528803-962

(3) Medium Base 100w max.

T24 EN★

6528803EN3-962(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

DAMP

**THREE LIGHT
SEMI-FLUSH
CEILING MOUNT**

D: 16" H: 12.5"

T24

7728803-962

(3) Medium Base 100w max.

T24 EN★

7728803EN3-962(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

DAMP

**ONE LIGHT
MINI-PENDANT**

D: 5.5" H: 6.375"

Supplied with 10' of Wire,
(1) 6" stem, (3) 12" stems
and sloped ceiling mounting hardware

T24

6128801-962

(1) Medium Base 100w max.

T24 EN★

6128801EN3-962(1) Med. Base LED 3000K,
9.5w Bulb Lamps incl.

DAMP +

**ONE LIGHT
WALL / BATH**

W: 5.5" H: 8.25" E: 7.25"

Height from center of outlet box
up: 4.375" down: 3.875"

T24

4128801-962

(1) Medium Base 100w max.

T24 EN★

4128801EN3-962(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

DAMP +

**CANFIELD
WALL / BATH
COLLECTION**

Brushed Nickel

See more Canfield
Wall / Bath on p.404

CANFIELD

DAMP

NINE LIGHT CHANDELIER

D: 31.375" H: 26"
6' of wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3128809-710

(9) Medium Base 100w max.

T24 EN★

3128809EN3-710

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

FIVE LIGHT CHANDELIER

D: 23.875" H: 14.5"
6' of wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24


3128805-710

(5) Medium Base 100w max.

T24 EN★

3128805EN3-710

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 19.625" H: 13.125"
6' of wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3128803-710

(3) Medium Base 100w max.

T24 EN★

3128803EN3-710

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP

**THREE LIGHT
UPLIGHT PENDANT**

D: 16" H: 18.5"
10' wire pre-laced through 6' chain

T24

6528803-710
(3) Medium Base 100w max.

T24 EN★

6528803EN3-710
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

**THREE LIGHT
SEMI-FLUSH
CEILING MOUNT**

D: 16" H: 12.5"

T24

7728803-710
(3) Medium Base 100w max.

T24 EN★

7728803EN3-710
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

**ONE LIGHT
MINI-PENDANT**

D: 5.5" H: 6.375"
Supplied with 10' of Wire,
(1) 6" stem, (3) 12" stems
and sloped ceiling mounting hardware

T24

6128801-710
(1) Medium Base 100w max.

T24 EN★

6128801EN3-710
(1) Med. Base LED 3000K,
9.5w Bulb Lamps incl.



DAMP +

**ONE LIGHT
WALL / BATH**

W: 5.5" H: 8.25" E: 7.25"
Height from center of outlet box
up: 4.375" down: 3.875"

T24

4128801-710
(1) Medium Base 100w max.

T24 EN★

4128801EN3-710
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

**CANFIELD
WALL / BATH
COLLECTION**

Burnt Sienna

See more Canfield
Wall / Bath on p.404

KERRVILLE

DAMP

NINE LIGHT CHANDELIER

D: 29" H: 29.5"

10' wire pre-laced through 6' chain

T24

3115209-05

(9) Medium Base 75w max.

T24

EN★

3115209EN3-05

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Chrome Finish on p.100



CHROME FINISH
SATIN ETCHED GLASS

DAMP

NINE LIGHT CHANDELIER

D: 29" H: 29.5"
10' wire pre-laced through 6' chain

T24

3115209-962
(9) Medium Base 75w max.

T24 EN★

3115209EN3-962
(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel Finish on p.102



BRUSHED NICKEL FINISH
SATIN ETCHED GLASS

DAMP

NINE LIGHT CHANDELIER

D: 29" H: 29.5"
10' wire pre-laced through 6' chain

T24

3115209-782
(9) Medium Base 75w max.

T24 EN★

3115209EN3-782
(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Heirloom Bronze Finish on p.104



HEIRLOOM BRONZE FINISH
SATIN ETCHED GLASS

KERRVILLE

DAMP +

FIVE LIGHT CHANDELIER

D: 20.5" H: 17" Downlight H: 24.75"
6' wire pre-laced through 3' chain

T24

3115205-05

(5) Medium Base 100w max.

T24 EN★

3115205EN3-05

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

THREE LIGHT CHANDELIER

D: 18" H: 15" Downlight H: 22"
6' wire pre-laced through 3' chain

T24

3115203-05

(3) Medium Base 100w max.

T24 EN★

3115203EN3-05

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT PENDANT

D: 19.25" H: 18.5"
6' wire pre-laced through 3' chain

T24

6615203-05

(3) Medium Base 100w max.

T24 EN★

6615203EN3-05

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP +

**TWO LIGHT
SEMI-FLUSH
CONVERTIBLE PENDANT**

D: 15" H: 10.5" Semi-Flush H: 9"
6' wire pre-laced through 3' chain

T24

7715202-05
(2) Medium Base 100w max.

T24 EN★

7715202EN3-05
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT PENDANT

D: 15" H: 8"
6' wire pre-laced through 3' chain

T24

6515201-05
(1) Medium Base 100w max.

T24 EN★

6515201EN3-05
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP

**ONE LIGHT
MINI-PENDANT**

D: 4.5" H: 6.5"
6' wire, (3) 12" stems, 12" chain
and sloped ceiling mounting hardware

T24

6115201-05
(1) Medium Base 100w max.

T24 EN★

6115201EN3-05
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**ONE LIGHT
WALL / BATH**

W: 4.75" H: 9.75" E: 6.75"
Height from center of outlet box
up: 5.75" down: 4"

T24

4115201-05
(1) Medium Base 100w max.

T24 EN★

4115201EN3-05
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**KERRVILLE
WALL / BATH
COLLECTION**

Chrome Finish

See more Kerrville
Wall / Bath on p.434

Recommended
Products



GEARY PENDANT
Brushed Nickel
p.346



GEARY CEILING
FLUSH MOUNT
Chrome
p.366

KERRVILLE

DAMP +

FIVE LIGHT CHANDELIER

D: 20.5" H: 17" Downlight H: 24.75"
6' wire pre-laced through 3' chain

T24

3115205-962

(5) Medium Base 100w max.

T24 EN★

3115205EN3-962

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

THREE LIGHT CHANDELIER

D: 18" H: 15" Downlight H: 22"
6' wire pre-laced through 3' chain

T24

3115203-962

(3) Medium Base 100w max.

T24 EN★

3115203EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT PENDANT

D: 19.25" H: 18.5"
6' wire pre-laced through 3' chain

T24

6615203-962

(3) Medium Base 100w max.

T24 EN★

6615203EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP +

**TWO LIGHT
SEMI-FLUSH
CONVERTIBLE PENDANT**D: 15" H: 10.5" Semi-Flush H: 9"
6' wire pre-laced through 3' chain

T24

7715202-962

(2) Medium Base 100w max.

T24 EN★

7715202EN3-962(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

DAMP

ONE LIGHT PENDANTD: 15" H: 8"
6' wire pre-laced through 3' chain

T24

6515201-962

(1) Medium Base 100w max.

T24 EN★

6515201EN3-962(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

DAMP

**ONE LIGHT
MINI-PENDANT**D: 4.5" H: 6.5"
6' wire, (3) 12" stems, 12" chain
and sloped ceiling mounting hardware

T24

6115201-962

(1) Medium Base 100w max.

T24 EN★

6115201EN3-962(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

DAMP +

**ONE LIGHT
WALL / BATH**W: 4.75" H: 9.75" E: 6.75"
Height from center of outlet box
up: 5.75" down: 4"

T24

4115201-962

(1) Medium Base 100w max.

T24 EN★

4115201EN3-962(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

DAMP +

**KERRVILLE
WALL / BATH
COLLECTION**

Brushed Nickel Finish

See more Kerrville
Wall / Bath on p.434Recommended
ProductsGEARY PENDANT
Brushed Nickel
p.346GEARY CEILING
FLUSH MOUNT
Brushed Nickel
p.366

KERRVILLE

DAMP +

FIVE LIGHT CHANDELIER

D: 20.5" H: 17" Downlight H: 24.75"
6' wire pre-laced through 3' chain

T24

3115205-782

(5) Medium Base 100w max.

T24 EN★

3115205EN3-782

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

THREE LIGHT CHANDELIER

D: 18" H: 15" Downlight H: 22"
6' wire pre-laced through 3' chain

T24

3115203-782

(3) Medium Base 100w max.

T24 EN★

3115203EN3-782

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT PENDANT

D: 19.25" H: 18.5"
6' wire pre-laced through 3' chain

T24

6615203-782

(3) Medium Base 100w max.

T24 EN★

6615203EN3-782

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP +

**TWO LIGHT
SEMI-FLUSH
CONVERTIBLE PENDANT**

D: 15" H: 10.5" Semi-Flush H: 9"
6' wire pre-laced through 3' chain

T24

7715202-782

(2) Medium Base 100w max.

T24 EN★

7715202EN3-782

(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT PENDANT

D: 15" H: 8"
6' wire pre-laced through 3' chain

T24

6515201-782

(1) Medium Base 100w max.

T24 EN★

6515201EN3-782

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP

**ONE LIGHT
MINI-PENDANT**

D: 4.5" H: 6.5"
6' wire, (3) 12" stems, 12" chain
and sloped ceiling mounting hardware

T24

6115201-782

(1) Medium Base 100w max.

T24 EN★

6115201EN3-782

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**ONE LIGHT
WALL / BATH**

W: 4.75" H: 9.75" E: 6.75"
Height from center of outlet box
up: 5.75" down: 4"

T24

4115201-782

(1) Medium Base 100w max.

T24 EN★

4115201EN3-782

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**KERRVILLE
WALL / BATH
COLLECTION**

Heirloom Bronze

See more Kerrville
Wall / Bath on p.434

Recommended
Products



GEARY PENDANT
Heirloom Bronze
p.346



GEARY CEILING
FLUSH MOUNT
Heirloom Bronze
p.366

SUNSET DRIVE

FIVE LIGHT SINGLE TIER CHANDELIER

D: 26.75" H: 16.375"
Supplied with 15' of wire,
(1) 6" stem, (4) 12" stems

T24

F2405/5BS

(5) Candelabra Base 60w max.

See more Brushed Steel Finish on p.108



BRUSHED STEEL FINISH
STRIATED PEARL GLASS

**FIVE LIGHT
SINGLE TIER CHANDELIER**

D: 26.75" H: 16.375"
Supplied with 15' of wire,
(1) 6" stem, (4) 12" stems

T24

F2405/5CB

(5) Candelabra Base 60w max.

See more Corinthian Bronze Finish on p.109



CORINTHIAN BRONZE FINISH
STRIATED PEARL GLASS

SUNSET DRIVE

BRUSHED STEEL FINISH [-BS] / STRIATED PEARL GLASS



THREE LIGHT ISLAND CHANDELIER

L: 40" W: 8" H: 12.25"
Supplied with 15' of wire,
(1) 6" stem, (4) 12" stems

T24

F2402/3BS

(3) Medium Base 100w max.



THREE LIGHT KITCHEN CHANDELIER

D: 27" H: 11"
Supplied with 15' of wire,
(1) 6" stem, (4) 12" stems

T24

F2403/3BS

(3) Medium Base 100w max.



THREE LIGHT UPLIGHT CHANDELIER

D: 18.375" H: 12"
Supplied with 15' of wire,
(1) 6" stem, (4) 12" stems

T24

F2404/3BS

(3) Medium Base 100w max.



ONE LIGHT MINI-PENDANT

D: 8" H: 7.25"
Supplied with 15' of wire,
(1) 6" stem, (3) 12" stems

T24

P1153BS

(1) Medium Base 100w max.



DAMP +

ONE LIGHT WALL SCONCE

H: 10" W: 4.5" E: 5.75"
Height from center of outlet box
up: 5" down: 5"

T24

VS14901-BS

(1) Medium Base 100w max.



DAMP +

SUNSET DRIVE VANITY COLLECTION

Brushed Steel

See more Sunset Drive
Vanity on p.414



SUNSET DRIVE CEILING COLLECTION

Chrome
Brushed Steel

See more Sunset Drive
Ceiling on p.370



**THREE LIGHT
ISLAND CHANDELIER**

L: 40" W: 8" H: 12.25"
Supplied with 15' of wire,
(1) 6" stem, (4) 12" stems

T24

F2402/3CB

(3) Medium Base 100w max.



**THREE LIGHT
KITCHEN CHANDELIER**

D: 27" H: 11"
Supplied with 15' of wire,
(1) 6" stem, (4) 12" stems

T24

F2403/3CB

(3) Medium Base 100w max.



**THREE LIGHT
UPLIGHT CHANDELIER**

D: 18.375" H: 12"
Supplied with 15' of wire,
(1) 6" stem, (4) 12" stems

T24

F2404/3CB

(3) Medium Base 100w max.



**ONE LIGHT
MINI-PENDANT**

D: 8" H: 7.25"
Supplied with 15' of wire,
(1) 6" stem, (3) 12" stems

T24

P1153CB

(1) Medium Base 100w max.



**SUNSET DRIVE
CEILING COLLECTION**

Corinthian Bronze
Oil Rubbed Bronze

See more Sunset Drive
Ceiling on p.370

CORSICANA

PRODUCT SHOWN: CORSICANA FIVE LIGHT
CHANDELIER IN HEIRLOOM BRONZE FINISH



DAMP

FIVE LIGHT CHANDELIER

L: 40" W: 12" H: 13.75"
10' wire, (6) 12" stems, (2) 6" stems

T24

3225005-782

(5) Medium Base 100w max.

T24

EN★

3225005EN3-782

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 17" H: 13.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3125003-782

(3) Medium Base 100w max.

T24

EN★

3125003EN3-782

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT MINI-PENDANT

D: 6" H: 8.25"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6125001-782

(1) Medium Base 100w max.

T24

EN★

6125001EN3-782

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

Recommended
Products

GEARY PENDANT
Heirloom Bronze
p.346



GEARY CEILING
FLUSH MOUNT
Heirloom Bronze
p.366

DUNNING

DAMP

FIVE LIGHT CHANDELIER

L: 22" W: 22" H: 25.25"

10' wire pre-laced through 3' chain

T24

3113305-846

(5) Medium Base 100w max.

T24 EN★

3113305EN3-846

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



STARDUST FINISH WITH CERUSED OAK ACCENTS
CREME PARCHMENT GLASS

DAMP

FOUR LIGHT ISLAND PENDANT


L: 36" W: 11" H: 25"
10' wire pre-laced through 3' chain

T24

6613304-846
(4) Medium Base 100w max.

T24 EN★

6613304EN3-846
(4) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

L: 16.5" W: 16.5" H: 21.75"
10' wire pre-laced through 3' chain

T24

3113303-846
(3) Medium Base 100w max.

T24 EN★

3113303EN3-846
(3) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



DAMP

TWO LIGHT CEILING FLUSH MOUNT

L: 13.5" W: 13.5" H: 7.5"

T24

7513302-846
(2) Medium Base 60w max.



DAMP

ONE LIGHT MINI-PENDANT

L: 6" W: 6" H: 9.5"
10' wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

6113301-846
(1) Medium Base 100w max.

T24 EN★

6113301EN3-846
(1) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



DAMP +

ONE LIGHT WALL / BATH

W: 5" H: 8.25" E: 6"
Height from center of outlet box up: 5.75" down: 2.5"

T24

4113301-846
(1) Medium Base 100w max.

T24 EN★

4113301EN3-846
(1) Med. Base LED 3000K, 9.5w, 800 lumen lamp incl.



DAMP +

DUNNING WALL / BATH COLLECTION

Stardust Finish

See more Dunning Wall / Bath on p.436

SFERA

DAMP

SIX LIGHT CHANDELIER

D: 24.5" H: 32.25"

14' wire pre-laced through 12' chain

T24

3110406-715

(6) Medium Base 100w max.

T24 EN★

3110406EN3-715

(6) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

See more Mercury Glass on p.116



AUTUMN BRONZE FINISH
MERCURY GLASS

DAMP

SIX LIGHT CHANDELIER

D: 24.5" H: 32.25"

14' wire pre-laced through 12' chain

T24

3190406-715

(6) Medium Base 100w max.

T24

EN★

3190406EN3-715(6) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

See more Cafe Tint Glass on p.118

AUTUMN BRONZE FINISH
CAFE TINT GLASS

SFERA

DAMP

FOUR LIGHT CHANDELIER

D: 18.5" H: 24.5"

14' wire pre-laced through 12' chain

T24

3110404-715

(4) Medium Base 100w max.

T24 EN★

3110404EN3-715

(4) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP

THREE LIGHT PENDANT

D: 18.5" H: 24.5"

14' wire pre-laced through 12' chain

T24

6610403-715

(3) Medium Base 100w max.

T24 EN★

6610403EN3-715

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 13.5" H: 18.25" Semi-Flush H: 16.25"

14' wire pre-laced through 12' chain

T24

7710402-715

(2) Medium Base 100w max.

T24 EN★

7710402EN3-715

(2) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.





DAMP

**THREE LIGHT
CEILING FLUSH MOUNT**

D: 14.25" H: 10.5"

T24

7510403-715
(3) Medium Base 60w max.

T24 EN★

7510403EN3-715
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

DAMP

**ONE LIGHT
MINI-PENDANT**

D: 4" H: 7.25"

10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6110401-715
(1) Medium Base 100w max.

T24 EN★

6110401EN3-715
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

DAMP +

**ONE LIGHT
WALL / BATH**

W: 5" H: 11" E: 6"

Height from center of outlet box
up: 8.5" down: 2.5"

T24

4110401-715
(1) Medium Base 100w max.

T24 EN★

4110401EN3-715
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

DAMP +

**SFERA
WALL / BATH
COLLECTION**

Mercury Glass

See more Sfera
Wall / Bath on p.401

SFERA

DAMP

FOUR LIGHT CHANDELIER

D: 18.5" H: 24.5"
14' wire pre-laced through 12' chain

T24

3190404-715
(4) Medium Base 100w max.

T24 EN★

3190404EN3-715
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP

THREE LIGHT PENDANT

D: 18.5" H: 24.5"
14' wire pre-laced through 12' chain

T24

6690403-715
(3) Medium Base 100w max.

T24 EN★

6690403EN3-715
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 13.5" H: 18.25" Semi-Flush H: 16.25"
14' wire pre-laced through 12' chain

T24

7790402-715
(2) Medium Base 100w max.

T24 EN★

7790402EN3-715
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.





DAMP

**THREE LIGHT
CEILING FLUSH MOUNT**

D: 14.25" H: 10.5"

T24

7590403-715
(3) Medium Base 60w max.

T24 EN★

7590403EN3-715
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP

**ONE LIGHT
MINI-PENDANT**

D: 4" H: 7.25"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6190401-715
(1) Medium Base 100w max.

T24 EN★

6190401EN3-715
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



SMOKY AMBER GLASS

DAMP +

**ONE LIGHT
WALL / BATH**

W: 5" H: 11" E: 6"
Height from center of outlet box
up: 8.5" down: 2.5"

T24

4190401-715
(1) Medium Base 100w max.

T24 EN★

4190401EN3-715
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**SFERA
WALL / BATH
COLLECTION**

Smoky Amber Glass

See more Sfera
Wall / Bath on p.401

SOCORRO

PRODUCT SHOWN: SOCORRO SIX LIGHT HALL / FOYER
IN WASHED PINE FINISH AND CHROME ACCENTS



DAMP

SIX LIGHT CHANDELIER

D: 40" H: 31.25"
12' wire pre-laced through 10' chain

T24

3224906-872
(6) Candelabra Base 60w max.

T24 EN★

3224906EN-872
(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

See more Washed Pine Finish
on p.122



WASHED PINE FINISH
CHROME ACCENTS

DAMP

SIX LIGHT CHANDELIER

D: 40" H: 31.25"
12' wire pre-laced through 10' chain

T24

3224906-846
(6) Candelabra Base 60w max.

T24 EN★

3224906EN-846
(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

See more Stardust Finish
on p.124



STARDUST FINISH
CERUSED OAK ACCENTS

SOCORRO

DAMP

SIX LIGHT HALL / FOYER

D: 25" H: 31.75"

12' wire pre-laced through 10' chain

T24

5124906-872

(6) Candelabra Base 60w max.

T24 EN★

5124906EN-872

(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

SIX LIGHT CHANDELIER

D: 26" H: 22"

12' wire pre-laced through 10' chain

T24

3124906-872

(6) Candelabra Base 60w max.

T24 EN★

3124906EN-872

(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

**FOUR LIGHT
HALL / FOYER**D: 21" H: 27.5"
12' wire pre-laced through 10' chain

T24

5124904-872
(4) Candelabra Base 60w max.

T24 EN★

5124904EN-872
(4) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

DAMP

FOUR LIGHT CHANDELIERD: 22" H: 18.5"
12' wire pre-laced through 10' chain

T24

3124904-872
(4) Candelabra Base 60w max.

T24 EN★

3124904EN-872
(4) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

SOCORRO

DAMP

SIX LIGHT HALL / FOYER

D: 25" H: 31.75"

12' wire pre-laced through 10' chain

T24

5124906-846

(6) Candelabra Base 60w max.

T24 EN★

5124906EN-846

(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

SIX LIGHT CHANDELIER

D: 26" H: 22"

12' wire pre-laced through 10' chain

T24

3124906-846

(6) Candelabra Base 60w max.

T24 EN★

3124906EN-846

(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

**FOUR LIGHT
HALL / FOYER**

D: 21" H: 27.5"

12' wire pre-laced through 10' chain

T24

5124904-846

(4) Candelabra Base 60w max.

T24 EN★

5124904EN-846(4) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

DAMP

FOUR LIGHT CHANDELIER

D: 22" H: 18.5"

12' wire pre-laced through 10' chain

T24

3124904-846

(4) Candelabra Base 60w max.

T24 EN★

3124904EN-846(4) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

THORNWOOD

PRODUCT SHOWN: THORNWOOD MEDIUM FOUR LIGHT HALL / FOYER
IN WASHED PINE AND WEATHERED IRON ACCENTS



DAMP

**LARGE EIGHT LIGHT
HALL / FOYER**

L: 23.125" W: 23.125" H: 38"

Supplied with 10' of wire,
(3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6526308-872

(8) Candelabra Base 60w max.

T24 EN★

6526308EN-872(8) Cand. Base LED 2700k
3.5w, 350 lumen lamps incl.WASHED PINE FINISH WITH
WEATHERED IRON ACCENTS

THORNWOOD

DAMP

EIGHT LIGHT ISLAND PENDANT

L: 49" W: 13.75" H: 14.5"
Supplied with 10' of wire,
(2) 6" stems, (6) 12" stems

T24

6626308-872

(8) Candelabra Base 60w max.

T24 EN★

6626308EN-872

(8) Cand. Base LED 2700k
3.5w, 350 lumen lamps incl.



DAMP

MEDIUM FOUR LIGHT HALL / FOYER

L: 17" W: 17" H: 20.5"
Supplied with 10' of wire,
(3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6526304-872

(4) Candelabra Base 60w max.

T24 EN★

6526304EN-872

(4) Cand. Base LED 2700k
3.5w, 350 lumen lamps incl.



DAMP

**SMALL THREE LIGHT
HALL / FOYER**

L: 12" W: 12" H: 14"
Supplied with 10' of wire,
(3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6526303-872
(3) Candelabra Base 60w max.

T24 EN★

6526303EN-872
(3) Cand. Base LED 2700k
3.5w, 350 lumen lamps incl.



DAMP

**FOUR LIGHT
CEILING FLUSH MOUNT**

L: 14" W: 14" H: 10.25"

T24

7526304-872
(4) Candelabra Base 60w max.

T24 EN★

7526304EN-872
(4) Cand. Base LED 2700k
3.5w, 350 lumen lamps incl.



DAMP

**TWO LIGHT
WALL / BATH SCONCE**

W: 7.5" H: 18" E: 5.25"

T24

4126302-872
(2) Candelabra Base 60w max.

T24 EN★

4126302EN-872
(2) Cand. Base LED 2700k
3.5w, 350 lumen lamps incl.

DAVLIN

PRODUCT SHOWN: DAVLIN FOUR LIGHT MEDIUM HALL / FOYER
IN STARDUST FINISH WITH CERUSED OAK ACCENTS



DAMP

**SIX LIGHT
LARGE HALL / FOYER**

D: 26" H: 35.25"
10' wire pre-laced through 6' chain

T24

6551106-846
(6) Candelabra Base 60w max.

T24 EN★

6551106EN-846
(6) Candelabra Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

**FOUR LIGHT
MEDIUM HALL / FOYER**

D: 22" H: 31.25"
10' wire pre-laced through 6' chain

T24

6551104-846
(4) Candelabra Base 60w max.

T24 EN★

6551104EN-846
(4) Candelabra Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

**THREE LIGHT
SMALL HALL / FOYER**

D: 18" H: 26"
10' wire pre-laced through 6' chain

T24

6551103-846
(3) Candelabra Base 60w max.

T24 EN★

6551103EN-846
(3) Candelabra Base LED 2700K,
3.5w, 350 lumen lamps incl.



HARTSVILLE

NINE LIGHT CHANDELIER

D: 30.75" H: 36.5"

Supplied with 15' of wire and 7' of chain

T24

F2999/9DWZ/WO

(9) Candelabra Base 60w max.



DARK WEATHERED ZINC WITH WEATHERED OAK ACCENTS

SIX LIGHT CHANDELIER

L: 42.5" W: 14.75" H: 18.125"
Supplied with 15' of wire and 5' of chain

T24

F3000/6DWZ/WO
(6) Candelabra Base 60w max.



FIVE LIGHT CHANDELIER

D: 23.5" H: 25.5"
Supplied with 15' of wire and 5' of chain

T24

F2998/5DWZ/WO
(5) Candelabra Base 60w max.



THREE LIGHT CHANDELIER

D: 16.5" H: 18.625"
Supplied with 15' of wire and 5' of chain

T24

F2997/3DWZ/WO
(3) Candelabra Base 60w max.



ONE LIGHT MINI-PENDANT

D: 7.75" H: 15.25"
Supplied with 15' of wire and 5' of chain

T24

P1341DWZ/WO
(1) Candelabra Base 60w max.



DAMP ADA

TWO LIGHT SCONCE

W: 6.125" H: 7.25" E: 4"

T24

WB1756DWZ/WO
(2) Candelabra Base 60w max.



DAMP ADA

ONE LIGHT SCONCE

W: 4.5" H: 7.25" E: 4"

T24

WB1755DWZ/WO
(1) Candelabra Base 60w max.

BOUGHTON

DAMP

TWENTY FOUR LIGHT CHANDELIER


D: 64" H: 59.5"

Supplied with 20' of wire and 7' of chain

T24

F3208/24AF

(24) Candelabra Base 60w max.



ANTIQUE FORGED IRON FINISH


DAMP

EIGHTEEN LIGHT CHANDELIER

D: 45.5" H: 44"
Supplied with 20' of wire and 7' of chain

T24

F3207/18AF
(18) Candelabra Base 60w max.



DAMP

TEN LIGHT CHANDELIER

D: 30.5" H: 30.5"
Supplied with 20' of wire and 7' of chain

T24

F3206/10AF
(10) Candelabra Base 60w max.



DAMP

SIX LIGHT CHANDELIER

D: 27.5" H: 26.625"
Supplied with 15' of wire and 5' of chain

T24

F3205/6AF
(6) Candelabra Base 60w max.



GREENBRIER

IRON OXIDE FINISH [-10]

DAMP


SIX LIGHT FOYER CHANDELIER

L: 17" W: 17" H: 29.375"
Supplied with 15' of wire,
(4) 12" stems, (1) 6" stem

T24

F3197/6IO

(6) Candelabra Base 60w max.



DAMP


FOUR LIGHT HALL / FOYER

L: 17" W: 17" H: 22.375"
Supplied with 15' of wire,
(4) 12" stems, (1) 6" stem

T24

F3195/4IO

(4) Candelabra Base 60w max.



DAMP

THREE LIGHT FOYER HALL / FOYER

L: 12" W: 12" H: 15.25"
Supplied with 15' of wire,
(3) 12" stems, (1) 6" stem

T24

F3196/3IO

(3) Candelabra Base 60w max.

DAMP

LARGE SIX LIGHT HALL / FOYER


L: 22" W: 22" H: 47.5"
 Supplied with 10' of wire,
 (3) 12" stems, (1) 6" stem
 and sloped ceiling mounting hardware

T24

6531506-808
 (6) Candelabra Base 60w max.

T24 EN★

6531506EN-808
 (6) Cand. Base LED 2700K,
 3.5w, 350 lumen lamps incl.



DAMP

MEDIUM FOUR LIGHT HALL / FOYER

L: 15" W: 15" H: 34.75"
 Supplied with 10' of wire,
 (3) 12" stems, (1) 6" stem
 and sloped ceiling mounting hardware

T24

6531504-808
 (4) Candelabra Base 60w max.

T24 EN★

6531504EN-808
 (4) Cand. Base LED
 3.5w, 350 lumen lamps incl.



DAMP

SMALL THREE LIGHT HALL / FOYER

L: 12" W: 12" H: 22.625"
 Supplied with 10' of wire,
 (3) 12" stems, (1) 6" stem
 and sloped ceiling mounting hardware

T24

6531503-808
 (3) Candelabra Base 60w max.

T24 EN★

6531503EN-808
 (3) Cand. Base LED
 3.5w, 350 lumen lamps incl.



DAMP

FOUR LIGHT SEMI-FLUSH MOUNT

D: 15.25" H: 12"

T24

7731504-808
 (4) Candelabra Base 60w max.

T24 EN★

7731504EN-808
 (4) Cand. Base LED
 3.5w, 350 lumen lamps incl.



DAMP ADA

TWO LIGHT WALL / BATH SCONCE

W: 12.5" H: 20.75" E: 4"

T24

4131502-808
 (2) Candelabra Base 60w max.

T24 EN★

4131502EN-808
 (2) Cand. Base LED
 3.5w, 350 lumen lamps incl.

CORBEILLE

NINE LIGHT CHANDELIER

D: 27" H: 35"

10' wire pre-laced through 3' chain

T24

3280409-846

(9) Candelabra Base 60w max.

T24 EN★

3280409EN-846

(9) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



STARDUST FINISH WITH CERUSED OAK ACCENTS

FIVE LIGHT CHANDELIER

D: 21.5" H: 29"
10' wire pre-laced through 3' chain

T24

3280405-846
(5) Candelabra Base 60w max.

T24 EN★

3280405EN-846
(5) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



THREE LIGHT PENDANT

D: 19" H: 27"
10' wire pre-laced through 3' chain

T24

6680403-846
(3) Medium Base 100w max.

T24 EN★

6680403EN3-846
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



+

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 15.25" H: 16" Semi-Flush H: 14"
10' wire pre-laced through 3' chain

T24

7780402-846
(2) Medium Base 100w max.

T24 EN★

7780402EN3-846
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

TWO LIGHT CEILING FLUSH MOUNT

D: 15.25" H: 8"

T24

7580402-846
(2) Medium Base 60w max.

T24 EN★

7580402EN3-846
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

Recommended Products



LONOKE PENDANT
Stardust,
Heirloom Bronze
p.326



DUNNING WALL / BATH
Stardust
p.436

DAMP

FIVE LIGHT CHANDELIER

D: 29" H: 37.25"

10' of wire pre-laced through 6' of chain

T24

3101905-872

(5) Candelabra Base 60w max.

T24 EN★

3101905EN-872

(5) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



WASHED PINE FINISH
STARDUST ACCENTS

DAMP

FOUR LIGHT CHANDELIER

D: 20" H: 23.75"
10' of wire pre-laced through 6' of chain

T24

3101904-872
(4) Candelabra Base 60w max.

T24 EN★

3101904EN-872
(4) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 16" H: 20.125"
10' of wire pre-laced through 6' of chain

T24

3101903-872
(3) Candelabra Base 60w max.

T24 EN★

3101903EN-872
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

TWO LIGHT CHANDELIER

D: 13" H: 18"
10' of wire pre-laced through 6' of chain

T24

3101902-872
(2) Candelabra Base 60w max.

T24 EN★

3101902EN-872
(2) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

THREE LIGHT CEILING FLUSH MOUNT

D: 14" H: 6.25"

T24

7501903-872
(3) Candelabra Base 60w max.

T24 EN★

7501903EN-872
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

MORILL

NINE LIGHT CHANDELIER

D: 31.5" H: 30"

10' wire pre-laced through 6' chain

T24

3127809-839

(9) Medium Base 60w max.



BLACKSMITH FINISH
CLEAR SEEDED GLASS

FIVE LIGHT CHANDELIER

D: 26.5" H: 20.5"
10' wire pre-laced through 6' chain

T24

3127805-839

(5) Medium Base 60w max.

**THREE LIGHT CHANDELIER**

D: 19.5" H: 18"
6' wire pre-laced through 3' chain

T24

3127803-839

(3) Medium Base 60w max.



MORILL

THREE LIGHT HALL / FOYER

D: 12.25" H: 17.75"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

5127803-839

(3) Candelabra Base 60w max.

T24 EN★

5127803EN-839

(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

ONE LIGHT PENDANT

D: 12" H: 10.125"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6227801-839

(1) Medium Base 75w max.





DAMP

TWO LIGHT SEMI-FLUSH

D: 15" H: 11.625"
10' wire pre-laced through 6' chain

T24

7727802-839
(2) Medium Base 75w max.



DAMP

THREE LIGHT CEILING FLUSH MOUNT

D: 11.25" H: 7.5"

T24

7527803-839
(3) Candelabra Base 40w max.

T24 EN★

7527803EN-839
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

ONE LIGHT WALL / BATH

W: 5" H: 8.25" E: 7.25"
Height from center of outlet box
up: 3.75"

T24

4127801-839
(1) Medium Base 60w max.



DAMP

MORILL WALL / BATH COLLECTION

Blacksmith Finish

See more Morill
Wall / Bath on p.421

Recommended
Products



RAVENWOOD MANOR
Stardust
p.158



GEARY CEILING
FLUSH MOUNT
Blacksmith
p.366

ELSA

DAMP

FIVE LIGHT CHANDELIER

D: 25" H: 19"

10' wire pre-laced through 6' chain

T24

3120305-782

(5) Medium Base 75w max.



HEIRLOOM BRONZE FINISH
CLEAR SEEDED GLASS



DAMP

THREE LIGHT CHANDELIERD: 20" H: 18.625"
6' wire pre-laced through 3' chain

T24

3120303-782

(3) Medium Base 75w max.



DAMP

**THREE LIGHT
CEILING FLUSH MOUNT**

D: 11.25" H: 7.5"

T24

7514503-782

(3) Candelabra Base 40w max.

T24 EN★

7514503EN-782

(3) Cand. Base LED 2700k
3.5w, 350 lumen lamps incl.

DAMP

**TWO LIGHT
SEMI-FLUSH**

D: 14.75" H: 10.375"

T24

7714502-782

(2) Medium Base 75w max.



DAMP

ONE LIGHT PENDANTD: 12" H: 10.125"
10' of wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6220301-782

(1) Medium Base 75w max.



DAMP +

**ONE LIGHT
WALL / BATH**W: 6" H: 9.25" E: 7.875"
Height from center of outlet box
up: 4.75" down: 4.5"

T24

4120301-782

(1) Medium Base 75w max.



DAMP +

**ELSA
WALL / BATH
COLLECTION**See more Elsa
Wall / Bath on p.437

COWEN

DAMP

SIX LIGHT HALL / FOYER

D: 19.75" H: 32"

10' of wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

5128606-802

(6) Medium Base 60w max.



OBSIDIAN MIST FINISH

DAMP

FIVE LIGHT ISLAND PENDANT

L: 41.625" W: 16.125" H: 11.75"
10' of wire, (6) 12" stems, (2) 6" stems

T24

6628605-802
(5) Medium Base 60w max.



DAMP

THREE LIGHT PENDANT

D: 22.875" H: 10.375"
10' of wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

6528603-802
(3) Medium Base 60w max.



DAMP +

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 16.625" H: 14" Semi-Flush H: 12.625"
6' wire pre-laced through 3' chain

T24

7728602-802
(2) Medium Base 60w max.



DAMP

ONE LIGHT MINI-PENDANT

D: 8" H: 12"
10' of wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

6128601-802
(1) Medium Base 60w max.

Recommended Product



COWEN
WALL SCONCE
Obsidian Mist
p.445

GEREON

PRODUCT SHOWN: GEREON LARGE FOUR
LIGHT PENDANT IN BLACK FINISH



DAMP

LARGE FOUR LIGHT PENDANT

D: 24"H: 10.5"
10' wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

6528504-12
(4) Medium Base 60w max.



DAMP

MEDIUM THREE LIGHT PENDANT

D: 19" H: 9.375"
10' wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

6528503-12
(3) Medium Base 60w max.




DAMP +

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 16" H: 11.75" Semi-Flush H: 11"
6' wire pre-laced through 3' chain

T24

7728502-12
(2) Medium Base 60w max.



DAMP

ONE LIGHT MINI-PENDANT

D: 8" H: 12"
10' wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

6128501-12
(1) Medium Base 60w max.



Recommended Product



GEREON WALL SCONCE
Black
p.445

BELTON

FIVE LIGHT UP CHANDELIER

D: 23.875" H: 10.5"
Supplied with 6' of Wire,
(1) 6" stem, (3) 12" stems
and sloped ceiling mounting hardware

T24

3214505-962

(5) Medium Base 60w max.

See more Brushed Nickel Finish on p.154



BRUSHED NICKEL FINISH
CLEAR SEEDED GLASS

**FIVE LIGHT
UP CHANDELIER**

D: 23.875" H: 10.5"
Supplied with 6' of Wire,
(1) 6" stem, (3) 12" stems
and sloped ceiling mounting hardware

T24

3214505-782

(5) Medium Base 60w max.

See more Heirloom Bronze Finish on p.156



HEIRLOOM BRONZE FINISH
CLEAR SEEDED GLASS

BELTON

FIVE LIGHT CHANDELIER

D: 24" H: 10.5"
6' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3114505-962

(5) Medium Base 60w max.



FOUR LIGHT ISLAND PENDANT

L: 40.75" W: 5.5" H: 15"
6' wire, (3) 12" stems, (1) 6" stem

T24

6614504-962

(4) Medium Base 60w max.



THREE LIGHT CHANDELIER

D: 20" H: 10.5"
6' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3114503-962

(3) Medium Base 60w max.



DAMP

THREE LIGHT CEILING FLUSH MOUNT

D: 11.25" H: 7.5"

T24

7514503-962

(3) Candelabra 40 watt light bulbs



DAMP

TWO LIGHT SEMI-FLUSH

D: 15" H: 11.625"
10' wire pre-laced through 6' chain

T24

7714502-962

(2) Medium Base 75w max.

T24 EN★

7514503EN-962

(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamp incl.



**LARGE
ONE LIGHT PENDANT**

D: 16" H: 12.75"
6' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6614501-962

(1) Medium Base 100w max.



**MEDIUM
ONE LIGHT PENDANT**

D: 12.75" H: 11.5"
6' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6514501-962

(1) Medium Base 100w max.



**ONE LIGHT
MINI-PENDANT**

D: 5.5" H: 9"
6' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6114501-962

(1) Medium Base 60w max.



DAMP +

**ONE LIGHT
WALL / BATH**

W: 5.5" H: 9.75" E: 6.75"
Height from center of outlet box
up: 5.5" down: 4.25"

T24

4114501-962

(1) Medium Base 60w max.



DAMP +

**BELTON
WALL / BATH
COLLECTION**

Brushed Nickel

See more Belton
Wall / Bath on p.420

Recommended
Product



GEARY CEILING
FLUSH MOUNT
Brushed Nickel
p.366

BELTON

FIVE LIGHT CHANDELIER

D: 24" H: 10.5"
6' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3114505-782
(5) Medium Base 60w max.



FOUR LIGHT ISLAND PENDANT

L: 40.75" W: 5.5" H: 15"
6' wire, (3) 12" stems, (1) 6" stem

T24

6614504-782
(4) Medium Base 60w max.



THREE LIGHT CHANDELIER

D: 20" H: 10.5"
6' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3114503-782
(3) Medium Base 60w max.



DAMP

THREE LIGHT CEILING FLUSH MOUNT

D: 11.25" H: 7.5"

T24

7514503-782
(3) Candelabra 40 watt light bulbs



DAMP

TWO LIGHT SEMI-FLUSH

D: 15" H: 11.625"
10' wire pre-laced through 6' chain

T24

7714502-782
(2) Medium Base 75w max.

T24 EN★

7514503EN-782
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamp incl.



**LARGE
ONE LIGHT PENDANT**

D: 16" H: 12.75"
6' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6614501-782
(1) Medium Base 100w max.



**MEDIUM
ONE LIGHT PENDANT**

D: 12.75" H: 11.5"
6' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6514501-782
(1) Medium Base 100w max.



DAMP

ONE LIGHT PENDANT

D: 12" H: 10.125"
10' of wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6220301-782
(1) Base Medium 75 watt light bulb



**ONE LIGHT
MINI-PENDANT**

D: 5.5" H: 9"
6' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6114501-782
(1) Medium Base 60w max.



DAMP +

**ONE LIGHT
WALL / BATH**

W: 5.5" H: 9.75" E: 6.75"
Height from center of outlet box
up: 5.5" down: 4.25"

T24

4114501-782
(1) Medium Base 60w max.



DAMP +

**BELTON
WALL / BATH
COLLECTION**

Heirloom Bronze

See more Belton
Wall / Bath on p.420

Recommended
Product



GEARY CEILING
FLUSH MOUNT
Heirloom Bronze
p.366

RAVENWOOD MANOR

DAMP

NINE LIGHT CHANDELIER

D: 31" H: 23"

12' wire pre-laced through 10' chain

T24

3110209-846

(9) Medium Base 60w max.



STARDUST FINISH

DAMP

EIGHT LIGHT CHANDELIER

L: 34" W: 12" H: 8"
10' wire, (6) 12" stems, (2) 6" stems

T24

3110208-846
(8) Medium Base 60w max.



DAMP

FIVE LIGHT CHANDELIER

D: 25" H: 21.75"
12' wire pre-laced through 10' chain

T24

3110205-846
(5) Medium Base 60w max.



PERRYTON

PRODUCTS SHOWN: PERRYTON MEDIUM FOUR
LIGHT HALL / FOYER IN BLACKSMITH FINISH



DAMP

**EIGHT LIGHT
HALL / FOYER**

L: 19" W: 19" H: 30.75"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware.
Includes two sets of accent candle
holders in Chrome and Heirloom Bronze.

T24

5115008-782
(8) Candelabra Base 60w max.

T24 EN★

5115008EN-782
(8) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

See more Heirloom Bronze Finish on p.162



HEIRLOOM BRONZE FINISH

DAMP

**EIGHT LIGHT
HALL / FOYER**

L: 19" W: 19" H: 30.75"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware.
Includes two sets of accent candle
holders in Chrome and Heirloom Bronze.


T24

5115008-839
(8) Candelabra Base 60w max.

T24 EN★

5115008EN-839
(8) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

See more Blacksmith Finish on p.163



BLACKSMITH FINISH
SHOWN WITH INCLUDED CHROME ACCENT HOLDERS

DAMP

EIGHT LIGHT ISLAND PENDANT

L: 40" W: 12" H: 16.75"
 10' wire, (6) 12" stems, (2) 6" stems
 Includes two sets of accent candle holders in Chrome and Heirloom Bronze.

T24

6615008-782
 (8) Candelabra Base 60w max.

T24 EN★

6615008EN-782
 (8) Cand. Base LED 2700K,
 3.5w, 350 lumen lamps incl.



SHOWN WITH INCLUDED CHROME ACCENT HOLDERS

DAMP

MEDIUM FOUR LIGHT HALL / FOYER

L: 15.5" W: 15.5" H: 23.25"
 10' wire, (3) 12" stems, (1) 6" stem
 and sloped ceiling mounting hardware.
 Includes two sets of accent candle holders in Chrome and Heirloom Bronze.

T24

5115004-782
 (4) Candelabra Base 60w max.

T24 EN★

5115004EN-782
 (4) Cand. Base LED 2700K,
 3.5w, 350 lumen lamps incl.



DAMP

SMALL FOUR LIGHT HALL / FOYER

L: 12.25" W: 12.25" H: 18.5"
 10' wire, (3) 12" stems, (1) 6" stem
 and sloped ceiling mounting hardware.
 Includes two sets of accent candle holders in Chrome and Heirloom Bronze.

T24

5215004-782
 (4) Candelabra Base 60w max.

T24 EN★

5215004EN-782
 (4) Cand. Base LED 2700K,
 3.5w, 350 lumen lamps incl.



DAMP

**EIGHT LIGHT
ISLAND PENDANT**


L: 40" W: 12" H: 16.75"
10' wire, (6) 12" stems, (2) 6" stems
Includes two sets of accent candle
holders in Chrome and Heirloom Bronze.

T24

6615008-839
(8) Candelabra Base 60w max.

T24 EN★

6615008EN-839
(8) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

**MEDIUM FOUR LIGHT
HALL / FOYER**


L: 15.5" W: 15.5" H: 23.25"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware.
Includes two sets of accent candle
holders in Chrome and Heirloom Bronze.

T24

5115004-839
(4) Candelabra Base 60w max.

T24 EN★

5115004EN-839
(4) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



SHOWN WITH INCLUDED CHROME ACCENT HOLDERS

DAMP

**SMALL FOUR LIGHT
HALL / FOYER**

L: 12.25" W: 12.25" H: 18.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware.
Includes two sets of accent candle
holders in Chrome and Heirloom Bronze.

T24

5215004-839
(4) Candelabra Base 60w max.

T24 EN★

5215004EN-839
(4) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



CHATAUQUA

DAMP

SIX LIGHT HALL / FOYER

L: 16" W: 16" H: 27.875"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

5140506-71
(6) Medium Base 100w max.

T24 EN★

5140506EN3-71
(6) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Antique Bronze Finish on p.166



ANTIQUE BRONZE FINISH
ETCHED GLASS, WHITE INSIDE

DAMP

**SIX LIGHT
HALL / FOYER**

L: 16" W: 16" H: 27.875"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

5140506-846

(6) Medium Base 100w max.

T24 EN★

5140506EN3-846

(6) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Stardust Finish on p.168



STARDUST FINISH
ETCHED GLASS, WHITE INSIDE

CHATAUQUA

DAMP

FIVE LIGHT CHANDELIER

L: 22.25" W: 22.25" H: 12.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3140505-71

(5) Medium Base 100w max.

T24 EN★

3140505EN3-71

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

FOUR LIGHT ISLAND PENDANT

L: 36" W: 8" H: 12.5"
10' wire, (6) 12" stems, (2) 6" stems

T24

6640504-71

(4) Medium Base 100w max.

T24 EN★

6640504EN3-71

(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT HALL / FOYER

L: 14.25" W: 14.25" H: 20.5"
10' wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

5140503-71
(3) Medium Base 100w max.

T24 EN★

5140503EN3-71
(3) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

L: 17.375" W: 17.375" H: 13.125"
10' wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

3140503-71
(3) Medium Base 100w max.

T24 EN★

3140503EN3-71
(3) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.

DAMP

ONE LIGHT MINI-PENDANT

L: 6.25" W: 6.25" H: 11.5"
10' wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

6140501-71
(1) Medium Base 100w max.

T24 EN★

6140501EN3-71
(1) Med. Base LED 3000K, 9.5w, 800 lumen lamp incl.



Recommended Product



GEARY CEILING FLUSH MOUNT
Heirloom Bronze
p.366

CHATAUQUA

DAMP

FIVE LIGHT CHANDELIER

L: 22.25" W: 22.25" H: 12.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3140505-846

(5) Medium Base 100w max.

T24 EN★

3140505EN3-846

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

FOUR LIGHT ISLAND PENDANT

L: 36" W: 8" H: 12.5"
10' wire, (6) 12" stems, (2) 6" stems

T24

6640504-846

(4) Medium Base 100w max.

T24 EN★

6640504EN3-846

(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT HALL / FOYER

L: 14.25" W: 14.25" H: 20.5"
10' wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

5140503-846
(3) Medium Base 100w max.

T24 EN★

5140503EN3-846
(3) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

L: 17.375" W: 17.375" H: 13.125"
10' wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

3140503-846
(3) Medium Base 100w max.

T24 EN★

3140503EN3-846
(3) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT MINI-PENDANT

L: 6.25" W: 6.25" H: 11.5"
10' wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

6140501-846
(1) Medium Base 100w max.

T24 EN★

6140501EN3-846
(1) Med. Base LED 3000K, 9.5w, 800 lumen lamp incl.

Recommended Product



GEARY CEILING FLUSH MOUNT
Blacksmith
p.366

MOFFET STREET

DAMP

EIGHT LIGHT HALL / FOYER

L: 19" W: 19" H: 31.125"
10' of wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

5134508-848

(8) Candelabra Base 60w max.

T24 EN★

5134508EN-848

(8) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

See more Satin Bronze Finish on p.172



SATIN BRONZE FINISH

DAMP

**EIGHT LIGHT
HALL / FOYER**

L: 19" W: 19" H: 31.125"
10' of wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

5134508-962

(8) Candelabra Base 60w max.

T24 EN★

5134508EN-962

(8) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

See more Brushed Nickel Finish on p.173



BRUSHED NICKEL FINISH

DAMP

**EIGHT LIGHT
HALL / FOYER**

L: 19" W: 19" H: 31.125"
10' of wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

5134508-872

(8) Candelabra Base 60w max.

T24 EN★

5134508EN-872

(8) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

See more Washed Pine Finish on p.174



WASHED PINE FINISH
CHROME ACCENTS

DAMP

SIX LIGHT ISLAND PENDANT

L: 42" W: 12" H: 15"
10' of wire, (6) 12" stems, (2) 6" stems

T24

6634506-848
(6) Candelabra Base 60w max.

T24 EN★

6634506EN-848
(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

FOUR LIGHT HALL / FOYER

L: 15.5" W: 15.5" H: 23.125"
10' of wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

5134504-848
(4) Candelabra Base 60w max.

T24 EN★

5134504EN-848
(4) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

THREE LIGHT HALL / FOYER

L: 10.5" W: 10.5" H: 15"
10' of wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

5134503-848
(3) Candelabra Base 60w max.

T24 EN★

5134503EN-848
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

ONE LIGHT WALL / BATH

W: 7" H: 12" E: 6"
Height from center of outlet box up: 6"

T24

4134501-848
(1) Candelabra Base 60w max.

T24 EN★

4134501EN-848
(1) Cand. Base LED 2700K,
3.5w, 350 lumen lamp incl.

DAMP

SIX LIGHT ISLAND PENDANT

L: 42" W: 12" H: 15"


10' of wire, (6) 12" stems, (2) 6" stems

T24

6634506-962

(6) Candelabra Base 60w max.

T24 EN★

6634506EN-962(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

DAMP

**FOUR LIGHT
HALL / FOYER**

L: 15.5" W: 15.5" H: 23.125"

10' of wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

5134504-962

(4) Candelabra Base 60w max.

T24 EN★

5134504EN-962(4) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

DAMP

**THREE LIGHT
HALL / FOYER**

L: 10.5" W: 10.5" H: 15"

10' of wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

5134503-962

(3) Candelabra Base 60w max.

T24 EN★

5134503EN-962(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

DAMP

**ONE LIGHT
WALL / BATH**

W: 7" H: 12" E: 6"

Height from center of outlet box
up: 6"

T24

4134501-962

(1) Candelabra Base 60w max.

T24 EN★

4134501EN-962(1) Cand. Base LED 2700K,
3.5w, 350 lumen lamp incl.

DAMP

SIX LIGHT ISLAND PENDANT

L: 42" W: 12" H: 15"
10' of wire, (6) 12" stems, (2) 6" stems

T24

6634506-872
(6) Candelabra Base 60w max.

T24 EN★

6634506EN-872
(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

FOUR LIGHT HALL / FOYER

L: 15.5" W: 15.5" H: 23.125"
10' of wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

5134504-872
(4) Candelabra Base 60w max.

T24 EN★

5134504EN-872
(4) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

THREE LIGHT HALL / FOYER

L: 10.5" W: 10.5" H: 15"
10' of wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

5134503-872
(3) Candelabra Base 60w max.

T24 EN★

5134503EN-872
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

ONE LIGHT WALL / BATH

W: 7" H: 12" E: 6"
Height from center of outlet box up: 6"

T24

4134501-872
(1) Candelabra Base 60w max.

T24 EN★

4134501EN-872
(1) Cand. Base LED 2700K,
3.5w, 350 lumen lamp incl.

PRODUCT SHOWN: MOFFET STREET SIX LIGHT ISLAND
PENDANT IN WASHED PINE AND CHROME ACCENTS



FOUR LIGHT ISLAND PENDANT

L: 36" W: 16.5" H: 14"
10' wire, (6) 12" stems, (2) 6" stems

T24
65266-962
(4) Medium Base 100w max.

T24 EN★
65266EN3-962
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



FOUR LIGHT PENDANT

D: 24" H: 13"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24
65262-962
(4) Medium Base 100w max.

T24 EN★
65262EN3-962
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT PENDANT

D: 19" H: 10.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24
65263-962
(3) Medium Base 100w max.

T24 EN★
65263EN3-962
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



TWO LIGHT PENDANT

D: 14" H: 9"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24
65264-962
(2) Medium Base 100w max.

T24 EN★
65264EN3-962
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



TWO LIGHT FLUSH / SEMI-FLUSH CONVERTIBLE

D: 14" H: 8.5" Semi-Flush H: 12.75"

T24
77262-962
(2) Medium Base 100w max.

T24 EN★
77262EN3-962
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

Recommended Product



GEARY PENDANT
Brushed Nickel
p.346

FOUR LIGHT ISLAND PENDANT

L: 36" W: 16.5" H: 14"
10' wire, (6) 12" stems, (2) 6" stems

T24

65266-710
(4) Medium Base 100w max.

T24 EN★

65266EN3-710
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



FOUR LIGHT PENDANT

D: 24" H: 13"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

65262-710
(4) Medium Base 100w max.

T24 EN★

65262EN3-710
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT PENDANT

D: 19" H: 10.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

65263-710
(3) Medium Base 100w max.

T24 EN★

65263EN3-710
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



TWO LIGHT PENDANT

D: 14" H: 9"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

65264-710
(2) Medium Base 100w max.

T24 EN★

65264EN3-710
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



+

TWO LIGHT FLUSH / SEMI-FLUSH CONVERTIBLE

D: 14" H: 8.5" Semi-Flush H: 12.75"

T24

77262-710
(2) Medium Base 100w max.

T24 EN★

77262EN3-710
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

Recommended Product



GEARY PENDANT
Burnt Sienna,
Heirloom Bronze,
Blacksmith
p.346

JOURDANTON

DAMP

FOUR LIGHT ISLAND PENDANT

L: 45.25" W: 12.25" H: 8.25"
10' wire, (6) 12" stems, (2) 6" stems

T24

6615504-962
(4) Medium Base 60w max.

T24 EN★

6615504EN3-962
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



BRUSHED NICKEL FINISH
STAINLESS STEEL OUTER SHADE & CREAM FAUX SILK INNER SHADE / SATIN ETCHED GLASS DIFFUSER

DAMP

FOUR LIGHT PENDANT

D: 24.5" H: 8.25"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6515504-962
(4) Medium Base 60w max.

T24 EN★

6515504EN3-962
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT PENDANT

D: 20.75" H: 8.25"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6515503-962
(3) Medium Base 60w max.

T24 EN★

6515503EN3-962
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 15" H: 13.5" Semi-Flush H: 11.75"
6' wire pre-laced through 3' chain

T24

7715502-962
(2) Medium Base 60w max.

T24 EN★

7715502EN3-962
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT MINI-PENDANT

D: 7.5" H: 8.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6115501-962
(1) Medium Base 60w max.

T24 EN★

6115501EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



CARONDELET

PRODUCT SHOWN: CARONDELET FOUR LIGHT
CHANDELIER IN BURNT SIENNA FINISH



DAMP

SIX LIGHT CHANDELIER

D: 23.5" H: 24.25"
12' wire pre-laced through 10' chain

T24

3114006-965
(6) Medium Base 100w max.

T24 EN★

3114006EN3-965
(6) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Antique Brushed Nickel Finish
on p.182



ANTIQUE BRUSHED NICKEL FINISH
CRYSTAL GLASS

DAMP

SIX LIGHT CHANDELIER

D: 23.5" H: 24.25"
12' wire pre-laced through 10' chain

T24

3114006-710
(6) Medium Base 100w max.

T24 EN★

3114006EN3-710
(6) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Burnt Sienna Finish
on p.183



BURNT SIENNA FINISH
CRYSTAL GLASS



DAMP

FOUR LIGHT CHANDELIER

D: 18.25" H: 20"
12' wire pre-laced through 10' chain

T24

3114004-965
(4) Medium Base 100w max.

T24 EN★

3114004EN3-965
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 10.75" H: 15.25" Semi-Flush H: 13.25"
12' wire pre-laced through 10' chain

T24

7714002-965
(2) Medium Base 100w max.

T24 EN★

7714002EN3-965
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

TWO LIGHT CEILING FLUSH MOUNT

D: 10.75" H: 9"

T24

7514002-965
(2) Medium Base 100w max.

T24 EN★

7514002EN3-965
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT MINI-PENDANT

D: 5.25" H: 8"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6114001-965
(1) Medium Base 100w max.

T24 EN★

6114001EN3-965
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP

ONE LIGHT WALL / BATH

W: 8.5" H: 8.5" E: 4.75"
Height from center of outlet box
up: 4.25"

T24

4414001-965
(1) Medium Base 100w max.

T24 EN★

4414001EN3-965
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP

CARONDELET WALL / BATH

Antique Brushed Nickel Finish

See more Carondelet
Wall / Bath on p.443



DAMP

FOUR LIGHT CHANDELIER

D: 18.25" H: 20"
12" wire pre-laced through 10' chain

T24

3114004-710
(4) Medium Base 100w max.

T24 EN★

3114004EN3-710
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 10.75" H: 15.25" Semi-Flush H: 13.25"
12" wire pre-laced through 10' chain

T24

7714002-710
(2) Medium Base 100w max.

T24 EN★

7714002EN3-710
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

TWO LIGHT CEILING FLUSH MOUNT

D: 10.75" H: 9"

T24

7514002-710
(2) Medium Base 100w max.

T24 EN★

7514002EN3-710
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT MINI-PENDANT

D: 5.25" H: 8"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6114001-710
(1) Medium Base 100w max.

T24 EN★

6114001EN3-710
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP

ONE LIGHT WALL / BATH

W: 8.5" H: 8.5" E: 4.75"
Height from center of outlet box
up: 4.25"

T24

4414001-710
(1) Medium Base 100w max.

T24 EN★

4414001EN3-710
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP

CARONDELET WALL / BATH

Burnt Sienna Finish

See more Carondelet
Wall / Bath on p.443

ENGLEHORN

DAMP

NINE LIGHT CHANDELIER

D: 32.25" H: 25.5"

10' wire pre-laced through 3' chain

T24

3113409-05

(9) Medium Base 75w max.

T24

EN★

3113409EN3-05

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



CHROME FINISH WITH OPTIC CRYSTAL ACCENTS
ETCHED GLASS, WHITE INSIDE

DAMP

FIVE LIGHT CHANDELIER

D: 26.5" H: 21.75"
10' wire pre-laced through 3' chain

T24

3113405-05
(5) Medium Base 75w max.

T24 EN★

3113405EN3-05
(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 20" H: 18.75"
10' wire pre-laced through 3' chain

T24

3113403-05
(5) Medium Base 75w max.

T24 EN★

3113403EN3-05
(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



ENGLEHORN

DAMP

THREE LIGHT PENDANT

D: 20" H: 24"
10' wire pre-laced through 3' chain

T24

6613403-05
(3) Medium Base 100w max.

T24 EN★

6613403EN3-05
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 16" H: 16.75" Semi-Flush H: 14.5"
10' wire pre-laced through 3' chain

T24

7713402-05
(2) Medium Base 100w max.

T24 EN★

7713402EN3-05
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

**ONE LIGHT
MINI-PENDANT**

D: 4" H: 9.25"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6113401-05
(1) Medium Base 100w max.

T24 EN★

6113401EN3-05
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**ONE LIGHT
WALL / BATH**

W: 5" H: 13" E: 7"
Height from center of outlet box
up: 10.5" down: 2.5"

T24

4113401-05
(1) Medium Base 75w max.

T24 EN★

4113401EN3-05
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**ENGLEHORN
WALL / BATH
COLLECTION**

Chrome Finish

See more Englehorn
Wall / Bath on p.400

Recommended
Product



GEARY CEILING
FLUSH MOUNT
Chrome
p.366

HEWITT

DAMP

NINE LIGHT CHANDELIER

D: 28" H: 27.375"

Supplied with 20' of wire and 7' of chain

T24

F3313/9PN

(9) Candelabra Base 60w max.

See more Polished Nickel Finish on p.190



POLISHED NICKEL FINISH [-PN]
WHITE LINED PARCHMENT SHADES

DAMP

NINE LIGHT CHANDELIER

D: 28" H: 27.375"

Supplied with 20' of wire and 7' of chain

T24

F3313/9SN

(9) Candelabra Base 60w max.

See more Satin Nickel Finish on p.192



SATIN NICKEL FINISH [-SN]
WHITE LINED PARCHMENT SHADES

HEWITT

DAMP

EIGHT LIGHT LINEAR CHANDELIER

L: 46" W: 12.375" H: 11.625"
Supplied with 15' of wire,
(8) 12" stems, (2) 6" stems

T24

F3312/8PN

(8) Candelabra Base 60w max.



DAMP

SIX LIGHT CHANDELIER

D: 26" H: 21.375"
Supplied with 15' of wire and 5' of chain

T24

F3311/6PN

(6) Candelabra Base 60w max.



DAMP

FOUR LIGHT CHANDELIER

D: 20" H: 18.625"

Supplied with 15' of wire and 5' of chain

T24

F3310/4PN

(4) Candelabra Base 60w max.



DAMP

FOUR LIGHT SEMI FLUSH MOUNT

D: 15" H: 12.75"

T24

SF349PN

(4) Candelabra Base 60w max.



HEWITT

DAMP

EIGHT LIGHT LINEAR CHANDELIER

L: 46" W: 12.375" H: 11.625"
Supplied with 15' of wire,
(8) 12" stems, (2) 6" stems

T24

F3312/8SN

(8) Candelabra Base 60w max.



DAMP

SIX LIGHT CHANDELIER

D: 26" H: 21.375"
Supplied with 15' of wire and 5' of chain

T24

F3311/6SN

(6) Candelabra Base 60w max.



DAMP

FOUR LIGHT CHANDELIER

D: 20" H: 18.625"

Supplied with 15' of wire and 5' of chain

T24

F3310/4SN

(4) Candelabra Base 60w max.



DAMP

FOUR LIGHT SEMI FLUSH MOUNT

D: 15" H: 12.75"

T24

SF349SN

(4) Candelabra Base 60w max.



HETTINGER

PRODUCT SHOWN: HETTINGER SIX LIGHT
CHANDELIER IN BRUSHED NICKEL FINISH



DAMP

NINE LIGHT CHANDELIER

D: 30" H: 24.75"
10' wire pre-laced through 6' chain

T24

3139109-962
(9) Medium Base 60w max.

T24 EN★

3139109EN3-962
(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel Finish on p.196



BRUSHED NICKEL FINISH
ETCHED GLASS, WHITE INSIDE

DAMP

NINE LIGHT CHANDELIER

D: 30" H: 24.75"
10' wire pre-laced through 6' chain

T24

3139109-710
(9) Medium Base 60w max.

T24 EN★

3139109EN3-710
(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Burnt Sienna Finish on p.198



BURNT SIENNA FINISH
ETCHED GLASS, WHITE INSIDE

HETTINGER

DAMP

SIX LIGHT CHANDELIER

D: 24.5" H: 18.25"
10' wire pre-laced through 6' chain

T24

3139106-962
(6) Medium Base 100w max.

T24 EN★

3139106EN3-962
(6) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT PENDANT

D: 19" H: 22.25"
10' wire pre-laced through 6' chain

T24

6639103-962
(3) Medium Base 100w max.

T24 EN★

6639103EN3-962
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP +

**TWO LIGHT
SEMI-FLUSH
CONVERTIBLE PENDANT**

D: 13.25" H: 11.25" Semi-Flush H: 10.5"
10' wire pre-laced through 3' chain

T24

7739102-962
(2) Medium Base 100w max.

T24 EN★

7739102EN3-962
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

**ONE LIGHT
MINI-PENDANT**

D: 3.5" H: 7.25"
12' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6124601-962
(1) Medium Base 100w max.

T24 EN★

6124601EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**ONE LIGHT
WALL / BATH**

W: 4.5" H: 8" E: 5"
Height from center of outlet box
up: 5.75" down: 2.25"

T24

4139101-962
(1) Medium Base 100w max.

T24 EN★

4139101EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**HETTINGER
WALL / BATH
COLLECTION**

Brushed Nickel

See more Hettinger
Wall / Bath on p.396

Recommended
Products



GEARY PENDANT
Brushed Nickel
p.346



CANFIELD
PENDANT
Brushed Nickel
p.95



GEARY CEILING
FLUSH MOUNT
Brushed Nickel
p.366

HETTINGER

DAMP

SIX LIGHT CHANDELIER

D: 24.5" H: 18.25"

10' wire pre-laced through 6' chain

T24

3139106-710

(6) Medium Base 100w max.

T24 EN★

3139106EN3-710

(6) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT PENDANT

D: 19" H: 22.25"

10' wire pre-laced through 6' chain

T24

6639103-710

(3) Medium Base 100w max.

T24 EN★

6639103EN3-710

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP +

**TWO LIGHT
SEMI-FLUSH
CONVERTIBLE PENDANT**

D: 13.25" H: 11.25" Semi-Flush H: 10.5"
10' wire pre-laced through 3' chain

T24

7739102-710
(2) Medium Base 100w max.

T24 EN★

7739102EN3-710
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

**ONE LIGHT
MINI-PENDANT**

D: 3.5" H: 7.25"
12' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6124601-710
(1) Medium Base 100w max.

T24 EN★

6124601EN3-710
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**ONE LIGHT
WALL / BATH**

W: 4.5" H: 8" E: 5"
Height from center of outlet box
up: 5.75" down: 2.25"

T24

4139101-710
(1) Medium Base 100w max.

T24 EN★

4139101EN3-710
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**HETTINGER
WALL / BATH
COLLECTION**
Burnt Sienna

See more Hettinger
Wall / Bath on p.396

Recommended
Products



GEARY PENDANT
Burnt Sienna
p.346



CANFIELD
PENDANT
Burnt Sienna
p.97



GEARY CEILING
FLUSH MOUNT
Burnt Sienna
p.366

PARKFIELD

DAMP

NINE LIGHT CHANDELIER

D: 33.5" H: 31.5"

10' wire pre-laced through 6' chain

T24

3113009-962

(9) Medium Base 75w max.

T24

EN★

3113009EN3-962

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

See more Brushed Nickel Finish on p.202



BRUSHED NICKEL FINISH
ETCHED GLASS, WHITE INSIDE

DAMP

NINE LIGHT CHANDELIER

D: 33.5" H: 31.5"
10' wire pre-laced through 6' chain

T24

3113009-845
(9) Medium Base 75w max.

T24 EN★

3113009EN3-845
(9) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

See more Flemish Bronze Finish on p.204



FLEMISH BRONZE FINISH
CREME PARCHMENT GLASS

PARKFIELD

DAMP

FIVE LIGHT CHANDELIER

D: 24.75" H: 21"
10' wire pre-laced through 6' chain

T24

3113005-962
(5) Medium Base 75w max.

T24 EN★

3113005EN3-962
(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT DOWNLIGHT CHANDELIER

D: 18.5" H: 19.75"
6' wire pre-laced through 3' chain

T24

3213003-962
(3) Medium Base 75w max.

T24 EN★

3213003EN3-962
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT PENDANT

D: 19" H: 22.75"
6' wire pre-laced through 3' chain

T24

6613003-962
(3) Medium Base 75w max.

T24 EN★

6613003EN3-962
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 15" H: 13.75" Semi-Flush H: 12"
6' wire pre-laced through 3' chain

T24

7713002-962
(2) Medium Base 75w max.

T24 EN★

7713002EN3-962
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP

**TWO LIGHT
CEILING FLUSH MOUNT**

D: 13.25" H: 6.25"

T24

75520-962

(2) Medium Base 60w max.

T24 EN★

75520EN3-962(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

DAMP

ONE LIGHT PENDANT

D: 15" H: 6"

6' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6513001-962

(1) Medium Base 75w max.

T24 EN★

6513001EN3-962(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

DAMP

**ONE LIGHT
MINI-PENDANT**

L: 5.25" W: 5.25" H: 6.75"

6' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6113001-962

(1) Medium Base 75w max.

T24 EN★

6113001EN3-962(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

DAMP +

**ONE LIGHT
WALL / BATH**

W: 5.5" H: 10" E: 6"

Height from center of outlet box
up: 7.25" down: 2.75"

T24

4113001-962

(1) Medium Base 75w max.

T24 EN★

4113001EN3-962(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

DAMP +

**PARKFIELD
WALL / BATH
COLLECTION**

Brushed Nickel

See more Parkfield
Wall / Bath on p.408

PARKFIELD

DAMP

FIVE LIGHT CHANDELIER


D: 24.75" H: 21"
10' wire pre-laced through 6' chain

T24

3113005-845
(5) Medium Base 75w max.

T24 EN★

3113005EN3-845
(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT DOWNLIGHT CHANDELIER


D: 18.5" H: 19.75"
6' wire pre-laced through 3' chain

T24

3213003-845
(3) Medium Base 75w max.

T24 EN★

3213003EN3-845
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT PENDANT

D: 19" H: 22.75"
6' wire pre-laced through 3' chain

T24

6613003-845
(3) Medium Base 75w max.

T24 EN★

6613003EN3-845
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 15" H: 13.75" Semi-Flush H: 12"
6' wire pre-laced through 3' chain

T24

7713002-845
(2) Medium Base 75w max.

T24 EN★

7713002EN3-845
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP

**TWO LIGHT
CEILING FLUSH MOUNT**

D: 13.25" H: 6.25"

T24

75520-845

(2) Medium Base 60w max.

T24 EN★

75520EN3-845

(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT PENDANT

D: 15" H: 6"

6' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6513001-845

(1) Medium Base 75w max.

T24 EN★

6513001EN3-845

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP

**ONE LIGHT
MINI-PENDANT**

L: 5.25" W: 5.25" H: 6.75"

6' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6113001-845

(1) Medium Base 75w max.

T24 EN★

6113001EN3-845

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

**ONE LIGHT
WALL / BATH**

W: 5.5" H: 10" E: 6"

Height from center of outlet box
up: 7.25" down: 2.75"

T24

4113001-845

(1) Medium Base 75w max.

T24 EN★

4113001EN3-845

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

**PARKFIELD
WALL / BATH
COLLECTION**

Flemish Bronze

See more Parkfield
Wall / Bath on p.408

ELLIS HARPER

DAMP

EIGHT LIGHT CHANDELIER

L: 35.5" W: 35.5" H: 27.75"
Supplied with 10' of wire,
(3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3113708-962

(8) Medium Base 75w max.

T24 EN★

3113708EN3-962

(8) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel Finish
on p.208



Canopy Detail



BRUSHED NICKEL FINISH
ETCHED, WHITE INSIDE GLASS

DAMP

EIGHT LIGHT CHANDELIER

L: 35.5" W: 35.5" H: 27.75"
 Supplied with 10' of wire,
 (3) 12" stems, (1) 6" stem
 and sloped ceiling mounting hardware

T24

3113708-778

(8) Medium Base 75w max.

T24 EN★

3113708EN3-778

(8) Med. Base LED 3000K,
 9.5w, 800 lumen lamps incl.

See more Brushed Oil Rubbed Bronze Finish
 on p.210



Canopy Detail



BRUSHED OIL RUBBED BRONZE FINISH
 ETCHED, WHITE INSIDE GLASS

ELLIS HARPER

DAMP

FIVE LIGHT ISLAND PENDANT

L: 46.75" W: 5.75" H: 18"
Supplied with 10' of wire,
(2) 6" stems, (6) 12" stems

T24

6613705-962
(5) Medium Base 75w max.

T24 EN★

6613705EN3-962
(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

FOUR LIGHT CHANDELIER

L: 24.75" W: 24.75" H: 19.25"
Supplied with 10' of wire,
(3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3113704-962
(4) Medium Base 75w max.

T24 EN★

3113704EN3-962
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP

**ONE LIGHT
MINI-PENDANT**

L: 5.75" W: 5.75" H: 12"
Supplied with 10' of wire,
(3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6113701-962

(1) Medium Base 75w max.

T24 EN★

6113701EN3-962

(1) Med. Base LED 3000K,
9.5w 800 lumen lamp incl.



DAMP

**TWO LIGHT
CEILING SEMI-FLUSH MOUNT**

L: 13" W: 13" H: 7.5"

T24

7713702-962

(2) Medium Base 75w max.

T24 EN★

7713702EN3-962

(2) Med. Base LED 3000K,
9.5w 800 lumen lamp incl.



DAMP

**TWO LIGHT
CEILING FLUSH MOUNT**

L: 13" W: 13" H: 5.375"

T24

7513702-962

(2) Medium Base 60w max.

T24 EN★

7513702EN3-962

(2) Med. Base LED 3000K,
9.5w 800 lumen lamp incl.



DAMP +

**ONE LIGHT
WALL / BATH SCONCE**

W: 5.75" H: 10.125" E: 6.625"
Height from center of outlet box
up: 7.625" down: 2.5"

T24

4113701-962

(1) Medium Base 75w max.

T24 EN★

4113701EN3-962

(1) Med. Base LED 3000K,
9.5w 800 lumen lamp incl.



DAMP +

**ELLIS HARPER
WALL / BATH
COLLECTION**

Brushed Nickel

See more Ellis Harper
Wall / Bath on p.410

ELLIS HARPER

DAMP

FIVE LIGHT ISLAND PENDANT

L: 46.75" W: 5.75" H: 18"
Supplied with 10' of wire,
(2) 6" stems, (6) 12" stems

T24

6613705-778

(5) Medium Base 75w max.

T24 EN★

6613705EN3-778

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

FOUR LIGHT CHANDELIER

L: 24.75" W: 24.75" H: 19.25"
Supplied with 10' of wire,
(3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

3113704-778

(4) Medium Base 75w max.

T24 EN★

3113704EN3-778

(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP

**ONE LIGHT
MINI-PENDANT**

L: 5.75" W: 5.75" H: 12"

Supplied with 10' of wire,
(3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6113701-778

(1) Medium Base 75w max.

T24 EN★

6113701EN3-778(1) Med. Base LED 3000K,
9.5w 800 lumen lamp incl.

DAMP

**TWO LIGHT
CEILING SEMI-FLUSH MOUNT**

L: 13" W: 13" H: 7.5"

T24

7713702-778

(2) Medium Base 75w max.

T24 EN★

7713702EN3-778(2) Med. Base LED 3000K,
9.5w 800 lumen lamp incl.

DAMP

**TWO LIGHT
CEILING FLUSH MOUNT**

L: 13" W: 13" H: 5.375"

T24

7513702-778

(2) Medium Base 60w max.

T24 EN★

7513702EN3-778(2) Med. Base LED 3000K,
9.5w 800 lumen lamp incl.

DAMP +

**ONE LIGHT
WALL / BATH SCONCE**

W: 5.75" H: 10.125" E: 6.625"

Height from center of outlet box
up: 7.625" down: 2.5"

T24

4113701-778

(1) Medium Base 75w max.

T24 EN★

4113701EN3-778(1) Med. Base LED 3000K,
9.5w 800 lumen lamp incl.

DAMP +

**ELLIS HARPER
WALL / BATH
COLLECTION**

Brushed Oil Rubbed Bronze

See more Ellis Harper
Wall / Bath on p.410

FRANPORT

PRODUCT SHOWN: FRANPORT FIFTEEN LIGHT
CHANDELIER IN BURNT SIENNA FINISH



DAMP 50LB

FIFTEEN LIGHT CHANDELIER

D: 42.5" H: 35.625"
10' wire pre-laced through 6' chain

T24

3128915-962
(15) Medium Base 60w max.

T24 EN★

3128915EN3-962
(15) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel Finish on p.214



BRUSHED NICKEL FINISH
ETCHED GLASS, WHITE INSIDE

DAMP 50LB

FIFTEEN LIGHT CHANDELIER

D: 42.5" H: 35.625"
10' wire pre-laced through 6' chain

T24

3128915-710
(15) Medium Base 60w max.

T24 EN★

3128915EN3-710
(15) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Burnt Sienna Finish on p.216



BURNT SIENNA FINISH
ETCHED GLASS, WHITE INSIDE

FRANPORT

DAMP

NINE LIGHT CHANDELIER

D: 30" H: 27.625"

10' wire pre-laced through 6' chain

T24

3128909-962

(9) Medium Base 100w max.

T24 EN★

3128909EN3-962

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

FIVE LIGHT CHANDELIER

D: 26" H: 22.875"

10' wire pre-laced through 6' chain

T24

3128905-962

(5) Medium Base 100w max.

T24 EN★

3128905EN3-962

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 20" H: 21"

10' wire pre-laced through 6' chain

T24

3128903-962

(3) Medium Base 100w max.

T24 EN★

3128903EN3-962(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

DAMP +

**ONE LIGHT
WALL / BATH**

W: 5" H: 8" E: 6.875"

Height from center of outlet box

up: 4" down: 4"

T24

4128901-962

(1) Medium Base 100w max.

T24 EN★

4128901EN3-962(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

DAMP +

**FRANPORT
WALL / BATH
COLLECTION**

Brushed Nickel

See more Franport
Wall / Bath on p.406Recommended
ProductsGEARY PENDANT
Brushed Nickel
p.346NASH CEILING
FLUSH MOUNT
Brushed Nickel
p.364

FRANPORT

DAMP

NINE LIGHT CHANDELIER

D: 30" H: 27.625"
10' wire pre-laced through 6' chain

T24

3128909-710

(9) Medium Base 100w max.

T24 EN★

3128909EN3-710

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

FIVE LIGHT CHANDELIER

D: 26" H: 22.875"
10' wire pre-laced through 6' chain

T24

3128905-710

(5) Medium Base 100w max.

T24 EN★

3128905EN3-710

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 20" H: 21"
10' wire pre-laced through 6' chain

T24

3128903-710
(3) Medium Base 100w max.

T24 EN★

3128903EN3-710
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

ONE LIGHT WALL / BATH

W: 5" H: 8" E: 6.875"
Height from center of outlet box
up: 4" down: 4"

T24

4128901-710
(1) Medium Base 100w max.

T24 EN★

4128901EN3-710
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

FRANPORT WALL / BATH COLLECTION

Burnt Sienna

See more Franport
Wall / Bath on p.406

Recommended Products



GEARY PENDANT
Burnt Sienna
p.346



NASH CEILING
FLUSH MOUNT
Heirloom Bronze
p.364



NINE LIGHT CHANDELIER

D: 30" H: 24" Downlight H: 28.75"
12' wire pre-laced through 10' chain



31062-962

(9) Medium Base 100w max.



31062EN3-962

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel Finish on p.220



BRUSHED NICKEL FINISH
SATIN WHITE GLASS

**NINE LIGHT CHANDELIER**

D: 30" H: 24" Downlight H: 28.75"
12' wire pre-laced through 10' chain

T24

31062-782

(9) Medium Base 100w max.

T24

EN★

31062EN3-782

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Heirloom Bronze Finish on p.222



HEIRLOOM BRONZE FINISH
SATIN ETCHED GLASS

SUSSEX



FIVE LIGHT CHANDELIER

D: 24" H: 15.5" Downlight H: 20"
12' wire pre-laced through 10' chain

T24

31061-962

(5) Medium Base 100w max.

T24 EN*

31061EN3-962

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT CHANDELIER

D: 22" H: 15.5" Downlight H: 20"
12' wire pre-laced through 10' chain

T24

31060-962

(3) Medium Base 100w max.

T24 EN*

31060EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT ISLAND PENDANT

L: 26" W: 7.5" H: 18.25"
(2) 12' strips of wire pre-laced through 10' chain

T24

66061-962

(3) Medium Base 100w max.

T24 EN*

66061EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





+
**THREE LIGHT
 SEMI-FLUSH
 CONVERTIBLE PENDANT**

D: 15.25" H: 16.75" Semi-Flush H: 15"
 12' wire pre-laced through 10' chain

T24

66062-962
 (3) Medium Base 100w max.

T24 EN★

66062EN3-962
 (3) Med. Base LED 3000K,
 9.5w, 800 lumen lamps incl.



**THREE LIGHT
 CEILING SEMI-FLUSH MOUNT**

D: 15.75" H: 12.5"

T24

75061-962
 (3) Medium Base 100w max.

T24 EN★

75061EN3-962
 (3) Med. Base LED 3000K,
 9.5w, 800 lumen lamps incl.



ONE LIGHT PENDANT

D: 15.75" H: 20"
 12' wire pre-laced through 10' chain

T24

66060-962
 (1) Medium Base 150w max.

T24 EN★

66060EN3-962
 (1) Med. Base LED 3000K,
 9.5w, 800 lumen lamp incl.



**ONE LIGHT
 MINI-PENDANT**

D: 7.5" H: 7.5"
 10' wire, (3) 12" stems, 12" chain

T24

61060-962
 (1) Medium Base 100w max.

T24 EN★

61060EN3-962
 (1) Med. Base LED 3000K,
 9.5w, 800 lumen lamp incl.



DAMP +

**ONE LIGHT
 WALL / BATH**

W: 7.5" H: 10.25" E: 10.25"
 Height from center of outlet box
 up: 7" down: 3.25"

T24

44060-962
 (1) Medium Base 100w max.

T24 EN★

44060EN3-962
 (1) Med. Base LED 3000K,
 9.5w, 800 lumen lamp incl.



DAMP +

**SUSSEX
 WALL / BATH
 COLLECTION**

Brushed Nickel

See more Sussex
 Wall / Bath on p.424

**Recommended
 Product**



GEARY CEILING
 FLUSH MOUNT
 Brushed Nickel
 p.366

SUSSEX



FIVE LIGHT CHANDELIER

D: 24" H: 15.5" Downlight H: 20"
12' wire pre-laced through 10' chain

T24

31061-782

(5) Medium Base 100w max.

T24 EN★

31061EN3-782

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT CHANDELIER

D: 22" H: 15.5" Downlight H: 20"
12' wire pre-laced through 10' chain

T24

31060-782

(3) Medium Base 100w max.

T24 EN★

31060EN3-782

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT ISLAND PENDANT

L: 26" W: 7.5" H: 18.25"
(2) 12' strips of wire pre-laced through 10' chain

T24

66061-782

(3) Medium Base 100w max.

T24 EN★

66061EN3-782

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





+
**THREE LIGHT
 SEMI-FLUSH
 CONVERTIBLE PENDANT**

D: 15.25" H: 16.75" Semi-Flush H: 15"
 12' wire pre-laced through 10' chain

T24
66062-782
 (3) Medium Base 100w max.

T24 EN★
66062EN3-782
 (3) Med. Base LED 3000K,
 9.5w, 800 lumen lamps incl.



**THREE LIGHT
 CEILING SEMI-FLUSH MOUNT**
 D: 15.75" H: 12.5"

T24
75061-782
 (3) Medium Base 100w max.

T24 EN★
75061EN3-782
 (3) Med. Base LED 3000K,
 9.5w, 800 lumen lamps incl.



ONE LIGHT PENDANT

D: 15.75" H: 20"
 12' wire pre-laced through 10' chain

T24
66060-782
 (1) Medium Base 150w max.

T24 EN★
66060EN3-782
 (1) Med. Base LED 3000K,
 9.5w, 800 lumen lamp incl.



**ONE LIGHT
 MINI-PENDANT**

D: 7.5" H: 7.5"
 10' wire, (3) 12" stems, 12" chain

T24
61060-782
 (1) Medium Base 100w max.

T24 EN★
61060EN3-782
 (1) Med. Base LED 3000K,
 9.5w, 800 lumen lamp incl.



DAMP +
**ONE LIGHT
 WALL / BATH**

W: 7.5" H: 10.25" E: 10.25"
 Height from center of outlet box
 up: 7" down: 3.25"

T24
44060-782
 (1) Medium Base 100w max.

T24 EN★
44060EN3-782
 (1) Med. Base LED 3000K,
 9.5w, 800 lumen lamp incl.



DAMP +
**SUSSEX
 WALL / BATH
 COLLECTION**

Heirloom Bronze

See more Sussex
 Wall / Bath on p.424

Recommended
 Product



GEARY CEILING
 FLUSH MOUNT
 Heirloom Bronze
 p.366

HANFORD

DAMP 50LB

FIFTEEN LIGHT CHANDELIER

D: 43.25" H: 42.75"

12' wire pre-laced through 10' chain

T24

3124515-962

(15) Medium Base 60w max.

T24 EN★

3124515EN3-962

(15) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel Finish on p.226



BRUSHED NICKEL FINISH
SATIN ETCHED GLASS

DAMP 50LB**FIFTEEN LIGHT CHANDELIER**

D: 43.25" H: 42.75"
12' wire pre-laced through 10' chain

T24**3124515-710**

(15) Medium Base 60w max.

T24 EN★**3124515EN3-710**

(15) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Burnt Sienna Finish on p.228



BURNT SIENNA FINISH
SATIN ETCHED GLASS

HANFORD

DAMP

NINE LIGHT CHANDELIER

D: 33" H: 37"

12' wire pre-laced through 10' chain

T24

3124509-962

(9) Medium Base 100w max.

T24

EN★

3124509EN3-962

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

FIVE LIGHT CHANDELIER

D: 27.75" H: 27.75"

6' wire pre-laced through 3' chain

T24

3124505-962

(5) Medium Base 100w max.

T24

EN★

3124505EN3-962

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT HALL / FOYER

D: 18.25" H: 32.75"

6' wire pre-laced through 3' chain

T24

5224503-962

(3) Medium Base 100w max.

T24

EN★

5224503EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP

THREE LIGHT PENDANT

D: 20.75" H: 22.75"

6' wire pre-laced through 3' chain

T24

6624503-962

(3) Medium Base 100w max.

T24 EN★

6624503EN3-962(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 20.75" H: 14.25" Semi-Flush H: 11.75"

6' wire pre-laced through 3' chain

T24

7724503-962

(3) Medium Base 100w max.

T24 EN★

7724503EN3-962(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

DAMP

ONE LIGHT MINI-PENDANT

D: 5.25" H: 6.75"

10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6124501-962

(1) Medium Base 100w max.

T24 EN★

6124501EN3-962(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

DAMP +

ONE LIGHT WALL / BATH

W: 5.25" H: 10.25" E: 6.75"

Height from center of outlet box
up: 7.25" down: 3"

T24

4124501-962

(1) Medium Base 100w max.

T24 EN★

4124501EN3-962(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

DAMP +

HANFORD WALL / BATH COLLECTION

Brushed Nickel

See more Hanford
Wall / Bath on p.416Recommended
ProductsGEARY PENDANT
Brushed Nickel
p.346NASH CEILING
FLUSH MOUNT
Brushed Nickel
p.364

HANFORD

DAMP

NINE LIGHT CHANDELIER

D: 33" H: 37"

12' wire pre-laced through 10' chain

T24

3124509-710

(9) Medium Base 100w max.

T24 EN★

3124509EN3-710

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

FIVE LIGHT CHANDELIER

D: 27.75" H: 27.75"

6' wire pre-laced through 3' chain

T24

3124505-710

(5) Medium Base 100w max.

T24 EN★

3124505EN3-710

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT HALL / FOYER

D: 18.25" H: 32.75"

6' wire pre-laced through 3' chain

T24

5224503-710

(3) Medium Base 100w max.

T24 EN★

5224503EN3-710

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP

THREE LIGHT PENDANT

D: 20.75" H: 22.75"
6' wire pre-laced through 3' chain

T24

6624503-710
(3) Medium Base 100w max.

T24 EN★

6624503EN3-710
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

THREE LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 20.75" H: 14.25" Semi-Flush H: 11.75"
6' wire pre-laced through 3' chain

T24

7724503-710
(3) Medium Base 100w max.

T24 EN★

7724503EN3-710
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT MINI-PENDANT

D: 5.25" H: 6.75"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6124501-710
(1) Medium Base 100w max.

T24 EN★

6124501EN3-710
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

ONE LIGHT WALL / BATH

W: 5.25" H: 10.25" E: 6.75"
Height from center of outlet box
up: 7.25" down: 3"

T24

4124501-710
(1) Medium Base 100w max.

T24 EN★

4124501EN3-710
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

HANFORD WALL / BATH COLLECTION

Burnt Sienna

See more Hanford
Wall / Bath on p.416

Recommended Products



GEARY PENDANT
Burnt Sienna
p.346



NASH CEILING
FLUSH MOUNTS
Heirloom Bronze
p.364

ELMWOOD PARK

PRODUCT SHOWN: ELMWOOD PARK FOUR LIGHT
ISLAND PENDANT IN BRUSHED NICKEL FINISH



DAMP

NINE LIGHT CHANDELIER

D: 32" H: 27.625"
12' of wire pre-laced through 6' of chain

T24

3137309-962
(9) Medium Base 75w max.

T24 EN★

3137309EN3-962
(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See More Brushed Nickel Finish on p.232



BRUSHED NICKEL FINISH
SATIN ETCHED WITH CLEAR GLASS

DAMP

NINE LIGHT CHANDELIER

D: 32" H: 27.625"
12' of wire pre-laced through 6' of chain

T24

3137309-782
(9) Medium Base 75w max.

T24 EN★

3137309EN3-782
(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See More Heirloom Bronze Finish on p.234



HEIRLOOM BRONZE FINISH
SATIN ETCHED WITH CLEAR GLASS

ELMWOOD PARK

DAMP

FIVE LIGHT CHANDELIER

D: 26" H: 24.125"
12' of wire pre-laced through 6' of chain

T24

3137305-962
(5) Medium Base 75w max.

T24 EN★

3137305EN3-962
(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

FOUR LIGHT ISLAND PENDANT


L: 40" W: 4.375" H: 24.75"
Supplied with 6' of wire, (3) 12" stems,
(3) 12" stems, (1) 6" stem, (1) 6" stem

T24

6637304-962
(4) Medium Base 75w max.

T24 EN★

6637304EN3-962
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 20.5" H: 21"
6' of wire pre-laced through 3' of chain

T24

3137303-962
(3) Medium Base 75w max.

T24 EN★

3137303EN3-962
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP

THREE LIGHT PENDANT

D: 19" H: 18"

Supplied with 6' of wire, (3) 12" stems, (1) 6" stem, (1) 6" stem and sloped ceiling mounting hardware

T24

6537303-962

(3) Medium Base 75w max.

T24 EN★

6537303EN3-962

(3) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT SEMI-FLUSH MOUNT

D: 19" H: 15.75"

T24

7737303-962

(3) Medium Base 75w max.

T24 EN★

7737303EN3-962

(3) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



DAMP

TWO LIGHT SEMI-FLUSH MOUNT

D: 15" H: 11"

T24

7737302-962

(2) Medium Base 75w max.

T24 EN★

7737302EN3-962

(2) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



DAMP

TWO LIGHT CEILING FLUSH MOUNT

D: 14" H: 6.125"

T24

7537302-962

(2) Medium Base 60w max.

T24 EN★

7537302EN3-962

(2) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT MINI-PENDANT

D: 4.375" H: 6.875"

Supplied with 6' of wire, (3) 12" stems, (1) 6" stem, (1) 6" stem and sloped ceiling mounting hardware

T24

6137301-962

(1) Medium Base 75w max.

T24 EN★

6137301EN3-962

(1) Med. Base LED 9.5w Bulb lamps incl.



DAMP +

ONE LIGHT WALL / BATH SCONCE

W: 4.5" H: 8" E: 6.25"

Height from center of outlet box up: 5" down: 3"

T24

4137301-962

(1) Medium Base 75w max.

T24 EN★

4137301EN3-962

(1) Med. Base LED 9.5w Bulb lamps



DAMP +

ELMWOOD PARK WALL / BATH COLLECTION

Brushed Nickel Finish

See more Elmwood Park Wall / Bath on p.392

ELMWOOD PARK

DAMP

FIVE LIGHT CHANDELIER

D: 26" H: 24.125"
12' of wire pre-laced through 6' of chain

T24

3137305-782

(5) Medium Base 75w max.

T24 EN★

3137305EN3-782

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

FOUR LIGHT ISLAND PENDANT

L: 40" W: 4.375" H: 24.75"
Supplied with 6' of wire, (3) 12" stems,
(3) 12" stems, (1) 6" stem, (1) 6" stem

T24


6637304-782

(4) Medium Base 75w max.

T24 EN★

6637304EN3-782

(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 20.5" H: 21"
6' of wire pre-laced through 3' of chain

T24

3137303-782

(3) Medium Base 75w max.

T24 EN★

3137303EN3-782

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP

THREE LIGHT PENDANT

D: 19" H: 18"

Supplied with 6' of wire, (3) 12" stems, (1) 6" stem, (1) 6" stem and sloped ceiling mounting hardware

T24

6537303-782

(3) Medium Base 75w max.

T24 EN★

6537303EN3-782

(3) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT SEMI-FLUSH MOUNT

D: 19" H: 15.75"

T24

7737303-782

(3) Medium Base 75w max.

T24 EN★

7737303EN3-782

(3) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



DAMP

TWO LIGHT SEMI-FLUSH MOUNT

D: 15" H: 11"

T24

7737302-782

(2) Medium Base 75w max.

T24 EN★

7737302EN3-782

(2) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



DAMP

TWO LIGHT CEILING FLUSH MOUNT

D: 14" H: 6.125"

T24

7537302-782

(2) Medium Base 60w max.

T24 EN★

7537302EN3-782

(2) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT MINI-PENDANT

D: 4.375" H: 6.875"

Supplied with 6' of wire, (3) 12" stems, (1) 6" stem, (1) 6" stem and sloped ceiling mounting hardware

T24

6137301-782

(1) Medium Base 75w max.

T24 EN★

6137301EN3-782

(1) Med. Base LED 9.5w Bulb lamps incl.



DAMP +

ONE LIGHT WALL / BATH SCONCE

W: 4.5" H: 8" E: 6.25"

Height from center of outlet box up: 5" down: 3"

T24

4137301-782

(1) Medium Base 75w max.

T24 EN★

4137301EN3-782

(1) Med. Base LED 9.5w Bulb lamps



DAMP +

ELMWOOD PARK WALL / BATH COLLECTION

Heirloom Bronze Finish

See more Elmwood Park Wall / Bath on p.392

VINTNER

EIGHTEEN LIGHT CHANDELIER

D: 43.125" H: 45.375"
Supplied with 20' of wire
and 7' of chain

T24

F2962/9+6+3SN

(18) Medium Base 75w max.

See more Satin Nickel Finish on p.238



SATIN NICKEL FINISH
WHITE OPAL ETCHED GLASS

**EIGHTEEN LIGHT
CHANDELIER**

D: 43.125" H: 45.375"
Supplied with 20' of wire
and 7' of chain

T24

F2962/9+6+3HTBZ
(18) Medium Base 75w max.

See more Heritage Bronze Finish on p.240



HERITAGE BRONZE FINISH
WHITE OPAL ETCHED GLASS

NINE LIGHT CHANDELIER

D: 32.125" H: 32.125"
Supplied with 20' of wire
and 7' of chain

T24

F2961/6+3SN
(9) Medium Base 75w max.



FIVE LIGHT CHANDELIER

D: 26" H: 23.875"
Supplied with 15' of wire
and 5' of chain

T24

F2960/5SN
(5) Medium Base 75w max.



THREE LIGHT CHANDELIER

D: 19" H: 18"
Supplied with 15' of wire
and 5' of chain

T24

F2963/3SN
(3) Medium Base 75w max.



THREE LIGHT LINEAR CHANDELIER

W: 35" H: 22.625"
Supplied with 15' of wire,
(1) 6" stem, (4) 12" stems

T24

F2965/3SN
(3) Medium Base 75w max.





**THREE LIGHT
CHANDELIER**

D: 25.875" H: 21.875"
Supplied with 15' of wire
and 5' of chain

T24

F2964/3SN

(3) Medium Base 75w max.



**THREE LIGHT
UPLIGHT CHANDELIER**

D: 20.125" H: 26.875"
Supplied with 15' of wire
and 5' of chain

T24

F2966/3SN

(3) Medium Base 75w max.



**ONE LIGHT
MINI-PENDANT**

W: 7.125" H: 12.625"
Supplied with 15' of wire,
(1) 6" stem, (3) 12" stems

T24

P1329SN

(1) Medium Base 75w max.



**THREE LIGHT
SEMI-FLUSH**

D: 14.5" H: 11.625"

T24

SF317SN

(3) Medium Base 60w max.



DAMP +

**ONE LIGHT
WALL SCONCE**

W: 5.5" H: 9" E: 6.625"
Height from center of outlet box
up: 3.5" down: 5.5"

T24

VS20101SN

(1) Medium Base 75w max.



DAMP +

**VINTNER
VANITY COLLECTION**

Satin Nickel

See more Vintner
Vanity on p.418



**VINTNER
CEILING COLLECTION**

Satin nickel

See more Vintner
Ceiling on p.373

VINTNER

NINE LIGHT CHANDELIER

D: 32.125" H: 32.125"
Supplied with 20' of wire
and 7' of chain

T24

F2961/6+3HTBZ
(9) Medium Base 75w max.



FIVE LIGHT CHANDELIER

D: 26" H: 23.875"
Supplied with 15' of wire
and 5' of chain

T24

F2960/5HTBZ
(5) Medium Base 75w max.



THREE LIGHT CHANDELIER

D: 19" H: 18"
Supplied with 15' of wire
and 5' of chain

T24

F2963/3HTBZ
(3) Medium Base 75w max.



THREE LIGHT LINEAR CHANDELIER

W: 35" H: 22.625"
Supplied with 15' of wire,
(1) 6" stem, (4) 12" stems

T24

F2965/3HTBZ
(3) Medium Base 75w max.





**THREE LIGHT
CHANDELIER**

D: 25.875" H: 21.875"
Supplied with 15' of wire
and 5' of chain

T24

F2964/3HTBZ

(3) Medium Base 75w max.



**THREE LIGHT
UPLIGHT CHANDELIER**

D: 20.125" H: 26.875"
Supplied with 15' of wire
and 5' of chain

T24

F2966/3HTBZ

(3) Medium Base 75w max.



**ONE LIGHT
MINI-PENDANT**

W: 7.125" H: 12.625"
Supplied with 15' of wire,
(1) 6" stem, (3) 12" stems

T24

P1329HTBZ

(1) Medium Base 75w max.



**THREE LIGHT
SEMI-FLUSH**

D: 14.5" H: 11.625"

T24

SF317HTBZ

(3) Medium Base 60w max.



DAMP +

**ONE LIGHT
WALL SCONCE**

W: 5.5" H: 9" E: 6.625"
Height from center of outlet box
up: 3.5" down: 5.5"

T24

VS20101HTBZ

(1) Medium Base 75w max.



DAMP +

**VINTNER
VANITY COLLECTION**

Heritage Bronze

See more Vintner
Vanity on p.418



**VINTNER
CEILING COLLECTION**
Heritage Bronze

See more Vintner
Ceiling on p.373

DAMP

NINE LIGHT CHANDELIER

D: 35" H: 35"

10' wire pre-laced through 6' chain

T24

3139009-962

(9) Medium Base 75w max.

T24

EN★

3139009EN3-962

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel Finish on p.244



BRUSHED NICKEL FINISH
SATIN ETCHED GLASS

DAMP

NINE LIGHT CHANDELIER

D: 35" H: 35"

10' wire pre-laced through 6' chain

T24

3139009-782

(9) Medium Base 75w max.

T24 EN★

3139009EN3-782(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Heirloom Bronze Finish on p.246

HEIRLOOM BRONZE FINISH
SATIN ETCHED GLASS

EMMONS

DAMP

FIVE LIGHT CHANDELIER

D: 24" H: 26.75"

10' wire pre-laced through 6' chain

T24

3139005-962

(5) Medium Base 100w max.

T24 EN★

3139005EN3-962

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 19.5" H: 22.5"

6' wire pre-laced through 3' chain

T24

3139003-962

(3) Medium Base 100w max.

T24 EN★

3139003EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT PENDANT

D: 17.75" H: 22.5"

10' wire pre-laced through 6' chain

T24

6639003-962

(3) Medium Base 100w max.

T24 EN★

6639003EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP

**TWO LIGHT
SEMI-FLUSH**

D: 13" H: 9"

T24

7739002-962

(2) Medium Base 100w max.

T24 EN★

7739002EN3-962(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

DAMP

**ONE LIGHT
MINI-PENDANT**

D: 6" H: 5.75"

6' wire, (1) 12" stem, (1) 6" stem
and sloped ceiling mounting hardware

T24

6139001-962

(1) Medium Base 100w max.

T24 EN★

6139001EN3-962(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

DAMP +

**ONE LIGHT
WALL / BATH**

W: 6" H: 6.25" E: 7.5"

Height from center of outlet box
up: 3.75" down: 2.5"

T24

4139001-962

(1) Medium Base 100w max.

T24 EN★

4139001EN3-962(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

DAMP +

**EMMONS
WALL / BATH
COLLECTION**

Brushed Nickel

See more Emmons
Wall / Bath on p.423Recommended
ProductsGEARY PENDANT
Brushed Nickel
p.346GEARY CEILING
FLUSH MOUNTS
Brushed Nickel
p.366

EMMONS

DAMP

FIVE LIGHT CHANDELIER

D: 24" H: 26.75"
10' wire pre-laced through 6' chain

T24

3139005-782

(5) Medium Base 100w max.

T24 EN★

3139005EN3-782

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 19.5" H: 22.5"
6' wire pre-laced through 3' chain

T24

3139003-782

(3) Medium Base 100w max.

T24 EN★

3139003EN3-782

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT PENDANT

D: 17.75" H: 22.5"
10' wire pre-laced through 6' chain

T24

6639003-782

(3) Medium Base 100w max.

T24 EN★

6639003EN3-782

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP

TWO LIGHT SEMI-FLUSH

D: 13" H: 9"

T24

7739002-782

(2) Medium Base 100w max.

T24

EN★

7739002EN3-782

(2) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT MINI-PENDANT

D: 6" H: 5.75"

6' wire, (1) 12" stem, (1) 6" stem and sloped ceiling mounting hardware

T24

6139001-782

(1) Medium Base 100w max.

T24

EN★

6139001EN3-782

(1) Med. Base LED 3000K, 9.5w, 800 lumen lamp incl.



DAMP

+

ONE LIGHT WALL / BATH

W: 6" H: 6.25" E: 7.5"

Height from center of outlet box up: 3.75" down: 2.5"

T24

4139001-782

(1) Medium Base 100w max.

T24

EN★

4139001EN3-782

(1) Med. Base LED 3000K, 9.5w, 800 lumen lamp incl.



DAMP

+

EMMONS WALL / BATH COLLECTION

Heirloom Bronze

See more Emmons Wall / Bath on p.423

Recommended Products



GEARY PENDANT
Heirloom Bronze
p.346



GEARY CEILING FLUSH MOUNTS
Heirloom Bronze
p.366

BARRINGTON

FIFTEEN LIGHT CHANDELIER

D: 38" H: 44.5"
Supplied with 10' of wire
and 8' of chain

T24

F2254/6+6+3ORB

(15) Medium Base 75w max.

See more Oil Rubbed Bronze Finish on p.252



OIL RUBBED BRONZE FINISH
WHITE OPAL ETCHED GLASS

**NINE LIGHT
CHANDELIER**

D: 29" H: 30"
Supplied with 10' of wire
and 8' of chain

T24**F2253/6+3BS**

(9) Medium Base 100w max.

See more Brushed Steel Finish on p.250



BRUSHED STEEL FINISH
WHITE OPAL ETCHED GLASS

**NINE LIGHT
CHANDELIER**

D: 29" H: 30"
Supplied with 10' of wire
and 8' of chain

T24**F2253/6+3ORB**

(9) Medium Base 100w max.



OIL RUBBED BRONZE FINISH
WHITE OPAL ETCHED GLASS

BARRINGTON



FIVE LIGHT CHANDELIER

D: 25.5" H: 25.375"
Supplied with 8' of wire
and 6' of chain

T24

F2252/5BS

(5) Medium Base 100w max.



FOUR LIGHT CHANDELIER

D: 26" H: 23.25"
Supplied with 8' of wire
and 6' of chain

T24

F2251/4BS

(4) Medium Base 100w max.



THREE LIGHT CHANDELIER

D: 22.5" H: 22.75"
Supplied with 8' of wire
and 6' of chain

T24

F2250/3BS

(3) Medium Base 100w max.




THREE LIGHT LINEAR CHANDELIER

L: 44" W: 12" H: 17.25"
Supplied with 8' of wire,
(4) 12" stems, (1) 6" stem

T24

F2248/3BS

(3) Medium Base 100w max.



THREE LIGHT UPLIGHT PENDANT

D: 18" H: 21"
Supplied with 8' of wire
and 6' of chain

T24

F2246/3BS

(3) Medium Base 100w max.



**THREE LIGHT
FLUSH MOUNT**
D: 16.5" H: 5.75"

T24

FM273BS
(3) Medium Base 60w max.



**TWO LIGHT
SEMI-FLUSH MOUNT**
D: 15" H: 11.5"

T24

SF241BS
(2) Medium Base 100w max.



**TWO LIGHT
SEMI-FLUSH MOUNT**
D: 13" H: 7.5"

T24

SF240BS
(2) Medium Base 60w max.



**ONE LIGHT
MINI-PENDANT**

D: 8" H: 6"
Supplied with 8' of wire,
(3) 12" stems, (1) 6" stem

T24

P1117BS
(1) Medium Base 100w max.



DAMP ADA

WALL SCONCE

W: 5.25" H: 15.25" E: 4"
Height from center of outlet box
up: 4"

T24

WB1341BS
(1) Medium Base 100w max.

LED

WB1341BS-L1



DAMP

ONE LIGHT WALL SCONCE

W: 5" H: 16" E: 6.75"
Height from center of outlet box
up: 4.5" down: 11"

VS12701-BS

(1) Medium Base 100w max.



DAMP +

**BARRINGTON
WALL / BATH
COLLECTION**

Brushed Steel

See more Barrington
Wall / Bath on p.431

BARRINGTON



FIVE LIGHT CHANDELIER

D: 25.5" H: 25.375"
Supplied with 8' of wire
and 6' of chain

T24

F2252/5ORB
(5) Medium Base 100w max.



FOUR LIGHT CHANDELIER

D: 26" H: 23.25"
Supplied with 8' of wire
and 6' of chain

T24

F2251/4ORB
(4) Medium Base 100w max.



THREE LIGHT CHANDELIER

D: 22.5" H: 22.75"
Supplied with 8' of wire
and 6' of chain

T24

F2250/3ORB
(3) Medium Base 100w max.



THREE LIGHT LINEAR CHANDELIER

L: 44" W: 12" H: 17.25"
Supplied with 8' of wire,
(4) 12" stems, (1) 6" stem

T24

F2248/3ORB
(3) Medium Base 100w max.



THREE LIGHT UPLIGHT PENDANT

D: 22" H: 22.25"
Supplied with 8' of wire
and 6' of chain

T24

F2245/3ORB
(3) Medium Base 100w max.



THREE LIGHT UPLIGHT PENDANT

D: 18" H: 21"
Supplied with 8' of wire
and 6' of chain

T24

F2246/3ORB
(3) Medium Base 100w max.



THREE LIGHT FLUSH MOUNT
D: 16.5" H: 5.75"

T24

FM273ORB
(3) Medium Base 60w max.



TWO LIGHT SEMI-FLUSH MOUNT
D: 15" H: 11.5"

T24

SF241ORB
(2) Medium Base 100w max.



TWO LIGHT SEMI-FLUSH MOUNT
D: 13" H: 7.5"

T24

SF240ORB
(2) Medium Base 60w max.



ONE LIGHT MINI-PENDANT

D: 8" H: 6"
Supplied with 8' of wire,
(3) 12" stems, (1) 6" stem

T24

P1117ORB
(1) Medium Base 100w max.



DAMP ADA

WALL SCONCE

W: 5.25" H: 15.25" E: 4"
Height from center of outlet box
up: 4"

T24

WB1341ORB
(1) Medium Base 100w max.

LED

WB1341ORB-L1



DAMP

ONE LIGHT WALL SCONCE

W: 5" H: 16" E: 6.75"
Height from center of outlet box
up: 4.5" down: 11"

VS12701-ORB

(1) Medium Base 100w max.



DAMP +

BARRINGTON WALL / BATH COLLECTION

Oil Rubbed Bronze

See more Barrington
Wall / Bath on p.431

METCALF

PRODUCT SHOWN: METCALF NINE LIGHT
CHANDELIER IN BRUSHED NICKEL FINISH



DAMP

NINE LIGHT CHANDELIER

D: 31" H: 35.75"
10' wire pre-laced through 6' chain

T24

3113209-962
(9) Medium Base 75w max.

T24 EN★

3113209EN3-962
(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel Finish on p.256



BRUSHED NICKEL FINISH
SATIN ETCHED GLASS

DAMP

NINE LIGHT CHANDELIER

D: 31" H: 35.75"
10' wire pre-laced through 6' chain

T24

3113209-715
(9) Medium Base 75w max.

T24 EN★

3113209EN3-715
(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Autumn Bronze Finish on p.258



AUTUM BRONZE FINISH
SATIN ETCHED GLASS

METCALF

DAMP

FIVE LIGHT CHANDELIER

D: 26" H: 25.75"
6' wire pre-laced through 3' chain

T24

3113205-962
(5) Medium Base 75w max.

T24 EN★

3113205EN3-962
(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 22" H: 22"
6' wire pre-laced through 3' chain

T24

3113203-962
(3) Medium Base 75w max.

T24 EN★

3113203EN3-962
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT PENDANT

D: 22" H: 24"
6' wire pre-laced through 3' chain

T24

6613203-962
(3) Medium Base 75w max.

T24 EN★

6613203EN3-962
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 15" H: 16.25" Semi-Flush H: 14.75"
6' wire pre-laced through 3' chain

T24

7713202-962
(2) Medium Base 75w max.

T24 EN★

7713202EN3-962
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP

ONE LIGHT PENDANT

D: 15" H: 7.5"
8' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6513201-962

(1) Medium Base 75w max.

T24 EN★

6513201EN3-962

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT MINI-PENDANT

D: 6.25" H: 7"
8' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6113201-962

(1) Medium Base 75w max.

T24 EN★

6113201EN3-962

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

ONE LIGHT WALL / BATH

W: 6.25" H: 10.75" E: 7.25"
Height from center of outlet box
up: 8.25" down: 2.5"

T24

4113201-962

(1) Medium Base 100w max.

T24 EN★

4113201EN3-962

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

METCALF WALL / BATH COLLECTION

Brushed Nickel

See more Metcalf
Wall / Bath on p.417

Recommended Products



GEARY PENDANT
Brushed Nickel
p.346



NASH CEILING
FLUSH MOUNT
Brushed Nickel
p.364

METCALF

DAMP

FIVE LIGHT CHANDELIER

D: 26" H: 25.75"
6' wire pre-laced through 3' chain

T24

3113205-715
(5) Medium Base 75w max.

T24 EN★

3113205EN3-715
(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 22" H: 22"
6' wire pre-laced through 3' chain

T24

3113203-715
(3) Medium Base 75w max.

T24 EN★

3113203EN3-715
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT PENDANT

D: 22" H: 24"
6' wire pre-laced through 3' chain

T24

6613203-715
(3) Medium Base 75w max.

T24 EN★

6613203EN3-715
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 15" H: 16.25" Semi-Flush H: 14.75"
6' wire pre-laced through 3' chain

T24

7713202-715
(2) Medium Base 75w max.

T24 EN★

7713202EN3-715
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP

ONE LIGHT PENDANT

D: 15" H: 7.5"
8' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6513201-715

(1) Medium Base 75w max.

T24 EN★

6513201EN3-715

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT MINI-PENDANT

D: 6.25" H: 7"
8' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6113201-715

(1) Medium Base 75w max.

T24 EN★

6113201EN3-715

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

ONE LIGHT WALL / BATH

W: 6.25" H: 10.75" E: 7.25"
Height from center of outlet box
up: 8.25" down: 2.5"

T24

4113201-715

(1) Medium Base 100w max.

T24 EN★

4113201EN3-715

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

METCALF WALL / BATH COLLECTION

Autumn Bronze

See more Metcalf
Wall / Bath on p.417

Recommended Products



GEARY PENDANT
Heirloom Bronze
p.346



NASH CEILING
FLUSH MOUNT
Heirloom Bronze
p.364

SEVILLE

PRODUCT SHOWN: SEVILLE NINE LIGHT
CHANDELIER IN BURNT SIENNA FINISH



DAMP

NINE LIGHT CHANDELIER

D: 28.875" H: 27.125"
10' wire pre-laced through 6' chain

T24

3120209-962

(9) Medium Base 75w max.

T24

EN★

3120209EN3-962

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel Finish on p.262



BRUSHED NICKEL FINISH
ETCHED GLASS, WHITE INSIDE

DAMP

NINE LIGHT CHANDELIER

D: 28.875" H: 27.125"
10' wire pre-laced through 6' chain

T24

3120209-710

(9) Medium Base 75w max.

T24

EN★

3120209EN3-710

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Burnt Sienna Finish on p.264



BURNT SIENNA FINISH
ETCHED GLASS, WHITE INSIDE

SEVILLE

DAMP

FIVE LIGHT SHADE CHANDELIER

D: 21.5" H: 22.125"
6' of Wire Pre-laced through 3.5' of Chain

T24

3320205-962

(5) Candelabra Base 60w max.

T24 EN★

3320205EN-962

(5) LED Cand. Base 2700k,
3.5w, 350 lumen lamps incl.



DAMP

FIVE LIGHT CHANDELIER

D: 21" H: 17.5"
6' wire pre-laced through 3' chain

T24

3120205-962

(5) Medium Base 75w max.

T24 EN★

3120205EN3-962

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

FIVE LIGHT CHANDELIER

D: 21" H: 17.25"
6' wire pre-laced through 3' chain

T24

3220205-962

(5) Medium Base 75w max.

T24 EN★

3220205EN3-962

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 17" H: 15.74"

6' wire pre-laced through 3' chain

T24

3120203-962

(3) Medium Base 75w max.

T24 EN★

3120203EN3-962(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

DAMP

ONE LIGHT MINI-PENDANT

D: 4" H: 7"

Supplied with 10' of Wire,
(1) 6" stem, (3) 12" stems
and sloped ceiling mounting hardware

T24

6120201-962

(1) Medium Base 100w max.

T24 EN★

6120201EN3-962(1) LED Medium Base
9.5w Bulb Lamps incl.

DAMP +

ONE LIGHT WALL / BATHW: 4.75" H: 8.5" E: 6.625"
Height from center of outlet box
up: 3.375" down: 5.125"

T24

4120201-962

(1) Medium Base 75w max.

T24 EN★

4120201EN3-962(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

DAMP +

SEVILLE WALL / BATH COLLECTIONBrushed Nickel
ChromeSee more Seville
Wall / Bath on p.432Recommended
ProductsGEARY PENDANT
Brushed Nickel
p.346GEARY CEILING
FLUSH MOUNT
Brushed Nickel
p.366

SEVILLE

DAMP

FIVE LIGHT SHADE CHANDELIER

D: 21.5" H: 22.125"
6' of Wire Pre-laced through 3.5' of Chain

T24

3320205-710

(5) Candelabra Base 60w max.

T24 EN★

3320205EN-710

(5) LED Cand. Base 2700k,
3.5w, 350 lumen lamps incl.



DAMP

FIVE LIGHT CHANDELIER

D: 21" H: 17.5"
6' wire pre-laced through 3' chain

T24

3120205-710

(5) Medium Base 75w max.

T24 EN★

3120205EN3-710

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

FIVE LIGHT CHANDELIER

D: 21" H: 17.25"
6' wire pre-laced through 3' chain

T24


3220205-710

(5) Medium Base 75w max.

T24 EN★

3220205EN3-710

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 17" H: 15.74"
6' wire pre-laced through 3' chain

T24

3120203-710
(3) Medium Base 75w max.

T24 EN★

3120203EN3-710
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

ONE LIGHT MINI-PENDANT

D: 4" H: 7"
Supplied with 10' of Wire,
(1) 6" stem, (3) 12" stems
and sloped ceiling mounting hardware

T24

6120201-710
(1) Medium Base 100w max.

T24 EN★

6120201EN3-710
(1) LED Medium Base
9.5w Bulb Lamps incl.



Recommended Products



GEARY PENDANT
Burnt Sienna
p.346



GEARY CEILING
FLUSH MOUNT
Burnt Sienna
p.366



DAMP +

ONE LIGHT WALL / BATH

W: 4.75" H: 8.5" E: 6.625"
Height from center of outlet box
up: 3.375" down: 5.125"

T24

4120201-710
(1) Medium Base 75w max.

T24 EN★

4120201EN3-710
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

SEVILLE WALL / BATH COLLECTION

Burnt Sienna

See more Seville
Wall / Bath on p.432

WINDGATE

FIVE LIGHT UPLIGHT CHANDELIER

D: 20.5" H: 16.75"
6' wire pre-laced through 3' chain

T24

35940-962

(5) Medium Base 100w max.

T24 EN★

35940EN3-962

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel Finish on p.268



BRUSHED NICKEL FINISH
ALABASTER GLASS

**FIVE LIGHT
UPLIGHT CHANDELIER**

D: 20.5" H: 16.75"
6' wire pre-laced through 3' chain

T24

35940-782

(5) Medium Base 100w max.

T24 EN★

35940EN3-782

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Heirloom Bronze Finish on p.270



HEIRLOOM BRONZE FINISH
ALABASTER GLASS

WINDGATE

FIVE LIGHT DOWNLIGHT CHANDELIER

D: 20" H: 14"
6' wire pre-laced through 3' chain

T24

35950-962

(5) Medium Base 100w max.

T24 EN★

35950EN3-962

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT DOWNLIGHT CHANDELIER

D: 20" H: 14"
6' wire pre-laced through 3' chain

T24

35949-962

(3) Medium Base 100w max.

T24 EN★

35949EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT UPLIGHT CHANDELIER

D: 20.5" H: 16.75"
6' wire pre-laced through 3' chain

T24

35939-962

(3) Medium Base 100w max.

T24 EN★

35939EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



TWO LIGHT PENDANT

D: 15.75" H: 20.75"
8' wire pre-laced through 4' chain

T24

65941-962

(2) Medium Base 100w max.

T24 EN★

65941EN3-962

(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





+
**TWO LIGHT
SEMI-FLUSH
CONVERTIBLE PENDANT**

D: 13" H: 11" Semi-Flush H: 9.5"
8' wire pre-laced through 3' chain

T24

77950-962
(2) Medium Base 100w max.

T24 EN★

77950EN3-962
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



**LARGE
ONE LIGHT PENDANT**

D: 15.75" H: 9.5"
8' wire pre-laced through 4' chain

T24

65942-962
(1) Medium Base 150w max.

T24 EN★

65942EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



ONE LIGHT PENDANT

D: 13.25" H: 9"
6' wire pre-laced through 3' chain

T24

65940-962
(1) Medium Base 150w max.

T24 EN★

65940EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



**ONE LIGHT
MINI-PENDANT**

D: 7.5" H: 6.5"
8' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

61940-962
(1) Medium Base 100w max.

T24 EN★

61940EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**ONE LIGHT
WALL / BATH**

W: 5.5" H: 9" E: 8"
Height from center of outlet box
up: 4" down: 5"

T24

41939-962
(1) Medium Base 60w max.

T24 EN★

41939EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**WINDGATE
WALL / BATH
COLLECTION**

Brushed Nickel

See more Windgate
Wall / Bath on p.441



DAMP

**WINDGATE CEILING
FLUSH MOUNTS**

Brushed Nickel

See Windgate
Flush Mounts on p.365

Recommended
Product



GEARY PENDANT
Brushed Nickel
p.346

WINDGATE

FIVE LIGHT DOWNLIGHT CHANDELIER

D: 20" H: 14"
6' wire pre-laced through 3' chain

T24

35950-782

(5) Medium Base 100w max.

T24 EN★

35950EN3-782

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT DOWNLIGHT CHANDELIER

D: 20" H: 14"
6' wire pre-laced through 3' chain

T24

35949-782

(3) Medium Base 100w max.

T24 EN★

35949EN3-782

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT UPLIGHT CHANDELIER

D: 20.5" H: 16.75"
6' wire pre-laced through 3' chain

T24

35939-782

(3) Medium Base 100w max.

T24 EN★

35939EN3-782

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



TWO LIGHT PENDANT

D: 15.75" H: 20.75"
8' wire pre-laced through 4' chain

T24

65941-782

(2) Medium Base 100w max.

T24 EN★

65941EN3-782

(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





+
**TWO LIGHT
 SEMI-FLUSH
 CONVERTIBLE PENDANT**
 D: 13" H: 11" Semi-Flush H: 9.5"
 8' wire pre-laced through 3' chain

T24
77950-782
 (2) Medium Base 100w max.

T24 EN★
77950EN3-782
 (2) Med. Base LED 3000K,
 9.5w, 800 lumen lamps incl.



**LARGE
 ONE LIGHT PENDANT**
 D: 15.75" H: 9.5"
 8' wire pre-laced through 4' chain

T24
65942-782
 (1) Medium Base 150w max.

T24 EN★
65942EN3-782
 (1) Med. Base LED 3000K,
 9.5w, 800 lumen lamp incl.



ONE LIGHT PENDANT
 D: 13.25" H: 9"
 6' wire pre-laced through 3' chain

T24
65940-782
 (1) Medium Base 150w max.

T24 EN★
65940EN3-782
 (1) Med. Base LED 3000K,
 9.5w, 800 lumen lamp incl.



**ONE LIGHT
 MINI-PENDANT**
 D: 7.5" H: 6.5"
 8' wire, (3) 12" stems, (1) 6" stem
 and sloped ceiling mounting hardware

T24
61940-782
 (1) Medium Base 100w max.

T24 EN★
61940EN3-782
 (1) Med. Base LED 3000K,
 9.5w, 800 lumen lamp incl.



DAMP +
**ONE LIGHT
 WALL / BATH**
 W: 5.5" H: 9" E: 8"
 Height from center of outlet box
 up: 4" down: 5"

T24
41939-782
 (1) Medium Base 60w max.

T24 EN★
41939EN3-782
 (1) Med. Base LED 3000K,
 9.5w, 800 lumen lamp incl.



DAMP +
**WINDGATE
 WALL / BATH
 COLLECTION**
 Heirloom Bronze
 See more Windgate
 Wall / Bath on p.441



DAMP
**WINDGATE CEILING
 FLUSH MOUNTS**
 Heirloom Bronze
 See Windgate
 Flush Mounts on p.365

Recommended
 Product



GEARY PENDANT
 Heirloom Bronze
 p.346

BANNOCK

DAMP

NINE LIGHT CHANDELIER

D: 28" H: 26"

10' wire pre-laced through 6' chain

T24

3116609-962

(9) Medium Base 75w max.

T24 EN★

3116609EN3-962

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel Finish on p.274



BRUSHED NICKEL FINISH
SATIN ETCHED GLASS

DAMP

NINE LIGHT CHANDELIER

D: 28" H: 26"

10' wire pre-laced through 6' chain

T24

3116609-782

(9) Medium Base 75w max.

T24 EN*

3116609EN3-782

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Heirloom Bronze Finish on p.276



HEIRLOOM BRONZE FINISH
SATIN ETCHED GLASS

BANNOCK

DAMP

FIVE LIGHT CHANDELIER

D: 22" H: 15.75"

10' wire pre-laced through 6' chain

T24

3116605-962

(5) Medium Base 75w max.

T24 EN★

3116605EN3-962

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 19.75" H: 14.75"

6' wire pre-laced through 3' chain

T24

3116603-962

(3) Medium Base 75w max

T24 EN★

3116603EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP +

**TWO LIGHT
SEMI-FLUSH
CONVERTIBLE PENDANT**

D: 13.5" H: 11.25" Semi-Flush H: 10.5"
6' wire pre-laced through 3' chain

T24

7716602-962
(2) Medium Base 75w max.

T24 EN★

7716602EN3-962
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

**ONE LIGHT
MINI-PENDANT**

D: 4.75" H: 6"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6116601-962
(1) Medium Base 75w max.

T24 EN★

6116601EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**ONE LIGHT
WALL / BATH**

W: 5" H: 8.75" E: 7.25"
Height from center of outlet box
up: 6.25" down: 2.5"

T24

4116601-962
(1) Medium Base 75w max.

T24 EN★

4116601EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**BANNOCK
WALL / BATH
COLLECTION**

Brushed Nickel

See more Bannock
Wall / Bath on p.419

Recommended
Products



GEARY PENDANT
Brushed Nickel
p.346



GEARY CEILING
FLUSH MOUNT
Brushed Nickel
p.366

BANNOCK

DAMP

FIVE LIGHT CHANDELIER

D: 22" H: 15.75"

10' wire pre-laced through 6' chain

T24

3116605-782

(5) Medium Base 75w max.

T24

EN★

3116605EN3-782

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT CHANDELIER

D: 19.75" H: 14.75"

6' wire pre-laced through 3' chain

T24

3116603-782

(3) Medium Base 75w max

T24

EN★

3116603EN3-782

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





DAMP +

**TWO LIGHT
SEMI-FLUSH
CONVERTIBLE PENDANT**

D: 13.5" H: 11.25" Semi-Flush H: 10.5"
6' wire pre-laced through 3' chain

T24

7716602-782
(2) Medium Base 75w max.

T24 EN★

7716602EN3-782
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

**ONE LIGHT
MINI-PENDANT**

D: 4.75" H: 6"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6116601-782
(1) Medium Base 75w max.

T24 EN★

6116601EN3-782
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**ONE LIGHT
WALL / BATH**

W: 5" H: 8.75" E: 7.25"
Height from center of outlet box
up: 6.25" down: 2.5"

T24

4116601-782
(1) Medium Base 75w max.

T24 EN★

4116601EN3-782
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**BANNOCK
WALL / BATH
COLLECTION**

Heirloom Bronze

See more Bannock
Wall / Bath on p.419

Recommended
Products



GEARY PENDANT
Heirloom Bronze
p.346



GEARY CEILING
FLUSH MOUNT
Heirloom Bronze
p.366

HOLMAN

NINE LIGHT CHANDELIER

D: 29.75" H: 25.75"

6' wire pre-laced through 3' chain

T24

31810-962

(9) Medium Base 60w max.

T24 EN★

31810EN3-962

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel Finish on p.280



BRUSHED NICKEL FINISH
SATIN ETCHED GLASS

NINE LIGHT CHANDELIER

D: 29.75" H: 25.75"

6' wire pre-laced through 3' chain

T24

31810-782

(9) Medium Base 60w max.

T24 EN★

31810EN3-782(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Heirloom Bronze Finish on p.282

HEIRLOOM BRONZE FINISH
SATIN ETCHED GLASS

NINE LIGHT CHANDELIER

D: 27.75" H: 25.75"
6' wire pre-laced through 3' chain

T24

32810-962

(9) Candelabra Base 60w max.

T24 EN★

32810EN-962

(9) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



SIX LIGHT HALL / FOYER

D: 18" H: 40"
12' wire pre-laced through 10' chain

T24

51807-962

(6) Candelabra Base 60w max.

T24 EN★

51807EN-962

(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



+

FIVE LIGHT CHANDELIER

D: 20" H: 12.5" Downlight H: 14.75"
10' wire pre-laced through 3' chain

T24


31808-962

(5) Medium Base 60w max.

T24 EN★

31808EN3-962

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



FIVE LIGHT CHANDELIER

D: 18" H: 16"
10' wire pre-laced through 3' chain

T24


31809-962

(5) Candelabra Base 60w max.

T24 EN★

31809EN-962

(5) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



+

THREE LIGHT CHANDELIER

D: 18" H: 10.25" Downlight H: 13.75"
10' wire pre-laced through 3' chain

T24


31806-962

(3) Medium Base 60w max.

T24 EN★

31806EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



**THREE LIGHT
HALL / FOYER**

D: 16.25" H: 25"
12' wire pre-laced through 10' chain

T24

51806-962
(3) Candelabra Base 60w max.

T24 EN★

51806EN-962
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

**THREE LIGHT CHANDELIER**

D: 16" H: 14.75"
10' wire pre-laced through 3' chain

T24

31807-962
(3) Candelabra Base 60w max.

T24 EN★

31807EN-962
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

**THREE LIGHT PENDANT**

D: 18" H: 18"
6' wire pre-laced through 3' chain

T24

66808-962
(3) Medium Base 60w max.

T24 EN★

66808EN3-962
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

**+
TWO LIGHT
SEMI-FLUSH
CONVERTIBLE PENDANT**

D: 13.25" H: 13.75" Semi-Flush H: 12"
10' wire pre-laced through 3' chain

T24

77806-962
(2) Medium Base 75w max.

T24 EN★

77806EN3-962
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

**ONE LIGHT PENDANT**

D: 15" H: 12.25"
10' wire pre-laced through 3' chain

T24

65806-962
(1) Medium Base 100w max.

T24 EN★

65806EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

**ONE LIGHT
MINI-PENDANT**

D: 5.25" H: 6.5"
10' wire, (3) 12" stems, 12" chain

T24

61806-962
(1) Medium Base 60w max.

T24 EN★

61806EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**ONE LIGHT
WALL / BATH**

W: 5.25" H: 10.25" E: 7.25"
Height from center of outlet box
up: 6.5" down: 3.75"

T24

41806-962
(1) Medium Base 60w max.

T24 EN★

41806EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



DAMP +

**HOLMAN
WALL / BATH
COLLECTION**

Brushed Nickel

See more Holman
Wall / Bath on p.422

Recommended
Products

GEARY PENDANT
Brushed Nickel
p.346



GEARY CEILING
FLUSH MOUNT
Brushed Nickel
p.366

NINE LIGHT CHANDELIER

D: 27.75" H: 25.75"
6' wire pre-laced through 3' chain

T24

32810-782

(9) Candelabra Base 60w max.

T24 EN★

32810EN-782

(9) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



SIX LIGHT HALL / FOYER

D: 18" H: 40"
12' wire pre-laced through 10' chain

T24

51807-782

(6) Candelabra Base 60w max.

T24 EN★

51807EN-782

(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



+

FIVE LIGHT CHANDELIER

D: 20" H: 12.5" Downlight H: 14.75"
10' wire pre-laced through 3' chain

T24


31808-782

(5) Medium Base 60w max.

T24 EN★

31808EN3-782

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



FIVE LIGHT CHANDELIER

D: 18" H: 16"
10' wire pre-laced through 3' chain

T24


31809-782

(5) Candelabra Base 60w max.

T24 EN★

31809EN-782

(5) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



+

THREE LIGHT CHANDELIER

D: 18" H: 10.25" Downlight H: 13.75"
10' wire pre-laced through 3' chain

T24


31806-782

(3) Medium Base 60w max.

T24 EN★

31806EN3-782

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



**THREE LIGHT HALL / FOYER**

D: 16.25" H: 25"
12' wire pre-laced through 10' chain

T24

51806-782

(3) Candelabra Base 60w max.

T24 EN★

51806EN-782

(3) Cand. Base LED 2700K, 3.5w, 350 lumen lamps incl.

**THREE LIGHT CHANDELIER**

D: 16" H: 14.75"
10' wire pre-laced through 3' chain

T24

31807-782

(3) Candelabra Base 60w max.

T24 EN★

31807EN-782

(3) Cand. Base LED 2700K, 3.5w, 350 lumen lamps incl.

**THREE LIGHT PENDANT**

D: 18" H: 18"
6' wire pre-laced through 3' chain

T24

66808-782

(3) Medium Base 60w max.

T24 EN★

66808EN3-782

(3) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



+

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 13.25" H: 13.75" Semi-Flush H: 12"
10' wire pre-laced through 3' chain

T24

77806-782

(2) Medium Base 75w max.

T24 EN★

77806EN3-782

(2) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.

**ONE LIGHT PENDANT**

D: 15" H: 12.25"
10' wire pre-laced through 3' chain

T24

65806-782

(1) Medium Base 100w max.

T24 EN★

65806EN3-782

(1) Med. Base LED 3000K, 9.5w, 800 lumen lamp incl.

**ONE LIGHT MINI-PENDANT**

D: 5.25" H: 6.5"
10' wire, (3) 12" stems, 12" chain

T24

61806-782

(1) Medium Base 60w max.

T24 EN★

61806EN3-782

(1) Med. Base LED 3000K, 9.5w, 800 lumen lamp incl.



DAMP +

ONE LIGHT WALL / BATH

W: 5.25" H: 10.25" E: 7.25"
Height from center of outlet box up: 6.5" down: 3.75"

T24

41806-782

(1) Medium Base 60w max.

T24 EN★

41806EN3-782

(1) Med. Base LED 3000K, 9.5w, 800 lumen lamp incl.



DAMP +

HOLMAN WALL / BATH COLLECTION

Heirloom Bronze

See more Holman Wall / Bath on p.422

Recommended Products



GEARY PENDANT
Heirloom Bronze
p.346



GEARY CEILING FLUSH MOUNTS
Heirloom Bronze
p.366

WHEATON

NINE LIGHT CHANDELIER

D: 31" H: 30.25"

12' wire pre-laced through 10' chain

T24

31627-962

(9) Medium Base 100w max.

T24 EN★

31627EN3-962

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel Finish on p.286



BRUSHED NICKEL FINISH
SATIN ETCHED GLASS

NINE LIGHT CHANDELIER

D: 31" H: 30.25"
12' wire pre-laced through 10' chain

T24

31627-782

(9) Medium Base 100w max.

T24 EN★

31627EN3-782

(9) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Heirloom Bronze Finish on p.288



HEIRLOOM BRONZE FINISH
SATIN ETCHED GLASS

WHEATON

FIVE LIGHT CHANDELIER

D: 24" H: 18"

12' wire pre-laced through 10' chain

T24

31626-962

(5) Medium Base 100w max.

T24 EN★

31626EN3-962

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT CHANDELIER

D: 22" H: 18"

12' wire pre-laced through 10' chain

T24

31625-962

(3) Medium Base 100w max.

T24 EN★

31625EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT PENDANT

D: 16.75" H: 21.5"

12' wire pre-laced through 10' chain

T24

65626-962

(3) Medium Base 100w max.

T24 EN★

65626EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





**TWO LIGHT
SEMI-FLUSH
CONVERTIBLE PENDANT**

D: 12.5" H: 15.75" Semi-Flush H: 12.25"
12' wire pre-laced through 10' chain



77625-962
(2) Medium Base 100w max.



77625EN3-962
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



ONE LIGHT PENDANT

D: 15.25" H: 12.5"
12' wire pre-laced through 10'
chain



65625-962
(1) Medium Base 150w max.



65625EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



ONE LIGHT MINI-PENDANT

D: 7" H: 11.75"
10' wire, (3) 12" stems, 12" chain



61625-962
(1) Medium Base 100w max.



61625EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



ONE LIGHT WALL / BATH

W: 6.5" H: 7.75" E: 8.25"
Height from center of outlet box
up: 3.75" down: 4"



44625-962
(1) Medium Base 100w max.



44625EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



**WHEATON
WALL / BATH
COLLECTION**

Brushed Nickel

See more Wheaton
Wall / Bath on p.440

**Recommended
Products**



GEARY PENDANT
Brushed Nickel
p.346



GEARY CEILING
FLUSH MOUNT
Brushed Nickel
p.366

WHEATON

FIVE LIGHT CHANDELIER

D: 24" H: 18"

12' wire pre-laced through 10' chain

T24

31626-782

(5) Medium Base 100w max.

T24 EN★

31626EN3-782

(5) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT CHANDELIER

D: 22" H: 18"

12' wire pre-laced through 10' chain

T24

31625-782

(3) Medium Base 100w max.

T24 EN★

31625EN3-782

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



THREE LIGHT PENDANT

D: 16.75" H: 21.5"

12' wire pre-laced through 10' chain

T24

65626-782

(3) Medium Base 100w max.

T24 EN★

65626EN3-782

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.





TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 12.5" H: 15.75" Semi-Flush H: 12.25"
12' wire pre-laced through 10' chain



77625-782
(2) Medium Base 100w max.



77625EN3-782
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



ONE LIGHT PENDANT

D: 15.25" H: 12.5"
12' wire pre-laced through 10'
chain



65625-782
(1) Medium Base 150w max.



65625EN3-782
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



ONE LIGHT MINI-PENDANT

D: 7" H: 11.75"
10' wire, (3) 12" stems, 12" chain



61625-782
(1) Medium Base 100w max.



61625EN3-782
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



ONE LIGHT WALL / BATH

W: 6.5" H: 7.75" E: 8.25"
Height from center of outlet box
up: 3.75" down: 4"



44625-782
(1) Medium Base 100w max.



44625EN3-782
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



WHEATON WALL / BATH COLLECTION

Heirloom Bronze

See more Wheaton
Wall / Bath on p.440

Recommended
Products



GEARY PENDANT
Heirloom Bronze
p.346



GEARY CEILING
FLUSH MOUNT
Heirloom Bronze
p.366

STIRLING

NINE LIGHT CHANDELIER

D: 30" H: 32.5"

12' wire pre-laced through 10' chain

T24

31952-962

(9) Candelabra Base 60w max.

T24 EN★

31952EN-962

(9) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

See more Brushed Nickel Finish on p.292



BRUSHED NICKEL FINISH
WHITE LINEN SHADES

NINE LIGHT CHANDELIER

D: 30" H: 32.5"

12' wire pre-laced through 10' chain

T24

31952-710

(9) Candelabra Base 60w max.

T24 EN★

31952EN-710(9) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

See more Burnt Sienna Finish on p.294

BURNT SIENNA FINISH
BEIGE LINEN SHADES

STIRLING

SIX LIGHT ISLAND PENDANT

L: 35" W: 17.5" H: 13.25"
10' wire, (2) 12" stems, (1) 6" stem

T24

66953-962

(6) Candelabra Base 60w max.

T24 EN★

66953EN-962

(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



FIVE LIGHT CHANDELIER

L: 35" W: 17.5" H: 13.25"
10' wire, (2) 12" stems, (1) 6" stem

T24

31942-962

(5) Candelabra Base 60w max.

T24 EN★

31942EN-962

(5) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



FOUR LIGHT ISLAND PENDANT

L: 37" W: 6.5" H: 12.75"
10' wire, (2) 12" stems, (1) 6" stem

T24

66952-962

(4) Candelabra Base 60w max.

T24 EN★

66952EN3-962

(4) Cand. Base LED 2700K,
3.5w, 800 lumen lamps incl.



WITH SATIN ETCHED
GLASS DIFFUSER

THREE LIGHT PENDANT

D: 19" H: 26.25"
12' wire pre-laced through 10" chain

T24

65953-962

(3) Medium Base 100w max.

T24 EN★

65953EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



WITH SATIN ETCHED
GLASS DIFFUSER

+

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 14" H: 14.75" Semi-flush H: 12.75"
12' wire pre-laced through 10" chain

T24

77952-962

(2) Medium Base 60w max.

T24 EN★

77952EN3-962

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

WITH SATIN ETCHED
GLASS DIFFUSER**TWO LIGHT
CEILING FLUSH MOUNT**

D: 14" H: 7.25"

T24

75952-962
(2) Medium Base 100w max.

T24 EN★

75952EN3-962
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.WITH SATIN ETCHED
GLASS DIFFUSER**ONE LIGHT PENDANT**D: 16" H: 10.25" H: 13.25"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

65952-962
(1) Medium Base 100w max.

T24 EN★

65952EN3-962
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.**ONE LIGHT
MINI-PENDANT**D: 6.5" H: 8.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

61952-962
(1) Medium Base 100w max.

T24 EN★

61952EN3-962
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.**ONE LIGHT
WALL SCONCE**W: 5.5" H: 14.5" E: 7.25"
Height from center of outlet box
up: 9.5"

T24

41260-962
(2) Medium Base 100w max.

T24 EN★

41260EN-962
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

CASED OPAL ETCHED GLASS

DAMP +

**ONE LIGHT
WALL / BATH**W: 5.5" H: 11.25" E: 6.75"
Height from center of outlet box
up: 6.25" down: 5"

T24

44952-962
(1) Medium Base 100w max.

T24 EN★

44952EN3-962
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

**STIRLING
WALL / BATH
COLLECTION**Brushed Nickel
ChromeSee more Stirling
Wall / Bath on p.399Recommended
ProductGEARY PENDANT
Brushed Nickel
p.346

STIRLING

SIX LIGHT ISLAND PENDANT

L: 35" W: 17.5" H: 13.25"
10' wire, (2) 12" stems, (1) 6" stem

T24

66953-710

(6) Candelabra Base 60w max.

T24 EN★

66953EN-710

(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



FIVE LIGHT CHANDELIER

L: 35" W: 17.5" H: 13.25"
10' wire, (2) 12" stems, (1) 6" stem

T24

31942-710

(5) Candelabra Base 60w max.

T24 EN★

31942EN-710

(5) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



FOUR LIGHT ISLAND PENDANT

L: 37" W: 6.5" H: 12.75"
10' wire, (2) 12" stems, (1) 6" stem

T24

66952-710

(4) Candelabra Base 60w max.

T24 EN★

66952EN3-710

(4) Cand. Base LED 2700K,
3.5w, 800 lumen lamps incl.



WITH SATIN ETCHED
GLASS DIFFUSER

THREE LIGHT PENDANT

D: 19" H: 26.25"
12' wire pre-laced through 10" chain

T24

65953-710

(3) Medium Base 100w max.

T24 EN★

65953EN3-710

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



WITH SATIN ETCHED
GLASS DIFFUSER

+

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 14" H: 14.75" Semi-flush H: 12.75"
12' wire pre-laced through 10" chain

T24

77952-710

(2) Medium Base 60w max.

T24 EN★

77952EN3-710

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



WITH SATIN ETCHED GLASS DIFFUSER

TWO LIGHT CEILING FLUSH MOUNT

D: 14" H: 7.25"

T24

75952-710

(2) Medium Base 100w max.

T24 EN★

75952EN3-710

(2) Med. Base LED 3000k, 9.5w, 800 lumen lamps incl.



WITH SATIN ETCHED GLASS DIFFUSER

ONE LIGHT PENDANT

D: 16" H: 10.25" H: 13.25"
10' wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

65952-710

(1) Medium Base 100w max.

T24 EN★

65952EN3-710

(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



ONE LIGHT MINI-PENDANT

D: 6.5" H: 8.5"
10' wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

61952-710

(1) Medium Base 100w max.

T24 EN★

61952EN3-710

(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



ONE LIGHT WALL SCONCE

W: 5.5" H: 14.5" E: 7.25"
Height from center of outlet box up: 9.5"

T24

41260-710

(2) Medium Base 100w max.

T24 EN★

41260EN-710

(2) Med. Base LED 3000k, 9.5w, 800 lumen lamps incl.



CASED OPAL ETCHED GLASS

DAMP +

ONE LIGHT WALL / BATH

W: 5.5" H: 11.25" E: 6.75"
Height from center of outlet box up: 6.25" down: 5"

T24

44952-710

(1) Medium Base 100w max.

T24 EN★

44952EN3-710

(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



DAMP +

STIRLING WALL / BATH COLLECTION

Burnt Sienna

See more Stirling Wall / Bath on p.399

Recommended Product



GEARY PENDANT
Burnt Sienna
p.346

DRAWING ROOM

SIX LIGHT SINGLE TIER CHANDELIER

D: 28" H: 30.5"
Supplied with 15' of wire
and 5' of chain

T24

F2224/6WAL

(6) Medium Base 100w max.



WALNUT FINISH
AMBER SNOW SCAVO GLASS

FIVE LIGHT KITCHEN CHANDELIER

D: 25" H: 21.25"
 Supplied with 15' of wire
 and 5' of chain

T24

F2397/5WAL
 (5) Medium Base 100w max.



+

FOUR LIGHT MINI CHANDELIER

D: 18" H: 20" Flush H: 18.75"
 Supplied with 15' of wire
 and 5' of chain

T24

F2221/4WAL
 (4) Medium Base 100w max.



THREE LIGHT ISLAND CHANDELIER

L: 38" W: 9" H: 24"
 Supplied with 15' of wire
 and (2) 5' of chains

T24

F2218/3WAL
 (3) Medium Base 100w max.




THREE LIGHT KITCHEN CHANDELIER

D: 25" H: 19.5"
 Supplied with 15' of wire
 and 5' of chain

T24

F2219/3WAL
 (3) Medium Base 100w max.



DRAWING ROOM

FOUR LIGHT UPLIGHT CHANDELIER

D: 27" H: 31.5"
Supplied with 15' of wire
and 5' of chain

T24

F2222/4WAL

(4) Medium Base 100w max.



+

TWO LIGHT UPLIGHT CHANDELIER

D: 17" H: 21.25" Flush H: 20"
Supplied with 15' of wire
and 5' of chain

T24

F2223/2WAL

(2) Medium Base 100w Max.



THREE LIGHT INDOOR SEMI-FLUSH MOUNT

D: 15.5" H: 14.5"

T24

SF220WAL

(3) Medium Base 100w Max.



DAMP

THREE LIGHT INDOOR FLUSH MOUNT

D: 14" H: 9"

T24

FM261WAL

(3) Medium Base 60w Max.



TWO LIGHT INDOOR SEMI-FLUSH

D: 17.25" H: 13.5"

T24

SF239WAL

2 Medium Base 100w Max.



**TWO LIGHT
INDOOR SEMI-FLUSH**
D: 14.5" H: 11.5"

T24
SF238WAL
(2) Medium Base 100w Max.



**ONE LIGHT
MINI-PENDANT**
D: 9" H: 7"
Supplied with 15' of wire,
(3) 12" stems, (1) 6" stem

T24
P1114WAL
(1) Medium Base 100w Max.



**TWO LIGHT
INDOOR FLUSH MOUNT**
D: 13" H: 6"

T24
FM269WAL
(2) Medium Base 60w Max.



DAMP ADA
ONE LIGHT SCONCE
W: 9" H: 12.25" E: 4"
Height from center of outlet box
up: 3.875"

T24
WB1288WAL
(1) Medium Base 100w Max.



DAMP ADA
ONE LIGHT SCONCE
W: 6.25" H: 8" E: 4"
Height from center of outlet box
up: 2.125"
Requires a 2" X 4" outlet box
for installation

T24
WB1330WAL
(1) Candelabra Base 60w Max.



DAMP +
**ONE LIGHT
WALL / BATH**
W: 6.25" H: 9.75" E: 7"
Height from center of outle box
up: 4.75" down: 5"

T24
VS11201-WAL
(1) Medium Base 100w Max.



DAMP +
**DRAWING ROOM
WALL / BATH COLLECTION**
Walnut

See more Drawing Room
Vanity on p.442

TRADITIONAL

TEN LIGHT CHANDELIER

D: 23.5" H: 21.75"

12' wire pre-laced through 3' chain

T24

3413-962

(10) Candelabra Base 60w max.

T24 EN★

3413EN-962

(10) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



FIVE LIGHT CHANDELIER

D: 23.5" H: 18.25"
12' wire pre-laced through 3' chain

T24

3410-962

(5) Candelabra Base 60w max.

T24 EN★

3410EN-962

(5) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



PRODUCT SHOWN: BRONZVILLE THREE
LIGHT PENDANT IN SATIN BRONZE FINISH



PENDANT

collections

DAVI

DAMP

SIX LIGHT PENDANT

D: 24.875" H: 20.375"
Supplied with 10' of wire,
(3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6580506-05

(6) Candelabra Base 60w max.

T24

EN★

6580506EN-05

(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



CHROME FINISH

DAMP

SIX LIGHT PENDANT

D: 24.875" H: 20.375"

Supplied with 10' of wire,
(3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6580506-848

(6) Candelabra Base 60w max.

T24 EN★

6580506EN-848(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.

SATIN BRONZE FINISH

BRONZEVILLE

PRODUCT SHOWN: BRONZEVILLE THREE
LIGHT PENDANT IN SATIN BRONZE FINISH



DAMP

THREE LIGHT PENDANT

D: 21.75" H: 22.5"
 Supplied with 10' of wire,
 (1) 6" stem, (3) 12" stems
 and sloped ceiling mounting hardware

T24

6514303-962
 (3) Medium Base 60w max.



BRUSHED NICKEL FINISH
 CLEAR SEEDED GLASS

DAMP

ONE LIGHT PENDANT

D: 14.25" H: 17.625"
 Supplied with 10' of wire,
 (1) 6" stem, (3) 12" stems
 and sloped ceiling mounting hardware

T24

6514301-962
 (1) Medium Base 60w max.



BRUSHED NICKEL FINISH
 CLEAR SEEDED GLASS

DAMP

THREE LIGHT PENDANT

D: 21.75" H: 22.5"
 Supplied with 10' of wire,
 (1) 6" stem, (3) 12" stems
 and sloped ceiling mounting hardware

T24

6514303-848
 (3) Medium Base 60w max.



SATIN BRONZE FINISH
 CLEAR SEEDED GLASS

DAMP

ONE LIGHT PENDANT

D: 14.25" H: 17.625"
 Supplied with 10' of wire,
 (1) 6" stem, (3) 12" stems
 and sloped ceiling mounting hardware

T24

6514301-848
 (1) Medium Base 60w max.



SATIN BRONZE FINISH
 CLEAR SEEDED GLASS

LEO - HANGING GLOBE PENDANTS

EXTRA LARGE PENDANT

D: 14" H: 14.75"
4.5' black field adjustable cord

T24

6801801-04

(1) Medium Base 100w max.

See more Satin Aluminum Finish
with Clear Seeded Glass on p.310



SATIN ALUMINUM FINISH
CLEAR SEEDED GLASS

EXTRA LARGE PENDANT

D: 14" H: 14.75"
4.5' black field adjustable cord

T24

6801801-848

(1) Medium Base 100w max.

See more Satin Bronze Finish
with Clear Seeded Glass on p.311



SATIN BRONZE FINISH
CLEAR SEEDED GLASS

LEO - HANGING GLOBE PENDANTS

EXTRA LARGE PENDANT

D: 14" H: 14.75"
4.5' white field adjustable cord

T24

6024-15

(1) Medium Base 150w max.

T24 EN★

6024EN3-15

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

602493S-15

LED: 3000K, 14 watts,
1000 gross lumens

See more White Finish on p.312



WHITE FINISH
WHITE GLASS

EXTRA LARGE PENDANT

D: 14" H: 14.75"
4.5' black field adjustable cord

T24

6024-04

(1) Medium Base 150w max.

T24 EN★

6024EN3-04

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

602493S-04

LED: 3000K, 14 watts,
1000 gross lumens

See more Satin Aluminum Finish
with White Glass on p.312



SATIN ALUMINUM FINISH
WHITE GLASS

EXTRA LARGE PENDANT

D: 14" H: 14.75"
4.5' black field adjustable cord

T24

6024-848

(1) Medium Base 150w max.

T24 EN★

6024EN3-848

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

602493S-848

LED: 3000K, 14 watts,
1000 gross lumens

See more Satin Bronze Finish
with White Glass on p.312



SATIN BRONZE FINISH
WHITE GLASS

LEO - HANGING GLOBE PENDANTS

SATIN ALUMINUM FINISH [-04] / CLEAR SEEDED GLASS

LARGE PENDANT

D: 12" H: 12.5"
4.5' black field adjustable cord

T24

6701801-04

(1) Medium Base 100w max.



MEDIUM PENDANT

D: 10" H: 10.75"
4.5' white field adjustable cord

T24

6601801-04

(1) Medium Base 100w max.




SMALL PENDANT

D: 8" H: 8.5"
4.5' black field adjustable cord

T24

6501801-04

(1) Medium Base 60w max.



Recommended Products



LEO GLOBE CEILING
FLUSH MOUNT
Satin Aluminum
p.375



MULTI-PORT
CANOPIES
Brushed Nickel
p.358

LARGE PENDANT

D: 12" H: 12.5"
4.5' black field adjustable cord

T24

6701801-848

(1) Medium Base 100w max.



MEDIUM PENDANT

D: 10" H: 10.75"
4.5' white field adjustable cord

T24

6601801-848

(1) Medium Base 100w max.



SMALL PENDANT

D: 8" H: 8.5"
4.5' black field adjustable cord

T24

6501801-848

(1) Medium Base 60w max.



Recommended Products



LEO GLOBE CEILING
FLUSH MOUNT
Satin Bronze
p.375



MULTI-PORT
CANOPIES
Satin Bronze
p.358

LEO - HANGING GLOBE PENDANTS

LARGE PENDANT

D: 12" H: 12.5"
4.5' white field adjustable cord

T24

6022-15

(1) Medium Base 150w max.

T24 EN★

6022EN3-15

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

602293S-15

LED: 3000K, 14 watts,
1000 gross lumens



WHITE FINISH
WHITE GLASS

LARGE PENDANT

D: 12" H: 12.5"
4.5' black field adjustable cord

T24

6022-04

(1) Medium Base 150w max.

T24 EN★


6022EN3-04

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

602293S-04

LED: 3000K, 14 watts,
1000 gross lumens



SATIN ALUMINUM FINISH
WHITE GLASS

LARGE PENDANT

D: 12" H: 12.5"
4.5' white field adjustable cord

T24

6022-848

(1) Medium Base 150w max.

T24 EN★

6022EN3-848

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

602293S-848

LED: 3000K, 14 watts,
1000 gross lumens



SATIN BRONZE FINISH
WHITE GLASS

LEO - HANGING GLOBE PENDANTS

MEDIUM PENDANT

D: 10" H: 10.75"
4.5' white field adjustable cord

T24


6020-15
(1) Medium Base 150w max.

T24 EN★

6020EN3-15
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

602093S-15
LED: 3000K, 14 watts,
1000 gross lumens



WHITE FINISH
WHITE GLASS

MEDIUM PENDANT

D: 10" H: 10.75"
4.5' black field adjustable cord

T24


6020-04
(1) Medium Base 150w max.

T24 EN★

6020EN3-04
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

602093S-04
LED: 3000K, 14 watts,
1000 gross lumens



SATIN ALUMINUM FINISH
WHITE GLASS

MEDIUM PENDANT

D: 10" H: 10.75"
4.5' white field adjustable cord

T24


6020-848
(1) Medium Base 150w max.

T24 EN★

6020EN3-848
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

602093S-848
LED: 3000K, 14 watts,
1000 gross lumens



SATIN BRONZE FINISH
WHITE GLASS

SMALL PENDANT

D: 8" H: 8.5"
4.5' white field adjustable cord

T24


6018-15
(1) Medium Base 100w max.

T24 EN★

6018EN3-15
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

601893S-15
LED: 3000K, 9 watts,
700 gross lumens



WHITE FINISH
WHITE GLASS

SMALL PENDANT

D: 8" H: 8.5"
4.5' black field adjustable cord

T24


6018-04
(1) Medium Base 100w max.

T24 EN★

6018EN3-04
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

601893S-04
LED: 3000K, 9 watts,
700 gross lumens



SATIN ALUMINUM FINISH
WHITE GLASS

SMALL PENDANT

D: 8" H: 8.5"
4.5' white field adjustable cord

T24


6018-848
(1) Medium Base 100w max.

T24 EN★

6018EN3-848
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

601893S-848
LED: 3000K, 9 watts,
700 gross lumens



SATIN BRONZE FINISH
WHITE GLASS

Recommended Products



LEO GLOBE CEILING
FLUSH MOUNT
Satin Bronze,
White,
Satin Aluminum
p.375



MULTI-PORT
CANOPIES
Satin Bronze,
White,
Satin Aluminum
p.358

BAYLOR

DAMP

ONE LIGHT PENDANT

D: 12" H: 17.25"
Supplied with 15' of wire,
(3) 12" stems, (1) 6" stem

T24

P1461SN

(1) Medium Base 60w max.



SATIN NICKEL FINISH
CLEAR SEEDED GLASS

DAMP

ONE LIGHT PENDANT

D: 12" H: 17.25"
Supplied with 15' of wire,
(3) 12" stems, (1) 6" stem

T24

P1461ORB

(1) Medium Base 60w max.



OIL RUBBED BRONZE FINISH
CLEAR SEEDED GLASS

ARILDA

DAMP

ONE LIGHT PENDANT

D: 9" H: 19"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6537001-962

(1) Medium Base 60w max.



BRUSHED NICKEL FINISH
CLEAR GLASS

DAMP

ONE LIGHT PENDANT

D: 9" H: 19"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6537001-782

(1) Medium Base 60w max.



HEIRLOOM BRONZE FINISH
CLEAR GLASS

DAMP


ONE LIGHT PENDANT

D: 13" H: 16.875"
Supplied with 15' of wire,
(3) 12" stems, (1) 6" stem

T24

P1483CH

(1) Medium Base 60w max.



CHROME FINISH
CLEAR GLASS

DAMP

ONE LIGHT PENDANT

D: 13" H: 16.875"
Supplied with 15' of wire,
(3) 12" stems, (1) 6" stem

T24

P1483SN

(1) Medium Base 60w max.



SATIN NICKEL FINISH
CLEAR GLASS

DAMP

ONE LIGHT PENDANT

D: 13" H: 16.875"
Supplied with 15' of wire,
(3) 12" stems, (1) 6" stem

T24

P1483ORB

(1) Medium Base 60w max.



OIL RUBBED BRONZE FINISH
CLEAR GLASS

MARINO

DAMP

ONE LIGHT PENDANT

D: 9.25" H: 16.25"
Supplied with 15' of wire,
(1) 6" stem, (3) 12" stems

T24

P1484CH

(1) Medium Base 60w max.



CHROME FINISH
CLEAR GLASS

DAMP

ONE LIGHT PENDANT

D: 9.25" H: 16.25"
Supplied with 15' of wire,
(1) 6" stem, (3) 12" stems

T24

P1484SN

(1) Medium Base 60w max.



SATIN NICKEL FINISH
CLEAR GLASS

DAMP

ONE LIGHT PENDANT

D: 9.25" H: 16.25"
Supplied with 15' of wire,
(1) 6" stem, (3) 12" stems

T24

P1484ORB

(1) Medium Base 60w max.



OIL RUBBED BRONZE FINISH
CLEAR GLASS

DAMP

ONE LIGHT PENDANT

D: 7.125" H: 13 "
10' of wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6536901-962

(1) Medium Base 60w max.



BRUSHED NICKEL FINISH
CLEAR SEEDED GLASS

DAMP

ONE LIGHT PENDANT

D: 7.125" H: 13 "
10' of wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6536901-782

(1) Medium Base 60w max.



HEIRLOOM BRONZE FINISH
CLEAR SEEDED GLASS

DAMP

**ONE LIGHT
MINI-PENDANT**

D: 7" H: 13.5"
Supplied with 15' of wire

T24

P1441SN
(1) Medium Base 60w max.



SATIN NICKEL FINISH
CLEAR GLASS

DAMP

**ONE LIGHT
MINI-PENDANT**

D: 7" H: 13.5"
Supplied with 15' of wire

T24

P1441ORB
(1) Medium Base 60w max.



OIL RUBBED BRONZE FINISH
CLEAR GLASS

DAMP

**ONE LIGHT
MINI-PENDANT**

D: 9.75" H: 9.5"
Supplied with 15' of wire

T24

P1440SN
(1) Medium Base 60w max.



SATIN NICKEL FINISH
CLEAR GLASS

DAMP

**ONE LIGHT
MINI-PENDANT**

D: 9.75" H: 9.5"
Supplied with 15' of wire

T24

P1440ORB
(1) Medium Base 60w max.



OIL RUBBED BRONZE FINISH
CLEAR GLASS

PRATT STREET PRISMATIC

PRODUCT SHOWN: PRATT STREET PRISMATIC THREE
LIGHT PENDANT IN AUTUMN BRONZE FINISH



PRATT STREET PRISMATIC

DAMP

LARGE PENDANT

D: 16.25" H: 10"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

65062-962
(3) Medium Base 75w max.

T24 EN★

65062EN3-962
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



BRUSHED NICKEL FINISH
PRISMATIC GLASS & DIFFUSER

DAMP

MEDIUM PENDANT

D: 12.75" H: 8.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

65061-962
(2) Medium Base 75w max.

T24 EN★

65061EN3-962
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



BRUSHED NICKEL FINISH
PRISMATIC GLASS & DIFFUSER

DAMP

SMALL PENDANT

D: 11" H: 7.25"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

65060-962
(1) Medium Base 75w max.

T24 EN★

65060EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



BRUSHED NICKEL FINISH
PRISMATIC GLASS & DIFFUSER

DAMP

LARGE PENDANT

D: 16.25" H: 10"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

65062-715
(3) Medium Base 75w max.

T24 EN★

65062EN3-715
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



AUTUMN BRONZE FINISH
PRISMATIC GLASS & DIFFUSER

DAMP

MEDIUM PENDANT

D: 12.75" H: 8.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

65061-715
(2) Medium Base 75w max.

T24 EN★

65061EN3-715
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



AUTUMN BRONZE FINISH
PRISMATIC GLASS & DIFFUSER

DAMP

SMALL PENDANT

D: 11" H: 7.25"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

65060-715
(1) Medium Base 75w max.

T24 EN★

65060EN3-715
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



AUTUMN BRONZE FINISH
PRISMATIC GLASS & DIFFUSER

DAWES

PRODUCT SHOWN: DAWES THREE LIGHT
HALL / FOYER IN BRUSHED NICKEL FINISH



**THREE LIGHT
HALL / FOYER**

D: 15.75" H: 23.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

5126003-962

(3) Medium Base 75w max.



BRUSHED NICKEL FINISH
CLEAR SEEDED GLASS

**THREE LIGHT
HALL / FOYER**

D: 15.75" H: 23.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

5126003-710

(3) Medium Base 75w max.



BURNT SIENNA FINISH
CLEAR SEEDED GLASS

DAMP

LARGE FOUR LIGHT HALL / FOYER

L: 14" W: 14" H: 27.25"

10' wire pre-laced through 6' chain

T24

5340604-782

(4) Candelabra Base 60w max.

T24 EN★

5340604EN-782

(4) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

MEDIUM THREE LIGHT HALL / FOYER

L: 12" W: 12" H: 23.5"

10' wire pre-laced through 6' chain

T24

5240603-782

(3) Candelabra Base 60w max.

T24 EN★

5240603EN-782

(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

SMALL THREE LIGHT HALL / FOYER

L: 10" W: 10" H: 19.75"

10' wire pre-laced through 6' chain

T24

5140603-782

(3) Candelabra Base 60w max.

T24 EN★

5140603EN-782

(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

**LARGE FOUR LIGHT
HALL / FOYER**

L: 14" W: 14" H: 27.25"
10' wire pre-laced through 6' chain

T24

5340604-12
(4) Candelabra Base 60w max.

T24 EN★

5340604EN-12
(4) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

**MEDIUM THREE LIGHT
HALL / FOYER**

L: 12" W: 12" H: 23.5"
10' wire pre-laced through 6' chain

T24

5240603-12
(3) Candelabra Base 60w max.

T24 EN★

5240603EN-12
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



DAMP

**SMALL THREE LIGHT
HALL / FOYER**

L: 10" W: 10" H: 19.75"
10' wire pre-laced through 6' chain

T24

5140603-12
(3) Candelabra Base 60w max.

T24 EN★

5140603EN-12
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



ROME

DAMP

LARGE SIX LIGHT HALL / FOYER

D: 15" H: 23.375"
10' of Wire Pre-laced
through 5' of Chain

T24

5134906-05

(6) Candelabra Base 60w max.

T24 EN★

5134906EN-05

(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



CHROME FINISH

DAMP

LARGE SIX LIGHT HALL / FOYER

D: 15" H: 23.375"
10' of Wire Pre-laced
through 5' of Chain

T24

5134906-962

(6) Candelabra Base 60w max.

T24 EN★

5134906EN-962

(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



BRUSHED NICKEL FINISH

DAMP

LARGE SIX LIGHT HALL / FOYER

D: 15" H: 23.375"
10' of Wire Pre-laced
through 5' of Chain

T24

5134906-782

(6) Candelabra Base 60w max.

T24 EN★

5134906EN-782

(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



HEIRLOOM BRONZE FINISH

DAMP

**SMALL THREE LIGHT
HALL / FOYER**

D: 12.875" H: 18.75"
8' of Wire Pre-laced
through 3.5' of Chain

T24

5134903-05
(3) Candelabra Base 60w max.

T24 EN★

5134903EN-05
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



CHROME FINISH

DAMP

**SMALL THREE LIGHT
HALL / FOYER**

D: 12.875" H: 18.75"
8' of Wire Pre-laced
through 3.5' of Chain

T24

5134903-962
(3) Candelabra Base 60w max.

T24 EN★

5134903EN-962
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



BRUSHED NICKEL FINISH

DAMP

**SMALL THREE LIGHT
HALL / FOYER**

D: 12.875" H: 18.75"
8' of Wire Pre-laced
through 3.5' of Chain

T24

5134903-782
(3) Candelabra Base 60w max.

T24 EN★

5134903EN-782
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



HEIRLOOM BRONZE FINISH

LONOKE

PRODUCTS SHOWN: LONOKE MEDIUM
THREE LIGHT HALL / FOYER IN STARDUST
FINISH WITH CERUSED OAK ACCENTS





HEIRLOOM BRONZE FINISH

DAMP

LARGE FOUR LIGHT HALL / FOYER

D: 19" H: 29.75"
10' wire pre-laced through 6' chain

T24

5340704-782
(4) Candelabra Base 60w max.

T24 EN★

5340704EN-782
(4) Cand. Base LED 2700K, 3.5w, 350 lumen lamps incl.



HEIRLOOM BRONZE FINISH

DAMP

MEDIUM THREE LIGHT HALL / FOYER

D: 14.25" H: 23.25"
10' wire pre-laced through 6' chain

T24

5240703-782
(3) Candelabra Base 60w max.

T24 EN★

5240703EN-782
(3) Cand. Base LED 2700K, 3.5w, 350 lumen lamps incl.



HEIRLOOM BRONZE FINISH

DAMP

SMALL THREE LIGHT HALL / FOYER

D: 10.5" H: 19.5"
10' wire pre-laced through 6' chain

T24

5140703-782
(3) Candelabra Base 60w max.

T24 EN★

5140703EN-782
(3) Cand. Base LED 2700K, 3.5w, 350 lumen lamps incl.



STARDUST FINISH WITH CERUSED OAK ACCENTS

DAMP

LARGE FOUR LIGHT HALL / FOYER

D: 19" H: 29.75"
10' wire pre-laced through 6' chain

T24

5340704-846
(4) Candelabra Base 60w max.

T24 EN★

5340704EN-846
(4) Cand. Base LED 2700K, 3.5w, 350 lumen lamps incl.



STARDUST FINISH WITH CERUSED OAK ACCENTS

DAMP

MEDIUM THREE LIGHT HALL / FOYER

D: 14.25" H: 23.25"
10' wire pre-laced through 6' chain

T24

5240703-846
(3) Candelabra Base 60w max.

T24 EN★

5240703EN-846
(3) Cand. Base LED 2700K, 3.5w, 350 lumen lamps incl.



STARDUST FINISH WITH CERUSED OAK ACCENTS

DAMP

SMALL THREE LIGHT HALL / FOYER

D: 10.5" H: 19.5"
10' wire pre-laced through 6' chain

T24

5140703-846
(3) Candelabra Base 60w max.

T24 EN★

5140703EN-846
(3) Cand. Base LED 2700K, 3.5w, 350 lumen lamps incl.

SIX LIGHT HALL / FOYER

D: 16.75" H: 29.75"
12' wire, 88" chain

T24

5233-962

(6) Candelabra Base 60w max.

T24 EN★

5233EN-962

(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



+

THREE LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 9.5" H: 16" Semi-Flush H: 15.25"
12' wire, 4' chain

T24

5231-962

(3) Candelabra Base 40w max.

T24 EN★

5231EN-962

(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



+

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 7.25" H: 12" Semi-Flush H: 11.25"
12' wire, 4' chain

T24

5232-962

(2) Candelabra Base 40w max.

T24 EN★

5232EN-962

(2) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



Recommended
Product



BRETTON CEILING
Brushed Nickel
p.376

**SIX LIGHT
HALL / FOYER**

D: 16.75" H: 29.75"
12' wire, 88" chain

T24

5233-782

(6) Candelabra Base 60w max.

T24 EN★

5233EN-782

(6) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



+

**THREE LIGHT SEMI-FLUSH
CONVERTIBLE PENDANT**

D: 9.5" H: 16" Semi-Flush H: 15.25"
12' wire, 4' chain

T24

5231-782

(3) Candelabra Base 40w max.

T24 EN★

5231EN-782

(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



+

**TWO LIGHT SEMI-FLUSH
CONVERTIBLE PENDANT**

D: 7.25" H: 12" Semi-Flush H: 11.25"
12' wire, 4' chain

T24

5232-782

(2) Candelabra Base 40w max.

T24 EN★

5232EN-782

(2) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



Recommended
Product



BRETTON CEILING
Heirloom Bronze
p.376

PRATT STREET METAL

PRODUCT SHOWN: PRATT STREET LARGE
PENDANT IN AUTUMN BRONZE FINISH



DAMP

LARGE PENDANT

D: 16" H: 13.25"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

65087-962
(3) Medium Base 75w max.

T24 EN★

65087EN3-962
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

6508793S-962
LED: 3000K, 28 watts,
2000 gross lumens

See more Brushed Nickel Finish
on p.332



BRUSHED NICKEL FINISH
PRISMATIC GLASS DIFFUSER

DAMP

LARGE PENDANT

D: 16" H: 13.25"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

65087-848
(3) Medium Base 75w max.

T24 EN★

65087EN3-848
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

6508793S-848
LED: 3000K, 28 watts,
2000 gross lumens

See more Satin Bronze Finish
on p.332



SATIN BRONZE FINISH
PRISMATIC GLASS DIFFUSER

DAMP

LARGE PENDANT

D: 16" H: 13.25"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

65087-715
(3) Medium Base 75w max.

T24 EN★

65087EN3-715
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

6508793S-715
LED: 3000K, 28 watts,
2000 gross lumens

See more Autumn Bronze Finish
on p.332



AUTUMN BRONZE FINISH
PRISMATIC GLASS DIFFUSER

PRATT STREET METAL

DAMP

MEDIUM PENDANT

D: 13" H: 9.75"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

65086-962
(2) Medium Base 75w max.

T24 EN★

65086EN3-962
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

6508693S-962
LED: 3000K, 14 watts,
1000 gross lumens



BRUSHED NICKEL FINISH
PRISMATIC GLASS DIFFUSER

DAMP

MEDIUM PENDANT

D: 13" H: 9.75"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24


65086-848
(2) Medium Base 75w max.

T24 EN★

65086EN3-848
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

6508693S-848
LED: 3000K, 14 watts,
1000 gross lumens



SATIN BRONZE FINISH
PRISMATIC GLASS DIFFUSER

DAMP

MEDIUM PENDANT

D: 13" H: 9.75"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

65086-715
(2) Medium Base 75w max.

T24 EN★

65086EN3-715
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

6508693S-715
LED: 3000K, 14 watts,
1000 gross lumens



AUTUMN BRONZE FINISH
PRISMATIC GLASS DIFFUSER

DAMP

SMALL PENDANT

D: 9.5" H: 8.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

65085-962
(1) Medium Base 75w max.

T24 EN★

65085EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

6508593S-962
LED: 3000K, 14 watts,
1000 gross lumens



BRUSHED NICKEL FINISH
PRISMATIC GLASS DIFFUSER

DAMP

SMALL PENDANT

D: 9.5" H: 8.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

65085-848
(1) Medium Base 75w max.

T24 EN★

65085EN3-848
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

6508593S-848
LED: 3000K, 14 watts,
1000 gross lumens



SATIN BRONZE FINISH
PRISMATIC GLASS DIFFUSER

DAMP

SMALL PENDANT

D: 9.5" H: 8.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

65085-715
(1) Medium Base 75w max.

T24 EN★

65085EN3-715
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

6508593S-715
LED: 3000K, 14 watts,
1000 gross lumens



AUTUMN BRONZE FINISH
PRISMATIC GLASS DIFFUSER

STONE STREET

PRODUCTS SHOWN: STONE STREET THREE LIGHT
PENDANTS IN BRUSHED NICKEL FINISH



DAMP +

THREE LIGHT PENDANT

D: 21.75" H: 19.5"
 10' wire, (3) 12" stems, (1) 6" stem
 and sloped ceiling mounting hardware.
 Head swivels.

T24

6514403-962
 (3) Medium Base 60w max.

T24 EN★

6514403EN3-962
 (3) Med. Base LED 3000K,
 9.5w, 800 lumen lamps incl.

See More Brushed Nickel Finish
 on p.336



BRUSHED NICKEL FINISH
 SATIN ETCHED GLASS DIFFUSER

DAMP +

THREE LIGHT PENDANT

D: 21.75" H: 19.5"
 10' wire, (3) 12" stems, (1) 6" stem
 and sloped ceiling mounting hardware.
 Head swivels.


T24

6514403-848
 (3) Medium Base 60w max.

T24 EN★

6514403EN3-848
 (3) Med. Base LED 3000K,
 9.5w, 800 lumen lamps incl.

See More Satin Bronze Finish
 on p.336



SATIN BRONZE FINISH
 SATIN ETCHED GLASS DIFFUSER

DAMP +

THREE LIGHT PENDANT

D: 21.75" H: 19.5"
 10' wire, (3) 12" stems, (1) 6" stem
 and sloped ceiling mounting hardware.
 Head swivels.


T24

6514403-710
 (3) Medium Base 60w max.

T24 EN★

6514403EN3-710
 (3) Med. Base LED 3000K,
 9.5w, 800 lumen lamps incl.

See More Burnt Sienna Finish
 on p.336



BURNT SIENNA FINISH
 SATIN ETCHED GLASS DIFFUSER

STONE STREET

DAMP +

TWO LIGHT PENDANT

D: 17.25" H: 15.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware.
Head swivels.

T24

6514402-962
(2) Medium Base 60w max.

T24 EN★

6514402EN3-962
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



BRUSHED NICKEL FINISH
SATIN ETCHED GLASS DIFFUSER

DAMP +

TWO LIGHT PENDANT


D: 17.25" H: 15.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware.
Head swivels.

T24

6514402-848
(2) Medium Base 60w max.

T24 EN★

6514402EN3-848
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



SATIN BRONZE FINISH
SATIN ETCHED GLASS DIFFUSER

DAMP +

TWO LIGHT PENDANT


D: 17.25" H: 15.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware.
Head swivels.

T24

6514402-710
(2) Medium Base 60w max.

T24 EN★

6514402EN3-710
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



BURNT SIENNA FINISH
SATIN ETCHED GLASS DIFFUSER

DAMP +

ONE LIGHT PENDANT

D: 13.25" H: 12"
 10' wire, (3) 12" stems, (1) 6" stem
 and sloped ceiling mounting hardware.
 Head swivels.

T24

6514401-962
 (1) Medium Base 75w max.

T24 EN★

6514401EN3-962
 (1) Med. Base LED 3000K,
 9.5w, 800 lumen lamp incl.



BRUSHED NICKEL FINISH
 SATIN ETCHED GLASS DIFFUSER

DAMP +

ONE LIGHT PENDANT

D: 13.25" H: 12"
 10' wire, (3) 12" stems, (1) 6" stem
 and sloped ceiling mounting hardware.
 Head swivels.

T24

6514401-848
 (1) Medium Base 75w max.

T24 EN★

6514401EN3-848
 (1) Med. Base LED 3000K,
 9.5w, 800 lumen lamp incl.



SATIN BRONZE FINISH
 SATIN ETCHED GLASS DIFFUSER

DAMP +

ONE LIGHT PENDANT

D: 13.25" H: 12"
 10' wire, (3) 12" stems, (1) 6" stem
 and sloped ceiling mounting hardware.
 Head swivels.

T24

6514401-710
 (1) Medium Base 75w max.

T24 EN★

6514401EN3-710
 (1) Med. Base LED 3000K,
 9.5w, 800 lumen lamp incl.



BURNT SIENNA FINISH
 SATIN ETCHED GLASS DIFFUSER

DIVISION STREET

DAMP

ONE LIGHT PENDANT

D: 15" H: 14"
12' black field adjustable cord

T24

6517401-962
(1) Medium Base 100w max.

T24 EN★

6517401EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

6517493S-962
LED: 3000K, 14 watts,
1000 gross lumens



BRUSHED NICKEL FINISH

DAMP

ONE LIGHT PENDANT

D: 15" H: 14"
12' black field adjustable cord

T24

6517401-710
(1) Medium Base 100w max.

T24 EN★

6517401EN3-710
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

6517493S-710
LED: 3000K, 14 watts,
1000 gross lumens



BURNT SIENNA FINISH

DAMP

ONE LIGHT PENDANT

D: 15" H: 14"
12' black field adjustable cord

T24

6517401-846
(1) Medium Base 100w max.

T24 EN★

6517401EN3-846
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

6517493S-846
LED: 3000K, 14 watts,
1000 gross lumens



STARDUST FINISH

DAMP 

INDOOR / OUTDOOR PENDANT

D: 13.25" H: 11.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24


6247701-04
(1) Medium Base 100w max.

T24 EN★

6247701EN3-04
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

6247793S-04
LED: 3000K, 14 watts,
1000 gross lumens



SATIN ALUMINUM FINISH

DAMP 

INDOOR / OUTDOOR PENDANT

D: 13.25" H: 11.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6247701-44
(1) Medium Base 100w max.

T24 EN★

6247701EN3-44
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

6247793S-44
LED: 3000K, 14 watts,
1000 gross lumens



WEATHERED COPPER FINISH

Recommended Product



FREDRICKSBURG
OUTDOOR
Satin Aluminum,
Weathered Copper
p.568

HUDSON STREET



PRODUCTS SHOWN: HUDSON STREET ONE
LIGHT PENDANT IN BURNT SIENNA FINISH
DESIGNER: JLV CREATIVE
BUILDER: CRESCENT HOMES
PHOTOGRAPHER: ROB MCDANIEL

DAMP

ONE LIGHT PENDANT

D: 15.75" H: 15"
12' black field adjustable cord

T24

6525401-04
(1) Medium Base 100w max.

T24 EN★

6525401EN3-04
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



SATIN ALUMINUM FINISH

DAMP

ONE LIGHT PENDANT

D: 15.75" H: 15"
12' black field adjustable cord

T24

6525401-846
(1) Medium Base 100w max.

T24 EN★

6525401EN3-846
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



STARDUST FINISH

DAMP

ONE LIGHT PENDANT

D: 15.75" H: 15"
12' black field adjustable cord

T24

6525401-710
(1) Medium Base 100w max.

T24 EN★

6525401EN3-710
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



BURNT SIENNA FINISH

JEYNE

DAMP

LARGE ONE LIGHT PENDANT

D: 13.875" H: 11.375"
10' of wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6746501-44

(1) Medium Base 60w max.

T24 EN★

6746501EN3-44

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



WEATHERED COPPER FINISH [-44]

DAMP

LARGE ONE LIGHT PENDANT

D: 13.875" H: 11.375"
10' of wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6746501-782

(1) Medium Base 60w max.

T24 EN★

6746501EN3-782

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



HEIRLOOM BRONZE FINISH [-782]

DAMP

MEDIUM ONE LIGHT PENDANT

D: 10.125" H: 11.25"
10' of wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

6646501-44
(1) Medium Base 60w max.

T24 EN★

6646501EN3-44
(1) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



WEATHERED COPPER FINISH [-44]

DAMP

ONE LIGHT MINI-PENDANT

D: 7.5" H: 9.25"
10' of wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

6146501-44
(1) Medium Base 60w max.

T24 EN★

6146501EN3-44
(1) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



WEATHERED COPPER FINISH [-44]

DAMP

MEDIUM ONE LIGHT PENDANT

D: 10.125" H: 11.25"
10' of wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

6646501-782
(1) Medium Base 60w max.

T24 EN★

6646501EN3-782
(1) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



HEIRLOOM BRONZE FINISH [-782]

DAMP

ONE LIGHT MINI-PENDANT

D: 7.5" H: 9.25"
10' of wire, (3) 12" stems, (1) 6" stem and sloped ceiling mounting hardware

T24

6146501-782
(1) Medium Base 60w max.

T24 EN★

6146501EN3-782
(1) Med. Base LED 3000K, 9.5w, 800 lumen lamps incl.



HEIRLOOM BRONZE FINISH [-782]

SEBRING

DAMP

ONE LIGHT PENDANT

D: 16.75" H: 15"
10' wire, (3) 12" stems, 12" chain

T24

6658-98
(1) Medium Base 100w max.

T24 WOD EN★ LED

665893S-98
LED: 3000K, 14 watts,
1000 gross lumens



BRUSHED STAINLESS FINISH, WHITE INSIDE
CLEAR SEEDED GLASS

DAMP

ONE LIGHT PENDANT


D: 16.75" H: 15"
10' wire, (3) 12" stems, 12" chain

T24

6658-44
(1) Medium Base 100w max.

T24 WOD EN★ LED

665893S-44
LED: 3000K, 14 watts,
1000 gross lumens



WEATHERED COPPER FINISH
CLEAR SEEDED GLASS

DAMP

ONE LIGHT MINI-PENDANT

D: 8" H: 9"
10' wire, (3) 12" stems, 12" chain

T24

6150-98
(1) Medium Base 100w max.

T24 WOD EN★ LED

615093S-98
LED: 3000K, 9 watts,
700 gross lumens



BRUSHED STAINLESS FINISH, WHITE INSIDE
CLEAR SEEDED GLASS

DAMP

ONE LIGHT MINI-PENDANT


D: 8" H: 9"
10' wire, (3) 12" stems, 12" chain

T24

6150-44
(1) Medium Base 100w max.

T24 WOD EN★ LED

615093S-44
LED: 3000K, 9 watts,
700 gross lumens



WEATHERED COPPER FINISH
CLEAR SEEDED GLASS

Recommended Product



SEBRING OUTDOOR
Brushed Stainless
Weathered Copper,
Black
p.538

LARGE THREE LIGHT PENDANT

D: 14" H: 28.75"
12' wire pre-laced through 10' chain

T24

65047-715
(3) Candelabra Base 60w max.

T24 EN★

65047EN-715
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



SMALL THREE LIGHT PENDANT

D: 11.75" H: 24"
12' wire pre-laced through 10' chain

T24

65046-715
(3) Candelabra Base 60w max.

T24 EN★

65046EN-715
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



+

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 8.5" H: 15.75" Semi-Flush H: 15.5"
12' wire pre-laced through 10' chain

T24

77046-715
(2) Candelabra Base 60w max.

T24 EN★

77046EN-715
(2) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



GEARY

PRODUCT SHOWN: GEARY LARGE FOUR LIGHT
SEMI-FLUSH / PENDANT IN BRUSHED NICKEL FINISH



DAMP

**LARGE
FOUR LIGHT PENDANT**

D: 25" H: 27.125"
10' wire pre-laced through 6' chain

T24

6616504-962
(4) Medium Base 100w max.

T24 EN★

6616504EN3-962
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Brushed Nickel on p.348



BRUSHED NICKEL FINISH
SATIN ETCHED GLASS

DAMP

**LARGE
FOUR LIGHT PENDANT**

D: 25" H: 27.125"
10' wire pre-laced through 6' chain


T24

6616504-710
(4) Medium Base 100w max.

T24 EN★

6616504EN3-710
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Burnt Sienna on p.349



BURNT SIENNA FINISH
SATIN ETCHED GLASS

DAMP

**LARGE
FOUR LIGHT PENDANT**

D: 25" H: 27.125"
10' wire pre-laced through 6' chain

T24

6616504-782
(4) Medium Base 100w max.

T24 EN★

6616504EN3-782
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Heirloom Bronze on p.350



HEIRLOOM BRONZE FINISH
SATIN ETCHED GLASS

DAMP

**LARGE
FOUR LIGHT PENDANT**

D: 25" H: 27.125"
10' wire pre-laced through 6' chain


T24

6616504-839
(4) Medium Base 100w max.

T24 EN★

6616504EN3-839
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

See more Blacksmith on p.351



BLACKSMITH FINISH
SATIN ETCHED GLASS

DAMP +

**LARGE FOUR LIGHT
SEMI-FLUSH / PENDANT**

D: 25" H: 18.5" Semi-Flush H: 17"
6' wire pre-laced through 3' chain

T24

7716504-962
(4) Medium Base 100w max.

T24 EN★

7716504EN3-962
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

**MEDIUM THREE LIGHT
PENDANT**

D: 18.625" H: 20.625"
10' wire pre-laced through 6' chain

T24

6616503-962
(3) Medium Base 100w max.

T24 EN★

6616503EN3-962
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

**MEDIUM THREE LIGHT
SEMI-FLUSH / PENDANT**

D: 18.625" H: 16.375" Semi-Flush H: 14.875"
6' wire pre-laced through 3' chain

T24

7716503-962
(3) Medium Base 100w max.

T24 EN★

7716503EN3-962
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

**SMALL TWO LIGHT
SEMI-FLUSH / PENDANT**

D: 13.875" H: 12.375" Semi-Flush 11.375"
6' wire pre-laced through 3' chain

T24

7716502-962
(2) Medium Base 100w max.

T24 EN★

7716502EN3-962
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



Recommended
Product



GEARY CEILING
FLUSH MOUNT
Brushed Nickel
p.366

DAMP +

**LARGE FOUR LIGHT
SEMI-FLUSH / PENDANT**

D: 25" H: 18.5" Semi-Flush H: 17"
6' wire pre-laced through 3' chain

T24

7716504-710
(4) Medium Base 100w max.

T24 EN★

7716504EN3-710
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

**MEDIUM THREE LIGHT
PENDANT**

D: 18.625" H: 20.625"
10' wire pre-laced through 6' chain

T24

6616503-710
(3) Medium Base 100w max.

T24 EN★

6616503EN3-710
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

**MEDIUM THREE LIGHT
SEMI-FLUSH / PENDANT**

D: 18.625" H: 16.375" Semi-Flush H: 14.875"
6' wire pre-laced through 3' chain

T24

7716503-710
(3) Medium Base 100w max.

T24 EN★

7716503EN3-710
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

**SMALL TWO LIGHT
SEMI-FLUSH / PENDANT**

D: 13.875" H: 12.375" Semi-Flush 11.375"
6' wire pre-laced through 3' chain

T24

7716502-710
(2) Medium Base 100w max.

T24 EN★

7716502EN3-710
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



Recommended
Product



GEARY CEILING
FLUSH MOUNT
Burnt Sienna
p.366

DAMP +

LARGE FOUR LIGHT SEMI-FLUSH / PENDANT

D: 25" H: 18.5" Semi-Flush H: 17"
6' wire pre-laced through 3' chain

T24

7716504-782
(4) Medium Base 100w max.

T24 EN★

7716504EN3-782
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

MEDIUM THREE LIGHT PENDANT

D: 18.625" H: 20.625"
10' wire pre-laced through 6' chain

T24

6616503-782
(3) Medium Base 100w max.

T24 EN★

6616503EN3-782
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

MEDIUM THREE LIGHT SEMI-FLUSH / PENDANT

D: 18.625" H: 16.375" Semi-Flush H: 14.875"
6' wire pre-laced through 3' chain

T24

7716503-782
(3) Medium Base 100w max.

T24 EN★

7716503EN3-782
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

SMALL TWO LIGHT SEMI-FLUSH / PENDANT

D: 13.875" H: 12.375" Semi-Flush 11.375"
6' wire pre-laced through 3' chain

T24

7716502-782
(2) Medium Base 100w max.

T24 EN★

7716502EN3-782
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



Recommended Product



GEARY CEILING FLUSH MOUNT
Heirloom Bronze
p.366

DAMP +

**LARGE FOUR LIGHT
SEMI-FLUSH / PENDANT**


D: 25" H: 18.5" Semi-Flush H: 17"
6' wire pre-laced through 3' chain

T24

7716504-839
(4) Medium Base 100w max.

T24 EN★

7716504EN3-839
(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP

**MEDIUM THREE LIGHT
PENDANT**

D: 18.625" H: 20.625"
10' wire pre-laced through 6' chain

T24

6616503-839
(3) Medium Base 100w max.

T24 EN★

6616503EN3-839
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

**MEDIUM THREE LIGHT
SEMI-FLUSH / PENDANT**

D: 18.625" H: 16.375" Semi-Flush H: 14.875"
6' wire pre-laced through 3' chain

T24

7716503-839
(3) Medium Base 100w max.

T24 EN★

7716503EN3-839
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



DAMP +

**SMALL TWO LIGHT
SEMI-FLUSH / PENDANT**

D: 13.875" H: 12.375" Semi-Flush 11.375"
6' wire pre-laced through 3' chain

T24

7716502-839
(2) Medium Base 100w max.

T24 EN★

7716502EN3-839
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



Recommended
Product



GEARY CEILING
FLUSH MOUNT
Blacksmith
p.366

ACADEMY



CHROME FINISH
SATIN WHITE GLASS

DAMP

EXTRA LARGE PENDANT

D: 17" H: 12.25"
10' wire, (3) 12" stems, 12" chain

T24

65439-05
(1) Medium Base 100w max.

T24 EN★

65439EN3-05
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



BRUSHED NICKEL FINISH
SATIN WHITE GLASS

DAMP

EXTRA LARGE PENDANT

D: 17" H: 12.25"
10' wire, (3) 12" stems, 12" chain

T24

65439-962
(1) Medium Base 100w max.

T24 EN★

65439EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



HEIRLOOM BRONZE FINISH
SATIN WHITE GLASS

DAMP

EXTRA LARGE PENDANT

D: 17" H: 12.25"
10' wire, (3) 12" stems, 12" chain

T24

65439-782
(1) Medium Base 100w max.

T24 EN★

65439EN3-782
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



CHROME FINISH
SATIN WHITE GLASS

DAMP

LARGE PENDANT

D: 13" H: 10.75"
10' wire, (3) 12" stems, 12" chain

T24

65438-05
(1) Medium Base 100w max.

T24 EN★

65438EN3-05
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



BRUSHED NICKEL FINISH
SATIN WHITE GLASS

DAMP

LARGE PENDANT

D: 13" H: 10.75"
10' wire, (3) 12" stems, 12" chain

T24

65438-962
(1) Medium Base 100w max.

T24 EN★

65438EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



HEIRLOOM BRONZE FINISH
SATIN WHITE GLASS

DAMP

LARGE PENDANT

D: 13" H: 10.75"
10' wire, (3) 12" stems, 12" chain

T24

65438-782
(1) Medium Base 100w max.

T24 EN★

65438EN3-782
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



CHROME FINISH
SATIN WHITE GLASS

DAMP

MEDIUM PENDANT

D: 11.5" H: 9.75"
10' wire, (3) 12" stems, 12" chain

T24

65437-05
(1) Medium Base 75w max.

T24 EN★

65437EN3-05
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



BRUSHED NICKEL FINISH
SATIN WHITE GLASS

DAMP

MEDIUM PENDANT

D: 11.5" H: 9.75"
10' wire, (3) 12" stems, 12" chain

T24

65437-962
(1) Medium Base 75w max.

T24 EN★

65437EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



HEIRLOOM BRONZE FINISH
SATIN WHITE GLASS

DAMP

MEDIUM PENDANT

D: 11.5" H: 9.75"
10' wire, (3) 12" stems, 12" chain

T24

65437-782
(1) Medium Base 75w max.

T24 EN★

65437EN3-782
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



CHROME FINISH
SATIN WHITE GLASS

DAMP

SMALL PENDANT

D: 6.75" H: 7.5"
10' wire, (3) 12" stems, 12" chain

T24

65436-05
(1) Medium Base 75w max.

T24 EN★

65436EN3-05
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



BRUSHED NICKEL FINISH
SATIN WHITE GLASS

DAMP

SMALL PENDANT

D: 6.75" H: 7.5"
10' wire, (3) 12" stems, 12" chain

T24

65436-962
(1) Medium Base 75w max.

T24 EN★

65436EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



HEIRLOOM BRONZE FINISH
SATIN WHITE GLASS

DAMP

SMALL PENDANT

D: 6.75" H: 7.5"
10' wire, (3) 12" stems, 12" chain

T24

65436-782
(1) Medium Base 75w max.

T24 EN★

65436EN3-782
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

Recommended
Products



ACADEMY
WALL/BATH
Chrome,
Brushed Nickel,
Heirloom Bronze
p.427



ACADEMY
FLUSH MOUNT
Chrome
Brushed Nickel,
Heirloom Bronze
p.372

MONTREAL

ONE LIGHT MINI-PENDANT

D: 7.75" H: 7"
10' wire, (3) 12" stems, 12" chain

T24


61180-965

(1) Medium Base 100w max.

T24 EN★

61180EN3-965

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



ANTIQUE BRUSHED NICKEL FINISH
ETCHED GLASS, WHITE INSIDE

ONE LIGHT MINI-PENDANT

D: 7.75" H: 7"
10' wire, (3) 12" stems, 12" chain

T24

61180-710

(1) Medium Base 100w max.

T24 EN★

61180EN3-710

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



BURNT SIENNA FINISH
CAFE TINT GLASS

Recommended Product



MONTREAL
WALL/BATH
Antique Brushed Nickel,
Burnt Sienna
p.426

PAINTED SHADE PENDANTS

ONE LIGHT PENDANT

D: 15.75" H: 8.25"
4.5' black field adjustable cord

T24

6519-63

(1) Medium Base 150w max.

T24 EN★

6519EN3-63

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



PAINTED BRUSHED STAINLESS FINISH
WHITE INSIDE

ONE LIGHT PENDANT

D: 15.75" H: 8.25"
4.5' white field adjustable cord

T24

6519-21

(1) Medium Base 150w max.

T24 EN★

6519EN3-21

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



RED FINISH
WHITE INSIDE

ONE LIGHT PENDANT

D: 15.75" H: 8.25"
4.5' black field adjustable cord

T24

6519-98

(1) Medium Base 150w max.

T24 EN★

6519EN3-98

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



PAINTED ANTIQUE BRUSHED COPPER FINISH
WHITE INSIDE

FOUR LIGHT LARGE PENDANT

D: 22.5" H: 18"
Supplied with 15' of wire,
(4) 12" stems, (1) 6" stem

T24

F2343/4BS

(4) Medium Base 100w max.



ONE LIGHT MINI PENDANT

D: 8" H: 6.125"
Supplied with 15' of wire,
(1) 6" stem, (3) 12" stems

T24

P1137BS

(1) Halogen G9 Mini 75w max.



Recommended Products



CASUAL LUXURY
WALL / BATH
Brushed Steel
p.402



CASUAL LUXURY
FLUSH MOUNT
Brushed Steel
p.372

THREE LIGHT PENDANT

D: 19.25" H: 13.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6628003-962
(3) Medium Base 100w max.

T24 EN★

6628003EN3-962
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



BRUSHED NICKEL FINISH
OFF-WHITE FAUX SILK FABRIC
SATIN ETCHED GLASS DIFFUSER

+

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT

D: 16.25" H: 12" Semi-flush H: 10.75"
6' wire pre-laced through 3' of chain

T24

7728002-962
(2) Medium Base 100w max.

T24 EN★

7728002EN3-962
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



BRUSHED NICKEL FINISH
OFF-WHITE FAUX SILK FABRIC
SATIN ETCHED GLASS DIFFUSER

THREE LIGHT PENDANT

D: 19.25" H: 13.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting hardware

T24

6628003-782
(3) Medium Base 100w max.

T24 EN★

6628003EN3-782
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



HEIRLOOM BRONZE FINISH
OFF-WHITE FAUX SILK FABRIC
SATIN ETCHED GLASS DIFFUSER

+

TWO LIGHT SEMI-FLUSH CONVERTIBLE PENDANT


D: 16.25" H: 12" Semi-flush H: 10.75"
6' wire pre-laced through 3' of chain

T24

7728002-782
(2) Medium Base 100w max.

T24 EN★

7728002EN3-782
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



HEIRLOOM BRONZE FINISH
OFF-WHITE FAUX SILK FABRIC
SATIN ETCHED GLASS DIFFUSER

MULTI-PORT CANOPIES

PRODUCT SHOWN: TOWNER FIVE LIGHT
CLUSTER IN SATIN BRONZE FINISH



MULTI-PORT CANOPIES



SMALL LEO - HANGING GLOBE
6501801-848
Clear Seeded Glass
p.311
Unassembled

6018-848
6018EN3-848
601893S-848
White Glass
p.313
Unassembled



TOWNER FIVE LIGHT CLUSTER
5141305-848
5141305EN3-848
p.70
Preassembled

TOWNER MINI PENDANT
6141301-848,
6141301EN3-848,
p.71
Unassembled



DRISCOLL MINI PENDANT
6140401-848
6140401EN3-848
p.76
Unassembled



SATIN BRONZE FINISH

DAMP
FIVE LIGHT CLUSTER CANOPY

D: 12.25" H: 2"

7449405-848



SMALL OR MEDIUM LEO - HANGING GLOBE
6601801-848
Clear Seeded Glass
p.311

6501801-848
6020-848
6020EN3-848
602093S-848
6018-848
6018EN3-848
601893S-848
White Glass
p.313
Unassembled



TOWNER THREE LIGHT CLUSTER
5141303-848
5141303EN3-848
p.71
Preassembled

TOWNER MINI PENDANT
6141301-848,
6141301EN3-848,
p.71
Unassembled



DRISCOLL MINI PENDANT
6140401-848
6140401EN3-848
p.76
Unassembled



SATIN BRONZE FINISH

DAMP
THREE LIGHT CLUSTER CANOPY

D: 9.5" H: 2"

7449403-848

MULTI-PORT CANOPIES



WHITE FINISH

DAMP

FIVE LIGHT CLUSTER CANOPY

D: 12.25" H: 2"

7449405-15



SMALL LEO-HANGING GLOBE

6018-15,
6018EN3-15,
601893S-15

White Finish / White Glass
Unassembled
p.313



BRUSHED NICKEL FINISH

DAMP

FIVE LIGHT CLUSTER CANOPY

D: 12.25" H: 2"

7449405-962



TOWNER FIVE LIGHT CLUSTER

5141305-962
5141305EN3-962

Brushed Nickel Finish
Preassembled
p.72

TOWNER ONE LIGHT MINI-PENDANT

6141301-962

Brushed Nickel Finish
Unassembled
p.73



DRISCOLL MINI-PENDANT

6140401-962
6140401EN3-962

Brushed Nickel Finish
Unassembled
p.77



SMALL LEO - HANGING GLOBE

6501801-04

Satin Aluminum Finish /
Clear Seeded Glass
Unassembled
p.310



SMALL LEO - HANGING GLOBE

6018-04,
6018EN3-04,
601893S-04

Satin Aluminum Finish /
White Glass
Unassembled
p.313

MULTI-PORT CANOPIES

MEDIUM LEO-HANGING GLOBE
6020-15,
6020EN3-15,
602093S-15
White Finish /
White Glass
Unassembled
p.313



SMALL LEO-HANGING GLOBE
6018-15,
6018EN3-15,
601893S-15
White Finish /
White Glass
Unassembled
p.313



WHITE FINISH

DAMP

THREE LIGHT CLUSTER CANOPY

D: 9.5" H: 2"

7449403-15

TOWNER THREE LIGHT CLUSTER
5141303-962
5141303EN3-962
Brushed Nickel Finish
Preassembled
p.73



DRISCOLL MINI-PENDANT
6140401-962
6140401EN3-962
Brushed Nickel Finish
Unassembled
p.77



SMALL LEO - HANGING GLOBE
6501801-04
Satin Aluminum Finish /
Clear Seeded Glass
Unassembled
p.310



BRUSHED NICKEL FINISH

DAMP

THREE LIGHT CLUSTER CANOPY

D: 9.5" H: 2"

7449403-962

TOWNER ONE LIGHT MINI-PENDANT
6141301-962
Brushed Nickel Finish
Unassembled
p.73

SMALL LEO - HANGING GLOBE
6018-04,
6018EN3-04,
601893S-04
Satin Aluminum Finish /
White Glass
Unassembled
p.313



MEDIUM LEO - HANGING GLOBE
6601801-04
Satin Aluminum Finish /
Clear Seeded Glass
Unassembled
p.310



MEDIUM LEO - HANGING GLOBE
6020-04,
6020EN3-04,
602093S-04
Satin Aluminum Finish /
White Glass
Unassembled
p.313



PRODUCTS SHOWN: NASH MEDIUM CEILING FLUSH MOUNT IN BRUSHED NICKEL FINISH AND PARKFIELD ONE LIGHT WALL / BATH IN BRUSHED NICKEL FINISH





CEILING

collections



LARGE - WHITE FINISH [-15]
SATIN ETCHED GLASS



MEDIUM - CHROME FINISH [-05]
SATIN ETCHED GLASS



SMALL - BRUSHED NICKEL FINISH [-962]
SATIN ETCHED GLASS



LARGE - SATIN BRONZE FINISH [-848]
SATIN ETCHED GLASS



MEDIUM - HEIRLOOM BRONZE FINISH [-782]
SATIN ETCHED GLASS

DAMP

LARGE CEILING FLUSH MOUNT

D: 16.75" H: 5.5"

T24

75436 (-15,-05,-962,-848,-782)
(3) Medium Base 60w max.

T24 EN★

75436EN3 (-15,-05,-962,-848,-782)
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

T24 WOD LED

7543693S (-15,-05,-962,-848,-782)
LED: 3000K, 28 watts,
2000 gross lumens

DAMP

MEDIUM CEILING FLUSH MOUNT

D: 14" H: 4.5"

T24

75435 (-15,-05,-962,-848,-782)
(2) Medium Base 60w max.

T24 EN★

75435EN3 (-15,-05,-962,-848,-782)
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

T24 WOD LED

7543593S (-15,-05,-962,-848,-782)
LED: 3000K, 14 watts,
1000 gross lumens

DAMP

SMALL CEILING FLUSH MOUNT

D: 11.5" H: 4"

T24

75434 (-15,-05,-962,-848,-782)
(1) Medium Base 60w max.

T24 EN★

75434EN3 (-15,-05,-962,-848,-782)
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD LED

7543493S (-15,-05,-962,-848,-782)
LED: 3000K, 14 watts,
1000 gross lumens



HEIRLOOM BRONZE FINISH
AMBER SCAVO GLASS



HEIRLOOM BRONZE FINISH
AMBER SCAVO GLASS



HEIRLOOM BRONZE FINISH
AMBER SCAVO GLASS

DAMP

LARGE CEILING FLUSH MOUNT

D: 16.75" H: 5.5"

T24

75446-782
(3) Medium Base 60w max.

T24 EN★

75446EN3-782
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

T24 WOD LED

7544693S-782
LED: 3000K, 28 watts,
2000 gross lumens

DAMP

MEDIUM CEILING FLUSH MOUNT

D: 14" H: 4.5"

T24

75445-782
(2) Medium Base 60w max.

T24 EN★

75445EN3-782
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

T24 WOD LED

7544593S-782
LED: 3000K, 14 watts,
1000 gross lumens

DAMP

SMALL CEILING FLUSH MOUNT

D: 11.5" H: 4"

T24

75444-782
(1) Medium Base 60w max.

T24 EN★

75444EN3-782
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD LED

7544493S-782
LED: 3000K, 14 watts,
1000 gross lumens

Recommended Products



WINDGATE INDOOR
Brushed Nickel,
Heirloom Bronze
p.266



WINDGATE
WALL / BATH
Chrome,
Brushed Nickel,
Heirloom Bronze
p.441



WHITE FINISH [-15]
ALABASTER GLASS



WHITE FINISH [-15]
ALABASTER GLASS



WHITE FINISH [-15]
ALABASTER GLASS



BRUSHED NICKEL FINISH [-962]
ALABASTER GLASS



BRUSHED NICKEL FINISH [-962]
ALABASTER GLASS



BRUSHED NICKEL FINISH [-962]
ALABASTER GLASS



HEIRLOOM BRONZE FINISH [-782]
ALABASTER GLASS



HEIRLOOM BRONZE FINISH [-782]
ALABASTER GLASS



HEIRLOOM BRONZE FINISH [-782]
ALABASTER GLASS

DAMP

THREE LIGHT CEILING FLUSH MOUNT

D: 15" H: 5.5"

T24

75943 (-15,-962,-782)
(3) Medium Base 60w max.

T24 EN★

75943EN3 (-15,-962,-782)
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

DAMP

TWO LIGHT CEILING FLUSH MOUNT

D: 13" H: 5.25"

T24

75942 (-15,-962,-782)
(2) Medium Base 60w max.

T24 EN★

75942EN3 (-15,-962,-782)
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

DAMP

ONE LIGHT CEILING FLUSH MOUNT

D: 11.5" H: 4.5"

T24

75940 (-15,-962,-782)
(1) Medium Base 100w max.

T24 EN★

75940EN3 (-15,-962,-782)
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



LARGE - CHROME FINISH [-05]
SATIN ETCHED GLASS



MEDIUM - BRUSHED NICKEL FINISH [-962]
SATIN ETCHED GLASS



SMALL - ANTIQUE BRUSHED NICKEL FINISH [-965]
SATIN ETCHED GLASS



LARGE - HEIRLOOM BRONZE FINISH [-782]
SATIN ETCHED GLASS



MEDIUM - BLACKSMITH FINISH [-839]
SATIN ETCHED GLASS

DAMP

LARGE CEILING FLUSH MOUNT

D: 14.5" H: 6.5"

T24

77065 (-05,-962,-965,-782,-839)
(3) Medium Base 60w max.

T24 EN★

77065EN3 (-05,-962,-965,-782,-839)
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

7716593S (-05,-962,-965,-782,-839)
LED: 3000K, 28 watts,
2000 gross lumens

DAMP

MEDIUM CEILING FLUSH MOUNT

D: 12.5" H: 5.5"

T24

77064 (-05,-962,-965,-782,-839)
(2) Medium Base 60w max.

T24 EN★

77064EN3 (-05,-962,-965,-782,-839)
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

7716493S (-05,-962,-965,-782,-839)
LED: 3000K, 14 watts,
1000 gross lumens

DAMP

SMALL CEILING FLUSH MOUNT

D: 10.5" H: 5.5"

T24

77063 (-05,-962,-965,-782,-839)
(1) Medium Base 60w max.

T24 EN★

77063EN3 (-05,-962,-965,-782,-839)
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

7716393S (-05,-962,-965,-782,-839)
LED: 3000K, 14 watts,
1000 gross lumens



BURNT SIENNA FINISH
SATIN ETCHED GLASS

DAMP

**LARGE CEILING
FLUSH MOUNT**

D: 14.5" H: 6.5"

T24

77265-710

(3) Medium Base 60w max.

T24 EN★

77265EN3-710

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

7726593S-710

LED: 3000K, 28 watts,
2000 gross lumens



BURNT SIENNA FINISH
SATIN ETCHED GLASS

DAMP

**MEDIUM CEILING
FLUSH MOUNT**

D: 12.5" H: 5.5"

T24

77264-710

(2) Medium Base 60w max.

T24 EN★

77264EN3-710

(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

7726493S-710

LED: 3000K, 14 watts,
1000 gross lumens



BURNT SIENNA FINISH
SATIN ETCHED GLASS

DAMP

**SMALL CEILING
FLUSH MOUNT**

D: 10.5" H: 5.5"

T24

77263-710

(1) Medium Base 60w max.

T24 EN★

77263EN3-710

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

7726393S-710

LED: 3000K, 14 watts,
1000 gross lumens



BURNT SIENNA FINISH
AMBER SCAVO GLASS

DAMP

**LARGE CEILING
FLUSH MOUNT**

D: 14.5" H: 6.5"

T24

77065-710

(3) Medium Base 60w max.

T24 EN★

77065EN3-710

(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

7716593S-710

LED: 3000K, 28 watts,
2000 gross lumens



BURNT SIENNA FINISH
AMBER SCAVO GLASS

DAMP

**MEDIUM CEILING
FLUSH MOUNT**

D: 12.5" H: 5.5"

T24

77064-710

(2) Medium Base 60w max.

T24 EN★

77064EN3-710

(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

7716493S-710

LED: 3000K, 14 watts,
1000 gross lumens



BURNT SIENNA FINISH
AMBER SCAVO GLASS

DAMP

**SMALL CEILING
FLUSH MOUNT**

D: 10.5" H: 5.5"

T24

77063-710

(1) Medium Base 60w max.

T24 EN★

77063EN3-710

(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

7716393S-710

LED: 3000K, 14 watts,
1000 gross lumens



DAMP

OVAL LED CEILING FLUSH MOUNT

L: 32.25" W: 18" H: 4"

T24 EN★ LED

7950893S-962

LED: 3000K, 53 watts,
3295 gross lumens



DAMP

LARGE LED CEILING FLUSH MOUNT

D: 17.75" H: 4.25"

T24 EN★ LED

7750893S-962

LED: 3000K, 34 watts,
2045 gross lumens



DAMP

MEDIUM LED CEILING FLUSH MOUNT

D: 14.5" H: 4.125"

T24 EN★ LED

7650893S-962

LED: 3000K, 23 watts,
1395 gross lumens



DAMP

**OVAL LED CEILING
FLUSH MOUNT**

L: 32.25" W: 18" H: 4"

T24 EN★ LED

7950893S-782

LED: 3000K, 53 watts,
3295 gross lumens



DAMP

**LARGE LED CEILING
FLUSH MOUNT**

D: 17.75" H: 4.25"

T24 EN★ LED

7750893S-782

LED: 3000K, 34 watts,
2045 gross lumens



DAMP

**MEDIUM LED
CEILING FLUSH MOUNT**

D: 14.5" H: 4.125"

T24 EN★ LED

7650893S-782

LED: 3000K, 23 watts,
1395 gross lumens

SUNSET DRIVE



CHROME FINISH
WHITE OPAL ETCHED GLASS

DAMP

FOUR LIGHT SEMI-FLUSH MOUNT

D: 22" H: 13.25"

T24

SF254CH
(4) Medium Base 100w max.



BRUSHED STEEL FINISH
WHITE OPAL ETCHED GLASS

DAMP

FOUR LIGHT SEMI-FLUSH MOUNT

D: 22" H: 13.25"

T24

SF254BS
(4) Medium Base 100w max.



OIL RUBBED BRONZE FINISH
WHITE OPAL ETCHED GLASS

DAMP

FOUR LIGHT SEMI-FLUSH MOUNT

D: 22" H: 13.25"

T24

SF254ORB
(4) Medium Base 100w max.



CHROME FINISH
WHITE OPAL ETCHED GLASS

DAMP

THREE LIGHT SEMI-FLUSH MOUNT

D: 16" H: 10.375"

T24

SF258CH
(3) Medium Base 100w max.



BRUSHED STEEL FINISH
WHITE OPAL ETCHED GLASS

DAMP

THREE LIGHT SEMI-FLUSH MOUNT

D: 16" H: 10.375"

T24

SF258BS
(3) Medium Base 100w max.



OIL RUBBED BRONZE FINISH
WHITE OPAL ETCHED GLASS

DAMP

THREE LIGHT SEMI-FLUSH MOUNT

D: 16" H: 10.375"

T24

SF258ORB
(3) Medium Base 100w max.



CHROME FINISH
WHITE OPAL ETCHED GLASS

DAMP

TWO LIGHT SEMI-FLUSH MOUNT

D: 12.875" H: 7.75"

T24

SF259CH
(2) Medium Base 100w max.



BRUSHED STEEL FINISH
WHITE OPAL ETCHED GLASS

DAMP

TWO LIGHT SEMI-FLUSH MOUNT

D: 12.875" H: 7.75"

T24

SF259BS
(2) Medium Base 100w max.



CORINTHIAN BRONZE FINISH
STRIATED PEARL GLASS

DAMP

TWO LIGHT SEMI-FLUSH MOUNT

D: 12.875" H: 7.75"

T24

SF259CB
(2) Medium Base 100w max.



OIL RUBBED BRONZE FINISH
WHITE OPAL ETCHED GLASS

DAMP

TWO LIGHT SEMI-FLUSH MOUNT

D: 12.875" H: 7.75"

T24

SF259ORB
(2) Medium Base 100w max.

Recommended Products



SUNSET DRIVE
INDOOR
Brushed Steel
Corinthian Bronze
p.106



SUNSET DRIVE
WALL / BATH
Brushed Steel
p.414



BRUSHED STEEL FINISH
WHITE OPAL ETCHED GLASS

DAMP

THREE LIGHT FLUSH MOUNT

D: 16" H: 6.25"

T24

FM312BS

(3) Medium Base 60w max.



CHROME FINISH
WHITE OPAL ETCHED GLASS

DAMP

THREE LIGHT FLUSH MOUNT

D: 16" H: 6.25"

T24

FM312CH

(3) Medium Base 60w max.



OIL RUBBED BRONZE FINISH
WHITE OPAL ETCHED GLASS

DAMP

THREE LIGHT FLUSH MOUNT

D: 16" H: 6.25"

T24

FM312ORB

(3) Medium Base 60w max.



CHROME FINISH
WHITE OPAL ETCHED GLASS

DAMP

TWO LIGHT FLUSH MOUNT

D: 13.5" H: 4.75"

T24

FM313CH

(2) Medium Base 60w max.



BRUSHED STEEL FINISH
WHITE OPAL ETCHED GLASS

DAMP

TWO LIGHT FLUSH MOUNT

D: 13.5" H: 4.75"

T24

FM313BS

(2) Medium Base 60w max.



CORINTHIAN BRONZE FINISH
STRIATED PEARL GLASS

DAMP

TWO LIGHT FLUSH MOUNT

D: 13.5" H: 4.75"

T24

FM313CB

(2) Medium Base 60w max.



OIL RUBBED BRONZE FINISH
WHITE OPAL ETCHED GLASS

DAMP

TWO LIGHT FLUSH MOUNT

D: 13.5" H: 4.75"

T24

FM313ORB

(2) Medium Base 60w max.

CASUAL LUXURY

BRUSHED STEEL FINISH [BS] / FABRIC IN SILVER ORGANZA FINISH SHADE



DAMP

TWO LIGHT INDOOR SEMI-FLUSH MOUNT

D: 13" H: 9.125"

T24

SF251BS

(2) Medium Base 100w max.



DAMP

TWO LIGHT INDOOR FLUSH MOUNT

D: 13" H: 5.25"

T24

SF291BS

(2) Medium Base 60w max.

Recommended Products



CASUAL LUXURY PENDANT
Brushed Steel
p.356



CASUAL LUXURY WALL / BATH
Brushed Steel
p.402

ACADEMY



CHROME FINISH [-05]
SATIN WHITE GLASS



BRUSHED NICKEL FINISH [-962]
SATIN WHITE GLASS



HEIRLOOM BRONZE FINISH [-782]
SATIN WHITE GLASS

DAMP

LARGE CEILING SEMI-FLUSH MOUNT

D: 13" H: 12.5"

T24

77437 (-05, 962, 782)

(1) Medium Base 100w max.

T24 EN★

77437EN3 (-05, 962, 782)

(1) Med. Base LED 3000K, 9.5w, 800 lumen lamp incl.

DAMP

MEDIUM CEILING SEMI-FLUSH MOUNT

D: 11.5" H: 11.75"

T24

77436 (-05, 962, 782)

(1) Medium Base 75w max.

T24 EN★

77436EN3 (-05, 962, 782)

(1) Med. Base LED 3000K, 9.5w, 800 lumen lamp incl.

Recommended Products



ACADEMY PENDANT
Chrome,
Brushed Nickel,
Heirloom Bronze
p.352



ACADEMY WALL / BATH
Chrome,
Brushed Nickel,
Heirloom Bronze
p.427

Recommended Products



VINTNER INDOOR
Satin Nickel,
Heritage Bronze
p.236



VINTNER INDOOR
WALL / BATH
Satin Nickel,
Heritage Bronze
p.418



SATIN NICKEL FINISH
WHITE OPAL ETCHED GLASS

DAMP

15" FLUSH MOUNT

D: 15" H: 6.375"

T24

FM413SN

(3) Medium Base 60w max.



HERITAGE BRONZE FINISH
WHITE OPAL ETCHED GLASS

DAMP

15" FLUSH MOUNT

D: 15" H: 6.375"

T24

FM413HTBZ

(3) Medium Base 60w max.



SATIN NICKEL FINISH
WHITE OPAL ETCHED GLASS

DAMP

13" FLUSH MOUNT

D: 13" H: 5.875"

T24

FM412SN

(2) Medium Base 60w max.



HERITAGE BRONZE FINISH
WHITE OPAL ETCHED GLASS

DAMP

13" FLUSH MOUNT

D: 13" H: 5.875"

T24

FM412HTBZ

(2) Medium Base 60w max.



SATIN NICKEL FINISH
WHITE OPAL ETCHED GLASS

DAMP

11" FLUSH MOUNT

D: 11" H: 5.75"

T24

FM411SN

(2) Medium Base 40w max.



HERITAGE BRONZE FINISH
WHITE OPAL ETCHED GLASS

DAMP

11" FLUSH MOUNT

D: 11" H: 5.75"

T24

FM411HTBZ

(2) Medium Base 40w max.

WEBSTER



WHITE FINISH [-15]
SMOOTH WHITE GLASS

DAMP

**MEDIUM WALL / CEILING
FLUSH MOUNT**

D: 9.5" H: 5.75" E: 5.75"

T24

5328 (-15,-962,-782)
(2) Medium Base 60w max.

T24 EN★

5328EN3 (-15,-962,-782)
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



BRUSHED NICKEL FINISH [-962]
SMOOTH WHITE GLASS

DAMP

**SMALL WALL / CEILING
FLUSH MOUNT**

D: 7.75" H: 5.25" E: 5.25"

T24

5326 (-15,-962,-782)
(1) Medium Base 60w max.

T24 EN★

5326EN3 (-15,-962,-782)
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



HEIRLOOM BRONZE FINISH [-782]
SMOOTH WHITE GLASS



WHITE FINISH
WHITE ACRYLIC DIFFUSER

DAMP

**SMALL LED
WALL / CEILING
FLUSH MOUNT**

D: 8" H: 2.75"

T24 LED

5590193S-15
LED: 3000K, 14 watts
800 gross lumens

TOMKIN



WHITE FINISH
WHITE GLASS

DAMP

**ONE LIGHT CEILING
FLUSH MOUNT**

D: 6" H: 7.5"

T24

5366-15
(1) Medium Base 60w max.

T24 EN★

5366EN3-15
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



WHITE FINISH
WHITE GLASS, PULL CHAIN

DAMP

**ONE LIGHT CEILING
FLUSH MOUNT**

D: 6" H: 7.5"

T24

5367PC-15
(1) Medium Base 60w max.

T24 EN★

5367PCEN3-15
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



BRUSHED NICKEL FINISH
WHITE GLASS

DAMP

**ONE LIGHT CEILING
FLUSH MOUNT**

D: 6" H: 7.5"

T24

5366-962
(1) Medium Base 60w max.

T24 EN★

5366EN3-962
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.



HEIRLOOM BRONZE FINISH
WHITE GLASS

DAMP

**ONE LIGHT CEILING
FLUSH MOUNT**

D: 6" H: 7.5"

T24

5366-782
(1) Medium Base 60w max.

T24 EN★

5366EN3-782
(1) Med. Base LED 3000K,
9.5w, 800 lumen lamp incl.

LEO - HANGING GLOBE

Recommended Product



LEO - HANGING GLOBE PENDANT
Heirloom Bronze,
Brushed Nickel,
Satin Bronze
p.308



SATIN ALUMINUM FINISH
CLEAR SEEDED GLASS

DAMP

**ONE LIGHT
WALL / CEILING
SEMI-FLUSH MOUNT**

D: 8" H: 9.625"

T24

7501801-04
(1) Medium Base 60w max.



SATIN BRONZE FINISH
CLEAR SEEDED GLASS

DAMP

**ONE LIGHT
WALL / CEILING
SEMI-FLUSH MOUNT**

D: 8" H: 9.625"

T24

7501801-848
(1) Medium Base 60w max.



WHITE FINISH
WHITE SMOOTH GLASS

DAMP

**ONE LIGHT
WALL / CEILING
SEMI-FLUSH MOUNT**

D: 8" H: 9.625"

T24

7518-15
(1) Medium Base 60w max.

T24 EN★

7518EN3-15
(1) Med. Base LED
9.5w Bulb lamps incl.



SATIN ALUMINUM FINISH
WHITE SMOOTH GLASS

DAMP

**ONE LIGHT
WALL / CEILING
SEMI-FLUSH MOUNT**

D: 8" H: 9.625"

T24

7518-04
(1) Medium Base 60w max.

T24 EN★

7518EN3-04
(1) Med. Base LED
9.5w Bulb lamps incl.



SATIN BRONZE FINISH
WHITE SMOOTH GLASS

DAMP

**ONE LIGHT
WALL / CEILING
SEMI-FLUSH MOUNT**

D: 8" H: 9.625"

T24

7518-848
(1) Medium Base 60w max.

T24 EN★

7518EN3-848
(1) Med. Base LED
9.5w Bulb lamps incl.

Recommended
Product



BRETTON PENDANT
Heirloom Bronze,
Brushed Nickel
p.328



BRUSHED NICKEL FINISH
CLEAR BEVELED GLASS

DAMP

**THREE LIGHT
CEILING FLUSH MOUNT**

L: 8.75" W: 10" H: 6"

T24

7648-962
(3) Candelabra Base 40w max.

T24 EN★

7648EN-962
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



HEIRLOOM BRONZE FINISH
CLEAR BEVELED GLASS

DAMP

**THREE LIGHT
CEILING FLUSH MOUNT**

L: 8.75" W: 10" H: 6"

T24

7648-782
(3) Candelabra Base 40w max.

T24 EN★

7648EN-782
(3) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



BRUSHED NICKEL FINISH
CLEAR BEVELED GLASS

DAMP

**TWO LIGHT
CEILING FLUSH MOUNT**

L: 7" W: 8" H: 6"

T24

7647-962
(2) Candelabra Base 40w max.

T24 EN★

7647EN-962
(2) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



HEIRLOOM BRONZE FINISH
CLEAR BEVELED GLASS

DAMP

**TWO LIGHT
CEILING FLUSH MOUNT**

L: 7" W: 8" H: 6"

T24

7647-782
(2) Candelabra Base 40w max.

T24 EN★

7647EN-782
(2) Cand. Base LED 2700K,
3.5w, 350 lumen lamps incl.



BRUSHED NICKEL FINISH
CLEAR BEVELED GLASS

DAMP

**FOUR LIGHT CEILING
FLUSH MOUNT**

D: 11" H: 6.5"

T24

7662-962
(4) Candelabra Base 25w max.



POLISHED BRASS FINISH
CLEAR BEVELED GLASS

DAMP

**FOUR LIGHT CEILING
FLUSH MOUNT**

D: 11" H: 6.5"

T24

7662-02
(4) Candelabra Base 25w max.



BRUSHED NICKEL FINISH
CLEAR BEVELED GLASS

DAMP

**THREE LIGHT CEILING
FLUSH MOUNT**

D: 9" H: 6"

T24

7661-962
(3) Candelabra Base 25w max.



POLISHED BRASS FINISH
CLEAR BEVELED GLASS

DAMP

**THREE LIGHT CEILING
FLUSH MOUNT**

D: 9" H: 6"

T24

7661-02
(3) Candelabra Base 25w max.

HOLLY

WHITE FINISH [-15] / WHITE ACRYLIC DIFFUSER



DAMP

LARGE LED CEILING FLUSH MOUNT

D: 16.5" H: 4.75"

T24 EN★ LED

5739493S-15

LED: 3000K, 34 watts,
2045 gross lumens



DAMP

MEDIUM LED CEILING FLUSH MOUNT

D: 14" H: 4.25"

T24 EN★ LED

5639493S-15

LED: 3000K, 23 watts,
1395 gross lumens

HAYLEE

WHITE FINISH [-15] / WHITE ACRYLIC DIFFUSER



DAMP

LARGE LED CEILING FLUSH MOUNT

D: 14.625" H: 3.75"

T24 EN★ LED

5792593S-15

LED: 3000K, 34 watts,
2045 gross lumens



DAMP

MEDIUM LED CEILING FLUSH MOUNT

D: 13.25" H: 3.5"

T24 EN★ LED

5692593S-15

LED: 3000K, 23 watts,
1395 gross lumens



DAMP

LARGE CEILING FLUSH MOUNT

D: 16.25" H: 4"

T24

7543503-962
(3) Medium Base 60w max.

T24 EN★

7543503EN3-962
(3) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

7643593S-962
LED: 3000K, 28 watts,
2000 gross lumens

DAMP

MEDIUM CEILING FLUSH MOUNT

D: 12.25" H: 4"

T24

7543502-962
(2) Medium Base 60w max.

T24 EN★

7543502EN3-962
(2) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED


7443593S-962
LED: 3000K, 14 watts,
1000 gross lumens

DAMP

LARGE LED SQUARE CEILING FLUSH MOUNT

L: 16" W: 16" H: 3.25"

T24 EN★ LED

5776093S-15
LED: 3000K, 34 watts,
2045 gross lumens

DAMP

MEDIUM LED SQUARE CEILING FLUSH MOUNT

L: 14.5" W: 14.5" H: 3.125"

T24 EN★ LED

5676093S-15
LED: 3000K, 23 watts,
1395 gross lumens

DAMP

SMALL LED SQUARE CEILING FLUSH MOUNT

L: 10.75" W: 10.75" H: 2.875"

T24 EN★ LED

5576093S-15
LED: 3000K, 15 watts,
950 gross lumens

TRAVERSE LOTUS



WET

12" ROUND

D: 12" H: .93"

T24 EN★ LED

149212RD-15

LED: 3000K, 22 watts,
1400 gross lumens



WET

9" ROUND

D: 9" H: .67"

T24 EN★ LED

14929RD-15

LED: 3000K, 18 watts,
1150 gross lumens



WET

7" ROUND

D: 7" H: .67"

T24 EN★ LED

14927RD-15

LED: 3000K, 15 watts,
850 gross lumens



WET


5" ROUND

D: 5" H: .67"

T24 EN★ LED

14925RD-15

LED: 3000K, 10 watts,
550 gross lumens



WET

12" SQUARE

D: 12" H: .93"

T24 EN★ LED

149212SQ-15

LED: 3000K, 22 watts,
1400 gross lumens



WET

9" SQUARE

W: 9" H: .67"

T24 EN★ LED

14929SQ-15

LED: 3000K, 18 watts,
1150 gross lumens



WET

6" SQUARE

W: 6" H: .67"

T24 EN★ LED

14926SQ-15

LED: 3000K, 15 watts,
850 gross lumens



WET

4" SQUARE

W: 4" H: .67"

T24 EN★ LED

14924SQ-15

LED: 3000K, 10 watts,
550 gross lumens

DROP LENS FLUORESCENT



WHITE FINISH
WHITE ACRYLIC DIFFUSER

DAMP

FOUR LIGHT CEILING FLUSH MOUNT

L: 51.75" W: 18.5" H: 3.5"

T24 FL EN★

59361LE-15
(4) Medium Bi-Pin T8 32w max.
120V NPF Electronic Ballast



OIL RUBBED BRONZE FINISH
WHITE ACRYLIC DIFFUSER

DAMP

FOUR LIGHT CEILING FLUSH MOUNT

L: 51.75" W: 18.5" H: 3.5"

T24 FL EN★

59361LE-790
(4) Medium Bi-Pin T8 32w max.
120V NPF Electronic Ballast



WHITE FINISH
WHITE ACRYLIC DIFFUSER

DAMP

FOUR LIGHT CEILING FLUSH MOUNT

L: 27.75" W: 27.75" H: 3.5"

T24 FL EN★

59360LE-15
(4) Medium Bi-Pin T8 17w max.
120V NPF Electronic Ballast



OIL RUBBED BRONZE FINISH
WHITE ACRYLIC DIFFUSER

DAMP

FOUR LIGHT CEILING FLUSH MOUNT

L: 27.75" W: 27.75" H: 3.5"

T24 FL EN★

59360LE-790
(4) Medium Bi-Pin T8 17w max.
120V NPF Electronic Ballast



DAMP

**FOUR FOOT LED CEILING
FLUSH MOUNT**

L: 51" W: 10.25" H: 3.25"

T24 LED EN★

5927093S-15

LED: 3000K, 41 watts
3000 gross lumens



DAMP

**TWO FOOT LED CEILING
FLUSH MOUNT**

L: 26" W: 10.25" H: 3.25"

T24 LED EN★

5727093S-15

LED: 3000K, 27 watts
2000 gross lumens



DAMP ADA +

FOUR FOOT LED CEILING / WALL MOUNT

L: 46.5" W: 1.75" H: 1.875"
Height from center of the outlet box
horizontal: 0.875" vertical: 23.25"

T24 LED EN★

5920593S-15
LED: 3000K, 39 watts
3000 gross lumens



DAMP ADA +

TWO FOOT LED CEILING FLUSH MOUNT

L: 23" W: 1.75" H: 1.875"
Height from center of the outlet box
horizontal: 0.875" vertical: 11.5"

T24 LED EN★

5720593S-15
LED: 3000K, 19 watts
1500 gross lumens



DAMP

**TWO LIGHT MULTI-VOLT
CEILING / WALL MOUNT**

W: 48.25" H: 4.5" E: 4.5"
Height from center of outlet box
horizontal: 2.25" vertical: 24.25"

T24 FL

49026LE-15

(2) Medium Bi-Pin T8 32w max.
120/277V HPF Electronic Ballast



DAMP

**TWO LIGHT MULTI-VOLT
CEILING / WALL MOUNT**

W: 24.25" H: 4.5" E: 4.5"
Height from center of outlet box
horizontal: 2.25" vertical: 12.25"

T24 FL

49024LE-15

(2) Medium Bi-Pin T8 17w max.
120/277V HPF Electronic Ballast



DAMP

FOUR LIGHT CEILING FLUSH MOUNT

L: 51.5" W: 16.75" H: 5.75"

T24 FL

59271LE-15

(4) Medium Bi-Pin T8 32w max.
120V NPF Electronic Ballast



DAMP

TWO LIGHT CEILING FLUSH MOUNT

L: 51.5" W: 11.25" H: 5.75"

T24 FL

59270LE-15

(2) Medium Bi-Pin T8 32w max.
120V NPF Electronic Ballast



DAMP

**LINEAR LED
CEILING FLUSH MOUNT**

L: 48" W: 6.75" H: 2.5"

T24 LED EN★

5913291S-15
LED: 2700K, 25 watts,
2200 gross lumens

DAMP

**LINEAR FLOURESCENT
TWO LIGHT CEILING
FLUSH MOUNT**

L: 48" W: 6.75" H: 2.5"

T24 FL

59132LE-15
(2) Medium Bi-Pin T8 32w max.
120V NPF Electronic Ballast



DAMP

**LINEAR LED
CEILING FLUSH MOUNT**

L: 24" W: 6.75" H: 2.5"

T24 LED EN★

5913691S-15
LED: 2700K, 14 watts,
1200 gross lumens

DAMP

**LINEAR FLOURESCENT
TWO LIGHT CEILING
FLUSH MOUNT**

L: 24" W: 6.75" H: 2.5"

T24 EN★ FL

59136LE-15
(2) Medium Bi-Pin T8 17w max.
120V NPF Electronic Ballast



**FOUR LIGHT TRACK
LIGHTING KIT**

L: 48" W: 4.75" H: 13.25"

T24

2530404-962

(4) Med. Base 60w max.

T24 EN★

2530404EN3-962

(4) Med. Base LED 3000K,
9.5w, 800 lumen lamps incl.



**FOUR LIGHT
LED CURVED TRACK LIGHT**

L: 36.625" W: 5" H: 7.375"
Adjustable track heads

T24 EN★ LED

2637204S-962



**FOUR LIGHT
LED STRAIGHT TRACK LIGHT**

L: 36.625" W: 5" H: 6.875"
Adjustable track heads

T24 EN★ LED

2537204S-962



**THREE LIGHT
LED CURVED TRACK LIGHT**

L: 24.375" W: 5" H: 7.125"
Adjustable track heads

T24 EN★ LED

2637203S-962



**THREE LIGHT
LED STRAIGHT TRACK LIGHT**

L: 24.375" W: 5" H: 6.875"
Adjustable track heads

T24 EN★ LED

2537203S-962

PRODUCTS SHOWN: HETTINGER THREE LIGHT WALL / BATH IN BRUSHED NICKEL FINISH





WALL/BATH

collections

ELMWOOD PARK

Recommended Product



ELMWOOD PARK
INDOOR
Brushed Nickel,
Heirloom Bronze
p.230



FOUR LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
SATIN ETCHED WITH CLEAR OUTER GLASS



THREE LIGHT WALL / BATH – HEIRLOOM BRONZE FINISH [-782]
SATIN ETCHED WITH CLEAR OUTER GLASS



THREE LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
SATIN ETCHED WITH CLEAR OUTER GLASS



ONE LIGHT WALL / BATH – HEIRLOOM BRONZE FINISH [-782]
SATIN ETCHED WITH CLEAR OUTER GLASS

DAMP +

FOUR LIGHT BATH

W: 31.25" H: 8.5" E: 6.25"
Height from center of outlet box
up: 6.25" down: 2.25"

T24

4437304 (-962,-782)
(4) Medium Base 75w max.

T24 EN★

4437304EN3 (-962,-782)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT BATH

W: 22.25" H: 8.5" E: 6.25"
Height from center of outlet box
up: 6.25" down: 2.25"

T24

4437303 (-962,-782)
(3) Medium Base 75w max.

T24 EN★

4437303EN3 (-962,-782)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT BATH

W: 13.25" H: 8.5" E: 6.25"
Height from center of outlet box
up: 6.25" down: 2.25"

T24

4437302 (-962,-782)
(2) Medium Base 75w max.

T24 EN★

4437302EN3 (-962,-782)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH SCONCE

W: 4.5" H: 8" E: 6.25"
Height from center of outlet box
up: 5" down: 3"

T24

4137301 (-962,-782)
(1) Medium Base 75w max.

T24 EN★

4137301EN3 (-962,-782)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

Recommended Product



ZIRE INDOOR
Chrome,
Brushed Nickel,
Oil Rubbed Bronze
p.52



FOUR LIGHT WALL / BATH – CHROME FINISH [-05]
ETCHED GLASS, WHITE INSIDE



THREE LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
ETCHED GLASS, WHITE INSIDE



THREE LIGHT WALL / BATH – BRUSHED OIL RUBBED BRONZE FINISH [-778]
ETCHED GLASS, WHITE INSIDE



ONE LIGHT WALL / BATH – CHROME FINISH [-05]
ETCHED GLASS, WHITE INSIDE

DAMP +

FOUR LIGHT BATH

W: 34" H: 7.875" E: 5.5"
Height from center of outlet box
up: 4.875" down: 3"

T24

4490304 (-05,-962,-778)
(4) Medium Base 75w max.

T24 EN★

4490304EN3 (-05,-962,-778)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT BATH

W: 24" H: 7.875" E: 5.5"
Height from center of outlet box
up: 4.875" down: 3"

T24

4490303 (-05,-962,-778)
(3) Medium Base 75w max.

T24 EN★

4490303EN3 (-05,-962,-778)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT BATH

W: 14" H: 7.875" E: 5.5"
Height from center of outlet box
up: 4.875" down: 3"

T24

4490302 (-05,-962,-778)
(2) Medium Base 75w max.

T24 EN★

4490302EN3 (-05,-962,-778)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH SCONCE

W: 4.375" H: 7.875" E: 6.5"
Height from center of outlet box
up: 4.375" down: 3.5"

T24

4190301 (-05,-962,-778)
(1) Medium Base 75w max.

T24 EN★

4190301EN3 (-05,-962,-778)
(1) Med. Base LED
9.5w, 800 lumen lamps incl.

ALTURAS

PRODUCTS SHOWN: ALTURAS THREE LIGHT WALL / BATH IN BRUSHED NICKEL FINISH



Recommended Product



ALTURAS INDOOR
Brushed Nickel,
Satin Bronze,
Brushed Oil
Rubbed Bronze
p.60



FOUR LIGHT WALL / BATH – CHROME FINISH [-05]
ETCHED GLASS, WHITE INSIDE



THREE LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
ETCHED GLASS, WHITE INSIDE



TWO LIGHT WALL / BATH – SATIN BRONZE FINISH [-848]
ETCHED GLASS, WHITE INSIDE



ONE LIGHT WALL / BATH
BRUSHED OIL RUBBED BRONZE FINISH [-778]
ETCHED GLASS, WHITE INSIDE

DAMP +

FOUR LIGHT WALL / BATH

W: 30.5" H: 9.25" E: 7.25"
Height from center of outlet box
up: 6.25" down: 3"

T24

4424604 (-05,-962,-848,-778)
(4) Medium Base 100w max.

T24 EN★

4424604EN3 (-05,-962,-848,-778)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

THREE LIGHT WALL / BATH

W: 22" H: 9.25" E: 7.5"
Height from center of outlet box
up: 6.25" down: 3"

T24

4424603 (-05,-962,-848,-778)
(3) Medium Base 100w max.

T24 EN★

4424603EN3 (-05,-962,-848,-778)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

TWO LIGHT WALL / BATH

W: 13.5" H: 9.25" E: 6.5"
Height from center of outlet box
up: 6.25" down: 3"

T24

4424602 (-05,-962,-848,-778)
(2) Medium Base 100w max.

T24 EN★

4424602EN3 (-05,-962,-848,-778)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

ONE LIGHT WALL / BATH

W: 4.5" H: 8.75" E: 6.25"
Height from center of outlet box
up: 5.75" down: 3"

T24

4124601 (-05,-962,-848,-778)
(1) Medium Base 100w max.

T24 EN★

4124601EN3 (-05,-962,-848,-778)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

HETTINGER

PRODUCT SHOWN: HETTINGER FOUR LIGHT WALL / BATH IN CHROME FINISH



Recommended Product



HETTINGER INDOOR
Brushed Nickel,
Burnt Sienna
p.194



FOUR LIGHT WALL / BATH – CHROME FINISH [-05]
ETCHED GLASS, WHITE INSIDE



THREE LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
ETCHED GLASS, WHITE INSIDE



TWO LIGHT WALL / BATH – BURNT SIENNA FINISH [-710]
ETCHED GLASS, WHITE INSIDE



ONE LIGHT WALL / BATH – CHROME FINISH [-05]
ETCHED GLASS, WHITE INSIDE

DAMP +

FOUR LIGHT WALL / BATH

W: 29" H: 8" E: 6.25"
Height from center of outlet box
up: 5.75" down: 2.25"

T24

4439104 (-05,-962,-710)
(4) Medium Base 100w max.

T24 EN★

4439104EN3 (-05,-962,-710)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

THREE LIGHT WALL / BATH

W: 20.5" H: 8" E: 6.25"
Height from center of outlet box
up: 5.75" down: 2.25"

T24

4439103 (-05,-962,-710)
(3) Medium Base 100w max.

T24 EN★

4439103EN3 (-05,-962,-710)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

TWO LIGHT WALL / BATH

W: 13.5" H: 8" E: 5.75"
Height from center of outlet box
up: 5.75" down: 2.25"

T24

4439102 (-05,-962,-710)
(2) Medium Base 100w max.

T24 EN★

4439102EN3 (-05,-962,-710)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

ONE LIGHT WALL / BATH

W: 4.5" H: 8" E: 5"
Height from center of outlet box
up: 5.75" down: 2.25"

T24

4139101 (-05,-962,-710)
(1) Medium Base 100w max.

T24 EN★

4139101EN3 (-05,-962,-710)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended
Product



OSLO INDOOR
Chrome,
Brushed Nickel,
Blacksmith
p.84



FOUR LIGHT WALL / BATH – CHROME FINISH [-05]
CASED OPAL ETCHED GLASS



THREE LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
CASED OPAL ETCHED GLASS



TWO LIGHT WALL / BATH – BLACKSMITH FINISH [-839]
CASED OPAL ETCHED GLASS



ONE LIGHT WALL / BATH – CHROME FINISH [-05]
CASED OPAL ETCHED GLASS

DAMP +

**FOUR LIGHT
WALL / BATH**

W: 27.5" H: 8.5" E: 5.5"
Height from center of outlet box
up: 6.25" down: 2.25"

T24

41163 (-05,-962,-839)
(4) Medium Base 100w max.

T24 EN★

41163EN3 (-05,-962,-839)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

**THREE LIGHT
WALL / BATH**

W: 20" H: 8.5" E: 5.5"
Height from center of outlet box
up: 6.25" down: 2.25"

T24

41162 (-05,-962,-839)
(3) Medium Base 100w max.

T24 EN★

41162EN3 (-05,-962,-839)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

**TWO LIGHT
WALL / BATH**

W: 12.5" H: 8.5" E: 5.5"
Height from center of outlet box
up: 6.25" down: 2.25"

T24

41161 (-05,-962,-839)
(2) Medium Base 100w max.

T24 EN★

41161EN3 (-05,-962,-839)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

**ONE LIGHT
WALL / BATH**

W: 4.75" H: 8.75" E: 5.5"
Height from center of outlet box
up: 4.75" down: 4"

T24

41160 (-05,-962,-839)
(1) Medium Base 100w max.


T24 EN★

41160EN3 (-05,-962,-839)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Product



STIRLING INDOOR
Brushed Nickel,
Burnt Sienna
p.290



FOUR LIGHT WALL / BATH – CHROME FINISH [-05]
CASED OPAL ETCHED GLASS



THREE LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
CASED OPAL ETCHED GLASS



TWO LIGHT WALL / BATH – BURNT SIENNA FINISH [-710]
CASED OPAL ETCHED GLASS



ONE LIGHT WALL / BATH – CHROME FINISH [-05]
CASED OPAL ETCHED GLASS

DAMP +

FOUR LIGHT WALL / BATH

W: 31" H: 11.25" E: 7"
Height from center of outlet box
up: 6.25" down: 5"

T24

44955 (-05,-962,-710)
(4) Medium Base 100w max.

T24 EN★

44955EN3 (-05,-962,-710)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT WALL / BATH

W: 22" H: 11.25" E: 7"
Height from center of outlet box
up: 6.25" down: 5"

T24

44954 (-05,-962,-710)
(3) Medium Base 100w max.

T24 EN★

44954EN3 (-05,-962,-710)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT WALL / BATH

W: 13" H: 11.25" E: 7"
Height from center of outlet box
up: 6.25" down: 5"

T24

44953 (-05,-962,-710)
(2) Medium Base 100w max.

T24 EN★

44953EN3 (-05,-962,-710)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH

W: 5.5" H: 11.25" E: 6.75"
Height from center of outlet box
up: 6.25" down: 5"

T24

44952 (-05,-962,-710)
(1) Medium Base 100w max.

T24 EN★

44952EN3 (-05,-962,-710)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Product



ENGLEHORN INDOOR
Chrome
p.184



FOUR LIGHT WALL / BATH



THREE LIGHT WALL / BATH



TWO LIGHT WALL / BATH



ONE LIGHT WALL / BATH

DAMP +

FOUR LIGHT WALL / BATH

W: 34.5" H: 12.75" E: 6"
Height from center of outlet box
up: 10.25" down: 2.5"

T24

4413404-05
(4) Medium Base 75w max.

T24 EN★

4413404EN3-05
(4) Med. Base LED 3000k,
9w, 800 lumen lamps incl.

DAMP +

THREE LIGHT WALL / BATH

W: 24.5" H: 11.75" E: 6"
Height from center of outlet box
up: 9.25" down: 2.5"

T24

4413403-05
(3) Medium Base 75w max.

T24 EN★

4413403EN3-05
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT WALL / BATH

W: 14.5" H: 12.75" E: 6"
Height from center of outlet box
up: 10.25" down: 2.5"

T24

4413402-05
(2) Medium Base 75w max.

T24 EN★

4413402EN3-05
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH

W: 5" H: 13" E: 7"
Height from center of outlet box
up: 10.5" down: 2.5"

T24

4113401-05
(1) Medium Base 75w max.

T24 EN★

4113401EN3-05
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Product



SFERA INDOOR
Mercury Glass,
Cafe Tint Glass
p.114



FOUR LIGHT WALL / BATH – AUTUMN BRONZE FINISH [-715]
SMOKY AMBER GLASS



THREE LIGHT WALL / BATH – AUTUMN BRONZE FINISH [-715]
MERCURY GLASS



TWO LIGHT WALL / BATH – AUTUMN BRONZE FINISH [-715]
SMOKY AMBER GLASS



ONE LIGHT WALL / BATH – AUTUMN BRONZE FINISH [-715]
MERCURY GLASS

DAMP +

FOUR LIGHT WALL / BATH

W: 34" H: 11" E: 6.75"
Height from center of outlet box
up: 8.5" down: 2.5"

T24

4410404-715 Mercury Glass
4491404-715 Smoky Amber Glass
(4) Medium Base 100w max.

T24 EN★

4410404EN3-715 Mercury Glass
4491404EN3-715 Smoky Amber Glass
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT WALL / BATH

W: 24" H: 11" E: 6.75"
Height from center of outlet box
up: 8.5" down: 2.5"

T24

4410403-715 Mercury Glass
4491403-715 Smoky Amber Glass
(3) Medium Base 100w max.

T24 EN★

4410403EN3-715 Mercury Glass
4491403EN3-715 Smoky Amber Glass
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT WALL / BATH

W: 14.25" H: 11" E: 6.5"
Height from center of outlet box
up: 8.5" down: 2.5"

T24

4410402-715 Mercury Glass
4491402-715 Smoky Amber Glass
(2) Medium Base 100w max.

T24 EN★

4410402EN3-715 Mercury Glass
4491402EN3-715 Smoky Amber Glass
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH

W: 5" H: 11" E: 6"
Height from center of outlet box
up: 8.5" down: 2.5"

T24

4110401-715 Mercury Glass
4191401-715 Smoky Amber Glass
(1) Medium Base 100w max.

T24 EN★

4110401EN3-715 Mercury Glass
4191401EN3-715 Smoky Amber Glass
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

CASUAL LUXURY

PRODUCT SHOWN: CASUAL LUXURY THREE LIGHT
WALL / BATH IN BRUSHED STEEL FINISH
DESIGNER: DAN RAK DESIGN



Recommended
ProductsCASUAL LUXURY
PENDANT
Brushed Steel
p.356CASUAL LUXURY
FLUSH MOUNT
Brushed Steel
p.372

FOUR LIGHT WALL / BATH



THREE LIGHT WALL / BATH



TWO LIGHT WALL / BATH



ONE LIGHT WALL SCONCE

DAMP**FOUR LIGHT
WALL / BATH**

L: 36" H: 6.75" E: 7.5"
Height from center of outlet box
up: 4.5"

VS13704-BS
(4) Halogen G9 Mini
75w max.Lamps incl.

DAMP**THREE LIGHT
WALL / BATH**

L: 26" H: 6.75" E: 7.5"
Height from center of outlet box
up: 4.5"

VS13703-BS
(3) Halogen G9 Mini
75w max.Lamps incl.

DAMP**TWO LIGHT
WALL / BATH**

L: 18.125" H: 6.75" E: 7.5"
Height from center of outlet box
up: 4.5"

VS13702-BS
(2) Halogen G9 Mini
75w max.Lamps incl.

DAMP**ONE LIGHT
WALL SCONCE**

L: 6" H: 11.25" E: 6.5"
Height from center of outlet box
up: 6.4375"

WB1378-BS
(1) Halogen G9 Mini
75w max. Lamp incl.

Recommended Product



CANFIELD INDOOR
Brushed Nickel,
Burnt Sienna
p.93



FOUR LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
ETCHED GLASS, WHITE INSIDE



THREE LIGHT WALL / BATH – BURNT SIENNA FINISH [-710]
ETCHED GLASS, WHITE INSIDE



TWO LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
ETCHED GLASS, WHITE INSIDE



ONE LIGHT WALL / BATH – BURNT SIENNA FINISH [-710]
ETCHED GLASS, WHITE INSIDE

DAMP +

FOUR LIGHT WALL / BATH

W: 31.875" H: 8.375" E: 7.25"
Height from center of outlet box
up: 5.75" down: 2.5"

T24

4428804 (-962,-710)
(4) Medium Base 100w max.

T24 EN★

4428804EN3 (-962,-710)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

THREE LIGHT WALL / BATH

W: 23.125" H: 8.375" E: 7.25"
Height from center of outlet box
up: 5.75" down: 2.5"

T24

4428803 (-962,-710)
(3) Medium Base 100w max.

T24 EN★

4428803EN3 (-962,-710)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

TWO LIGHT WALL / BATH

W: 14.25" H: 8.375" E: 7.25"
Height from center of outlet box
up: 5.75" down: 2.5"

T24

4428802 (-962,-710)
(2) Medium Base 100w max.

T24 EN★

4428802EN3 (-962,-710)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

ONE LIGHT WALL / BATH

W: 5.5" H: 8.25" E: 7.25"
Height from center of outlet box
up: 4.375" down: 3.875"

T24

4128801 (-962,-710)
(1) Medium Base 100w max.

T24 EN★

4128801EN3 (-962,-710)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Product



DRISCOLL INDOOR
Brushed Nickel,
Satin Bronze
p.74



FOUR LIGHT WALL / BATH – CHROME FINISH [-05]
ETCHED GLASS, WHITE INSIDE



THREE LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
ETCHED GLASS, WHITE INSIDE



TWO LIGHT WALL / BATH – SATIN BRONZE FINISH [-848]
ETCHED GLASS, WHITE INSIDE



ONE LIGHT WALL / BATH – CHROME FINISH [-05]
ETCHED GLASS, WHITE INSIDE

DAMP +

FOUR LIGHT WALL / BATH

W: 30.75" H: 12" E: 7"
Height from center of outlet box
up: 8.75" down: 3.25"

T24

4440404 (-05,-962,-848)
(4) Medium Base 100w max.

T24 EN★

4440404EN3 (-05,-962,-848)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT WALL / BATH

W: 24.5" H: 12" E: 7"
Height from center of outlet box
up: 8.75" down: 3.25"

T24

4440403 (-05,-962,-848)
(3) Medium Base 100w max.

T24 EN★

4440403EN3 (-05,-962,-848)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT WALL / BATH

W: 15.5" H: 12" E: 7"
Height from center of outlet box
up: 8.75" down: 3.25"

T24

4440402 (-05,-962,-848)
(2) Medium Base 100w max.

T24 EN★

4440402EN3 (-05,-962,-848)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP

ONE LIGHT WALL / BATH

W: 5.25" H: 11.75" E: 6.75"
Height from center of outlet box
up: 8.75"

T24

4140401 (-05,-962,-848)
(1) Medium Base 100w max.

T24 EN★

4140401EN3 (-05,-962,-848)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Product



FRANPORT INDOOR
Brushed Nickel,
Burnt Sienna
p.212



FOUR LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
ETCHED GLASS, WHITE INSIDE



THREE LIGHT WALL / BATH – BURNT SIENNA FINISH [-710]
ETCHED GLASS, WHITE INSIDE



TWO LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
ETCHED GLASS, WHITE INSIDE



ONE LIGHT WALL / BATH – BURNT SIENNA FINISH [-710]
ETCHED GLASS, WHITE INSIDE

DAMP +

FOUR LIGHT WALL / BATH

W: 29.375" H: 8.25" E: 6.25"
Height from center of outlet box
up: 5.75" down: 2.5"

T24

4428904 (-962,-710)
(4) Medium Base 100w max.

T24 EN★

4428904EN3 (-962,-710)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

THREE LIGHT WALL / BATH

W: 21" H: 8.25" E: 6.25"
Height from center of outlet box
up: 5.75" down: 2.5"

T24

4428903 (-962,-710)
(3) Medium Base 100w max.

T24 EN★

4428903EN3 (-962,-710)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

TWO LIGHT WALL / BATH

W: 13.25" H: 8.25" E: 6.25"
Height from center of outlet box
up: 5.75" down: 2.5"

T24

4428902 (-962,-710)
(2) Medium Base 100w max.

T24 EN★

4428902EN3 (-962,-710)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

ONE LIGHT WALL / BATH

W: 5" H: 8" E: 6.875"
Height from center of outlet box
up: 4" down: 4"

T24

4128901 (-962,-710)
(1) Medium Base 100w max.

T24 EN★

4128901EN3 (-962,-710)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



FOUR LIGHT WALL / BATH – CHROME FINISH [-05]
ETCHED GLASS, WHITE INSIDE



THREE LIGHT WALL / BATH – BURNT SIENNA FINISH [-710]
ETCHED GLASS, WHITE INSIDE



THREE LIGHT WALL / BATH – CHROME FINISH [-05]
ETCHED GLASS, WHITE INSIDE



ONE LIGHT WALL / BATH – BURNT SIENNA FINISH [-710]
ETCHED GLASS, WHITE INSIDE

DAMP +

FOUR LIGHT WALL / BATH

W: 29.375" H: 8.125" E: 6.25"
Height from center of outlet box
up: 5.75" down: 2.5"

T24

4423004 (-05,-710)
(4) Medium Base 100w max.

T24 EN★

4423004EN3 (-05,-710)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT WALL / BATH

W: 21" H: 8.125" E: 6.25"
Height from center of outlet box
up: 5.75" down: 2.5"

T24

4423003 (-05,-710)
(3) Medium Base 100w max.

T24 EN★

4423003EN3 (-05,-710)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT WALL / BATH

W: 13.25" H: 8.125" E: 6.25"
Height from center of outlet box
up: 5.75" down: 2.5"

T24

4423002 (-05,-710)
(2) Medium Base 100w max.

T24 EN★

4423002EN3 (-05,-710)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH

W: 5" H: 8" E: 6.875"
Height from center of outlet box
up: 4" down: 4"

T24

4123001 (-05,-710)
(1) Medium Base 100w max.

T24 EN★

4123001EN3 (-05,-710)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

PARKFIELD

PRODUCT SHOWN: PARKFIELD ONE LIGHT WALL / BATH IN BRUSHED NICKEL FINISH



Recommended Product



PARKFIELD INDOOR
Brushed Nickel,
Flemish Bronze
p.200



FOUR LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
ETCHED GLASS, WHITE INSIDE



THREE LIGHT WALL / BATH – FLEMISH BRONZE FINISH [-845]
CREME PARCHMENT GLASS



TWO LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
ETCHED GLASS, WHITE INSIDE



ONE LIGHT WALL / BATH – FLEMISH BRONZE FINISH [-845]
CREME PARCHMENT GLASS

DAMP +

FOUR LIGHT WALL / BATH

W: 30.75" H: 9.75" E: 6"
Height from center of outlet box
up: 7" down: 2.75"

T24

4413004 (-962,-845)
(4) Medium Base 75w max.

T24 EN★

4413004EN3 (-962,-845)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT WALL / BATH

W: 24" H: 9.75" E: 6"
Height from center of outlet box
up: 7" down: 2.75"

T24

4413003 (-962,-845)
(3) Medium Base 75w max.

T24 EN★

4413003EN3 (-962,-845)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT WALL / BATH

W: 14.75" H: 9.75" E: 6"
Height from center of outlet box
up: 7" down: 2.75"

T24

4413002 (-962,-845)
(2) Medium Base 75w max.

T24 EN★

4413002EN3 (-962,-845)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH

W: 5.5" H: 10" E: 6"
Height from center of outlet box
up: 7.25" down: 2.75"

T24

4113001 (-962,-845)
(1) Medium Base 75w max.

T24 EN★

4113001EN3 (-962,-845)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Product



FOUR LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
ETCHED GLASS, WHITE INSIDE



ELLIS HARPER
INDOOR
Brushed Nickel,
Oil Rubbed Bronze
p.206



THREE LIGHT WALL / BATH – BRUSHED OIL RUBBED BRONZE FINISH [-778]
ETCHED GLASS, WHITE INSIDE



THREE LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
ETCHED GLASS, WHITE INSIDE



ONE LIGHT WALL / BATH – BRUSHED OIL RUBBED BRONZE FINISH [-778]
ETCHED GLASS, WHITE INSIDE

DAMP +

FOUR LIGHT BATH

W: 32.5" H: 9.125" E: 6.625"
Height from center of outlet box
up: 7.625" down: 1.5"

T24

4413704 (-962,-778)
(4) Medium Base 75w max.

T24 EN★

4413704EN3 (-962,-778)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT BATH

W: 23.625" H: 9.125" E: 6.625"
Height from center of outlet box
up: 7.625" down: 1.5"

T24

4413703 (-962,-778)
(3) Medium Base 75w max.

T24 EN★

4413703EN3 (-962,-778)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT BATH

W: 16.125" H: 9.125" E: 6.625"
Height from center of outlet box
up: 7.625" down: 1.5"

T24

4413702 (-962,-778)
(2) Medium Base 75w max.

T24 EN★

4413702EN3 (-962,-778)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH SCONCE


W: 5.75" H: 10.125" E: 6.625"
Height from center of outlet box
up: 7.625" down: 2.5"

T24

4113701 (-962,-778)
(1) Medium Base 75w max.

T24 EN★

4113701EN3 (-962,-778)
(1) Med. Base LED 3000k,
9.5w Bulb lamps incl.



FOUR LIGHT WALL / BATH – CHROME FINISH [-05]
ETCHED GLASS, WHITE INSIDE



THREE LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
ETCHED GLASS, WHITE INSIDE



TWO LIGHT WALL / BATH – BURNT SIENNA FINISH [-710]
ETCHED GLASS, WHITE INSIDE



ONE LIGHT WALL / BATH – CHROME FINISH [-05]
ETCHED GLASS, WHITE INSIDE

DAMP +

FOUR LIGHT WALL / BATH

W: 31.75" H: 10" E: 7.5"
Height from center of outlet box
up: 7.5" down: 2.5"

T24

4450404 (-05,-962,-710)
(4) Medium Base 100w max.

T24 EN★

4450404EN3 (-05,-962,-710)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT WALL / BATH

W: 24.25" H: 10" E: 7.5"
Height from center of outlet box
up: 7.5" down: 2.5"

T24

4450403 (-05,-962,-710)
(3) Medium Base 100w max.

T24 EN★

4450403EN3 (-05,-962,-710)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT WALL / BATH

W: 16.5" H: 10" E: 7.5"
Height from center of outlet box
up: 7.5" down: 2.5"

T24

4450402 (-05,-962,-710)
(2) Medium Base 100w max.

T24 EN★

4450402EN3 (-05,-962,-710)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH

W: 5.75" H: 10" E: 7"
Height from center of outlet box
up: 7.5" down: 2.5"

T24

4150401 (-05,-962,-710)
(1) Medium Base 100w max.

T24 EN★

4150401EN3 (-05,-962,-710)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

BAYFIELD

PRODUCTS SHOWN: BAYFIELD ONE LIGHT WALL / BATH IN BRUSHED NICKEL FINISH





FOUR LIGHT WALL / BATH – CHROME FINISH [-05]
ETCHED GLASS, WHITE INSIDE



THREE LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
ETCHED GLASS, WHITE INSIDE



TWO LIGHT WALL / BATH – BURNT SIENNA FINISH [-710]
ETCHED GLASS, WHITE INSIDE



ONE LIGHT WALL / BATH – CHROME FINISH [-05]
ETCHED GLASS, WHITE INSIDE

DAMP +

FOUR LIGHT WALL / BATH

W: 27.5" H: 7.75" E: 6.75"
Height from center of outlet box
up: 5.5" down: 2.25"

T24

4411604 (-05,-962,-710)
(4) Medium Base 100w max.

T24 EN★

4411604EN3 (-05,-962,-710)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT WALL / BATH

W: 20" H: 7.75" E: 6.75"
Height from center of outlet box
up: 5.5" down: 2.25"

T24

4411603 (-05,-962,-710)
(3) Medium Base 100w max.

T24 EN★

4411603EN3 (-05,-962,-710)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT WALL / BATH

W: 13.25" H: 7.75" E: 6.75"
Height from center of outlet box
up: 5.5" down: 2.25"

T24

4411602 (-05,-962,-710)
(2) Medium Base 100w max.

T24 EN★

4411602EN3 (-05,-962,-710)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH

W: 5" H: 7.75" E: 6.25"
Height from center of outlet box
up: 4.5" down: 3.25"

T24

4111601 (-05,-962,-710)
(1) Medium Base 100w max.

T24 EN★

4111601EN3 (-05,-962,-710)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

SUNSET DRIVE

BRUSHED STEEL FINISH [-BS] / WHITE OPAL ETCHED GLASS



FOUR LIGHT WALL / BATH



THREE LIGHT WALL / BATH



TWO LIGHT WALL / BATH



ONE LIGHT WALL SCONCE

Recommended Products



SUNSET DRIVE
INDOOR
Brushed Steel,
Corinthian Bronze
p.106



SUNSET DRIVE
CEILING
Chrome,
Brushed Steel,
Corinthian Bronze,
Oil Rubbed Bronze
p.370

DAMP +

FOUR LIGHT WALL / BATH

L: 31.5" H: 8.625" E: 5.375"
Height from center of outlet box
up: 6.375" down: 2.25"

T24

VS14904-BS
(4) Medium Base 100w max.

DAMP +

THREE LIGHT WALL / BATH

L: 22.375" H: 8.625" E: 5.375"
Height from center of outlet box
up: 6.375" down: 2.25"

T24

VS14903-BS
(3) Medium Base 100w max.

DAMP +

TWO LIGHT WALL / BATH

L: 14" H: 8.625" E: 5.375"
Height from center of outlet box
up: 6.375" down: 2.25"

T24

VS14902-BS
(2) Medium Base 100w max.

DAMP +

ONE LIGHT WALL SCONCE

H: 10" W: 4.5" E: 5.75"
Height from center of outlet box
up: 5" down: 5"

T24

VS14901-BS
(1) Medium Base 100w max.



FIVE LIGHT WALL / BATH - CHROME FINISH [CH]
WHITE OPAL ETCHED GLASS



THREE LIGHT WALL / BATH - SATIN NICKEL FINISH [SN]
WHITE OPAL ETCHED GLASS



TWO LIGHT WALL / BATH - CHROME FINISH [CH]
WHITE OPAL ETCHED GLASS



ONE LIGHT WALL SCONCE - SATIN NICKEL FINISH [SN]
WHITE OPAL ETCHED GLASS

DAMP +

FIVE LIGHT WALL / BATH

W: 38" H: 9" E: 5.75"
Height from center of outlet box
up: 6.25" down: 2.75"

T24

VS23605 (CH,SN)
(5) Medium Base 75w max.

DAMP +

THREE LIGHT WALL / BATH

W: 21.25" H: 9" E: 5.75"
Height from center of outlet box
up: 6.5" down: 2.5"

T24

VS23603 (CH,SN)
(3) Medium Base 75w max.

DAMP +

TWO LIGHT WALL / BATH

W: 13" H: 9" E: 5.75"
Height from center of outlet box
up: 6.5" down: 2.5"

T24

VS23602 (CH,SN)
(2) Medium Base 75w max.

DAMP +

ONE LIGHT WALL SCONCE

W: 5" H: 9" E: 5.75"
Height from center of outlet box
up: 6.5" down: 2.5"

T24

VS23601 (CH,SN)
(1) Medium Base 75w max.

HANFORD

Recommended Product



HANFORD INDOOR
Brushed Nickel,
Burnt Sienna
p.224



FOUR LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
SATIN ETCHED GLASS



THREE LIGHT WALL / BATH – BURNT SIENNA FINISH [-710]
SATIN ETCHED GLASS



TWO LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
SATIN ETCHED GLASS



ONE LIGHT WALL / BATH – BURNT SIENNA FINISH [-710]
SATIN ETCHED GLASS

DAMP +

FOUR LIGHT WALL / BATH

W: 33.5" H: 11.25" E: 6.5"
Height from center of outlet box
up: 6" down: 5.25"

T24

4424504 (-962,-710)
(4) Medium Base 100w max.

T24 EN★

4424504EN3 (-962,-710)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT WALL / BATH

W: 24" H: 10.75" E: 6.5"
Height from center of outlet box
up: 6" down: 4.75"

T24

4424503 (-962,-710)
(3) Medium Base 100w max.

T24 EN★

4424503EN3 (-962,-710)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT WALL / BATH

W: 14.5" H: 9.75" E: 6.5"
Height from center of outlet box
up: 6" down: 3.75"

T24

4424502 (-962,-710)
(2) Medium Base 100w max.

T24 EN★

4424502EN3 (-962,-710)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH

W: 5.25" H: 10.25" E: 6.75"
Height from center of outlet box
up: 7.25" down: 3"

T24

4124501 (-962,-710)
(1) Medium Base 100w max.

T24 EN★

4124501EN3 (-962,-710)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Product



METCALF INDOOR
Brushed Nickel,
Autumn Bronze
p.254



FOUR LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
SATIN ETCHED GLASS



THREE LIGHT WALL / BATH – AUTUMN BRONZE FINISH [-715]
SATIN ETCHED GLASS



TWO LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
SATIN ETCHED GLASS



ONE LIGHT WALL / BATH – AUTUMN BRONZE FINISH [-715]
SATIN ETCHED GLASS

DAMP +

FOUR LIGHT WALL / BATH

W: 34.5" H: 11" E: 7.25"
Height from center of outlet box
up: 8.5" down: 2.5"

T24

4413204 (-962,-715)
(4) Medium Base 100w max.

T24 EN★

4413204EN3 (-962,-715)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT WALL / BATH

W: 25" H: 11" E: 7.25"
Height from center of outlet box
up: 8.5" down: 2.5"

T24

4413203 (-962,-715)
(3) Medium Base 100w max.

T24 EN★

4413203EN3 (-962,-715)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT WALL / BATH

W: 15.5" H: 11" E: 7.25"
Height from center of outlet box
up: 8.5" down: 2.5"

T24

4413202 (-962,-715)
(2) Medium Base 100w max.

T24 EN★

4413202EN3 (-962,-715)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH

W: 6.25" H: 10.75" E: 7.25"
Height from center of outlet box
up: 8.25" down: 2.5"

T24

4113201 (-962,-715)
(1) Medium Base 100w max.

T24 EN★

4113201EN3 (-962,-715)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Products



VINTNER INDOOR
Satin Nickel,
Heritage Bronze
p.236



VINTNER CEILING
Satin Nickel,
Heritage Bronze
p.373



FOUR LIGHT WALL / BATH – SATIN NICKEL FINISH [-SN]
OPAL ETCHED GLASS



THREE LIGHT WALL / BATH – HERITAGE BRONZE FINISH [-HTBZ]
OPAL ETCHED GLASS



TWO LIGHT WALL / BATH – SATIN NICKEL FINISH [-SN]
OPAL ETCHED GLASS



ONE LIGHT SCONCE – HERITAGE BRONZE FINISH [-HTBZ]
OPAL ETCHED GLASS

DAMP +

FOUR LIGHT WALL / BATH

W: 34.375" H: 8.875" E: 5.75"
Height from center of outlet box
up: 6.125" down: 2.75"

T24

VS20104 (SN, HTBZ)
(4) Medium Base 75w max.

DAMP +

THREE LIGHT WALL / BATH

W: 23" H: 8.75" E: 5.75"
Height from center of outlet box
up: 6" down: 2.75"

T24

VS20103 (SN, HTBZ)
(3) Medium Base 75w max.

DAMP +

TWO LIGHT WALL / BATH

W: 15.375" H: 9.125" E: 5.625"
Height from center of outlet box
up: 6.375" down: 2.75"

T24

VS20102 (SN, HTBZ)
(2) Medium Base 75w max.

DAMP +

ONE LIGHT SCONCE

W: 5.5" H: 9" E: 6.625"
Height from center of outlet box
up: 3.5" down: 5.625"

T24

VS20101 (SN, HTBZ)
(1) Medium Base 75w max.

Recommended Product



BANNOCK INDOOR
Brushed Nickel,
Heirloom Bronze
p.272



FOUR LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
SATIN ETCHED GLASS



THREE LIGHT WALL / BATH – HEIRLOOM BRONZE FINISH [-782]
SATIN ETCHED GLASS



TWO LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
SATIN ETCHED GLASS



ONE LIGHT WALL / BATH – HEIRLOOM BRONZE FINISH [-782]
SATIN ETCHED GLASS

DAMP +

FOUR LIGHT WALL / BATH

W: 29" H: 8.75" E: 6.25"
Height from center of outlet box
up: 6.25" down: 2.5"

T24

4416604 (-962,-782)
(4) Medium Base 75w max.

T24 EN★

4416604EN3 (-962,-782)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT WALL / BATH

W: 21" H: 8.75" E: 6.25"
Height from center of outlet box
up: 6.25" down: 2.5"

T24

4416603 (-962,-782)
(3) Medium Base 75w max.

T24 EN★

4416603EN3 (-962,-782)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT WALL / BATH

W: 13.25" H: 8.75" E: 6.25"
Height from center of outlet box
up: 6.25" down: 2.5"

T24

4416602 (-962,-782)
(2) Medium Base 75w max.

T24 EN★

4416602EN3 (-962,-782)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH

W: 5" H: 8.75" E: 7.25"
Height from center of outlet box
up: 6.25" down: 2.5"

T24

4116601 (-962,-782)
(1) Medium Base 75w max.

T24 EN★

4116601EN3 (-962,-782)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Product



BELTON INDOOR
Brushed Nickel,
Heirloom Bronze
p.152



FOUR LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
CLEAR SEEDED GLASS



THREE LIGHT WALL / BATH – HEIRLOOM BRONZE FINISH [-782]
CLEAR SEEDED GLASS



TWO LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
CLEAR SEEDED GLASS



ONE LIGHT WALL / BATH – HEIRLOOM BRONZE FINISH [-782]
CLEAR SEEDED GLASS

DAMP +

**FOUR LIGHT
WALL / BATH**

W: 28.75" H: 10.75" E: 6.75"
Height from center of outlet box
up: 8.5" down: 2.25"

T24

4414504 (-962,-782)
(4) Medium Base 60w max.

DAMP +

**THREE LIGHT
WALL / BATH**

W: 21" H: 10.75" E: 6.75"
Height from center of outlet box
up: 8.5" down: 2.25"

T24

4414503 (-962,-782)
(3) Medium Base 60w max.

DAMP +

**TWO LIGHT
WALL / BATH**

W: 15" H: 10.75" E: 6.75"
Height from center of outlet box
up: 8.5" down: 2.25"

T24

4414502 (-962,-782)
(2) Medium Base 60w max.

DAMP +

**ONE LIGHT
WALL / BATH**

W: 5.5" H: 9.75" E: 6.75"
Height from center of outlet box
up: 5.5" down: 4.25"

T24

4114501 (-962,-782)
(1) Medium Base 60w max.

Recommended Product



MORILL INDOOR
Blacksmith
p.142



FOUR LIGHT WALL / BATH



THREE LIGHT WALL / BATH



TWO LIGHT WALL / BATH



ONE LIGHT WALL / BATH

DAMP

FOUR LIGHT WALL / BATH

W: 28.5" H: 8.25" E: 7.75"
Height from center of outlet box up: 3.75"

T24

4427804-839
(4) Medium Base 60w max.

DAMP

THREE LIGHT WALL / BATH

W: 20.5" H: 8.25" E: 7.75"
Height from center of outlet box up: 3.75"

T24

4427803-839
(3) Medium Base 60w max.

DAMP

TWO LIGHT WALL / BATH

W: 13.25" H: 8.25" E: 7.75"
Height from center of outlet box up: 3.75"

T24

4427802-839
(2) Medium Base 60w max.

DAMP

ONE LIGHT WALL / BATH

W: 5" H: 8.25" E: 7.25"
Height from center of outlet box up: 3.75"

T24

4127801-839
(1) Medium Base 60w max.

Recommended Product



HOLMAN INDOOR
Brushed Nickel,
Heirloom Bronze
p.278



FOUR LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
SATIN ETCHED GLASS



THREE LIGHT WALL / BATH – HEIRLOOM BRONZE FINISH [-782]
SATIN ETCHED GLASS



TWO LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
SATIN ETCHED GLASS



ONE LIGHT WALL / BATH – HEIRLOOM BRONZE FINISH [-782]
SATIN ETCHED GLASS

DAMP +

**FOUR LIGHT
WALL / BATH**

W: 24.5" H: 9" E: 7.25"
Height from center of outlet box
up: 6.5" down: 2.5"

T24

44808 (-962,-782)
(4) Medium Base 60w max.

T24 EN★

44808EN3 (-962,-782)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

**THREE LIGHT
WALL / BATH**

W: 18" H: 9" E: 7.25"
Height from center of outlet box
up: 6.5" down: 2.5"

T24

44807 (-962,-782)
(3) Medium Base 60w max.

T24 EN★

44807EN3 (-962,-782)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

**TWO LIGHT
WALL / BATH**

W: 11.75" H: 9" E: 7.25"
Height from center of outlet box
up: 6.5" down: 2.5"

T24

44806 (-962,-782)
(2) Medium Base 60w max.

T24 EN★

44806EN3 (-962,-782)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

**ONE LIGHT
WALL / BATH**

W: 5.25" H: 10.25" E: 7.25"
Height from center of outlet box
up: 6.5" down: 3.75"

T24

41806 (-962,-782)
(1) Medium Base 60w max.

T24 EN★

41806EN3 (-962,-782)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Products



EMMONS INDOOR
Brushed Nickel,
Heirloom Bronze
p.242



FOUR LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
SATIN ETCHED GLASS



THREE LIGHT WALL / BATH – HEIRLOOM BRONZE FINISH [-782]
SATIN ETCHED GLASS



TWO LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
SATIN ETCHED GLASS



ONE LIGHT WALL / BATH – HEIRLOOM BRONZE FINISH [-782]
SATIN ETCHED GLASS

DAMP +

FOUR LIGHT WALL / BATH

W: 32" H: 6.25" E: 7.5"
Height from center of outlet box
up: 3.75" down: 2.5"

T24

4439004 (-962,-782)
(4) Medium Base 100w max.

T24 EN★

4439004EN3 (-962,-782)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT WALL / BATH

W: 23.25" H: 6.25" E: 7.5"
Height from center of outlet box
up: 3.75" down: 2.5"

T24

4439003 (-962,-782)
(3) Medium Base 100w max.

T24 EN★

4439003EN3 (-962,-782)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT WALL / BATH

W: 14.75" H: 6.25" E: 7.5"
Height from center of outlet box
up: 3.75" down: 2.5"

T24

4439002 (-962,-782)
(2) Medium Base 100w max.

T24 EN★

4439002EN3 (-962,-782)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH

W: 6" H: 6.25" E: 7.5"
Height from center of outlet box
up: 3.75" down: 2.5"

T24

4139001 (-962,-782)
(1) Medium Base 100w max.

T24 EN★

4139001EN3 (-962,-782)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

SUSSEX

PRODUCT SHOWN: SUSSEX TWO LIGHT WALL / BATH IN CHROME



Recommended Products



SUSSEX INDOOR
Brushed Nickel,
Heirloom Bronze
p.218



FOUR LIGHT WALL / BATH – CHROME FINISH [-05]
SATIN WHITE GLASS



THREE LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
SATIN WHITE GLASS



TWO LIGHT WALL / BATH – HEIRLOOM BRONZE FINISH [-782]
SATIN ETCHED GLASS



ONE LIGHT WALL / BATH – CHROME FINISH [-05]
SATIN WHITE GLASS

DAMP +

FOUR LIGHT WALL / BATH

W: 32.25" H: 10.25" E: 10.25"
Height from center of outlet box
up: 7" down: 3.25"

T24

44063-05 Satin White Glass
44063-962 Satin White Glass
44063-782 Satin Etched Glass
(4) Medium Base 100w max.

T24 EN★

44063EN3-05 Satin White Glass
44063EN3-962 Satin White Glass
44063EN3-782 Satin Etched Glass
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT WALL / BATH

W: 24" H: 10.25" E: 10.25"
Height from center of outlet box
up: 7" down: 3.25"

T24

44062-05 Satin White Glass
44062-962 Satin White Glass
44062-782 Satin Etched Glass
(3) Medium Base 100w max.

T24 EN★

44062EN3-05 Satin White Glass
44062EN3-962 Satin White Glass
44062EN3-782 Satin Etched Glass
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT WALL / BATH

W: 18" H: 10.25" E: 10.25"
Height from center of outlet box
up: 7" down: 3.25"

T24

44061-05 Satin White Glass
44061-962 Satin White Glass
44061-782 Satin Etched Glass
(2) Medium Base 100w max.

T24 EN★

44061EN3-05 Satin White Glass
44061EN3-962 Satin White Glass
44061EN3-782 Satin Etched Glass
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH

W: 7.5" H: 10.25" E: 10.25"
Height from center of outlet box
up: 7" down: 3.25"

T24

44060-05 Satin White Glass
44060-962 Satin White Glass
44060-782 Satin Etched Glass
(1) Medium Base 100w max.

T24 EN★

44060EN3-05 Satin White Glass
44060EN3-962 Satin White Glass
44060EN3-782 Satin Etched Glass
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

MONTREAL

Recommended Product



MONTREAL PENDANT
Antique Brushed Nickel,
Burnt Sienna
p.354



FOUR LIGHT WALL / BATH – ANTIQUE BRUSHED NICKEL FINISH [-965]
ETCHED GLASS, WHITE INSIDE



THREE LIGHT WALL / BATH – BURNT SIENNA FINISH [-710]
CAFE TINT GLASS



TWO LIGHT WALL / BATH – ANTIQUE BRUSHED NICKEL FINISH [-965]
ETCHED GLASS, WHITE INSIDE



ONE LIGHT WALL / BATH – BURNT SIENNA FINISH [-710]
CAFE TINT GLASS

DAMP +

FOUR LIGHT WALL / BATH

W: 36.75" H: 8.25" E: 9.75"
Height from center of outlet box
up: 5.25" down: 3"

T24

41183 (-965,-710)
(4) Medium Base 100w max.

T24 EN★

41183EN3 (-965,-710)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT WALL / BATH

W: 27" H: 8.25" E: 9.75"
Height from center of outlet box
up: 5.25" down: 3"

T24

41182 (-965,-710)
(3) Medium Base 100w max.

T24 EN★

41182EN3 (-965,-710)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT WALL / BATH

W: 17.5" H: 8.25" E: 9.75"
Height from center of outlet box
up: 5.25" down: 3"

T24

41181 (-965,-710)
(2) Medium Base 100w max.

T24 EN★

41181EN3 (-965,-710)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH

W: 7.75" H: 8.5" E: 9.75"
Height from center of outlet box
up: 4" down: 4.5"

T24

41180 (-965,-710)
(1) Medium Base 100w max.

T24 EN★

41180EN3 (-965,-710)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Products



ACADEMY PENDANT
Chrome,
Brushed Nickel,
Heirloom Bronze
p.352



ACADEMY CEILING
Chrome,
Brushed Nickel,
Heirloom Bronze
p.372



FOUR LIGHT WALL / BATH – CHROME FINISH [-05]
ETCHED GLASS, WHITE INSIDE



THREE LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
ETCHED GLASS, WHITE INSIDE



TWO LIGHT WALL / BATH – HEIRLOOM BRONZE [-782]
ETCHED GLASS, WHITE INSIDE



ONE LIGHT WALL / BATH – CHROME FINISH [-05]
ETCHED GLASS, WHITE INSIDE

DAMP

FOUR LIGHT WALL / BATH

W: 31.5" H: 10" E: 10"
Height from center of outlet box up: 3"

T24

44439 (-05,-962,-782)
(4) Medium Base 60w max.

T24 EN★

44439EN3 (-05,-962,-782)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP

THREE LIGHT WALL / BATH

W: 23.25" H: 10" E: 10"
Height from center of outlet box up: 3"

T24

44438 (-05,-962,-782)
(3) Medium Base 60w max.

T24 EN★

44438EN3 (-05,-962,-782)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP

TWO LIGHT WALL / BATH

W: 17.25" H: 10" E: 10"
Height from center of outlet box up: 3"

T24

44437 (-05,-962,-782)
(2) Medium Base 60w max.

T24 EN★

44437EN3 (-05,-962,-782)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP

ONE LIGHT WALL / BATH

W: 6.75" H: 10" E: 10"
Height from center of outlet box up: 3"

T24

44436 (-05,-962,-782)
(1) Medium Base 60w max.

T24 EN★

44436EN3 (-05,-962,-782)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.



DAMP +

**FOUR LIGHT
WALL / BATH**

W: 25.5" H: 10.5" E: 8.25"
Height from center of outlet box
up: 7.75" down: 2.75"

T24

40126-05
(4) Medium Base 100w max.

T24 EN★

40126EN3-05
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.



DAMP +

**THREE LIGHT
WALL / BATH**

W: 18.75" H: 10.5" E: 8.25"
Height from center of outlet box
up: 7.75" down: 2.75"

T24

40125-05
(3) Medium Base 100w max.

T24 EN★

40125EN3-05
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.



DAMP +

**TWO LIGHT
WALL / BATH**

W: 13.25" H: 10.5" E: 8.25"
Height from center of outlet box
up: 7.75" down: 2.75"

T24

40124-05
(2) Medium Base 100w max.

T24 EN★

40124EN3-305
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.



DAMP +

**FOUR LIGHT
WALL / BATH**

W: 24.75" H: 7.75" E: 8.25"
Height from center of outlet box
up: 3.5" down: 4.25"

T24

40012-773

(4) Medium Base 100w max.

T24 EN★

40012EN3-05

(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.



DAMP +

**THREE LIGHT
WALL / BATH**

W: 18.25" H: 7.75" E: 7.5"
Height from center of outlet box
up: 3.5" down: 4.25"

T24

40011-773

(3) Medium Base 100w max.

T24 EN★

40011EN3-773

(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.



DAMP +

**TWO LIGHT
WALL / BATH**

W: 13" H: 7.75" E: 7.5"
Height from center of outlet box
up: 3.5" down: 4.25"

T24

40010-773

(2) Medium Base 100w max.

T24 EN★

40010EN3-773

(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

WESTMONT

BRUSHED NICKEL FINISH [-962] / SATIN WHITE GLASS



DAMP

FOUR LIGHT WALL / BATH

W: 23.5" H: 8" E: 8.25"
Height from center of outlet box down: 2.75"

T24

44021-962
(4) Medium Base 100w max.

T24 EN★

44021EN3-962
(4) Med. Base LED 3000k, 9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT WALL / BATH

W: 17" H: 8.25" E: 8.5"
Height from center of outlet box down: 3"

T24

44020-962
(3) Medium Base 100w max.

T24 EN★

44020EN3-962
(3) Med. Base LED 3000k, 9.5w, 800 lumen lamps incl.



DAMP

TWO LIGHT WALL / BATH

W: 12" H: 8.25" E: 7.5"
Height from center of outlet box down: 2.75"

T24

44019-962
(2) Medium Base 100w max.

T24 EN★

44019EN3-962
(2) Med. Base LED 3000k, 9.5w, 800 lumen lamps incl.

BROOKCHESTER

CHROME FINISH [-05] / CLEAR RIBBED GLASS



DAMP

FOUR LIGHT WALL / BATH

W: 23.5" H: 8.25" E: 8"
Height from center of outlet box down: 3"

T24

4873-05
(4) Medium Base 100w max.

T24 EN★

4873EN3-05
(4) Med. Base LED 3000k, 9.5w, 800 lumen lamps incl.



DAMP

THREE LIGHT WALL / BATH

W: 17" H: 8" E: 8.5"
Height from center of outlet box down: 3"

T24

4872-05
(3) Medium Base 100w max.

T24 EN★

4872EN3-05
(3) Med. Base LED 3000k, 9.5w, 800 lumen lamps incl.



DAMP

TWO LIGHT WALL / BATH

W: 12" H: 8.25" E: 7.5"
Height from center of outlet box down: 3"

T24

4871-05
(2) Medium Base 100w max.

T24 EN★

4871EN3-05
(2) Med. Base LED 3000k, 9.5w, 800 lumen lamps incl.

Recommended Products



BARRINGTON INDOOR
Brushed Steel,
Oil Rubbed Bronze
p.248



BARRINGTON SCONCE
Brushed Steel,
Oil Rubbed Bronze
p.447



FOUR LIGHT WALL / BATH - BRUSHED STEEL FINISH [-BS]
WHITE OPAL ETCHED GLASS



THREE LIGHT WALL / BATH - OIL RUBBED BRONZE FINISH [-ORB]
WHITE OPAL ETCHED GLASS



TWO LIGHT WALL / BATH - BRUSHED STEEL FINISH [-BS]
WHITE OPAL ETCHED GLASS



ONE LIGHT WALL SCONCE - OIL RUBBED BRONZE FINISH [-ORB]
WHITE OPAL ETCHED GLASS

DAMP +

FOUR LIGHT WALL / BATH

L: 37" H: 8.5" E: 6.5"
Height from center of outlet box
up: 3.125" down: 5.375"

T24

VS12704 (-BS,-ORB)
(4) Medium Base 100w max.

DAMP +

THREE LIGHT WALL / BATH

L: 24" H: 8.5" E: 6.5"
Height from center of outlet box
up: 3.125" down: 5.375"

T24

VS12703 (-BS,-ORB)
(3) Medium Base 100w max.

DAMP +

TWO LIGHT WALL / BATH

L: 18" H: 8.5" E: 6.5"
Height from center of outlet box
up: 3.125" down: 5.375"

T24

VS12702 (-BS,-ORB)
(2) Medium Base 100w max.

DAMP

ONE LIGHT WALL SCONCE

W:5" H: 16" E: 6.75"
Height from center of outlet box
up: 4.5"

T24

VS12701 (-BS,-ORB)
(1) Medium Base 100w max.

SEVILLE



FIVE LIGHT WALL / BATH – CHROME FINISH [-05]
ETCHED GLASS, WHITE INSIDE



FOUR LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
ETCHED GLASS, WHITE INSIDE

DAMP +

FIVE LIGHT WALL / BATH

W: 35.875" H: 8.5" E: 6.625"
Height from center of outlet box
up: 3.375" down: 5.125"

T24

4420205 (-05,-962,-710)
(5) Medium Base 75w max.

T24 EN★

4420205EN3 (-05,-962,-710)
(5) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

FOUR LIGHT WALL / BATH

W: 28.375" H: 8.5" E: 6.625"
Height from center of outlet box
up: 3.375" down: 5.125"

T24

4420204 (-05,-962,-710)
(4) Medium Base 75w max.

T24 EN★

4420204EN3 (-05,-962,-710)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Product



SEVILLE INDOOR
Brushed Nickel,
Burnt Sienna
p.260



THREE LIGHT WALL / BATH – BURNT SIENNA FINISH [-710]
ETCHED GLASS, WHITE INSIDE



TWO LIGHT WALL / BATH – CHROME FINISH [-05]
ETCHED GLASS, WHITE INSIDE



ONE LIGHT WALL / BATH - BRUSHED NICKEL FINISH [-962]
ETCHED GLASS, WHITE INSIDE

DAMP +

THREE LIGHT WALL / BATH

W: 21" H: 8.5" E: 6.625"
Height from center of outlet box
up: 3.375" down: 5.125"

T24

4420203 (-05,-962,-710)
(3) Medium Base 75w max.

T24 EN★

4420203EN3 (-05,-962,-710)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

TWO LIGHT WALL / BATH

W: 13.5" H: 8.5" E: 6.625"
Height from center of outlet box
up: 3.375" down: 5.125"

T24

4420202 (-05,-962,-710)
(2) Medium Base 75w max.

T24 EN★

4420202EN3 (-05,-962,-710)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

ONE LIGHT WALL / BATH

W: 4.75" H: 8.5" E: 6.625"
Height from center of outlet box
up: 3.375" down: 5.125"

T24

4120201 (-05,-962,-710)
(1) Medium Base 75w max.

T24 EN★

4120201EN3 (-05,-962,-710)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Product



KERRVILLE INDOOR
Chrome,
Brushed Nickel,
Heirloom Bronze
p.98



FOUR LIGHT WALL / BATH – CHROME FINISH [-05]
SATIN ETCHED GLASS



THREE LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
SATIN ETCHED GLASS



TWO LIGHT WALL / BATH – HEIRLOOM BRONZE FINISH [-782]
SATIN ETCHED GLASS



ONE LIGHT WALL / BATH – CHROME FINISH [-05]
SATIN ETCHED GLASS

DAMP +

FOUR LIGHT WALL / BATH

W: 24.75" H: 9" E: 6.75"
Height from center of outlet box
up: 6.75" down: 2.25"

T24

4415204 (-05,-962,-782)
(4) Medium Base 100w max.

T24 EN★

4415204EN3 (-05,-962,-782)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

THREE LIGHT WALL / BATH

W: 18" H: 9" E: 6.75"
Height from center of outlet box
up: 6.75" down: 2.25"

T24

4415203 (-05,-962,-782)
(3) Medium Base 100w max.

T24 EN★

4415203EN3 (-05,-962,-782)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

TWO LIGHT WALL / BATH

W: 12" H: 9" E: 6.75"
Height from center of outlet box
up: 6.75" down: 2.25"

T24

4415202 (-05,-962,-782)
(2) Medium Base 100w max.

T24 EN★

4415202EN3 (-05,-962,-782)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

ONE LIGHT WALL / BATH

W: 4.75" H: 9.75" E: 6.75"
Height from center of outlet box
up: 5.75" down: 4"

T24

4415201 (-05,-962,-782)
(1) Medium Base 100w max.

T24 EN★

4415201EN3 (-05,-962,-782)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Products



WINNETKA INDOOR
Brushed Nickel,
Blacksmith
p.78



WINNETKA
OUTDOOR
Blacksmith
p.542



FOUR LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
SATIN ETCHED GLASS



THREE LIGHT WALL / BATH – BLACKSMITH FINISH [-839]
SATIN ETCHED GLASS



TWO LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
SATIN ETCHED GLASS



ONE LIGHT WALL / BATH – BLACKSMITH FINISH [-839]
SATIN ETCHED GLASS

DAMP +

FOUR LIGHT WALL / BATH

W: 32" H: 9.25" E: 8.5"
Height from center of outlet box
up: 4" down: 5.25"

T24

44663 (-962,-839)
(4) Medium Base 100w max.

T24 EN★

44663EN3 (-962,-839)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

THREE LIGHT WALL / BATH

W: 23" H: 9.25" E: 8.5"
Height from center of outlet box
up: 4" down: 5.25"

T24

44662 (-962,-839)
(3) Medium Base 100w max.

T24 EN★

44662EN3 (-962,-839)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

TWO LIGHT WALL / BATH

W: 14" H: 9.25" E: 8.5"
Height from center of outlet box
up: 4" down: 5.25"

T24

44661 (-962,-839)
(2) Medium Base 100w max.

T24 EN★

44661EN3 (-962,-839)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP +

ONE LIGHT WALL / BATH

W: 6" H: 9.25" E: 7.5"
Height from center of outlet box
up: 4" down: 5.25"

T24

44660 (-962,-839)
(1) Medium Base 100w max.

T24 EN★

44660EN3 (-962,-839)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Products



DUNNING INDOOR
Stardust
p.112



LONOKE
PENDANTS
Stardust
p.326



FOUR LIGHT WALL / BATH



THREE LIGHT WALL / BATH



TWO LIGHT WALL / BATH



ONE LIGHT WALL / BATH

DAMP +

FOUR LIGHT WALL / BATH

W: 26.25" H: 8.25" E: 6"
Height from center of outlet box
up: 5.75" down: 2.5"

T24

4413304-846
(4) Medium Base 100w max.

T24 EN★

4413304EN3-846
(4) Med. Base LED 3000k,
9w, 800 lumen lamps incl.

DAMP +

THREE LIGHT WALL / BATH

W: 21" H: 8.25" E: 6"
Height from center of outlet box
up: 5.75" down: 2.5"

T24

4413303-846
(3) Medium Base 100w max.

T24 EN★

4413303EN3-846
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT WALL / BATH

W: 14" H: 8.25" E: 6"
Height from center of outlet box
up: 5.75" down: 2.5"

T24

4413302-846
(2) Medium Base 100w max.

T24 EN★

4413302EN3-846
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH

W: 5" H: 8.25" E: 6"
Height from center of outlet box
up: 5.75" down: 2.5"

T24

4113301-846
(1) Medium Base 100w max.

T24 EN★

4113301EN3-846
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Product



ELSA INDOOR
Heirloom Bronze
p.146



FOUR LIGHT WALL / BATH



THREE LIGHT WALL / BATH



TWO LIGHT WALL / BATH



ONE LIGHT WALL / BATH

DAMP +

FOUR LIGHT WALL / BATH

W: 33" H: 9.25" E: 7.875"
Height from center of outlet box
up: 4.75" down: 4.5"

T24

4420304-782
(4) Medium Base 75w max.

DAMP +

THREE LIGHT WALL / BATH

W: 24" H: 9.25" E: 7.875"
Height from center of outlet box
up: 4.75" down: 4.5"

T24

4420303-782
(3) Medium Base 75w max.

DAMP +

TWO LIGHT WALL / BATH

W: 10" H: 9.25" E: 7.875"
Height from center of outlet box
up: 4.75" down: 4.5"

T24

4420302-782
(2) Medium Base 75w max.

DAMP +

ONE LIGHT WALL / BATH

W: 6" H: 9.25" E: 7.875"
Height from center of outlet box
up: 4.75" down: 4.5"

T24

4120301-782
(1) Medium Base 75w max.



SIX LIGHT WALL / BATH – CHROME FINISH [-05]
SATIN ETCHED GLASS



FIVE LIGHT WALL / BATH – ANTIQUE BRUSHED NICKEL FINISH [-965]
SATIN ETCHED GLASS



FOUR LIGHT WALL / BATH – HEIRLOOM BRONZE FINISH [-782]
SMOKY AMBER GLASS

DAMP +

SIX LIGHT WALL / BATH

W: 50" H: 9" E: 8.5"
Height from center of outlet box
up: 4.5" down: 4.5"

T24

44855 (-05,-965,-782)
(6) Medium Base 100w max.

T24 EN★

44855EN3 (-05,-965,-782)
(6) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

FIVE LIGHT WALL / BATH

W: 41.25" H: 9" E: 8.5"
Height from center of outlet box
up: 4.5" down: 4.5"

T24

44854 (-05,-965,-782)
(5) Medium Base 100w max.

T24 EN★

44854EN3 (-05,-965,-782)
(5) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

FOUR LIGHT WALL / BATH

W: 32.5" H: 9" E: 8.5"
Height from center of outlet box
up: 4.5" down: 4.5"

T24

44853 (-05,-965,-782)
(4) Medium Base 100w max.

T24 EN★

44853EN3 (-05,-965,-782)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.



THREE LIGHT WALL / BATH – CHROME FINISH [-05]
SATIN ETCHED GLASS



TWO LIGHT WALL / BATH – ANTIQUE BRUSHED NICKEL FINISH [-965]
SATIN ETCHED GLASS



ONE LIGHT WALL / BATH – HEIRLOOM BRONZE FINISH [-782]
SMOKY AMBER GLASS

DAMP +

**THREE LIGHT
WALL / BATH**

W: 24" H: 9" E: 8.5"
Height from center of outlet box
up: 4.5" down: 4.5"

T24

44852 (-05,-965,-782)
(3) Medium Base 100w max.

T24 EN★

44852EN3 (-05,-965,-782)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

**TWO LIGHT
WALL / BATH**

W: 15.25" H: 9" E: 8.5"
Height from center of outlet box
up: 4.5" down: 4.5"

T24

44851 (-05,-965,-782)
(2) Medium Base 100w max.

T24 EN★

44851EN3 (-05,-965,-782)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

**ONE LIGHT
WALL / BATH**

W: 6.5" H: 9" E: 8.5"
Height from center of outlet box
up: 4.5" down: 4.5"

T24

44850 (-05,-965,-782)
(1) Medium Base 100w max.

T24 EN★

44850EN3 (-05,-965,-782)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Product



WHEATON INDOOR
Brushed Nickel,
Heirloom Bronze
p.284



FOUR LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
SATIN ETCHED GLASS



THREE LIGHT WALL / BATH – HEIRLOOM BRONZE FINISH [-782]
SATIN ETCHED GLASS



TWO LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
SATIN ETCHED GLASS



ONE LIGHT WALL / BATH – HEIRLOOM BRONZE FINISH [-782]
SATIN ETCHED GLASS

DAMP +

FOUR LIGHT WALL / BATH

W: 32.5" H: 7.75" E: 8.25"
Height from center of outlet box
up: 3.75" down: 4"

T24

44628 (-962,-782)
(4) Medium Base 100w max.

T24 EN★

44628EN3 (-962,-782)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT WALL / BATH

W: 23.75" H: 7.75" E: 8.25"
Height from center of outlet box
up: 3.75" down: 4"

T24

44627 (-962,-782)
(3) Medium Base 100w max.

T24 EN★

44627EN3 (-962,-782)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT WALL / BATH

W: 15.25" H: 7.75" E: 8.25"
Height from center of outlet box
up: 3.75" down: 4"

T24

44626 (-962,-782)
(2) Medium Base 100w max.

T24 EN★

44626EN3 (-962,-782)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH

W: 6.5" H: 7.75" E: 8.25"
Height from center of outlet box
up: 3.75" down: 4"

T24

44625 (-962,-782)
(1) Medium Base 100w max.

T24 EN★

44625EN3 (-962,-782)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Products



WINDGATE INDOOR
Chrome,
Brushed Nickel,
Heirloom Bronze
p.266



WINDGATE CEILING
FLUSH MOUNT
Chrome,
Brushed Nickel,
Heirloom Bronze
p.365



FOUR LIGHT WALL / BATH – CHROME FINISH [-05]
ALABASTER GLASS



THREE LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]
ALABASTER GLASS



TWO LIGHT WALL / BATH – HEIRLOOM BRONZE FINISH [-782]
ALABASTER GLASS



ONE LIGHT WALL / BATH – CHROME FINISH [-05]
ALABASTER GLASS

DAMP +

FOUR LIGHT WALL / BATH

W: 30.25" H: 8.25" E: 8"
Height from center of outlet box
up: 3.25" down: 5"

T24

44942 (-05,-962,-782)
(4) Medium Base 100w max.

T24 EN★

44942EN3 (-05,-962,-782)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

THREE LIGHT WALL / BATH

W: 24.25" H: 8.25" E: 8"
Height from center of outlet box
up: 3.25" down: 5"

T24

44941 (-05,-962,-782)
(3) Medium Base 100w max.

T24 EN★

44941EN3 (-05,-962,-782)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

TWO LIGHT WALL / BATH

W: 12.5" H: 8.25" E: 8"
Height from center of outlet box
up: 3.25" down: 5"

T24

44940 (-05,-962,-782)
(2) Medium Base 100w max.

T24 EN★

44940EN3 (-05,-962,-782)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP +

ONE LIGHT WALL / BATH

W: 5.5" H: 9" E: 8"
Height from center of outlet box
up: 4" down: 5"

T24

41939 (-05,-962,-782)
(1) Medium Base 100w max.

T24 EN★

41939EN3 (-05,-962,-782)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Product



DRAWING ROOM
INDOOR
Walnut
p.296



FOUR LIGHT WALL / BATH



THREE LIGHT WALL / BATH



TWO LIGHT WALL / BATH



ONE LIGHT WALL / BATH

DAMP +

FOUR LIGHT WALL / BATH

W: 37.75" H: 10" E: 5.75"
Height from center of outlet box
up: 5.25" down: 5.25"

T24

VS11204-WAL

(4) Medium Base 100w max.

DAMP +

THREE LIGHT WALL / BATH

W: 27.25" H: 9" E: 5.75"
Height from center of outlet box
up: 4.75" down: 4.25"

T24

VS11203-WAL

(3) Medium Base 100w max.

DAMP +

TWO LIGHT WALL / BATH

L: 18.25" H: 10.5" E: 5.75"
Height from center of outlet box
up: 5.25" down: 5.25"

T24

VS11202-WAL

(2) Medium Base 100w max.

DAMP +

ONE LIGHT WALL / BATH

W: 6.25" H: 9.75" E: 7"
Height from center of outlet box
up: 4.75" down: 5"

T24

VS11201-WAL

(1) Medium Base 100w max.

Recommended Product



CARONDELET INDOOR
Antique Brushed Nickel,
Burnt Sienna
p.180



FOUR LIGHT WALL / BATH – ANTIQUE BRUSHED NICKEL FINISH [-965]
CRYSTAL GLASS



THREE LIGHT WALL / BATH – BURNT SIENNA FINISH [-710]
CRYSTAL GLASS



TWO LIGHT WALL / BATH – ANTIQUE BRUSHED NICKEL FINISH [-965]
CRYSTAL GLASS



ONE LIGHT WALL / BATH – BURNT SIENNA FINISH [-710]
CRYSTAL GLASS

DAMP

FOUR LIGHT WALL / BATH

W: 26.25" H: 6" E: 5"
Height from center of outlet box up: 3"

T24

4414004 (-965,-710)
(4) Medium Base 100w max.

T24 EN★

4414004EN3 (-965,-710)
(4) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP

THREE LIGHT WALL / BATH

W: 20.25" H: 6" E: 5"
Height from center of outlet box up: 3"

T24

4414003 (-965,-710)
(3) Medium Base 100w max.

T24 EN★

4414003EN3 (-965,-710)
(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP

TWO LIGHT WALL / BATH

W: 13.5" H: 6" E: 5"
Height from center of outlet box up: 3"

T24

4414002 (-965,-710)
(2) Medium Base 100w max.

T24 EN★

4414002EN3 (-965,-710)
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP

ONE LIGHT WALL / BATH

W: 8.5" H: 8.5" E: 4.75"
Height from center of outlet box up: 4.25"

T24

4414001 (-965,-710)
(1) Medium Base 100w max.

T24 EN★

4414001EN3 (-965,-710)
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

TOWNER



SATIN BRONZE FINISH
BLACK STEEL SHADE

DAMP +

ONE LIGHT WALL / BATH

W: 7" H: 8.375" E: 8"
Height from center of outlet box
up: 6" down: 2.375"

T24

4141301-848
(1) Medium Base 60w max.

T24 EN★

4141301EN3-848
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



BRUSHED NICKEL FINISH
BLACK STEEL SHADE

DAMP +

ONE LIGHT WALL / BATH

W: 7" H: 8.375" E: 8"
Height from center of outlet box
up: 6" down: 2.375"

T24

4141301-962
(1) Medium Base 60w max.

T24 EN★

4141301EN3-962
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

Recommended Product



TOWNER INDOOR
Brushed Nickel,
Satin Bronze
p.68

HEWITT



POLISHED NICKEL FINISH

DAMP

ONE LIGHT WALL SCONCE

W: 5" H: 19.5" E: 5"
Height from center of outlet box
up: 12"

T24

WB1873PN
(1) Candelabra Base 60w max.



ANTIQUe BRONZE FINISH

DAMP

ONE LIGHT WALL SCONCE

W: 5" H: 19.5" E: 5"
Height from center of outlet box
up: 12"

T24

WB1873ANBZ
(1) Candelabra Base 60w max.

Recommended Product



HEWITT INDOOR
Polished Nickel,
Satin Nickel
p.188



DAMP ADA

**ONE LIGHT
WALL / BATH**

W: 8" H: 12" E: 4"
Height from center of outlet box
up: 6"

T24

4128501-12
(1) Medium Base 60w max.

Recommended
Product



GEREON INDOOR
Black
p.150



DAMP

**ONE LIGHT
WALL / BATH**

W: 8" H: 12" E: 4.25"
Height from center of outlet box
up: 6"

T24

4128601-802
(1) Medium Base 60w max.

Recommended
Product



COWEN INDOOR
Obsidian Mist
p.148

CARRA

WHITE WASH FINISH [-808] WITH WEATHERED ZINC [-797] ACCENTS



DAMP ADA

TWO LIGHT WALL / BATH SCONCE

W: 12.5" H: 20.75" E: 4"

T24

4131502-808

(2) Candelabra Base 60w max.

T24 EN★

4131502EN-808

(2) LED Cand. Base LED 2700k,
3.5w 350 lumen lamps incl.

Recommended Product



CARRA INDOOR
White Wash Finish with
Weathered Zinc Accents
p.137

HARTSVILLE

DARK WEATHERED ZINC AND WEATHERED OAK [-DWZ/WO]



DAMP ADA

TWO LIGHT WALL / BATH SCONCE

W: 6.125" H: 7.25" E: 4"

T24

WB1756DWZ/WO

(2) Candelabra Base 60w max.



DAMP ADA

ONE LIGHT WALL / BATH SCONCE

W: 4.5" H: 7.25" E: 4"

T24

WB1755DWZ/WO

(1) Candelabra Base 60w max.

Recommended Product



HARTSVILLE
INDOOR
Dark Weathered Zinc
& Weathered Oak
p.132

MOFFET STREET



BRUSHED NICKEL FINISH



SATIN BRONZE FINISH



WASHED PINE FINISH
CHROME ACCENTS

Recommended Product



MOFFET STREET
INDOOR
Brushed Nickel,
Satin Bronze,
Washed Pine
p.170

DAMP

ONE LIGHT WALL / BATH

W: 7" H: 12" E" 6"

Height from center of outlet box
up: 6"

T24

4134501-962

(1) Candelabra Base 60w max.

T24 EN★

4134501EN-962

(1) Candelabra Base LED 2700k,
3.5w, 350 lumen lamp incl.

DAMP

ONE LIGHT WALL / BATH

W: 7" H: 12" E" 6"

Height from center of outlet box
up: 6"

T24

4134501-848

(1) Candelabra Base 60w max.

T24 EN★

4134501EN-848

(1) Candelabra Base LED 2700k,
3.5w, 350 lumen lamp incl.

DAMP

ONE LIGHT WALL / BATH

W: 7" H: 12" E" 6"

Height from center of outlet box
up: 6"

T24

4134501-872

(1) Candelabra Base 60w max.

T24 EN★

4134501EN-872

(1) Candelabra Base LED 2700k,
3.5w, 350 lumen lamp incl.

BARRINGTON



BRUSHED STEEL FINISH
WHITE OPAL ETCHED GLASS



OIL RUBBED BRONZE FINISH
WHITE OPAL ETCHED GLASS

Recommended Products



BARRINGTON INDOOR
Brushed Steel,
Oil Rubbed Bronze
p.248



BARRINGTON
WALL / BATH
Brushed Steel,
Oil Rubbed Bronze
p.431

DAMP ADA

WALL SCONCE

W: 5.25" H:15.25" E: 4"

Height from center of outlet box
up: 4"

T24

WB1341BS

(1) Medium Base 100w max.

T24 LED

WB1341BS-L1

LED 3000k, 10 watts,
900 gross lumens

DAMP ADA

WALL SCONCE

W: 5.25" H:15.25" E: 4"

Height from center of outlet box
up: 4"

T24

WB1341ORB

(1) Medium Base 100w max.

T24 LED

WB1341ORB-L1

LED 3000k, 10 watts,
900 gross lumens

WALL / BATH SCONCES



WHITE FINISH
WHITE GLASS

DAMP

STEPPED GLASS ONE LIGHT WALL / BATH SCONCE

W: 10.75" H: 5.25" E: 4.25"
Height from center of outlet box
up: 2.5"

T24

4123-15

(1) Medium Base 100w max.

T24 EN★

4123EN3-15

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WHITE FINISH
WHITE ACRYLIC DIFFUSER

DAMP

EDLA ONE LIGHT WALL / BATH SCONCE

W: 13.75" H: 6.75" E: 5.25"
Height from center of outlet box
up: 4"

T24

4138-15

(1) Medium Base 100w max.

T24 EN★

4138EN3-15

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

ADA SCONCES



BRUSHED NICKEL FINISH
SATIN WHITE ACRYLIC DIFFUSER

DAMP ADA

RAVEL LED WALL / BATH SCONCE

W: 9.5" H: 10.5" E: 4"
Height from center of outlet box up: 5.25"

T24 WOD EN★ LED

4933593S-962
LED: 3000k, 14 watts,
1000 gross lumens



BRUSHED NICKEL FINISH
SATIN WHITE ACRYLIC DIFFUSER

DAMP ADA

FARON LED WALL / BATH SCONCE

W: 6" H: 12.5" E: 3.5"
Height from center of outlet box up: 6.25"

T24 WOD EN★ LED

4934093S-962
LED: 3000k, 14 watts,
1000 gross lumens



BURNT SIENNA FINISH
SATIN WHITE ACRYLIC DIFFUSER

DAMP ADA

TRUSS LED WALL / BATH SCONCE

W: 7.5" H: 13.5" E: 3.25"
Height from center of outlet box up: 6.75"

T24 WOD EN★ LED

4933193S-710
LED: 3000k, 14 watts,
1000 gross lumens



WITH BRUSHED NICKEL &
HEIRLOOM BRONZE ENDCAPS
WITH SATIN ETCHED GLASS

DAMP ADA

METROPOLIS ONE LIGHT WALL / BATH SCONCE

W: 8" H: 8.25" E: 4"
Height from center of outlet box up: 3.25"

T24

41036-999
(1) Medium Base 100w max.

T24 EN★

41036EN3-999
(1) Med. Base LED 3000k,
9w, 800 lumen lamp incl.



BRUSHED NICKEL FINISH
OPAL CASED ETCHED GLASS

DAMP ADA

NEARU ONE LIGHT WALL / BATH SCONCE

W: 8" H: 10.5" E: 4"
Height from center of outlet box up: 5.75"

T24

49119-962
(1) Medium Base 60w max.

T24 EN★

49119EN3-962
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



HEIRLOOM BRONZE FINISH
OPAL CASED ETCHED GLASS

DAMP ADA

NEARU ONE LIGHT WALL / BATH SCONCE

W: 8" H: 10.5" E: 4"
Height from center of outlet box up: 5.75"

T24

49119-782
(1) Medium Base 60w max.

T24 EN★

49119EN3-782
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



BRUSHED NICKEL FINISH
WHITE GLASS

DAMP ADA

ALVY ONE LIGHT WALL / BATH SCONCE

W: 15" H: 7.5" E: 4"
Height from center of outlet box up: 3"

T24

4135-962
(1) Medium Base 100w max.

T24 EN★

4135EN3-962
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WHITE FINISH
WHITE GLASS

DAMP ADA

NEVA ONE LIGHT WALL / BATH SCONCE

W: 11.5" H: 5.75" E: 4"
Height from center of outlet box up: 2.5"

T24

4148-15
(1) Medium Base 100w max.

T24 EN★

4148EN3-15
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

414893S-15
LED: 3000k, 14 watts,
1000 gross lumens



DAMP ADA +

LARGE LED WALL / BATH

W: 36.875" H: 4.5" E: 4"
Height from center of outlet box
horizontal: 2.25" vertical: 12.375"

T24 EN*

4734691S-962
LED: 3000k, 33 watts,
2950 gross lumens



DAMP ADA +

MEDIUM LED WALL / BATH

W: 24.75" H: 4.5" E: 4"
Height from center of outlet box
horizontal: 2.25" vertical: 12.375"

T24 EN*

4534691S-962
LED: 3000k, 22 watts,
1950 gross lumens



DAMP ADA +

SMALL LED WALL / BATH

W: 19.625" H: 4.5" E: 4"
Height from center of outlet box
horizontal: 2.25" vertical: 9.75"

T24 EN*

4434691S-962
LED: 3000k, 16.5 watts,
1450 gross lumens



DAMP ADA +

**LARGE LED
WALL / BATH**

W: 35.875" H: 5" E: 3.875"
Height from center of outlet box
horizontal: 2.5" vertical: 18"

T24 EN★

4616191S-962

LED: 3000k, 33 watts,
2950 gross lumens



DAMP ADA +

**MEDIUM LED
WALL / BATH**

W: 23.75" H: 5" E: 3.875"
Height from center of outlet box
horizontal: 2.5" vertical: 11.875"

T24 EN★

4516191S-962

LED: 3000k, 22 watts,
1950 gross lumens



DAMP ADA +

**SMALL LED
WALL / BATH**

W: 18.625" H: 5" E: 3.875"
Height from center of outlet box
horizontal: 2.5" vertical: 9.375"

T24 EN★

4416191S-962

LED: 3000k, 16.5 watts,
1450 gross lumens



DAMP +

**LARGE LED
WALL / BATH**

W: 36" H: 4.25" E: 5"
Height from center of outlet box
horizontal: 2.25" vertical: 18"

T24 LED

4522991S-962
LED: 2700K, 33 watts,
2700 gross lumens



DAMP +

**MEDIUM LED
WALL / BATH**

W: 23.25" H: 4.25" E: 5"
Height from center of outlet box
horizontal: 2.25" vertical: 11.75"

T24 LED

4422991S-962
LED: 2700K, 22 watts,
1800 gross lumens



DAMP ADA +

**SMALL LED
WALL / BATH**

W: 4.5" H: 8" E: 4"
Height from center of outlet box
up: 4.5" down: 3.5"

T24 LED

4122991S-962
LED: 2700K, 11 watts,
900 gross lumens



DAMP ADA +

LARGE LED WALL / BATH

W: 36.5" H: 4.75" E: 3.75"
Height from center of outlet box
horizontal: 2.5" vertical: 18.25"

T24 LED

4635591S-962
LED: 2700K, 33 watts,
2700 gross lumens



DAMP ADA +

MEDIUM LED WALL / BATH

W: 25" H: 4.75" E: 3.5"
Height from center of outlet box
horizontal: 2.5" vertical: 12.5"

T24 LED

4535591S-962
LED: 2700K, 22 watts,
1800 gross lumens

DAMP ADA +

SMALL LED WALL / BATH

W: 19.25" H: 4.75" E: 3.5"
Height from center of outlet box
horizontal: 2.5" vertical: 9.75"

T24 LED

4435591S-962
LED: 2700K, 16.5 watts,
1350 gross lumens

BRAUNFELS

PRODUCTS SHOWN: BRAUNFELS MEDIUM LED WALL / BATH IN SATIN ALUMINUM FINISH





EXTRA LARGE LED WALL / BATH – SATIN ALUMINUM FINISH [-04]
FROSTED ACRYLIC DIFFUSER & CLEAR OUTER ACRYLIC SHADE



LARGE LED WALL / BATH – BURNT SIENNA FINISH [-710]
FROSTED ACRYLIC DIFFUSER & CLEAR OUTER ACRYLIC SHADE



MEDIUM LED WALL / BATH – SATIN ALUMINUM FINISH [-04]
FROSTED ACRYLIC DIFFUSER & CLEAR OUTER ACRYLIC SHADE



SMALL LED WALL / BATH – BURNT SIENNA FINISH [-710]
FROSTED ACRYLIC DIFFUSER & CLEAR OUTER ACRYLIC SHADE

DAMP ADA +

EXTRA LARGE LED WALL / BATH

W: 50" H: 5" E: 3.75"
Height from center of outlet box
horizontal: 2.5" vertical: 25"

T24 LED

4735793S (-04,-710)
LED: 3000k, 44 watts,
3600 gross lumens

DAMP ADA +

LARGE LED WALL / BATH

W: 38" H: 5" E: 3.75"
Height from center of outlet box
horizontal: 2.5" vertical: 19"

T24 LED

4635793S (-04,-710)
LED: 3000k, 33 watts,
2700 gross lumens

DAMP ADA +

MEDIUM LED WALL / BATH

W: 26" H: 5" E: 3.75"
Height from center of outlet box
horizontal: 2.5" vertical: 13"

T24 LED

4535793S (-04,-710)
LED: 3000k, 22 watts,
1800 gross lumens

DAMP ADA +

SMALL LED WALL / BATH

W: 20" H: 5" E: 3.75"
Height from center of outlet box
horizontal: 2.5" vertical: 10"

T24 LED

4435793S (-04,-710)
LED: 3000k, 16.5 watts,
1350 gross lumens

CENTER STAGE



EIGHT LIGHT WALL / BATH - CHROME FINISH [-05]



SIX LIGHT WALL / BATH - BRUSHED STAINLESS FINISH [-98]



FIVE LIGHT WALL / BATH - CHROME FINISH [-05]



FOUR LIGHT WALL / BATH - BRUSHED STAINLESS FINISH [-98]



THREE LIGHT WALL / BATH - CHROME FINISH [-05]

DAMP +

EIGHT LIGHT WALL / BATH

W: 48" H: 4.25" E: 2.25"
Height from center of outlet box
horizontal: 2.25" vertical: 24"

T24

4740 (-05,-98)
(8) Medium Base
G25 100w max.

DAMP +

SIX LIGHT WALL / BATH

W: 36" H: 4.25" E: 2.25"
Height from center of outlet box
horizontal: 2.25" vertical: 18"

T24

4739 (-05,-98)
(6) Medium Base
G25 100w max.

DAMP +

FIVE LIGHT WALL / BATH

W: 30" H: 4.25" E: 2.25"
Height from center of outlet box
horizontal: 2.25" vertical: 15"

T24

4735 (-05,-98)
(5) Medium Base
G25 100w max.

DAMP +

FOUR LIGHT WALL / BATH

W: 24" H: 4.25" E: 2.25"
Height from center of outlet box
horizontal: 2.25" vertical: 12"

T24

4738 (-05,-98)
(4) Medium Base
G25 100w max.

DAMP +

THREE LIGHT WALL / BATH

W: 18" H: 4.25" E: 2.25"
Height from center of outlet box
horizontal: 2.25" vertical: 9"

T24

4737 (-05,-98)
(3) Medium Base
G25 100w max.



EIGHT LIGHT WALL / BATH – CHROME FINISH [-05]



SIX LIGHT WALL / BATH – BRUSHED NICKEL FINISH [-962]



FOUR LIGHT WALL / BATH – CHROME FINISH [-05]

DAMP +

EIGHT LIGHT WALL / BATH

W: 48" H: 4.75" E: 2.5"
 Height from center of outlet box
 horizontal: 2.5" vertical: 24"

T24

4703 (-05,-962)
 (8) Medium Base
 G25 100w max.

DAMP +

SIX LIGHT WALL / BATH

W: 36" H: 4.75" E: 2.5"
 Height from center of outlet box
 horizontal: 2.5" vertical: 18"

T24

4702 (-05,-962)
 (6) Medium Base
 G25 100w max.

DAMP +

FOUR LIGHT WALL / BATH

W: 24" H: 4.75" E: 2.5"
 Height from center of outlet box
 horizontal: 2.5" vertical: 12"

T24

4701 (-05,-962)
 (4) Medium Base
 G25 100w max.

PRODUCTS SHOWN: CRITTENDEN LARGE ONE LIGHT OUTDOOR WALL LANTERN IN SATIN ALUMINUM FINISH AND DRISCOLL FIVE LIGHT CHANDELIER IN BRUSHED NICKEL FINISH





OUTDOOR

collections

STONESTRONG COMPOSITE

Designed for Beauty, Engineered for the Elements

With the introduction of four collections of outdoor lighting fixtures made from StoneStrong, you now get the best of both worlds: The versatility, styles and range of price points you've come to expect from Generation Lighting, coupled with the rugged, no-nonsense durability of this remarkable proprietary material.

Stonestrong material is especially well-suited for harsh climates where prolonged exposure to salty air, rain, sun, snow and humidity – even debris and pollutants – is the rule, not the exception.

BENEFITS:

- Rustproof
- 5 year warranty
- Resists corrosion, fading, fire, acids and alkali
- 2x strength of resin
- Withstands temperatures ranging from -20°F up to 120°F
- Eco-friendly - complies with Restriction of Hazardous Substances (RoHS)
- Maintains fine design details and textures
- Coastal region approved



CHOOSE FROM FOUR COLLECTIONS AND FOUR FINISHES:



GALVYN COLLECTION
ANTIQUÉ BRONZE [-71]
p.462



CALDER COLLECTION
BLACK [-12]
p.472



MELITO COLLECTION
WEATHERED COPPER [-44]
p.528



GAELAN COLLECTION
PAINTED BRUSHED NICKEL [-753]
p.470



Photography: ©Jessica Klewicki Glynn | Instagram: @jessglynnphoto
Designer: Knowles Interior Design

STONESTRONG COMPOSITE



StoneStrong material is molded together, enabling custom design capabilities with unique forms, fine detailing, and richer texture than what can be achieved with aluminum or resin.

GALVYN COLLECTION
ANTIQUÉ BRONZE [-71]
p.462



WET SS

**EXTRA LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 12.625" H: 22.625" E: 12.75"
Height from center of outlet box
up: 4"

T24

8829301-71
(1) Medium Base 75w max.

T24 EN★

8829301EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 9.875" H: 18.75" E: 10.375"
Height from center of outlet box
up: 4"

T24

8729301-71
(1) Medium Base 75w max.

T24 EN★

8729301EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**

W: 8.125" H: 14.125" E: 8.625"
Height from center of outlet box
up: 4"

T24

8629301-71
(1) Medium Base 75w max.

T24 EN★

8629301EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 6.625" H: 11.875" E: 6.875"
Height from center of outlet box
up: 3"

T24

8529301-71
(1) Medium Base 75w max.

T24 EN★

8529301EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP SS

OUTDOOR PENDANT

D: 9.875" H: 19.625"
10' of wire pre-laced through 3' of chain

T24

6229301-71
(1) Medium Base 75w max.

T24 EN★

6229301EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

**ONE LIGHT OUTDOOR
POST LANTERN**

D: 9.875" H: 20.625"

T24

8229301-71
(1) Medium Base 75w max.

T24 EN★

8229301EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

**EXTRA LARGE ONE LIGHT
OUTDOOR WALL LANTERN**W: 12.625" H: 22.625" E: 12.75"
Height from center of outlet box
up: 4"

T24

8829301-12
(1) Medium Base 75w max.

T24 EN★

8829301EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

WET SS

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**W: 9.875" H: 18.75" E: 10.375"
Height from center of outlet box
up: 4"

T24

8729301-12
(1) Medium Base 75w max.

T24 EN★

8729301EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

WET SS

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**W: 8.125" H: 14.125" E: 8.625"
Height from center of outlet box
up: 4"

T24

8629301-12
(1) Medium Base 75w max.

T24 EN★

8629301EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

WET SS

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**W: 6.625" H: 11.875" E: 6.875"
Height from center of outlet box
up: 3"

T24

8529301-12
(1) Medium Base 75w max.

T24 EN★

8529301EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP SS

OUTDOOR PENDANTD: 9.875" H: 19.625"
10' of wire pre-laced through 3' of chain

T24

6229301-12
(1) Medium Base 75w max.

T24 EN★

6229301EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

WET SS

**ONE LIGHT OUTDOOR
POST LANTERN**

D: 9.875" H: 20.625"

T24

8229301-12
(1) Medium Base 75w max.

T24 EN★

8229301EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

CHILDRESS

PRODUCT SHOWN: CHILDRESS LARGE OUTDOOR WALL LANTERN IN ANTIQUE BRONZE FINISH



WET

**EXTRA LARGE
OUTDOOR WALL LANTERN**

W: 15" H: 35.5" E: 19.25"
 Height from center of outlet box
 up: 18.25"

T24

8836302-71

(2) Medium Base 100w max.

T24 EN★

8836302EN3-71

(2) Med. Base LED 3000k,
 9.5w, 800 lumen lamps incl.

See more Antique Bronze Finish on p.466



ANTIQUE BRONZE FINISH
 SATIN ETCHED GLASS

WET

**EXTRA LARGE
OUTDOOR WALL LANTERN**

W: 15" H: 35.5" E: 19.25"
 Height from center of outlet box
 up: 18.25"

T24

8836302-12

(2) Medium Base 100w max.

T24 EN★

8836302EN3-12

(2) Med. Base LED 3000k,
 9.5w, 800 lumen lamps incl.

See more Black Finish on p.468



BLACK FINISH
 SATIN ETCHED GLASS

CHILDRESS

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 9" H: 21.25" E: 11.75"
Height from center of outlet box
up: 10.25"

T24

8736301-71
(1) Medium Base 100w max.

T24 EN★

8736301EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 6.5" H: 14.75" E: 8.5"
Height from center of outlet box
up: 7.75"

T24

8636301-71
(1) Medium Base 100w max.

T24 EN★

8636301EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 5.5" H: 12.75" E: 7.75"
Height from center of outlet box
up: 7"

T24

8536301-71
(1) Medium Base 60w max.

T24 EN★

8536301EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

OUTDOOR ONE LIGHT PENDANT

D: 9" H: 19.25"
6' wire pre-laced through 3' chain

T24

6236301-71
(1) Medium Base 100w max.

T24 EN★

6236301EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

OUTDOOR ONE LIGHT POST LANTERN

D: 9" H: 20.5"

T24

8236301-71
(1) Medium Base 100w max.

T24 EN★

8236301EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

OUTDOOR TWO LIGHT CEILING FLUSH MOUNT

L: 13.5" W: 13.5" H: 8.25"

T24

7836302-71
(2) Medium Base 60w max.

T24 EN★

7836302EN3-71
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.



CHILDRESS

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 9" H: 21.25" E: 11.75"
Height from center of outlet box
up: 10.25"

T24

8736301-12
(1) Medium Base 100w max.

T24 EN★

8736301EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 6.5" H: 14.75" E: 8.5"
Height from center of outlet box
up: 7.75"

T24

8636301-12
(1) Medium Base 100w max.

T24 EN★

8636301EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 5.5" H: 12.75" E: 7.75"
Height from center of outlet box
up: 7"

T24

8536301-12
(1) Medium Base 60w max.

T24 EN★

8536301EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

**OUTDOOR
ONE LIGHT PENDANT**D: 9" H: 19.25"
6' wire pre-laced through 3' chain

T24

6236301-12
(1) Medium Base 100w max.

T24 EN★

6236301EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

WET

**OUTDOOR ONE LIGHT
POST LANTERN**

D: 9" H: 20.5"

T24

8236301-12
(1) Medium Base 100w max.

T24 EN★

8236301EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP

**OUTDOOR TWO LIGHT
CEILING FLUSH MOUNT**

L: 13.5" W: 13.5" H: 8.25"

T24

7836302-12
(2) Medium Base 60w max.

T24 EN★

7836302EN3-12
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

WET SS

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 8.5" H: 16.75" E: 8.75"
Height from center of outlet box
up: 8.375"

T24

8747431-753
(1) Medium Base 75w max.

T24 EN★

8747431EN3-753
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 7" H: 15.25" E: 7.375"
Height from center of outlet box
up: 7.75"

T24

8647431-753
(1) Medium Base 75w max.

T24 EN★

8647431EN3-753
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 5.375" H: 10.25" E: 5.875"
Height from center of outlet box
up: 6.5"

T24

8547431-753
(1) Medium Base 75w max.

T24 EN★

8547431EN3-753
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP SS

ONE LIGHT OUTDOOR PENDANT

L: 8.5" W: 8.5" H: 16.75"
10' wire pre-laced through 3' chain

T24

6247431-753
(1) Medium Base 75w max.

T24 EN★

6247431EN3-753
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 8.5" H: 16.75" E: 8.75"
Height from center of outlet box
up: 8.375"

T24

8747401-12

(1) Medium Base 75w max.

T24 EN★

8747401EN3-12

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7" H: 15.25" E: 7.375"
Height from center of outlet box
up: 7.75"

T24

8647401-12

(1) Medium Base 75w max.

T24 EN★

8647401EN3-12

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 5.375" H: 10.25" E: 5.875"
Height from center of outlet box
up: 6.5"

T24

8547401-12

(1) Medium Base 75w max.

T24 EN★

8547401EN3-12

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP SS

**ONE LIGHT
OUTDOOR PENDANT**

L: 8.5" W: 8.5" H: 16.75"
10' wire pre-laced through 3' chain

T24

6247401-12

(1) Medium Base 75w max.

T24 EN★

6247401EN3-12

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.





WET SS

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 10" H: 16.5" E: 11.375"
Height from the center of outlet box
up: 5.25"

T24

8750701-71
(1) Medium Base 75w max.

T24 EN★

8750701EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7.875" H: 13.25" E: 9.125"
Height from the center of outlet box
up: 4.125"

T24

8650701-71
(1) Medium Base 75w max.

T24 EN★

8650701EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 6" H: 10" E: 7.25"
Height from the center of outlet box
up: 3.875"

T24

8550701-71
(1) Medium Base 75w max.

T24 EN★

8550701EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP SS

**ONE LIGHT
OUTDOOR PENDANT**

D: 10" H: 16.125"
10' wire pre-laced through 3' chain

T24

6250701-71
(1) Medium Base 75w max.

T24 EN★

6250701EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

**ONE LIGHT
OUTDOOR POST LANTERN**

D: 10" H: 20"

T24

8250701-71
(1) Medium Base 75w max.

T24 EN★

8250701EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 10" H: 16.5" E: 11.375"
Height from the center of outlet box
up: 5.25"

T24

8750701-12
(1) Medium Base 75w max.

T24 EN★

8750701EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7.875" H: 13.25" E: 9.125"
Height from the center of outlet box
up: 4.125"

T24

8650701-12
(1) Medium Base 75w max.

T24 EN★

8650701EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 6" H: 10" E: 7.25"
Height from the center of outlet box
up: 3.875"

T24

8550701-12
(1) Medium Base 75w max.

T24 EN★

8550701EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP SS

**ONE LIGHT
OUTDOOR PENDANT**

D: 10" H: 16.125"
10' wire pre-laced through 3' chain

T24

6250701-12
(1) Medium Base 75w max.

T24 EN★

6250701EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

**ONE LIGHT
OUTDOOR POST LANTERN**

D: 10" H: 20"

T24

8250701-12
(1) Medium Base 75w max.

T24 EN★

8250701EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

PERRYWOOD

WET

LARGE THREE LIGHT OUTDOOR WALL LANTERN

W: 12" H: 23" E: 14"

Height from center of outlet box
up: 10.625"

T24

8714203-12

(3) Candelabra Base 60w max.

T24 EN★

8714203EN-12

(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

MEDIUM THREE LIGHT OUTDOOR WALL LANTERN

W: 9.5" H: 18" E: 11.25"

Height from center of outlet box
up: 8.125"

T24

8614203-12

(3) Candelabra Base 40w max.

T24 EN★

8614203EN-12

(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7.875" H: 15" E: 9.25"
Height from center of outlet box
up: 6.875" down: 8.125"

T24

8514201-12

(3) Medium Base 60w max.

T24 EN★

8514201EN3-12(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

WET

**EXTRA SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 6.5" H: 12" E: 7.875"
Height from center of outlet box
up: 5.4375" down: 6.5625"

T24

8414201-12

(3) Medium Base 60w max.

T24 EN★

8414201EN3-12(3) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

DAMP

**THREE LIGHT
OUTDOOR PENDANT**

W: 9.5" H: 18.875"
6' wire pre-laced through 3' chain

T24

6214203-12

(3) Candelabra Base 40w max.

T24 EN★

6214203EN-12(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.

WET

**THREE LIGHT
OUTDOOR POST LANTERN**

D: 9.5" H: 19.875"

T24

8214203-12

(3) Candelabra Base 60w max.

T24 EN★

8214203EN-12(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 10" H: 16.25" E: 12"
Height from center of outlet box up: 9"

T24

84050-185
(1) Medium Base 100w max.

T24 EN★

84050EN3-185
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 8" H: 13.25" E: 10"
Height from center of outlet box up: 8.25"

T24

84049-185
(1) Medium Base 100w max.

T24 EN★

84049EN3-185
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 6" H: 8.25" E: 7.75"
Height from center of outlet box up: 3.25"

T24

84048-185
(1) Medium Base 100w max.

T24 EN★

84048EN3-185
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



DAMP

ONE LIGHT OUTDOOR PENDANT

D: 10" H: 17"
10' wire pre-laced through 10' chain

T24

60048-185
(1) Medium Base 100w max.

T24 EN★

60048EN3-185
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET

ONE LIGHT OUTDOOR POST LANTERN

D: 10" H: 17.25"

T24

82048-185
(1) Medium Base 100w max.

T24 EN★

82048EN3-185
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



DAMP

TWO LIGHT OUTDOOR CEILING FLUSH MOUNT

D: 13.25" H: 7.5"

T24

88048-185
(2) Medium Base 100w max.

T24 EN★

88048EN3-185
(2) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 10" H: 16.25" E: 12"
Height from center of outlet box up: 9"

T24

84050-12
(1) Medium Base 100w max.

T24 EN★

84050EN3-12
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.

T24 EN★

84050PEN3-12
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl. photocell included



WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 8" H: 13.25" E: 10"
Height from center of outlet box up: 8.25"

T24

84049-12
(1) Medium Base 100w max.

T24 EN★

84049EN3-12
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.

T24 EN★

84049PEN3-12
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl. photocell included



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 6" H: 8.25" E: 7.75"
Height from center of outlet box up: 3.25"

T24

84048-12
(1) Medium Base 100w max.

T24 EN★

84048EN3-12
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.

T24 EN★

84048PEN3-12
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl. photocell included

DAMP

ONE LIGHT OUTDOOR PENDANT

D: 10" H: 17"
10' wire pre-laced through 10' chain

T24 EN★

60048PEN3-12
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl. photocell included



WET

ONE LIGHT OUTDOOR POST LANTERN

D: 10" H: 17.25"

T24 EN★

82048PEN3-12
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl. photocell included



DAMP

TWO LIGHT OUTDOOR CEILING FLUSH MOUNT

D: 13.25" H: 7.5"

T24 EN★

88048PEN3-12
(2) Med. Base LED 3000k, 9.5w, 800 lumen lamps incl. photocell included



CHATHAM

WET

LARGE TWO LIGHT OUTDOOR WALL LANTERN

W: 9.25" H: 21" E: 10"
Height from center of outlet box
up: 8.5"

T24

8463-44
(2) Candelabra Base 40w max.

T24

8463EN-44
(2) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.

See more Weathered Copper Finish
with Clear Seeded Glass on p.480



WEATHERED COPPER FINISH
CLEAR SEEDED GLASS

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 9.25" H: 21" E: 10"
Height from center of outlet box
up: 8.5"

T24

89273-44
(1) Medium Base 100w max.

T24 EN★

89273EN3-44
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

See more Weathered Copper Finish
with Frosted Seeded Glass on p.481



WEATHERED COPPER FINISH
FROSTED SEEDED GLASS

WET

**LARGE TWO LIGHT
OUTDOOR WALL LANTERN**

W: 9.25" H: 21" E: 10"
Height from center of outlet box
up: 8.5"

T24

8463-46
(2) Candelabra Base 40w max.

T24

8463EN-46
(2) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.

See more Oxidized Bronze Finish
with Clear Seeded Glass on p.482



OXIDIZED BRONZE FINISH
CLEAR SEEDED GLASS

WET

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 9.25" H: 21" E: 10"
Height from center of outlet box
up: 8.5"

T24

89273-46
(1) Medium Base 100w max.

T24 EN★

89273EN3-46
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

See more Oxidized Bronze Finish
with Frosted Seeded Glass on p.483



OXIDIZED BRONZE FINISH
FROSTED SEEDED GLASS

WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 6.75" H: 14.5" E: 7.5"
Height from center of outlet box
up: 6"

T24

8462-44

(1) Medium Base 100w max.



WET ☾

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 6.75" H: 14.5" E: 7.5"
Height from center of outlet box
up: 6"

T24

8462D-44

(1) Medium Base 100w max.

T24 EN★

8462DEN3-44

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



CLEAR SEEDED GLASS WITH
WHITE ALUMINUM BACKING

DAMP

TWO LIGHT OUTDOOR PENDANT

L: 9.25" W: 9.25" H: 19"
10' wire pre-laced through 3' chain

T24

6062-44

(2) Candelabra Base 40w max.

T24 EN★

6062EN-44

(2) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

TWO LIGHT OUTDOOR POST LANTERN

L: 9.25" W: 9.25" H: 22.75"

T24

8262-44

(2) Candelabra Base 60w max.

T24 EN★

8262EN-44

(2) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET **LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 9.25" H: 21" E: 10"
Height from center of outlet box
up: 8.5"

T24

8463D-44

(1) Medium Base 100w max.

T24 **8463DEN3-44**

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



CLEAR SEEDED GLASS WITH
WHITE ALUMINUM BACKING

WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 6.75" H: 14.5" E: 7.5"
Height from center of outlet box
up: 6"

T24

89062-44

(1) Medium Base 100w max.

T24 **89062EN3-44**

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

**ONE LIGHT
OUTDOOR PENDANT**

L: 9.25" W: 9.25" H: 19"
10' wire pre-laced through 6' chain

T24

69272-44

(1) Medium Base 100w max.

T24 **69272EN3-44**

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**ONE LIGHT OUTDOOR
POST LANTERN**

L: 9.25" W: 9.25" H: 22.75"

T24

82973-44

(1) Medium Base 100w max.

T24 **82973EN3-44**

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 6.75" H: 14.5" E: 7.5"
Height from center of outlet box
up: 6"

T24

8462-46
(1) Medium Base 100w max.



DAMP

**TWO LIGHT
OUTDOOR PENDANT**

L: 9.25" W: 9.25" H: 19"
10' wire pre-laced through 3' chain

T24

6062-46
(2) Candelabra Base 40w max.

T24 EN★

6062EN-46
(2) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

**TWO LIGHT
OUTDOOR POST LANTERN**

L: 9.25" W: 9.25" H: 22.75"

T24

8262-46
(2) Candelabra Base 60w max.

T24 EN★

8262EN-46
(2) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 6.75" H: 14.5" E: 7.5"
Height from center of outlet box
up: 6"

T24

89062-46
(1) Medium Base 100w max.

T24 EN★

89062EN3-46
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

**ONE LIGHT
OUTDOOR PENDANT**

L: 9.25" W: 9.25" H: 19"
10' wire pre-laced through 6' chain

T24

69272-46
(1) Medium Base 100w max.

T24 EN★

69272EN3-46
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**ONE LIGHT
OUTDOOR POST LANTERN**

L: 9.25" W: 9.25" H: 22.75"

T24

82973-46
(1) Medium Base 100w max.

T24 EN★

82973EN3-46
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



TERRACE

WET

ONE LIGHT WALL LANTERN

W: 9.5" H: 18.375" E: 10.25"
Height from center of outlet box
up: 6"

T24

OL4003ORB
(1) Medium Base 150w max.



WET

ONE LIGHT WALL LANTERN

W: 8" H: 16" E: 8.75"
Height from center of outlet box
up: 4.75"

T24

OL4002ORB
(1) Medium Base 100w max.



WET

**ONE LIGHT
WALL LANTERN**

W: 6" H: 11.75" E: 6.75"
Height from center of outlet box
up: 3"

T24

OL4001ORB

(1) Medium Base 100w max.



WET

**ONE LIGHT
WALL LANTERN**

W: 4.5" H: 8.25" E: 6"
Height from center of outlet box
up: 2.5"

T24

OL4000ORB

(1) Medium Base 60w max.



DAMP

**ONE LIGHT
HANGING LANTERN**

L: 8" W: 8" H: 16.75"
Supplied with 15' of wire and
6' of chain

T24

OL4011ORB

(1) Medium Base 150w max.



WET

**ONE LIGHT
POST / PIER LANTERN**

L: 9.5" W: 9.5" H: 22.5"

T24

OL4007ORB

(1) Medium Base 150w max.



HERMITAGE

WET

LARGE THREE LIGHT OUTDOOR WALL LANTERN

W: 11" H: 20.75" E: 12.75"
Height from center of outlet box:
up: 7.75"

T24

88083-965
(3) Candelabra Base 40w max.

T24 EN★

88083EN-965
(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.

See More Antique Brushed Nickel Finish
with Clear Glass on pages 488 - 491



ANTIQUE BRUSHED NICKEL FINISH
CLEAR GLASS

WET

**LARGE THREE LIGHT
OUTDOOR WALL LANTERN**

W: 11" H: 20.75" E: 12.75"
Height from center of outlet box:
up: 7.75"

T24

88083-71

(3) Candelabra Base 40w max.

T24 EN★

88083EN-71

(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.

See More Antique Bronze Finish
with Clear Glass on pages 488 - 491



ANTIQUE BRONZE FINISH
CLEAR GLASS

WET

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 11" H: 19.75" E: 12.75"
Height from center of outlet box
up: 7.75"

T24

89193-71

(1) Medium Base 100w max.

T24 EN★

89193EN3-71

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 EN★

89193DEN3-71

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

See More Antique Bronze Finish
with Frosted Glass on pages 488 - 491



ANTIQUE BRONZE FINISH
FROSTED GLASS

HERMITAGE

WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 9" H: 15.25" E: 10.5"
Height from center of outlet box
up: 6"

T24

88082-965
(1) Medium Base 100w max.



ANTIQUE BRUSHED NICKEL FINISH
CLEAR GLASS

WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 9" H: 15.25" E: 10.5"
Height from center of outlet box
up: 6"

T24

88082-71
(1) Medium Base 100w max.



ANTIQUE BRONZE FINISH
CLEAR GLASS

WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 9" H: 15.25" E: 10.5"
Height from center of outlet box
up: 6"

T24

89192-71
(1) Medium Base 100w max.

T24 EN★

89192EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 EN★ 🌙

89192DEN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



ANTIQUE BRONZE FINISH
FROSTED GLASS

WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 7" H: 13.5" E: 8.25"
Height from center of outlet box
up: 4.75"

T24

88081-965

(1) Medium Base 100w max.



ANTIQUE BRUSHED NICKEL FINISH
CLEAR GLASS

WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 7" H: 13.5" E: 8.25"
Height from center of outlet box
up: 4.75"

T24

88081-71

(1) Medium Base 100w max.



ANTIQUE BRONZE FINISH
CLEAR GLASS

WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 7" H: 13.5" E: 8.25"
Height from center of outlet box
up: 4.75"

T24

89181-71

(1) Medium Base 100w max.

T24 EN★

89181EN3-71

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 EN★

89181DEN3-71

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



ANTIQUE BRONZE FINISH
FROSTED GLASS

HERMITAGE

DAMP

THREE LIGHT OUTDOOR PENDANT

D: 11" H: 19"

10' wire pre-laced through 4' chain

T24

60081-965

(3) Candelabra Base 40w max.

T24 EN★

60081EN-965

(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



ANTIQUE BRUSHED NICKEL FINISH
CLEAR GLASS

DAMP

THREE LIGHT OUTDOOR PENDANT

D: 11" H: 19"

10' wire pre-laced through 4' chain"

T24

60081-71

(3) Candelabra Base 40w max.

T24 EN★

60081EN-71

(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



ANTIQUE BRONZE FINISH
CLEAR GLASS

DAMP

OUTDOOR PENDANT

D: 11" H: 18"

10' wire pre-laced through 4' chain

T24

69191-71

(1) Medium Base 100w max.

T24 EN★

69191EN3-71

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



ANTIQUE BRONZE FINISH
FROSTED GLASS

WET

THREE LIGHT OUTDOOR POST LANTERN

D: 11" H: 20.25"

T24

82081-965
(3) Candelabra Base 60w max.

T24 EN★

82081EN-965
(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



ANTIQUE BRUSHED NICKEL FINISH
CLEAR GLASS

WET

THREE LIGHT OUTDOOR POST LANTERN

D: 11" H: 20.25"

T24

82081-71
(3) Candelabra Base 60w max.

T24 EN★

82081EN-71
(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



ANTIQUE BRONZE FINISH
CLEAR GLASS

WET

OUTDOOR POST LANTERN

D: 11" H: 20.25"

T24

89298-71
(1) Medium Base 100w max.

T24 EN★

89298EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



ANTIQUE BRONZE FINISH
FROSTED GLASS



WET

**EXTRA LARGE FOUR LIGHT
OUTDOOR WALL LANTERN**

W: 12" H: 20" E: 13.125"
Height from center of outlet box
up: 6"

T24

OL5904CB

(4) Candelabra Base 60w max.



WET

**LARGE THREE LIGHT
OUTDOOR WALL LANTERN**

W: 10.25" H: 17" E: 11.5"
Height from center of outlet box
up: 6"

T24

OL5902CB

(3) Candelabra Base 60w max.



WET

**MEDIUM TWO LIGHT
OUTDOOR WALL LANTERN**

W: 8" H: 14.5" E: 9.5"
Height from center of outlet box
up: 5"

T24

OL5901CB

(2) Candelabra Base 60w max.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 6.25" H: 10.75" E: 7.25"
Height from center of outlet box
up: 3.5"

T24

OL5900CB

(1) Medium Base 100w max.



DAMP

**THREE LIGHT
OUTDOOR PENDANT**

D: 10.25" H: 21"
Supplied with 7' of wire and 5' of chain

T24

OL5911CB

(3) Candelabra Base 60w max.



WET

**THREE LIGHT
OUTDOOR POST LANTERN**

D: 10.25" H: 22.25"

T24

OL5907CB

(3) Candelabra Base 60w max.



WET

**EXTRA LARGE FOUR LIGHT
OUTDOOR WALL LANTERN**

W: 12" H: 20" E: 13.125"
Height from center of outlet box
up: 6"

T24

OL5904BK

(4) Candelabra Base 60w max.



WET

**LARGE THREE LIGHT
OUTDOOR WALL LANTERN**

W: 10.25" H: 17" E: 11.5"
Height from center of outlet box
up: 6"

T24

OL5902BK

(3) Candelabra Base 60w max.



WET

**MEDIUM TWO LIGHT
OUTDOOR WALL LANTERN**

W: 8" H: 14.5" E: 9.5"
Height from center of outlet box
up: 5"

T24

OL5901BK

(2) Candelabra Base 60w max.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 6.25" H: 10.75" E: 7.25"
Height from center of outlet box
up: 3.5"

T24

OL5900BK

(1) Medium Base 100w max.



DAMP

**THREE LIGHT
OUTDOOR PENDANT**

D: 10.25" H: 21"
Supplied with 7' of wire and 5' of chain

T24

OL5911BK

(3) Candelabra Base 60w max.



WET

**THREE LIGHT
OUTDOOR POST LANTERN**

D: 10.25" H: 22.25"

T24

OL5907BK

(3) Candelabra Base 60w max.

TRAFALGAR

PRODUCT SHOWN: TRAFALGAR TWO LIGHT OUTDOOR WALL LANTERN IN OXIDIZED BRONZE FINISH



WET

**LARGE THREE LIGHT
OUTDOOR WALL LANTERN**

W: 12.25" H: 23.5" E: 14.25"
Height from center of outlet box
up: 11.5"

T24

8461-46
(3) Candelabra Base 40w max.

T24 EN★

8461EN-46
(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

**MEDIUM TWO LIGHT
OUTDOOR WALL LANTERN**

W: 9" H: 18" E: 11.5"
Height from center of outlet box
up: 10.5"

T24

8460-46
(2) Candelabra Base 40w max.

T24 EN★

8460EN-46
(2) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

**SMALL TWO LIGHT
OUTDOOR WALL LANTERN**

W: 7.5" H: 14.75" E: 9.75"
Height from center of outlet box
up: 8"

T24

8459-46
(2) Candelabra Base 40w max.

T24 EN★

8459EN-46
(2) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



DAMP

**THREE LIGHT
OUTDOOR PENDANT**

D: 12.25" H: 20.75"
10' wire pre-laced through 3' chain

T24

6059-46
(3) Candelabra Base 40w max.

T24 EN★

6059EN-46
(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

**THREE LIGHT
OUTDOOR POST LANTERN**

D: 12.25" H: 22.75"

T24

8259-46
(3) Candelabra Base 60w max.

T24 EN★

8259EN-46
(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.

CAPE MAY

WET

**EXTRA LARGE
ONE LIGHT
OUTDOOR WALL LANTERN**

D: 13" H: 29.75" E: 16"
Height from center of outlet box
up: 11.25"

T24

88243-780

(1) Medium Base 100w max.

T24

EN★

88243EN3-780

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



BURLED IRON FINISH
ETCHED, HAMMERED GLASS WITH LIGHT AMBER TINT

WET

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

D: 11" H: 26.25" E: 13.75"
Height from center of outlet box
up: 9.25"

T24

88242-780
(1) Medium Base 100w max.

T24 EN★

88242EN3-780
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**

D: 9" H: 15.5" E: 10"
Height from center of outlet box
up: 4.5"

T24

88241-780
(1) Medium Base 100w max.

T24 EN★

88241EN3-780
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

D: 7" H: 10.5" E: 8"
Height from center of outlet box
up: 3"

T24

88240-780
(1) Medium Base 100w max.

T24 EN★

88240EN3-780
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 ☾

88240D-780
(1) Medium Base 100w max.

T24 EN★ ☾

88240DEN3-780
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**ONE LIGHT
OUTDOOR POST LANTERN**

D: 11" H: 23"

T24

82240-780
(1) Medium Base 100w max.

T24 EN★

82240EN3-780
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



BAKERSVILLE

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 7.75" H: 17" E: 8.5"
Height from center of outlet box up: 14"

T24

88941-782
(1) Medium Base 100w max.



HEIRLOOM BRONZE FINISH
CLEAR BEVELED GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 7.75" H: 17" E: 8.5"
Height from center of outlet box up: 14"

T24

89941-782
(1) Medium Base 100w max.

T24 EN★

89941EN3-782
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



HEIRLOOM BRONZE FINISH
SATIN ETCHED GLASS



HEIRLOOM BRONZE FINISH
CLEAR BEVELED GLASS



HEIRLOOM BRONZE FINISH
SATIN ETCHED GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 6.5" H: 15.5" E: 7.75"
Height from center of outlet box up: 12.25"

T24

88940-782
(1) Medium Base 100w max.

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 6.5" H: 15.5" E: 7.75"
Height from center of outlet box up: 12.25"

T24

89940-782
(1) Medium Base 100w max.

T24 EN★

89940EN3-782
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 7.75" H: 17" E: 8.5"
Height from center of outlet box up: 14"

T24

88941-12
(1) Medium Base 100w max.



BLACK FINISH
CLEAR BEVELED GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 7.75" H: 17" E: 8.5"
Height from center of outlet box up: 14"

T24

89941-12
(1) Medium Base 100w max.

T24 EN★

89941EN3-12
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



BLACK FINISH
SATIN ETCHED GLASS



BLACK FINISH
CLEAR BEVELED GLASS



BLACK FINISH
SATIN ETCHED GLASS



BLACK FINISH
CLEAR BEVELED GLASS



BLACK FINISH
SATIN ETCHED GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 6.5" H: 15.5" E: 7.75"
Height from center of outlet box up: 12.25"

T24

88940-12
(1) Medium Base 100w max.

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 6.5" H: 15.5" E: 7.75"
Height from center of outlet box up: 12.25"

T24

89940-12
(1) Medium Base 100w max.

T24 EN★

89940EN3-12
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.

DAMP

TWO LIGHT OUTDOOR CEILING FLUSH MOUNT

D: 12.75" H: 7.5"

T24

78136-12
(2) Medium Base 60w max.

DAMP

TWO LIGHT OUTDOOR CEILING FLUSH MOUNT

D: 12.75" H: 7.5"

T24

79136-12
(2) Medium Base 60w max.

T24 EN★

79136EN3-12
(2) Med. Base LED 3000k, 9.5w, 800 lumen lamps incl.

SEVIER

WET

EXTRA LARGE THREE LIGHT DOWNLIGHT OUTDOOR WALL LANTERN

W: 12.5" H: 23.25" E: 11.5"
Height from center of outlet box
up: 4"

T24

8738703-71

(3) Candelabra Base 60w max.

T24 EN★

8738703EN-71

(3) Cand. Base LED 2700k,
3.5w, lumen lamps incl.

See more Antique Bronze Finish
on p.502



ANTIQUÉ BRONZE FINISH
CLEAR GLASS

WET

**EXTRA LARGE
THREE LIGHT DOWNLIGHT
OUTDOOR WALL LANTERN**

W: 12.5" H: 23.25" E: 11.5"
Height from center of outlet box
up: 4"

T24

8738703-12
(3) Candelabra Base 60w max.

T24 EN★

8738703EN-12
(3) Cand. Base LED 2700k,
3.5w, lumen lamps incl.

See more Black Finish
on p.503



BLACK FINISH
CLEAR GLASS



WET

**LARGE ONE LIGHT
UPLIGHT OUTDOOR
WALL LANTERN**

W: 9.5" H: 21.75" E: 8.75"
Height from center of outlet box
up: 18.75"

T24

8638701-71

(1) Medium Base 100w max.



WET

**LARGE ONE LIGHT
DOWNLIGHT OUTDOOR
WALL LANTERN**

W: 9.5" H: 18.75" E: 8.75"
Height from center of outlet box
up: 2.75"

T24

8438701-71

(1) Medium Base 100w max.



WET

**SMALL ONE LIGHT
UPLIGHT OUTDOOR
WALL LANTERN**

W: 6.5" H: 16.25" E: 7.75"
Height from center of outlet box
up: 13.5"

T24

8538701-71

(1) Medium Base 100w max.



WET

**SMALL ONE LIGHT
DOWNLIGHT OUTDOOR
WALL LANTERN**

W: 6.5" H: 12.5" E: 7.75"
Height from center of outlet box
up: 2.75"

T24

8338701-71

(1) Medium Base 100w max.



DAMP

**ONE LIGHT
OUTDOOR PENDANT**

D: 9.5" H: 16.75"
6' wire pre-laced through 3' chain

T24

6238701-71

(1) Medium Base 100w max.



WET

**ONE LIGHT OUTDOOR
POST LANTERN**

D: 9.5" H: 27.25"

T24

8238701-71

(1) Medium Base 100w max.



WET

LARGE ONE LIGHT UPLIGHT OUTDOOR WALL LANTERN

W: 9.5" H: 21.75" E: 8.75"
Height from center of outlet box up: 18.75"

T24

8638701-12
(1) Medium Base 100w max.



WET

LARGE ONE LIGHT DOWNLIGHT OUTDOOR WALL LANTERN

W: 9.5" H: 18.75" E: 8.75"
Height from center of outlet box up: 2.75"

T24

8438701-12
(1) Medium Base 100w max.



WET

SMALL ONE LIGHT UPLIGHT OUTDOOR WALL LANTERN

W: 6.5" H: 16.25" E: 7.75"
Height from center of outlet box up: 13.5"

T24

8538701-12
(1) Medium Base 100w max.



WET

SMALL ONE LIGHT DOWNLIGHT OUTDOOR WALL LANTERN

W: 6.5" H: 12.5" E: 7.75"
Height from center of outlet box up: 2.75"

T24

8338701-12
(1) Medium Base 100w max.



DAMP

ONE LIGHT OUTDOOR PENDANT

D: 9.5" H: 16.75"
6' wire pre-laced through 3' chain

T24

6238701-12
(1) Medium Base 100w max.



WET

ONE LIGHT OUTDOOR POST LANTERN

D: 9.5" H: 27.25"

T24

8238701-12
(1) Medium Base 100w max.



WET +

EXTRA LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 8.5" H: 19.25" E: 9.5"
Height from center of outlet box up: 16.5" down: 2.75"

T24

84532-746
(1) Medium Base 100w max.

T24 EN★

84532EN3-746
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 8.5" H: 15" E: 9.5"
Height from center of outlet box up: 2.75"

T24

84531-746
(1) Medium Base 100w max.

T24 EN★

84531EN3-746
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET +

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 6.5" H: 15" E: 8.5"
Height from center of outlet box up: 12.25" down: 2.75"

T24

84530-746
(1) Medium Base 100w max.

T24 EN★

84530EN3-746
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 6.5" H: 11.5" E: 8.5"
Height from center of outlet box up: 2.75"

T24

84529-746
(1) Medium Base 100w max.

T24 EN★

84529EN3-746
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



DAMP +

ONE LIGHT OUTDOOR SEMI-FLUSH CONVERTIBLE PENDANT

L: 6.5" W: 6.5" H: 10.5" Semi-flush H: 9.75"
10' wire pre-laced through 4" chain

T24

60529-746
(1) Medium Base 100w max.

T24 EN★

60529EN3-746
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET

ONE LIGHT OUTDOOR POST LANTERN

L: 8.5" W: 8.5" H: 20.25"

T24

82529-746
(1) Medium Base 100w max.

T24 EN★

82529EN3-746
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET +
EXTRA LARGE ONE LIGHT OUTDOOR WALL LANTERN
 W: 8.5" H: 19.25" E: 9.5"
 Height from center of outlet box up: 16.5" down: 2.75"

T24
84032-746
 (1) Medium Base 100w max.



WET
LARGE ONE LIGHT OUTDOOR WALL LANTERN
 W: 8.5" H: 15" E: 9.5"
 Height from center of outlet box up: 2.75"

T24
84031-746
 (1) Medium Base 100w max.



WET +
MEDIUM ONE LIGHT OUTDOOR WALL LANTERN
 W: 6.5" H: 15" E: 8.5"
 Height from center of outlet box up: 12.25" down: 2.75"

T24
84030-746
 (1) Medium Base 100w max.



WET
SMALL ONE LIGHT OUTDOOR WALL LANTERN
 W: 6.5" H: 11.5" E: 8.5"
 Height from center of outlet box up: 2.75"

T24
84029-746
 (1) Medium Base 100w max.



DAMP +
ONE LIGHT OUTDOOR SEMI-FLUSH CONVERTIBLE PENDANT
 L: 6.5" W: 6.5" H: 10.5" Semi-flush H: 9.75"
 10' wire pre-laced through 4" chain

T24
60029-746
 (1) Medium Base 100w max.



WET
ONE LIGHT OUTDOOR POST LANTERN
 L: 8.5" W: 8.5" H: 20.25"

T24
82029-746
 (1) Medium Base 100w max.



WET +
EXTRA LARGE ONE LIGHT OUTDOOR WALL LANTERN
 W: 8.5" H: 19.25" E: 9.5"
 Height from center of outlet box up: 16.5" down: 2.75"

T24
84532-12
 (1) Medium Base 100w max.

T24 EN★
84532EN3-12
 (1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET
LARGE ONE LIGHT OUTDOOR WALL LANTERN
 W: 8.5" H: 15" E: 9.5"
 Height from center of outlet box up: 2.75"

T24
84531-12
 (1) Medium Base 100w max.

T24 EN★
84531EN3-12
 (1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET +
MEDIUM ONE LIGHT OUTDOOR WALL LANTERN
 W: 6.5" H: 15" E: 8.5"
 Height from center of outlet box up: 12.25" down: 2.75"

T24
84530-12
 (1) Medium Base 100w max.

T24 EN★
84530EN3-12
 (1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET
SMALL ONE LIGHT OUTDOOR WALL LANTERN
 W: 6.5" H: 11.5" E: 8.5"
 Height from center of outlet box up: 2.75"

T24
84529-12
 (1) Medium Base 100w max.

T24 EN★
84529EN3-12
 (1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



DAMP +
ONE LIGHT OUTDOOR SEMI-FLUSH CONVERTIBLE PENDANT
 L: 6.5" W: 6.5" H: 10.5" Semi-flush H: 9.75"
 10' wire pre-laced through 4" chain

T24
60529-12
 (1) Medium Base 100w max.

T24 EN★
60529EN3-12
 (1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET
ONE LIGHT OUTDOOR POST LANTERN
 L: 8.5" W: 8.5" H: 20.25"

T24
82529-12
 (1) Medium Base 100w max.

T24 EN★
82529EN3-12
 (1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET +

EXTRA LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 8.5" H: 19.25" E: 9.5"
Height from center of outlet box up: 16.5" down: 2.75"

T24

84032-12

(1) Medium Base 100w max.



WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 8.5" H: 15" E: 9.5"
Height from center of outlet box up: 2.75"

T24

84031-12

(1) Medium Base 100w max.



WET +

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 6.5" H: 15" E: 8.5"
Height from center of outlet box up: 12.25" down: 2.75"

T24

84030-12

(1) Medium Base 100w max.



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 6.5" H: 11.5" E: 8.5"
Height from center of outlet box up: 2.75"

T24

84029-12

(1) Medium Base 100w max.



DAMP +

ONE LIGHT OUTDOOR SEMI-FLUSH CONVERTIBLE PENDANT

L: 6.5" W: 6.5" H: 10.5" Semi-flush H: 9.75"
10' wire pre-laced through 4" chain

T24

60029-12

(1) Medium Base 100w max.



WET

ONE LIGHT OUTDOOR POST LANTERN

L: 8.5" W: 8.5" H: 20.25"

T24

82029-12

(1) Medium Base 100w max.

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 7.75" H: 23.5" E: 10.75"
Height from center of outlet box up: 16"

T24

89103-12

(1) Medium Base 100w max.

T24

EN★

89103EN3-12

(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 6.25" H: 19.75" E: 10"
Height from center of outlet box up: 15.25"

T24

89102-12

(1) Medium Base 100w max.

T24

EN★

89102EN3-12

(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 6" H: 9.75" E: 6.75"
Height from center of outlet box up: 2.5"

T24

89101-12

(1) Medium Base 100w max.

T24

EN★

89101EN3-12

(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



ETCHED GLASS, WHITE INSIDE

DAMP

TWO LIGHT OUTDOOR CEILING FLUSH MOUNT

D: 12.75" H: 7.5"

T24

79136-12

(2) Medium Base 60w max.

T24

EN★

79136EN3-12

(2) Med. Base LED 3000k, 9.5w, 800 lumen lamps incl.

WET

LARGE TWO LIGHT OUTDOOR WALL LANTERN

W: 7.75" H: 23.5" E: 10.75"
Height from center of outlet box up: 16"

T24

88201-12
(2) Candelabra Base 60w max.

T24 EN★

88201EN-12
(2) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 6.25" H: 19.75" E: 10"
Height from center of outlet box up: 15.25"

T24

88200-12
(1) Medium Base 100w max.



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 6" H: 9.75" E: 6.75"
Height from center of outlet box up: 2.5"

T24

85200-12
(1) Medium Base 100w max.

WET

TWO LIGHT OUTDOOR POST LANTERN

D: 7.75" H: 23"

T24

82200-12
(2) Candelabra Base 60w max.

T24 EN★

82200EN-12
(2) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



DAMP

TWO LIGHT OUTDOOR CEILING FLUSH MOUNT

D: 12.75" H: 7.5"

T24

78136-12
(2) Medium Base 60w max.



WET +

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 7" H: 25.5" H Without Tail: 17.75" E: 7"
Height from center of outlet box
up: 15"

T24

8510-02
(1) Medium Base 100w max.



WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 7" H: 12.25" E: 7.25"
Height from center of outlet box
up: 3.25"

T24

8509-02
(1) Medium Base 100w max.



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 5.75" H: 10.5" E: 5.75"
Height from center of outlet box
up: 7.25"

T24

8507-02
(1) Medium Base 100w max.



DAMP +

ONE LIGHT OUTDOOR SEMI-FLUSH CONVERTIBLE PENDANT

D: 7" H: 12.5" Semi Flush H: 13"
10' wire pre-laced through 4' chain

T24

6008-02
(1) Medium Base 100w max.



WET

ONE LIGHT OUTDOOR POST LANTERN

D: 7" H: 15.75"

T24

8209-02
(1) Medium Base 100w max.

WET +

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7" H: 25.5" H Without Tail: 17.75" E: 7"
Height from center of outlet box
up: 15"

T24

8510-12
(1) Medium Base 100w max.



WET

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7" H: 12.25" E: 7.25"
Height from center of outlet box
up: 3.25"

T24

8509-12
(1) Medium Base 100w max.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 5.75" H: 10.5" E: 5.75"
Height from center of outlet box
up: 7.25"

T24

8507-12
(1) Medium Base 100w max.



DAMP +

**ONE LIGHT
OUTDOOR SEMI-FLUSH
CONVERTIBLE PENDANT**

D: 7" H: 12.5" Semi Flush H: 13"
10' wire pre-laced through 4' chain

T24

6008-12
(1) Medium Base 100w max.



WET

**ONE LIGHT
OUTDOOR POST LANTERN**

D: 7" H: 15.75"

T24

8209-12
(1) Medium Base 100w max.

LANCASTER

WET

LARGE THREE LIGHT OUTDOOR WALL LANTERN

W: 11.75" H: 23" E: 11"
Height from center of outlet box
up: 10"

T24

8040-965
(3) Candelabra Base 40w max.

T24 EN★

8040EN-965
(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.

See more Antique Brushed Nickel Finish
with Clear Curved Beveled Glass on p.514



ANTIQUE BRUSHED NICKEL FINISH
CLEAR CURVED BEVELED GLASS

WET

LARGE THREE LIGHT OUTDOOR WALL LANTERN

W: 11.75" H: 23" E: 11"
Height from center of outlet box
up: 10"

T24

8040-02
(3) Candelabra Base 40w max.

T24 EN★

8040EN-02
(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.

See more Polished Bronze Finish
with Clear Curved Beveled Glass on p.515



POLISHED BRASS FINISH
CLEAR CURVED BEVELED GLASS

WET

**LARGE THREE LIGHT
OUTDOOR WALL LANTERN**

W: 11.75" H: 23" E: 11"
Height from center of outlet box
up: 10"

T24

8040-71

(3) Candelabra Base 40w max.

T24 EN★

8040EN-71

(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.

See more Antique Bronze Finish
with Clear Curved Beveled Glass on p.516



ANTIQUE BRONZE FINISH
CLEAR CURVED BEVELED GLASS

WET

**LARGE THREE LIGHT
OUTDOOR WALL LANTERN**

W: 11.75" H: 23" E: 11"
Height from center of outlet box
up: 10"

T24

8040-12

(3) Candelabra Base 40w max.

T24 EN★

8040EN-12

(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.

See more Black Finish
with Clear Curved Beveled Glass on p.517



BLACK FINISH
CLEAR CURVED BEVELED GLASS



WET

**LARGE TWO LIGHT
OUTDOOR WALL LANTERN**

W: 10" H: 20.5" E: 9.5"
Height from center of outlet box
up: 9.5"

T24

8039-965
(2) Candelabra Base 40w max.

T24 EN★

8039EN-965
(2) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7.75" H: 14" E: 7.5"
Height from center of outlet box
up: 6.5"

T24

8067-965
(1) Medium Base 100w max.



WET

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7.75" H: 12" E: 7.5"
Height from center of outlet box
up: 4.5"

T24

8038-965
(1) Medium Base 100w max.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7" H: 12" E: 7"
Height from center of outlet box
up: 5.75"

T24

8037-965
(1) Medium Base 100w max.



DAMP

**THREE LIGHT
OUTDOOR PENDANT**

D: 11.75" H: 20.75"
10' wire pre-laced through 4' chain

T24

6039-965
(3) Candelabra Base 40w max.

T24 EN★

6039EN-965
(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

**THREE LIGHT
OUTDOOR POST LANTERN**

D: 11.75" H: 24"

T24

8239-965
(3) Candelabra Base 60w max.

T24 EN★

8239EN-965
(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

**TWO LIGHT
OUTDOOR POST LANTERN**

D: 10" H: 21.5"

T24

8229-965
(2) Candelabra Base 60w max.

T24 EN★

8229EN-965
(2) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

**LARGE TWO LIGHT
OUTDOOR WALL LANTERN**

W: 10" H: 20.5" E: 9.5"
Height from center of outlet box
up: 9.5"

T24

8039-02
(2) Candelabra Base 40w max.

T24 EN★

8039EN-02
(2) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7.75" H: 14" E: 7.5"
Height from center of outlet box
up: 6.5"

T24

8067-02
(1) Medium Base 100w max.



WET

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7.75" H: 12" E: 7.5"
Height from center of outlet box
up: 4.5"

T24

8038-02
(1) Medium Base 100w max.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7" H: 12" E: 7"
Height from center of outlet box
up: 5.75"

T24

8037-02
(1) Medium Base 100w max.



DAMP

**THREE LIGHT
OUTDOOR PENDANT**

D: 11.75" H: 20.75"
10' wire pre-laced through 4' chain

T24

6039-02
(3) Candelabra Base 40w max.

T24 EN★

6039EN-02
(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

**THREE LIGHT
OUTDOOR POST LANTERN**

D: 11.75" H: 24"

T24

8239-02
(3) Candelabra Base 60w max.

T24 EN★

8239EN-02
(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

**TWO LIGHT
OUTDOOR POST LANTERN**

D: 10" H: 21.5"

T24

8229-02
(2) Candelabra Base 60w max.

T24 EN★

8229EN-02
(2) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET
**LARGE TWO LIGHT
 OUTDOOR WALL LANTERN**

W: 10" H: 20.5" E: 9.5"
 Height from center of outlet box
 up: 9.5"

T24
8039-71
 (2) Candelabra Base 40w max.

T24 EN★
8039EN-71
 (2) Cand. Base LED 2700k,
 3.5w, 350 lumen lamps incl.



WET
**MEDIUM ONE LIGHT
 OUTDOOR WALL LANTERN**

W: 7.75" H: 14" E: 7.5"
 Height from center of outlet box
 up: 6.5"

T24
8067-71
 (1) Medium Base 100w max.



WET
**MEDIUM ONE LIGHT
 OUTDOOR WALL LANTERN**

W: 7.75" H: 12" E: 7.5"
 Height from center of outlet box
 up: 4.5"

T24
8038-71
 (1) Medium Base 100w max.



WET
**SMALL ONE LIGHT
 OUTDOOR WALL LANTERN**

W: 7" H: 12" E: 7"
 Height from center of outlet box
 up: 5.75"

T24
8037-71
 (1) Medium Base 100w max.



DAMP
**THREE LIGHT
 OUTDOOR PENDANT**

D: 11.75" H: 20.75"
 10' wire pre-laced through 4' chain

T24
6039-71
 (3) Candelabra Base 40w max.

T24 EN★
6039EN-71
 (3) Cand. Base LED 2700k,
 3.5w, 350 lumen lamps incl.



WET
**THREE LIGHT
 OUTDOOR POST LANTERN**

D: 11.75" H: 24"

T24
8239-71
 (3) Candelabra Base 60w max.

T24 EN★
8239EN-71
 (3) Cand. Base LED 2700k,
 3.5w, 350 lumen lamps incl.



WET
**TWO LIGHT
 OUTDOOR POST LANTERN**

D: 10" H: 21.5"

T24
8229-71
 (2) Candelabra Base 60w max.

T24 EN★
8229EN-71
 (2) Cand. Base LED 2700k,
 3.5w, 350 lumen lamps incl.



WET

**LARGE TWO LIGHT
OUTDOOR WALL LANTERN**

W: 10" H: 20.5" E: 9.5"
Height from center of outlet box
up: 9.5"

T24

8039-12
(2) Candelabra Base 40w max.

T24 EN★

8039EN-12
(2) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7.75" H: 14" E: 7.5"
Height from center of outlet box
up: 6.5"

T24

8067-12
(1) Medium Base 100w max.



WET

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7.75" H: 12" E: 7.5"
Height from center of outlet box
up: 4.5"

T24

8038-12
(1) Medium Base 100w max.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7" H: 12" E: 7"
Height from center of outlet box
up: 5.75"

T24

8037-12
(1) Medium Base 100w max.



DAMP

**THREE LIGHT
OUTDOOR PENDANT**

D: 11.75" H: 20.75"
10' wire pre-laced through 4' chain

T24

6039-12
(3) Candelabra Base 40w max.

T24 EN★

6039EN-12
(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

**THREE LIGHT
OUTDOOR POST LANTERN**

D: 11.75" H: 24"

T24

8239-12
(3) Candelabra Base 60w max.

T24 EN★

8239EN-12
(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



WET

**TWO LIGHT
OUTDOOR POST LANTERN**

D: 10" H: 21.5"

T24

8229-12
(2) Candelabra Base 60w max.

T24 EN★

8229EN-12
(2) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.

WET

EXTRA LARGE TWO LIGHT OUTDOOR WALL LANTERN

W: 7" H: 20.25" E: 7.75"
Height from center of outlet box up: 6.5"

T24

8468-71
(2) Candelabra Base 40w max.

T24 EN★

8468EN-71
(2) Cand. Base LED 2700k, 3.5w, 350 lumen lamps incl.



WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 7" H: 17" E: 8"
Height from center of outlet box up: 6.5"

T24

8458-71
(1) Medium Base 100w max.



ETCHED TIFFANY GLASS WITH WHITE ALUMINUM BACKING

WET ☾

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 7" H: 17" E: 8"
Height from center of outlet box up: 6.5"

T24

84158D-71
(1) Medium Base 100w max.

T24 EN★

84158DEN3-71
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 5.25" H: 12.5" E: 5.75"
Height from center of outlet box up: 6"

T24

8457-71
(1) Medium Base 100w max.



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 4" H: 11.25" E: 5.75"
Height from center of outlet box up: 6"

T24

8456-71
(1) Medium Base 100w max.



WET

ONE LIGHT OUTDOOR POST LANTERN

L: 7" W: 7" H: 17.25"

T24

8257-71
(1) Medium Base 100w max.

WET

EXTRA LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 7" H: 20.25" W: 7.75"
Height from center of outlet box up: 6.5"

T24

84670-71
(1) Medium Base 100w max.

T24 EN★

84670EN3-71
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 7" H: 17" E: 8"
Height from center of outlet box up: 6.5"

T24

84580-71
(1) Medium Base 100w max.

T24 EN★

84580EN3-71
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



ETCHED TIFFANY GLASS WITH WHITE ALUMINUM BACKING

WET ☾

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 5.25" H: 12.5" E: 5.75"
Height from center of outlet box up: 6"

T24

84157D-71
(1) Medium Base 100w max.

T24 EN★

84157DEN3-71
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.

WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 5.25" H: 12.5" E: 5.75"
Height from center of outlet box up: 6"

T24

84570-71
(1) Medium Base 100w max.

T24 EN★

84570EN3-71
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.

WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 4" H: 11.25" E: 5.75"
Height from center of outlet box up: 6"

T24

84560-71
(1) Medium Base 100w max.

T24 EN★

84560EN3-71
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.

WET

ONE LIGHT OUTDOOR POST LANTERN

L: 7" W: 7" H: 17.25"

T24

82570-71
(1) Medium Base 100w max.

T24 EN★

82570EN3-71
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET

EXTRA LARGE TWO LIGHT OUTDOOR WALL LANTERN

W: 7" H: 20.25" E: 7.75"
Height from center of outlet box up: 6.5"

T24

8468-965
(2) Candelabra Base 40w max.

T24 EN★

8468EN-965
(2) Cand. Base LED 2700k, 3.5w, 350 lumen lamps incl.



WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 7" H: 17" E: 8"
Height from center of outlet box up: 6.5"

T24

8458-965
(1) Medium Base 100w max.



WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 5.25" H: 12.5" E: 5.75"
Height from center of outlet box up: 6"

T24

8457-965
(1) Medium Base 100w max.



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 4" H: 11.25" E: 5.75"
Height from center of outlet box up: 6"

T24

8456-965
(1) Medium Base 100w max.



WET

ONE LIGHT OUTDOOR POST LANTERN

L: 7" W: 7" H: 17.25"

T24

8257-965
(1) Medium Base 100w max.

WET

EXTRA LARGE TWO LIGHT OUTDOOR WALL LANTERN

W: 7" H: 20.25" E: 7.75"
Height from center of outlet box up: 6.5"

T24

8468-12
(2) Candelabra Base 40w max.

T24 EN★

8468EN-12
(2) Cand. Base LED 2700k, 3.5w, 350 lumen lamps incl.



WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 7" H: 17" E: 8"
Height from center of outlet box up: 6.5"

T24

8458-12
(1) Medium Base 100w max.



ETCHED TIFFANY GLASS
PAINTED WHITE INSIDE

WET ☾

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 7" H: 17" E: 8"
Height from center of outlet box up: 6.5"

T24

84158D-12
(1) Medium Base 100w max.

T24 EN★

84158DEN3-12
(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 5.25" H: 12.5" E: 5.75"
Height from center of outlet box up: 6"

T24

8457-12
(1) Medium Base 100w max.



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 4" H: 11.25" E: 5.75"
Height from center of outlet box up: 6"

T24

8456-12
(1) Medium Base 100w max.



WET

ONE LIGHT OUTDOOR POST LANTERN

L: 7" W: 7" H: 17.25"

T24

8257-12
(1) Medium Base 100w max.

NEW CASTLE

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 4.25" H: 8.25" E: 5.5"
Height from center of outlet box
up: 2.75"

T24

8592-15
(1) Medium Base 100w max.



WHITE FINISH
CLEAR GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 4.25" H: 8.25" E: 5.5"
Height from center of outlet box
up: 2.75"

T24

8592001-15
(1) Medium Base 100w max.

T24 EN★

8592001EN3-15
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WHITE FINISH
SATIN ETCHED GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 4.25" H: 8.25" E: 5.5"
Height from center of outlet box
up: 2.75"

T24

8592-965
(1) Medium Base 100w max.



ANTIQUE BRUSHED NICKEL FINISH
CLEAR GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 4.25" H: 8.25" E: 5.5"
Height from center of outlet box
up: 2.75"

T24

8592001-965
(1) Medium Base 100w max.

T24 EN★

8592001EN3-965
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



ANTIQUE BRUSHED NICKEL FINISH
SATIN ETCHED GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 4.25" H: 8.25" E: 5.5"
Height from center of outlet box
up: 2.75"

T24

8592-71

(1) Medium Base 100w max.



ANTIQUE BRONZE FINISH
CLEAR GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 4.25" H: 8.25" E: 5.5"
Height from center of outlet box
up: 2.75"

T24

8592001-71

(1) Medium Base 100w max.

T24 EN★

8592001EN3-71

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



ANTIQUE BRONZE FINISH
SATIN ETCHED GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 4.25" H: 8.25" E: 5.5"
Height from center of outlet box
up: 2.75"

T24

8592-12

(1) Medium Base 100w max.



BLACK FINISH
CLEAR GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 4.25" H: 8.25" E: 5.5"
Height from center of outlet box
up: 2.75"

T24

8592001-12

(1) Medium Base 100w max.

T24 EN★

8592001EN3-12

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



BLACK FINISH
SATIN ETCHED GLASS

BRENTWOOD

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 10.25" H: 28" E: 10.75"
Height from center of outlet box
up: 15"

T24

8823-12

(1) Medium Base 100w max.

See more Black Powdercoat Finish
with Clear Glass on p.526



BLACK POWDERCOAT FINISH
CLEAR GLASS

WET

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 10.25" H: 28" E: 10.75"
Height from center of outlet box
up: 15"

T24

89823-12

(1) Medium Base 100w max.

T24 EN★

89823EN3-12

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

See more Black Powdercoat Finish
with Smooth White Glass on p.527



BLACK POWDERCOAT FINISH
SMOOTH WHITE GLASS



WET

**MEDIUM ONE LIGHT
DOWNLIGHT OUTDOOR
WALL LANTERN**

W: 10.25" H: 18" E: 10.75"
Height from center of outlet box
up: 4.75"

T24

8825-12

(1) Medium Base 100w max.



WET

**MEDIUM ONE LIGHT
UPLIGHT OUTDOOR
WALL LANTERN**

W: 10.25" H: 19.75" E: 10.75"
Height from center of outlet box
up: 15"

T24

8824-12

(1) Medium Base 100w max.



WET

**SMALL ONE
LIGHT OUTDOOR
WALL LANTERN**

W: 7" H: 10.25" E: 7"
Height from center of outlet box
up: 6"

T24

8822-12

(1) Medium Base 60w max.



DAMP

**ONE LIGHT
OUTDOOR PENDANT**

D: 10.25" H: 18.75"
10' wire pre-laced through 3' chain

T24

6025-12

(1) Medium Base 100w max.



WET

**THREE LIGHT
OUTDOOR POST LANTERN**

D: 13" H: 25.75"

T24

8231-12

(3) Candelabra Base 60w max.

T24 EN★

8231EN-12

(3) Cand. Base LED 2700k,
3.5w, 350 lumen lamps incl.



CLEAR BEVELED GLASS

DAMP

**TWO LIGHT OUTDOOR
CEILING FLUSH MOUNT**

D: 12.75" H: 7.5"

T24

78136-12

(2) Medium Base 60w max.



WET

**MEDIUM ONE LIGHT
DOWNLIGHT OUTDOOR
WALL LANTERN**

W: 10.25" H: 18" E: 10.75"
Height from center of outlet box
up: 4.75"

T24

89825-12
(1) Medium Base 100w max.

T24 EN★

89825EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**MEDIUM ONE LIGHT
UPLIGHT OUTDOOR
WALL LANTERN**

W: 10.25" H: 19.75" E: 10.75"
Height from center of outlet box
up: 15"

T24

89824-12
(1) Medium Base 100w max.

T24 EN★

89824EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**SMALL ONE
LIGHT OUTDOOR
WALL LANTERN**

W: 7" H: 10.25" E: 7"
Height from center of outlet box
up: 6"

T24

89822-12
(1) Medium Base 60w max.

T24 EN★

89822EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

**ONE LIGHT
OUTDOOR PENDANT**

D: 10.25" H: 18.75"
10' wire pre-laced through 3' chain

T24

69025-12
(1) Medium Base 100w max.

T24 EN★

69025EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**ONE LIGHT
OUTDOOR POST LANTERN**

D: 13" H: 25.75"

T24

89025-12
(1) Medium Base 100w max.

T24 EN★

89025EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



ETCHED GLASS, WHITE INSIDE

DAMP

**TWO LIGHT OUTDOOR
CEILING FLUSH MOUNT**

D: 12.75" H: 7.5"

T24

79136-12
(2) Medium Base 60w max.

T24 EN★

79136EN3-12
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

WET SS

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 9" H: 18" E: 6.5"

Height from center of outlet box
up: 4.75"

T24

8719601-12

(1) Medium Base 75w max.

T24 EN★

8719601EN3-12

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 7" H: 13" E: 5.75"

Height from center of outlet box
up: 3.625"

T24

8619601-12

(1) Medium Base 75w max.

T24 EN★

8619601EN3-12

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 6" H: 9" E: 5"

Height from center of outlet box
up: 3.75"

T24

8519601-12

(1) Medium Base 75w max.

T24 EN★

8519601EN3-12

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 9" H: 18" E: 6.5"
Height from center of outlet box
up: 4.75"

T24

8719601-44

(1) Medium Base 75w max.

T24 EN★

8719601EN3-44

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7" H: 13" E: 5.75"
Height from center of outlet box
up: 3.625"

T24

8619601-44

(1) Medium Base 75w max.

T24 EN★

8619601EN3-44

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET SS

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 6" H: 9" E: 5"
Height from center of outlet box
up: 3.75"

T24

8519601-44

(1) Medium Base 75w max.

T24 EN★

8519601EN3-44

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



MULLBERRY HILL

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 5.75" H: 8.75" E: 4.5"
Height from center of outlet box
up: 5"

T24

8588-15
(1) Medium Base 100w max.



WHITE FINISH
CLEAR BEVELED GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 5.75" H: 8.75" E: 4.5"
Height from center of outlet box
up: 5"

T24

8788-15
(1) Medium Base 100w max.

T24 EN★

8988EN3-15
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WHITE FINISH
WHITE GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 5.75" H: 8.75" E: 4.5"
Height from center of outlet box
up: 5"

T24

8588-155
(1) Medium Base 100w max.



PEWTER FINISH
CLEAR BEVELED GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 5.75" H: 8.75" E: 4.5"
Height from center of outlet box
up: 5"

T24

8788-155
(1) Medium Base 100w max.

T24 EN★

8988EN3-155
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



PEWTER FINISH
WHITE GLASS

WET

**ONE LIGHT
OUTDOOR WALL LANTERN**

W: 5.75" H: 8.75" E: 4.5"
Height from center of outlet box
up: 5"

T24

8588-10
(1) Medium Base 100w max.



BRONZE FINISH
CLEAR BEVELED GLASS

WET

**ONE LIGHT
OUTDOOR WALL LANTERN**

W: 5.75" H: 8.75" E: 4.5"
Height from center of outlet box
up: 5"

T24

8788-10
(1) Medium Base 100w max.

T24 **EN★**

8988EN3-10
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



BRONZE FINISH
WHITE GLASS

WET

**ONE LIGHT
OUTDOOR WALL LANTERN**

W: 5.75" H: 8.75" E: 4.5"
Height from center of outlet box
up: 5"

T24

8588-12
(1) Medium Base 100w max.



BLACK FINISH
CLEAR BEVELED GLASS

WET

**ONE LIGHT
OUTDOOR WALL LANTERN**

W: 5.75" H: 8.75" E: 4.5"
Height from center of outlet box
up: 5"

T24

8788-12
(1) Medium Base 100w max.

T24 **EN★**

8988EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



BLACK FINISH
WHITE GLASS

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 8.5" H: 16.75" E: 10.75"
Height from center of outlet box
up: 6"

T24

8624401-71
(1) Medium Base 100w max.



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 6" H: 12.25" E: 8"
Height from center of outlet box
up: 4.75"

T24

8524401-71
(1) Medium Base 100w max.



DAMP

ONE LIGHT OUTDOOR PENDANT

D: 10.25" H: 18.25"
10' wire pre-laced through 3' chain

T24

6224401-71
(1) Medium Base 100w max.



WET

ONE LIGHT OUTDOOR POST LANTERN

D: 10.25" H: 22.25"

T24

8224401-71
(1) Medium Base 100w max.



DAMP

TWO LIGHT OUTDOOR FLUSH MOUNT

D: 12.25" H: 5.5"

T24

7824402-71
(2) Medium Base 75w max.

WET

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 8.5" H: 16.75" E: 10.75"
Height from center of outlet box
up: 6"

T24

8624451-71
(1) Medium Base 100w max.

T24 EN★

8624451EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 EN★ ☾

8624451DEN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 6" H: 12.25" E: 8"
Height from center of outlet box
up: 4.75"

T24

8524451-71
(1) Medium Base 100w max.

T24 EN★

8524451EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 EN★ ☾

8524451DEN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

**ONE LIGHT
OUTDOOR PENDANT**

D: 10.25" H: 18.25"
10' wire pre-laced through 3' chain

T24

6224451-71
(1) Medium Base 100w max.

T24 EN★

6224451EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**ONE LIGHT
OUTDOOR POST LANTERN**

D: 10.25" H: 22.25"

T24

8224451-71
(1) Medium Base 100w max.

T24 EN★

8224451EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

**TWO LIGHT
OUTDOOR FLUSH MOUNT**

D: 12.25" H: 5.5"

T24

7824452-71
(2) Medium Base 75w max.

T24 EN★

7824452EN3-71
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

WET

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 8.5" H: 16.75" E: 10.75"
Height from center of outlet box
up: 6"

T24

8624401-12
(1) Medium Base 100w max.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 6" H: 12.25" E: 8"
Height from center of outlet box
up: 4.75"

T24

8524401-12
(1) Medium Base 100w max.



DAMP

**ONE LIGHT
OUTDOOR PENDANT**

D: 10.25" H: 18.25"
10' wire pre-laced through 3' chain

T24

6224401-12
(1) Medium Base 100w max.



WET

**ONE LIGHT
OUTDOOR POST LANTERN**

D: 10.25" H: 22.25"

T24

8224401-12
(1) Medium Base 100w max.



DAMP

**TWO LIGHT
OUTDOOR FLUSH MOUNT**

D: 12.25" H: 5.5"

T24

7824402-12
(2) Medium Base 75w max.

WET

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 8.5" H: 16.75" E: 10.75"
Height from center of outlet box
up: 6"

T24

8624451-12
(1) Medium Base 100w max.

T24 EN★

8624451EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 EN★ ☾

8624451DEN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 6" H: 12.25" E: 8"
Height from center of outlet box
up: 4.75"

T24

8524451-12
(1) Medium Base 100w max.

T24 EN★

8524451EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 EN★ ☾

8524451DEN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

**ONE LIGHT
OUTDOOR PENDANT**

D: 10.25" H: 18.25"
10' wire pre-laced through 3' chain

T24

6224451-12
(1) Medium Base 100w max.

T24 EN★

6224451EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**ONE LIGHT
OUTDOOR POST LANTERN**

D: 10.25" H: 22.25"

T24

8224451-12
(1) Medium Base 100w max.

T24 EN★

8224451EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

**TWO LIGHT
OUTDOOR FLUSH MOUNT**

D: 12.25" H: 5.5"

T24

7824452-12
(2) Medium Base 75w max.

T24 EN★

7824452EN3-12
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.



WET ADA +

**ONE LIGHT
OUTDOOR WALL LANTERN**

L: 10" W: 5" H: 3.75" E: 3.75"
Height from center of outlet box
horizontal: 2.5" vertical: 5"

T24

8335-15
(1) Medium Base 60w max.

T24 EN★

8335EN3-15
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET ADA +

**ONE LIGHT
OUTDOOR WALL LANTERN**

L: 10" W: 5" H: 4" E: 4"
Height from center of outlet box
horizontal: 2.5" vertical: 5"

T24

89806-15
(1) Medium Base 60w max.

T24 EN★

89806EN3-15
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET ADA

**ONE LIGHT
OUTDOOR WALL LANTERN**

L: 10" W: 5" H: 4" E: 4"
Height from center of outlet box
up: 2.5"

T24

89805-15
(1) Medium Base 60w max.

T24 EN★

89805EN3-15
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**ONE LIGHT OUTDOOR
WALL / CEILING MOUNT**

D: 10" H: 5" E: 5"
Height from center of outlet box
up: 5"

T24

83057-15
(1) Medium Base 75w max.

T24 EN★

83057EN3-15
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**ONE LIGHT OUTDOOR
WALL / CEILING MOUNT**

D: 10" H: 5" E: 5"
Height from center of outlet box
up: 5"

T24

89807-15
(1) Medium Base 75w max.

T24 EN★

89807EN3-15
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET ADA +

ONE LIGHT OUTDOOR WALL LANTERN

L: 10" W: 5" H: 3.75" E: 3.75"
Height from center of outlet box
horizontal: 2.5" vertical: 5"

T24

8335-12

(1) Medium Base 60w max.

T24 EN★

8335EN3-12

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET ADA +

ONE LIGHT OUTDOOR WALL LANTERN

L: 10" W: 5" H: 4" E: 4"
Height from center of outlet box
horizontal: 2.5" vertical: 5"

T24

89806-12

(1) Medium Base 60w max.

T24 EN★

89806EN3-12

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET ADA

ONE LIGHT OUTDOOR WALL LANTERN

L: 10" W: 5" H: 4" E: 4"
Height from center of outlet box
up: 2.5"

T24

89805-12

(1) Medium Base 60w max.

T24 EN★

89805EN3-12

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

ONE LIGHT OUTDOOR WALL / CEILING MOUNT

D: 10" H: 5" E: 5"
Height from center of outlet box
up: 5"

T24


83057-12

(1) Medium Base 75w max.

T24 EN★

83057EN3-12

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

ONE LIGHT OUTDOOR WALL / CEILING MOUNT

D: 10" H: 5" E: 5"
Height from center of outlet box
up: 5"

T24

89807-12

(1) Medium Base 75w max.

T24 EN★

89807EN3-12

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 11.25" H: 15.75" E: 13.5"
Height from center of outlet box
up: 9.5"

T24

8871-98
(1) Medium Base 100w max.

T24 WOD EN★

887193S-98
LED: 3000k, 14 watts,
1000 gross lumens



BRUSHED STAINLESS FINISH, WHITE INSIDE
CLEAR SEEDED GLASS

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 11.25" H: 15.75" E: 13.5"
Height from center of outlet box
up: 9.5"

T24

8871-44
(1) Medium Base 100w max.

T24 WOD EN★

887193S-44
LED: 3000k, 14 watts,
1000 gross lumens



WEATHERED COPPER FINISH
CLEAR SEEDED GLASS

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 11.25" H: 15.75" E: 13.5"
Height from center of outlet box
up: 9.5"

T24

8871-12
(1) Medium Base 100w max.

T24 WOD EN★

887193S-12
LED: 3000k, 14 watts,
1000 gross lumens



BLACK FINISH
CLEAR SEEDED GLASS

WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 8" H: 11.25" E: 9.25"
Height from center of outlet box
up: 6.25"

T24

8870-98
(1) Medium Base 100w max.

T24 WOD EN★

887093S-98
LED: 3000k, 9 watts,
700 gross lumens



BRUSHED STAINLESS FINISH, WHITE INSIDE
CLEAR SEEDED GLASS

Recommended
Product



SEBRING PENDANTS
Brushed Nickel,
Weathered Copper
p.344

WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 8" H: 11.25" E: 9.25"
Height from center of outlet box
up: 6.25"

T24

8870-44
(1) Medium Base 100w max.

T24 WOD EN★

887093S-44
LED: 3000k, 9 watts,
700 gross lumens



WEATHERED COPPER FINISH
CLEAR SEEDED GLASS

WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 8" H: 11.25" E: 9.25"
Height from center of outlet box
up: 6.25"

T24

8870-12
(1) Medium Base 100w max.

T24 WOD EN★

887093S-12
LED: 3000k, 9 watts,
700 gross lumens



BLACK FINISH
CLEAR SEEDED GLASS

SEBRING

WET

ONE LIGHT OUTDOOR POST LANTERN

D: 11.25" H: 15.75" E: 16"

T24

8269-98

(1) Medium Base 100w max.

T24

WOD EN★

826993S-98

LED: 3000k, 14 watts,
1000 gross lumens



BRUSHED STAINLESS FINISH, WHITE INSIDE
CLEAR SEEDED GLASS

WET

ONE LIGHT OUTDOOR POST LANTERN

D: 11.25" H: 15.75" E: 16"

T24

8269-44

(1) Medium Base 100w max.

T24

WOD EN★

826993S-44

LED: 3000k, 14 watts,
1000 gross lumens



WEATHERED COPPER FINISH
CLEAR SEEDED GLASS

WET

ONE LIGHT OUTDOOR POST LANTERN

D: 11.25" H: 15.75" E: 16"

T24

8269-12

(1) Medium Base 100w max.

T24

WOD EN★

826993S-12

LED: 3000k, 14 watts,
1000 gross lumens



BLACK FINISH
CLEAR SEEDED GLASS

DAMP

**ONE LIGHT
OUTDOOR FLUSH MOUNT**

D: 11.25" H: 9.25"

T24

8869-98

(1) Medium Base 100w max.

T24 WOD EN★

886993S-98

LED: 3000k, 14 watts,
1000 gross lumens



BRUSHED STAINLESS FINISH, WHITE INSIDE
CLEAR SEEDED GLASS

Recommended
Product



SEBRING PENDANTS
Brushed Nickel,
Weathered Copper
p.344

DAMP

**ONE LIGHT
OUTDOOR FLUSH MOUNT**

D: 11.25" H: 9.25"

T24

8869-44

(1) Medium Base 100w max.

T24 WOD EN★

886993S-44

LED: 3000k, 14 watts,
1000 gross lumens



WEATHERED COPPER FINISH
CLEAR SEEDED GLASS

DAMP

**ONE LIGHT
OUTDOOR FLUSH MOUNT**

D: 11.25" H: 9.25"

T24

8869-12

(1) Medium Base 100w max.

T24 WOD EN★

886993S-12

LED: 3000k, 14 watts,
1000 gross lumens



BLACK FINISH
CLEAR SEEDED GLASS

WINNETKA

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 10" H: 14.5" E: 12"

Height from center of outlet box
up: 3.25"

T24

88662-185

(1) Medium Base 150w max.

T24 **EN★**

88662EN3-185

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



FORGED IRON FINISH
SATIN ETCHED GLASS

WET

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**

W: 8" H: 12.25" E: 9.5"
Height from center of outlet box
up: 2.75"

T24

88661-185
(1) Medium Base 100w max.

T24 EN★

88661EN3-185
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 6" H: 10.25" E: 7.5"
Height from center of outlet box
up: 2.5"

T24

88660-185
(1) Medium Base 100w max.

T24 EN★

88660EN3-185
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



Recommended
Products



WINNETKA INDOOR
Brushed Nickel,
Blacksmith
p.78



WINNETKA
WALL / BATH
Brushed Nickel,
Blacksmith
p.435



DAMP

**ONE LIGHT
OUTDOOR PENDANT**

D: 10" H: 20"
10' wire pre-laced through 3' chain

T24

60660-185
(1) Medium Base 100w max.

T24 EN★

60660EN3-185
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**ONE LIGHT OUTDOOR
POST LANTERN**

D: 10" H: 17.75"

T24

82660-185
(1) Medium Base 100w max.

T24 EN★

82660EN3-185
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

**ONE LIGHT OUTDOOR
CEILING FLUSH MOUNT**

D: 10" H: 7"

T24

78660-185
(1) Medium Base 100w max.

T24 EN★

78660EN3-185
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

CROWELL

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 12" H: 19.5" E: 14"
Height from center of outlet box
up: 6"

T24

8847901-71
(1) Medium Base 100w max.

T24 EN★

8847901EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 EN★ ☾

8847901DEN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 9" H: 15" E: 11"
Height from center of outlet box
up: 5"

T24

8747901-71
(1) Medium Base 100w max.

T24 EN★

8747901EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 EN★ ☾

8747901DEN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 6" H: 10" E: 7.5"
Height from center of outlet box
up: 3.25"

T24

8547901-71
(1) Medium Base 60w max.

T24 EN★

8547901EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 EN★ ☾

8547901DEN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**ONE LIGHT
OUTDOOR POST LANTERN**

D: 9" H: 17"

T24

8247901-71

(1) Medium Base 100w max.

T24

EN★

8247901EN3-71

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

**ONE LIGHT
OUTDOOR PENDANT**

D: 9" H: 15.75"

6' wire pre-laced through 3' chain

T24

6247901-71

(1) Medium Base 100w max.

T24

EN★

6247901EN3-71

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

**TWO LIGHT
OUTDOOR CEILING FLUSH MOUNT**

D: 14.25" H: 7"

T24

7847902-71

(2) Medium Base 60w max.

T24

EN★

7847902EN3-71

(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.



CROWELL

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 12" H: 19.5" E: 14"
Height from center of outlet box
up: 6"

T24

8847901-12
(1) Medium Base 100w max.

T24 EN★

8847901EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 EN★ ☾

8847901DEN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 9" H: 15" E: 11"
Height from center of outlet box
up: 5"

T24

8747901-12
(1) Medium Base 100w max.

T24 EN★

8747901EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 EN★ ☾

8747901DEN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 6" H: 10" E: 7.5"
Height from center of outlet box
up: 3.25"

T24

8547901-12
(1) Medium Base 60w max.

T24 EN★

8547901EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 EN★ ☾

8547901DEN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**ONE LIGHT
OUTDOOR POST LANTERN**

D: 9" H: 17"

T24

8247901-12

(1) Medium Base 100w max.

T24

EN★

8247901EN3-12(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP

**ONE LIGHT
OUTDOOR PENDANT**

D: 9" H: 15.75"

6' wire pre-laced through 3' chain

T24

6247901-12

(1) Medium Base 100w max.

T24

EN★

6247901EN3-12(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

DAMP

**TWO LIGHT
OUTDOOR CEILING FLUSH MOUNT**

D: 14.25" H: 7"

T24

7847902-12

(2) Medium Base 60w max.

T24

EN★

7847902EN3-12(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 9" H: 14" E: 10.5"
Height from center of outlet box
up: 3.25"

T24

88027-57

(1) Medium Base 100w max.

See more Weathered Pewter Finish
with Clear Seeded Glass on p.550



WEATHERED PEWTER FINISH
CLEAR SEEDED GLASS

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 9" H: 14" E: 10.5"
Height from center of outlet box
up: 3.25"

T24

89031-57

(1) Medium Base 100w max.

T24 EN★

89031EN3-57

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

8903197S-57

LED: 2700k, 14 watts,
1000 gross lumens

See more Weathered Pewter Finish
with Etched Seeded Glass on p.551



WEATHERED PEWTER FINISH
ETCHED SEEDED GLASS

WET

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 9" H: 14" E: 10.5"
Height from center of outlet box
up: 3.25"

T24

88027-12

(1) Medium Base 100w max.

See more Black Finish
with Clear Seeded Glass on p.552



BLACK FINISH
CLEAR SEEDED GLASS

WET

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 9" H: 14" E: 10.5"
Height from center of outlet box
up: 3.25"

T24

89031-12

(1) Medium Base 100w max.

T24 EN★

89031EN3-12

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

8903197S-12

LED: 2700k, 14 watts,
1000 gross lumens

See more Black Finish
with Etched Seeded Glass on p.553



BLACK FINISH
ETCHED SEEDED GLASS

WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 7" H: 11" E: 8.5"
Height from center of outlet box
up: 3.25"

T24

88025-57
(1) Medium Base 60w max.



DAMP

ONE LIGHT OUTDOOR PENDANT

L: 9" W: 9" H: 13.75"
12' wire pre-laced through 10' chain

T24

62027-57
(1) Medium Base 100w max.



WET

ONE LIGHT OUTDOOR POST LANTERN

L: 9" W: 9" H: 15"

T24

82027-57
(1) Medium Base 100w max.



DAMP

TWO LIGHT OUTDOOR CEILING FLUSH MOUNT

L: 9" W: 9" H: 6.25"

T24

78027-57
(2) Medium Base 75w max.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7" H: 11" E: 8.5"
Height from center of outlet box
up: 3.25"

T24

89029-57
(1) Medium Base 60w max.

T24 EN★

89029EN3-57
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

8902997S-57
LED: 2700k, 9 watts,
700 gross lumens



DAMP

**ONE LIGHT
OUTDOOR PENDANT**

L: 9" W: 9" H: 13.75"
12' wire pre-laced through 10' chain

T24

69029-57
(1) Medium Base 100w max.

T24 EN★

69029EN3-57
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

6902997S-57
LED: 2700k, 14 watts,
1000 gross lumens



WET

**ONE LIGHT
OUTDOOR POST LANTERN**

L: 9" W: 9" H: 15"

T24

89129-57
(1) Medium Base 100w max.

T24 EN★

89129EN3-57
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

**TWO LIGHT OUTDOOR
CEILING FLUSH MOUNT**

L: 9" W: 9" H: 6.25"

T24

79039-57
(1) Medium Base 75w max.

T24 EN★

79039EN3-57
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

7903997S-57
LED: 2700k, 14 watts,
1000 gross lumens



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 7" H: 11" E: 8.5"
Height from center of outlet box
up: 3.25"

T24

88025-12
(1) Medium Base 60w max.



DAMP

ONE LIGHT OUTDOOR PENDANT

L: 9" W: 9" H: 13.75"
12' wire pre-laced through 10' chain

T24

62027-12
(1) Medium Base 100w max.



WET

ONE LIGHT OUTDOOR POST LANTERN

L: 9" W: 9" H: 15"

T24

82027-12
(1) Medium Base 100w max.



DAMP

TWO LIGHT OUTDOOR CEILING FLUSH MOUNT

L: 9" W: 9" H: 6.25"

T24

78027-12
(2) Medium Base 75w max.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7" H: 11" E: 8.5"
Height from center of outlet box
up: 3.25"

T24

89029-12
(1) Medium Base 60w max.

T24 EN★

89029EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

8902997S-12
LED: 2700k, 9 watts,
700 gross lumens



DAMP

**ONE LIGHT
OUTDOOR PENDANT**

L: 9" W: 9" H: 13.75"
12' wire pre-laced through 10' chain

T24

69029-12
(1) Medium Base 100w max.

T24 EN★

69029EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

6902997S-12
LED: 2700k, 14 watts,
1000 gross lumens



WET

**ONE LIGHT
OUTDOOR POST LANTERN**

L: 9" W: 9" H: 15"

T24

89129-12
(1) Medium Base 100w max.

T24 EN★

89129EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

**TWO LIGHT OUTDOOR
CEILING FLUSH MOUNT**

L: 9" W: 9" H: 6.25"

T24

79039-12
(1) Medium Base 75w max.

T24 EN★

79039EN3-12
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

7903997S-12
LED: 2700k, 14 watts,
1000 gross lumens



WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 7.25" H: 11.75" E: 9.5"
Height from center of outlet box
up: 3.25"

T24

89132-12
(1) Medium Base 100w max.

T24 EN★

89132EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 6" H: 10" E: 9"
Height from center of outlet box
up: 3.25"

T24

89131-12
(1) Medium Base 100w max.

T24 EN★

89131EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

ONE LIGHT OUTDOOR PENDANT

L: 7.25" W: 7.25" H: 11.25"
10' wire pre-laced through 6' chain

T24

69131-12
(1) Medium Base 100w max.

T24 EN★

69131EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

ONE LIGHT OUTDOOR POST LANTERN

L: 7.25" W: 7.25" H: 16.5"

T24

89231-12
(1) Medium Base 100w max.

T24 EN★

89231EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

TWO LIGHT OUTDOOR CEILING FLUSH MOUNT

L: 10.75" W: 10.75" H: 6.5"

T24

79131-12
(2) Medium Base 60w max.

T24 EN★

79131EN3-12
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

WET

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7.25" H: 11.75" E: 9.5"
Height from center of outlet box
up: 3.25"

T24

88132-12
(1) Medium Base 100w max.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 6" H: 10" E: 9"
Height from center of outlet box
up: 3.25"

T24

88131-12
(1) Medium Base 100w max.



DAMP

**ONE LIGHT
OUTDOOR PENDANT**

L: 7.25" W: 7.25" H: 11.25"
10' wire pre-laced through 6' chain

T24

60131-12
(1) Medium Base 100w max.



WET

**ONE LIGHT
OUTDOOR POST LANTERN**

L: 7.25" W: 7.25" H: 16.5"

T24

82131-12
(1) Medium Base 100w max.



DAMP

**TWO LIGHT OUTDOOR
CEILING FLUSH MOUNT**

L: 10.75" W: 10.75" H: 6.5"

T24

78131-12
(2) Medium Base 60w max.

MEDFORD LAKES

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 11" H: 17" E: 12"
Height from center of outlet box
up: 9.75"

T24

88882-51

(1) Medium Base 100w max.

T24 EN★

88882EN3-51

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



STATUARY BRONZE FINISH
ETCHED HAMMERED GLASS WITH LIGHT AMBER TINT

WET

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**

W: 9" H: 14.25" E: 10"
Height from center of outlet box
up: 8.5"

T24

88881-51
(1) Medium Base 100w max.

T24 EN★

88881EN3-51
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7" H: 11" E: 8"
Height from center of outlet box
up: 6.5"

T24

88880-51
(1) Medium Base 100w max.

T24 EN★

88880EN3-51
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

**ONE LIGHT
OUTDOOR PENDANT**

L: 11" W: 11" H: 14.75"
10' wire pre-laced through 3' chain

T24

60880-51
(1) Medium Base 100w max.

T24 EN★

60880EN3-51
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WET

**ONE LIGHT
OUTDOOR POST LANTERN**

L: 11" W: 11" H: 16.25"

T24

82880-51
(1) Medium Base 100w max.

T24 EN★

82880EN3-51
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



DAMP

**TWO LIGHT OUTDOOR
CEILING FLUSH MOUNT**

L: 13" W: 13" H: 7"

T24

78880-51
(2) Medium Base 60w max.

T24 EN★

78880EN3-51
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

WRIGHT HOUSE

WET

ONE LIGHT WALL LANTERN

W: 9" H: 13.875" E: 10.4375"
Height from center of outlet box
up: 2.5"

T24

OL8502SBR

(1) Medium Base 100w max.

See more Sorrel Brown Finish
with Striated Ivory Glass on p.560



SORREL BROWN [SBR]
STRIATED IVORY GLASS

WET

ONE LIGHT WALL LANTERN

W: 9" H: 13.875" E: 10.4375"
Height from center of outlet box
up: 2.5"

T24

OL8502ORB

(1) Medium Base 100w max.

See more Oil Rubbed Bronze Finish
with Opal Etched Glass on p.561



OIL RUBBED BRONZE [ORB]
WHITE OPAL ETCHED GLASS

WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 7.875" H: 12.5" E: 9.1875"
Height from center of outlet box
up: 2.375"

T24

OL8501SBR
(1) Medium Base 100w max.



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 7" H: 10.3125" E: 8.3125"
Height from center of outlet box
up: 2.0625"

T24

OL8500SBR
(1) Medium Base 60w max.



DAMP

ONE LIGHT OUTDOOR PENDANT

L: 7.875" W: 7.875" H: 12.25"
Supplied with 15' of wire

T24

OL8511SBR
(1) Medium Base 100w max.



WET

ONE LIGHT OUTDOOR POST LANTERN

L: 9" W: 9" H: 16.1875"

T24

OL8508SBR
(1) Medium Base 100w max.



DAMP

TWO LIGHT OUTDOOR CEILING FLUSH MOUNT

L: 9" W: 9" H: 6.8125"

T24

OL8513SBR
(2) Medium Base 60w max.

WET

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**

W:7.875" H:12.5" E:9.1875"
Height from center of outlet box
up: 2.375"

T24

OL8501ORB
(1) Medium Base 100w max.



WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W:7" H:10.3125" E:8.3125"
Height from center of outlet box
up: 2.0625"

T24

OL8500ORB
(1) Medium Base 60w max.



DAMP

**ONE LIGHT
OUTDOOR PENDANT**

L: 7.875" W: 7.875" H: 12.25"
Supplied with 15' of wire

T24

OL8511ORB
(1) Medium Base 100w max.



WET

**ONE LIGHT
OUTDOOR POST LANTERN**

L: 9" W: 9" H: 16.1875"

T24

OL8508ORB
(1) Medium Base 100w max.



DAMP

**TWO LIGHT
OUTDOOR CEILING
FLUSH MOUNT**

L: 9" W: 9" H:6.8125"

T24

OL8513ORB
(2) Medium Base 60w max.

MARINUS

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 9" H: 15.5" E: 7.625"
Height from center of outlet box
up: 6.875"

T24

8737101-839

(1) Medium Base 75w max.



BLACKSMITH FINISH
CLEAR GLASS

WET

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 7.75" H: 13.75" E: 6.75"
Height from center of outlet box
up: 6"

T24

8637101-839

(1) Medium Base 75w max.



WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 6" H: 11.625" E: 5.625"
Height from center of outlet box
up: 4.875"

T24

8537101-839

(1) Medium Base 75w max.



BARN LIGHT

PRODUCT SHOWN: BARN LIGHT EXTRA LARGE ONE LIGHT OUTDOOR WALL LANTERN IN WEATHERED PEWTER FINISH



WET  

EXTRA LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 16" H: 15" E: 24" to 30"
6" Extendable arm included
Height from center of outlet box
up: 5.875"

T24

8837401-57

(1) Medium Base 100w max.

T24 

8837401EN3-57

(1) Med. Base LED
9.5w 800 lumen lamp incl.

See More Weathered Pewter Finish on p.566



WEATHERED PEWTER FINISH

WET  

EXTRA LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 16" H: 15" E: 24" to 30"
6" Extendable arm included
Height from center of outlet box
up: 5.875"

T24

8837401-12

(1) Medium Base 100w max.

T24 

8837401EN3-12

(1) Med. Base LED
9.5w 800 lumen lamp incl.

See More Black Finish on p.567



BLACK FINISH

BARN LIGHT

WEATHERED PEWTER FINISH [-57]

WET  

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 14" H: 13.5" E: 21.125" to 27.125"
6" Extendable arm included
Height from center of outlet box
up: 5.25"

T24

8737401-57

(1) Medium Base 100w max.

T24 

8737401EN3-57

(1) Med. Base LED
9.5w 800 lumen lamp incl.



WET  

MEDIUM ONE LIGHT OUTDOOR WALL LANTERN

W: 12" H: 10.625" E: 17.125" to 23.125"
6" Extendable arm included
Height from center of outlet box
up: 4.125"

T24

8637401-57

(1) Medium Base 100w max.

T24 

8637401EN3-57

(1) Med. Base LED
9.5w 800 lumen lamp incl.



WET  

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 8" H: 10" E: 12.375" to 18.375"
6" Extendable arm included
Height from center of outlet box
up: 3.375"

T24

8537401-57

(1) Medium Base 100w max.

T24 

8537401EN3-57

(1) Med. Base LED
9.5w 800 lumen lamp incl.

WET  

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 14" H: 13.5" E: 21.125" to 27.125"
6" Extendable arm included
Height from center of outlet box
up: 5.25"

T24

8737401-12
(1) Medium Base 100w max.

T24 

8737401EN3-12
(1) Med. Base LED
9.5w 800 lumen lamp incl.



WET  

**MEDIUM ONE LIGHT
OUTDOOR WALL LANTERN**

W: 12" H: 10.625" E: 17.125" to 23.125"
6" Extendable arm included
Height from center of outlet box
up: 4.125"

T24

8637401-12
(1) Medium Base 100w max.

T24 

8637401EN3-12
(1) Med. Base LED
9.5w 800 lumen lamp incl.



WET  

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 8" H: 10" E: 12.375" to 18.375"
6" Extendable arm included
Height from center of outlet box
up: 3.375"

T24

8537401-12
(1) Medium Base 100w max.

T24 

8537401EN3-12
(1) Med. Base LED
9.5w 800 lumen lamp incl.

FREDRICKSBURG

PRODUCT SHOWN: FREDRICKSBURG LARGE ONE LIGHT OUTDOOR WALL LANTERN IN WEATHERED COPPER FINISH



WET 

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 13.25" H: 16" E: 15.25"
Height from center of outlet box
up: 7.5"

T24

8647701-04

(1) Medium Base 100w max.

T24 EN★

8647701EN3-04

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 WOD EN★

8647793S-04

LED: 3000k, 14 watts,
1000 gross lumens

See more Satin Aluminum Finish on p.570



WET 

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 13.25" H: 16" E: 15.25"
Height from center of outlet box
up: 7.5"

T24

8647701-44

(1) Medium Base 100w max.

T24 EN★

8647701EN3-44

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 WOD EN★

8647793S-44

LED: 3000k, 14 watts,
1000 gross lumens

See more Weathered Copper Finish on p.571



WET 

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 10" H: 12" E: 11.75"
Height from center of outlet box
up: 5.75"

T24

8547701-04
(1) Medium Base 100w max.

T24 

8547701EN3-04
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24  

8547793S-04
LED: 3000k, 14 watts,
1000 gross lumens



DAMP 

ONE LIGHT OUTDOOR PENDANT

D: 13.25" H: 11.5"
10' wire, (3) 12" stems, (1) 6" stem
and sloped ceiling mounting Hardware

T24

6247701-04
(1) Medium Base 100w max.

T24 

6247701EN3-04
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24  

6247793S-04
LED: 3000k, 14 watts,
1000 gross lumens



WET **SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 10" H: 12" E: 11.75"
 Height from center of outlet box
 up: 5.75"

T24

8547701-44

(1) Medium Base 100w max.

T24 **8547701EN3-44**

(1) Med. Base LED 3000k,
 9.5w, 800 lumen lamp incl.

T24  **8547793S-44**

LED: 3000k, 14 watts,
 1000 gross lumens

DAMP **ONE LIGHT
OUTDOOR PENDANT**

D: 13.25" H: 11.5"
 10' wire, (3) 12" stems, (1) 6" stem
 and sloped ceiling mounting Hardware

T24

6247701-44

(1) Medium Base 100w max.

T24 **6247701EN3-44**

(1) Med. Base LED 3000k,
 9.5w, 800 lumen lamp incl.

T24  **6247793S-44**

LED: 3000k, 14 watts,
 1000 gross lumens



CRITTENDEN

PRODUCT SHOWN: CRITTENDEN ONE LIGHT OUTDOOR WALL LANTERN IN SATIN ALUMINUM FINISH



WET **ONE LIGHT
OUTDOOR WALL LANTERN**

W: 10" H: 8.5" E: 11.5"
Height from center of outlet box
up: 2.5"

T24

8538501-04
(1) Medium Base 75w max.

T24 

8538501EN3-04
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



SATIN ALUMINUM FINISH

WET **ONE LIGHT
OUTDOOR WALL LANTERN**

W: 10" H: 8.5" E: 11.5"
Height from center of outlet box
up: 2.5"

T24

8538501-12
(1) Medium Base 75w max.

T24 

8538501EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



BLACK FINISH

RENVILLE

PRODUCT SHOWN: RENVILLE SMALL ONE LIGHT OUTDOOR WALL LANTERN IN BLACK FINISH





SATIN ALUMINUM FINISH
SATIN ETCHED GLASS

WET

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7" H: 10.25" E: 8"
Height from center of outlet box
up: 3.5"

T24

8638601-04
(1) Medium Base 100w max.

T24 EN★

8638601EN3-04
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



ANTIQU BRONZE FINISH
SATIN ETCHED GLASS

WET

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7" H: 10.25" E: 8"
Height from center of outlet box
up: 3.5"

T24

8638601-71
(1) Medium Base 100w max.

T24 EN★

8638601EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



BLACK FINISH
SATIN ETCHED GLASS

WET

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 7" H: 10.25" E: 8"
Height from center of outlet box
up: 3.5"

T24

8638601-12
(1) Medium Base 100w max.

T24 EN★

8638601EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



SATIN ALUMINUM FINISH
SATIN ETCHED GLASS

WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 5.25" H: 7.5" E: 5.75"
Height from center of outlet box
up: 2.5"

T24

8538601-04
(1) Medium Base 60w max.

T24 EN★

8538601EN3-04
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



ANTIQU BRONZE FINISH
SATIN ETCHED GLASS

WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 5.25" H: 7.5" E: 5.75"
Height from center of outlet box
up: 2.5"

T24

8538601-71
(1) Medium Base 60w max.

T24 EN★

8538601EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



BLACK FINISH
SATIN ETCHED GLASS

WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 5.25" H: 7.5" E: 5.75"
Height from center of outlet box
up: 2.5"

T24

8538601-12
(1) Medium Base 60w max.

T24 EN★

8538601EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 8" H: 24.625" E: 6.875"
Height from center of outlet box up: 12.3125"

T24

8718301-04
(1) Medium Base 60w max.

T24 EN★

8718301EN3-04
(1) LED Medium Base
9.5w Bulb lamps included.



CYLINDRICAL GLASS

WET

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 8" H: 24.625" E: 6.75"
Height from center of outlet box up: 12.3125"

T24

8720701-04
(1) Medium Base 60w max.

T24 EN★

8720701EN3-04
(1) LED Medium Base
9.5w Bulb lamps included.



SQUARE GLASS

WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 4.5" H: 14" E: 4.25"
Height from center of outlet box up: 7"

T24

8518301-04
1 Medium Base 60w max.

T24 EN★

8518301EN3-04
(1) LED Medium Base
9.5w Bulb lamps included.



CYLINDRICAL GLASS

WET

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 4.5" H: 14" E: 4.125"
Height from center of outlet box up: 7"

T24

8520701-04
1 Medium Base 60w max.

T24 EN★

8520701EN3-04
(1) LED Medium Base
9.5w Bulb lamps included.



SQUARE GLASS

WET

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 8" H: 24.625" E: 6.875"
Height from center of outlet box
up: 12.3125"

T24

8718301-71
(1) Medium Base 60w max.

T24 EN★

8718301EN3-71
(1) LED Medium Base
9.5w Bulb lamps included.



CYLINDRICAL GLASS

WET

**LARGE ONE LIGHT
OUTDOOR WALL LANTERN**

W: 8" H: 24.625" E: 6.75"
Height from center of outlet box
up: 12.3125"

T24

8720701-71
(1) Medium Base 60w max.

T24 EN★

8720701EN3-71
(1) LED Medium Base
9.5w Bulb lamps included.



SQUARE GLASS

WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 4.5" H: 14" E: 4.25"
Height from center of outlet box
up: 7"

T24

8518301-71
(1) Medium Base 60w max.

T24 EN★

8518301EN3-71
(1) LED Medium Base
9.5w Bulb lamps included.



CYLINDRICAL GLASS

WET

**SMALL ONE LIGHT
OUTDOOR WALL LANTERN**

W: 4.5" H: 14" E: 4.125"
Height from center of outlet box
up: 7"

T24

8520701-71
(1) Medium Base 60w max.

T24 EN★

8520701EN3-71
(1) LED Medium Base
9.5w Bulb lamps included.



SQUARE GLASS

OUTDOOR CYLINDERS

WET

LARGE TWO LIGHT UP/DOWN OUTDOOR WALL LANTERN

W: 6" H: 18.25" E: 8.75"

Height from center of outlet box
up: 9.25"

T24

8313902-15

(2) Medium Base BR40 100w max.

T24 EN★

8313902EN3-15

(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

8413997S-15

LED: 2700k, 28 watts,
2000 gross lumens

See More White Finish
on pages 580-583



WHITE FINISH
CLEAR TEMPERED GLASS DIFFUSER
(FOR TOP)

WET

LARGE TWO LIGHT UP/DOWN OUTDOOR WALL LANTERN

W: 6" H: 18.25" E: 8.75"
Height from center of outlet box
up: 9.25"

T24

8313902-753
(2) Medium Base BR40 100w max.

T24 EN★

8313902EN3-753
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

8413997S-753
LED: 2700k, 28 watts,
2000 gross lumens

See More Powder Coated Brushed Nickel Finish
on pages 580-583



POWDER COATED BRUSHED NICKEL FINISH
CLEAR TEMPERED GLASS DIFFUSER
(FOR TOP)

WET

LARGE TWO LIGHT UP/DOWN OUTDOOR WALL LANTERN

W: 6" H: 18.25" E: 8.75"
Height from center of outlet box
up: 9.25"

T24

8313902-10
(2) Medium Base BR40 100w max.

T24 EN★

8313902EN3-10
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

8413997S-10
LED: 2700k, 28 watts,
2000 gross lumens

See More Powder Coated Bronze Finish
on pages 580-583



POWDER COATED BRONZE FINISH
CLEAR TEMPERED GLASS DIFFUSER
(FOR TOP)

OUTDOOR CYLINDERS

WET

SMALL TWO LIGHT UP/DOWN OUTDOOR WALL LANTERN

W: 5.25" H: 14.25" E: 8"
Height from center of outlet box
up: 7.25"

T24 EN★

8313802-15
(2) Medium Base BR30 65w max.

T24 EN★

8313802EN3-15
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

8413897S-15
LED: 2700k, 28 watts,
2000 gross lumens



WHITE FINISH
CLEAR TEMPERED GLASS DIFFUSER
(FOR TOP)

WET

SMALL TWO LIGHT UP/DOWN OUTDOOR WALL LANTERN

W: 5.25" H: 14.25" E: 8"
Height from center of outlet box
up: 7.25"

T24 EN★

8313802-753
(2) Medium Base BR30 65w max.

T24 EN★

8313802EN3-753
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

8413897S-753
LED: 2700k, 28 watts,
2000 gross lumens



POWDER COATED BRUSHED NICKEL FINISH
CLEAR TEMPERED GLASS DIFFUSER
(FOR TOP)

WET

SMALL TWO LIGHT UP/DOWN OUTDOOR WALL LANTERN

W: 5.25" H: 14.25" E: 8"
Height from center of outlet box
up: 7.25"

T24 EN★

8313802-10
(2) Medium Base BR30 65w max.

T24 EN★

8313802EN3-10
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

8413897S-10
LED: 2700k, 28 watts,
2000 gross lumens



POWDER COATED BRONZE FINISH
CLEAR TEMPERED GLASS DIFFUSER
(FOR TOP)

WET 

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 6" H: 9" E: 8.75"
Height from center of outlet box
up: 4.5"

T24 

8313901-15
(1) Medium Base BR40 100w max.

T24 EN★

8313901EN3-15
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

8313997S-15
LED: 2700k, 14 watts,
1000 gross lumens



WHITE FINISH
CLEAR TEMPERED GLASS DIFFUSER
(FOR TOP)

WET 

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 6" H: 9" E: 8.75"
Height from center of outlet box
up: 4.5"

T24 

8313901-753
(1) Medium Base BR40 100w max.

T24 EN★

8313901EN3-753
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

8313997S-753
LED: 2700k, 14 watts,
1000 gross lumens



POWDER COATED BRUSHED NICKEL FINISH
CLEAR TEMPERED GLASS DIFFUSER
(FOR TOP)

WET 

LARGE ONE LIGHT OUTDOOR WALL LANTERN

W: 6" H: 9" E: 8.75"
Height from center of outlet box
up: 4.5"

T24 

8313901-10
(1) Medium Base BR40 100w max.

T24 EN★

8313901EN3-10
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

T24 WOD EN★ LED

8313997S-10
LED: 2700k, 14 watts,
1000 gross lumens



POWDER COATED BRONZE FINISH
CLEAR TEMPERED GLASS DIFFUSER
(FOR TOP)

OUTDOOR CYLINDERS

WET 

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 5.25" H: 7.25" E: 8"
Height from center of outlet box
up: 2.75"

T24  EN★

8313801-15
(1) Medium Base BR30 65w max.

T24 EN★

8313801EN3-15
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

8313897S-15
LED: 2700k, 14 watts,
1000 gross lumens



WHITE FINISH
CLEAR TEMPERED GLASS DIFFUSER
(FOR TOP)

WET 

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 5.25" H: 7.25" E: 8"
Height from center of outlet box
up: 2.75"

T24  EN★

8313801-753
(1) Medium Base BR30 65w max.

T24 EN★

8313801EN3-753
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

8313897S-753
LED: 2700k, 14 watts,
1000 gross lumens



POWDER COATED BRUSHED NICKEL FINISH
CLEAR TEMPERED GLASS DIFFUSER
(FOR TOP)

WET 

SMALL ONE LIGHT OUTDOOR WALL LANTERN

W: 5.25" H: 7.25" E: 8"
Height from center of outlet box
up: 2.75"

T24  EN★

8313801-10
(1) Medium Base BR30 65w max.

T24 EN★

8313801EN3-10
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

8313897S-10
LED: 2700k, 14 watts,
1000 gross lumens



POWDER COATED BRONZE FINISH
CLEAR TEMPERED GLASS DIFFUSER
(FOR TOP)

OUTDOOR CYLINDERS



WHITE FINISH
CLEAR TEMPERED GLASS DIFFUSER
(FOR TOP)

DAMP

LARGE ONE LIGHT OUTDOOR CEILING FLUSH MOUNT

D: 6" H: 9"

T24 EN★

7813901-15

(1) Medium Base BR40 100w max.

T24 EN★

7813901EN3-15

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

7813997S-15

LED: 2700k, 14 watts,
1000 gross lumens



POWDER COATED BRUSHED NICKEL FINISH
CLEAR TEMPERED GLASS DIFFUSER
(FOR TOP)

DAMP

LARGE ONE LIGHT OUTDOOR CEILING FLUSH MOUNT

D: 6" H: 9"

T24 EN★

7813901-10

(1) Medium Base BR40 100w max.

T24 EN★

7813901EN3-10

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

7813997S-10

LED: 2700k, 14 watts,
1000 gross lumens



POWDER COATED BRONZE FINISH
CLEAR TEMPERED GLASS DIFFUSER
(FOR TOP)

DAMP

LARGE ONE LIGHT OUTDOOR CEILING FLUSH MOUNT

D: 6" H: 9"

T24 EN★

7813901-753

(1) Medium Base BR40 100w max.

T24 EN★

7813901EN3-753

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

7813997S-753

LED: 2700k, 14 watts,
1000 gross lumens



WHITE FINISH
CLEAR TEMPERED GLASS DIFFUSER
(FOR TOP)

DAMP

SMALL ONE LIGHT OUTDOOR CEILING FLUSH MOUNT

D: 5.25" H: 6.75"

T24 EN★

7813801-15

(1) Medium Base BR30 65w max.

T24 EN★

7813801EN3-15

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

7813897S-15

LED: 2700k, 14 watts,
1000 gross lumens



POWDER COATED BRUSHED NICKEL FINISH
CLEAR TEMPERED GLASS DIFFUSER
(FOR TOP)

DAMP

SMALL ONE LIGHT OUTDOOR CEILING FLUSH MOUNT

D: 5.25" H: 6.75"

T24 EN★

7813801-753

(1) Medium Base BR30 65w max.

T24 EN★

7813801EN3-753

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

7813897S-753

LED: 2700k, 14 watts,
1000 gross lumens



POWDER COATED BRONZE FINISH
CLEAR TEMPERED GLASS DIFFUSER
(FOR TOP)

DAMP

SMALL ONE LIGHT OUTDOOR CEILING FLUSH MOUNT

D: 5.25" H: 6.75"

T24 EN★

7813801-10

(1) Medium Base BR30 65w max.

T24 EN★

7813801EN3-10

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.

T24 WOD EN★ LED

7813897S-10

LED: 2700k, 14 watts,
1000 gross lumens

OUTDOOR WALL LANTERNS



PAINTABLE CERAMIC FINISH



ONE LIGHT OUTDOOR WALL LANTERN

W: 8" H: 10" E: 5.75"
Height from center of outlet box
up: 4.25"



8304701-714

(1) Medium Base 75w max.



8304701EN3-714

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



PAINTABLE CERAMIC FINISH



ONE LIGHT OUTDOOR WALL LANTERN

W: 8" H: 10" E: 5.75"
Height from center of outlet box
up: 4.25"



8304801-714

(1) Medium Base 75w max.



8304801EN3-714

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



PAINTABLE CERAMIC FINISH



ONE LIGHT OUTDOOR WALL LANTERN

W: 8" H: 10" E: 5.75"
Height from center of outlet box
up: 4.25"



83046-714

(1) Medium Base 100w max.



83046EN3-714

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

OUTDOOR WALL LANTERNS



WHITE FINISH POLYCARBONATE
WHITE GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 6" H: 7.25" E: 7"
Height from center of outlet box up: 2.25"

T24

8753-15

(1) Medium Base 60w max.

T24 EN★

8753EN3-15

(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



BLACK FINISH POLYCARBONATE
WHITE GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 6" H: 7.25" E: 7"
Height from center of outlet box up: 2.25"

T24

8753-34

(1) Medium Base 60w max.

T24 EN★

8753EN3-34

(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



BLACK FINISH POLYCARBONATE
WHITE ACRYLIC DIFFUSER

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 6" H: 8" E: 6.75"
Height from center of outlet box up: 2.75"

T24 EN★

8955EN3-12

(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.



BLACK FINISH
WHITE POLYCARBONATE DIFFUSER

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 4.5" H: 7.5" E: 5.75"
Height from center of outlet box up: 2.5"

T24 EN★

8909PEN3-12

(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl. photocell included



WHITE FINISH POLYCARBONATE
CLEAR GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 4.5" H: 6" E: 5.5"
Height from center of outlet box up: 3.75"

T24

8750-15

(1) Medium Base 60w max.



BLACK FINISH POLYCARBONATE
CLEAR GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 4.5" H: 6" E: 5.5"
Height from center of outlet box up: 3.75"

T24

8750-12

(1) Medium Base 60w max.



BLACK FINISH
CLEAR GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 4.5" H: 7.5" E: 5.75"
Height from center of outlet box up: 2.25"

T24

8550-12

(1) Medium Base 100w max.



BLACK FINISH
SATIN ETCHED GLASS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 4.5" H: 7.5" E: 5.75"
Height from center of outlet box up: 2.25"

T24

8550001-12

(1) Medium Base 100w max.

T24 EN★

8550001EN3-12

(1) Med. Base LED 3000k, 9.5w, 800 lumen lamp incl.

OUTDOOR WALL LANTERNS

WET 

ONE LIGHT OUTDOOR WALL LANTERN

W: 8" H: 25" Without Tail H: 20" E: 9"
Height from center of outlet box
up: 15.25"

T24

8765-15

(1) Medium Base 100w max.



WHITE FINISH POLYCARBONATE
CLEAR BEVELED ACRYLIC PANELS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 8" H: 17.5" E: 8.5"
Height from center of outlet box
up: 10.75"

T24

8720-15

(1) Medium Base 60w max.



WHITE FINISH POLYPROPYLENE
CLEAR BEVELED ACRYLIC DIFFUSER

OUTDOOR WALL LANTERNS

WET +

ONE LIGHT OUTDOOR WALL LANTERN

W: 8" H: 25" Without Tail H: 20" E: 9"
Height from center of outlet box
up: 15.25"

T24

8765-12

(1) Medium Base 100w max.



BLACK FINISH POLYCARBONATE
CLEAR BEVELED ACRYLIC PANELS

WET

ONE LIGHT OUTDOOR WALL LANTERN

W: 8" H: 17.5" E: 8.5"
Height from center of outlet box
up: 10.75"

T24

8720-32

(1) Medium Base 60w max.



BLACK FINISH POLYPROPYLENE
CLEAR BEVELED ACRYLIC DIFFUSER

OUTDOOR POST LANTERNS



WHITE FINISH POLYCARBONATE
CLEAR BEVELED ACRYLIC DIFFUSER

WET

ONE LIGHT OUTDOOR POST LANTERN

L: 8" W: 8" H: 18"

T24

8255-15

(1) Medium Base 100w max.



BLACK FINISH POLYCARBONATE
CLEAR BEVELED ACRYLIC DIFFUSER

WET

ONE LIGHT OUTDOOR POST LANTERN

L: 8" W: 8" H: 18"

T24

8255-12

(1) Medium Base 100w max.



BLACK FINISH POLYPROPYLENE
CLEAR BEVELED ACRYLIC DIFFUSER

WET

ONE LIGHT OUTDOOR POST LANTERN

L: 8" W: 8" H: 11"

T24

8275-32

(1) Medium Base 60w max.



BLACK FINISH
FROSTED ACRYLIC DIFFUSER

WET

ONE LIGHT OUTDOOR POST LANTERN

L: 10.5" W: 10.5" H: 18"

T24

82065-12

(1) Medium Base 100w max.

T24 EN★

82065EN3-12

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



BLACK FINISH POLYCARBONATE
WHITE ACRYLIC DIFFUSER

WET

ONE LIGHT OUTDOOR POST LANTERN

D: 14" H: 15"

T24

8254-68

(1) Medium Base 150w max.

T24 EN★

8254EN3-68

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



BLACK FINISH POLYCARBONATE
WHITE ACRYLIC DIFFUSER

WET

ONE LIGHT OUTDOOR POST LANTERN

D: 12" H: 13"

T24

8252-68

(1) Medium Base 100w max.

T24 EN★

8252EN3-68

(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

OUTDOOR POSTS



BLACK FINISH

WET

ALUMINUM PEDESTAL MOUNT ADAPTER*

L: 6" W: 6" H: 4.25"

8014-12

*Only for use with lanterns up to 36" H.



WHITE FINISH [-15]

WET

ALUMINUM POST WITH PHOTO CELL

D: 3" H: 84"

8112-15

WHITE

8112-12

BLACK



BLACK FINISH [-12]

WET

STEEL POST

D: 3" H: 84"

8102-15

WHITE

8102-12

BLACK



ANTIQU BRONZE FINISH [-71]

WET

ALUMINUM POST

D: 3" H: 84"

8101-15

WHITE

8101-12

BLACK

8101-71

ANTIQU BRONZE



WHITE FINISH [-15]

WET

ALUMINUM POST WITH LADDER REST AND PHOTOCCELL

D: 3" H: 84"

8114-15

WHITE

8114-12

BLACK



ANTIQU BRONZE FINISH [-71]

WET

ALUMINUM POST WITH LADDER REST

D: 3" H: 84"

8105-15

WHITE

8105-71

ANTIQU BRONZE

8105-12

BLACK



BLACK FINISH [-12]

WET

STEEL POST WITH LADDER REST

D: 3" H: 84"

8106-12

BLACK

8118-12

BLACK with photocell



BLACK FINISH [-12]

WET

CAST ALUMINUM POST

W: 10.5" H: 71" E: 9"

8120-12

BLACK

OUTDOOR CEILING FLUSH MOUNTS



WHITE POLYPROPYLENE
CLEAR TEXTURED GLASS

DAMP

TWO LIGHT OUTDOOR CEILING FLUSH MOUNT

L: 10.25" W: 10.25" H: 5.5"

T24

7569-15
(2) Medium Base 60w max.

T24 EN★

7569EN3-15
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.



WHITE POLYPROPYLENE
CLEAR TEXTURED GLASS

DAMP

ONE LIGHT OUTDOOR CEILING FLUSH MOUNT


L: 8.25" W: 8.25" H: 4.75"

T24

7567-15
(1) Medium Base 60w max.

T24 EN★

7567EN3-15
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



BLACK POLYPROPYLENE
CLEAR TEXTURED GLASS

DAMP

TWO LIGHT OUTDOOR CEILING FLUSH MOUNT

L: 10.25" W: 10.25" H: 5.5"

T24

7569-12
(2) Medium Base 60w max.

T24 EN★

7569EN3-12
(2) Med. Base LED 3000k,
9.5w, 800 lumen lamps incl.



BLACK POLYPROPYLENE
CLEAR TEXTURED GLASS

DAMP

ONE LIGHT OUTDOOR CEILING FLUSH MOUNT

L: 8.25" W: 8.25" H: 4.75"

T24

7567-12
(1) Medium Base 60w max.

T24 EN★

7567EN3-12
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.

OUTDOOR CEILING FLUSH MOUNTS



ANTIQUe BRONZE FINISH
CLEAR TEXTURED GLASS

DAMP

ONE LIGHT OUTDOOR CEILING FLUSH MOUNT

L: 7.5" W: 7.5" H: 5.25"

T24

75467-71
(1) Medium Base 60w max.

T24 EN★

75467EN3-71
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



WHITE FINISH
WHITE ACRYLIC DIFFUSER

DAMP ADA

TWO LIGHT OUTDOOR WALL / CEILING MOUNT

L: 10.25" W: 10.25" H: 4" E: 4"

T24 EN★

7916EN3-68
(2) GU24 Base LED 3000k,
9.5w, 800 lumen lamps incl.



WHITE FINISH
WHITE RIBBED POLYCARBONATE DIFFUSER

DAMP ADA

ONE LIGHT OUTDOOR WALL / CEILING MOUNT

L: 7.5" W: 5.25" H: 4" E: 4"

T24

4325-68
(1) Medium Base 60w max.

T24 EN★

4325EN3-68
(1) Med. Base LED 3000k,
9.5w, 800 lumen lamp incl.



ANTIQUe BRONZE FINISH
CLEAR SEEDED GLASS

DAMP

TWO LIGHT OUTDOOR CEILING FLUSH MOUNT

D: 13" H: 5.5"

T24

7821402-71
(2) Medium Base 60w max.



BLACK FINISH
CLEAR SEEDED GLASS

DAMP

TWO LIGHT OUTDOOR CEILING FLUSH MOUNT

D: 13" H: 5.5"

T24

7821402-12
(2) Medium Base 60w max.

ADDRESS LIGHTS

120V LED



WHITE POWDERCOAT FINISH

WET

LED ADDRESS LIGHT

W: 12.25" H: 7" E: 2.25"

LED

96091S-15

LED: 3000k, 120V, 2 watts,
120 gross lumens



ANTIQUE BRONZE POWDERCOAT FINISH

WET

LED ADDRESS LIGHT

W: 12.25" H: 7" E: 2.25"

LED

96091S-71

LED: 3000k, 120V, 2 watts,
120 gross lumens



BLACK POWDERCOAT FINISH

WET

LED ADDRESS LIGHT

W: 12.25" H: 7" E: 2.25"

LED

96091S-12

LED: 3000k, 120V, 2 watts,
120 gross lumens

LOW-VOLTAGE



ANTIQUE BRONZE POWDERCOAT FINISH

WET

ADDRESS LIGHT

W: 12.5" H: 7" E: 2.25"

9600-71

(2) Wedge Base T3¼
5w 16v lamps included



BLACK POWDERCOAT FINISH

WET

ADDRESS LIGHT

W: 12.5" H: 7" E: 2.25"

9600-12

(2) Wedge Base T3¼
5w 16v lamps included



WET

TRANSFORMER

L: 2.5" W: 2.125" H: 2"

9647

16V, Class II



90610-68



90611-68



90612-68



90613-68



90614-68



90615-68



90616-68



90617-68



90618-68



90616-68



90619-68



90621-68

WET

NUMBER TILES

W: 2.25" H: 5"

OUTDOOR



WHITE FINISH ALUMINUM

WET +

TWO LIGHT ADJUSTABLE SWIVEL FLOOD LIGHT

W: 22" H: 12.5" E: 11.25"
Heads swivel

T24

8607-15
(2) Medium Base BR40 120w max.



BLACK FINISH ALUMINUM

WET +

TWO LIGHT ADJUSTABLE SWIVEL FLOOD LIGHT

W: 22" H: 12.5" E: 11.25"
Heads swivel

T24

8607-12
(2) Medium Base BR40 120w max.



WHITE FINISH POLYCARBONATE

WET +

TWO LIGHT ADJUSTABLE SWIVEL FLOOD LIGHT

W: 9.5" H: 11" E: 2.5"
Adjustable heads

T24

8642-15
(2) Medium Base PAR38 90w max.



BLACK FINISH POLYCARBONATE

WET +

TWO LIGHT ADJUSTABLE SWIVEL FLOOD LIGHT

W: 9.5" H: 11" E: 2.5"
Adjustable heads

T24

8642-12
(2) Medium Base PAR38 90w max.



EMERALD GREEN POWDERCOAT FINISH

WET

**ONE LIGHT OUTDOOR
PATH LIGHT**

D: 5.875" H: 7"

T24

9226-95

(1) Medium Base 75w max.



BLACK POWDERCOAT FINISH

WET

**ONE LIGHT OUTDOOR
PATH LIGHT**

D: 5.875" H: 7"

T24

9226-12

(1) Medium Base 75w max.

PRODUCTS SHOWN: TRAVERSE UNLIMITED ROUND IN WHITE FINISH AND
PRATT STREET METAL LARGE ONE LIGHT PENDANT IN BRUSHED NICKEL FINISH





RECESSED

collections

TRAVERSE LED

PRODUCTS SHOWN: WESTMINSTER SMALL THREE
LIGHT HALL / FOYER IN AUTUMN BRONZE
DESIGN: JLV CREATIVE
BUILDER: CRESCENT HOMES
PHOTOGRAPHER: CAROLINE TAN



Generation Lighting has revolutionized the world of recessed downlights with our Traverse line of LED-light modules. The Traverse lineup does more than just eliminate many of the LED pain points that used to turn off consumers. It also provides you with one-stop shopping, courtesy of seven different downlight options that provide superior performance and value at various price points: the Unlimited, Lyte, Insert, 4-inch, Mirage, Lotus, and Aubrey Wall Wash.

Generation Lighting Traverse downlights feature advanced technology that enhances job-site productivity and efficiency with quick, easy Installations. At the same time, they provide consumers with eye-pleasing, long-lasting, energy-efficient and more cost-effective LED lighting solutions. In short, the Traverse line is exactly what you'd expect from Generation Lighting, which has dominated the LED-lighting market for the last decade.

SELECT YOUR PRODUCT



TRAVERSE MIRAGE
p.600



**TRAVERSE AUBREY
WALL WASH**
p.601



TRAVERSE LYTE
p.606



TRAVERSE UNLIMITED SQUARE AND ROUND
p.608



TRAVERSE LOTUS SQUARE AND ROUND
p.602



TRAVERSE 4"
p.611




TRAVERSE INSERT
p.610

TRAVERSE MIRAGE



TRAVERSE MIRAGE

14916RD-15



FEATURES & BENEFITS

- Recessed look and feel with unparalleled Efficacy of LED
- Economical, long lasting upgrade to standard recessed lighting
- Provides visually pleasing, color accurate 90CRI illumination
- Dimmable down to 10%
- ENERGY STAR® Qualified
- Title-24 Compliant
- Wet Rated for shower ceiling installations
- Flat lens
- Easy to install

DIMMER COMPATIBILITY

Forbes & Lomax	FLR603P
Lutron	SELV-300P, DVELV-300P, NTELV-500, RRD-6NA, MAELV-600, HQRD-6NA, TGCL-153P, DVCL-153P, S-600P, DV-600P, PD-5NE-WH, SCL-153P, AYCL-153P, CTCL-153P, LGCL-153P, MACL-153M, PD-6WCL
Legrand	HCL45-3PW, ADTH700RMTUW1, ADTP600RMHW1
Insteon	24770
Leviton	DSL06-1LZ

SPECIFICATIONS



Item Number	14916RD-15
Item Name	Traverse Mirage
Finish	White [-15]
Color Temperature	3000K
Lumens Delivered	650
Watts Consumed	11.5
Efficacy	57
Color Rendering Index	90 CRI
Beam Spread	Lambertian
Rated Average Life	50,000 hours to 70%
Dimmable ⁽¹⁾	Yes to <10%
Warm On Dim	No
Voltage	120V
Power Factor	>.9
Ambient Operating Temp.	-40°C to +35°C
Construction	Die Cast Metal
Lens	Polycarbonate
Warranty	5 years
Installation	New Construction (3"/4" Round, 4" Square / Octagonal, 4" Pancake)
Qualifications	EN★ WET T24

⁽¹⁾ Dims best with electronic low Voltage (ELV) dimmers. When sizing the dimmer, de-rate it by 30% to account for in-rush current. (i.e. a standard 600 watt dimmer will have a 420 watt capacity when used with these fixtures).

TRAVERSE AUBREY WALL WASH



**TRAVERSE AUBREY
WALL WASH**
14936RD-15



FEATURES & BENEFITS

- Designed for superior performance and value
- Economical, longer lasting alternative to standard recessed downlights
- Provides visually pleasing, color accurate illumination (90 CRI)
- ENERGY STAR® Qualified
- Title-24 Compliant
- Wet rated for shower ceiling Installations
- Dimmable down to 10%*
- Angled housing for optimal light performance displayed on a wall
- Easy to install

DIMMER COMPATIBILITY

Forbes & Lomax	FLR603P
Legrand	HCL45-3PW, ADTP600RMHW1, ADTH700RMTUW1
Insteon	2477D
Lutron	GL-600P-WH, S-600P, DV-600P, AY-600P-WH, D-600P-WH, TGCL-153P, DVCL-153P, DSL06-1LZ, MACL-153M, PD-6WCL, SELV-300P, DVELV-300P, NTELV-500, RRD-6NA, MAELV-600, MRF-2-6ELV, HQRD-6NA

SPECIFICATIONS

Item Number	14936RD-15
Item Name	Traverse Aubrey Wall Wash
Finish	White [-15]
Color Temperature	3000K
Lumens Delivered	500
Watts Consumed	9
Efficacy	56
Color Rendering Index	90 CRI
Beam Spread	Lambertian
Rated Average Life	50,000 hours to 70%
Dimmable ⁽¹⁾	Yes to <10%
Voltage	120V
Power Factor	>.9
Ambient Operating Temp.	-40°C to +35°C
Lens	Polycarbonate
Warranty	5 years
Installation	New Construction (3/4" Round, 4" Square/Octagonal)
Qualifications	EN★ WET T24


⁽¹⁾Dims best with electronic low Voltage (ELV) dimmers. When sizing the dimmer, de-rate it by 30% to account for in-rush current. (i.e. a standard 600 watt dimmer will have a 420 watt capacity when used with these fixtures).

TRAVERSE LOTUS ROUND




**TRAVERSE
LOTUS ROUND 12"**

149212RD-15




**TRAVERSE
LOTUS ROUND 9"**

14929RD-15




**TRAVERSE
LOTUS ROUND 7"**

14927RD-15



**TRAVERSE
LOTUS ROUND 5"**

14925RD-15



DIMMER COMPATIBILITY

Forbes & Lomax	FLR603P
Lutron	SELV-300P, DVELV-300P, NTELV-500, RRD-6NA, MAELV-600, HQRD-6NA, TGCL-153P, DVCL-153P, S-600P, DV-600P, PD-5NE-WH, SCL-153P, AYCL-153P, CTCL-153P, LGCL-153P, MACL-153M, PD-6WCL
Legrand	HCL45-3PW, ADTH700RMTUW1, ADTP60ORMHW1
Insteon	24770
Leviton	DSL06-1LZ

FEATURES & BENEFITS


- Designed for superior performance and value
- Economical, longer lasting alternative to standard recessed downlights
- Provides visually pleasing, color accurate illumination (90 CRI)
- Easy to install:
 - Standard 120V lighting fixture
 - Mounts on all standard junction boxes, including pan junction box
- Retrofits into most common recessed lighting housings with optional Edison base adapter (5" and 6" uses part #14795)
- ENERGY STAR® qualified
- Title-24 Compliant
- Wet rated for shower ceiling installations
- Dimmable down to 5%*

SPECIFICATIONS

Item Number	149212RD-15	14929RD-15	14927RD-15	14925RD-15
Item Name	Traverse Lotus 12" Round	Traverse Lotus 9" Round	Traverse Lotus 7" Round	Traverse Lotus 5" Round
Finish	White [-15]	White [-15]	White [-15]	White [-15]
Color Temperature	3000K	3000K	3000K	3000K
Lumens Delivered	1400	1150	850	550
Watts Consumed	22 watts	18 watts	15 watts	10 watts
Efficacy	64 lm/w	64 lm/w	57 lm/w	55 lm/w
Color Rendering Index	90 CRI	90 CRI	90 CRI	90 CRI
Beam Spread	Lambertian	Lambertian	Lambertian	Lambertian
Rated Average Life	50,000 hours to 70%	50,000 hours to 70%	50,000 hours to 70%	50,000 hours to 70%
Dimmable ⁽¹⁾	Yes to 10%	Yes to <10%	Yes to <10%	Yes to <10%
Voltage	120V	120V	120V	120V
Power Factor	>.9	>.9	>.9	>.9
Ambient Operating Temp.	-40°C to +35°C	-40°C to +35°C	-40°C to +35°C	-40°C to +35°C
Lens	Polycarbonate	Polycarbonate	Polycarbonate	Polycarbonate
Warranty	5 years	5 years	5 years	5 years
Installation	New Construction (3"/4" Round, 4" Square/ Octagonal, 4" Pancake)	New Construction (3"/4" Round, 4" Square/ Octagonal, 4" Pancake)	New Construction (3"/4" Round, 4" Square/ Octagonal, 4" Pancake)	New Construction (3"/4" Round, 4" Square/ Octagonal, 4" Pancake)
Qualifications	EN★ WET T24	EN★ WET T24	EN★ WET T24	EN★ WET T24


⁽¹⁾ Dims best with electronic low Voltage (ELV) dimmers. When sizing the dimmer, de-rate it by 30% to account for in-rush current. (i.e. a standard 600 watt dimmer will have a 420 watt capacity when used with these fixtures).

TRAVERSE LOTUS SQUARE





**TRAVERSE
LOTUS SQUARE 12"**

149212SQ-15




**TRAVERSE
LOTUS SQUARE 9"**

14929SQ-15




**TRAVERSE
LOTUS SQUARE 6"**

14926SQ-15



**TRAVERSE
LOTUS ROUND 4"**

14924SQ-15



DIMMER COMPATIBILITY

Forbes & Lomax	FLR603P
Lutron	SELV-300P, DVELV-300P, NTELV-500, RRD-6NA, MAELV-600, HQRD-6NA, TGCL-153P, DVCL-153P, S-600P, DV-600P, PD-5NE-WH, SCL-153P, AYCL-153P, CTCL-153P, LGCL-153P, MACL-153M, PD-6WCL
Legrand	HCL45-3PW, ADTH700RMTUW1, ADTP600RMHW1
Insteon	24770
Leviton	DSL06-1LZ

FEATURES & BENEFITS


- Designed for superior performance and value
- Economical, longer lasting alternative to standard recessed downlights
- Provides visually pleasing, color accurate illumination (90 CRI)
- Easy to install:
 - Standard 120V lighting fixture
 - Mounts on all standard junction boxes, including pan junction box
- Retrofits into most common recessed lighting housings with optional Edison base adapter (5" and 6" uses part #14795)
- ENERGY STAR® qualified
- Title-24 Compliant
- Wet rated for shower ceiling Installations
- Dimmable down to 5%*

SPECIFICATIONS

Item Number	149212SQ-15	14929SQ-15	14926SQ-15	14924SQ-15
Item Name	Traverse Lotus 12" Square	Traverse Lotus 9" Square	Traverse Lotus 6" Square	Traverse Lotus 4" Square
Finish	White [-15]	White [-15]	White [-15]	White [-15]
Color Temperature	3000K	3000K	3000K	3000K
Lumens Delivered	1400	1150	850	550
Watts Consumed	22 watts	18 watts	15 watts	10 watts
Efficacy	64 lm/w	64 lm/w	57 lm/w	55 lm/w
Color Rendering Index	90 CRI	90 CRI	90 CRI	90 CRI
Beam Spread	Lambertian	Lambertian	Lambertian	Lambertian
Rated Average Life	50,000 hours to 70%	50,000 hours to 70%	50,000 hours to 70%	50,000 hours to 70%
Dimmable ⁽¹⁾	Yes to 10%	Yes to <10%	Yes to <10%	Yes to <10%
Voltage	120V	120V	120V	120V
Power Factor	>.9	>.9	>.9	>.9
Ambient Operating Temp.	-40°C to +35°C	-40°C to +35°C	-40°C to +35°C	-40°C to +35°C
Lens	Polycarbonate	Polycarbonate	Polycarbonate	Polycarbonate
Warranty	5 years	5 years	5 years	5 years
Installation	New Construction (3/4" Round, 4" Square/ Octagonal, 4" Pancake)	New Construction (3/4" Round, 4" Square/ Octagonal, 4" Pancake)	New Construction (3/4" Round, 4" Square/ Octagonal, 4" Pancake)	New Construction (3/4" Round, 4" Square/ Octagonal, 4" Pancake)
Qualifications	EN★ WET T24	EN★ WET T24	EN★ WET T24	EN★ WET T24

⁽¹⁾Dims best with electronic low Voltage (ELV) dimmers. When sizing the dimmer, de-rate it by 30% to account for in-rush current. (i.e. a standard 600 watt dimmer will have a 420 watt capacity when used with these fixtures).

TRAVERSE LYTE



OPTIONAL RETROFIT KIT

14795

For housings with or without integral "C" clips

OPTIONAL GASKET COMPONENT

620390

For wet applications; easy install without silicone application

FEATURES & BENEFITS

- Designed for superior performance and value
- Economical, longer lasting alternative to standard recessed downlights
- Provides visually pleasing, color accurate illumination (90 CRI)
- Easy to install:
 - Standard 120V lighting fixture
 - Mounts on all standard junction boxes, including pan junction box
- Retrofits into most common recessed lighting housings with optional Edison base adapter (5" and 6" uses part #14795)
- ENERGY STAR® qualified
- Title-24 Compliant
- Wet rated for shower ceiling installations
- Dimmable down to 5%*

DIMMER COMPATIBILITY

Forbes & Lomax	FLR603P
Legrand	HCL45-3PW, ADTP600RMHW1, ADTH70ORMTUW1
Insteon	2477D
Lutron	GL-600P-WH, S-600P, DV-600P, AY-600P-WH, D-600P-WH, TGCL-153P, DVCL-153P, DSL06-1LZ, MAEL-153M, PD-6WCL, SELV-300P, DVELV-300P, NTELV-500, RRD-6NA, MAELV-600, MRF-2-6ELV, HQRD-6NA

RECESSED HOUSING COMPATIBILITY

All-Pro	EI500AT, EI500RAT, ET500, ET500R, EI700AT, EI700RAT, EI700ATNB, EI700, EI700R, EI700NB, ET700, ET700R, EI700U, EI700UAT, EI2700AT, EI2700, ET2700, ET2700R
Capri	CR1, PR1, QL1, R9ASIC
Commercial Electric	H3, H17, H18
Elco	EL71CA
Halo	H7ICAT, H7RICAT, H7ICT, H7RICT, H7ICATNB, H7ICTNB, H7T, H7RT, H7TNB, H7TCP, H7UICAT, H7UICAT, H27ICAT, H27RICAT, H27ICT, H27RICT, H27T, H27RT, H5ICAT, H5RICAT, H5T, H5RT, H25ICAT
Juno	ICC22/R/W/S, IC23/W, IC21/R, TC2/R, IC20, IC25/W/S, TC20
Lightolier	11041CS/ICR/SIC/SICR, 11041CX (with ML7RAB housing adapter)
Lithonia Lighting	L7X, L7XP
Prescolite	IBXS
Progress	P87 (with ML7RAB housing adapter). Requires mounting clip accessory (sold separately). Consult factory for details.
Generation Lighting	1128, 1128QC, 11028, 11028QC, 11128, 11128QC, 11118, 11018, 1128FB
Thomas	PS1, PS9RM


SPECIFICATIONS

Item Number	14520S-15
Item Name	Traverse Lyte
Finish	White [-15]
Color Temperature	3000K
Lumens Delivered	800
Watts Consumed	13
Efficacy	62 lm/w
Color Rendering Index	90 CRI
Beam Spread	Lambertian
Rated Average Life	50,000 hours to 70%
Dimmable ⁽¹⁾	Yes to <5%
Voltage	120V
Power Factor	>.9
Ambient Operating Temp.	-40°C to +35°C
Construction	Stamped aluminum, powder coated
Lens	Polycarbonate
Warranty	5 years
Installation	New Construction on 3" and 4" round junction boxes, 4" square / octagon. Retrofit requires 14795, 4" pancake
Qualifications	EN★ WET T24

⁽¹⁾Dims best with electronic low Voltage (ELV) dimmers. When sizing the dimmer, de-rate it by 30% to account for in-rush current. (i.e. a standard 600 watt dimmer will have a 420 watt capacity when used with these fixtures).

PRODUCTS SHOWN: TRAVERSE LED LYTE IN WHITE FINISH







7"
178 mm

TRAVERSE UNLIMITED ROUND

14300S-15
White Finish




4.2"
107 mm



5.9"
150 mm

TRAVERSE UNLIMITED SQUARE

14301S-15
White Finish



4.2"
107 mm

FEATURES & BENEFITS

- Both new installs and retrofit
- Fast and seamless Installation
 - Standard 120V lighting fixture
 - Does not require a junction box
- Designed for superior performance and value
- Provides visually pleasing, color accurate illumination (90 CRI)
- ENERGY STAR® qualified
- Title-24 Compliant
- Wet rated for shower ceiling Installations
- IC Rated

DIMMER COMPATIBILITY

Forbes & Lomax	FLR603P
Legrand	HCL45-3PW
Insteon	DSL06-1LZ
Lutron	SELV-300P, DVELV-300P, NTELV-500, RRD-6NA, MRF-2-6ELV-120, HQRD-6NA, TGCL-153P, SCL-153P-WH, DVCL-153P, LGCL-153P, MACL-153M, PD-6WCL, AY-600P-WH, D-600P-WH, GL-600P-WH, S-600P, DV-600P

SPECIFICATIONS

Item Number	14300S(-xx)	14301S(-xx)
Item Name	Traverse Unlimited Round	Traverse Unlimited Square
Finishes	White [-15], Antique Bronze [-171] Satin Nickel [-849]	White [-15], Antique Bronze [-171] Satin Nickel [-849]
Color Temperature	3000K	3000K
Lumens Delivered	780	780
Watts Consumed	14 watts	14 watts
Efficacy	57 lm/w	57 lm/w
Color Rendering Index	90 CRI	90 CRI
Beam Spread	Lambertian	Lambertian
Rated Average Life	50,000 hours to 70%	50,000 hours to 70%
Dimmable ⁽¹⁾	Yes to 5%	Yes to 5%
Warm On Dim	No	No
Voltage	120V	120V
Power Factor	>.9	>.9
Ambient Operating Temp.	-20°C to +45°C	-20°C to +45°C
Construction	Spun aluminum, powder coated	Cast aluminum, powder coated
Lens	Polycarbonate	Polycarbonate
Warranty	5 years	5 years
Installation	New Construction, remodel, and Retrofit	New Construction, remodel, and Retrofit
Qualifications	IC Rated EN★ WET T24	IC Rated EN★ WET T24

EASY INSTALL IN 4 MINUTES OR LESS | NO JUNCTION BOX NEEDED




Step 1:

Pull wire to approximate location of fixture during rough-in, leaving enough to reach the Traverse Unlimited unit at install.



Step 2:

Cut hole in ceiling where the Traverse Unlimited unit will be installed.



Step 3:

Open Traverse Unlimited's integrated junction box cover. Pull wire out through the cut hole, trim to length, and strip wire ends.



Step 4:

Insert stripped wire ends into the speed connectors, supplied on the Traverse Unlimited units. Close the junction box cover.



Step 5:


Fold the spring loaded arms back against the Traverse Unlimited housing and slip unit up into cut hole while pulling wire back to avoid extra weight on the back of the unit.



Step 6:


Above the ceiling, spring loaded arms will release, pulling the unit up and into place.

TRAVERSE INSERT



TRAVERSE INSERT

14760SC-15 | 14761SC-15



FEATURES & BENEFITS

- Recessed look and feel with unparalleled Efficacy of LED
- Economical, long lasting upgrade to standard recessed lighting
- Provides visually pleasing, color accurate 90CRI illumination
- Easily installs into most recessed lighting housings with included Edison adapter
- ENERGY STAR® qualified
- Title-24 Compliant
- Dimmable down to 10%
- IC rated with approved housings
- Wet Rated for shower ceiling installations

DIMMER COMPATIBILITY

Forbes & Lomax	FLR603P
Lutron	SELV-300P, DVELV-300P, NTELV-500, RRD-6NA, MAELV-600, HQRD-6NA, TGCL-153P, SCL-153P, DVCL-153P, LGCL-153P, DSLO6-1LZ, GL-600P, S-600P, DV-600P, PD-5NE-WH, MACL-153M, PD-6wCL, AY-600P-WH, D-600P-WH
Legrand	HCL45-3PW, ADTP600RMHW1
Insteon	24770


RECESSED HOUSING COMPATIBILITY

All-Pro	EI700AT, EI700RAT, EI700ATNB, EI700, EI700R, EI700NB, ET700, ET700R, EI700U, EI700UAT, EI2700AT, EI2700, ET2700, ET2700R
Capri	CRI1, PR1, QL1, R9ASIC
Commercial Electric	H3, H17, H18
Elco	EL71CA
Halo	H7ICAT, H7RICAT, H7ICT, H7RICT, H7ICATNB, H7ICTNB, H7T, H7RT, H7TNB, H7TCP, H7UICAT, H7UICAT, H27RICAT, H27RICT, H27T, H27RT
Juno	ICC22/R/W/S, IC23/W, IC21/R, TC2/R
Lightolier	11041CS/ICR/SIC/SICR, 1104ICX (with ML7RAB housing adapter)
Lithonia Lighting	L7X, L7XP
Prescolite	IBXS
Progress	P87 (with ML7RAB housing adapter). Requires mounting clip accessory (sold separately). Consult factory for details.
Generation Lighting	1128, 1128QC, 11028, 11028QC, 11018, 1128FB
Thomas	PS1, PS9RM

SPECIFICATIONS

Item Number	14760SC-15	14761SC-15
Item Name	Traverse Insert	Traverse Insert
Finish	White [-15]	White [-15]
Color Temperature	2700K	3000K
Lumens Delivered	780	780
Watts Consumed	12 watts	12 watts
Efficacy	65 lm/w	65 lm/w
Color Rendering Index	90 CRI	90 CRI
Beam Spread	Lambertian	Lambertian
Rated Average Life	50,000 hours to 70%	50,000 hours to 70%
Dimmable ¹	Yes to 5%	Yes to 5%
Warm On Dim	No	No
Voltage	120V	120V
Power Factor	>.9	>.9
Ambient Operating Temp.	-40°C to +35°C	-40°C to +35°C
Warranty	5 years	5 years
Installation	6" recess retrofit	6" recess retrofit
Qualifications	EN★ WET T24	EN★ WET T24

¹ Dims best with electronic low Voltage (ELV) dimmers. When sizing the dimmer, de-rate it by 30% to account for in-rush current. (i.e. a standard 600 watt dimmer will have a 420 watt capacity when used with these fixtures).



OPTIONAL RETROFIT KITS

14791
for housings with integral "C" clips

14610
for housings without integral "C" clips

FEATURES & BENEFITS

- Designed for superior performance and value
- Economical, longer lasting alternative to standard recessed downlights
- Provides visually pleasing, color accurate illumination (90 CRI)
- Warm-on-dim feature creates a progressively warmer colored light as it is dimmed so you can create just the right mood for your space
- Easy to install:
 - Standard 120V lighting fixture
 - Mounts to standard 4" round / octagon junction box with 1.5 inch depth
- Title-24 Compliant
- Retrofits into most common recessed lighting housings with optional Edison base adapter (part #14791)
- Wet rated for shower ceiling installations
- Dimmable down to 5%*

DIMMER COMPATIBILITY

FOR 14705SC

Forbes & Lomax	FLR603P
Lutron	SELV-300P, DVELV-300P, NTELV-500, RRD-6NA, MAELV-600, MRF-2-6ELV-120, HQRD-6NA, TGCL-153P, SCL-153P, DVCL-153P, LGCL-153P, DSLO6-1LZ, GL-600P, S-600P, DV-600P

FOR 14706SC

Lutron	MAELV-600, MRF-2-6ELV, HQRD-6NA
--------	---------------------------------

RECESSED HOUSING COMPATIBILITY

The Traverse 4" fits into most 4" recessed housings including the following:

All-Pro	ET400R, EI400 ATSB, ET 400 ATSB, ET400R ATSB
Commercial Electric	HBR2000R, HBR2000BA
Halo	H99RTAT, H99RT
Juno	TC1R, TC1, IC1
Lithonia Lighting	L3, L3R
Generation Lighting	1105, 1115, 1179

SPECIFICATIONS

Item Number	14705SC-15	14706SC-15
Item Name	Traverse 4"	Traverse 4"
Finish	White [-15]	White [-15]
Color Temperature	2700-2200K	3000-2200K
Lumens Delivered	500	500
Watts Consumed	9 watts	9 watts
Efficacy	53 lm/w	53 lm/w
Color Rendering Index	90 CRI	90 CRI
Beam Spread	Lambertian	Lambertian
Rated Average Life	50,000 hours to 70%	50,000 hours to 70%
Dimmable ¹	Yes to 5%	Yes to 5%
Warm On Dim	Yes	Yes
Voltage	120V	120V
Power Factor	>.9	>.9
Ambient Operating Temp.	-40°C to +35°C	-40°C to +35°C
Construction	Stamped aluminum, powder coated	Stamped aluminum, powder coated
Lens	Polycarbonate snap in	Polycarbonate snap in
Warranty	5 years	5 years
Installation	4" recess retrofit and 4" round, square, or octagonal j-box with a minimum depth of 1.5"	4" recess retrofit and 4" round, square, or octagonal j-box with a minimum depth of 1.5"
Qualifications	WET WOD T24	WET WOD T24

¹ Dims best with electronic low Voltage (ELV) dimmers. When sizing the dimmer, de-rate it by 30% to account for in-rush current. (i.e. a standard 600 watt dimmer will have a 420 watt capacity when used with these fixtures).

LUCARNE LED NICHE LIGHTS

PRODUCT SHOWN: LUCARNE ROUND ADJUSTABLE DOWNLIGHT IN WHITE FINISH



The Lucarne LED niche lights from Generation Lighting combine a compact size with advanced LEDs to provide superior quality light from a small package. Available in fixed or adjustable downlights, each of these units feature 90 CRI in your choice of 2700K or 3000K and are available in either 12 or 24 volts. For maximum flexibility, each light ships with both a 30° or 65° beam spread lens included so you can adjust as needed during installation or easily reconfigure at a later date.

With a choice of three finishes, these niche lights are easy to place in virtually any setting. Whether you are looking for accent lighting to draw attention to architectural details of a space, wanting to highlight items on display, or just provide an additional layer of lighting to a room, the Lucarne LED Niche lights provide you the ultimate flexibility and level of illumination.


STEP

1

CHOOSE A DESIGN

p.614

Select either adjustable or fixed downlight versions based on your application.




STEP

2

SELECT TRANSFORMER

p.616

Lucarne LED Niche lights work with any of the Generation Lighting LX AC Transformers



LUCARNE LED NICHE LIGHTS

STEP


1

CHOOSE A DESIGN

Lucarne LED Niche Lighting is a versatile accent lighting option for your home or commercial space. With multiple color temperatures and beam spread options available you can customize your installation to direct light where and how it is needed. For highlighting objects, drawing attention to architectural details and improving overall illumination indoors or out, Lucarne Niche Lights adds a designer's touch.



ROUND FIXED DOWN LIGHT




Item Number (12V)	95411S(-xx)	95412S(-xx)
Item Number (24V)	95511S(-xx)	95512S(-xx)
Finish	White [-15], Antique Bronze [-171], Silver [-849]	
Color Temperature	2700K	3000K
Voltage	12v AC or 24v AC	
Delivered Lumens	300	
Power Consumption	5.5w	
Efficacy	55 lm/w	
Color Rendering Index	90	
Rated Average Life	50,000 hours to 70%	
Dimming Range ⁽¹⁾	Down to 10%	
Included Lenses	30° and 65°	
Material	Steel/Aluminum	
Certification	WET and IC Rated	

⁽¹⁾ Generation LED Niche Lights perform best with electronic transformers and electronic low-voltage (ELV) dimmers.

LUCARNE LED NICHE LIGHTS



ROUND ADJUSTABLE DOWN LIGHT



Item Number (12V)	95416S(-xx)	95417S(-xx)
Item Number (24V)	95516S(-xx)	95517S(-xx)
Finish	White [-15], Antique Bronze [-171], Silver [-849]	
Color Temperature	2700K	3000K
Voltage	12v AC or 24v AC	
Delivered Lumens	300	
Power Consumption	5.5w	
Efficacy	55 lm/w	
Color Rendering Index	90	
Rated Average Life	50,000 hours to 70%	
Dimming Range ⁽¹⁾	Down to 10%	
Included Lenses	30° and 65°	
Material	Steel/Aluminum	
Certification	DAMP and IC Rated	

⁽¹⁾ Generation LED Niche Lights perform best with electronic transformers and electronic low-voltage (ELV) dimmers.

LUCARNE LED NICHE LIGHTS

STEP
2

CHOOSE TRANSFORMER

Electronic Transformers

The zero-load electronic transformers from Generation Lighting Systems provide industry leading technology in a small form factor. All of these transformers include Radio Frequency Interference modules to eliminate interference that can occur when dimming low-voltage fixtures. These units also all feature local on/off switches and have a user replaceable secondary side of the transformer that can be swapped without an electrician or even needing to touch the primary wiring.



75W 24V ZERO-LOAD TRANSFORMER

L: 7.805" W: 1.36" H: 0.949"
Hardwire to power source and operate remotely or with installed switch. Secondary side features quick connection for fast install.
Wattage: 0w-75w Class II
Input: 120v AC Output: 24v AC
Max Run: 35 ft.

96623S-12
Black finish



75W 12V ZERO-LOAD TRANSFORMER

L: 7.805" W: 1.36" H: 0.949"
Hardwire to power source and operate remotely or with installed switch. Secondary side features quick connection for fast install.
Wattage: 0w-75w Class II
Input: 120v AC Output: 12v AC
Max Run: 35 ft.

96622S-12
Black Finish



150W 12V ZERO-LOAD TRANSFORMER

L: 8.385" W: 2.53" H: 1.219"
Hardwire to power source and operate remotely or with installed switch.
Wattage: 0w-150w Class I
Input: 120v AC Output: 12v AC
Max Run: 35 ft.

96624S-12
Black Finish

Magnetic Transformer



250W, 24V SINGLE OUTPUT HARDWIRE TRANSFORMER

L: 10.75" W: 4.5" H: 4.25"

94461-12
Black Finish

UL/cUL Listed. NEX 411 approved, thermally protected, dimmable and have resettable magnetic circuit breakers for short circuit protection. Housings feature easy-hang bracket wiring access door and knockouts for line voltage entry. Include boost tap for use when transformer is located 20' or more from first light.



ROMEX CONNECTOR

L: 1.5" W: 1.25" H: 2.25"
Use in lieu of existing cap on top of Lucarne Niche Lights for Romex and MC connections.

95620

PRODUCT SHOWN: LUCARNE ROUND FIXED DOWNLIGHT IN WHITE FINISH



RECESSED HOUSING

PRODUCTS SHOWN: 4" MULTIPLIER TRIM IN WHITE FINISH AND LED DISK LIGHTS (OBSCURED)



Selecting the right recessed housing begins with knowing the Installation method as well as understanding how the space will be used. The guide below will help you with the process of selecting your housing.

STEP
1

REMODEL OR NEW CONSTRUCTION

A "remodel" Installation typically is an existing room project where the Installation is made by cutting through existing ceiling materials. The housing will not be supported by joists but by the ceiling material, such as drywall.

A "new Construction" project is one that has access to the ceiling and joists; where insulation and drywall are not yet installed. New Construction housings are nailed directly into the joists with adjustable bar hangers.

STEP
2

IC OR NON-IC HOUSING

IC (insulation contact) housings can come in direct contact with insulation materials. Insulation should not be compressed.

Non-IC (no insulation contact) housings are for areas without insulation or where insulation can be kept a minimum of 3" away from housing.

STEP
3

SIZE OF HOUSING

4" housings are designed for a smaller, sleek look in your ceiling. Best used in smaller spaces for a minimal look.



6" housings are for the standard large aperture approach in your ceiling. Can be used in tall entryways and two-story hallways or high ceilings.

ADDITIONAL CONSIDERATIONS

AIR-TIGHT HOUSINGS are sealed to prevent air from escaping into the ceiling / floor above; a benefit to heating /cooling efficiency.

A RECESSED TRIM is the "ring" blending the recessed housing, lamp and ceiling material into a clean finish.

BAFFLES are the cone-like piece that surrounds the inside of the housing around the bulb; they can be smooth or ridged and help shape the light and minimize glare.



1179
New Construction / IC Airtight

Airtight construction

Meets airtight requirements for 2.0 CFM or less air leakage.

Safe – thermally protected, listed for damp location

IC housings approved for use in direct contact with insulation.

Adjustable housing

Housing adjusts vertically for various ceiling thicknesses

Junction box

Features snap-on covers, pry-out knockouts, riveted ground wire, and through-circuit wiring, with 2-in/2-out #12 wire.



WHITE FROSTED GLASS

WET
4" SHOWER TRIM

1152AT-15
(1) Medium Base
PAR20 35w max.



CLEAR FRESNEL GLASS

WET
4" SHOWER TRIM

1153AT-15
(1) Medium Base
PAR20 35w max.



WHITE FINISH

DAMP
4" BAFFLE TRIM

1156AT-14
(1) Medium Base
PAR20 50w max.



WHITE FINISH

DAMP
4" EYEBALL TRIM


1166AT-15
(1) Medium Base
PAR20 50w max.



WHITE FINISH

DAMP
4" MULTIPLIER TRIM

1162AT-14
(1) Medium Base
PAR20 50w max.



1115
Remodel / Non-IC

Safe – thermally protected, listed for damp location

Non-IC housings approved for use at least 3" away from insulation.

Junction box

Features snap-on covers, pry-out knockouts, riveted ground wire, and through-circuit wiring, with 2-in/2-out #12 wire.



WHITE FROSTED GLASS

WET

4" SHOWER TRIM

1152AT-15
(1) Medium Base
PAR20 35w max.



CLEAR FRESNEL GLASS

WET

4" SHOWER TRIM

1153AT-15
(1) Medium Base
PAR20 35w max.



WHITE FINISH

DAMP

4" BAFFLE TRIM

1156AT-14
(1) Medium Base
PAR20 50w max.



WHITE FINISH

DAMP

4" EYEBALL TRIM

1166AT-15
(1) Medium Base
PAR20 50w max.



WHITE FINISH

DAMP

4" MULTIPLIER TRIM

1162AT-14
(1) Medium Base
PAR20 50w max.

Adjustable socket assembly provides flexibility in lamping options.


Notch for T-Bar ceilings, no clips required.



Hinged door allows full access for wiring.

Quick Hit™ captive nails included and positioned for fast, easy installation. Tab to locate on bottom of joist.

Break-away bar hangers extend and will not fall out of plaster flange.



1128 & 1128QC
New Construction / IC Airtight

Airtight Construction

Meets airtight requirements for 2.0 CFM or less air leakage.

Safe – thermally protected, listed for damp location

IC housings approved for use in direct contact with insulation.

Adjustable housing

Housing adjusts vertically for various ceiling thicknesses.

Junction box with integral Romex connector

Features quick-push and lock connector and through-circuit wiring with 4-in/4-out #12 wire.

Quick Connectors

QC models come with quick connect wire connectors for fast connections to house wire.



WHITE FINISH



WHITE DEEP CONE BAFFLE



WHITE ALUMINUM RING CLEAR FRESNEL GLASS



WHITE DEEP CONE BAFFLE



WHITE ALUMINUM RING WHITE GLASS DIFFUSER

DAMP

6" BAFFLE TRIM

1126-14
(1) Medium Base PAR30L 75w max.
(1) Medium Base PAR30S 50w max.
(1) Medium Base BR30 65w max.

DAMP

6" BAFFLE TRIM

1151AT-14
(1) Medium Base PAR30L 75w max.
(1) Medium Base PAR30S 50w max.
(1) Medium Base BR30 65w max.

WET

6" SHOWER TRIM

1155AT-15
(1) Medium Base 40w max.

WET



6" OPEN SHOWER TRIM

1154AT-14
(1) Medium Base PAR30L 75w max.
(1) Medium Base PAR30S 50w max.
(1) Medium Base PAR38 90w max.

WET

6" SHOWER TRIM

1133AT-15
(1) Medium Base 40w max.



11028QC
New Construction / IC Airtight

Airtight Construction

Meets airtight requirements for 2.0 CFM or less air leakage.

Safe – thermally protected, listed for damp location

IC housings approved for use in direct contact with insulation.

Adjustable housing

Housing adjusts vertically for various ceiling thicknesses.

Junction box with integral Romex connector

Features quick-push and lock connector and through-circuit wiring with 4-in/4-out #12 wire.

Quick Connectors

QC models come with quick connect wire connectors for fast connections to house wire.



WHITE ALUMINUM RING
WHITE GLASS DIFFUSER

WET

6" FLAT GLASS SHOWER TRIM

11033AT-15
(1) Medium Base
40w max.



WHITE DEEP
CONE BAFFLE

WET

6" OPEN SHOWER TRIM

1154AT-14
(1) Medium Base
PAR30L 75w max.
(1) Medium Base
PAR30S 50w max.
(1) Medium Base
PAR38 90w max.



WHITE DEEP
CONE BAFFLE



DAMP

6" BAFFLE TRIM

1151AT-14
(1) Medium Base
PAR30L 75w max.
(1) Medium Base
PAR30S 50w max.
(1) Medium Base
BR30 65w max.
(1) Medium Base
PAR38 90w max.

6" HOUSING 11019

NEW CONSTRUCTION / IC / SHALLOW AIRTIGHT



11019

New Construction / IC / Shallow Airtight

Airtight Construction

Meets airtight requirements for 2.0 CFM or less air leakage.

Safe – thermally protected, listed for damp location

IC housings approved for use in direct contact with insulation.

Adjustable Housing

Housing adjusts vertically for various ceiling thicknesses

Junction box

Features quick-push and lock connector and through-circuit wiring with 4in/4-out #12 wire.



WHITE DEEP
CONE BAFFLE

DAMP

6" BAFFLE TRIM

1158AT-14

- (1) Medium Base PAR30L 75w max.
- (1) Medium Base PAR30S 50w max.
- (1) Medium Base BR30 65w max.





WHITE ALUMINUM RING
WHITE GLASS DIFFUSER

WET

6" FLAT GLASS SHOWER TRIM

11033AT-15

- (1) Medium Base 40w max.



11018
Remodel / IC Airtight

Airtight Construction

Meets airtight requirements for 2.0 CFM or less air leakage.

Safe – thermally protected, listed for damp location

IC housings approved for use in direct contact with insulation.

Fast, easy installation

Provided with mounting clips

Junction box

Features snap-on covers, pry-out knockouts, riveted ground wire, and through-circuit wiring, with 2-in/2-out #12 wire.



WHITE ALUMINUM RING
WHITE FRESNEL GLASS DIFFUSER

WET

6" FLAT GLASS SHOWER TRIM

11033AT-15
(1) Medium Base
40w max.



WHITE DEEP
CONE BAFFLE

DAMP

6" BAFFLE TRIM

1151AT-14
(1) Medium Base
PAR30L 75w max.
(1) Medium Base
PAR30S 50w max.
(1) Medium Base
BR30 65w max.
(1) Medium Base
PAR38 90w max.



WHITE DEEP
CONE BAFFLE

WET

6" OPEN SHOWER TRIM

1154AT-14
(1) Medium Base
PAR30L 75w max.
(1) Medium Base
PAR30S 50w max.
(1) Medium Base
PAR38 90w max.

6" HOUSING: 1109

NEW CONSTRUCTION / IC AIRTIGHT / SLOPED CEILING

Adjustable socket assembly provides flexibility in lamping options.


Break-away bar hangers extend and will not fall out of plaster flange.

Designed to fit ceiling slopes of 15° to 45°.



Quick Hit™ captive nails included and positioned for fast, easy installation.

Tab to locate on bottom of joist.



1109
New Construction / IC Airtight / Sloped Ceiling

Airtight Construction

Meets airtight requirements for 2.0 CFM or less air leakage.

Safe – thermally protected, listed for damp location

IC housings approved for use in direct contact with insulation.

Adjustable Housing

Housing adjusts vertically for various ceiling thicknesses

Junction box

Features quick-push and lock connector and through-circuit wiring with 4in/4-out #12 wire.



WHITE FINISH

DAMP

6" SLOPED TRIM

1121-14
(1) Medium Base
PAR38 75w max.

PRODUCT SHOWN: TOWNER ONE LIGHT MINI
PENDANTS IN SATIN BRONZE FINISH
DESIGNER: JLV CREATIVE
BUILDER: CRESCENT HOMES
PHOTOGRAPHER: ROB MCDANIEL



PRODUCTS SHOWN: LX CABLE HIGH OUTPUT MODULES (OBSCURED)
AND JANE 200 LED TAPE (OBSCURED)





LIGHTING SYSTEMS

LX Cable / LED Tape

LX CABLE SYSTEM

PRODUCT SHOWN: LX CABLE SYSTEM LED FESTOON (OBSCURED)



The Generation Lighting LX Cable System is our premier lighting solution giving users the utmost flexibility to easily design and install customized lighting to meet the specific needs of their space. Simply identify the length of run for which you will need cable, select a transformer and choose the lamping modules best suited for your application.

Our LX Cable System is uniquely engineered so that you can mix and match any of our lamping modules on the same system and the snap-on design enables quick installation and the ability to adjust over time as lighting needs or preferences change.

STEP
1

CHOOSE LAMPS AND HOLDERS

Select from a variety of low profile linear lamps and lamp holders that suit your application.



HIGH OUTPUT MODULE
p.632



LED FESTOON
p.634



XENON FESTOON
p.636



WEDGE-BASED LAMPS
p.638

	HIGH OUTPUT MODULE p.632	LED FESTOON p.634	XENON FESTOON p.636	WEDGE-BASED LAMPS p.638
Features	Frosted diffuser that minimizes pixelation even on polished stone counters Available in 2 lengths to fit more spaces	Up to 80% energy savings over xenon Can be used with existing systems Generate less heat than xenon	Tried and true solution that has proven itself Available in lower color temperatures Longer lamp life-span than wedge based	Most economical solution Good lumen output Available in very low color temperatures for candle-light effect
Options	2 lengths 2 color temperatures 12V AC	2 color temperatures Clear or Frosted 12V AC	2 color temperatures Clear or Frosted 5 or 10 watts 12V AC	3 color temperatures Xenon or incandescent T3 1/4 base 3 or 5 watts
Price	\$\$	\$	\$	\$

STEP
2

SELECT CABLE

p.640

Select from a variety of low profile linear lamps and lamp holders that suit your application.

STEP
3

SELECT TRACK

p.640

4' Noryl® track section may be easily cut to desired length.

STEP
4

SELECT COMPONENTS

p.641

Additional components are available including screws, track clips, tape, connectors etc.

STEP
5


SELECT TRANSFORMER

p.642

Electronic and magnetic, 12v, 60w up to 300w output.

LX CABLE SYSTEM | LAMP - HIGH OUTPUT LED MODULE

PRODUCTS SHOWN: HIGH OUTPUT LED MODULES




LX CABLE SYSTEM | LAMP - HIGH OUTPUT LED MODULE

STEP
1

CHOOSE LAMPS AND HOLDERS

The miniature, High Output LED Modules can be used with 12v Generation Lighting LX Cable Systems powered by magnetic low-voltage or electronic low-voltage transformers. Simply snap the LED modules onto LX track and cable to provide a generous amount of illumination without the need for a lampholder. These high intensity LED modules utilize wider recommended spacing than our festoons while still providing even surface illumination.



Item Number	98700S-986	98701S-986	98702S-986	98703S-986
Length	2"		4"	
Color Temperature	2700K	3000K	2700K	3000K
Voltage	12v AC			
Finish	Tinted Aluminum [-986]			
Diffuser	Frosted			
Delivered Lumens	85	90	220	230
Power Consumption	1.7w		4w	
Efficacy	50 lm/w	53 lm/w	55 lm/w	58 lm/w
Color Rendering Index	90 CRI			
Rated Average Life	50,000 hours to 70%			
Dimmable ⁽¹⁾	Down to 10%			
Installation	High Output LED Modules snap onto the LX track			
Recommended Spacing	6" on center (1" minimum separation)		12" on center (1" minimum separation)	
Certification	ETL			


(1) Generation Lighting High Output LED Modules are dimmable on magnetic and electronic low voltage systems. For magnetic systems, a standard incandescent or magnetic low voltage (MLV) dimmer can be used. For electronic, an electronic low voltage (ELV) dimmer is recommended.

LX CABLE SYSTEM | LAMP - FESTOON LED

STEP
1

CHOOSE LAMPS

Upgrade to our LX LED Festoons from our 5w Xenon Festoons and realize an energy savings of over 80% without compromising light output. LX LED Festoons snap into LX Festoon Lampholders (sold separately), making retrofitting of existing systems easy. For new systems, pick a matching LX Festoon Lampholder and clip them onto your LX Cable and Track. LX LED Festoons are available in 2700, 3000, and 4000K, in 12v.




Item Number	96116S(-xx)	96118S(-xx)
Finish	Clear [-32], Frosted [-33]	
Color Temperature	2700K	3000K
Voltage	12v AC	
Delivered Lumens	59	60
Power Consumption	.708w	
Efficacy	83 lm/w	85 lm/w
Color Rendering Index	>90 CRI	
Rated Average Life	50,000 hours to 70%	
Dimmable ⁽¹⁾	Down to 10%	
Lamp Base	Festoon	
Recommended Spacing	4" on center (1" minimum separation)	
Certification	cETL, damp rated	

⁽¹⁾ LX LED Festoons are dimmable on magnetic and electronic low voltage systems. For magnetic systems, a standard incandescent or magnetic low voltage (MLV) dimmer can be used. For electronic, an electronic low voltage (ELV) dimmer is recommended. Lamps in chart above only compatible with Festoon Lampholder 9830.

Festoon Lampholder


For use with our highly specified LED and xenon festoons, Generation Lighting LX Festoon Lampholders feature a high quality reflector and base for directing light where you need it. Our Accent Task Socket for general applications provides crisp linear lighting. Each lampholder snaps onto LX Track and Cable with ease and can be spaced based on your criteria.



Item Number	9830(-xx)
Reflector	"L" Accent Task Socket
Voltage	12V AC
Lamp Base	Festoon
Certification	cETL, damp rated
Maximum Wattage	(1) 10w Xenon Festoon (1) LED Festoon
Recommended Minimum Spacing	2" on center (5w Xenon) 4" on center (LED Festoon)
Material / Finish	Black [-12] and White [-15] Heat resistant polycarbonate base and anodized aluminum reflector

Application Guide


Application	Recommended Spacing on Center	Suggested Lamp Source(s)
Above Cabinet	6" - 12"	LED Festoon
Under Cabinet	2" - 6"	LED Festoon
Inside Cabinet	1 - 2 per shelf	LED Festoon
Toe Space	4"	LED Festoon
Showcase	4" - 6"	LED Festoon
Cove	2" - 6"	LED Festoon



Choose either Method "A" or "B" for even illumination on a vertical surface where cove lighting is desired. These easy to use spacing guidelines assure even vertical illumination when the suggested spacing and distances are followed.

METHOD A

Lighting system installed on angled surfaces.




For 6" on center
6" from vertical surface

For 4" on center
4" from vertical surface

For 2" on center
2" from vertical surface

METHOD B

Lighting system installed on horizontal (flat) surfaces.



For 6" on center
6" from vertical surface

For 4" on center
4" from vertical surface


For 2" on center
2" from vertical surface

LX CABLE SYSTEM | LAMP - XENON FESTOON

STEP
1

CHOOSE LAMPS

Generation Lighting LX Xenon Festoons revolutionized the under cabinet lighting industry and continue to be an industry standard. They are available in 5 and 10w. Our directional lampholder to easily positions light where you need it (lampholder sold separately).



Item Number	97118(-xx)	97119(-xx)
Color Temperature	2550K	2650K
Voltage	12v AC	12v AC
Rated Watts	5 watts	10 watts
Finish	Clear [-32], Frosted [-33]	
Gross Lumens	33	83
Power Consumption	4.2w	8.4w
Efficacy	8 lm/w	10 lm/w
Color Rendering Index	>90 CRI	
Rated Average Life	16,000 hours	12,000 hours
Dimmable	Yes	
Lamp Base	Festoon	
Recommended Spacing	4" on center (1" minimum separation)	


Lamps in chart above only compatible with Festoon Lampholder 9830.

Footcandle & Spacing Chart

Lamp Item #	Lampholder Spacing	Distance to Illuminated Surface				
		6"	12"	18"	24"	30"
97118(-xx)	2"	114	52	24	14	10
	4"	71	32	15	8.9	6.4
	6"	64	29	13	8	5.7
	8"	57	26	12	7.1	5.1
	10"	51	23	11	6.3	4.5
	12"	45	20	9.5	5.6	4.0
97119(-xx)	4"	179	81	38	22	16
	6"	160	72	34	20	14
	8"	142	64	30	18	13
	10"	128	58	27	16	11
	12"	114	52	24	14	10

Festoon Lampholders


For use with our highly specified LED and xenon festoons, Generation Lighting LX Festoon Lampholders feature a high quality reflector and base for directing light where you need it. Our Accent Task Socket for general applications provides crisp linear lighting. Each lampholder snaps onto LX Track and Cable with ease and can be spaced based on your criteria.



Item Number	9830(-xx)
Reflector	"L" Accent Task Socket
Voltage	12V AC
Lamp Base	Festoon
Certification	cETL, damp rated
Maximum Wattage	(1) 10w Xenon Festoon (1) LED Festoon
Recommended Minimum Spacing	2" on center (5w Xenon) 4" on center (LED Festoon)
Material / Finish	Black [-12], White [-15] Heat resistant polycarbonate base and anodized aluminum reflector

Application Guide


Application	Recommended Spacing on Center	Suggested Lamp Source(s)
Above Cabinet	6" - 12"	LED Festoon
Under Cabinet	2" - 6"	LED Festoon
Inside Cabinet	1 - 2 per shelf	LED Festoon
Toe Space	4"	LED Festoon
Showcase	4" - 6"	LED Festoon
Cove	2" - 6"	LED Festoon



Choose either Method "A" or "B" for even illumination on a vertical surface where cove lighting is desired. These easy to use spacing guidelines assure even vertical illumination when the suggested spacing and distances are followed.

METHOD A

Lighting system installed on angled surfaces.




For 6" on center
6" from vertical surface

For 4" on center
4" from vertical surface

For 2" on center
2" from vertical surface

METHOD B

Lighting system installed on horizontal (flat) surfaces.



For 6" on center
6" from vertical surface

For 4" on center
4" from vertical surface



For 2" on center
2" from vertical surface

LX CABLE SYSTEM | LAMP - WEDGE BASE

STEP
1

CHOOSE LAMPS & LAMPHOLDER


LX Wedge Base Lamps provide illumination for a varied list of applications. LX Wedge Base Lamps add another level of versatility to Generation Lighting LX Cable systems.



Item Number	9728	9731	9732
Lamp Type	T3¼ Incandescent	T3¼ Xenon	T3¼ Xenon
Color Temperature	2300K	2400K	2550K
Voltage	12v AC	12v AC	12v AC
Rated Watts	5w	3w	5w
Gross Lumens	23	15	33
Power Consumption	4w	2.7w	4.2w
Efficacy	6 lm/w	6 lm/w	8 lm/w
Color Rendering Index	>90 CRI	>90 CRI	>90 CRI
Rated Average Life	9,000 hours	19,000 hours	8,000 hours
Dimmable	Yes	Yes	Yes
Lamp Base	Wedge	Wedge	Wedge
Minimum Spacing	4" on center	4" on center	4" on center

Wedge Base Lampholders

For use with our xenon and incandescent wedge base lamps, Generation Lighting LX Wedge Base Lampholders feature a high quality reflector for minimizing light loss from your selected lamps. Each lampholder snaps onto LX Track and Cable with ease and can be spaced based on your criteria and lamp source (sold separately).



Item Number	9428(-xx)
Reflector	Two lamp socket, ideal for cove lighting
Voltage	12v
Certification	cETL, damp rated
Lamp Type	T3¼ Wedge
Max. Wattage	(2) 5w incandescent or xenon
Min. Spacing	4" on center
Material / Finish	Black [-12] and White [-15] anodized aluminum reflector and heat resistant polycarbonate.

Application Guide

Application	Recommended Spacing on Center	Suggested Lamp Source(s)
Above Cabinet	2" - 4"	3w-5w Incandescent or Xenon
Inside Cabinet	1 - 2 per shelf	3w-5w Incandescent or Xenon
Toe Space	2" - 4"	3w-5w Incandescent or Xenon
Cove	4"	3w-5w Incandescent or Xenon

LX CABLE SYSTEM | COMPONENTS

STEP

2

SELECT CABLE

Spools of cable especially designed with easy piercing, self-sealing insulation over stranded copper wire for use with Generation Lighting LX Cable Lighting system. Markings for lampholder placement every 2". Designed to be mounted in Generation Lighting LX Track.



WHITE FINISH [-15]



BLACK FINISH [-12]

INDOOR 100' SPOOL¹

L: 100' W: .375" H: .187"

9471-12
Black Finish

9471-15
White Finish

INDOOR 50' SPOOL¹

L: 50' W: .375" H: .187"

9470-12
Black Finish

9470-15
White Finish

INDOOR 25' SPOOL¹

L: 25' W: 0.375" H: 0.187"

9469-12
Black Finish

9469-15
White Finish

¹LX 10/2 AWG 105° C cable is rated for indoor use only. Maximum wattage per length 300w at 12v; 600w at 24v cable is not rated to run behind walls. Check with local codes.

STEP

3

SELECT TRACK



TRACK

L: 48" W: .5" H: .25"

Noryl® track to support cable and lampholders. Use double faced tape (9450), track clip (9438) or screws (9862) through pre-drilled holes to attach track to surface. Track may be flexed, notched, curved and easily cut for various applications.

9435-12
Black Finish

9435-15
White Finish



TRACK WITH FASCIA PANEL

L: 48" W: .875" H: 1.125"

One piece Noryl® fascia panel with integral track to support cable and lampholders. Use under shelves or where system cannot be hidden behind a lip on cabinets. Track/fascia may be easily cut to various lengths. Use double faced tape (9450) track clip (9438) or screws (9862) through pre-drilled holes to attach track/fascia to surface. Use double-faced tape on glass and other smooth surfaces.

9443-12
Black Finish

9443-15
White Finish

STEP
4

SELECT COMPONENTS



TRACK CLIP

L: 1" W: .75" H: .343"

Polycarbonate track mounting clip. Easily snaps on at any point along 9435 track or 9443 track/fascia panel to secure to surface. Space clips according to weight of fixtures, to prevent track from sagging. Includes .375" long #4 screw.

9438-12

Black Finish

9438-15

White Finish




DOUBLE FACED TAPE

L: 25' W: .375" H: .031"

Specially designed "High Adhesion" 3M™ double-faced tape for use with 9435 track and 9443 track/fascia panel. Allow minimum 24 hours curing of adhesive prior to applying power to the circuit.

9450

3M™




SCREWS

#4 L: .375"

3/8" long #4 Phillips flat head screws for attaching 9435 track or 9443 track/fascia panel to surface. Each box contains 50 screws.

9862

Zinc finish



TAP OFF CONNECTOR

L: 1.5" W: 1.5" H: .437"


Polycarbonate tap off connector. Use to tap off of low voltage Generation Lighting® Cable and create a parallel run for shelving, etc. Corrosion resistant contacts pierce the specially designed Generation Lighting® cable for electrical connection. Listed 12v and 24v. Wet location 12v only. Maximum wattage after connection on 105°C Generation Lighting® tap cable: 200w at 12v; 375w at 24v.

9380-12

Black Finish

9380-15

White Finish



MINIATURE WIRING COMPARTMENT / SPLICER

L: 2" W: .968" H: .625"

Polycarbonate splicer with cover for connection between transformer extension wire (i.e. Romex) and low voltage cable, or LED Tape Connector. Maximum 25 amps.

9459-12

Black Finish

9459-15

White Finish



FUSED PLUG

L: .875" W: .75" H: .812"

For powering multiple Generation Lighting low voltage luminaires from an LX Cable System. See page "Technical Information" on page 668 for detailed wiring information.

9488-12

Black Finish

9488-15

White Finish



WIRING COMPARTMENT

L: 2" W: 1.312" H: 1.25"

Steel wiring compartment with hole for .5" conduit connector, snap on cover and opening for track and cable. Includes terminal block for connection between transformer extension wire (i.e. Romex type) and low voltage cable. Maximum 25 amps.

9481-12

Black Finish

9481-15

White Finish

LX CABLE SYSTEM | TRANSFORMERS

STEP
5

SELECT TRANSFORMER

Magnetic Transformers

Magnetic transformers are encased in a powder coated metal enclosure that is potted to minimize noise and vibration. All are UL/cUL Listed, NEC 411 Approved, thermally protected, dimmable and have resettable magnetic circuit breakers for short circuit protection. Housings feature easy-hang bracket, wiring access door and knockouts for line voltage entry.



HARDWIRE 12V MAGNETIC TRANSFORMER

Include boost tap for use when transformer is located 20' or more from first light.

75W 12V SINGLE OUTPUT

L: 8.75" W: 4.25" H: 3.75"

94458-12

Black Finish

150W 12V SINGLE OUTPUT

L: 10.5" W: 4.312" H: 4.312"

94460-12

Black Finish

300W 12V SINGLE OUTPUT

L: 10.5" W: 4.375" H: 3.875"

94462-12

Black Finish

Electronic Transformers

The zero-load electronic transformers from Generation Lighting provide industry leading technology in a small form factor. All now include Radio Frequency Interference modules to eliminate interference that can occur when dimming low-voltage fixtures. These units also have the added benefits of local on/off switches and a user replaceable secondary side of the transformer that can be swapped without an electrician or even needing to touch the primary wiring.



60W AC CLASS II⁽¹⁾

L: 2.75" W: 1.5" H: 1.125"
 UL 2108, flame resistant plastic enclosure. Includes terminal block for 12/2 AWG max Romex type input and 10/2 AWG LX Cable output. Designed to be mounted vertically at the bottom of the unit. 6" input and output leads for easy installation.
 Wattage: 15w – 60w Class II
 Input: 120v AC Output: 12V AC
 Max Run: 35 ft.

9454-12
 Black Finish

⁽¹⁾Should not be used with LED systems.



75W 12V ZERO-LOAD TRANSFORMER

L: 7.805" W: 1.36" H: 0.949"
 Hardwire to power source and operate remotely or with installed switch. Secondary side features quick connection for fast install.
 Wattage: 0w-75w Class II
 Input: 120v AC Output: 12v AC
 Max Run: 35 ft.

96622S-12
 Black Finish



150W AC CLASS I

L: 6.25" W: 2.25" H: 1.67"
 UL 2108, flame resistant plastic enclosure. Includes terminal block for 12/2 AWG max Romex type input and 10/2 AWG LX Cable output. Designed to be mounted vertically at the bottom of the unit.
 Wattage: 60w – 150w Class I
 Input: 120v AC Output: 12V AC
 Max Run: 35 ft.

9456-12
 Black Finish

⁽¹⁾Should not be used with LED systems.



150W 12V ZERO-LOAD TRANSFORMER

L: 8.385" W: 2.53" H: 1.219"
 Hardwire to power source and operate remotely or with installed switch.
 Wattage: 0w-150w Class I
 Input: 120v AC Output: 12v AC
 Max Run: 35 ft.

96624S-12
 Black Finish

JANE LED TAPE

PRODUCTS SHOWN: JANE 200 LED TAPE (OBSCURED)
AND STIRLING ONE LIGHT WALL SCONCE IN BRUSHED NICKEL FINISH




STEP
1

CHOOSE TAPE

Jane LED Tape is perfect for a wide range of indoor applications where space is limited. Its low-profile design and flexibility allow for discrete installation in spaces like under cabinets, cove ceilings, toe-kicks, in cabinets or even in drawers. Jane 200 features high quality LED diodes that meet a stringent three-step binning threshold for maintaining a consistent color of light across an entire run.



JANE 200



2700K	900004-15	900006-15
3000K	900005-15	900007-15
Length	40'	10'
Finish	White [-15]	
Voltage	24v DC	
Lumens Delivered (@ 3000K)	200/ft	
Power Consumption	2.2w/ft	
Efficacy	90.9 lm/w	90.9 lm/w
Color Rendering Index	90 CRI	
Rated Average Life	50,000 hours to 70%	
Certification	IP20 Rated for Indoor Use, ENERGY STAR® Qualified	
Dimmable ⁽¹⁾	Yes, to 10%	
Max. Run Length	40'	
Installation	Cut every 6" to fit your space. Every cut piece can be powered. Connect to transformer using connector cord. You may also connect strips together using available connector cords.	

⁽¹⁾ Jane LED Tape is dimmable on magnetic and electronic low voltage systems. For magnetic systems, a standard incandescent or magnetic low voltage (MLV) dimmer can be used. For electronic, an electronic low voltage (ELV) dimmer is recommended.

STEP
2

SELECT ACCESSORIES

p.646

STEP
3

SELECT TRANSFORMER

p.647

JANE LED TAPE | ACCESSORIES

STEP
2

SELECT ACCESSORIES

Tape Tracks



LED TAPE TRACK

L: 48" W: .75" H: .5"

98670-15

White Finish

Polycarbonate track for use on Jane LED Tape. Comes in 4' sections that can easily be cut to size in the field. Mounts flat or at a 45 degree angle using screws or double-sided tape.



FLAT LENS

L: 48" W: .625" H: .060"

98673-97

Frosted Finish

Flat, frosted lens for use with LED tape track to protect LED tape and reduce pixelation while providing a wider beam of light. (Track not included)

Connector Cords

Cords with fold-over clasps on either end for quick and secure connections between two pieces of Jane 200 LED Tape



96" POWER CORD

L: 96"

9050000-15

White Finish

For connecting Jane LED Tape to 24v DC Transformer. Cord has bare leads on one end for easy wiring to transformer and a fold-over clasp on the other for a quick, secure connection to LED tape.



72" CONNECTOR CORD

L: 72"

905040-15

White Finish



36" CONNECTOR CORD

L: 36"

905007-15

White Finish



24" CONNECTOR CORD

L: 24"

905006-15

White Finish



18" CONNECTOR CORD

L: 18"

905005-15

White Finish



12" CONNECTOR CORD

L: 12"

905004-15

White Finish



6" CONNECTOR CORD

L: 6"

905003-15

White Finish



3" CONNECTOR CORD

L: 3"

905002-15

White Finish




JOINER CONNECTOR

L: .812" W: .5" H: .187"

905001-15

White Finish

Adapter with fold-over clasps on each end for linking two pieces of Jane 200 tape together with minimal gap.



TRACK SCREWS

#4 L: .375"

9862

Pack of 50, 3/8" long #4 Philips flat head screws for securely mounting LED tape track.



DOUBLE FACED TAPE

L: 300" W: .375" H: .031"

9450

Specially designed "High Adhesion" 3M double-faced tape for use with LED tape track. Allow a minimum of 24 hours curing.

10 PACK LED TAPE CLIPS

905045-32

Brushed Steel Finish

10 pack of metal clips for securing LED tape.

STEP
3

SELECT TRANSFORMER

Electronic Transformers



60W, 24V DC SINGLE OUTPUT TRANSFORMER

L: 9.375" W: 2.5" H: 1.375"

98745S-12

Black Finish

60w, 120v Primary, 24v DC Secondary, Electronic Transformer. Black Powder Coated Enclosure. Indoor Use Only.



150W, 24V DC SINGLE OUTPUT TRANSFORMER

L: 11" W: 4" H: 2.25"

98746S-12

Black Finish

105w, 120v Primary, 24v DC Secondary, Electronic Transformer. Black Powder Coated Enclosure. Indoor Use Only.



150W, 24V DC SINGLE OUTPUT TRANSFORMER

L: 11" W: 4" H: 2.25"

98747S-12

Black Finish

150w, 120v Primary, 24v DC Secondary, Electronic Transformer. Black Powder Coated Enclosure. Indoor Use Only.

Magnetic Transformer



200W, 24V DC SINGLE OUTPUT TRANSFORMER

L: 8.78" W: 3.75" H: 4.25"

98743S-12

Black Finish

200w, 120v Primary, 24v DC Secondary, Magnetic Transformer, Black Powder Coated Enclosure, Wet or Dry Location

PRODUCT SHOWN: LED DISK LIGHTING (OBSCURED)





UNDERCABINET

collections

VIVID 120V LED


STEP
1

CHOOSE FIXTURES

The Vivid LED Under cabinet series takes the classic xenon or fluorescent under cabinet light to the next level. Using high quality LED technology, these fixtures achieve great light output and a high level of energy efficiency at an extremely affordable price point. With local on/off switches and the ability to be dimmed down to 10% these fixtures work well for different activities or times of day.



WHITE FINISH [-15]



2700K	49274S-15	49275S-15	49276S-15	49277S-15	49278S-15
3000K	49374S-15	49375S-15	49376S-15	49377S-15	49378S-15
Length	7.5"	12"	18"	24"	30"
Voltage	120v Direct Wire				
Lumens (@ 3000K)	343	575	900	1245	1461
Power Consumption	6.4w	9.7w	15.5w	20.6w	26w
Efficacy	54 lm/w	59 lm/w	58 lm/w	60 lm/w	55 lm/w
Color Rendering Index	90 CRI				
Rated Average Life	50,000 hours to 70%				
Dimming range ⁽¹⁾	Down to 10%				
Installation	Hard wire or plug in with optional power cord accessory. Link multiple units with optional connector cords.				
Certification	ETL Dry location, ENERGY STAR Qualified, Title 24 Certified				
Features	Local on/off switch				

(1) Vivid 120V LED is dimmable with a standard incandescent or electronic low voltage (ELV) dimmer. When sizing dimmer, consult with the dimmer manufacturer for information on de-rating the dimmer for in-rush current.

STEP
2

SELECT ACCESSORIES

Connectors

Use to join Vivid Undercabinet fixtures together in sequence.



3" CONNECTOR CORD

L: 3"

95220S-15
White Finish



6" CONNECTOR CORD

L: 6"

95221S-15
White Finish



12" CONNECTOR CORD

L: 12"

95222S-15
White Finish



18" CONNECTOR CORD

L: 18"

95223S-15
White Finish



MALE TO MALE CONNECTOR

L: 1"

95236S-15
White Finish

Use to join Vivid Undercabinet fixtures together in sequence with no gap in between units.



FEMALE TO FEMALE CONNECTOR

L: 1"

95237S-15
White Finish

Use to join a power and connector cord or two connector cords for longer runs.

Power Cords

For plug-in installs where Vivid Undercabinet unit will be powered via a wall outlet.



24" POWER CORD

L: 24"

95230S-15
White Finish



72" POWER CORD

L: 72"

95231S-15
White Finish

SELF-CONTAINED FLUORESCENT




STEP
1

CHOOSE FIXTURES

Self-Contained Fluorescent Lighting is designed with quality and performance in mind. The low profile design is optimal for confined areas. High performance electronic ballasts and T5 lamps provide instant-on, flicker-free light. Contains multiple knockouts for ease of installation and linking units together.



WHITE FINISH [-15]



Item Number	4975BLE-15	4976BLE-15	4977BLE-15
Finish	White [-15]		
Length	12.25"	21.25"	24.5"
Color Temperature	3000K		
Voltage	120v AC		
Gross Lumens ⁽¹⁾	390	855	780
Power Consumption	8w	13w	16w
Efficacy	49 lm/w	66 lm/w	49 lm/w
Color Rendering Index	>82 CRI		
Rated Average Lamp Life	10,000 hours		
Dimmable	No		
Minimum Spacing	Adjacent mounting capable		
Includes	T5 lamp		
Certification	DAMP T24		

⁽¹⁾ Gross lumen level is derived from lamp source output. Some illumination is lost through diffuser. Actual light delivered to surface will be less.

Optional Accessory



ON/OFF SWITCH

Snaps into switch knock out on Self-Contained Fluorescent fixtures.

9027-15
White Finish

PRODUCT SHOWN: SELF-CONTAINED FLOURESCENT (OBSURED)



LED DISK LIGHTING


STEP
1

CHOOSE INDIVIDUAL DISKS*


LED Disk Lighting is ideal for residential, commercial and retail applications with its ample lumen output and versatility. The low-profile 12v LED Disks can easily be daisy-chain or hub-and-spoke linked to power a maximum of six disks on one transformer. Choose from plug-in or hardwire transformers, or power your disks from an LX Cable System using our Fused Plug (9488).



WHITE FINISH [-15]



BLACK FINISH [-12]



Item Number	98860SW (-xx)
Finish	Black [-12], White [-15]
Color Temperature	3000K
Voltage	12v AC
Lumens	170
Power Consumption	4w
Efficacy	43 lm/w
Color Rendering Index	>85 CRI
Rated Average Life	40,000 hours to 70%
Dimmable ⁽¹⁾	Down to 10%
Certification	cETL, damp rated
Material	Low-profile, die-cast aluminum with captive screw and 36" linking cord
Included Accessories	36" connector cord, three cord clips
Optional Accessory	Connection Hub

⁽¹⁾ LED Disks are dimmable on magnetic and electronic low voltage systems. For magnetic systems, a standard incandescent or magnetic low voltage (MLV) dimmer can be used. For electronic, an electronic low voltage (ELV) dimmer is recommended.

* For pre-packaged kits, see page 657

Photometrics⁽²⁾


AVERAGE LUMINANCE TABLE (cd/m2)

Angle	HORIZONTAL ANGLE (DEGREES)		
	0°	45°	90°
0°	136	136	136
45°	175	146	112
55°	159	125	92
65°	142	100	69
75°	119	72	44
85°	44	25	11

VERTICAL ANGLE (DEGREES)

⁽²⁾ Photometry based on (1) 98860SW(-xx) LED Disk in 3000K CCT.

POLAR CANDELA CHART



ZONEN LUMEN SUMMARY

Zone	Lumens	% of Lamp
0° - 30°	56.7	32.5
0° - 40°	93.4	53.6
0° - 60°	157.7	90.4
0° - 90°	174.4	100
90° - 180°	0	0
0° - 180°	174.4	100

STEP
2

SELECT ACCESSORIES



MINIATURE WIRING COMPARTMENT / SPLICER

L: 2" W: .968" H: .625"

9459-15

White Finish

9459-12

Black Finish

Polycarbonate splicer with cover for connection between transformer extension wire (i.e. Romex) and low voltage cable or LED Disk Connector. Maximum 25 amps.



DAMP

CONNECTION HUB

L: 3" W: 1.25" H: .4375"

98641S-15

White Finish

98641S-12

Black Finish



FUSED PLUG

L: .875" W: .75" H: .812"

For powering multiple Generation Lighting low voltage luminaires from an LX Cable System. See page 668 for detailed wiring information.

9488-15

White Finish

9488-12

Black Finish

LED DISK LIGHTING | TRANSFORMERS

STEP
3

SELECT TRANSFORMER

The transformers listed below are our recommendations for use with the LED Disk lighting system. ⁽¹⁾

Plug-In⁽²⁾



SHOWN IN (-12) BLACK FINISH

30W 12V AC ZERO LOAD

L: 3.3125" W: 1.5" H: 1.25"
Wattage: 0w – 30w Class II
Input: 120v AC | Output: 12v AC

98640S-15

White Finish

98640S-12

Black Finish

Transformer consumes 1-1.5w. Includes on/off switch and 8' output cord for connection to first LED Disk Light in a row or optional connection hub.

Hardwire⁽²⁾

The new zero-load electronic transformers provide industry leading technology in a small form factor. All of the new transformers include Radio Frequency Interference modules to eliminate interference that can occur when dimming low-voltage fixtures. These units also all feature local on/off switches and have a user replaceable secondary side of the transformer that can be swapped without an electrician or even needing to touch the primary wiring. Hardwire to power source and operate remotely or with installed switch. Secondary side features quick connection for fast install.



75W 12V ZERO-LOAD TRANSFORMER

L: 7.805" W: 1.36" H: 0.949"
Wattage: 0w-75w Class II
Input: 120v AC | Output: 12v AC
Max Run: 35 ft.

96622S-12

Black Finish



150W 12V ZERO-LOAD TRANSFORMER

L: 8.385" W: 2.53" H: 1.219"
Wattage: 0w-75w Class II
Input: 120v AC | Output: 12v AC
Max Run: 35 ft.

96624S-12

Black Finish

⁽¹⁾ Wiring LED Disks to Transformer without Output Cord: Using an LED Disk Connector Cord, cut and remove the male end. Strip your cables and wire normally to 12v output side of your transformer. Electronic transformers require electronic low-voltage dimmers to dim properly.

⁽²⁾ All LED Disk electronic transformers require pairing with an electronic low voltage (ELV) dimmer for dimming.

STEP
1

SELECT LED DISK KIT


Our LED Disk Lighting Kits offer two and three light, all-in-one packages for added convenience. Each package includes a plug-in 12v 30w zero load transformer, a LED Disk Connection Hub and all necessary mounting components. Up to six LED Disk Lights can be powered from one transformer and connection hub.



THREE LIGHT LED DISK KIT SHOWN IN BLACK



WHITE FINISH [-15]




BLACK FINISH [-12]


Item Number	98862SW(-xx)	98863SW(-xx)
Finish	White [-15], Black [-12]	
Number of Disks	Two	Three
Color Temperature	3000K	3000K
Voltage	12v AC	
Total Lumens	340	510
Total Power Consumption	8w	12w
Efficacy	43 lm/w	43 lm/w
Color Rendering Index	>85 CRI	
Rated Average Life	40,000 hours to 70%	
Dimmable ⁽¹⁾	Yes	
Certification	cETL, damp rated	
Material	Low-profile, die-cast aluminum with captive screw and 36" linking cord	
Included Accessories	12V AC 30w Plug-in Transformer, LED Disk Connection Hub	

(1) LED Disks are dimmable on magnetic and electronic low voltage systems. For magnetic systems, a standard incandescent or magnetic low voltage (MLV) dimmer can be used. For electronic, an electronic low voltage (ELV) dimmer is recommended.

Mounting Options



SURFACE MOUNT VIA CAPTIVE SCREW



RECESSED MOUNT VIA 2³/₈" DIAMETER HOLE

PRODUCTS SHOWN: LOUVRE LED BRICK LIGHTS IN ANTIQUE BRONZE FINISH





LED STEP/BRICK LIGHTING

LED STEP / LED BRICK LIGHTING



PRODUCTS SHOWN: LOUVER HORIZONTAL STEP LIGHTS
IN SATIN NICKEL FINISH

LED Step and LED Brick Lights from Generation Lighting are a perfectly balanced blend of the latest LED light guide technology with the high quality craftsmanship and beautiful design. We've taken expertise from our broad line of task, accent, and undercabinet lighting systems and applied it to a compact form factor to help you make an even bigger impact on the spaces you illuminate. Extensive use of high quality, die-cast metal and premium finishes ensure enduring aesthetic appeal while being backed by a five-year warranty.

LED STEP LIGHT

STEP 1
1 CHOOSE LED STEP LIGHTING DESIGN
p.662

STEP 2
2 CHOOSE LED STEP LIGHTING LAMPING
p.663



LED BRICK LIGHT


STEP 1
1 CHOOSE LED BRICK LIGHTING DESIGN
p.664

STEP 2
2 CHOOSE LED BRICK LIGHTING LAMPING
p.665



Optimized Performance

Each housing's LED light guide is purpose-built to push the light down towards the floor at an assertive angle for excellent coverage as close to the wall as possible while throwing the remaining light outward for soft area illumination.



Light Guide

Generation Lighting LED Brick and Step Light housing's light guide throws light in a wide pattern closer to the wall

LED STEP LIGHTING

STEP
1

CHOOSE LED STEP LIGHT DESIGN



LOUVER

A modern, miniature interpretation of a classic louvered design provides great directional light control.



TARPA

This handsome design inspired by sleek metal awnings delivers ultimate directional light control.



VITRA

A simple, yet sophisticated design maximizes light output and delivers a clean, crisp aesthetic.

STEP
2

CHOOSE LED STEP LIGHT FINISH & LAMPING




WHITE [-15]



SATIN NICKEL [-849]



ANTIQUE BRONZE [-171]



Style	LOUVER	TARPA	VITRA
120V	93401S(-XX)	93403S(-XX)	93405S(-XX)
120V Turtle Light (Amber 560 Nm)	93481S(-XX)	93483S(-XX)	93485S(-XX)
Finish	White [-15] Antique Bronze [-171] Satin Nickel [-849]	White [-15] Antique Bronze [-171] Satin Nickel [-849]	White [-15] Antique Bronze [-171] Satin Nickel [-849]
Face Plate Dimensions	L: 4.7" H: 3" D: .37"	L: 4.7" H: 3" D: .94"	L: 4.7" H: 3" D: .27"
Input Voltage	120v		
Delivered Lumens	Up to 90		
Power Consumption	3.3w		
Efficacy	36 lm/w		
Color Temperature	3000K		
Color Rendering Index	90 CRI		
Rated Average Life	50,000 hrs to 70%		
Dimmable	Down to 10% with ELV Dimmer (120v, 3000K units only)		
Listings	Suitable for indoor or outdoor installations. cETL and IP-65 Wet Listed.		
Installation	Installs in a single, 2" x 4", switch box with a minimum depth of 2"		

LED BRICK LIGHTING

STEP
1

CHOOSE LED BRICK LIGHT DESIGN



LOUVER

A modern, miniature interpretation of a classic louvered design provides great directional light control.



TARPA

This handsome design inspired by sleek metal awnings delivers ultimate directional light control.



VITRA

A simple, yet sophisticated design maximizes light output and delivers a clean, crisp aesthetic.

STEP
2

CHOOSE LED BRICK LIGHT FINISH & LAMPING




WHITE [-15]



SATIN NICKEL [-849]



ANTIQUe BRONZE [-171]



Style	LOUVER	TARPA	VITRA
120v	94401S(-XX)	94403S(-XX)	94405S(-XX)
120V Turtle light (Amber 560 Nm)	94481S(-XX)	94483S(-XX)	94485S(-XX)
Face Plate Dimensions	L: 8.5" W: 3.32" H: 0.45"	L: 8.5" W: 3.32" H: 1.02"	L: 8.5" W: 3.32" H: .385"
Finish	White [-15] Antique Bronze [-171] Satin Nickel [-849]	White [-15] Antique Bronze [-171] Satin Nickel [-849]	White [-15] Antique Bronze [-171] Satin Nickel [-849]
Input Voltage	120v AC		
Delivered Lumens	Up to 300		
Power Consumption	8.6w (9.3w for Turtle)		
Efficacy	35 lumens/watt		
Color Temperature	3000K		
Color Rendering Index	90 CRI		
Rated Average Life	50,000 hrs to 70%		
Dimmable	Down to 10% with ELV Dimmer (120v, 3000K units only)		
Listings	Suitable for indoor or outdoor installations. cETL and IP-65 Wet Listed		
Installation	Suitable for brick and poured concrete.		

TECHNICAL INFORMATION

ELECTRONIC TRANSFORMERS

Electronic transformers range in size from single output 60w (Class II), single output 150w zero-load, and single output 150w (Class I). Our transformers run quiet, are instant-on, feature fire-rated housings and dim easily with electronic low-voltage (ELV) dimmers. Generation Lighting Electronic Transformers specify whether they have a minimum load requirement — starting at 15w — or whether they are zero-load capable. Zero-load transformers have been designed for the low wattage draws of LED technology. For proper operation of an electronic transformer, the wattage load must fall within the specified range. Generation Lighting Electronic Transformers are moisture and shock resistant, featuring soft start circuitry for increased lamp life. Electronic transformers, as with many electronic components, may cause radio frequency interference (RFI). Our Electronic Transformers have built-in filters to help eliminate RFI. Should RFI be noticeable, rotate the unit to change the direction of the electronic field or replace with a magnetic transformer, which will not cause RFI.

MAGNETIC TRANSFORMERS

Generation Lighting laminated magnetic transformers are core and coil, isolated type transformers. We offer several sizes of laminated magnetic transformers ranging from 75 to 300w at 12v, and 60 to 200w at 24v in either AC or DC. Each transformer features thermal protection on the primary (120v) side. Our laminated magnetic transformers have resettable thermal circuit breakers on the low voltage side. Other features include a faraday shield, potted and encased core and coil for added safety and ease of installation. A boost tap is integrated to single-tap magnetic transformers to compensate for voltage drop. For optimum operation we recommend the load on all laminated magnetic transformers be between 50 and 100% of the rated wattage when used with xenon and halogen light sources. Magnetic transformers are zero load with LED lamp source. Not meeting minimum recommend loads can overdrive luminaires and greatly reduce lamp life. Be sure to keep insulation away from transformers. Magnetic transformers should be mounted vertically. If the transformer must be mounted horizontally, the ambient temperature must be below 120°F and the maximum load should be reduced to 80% of output.

OPERATING TEMPERATURES

Generation Lighting systems require adequate ventilation to dissipate heat generated during their operation. Care must be taken to avoid installing the system in confined areas where excessive heat may result in the transformer circuit breaker tripping or causing damage to the system and/or the area being illuminated. Surface temperatures on transformers, wiring and luminaires must not exceed 90°C (194°F).

DIMMING

When dimming a low-voltage system, it is recommended that the dimming occur on the primary side of the transformer, reducing the power coming into the transformer. The dimmer must be matched to the type of transformer that's powering the system.

- For electronic transformers use an electronic low voltage (ELV) dimmer.
- For magnetic transformers use a standard, incandescent line voltage dimmer or a magnetic low voltage (MLV) dimmer.

REMOTE MOUNTING

When a transformer needs to be mounted in a remote location, a properly sized jumper wire (the cable between the transformer and the start of the lighting run, or between two illuminated sections) must be used. The jumper wire can be Generation Lighting Cable run in additional protection (9435 track and 9439 cover or listed conduit), Romex or Type AC. Be sure to check with your local electrical inspector. The jumper wire and lighting run must be connected in an approved wiring compartment, such as 9459 (-xx) or 9481 (-xx).

POWERING SYSTEMS

We recommend all systems used with Generation Lighting Systems be powered on the line voltage (120v or primary) side of the connection for optimum performance and safety. For applications which require operating to be done on the low voltage (secondary) side of the connection, there are two factors which need to be considered:

- It is very important that the switch used is rated for the amperage created; and
- Meet minimum load on electronic transformer To calculate amperage, use the following formula:
Amperage = Wattage / Voltage

VOLTAGE DROP

Voltage drop is the difference between voltage of luminaires close to the transformer and luminaires at the end of an illuminated section.

- All lamp sources function optimally with no more than 10% voltage drop. Voltage outside of this range will affect lamp life and overall performance.
- To compensate for voltage drop, please calculate as stated below and use appropriate wire.

CALCULATING VOLTAGE DROP:

Step 1:

Amps (Watts/Voltage) x Run/Length x 2 (for AC circuit) x Resistance per Foot(1) = Voltage Drop (in Volts)

Step 2:

- For 12v systems add voltage drop to 12 to determine tap to use.
- For 24v systems add voltage drop to 24 to determine tap to use.

RESISTANCE PER FOOT CHART⁽¹⁾

Wire Size	Resistance
4	0.000249
6	0.000395
8	0.000640
10*	0.001080
12	0.001620
14	0.002525
16	0.004016
18	0.006385


*Size of 10/2 AWG Generation Lighting Cable

TECHNICAL INFORMATION

FUSED PLUG

Our 5 amperes Fused Plug turns the Generation Lighting LX Cable into a buss system, capable of powering multiple luminaire types. Tap on our LED Disks to your linear LX Cable System with ease. No other system matches the versatility and installation options of Generation Lighting Systems.


- Multiple luminaire types, one transformer
- Add Generation Lighting LED Disk to a new or existing LX Cable Lighting System
- Snaps onto Generation Lighting Cable and Track
- Insert 18/2 cord into plug and press in contacts for connection
- 5 amp limit on each Fused Plug



Item Number	9488(-xx)
Voltage	12v and 24v
Max. Wattage	60w at 12v, 120w at 24v
Certification	cETL, damp location
Material / Finish	Black [-12], White [-15] Polycarbonate with corrosion resistant contacts

FUSED PLUG WITH LED DISKS

- Wire LED Disk directly to Fused Plug or use LX Cable Extension with Wiring Compartment
- Hub connector can also be used to wire multiple disks off of Fused Plug
- Place 9488 Fused Plug onto LX Cable and Track



FUSED PLUG WITH LED DISKS

PRODUCTS SHOWN: VITRA LED STEP LIGHTS
IN ANTIQUE BRONZE FINISH



PRODUCTS SHOWN: ALTURAS NINE LIGHT CHANDELIER IN SATIN BRONZE FINISH AND TRAVERSE LED UNLIMITED SQUARE IN WHITE FINISH





RESOURCES

TRANSFORMER REFERENCE CHART

Electronic AC Transformers

Part Number	Name	AC/DC	Type	Voltage	Connection (Hardware, Plug-in)
9454-12	60w AC Class II Transformer	AC	Electronic	120v/12v	Hard-wire
9456-12	150w AC Class I Transformer	AC	Electronic	120v/12v	Hard-wire
96622S-12	75w 12v Zero-Load Transformer	AC	Electronic	120v/12v	Hard-wire
96624S-12	150w 12v Zero-Load Transformer	AC	Electronic	120v/12v	Hard-wire
96623S-12	75w 24v Zero-Load Transformer	AC	Electronic	120v/24v	Hard-wire

Magnetic AC Transformers

Part Number	Name	AC/DC	Type	Connection
94458-12	75w, 12v Magnetic Transformer	AC	Magnetic	Hard-wire
94460-12	150w, 12v Magnetic Transformer	AC	Magnetic	Hard-wire
94462-12	300w, 12v Magnetic Transformer	AC	Magnetic	Hard-wire
94461-12	250w, 24v Magnetic Transformer	AC	Magnetic	Hard-wire

Electronic DC Transformers

Part Number	Name	AC/DC	Type	Connection
98745S-12	60w 24v DC Transformer	DC	Electronic	Hard-wire
98746S-12	105w 24v DC Transformer	DC	Electronic	Hard-wire
98747S-12	150w 24v DC Transformer	DC	Electronic	Hard-wire

Magnetic DC Transformers

Part Number	Name	AC/DC	Type	Connection
98743S-12	200w 24v DC Magnetic Transformer, Wet or Dry Location	DC	Magnetic	Hard-wire

TRANSFORMER REFERENCE CHART











	Wattage	Primary Voltage (in)	Secondary Voltage (out)	Minimum Load (electronic only)	Dimensions	Listing
	60w	120v	12v	15w	L: 2.75" W: 1.5" H: 1.125"	cUL dry
	150w	120v	12v	60w	L: 6.25" W: 2.25" H: 1.67"	cUL dry
	75w	120v	12v	Zero Load	L: 7.805" W: 1.36" H: 0.949"	cETL dry
	150w	120v	12v	Zero Load	L: 8.385" W: 2.53" H: 1.219"	cETL dry
	75w	120v	24v	Zero Load	L: 7.805" W: 1.36" H: 0.949"	cETL dry

	Wattage	Primary Voltage (in)	Secondary Voltage (out)	Minimum Load (electronic only)	Dimensions	Listing
	75w	120v	12v	N/A	L: 8.75" W: 4.25" H: 3.75"	cUL Dry
	150w	120v	12v	N/A	L: 10.5" W: 4.313" H: 4.313"	cUL Dry
	300w	120v	12v	N/A	L: 10.563" W: 4.375" H: 3.875"	cUL Dry
	250w	120v	24v	N/A	L: 10.75" W: 4.5" H: 4.25"	cUL Dry

	Wattage	Primary Voltage (in)	Secondary Voltage (out)	Minimum Load (electronic only)	Dimensions	Listing
	60w	120v	24v	Zero Load	L: 9.5" W: 4.125" H: 2.125"	cETL Damp
	105w	120v	24v	Zero Load	L: 9.5" W: 4.125" H: 2.125"	cETL Damp
	150w	120v	24v	Zero Load	L: 9.5" W: 4.125" H: 2.125"	cETL Damp



	Wattage	Primary Voltage (in)	Secondary Voltage (out)	Minimum Load (electronic only)	Dimensions	Listing
	200w	120v	24v	N/A	L: 8.875" W: 4.375" H: 4"	cETL Wet

LAMP REFERENCE CHART

	Item Number	Wattage	Voltage	Light Output (Lumens)	Efficacy (LM/W)	Lamp Type	Base Type	Light Source	Color Temperature
	97500S	6.5	120V	650	100	Vintage ST19	Medium	LED	2300K
	S9188	7	120V	350	N/A	E26	Medium	LED	N/A
	97531S	3.5	120V	160	45.7	T6	Candelabra	LED	2200K
	97532S	3.5	120V	160	45.7	T6	Candelabra	LED	2700K
	97541S	4.5	120V	300	66.7	T14	Medium	LED	2200K
	97542S	4.5	120V	300	66.7	T14	Medium	LED	2700K
	97502S	9	120V	800	80	A19	Medium	LED	2700K
	LTB10C35027CB	3.5	120V	350	100	B10	Candelabra	LED	2700K
	9728	5	12V AC	23	6	T3¼	Wedge	Incandescent	2300K
	9731	3	12V AC	15	6	T3¼	Wedge	Xenon	2400K
	9732	5	12V AC	33	8	T3¼	Wedge	Xenon	2550K
	9774	18	12V AC	210	13	T5	Wedge	Xenon	2800K
	9777	12	12V AC	120	10	T5	Wedge	Incandescent	2750K
	96116S-32	.708	12V AC	59	83	T3	Festoon	LED	2700K
	96116S-33	.708	12V AC	59	83	T3	Festoon	LED	2700K
	96118S-32	.708	12V AC	60	85	T3	Festoon	LED	3000K
	96118S-33	.708	12V AC	60	85	T3	Festoon	LED	3000K
	97118-32	5	12V AC	33	8	T3	Festoon	Xenon	2550K
	97118-33	5	12V AC	33	8	T3	Festoon	Xenon	2550K
	97119-32	10	12V AC	83	10	T3	Festoon	Xenon	2650K
	97119-33	10	12V AC	83	10	T3	Festoon	Xenon	2650K

* When dimming LED light sources, derate your dimmer to 25% of its rated capacity. For example, a 600 watt dimmer should be derated to 150 watt capacity. Consult your dimmer manufacturer for more information and restrictions.

LAMP REFERENCE CHART

	Beam Spread	CRI	Rated Life (Hours)	Comparable Equivalent	Warranty	Dimmable	Certification	Dimensions	Energy Star	Location Rating
	360°	80	15,000	60W Incandescent	3-Year Ltd.	Yes*	RoHS	D: 2.375" L: 5.375"	--	Damp
	40°	--	25,000	50w Incandescent	3-Year Ltd.	No	RoHS	D: 2.5" L: 3.25"	--	Damp
	360°	90	15,000	40w Incandescent	3-Year Ltd.	Yes*	RoHS	D: .75" L: 3.25"	--	Damp encl.
	360°	90	15,000	40w Incandescent	3-Year Ltd.	Yes*	RoHS	D: .75" L: 3.25"	--	Damp encl.
	360°	90	15,000	60w Incandescent	3-Year Ltd.	Yes*	RoHS	D: 1.75" L: 4.2"	--	Damp encl.
	360°	90	15,000	60w Incandescent	3-Year Ltd.	Yes*	RoHS	D: 1.75" L: 4.2"	--	Damp encl.
	300°	90	25,000	60w Incandescent	5-Year Ltd.	Yes*	RoHS	D: 2.36" L: 4.37"	 CEC	Damp
	300°	90	25,000	40w Incandescent	3-Year Ltd.	Yes*	RoHS	D: 1.25" L: 4.25"	 CEC	Damp encl.
	--	90	9,000	--	1-Year Ltd.	Yes*	RoHS	D: .406" L: .906"	--	Damp
	--	90	19,000	--	1-Year Ltd.	Yes*	RoHS	D: .406" L: .906"	--	Damp
	--	90	8,000	--	1-Year Ltd.	Yes*	RoHS	D: .406" L: .906"	--	Damp
	--	90	10,000	--	1-Year Ltd.	Yes*	RoHS	D: .594" L: 1.406"	--	Damp
	--	90	2,000	--	1-Year Ltd.	Yes*	RoHS	D: .594" L: 1.406"	--	Damp
	--	90	50,000 to 70%	--	3-Year Ltd.	Yes*	RoHS	D: .466" L: 1.649"	--	Damp
	--	90	50,000 to 70%	--	3-Year Ltd.	Yes*	RoHS	D: .466" L: 1.649"	--	Damp
	--	90	50,000 to 70%	--	3-Year Ltd.	Yes*	RoHS	D: .466" L: 1.649"	--	Damp
	--	90	50,000 to 70%	--	3-Year Ltd.	Yes*	RoHS	D: .466" L: 1.649"	--	Damp
	--	90	16,000	--	1-Year Ltd.	Yes*	RoHS	D: .375" L: 1.687"	--	--
	--	90	16,000	--	1-Year Ltd.	Yes*	RoHS	D: .375" L: 1.687"	--	--
	--	90	12,000	--	1-Year Ltd.	Yes*	RoHS	D: .375" L: 1.687"	--	--
	--	90	12,000	--	1-Year Ltd.	Yes*	RoHS	D: .375" L: 1.687"	--	--

** An electronic low voltage (ELV) dimmer is recommended when dimming low voltage lamps. Follow the de-rating recommendations above for optimal performance.

FL Flood **NFL** Narrow Flood

CHAIN & STEMS

TO ORDER ADDITIONAL CHAIN OR STEMS:

1. Locate the row for your collection and fixture.
2. Write down the style number in the chain or stem column.
3. Replace the "xxx" with the desired finish code from Finishes Available column.

Collection	Chain	Stems	Sloped Ceiling Mounting Hardware	Finishes Available
Academy	9100-xxx	9199-xxx	9122-xxx	Chrome [-05], Brushed Nickel [-962], Heirloom Bronze [-782]
Alturas	9100-xxx	9199-xxx	9122-xxx	Brushed Nickel [-962], Satin Bronze [-848], Brushed Oil Rubbed Bronze [-778]
Arilda	-	9199-xxx	9122-xxx	Brushed Nickel [-962], Heirloom Bronze [-782]
Bannock	9100-xxx	9199-xxx	9122-xxx	Brushed Nickel [-962], Heirloom Bronze [-782]
Belton	-	9199-xxx	9122-xxx	Brushed Nickel [-962], Heirloom Bronze [-782]
Brentwood	9103-xxx	-	-	Black [-12]
Bretton (5233-xxx)	9103-xxx	-	-	Brushed Nickel [-962], Heirloom Bronze [-782]
Bretton (all others)	9100-xxx	-	-	Brushed Nickel [-962], Heirloom Bronze [-782]
Bronzeville	-	9199-xxx	9122-xxx	Brushed Nickel [-962], Satin Bronze [-848]
Calder	9103-xxx	-	-	Black [-12], Antique Bronze [-71]
Canfield (31288-15-xxx)	9116-xxx	-	-	Brushed Nickel [-962], Burnt Sienna [-710]
Canfield	9100-xxx	9199-xxx	9122-xxx	Brushed Nickel [-962], Burnt Sienna [-710]
Carondelet (3114006-xxx)	9116-xxx	-	-	Antique Brushed Nickel [-965], Burnt Sienna [-710]
Carondelet (all others)	9100-xxx	9199-xxx	9122-xxx	Antique Brushed Nickel [-965], Burnt Sienna [-710]
Carra	-	9199-xxx	9122-xxx	Weathered Zinc [-797]**
Chatauqua	-	9199-xxx	9122-xxx	Antique Bronze [-71], Stardust [-846]
Chatham	9103-xxx	-	-	Oxidized Bronze [-46], Weathered Copper [-44]
Childress	9100-xxx	-	-	Antique Bronze [-71], Black [-12]
Classico	9103-xxx	-	-	Polished Brass [-02], Black [-12]
Corbeille	9100-xxx	-	-	Stardust [-846]
Corsicana	-	9199-xxx	9122-xxx	Heirloom Bronze [-782]
Cowen	9103-xxx	9199-xxx	9122-xxx	Obsidian Mist [-802]
Crowell	9100-xxx	-	-	Antique Bronze [-71], Black [-12]
Davlin	9103-xxx	-	-	Stardust [-846]
Davi	-	9199-xxx	9122-xxx	Chrome [-05], Satin Bronze [-848]
Dawes	-	9199-xxx	9122-xxx	Brushed Nickel [-962], Burnt Sienna [-710]
Dayna	-	9199-xxx	9122-xxx	Brushed Nickel [-962], Burnt Sienna [-710]
Driscoll (3140409-xxx)	9116-xxx	-	-	Brushed Nickel [-962], Satin Bronze [-848]

**Accessories come in accent finish

Collection	Chain	Stems	Sloped Ceiling Mounting Hardware	Finishes Available
Driscoll (all others)	9100-xxx	-	-	Brushed Nickel [-962], Satin Bronze [-848]
Dunning	9103-xxx	9199-xxx	9122-xxx	Stardust [-846]
Ellis Harper	-	9199-xxx	9122-xxx	Brushed Nickel [-962], Brushed Oil Rubbed Bronze [-778]
Elmwood Park	9100-xxx	9199-xxx	9122-xxx	Brushed Nickel [-962], Heirloom Bronze [-782]
Elsa	9103-xxx	9199-xxx	9122-xxx	Heirloom Bronze [-782]
Emmons	9100-xxx	9199-xxx	9122-xxx	Brushed Nickel [-962], Heirloom Bronze [-782]
Englehorn (3113409-xxx)	9116-xxx	-	-	Chrome [-05]
Englehorn (all others)	9100-xxx	9199-xxx	9122-xxx	Chrome [-05]
Franport (3128909-xxx & 3128915-xxx)	9116-xxx	-	-	Brushed Nickel [-962], Burnt Sienna [-710]
Franport (All others)	9100-xxx	-	-	Brushed Nickel [-962], Burnt Sienna [-710]
Fredricksburg	-	9199-xxx	9122-xxx	Weathered Copper [-44], Satin Aluminum [-04]
Gaelan	9103-xxx	-	-	Black [-12], Painted Brushed Nickel [-753]
Galvyn	9103-xxx	-	-	Black [-12], Antique Bronze [-71]
Geary	9100-xxx	-	-	Burnt Sienna [-710], Heirloom Bronze [-782], Blacksmith [-839], Brushed Nickel [-962]
Gereon	9103-xxx	9199-xxx	9122-xxx	Black [-12]
Hanford (3124515-xxx & 3124509-xxx)	9116-xxx	-	-	Brushed Nickel [-962], Burnt Sienna [-710]
Hanford (all others)	9100-xxx	9199-xxx	9122-xxx	Brushed Nickel [-962], Burnt Sienna [-710]
Hermitage	9103-xxx	-	-	Antique Brushed Nickel [-965], Antique Bronze [-71]
Herrington	9103-xxx	-	-	Black [-12]
Hettinger	9100-xxx	9199-xxx	9122-xxx	Brushed Nickel [-962], Burnt Sienna [-710]
Holman	9100-xxx	9199-xxx	9122-xxx	Brushed Nickel [-962], Heirloom Bronze [-782]
Hunnington	9100-xxx	-	-	Black [-12], Weathered Pewter [-57]
Jeyne	-	9199-xxx	9122-xxx	Weathered Copper [-44], Heirloom Bronze [-782]
Jourdanton	9100-xxx	9199-xxx	9122-xxx	Brushed Nickel [-962]
Kea	-	9199-xxx	9122-xxx	Brushed Nickel [-962], Brushed Nickel [-962]
Kent	9103-xxx	-	-	Black [-12], Oxford Bronze [-746]
Kerrville	9100-xxx	9199-xxx	9122-xxx	Chrome [-05], Brushed Nickel [-962], Heirloom Bronze [-782]
Labette	9100-xxx	-	-	Black [-12], Heirloom Bronze [-782]
Lancaster	9100-xxx	-	-	Antique Bronze [-71], Antique Brushed Nickel [-965], Black [-12], Polished Brass [-02]
Lonoke	9100-xxx	-	-	Heirloom Bronze [-782], Stardust [-846]
Medford Lakes	9103-xxx	-	-	Statuary Bronze [-51]
Metcalf	9100-xxx	9199-xxx	9122-xxx	Brushed Nickel [-962], Autumn Bronze [-715]

**Accessories come in accent finish

CHAIN & STEMS

Collection	Chain	Stems	Sloped Ceiling Mounting Hardware	Finishes Available
Moffet Street	–	9199-xxx	9122-xxx	Chrome [-05]**, Brushed Nickel [-962], Satin Bronze [-848]
Montreal	9100-xxx	–	–	Antique Brushed Nickel [-965], Burnt Sienna [-710]
Morill	9103-xxx	9199-xxx	9122-xxx	Blacksmith [-839]
Nance	9100-xxx	9199-xxx	9122-xxx	Brushed Nickel [-962], Heirloom Bronze [-782]
Oglesby	9100-xxx	–	–	Stardust [-846]**
Oslo (66160-xxx)	–	9196-xxx	–	Chrome [-05], Brushed Nickel, [-962], Blacksmith [-839]
Oslo (31162-xxx)	9116-xxx	–	–	Chrome [-05], Brushed Nickel, [-962], Blacksmith [-839]
Oslo (all others)	9100-xxx	9199-xxx	9122-xxx	Chrome [-05], Brushed Nickel, [-962], Blacksmith [-839]
Parkfield (3113009-xxx)	9107-xxx	–	–	Brushed Nickel [-962], Flemish Bronze [-845]
Parkfield (all others)	9103-xxx	9199-xxx	9122-xxx	Brushed Nickel [-962], Flemish Bronze [-845]
Perryton	–	9199-xxx	9122-xxx	Heirloom Bronze [-782], Blacksmith [-839]
Perrywood	9103-xxx	–	–	Black [-12]
Pratt Street Metal	–	9199-xxx	9122-xxx	Brushed Nickel [-962], Satin Bronze [-848], Autumn Bronze [-715]
Pratt Street Prismatic	–	9199-xxx	9122-xxx	Brushed Nickel [-962], Autumn Bronze [-715]
Ravenwood Manor	9103-xxx	9199-xxx	–	Stardust [-846]
Romee	9100-xxx	–	–	Chrome [-05], Brushed Nickel [-962], Heirloom Bronze [-782]
Sauganash	9103-xxx	–	–	Antique Bronze [-71], Black [-12]
Sebring	9103-xxx	9199-xxx	–	Brushed Stainless [-98], Weathered Copper [-44]
Sevier	9100-xxx	–	–	Black [-12], Antique Bronze [-71]
Seville	9100-xxx	9199-xxx	9122-xxx	Brushed Nickel [-962], Burnt Sienna [-710]
Sfera (3110406-xxx)	9116-xxx	–	–	Autumn Bronze [-715]
Sfera (All others)	9100-xxx	9199-xxx	9122-xxx	Autumn Bronze [-715]
Socorro	9100-xxx	–	–	Chrome [-05]**, Stardust [-846]
Stirling (31952-xxx)	9116-xxx	–	–	Brushed Nickel [-962], Burnt Sienna [-710]
Stirling (all others)	9100-xxx	9199-xxx	9122-xxx	Brushed Nickel [-962], Burnt Sienna [-710]
Stone Street	–	9199-xxx	9122-xxx	Brushed Nickel [-962], Satin Bronze [-848], Burnt Sienna [-710]
Sussex	9100-xxx	9199-xxx	9122-xxx	Brushed Nickel [-962], Heirloom Bronze [-782]
Thornwood	–	9199-xxx	9122-xxx	Weathered Iron [-819] **
Towner	–	9199-xxx	9122-xxx	Brushed Nickel [-962], Satin Bronze [-848]
Traditional	9100-xxx	–	–	Brushed Nickel [-962]
Trafalgar	9103-xxx	–	–	Oxidized Bronze [-46]
Westminster	9100-xxx	–	–	Autumn Bronze [-715]
Wheaton	9100-xxx	9199-xxx	9122-xxx	Brushed Nickel [-962], Heirloom Bronze [-782]
Windgate	9100-xxx	9199-xxx	9122-xxx	Brushed Nickel [-962], Heirloom Bronze [-782]

**Accessories come in accent finish

Collection	Chain	Stems	Sloped Ceiling Mounting Hardware	Finishes Available
Winnetka (31663-xxx)	9107-xxx	-	-	Brushed Nickel [-962], Blacksmith [-839]
Winnetka (all others)	9103-xxx	9199-xxx	9122-xxx	Brushed Nickel [-962], Blacksmith [-839]
Winnetka Outdoor	9103-xxx	-	-	Forged Iron [-185]
Yorktown	9100-xxx	-	-	Forged Iron [-185], Black [-12]
Zire	9103-xxx	9199-xxx	9122-xxx	Chrome [-05], Brushed Nickel [-962], Brushed Oil Rubbed Bronze [-778]



9032-24
Grey Finish



9032-12
Black Finish

DECORATIVE WIRE EXTENDER

L: 0.812" W: 0.562" H: 0.5"
Wattage: 600w max.

9032-24 / 9032-12

Snap together splicer/wire extender for 18/2 SPT 11/2 and ground wire. Corrosion resistant contacts simply pierce the conductors for the electrical connection. Fits into a link of chain. Must be used with approved chain only.

INDEX

11018	625	31060-782	222	3114004EN3-710	183
11019	624	31060-962	220	3114004EN3-965	182
11028QC	623	31060EN3-782	222	3114006-710	181
11033AT-15	623, 624, 625	31060EN3-962	220	3114006-965	181
1109	626	31061-782	222	3114006EN3-710	181
1115	621	31061-962	220	3114006EN3-965	181
1121-14	626	31061EN3-782	222	3114503-782	156
1126-14	622	31061EN3-962	220	3114503-962	154
1128	622	31062-782	219	3114505-782	156
1128QC	622	31062-962	218	3114505-962	154
1133AT-15	622	31062EN3-782	219	3115203-05	100
1151AT-14	622, 623, 625	31062EN3-962	218	3115203-782	104
1152AT-15	620, 621	3110205-846	159	3115203-962	102
1153AT-15	620, 621	3110208-846	159	3115203EN3-05	100
1154AT-14	622, 623, 625	3110209-846	158	3115203EN3-782	104
1155AT-15	622	3110404-715	116	3115203EN3-962	102
1156AT-14	620, 621	3110404EN3-715	116	3115205-05	100
1158AT-14	624	3110406-715	114	3115205-782	104
1162AT-14	620, 621	3110406EN3-715	114	3115205-962	102
1166AT-15	620, 621	3113005-845	204	3115205EN3-05	100
1179	620	3113005-962	202	3115205EN3-782	104
14300S-15	608	3113005EN3-845	204	3115205EN3-962	102
14300S-71	608	3113005EN3-962	202	3115209-05	98
14300S-849	608	3113009-845	201	3115209-782	99
14301S-15	608	3113009-962	200	3115209-962	99
14301S-71	608	3113009EN3-845	201	3115209EN3-05	98
14301S-849	608	3113009EN3-962	200	3115209EN3-782	99
14520S-15	606	3113203-715	258	3115209EN3-962	99
14610	611	3113203-962	256	31160-05	86
14705SC-15	611	3113203EN3-715	258	31160-839	90
14706SC-15	611	3113203EN3-962	256	31160-962	88
14760SC-15	610	3113205-715	258	31160EN3-05	86
14761SC-15	610	3113205-962	256	31160EN3-839	90
14791	611	3113205EN3-715	258	31160EN3-962	88
14795	606	3113205EN3-962	256	31161-05	86
14916RD-15	600	3113209-715	255	31161-839	90
149212RD-15	380, 602, 603	3113209-962	255	31161-962	88
149212SQ-15	381, 604, 605	3113209EN3-715	255	31161EN3-05	86
14924SQ-15	381, 604, 605	3113209EN3-962	255	31161EN3-839	90
14925RD-15	380, 602, 603	3113303-846	113	31161EN3-962	88
14926SQ-15	381, 604, 605	3113303EN3-846	113	31162-05	84
14927RD-15	380, 602, 603	3113305-846	112	31162-839	85
14929RD-15	380, 602, 603	3113305EN3-846	112	31162-962	85
14929SQ-15	381, 604, 605	3113403-05	185	31162EN3-05	84
14936RD-15	601	3113403EN3-05	185	31162EN3-839	85
2530404-962	388	3113405-05	185	31162EN3-962	85
2530404EN3-962	388	3113405EN3-05	185	3116603-782	276
2537203S-962	389	3113409-05	184	3116603-962	274
2537204S-962	389	3113409EN3-05	184	3116603EN3-782	276
2637203S-962	389	3113704-778	210	3116603EN3-962	274
2637204S-962	389	3113704-962	208	3116605-782	276
3101902-872	141	3113704EN3-778	210	3116605-962	274
3101902EN-872	141	3113704EN3-962	208	3116605EN3-782	276
3101903-872	141	3113708-778	207	3116605EN3-962	274
3101903EN-872	141	3113708-962	206	3116609-782	273
3101904-872	141	3113708EN3-778	207	3116609-962	272
3101904EN-872	141	3113708EN3-962	206	3116609EN3-782	273
3101905-872	140	3114004-710	183	3116609EN3-962	272
3101905EN-872	140	3114004-965	182	3120203-710	265

3120203-962	263	3128805-710	96	3139109EN3-962	195
3120203EN3-710	265	3128805-962	94	3140403-848	76
3120203EN3-962	263	3128805EN3-710	96	3140403-962	77
3120205-710	264	3128805EN3-962	94	3140403EN3-848	76
3120205-962	262	3128809-710	96	3140403EN3-962	77
3120205EN3-710	264	3128809-962	94	3140405-848	76
3120205EN3-962	262	3128809EN3-710	96	3140405-962	77
3120209-710	261	3128809EN3-962	94	3140405EN3-848	76
3120209-962	261	3128815-710	93	3140405EN3-962	77
3120209EN3-710	261	3128815-962	93	3140409-848	74
3120209EN3-962	261	3128815EN3-710	93	3140409-962	75
3120303-782	147	3128815EN3-962	93	3140409EN3-848	74
3120305-782	146	3128903-710	217	3140409EN3-962	75
3124505-710	228	3128903-962	215	3140503-71	167
3124505-962	226	3128903EN3-710	217	3140503-846	169
3124505EN3-710	228	3128903EN3-962	215	3140503EN3-71	167
3124505EN3-962	226	3128905-710	216	3140503EN3-846	169
3124509-710	228	3128905-962	214	3140505-71	166
3124509-962	226	3128905EN3-710	216	3140505-846	168
3124509EN3-710	228	3128905EN3-962	214	3140505EN3-71	166
3124509EN3-962	226	3128909-710	216	3140505EN3-846	168
3124515-710	225	3128909-962	214	3141303-848	71
3124515-962	224	3128909EN3-710	216	3141303-962	73
3124515EN3-710	225	3128909EN3-962	214	3141303EN3-848	71
3124515EN3-962	224	3128915-710	213	3141303EN3-962	73
3124603-778	66	3128915-962	213	3141305-848	70
3124603-848	62	3128915EN3-710	213	3141305-962	72
3124603-962	64	3128915EN3-962	213	3141305EN3-848	70
3124603EN3-778	66	3137303-782	234	3141305EN3-962	72
3124603EN3-848	62	3137303-962	232	3141307-848	70
3124603EN3-962	64	3137303EN3-782	234	3141307-962	72
3124605-778	66	3137303EN3-962	232	3141307EN3-848	70
3124605-848	62	3137305-782	234	3141307EN3-962	72
3124605-962	64	3137305-962	232	31625-782	288
3124605EN3-778	66	3137305EN3-782	234	31625-962	286
3124605EN3-848	62	3137305EN3-962	232	31625EN3-782	288
3124605EN3-962	64	3137309-782	231	31625EN3-962	286
3124609-778	61	3137309-962	231	31626-782	288
3124609-848	61	3137309EN3-782	231	31626-962	286
3124609-962	61	3137309EN3-962	231	31626EN3-782	288
3124609EN3-778	61	3139003-782	246	31626EN3-962	286
3124609EN3-848	61	3139003-962	244	31627-782	285
3124609EN3-962	61	3139003EN3-782	246	31627-962	284
3124904-846	125	3139003EN3-962	244	31627EN3-782	285
3124904-872	123	3139005-782	246	31627EN3-962	284
3124904EN-846	125	3139005-962	244	31660-839	82
3124904EN-872	123	3139005EN3-782	246	31660-962	80
3124906-846	124	3139005EN3-962	244	31660EN3-839	82
3124906-872	122	3139009-782	243	31660EN3-962	80
3124906EN-846	124	3139009-962	242	31661-839	82
3124906EN-872	122	3139009EN3-782	243	31661-962	80
3125003-782	111	3139009EN3-962	242	31661EN3-839	82
3125003EN3-782	111	3139106-710	198	31661EN3-962	80
3127803-839	143	3139106-962	196	31662-839	82
3127805-839	143	3139106EN3-710	198	31662-962	80
3128803-710	96	3139106EN3-962	196	31662EN3-839	82
3128803-962	94	3139109-710	195	31662EN3-962	80
3128803EN3-710	96	3139109-962	195	31663-839	79
3128803EN3-962	94	3139109EN3-710	195	31663-962	78

INDEX

31663EN3-839	79	3220205-710	264	4111601-05	413
31663EN3-962	78	3220205-962	262	4111601-710	413
31806-782	282	3220205EN3-710	264	4111601-962	413
31806-962	280	3220205EN3-962	262	4111601EN3-05	413
31806EN3-782	282	3224906-846	121	4111601EN3-710	413
31806EN3-962	280	3224906-872	121	4111601EN3-962	413
31807-782	283	3224906EN-846	121	4113001-845	205, 409
31807-962	281	3224906EN-872	121	4113001-962	203, 409
31807EN-782	283	3225005-782	111	4113001EN3-845	205, 409
31807EN-962	281	3225005EN3-782	111	4113001EN3-962	203, 409
31808-782	282	3280405-846	139	4113201-715	259, 417
31808-962	280	3280405EN-846	139	4113201-962	257, 417
31808EN3-782	282	3280409-846	138	4113201EN3-715	259, 417
31808EN3-962	280	3280409EN-846	138	4113201EN3-962	257, 417
31809-782	282	32810-782	282	4113301-846	113, 436
31809-962	280	32810-962	280	4113301EN3-846	113, 436
31809EN-782	282	32810EN-782	282	4113401-05	187, 400
31809EN-962	280	32810EN-962	280	4113401EN3-05	187, 400
31810-782	279	3320205-710	264	4113701-778	211, 410
31810-962	278	3320205-962	262	4113701-962	209, 410
31810EN3-782	279	3320205EN-710	264	4113701EN3-778	211, 410
31810EN3-962	278	3320205EN-962	262	4113701EN3-962	209, 410
3190303-05	54	3410-962	301	4114501-782	157
3190303-778	58	3410EN-962	301	4114501-962	155
3190303-962	56	3413-962	300	4115201-05	101, 434
3190303EN-05	54	3413EN-962	300	4115201-782	105, 434
3190303EN-778	58	35939-782	270	4115201-962	103, 434
3190303EN-962	56	35939-962	268	4115201EN3-05	101, 434
3190305-05	54	35939EN3-782	270	4115201EN3-710	434
3190305-778	58	35939EN3-962	268	4115201EN3-782	105
3190305-962	56	35940-782	267	4115201EN3-962	103, 434
3190305EN-05	54	35940-962	266	41160-05	87, 398
3190305EN-778	58	35940EN3-782	267	41160-839	91, 398
3190305EN-962	56	35940EN3-962	266	41160-962	89, 398
3190309-05	52	35949-782	270	41160EN3-05	87, 398
3190309-778	53	35949-962	268	41160EN3-839	91, 398
3190309-962	53	35949EN3-782	270	41160EN3-962	89, 398
3190309EN-05	52	35949EN3-962	268	41161-05	398
3190309EN-778	53	35950-782	270	41161-839	398
3190309EN-962	53	35950-962	268	41161-962	398
3190404-715	118	35950EN3-782	270	41161EN3-05	398
3190404EN3-715	118	35950EN3-962	268	41161EN3-839	398
3190406-715	115	40010-773	429	41161EN3-962	398
3190406EN3-715	115	40010EN3-773	429	41162-05	398
31942-710	294	40011-773	429	41162-839	398
31942-962	292	40011EN3-773	429	41162-962	398
31942EN-710	294	40012-773	429	41162EN3-05	398
31942EN-962	292	40012EN3-05	429	41162EN3-839	398
31952-710	291	40124-05	428	41162EN3-962	398
31952-962	290	40124EN3-305	428	41163-05	398
31952EN-710	291	40125-05	428	41163-839	398
31952EN-962	290	40125EN3-05	428	41163-962	398
3213003-845	204	40126-05	428	41163EN3-05	398
3213003-962	202	40126EN3-05	428	41163EN3-839	398
3213003EN3-845	204	41036-999	449	41163EN3-962	398
3213003EN3-962	202	41036EN3-999	449	4116601-782	277, 419
3214505-782	153	4110401-715	117, 401	4116601-962	275, 419
3214505-962	152	4110401EN3-715	117, 401	4116601EN3-782	277, 419

4116601EN3-962	275, 419	4128901EN3-710	217, 406	4190401EN3-715	119
41180-710	426	4128901EN3-962	215, 406	4191401-715	401
41180-965	426	4131502-808	137, 446	4191401EN3-715	401
41180EN3-710	426	4131502EN-808	137, 446	41939-05	441
41180EN3-965	426	4134501-848	172, 447	41939-782	271, 441
41181-710	426	4134501-872	174, 447	41939-962	269, 441
41181-965	426	4134501-962	173, 447	41939EN3-05	441
41181EN3-710	426	4134501EN-848	172, 447	41939EN3-782	271, 441
41181EN3-965	426	4134501EN-872	174, 447	41939EN3-962	269, 441
41182-710	426	4134501EN-962	173, 447	4325-68	591
41182-965	426	4135-962	449	4325EN3-68	591
41182EN3-710	426	4135EN3-962	449	44019-962	430
41182EN3-965	426	4137301-782	235, 392	44019EN3-962	430
41183-710	426	4137301-962	233, 392	44020-962	430
41183-965	426	4137301EN3-782	235, 392	44020EN3-962	430
41183EN3-710	426	4137301EN3-962	233, 392	44021-962	430
41183EN3-965	426	4138-15	448	44021EN3-962	430
4120201-05	433	4138EN3-15	448	44060-05	425
4120201-710	265, 433	4139001-782	247, 423	44060-782	223, 425
4120201-962	263, 433	4139001-962	245, 423	44060-962	221, 425
4120201EN3-05	433	4139001EN3-782	247, 423	44060EN3-05	425
4120201EN3-710	265, 433	4139001EN3-962	245, 423	44060EN3-782	223, 425
4120201EN3-962	263, 433	4139101-05	397	44060EN3-962	221, 425
4120301-782	147, 437	4139101-710	199, 397	44061-05	425
4122991S-962	452	4139101-962	197, 397	44061-782	425
4123-15	448	4139101EN3-05	397	44061-962	425
4123001-05	407	4139101EN3-710	199, 397	44061EN3-05	425
4123001-710	407	4139101EN3-962	197, 397	44061EN3-782	425
4123001EN3-05	407	4140401-05	405	44061EN3-962	425
4123001EN3-710	407	4140401-848	76, 405	44062-05	425
4123EN3-15	448	4140401-962	77, 405	44062-782	425
4124501-710	229, 416	4140401EN3-05	405	44062-962	425
4124501-962	227, 416	4140401EN3-848	76, 405	44062EN3-05	425
4124501EN3-710	229, 416	4140401EN3-962	77, 405	44062EN3-782	425
4124501EN3-962	227, 416	4141301-848	71, 444	44062EN3-962	425
4124601-05	395	4141301-962	73, 444	44063-05	425
4124601-778	67, 395	4141301EN3-848	71, 444	44063-782	425
4124601-848	63, 395	4141301EN3-962	73, 444	44063-962	425
4124601-962	65, 395	4148-15	449	44063EN3-05	425
4124601EN3-05	395	414893S-15	449	44063EN3-782	425
4124601EN3-778	67, 395	4148EN3-15	449	44063EN3-962	425
4124601EN3-848	63, 395	4150401-05	411	4410402-715	401
4124601EN3-962	65, 395	4150401-710	411	4410402EN3-715	401
41260-710	295	4150401-962	411	4410403-715	401
41260-962	293	4150401EN3-05	411	4410403EN3-715	401
41260EN-710	295	4150401EN3-710	411	4410404-715	401
41260EN-962	293	4150401EN3-962	411	4410404EN3-715	401
4126302-872	129	41806-782	283, 422	4411602-05	413
4126302EN-872	129	41806-962	281, 422	4411602-710	413
4127801-839	145, 421	41806EN3-782	283, 422	4411602-962	413
4128501-12	445	41806EN3-962	281, 422	4411602EN3-05	413
4128601-802	445	4190301-05	55, 393	4411602EN3-710	413
4128801-710	97, 404	4190301-778	59, 393	4411602EN3-962	413
4128801-962	95, 404	4190301-962	57, 393	4411603-05	413
4128801EN3-710	97, 404	4190301EN3-05	55, 393	4411603-710	413
4128801EN3-962	95, 404	4190301EN3-778	59, 393	4411603-962	413
4128901-710	217, 406	4190301EN3-962	57, 393	4411603EN3-05	413
4128901-962	215, 406	4190401-715	119	4411603EN3-710	413

INDEX

4411603EN3-962	413	4414001EN3-965	182, 443	4420203-05	433
4411604-05	413	4414002-710	443	4420203-710	433
4411604-710	413	4414002-965	443	4420203-962	433
4411604-962	413	4414002EN3-710	443	4420203EN3-05	433
4411604EN3-05	413	4414002EN3-965	443	4420203EN3-710	433
4411604EN3-710	413	4414003-710	443	4420203EN3-962	433
4411604EN3-962	413	4414003-965	443	4420204-05	432
4413002-845	409	4414003EN3-710	443	4420204-710	432
4413002-962	409	4414003EN3-965	443	4420204-962	432
4413002EN3-845	409	4414004-710	443	4420204EN3-05	432
4413002EN3-962	409	4414004-965	443	4420204EN3-710	432
4413003-845	409	4414004EN3-710	443	4420204EN3-962	432
4413003-962	409	4414004EN3-965	443	4420205-05	432
4413003EN3-845	409	4414501-782	420	4420205-710	432
4413003EN3-962	409	4414501-962	420	4420205-962	432
4413004-845	409	4414502-782	420	4420205EN3-05	432
4413004-962	409	4414502-962	420	4420205EN3-710	432
4413004EN3-845	409	4414503-782	420	4420205EN3-962	432
4413004EN3-962	409	4414503-962	420	4420302-782	437
4413202-715	417	4414504-782	420	4420303-782	437
4413202-962	417	4414504-962	420	4420304-782	437
4413202EN3-715	417	4415202-05	434	4422991S-962	452
4413202EN3-962	417	4415202-782	434	4423002-05	407
4413203-715	417	4415202-962	434	4423002-710	407
4413203-962	417	4415202EN3-05	434	4423002EN3-05	407
4413203EN3-715	417	4415202EN3-782	434	4423002EN3-710	407
4413203EN3-962	417	4415202EN3-962	434	4423003-05	407
4413204-715	417	4415203-05	434	4423003-710	407
4413204-962	417	4415203-782	434	4423003EN3-05	407
4413204EN3-715	417	4415203-962	434	4423003EN3-710	407
4413204EN3-962	417	4415203EN3-05	434	4423004-05	407
4413302-846	436	4415203EN3-782	434	4423004-710	407
4413302EN3-846	436	4415203EN3-962	434	4423004EN3-05	407
4413303-846	436	4415204-05	434	4423004EN3-710	407
4413303EN3-846	436	4415204-782	434	4424502-710	416
4413304-846	436	4415204-962	434	4424502-962	416
4413304EN3-846	436	4415204EN3-05	434	4424502EN3-710	416
4413402-05	400	4415204EN3-782	434	4424502EN3-962	416
4413402EN3-05	400	4415204EN3-962	434	4424503-710	416
4413403-05	400	4416191S-962	451	4424503-962	416
4413403EN3-05	400	4416602-782	419	4424503EN3-710	416
4413404-05	400	4416602-962	419	4424503EN3-962	416
4413404EN3-05	400	4416602EN3-782	419	4424504-710	416
4413702-778	410	4416602EN3-962	419	4424504-962	416
4413702-962	410	4416603-782	419	4424504EN3-710	416
4413702EN3-778	410	4416603-962	419	4424504EN3-962	416
4413702EN3-962	410	4416603EN3-782	419	4424602-05	395
4413703-778	410	4416603EN3-962	419	4424602-778	395
4413703-962	410	4416604-782	419	4424602-848	395
4413703EN3-778	410	4416604-962	419	4424602-962	395
4413703EN3-962	410	4416604EN3-782	419	4424602EN3-05	395
4413704-778	410	4416604EN3-962	419	4424602EN3-778	395
4413704-962	410	4420202-05	433	4424602EN3-848	395
4413704EN3-778	410	4420202-710	433	4424602EN3-962	395
4413704EN3-962	410	4420202-962	433	4424603-05	395
4414001-710	183, 443	4420202EN3-05	433	4424603-778	395
4414001-965	182, 443	4420202EN3-710	433	4424603-848	395
4414001EN3-710	183, 443	4420202EN3-962	433	4424603-962	395

4424603EN3-05	395	4439002EN3-962	423	4450402-710	411
4424603EN3-778	395	4439003-782	423	4450402-962	411
4424603EN3-848	395	4439003-962	423	4450402EN3-05	411
4424603EN3-962	395	4439003EN3-782	423	4450402EN3-710	411
4424604-05	395	4439003EN3-962	423	4450402EN3-962	411
4424604-778	395	4439004-782	423	4450403-05	411
4424604-848	395	4439004-962	423	4450403-710	411
4424604-962	395	4439004EN3-782	423	4450403-962	411
4424604EN3-05	395	4439004EN3-962	423	4450403EN3-05	411
4424604EN3-778	395	4439103-05	397	4450403EN3-710	411
4424604EN3-848	395	4439103-710	397	4450403EN3-962	411
4424604EN3-962	395	4439103-962	397	4450404-05	411
4427802-839	421	4439103EN3-05	397	4450404-710	411
4427803-839	421	4439103EN3-710	397	4450404-962	411
4427804-839	421	4439103EN3-962	397	4450404EN3-05	411
4428802-710	404	4439104-05	397	4450404EN3-710	411
4428802-962	404	4439104-710	397	4450404EN3-962	411
4428802EN3-710	404	4439104-962	397	44625-782	289, 440
4428802EN3-962	404	4439104EN3-05	397	44625-962	287, 440
4428803-710	404	4439104EN3-710	397	44625EN3-782	289, 440
4428803-962	404	4439104EN3-962	397	44625EN3-962	287, 440
4428803EN3-710	404	4440403-05	405	44626-782	440
4428803EN3-962	404	4440403-848	405	44626-962	440
4428804-710	404	4440403-962	405	44626EN3-782	440
4428804-962	404	4440403EN3-05	405	44626EN3-962	440
4428804EN3-710	404	4440403EN3-848	405	44627-782	440
4428804EN3-962	404	4440403EN3-962	405	44627-962	440
4428902-710	406	4440404-05	405	44627EN3-782	440
4428902-962	406	4440404-848	405	44627EN3-962	440
4428902EN3-710	406	4440404-962	405	44628-782	440
4428902EN3-962	406	4440404EN3-05	405	44628-962	440
4428903-710	406	4440404EN3-848	405	44628EN3-782	440
4428903-962	406	4440404EN3-962	405	44628EN3-962	440
4428903EN3-710	406	44436-05	427	44660-839	83, 435
4428903EN3-962	406	44436-782	427	44660-962	81, 435
4428904-710	406	44436-962	427	44660EN3-839	83, 435
4428904-962	406	44436EN3-05	427	44660EN3-962	81, 435
4428904EN3-710	406	44436EN3-782	427	44661-839	435
4428904EN3-962	406	44436EN3-962	427	44661-962	435
4434691S-962	450	44437-05	427	44661EN3-839	435
4435591S-962	453	44437-782	427	44661EN3-962	435
4435793S-04	455	44437-962	427	44662-839	435
4435793S-710	455	44437EN3-05	427	44662-962	435
4437302-782	392	44437EN3-782	427	44662EN3-839	435
4437302-962	392	44437EN3-962	427	44662EN3-962	435
4437302EN3-782	392	44438-05	427	44663-839	435
4437302EN3-962	392	44438-782	427	44663-962	435
4437303-782	392	44438-962	427	44663EN3-839	435
4437303-962	392	44438EN3-05	427	44663EN3-962	435
4437303EN3-782	392	44438EN3-782	427	44806-782	422
4437303EN3-962	392	44438EN3-962	427	44806-962	422
4437304-782	392	44439-05	427	44806EN3-782	422
4437304-962	392	44439-782	427	44806EN3-962	422
4437304EN3-782	392	44439-962	427	44807-782	422
4437304EN3-962	392	44439EN3-05	427	44807-962	422
4439002-782	423	44439EN3-782	427	44807EN3-782	422
4439002-962	423	44439EN3-962	427	44807EN3-962	422
4439002EN3-782	423	4450402-05	411	44808-782	422

INDEX

44808-962	422	4491403-715	401	4702-05	457
44808EN3-782	422	4491403EN3-715	401	4702-962	457
44808EN3-962	422	4491404-715	401	4703-05	457
44850-05	439	4491404EN3-715	401	4703-962	457
44850-782	439	44940-05	441	4734691S-962	450
44850-965	439	44940-782	441	4735-05	456
44850EN3-05	439	44940-962	441	4735-98	456
44850EN3-782	439	44940EN3-05	441	4735793S-04	455
44850EN3-965	439	44940EN3-782	441	4735793S-710	455
44851-05	439	44940EN3-962	441	4737-05	456
44851-782	439	44941-05	441	4737-98	456
44851-965	439	44941-782	441	4738-05	456
44851EN3-05	439	44941-962	441	4738-98	456
44851EN3-782	439	44941EN3-05	441	4739-05	456
44851EN3-965	439	44941EN3-782	441	4739-98	456
44852-05	439	44941EN3-962	441	4740-05	456
44852-782	439	44942-05	441	4740-98	456
44852-965	439	44942-782	441	4871-05	430
44852EN3-05	439	44942-962	441	4871EN3-05	430
44852EN3-782	439	44942EN3-05	441	4872-05	430
44852EN3-965	439	44942EN3-782	441	4872EN3-05	430
44853-05	438	44942EN3-962	441	4873-05	430
44853-782	438	44952-05	399	4873EN3-05	430
44853-965	438	44952-710	399	49024LE-15	385
44853EN3-05	438	44952-962	293, 295, 399	49026LE-15	385
44853EN3-782	438	44952EN3-05	399	49119-782	449
44853EN3-965	438	44952EN3-710	399	49119-962	449
44854-05	438	44952EN3-782	293, 295	49119EN3-782	449
44854-782	438	44952EN3-962	399	49119EN3-962	449
44854-965	438	44953-05	399	49274S-15	650
44854EN3-05	438	44953-710	399	49275S-15	650
44854EN3-782	438	44953-962	399	49276S-15	650
44854EN3-965	438	44953EN3-05	399	49277S-15	650
44855-05	438	44953EN3-710	399	49278S-15	650
44855-782	438	44953EN3-962	399	4933193S-710	449
44855-965	438	44954-05	399	4933593S-962	449
44855EN3-05	438	44954-710	399	4934093S-962	449
44855EN3-782	438	44954-962	399	49374S-15	650
44855EN3-965	438	44954EN3-05	399	49375S-15	650
4490302-05	393	44954EN3-710	399	49376S-15	650
4490302-778	393	44954EN3-962	399	49377S-15	650
4490302-962	393	44955-05	399	49378S-15	650
4490302EN3-05	393	44955-710	399	4975BLE-15	652
4490302EN3-778	393	44955-962	399	4976BLE-15	652
4490302EN3-962	393	44955EN3-05	399	4977BLE-15	652
4490303-05	393	44955EN3-710	399	5115004-782	162
4490303-778	393	44955EN3-962	399	5115004-839	163
4490303-962	393	4516191S-962	451	5115004EN-782	162
4490303EN3-05	393	4522991S-962	452	5115004EN-839	163
4490303EN3-778	393	4534691S-962	450	5115008-782	161
4490303EN3-962	393	4535591S-962	453	5115008-839	161
4490304-05	393	4535793S-04	455	5115008EN-782	161
4490304-778	393	4535793S-710	455	5115008EN-839	161
4490304-962	393	4616191S-962	451	5124904-846	125
4490304EN3-05	393	4635591S-962	453	5124904-872	123
4490304EN3-778	393	4635793S-04	455	5124904EN-846	125
4490304EN3-962	393	4635793S-710	455	5124904EN-872	123
4491402-715	401	4701-05	457	5124906-846	124
4491402EN3-715	401	4701-962	457	5124906-872	122

5124906EN-846	124	5141305EN3-848	70, 359	5366-782	374
5124906EN-872	122	5141305EN3-962	72, 360	5366-962	374
5126003-710	321	51806-782	283	5366EN3-15	374
5126003-962	321	51806-962	281	5366EN3-782	374
5127803-839	144	51806EN-782	283	5366EN3-962	374
5127803EN-839	144	51806EN-962	281	5367PC-15	374
5128606-802	148	51807-782	282	5367PCEN3-15	374
5134503-848	172	51807-962	280	5576093S-15	379
5134503-872	174	51807EN-782	282	5590193S-15	374
5134503-962	173	51807EN-962	280	5639493S-15	378
5134503EN-848	172	5215004-782	162	5676093S-15	379
5134503EN-872	174	5215004-839	163	5692593S-15	378
5134503EN-962	173	5215004EN-782	162	5720593S-15	384
5134504-848	172	5215004EN-839	163	5727093S-15	383
5134504-872	174	5224503-710	228	5739493S-15	378
5134504-962	173	5224503-962	226	5792593S-15	378
5134504EN-848	172	5224503EN3-710	228	5913291S-15	387
5134504EN-872	174	5224503EN3-962	226	59132LE-15	387
5134504EN-962	173	5231-782	329	5913691S-15	387
5134508-848	170	5231-962	328	59136LE-15	387
5134508-872	171	5231EN-782	329	5920593S-15	384
5134508-962	171	5231EN-962	328	5927093S-15	383
5134508EN-848	170	5232-782	329	59270LE-15	386
5134508EN-872	171	5232-962	328	59271LE-15	386
5134508EN-962	171	5232EN-782	329	59360LE-15	382
5134903-05	325	5232EN-962	328	59360LE-790	382
5134903-782	325	5233-782	329	59361LE-15	382
5134903-962	325	5233-962	328	59361LE-790	382
5134903EN-05	325	5233EN-782	329	60029-12	507
5134903EN-782	325	5233EN-962	328	60029-746	505
5134903EN-962	325	5240603-12	323	60048-185	476
5134906-05	324	5240603-782	322	60048EN3-185	476
5134906-782	324	5240603EN-12	323	60048PEN3-12	477
5134906-962	324	5240603EN-782	322	6008-02	510
5134906EN-05	324	5240703-782	327	6008-12	511
5134906EN-782	324	5240703-846	327	60081-71	490
5134906EN-962	324	5240703EN-782	327	60081-965	490
5140503-71	167	5240703EN-846	327	60081EN-71	490
5140503-846	169	5326-15	374	60081EN-965	490
5140503EN3-71	167	5326-782	374	60131-12	555
5140503EN3-846	169	5326-962	374	6018-04	313, 360, 361
5140506-71	164	5326EN3-15	374	6018-15	313, 360, 361
5140506-846	165	5326EN3-782	374	6018-848	313, 359
5140506EN3-71	164	5326EN3-962	374	601893S-04	313, 360, 361
5140506EN3-846	165	5328-15	374	601893S-15	313, 360, 361
5140603-12	323	5328-782	374	601893S-848	313, 359
5140603-782	322	5328-962	374	6018EN3-04	313, 360, 361
5140603EN-12	323	5328EN3-15	374	6018EN3-15	313, 360, 361
5140603EN-782	322	5328EN3-782	374	6018EN3-848	313, 359
5140703-782	327	5328EN3-962	374	6020-04	313, 361
5140703-846	327	5340604-12	323	6020-15	313, 361
5140703EN-782	327	5340604-782	322	6020-848	313, 359
5140703EN-846	327	5340604EN-12	323	602093S-04	313, 361
5141303-848	71, 359	5340604EN-782	322	602093S-15	313, 361
5141303-962	73, 361	5340704-782	327	602093S-848	313, 359
5141303EN3-848	71, 359	5340704-846	327	6020EN3-04	313, 361
5141303EN3-962	73, 361	5340704EN-782	327	6020EN3-15	313, 361
5141305-848	70, 359	5340704EN-846	327	6020EN3-848	313, 359
5141305-962	72, 360	5366-15	374	6022-04	312

INDEX

6022-15	312	6113701-962	209	6139001-782	247
6022-848	312	6113701EN3-778	211	6139001-962	245
602293S-04	312	6113701EN3-962	209	6139001EN3-782	247
602293S-15	312	6114001-710	183	6139001EN3-962	245
602293S-848	312	6114001-965	182	6140401-848	76, 359
6022EN3-04	312	6114001EN3-710	183	6140401-962	77, 360, 361
6022EN3-15	312	6114001EN3-965	182	6140401EN3-848	76, 359
6022EN3-848	312	6114501-782	157	6140401EN3-962	77, 360, 361
6024-04	309	6114501-962	155	6140501-71	167
6024-15	309	6115201-05	101	6140501-846	169
6024-848	309	6115201-782	105	6140501EN3-71	167
602493S-04	309	6115201-962	103	6140501EN3-846	169
602493S-15	309	6115201EN3-05	101	6141301-848	71, 359
602493S-848	309	6115201EN3-782	105	6141301-962	73, 360, 361
6024EN3-04	309	6115201EN3-962	103	6141301EN3-848	71, 359
6024EN3-15	309	6115501-962	179	6141301EN3-962	73
6024EN3-848	309	6115501EN3-962	179	6146501-44	343
6025-12	526	61160-05	87	6146501-782	343
6039-02	515	61160-839	91	6146501EN3-44	343
6039-12	517	61160-962	89	6146501EN3-782	343
6039-71	516	61160EN3-05	87	6150-44	344
6039-965	514	61160EN3-839	91	6150-98	344
6039EN-02	515	61160EN3-962	89	615093S-44	344
6039EN-12	517	6116601-782	277	615093S-98	344
6039EN-71	516	6116601-962	275	61625-782	289
6039EN-965	514	6116601EN3-782	277	61625-962	287
60529-12	506	6116601EN3-962	275	61625EN3-782	289
60529-746	504	61180-710	354	61625EN3-962	287
60529EN3-12	506	61180-965	354	61660-839	83
60529EN3-746	504	61180EN3-710	354	61660-962	81
6059-46	495	61180EN3-965	354	61660EN3-839	83
6059EN-46	495	6120201-710	265	61660EN3-962	81
6062-44	480	6120201-962	263	61806-782	283
6062-46	482	6120201EN3-710	265	61806-962	281
6062EN-44	480	6120201EN3-962	263	61806EN3-782	283
6062EN-46	482	6124501-710	229	61806EN3-962	281
60660-185	543	6124501-962	227	6190301-05	55
60660EN3-185	543	6124501EN3-710	229	6190301-778	59
60880-51	557	6124501EN3-962	227	6190301-962	57
60880EN3-51	557	6124601-710	199	6190401-715	119
61060-782	223	6124601-778	67	6190401EN3-715	119
61060-962	221	6124601-848	63	61940-782	271
61060EN3-782	223	6124601-962	65, 197	61940-962	269
61060EN3-962	221	6124601EN3-710	199	61940EN3-782	271
6110401-715	117	6124601EN3-778	67	61940EN3-962	269
6110401EN3-715	117	6124601EN3-848	63	61952-710	295
6113001-845	205	6124601EN3-962	65, 197	61952-962	293
6113001-962	203	6125001-782	111	61952EN3-710	295
6113001EN3-845	205	6125001EN3-782	111	61952EN3-962	293
6113001EN3-962	203	6128501-12	151	62027-12	552
6113201-715	259	6128601-802	149	62027-57	550
6113201-962	257	6128801-710	97	620390	606
6113201EN3-715	259	6128801-962	95	6214203-12	475
6113201EN3-962	257	6128801EN3-710	97	6214203EN-12	475
6113301-846	113	6128801EN3-962	95	6220301-782	147, 157
6113301EN3-846	113	6137301-782	235	6224401-12	534
6113401-05	187	6137301-962	233	6224401-71	532
6113401EN3-05	187	6137301EN3-782	235	6224451-12	535
6113701-778	211	6137301EN3-962	233	6224451-71	533

6224451EN3-12	535	65086-848	332	65160-05	87
6224451EN3-71	533	65086-962	332	65160-839	91
6227801-839	144	6508693S-715	332	65160-962	89
6229301-12	463	6508693S-848	332	65160EN3-05	87
6229301-71	462	6508693S-962	332	65160EN3-839	91
6229301EN3-12	463	65086EN3-715	332	65160EN3-962	89
6229301EN3-71	462	65086EN3-848	332	6517401-710	338
6236301-12	469	65086EN3-962	332	6517401-846	338
6236301-71	467	65087-715	331	6517401-962	338
6236301EN3-12	469	65087-848	331	6517401EN3-710	338
6236301EN3-71	467	65087-962	331	6517401EN3-846	338
6238701-12	503	6508793S-715	331	6517401EN3-962	338
6238701-71	502	6508793S-848	331	6517493S-710	338
6247401-12	471	6508793S-962	331	6517493S-846	338
6247401EN3-12	471	65087EN3-715	331	6517493S-962	338
6247431-753	470	65087EN3-848	331	6519-21	355
6247431EN3-753	470	65087EN3-962	331	6519-63	355
6247701-04	339, 570	6513001-845	205	6519-98	355
6247701-44	339, 571	6513001-962	203	6519EN3-21	355
6247701EN3-04	339, 570	6513001EN3-845	205	6519EN3-63	355
6247701EN3-44	339, 571	6513001EN3-962	203	6519EN3-98	355
6247793S-04	339, 570	6513201-715	259	6525401-04	341
6247793S-44	339, 571	6513201-962	257	6525401-710	341
6247901-12	547	6513201EN3-715	259	6525401-846	341
6247901-71	545	6513201EN3-962	257	6525401EN3-04	341
6247901EN3-12	547	6514301-848	307	6525401EN3-710	341
6247901EN3-71	545	6514301-962	307	6525401EN3-846	341
6250701-12	473	6514303-848	307	65262-710	177
6250701-71	472	6514303-962	307	65262-962	176
6250701EN3-12	473	6514401-710	337	65262EN3-710	177
6250701EN3-71	472	6514401-848	337	65262EN3-962	176
6501801-04	310, 360, 361	6514401-962	337	65263-710	177
6501801-848	311, 359	6514401EN3-710	337	65263-962	176
65046-715	345	6514401EN3-848	337	6526303-872	129
65046EN-715	345	6514401EN3-962	337	6526303EN-872	129
65047-715	345	6514402-710	336	6526304-872	128
65047EN-715	345	6514402-848	336	6526304EN-872	128
65060-715	319	6514402-962	336	6526308-872	127
65060-962	319	6514402EN3-710	336	6526308EN-872	127
65060EN3-715	319	6514402EN3-848	336	65263EN3-710	177
65060EN3-962	319	6514402EN3-962	336	65263EN3-962	176
65061-715	319	6514403-710	335	65264-710	177
65061-962	319	6514403-848	335	65264-962	176
65061EN3-715	319	6514403-962	335	65264EN3-710	177
65061EN3-962	319	6514403EN3-710	335	65264EN3-962	176
65062-715	319	6514403EN3-848	335	65266-710	177
65062-962	319	6514403EN3-962	335	65266-962	176
65062EN3-715	319	6514501-782	157	65266EN3-710	177
65062EN3-962	319	6514501-962	155	65266EN3-962	176
65085-715	333	6515201-05	101	6528503-12	151
65085-848	333	6515201-782	105	6528504-12	151
65085-962	333	6515201-962	103	6528603-802	149
6508593S-715	333	6515201EN3-05	101	6528803-710	97
6508593S-848	333	6515201EN3-782	105	6528803-962	95
6508593S-962	333	6515201EN3-962	103	6528803EN3-710	97
65085EN3-715	333	6515503-962	179	6528803EN3-962	95
65085EN3-848	333	6515503EN3-962	179	6531503-808	137
65085EN3-962	333	6515504-962	179	6531503EN-808	137
65086-715	332	6515504EN3-962	179	6531504-808	137

INDEX

6531504EN-808	137	65662EN3-839	82	6613304EN3-846	113
6531506-808	137	65662EN3-962	80	6613403-05	186
6531506EN-808	137	6580506-05	304	6613403EN3-05	186
6536901-782	316	6580506-848	305	6613705-778	210
6536901-962	316	6580506EN-05	304	6613705-962	208
6537001-782	314	6580506EN-848	305	6613705EN3-778	210
6537001-962	314	65806-782	283	6613705EN3-962	208
6537303-782	235	65806-962	281	6614501-782	157
6537303-962	233	65806EN3-782	283	6614501-962	155
6537303EN3-782	235	65806EN3-962	281	6614504-782	156
65436-05	353	6590301-05	55	6614504-962	154
65436-782	353	6590301-778	59	6615008-782	162
65436-962	353	6590301-962	57	6615008-839	163
65436EN3-05	353	65940-782	271	6615008EN-782	162
65436EN3-782	353	65940-962	269	6615008EN-839	163
65436EN3-962	353	65940EN3-782	271	6615203-05	100
65437-05	353	65940EN3-962	269	6615203-782	104
65437-782	353	65941-782	270	6615203-962	102
65437-962	353	65941-962	268	6615203EN3-05	100
65437EN3-05	353	65941EN3-782	270	6615203EN3-782	104
65437EN3-782	353	65941EN3-962	268	6615203EN3-962	102
65437EN3-962	353	65942-782	271	6615504-962	178
65438-05	352	65942-962	269	6615504EN3-962	178
65438-782	352	65942EN3-782	271	66160-05	86
65438-962	352	65942EN3-962	269	66160-839	90
65438EN3-05	352	65952-710	295	66160-962	88
65438EN3-782	352	65952-962	293	66160EN3-05	86
65438EN3-962	352	65952EN3-710	295	66160EN3-839	90
65439-05	352	65952EN3-962	293	66160EN3-962	88
65439-782	352	65953-710	294	6616503-710	349
65439-962	352	65953-962	292	6616503-782	350
65439EN3-05	352	65953EN3-710	294	6616503-839	351
65439EN3-782	352	65953EN3-962	292	6616503-962	348
65439EN3-962	352	6601801-04	310, 361	6616503EN3-710	349
6551103-846	131	6601801-848	311, 359	6616503EN3-782	350
6551103EN-846	131	66060-782	223	6616503EN3-839	351
6551104-846	131	66060-962	221	6616503EN3-962	348
6551104EN-846	131	66060EN3-782	223	6616504-710	347
6551106-846	131	66060EN3-962	221	6616504-782	347
6551106EN-846	131	66061-782	222	6616504-839	347
65625-782	289	66061-962	220	6616504-962	347
65625-962	287	66061EN3-782	222	6616504EN3-710	347
65625EN3-782	289	66061EN3-962	220	6616504EN3-782	347
65625EN3-962	287	66062-782	223	6616504EN3-839	347
65626-782	288	66062-962	221	6616504EN3-962	347
65626-962	286	66062EN3-782	223	6624503-710	229
65626EN3-782	288	66062EN3-962	221	6624503-962	227
65626EN3-962	286	6610403-715	116	6624503EN3-710	229
65660-839	83	6610403EN3-715	116	6624503EN3-962	227
65660-962	81	6613003-845	204	6624603-778	66
65660EN3-839	83	6613003-962	202	6624603-848	62
65660EN3-962	81	6613003EN3-845	204	6624603-962	64
65661-839	82	6613003EN3-962	202	6624603EN3-778	66
65661-962	80	6613203-715	258	6624603EN3-848	62
65661EN3-839	82	6613203-962	256	6624603EN3-962	64
65661EN3-962	80	6613203EN3-715	258	6626308-872	128
65662-839	82	6613203EN3-962	256	6626308EN-872	128
65662-962	80	6613304-846	113	6628003-782	357

6628003-962	357	66953EN-71	294	7518-848	375
6628003EN3-782	357	66953EN-962	292	7518EN3-04	375
6628003EN3-962	357	6701801-04	310	7518EN3-15	375
6628605-802	149	6701801-848	311	7518EN3-848	375
6634506-848	172	6746501-44	342	7526304-872	129
6634506-872	174	6746501-782	342	7526304EN-872	129
6634506-962	173	6746501EN3-44	342	7527803-839	145
6634506EN-848	172	6746501EN3-782	342	7527803EN-839	145
6634506EN-872	174	6801801-04	308	7537302-782	235
6634506EN-962	173	6801801-848	308	7537302-962	233
6637304-782	234	69025-12	527	7537302EN3-782	235
6637304-962	232	69025EN3-12	527	7537302EN3-962	233
6637304EN3-782	234	69029-12	553	75434-05	364
6637304EN3-962	232	69029-57	551	75434-15	364
6639003-782	246	6902997S-12	553	75434-782	364
6639003-962	244	6902997S-57	551	75434-848	364
6639003EN3-782	246	69029EN3-12	553	75434-962	364
6639003EN3-962	244	69029EN3-57	551	7543493S-05	364
6639103-710	198	69131-12	554	7543493S-15	364
6639103-962	196	69131EN3-12	554	7543493S-782	364
6639103EN3-710	198	69191-71	490	7543493S-848	364
6639103EN3-962	196	69191EN3-71	490	7543493S-962	364
6640504-71	166	69272-44	481	75434EN3-05	364
6640504-846	168	69272-46	483	75434EN3-15	364
6640504EN3-71	166	69272EN3-44	481	75434EN3-782	364
6640504EN3-846	168	69272EN3-46	483	75434EN3-848	364
6641308-848	68	7443593S-962	379	75434EN3-962	364
6641308-962	69	7449403-15	361	75435-05	364
6641308EN3-848	68	7449403-848	359	75435-15	364
6641308EN3-962	69	7449403-962	361	75435-782	364
6646501-44	343	7449405-15	360	75435-848	364
6646501-782	343	7449405-848	359	75435-962	364
6646501EN3-44	343	7449405-962	360	7543502-962	379
6646501EN3-782	343	7501801-04	375	7543502EN3-962	379
6658-44	344	7501801-848	375	7543503-962	379
6658-98	344	7501903-872	141	7543503EN3-962	379
665893S-44	344	7501903EN-872	141	7543593S-05	364
665893S-98	344	75061-782	223	7543593S-15	364
6680403-846	139	75061-962	221	7543593S-782	364
6680403EN3-846	139	75061EN3-782	223	7543593S-848	364
66808-782	283	75061EN3-962	221	7543593S-962	364
66808-962	281	7510403-715	117	75435EN3-05	364
66808EN3-782	283	7510403EN3-715	117	75435EN3-15	364
66808EN3-962	281	7513302-846	113	75435EN3-782	364
6690305-05	54	7513702-778	211	75435EN3-848	364
6690305-778	58	7513702-962	209	75435EN3-962	364
6690305-962	56	7513702EN3-778	211	75436-05	364
6690305EN-05	54	7513702EN3-962	209	75436-15	364
6690305EN-778	58	7514002-710	183	75436-782	364
6690305EN-962	56	7514002-965	182	75436-848	364
6690403-715	118	7514002EN3-710	183	75436-962	364
6690403EN3-715	118	7514002EN3-965	182	7543693S-05	364
66952-710	294	7514503-782	147, 156	7543693S-15	364
66952-962	292	7514503-962	154	7543693S-782	364
66952EN3-710	294	7514503EN-782	147, 156	7543693S-848	364
66952EN3-962	292	7514503EN-962	154	7543693S-962	364
66953-710	294	7518-04	375	75436EN3-05	364
66953-962	292	7518-15	375	75436EN3-15	364

INDEX

75436EN3-782	364	75952EN3-962	293	7713002EN3-962	202
75436EN3-848	364	7643593S-962	379	7713202-715	258
75436EN3-962	364	7647-782	376	7713202-962	256
75444-782	364	7647-962	376	7713202EN3-715	258
7544493S-782	364	7647EN-782	376	7713202EN3-962	256
75444EN3-782	364	7647EN-962	376	7713402-05	186
75445-782	364	7648-782	376	7713402EN3-05	186
7544593S-782	364	7648-962	376	7713702-778	211
75445EN3-782	364	7648EN-782	376	7713702-962	209
75446-782	364	7648EN-962	376	7713702EN3-778	211
7544693S-782	364	7650893S-782	369	7713702EN3-962	209
75446EN3-782	364	7650893S-962	368	7714002-710	183
75467-71	591	7661-02	377	7714002-965	182
75467EN3-71	591	7661-962	377	7714002EN3-710	183
75520-845	205	7662-02	377	7714002EN3-965	182
75520-962	203	7662-962	377	7714502-782	147, 156
75520EN3-845	205	77046-715	345	7714502-962	154
75520EN3-962	203	77046EN-715	345	7715202-05	101
75661-839	83	77063-05	366	7715202-782	105
75661-962	81	77063-710	367	7715202-962	103
75661EN3-839	83	77063-782	366	7715202EN3-05	101
75661EN3-962	81	77063-839	366	7715202EN3-782	105
75662-839	83	77063-962	366	7715202EN3-962	103
75662-962	81	77063-965	366	7715502-962	179
75662EN3-839	83	77063EN3-05	366	7715502EN3-962	179
75662EN3-962	81	77063EN3-710	367	77160-05	87
7567-12	590	77063EN3-782	366	77160-839	91
7567-15	590	77063EN3-839	366	77160-962	89
7567EN3-12	590	77063EN3-962	366	77160EN3-05	87
7567EN3-15	590	77063EN3-965	366	77160EN3-839	91
7569-12	590	77064-05	366	77160EN3-962	89
7569-15	590	77064-710	367	7716393S-05	366
7569EN3-12	590	77064-782	366	7716393S-710	367
7569EN3-15	590	77064-839	366	7716393S-782	366
7580402-846	139	77064-962	366	7716393S-839	366
7580402EN3-846	139	77064-965	366	7716393S-962	366
7590403-715	119	77064EN3-05	366	7716393S-965	366
7590403EN3-715	119	77064EN3-710	367	7716493S-05	366
75940-15	365	77064EN3-782	366	7716493S-710	367
75940-782	365	77064EN3-839	366	7716493S-782	366
75940-962	365	77064EN3-962	366	7716493S-839	366
75940EN3-15	365	77064EN3-965	366	7716493S-962	366
75940EN3-782	365	77065-05	366	7716493S-965	366
75940EN3-962	365	77065-710	367	7716502-710	349
75942-15	365	77065-782	366	7716502-782	350
75942-782	365	77065-839	366	7716502-839	351
75942-962	365	77065-962	366	7716502-962	348
75942EN3-15	365	77065-965	366	7716502EN3-710	349
75942EN3-782	365	77065EN3-05	366	7716502EN3-782	350
75942EN3-962	365	77065EN3-710	367	7716502EN3-839	351
75943-15	365	77065EN3-782	366	7716502EN3-962	348
75943-782	365	77065EN3-839	366	7716503-710	349
75943-962	365	77065EN3-962	366	7716503-782	350
75943EN3-15	365	77065EN3-965	366	7716503-839	351
75943EN3-782	365	7710402-715	116	7716503-962	348
75943EN3-962	365	7710402EN3-715	116	7716503EN3-710	349
75952-710	295	7713002-845	204	7716503EN3-782	350
75952-962	293	7713002-962	202	7716503EN3-839	351
75952EN3-710	295	7713002EN3-845	204	7716503EN3-962	348

7716504-710	349	7737303-962	233	7813897S-10	583
7716504-782	350	7737303EN3-782	235	7813897S-15	583
7716504-839	351	7737303EN3-962	233	7813897S-753	583
7716504-962	348	7739002-782	247	7813901-10	583
7716504EN3-710	349	7739002-962	245	7813901-15	583
7716504EN3-782	350	7739002EN3-782	247	7813901-753	583
7716504EN3-839	351	7739002EN3-962	245	7813901EN3-10	583
7716504EN3-962	348	7739102-710	199	7813901EN3-15	583
7716593S-05	366	7739102-962	197	7813901EN3-753	583
7716593S-710	367	7739102EN3-710	199	7813997S-10	583
7716593S-782	366	7739102EN3-962	197	7813997S-15	583
7716593S-839	366	77436-05	372	7813997S-753	583
7716593S-962	366	77436-782	372	7821402-12	591
7716593S-965	366	77436-962	372	7821402-71	591
7716602-782	277	77436EN3-05	372	7824402-12	534
7716602-962	275	77436EN3-782	372	7824402-71	532
7716602EN3-782	277	77436EN3-962	372	7824452-12	535
7716602EN3-962	275	77437-05	372	7824452-71	533
7724503-710	229	77437-782	372	7824452EN3-12	535
7724503-962	227	77437-962	372	7824452EN3-71	533
7724503EN3-710	229	77437EN3-05	372	7836302-12	469
7724503EN3-962	227	77437EN3-782	372	7836302-71	467
7724602-778	67	77437EN3-962	372	7836302EN3-12	469
7724602-848	63	7750893S-782	369	7836302EN3-71	467
7724602-962	65	7750893S-962	368	7847902-12	547
7724602EN3-778	67	77625-782	289	7847902-71	545
7724602EN3-848	63	77625-962	287	7847902EN3-12	547
7724602EN3-962	65	77625EN3-782	289	7847902EN3-71	545
77262-710	177	77625EN3-962	287	78660-185	543
77262-962	176	77660-839	83	78660EN3-185	543
77262EN3-710	177	77660-962	81	78880-51	557
77262EN3-962	176	77660EN3-839	83	78880EN3-51	557
77263-710	367	77660EN3-962	81	79039-12	553
7726393S-710	367	7780402-846	139	79039-57	551
77263EN3-710	367	7780402EN3-846	139	7903997S-12	553
77264-710	367	77806-782	283	7903997S-57	551
7726493S-710	367	77806-962	281	79039EN3-12	553
77264EN3-710	367	77806EN3-782	283	79039EN3-57	551
77265-710	367	77806EN3-962	281	79131-12	554
7726593S-710	367	7790402-715	118	79131EN3-12	554
77265EN3-710	367	7790402EN3-715	118	79136-12	499, 508, 527
7727802-839	145	77950-782	271	79136EN3-12	499, 508, 527
7728002-782	357	77950-962	269	7916EN3-68	591
7728002-962	357	77950EN3-782	271	7950893S-782	369
7728002EN3-782	357	77950EN3-962	269	7950893S-962	368
7728002EN3-962	357	77952-710	294	8014-12	589
7728502-12	151	77952-962	292	8037-02	515
7728602-802	149	77952EN3-710	294	8037-12	517
7728803-710	97	77952EN3-962	292	8037-71	516
7728803-962	95	78027-12	552	8037-965	514
7728803EN3-710	97	78027-57	550	8038-02	515
7728803EN3-962	95	78131-12	555	8038-12	517
7731504-808	137	78136-12	499, 509, 526	8038-71	516
7731504EN-808	137	7813801-10	583	8038-965	514
7737302-782	235	7813801-15	583	8039-02	515
7737302-962	233	7813801-753	583	8039-12	517
7737302EN3-782	235	7813801EN3-10	583	8039-71	516
7737302EN3-962	233	7813801EN3-15	583	8039-965	514
7737303-782	235	7813801EN3-753	583	8039EN-02	515

INDEX

8039EN-12	517	8229-12	517	8269-44	540
8039EN-71	516	8229-71	516	8269-98	540
8039EN-965	514	8229-965	514	826993S-12	540
8040-02	512	8229301-12	463	826993S-44	540
8040-12	513	8229301-71	462	826993S-98	540
8040-71	513	8229301EN3-12	463	8275-32	588
8040-965	512	8229301EN3-71	462	82880-51	557
8040EN-02	512	8229EN-02	515	82880EN3-51	557
8040EN-12	513	8229EN-12	517	82973-44	481
8040EN-71	513	8229EN-71	516	82973-46	483
8040EN-965	512	8229EN-965	514	82973EN3-44	481
8067-02	515	8231-12	526	82973EN3-46	483
8067-12	517	8231EN-12	526	83046-714	584
8067-71	516	8236301-12	469	83046EN3-714	584
8067-965	514	8236301-71	467	8304701-714	584
8101-12	589	8236301EN3-12	469	8304701EN3-714	584
8101-15	589	8236301EN3-71	467	8304801-714	584
8101-71	589	8238701-12	503	8304801EN3-714	584
8102-12	589	8238701-71	502	83057-12	537
8102-15	589	8239-02	515	83057-15	536
8105-12	589	8239-12	517	83057EN3-12	537
8105-15	589	8239-71	516	83057EN3-15	536
8105-71	589	8239-965	514	8313801-10	582
8106-12	589	8239EN-02	515	8313801-15	582
8112-12	589	8239EN-12	517	8313801-753	582
8112-15	589	8239EN-71	516	8313801EN3-10	582
8114-12	589	8239EN-965	514	8313801EN3-15	582
8114-15	589	8247901-12	547	8313801EN3-753	582
8118-12	589	8247901-71	545	8313802-10	580
8120-12	589	8247901EN3-12	547	8313802-15	580
82027-12	552	8247901EN3-71	545	8313802-753	580
82027-57	550	8250701-12	473	8313802EN3-10	580
82029-12	507	8250701-71	472	8313802EN3-15	580
82029-746	505	8250701EN3-12	473	8313802EN3-753	580
82048-185	476	8250701EN3-71	472	8313897S-10	582
82048EN3-185	476	8252-68	588	8313897S-15	582
82048PEN3-12	477	82529-12	506	8313897S-753	582
82065-12	588	82529-746	504	8313901-10	581
82065EN3-12	588	82529EN3-12	506	8313901-15	581
82081-71	491	82529EN3-746	504	8313901-753	581
82081-965	491	8252EN3-68	588	8313901EN3-10	581
82081EN-71	491	8254-68	588	8313901EN3-15	581
82081EN-965	491	8254EN3-68	588	8313901EN3-753	581
8209-02	510	8255-12	588	8313902-10	579
8209-12	511	8255-15	588	8313902-15	578
82131-12	555	8257-12	521	8313902-753	579
8214203-12	475	8257-71	518	8313902EN3-10	579
8214203EN-12	475	8257-965	520	8313902EN3-15	578
82200-12	509	82570-71	519	8313902EN3-753	579
82200EN-12	509	82570EN3-71	519	8313997S-10	581
82240-780	497	8259-46	495	8313997S-15	581
82240EN3-780	497	8259EN-46	495	8313997S-753	581
8224401-12	534	8262-44	480	8335-12	537
8224401-71	532	8262-46	482	8335-15	536
8224451-12	535	8262EN-44	480	8335EN3-12	537
8224451-71	533	8262EN-46	482	8335EN3-15	536
8224451EN3-12	535	82660-185	543	8338701-12	503
8224451EN3-71	533	82660EN3-185	543	8338701-71	502
8229-02	515	8269-12	540	84029-12	507

84030-12	507	8457-965	520	8524451EN3-12	535
84031-12	507	84570-71	519	8524451EN3-71	533
84031-746	505	84570EN3-71	519	8529301-12	463
84032-12	507	8458-12	521	8529301-71	462
84032-746	505	8458-71	518	8529301EN3-12	463
84048-12	477	8458-965	520	8529301EN3-71	462
84048-185	476	84580-71	519	8536301-12	468
84048EN3-12	477	84580EN3-71	519	8536301-71	466
84048EN3-185	476	8459-46	495	8536301EN3-12	468
84048PEN3-12	477	8459EN-46	495	8536301EN3-71	466
84049-12	477	8460-46	495	8537101-839	563
84049-185	476	8460EN-46	495	8537401-12	567
84049EN3-12	477	8461-46	495	8537401-57	566
84049EN3-185	476	8461EN-46	495	8537401EN3-12	567
84049PEN3-12	477	8462-44	480	8537401EN3-57	566
84050-12	477	8462-46	482	8538501-04	573
84050-185	476	8462D-44	480	8538501-12	573
84050EN3-12	477	8462DEN3-44	480	8538501EN3-04	573
84050EN3-185	476	8463-44	478	8538501EN3-12	573
84050PEN3-12	477	8463-46	479	8538601-04	575
8413897S-10	580	8463D-44	481	8538601-12	575
8413897S-15	580	8463DEN3-44	481	8538601-71	575
8413897S-753	580	8463EN-44	478	8538601EN3-04	575
8413997S-10	579	8463EN-46	479	8538601EN3-12	575
8413997S-15	578	84670-71	519	8538601EN3-71	575
8413997S-753	579	84670EN3-71	519	8538701-12	503
8414201-12	475	8468-12	521	8538701-71	502
8414201EN3-12	475	8468-71	518	8547401-12	471
84157D-71	519	8468-965	520	8547401EN3-12	471
84157DEN3-71	519	8468EN-12	521	8547431-753	470
84158D-12	521	8468EN-71	518	8547431EN3-753	470
84158D-71	518	8468EN-965	520	8547701-04	570
84158DEN3-12	521	8507-02	510	8547701-44	571
84158DEN3-71	518	8507-12	511	8547701EN3-04	570
8438701-12	503	8509-02	510	8547701EN3-44	571
8438701-71	502	8509-12	511	8547793S-04	570
84529-12	506	8510-02	510	8547793S-44	571
84529-746	504	8510-12	511	8547901-12	546
84529EN3-12	506	8514201-12	475	8547901-71	544
84529EN3-746	504	8514201EN3-12	475	8547901DEN3-12	546
84530-12	506	8518301-04	576	8547901DEN3-71	544
84530-746	504	8518301-71	577	8547901EN3-12	546
84530EN3-12	506	8518301EN3-04	576	8547901EN3-71	544
84530EN3-746	504	8518301EN3-71	577	8550-12	585
84531-12	506	8519601-12	528	8550001-12	585
84531-746	504	8519601-44	529	8550001EN3-12	585
84531EN3-12	506	8519601EN3-12	528	8550701-12	473
84531EN3-746	504	8519601EN3-44	529	8550701-71	472
84532-12	506	85200-12	509	8550701EN3-12	473
84532-746	504	8520701-04	576	8550701EN3-71	472
84532EN3-12	506	8520701-71	577	8588-10	531
84532EN3-746	504	8520701EN3-04	576	8588-12	531
8456-12	521	8520701EN3-71	577	8588-15	530
8456-71	518	8524401-12	534	8588-155	530
8456-965	520	8524401-71	532	8592-12	523
84560-71	519	8524451-12	535	8592-15	522
84560EN3-71	519	8524451-71	533	8592-71	523
8457-12	521	8524451DEN3-12	535	8592-965	522
8457-71	518	8524451DEN3-71	533	8592001-12	523

INDEX

8592001-15	522	8714203-12	474	88025-57	550
8592001-71	523	8714203EN-12	474	88027-12	549
8592001-965	522	8718301-04	576	88027-57	548
8592001EN3-12	523	8718301-71	577	88048-185	476
8592001EN3-15	522	8718301EN3-04	576	88048EN3-185	476
8592001EN3-71	523	8718301EN3-71	577	88048PEN3-12	477
8592001EN3-965	522	8719601-12	528	88081-71	489
8607-12	594	8719601-44	529	88081-965	489
8607-15	594	8719601EN3-12	528	88082-71	488
8614203-12	474	8719601EN3-44	529	88082-965	488
8614203EN-12	474	8720-15	586	88083-71	487
8619601-12	528	8720-32	587	88083-965	486
8619601-44	529	8720701-04	576	88083EN-71	487
8619601EN3-12	528	8720701-71	577	88083EN-965	486
8619601EN3-44	529	8720701EN3-04	576	88131-12	555
8624401-12	534	8720701EN3-71	577	88132-12	555
8624401-71	532	8729301-12	463	88200-12	509
8624451-12	535	8729301-71	462	88201-12	509
8624451-71	533	8729301EN3-12	463	88201EN-12	509
8624451DEN3-12	535	8729301EN3-71	462	8822-12	526
8624451DEN3-71	533	8736301-12	468	8823-12	524
8624451EN3-12	535	8736301-71	466	8824-12	526
8624451EN3-71	533	8736301EN3-12	468	88240-780	497
8629301-12	463	8736301EN3-71	466	88240D-780	497
8629301-71	462	8737101-839	562	88240DEN3-780	497
8629301EN3-12	463	8737401-12	567	88240EN3-780	497
8629301EN3-71	462	8737401-57	566	88241-780	497
8636301-12	468	8737401EN3-12	567	88241EN3-780	497
8636301-71	466	8737401EN3-57	566	88242-780	497
8636301EN3-12	468	8738703-12	501	88242EN3-780	497
8636301EN3-71	466	8738703-71	500	88243-780	496
8637101-839	563	8738703EN-12	501	88243EN3-780	496
8637401-12	567	8738703EN-71	500	8825-12	526
8637401-57	566	8747401-12	471	8829301-12	463
8637401EN3-12	567	8747401EN3-12	471	8829301-71	462
8637401EN3-57	566	8747431-753	470	8829301EN3-12	463
8638601-04	575	8747431EN3-753	470	8829301EN3-71	462
8638601-12	575	8747901-12	546	8836302-12	465
8638601-71	575	8747901-71	544	8836302-71	465
8638601EN3-04	575	8747901DEN3-12	546	8836302EN3-12	465
8638601EN3-12	575	8747901DEN3-71	544	8836302EN3-71	465
8638601EN3-71	575	8747901EN3-12	546	8837401-12	565
8638701-12	503	8747901EN3-71	544	8837401-57	565
8638701-71	502	8750-12	585	8837401EN3-12	565
8642-12	594	8750-15	585	8837401EN3-57	565
8642-15	594	8750701-12	473	8847901-12	546
8647401-12	471	8750701-71	472	8847901-71	544
8647401EN3-12	471	8750701EN3-12	473	8847901DEN3-12	546
8647431-753	470	8750701EN3-71	472	8847901DEN3-71	544
8647431EN3-753	470	8753-15	585	8847901EN3-12	546
8647701-04	569	8753-34	585	8847901EN3-71	544
8647701-44	569	8753EN3-15	585	88660-185	543
8647701EN3-04	569	8753EN3-34	585	88660EN3-185	543
8647701EN3-44	569	8765-12	587	88661-185	543
8647793S-04	569	8765-15	586	88661EN3-185	543
8647793S-44	569	8788-10	531	88662-185	542
8650701-12	473	8788-12	531	88662EN3-185	542
8650701-71	472	8788-15	530	8869-12	541
8650701EN3-12	473	8788-155	530	8869-44	541
8650701EN3-71	472	88025-12	552	8869-98	541

886993S-12	541	89181EN3-71	489	905005-15	646
886993S-44	541	89192-71	488	905006-15	646
886993S-98	541	89192DEN3-71	488	905007-15	646
8870-12	539	89192EN3-71	488	905040-15	646
8870-44	539	89193-71	487	905045-32	647
8870-98	539	89193DEN3-71	487	90610-68	593
887093S-12	539	89193EN3-71	487	90611-68	593
887093S-44	539	89231-12	554	90612-68	593
887093S-98	539	89231EN3-12	554	90613-68	593
8871-12	538	89273-44	478	90614-68	593
8871-44	538	89273-46	479	90615-68	593
8871-98	538	89273EN3-44	478	90616-68	593
887193S-12	538	89273EN3-46	479	90617-68	593
887193S-44	538	89298-71	491	90618-68	593
887193S-98	538	89298EN3-71	491	90619-68	593
88880-51	557	8955EN3-12	585	90621-68	593
88880EN3-51	557	89805-12	537	9226-12	595
88881-51	557	89805-15	536	9226-95	595
88881EN3-51	557	89805EN3-12	537	93401S-15	663
88882-51	556	89805EN3-15	536	93401S-171	663
88882EN3-51	556	89806-12	537	93401S-849	663
88940-12	499	89806-15	536	93403S-15	663
88940-782	498	89806EN3-12	537	93403S-171	663
88941-12	499	89806EN3-15	536	93403S-849	663
88941-782	498	89807-12	537	93405S-15	663
89025-12	527	89807-15	536	93405S-171	663
89025EN3-12	527	89807EN3-12	537	93405S-849	663
89029-12	553	89807EN3-15	536	93481S-15	663
89029-57	551	89822-12	527	93481S-171	663
8902997S-12	553	89822EN3-12	527	93481S-849	663
8902997S-57	551	89823-12	525	93483S-15	663
89029EN3-12	553	89823EN3-12	525	93483S-171	663
89029EN3-57	551	89824-12	527	93483S-849	663
89031-12	549	89824EN3-12	527	93485S-15	663
89031-57	548	89825-12	527	93485S-171	663
8903197S-12	549	89825EN3-12	527	93485S-849	663
8903197S-57	548	8988EN3-10	531	9380-12	641
89031EN3-12	549	8988EN3-12	531	9380-15	641
89031EN3-57	548	8988EN3-15	530	9428-12	639
89062-44	481	8988EN3-155	530	9428-15	639
89062-46	483	89940-12	499	9435-12	640
89062EN3-44	481	89940-782	498	9435-15	640
89062EN3-46	483	89940EN3-12	499	9438-12	641
8909PEN3-12	585	89940EN3-782	498	9438-15	641
89101-12	508	89941-12	499	94401S-15	665
89101EN3-12	508	89941-782	498	94401S-171	665
89102-12	508	89941EN3-12	499	94401S-849	665
89102EN3-12	508	89941EN3-782	498	94403S-15	665
89103-12	508	900004-15	645	94403S-171	665
89103EN3-12	508	900005-15	645	94403S-849	665
89129-12	553	900006-15	645	94405S-15	665
89129-57	551	900007-15	645	94405S-171	665
89129EN3-12	553	9027-15	652	94405S-849	665
89129EN3-57	551	9032-12	679	9443-12	640
89131-12	554	9032-24	679	9443-15	640
89131EN3-12	554	9050000-15	646	94458-12	642, 672
89132-12	554	905001-15	646	94460-12	642, 672
89132EN3-12	554	905002-15	646	94461-12	616, 672
89181-71	489	905003-15	646	94462-12	642, 672
89181DEN3-71	489	905004-15	646	94481S-15	665

INDEX

94481S-171	665	96091S-15	592	F2245/3ORB	252
94481S-849	665	96091S-71	592	F2246/3BS	250
94483S-15	665	96116S-32	634, 675	F2246/3ORB	252
94483S-171	665	96116S-33	634, 675	F2248/3BS	250
94483S-849	665	96118S-32	634, 675	F2248/3ORB	252
94485S-15	665	96118S-33	634, 675	F2250/3BS	250
94485S-171	665	9647	592	F2250/3ORB	252
94485S-849	665	96622S-12	616, 643, 656, 672	F2251/4BS	250
9450	641, 647			F2251/4ORB	252
9454-12	643, 672	96623S-12	616, 672	F2252/5BS	250
9456-12	643, 672	96624S-12	616, 643, 656, 672	F2252/5ORB	252
9459-12	641, 655			F2253/6+3BS	249
9459-15	641, 655	97118-32	636, 675	F2253/6+3ORB	249
9469-12	640	97118-33	636, 675	F2254/6+6+3ORB	248
9469-15	640	97119-32	636, 675	F2343/4BS	356
9470-12	640	97119-33	636, 675	F2397/5WAL	297
9470-15	640	9728	638, 675	F2402/3BS	108
9471-12	640	9731	638, 675	F2402/3CB	109
9471-15	640	9732	638, 675	F2403/3BS	108
9481-12	641	97500S	675	F2403/3CB	109
9481-15	641	97502S	675	F2404/3BS	108
9488-12	641, 655, 668	97531S	675	F2404/3CB	109
9488-15	641, 655, 668	97532S	675	F2405/5BS	106
95220S-15	651	97541S	675	F2405/5CB	107
95221S-15	651	97542S	675	F2960/5HTBZ	240
95222S-15	651	9774	675	F2960/5SN	238
95223S-15	651	9777	675	F2961/6+3HTBZ	240
95230S-15	651	9830-12	634, 637	F2961/6+3SN	238
95231S-15	651	9830-15	634, 637	F2962/9+6+3HTBZ	237
95236S-15	651	9862	641, 647	F2962/9+6+3SN	236
95237S-15	651	98640S-12	656	F2963/3HTBZ	240
95411S-15	614	98640S-15	656	F2963/3SN	238
95411S-171	614	98641S-12	655	F2964/3HTBZ	241
95411S-849	614	98641S-15	655	F2964/3SN	239
95412S-15	614	98670-15	646	F2965/3HTBZ	240
95412S-171	614	98673-97	646	F2965/3SN	238
95412S-849	614	98700S-986	633	F2966/3HTBZ	241
95416S-15	615	98701S-986	633	F2966/3SN	239
95416S-171	615	98702S-986	633	F2997/3DWZ/WO	133
95416S-849	615	98703S-986	633	F2998/5DWZ/WO	133
95417S-15	615	98743S-12	647, 673	F2999/9DWZ/WO	132
95417S-171	615	98745S-12	647, 672	F3000/6DWZ/WO	133
95417S-849	615	98746S-12	647, 672	F3195/4IO	136
95511S-15	614	98747S-12	647, 672	F3196/3IO	136
95511S-171	614	98860SW-12	654	F3197/6IO	136
95511S-849	614	98860SW-15	654	F3205/6AF	135
95512S-15	614	98862SW-12	657	F3206/10AF	135
95512S-171	614	98862SW-15	657	F3207/18AF	135
95512S-849	614	98863SW-12	657	F3208/24AF	134
95516S-15	615	98863SW-15	657	F3310/4PN	191
95516S-171	615			F3310/4SN	193
95516S-849	615	F		F3311/6PN	190
95517S-15	615			F3311/6SN	192
95517S-171	615	F2218/3WAL	297	F3312/8PN	190
95517S-849	615	F2219/3WAL	297	F3312/8SN	192
95620	616	F2221/4WAL	297	F3313/9PN	188
9600-12	592	F2222/4WAL	298	F3313/9SN	189
9600-71	592	F2223/2WAL	298	FM261WAL	298
96091S-12	592	F2224/6WAL	296	FM269WAL	299

COLLECTION INDEX

Academy	352, 372, 427	Dayna	176	Kolmar	383
ADA Sconces	449	De-Lovely	457	Labette	322
Address Lights	592	Denhelm	411	Lancaster	512
Alban	576	Divison Street	338	LED Brick Lighting	664
Aldridge	451	Doyle	317	LED Disk Lighting	654
Alexandria	429	Drawing Room	296, 442	LED Disk	
Alturas	60, 394	Driscoll	74, 405	Lighting Kit	657
Alvy	449	Drop Lens		LED Step Lighting	662
Arilda	314	Fluorescent	382	Leo-Hanging Globe	308, 375
Bakersville	498	Dunning	112, 436	Linear Flush Mount	386
Bannock	272, 419	East Benton	450	Lonoke	326
Barn Light	564	Edla	448	Lucarne LED	612
Barrington	248, 431, 447	Ellis Harper	206, 410	LX Cable System	630
Bayfield	412	Elmwood Park	230, 392	Mahone	368
Baylor	314	Elsa	146	Marino	315
Bayside	536	Emmons	242, 423	Marinus	562
Belton	152, 420	Englehorn	184, 400	Martinsville	492
Boughton	134	Faron	449	Medford Lakes	556
Bowan	384	Franport	212, 406	Melito	528
Braunfels	454	Fredricksburg	339, 568	Metcalf	254, 417
Brentwood	524	Gaelan	470	Metropolis	449
Bretton	328, 376	Galvyn	462	Moffet Street	170, 447
Bronzeville	306	Geary	346, 366	Montreal	354, 426
Brookchester	430	Gereon	150, 445	Morill	142, 421
Calder	472	Gladstone	438	Mullberry Hill	530
Canfield	92, 404	Grandover	377	Multi-Volt	385
Cape May	496	Greenbrier	136	Multi-Port Canopies	358
Carondelet	180, 443	Hanford	224, 416	Nance	357
Carra	137, 446	Haylee	378	Nash	364
Casual Luxury	356, 372, 402	Hartsville	132, 446	Nearu	449
Center Stage	456	Hermitage	486	Neva	449
Chatauqua	164	Herrington	554	New Castle	522
Chatham	478	Hettinger	194, 396	Oglesby	140
Childress	464	Hewitt	188, 444	Oslo	84, 398
Classico	510	Holly	378	Outdoor Ceiling	
Clip Ceiling	379	Holman	278, 422	Flush Mounts	590
Colusa	453	Hudson Street	340	Outdoor Cylinders	578
Corbeille	138	Hunnington	548	Outdoor Post	
Corsicana	110	Jamestowne	518	Lanterns	588
Cowen	148, 445	Jane LED Tape	644	Outdoor Posts	589
Crittenden	572	Jennie	415	Outdoor Wall	
Crowell	544	Jeyne	342	Lanterns	584
Davi	304	Jourdanton	178	Painted Shade	
Davlin	130	Kea	316	Pendants	355
Dawes	320	Kent	504	Parkfield	200, 408
		Kerrville	98, 434	Perryton	160
				Perrywood	474

Pratt Street Metal	330
Pratt Street	
Prismatic	318
Ravel	449
Ravenwood Manor	158
Recessed Housing	618
Renville	574
Romee	324
Sagemore	428
Sauganash	532
Sebring	344, 538
Self-Contained Fluorescent	652
Sevier	500
Seville	260, 432
Sfera	114, 401
Socorro	120
Stirling	290, 399
Stepped Glass	448
Stone Street	334
Sunset Drive	106, 370, 414
Sussex	218, 424
Talida Track Lighting	389
Terrace	484
Thornwood	126
Tomkin	374
Towner	68, 444
Track Lighting	388
Traditional	300
Trafalgar	494
Traverse 4"	611
Traverse Aubrey Wall Wash	601
Traverse Insert	610
Traverse Lotus	380, 602, 604
Traverse Lyte	606
Traverse Mirage	600
Traverse Unlimited	609
Truss	449
Vandeventer	452
Vintner	236, 373, 418
Vitus	379
Vivid 120V LED	650
Waseca	407
Webster	374

Westminster	345
Westmont	430
Wheaton	284, 440
Windgate	266, 365, 441
Winnetka	78, 435, 542
Wright House	558
Wynfield	508
Yorktown	476
Zire	52, 393
Zola	315

THINGS TO NOTE

Finish representations in this catalog are shown using high resolution digital reproduction, and while every effort has been made to render colors accurately, some may vary slightly from the actual product, especially hand-painted finishes due to the nature of hand craftsmanship.

Light bulbs are not included with lighting fixture products shown in this catalog, unless otherwise noted. Generation Lighting reserves the right, at any time to make changes in the construction and design of products listed without notice. The changes may be necessary by law or the availability of supplies.

ENERGY STAR® is a registered trademark of the United States Environmental Protection Agency.



The ENERGY STAR® label is designed to clearly identify products that are energy efficient — meaning they lower energy bills and help protect the environment while providing desired features, quality and performance. www.energystar.gov

Printed in the USA.

© 2019 Generation Lighting. All rights reserved.

