



**IMPORTANT  
TURN OFF POWER AT MAIN FUSE OR  
CIRCUIT BREAKER BOX BEFORE  
STARTING INSTALLATION**

**Carefully unpack and identify all parts before assembly. Bulbs are not included.**

1. Take fixture wires and ground wire exiting above center pipe and thread through fixture plate, lock washer, and hex nut. Then while removing any slack of wires in between parts, lock all together by fastening hex nut.
2. Screw the long threaded pipe into coupler located at bottom of socket assembly. Note correct position of threaded pipe at illustration.
3. Follow enclosed **“Multiple Standard Installation Instructions”** for electrical and fixture installation onto ceiling outlet box.
4. Install bulbs (not included). See relamping label located at socket area for type and maximum allowed wattage.
5. Spread open all arms so they are evenly spaced to each other.
6. Slide glass shade through the long threaded pipe until it rests onto bottom section of arms. Secure in position by fastening with a washer and a hex nut. Do not over tighten.
7. Slip cap and fasten finial onto threaded pipe.