

# GM Lighting

Phone: (708) 478-0100, (866) 671-0811, Fax: (708) 478-2640 [www.gmlighting.net](http://www.gmlighting.net)

## GM Lighting: LEDTask™: High Output, Standard Output Flexible LED Linear Ribbon and LED LightBar Hardwire 24VDC Power Supply Installation Instructions.

### For Models; LTH-24-2,-4,-8, AND LTH-24-15

Connect the LTW / LTW-WP Series Connectors to the DC output screw terminals located on the power supply making sure that the positive (+) from the LED ribbon is connected to the positive (+) screw terminal and the negative (-) from the LED ribbon to the negative (-) screw terminal. You can now connect your AC Input to the screw terminals clearly marked on the power supply. Ground – Neutral – Line. Please turn the power supply on at this time. If the ribbon does not light up, please check that all connections are correct polarity. Use these guidelines for the LED LightBar installations.

Consult NEC guidelines and your local codes.

