

# INSTALLATION INSTRUCTIONS

For Model # P4400-084/P4400-029/P4400-467 (04/01/2013)

TO INSTALL AS A PORTABLE UNIT

**WARNING! SHUT POWER OFF AT FUSE OR CIRCUIT BREAKER.**  
**AVERTISSEMENT! COUPER LE COURANT AU NIVEAU DES FUSIBLES OU DU DISJONCTEUR.**

## WARNING

- Risk of shock, do not plug in the unit before assembly.
- Do not exceed the maximum wattage rating. (NE PAS DEPASSER LA PUISSANCE NOMINALE MAXIMALE!)



## MOUNTING THE LUMINAIRE, PLUG VERSION (Fig.1 & Fig. 2)

For hardwire version see Fig. 3 & Fig. 4

1. Carefully unpack your new fixture and lay out all the parts on a clear area. Take care not to lose any small parts necessary for installation.
2. Using the mounting plate (A) as a guide, mark the location of the dry wall anchors (D). Pre-drill the holes for the drywall anchors and insert the anchors into the wall.
3. Secure the mounting plate (A) to wall using the screws (B) (Size: M4\*L1") into dry-wall anchors (D).
4. Align the fixture body (K) over mounting plate (A) and secure with four screws (C) (Size: #5-32N\*L0.3").
5. Install the cord cover bracket (G) to the wall with screws (H) (Size: M4\*L1") and dry-wall anchors (L).
6. Fix the cord (I) into the cord cover (J), and snap the cord cover (J) into the bracket (G).

Use tool (O) to install the halogen bulbs into socket in accordance with the fixture's specifications. (DO NOT EXCEED THE MAXIMUM WATTAGE RATING!) (NE PAS DEPASSER LA PUISSANCE NOMINALE MAXIMALE!)

7.



Lighted lamp is HOT!

**WARNING:** In handling of halogen bulb, care should be taken not to touch it with your bare hands. Oil residue will shorten the life of the halogen bulb. If you accidentally come in contact, wipe thoroughly with a clean, lint-free, cotton cloth. Allow the bulb to cool for 10 minutes before changing the bulb.

**WARNING – To reduce the risk of FIRE, ELECTRIC SHOCK, EXPOSURE TO EXCESSIVE UV RADIATION, OR INJURY TO PERSONS:**

1. Turn off/unplug and allow to cool before replacing bulb.
2. Bulb gets HOT quickly! Only contact switch/plug when turning on.
3. Do not touch hot lens, guard, or enclosure.
4. Do not remain in light if skin feels warm.
5. Do not look directly at lighted lamp.
6. Keep lamp away from materials that may burn.
7. Use only with a 50 watt or smaller bulb.
8. Do not touch the bulb at any time. Use a soft cloth. Oil from skin may damage bulb.
9. Do not operate the portable luminaire with a missing or damaged guard, lamp containment barrier, or UV filter.

# INSTALLATION INSTRUCTIONS

For Model # P4400-084/P4400-029/P4400-467 (New 04/01/2013)

TO INSTALL AS A FIXTURE UNIT

**WARNING! SHUT POWER OFF AT FUSE OR CIRCUIT BREAKER.**

**AVERTISSEMENT! COUPER LE COURANT AU NIVEAU DES FUSIBLES OU DU DISJONCTEUR.**

## MOUNTING THE FIXTURE, HARDWARE VERSION

(Fig. 3 & Fig. 4)

1. Shut off power at the circuit breaker and remove old fixture from wall, including the crossbar.
2. Remove the cord and plug by disconnecting the wire nuts to the cord
3. Secure the mounting bracket (A) to the outlet box using the screws (B). The side of the mounting bracket marked "GND" must face out (Fig.3).

## CONNECTING THE WIRES (Fig. 5)

5. Connect the electrical wires as shown in Fig. 5, making sure that all wire connectors are secured. If your outlet has a ground wire (green or bare copper), connect the fixture's ground wire to it. Otherwise, connect the fixture's ground wire directly to the mounting bracket by using the green screw provided.

## FINISHING THE INSTALLATION (Fig. 4)

6. Place fixture body (K) over the mounting bracket (A) and secure with four screws (C).
7. Insert plug (M) into the hole on the bottom of the fixture body (K).
8. Install the halogen bulbs into socket in accordance with the fixture's specifications. **(DO NOT EXCEED THE MAXIMUM WATTAGE RATING!) (NE PAS DEPASSER LA PUISSANCE NOMINALE MAXIMALE!)**

Replace the bulb using the provided suction cup (O)

Your installation is now complete. Return power to the outlet box and test the fixture.

