


Thomas & Betts

SHRINK-KON® HEAT SHRINKABLE INSULATING END CAPS



MATERIAL:

Thermally stabilized, modified polyolefin, inner portion of end cap provided with factory applied sealant.
 * Voltage Rating: 600 Volts Max. * Temperature Rating: 90°C Max. * Flame retardant.

INSTALLATION INSTRUCTIONS:

1. Slide expanded heat shrinkable cap over item to be covered.
2. Shrink the cap by applying heat, using a torch (Catalog Number SIT-1) or hot air blower (heat gun TBM750F or WT1400), or equivalent heat source. Tubing starts to shrink at 250-275°F.

CAUTION: KEEP HANDS AWAY FROM TORCH OR HEAT SOURCE.

3. Shrink the cap from the closed end toward the open end. As heat is applied, move heat source around the cap to be shrunk. **THIS WILL ENSURE EVEN SHRINKAGE.**
4. When the cap has been recovered (shrunk) enough to conform to the shape of the item covered and sealant is seen to flow, discontinue heating.

CATALOG NUMBER	CABLE RANGE	MINIMUM EXPANDED INSIDE DIA (INCHES)	MAXIMUM RECOVERED INSIDE DIA (INCHES)	NOMINAL RECOVERED WALL (INCHES)	EXPANDED NOMINAL LENGTH (INCHES)
HSC8 - 4	8 to 4 AWG	0.510	0.610	0.090	2 - 1/2
HSC2 - 20	2 to 2/0 AWG	0.750	0.240	0.090	2 - 1/2
HSC30 - 250	3/0 to 250 MCM	1.100	0.350	0.120	3
HSC300 - 600	300 to 600 MCM	1.500	0.470	0.160	3 - 1/4
HSC700 - 1000	700 to 1000 MCM	2.000	0.630	0.160	3 - 1/2
HSC300*	800 - 1250 MCM	3.500	1.180	0.160	4 - 1/2
HSC500*	1500 - 2500 MCM	4.700	1.570	0.170	5 - 1/2
HSC750	600 to 1000 MCM	2.7000	0.870	0.160	4

* ONLY CSA CERTIFIED

WARRANTY: Thomas & Betts sells this product with the understanding that the user will perform all necessary tests to determine the suitability of this product for the user's intended application. Thomas & Betts warrants that this product will be free from defects in materials and workmanship for a period of two (2) years following the date of purchase. Upon prompt notification of any warranted defect, Thomas & Betts will, at its option, repair or replace the defective product or refund the purchase price. Proof of purchase is required. Misuse or unauthorized modification of the product voids all warranties.

Limitations and Exclusions: THE ABOVE WARRANTY IS THE SOLE WARRANTY CONCERNING THIS PRODUCT, AND IS IN LIEU OF ALL OTHER WARRANTIES EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE, WHICH ARE SPECIFICALLY DISCLAIMED. LIABILITY FOR BREACH OF THE ABOVE WARRANTY IS LIMITED TO COST OF REPAIR OR REPLACEMENT OF THE PRODUCT, AND UNDER NO CIRCUMSTANCES WILL THOMAS & BETTS BE LIABLE FOR ANY INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES.

Thomas & Betts Corporation
 In Canada, Thomas & Betts Ltd., Iberville, P.Q.
 Memphis, TN 38125
 website: www.tnb.com