

Please go to [www. quozel. com](http://www. quozel. com) for product cleaning tips. Go to the **Care + Maintenance** selection.

**Tools Required:** None.

**Light Source:** (1) A19 Medium Base 100W Maximum, Alternate bulb (1) 23WCFL.

**Estimated Assembly Time:** 15-20 minutes

**Preparation:** Identify and inspect all parts before beginning installation. Check package content list and diagrams below to be sure all parts are present. If any parts are missing or damaged, do not attempt to assemble, install, or operate the fixture. Contact customer service for replacement parts.

**⚠ Warnings and Cautions**

Turn off electricity at circuit breaker or main fuse box before installation. Consult a licensed electrician if in doubt.

These instructions are provided for your safety. It is very important you read them completely before installing the fixture. We strongly recommend that a licensed, professional electrician perform the installation.

Disconnect fixture from power source before replacing bulbs. Make sure bulbs are given sufficient time to cool before removal. Do not subject glass parts to any shock while in operation or shattering may result.

**INSTALLATION**

A. Thread Socket Assembly onto the top end of Base. Hand tighten until snug.

B. Insert the Harp by pressing the bottom ends of the Harp into the Harp Clips.

C. Place the Shade onto the top end of the Harp. Secure them with the Finial and hand tighten until snug.

D. This fixture uses standard bulb with standard screw base. Maximum 100 watts. Insert bulb and screw snugly into place.

Your fixture is now assembled and ready to use. Enjoy!

	Q2316T	Q2316T1		
(1)	12316TQ	BASE	1	Q2316T
2	S12316FA	SHADE	1	
1	12316T1Q	BASE	1	Q2316T1
2	S12326FA	SHADE	1	

Thank you for purchasing a Quoizel product.  
 Need assistance with parts or assembly? Call Quoizel customer service at 1-631-273-2700  
 or visit us on-line at [www. quozel. com](http://www. quozel. com)