

CONSTRUCTION PRODUCTS  
**BUCHANAN**

# SPLICE CAP

**Crimp Connectors**



**CAUTION:** Turn off power before preparing wire or installing or removing connectors.

**TO INSTALL:** Strip wires approximately 3/4" long. Insert wires thru cap and twist. Insert Buchanan C24 or P24 pres-SURE-tool with latch at "A" or alternate tools listed. Crimp and cut flush.

**INSULATE:** with Buchanan 2007 Nylon Insulator

**TO REMOVE:** Snip cap at both ends of one crimp or squeeze alternately 90° apart between crimps.

UL and CSA listed as "pressure type wire connectors" and "fixture-type splicing connectors" for 2-10 #18, 2-7 #16, 2-5 #14, 2-4 #12, 2 #10 stranded and/or solid wire. UL listed for grounding equipment. Consult factory for complete listing.

**Alternate UL Listed Tools:**

- IDEAL 30-425 - Nest back & front Jaw
- T&B WT111M - Nest C, AB & B
- T&B WT161 - Center Nest
- T&B WT100M or WT1000 - Nest for bare Term. A, B, C
- T&B WT112M
- 3M TH220 - Nest 22-6 & 22-8
- Panduit CT200 - Nest 12-10, 22-14 & 22-10



**COPPER WIRE ONLY**

**IDEAL INDUSTRIES, INC.**

Sycamore, IL 60178, U.S.A.  
800-435-0705 • www.idealindustries.com  
**ND 7390-2**  
Made in U.S.A. of US and global components.


CAT. NO. QTY.  
**2006SB/1,000**



CONSTRUCTION PRODUCTS  
**BUCHANAN**

# SPLICE CAP

**Crimp Connectors**



**CAUTION:** Turn off power before preparing wire or installing or removing connectors.

**TO INSTALL:** Strip wires approximately 3/4" long. Insert wires thru cap and twist. Insert Buchanan C24 or P24 pres-SURE-tool with latch at "A" or alternate tools listed. Crimp and cut flush.

**INSULATE:** with Buchanan 2007 Nylon Insulator

**TO REMOVE:** Snip cap at both ends of one crimp or squeeze alternately 90° apart between crimps.

UL and CSA listed as "pressure type wire connectors" and "fixture-type splicing connectors" for 2-10 #18, 2-7 #16, 2-5 #14, 2-4 #12, 2 #10 stranded and/or solid wire. UL listed for grounding equipment. Consult factory for complete listing.

**Alternate UL Listed Tools:**

- IDEAL 30-425 - Nest back & front Jaw
- T&B WT111M - Nest C, AB & B
- T&B WT161 - Center Nest
- T&B WT100M or WT1000 - Nest for bare Term. A, B, C
- T&B WT112M
- 3M TH220 - Nest 22-6 & 22-8
- Panduit CT200 - Nest 12-10, 22-14 & 22-10



**COPPER WIRE ONLY**

**IDEAL INDUSTRIES, INC.**

Sycamore, IL 60178, U.S.A.  
800-435-0705 • www.idealindustries.com  
**ND 7390-2**  
Made in U.S.A. of US and global components.

CAT. NO. QTY.  
**2006SB/1,000**

