

LED TUBE INSTALLATION GUIDE – WARNING

NOTE: This lamp can replace 28W fluorescent T5 tubes with G5 bases.

CAUTION – RISK OF FIRE. IF THE LAMP OR LUMINAIRE EXHIBITS UNDESIRABLE OPERATION (BUZZING, FLICKERING, ETC.), IMMEDIATELY TURN OFF POWER, REMOVE LAMP FROM LUMINAIRE AND CONTACT THE MANUFACTURER.

WARNING – Risk of fire or electric shock. LED Retrofit Kit installation requires knowledge of luminaire electrical systems. If not qualified, do not attempt installation. Contact a qualified electrician. Installation should be performed only by a qualified electrician in accordance with the National Electrical Code and relevant local code.

WARNING – Risk of fire or electric shock. Install this kit only in the luminaires that have the construction features and dimensions shown in the photographs and/or drawings and where the input rating of the retrofit kit does not exceed the input rating of the luminaire.

WARNING – To prevent wiring damage or abrasion, do not expose wiring to edges of sheet metal or other sharp objects.

- Disconnect power at the source before installation, inspection or removal. Do not simply switch off fixture.
- Not intended for use with emergency exit fixtures or emergency exit lights.
- THIS LAMP ONLY OPERATES ON ELECTRONIC BALLASTS. IF LAMP DOES NOT LIGHT WHEN THE LUMINAIRE IS ENERGIZED, REMOVE LAMP FROM LUMINAIRE AND CONTACT LAMP MANUFACTURER OR QUALIFIED ELECTRICIAN.
- This lamp is not compatible with all ballasts. Before replacing existing fluorescent lamps, check compatibility of LED lamps and luminaire ballast.
- Do not use if product is damaged.
- This lamp might not be compatible with all dimmers. Please visit www.greencreative.com for compatibility information.
- Do not make or alter any open holes in an enclosure of wiring or electrical components during kit installation.
- Risk of fire or electric shock. Do not open or modify. No user serviceable parts inside.
- SUITABLE FOR DAMP LOCATIONS. Suitable for use in wet locations when used in an outdoor-rated fixture. Not for use where directly exposed to the weather or water.
- Complies with Part 15 of FCC. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) This device must accept any interference received including interference that may cause undesired operation.
- No external weight or mechanical force should be applied to lamp or components.
- MIN. LAMP COMPARTMENT DIMENSIONS 48.03"(L) x 23.82"(W) x 4.72"(H).
- Intended for operation with the following ballasts:

Philips #: ICN-2S28-T

Universal #: B228PUNV-C

LED TUBE INSTALLATION GUIDE – INSTALLATION STEPS

1. Switch-off power to luminaire.
2. Remove the cover lens (if provided).
3. Carefully remove all existing fluorescent tubes from luminaire. Note: Verify that the ballast is compatible with LED T5 tubes, see the ballast compatibility list.
4. Install LED lamp (one for each fluorescent lamp removed, ensure pins are firmly seated in lampholders).
5. Switch on power to luminaire and installation is now complete.

GUIDE D'INSTALLATION – ATTENTION

NOTE: Ce kit est pour remplacement de lampes de type T5 28W avec douille G5.

MISE EN GARDE – RISQUE D'INCENDIE. SI LA LAMPE OU LE LUMINAIRE MONTRE UN FONCTIONNEMENT INAPPROPRIÉ (BOURDONNEMENT, CLIGNOTEMENT, ETC.), INTERROMPRE IMMÉDIATEMENT LE COURANT, ENLEVER LA LAMPE DU LUMINAIRE ET CONTACTER LE FABRICANT.

ATTENTION – Risque d'incendie ou de choc électrique. L'installation de ce kit LED nécessite la connaissance des systèmes électriques des luminaires. L'installation doit être faite par un électricien qualifié en accord avec les normes électriques nationales et locales en vigueur.

ATTENTION – Risque d'incendie ou de choc électrique. Installer uniquement dans des luminaires aux spécificités et dimensions similaires au dessin et/ou photos.

ATTENTION – Afin d'éviter tout dommage ou abrasion ne pas laisser de câble en contact avec les bords métalliques ou autre endroit abrasif.

- Eteindre le courant au compteur avant vérification, installation ou suppression.
- Ne convient pas aux éclairages et luminaires de sorties de secours.
- CETTE LAMPE FONCTIONNE UNIQUEMENT SUR BALLAST ÉLECTRONIQUE. SI LA LAMPE NE FONCTIONNE PAS LORSQU'ELLE EST SOUS TENSION, RETIRER LA LAMPE DU LUMINAIRE, ET CONTACTER LE FABRIQUANT OU UN ÉLECTRICIEN QUALIFIÉ.
- Ne fonctionne pas avec tous les ballasts.
- Ne pas utiliser si le luminaire est endommagé.
- Cette lampe n'est pas compatible avec tous les gradateurs. Liste de comptabilité sur www.greencreative.com.
- Ne pas faire ou modifier des trous dans les boîtes de câblage ou tout composant électrique pendant l'installation.
- Risque de choc électrique. Ne pas ouvrir. Aucune pièce ne peut être changée à l'intérieur.
- CONVIENT AUX EMBLEMES HUMIDES. Convient aux emplacements mouillés si installé dans un luminaire pour extérieur. Ne pas utiliser si directement exposé aux éléments ou à l'eau.
- Ce produit est conforme à la partie 15 des règlements de la FCC. Son utilisation est soumise à deux conditions: 1) Ce produit ne cause pas d'interférence dangereuse, et 2) Ce produit peut accepter les interférences reçues qui pourraient causer des opérations non voulues.
- Ne pas appliquer de force sur la lampe ou les composants.
- Les dimensions minimum du compartiment de la lampe doivent être de: 48.03"(L) x 23.82"(W) x 4.72"(H).
- Cette lampe est prévue pour fonctionner avec les ballasts suivants.

Philips #: ICN-2S28-T

Universal #: B228PUNV-C

GUIDE D'INSTALLATION – ETAPES D'INSTALLATION

1. Couper le courant du luminaire.
2. Enlever le diffuseur (si applicable).
3. Retirer les lampes existantes du luminaire et vérifier que le type de ballast soit bien listé ci-dessus.
4. Installer les lampes LED (une lampe LED pour chaque lampe fluorescente remplacée et bien s'assurer que les broches soient bien insérées dans les douilles).
5. Allumer le courant du luminaire, l'installation est terminée.