

Specification Grade Dead Front GFCI, Light Almond

2085LA



GFCI DEAD FRONT, 10kA SCCR, 20A
125VAC, Light Almond

features & benefits

- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. FSUL Listed (Federal Specification WC596). Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire. Two back wire holes per terminal. GFCIs with Auto-Ground assure a positive ground to metal box.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- Extra-long strap. Button colors match the device face. Dual-direction test and reset buttons. Class A rated GFCI. Supplied with matching TP26 nylon wall plate. Tri-drive screws.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: Light Almond
Type: Dead Front GFCI
Style: Decorator

Listing Agencies/Third Party Information

CSA Listing Info: No
CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPS C: 39121614
UR: No

Dimensions

Depth U S: 0.98"
Height U S: 4.2"
Width U S: 1.72"

Technical Information

Amps: 20 Amp
Volts: 125
Volts A C: 125
Grade Type: Specification

Buy American Act Compliance

Country of Origin: CHINA
Buy American Act Status: No