

FLEXIBLE AND PORTABLE CORD

Welding Cable
EPDM Jacket
90C -600 Volt



CONSTRUCTION	
Conductor	- Fully annealed stranded bare copper, class K stranding
Jacket	- Black premium-grade Ethylene Propylene Diene Monomer (EPDM) - -03 = Red jacket - -04 = Green Jacket

Applications:

- Secondary voltage resistance welding leads
- Power supply applications not exceeding 600 volts AC

Features:

- Good flexibility
- Abrasion-resistant
- Good Color retention

Standards:

- RoHS compliant

Part #	AWG	Stranding	Nom. O.D.	Lbs./M'
B20601-03	6	259/30	.380"	135
B20601-04	6	259/30	.380"	135
B20601	6	259/30	.380"	135
B20401-04	4	374/30	.400"	176
B20401	4	374/30	.400"	172
B20401-03	4	374/30	.400"	172
B20201	2	625/30	.465"	260
B20201-04	2	625/30	.465"	260
B20201-03	2	625/30	.465"	260
B20101-04	1	778/30	.500"	347
B20101	1	778/30	.495"	317
B20101-03	1	778/30	.495"	317
B21/001-03	1/0	990/30	.560"	400
B21/001-04	1/0	990/30	.565"	421
B21/001	1/0	990/30	.560"	400
B22/001	2/0	1248/30	.615"	487
B22/001-03	2/0	1248/30	.615"	487
B22/001-04	2/0	1248/30	.615"	487
B23/001-04	3/0	1586/30	.675"	636
B23/001	3/0	1586/30	.670"	605
B23/001-03	3/0	1586/30	.670"	605
B24/001-03	4/0	2054/30	.750"	827
B24/001	4/0	2054/30	.750"	827
B24/001-04	4/0	2054/30	.750"	768
B225001	250	2496/30	.830"	976
B235001	350	3432/30	.960"	1338
B250001	500	5054/30	1.20"	1995

*Fittings are available for these products.

Note: The data shown are approximate and subject to standard industry and

manufacturer tolerances.

May not be suitable for all installations per National Electric Code