

FLEXIBLE AND PORTABLE CORD

Type G
90C -2000 Volt -UL



CONSTRUCTION	
Conductor	- Fully annealed Stranded Bare copper, ropelay stranding for maximum flexibility
Insulation	- EPDM for use up to 90C
Jacket	- Heavy duty thermoset CPE

Applications:

- Mining equipment, cranes, conveyors, and mobile equipment
- excellent impact resistance
- Withstands severe environmental conditions
- resistant to heat, acids, Oil, Moisture, and most chemicals

Standards:

- ICEA 5-75-381
- MSHA Approved

COLOR CODE CHART	
Cond. #	Color
1	Black
2	White
3	Red
4	Orange

Part #	AWG	Conductors	Stranding	Ground AWG	Insulation Thickness	Nom. O.D.	Lbs./M'
B60804	8	4	133	4 # 12	.060"	1.045"	690
B60604	6	4	259	4 # 12	.060"	1.125"	880
B60404	4	4	259	4 # 10	.060"	1.225"	1160
B60204	2	4	259	4 # 9	.060"	1.435"	1720
B60104	1	4	259	4 # 8	.060"	1.595"	2200
B61/004	1/0	4	259	4 # 7	.060"	1.73"	2705
B62/004	2/0	4	259	4 # 6	.080"	1.855"	3190
B63/004	3/0	4	259	4 # 5	.080"	2.04"	4005
B64/004	4/0	4	259	4 # 4	.080"	2.145"	4560
B625004	250	4	427	4 # 3	.095"	2.77"	7143
B635004	350	4	888	4 # 2	.095"	3.10"	6567
B650004	500	4	1235	4 # 1/0	.095"	3.400"	10822

*Fittings are available for these products.

Note: The information in this specification sheet is approximate and subject to standard industry and manufacturer tolerances. Please verify specific requirements with your Omni Cable account manager.