

EILEEN COLLECTION

Eileen 2 Light Vanity Light Brushed Nickel

5097NI (Brushed Nickel)



Project Name: _____

Location: _____

Type: _____

Qty: _____

Comments: _____

Certifications/Qualifications

Location Rating	CSA UL Listed Damp
-----------------	--------------------

Dimensions

Base Backplate	10.00 X 4.50
Chain/Stem Length	0.00"
Weight	3.05 LBS
Extension	6.00"
Height from center of Wall opening (Spec Sheet)	6.75"
Height	9.25"
Width	14.25"

Mounting/Installation

Install Glass Up or Down	Yes
Interior/Exterior	Interior
Mounting Style	Wall Mount
Mounting Weight	1.75 LBS

Primary Lamping

Lamp Included	Not Included
Lamp Type	A19
Light Source	Incandescent
Max or Nominal Watt	100W
# of Bulbs/LED Modules	2
Socket Type	Medium

Product/Ordering Information

Finish	Brushed Nickel
UPC	783927194914.00

Specifications

Diffuser Description	Satin Etched Cased Opal
----------------------	-------------------------

Kichler

7711 East Pleasant Valley Road Cleveland, Ohio 44131-8010 Toll free: 866.558.5706 or kichler.com

Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.

KICHLER®

