

2 Light Flush Mount Fluorescent Ceiling Light - Br 10827NI (Brushed Nickel)

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____



Dimensions

Height	3.25"
Width	16.00"

Ordering Information

Product ID	10827NI
Finish	Brushed Nickel
Available Finishes	NI, OZ

Dimensions

Base Backplate	16.00 DIA
Weight	4.85 LBS

Specifications

Material	Steel
Glass Description	White Acrylic

Electrical

Voltage	120V
---------	------

Qualifications

Safety Rated	Damp
Title 24	Yes
Warranty	www.kichler.com/warranty

Primary Lamping

Light Source	Compact Fluorescent
Lamp Included	Included
Number of Lights/LEDs	2
Max or Nominal Watt	26W
Socket Wire	105
Socket Type	G24Q-1
Lamp Type	G24Q3
Bulb Product ID	4014

Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.