



Carlton®

Rigid Non-Metallic Conduit Fittings & Accessories T&B Catalog Number:

UPC Number: E943H
03448106205
Status: Active
Description:

Male Terminal Adapter, Size 1-1/2 Inch, Length 2.105 Inches, Outer Diameter 2.188 Inches, Material PVC, Color Gray, For use with Schedule 40 and 80 Conduit, Pack of 25

Application

All sizes of rigid non-metallic conduit fittings are compatible with ENT when using ENT cement.

Rigid non-metallic conduit fittings are recommended for use with Carlton 1-1/4 in. to 2 in. Flex-Plus Blue ENT.

For adapting non-metallic conduits to boxes, threaded fittings and metallic systems.

General

Trade Size (inches) 1 1/2
Material Non-Metallic

Dimension Information

A-Typical (inches) 1.918
B-Typical (inches) 1.894
C-Typical (inches) 1 3/16
L-Typical (inches) 2 1/16
S-Typical (inches) 3/4
Maximum Outside Diameter (inches) 2 5/32
Minimum-D (inches) 1.566

Packaging

Package in Units 25
T&B Sold in UOM Each
T&B Weight Per UOM 10 lbs. per 100

Application Support

Specifications & Applications Available on Website

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321

Email:techsupport@tnb.com