



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## NEMA Freedom Series Non-Reversing Reset Overload Relay Starter

**AN16NN0A**

**UPC:** 782113604114

**Dimensions:** 6.75 IN \* 6.63 IN \* 4.63 IN (L \* W \* H)

**Notes:** Heater Packs must be purchased separately

**Warranty:** Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Special Features:** Starter w/C306 bi-metal OLR
- **Amperage Rating:** 135A
- **Full Load Current Range:** 120V/60 Hz or 110V/50 Hz
- **Horsepower:** 40 hp at 208V, 50 hp at 240V, 100 hp at 480,600V
- **Mounting:** Horizontal
- **Number Of Poles:** Three-pole
- **Phase:** Three-phase
- **Size:** 4

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [AN16NN0 3D Model Xchange](#)
- [AN16NN0 AutoCAD 2D Footprint](#)
- [AN16NN0 AutoCAD 2D Footprint \(mm\)](#)
- [AN16NN0 2D PDF](#)
- [AN16NN0 2D Drawing Xchange](#)
- [AN16NN0 3D Inventor](#)
- [Quick Selector - NEMA Contactors](#)

**Certifications:** No Data



**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.