

FLEXIBLE AND PORTABLE CORD

Type W -MultiConductor
600 Volt to 2000 Volt
90C -UL



CONSTRUCTION	
Conductor	- Fully annealed Stranded Bare copper, ropelay stranding for maximum flexibility
Insulation	- EPDM for use to 90C
Jacket	- Thermoset CPE

Applications:

- Mining equipment, cranes, conveyors, and mobile equipment
- Excellent impact resistance
- Withstands severe environmental conditions
- Resistant to heat, acids, oil, moisture, and most chemicals

Standards:

- ICEA S-75-381/NEMA WC-58
- UL Type W
- MSHA Approved
Sunlight resistant

COLOR CODE CHART	
Cond. #	Color
1	Black
2	White
3	Green
4	Red

Part #	AWG	Conductors	Stranding	Insulation Thickness	Nom. O.D.	Lbs./M'
B50804	8	4	133	.060"	.980"	615
B50604	6	4	259	.060"	1.07"	800
B50404	4	4	259	.060"	1.21"	1040
B50204	2	4	259	.080"	1.435"	1580
B50104	1	4	259	.080"	1.595"	2045
B51/004	1/0	4	259	.080"	1.705"	2430
B52/004	2/0	4	259	.080"	1.845"	2950
B53/004	3/0	4	259	.080"	1.965"	3430
B54/004	4/0	4	259	.080"	2.145"	3885
B525004	250	4	627	.095"	2.61"	5579
B535004	350	4	855	.095"	2.915"	6602.2
B550004	500	4	1221	.095"	3.34"	9896

*Fittings are available for these products.

Note: The data shown are approximate and subject to standard industry and manufacturer tolerances.