




## RIGID-IMC FITTINGS

### MALLEABLE IRON INSULATED GROUNDING BUSHINGS

[Download  
Specification Sheet](#)  
([https://www.sepco-usa.com/wp-content/uploads/2017/03/page\\_055.pdf](https://www.sepco-usa.com/wp-content/uploads/2017/03/page_055.pdf))



[Print](#)



### 30BI40L

Trade Size	<b>5"</b>
GROUNDING LUG CAPACITY	<b>#6 - #250MCM</b>
Dim A	<b>4.80</b>
Dim B	<b>6.00</b>
Dim C	<b>1.13</b>

Unit Pack	-
Master Pack	<b>10</b>
Lbs. / 100 Pcs.	<b>165</b>
UPC	<b>28067</b>
Competitor Part Number	-

**APPLICATION**

Used with a locknut to terminate threaded rigid and IMC conduit to a box or enclosure and to provide a smooth pulling surface. Thermoplastic liner prevents damage to wire insulation. Liner rated at 150°C.

**FEATURES**

The plastic liner won't chip, crack, swell or shrink. It resists corrosion, chemicals, and temperature extremes.

Set-screw provided with each fitting locks bushing in any desired position.

UL Listed for use with Copper or Aluminum Grounding Conductors.

**STANDARD****MATERIALS**

Malleable Iron/Open side tin plated aluminum lug.

**STANDARD****FINISH**

Zinc plated  
Optional Lug:  
Available with copper lug; use

suffix C instead of

L. Example

20BI4C.

## **UL LISTED**

E93683



## **OPTIONAL**

### **FINISH**

For additional

corrosion

protection, specify

Hot Dipped

Galvanized. Add

suffix 'G' to

Malleable Iron

catalog number.

Example 20BI4LG.

For

more information,

see page 14.

---