

## Rigid Non-Metallic Conduit Bodies & Covers

### T&B Catalog Number:



**UPC Number:** E986J  
**Status:** 03448106546  
**Description:** Active

Type LB Conduit Body, Volume 63 Cubic Inches, Size 2 Inches, Length 8-13/32 Inches, Width 3-5/32 Inches, Material PVC, Color Gray, For use with Schedule 40 and 80 Conduit

#### Features

Textured lids  
 Foam-in-place gasket

#### Application

For use with Rigid Conduit

#### General

Trade Size (inches) 2  
 Material Non-Metallic  
 Volume (cu.in.) 63  
 Conduit Body Shape LB

#### Dimension Information

C (inches) 1 5/32  
 H (inches) 2 9/16  
 L1 (inches) 9 31/32  
 L2 (inches) 8 13/32  
 L3 (inches) 7 1/4  
 Q (inches) 3 5/32  
 W (inches) 3 15/32

#### Packaging

Package in Units 10  
 T&B Sold in UOM Each  
 T&B Weight Per UOM 1.43 lbs. Each

#### Application Support

T&B Sales Drawings wsd-ac05071  
 Rigid Non-metallic Conduit Bodies Available on Website  
 Specifications & Applications Available on Website

#### Certifications



File Nbr:  
 E11461

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com

