

FEISS

EST. 1955

F2771/3BS: 3 - Light Pendant



Dimensions:

Diameter: 18" **Wire:** 96" (color/Clear Silver)
Height: 18 1/16" **Connection:** Mounted To Box
Weight: 7.59 lbs.

Bulbs:

3 - Medium 100w Max. 120v - Not included

Features:

- CFL Convertible. For commercial quotes, call 847.410.4602
-

Material List:

1 Body - Steel - Brushed Steel
 4 12" Stem - Steel - Brushed Steel
 1 6" Stem - Steel - Brushed Steel

Safety Listing:

Safety Listed for Dry Locations / IC

Instruction Sheets:

English (F2771)

Collection: Kincaid

UPC #: 014817483215

Finish: Brushed Steel (BS)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Hardback w/ Fabric	Off White Linen	1		18		7			18		

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			3/4	5 3/8		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	F2771/3BS	1	014817483215	20	20	9.5	2.199	10.5	150	Yes

Feiss reserves the right to revise the design of components of any product due to parts availability or change in safety listing standards without assuming any obligation or liability to modify any products previously manufactured and without notice. This literature depicts a product design that is the sole and exclusive property of Feiss. In compliance with U.S copyright and patent requirements, notification is hereby presented in this form that this literature, or the product it depicts, is not to be copied, altered or used in any manner without the express written consent of, or contrary to the best interests of Feiss 1/2 A Generation Brands Company.

NJ Pallet		34		48	40	75	83.333	357		No
NV Pallet		34		48	40	75	83.333	357		No