



# Carlon®

## Rigid Non-Metallic Conduit Bodies & Covers T&B Catalog Number:

**UPC Number:** E986N  
**Status:** 03448106551  
**Description:** Active

Type LB Conduit Body, Volume 390 Cubic Inches, Size 4 Inches, Length 15-7/8 Inches, Width 5-11/32 Inches, Material PVC, Color Gray, For use with Schedule 40 and 80 Conduit

### Features

Textured lids  
 Foam-in-place gasket

### Application

For use with Rigid Conduit

### General

Trade Size (inches) 4  
 Material Non-Metallic  
 Volume (cu.in.) 390  
 Conduit Body Shape LB

### Dimension Information


C (inches) 1 25/32  
 H (inches) 4 7/16  
 L1 (inches) 17 23/32  
 L2 (inches) 15 7/8  
 L3 (inches) 14 17/64  
 Q (inches) 5 11/32  
 W (inches) 5 21/32

### Packaging

T&B Order Multiple 4  
 Package in Units 4  
 T&B Sold in UOM Each  
 T&B Weight Per UOM 5.09 lbs. Each

### Application Support

Rigid Non-metallic Conduit Bodies Available on Website  
 Specifications & Applications Available on Website



**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com