



Catalog No. TC35365

Description: 400A 3P DBL THR N1 600V NONFUSE

UPC No 783164001808

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Double Throw

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Not UL listed.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- 60/75°C conductor rating.
- Full cover interlocks.

Descriptors

Category	Double Throw
Notes	Not suitable for use as service equipment. Solid neutral not available.
GO Schedule	SB

Specifications

Voltage	600 AC
Amperage	400 A
Poles	3
Wires	3
Fusing	No Fuse
Enclosure	NEMA 1 (Indoor)
Options	None
Wire Range (Cu/Al)	(2) 1/0-250 (Cu) or 2-600 (Cu)
GSA Compliance	Yes

Classifications

CSA Certified	No
UL Listed	No

Dimensions

Height	34.3 in
Depth	10.3 in
Width	20.4 in
Weight	89.0 lb

Publications

Title	Publication No.	Publication Type
Double-Throw Safety Switch, NEMA 3R 2 pages, 30-400 Ampere Double-Throw Safety Switch	DEH-44154	Installation and Instruction
600A - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH122	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.