

## Rigid Non-Metallic Conduit Bodies & Covers

### T&B Catalog Number:

E985H

### UPC Number:

03448106585

### Status:

Active

### Description:

Type LR Conduit Body, Volume 32 Cubic Inches, Size 1-1/2 Inch, Length 7-31/32 Inches, Width 2-3/4 Inches, Material PVC, Color Gray, For use with Schedule 40 and 80 Conduit

### Features

Textured lids

Foam-in-place gasket

### Application

For use with Rigid Conduit

### General

Trade Size (inches) 1-1/2

Material Non-Metallic

Volume (cu.in.) 32

Conduit Body Shape LR

### Dimension Information

C (inches) 1 3/32

H (inches) 2 5/16

L1 (inches) 7 31/32

L2 (inches) 6 13/32

L3 (inches) 6

Q (inches) 2 1/2

W (inches) 2 3/4

### Packaging

T&B Order Multiple 10

Package in Units 10

T&B Sold in UOM Each

T&B Weight Per UOM 82.75 lbs. per 100

### Application Support

T&B Sales Drawings wsd-ac04834

Rigid Non-metallic Conduit Bodies Available on Website

Specifications & Applications Available on Website

### Certifications

RoHS Compliance Yes

### Certifications



File Nbr:

E11461

For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com

