





AC-MC-FLEX FITTINGS

MALLEABLE IRON STRAIGHT CABLE CONNECTORS

[Download Specification Sheet](https://www.sepco-usa.com/wp-content/uploads/2017/03/page_145.pdf)  [Print](#) 

(https://www.sepco-usa.com/wp-content/uploads/2017/03/page_145.pdf)



C29T

Trade Size	1"
Ko Size	1"
Dim A	1.10
Dim B	0.57
Dim C	2.15
Unit Pack	10
Master Pack	100
Lbs. / 100 Pcs.	26
UPC	32903
	483I, 410-I,
	1710, IML-
	42-3, 24-
Competitor	100T, 3304,
Part Number	3304, XC-
	903, 256-I,
	153Mi

APPLICATION FEATURES

Used with Male hub
locknut to threads –
terminate NPS
steel or Provided
aluminum with steel
flexible locknut
metal
conduit to
enclosure.

STANDARD STANDARD

MATERIALS FINISH

Malleable Zinc Plated
Iron/Steel
Locknuts

UL LISTED

E198258

