



P1261ORB: 1 - Light Pendant



Dimensions:

Diameter: 5 3/4" **Wire:** 180" (color/Black)
Height: 10" **Connection:** Mounted To Box
Weight: 3.37 lbs.

Bulbs:

1 - Medium A19 100w Max. 120v - Not included

Features:

Material List:

1 Bobeche - Steel - Oil Rubbed Bronze
1 Body - Steel / Glass - Oil Rubbed Bronze
1 6" Stem - Steel - Oil Rubbed Bronze
3 12" Stem - Steel - Oil Rubbed Bronze

Safety Listing:

Safety Listed for Dry Locations / IC

Instruction Sheets:

English (P1261)
Trilingual (English, Spanish, and French) (P1261ORB)

Collection: Urban Renewal

Can be used with regular A19 or an Antique style Light bulb 60 Watt A19 as shown.

UPC #:014817483437

Finish: Oil Rubbed Bronze (ORB)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Clear Seeded	1				8	5 3/4				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	3/4			5 1/4		

Shipping Information:

Feiss reserves the right to revise the design of components of any product due to parts availability or change in safety listing standards without assuming any obligation or liability to modify any products previously manufactured and without notice. This literature depicts a product design that is the sole and exclusive property of Feiss . In compliance with U.S copyright and patent requirements, notification is hereby presented in this form that this literature, or the product it depicts, is not to be copied, altered or used in any manner without the express written consent of, or contrary to the best interests of Feiss 1/2 A Generation Brands Company.

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	P1261ORB	1	014817483437	14.5	9.75	8.5	0.695	3.85	150	Yes
Master Pack	P1261ORB	2	10014817483434	18.5	15.5	9.75	1.618	9.2	150	Yes
NJ Pallet		84		48	40	69	76.667	386.4		No
NV Pallet		84		48	40	69	76.667	386.4		No