

# Direct-Wire Fluorescent 21W WH

10043WH (White)

Project Name: \_\_\_\_\_

Location: \_\_\_\_\_

Type: \_\_\_\_\_

Qty: \_\_\_\_\_

Comments: \_\_\_\_\_

## Ordering Information

|            |         |
|------------|---------|
| Product ID | 10043WH |
| Finish     | White   |

## Dimensions

|        |          |
|--------|----------|
| Weight | 2.00 LBS |
|--------|----------|

## Photometrics

|                       |       |
|-----------------------|-------|
| Kelvin Temperature    | 2700K |
| Color Rendering Index | 85    |

## Specifications

|                   |         |
|-------------------|---------|
| Material          | Steel   |
| Glass Description | Frosted |

## Electrical

|                         |             |
|-------------------------|-------------|
| Voltage                 | 120V        |
| Input Voltage           | Single(120) |
| Operating Voltage Range | 108-132     |

## Qualifications

|              |  |
|--------------|--|
| Safety Rated | Dry  |
| Warranty     | <a href="http://www.kichler.com/warranty">www.kichler.com/warranty</a> |

## Installation

|             |     |
|-------------|-----|
| Direct Wire | Yes |
|-------------|-----|

## Primary Lamping

|                       |             |
|-----------------------|-------------|
| Light Source          | Fluorescent |
| Lamp Included         | Included    |
| Number of Lights/LEDs | 1           |
| Lamp Type             | CFL         |



## Dimensions

|        |        |
|--------|--------|
| Height | 1.00"  |
| Length | 34.50" |
| Width  | 3.50"  |

### Notes:

1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.

2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.