

Carlon®

Rigid Non-Metallic Conduit Fittings & Accessories T&B Catalog Number:



E977JC
03448106946
Active

UPC Number:
Status:
Description:

Conduit Clamp, Size 2 Inches, Length 4.18 Inches, Width 0.76 Inches, Height 2.49 Inches, Material PVC, Color Gray, Pack of 25

Features

Non-metallic clamps offer the same chemical resistance as Carlon non-metallic conduits for a complete, corrosion resistant system.

Application

UV inhibited for use in direct sunlight.

General

Trade Size (inches) 2
Material Non-Metallic

Dimension Information

A (mm)	64.5
B (mm)	89.9
E (mm)	4
C (mm)	106.1
D (mm)	19.3
F (mm)	26.6
A (inches)	2.54
B (inches)	3.54
C (inches)	4.18
D (inches)	0.76
E (inches)	0.16
F (inches)	1.05
G (inches)	2.29
H (inches)	2.49
H (mm)	63.2
J (inches)	0.315
Size (mm)	53

Packaging

T&B Order Multiple	25
Package in Units	25
T&B Sold in UOM	Each
T&B Weight Per UOM	6.25 lbs. per 100


Application Support

T&B Sales Drawings	wsd-ac03405
Specifications & Applications	Available on Website

Notes

To be used in accordance with conduit spacing requirements per NEC, Section 352.30

Certifications



RoHS Compliance

Yes

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com