

Liquidtight Flexible Non-Metallic Conduit & Fittings

T&B Catalog Number:

LT43E-NEW

UPC Number:

03448108788

Status:

Active

Description:

3/4 Inch Liquidtight Non-metallic Fitting

Features

Non-conductive and non-corrosive.

Resistant to oil, acid, ozone and alkaline.

Easy to install.

Approved for indoor and outdoor locations

UL listed for wet locations

Nitrile rubber 'O' ring for a liquidtight termination.

Temperatures up to 225 degree F (107 degree C)

Meets UL standard 514B.

Application

For use with Carflex conduit and Carflex X-Flex conduit.

General

Trade Size (inches)

3/4

Material

Non-Metallic

Dimension Information

Size (inches)

3/4

Degree of Bend

Straight

A (inches)

0.56

B (inches)

0.91

C (inches)

1.88

D (inches)

1.61

E (inches)

1.4

Packaging

T&B Order Multiple

50

Package in Units

50

T&B Sold in UOM

Each

T&B Weight Per UOM

12.5 lbs. per 100

Application Support

T&B Sales Drawings

wsd-ac04398

Product Overview-Carflex Liquidtight Flex-Available on Website

ible Tubing

Certifications

RoHS Compliance

Yes


Certifications



File Nbr:

E 32447

For further technical assistance, please contact us...



8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com