



Item #: F753-BNW	UPC Code: 706411042607
Product Family Name: Java	Finish: Brushed Nickel Wet
Category: Exterior Fan	Category Type: Ceiling Fan
Certification E75795	
Patents	
Notes:	

Image File Name:
F753-BNW_0.jpg



MEASUREMENTS

Blade Finish:	Reversible Blades:	
	No	
Blade Material:	Slope:	
ABS Construction	No	
Blade Sweep:	No. of Blades:	Blade Pitch:
54	3	14 DEGREES
Downrod 1:	Downrod 2:	Hanging Weight:
3.5	6	16.18
Ceiling to Lowest Point: (Dim A)	Downrod 1 Outside Dia:	Downrod 2 Outside Dia:
12.50	.75	.75
Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:
11.50	80	153 X 18mm

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	70		105		150
Amps:	0.28		0.37		0.42
Watts:	14.500		27.000		47.000
CFM:	2642.53		4100.00		5480.00
CFM/Watts:	182.24		151.85		116.60



FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
No	Yes	Yes
	Included Remote Control:	Included Wall Control:
	RCS213	
	Compatible Remote Control[s]:	Compatible Wall Control[s]:
		WCS213

LAMPING

No. of Bulbs:	Light Type:			
	N/A			
Max Bulb Wattage:	Socket:			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight
No	No			
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				

GLASS

Description:	Material:	
Part No.:	Quantity:	
Width:	Height:	Length:



SHIPPING

Carton Width:	Carton Height:	Carton Length:	
10.000	10.500	28.250	
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:	
18.458	1.717	Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack:
			1



Wet Location

Yes



Title 17

Yes



UL Listed

Yes