

FEATURES & SPECIFICATIONS

INTENDED USE

Combination emergency lighting unit and exit. Suitable for illuminating the path of egress and for marking the means of egress in accordance with Life Safety Code NFPA 101.

CONSTRUCTION

Injection-molded, flame-retardant, high-impact, thermoplastic housing with snap-fit design components for easy installation. Universal J-box pattern. Universal chevrons are easily removed for directional indication. Fully assembled single face with extra faceplate for easy field-conversion to double face. Track and swivel arrangement permits full range of lamp adjustment.

Letters 6" high with 3/4" stroke, with 100 ft viewing distance rating, based on UL924 standards.

OPTICS

The typical life of the LED lamp is 10 years. Two 1W LED lamps for emergency light.

ELECTRICAL

Dual-voltage input 120V or 277V AC; 9.6V output. Emergency combo provided with test switch, status indicator and rechargeable battery. Maintenance-free nickel-cadmium battery provides 90 minutes of emergency power. High output (HO) option provides up to 3W of LED remote capacity.

INSTALLATION

Top, back or end mounting capability (canopy included).

LISTINGS

UL Listed. Meets UL 924, NFPA 101, NFPA 70-NEC and OSHA illumination standards. Indoor damp location 32°F to 122°F (0°C to 50°C) listed standard.

WARRANTY

2-year limited warranty (Battery is prorated.). Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

All life safety equipment, including emergency lighting for path of egress must be maintained, serviced, and tested in accordance with all National Fire Protection Association (NFPA) and local codes. Failure to perform the required maintenance, service, or testing could jeopardize the safety of occupants and will void all warranties.

NOTE: Actual performance may differ as a result of end-user environment and application.

All values are design or typical values, measured under laboratory conditions at 25°C.


Specifications subject to change without notice.

LED Exit/Unit Combos



ECR LED

LED Combo



All dimensions are inches (centimeters).
Shipping weight: 3.6 lbs. (1.6 kgs.).

ORDERING INFORMATION

Catalog Number	UPC	Description	Supply Voltage	Input Wattage	Pallet Qty.	Standard Carton Qty.
ECR LED M6	784231874516	Red	120/277	3.8	108	6
ECG LED M6	784231874592	Green	120/277	3.2	108	6
ECR LED HO M6	784231874561	Red, high output	120/277	3.8	108	6
ECG LED HO M6	784231874615	Green, high output	120/277	3.2	108	6

Accessories: Order as separate catalog number.

ELA WG3	Wireguard (back mount only) ¹
ELA LED M12	Single remote lamp ^{2,3}
ELA LED T M12	Double remote lamp ^{2,3}
ELA LED WP M12	Single, weather-proof remote lamp ^{2,3}
ELA LED T WP M12	Double, weather-proof remote lamp ^{2,3}

Notes

- 1 See spec sheet [ELA-WG](#).
- 2 See spec sheet [LED-Remote Lamps](#).
- 3 Only available with HO option.