



Powering Business Worldwide

pe.eaton.com

Series G, EG-frame Molded Case Circuit Breaker

EGH3020FFB

UPC: 786685381831

Dimensions: 2.99 IN * 3 IN * 5.5 IN (L * W * H)

Notes: No Data

Warranty: Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Complete breaker
- **Frame Size:** EG-frame
- **Series:** Series G
- **Terminals:** Bolt-on
- **Trip Type:** Fixed thermal, fixed magnetic
- **Amperage Rating:** 20A
- **Interrupt Rating:** 100 kAIC at 240V, 70 kAIC at 415V, 65 kAIC at 480V, 35 kAIC at 600Y/347V
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 600Y/347V

Supporting documents:

- [Eatons Volume 4-Circuit Protection Catalog](#)
- [Eaton Specification Sheet - EGH3020FFB Specification](#)

Certifications:

- IEC Rated
- UL Listed
- CSA Certified

Product compliance:

- CE Marked



