



# S8995

8A19/LED/3000K /450L /120V /D  
 8 watt; A19 LED; 3000K; Medium base; 120 volts

### Features

- Solid State LED lighting
- A-shaped replacement lamp
- Long life
- Dimmable

### Top 3 Recommended Dimmers

- Lutron® MACL-153 Maestro®
- Lutron® CT-603PGH Incandescent
- Legrand® ADTP703TU (TRU Universal)



S8995

This item has been discontinued.  
 Suggested replacement:

- [S9107](#)

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S8995	045923089954	120	8	40W	A19	Medium	E26

  

Lamp Code	Dimmable/Non-Dimmable	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color
8A19/LED/3000K /450L /120V /D	Dimmable	4-1/4"	2.38"	450	25000	3000	Warm White

  

CRI	Pack	Package Type	RoHS Compliant	UL or ETL Listed	Warranty	Status	Suggested Substitute
80	12	CD/1	Yes	Yes	<a href="#">3 Year Limited</a>	Discontinued	<a href="#">S9107</a>



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

