

PLENUM CONTROL CABLE

**Multi-Conductor
Shielded, Plenum
NEC Type CMP and/or CL3P**



CONSTRUCTION	
Conductor	- Stranded or solid bare copper per ASTM B-3, B-8 and B-286
Insulation	- Premium-grade, color-coded Flexguard®VC
Shield	- Overall Flexfoil®polyester supported aluminum foil - Stranded tinned copper drain wire
Jacket	- Premium-grade natural Flexguard®VC - Sequential footage markings to facilitate installation - Temperature range: 0°C to +75°C - Ripcord available upon request

Applications:

- Power limited control circuits
- Wiring of the following systems:
- Intercom
- Security
- Audio
- Background music
- Suggested Voltage Rating: 300 Volts

Standards:

- NEC Article 725 Type CL3P (UL: 75°C, 150V)
- NEC Article 800 Type CMP (UL: 75°C, 300V)
- Designed to meet NFPA 262 Flame Test

COLOR CODE CHART	
Cond. #	Color
1	Black
2	Red
3	White
4	Green
5	Brown
6	Blue
7	Orange
8	Yellow
9	Purple
10	Gray
11	Pink
12	Tan

Part #	AWG	Conductors	Insulation Thickness	Jacket Thickness	Nom. O.D.	Lbs./M'
G111802	18	2	.008"	.015"	.164"	20.5
G111803	18	3	.008"	.015"	.153"	27.5
G111804	18	4	.008"	.015"	.169"	34
G111806	18	6	.010"	.015"	.204"	48.1
G111808	18	8	.010"	.015"	.264"	61
G111810	18	10	.006"	.015"	.264"	75.3
G111812	18	12	.006"	.015"	.273"	86.1
G111602	16	2	.006"	.015"	.154"	28.5
G111603	16	3	.006"	.015"	.164"	36
G111604	16	4	.006"	.015"	.181"	49.6

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.