

**Rigid Non-Metallic Conduit-Schedule 40 Elbows**  
**T&B Catalog Number:**

UA7AF-CAR

**UPC Number:**

03448113005

**Status:**

Active

**Description:**

Schedule 40 Elbow, Size 1 Inch, Bend Radius Standard, Bend Angle 45 Degrees, Material PVC, Pack of 15

**General**

|          |              |
|----------|--------------|
| Material | Non-Metallic |
| Color    | Gray         |

**Dimension Information**

|                |    |
|----------------|----|
| Size (inches)  | 1  |
| Degree of Bend | 45 |

**Packaging**

|                    |                    |
|--------------------|--------------------|
| T&B Order Multiple | 15                 |
| Package in Units   | 15                 |
| T&B Sold in UOM    | Each               |
| T&B Weight Per UOM | 26.88 lbs. per 100 |

**Application Support**

|                                                     |                      |
|-----------------------------------------------------|----------------------|
| Product Overview-PVC Conduit Repair System          | Available on Website |
| Product Overview-Schedule 40 & 80 Elbows & Fittings | Available on Website |
| Technical Specifications                            | Available on Website |

**Certifications**



File Nbr:  
E 323335

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com

