



GE
Lighting

66350 - F32T8/SPP50/ECO-LFL PULP TRY PK NEW COLOR TEMP

F32T8/SPP50/ECO

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	2.95 mg
Mercury-Picogram per mean lm hr	36.1
Rated Life Instant Start-Hrs	21000 h @ 3 h 30000 h @ 12 h
Rated Life Rapid Start - Hrs	30000 h @ 3 h 36000 h @ 12 h
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Sodalime glass
Rated Life Hours-nominal	30000 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T8

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	2725 lm
Nominal Initial Lumen per Watt	91
Initial Lumens-nominal	2900 lm
Color Rendering Index-CRI	80
Color Temperature	5000 K

PRODUCT INFORMATION

Product Code	66350
Description	F32T8/SPP50/ECO
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168663502
Standard Package GTIN	10043168663509
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168663502

DIMENSIONS

Diameter	1.0 in
Nominal Length	48.0 in

ELECTRICAL CHARACTERISTICS

Rated power (Watts)	32 W
---------------------	------