



61060-782: One Light Mini-Pendant



Collection: Sussex

Sussex One Light Mini Pendant in Heirloom Bronze Finish with Satin Etched Glass Shade. Three 12 Inch Stems, Chain and Canopy Included

The look that satisfies discerning taste. Part of our Sussex collection where past elements of design keep pace with today. Includes three interconnecting 12" stems, 12" of chain, and canopy.

For Additional Stems, Order 9199-782; Design #: D20066

UPC #: 785652610608

Finish: Heirloom Bronze (782)

Dimensions:

Diameter: 7 1/2"

Height: 7 1/2"

Overall Height: 58 1/2"

Wire: 120" (color/Brown)

Chain: 12"

Mounting Proc.: Cap Nuts

Connection: Mounted To Box

Bulbs:

- 1 - Medium A19 100w Max. 120v - Not included
- 1 - LED Medium A19 8w Max. 120v - Not included
- 1 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- A decorative canopy is included
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

- 1 Body - Steel - Heirloom Bronze
- 1 Chain - Steel - Heirloom Bronze
- 3 12" Stem - Steel - Heirloom Bronze

Safety Listing:

- Safety Listed for Dry Locations
- Safety Listed for Dry Locations

Instruction Sheets:

- English (HC-387)
- French (F-005)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Satin Etched	1				4 1/8	7 1/2	1 11/16			

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	3			6 5/8		

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	61060-782	1	785652610608	16	9.25	7.25	0.621	4.85	125	Yes
NJ Pallet		165		48	40	76	84.444	800.25		No
NV Pallet		165		48	40	76	84.444	800.25		No