



T&B[®]

Liquidtight Flexible Cord & Cable Fittings T&B Catalog Number:

UPC Number: 2536
78621002536
Status: Active
Description:

Liquidtight Strain Relief Cord Connector, 3/4 Inch, Straight, Cord Range 0.750 to 0.875 Inch, Malleable Iron

Application

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).
Meets Coast Guard CG293

General

Material Malleable Iron

Dimension Information

Hub Size (inches)	3/4
Dimension A (inches)	1 11/16
Dimension B (inches)	1 15/16
Dimension C (inches)	5/8
Cord Range (inches)	.750-.875
Throat Diameter (inches)	3/4

Specifications

3dmodel	Available on Website
Temperature Rating	105 C

Packaging

T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	24.5 lbs. per 100

Application Support

Product Overview	Available on Website
Specifications	Available on Website
Portable Cord Selection Table	Available on Website

Notes

Remove sufficient outer covering of cable to permit conductors to pass thru connector body.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com