



Hoffman

Screw-Cover, Type 3R

Catalog Number: A24R248NK
US List Price (USD): \$246.10

Bulletin Number:

- A90S3

Material:

- Steel



Model Code:

- 13521

Ship Wt. Std. Pkg. (lbs):

- 47.0

Interchangeable:

- False

IP Rating:

- IP32

Industry Standards:

UL 50, 50E Listed; Type 3R; File No. E27525 cUL Listed per CSA C22.2 No 94; Type 3R; File No. E27525 NEMA/EEMAC Type 3R IEC 60529, IP32

Description

Use this enclosure with or without knockouts in outdoor applications as a wiring or junction box.

Description:

- Drip shield top and seam-free sides, front and back
- Slip-on removable cover fastened with plated steel screws along bottom edge
- Handles on larger sizes (see table)
- Embossed mounting holes on back of enclosure
- Knockouts in bottom of 16 and 14 gauge enclosures
- Provision for padlocking
- No gasketing
- See also Accessories. Industrial Corrosion Inhibitors Electric Heater Grounding Device Mounting Bracket Kit Touch-Up Paint
- ANSI 61 gray polyester powder paint finish inside and out over pretreated surfaces.
- 16, 14 or 12 gauge galvanized steel
- Use this enclosure with or without knockouts in outdoor applications as a wiring or junction box.

Technical Data

Screw-Cover, Type 3R

Catalog Number	A24R248NK
A in.	24
B in.	24
C in.	8
D in.	12.19
Mounting H in.	13.00
Knockout Pattern	—
Body Style	C
Mounting J in.	1.12

Certifications



EU Certification



UL Certification

Documents



2D DXF CAD



3D STEP CAD



Spec Sheet



Dimension Drawing

No accessories available.