



Item #: **F659-PBL**
 Product Family Name: **Classica**
 Category: **Interior Fan**
 Certification: **4000048**
 Patents: © 2009 Minka Lighting, Inc.
 Notes:

UPC Code: **706411038648**
 Finish: **Provencal Blanc**
 Category Type: **Ceiling Fan**

Image File Name:
 F659-PBL_0.jpg



MEASUREMENTS

Blade Finish:	Reversible Blades:		
	No		
Blade Material:	Slope:		
Plywood Construction	No		
Blade Sweep:	No. of Blades:	Blade Pitch:	Hanging Weight:
54	5	14 degrees	23.15
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:
3.5	.75	6	.75
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:
14.00	11.75	80	172 x 16mm

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	64		120		188
Amps:	0.22		0.39		0.60
Watts:	9.800		29.800		71.600
CFM:	2226.00		4037.00		6313.00
CFM/Watts	227.14		135.47		88.17



FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
Yes	Yes	Yes
	Included Remote Control:	Included Wall Control:
	Compatible Remote Control[s]:	Compatible Wall Control[s]:
	RCS213, RCS223	WC105, WC106, WCS213, WCS223

LAMPING

No. of Bulbs:	Light Type:			
	N/A			
Max Bulb Wattage:	Socket:			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight
No	No			
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				

GLASS

Description:	Material:	
Part No.:	Quantity:	
Width:	Height:	Length:



SHIPPING

Carton Width:	Carton Height:	Carton Length:	
15.000	10.630	20.750	
Carton Weight:	Carton Cubit Feet:	Small Package Shippable:	
26.400	1.915	Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack:
			1



ENERGY STAR
 Yes



Title 17
 Yes



ETL Intertek
 Yes