

## Rigid Non-Metallic Conduit Bodies & Covers

### T&B Catalog Number:

E985F-CAR

### UPC Number:

03448113244

### Status:

Active

### Description:

Type LR Conduit Body, Volume 12 Cubic Inches, Size 1 Inch, Length 6-9/32 Inches, Width 2-1/32 Inches, Material PVC, Color Gray, For use with Schedule 40 and 80 Conduit, Pack of 10

### Features

Textured lids

Foam-in-place gasket

### Application

For use with Rigid Conduit

### General

Trade Size (inches)

1

Material

Non-Metallic

Volume (cu.in.)

12

Conduit Body Shape

LR

### Dimension Information

C (inches)

29/32

H (inches)

1 25/32

L1 (inches)

6 9/32

L2 (inches)

5 9/32

L3 (inches)

4 25/32

Q (inches)

1 3/4

W (inches)

2 1/32

### Packaging

T&B Order Multiple

10

Package in Units

10

T&B Sold in UOM

Each

T&B Weight Per UOM

34.5 lbs. per 100

### Application Support

T&B Sales Drawings

wsd-ac04179

Rigid Non-metallic Conduit Bodies

Available on Website

Specifications & Applications

Available on Website

### Certifications



File Nbr:

E11461

For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com

